

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332897

Luminaire Tested: **S124RDIP-S575D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332897
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D365U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3750.4 lumens
Efficiency: N/A
Efficacy: 136.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	62	60	56
2	93	86	80	75	87	81	76	71	72	68	65	64	61	58	56	54	52	48
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30	28
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	31	28	25	22
9	54	41	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7796	7796	7796	7796
5°	9043	7819	6912	7819
10°	10698	7785	6169	7785
15°	12357	7713	5300	7713
20°	13759	7614	4793	7614
25°	14203	7517	4450	7517
30°	12433	7399	4243	7399
35°	9678	7224	4119	7224
40°	7258	7024	4051	7024
45°	5730	6703	4015	6703
50°	4838	6332	3900	6332
55°	4217	5925	3690	5925
60°	3794	5503	3266	5503
65°	3345	5047	2810	5047
70°	3012	4574	2535	4574
75°	2523	4055	2162	4055
80°	2134	3454	2027	3454
85°	1806	2705	1806	2705



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.6	2.5
10°-20°	282.2	7.5
20°-30°	441.5	11.8
30°-40°	490.8	13.1
40°-50°	435.4	11.6
50°-60°	339.3	9.0
60°-70°	222.1	5.9
70°-80°	109.2	2.9
80°-90°	27.9	0.7
90°-100°	129.9	3.5
100°-110°	270.4	7.2
110°-120°	242.2	6.5
120°-130°	203.7	5.4
130°-140°	169.9	4.5
140°-150°	129.8	3.5
150°-160°	91.2	2.4
160°-170°	53.7	1.4
170°-180°	17.5	0.5
0°-30°	817.3	21.8
0°-40°	1308.0	34.9
0°-60°	2082.7	55.5
0°-90°	2442.1	65.1
90°-120°	642.6	17.1
90°-150°	1146.0	30.6
90°-180°	1308.0	34.9
0°-180°	3750.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	966	966	966	966	966	
5°	1116	965	853	965	1116	113
15°	1478	923	634	923	1478	420
25°	1594	844	500	844	1594	707
35°	982	733	418	733	982	616
45°	502	587	352	587	502	397
55°	300	421	262	421	300	273
65°	175	264	147	264	175	176
75°	81	130	69	130	81	89
85°	20	29	20	29	20	22
90°	7	0	7	0	7	7
95°	86	12	86	12	86	134
105°	497	41	497	41	497	492
115°	478	73	478	73	478	474
125°	381	101	381	101	381	346
135°	341	120	341	120	341	263
145°	278	139	278	139	278	176
155°	233	158	233	158	233	109
165°	203	172	203	172	203	58
175°	183	180	183	180	183	18
180°	180	180	180	180	180	



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1018.6	1021.4	1018.6	1018.3	1015.2	1014.3	1013.0	1009.0	1001.5	997.1	998.1
5°	1115.9	1125.6	1120.2	1119.4	1110.8	1102.3	1096.8	1084.4	1071.1	1062.2	1054.8
7.5°	1228.4	1234.0	1230.6	1225.1	1211.3	1203.4	1190.8	1174.4	1150.7	1132.5	1116.0
10°	1305.0	1309.6	1308.1	1298.0	1287.9	1267.2	1255.6	1232.6	1202.6	1178.9	1156.7
12.5°	1380.3	1385.3	1371.6	1372.1	1352.9	1336.6	1318.1	1289.3	1254.6	1224.0	1196.3
15°	1478.5	1472.3	1472.3	1464.5	1443.1	1420.5	1401.5	1371.1	1327.5	1291.0	1252.5
17.5°	1555.4	1557.6	1554.4	1536.0	1519.2	1495.9	1460.9	1425.5	1385.0	1335.9	1296.6
20°	1601.5	1601.5	1598.0	1585.5	1563.7	1538.8	1501.1	1462.6	1411.2	1361.8	1317.4
22.5°	1620.1	1621.4	1617.3	1607.0	1587.4	1563.1	1531.0	1491.8	1438.9	1383.3	1328.3
25°	1594.5	1601.8	1602.6	1599.9	1594.1	1579.3	1551.7	1511.6	1464.1	1403.8	1344.7
27.5°	1463.9	1473.2	1481.4	1494.8	1512.7	1522.1	1523.3	1502.9	1461.5	1403.5	1344.0
30°	1333.8	1341.5	1366.8	1399.9	1425.6	1448.9	1469.2	1474.6	1451.3	1399.1	1336.5
32.5°	1189.3	1199.9	1225.2	1260.8	1303.6	1343.1	1388.6	1411.7	1411.1	1379.8	1321.9
35°	982.0	989.8	1013.2	1050.5	1101.9	1160.6	1232.6	1288.6	1326.8	1324.0	1288.6
37.5°	792.0	800.8	824.4	855.4	905.2	977.9	1047.6	1124.8	1195.3	1234.9	1223.0
40°	688.7	689.1	712.0	743.9	790.6	854.0	929.9	1015.5	1094.1	1158.3	1170.7
42.5°	607.1	607.2	622.4	656.8	690.4	750.1	822.5	907.5	999.5	1073.6	1106.6
45°	501.9	505.4	517.9	538.5	564.9	615.5	673.5	752.5	855.6	943.5	998.4
47.5°	425.0	430.2	438.1	454.9	476.0	509.7	557.6	628.6	712.5	809.2	887.3
50°	385.2	386.0	396.1	405.4	423.7	450.6	492.6	551.7	628.8	721.7	808.5
52.5°	351.0	350.8	356.9	368.7	383.6	404.5	438.4	492.3	560.6	643.9	733.5
55°	299.6	301.5	306.2	315.5	326.8	341.6	368.5	408.9	462.6	533.8	615.1
57.5°	260.5	261.5	265.2	269.2	279.5	290.3	310.4	338.5	383.8	442.1	517.9
60°	235.0	235.4	236.6	242.4	250.6	260.7	274.3	298.0	336.2	389.5	449.4
62.5°	210.1	210.8	212.6	216.9	223.2	230.2	244.4	263.5	295.1	340.6	394.6
65°	175.1	175.5	178.2	179.8	184.8	191.0	201.5	214.4	236.2	274.3	315.2
67.5°	146.3	146.3	146.4	148.6	152.1	156.2	162.5	172.8	189.2	212.6	248.6
70°	127.6	127.6	128.4	129.6	131.5	135.0	138.5	146.3	158.4	177.4	205.0
72.5°	110.2	110.5	111.3	111.5	112.5	115.4	118.0	122.9	131.9	146.3	168.6
75°	80.9	82.1	84.0	85.6	87.5	87.2	89.9	93.0	95.7	104.3	117.1
77.5°	60.2	59.6	59.8	61.2	61.4	61.8	63.7	66.1	68.2	72.2	76.8
80°	45.9	45.9	47.1	47.5	47.1	47.5	49.4	50.6	51.4	52.9	57.2
82.5°	34.7	35.3	34.9	35.3	35.6	36.0	37.6	37.8	38.6	39.2	41.0
85°	19.5	19.8	20.2	19.5	19.5	19.5	20.2	20.6	21.4	21.0	21.8
87.5°	8.3	8.0	8.4	8.3	8.6	8.3	8.5	9.1	8.4	8.7	8.6
90°	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4	6.0	6.4	5.7
92.5°	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4	93.4	112.1	98.1
95°	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9	296.2	288.0	217.4
97.5°	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9	372.1	303.4	203.4
100°	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2	374.6	284.2	184.5
102.5°	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3	353.4	260.1	171.8
105°	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8	314.9	231.8	160.8
107.5°	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5	283.8	216.0	158.8
110°	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2	268.3	210.6	159.4



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3	259.5	208.1	161.1
115°	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5	251.3	206.8	164.3
117.5°	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7	247.6	206.4	167.8
120°	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7	245.6	206.4	170.4
122.5°	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3	243.4	206.1	172.9
125°	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6	239.6	205.7	176.7
127.5°	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5	234.6	204.9	179.8
130°	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8	231.5	204.6	182.0
132.5°	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9	228.7	204.4	184.0
135°	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7	224.4	203.9	187.0
137.5°	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3	220.8	203.9	188.7
140°	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0	218.8	203.6	190.1
142.5°	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1	217.1	203.6	191.3
145°	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5	214.2	202.9	191.9
147.5°	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9	211.6	201.6	192.3
150°	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1	209.6	200.7	192.3
152.5°	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0	207.3	199.3	191.7
155°	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3	203.9	197.2	190.9
157.5°	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3	200.5	195.0	189.9
160°	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2	197.9	193.3	189.1
162.5°	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1	195.7	191.6	188.2
165°	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7	191.9	189.1	186.6
167.5°	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6	188.5	186.5	184.9
170°	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0	186.3	184.8	183.8
172.5°	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8	184.3	183.1	182.7
175°	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7	182.0	181.3	181.3
177.5°	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7	180.5	180.2	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	995.0	990.6	988.4	983.4	977.5	974.4	971.6	967.6	962.3	956.7	952.6
5°	1045.5	1036.1	1024.4	1010.4	998.0	985.9	975.4	964.9	952.9	940.4	928.0
7.5°	1097.3	1078.9	1059.1	1036.1	1013.8	993.5	974.8	956.9	936.7	918.5	902.0
10°	1133.4	1108.5	1080.9	1051.7	1022.5	997.2	972.3	949.7	924.8	902.7	884.0
12.5°	1162.7	1133.4	1100.2	1063.8	1028.7	998.1	969.5	940.1	911.8	887.7	862.8
15°	1211.2	1171.1	1126.4	1082.8	1037.3	995.7	957.1	922.9	890.6	856.8	833.0
17.5°	1244.6	1197.0	1142.7	1090.3	1036.5	987.4	943.0	902.2	864.9	830.4	802.1
20°	1264.5	1212.0	1151.7	1092.1	1031.8	979.3	931.5	886.3	847.8	810.5	781.3
22.5°	1275.7	1217.6	1151.7	1089.3	1026.9	970.0	917.5	870.5	828.5	791.2	758.9
25°	1279.3	1217.0	1149.7	1078.1	1009.7	949.4	894.9	843.9	797.2	759.9	725.6
27.5°	1274.3	1201.0	1132.1	1058.6	988.0	924.4	867.2	813.6	766.9	726.8	691.7
30°	1266.8	1188.3	1114.3	1038.1	966.5	905.4	845.1	793.7	745.1	703.5	668.1
32.5°	1250.7	1172.7	1093.2	1015.0	942.5	879.6	822.4	770.7	723.0	680.4	642.8
35°	1218.6	1139.6	1053.2	973.1	901.9	836.5	782.8	733.0	687.5	642.0	602.3
37.5°	1176.3	1095.7	1009.7	922.0	850.7	789.0	739.7	693.0	648.5	607.0	563.0
40°	1136.5	1063.0	974.3	887.1	814.0	754.4	708.9	666.5	621.8	580.5	536.5
42.5°	1088.3	1025.6	936.0	848.5	776.3	718.9	676.5	635.1	594.4	554.4	508.5
45°	1007.7	960.3	876.2	792.2	719.4	662.6	623.7	587.1	551.3	513.2	470.0
47.5°	915.4	883.3	810.8	724.7	657.4	606.3	568.7	538.8	508.5	470.4	432.5
50°	851.3	830.7	760.7	682.1	617.9	570.8	532.3	504.2	479.0	442.4	408.5
52.5°	782.8	771.9	712.7	637.5	575.5	529.4	496.5	471.3	445.7	415.3	383.6
55°	678.6	684.4	634.2	569.2	510.9	472.0	442.0	421.0	399.2	373.5	349.0
57.5°	571.9	593.3	559.6	502.5	447.8	411.9	389.3	371.6	353.4	332.0	311.1
60°	508.1	526.0	507.0	456.8	408.9	375.5	354.5	340.8	322.5	303.1	287.1
62.5°	445.9	465.0	453.7	413.2	368.8	340.0	321.5	308.8	295.2	278.2	261.6
65°	367.7	380.1	374.7	346.7	315.2	290.6	273.5	264.2	251.7	239.3	224.5
67.5°	281.6	305.7	302.5	287.6	260.4	241.2	230.0	221.8	210.4	201.2	191.1
70°	231.5	253.7	253.3	241.2	226.4	208.5	200.8	193.8	183.6	174.7	166.5
72.5°	189.5	209.8	212.8	203.6	193.5	179.9	172.4	167.6	157.8	151.7	145.0
75°	132.7	147.5	151.4	151.4	146.7	139.7	133.1	130.0	122.9	117.5	113.6
77.5°	87.0	96.3	102.4	103.8	104.5	102.2	96.7	94.5	89.2	87.2	83.5
80°	61.5	67.7	74.7	77.0	79.0	78.2	75.9	74.3	69.3	67.3	65.8
82.5°	42.5	45.9	51.7	56.8	56.3	58.3	56.3	55.0	51.2	50.5	48.9
85°	22.2	22.6	23.3	26.8	28.8	29.6	30.0	29.2	28.0	28.0	25.3
87.5°	8.5	8.1	8.3	8.3	8.6	9.8	10.5	10.7	9.9	9.1	8.3
90°	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0	5.9	9.2	13.5
95°	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7	12.7	16.3	20.9
97.5°	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9	20.9	24.0	28.2
100°	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9	26.9	29.3	33.6
102.5°	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5	33.1	35.3	39.2
105°	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4	42.4	44.2	48.4
107.5°	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1	51.8	53.6	58.1
110°	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6	58.3	60.1	64.3



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8	64.5	66.6	70.5
115°	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8	73.9	76.3	79.9
117.5°	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1	83.1	85.3	89.2
120°	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4	89.1	91.5	95.4
122.5°	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0	94.7	97.2	100.8
125°	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4	102.8	105.0	108.9
127.5°	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0	109.1	111.7	116.1
130°	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7	113.1	115.9	121.2
132.5°	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4	116.5	120.2	125.2
135°	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5	121.9	125.5	131.5
137.5°	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7	127.0	130.9	136.6
140°	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4	130.4	134.3	140.3
142.5°	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3	134.4	138.0	143.7
145°	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9	140.0	143.5	148.4
147.5°	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2	145.5	148.7	153.7
150°	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1	149.5	152.3	156.6
152.5°	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8	152.9	155.7	159.7
155°	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0	158.3	160.5	164.0
157.5°	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0	163.0	165.0	167.7
160°	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1	166.1	167.5	170.0
162.5°	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9	168.7	169.8	172.0
165°	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1	172.1	172.8	174.6
167.5°	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3	174.9	175.3	176.6
170°	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7	176.4	176.7	177.8
172.5°	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1	177.8	177.8	178.6
175°	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5	179.2	179.2	179.5
177.5°	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2	179.9	179.6	179.9
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	948.3	945.2	941.1	936.4	930.8	925.9	923.7	925.5	926.5	924.0	923.7
5°	919.4	909.7	901.9	890.2	880.9	873.1	867.6	865.3	866.1	859.9	858.3
7.5°	886.9	875.4	862.7	848.8	835.9	824.5	818.5	815.2	808.6	805.8	801.0
10°	866.1	850.5	838.1	821.7	807.0	793.3	786.7	781.3	774.7	771.5	764.9
12.5°	844.6	826.6	812.9	795.9	780.8	764.4	758.1	748.0	737.6	731.1	722.6
15°	814.3	792.6	775.8	755.6	737.7	719.0	702.3	683.6	676.6	661.8	653.3
17.5°	778.9	756.8	736.1	709.0	681.4	658.2	640.3	622.5	611.7	602.3	597.9
20°	755.6	735.4	706.6	675.1	644.3	618.6	604.2	592.6	580.9	574.3	569.6
22.5°	733.5	707.7	674.2	640.2	609.5	589.4	577.2	565.2	555.7	549.4	543.2
25°	696.5	662.6	627.2	588.3	567.3	549.8	536.5	526.8	521.0	512.8	509.7
27.5°	658.4	617.4	578.3	552.2	530.3	514.3	502.8	495.5	488.1	482.8	478.8
30°	629.1	587.5	552.5	527.6	505.4	492.2	482.8	474.3	468.5	464.2	461.1
32.5°	600.2	558.6	529.1	502.4	484.9	472.0	462.0	455.6	451.0	445.5	443.6
35°	558.3	521.4	495.7	471.6	453.7	442.0	434.2	427.6	423.7	422.2	421.0
37.5°	518.1	487.8	460.2	440.4	424.5	415.3	406.1	402.9	400.2	397.4	398.7
40°	492.6	464.2	439.7	418.7	405.8	395.7	390.2	386.4	384.0	384.0	384.0
42.5°	470.5	442.7	418.8	400.0	387.1	378.6	372.5	369.2	368.5	368.1	370.0
45°	436.2	410.5	386.4	370.8	359.9	351.3	347.8	345.1	345.1	346.7	347.1
47.5°	402.2	378.1	358.7	341.3	331.3	326.0	322.9	321.5	321.7	323.2	325.0
50°	381.3	357.6	338.5	322.9	313.6	308.5	305.8	305.0	305.8	305.8	308.5
52.5°	358.6	337.3	318.6	305.5	294.9	290.2	288.7	287.6	288.1	289.3	290.5
55°	325.3	306.2	288.3	275.9	268.1	265.0	261.5	261.9	261.1	261.9	261.9
57.5°	291.9	274.8	258.1	248.2	241.4	236.9	233.1	234.1	233.0	232.8	232.2
60°	270.4	251.7	238.5	229.6	221.8	217.9	214.4	215.2	214.0	213.2	211.7
62.5°	247.1	231.5	218.9	210.3	204.0	199.5	196.0	195.2	192.5	189.9	186.4
65°	213.2	200.4	189.1	180.9	175.1	171.6	168.9	166.5	160.7	154.5	151.4
67.5°	180.3	171.0	160.5	153.6	148.9	144.3	139.1	135.1	129.6	126.2	124.3
70°	159.1	150.2	141.2	134.6	129.6	125.3	119.4	116.7	112.8	111.3	109.3
72.5°	138.9	130.6	122.2	116.3	110.9	107.5	103.0	100.2	98.5	97.9	95.9
75°	108.2	101.6	95.3	89.9	85.6	83.3	81.3	79.4	78.6	75.1	73.1
77.5°	78.9	74.5	70.7	66.8	63.7	62.2	58.4	56.2	54.9	53.2	52.8
80°	61.5	58.4	54.5	52.1	47.9	46.3	44.7	44.4	44.0	43.6	43.2
82.5°	46.2	43.1	39.2	37.8	36.7	35.7	34.8	34.4	34.0	34.2	34.2
85°	23.3	21.8	21.8	21.4	21.0	20.6	20.2	20.2	19.8	20.2	19.8
87.5°	8.3	8.0	8.5	7.8	8.3	8.4	8.0	8.1	8.5	8.0	8.0
90°	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4	6.7	7.1	7.1
92.5°	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4	52.2	41.6	34.5
95°	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9	207.1	159.7	125.5
97.5°	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9	366.6	332.0	295.1
100°	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2	433.3	416.0	389.8
102.5°	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3	459.3	464.3	453.4
105°	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8	457.0	492.0	506.5
107.5°	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5	420.6	469.8	501.4
110°	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2	392.3	443.6	482.4



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3	367.4	415.8	454.7
115°	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5	338.9	380.3	414.2
117.5°	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7	322.7	355.2	384.0
120°	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7	315.6	343.9	369.0
122.5°	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3	311.1	336.8	358.8
125°	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6	303.9	328.3	347.8
127.5°	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5	295.5	319.9	338.3
130°	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8	288.8	312.8	331.5
132.5°	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9	281.1	304.6	323.3
135°	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7	269.7	291.2	308.9
137.5°	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3	258.7	276.9	292.8
140°	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0	251.6	267.5	282.4
142.5°	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1	245.7	259.3	272.2
145°	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5	237.5	248.1	258.0
147.5°	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9	230.4	238.9	246.7
150°	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1	226.2	233.3	239.6
152.5°	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0	222.0	228.5	233.7
155°	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3	215.9	221.2	225.5
157.5°	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3	210.0	214.5	217.9
160°	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2	206.0	209.9	212.8
162.5°	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1	202.4	205.4	208.0
165°	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7	196.9	199.3	201.1
167.5°	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6	192.2	194.2	195.2
170°	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0	189.1	190.5	191.6
172.5°	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8	186.5	187.4	188.2
175°	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7	183.1	183.8	183.8
177.5°	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7	181.0	181.0	181.3
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	921.8	922.4	920.3	919.6	920.3	922.4	921.8	923.7	924.0	926.5	925.5
5°	855.2	854.4	852.5	852.9	852.5	854.4	855.2	858.3	859.9	866.1	865.3
7.5°	798.2	795.2	796.1	792.9	796.1	795.2	798.2	801.0	805.8	808.6	815.2
10°	763.4	759.1	755.6	752.5	755.6	759.1	763.4	764.9	771.5	774.7	781.3
12.5°	715.8	712.1	707.3	708.3	707.3	712.1	715.8	722.6	731.1	737.6	748.0
15°	648.2	642.4	633.0	634.2	633.0	642.4	648.2	653.3	661.8	676.6	683.6
17.5°	591.0	591.1	586.8	587.8	586.8	591.1	591.0	597.9	602.3	611.7	622.5
20°	561.4	558.7	559.1	557.9	559.1	558.7	561.4	569.6	574.3	580.9	592.6
22.5°	540.9	537.6	534.8	532.4	534.8	537.6	540.9	543.2	549.4	555.7	565.2
25°	506.2	503.9	500.4	499.6	500.4	503.9	506.2	509.7	512.8	521.0	526.8
27.5°	475.7	475.2	473.8	472.0	473.8	475.2	475.7	478.8	482.8	488.1	495.5
30°	457.9	457.2	456.4	455.2	456.4	457.2	457.9	461.1	464.2	468.5	474.3
32.5°	442.1	441.6	440.8	440.9	440.8	441.6	442.1	443.6	445.5	451.0	455.6
35°	419.4	419.0	418.3	417.9	418.3	419.0	419.4	421.0	422.2	423.7	427.6
37.5°	398.3	399.3	398.8	398.7	398.8	399.3	398.3	398.7	397.4	400.2	402.9
40°	383.6	384.0	384.8	384.4	384.8	384.0	383.6	384.0	384.0	384.0	386.4
42.5°	371.5	371.6	372.7	371.3	372.7	371.6	371.5	370.0	368.1	368.5	369.2
45°	349.8	352.1	351.7	351.7	351.7	352.1	349.8	347.1	346.7	345.1	345.1
47.5°	326.0	328.1	328.6	328.5	328.6	328.1	326.0	325.0	323.2	321.7	321.5
50°	310.5	309.7	310.9	310.5	310.9	309.7	310.5	308.5	305.8	305.8	305.0
52.5°	291.5	291.7	291.6	291.2	291.6	291.7	291.5	290.5	289.3	288.1	287.6
55°	262.2	262.6	261.9	262.2	261.9	262.6	262.2	261.9	261.9	261.1	261.9
57.5°	230.5	228.6	229.4	228.5	229.4	228.6	230.5	232.2	232.8	233.0	234.1
60°	207.8	204.7	203.9	202.3	203.9	204.7	207.8	211.7	213.2	214.0	215.2
62.5°	182.2	180.1	177.4	178.7	177.4	180.1	182.2	186.4	189.9	192.5	195.2
65°	148.2	146.7	145.5	147.1	145.5	146.7	148.2	151.4	154.5	160.7	166.5
67.5°	122.7	121.9	121.9	121.1	121.9	121.9	122.7	124.3	126.2	129.6	135.1
70°	109.3	108.2	108.2	107.4	108.2	108.2	109.3	109.3	111.3	112.8	116.7
72.5°	95.6	94.5	94.8	94.3	94.8	94.5	95.6	95.9	97.9	98.5	100.2
75°	70.8	68.9	68.9	69.3	68.9	68.9	70.8	73.1	75.1	78.6	79.4
77.5°	52.8	52.4	53.0	52.3	53.0	52.4	52.8	52.8	53.2	54.9	56.2
80°	43.2	42.8	42.4	43.6	42.4	42.8	43.2	43.2	43.6	44.0	44.4
82.5°	33.5	33.5	33.4	34.9	33.4	33.5	33.5	34.2	34.2	34.0	34.4
85°	20.2	19.5	20.2	19.5	20.2	19.5	20.2	19.8	20.2	19.8	20.2
87.5°	8.6	8.4	8.0	8.3	8.0	8.4	8.6	8.0	8.0	8.5	8.1
90°	7.4	7.8	7.4	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4
92.5°	30.3	28.4	27.2	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4
95°	108.1	97.2	90.8	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9
97.5°	269.7	248.5	237.9	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9
100°	359.1	337.5	326.9	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2
102.5°	434.6	419.0	407.8	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3
105°	507.2	504.3	499.4	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8
107.5°	518.8	526.9	530.4	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5
110°	507.5	522.4	528.7	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	483.2	501.2	510.1	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3
115°	442.1	463.3	474.7	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5
117.5°	407.8	425.6	437.0	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7
120°	389.1	404.7	413.9	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7
122.5°	375.8	389.1	396.9	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3
125°	361.9	372.2	378.9	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6
127.5°	352.5	361.6	367.3	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5
130°	346.0	354.8	360.5	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8
132.5°	337.5	347.5	352.9	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9
135°	323.0	332.9	338.6	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7
137.5°	306.1	315.8	320.5	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3
140°	294.8	302.5	307.5	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0
142.5°	283.2	290.4	294.8	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1
145°	266.8	272.8	276.4	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5
147.5°	253.2	258.4	261.0	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9
150°	245.3	249.9	252.0	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1
152.5°	238.5	242.2	243.5	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0
155°	229.0	231.8	232.9	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3
157.5°	220.5	222.7	223.3	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3
160°	214.9	217.0	217.4	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2
162.5°	209.5	211.6	212.0	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1
165°	202.5	203.9	203.6	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7
167.5°	195.9	196.9	196.8	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6
170°	192.3	192.6	192.3	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0
172.5°	188.6	188.9	188.6	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8
175°	183.8	184.5	183.8	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7
177.5°	181.0	181.3	180.7	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	923.7	925.9	930.8	936.4	941.1	945.2	948.3	952.6	956.7	962.3	967.6
5°	867.6	873.1	880.9	890.2	901.9	909.7	919.4	928.0	940.4	952.9	964.9
7.5°	818.5	824.5	835.9	848.8	862.7	875.4	886.9	902.0	918.5	936.7	956.9
10°	786.7	793.3	807.0	821.7	838.1	850.5	866.1	884.0	902.7	924.8	949.7
12.5°	758.1	764.4	780.8	795.9	812.9	826.6	844.6	862.8	887.7	911.8	940.1
15°	702.3	719.0	737.7	755.6	775.8	792.6	814.3	833.0	856.8	890.6	922.9
17.5°	640.3	658.2	681.4	709.0	736.1	756.8	778.9	802.1	830.4	864.9	902.2
20°	604.2	618.6	644.3	675.1	706.6	735.4	755.6	781.3	810.5	847.8	886.3
22.5°	577.2	589.4	609.5	640.2	674.2	707.7	733.5	758.9	791.2	828.5	870.5
25°	536.5	549.8	567.3	588.3	627.2	662.6	696.5	725.6	759.9	797.2	843.9
27.5°	502.8	514.3	530.3	552.2	578.3	617.4	658.4	691.7	726.8	766.9	813.6
30°	482.8	492.2	505.4	527.6	552.5	587.5	629.1	668.1	703.5	745.1	793.7
32.5°	462.0	472.0	484.9	502.4	529.1	558.6	600.2	642.8	680.4	723.0	770.7
35°	434.2	442.0	453.7	471.6	495.7	521.4	558.3	602.3	642.0	687.5	733.0
37.5°	406.1	415.3	424.5	440.4	460.2	487.8	518.1	563.0	607.0	648.5	693.0
40°	390.2	395.7	405.8	418.7	439.7	464.2	492.6	536.5	580.5	621.8	666.5
42.5°	372.5	378.6	387.1	400.0	418.8	442.7	470.5	508.5	554.4	594.4	635.1
45°	347.8	351.3	359.9	370.8	386.4	410.5	436.2	470.0	513.2	551.3	587.1
47.5°	322.9	326.0	331.3	341.3	358.7	378.1	402.2	432.5	470.4	508.5	538.8
50°	305.8	308.5	313.6	322.9	338.5	357.6	381.3	408.5	442.4	479.0	504.2
52.5°	288.7	290.2	294.9	305.5	318.6	337.3	358.6	383.6	415.3	445.7	471.3
55°	261.5	265.0	268.1	275.9	288.3	306.2	325.3	349.0	373.5	399.2	421.0
57.5°	233.1	236.9	241.4	248.2	258.1	274.8	291.9	311.1	332.0	353.4	371.6
60°	214.4	217.9	221.8	229.6	238.5	251.7	270.4	287.1	303.1	322.5	340.8
62.5°	196.0	199.5	204.0	210.3	218.9	231.5	247.1	261.6	278.2	295.2	308.8
65°	168.9	171.6	175.1	180.9	189.1	200.4	213.2	224.5	239.3	251.7	264.2
67.5°	139.1	144.3	148.9	153.6	160.5	171.0	180.3	191.1	201.2	210.4	221.8
70°	119.4	125.3	129.6	134.6	141.2	150.2	159.1	166.5	174.7	183.6	193.8
72.5°	103.0	107.5	110.9	116.3	122.2	130.6	138.9	145.0	151.7	157.8	167.6
75°	81.3	83.3	85.6	89.9	95.3	101.6	108.2	113.6	117.5	122.9	130.0
77.5°	58.4	62.2	63.7	66.8	70.7	74.5	78.9	83.5	87.2	89.2	94.5
80°	44.7	46.3	47.9	52.1	54.5	58.4	61.5	65.8	67.3	69.3	74.3
82.5°	34.8	35.7	36.7	37.8	39.2	43.1	46.2	48.9	50.5	51.2	55.0
85°	20.2	20.6	21.0	21.4	21.8	21.8	23.3	25.3	28.0	28.0	29.2
87.5°	8.0	8.4	8.3	7.8	8.5	8.0	8.3	8.3	9.1	9.9	10.7
90°	6.0	6.4	5.7	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4
92.5°	93.4	112.1	98.1	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0
95°	296.2	288.0	217.4	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7
97.5°	372.1	303.4	203.4	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9
100°	374.6	284.2	184.5	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9
102.5°	353.4	260.1	171.8	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5
105°	314.9	231.8	160.8	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4
107.5°	283.8	216.0	158.8	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1
110°	268.3	210.6	159.4	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	259.5	208.1	161.1	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8
115°	251.3	206.8	164.3	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8
117.5°	247.6	206.4	167.8	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1
120°	245.6	206.4	170.4	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4
122.5°	243.4	206.1	172.9	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0
125°	239.6	205.7	176.7	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4
127.5°	234.6	204.9	179.8	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0
130°	231.5	204.6	182.0	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7
132.5°	228.7	204.4	184.0	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4
135°	224.4	203.9	187.0	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5
137.5°	220.8	203.9	188.7	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7
140°	218.8	203.6	190.1	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4
142.5°	217.1	203.6	191.3	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3
145°	214.2	202.9	191.9	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9
147.5°	211.6	201.6	192.3	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2
150°	209.6	200.7	192.3	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1
152.5°	207.3	199.3	191.7	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8
155°	203.9	197.2	190.9	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0
157.5°	200.5	195.0	189.9	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0
160°	197.9	193.3	189.1	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1
162.5°	195.7	191.6	188.2	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9
165°	191.9	189.1	186.6	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1
167.5°	188.5	186.5	184.9	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3
170°	186.3	184.8	183.8	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7
172.5°	184.3	183.1	182.7	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1
175°	182.0	181.3	181.3	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5
177.5°	180.5	180.2	180.2	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	971.6	974.4	977.5	983.4	988.4	990.6	995.0	998.1	997.1	1001.5	1009.0
5°	975.4	985.9	998.0	1010.4	1024.4	1036.1	1045.5	1054.8	1062.2	1071.1	1084.4
7.5°	974.8	993.5	1013.8	1036.1	1059.1	1078.9	1097.3	1116.0	1132.5	1150.7	1174.4
10°	972.3	997.2	1022.5	1051.7	1080.9	1108.5	1133.4	1156.7	1178.9	1202.6	1232.6
12.5°	969.5	998.1	1028.7	1063.8	1100.2	1133.4	1162.7	1196.3	1224.0	1254.6	1289.3
15°	957.1	995.7	1037.3	1082.8	1126.4	1171.1	1211.2	1252.5	1291.0	1327.5	1371.1
17.5°	943.0	987.4	1036.5	1090.3	1142.7	1197.0	1244.6	1296.6	1335.9	1385.0	1425.5
20°	931.5	979.3	1031.8	1092.1	1151.7	1212.0	1264.5	1317.4	1361.8	1411.2	1462.6
22.5°	917.5	970.0	1026.9	1089.3	1151.7	1217.6	1275.7	1328.3	1383.3	1438.9	1491.8
25°	894.9	949.4	1009.7	1078.1	1149.7	1217.0	1279.3	1344.7	1403.8	1464.1	1511.6
27.5°	867.2	924.4	988.0	1058.6	1132.1	1201.0	1274.3	1344.0	1403.5	1461.5	1502.9
30°	845.1	905.4	966.5	1038.1	1114.3	1188.3	1266.8	1336.5	1399.1	1451.3	1474.6
32.5°	822.4	879.6	942.5	1015.0	1093.2	1172.7	1250.7	1321.9	1379.8	1411.1	1411.7
35°	782.8	836.5	901.9	973.1	1053.2	1139.6	1218.6	1288.6	1324.0	1326.8	1288.6
37.5°	739.7	789.0	850.7	922.0	1009.7	1095.7	1176.3	1223.0	1234.9	1195.3	1124.8
40°	708.9	754.4	814.0	887.1	974.3	1063.0	1136.5	1170.7	1158.3	1094.1	1015.5
42.5°	676.5	718.9	776.3	848.5	936.0	1025.6	1088.3	1106.6	1073.6	999.5	907.5
45°	623.7	662.6	719.4	792.2	876.2	960.3	1007.7	998.4	943.5	855.6	752.5
47.5°	568.7	606.3	657.4	724.7	810.8	883.3	915.4	887.3	809.2	712.5	628.6
50°	532.3	570.8	617.9	682.1	760.7	830.7	851.3	808.5	721.7	628.8	551.7
52.5°	496.5	529.4	575.5	637.5	712.7	771.9	782.8	733.5	643.9	560.6	492.3
55°	442.0	472.0	510.9	569.2	634.2	684.4	678.6	615.1	533.8	462.6	408.9
57.5°	389.3	411.9	447.8	502.5	559.6	593.3	571.9	517.9	442.1	383.8	338.5
60°	354.5	375.5	408.9	456.8	507.0	526.0	508.1	449.4	389.5	336.2	298.0
62.5°	321.5	340.0	368.8	413.2	453.7	465.0	445.9	394.6	340.6	295.1	263.5
65°	273.5	290.6	315.2	346.7	374.7	380.1	367.7	315.2	274.3	236.2	214.4
67.5°	230.0	241.2	260.4	287.6	302.5	305.7	281.6	248.6	212.6	189.2	172.8
70°	200.8	208.5	226.4	241.2	253.3	253.7	231.5	205.0	177.4	158.4	146.3
72.5°	172.4	179.9	193.5	203.6	212.8	209.8	189.5	168.6	146.3	131.9	122.9
75°	133.1	139.7	146.7	151.4	151.4	147.5	132.7	117.1	104.3	95.7	93.0
77.5°	96.7	102.2	104.5	103.8	102.4	96.3	87.0	76.8	72.2	68.2	66.1
80°	75.9	78.2	79.0	77.0	74.7	67.7	61.5	57.2	52.9	51.4	50.6
82.5°	56.3	58.3	56.3	56.8	51.7	45.9	42.5	41.0	39.2	38.6	37.8
85°	30.0	29.6	28.8	26.8	23.3	22.6	22.2	21.8	21.0	21.4	20.6
87.5°	10.5	9.8	8.6	8.3	8.3	8.1	8.5	8.6	8.7	8.4	9.1
90°	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4
92.5°	5.9	9.2	13.5	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4
95°	12.7	16.3	20.9	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9
97.5°	20.9	24.0	28.2	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9
100°	26.9	29.3	33.6	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2
102.5°	33.1	35.3	39.2	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3
105°	42.4	44.2	48.4	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8
107.5°	51.8	53.6	58.1	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5
110°	58.3	60.1	64.3	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	64.5	66.6	70.5	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3
115°	73.9	76.3	79.9	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5
117.5°	83.1	85.3	89.2	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7
120°	89.1	91.5	95.4	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7
122.5°	94.7	97.2	100.8	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3
125°	102.8	105.0	108.9	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6
127.5°	109.1	111.7	116.1	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5
130°	113.1	115.9	121.2	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8
132.5°	116.5	120.2	125.2	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9
135°	121.9	125.5	131.5	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7
137.5°	127.0	130.9	136.6	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3
140°	130.4	134.3	140.3	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0
142.5°	134.4	138.0	143.7	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1
145°	140.0	143.5	148.4	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5
147.5°	145.5	148.7	153.7	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9
150°	149.5	152.3	156.6	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1
152.5°	152.9	155.7	159.7	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0
155°	158.3	160.5	164.0	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3
157.5°	163.0	165.0	167.7	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3
160°	166.1	167.5	170.0	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2
162.5°	168.7	169.8	172.0	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1
165°	172.1	172.8	174.6	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7
167.5°	174.9	175.3	176.6	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6
170°	176.4	176.7	177.8	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0
172.5°	177.8	177.8	178.6	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8
175°	179.2	179.2	179.5	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7
177.5°	179.9	179.6	179.9	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	965.7	965.7	965.7	965.7	965.7	965.7	965.7
2.5°	1013.0	1014.3	1015.2	1018.3	1018.6	1021.4	1018.6
5°	1096.8	1102.3	1110.8	1119.4	1120.2	1125.6	1115.9
7.5°	1190.8	1203.4	1211.3	1225.1	1230.6	1234.0	1228.4
10°	1255.6	1267.2	1287.9	1298.0	1308.1	1309.6	1305.0
12.5°	1318.1	1336.6	1352.9	1372.1	1371.6	1385.3	1380.3
15°	1401.5	1420.5	1443.1	1464.5	1472.3	1472.3	1478.5
17.5°	1460.9	1495.9	1519.2	1536.0	1554.4	1557.6	1555.4
20°	1501.1	1538.8	1563.7	1585.5	1598.0	1601.5	1601.5
22.5°	1531.0	1563.1	1587.4	1607.0	1617.3	1621.4	1620.1
25°	1551.7	1579.3	1594.1	1599.9	1602.6	1601.8	1594.5
27.5°	1523.3	1522.1	1512.7	1494.8	1481.4	1473.2	1463.9
30°	1469.2	1448.9	1425.6	1399.9	1366.8	1341.5	1333.8
32.5°	1388.6	1343.1	1303.6	1260.8	1225.2	1199.9	1189.3
35°	1232.6	1160.6	1101.9	1050.5	1013.2	989.8	982.0
37.5°	1047.6	977.9	905.2	855.4	824.4	800.8	792.0
40°	929.9	854.0	790.6	743.9	712.0	689.1	688.7
42.5°	822.5	750.1	690.4	656.8	622.4	607.2	607.1
45°	673.5	615.5	564.9	538.5	517.9	505.4	501.9
47.5°	557.6	509.7	476.0	454.9	438.1	430.2	425.0
50°	492.6	450.6	423.7	405.4	396.1	386.0	385.2
52.5°	438.4	404.5	383.6	368.7	356.9	350.8	351.0
55°	368.5	341.6	326.8	315.5	306.2	301.5	299.6
57.5°	310.4	290.3	279.5	269.2	265.2	261.5	260.5
60°	274.3	260.7	250.6	242.4	236.6	235.4	235.0
62.5°	244.4	230.2	223.2	216.9	212.6	210.8	210.1
65°	201.5	191.0	184.8	179.8	178.2	175.5	175.1
67.5°	162.5	156.2	152.1	148.6	146.4	146.3	146.3
70°	138.5	135.0	131.5	129.6	128.4	127.6	127.6
72.5°	118.0	115.4	112.5	111.5	111.3	110.5	110.2
75°	89.9	87.2	87.5	85.6	84.0	82.1	80.9
77.5°	63.7	61.8	61.4	61.2	59.8	59.6	60.2
80°	49.4	47.5	47.1	47.5	47.1	45.9	45.9
82.5°	37.6	36.0	35.6	35.3	34.9	35.3	34.7
85°	20.2	19.5	19.5	19.5	20.2	19.8	19.5
87.5°	8.5	8.3	8.6	8.3	8.4	8.0	8.3
90°	6.7	7.1	7.1	7.4	7.8	7.4	7.4
92.5°	52.2	41.6	34.5	30.3	28.4	27.2	27.2
95°	207.1	159.7	125.5	108.1	97.2	90.8	86.2
97.5°	366.6	332.0	295.1	269.7	248.5	237.9	230.5
100°	433.3	416.0	389.8	359.1	337.5	326.9	324.1
102.5°	459.3	464.3	453.4	434.6	419.0	407.8	405.5
105°	457.0	492.0	506.5	507.2	504.3	499.4	497.3
107.5°	420.6	469.8	501.4	518.8	526.9	530.4	531.3
110°	392.3	443.6	482.4	507.5	522.4	528.7	531.9



TEST NUMBER: P332897

CATALOG NUMBER: S124RDIP-S575D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	367.4	415.8	454.7	483.2	501.2	510.1	515.2
115°	338.9	380.3	414.2	442.1	463.3	474.7	477.5
117.5°	322.7	355.2	384.0	407.8	425.6	437.0	439.2
120°	315.6	343.9	369.0	389.1	404.7	413.9	417.8
122.5°	311.1	336.8	358.8	375.8	389.1	396.9	400.8
125°	303.9	328.3	347.8	361.9	372.2	378.9	381.0
127.5°	295.5	319.9	338.3	352.5	361.6	367.3	369.4
130°	288.8	312.8	331.5	346.0	354.8	360.5	362.6
132.5°	281.1	304.6	323.3	337.5	347.5	352.9	355.0
135°	269.7	291.2	308.9	323.0	332.9	338.6	340.7
137.5°	258.7	276.9	292.8	306.1	315.8	320.5	323.0
140°	251.6	267.5	282.4	294.8	302.5	307.5	310.3
142.5°	245.7	259.3	272.2	283.2	290.4	294.8	296.7
145°	237.5	248.1	258.0	266.8	272.8	276.4	278.1
147.5°	230.4	238.9	246.7	253.2	258.4	261.0	261.7
150°	226.2	233.3	239.6	245.3	249.9	252.0	252.3
152.5°	222.0	228.5	233.7	238.5	242.2	243.5	243.9
155°	215.9	221.2	225.5	229.0	231.8	232.9	232.9
157.5°	210.0	214.5	217.9	220.5	222.7	223.3	223.3
160°	206.0	209.9	212.8	214.9	217.0	217.4	217.4
162.5°	202.4	205.4	208.0	209.5	211.6	212.0	211.7
165°	196.9	199.3	201.1	202.5	203.9	203.6	203.2
167.5°	192.2	194.2	195.2	195.9	196.9	196.8	196.5
170°	189.1	190.5	191.6	192.3	192.6	192.3	192.3
172.5°	186.5	187.4	188.2	188.6	188.9	188.6	188.0
175°	183.1	183.8	183.8	183.8	184.5	183.8	183.1
177.5°	181.0	181.0	181.3	181.0	181.3	180.7	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)