

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332945

Luminaire Tested: **S124RDIP-S795D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332945
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D1035U835-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7035.2 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47																				
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41																				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35																				
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30																				
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26																				
5	69	58	50	44	63	53	46	41	46	40	36	38	34	31	31	28	26	23																				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20																				
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18																				
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16																				
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15																				
10	47	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10656	10656	10656	10656
5°	12361	10689	9447	10689
10°	14623	10642	8432	10642
15°	16891	10543	7245	10543
20°	18806	10408	6552	10408
25°	19414	10276	6083	10276
30°	16995	10113	5800	10113
35°	13230	9875	5629	9875
40°	9921	9601	5538	9601
45°	7833	9162	5489	9162
50°	6612	8657	5330	8657
55°	5764	8099	5046	8099
60°	5186	7522	4466	7522
65°	4571	6898	3840	6898
70°	4116	6253	3465	6253
75°	3450	5540	2954	5540
80°	2920	4723	2771	4723
85°	2464	3696	2464	3696



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.9	1.8
10°-20°	385.8	5.5
20°-30°	603.4	8.6
30°-40°	670.8	9.5
40°-50°	595.2	8.5
50°-60°	463.8	6.6
60°-70°	303.6	4.3
70°-80°	149.3	2.1
80°-90°	39.7	0.6
90°-100°	367.0	5.2
100°-110°	763.9	10.9
110°-120°	684.2	9.7
120°-130°	575.5	8.2
130°-140°	479.9	6.8
140°-150°	366.6	5.2
150°-160°	257.7	3.7
160°-170°	151.6	2.2
170°-180°	49.3	0.7
0°-30°	1117.1	15.9
0°-40°	1787.9	25.4
0°-60°	2846.9	40.5
0°-90°	3339.5	47.5
90°-120°	1815.1	25.8
90°-150°	3237.1	46.0
90°-180°	3696.0	52.5
0°-180°	7035.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1320	1320	1320	1320	1320	
5°	1525	1319	1166	1319	1525	154
15°	2021	1262	867	1262	2021	575
25°	2180	1154	683	1154	2180	967
35°	1342	1002	571	1002	1342	841
45°	686	802	481	802	686	543
55°	410	575	358	575	410	372
65°	239	361	201	361	239	241
75°	111	178	95	178	111	122
85°	27	40	27	40	27	31
90°	21	1	21	1	21	18
95°	244	33	244	33	244	378
105°	1405	117	1405	117	1405	1389
115°	1349	206	1349	206	1349	1339
125°	1076	286	1076	286	1076	978
135°	962	340	962	340	962	743
145°	786	392	786	392	786	498
155°	658	446	658	446	658	307
165°	574	486	574	486	574	165
175°	517	507	517	507	517	50
180°	508	508	508	508	508	



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1392.3	1396.2	1392.3	1391.9	1387.7	1386.4	1384.7	1379.2	1368.9	1363.0	1364.3
5°	1525.3	1538.6	1531.2	1530.1	1518.4	1506.7	1499.2	1482.2	1464.1	1451.9	1441.8
7.5°	1679.1	1686.8	1682.1	1674.6	1655.7	1645.0	1627.7	1605.3	1572.9	1548.1	1525.4
10°	1783.8	1790.2	1788.0	1774.2	1760.4	1732.2	1716.2	1684.9	1643.9	1611.5	1581.2
12.5°	1886.7	1893.6	1874.8	1875.5	1849.3	1827.1	1801.8	1762.3	1715.0	1673.2	1635.2
15°	2021.0	2012.5	2012.5	2001.8	1972.6	1941.7	1915.7	1874.2	1814.6	1764.6	1712.0
17.5°	2126.1	2129.0	2124.7	2099.6	2076.6	2044.7	1996.9	1948.5	1893.2	1826.1	1772.3
20°	2189.0	2189.0	2184.3	2167.2	2137.5	2103.4	2051.8	1999.2	1929.0	1861.4	1800.8
22.5°	2214.6	2216.3	2210.6	2196.6	2169.8	2136.6	2092.7	2039.2	1966.8	1890.8	1815.7
25°	2179.5	2189.6	2190.6	2186.9	2178.9	2158.7	2121.0	2066.2	2001.3	1918.9	1838.0
27.5°	2001.0	2013.7	2024.9	2043.3	2067.8	2080.5	2082.2	2054.4	1997.8	1918.4	1837.1
30°	1823.1	1833.8	1868.3	1913.5	1948.7	1980.6	2008.2	2015.7	1983.8	1912.5	1826.9
32.5°	1625.7	1640.2	1674.8	1723.4	1781.9	1835.9	1898.0	1929.7	1928.9	1886.1	1806.9
35°	1342.4	1353.0	1384.9	1436.0	1506.2	1586.5	1684.9	1761.4	1813.6	1809.8	1761.4
37.5°	1082.6	1094.6	1126.9	1169.2	1237.3	1336.7	1431.9	1537.4	1633.8	1687.9	1671.8
40°	941.4	941.9	973.3	1016.9	1080.7	1167.4	1271.1	1388.1	1495.5	1583.3	1600.3
42.5°	829.9	830.0	850.7	897.7	943.7	1025.3	1124.3	1240.5	1366.2	1467.6	1512.7
45°	686.1	690.9	707.9	736.1	772.2	841.4	920.6	1028.6	1169.5	1289.7	1364.7
47.5°	581.0	588.0	598.8	621.8	650.6	696.7	762.2	859.2	973.9	1106.1	1212.8
50°	526.5	527.6	541.4	554.2	579.2	615.9	673.3	754.1	859.4	986.6	1105.2
52.5°	479.7	479.5	487.8	504.0	524.3	552.9	599.3	672.9	766.3	880.2	1002.6
55°	409.5	412.2	418.6	431.3	446.7	467.0	503.6	559.0	632.4	729.7	840.8
57.5°	356.1	357.5	362.5	367.9	382.1	396.8	424.3	462.7	524.6	604.3	707.9
60°	321.2	321.8	323.4	331.3	342.5	356.3	374.9	407.4	459.5	532.4	614.3
62.5°	287.2	288.1	290.6	296.4	305.1	314.6	334.1	360.2	403.3	465.6	539.4
65°	239.3	239.9	243.6	245.7	252.6	261.1	275.5	293.0	322.8	374.9	430.8
67.5°	200.0	200.0	200.2	203.1	207.8	213.5	222.1	236.1	258.6	290.6	339.8
70°	174.4	174.4	175.5	177.1	179.8	184.5	189.3	200.0	216.5	242.5	280.3
72.5°	150.6	151.0	152.1	152.4	153.8	157.7	161.3	168.1	180.3	200.0	230.5
75°	110.6	112.2	114.9	117.0	119.7	119.1	122.9	127.1	130.8	142.5	160.1
77.5°	82.3	81.5	81.8	83.6	83.9	84.5	87.1	90.4	93.2	98.7	105.0
80°	62.8	62.8	64.4	64.9	64.4	64.9	67.5	69.1	70.2	72.3	78.2
82.5°	47.4	48.3	47.8	48.3	48.6	49.1	51.4	51.7	52.8	53.6	56.1
85°	26.6	27.1	27.7	26.6	26.6	26.6	27.7	28.2	29.3	28.7	29.8
87.5°	13.6	13.1	13.8	13.6	13.8	13.4	13.6	14.2	13.2	13.8	13.4
90°	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0	17.0	18.0	16.0
92.5°	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1	263.8	316.7	277.1
95°	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7	836.6	813.6	614.0
97.5°	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0	1051.0	856.9	574.6
100°	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0	1058.2	802.6	521.1
102.5°	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4	998.3	734.8	485.2
105°	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1	889.5	654.9	454.2
107.5°	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1	801.6	610.2	448.6
110°	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4	757.7	595.0	450.2



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1	733.0	587.8	455.0
115°	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6	709.8	584.0	464.2
117.5°	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8	699.4	583.0	474.0
120°	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6	693.8	583.0	481.2
122.5°	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1	687.4	582.2	488.4
125°	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7	676.9	581.0	499.2
127.5°	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7	662.7	578.8	507.7
130°	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8	653.9	578.0	514.1
132.5°	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0	645.9	577.2	519.7
135°	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8	633.9	576.0	528.1
137.5°	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9	623.5	575.8	533.1
140°	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9	618.0	575.0	537.1
142.5°	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7	613.2	575.0	540.3
145°	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9	605.0	573.0	542.1
147.5°	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9	597.6	569.4	543.1
150°	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0	592.0	567.0	543.1
152.5°	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2	585.6	563.0	541.5
155°	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0	576.0	557.1	539.1
157.5°	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8	566.2	550.9	536.5
160°	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0	559.1	546.1	534.1
162.5°	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2	552.7	541.3	531.7
165°	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1	542.1	534.1	527.1
167.5°	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3	532.5	526.9	522.3
170°	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1	526.1	522.1	519.1
172.5°	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7	520.5	517.3	515.9
175°	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1	514.1	512.1	512.1
177.5°	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5	509.7	508.9	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1360.0	1354.1	1351.1	1344.3	1336.2	1331.9	1328.1	1322.6	1315.3	1307.7	1302.1
5°	1429.0	1416.3	1400.3	1381.2	1364.2	1347.7	1333.3	1319.0	1302.5	1285.4	1268.4
7.5°	1499.9	1474.8	1447.7	1416.3	1385.8	1358.0	1332.5	1308.0	1280.3	1255.6	1233.0
10°	1549.2	1515.2	1477.4	1437.6	1397.7	1363.1	1329.1	1298.2	1264.2	1233.9	1208.3
12.5°	1589.2	1549.2	1503.8	1454.1	1406.2	1364.4	1325.2	1285.0	1246.3	1213.4	1179.4
15°	1655.6	1600.8	1539.7	1480.1	1417.9	1361.0	1308.3	1261.5	1217.4	1171.1	1138.7
17.5°	1701.2	1636.2	1561.9	1490.3	1416.8	1349.7	1289.0	1233.2	1182.3	1135.0	1096.4
20°	1728.5	1656.7	1574.2	1492.9	1410.4	1338.6	1273.2	1211.5	1158.9	1107.8	1067.9
22.5°	1743.8	1664.3	1574.2	1489.0	1403.6	1325.9	1254.1	1189.8	1132.5	1081.4	1037.3
25°	1748.7	1663.6	1571.6	1473.7	1380.1	1297.7	1223.2	1153.6	1089.7	1038.7	991.9
27.5°	1741.9	1641.7	1547.4	1447.0	1350.4	1263.5	1185.4	1112.2	1048.3	993.5	945.5
30°	1731.7	1624.2	1523.2	1418.9	1321.1	1237.6	1155.1	1084.9	1018.5	961.6	913.2
32.5°	1709.5	1603.0	1494.2	1387.5	1288.3	1202.3	1124.1	1053.5	988.3	930.1	878.7
35°	1665.7	1557.8	1439.7	1330.1	1232.8	1143.4	1070.1	1002.0	939.8	877.5	823.3
37.5°	1608.0	1497.7	1380.2	1260.2	1162.8	1078.5	1011.1	947.2	886.5	829.7	769.6
40°	1553.5	1453.0	1331.7	1212.6	1112.6	1031.2	969.0	911.0	849.9	793.5	733.4
42.5°	1487.5	1401.9	1279.4	1159.8	1061.1	982.7	924.8	868.1	812.4	757.8	695.1
45°	1377.5	1312.6	1197.7	1082.8	983.4	905.7	852.5	802.5	753.6	701.5	642.5
47.5°	1251.3	1207.4	1108.2	990.6	898.6	828.7	777.3	736.5	695.1	643.0	591.2
50°	1163.7	1135.5	1039.7	932.3	844.6	780.2	727.6	689.3	654.7	604.7	558.4
52.5°	1070.1	1055.1	974.2	871.5	786.7	723.6	678.6	644.2	609.2	567.7	524.4
55°	927.5	935.5	866.9	778.1	698.3	645.1	604.2	575.4	545.7	510.6	477.1
57.5°	781.8	810.9	764.9	686.9	612.1	563.0	532.2	508.0	483.0	453.9	425.3
60°	694.6	719.0	693.0	624.4	559.0	513.2	484.5	465.9	440.9	414.3	392.5
62.5°	609.5	635.7	620.2	564.8	504.1	464.7	439.4	422.1	403.5	380.3	357.6
65°	502.6	519.6	512.2	473.9	430.8	397.3	373.9	361.1	344.1	327.1	306.9
67.5°	384.9	417.8	413.5	393.1	355.9	329.7	314.4	303.1	287.6	275.0	261.2
70°	316.4	346.8	346.2	329.7	309.5	285.1	274.4	264.9	251.0	238.8	227.6
72.5°	259.0	286.8	290.9	278.3	264.4	245.9	235.7	229.1	215.7	207.3	198.3
75°	181.4	201.6	206.9	206.9	200.5	190.9	181.9	177.6	168.1	160.6	155.3
77.5°	118.9	131.7	140.0	141.9	142.9	139.7	132.2	129.2	121.9	119.2	114.1
80°	84.0	92.5	102.1	105.3	108.0	106.9	103.7	101.6	94.7	92.0	89.9
82.5°	58.1	62.8	70.6	77.6	76.9	79.7	76.9	75.2	70.0	69.0	66.9
85°	30.3	30.8	31.9	36.7	39.4	40.4	41.0	39.9	38.3	38.3	34.6
87.5°	13.0	12.6	12.2	12.2	12.5	14.0	14.6	14.7	13.8	13.1	12.0
90°	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0	3.0	6.0	7.0
92.5°	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4	16.6	26.0	38.1
95°	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9	35.9	45.9	58.9
97.5°	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1	59.1	67.7	79.7
100°	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9	75.9	82.9	94.8
102.5°	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8	93.4	99.6	110.8
105°	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8	119.8	124.8	136.8
107.5°	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4	146.4	151.3	164.1
110°	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7	164.7	169.7	181.7



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3	182.3	188.1	199.3
115°	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7	208.6	215.6	225.6
117.5°	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0	234.8	241.0	252.0
120°	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6	251.6	258.6	269.5
122.5°	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6	267.5	274.5	284.7
125°	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5	290.5	296.5	307.5
127.5°	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1	308.3	315.5	328.0
130°	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5	319.5	327.4	342.4
132.5°	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8	329.0	339.4	353.6
135°	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4	344.4	354.4	371.4
137.5°	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0	358.8	369.8	385.9
140°	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4	368.4	379.4	396.3
142.5°	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6	379.6	389.7	405.9
145°	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3	395.3	405.3	419.3
147.5°	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1	411.1	419.9	434.3
150°	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3	422.3	430.3	442.3
152.5°	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7	431.9	439.9	451.0
155°	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2	447.2	453.2	463.2
157.5°	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4	460.4	466.0	473.8
160°	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2	469.2	473.2	480.2
162.5°	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2	476.4	479.6	485.8
165°	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2	486.2	488.2	493.2
167.5°	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2	494.2	495.2	499.0
170°	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2	498.2	499.2	502.2
172.5°	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1	502.2	502.3	504.5
175°	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1	506.1	506.1	507.1
177.5°	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9	508.1	507.3	508.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1296.2	1291.9	1286.4	1280.0	1272.4	1265.6	1262.6	1265.1	1266.4	1263.0	1262.6
5°	1256.7	1243.4	1232.8	1216.8	1204.1	1193.4	1186.0	1182.8	1183.9	1175.4	1173.2
7.5°	1212.4	1196.6	1179.2	1160.3	1142.6	1127.0	1118.8	1114.3	1105.3	1101.4	1094.9
10°	1183.9	1162.6	1145.6	1123.2	1103.0	1084.4	1075.4	1067.9	1058.9	1054.6	1045.6
12.5°	1154.5	1129.8	1111.1	1087.9	1067.3	1044.8	1036.2	1022.4	1008.3	999.3	987.7
15°	1113.1	1083.4	1060.5	1032.8	1008.4	982.8	960.0	934.4	924.9	904.7	893.0
17.5°	1064.7	1034.5	1006.2	969.1	931.4	899.7	875.3	850.8	836.2	823.3	817.3
20°	1032.8	1005.2	965.8	922.7	880.7	845.6	825.9	810.0	794.0	785.0	778.6
22.5°	1002.6	967.3	921.6	875.1	833.1	805.6	788.9	772.5	759.6	751.0	742.4
25°	952.0	905.7	857.3	804.1	775.4	751.5	733.4	720.1	712.1	701.0	696.7
27.5°	900.0	843.9	790.5	754.8	724.9	703.0	687.2	677.2	667.1	660.0	654.5
30°	860.0	803.1	755.2	721.2	690.9	672.8	660.0	648.3	640.3	634.5	630.2
32.5°	820.4	763.5	723.3	686.7	662.8	645.1	631.5	622.8	616.5	609.0	606.4
35°	763.2	712.7	677.6	644.6	620.1	604.2	593.5	584.5	579.2	577.0	575.4
37.5°	708.2	666.8	629.1	602.0	580.2	567.7	555.1	550.7	547.0	543.2	544.9
40°	673.3	634.5	601.0	572.3	554.7	540.9	533.4	528.1	524.9	524.9	524.9
42.5°	643.1	605.1	572.5	546.7	529.2	517.5	509.2	504.7	503.6	503.2	505.8
45°	596.2	561.1	528.1	506.8	491.9	480.2	475.5	471.7	471.7	473.9	474.4
47.5°	549.7	516.8	490.4	466.5	452.9	445.6	441.4	439.5	439.7	441.9	444.3
50°	521.2	488.8	462.7	441.4	428.7	421.7	418.0	417.0	418.0	418.0	421.7
52.5°	490.1	461.1	435.5	417.6	403.1	396.6	394.6	393.1	393.8	395.5	397.1
55°	444.6	418.6	394.1	377.1	366.4	362.2	357.4	357.9	356.9	357.9	357.9
57.5°	399.0	375.6	352.8	339.3	330.0	323.8	318.6	320.1	318.5	318.3	317.4
60°	369.6	344.1	326.0	313.8	303.1	297.8	293.0	294.1	292.5	291.4	289.3
62.5°	337.7	316.4	299.2	287.4	278.9	272.7	267.9	266.9	263.2	259.5	254.9
65°	291.4	273.9	258.5	247.3	239.3	234.5	230.8	227.6	219.6	211.1	206.9
67.5°	246.5	233.8	219.4	210.0	203.5	197.2	190.1	184.7	177.2	172.5	169.9
70°	217.5	205.3	193.1	184.0	177.1	171.3	163.3	159.6	154.2	152.1	149.4
72.5°	189.9	178.5	167.1	158.9	151.6	147.0	140.7	137.0	134.7	133.8	131.2
75°	147.9	138.8	130.3	122.9	117.0	113.8	111.2	108.5	107.4	102.6	100.0
77.5°	107.9	101.9	96.6	91.3	87.1	85.0	79.9	76.8	75.0	72.8	72.2
80°	84.0	79.8	74.5	71.3	65.4	63.3	61.2	60.6	60.1	59.6	59.0
82.5°	63.2	58.9	53.6	51.7	50.1	48.8	47.5	47.0	46.5	46.8	46.7
85°	31.9	29.8	29.8	29.3	28.7	28.2	27.7	27.7	27.1	27.7	27.1
87.5°	12.2	11.8	13.0	12.2	13.0	13.4	12.8	13.0	13.6	12.9	12.9
90°	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0	19.0	20.0	20.0
92.5°	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1	147.6	117.4	97.4
95°	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7	585.0	451.2	354.4
97.5°	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0	1035.4	937.8	833.6
100°	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0	1223.9	1175.0	1101.1
102.5°	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4	1297.4	1311.6	1280.8
105°	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1	1290.8	1389.6	1430.6
107.5°	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1	1188.0	1327.2	1416.2
110°	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4	1108.1	1252.9	1362.7



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1	1037.8	1174.6	1284.4
115°	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6	957.4	1074.2	1170.0
117.5°	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8	911.5	1003.3	1084.6
120°	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6	891.5	971.4	1042.2
122.5°	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1	878.7	951.4	1013.5
125°	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7	858.5	927.4	982.3
127.5°	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7	834.8	903.5	955.6
130°	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8	815.6	883.5	936.4
132.5°	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0	794.1	860.3	913.3
135°	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8	761.7	822.6	872.5
137.5°	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9	730.8	782.1	827.2
140°	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9	710.8	755.7	797.6
142.5°	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7	694.0	732.6	768.9
145°	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9	670.9	700.8	728.8
147.5°	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9	650.9	674.9	696.8
150°	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0	638.9	658.9	676.9
152.5°	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2	626.9	645.3	660.1
155°	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0	610.0	624.9	636.9
157.5°	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8	593.2	605.8	615.4
160°	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0	582.0	593.0	601.0
162.5°	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2	571.6	580.2	587.4
165°	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1	556.1	563.0	568.0
167.5°	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3	542.9	548.5	551.5
170°	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1	534.1	538.1	541.1
172.5°	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7	526.9	529.3	531.5
175°	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1	517.1	519.1	519.1
177.5°	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5	511.3	511.3	512.1
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1260.0	1260.9	1257.9	1257.0	1257.9	1260.9	1260.0	1262.6	1263.0	1266.4	1265.1
5°	1169.0	1167.9	1165.3	1165.8	1165.3	1167.9	1169.0	1173.2	1175.4	1183.9	1182.8
7.5°	1091.1	1087.0	1088.1	1083.9	1088.1	1087.0	1091.1	1094.9	1101.4	1105.3	1114.3
10°	1043.5	1037.6	1032.8	1028.6	1032.8	1037.6	1043.5	1045.6	1054.6	1058.9	1067.9
12.5°	978.4	973.4	966.9	968.2	966.9	973.4	978.4	987.7	999.3	1008.3	1022.4
15°	886.0	878.1	865.3	866.9	865.3	878.1	886.0	893.0	904.7	924.9	934.4
17.5°	807.9	808.0	802.1	803.5	802.1	808.0	807.9	817.3	823.3	836.2	850.8
20°	767.4	763.7	764.2	762.7	764.2	763.7	767.4	778.6	785.0	794.0	810.0
22.5°	739.4	734.8	731.1	727.8	731.1	734.8	739.4	742.4	751.0	759.6	772.5
25°	691.9	688.7	683.9	682.9	683.9	688.7	691.9	696.7	701.0	712.1	720.1
27.5°	650.2	649.6	647.7	645.2	647.7	649.6	650.2	654.5	660.0	667.1	677.2
30°	626.0	624.9	623.8	622.2	623.8	624.9	626.0	630.2	634.5	640.3	648.3
32.5°	604.3	603.6	602.6	602.7	602.6	603.6	604.3	606.4	609.0	616.5	622.8
35°	573.3	572.8	571.7	571.2	571.7	572.8	573.3	575.4	577.0	579.2	584.5
37.5°	544.4	545.8	545.1	545.0	545.1	545.8	544.4	544.9	543.2	547.0	550.7
40°	524.4	524.9	526.0	525.5	526.0	524.9	524.4	524.9	524.9	524.9	528.1
42.5°	507.8	507.9	509.4	507.6	509.4	507.9	507.8	505.8	503.2	503.6	504.7
45°	478.1	481.3	480.8	480.8	480.8	481.3	478.1	474.4	473.9	471.7	471.7
47.5°	445.7	448.4	449.2	449.1	449.2	448.4	445.7	444.3	441.9	439.7	439.5
50°	424.4	423.3	424.9	424.4	424.9	423.3	424.4	421.7	418.0	418.0	417.0
52.5°	398.5	398.7	398.6	398.0	398.6	398.7	398.5	397.1	395.5	393.8	393.1
55°	358.5	359.0	357.9	358.5	357.9	359.0	358.5	357.9	357.9	356.9	357.9
57.5°	315.1	312.5	313.6	312.3	313.6	312.5	315.1	317.4	318.3	318.5	320.1
60°	284.0	279.7	278.7	276.6	278.7	279.7	284.0	289.3	291.4	292.5	294.1
62.5°	249.1	246.1	242.5	244.2	242.5	246.1	249.1	254.9	259.5	263.2	266.9
65°	202.6	200.5	198.9	201.0	198.9	200.5	202.6	206.9	211.1	219.6	227.6
67.5°	167.7	166.6	166.6	165.5	166.6	166.6	167.7	169.9	172.5	177.2	184.7
70°	149.4	147.9	147.9	146.8	147.9	147.9	149.4	149.4	152.1	154.2	159.6
72.5°	130.7	129.1	129.6	128.9	129.6	129.1	130.7	131.2	133.8	134.7	137.0
75°	96.8	94.1	94.1	94.7	94.1	94.1	96.8	100.0	102.6	107.4	108.5
77.5°	72.2	71.7	72.4	71.5	72.4	71.7	72.2	72.2	72.8	75.0	76.8
80°	59.0	58.5	58.0	59.6	58.0	58.5	59.0	59.0	59.6	60.1	60.6
82.5°	45.8	45.7	45.6	47.7	45.6	45.7	45.8	46.7	46.8	46.5	47.0
85°	27.7	26.6	27.7	26.6	27.7	26.6	27.7	27.1	27.7	27.1	27.7
87.5°	14.0	13.8	13.1	13.6	13.1	13.8	14.0	12.9	12.9	13.6	13.0
90°	21.0	22.0	21.0	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0
92.5°	85.7	80.3	76.9	76.9	76.9	80.3	85.7	97.4	117.4	147.6	196.1
95°	305.5	274.5	256.6	243.6	256.6	274.5	305.5	354.4	451.2	585.0	739.7
97.5°	761.9	701.8	671.9	651.1	671.9	701.8	761.9	833.6	937.8	1035.4	1093.0
100°	1014.3	953.4	923.4	915.5	923.4	953.4	1014.3	1101.1	1175.0	1223.9	1204.0
102.5°	1227.5	1183.4	1151.9	1145.5	1151.9	1183.4	1227.5	1280.8	1311.6	1297.4	1198.4
105°	1432.6	1424.6	1410.6	1404.6	1410.6	1424.6	1432.6	1430.6	1389.6	1290.8	1118.1
107.5°	1465.5	1488.3	1498.3	1500.9	1498.3	1488.3	1465.5	1416.2	1327.2	1188.0	1004.1
110°	1433.6	1475.5	1493.5	1502.5	1493.5	1475.5	1433.6	1362.7	1252.9	1108.1	935.4



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1364.9	1415.6	1440.8	1455.3	1440.8	1415.6	1364.9	1284.4	1174.6	1037.8	885.1
115°	1248.9	1308.8	1340.7	1348.7	1340.7	1308.8	1248.9	1170.0	1074.2	957.4	834.6
117.5°	1151.9	1202.2	1234.5	1240.7	1234.5	1202.2	1151.9	1084.6	1003.3	911.5	809.8
120°	1099.1	1143.1	1169.0	1180.0	1169.0	1143.1	1099.1	1042.2	971.4	891.5	798.6
122.5°	1061.6	1099.1	1121.1	1132.1	1121.1	1099.1	1061.6	1013.5	951.4	878.7	789.1
125°	1022.3	1051.2	1070.2	1076.2	1070.2	1051.2	1022.3	982.3	927.4	858.5	772.7
127.5°	995.7	1021.5	1037.4	1043.4	1037.4	1021.5	995.7	955.6	903.5	834.8	752.7
130°	977.3	1002.3	1018.3	1024.3	1018.3	1002.3	977.3	936.4	883.5	815.6	736.8
132.5°	953.4	981.5	996.7	1002.7	996.7	981.5	953.4	913.3	860.3	794.1	720.0
135°	912.5	940.4	956.4	962.4	956.4	940.4	912.5	872.5	822.6	761.7	696.8
137.5°	864.5	892.1	905.3	912.5	905.3	892.1	864.5	827.2	782.1	730.8	675.9
140°	832.6	854.6	868.5	876.5	868.5	854.6	832.6	797.6	755.7	710.8	663.9
142.5°	799.8	820.2	832.6	838.2	832.6	820.2	799.8	768.9	732.6	694.0	652.7
145°	753.7	770.7	780.7	785.7	780.7	770.7	753.7	728.8	700.8	670.9	636.9
147.5°	715.2	729.8	737.4	739.1	737.4	729.8	715.2	696.8	674.9	650.9	623.9
150°	692.8	705.8	711.8	712.8	711.8	705.8	692.8	676.9	658.9	638.9	616.0
152.5°	673.7	684.2	687.8	688.8	687.8	684.2	673.7	660.1	645.3	626.9	607.2
155°	646.9	654.9	657.9	657.9	657.9	654.9	646.9	636.9	624.9	610.0	594.0
157.5°	622.9	628.9	630.7	630.7	630.7	628.9	622.9	615.4	605.8	593.2	579.8
160°	607.0	613.0	614.0	614.0	614.0	613.0	607.0	601.0	593.0	582.0	571.0
162.5°	591.8	597.8	598.8	598.0	598.8	597.8	591.8	587.4	580.2	571.6	562.2
165°	572.0	576.0	575.0	574.0	575.0	576.0	572.0	568.0	563.0	556.1	550.1
167.5°	553.5	556.1	555.9	555.1	555.9	556.1	553.5	551.5	548.5	542.9	538.3
170°	543.1	544.1	543.1	543.1	543.1	544.1	543.1	541.1	538.1	534.1	531.1
172.5°	532.7	533.7	532.7	531.1	532.7	533.7	532.7	531.5	529.3	526.9	524.7
175°	519.1	521.1	519.1	517.1	519.1	521.1	519.1	519.1	519.1	517.1	516.1
177.5°	511.3	512.1	510.5	508.9	510.5	512.1	511.3	512.1	511.3	511.3	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1262.6	1265.6	1272.4	1280.0	1286.4	1291.9	1296.2	1302.1	1307.7	1315.3	1322.6
5°	1186.0	1193.4	1204.1	1216.8	1232.8	1243.4	1256.7	1268.4	1285.4	1302.5	1319.0
7.5°	1118.8	1127.0	1142.6	1160.3	1179.2	1196.6	1212.4	1233.0	1255.6	1280.3	1308.0
10°	1075.4	1084.4	1103.0	1123.2	1145.6	1162.6	1183.9	1208.3	1233.9	1264.2	1298.2
12.5°	1036.2	1044.8	1067.3	1087.9	1111.1	1129.8	1154.5	1179.4	1213.4	1246.3	1285.0
15°	960.0	982.8	1008.4	1032.8	1060.5	1083.4	1113.1	1138.7	1171.1	1217.4	1261.5
17.5°	875.3	899.7	931.4	969.1	1006.2	1034.5	1064.7	1096.4	1135.0	1182.3	1233.2
20°	825.9	845.6	880.7	922.7	965.8	1005.2	1032.8	1067.9	1107.8	1158.9	1211.5
22.5°	788.9	805.6	833.1	875.1	921.6	967.3	1002.6	1037.3	1081.4	1132.5	1189.8
25°	733.4	751.5	775.4	804.1	857.3	905.7	952.0	991.9	1038.7	1089.7	1153.6
27.5°	687.2	703.0	724.9	754.8	790.5	843.9	900.0	945.5	993.5	1048.3	1112.2
30°	660.0	672.8	690.9	721.2	755.2	803.1	860.0	913.2	961.6	1018.5	1084.9
32.5°	631.5	645.1	662.8	686.7	723.3	763.5	820.4	878.7	930.1	988.3	1053.5
35°	593.5	604.2	620.1	644.6	677.6	712.7	763.2	823.3	877.5	939.8	1002.0
37.5°	555.1	567.7	580.2	602.0	629.1	666.8	708.2	769.6	829.7	886.5	947.2
40°	533.4	540.9	554.7	572.3	601.0	634.5	673.3	733.4	793.5	849.9	911.0
42.5°	509.2	517.5	529.2	546.7	572.5	605.1	643.1	695.1	757.8	812.4	868.1
45°	475.5	480.2	491.9	506.8	528.1	561.1	596.2	642.5	701.5	753.6	802.5
47.5°	441.4	445.6	452.9	466.5	490.4	516.8	549.7	591.2	643.0	695.1	736.5
50°	418.0	421.7	428.7	441.4	462.7	488.8	521.2	558.4	604.7	654.7	689.3
52.5°	394.6	396.6	403.1	417.6	435.5	461.1	490.1	524.4	567.7	609.2	644.2
55°	357.4	362.2	366.4	377.1	394.1	418.6	444.6	477.1	510.6	545.7	575.4
57.5°	318.6	323.8	330.0	339.3	352.8	375.6	399.0	425.3	453.9	483.0	508.0
60°	293.0	297.8	303.1	313.8	326.0	344.1	369.6	392.5	414.3	440.9	465.9
62.5°	267.9	272.7	278.9	287.4	299.2	316.4	337.7	357.6	380.3	403.5	422.1
65°	230.8	234.5	239.3	247.3	258.5	273.9	291.4	306.9	327.1	344.1	361.1
67.5°	190.1	197.2	203.5	210.0	219.4	233.8	246.5	261.2	275.0	287.6	303.1
70°	163.3	171.3	177.1	184.0	193.1	205.3	217.5	227.6	238.8	251.0	264.9
72.5°	140.7	147.0	151.6	158.9	167.1	178.5	189.9	198.3	207.3	215.7	229.1
75°	111.2	113.8	117.0	122.9	130.3	138.8	147.9	155.3	160.6	168.1	177.6
77.5°	79.9	85.0	87.1	91.3	96.6	101.9	107.9	114.1	119.2	121.9	129.2
80°	61.2	63.3	65.4	71.3	74.5	79.8	84.0	89.9	92.0	94.7	101.6
82.5°	47.5	48.8	50.1	51.7	53.6	58.9	63.2	66.9	69.0	70.0	75.2
85°	27.7	28.2	28.7	29.3	29.8	29.8	31.9	34.6	38.3	38.3	39.9
87.5°	12.8	13.4	13.0	12.2	13.0	11.8	12.2	12.0	13.1	13.8	14.7
90°	17.0	18.0	16.0	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0
92.5°	263.8	316.7	277.1	201.7	124.2	73.5	52.7	38.1	26.0	16.6	11.4
95°	836.6	813.6	614.0	375.4	211.6	124.8	82.9	58.9	45.9	35.9	32.9
97.5°	1051.0	856.9	574.6	337.4	202.3	135.4	100.2	79.7	67.7	59.1	59.1
100°	1058.2	802.6	521.1	317.5	204.7	145.8	113.8	94.8	82.9	75.9	75.9
102.5°	998.3	734.8	485.2	311.9	212.6	159.3	129.0	110.8	99.6	93.4	91.8
105°	889.5	654.9	454.2	314.5	231.6	183.7	154.7	136.8	124.8	119.8	116.8
107.5°	801.6	610.2	448.6	329.2	253.8	209.8	181.3	164.1	151.3	146.4	144.4
110°	757.7	595.0	450.2	340.4	270.5	226.6	199.7	181.7	169.7	164.7	162.7



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	733.0	587.8	455.0	352.4	286.5	244.2	217.2	199.3	188.1	182.3	180.3
115°	709.8	584.0	464.2	371.4	311.5	271.5	244.6	225.6	215.6	208.6	205.7
117.5°	699.4	583.0	474.0	390.7	335.6	297.7	269.7	252.0	241.0	234.8	232.0
120°	693.8	583.0	481.2	404.3	352.4	314.5	286.5	269.5	258.6	251.6	249.6
122.5°	687.4	582.2	488.4	417.1	368.4	330.4	303.3	284.7	274.5	267.5	265.6
125°	676.9	581.0	499.2	436.3	390.3	354.4	326.4	307.5	296.5	290.5	286.5
127.5°	662.7	578.8	507.7	452.8	410.7	376.0	347.8	328.0	315.5	308.3	305.1
130°	653.9	578.0	514.1	463.2	424.3	390.3	361.4	342.4	327.4	319.5	315.5
132.5°	645.9	577.2	519.7	473.6	435.5	401.5	374.2	353.6	339.4	329.0	325.8
135°	633.9	576.0	528.1	487.2	451.2	418.3	392.3	371.4	354.4	344.4	340.4
137.5°	623.5	575.8	533.1	496.8	463.2	432.5	407.7	385.9	369.8	358.8	355.0
140°	618.0	575.0	537.1	503.1	471.2	441.3	417.3	396.3	379.4	368.4	365.4
142.5°	613.2	575.0	540.3	507.9	478.4	449.2	426.1	405.9	389.7	379.6	376.6
145°	605.0	573.0	542.1	513.1	486.2	460.2	438.3	419.3	405.3	395.3	392.3
147.5°	597.6	569.4	543.1	517.7	494.2	469.8	450.0	434.3	419.9	411.1	410.1
150°	592.0	567.0	543.1	520.1	498.2	476.2	457.2	442.3	430.3	422.3	421.3
152.5°	585.6	563.0	541.5	521.7	501.4	481.8	464.4	451.0	439.9	431.9	431.7
155°	576.0	557.1	539.1	523.1	506.1	489.2	474.2	463.2	453.2	447.2	446.2
157.5°	566.2	550.9	536.5	523.1	509.5	495.2	483.4	473.8	466.0	460.4	460.4
160°	559.1	546.1	534.1	523.1	511.1	499.2	488.2	480.2	473.2	469.2	469.2
162.5°	552.7	541.3	531.7	523.1	512.7	501.6	493.0	485.8	479.6	476.4	477.2
165°	542.1	534.1	527.1	521.1	513.1	504.1	498.2	493.2	488.2	486.2	486.2
167.5°	532.5	526.9	522.3	518.7	512.9	506.3	501.8	499.0	495.2	494.2	495.2
170°	526.1	522.1	519.1	517.1	512.1	507.1	504.1	502.2	499.2	498.2	499.2
172.5°	520.5	517.3	515.9	515.5	511.3	507.9	505.7	504.5	502.3	502.2	503.1
175°	514.1	512.1	512.1	513.1	510.1	508.1	508.1	507.1	506.1	506.1	507.1
177.5°	509.7	508.9	508.9	510.5	508.9	508.1	508.1	508.1	507.3	508.1	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1328.1	1331.9	1336.2	1344.3	1351.1	1354.1	1360.0	1364.3	1363.0	1368.9	1379.2
5°	1333.3	1347.7	1364.2	1381.2	1400.3	1416.3	1429.0	1441.8	1451.9	1464.1	1482.2
7.5°	1332.5	1358.0	1385.8	1416.3	1447.7	1474.8	1499.9	1525.4	1548.1	1572.9	1605.3
10°	1329.1	1363.1	1397.7	1437.6	1477.4	1515.2	1549.2	1581.2	1611.5	1643.9	1684.9
12.5°	1325.2	1364.4	1406.2	1454.1	1503.8	1549.2	1589.2	1635.2	1673.2	1715.0	1762.3
15°	1308.3	1361.0	1417.9	1480.1	1539.7	1600.8	1655.6	1712.0	1764.6	1814.6	1874.2
17.5°	1289.0	1349.7	1416.8	1490.3	1561.9	1636.2	1701.2	1772.3	1826.1	1893.2	1948.5
20°	1273.2	1338.6	1410.4	1492.9	1574.2	1656.7	1728.5	1800.8	1861.4	1929.0	1999.2
22.5°	1254.1	1325.9	1403.6	1489.0	1574.2	1664.3	1743.8	1815.7	1890.8	1966.8	2039.2
25°	1223.2	1297.7	1380.1	1473.7	1571.6	1663.6	1748.7	1838.0	1918.9	2001.3	2066.2
27.5°	1185.4	1263.5	1350.4	1447.0	1547.4	1641.7	1741.9	1837.1	1918.4	1997.8	2054.4
30°	1155.1	1237.6	1321.1	1418.9	1523.2	1624.2	1731.7	1826.9	1912.5	1983.8	2015.7
32.5°	1124.1	1202.3	1288.3	1387.5	1494.2	1603.0	1709.5	1806.9	1886.1	1928.9	1929.7
35°	1070.1	1143.4	1232.8	1330.1	1439.7	1557.8	1665.7	1761.4	1809.8	1813.6	1761.4
37.5°	1011.1	1078.5	1162.8	1260.2	1380.2	1497.7	1608.0	1671.8	1687.9	1633.8	1537.4
40°	969.0	1031.2	1112.6	1212.6	1331.7	1453.0	1553.5	1600.3	1583.3	1495.5	1388.1
42.5°	924.8	982.7	1061.1	1159.8	1279.4	1401.9	1487.5	1512.7	1467.6	1366.2	1240.5
45°	852.5	905.7	983.4	1082.8	1197.7	1312.6	1377.5	1364.7	1289.7	1169.5	1028.6
47.5°	777.3	828.7	898.6	990.6	1108.2	1207.4	1251.3	1212.8	1106.1	973.9	859.2
50°	727.6	780.2	844.6	932.3	1039.7	1135.5	1163.7	1105.2	986.6	859.4	754.1
52.5°	678.6	723.6	786.7	871.5	974.2	1055.1	1070.1	1002.6	880.2	766.3	672.9
55°	604.2	645.1	698.3	778.1	866.9	935.5	927.5	840.8	729.7	632.4	559.0
57.5°	532.2	563.0	612.1	686.9	764.9	810.9	781.8	707.9	604.3	524.6	462.7
60°	484.5	513.2	559.0	624.4	693.0	719.0	694.6	614.3	532.4	459.5	407.4
62.5°	439.4	464.7	504.1	564.8	620.2	635.7	609.5	539.4	465.6	403.3	360.2
65°	373.9	397.3	430.8	473.9	512.2	519.6	502.6	430.8	374.9	322.8	293.0
67.5°	314.4	329.7	355.9	393.1	413.5	417.8	384.9	339.8	290.6	258.6	236.1
70°	274.4	285.1	309.5	329.7	346.2	346.8	316.4	280.3	242.5	216.5	200.0
72.5°	235.7	245.9	264.4	278.3	290.9	286.8	259.0	230.5	200.0	180.3	168.1
75°	181.9	190.9	200.5	206.9	206.9	201.6	181.4	160.1	142.5	130.8	127.1
77.5°	132.2	139.7	142.9	141.9	140.0	131.7	118.9	105.0	98.7	93.2	90.4
80°	103.7	106.9	108.0	105.3	102.1	92.5	84.0	78.2	72.3	70.2	69.1
82.5°	76.9	79.7	76.9	77.6	70.6	62.8	58.1	56.1	53.6	52.8	51.7
85°	41.0	40.4	39.4	36.7	31.9	30.8	30.3	29.8	28.7	29.3	28.2
87.5°	14.6	14.0	12.5	12.2	12.2	12.6	13.0	13.4	13.8	13.2	14.2
90°	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0
92.5°	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8	196.1
95°	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6	739.7
97.5°	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0	1093.0
100°	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2	1204.0
102.5°	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3	1198.4
105°	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5	1118.1
107.5°	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6	1004.1
110°	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7	935.4



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0	885.1
115°	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8	834.6
117.5°	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4	809.8
120°	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8	798.6
122.5°	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4	789.1
125°	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9	772.7
127.5°	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7	752.7
130°	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9	736.8
132.5°	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9	720.0
135°	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9	696.8
137.5°	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5	675.9
140°	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0	663.9
142.5°	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2	652.7
145°	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0	636.9
147.5°	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6	623.9
150°	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0	616.0
152.5°	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6	607.2
155°	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0	594.0
157.5°	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2	579.8
160°	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1	571.0
162.5°	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7	562.2
165°	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1	550.1
167.5°	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5	538.3
170°	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1	531.1
172.5°	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5	524.7
175°	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1	516.1
177.5°	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7	510.5
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0	1320.0
2.5°	1384.7	1386.4	1387.7	1391.9	1392.3	1396.2	1392.3
5°	1499.2	1506.7	1518.4	1530.1	1531.2	1538.6	1525.3
7.5°	1627.7	1645.0	1655.7	1674.6	1682.1	1686.8	1679.1
10°	1716.2	1732.2	1760.4	1774.2	1788.0	1790.2	1783.8
12.5°	1801.8	1827.1	1849.3	1875.5	1874.8	1893.6	1886.7
15°	1915.7	1941.7	1972.6	2001.8	2012.5	2012.5	2021.0
17.5°	1996.9	2044.7	2076.6	2099.6	2124.7	2129.0	2126.1
20°	2051.8	2103.4	2137.5	2167.2	2184.3	2189.0	2189.0
22.5°	2092.7	2136.6	2169.8	2196.6	2210.6	2216.3	2214.6
25°	2121.0	2158.7	2178.9	2186.9	2190.6	2189.6	2179.5
27.5°	2082.2	2080.5	2067.8	2043.3	2024.9	2013.7	2001.0
30°	2008.2	1980.6	1948.7	1913.5	1868.3	1833.8	1823.1
32.5°	1898.0	1835.9	1781.9	1723.4	1674.8	1640.2	1625.7
35°	1684.9	1586.5	1506.2	1436.0	1384.9	1353.0	1342.4
37.5°	1431.9	1336.7	1237.3	1169.2	1126.9	1094.6	1082.6
40°	1271.1	1167.4	1080.7	1016.9	973.3	941.9	941.4
42.5°	1124.3	1025.3	943.7	897.7	850.7	830.0	829.9
45°	920.6	841.4	772.2	736.1	707.9	690.9	686.1
47.5°	762.2	696.7	650.6	621.8	598.8	588.0	581.0
50°	673.3	615.9	579.2	554.2	541.4	527.6	526.5
52.5°	599.3	552.9	524.3	504.0	487.8	479.5	479.7
55°	503.6	467.0	446.7	431.3	418.6	412.2	409.5
57.5°	424.3	396.8	382.1	367.9	362.5	357.5	356.1
60°	374.9	356.3	342.5	331.3	323.4	321.8	321.2
62.5°	334.1	314.6	305.1	296.4	290.6	288.1	287.2
65°	275.5	261.1	252.6	245.7	243.6	239.9	239.3
67.5°	222.1	213.5	207.8	203.1	200.2	200.0	200.0
70°	189.3	184.5	179.8	177.1	175.5	174.4	174.4
72.5°	161.3	157.7	153.8	152.4	152.1	151.0	150.6
75°	122.9	119.1	119.7	117.0	114.9	112.2	110.6
77.5°	87.1	84.5	83.9	83.6	81.8	81.5	82.3
80°	67.5	64.9	64.4	64.9	64.4	62.8	62.8
82.5°	51.4	49.1	48.6	48.3	47.8	48.3	47.4
85°	27.7	26.6	26.6	26.6	27.7	27.1	26.6
87.5°	13.6	13.4	13.8	13.6	13.8	13.1	13.6
90°	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332945

CATALOG NUMBER: S124RDIP-S795D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)