

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332519-935

Luminaire Tested: **S124DIP-S350D1035U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332519-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1035U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4541.6 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	33	32	25				
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27	22				
3	78	69	62	56	69	62	56	51	49	45	42	37	35	32	26	25	23	18				
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	30	30	27	24	21	19	18	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	19	17	15	12				
7	55	44	36	31	50	39	33	28	32	27	23	24	21	18	18	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3971	3971	3971	3971
5°	4676	3981	3514	3981
10°	5599	3963	3163	3963
15°	6624	3924	2906	3924
20°	7377	3882	2674	3882
25°	7496	3822	2515	3822
30°	6378	3765	2466	3765
35°	4904	3671	2466	3671
40°	3822	3561	2512	3561
45°	3186	3394	2555	3394
50°	2804	3191	2641	3191
55°	2570	2949	2747	2949
60°	2407	2730	2876	2730
65°	2243	2487	2982	2487
70°	2049	2245	3050	2245
75°	1831	1978	3013	1978
80°	1534	1623	2920	1623
85°	1130	1176	2788	1176



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	1.1
10°-20°	147.7	3.3
20°-30°	234.2	5.2
30°-40°	260.7	5.7
40°-50°	237.3	5.2
50°-60°	193.9	4.3
60°-70°	138.4	3.0
70°-80°	76.2	1.7
80°-90°	23.2	0.5
90°-100°	316.0	7.0
100°-110°	657.7	14.5
110°-120°	589.1	13.0
120°-130°	495.5	10.9
130°-140°	413.2	9.1
140°-150°	315.7	7.0
150°-160°	221.9	4.9
160°-170°	130.5	2.9
170°-180°	42.5	0.9
0°-30°	429.9	9.5
0°-40°	690.5	15.2
0°-60°	1121.7	24.7
0°-90°	1359.6	29.9
90°-120°	1562.8	34.4
90°-150°	2787.1	61.4
90°-180°	3182.0	70.1
0°-180°	4541.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	492	492	492	492	492	
5°	577	491	434	491	577	59
15°	793	470	348	470	793	224
25°	842	429	282	429	842	371
35°	498	372	250	372	498	316
45°	279	297	224	297	279	220
55°	183	210	195	210	183	165
65°	117	130	156	130	117	116
75°	59	63	97	63	59	62
85°	12	13	30	13	12	15
90°	18	1	18	1	18	15
95°	210	28	210	28	210	325
105°	1209	101	1209	101	1209	1196
115°	1161	177	1161	177	1161	1153
125°	927	247	927	247	927	842
135°	829	293	829	293	829	640
145°	676	338	676	338	676	429
155°	566	384	566	384	566	264
165°	494	419	494	419	494	142
175°	445	437	445	437	445	43
180°	438	438	438	438	438	



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	523.5	523.4	521.8	521.4	520.3	518.8	518.5	515.8	510.7	508.2	507.6
5°	577.0	581.2	575.8	574.8	574.2	567.5	564.0	560.0	550.6	545.1	540.8
7.5°	641.0	641.4	639.1	637.3	632.1	626.2	617.4	608.0	596.8	585.3	576.5
10°	683.0	684.7	682.0	681.7	671.2	664.7	651.7	640.7	628.0	614.0	601.2
12.5°	727.4	725.1	723.8	715.1	713.1	701.2	686.0	674.8	655.2	639.0	622.0
15°	792.6	788.2	785.3	773.4	767.4	750.9	734.8	722.4	696.9	672.6	654.3
17.5°	831.0	835.4	828.9	823.9	808.7	797.0	780.6	754.5	734.6	704.5	681.3
20°	858.7	859.1	855.4	850.3	838.4	823.6	805.7	777.2	753.4	723.4	691.6
22.5°	866.2	866.3	864.7	860.0	850.8	839.0	820.9	797.0	768.2	735.6	703.8
25°	841.5	840.8	842.6	847.9	844.5	840.8	830.3	812.6	785.7	751.3	717.0
27.5°	750.1	755.8	766.1	779.1	791.7	801.2	803.9	800.3	783.7	755.4	719.5
30°	684.2	691.2	699.0	712.0	737.3	751.7	767.6	779.6	772.9	750.3	716.9
32.5°	611.9	613.6	625.1	639.9	663.1	690.9	716.1	740.5	748.6	736.8	708.9
35°	497.6	500.5	512.9	527.5	555.9	590.0	627.8	661.7	689.6	700.8	686.5
37.5°	406.0	414.2	423.0	438.8	463.7	494.4	533.7	577.6	619.1	647.0	651.8
40°	362.7	367.8	374.1	386.2	407.3	437.5	471.3	521.4	565.7	605.6	618.6
42.5°	328.5	331.5	335.4	346.2	362.3	392.4	423.3	467.4	511.7	559.5	581.3
45°	279.1	282.2	288.8	295.1	307.3	328.0	356.8	393.0	437.7	483.7	524.1
47.5°	243.6	245.5	249.3	256.1	266.6	280.3	303.6	333.9	375.2	420.0	463.0
50°	223.3	225.0	228.0	234.1	242.1	254.3	273.5	301.8	334.2	379.2	421.4
52.5°	207.3	208.0	210.3	214.4	220.8	231.0	246.8	270.2	300.3	340.4	382.5
55°	182.6	183.4	185.5	188.5	194.0	200.5	212.5	230.1	256.3	291.2	327.7
57.5°	162.2	162.8	164.5	165.7	170.2	175.5	184.8	197.3	217.1	246.8	279.3
60°	149.1	148.8	150.8	151.8	154.9	159.4	166.5	178.5	195.8	219.6	249.6
62.5°	136.5	135.9	137.6	139.0	140.7	144.5	150.3	159.7	173.8	195.4	221.3
65°	117.4	116.6	117.6	119.2	120.8	122.9	127.2	135.5	146.7	162.2	181.9
67.5°	98.2	99.1	99.3	100.0	101.0	103.8	106.7	112.6	120.5	132.9	149.6
70°	86.8	87.0	87.8	87.8	88.4	90.9	93.3	96.8	104.5	116.0	129.6
72.5°	75.4	76.3	75.9	76.5	77.1	78.7	80.4	83.8	90.3	98.8	110.4
75°	58.7	59.3	59.3	59.5	60.1	60.7	62.2	64.6	69.3	75.6	83.5
77.5°	42.8	42.9	43.1	43.9	43.9	44.9	45.9	47.9	50.2	54.5	59.4
80°	33.0	33.4	33.2	33.7	33.7	34.4	34.9	37.3	38.3	41.2	45.0
82.5°	24.2	24.6	24.5	25.1	25.5	25.7	26.2	27.2	28.2	30.7	32.3
85°	12.2	12.7	12.2	12.7	13.3	13.4	14.0	14.3	15.1	15.7	17.1
87.5°	7.2	7.7	7.8	7.8	8.0	8.2	8.2	7.8	8.3	8.6	9.0
90°	18.1	18.1	18.9	18.1	17.2	17.2	16.4	15.5	14.6	15.5	13.8
92.5°	66.2	66.2	69.1	73.8	83.9	101.1	127.1	168.8	227.1	272.7	238.6
95°	209.7	220.9	236.3	263.0	305.1	388.5	503.7	636.9	720.3	700.5	528.7
97.5°	560.6	578.5	604.2	656.0	717.7	807.4	891.5	941.1	904.9	737.8	494.7
100°	788.2	795.0	820.9	873.3	948.0	1011.7	1053.8	1036.6	911.1	691.0	448.7
102.5°	986.3	991.8	1018.9	1056.9	1102.8	1129.3	1117.1	1031.8	859.5	632.7	417.8
105°	1209.4	1214.5	1226.6	1233.5	1231.7	1196.4	1111.4	962.7	765.9	563.9	391.1
107.5°	1292.3	1290.0	1281.4	1261.8	1219.3	1142.7	1022.9	864.5	690.2	525.4	386.2
110°	1293.7	1285.9	1270.4	1234.3	1173.3	1078.7	954.1	805.4	652.4	512.3	387.6



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1253.0	1240.5	1218.8	1175.2	1105.9	1011.3	893.5	762.1	631.1	506.1	391.8
115°	1161.2	1154.3	1126.9	1075.3	1007.4	924.9	824.3	718.6	611.1	502.8	399.7
117.5°	1068.2	1062.9	1035.1	991.8	933.8	863.8	784.8	697.2	602.2	502.0	408.1
120°	1016.0	1006.5	984.2	946.3	897.3	836.4	767.6	687.6	597.4	502.0	414.3
122.5°	974.7	965.3	946.3	914.0	872.6	819.2	756.6	679.4	591.9	501.3	420.5
125°	926.6	921.4	905.1	880.2	845.8	798.5	739.2	665.3	582.8	500.2	429.8
127.5°	898.4	893.2	879.5	857.3	822.8	777.9	718.8	648.1	570.6	498.3	437.1
130°	881.9	876.8	863.0	841.5	806.2	760.7	702.2	634.4	563.0	497.7	442.6
132.5°	863.3	858.2	845.1	820.9	786.4	740.7	683.7	619.9	556.1	497.0	447.5
135°	828.6	823.5	809.7	785.7	751.2	708.3	655.8	599.9	545.8	495.9	454.7
137.5°	785.7	779.5	768.1	744.3	712.2	673.4	629.2	581.9	536.8	495.8	459.0
140°	754.7	747.8	735.8	716.9	686.7	650.7	612.0	571.6	532.1	495.1	462.4
142.5°	721.7	716.9	706.2	688.6	662.0	630.8	597.5	562.0	528.0	495.1	465.2
145°	676.5	672.2	663.6	648.9	627.5	603.4	577.6	548.4	520.9	493.4	466.7
147.5°	636.4	634.9	628.4	615.8	599.9	581.1	560.4	537.2	514.5	490.3	467.6
150°	613.7	612.9	607.7	596.5	582.8	567.3	550.1	530.4	509.7	488.2	467.6
152.5°	593.1	592.2	589.1	580.1	568.3	555.6	539.8	522.8	504.2	484.7	466.2
155°	566.5	566.5	563.9	557.0	548.4	538.0	525.2	511.4	495.9	479.7	464.2
157.5°	543.0	543.0	541.5	536.3	529.9	521.6	510.7	499.2	487.5	474.3	461.9
160°	528.7	528.7	527.8	522.6	517.5	510.6	501.1	491.6	481.4	470.2	459.9
162.5°	514.9	515.6	514.7	509.5	505.8	499.6	492.1	484.1	475.9	466.1	457.8
165°	494.2	495.1	495.9	492.5	489.0	484.7	478.8	473.6	466.7	459.9	453.8
167.5°	477.9	478.6	478.8	476.6	474.8	472.3	467.4	463.5	458.5	453.7	449.7
170°	467.6	467.6	468.5	467.6	465.9	463.3	459.9	457.3	453.0	449.5	446.9
172.5°	457.3	458.7	459.5	458.7	457.6	455.7	453.7	451.8	448.2	445.4	444.2
175°	445.2	446.9	448.7	446.9	446.9	446.9	445.2	444.4	442.6	440.9	440.9
177.5°	438.2	439.5	440.9	440.2	440.9	440.2	440.2	439.5	438.9	438.2	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	507.7	505.4	503.8	502.5	498.9	496.8	495.2	492.9	490.3	487.5	484.1
5°	536.5	529.6	524.5	516.8	509.5	503.3	497.0	491.3	484.4	476.8	471.3
7.5°	566.8	556.5	543.3	531.8	518.9	507.7	497.7	487.5	476.8	466.4	456.9
10°	586.1	572.8	558.1	540.8	524.5	510.1	496.6	483.5	470.9	458.3	447.5
12.5°	606.7	590.2	568.5	548.3	530.0	510.7	494.5	478.5	463.2	450.0	437.4
15°	634.6	610.7	585.7	558.5	534.5	511.9	489.7	469.5	452.4	434.8	422.6
17.5°	651.6	622.1	593.5	565.2	536.1	507.5	483.5	460.3	438.9	421.5	406.0
20°	662.9	633.5	597.9	569.6	534.9	505.6	477.9	451.9	429.6	411.0	395.1
22.5°	672.6	638.8	603.0	565.8	531.3	500.2	469.8	443.8	420.9	401.4	386.2
25°	678.0	639.0	600.3	563.2	524.1	487.2	459.7	429.1	404.7	384.1	367.8
27.5°	678.6	636.9	593.1	551.9	511.5	477.2	442.5	415.1	389.8	368.0	352.3
30°	676.7	633.4	586.3	541.7	501.1	463.8	433.6	403.9	378.0	356.4	340.1
32.5°	671.0	625.9	577.5	530.2	488.2	451.7	420.6	392.3	367.0	345.8	328.6
35°	654.5	609.8	558.4	509.2	466.2	429.4	401.2	372.5	347.2	327.1	310.6
37.5°	628.7	588.4	536.0	485.2	442.9	405.9	378.0	352.1	329.2	308.8	291.9
40°	606.2	570.8	518.1	468.6	423.0	387.8	361.7	337.9	315.2	295.8	279.7
42.5°	580.3	549.4	500.9	448.5	404.4	369.0	343.6	322.2	300.9	283.0	266.9
45°	534.1	513.7	468.0	419.6	373.7	340.3	316.1	297.3	279.4	261.8	248.4
47.5°	481.0	470.8	432.4	386.3	342.9	309.9	288.9	271.6	255.8	241.0	229.1
50°	445.2	440.3	407.2	362.7	321.2	290.2	269.0	254.1	240.6	227.6	216.4
52.5°	410.0	409.8	379.9	339.2	300.7	271.0	249.9	236.0	224.4	213.8	203.7
55°	356.2	361.9	338.5	302.2	267.8	240.8	221.9	209.5	201.3	192.6	185.0
57.5°	306.8	316.2	296.9	264.9	236.2	211.5	194.9	185.6	176.9	171.6	166.1
60°	274.5	283.4	268.4	241.5	214.4	193.2	177.5	169.1	161.6	157.9	154.0
62.5°	245.8	253.7	242.6	217.7	194.2	173.7	160.5	152.5	147.4	143.4	140.9
65°	204.8	211.5	201.9	183.8	163.6	147.3	136.6	130.2	125.4	123.7	120.8
67.5°	165.6	171.7	166.5	151.1	134.9	122.5	114.1	108.1	105.1	103.8	101.7
70°	142.2	148.4	142.8	129.4	116.9	106.6	98.6	95.1	92.1	91.5	88.7
72.5°	122.5	126.7	121.1	110.6	100.0	91.3	85.1	81.5	79.9	78.8	77.2
75°	91.9	95.6	91.9	83.8	76.2	70.1	64.8	63.4	61.6	61.0	59.9
77.5°	65.0	68.2	65.4	60.4	54.7	49.9	47.1	45.3	44.9	43.8	44.3
80°	49.7	51.7	49.1	45.6	41.2	37.9	35.9	34.9	33.7	33.2	34.0
82.5°	35.7	36.6	35.2	32.9	29.6	27.5	26.1	24.9	24.6	24.7	24.7
85°	18.5	18.3	18.2	16.1	15.1	13.7	12.8	12.7	12.4	12.8	13.3
87.5°	8.6	8.8	7.6	6.9	6.3	5.6	4.9	4.4	4.9	5.6	5.9
90°	12.1	12.1	6.9	6.9	6.0	5.2	2.6	0.9	2.6	5.2	6.0
92.5°	173.7	106.9	63.3	45.4	32.8	22.4	14.3	9.8	14.3	22.4	32.8
95°	323.2	182.2	107.5	71.4	50.7	39.5	30.9	28.3	30.9	39.5	50.7
97.5°	290.5	174.2	116.6	86.3	68.6	58.3	50.9	50.9	50.9	58.3	68.6
100°	273.4	176.2	125.5	98.0	81.6	71.4	65.3	65.3	65.3	71.4	81.6
102.5°	268.5	183.0	137.2	111.1	95.4	85.8	80.4	79.0	80.4	85.8	95.4
105°	270.8	199.4	158.2	133.2	117.8	107.5	103.1	100.6	103.1	107.5	117.8
107.5°	283.4	218.5	180.6	156.1	141.3	130.3	126.1	124.3	126.1	130.3	141.3
110°	293.1	232.9	195.1	171.9	156.4	146.1	141.8	140.1	141.8	146.1	156.4



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	303.4	246.7	210.3	187.0	171.6	162.0	157.0	155.2	157.0	162.0	171.6
115°	319.8	268.2	233.8	210.6	194.2	185.6	179.6	177.1	179.6	185.6	194.2
117.5°	336.4	289.0	256.3	232.2	217.0	207.5	202.2	199.8	202.2	207.5	217.0
120°	348.1	303.4	270.8	246.7	232.0	222.7	216.6	214.9	216.6	222.7	232.0
122.5°	359.1	317.2	284.5	261.1	245.1	236.3	230.3	228.7	230.3	236.3	245.1
125°	375.7	336.0	305.1	281.0	264.8	255.3	250.1	246.7	250.1	255.3	264.8
127.5°	389.9	353.6	323.7	299.5	282.4	271.6	265.4	262.7	265.4	271.6	282.4
130°	398.8	365.3	336.0	311.2	294.8	281.9	275.1	271.6	275.1	281.9	294.8
132.5°	407.8	375.0	345.7	322.2	304.4	292.2	283.3	280.5	283.3	292.2	304.4
135°	419.5	388.5	360.2	337.8	319.8	305.1	296.5	293.1	296.5	305.1	319.8
137.5°	427.7	398.8	372.4	351.0	332.3	318.4	308.9	305.7	308.9	318.4	332.3
140°	433.2	405.7	380.0	359.3	341.2	326.7	317.2	314.6	317.2	326.7	341.2
142.5°	437.3	411.9	386.8	366.9	349.5	335.5	326.8	324.3	326.8	335.5	349.5
145°	441.8	418.6	396.2	377.4	361.0	349.0	340.4	337.8	340.4	349.0	361.0
147.5°	445.7	425.5	404.5	387.4	373.9	361.5	354.0	353.1	354.0	361.5	373.9
150°	447.8	429.0	410.0	393.6	380.8	370.5	363.6	362.7	363.6	370.5	380.8
152.5°	449.2	431.7	414.8	399.8	388.3	378.8	371.9	371.7	371.9	378.8	388.3
155°	450.4	435.8	421.2	408.3	398.8	390.2	385.0	384.2	385.0	390.2	398.8
157.5°	450.4	438.7	426.4	416.2	407.9	401.2	396.4	396.4	396.4	401.2	407.9
160°	450.4	440.1	429.8	420.3	413.5	407.4	404.0	404.0	404.0	407.4	413.5
162.5°	450.4	441.4	431.9	424.5	418.3	412.9	410.2	410.9	410.2	412.9	418.3
165°	448.7	441.8	434.0	429.0	424.6	420.3	418.6	418.6	418.6	420.3	424.6
167.5°	446.6	441.6	435.9	432.0	429.6	426.4	425.5	426.4	425.5	426.4	429.6
170°	445.2	440.9	436.6	434.0	432.4	429.8	429.0	429.8	429.0	429.8	432.4
172.5°	443.8	440.2	437.3	435.4	434.4	432.5	432.4	433.2	432.4	432.5	434.4
175°	441.8	439.2	437.5	437.5	436.6	435.8	435.8	436.6	435.8	435.8	436.6
177.5°	439.5	438.2	437.5	437.5	437.5	436.8	437.5	438.2	437.5	436.8	437.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	482.4	481.0	478.9	476.0	473.5	470.9	470.2	469.2	471.2	469.6	469.1
5°	466.7	462.4	456.8	450.6	446.9	441.6	440.6	438.5	436.4	436.3	434.2
7.5°	449.9	443.6	436.4	430.0	424.0	418.2	414.4	413.6	410.6	408.8	406.8
10°	439.1	431.4	423.0	416.9	410.0	403.9	399.6	397.2	395.1	392.9	390.8
12.5°	426.5	418.2	411.3	404.7	396.5	391.8	384.8	380.6	380.1	380.1	374.9
15°	411.6	403.5	392.9	383.5	379.0	370.1	366.2	361.3	358.3	355.2	352.8
17.5°	394.7	384.5	376.3	365.5	357.0	349.8	344.7	341.8	337.2	332.9	329.8
20°	384.1	373.3	364.5	353.1	343.8	335.0	330.7	326.7	323.2	319.5	316.1
22.5°	373.3	362.1	351.4	340.3	331.6	322.3	318.1	312.6	309.4	307.3	303.8
25°	356.4	344.1	331.9	321.3	312.4	304.2	298.8	294.5	290.8	289.1	286.9
27.5°	337.9	325.8	314.0	302.0	291.8	285.9	281.5	278.3	276.1	274.0	272.9
30°	326.2	313.6	301.0	289.7	280.4	274.5	270.4	268.2	266.6	265.5	264.5
32.5°	314.4	301.9	288.6	278.4	269.9	264.7	261.6	259.3	258.6	258.2	257.8
35°	295.2	282.7	270.4	261.2	253.3	251.2	248.6	247.4	246.9	248.4	249.0
37.5°	276.8	265.1	253.8	245.0	239.7	236.8	235.8	235.9	237.4	238.6	240.0
40°	264.9	253.5	242.9	235.1	230.2	228.4	228.0	229.0	230.7	232.1	233.8
42.5°	253.3	242.1	232.5	225.2	221.8	220.1	220.3	221.4	223.7	225.4	227.8
45°	235.4	226.0	216.6	210.7	207.8	208.3	208.3	210.1	212.3	215.0	217.7
47.5°	218.4	209.0	201.3	196.3	194.8	194.5	195.6	198.0	201.2	204.5	208.2
50°	207.1	198.0	191.3	186.8	185.2	185.8	187.4	189.7	193.6	197.7	201.6
52.5°	195.4	187.3	181.1	176.9	175.7	176.8	178.5	182.0	185.5	189.9	194.5
55°	177.5	170.6	165.7	162.6	162.2	162.8	164.6	168.5	173.4	178.9	183.4
57.5°	159.6	153.8	149.3	147.2	147.4	148.0	151.0	155.6	160.8	166.7	172.5
60°	147.5	142.2	138.5	136.9	137.2	138.4	142.1	146.3	152.8	158.5	164.6
62.5°	136.1	131.5	127.9	126.5	126.2	128.9	132.4	136.8	143.4	149.7	156.4
65°	117.8	114.1	111.2	110.5	111.1	113.1	117.6	123.5	129.0	135.7	142.7
67.5°	99.9	96.9	94.9	95.2	96.0	99.0	102.7	107.8	114.1	121.1	127.9
70°	88.4	85.6	83.9	84.1	85.4	89.0	92.3	97.4	104.1	111.2	116.9
72.5°	76.7	74.8	73.4	74.2	75.4	77.9	82.1	87.1	93.1	99.7	105.7
75°	58.9	58.9	58.1	58.7	60.5	62.9	66.0	71.3	77.2	82.6	87.4
77.5°	43.7	43.2	43.7	44.5	45.5	48.5	52.0	55.8	60.2	65.5	69.6
80°	33.4	33.7	34.6	35.9	36.2	38.5	42.2	45.6	49.1	53.6	57.4
82.5°	25.1	25.3	25.8	27.4	27.8	30.2	32.5	36.0	39.2	42.2	45.4
85°	13.7	13.7	14.6	15.3	16.3	17.9	19.4	21.4	24.3	26.3	29.4
87.5°	6.6	6.6	8.3	8.6	9.5	10.6	10.8	12.7	13.5	14.6	16.0
90°	6.9	6.9	12.1	12.1	13.8	15.5	14.6	15.5	16.4	17.2	17.2
92.5°	45.4	63.3	106.9	173.7	238.6	272.7	227.1	168.8	127.1	101.1	83.9
95°	71.4	107.5	182.2	323.2	528.7	700.5	720.3	636.9	503.7	388.5	305.1
97.5°	86.3	116.6	174.2	290.5	494.7	737.8	904.9	941.1	891.5	807.4	717.7
100°	98.0	125.5	176.2	273.4	448.7	691.0	911.1	1036.6	1053.8	1011.7	948.0
102.5°	111.1	137.2	183.0	268.5	417.8	632.7	859.5	1031.8	1117.1	1129.3	1102.8
105°	133.2	158.2	199.4	270.8	391.1	563.9	765.9	962.7	1111.4	1196.4	1231.7
107.5°	156.1	180.6	218.5	283.4	386.2	525.4	690.2	864.5	1022.9	1142.7	1219.3
110°	171.9	195.1	232.9	293.1	387.6	512.3	652.4	805.4	954.1	1078.7	1173.3



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.0	210.3	246.7	303.4	391.8	506.1	631.1	762.1	893.5	1011.3	1105.9
115°	210.6	233.8	268.2	319.8	399.7	502.8	611.1	718.6	824.3	924.9	1007.4
117.5°	232.2	256.3	289.0	336.4	408.1	502.0	602.2	697.2	784.8	863.8	933.8
120°	246.7	270.8	303.4	348.1	414.3	502.0	597.4	687.6	767.6	836.4	897.3
122.5°	261.1	284.5	317.2	359.1	420.5	501.3	591.9	679.4	756.6	819.2	872.6
125°	281.0	305.1	336.0	375.7	429.8	500.2	582.8	665.3	739.2	798.5	845.8
127.5°	299.5	323.7	353.6	389.9	437.1	498.3	570.6	648.1	718.8	777.9	822.8
130°	311.2	336.0	365.3	398.8	442.6	497.7	563.0	634.4	702.2	760.7	806.2
132.5°	322.2	345.7	375.0	407.8	447.5	497.0	556.1	619.9	683.7	740.7	786.4
135°	337.8	360.2	388.5	419.5	454.7	495.9	545.8	599.9	655.8	708.3	751.2
137.5°	351.0	372.4	398.8	427.7	459.0	495.8	536.8	581.9	629.2	673.4	712.2
140°	359.3	380.0	405.7	433.2	462.4	495.1	532.1	571.6	612.0	650.7	686.7
142.5°	366.9	386.8	411.9	437.3	465.2	495.1	528.0	562.0	597.5	630.8	662.0
145°	377.4	396.2	418.6	441.8	466.7	493.4	520.9	548.4	577.6	603.4	627.5
147.5°	387.4	404.5	425.5	445.7	467.6	490.3	514.5	537.2	560.4	581.1	599.9
150°	393.6	410.0	429.0	447.8	467.6	488.2	509.7	530.4	550.1	567.3	582.8
152.5°	399.8	414.8	431.7	449.2	466.2	484.7	504.2	522.8	539.8	555.6	568.3
155°	408.3	421.2	435.8	450.4	464.2	479.7	495.9	511.4	525.2	538.0	548.4
157.5°	416.2	426.4	438.7	450.4	461.9	474.3	487.5	499.2	510.7	521.6	529.9
160°	420.3	429.8	440.1	450.4	459.9	470.2	481.4	491.6	501.1	510.6	517.5
162.5°	424.5	431.9	441.4	450.4	457.8	466.1	475.9	484.1	492.1	499.6	505.8
165°	429.0	434.0	441.8	448.7	453.8	459.9	466.7	473.6	478.8	484.7	489.0
167.5°	432.0	435.9	441.6	446.6	449.7	453.7	458.5	463.5	467.4	472.3	474.8
170°	434.0	436.6	440.9	445.2	446.9	449.5	453.0	457.3	459.9	463.3	465.9
172.5°	435.4	437.3	440.2	443.8	444.2	445.4	448.2	451.8	453.7	455.7	457.6
175°	437.5	437.5	439.2	441.8	440.9	440.9	442.6	444.4	445.2	446.9	446.9
177.5°	437.5	437.5	438.2	439.5	438.2	438.2	438.9	439.5	440.2	440.2	440.9
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	468.7	468.5	467.3	467.1	467.3	468.5	468.7	469.1	469.6	471.2	469.2
5°	433.0	432.0	431.4	433.6	431.4	432.0	433.0	434.2	436.3	436.4	438.5
7.5°	406.0	405.3	403.5	402.9	403.5	405.3	406.0	406.8	408.8	410.6	413.6
10°	388.8	388.0	386.3	385.9	386.3	388.0	388.8	390.8	392.9	395.1	397.2
12.5°	372.1	370.6	370.2	370.7	370.2	370.6	372.1	374.9	380.1	380.1	380.6
15°	350.1	349.2	347.0	347.7	347.0	349.2	350.1	352.8	355.2	358.3	361.3
17.5°	328.3	327.4	324.6	327.0	324.6	327.4	328.3	329.8	332.9	337.2	341.8
20°	314.6	313.0	311.6	311.3	311.6	313.0	314.6	316.1	319.5	323.2	326.7
22.5°	301.6	300.1	300.0	298.7	300.0	300.1	301.6	303.8	307.3	309.4	312.6
25°	285.2	283.9	283.4	282.4	283.4	283.9	285.2	286.9	289.1	290.8	294.5
27.5°	272.8	272.1	271.3	271.6	271.3	272.1	272.8	272.9	274.0	276.1	278.3
30°	265.1	264.9	264.5	264.5	264.5	264.9	265.1	264.5	265.5	266.6	268.2
32.5°	258.7	258.7	259.0	259.0	259.0	258.7	258.7	257.8	258.2	258.6	259.3
35°	249.9	250.5	250.8	250.2	250.8	250.5	249.9	249.0	248.4	246.9	247.4
37.5°	241.8	242.4	243.0	243.7	243.0	242.4	241.8	240.0	238.6	237.4	235.9
40°	235.6	236.9	237.4	238.4	237.4	236.9	235.6	233.8	232.1	230.7	229.0
42.5°	229.7	231.3	232.3	232.6	232.3	231.3	229.7	227.8	225.4	223.7	221.4
45°	220.7	222.3	223.8	223.8	223.8	222.3	220.7	217.7	215.0	212.3	210.1
47.5°	211.4	213.7	215.2	215.5	215.2	213.7	211.4	208.2	204.5	201.2	198.0
50°	205.0	207.8	209.3	210.3	209.3	207.8	205.0	201.6	197.7	193.6	189.7
52.5°	198.8	201.6	203.5	204.1	203.5	201.6	198.8	194.5	189.9	185.5	182.0
55°	188.0	192.2	194.4	195.2	194.4	192.2	188.0	183.4	178.9	173.4	168.5
57.5°	178.0	181.8	184.3	184.9	184.3	181.8	178.0	172.5	166.7	160.8	155.6
60°	170.1	174.3	177.5	178.1	177.5	174.3	170.1	164.6	158.5	152.8	146.3
62.5°	162.1	166.4	169.4	170.9	169.4	166.4	162.1	156.4	149.7	143.4	136.8
65°	148.4	152.7	155.5	156.1	155.5	152.7	148.4	142.7	135.7	129.0	123.5
67.5°	133.3	137.6	139.4	140.6	139.4	137.6	133.3	127.9	121.1	114.1	107.8
70°	122.7	126.1	128.2	129.2	128.2	126.1	122.7	116.9	111.2	104.1	97.4
72.5°	110.6	114.3	116.6	116.8	116.6	114.3	110.6	105.7	99.7	93.1	87.1
75°	92.1	95.4	96.6	96.6	96.6	95.4	92.1	87.4	82.6	77.2	71.3
77.5°	72.9	74.6	76.1	76.5	76.1	74.6	72.9	69.6	65.5	60.2	55.8
80°	60.5	61.6	62.8	62.8	62.8	61.6	60.5	57.4	53.6	49.1	45.6
82.5°	47.8	48.6	49.9	49.7	49.9	48.6	47.8	45.4	42.2	39.2	36.0
85°	28.9	30.7	30.6	30.1	30.6	30.7	28.9	29.4	26.3	24.3	21.4
87.5°	16.6	17.0	17.3	17.7	17.3	17.0	16.6	16.0	14.6	13.5	12.7
90°	18.1	18.9	18.1	18.1	18.1	18.9	18.1	17.2	17.2	16.4	15.5
92.5°	73.8	69.1	66.2	66.2	66.2	69.1	73.8	83.9	101.1	127.1	168.8
95°	263.0	236.3	220.9	209.7	220.9	236.3	263.0	305.1	388.5	503.7	636.9
97.5°	656.0	604.2	578.5	560.6	578.5	604.2	656.0	717.7	807.4	891.5	941.1
100°	873.3	820.9	795.0	788.2	795.0	820.9	873.3	948.0	1011.7	1053.8	1036.6
102.5°	1056.9	1018.9	991.8	986.3	991.8	1018.9	1056.9	1102.8	1129.3	1117.1	1031.8
105°	1233.5	1226.6	1214.5	1209.4	1214.5	1226.6	1233.5	1231.7	1196.4	1111.4	962.7
107.5°	1261.8	1281.4	1290.0	1292.3	1290.0	1281.4	1261.8	1219.3	1142.7	1022.9	864.5
110°	1234.3	1270.4	1285.9	1293.7	1285.9	1270.4	1234.3	1173.3	1078.7	954.1	805.4



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1175.2	1218.8	1240.5	1253.0	1240.5	1218.8	1175.2	1105.9	1011.3	893.5	762.1
115°	1075.3	1126.9	1154.3	1161.2	1154.3	1126.9	1075.3	1007.4	924.9	824.3	718.6
117.5°	991.8	1035.1	1062.9	1068.2	1062.9	1035.1	991.8	933.8	863.8	784.8	697.2
120°	946.3	984.2	1006.5	1016.0	1006.5	984.2	946.3	897.3	836.4	767.6	687.6
122.5°	914.0	946.3	965.3	974.7	965.3	946.3	914.0	872.6	819.2	756.6	679.4
125°	880.2	905.1	921.4	926.6	921.4	905.1	880.2	845.8	798.5	739.2	665.3
127.5°	857.3	879.5	893.2	898.4	893.2	879.5	857.3	822.8	777.9	718.8	648.1
130°	841.5	863.0	876.8	881.9	876.8	863.0	841.5	806.2	760.7	702.2	634.4
132.5°	820.9	845.1	858.2	863.3	858.2	845.1	820.9	786.4	740.7	683.7	619.9
135°	785.7	809.7	823.5	828.6	823.5	809.7	785.7	751.2	708.3	655.8	599.9
137.5°	744.3	768.1	779.5	785.7	779.5	768.1	744.3	712.2	673.4	629.2	581.9
140°	716.9	735.8	747.8	754.7	747.8	735.8	716.9	686.7	650.7	612.0	571.6
142.5°	688.6	706.2	716.9	721.7	716.9	706.2	688.6	662.0	630.8	597.5	562.0
145°	648.9	663.6	672.2	676.5	672.2	663.6	648.9	627.5	603.4	577.6	548.4
147.5°	615.8	628.4	634.9	636.4	634.9	628.4	615.8	599.9	581.1	560.4	537.2
150°	596.5	607.7	612.9	613.7	612.9	607.7	596.5	582.8	567.3	550.1	530.4
152.5°	580.1	589.1	592.2	593.1	592.2	589.1	580.1	568.3	555.6	539.8	522.8
155°	557.0	563.9	566.5	566.5	566.5	563.9	557.0	548.4	538.0	525.2	511.4
157.5°	536.3	541.5	543.0	543.0	543.0	541.5	536.3	529.9	521.6	510.7	499.2
160°	522.6	527.8	528.7	528.7	528.7	527.8	522.6	517.5	510.6	501.1	491.6
162.5°	509.5	514.7	515.6	514.9	515.6	514.7	509.5	505.8	499.6	492.1	484.1
165°	492.5	495.9	495.1	494.2	495.1	495.9	492.5	489.0	484.7	478.8	473.6
167.5°	476.6	478.8	478.6	477.9	478.6	478.8	476.6	474.8	472.3	467.4	463.5
170°	467.6	468.5	467.6	467.6	467.6	468.5	467.6	465.9	463.3	459.9	457.3
172.5°	458.7	459.5	458.7	457.3	458.7	459.5	458.7	457.6	455.7	453.7	451.8
175°	446.9	448.7	446.9	445.2	446.9	448.7	446.9	446.9	446.9	445.2	444.4
177.5°	440.2	440.9	439.5	438.2	439.5	440.9	440.2	440.9	440.2	440.2	439.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	470.2	470.9	473.5	476.0	478.9	481.0	482.4	484.1	487.5	490.3	492.9
5°	440.6	441.6	446.9	450.6	456.8	462.4	466.7	471.3	476.8	484.4	491.3
7.5°	414.4	418.2	424.0	430.0	436.4	443.6	449.9	456.9	466.4	476.8	487.5
10°	399.6	403.9	410.0	416.9	423.0	431.4	439.1	447.5	458.3	470.9	483.5
12.5°	384.8	391.8	396.5	404.7	411.3	418.2	426.5	437.4	450.0	463.2	478.5
15°	366.2	370.1	379.0	383.5	392.9	403.5	411.6	422.6	434.8	452.4	469.5
17.5°	344.7	349.8	357.0	365.5	376.3	384.5	394.7	406.0	421.5	438.9	460.3
20°	330.7	335.0	343.8	353.1	364.5	373.3	384.1	395.1	411.0	429.6	451.9
22.5°	318.1	322.3	331.6	340.3	351.4	362.1	373.3	386.2	401.4	420.9	443.8
25°	298.8	304.2	312.4	321.3	331.9	344.1	356.4	367.8	384.1	404.7	429.1
27.5°	281.5	285.9	291.8	302.0	314.0	325.8	337.9	352.3	368.0	389.8	415.1
30°	270.4	274.5	280.4	289.7	301.0	313.6	326.2	340.1	356.4	378.0	403.9
32.5°	261.6	264.7	269.9	278.4	288.6	301.9	314.4	328.6	345.8	367.0	392.3
35°	248.6	251.2	253.3	261.2	270.4	282.7	295.2	310.6	327.1	347.2	372.5
37.5°	235.8	236.8	239.7	245.0	253.8	265.1	276.8	291.9	308.8	329.2	352.1
40°	228.0	228.4	230.2	235.1	242.9	253.5	264.9	279.7	295.8	315.2	337.9
42.5°	220.3	220.1	221.8	225.2	232.5	242.1	253.3	266.9	283.0	300.9	322.2
45°	208.3	208.3	207.8	210.7	216.6	226.0	235.4	248.4	261.8	279.4	297.3
47.5°	195.6	194.5	194.8	196.3	201.3	209.0	218.4	229.1	241.0	255.8	271.6
50°	187.4	185.8	185.2	186.8	191.3	198.0	207.1	216.4	227.6	240.6	254.1
52.5°	178.5	176.8	175.7	176.9	181.1	187.3	195.4	203.7	213.8	224.4	236.0
55°	164.6	162.8	162.2	162.6	165.7	170.6	177.5	185.0	192.6	201.3	209.5
57.5°	151.0	148.0	147.4	147.2	149.3	153.8	159.6	166.1	171.6	176.9	185.6
60°	142.1	138.4	137.2	136.9	138.5	142.2	147.5	154.0	157.9	161.6	169.1
62.5°	132.4	128.9	126.2	126.5	127.9	131.5	136.1	140.9	143.4	147.4	152.5
65°	117.6	113.1	111.1	110.5	111.2	114.1	117.8	120.8	123.7	125.4	130.2
67.5°	102.7	99.0	96.0	95.2	94.9	96.9	99.9	101.7	103.8	105.1	108.1
70°	92.3	89.0	85.4	84.1	83.9	85.6	88.4	88.7	91.5	92.1	95.1
72.5°	82.1	77.9	75.4	74.2	73.4	74.8	76.7	77.2	78.8	79.9	81.5
75°	66.0	62.9	60.5	58.7	58.1	58.9	58.9	59.9	61.0	61.6	63.4
77.5°	52.0	48.5	45.5	44.5	43.7	43.2	43.7	44.3	43.8	44.9	45.3
80°	42.2	38.5	36.2	35.9	34.6	33.7	33.4	34.0	33.2	33.7	34.9
82.5°	32.5	30.2	27.8	27.4	25.8	25.3	25.1	24.7	24.7	24.6	24.9
85°	19.4	17.9	16.3	15.3	14.6	13.7	13.7	13.3	12.8	12.4	12.7
87.5°	10.8	10.6	9.5	8.6	8.3	6.6	6.6	5.9	5.6	4.9	4.4
90°	14.6	15.5	13.8	12.1	12.1	6.9	6.9	6.0	5.2	2.6	0.9
92.5°	227.1	272.7	238.6	173.7	106.9	63.3	45.4	32.8	22.4	14.3	9.8
95°	720.3	700.5	528.7	323.2	182.2	107.5	71.4	50.7	39.5	30.9	28.3
97.5°	904.9	737.8	494.7	290.5	174.2	116.6	86.3	68.6	58.3	50.9	50.9
100°	911.1	691.0	448.7	273.4	176.2	125.5	98.0	81.6	71.4	65.3	65.3
102.5°	859.5	632.7	417.8	268.5	183.0	137.2	111.1	95.4	85.8	80.4	79.0
105°	765.9	563.9	391.1	270.8	199.4	158.2	133.2	117.8	107.5	103.1	100.6
107.5°	690.2	525.4	386.2	283.4	218.5	180.6	156.1	141.3	130.3	126.1	124.3
110°	652.4	512.3	387.6	293.1	232.9	195.1	171.9	156.4	146.1	141.8	140.1



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	631.1	506.1	391.8	303.4	246.7	210.3	187.0	171.6	162.0	157.0	155.2
115°	611.1	502.8	399.7	319.8	268.2	233.8	210.6	194.2	185.6	179.6	177.1
117.5°	602.2	502.0	408.1	336.4	289.0	256.3	232.2	217.0	207.5	202.2	199.8
120°	597.4	502.0	414.3	348.1	303.4	270.8	246.7	232.0	222.7	216.6	214.9
122.5°	591.9	501.3	420.5	359.1	317.2	284.5	261.1	245.1	236.3	230.3	228.7
125°	582.8	500.2	429.8	375.7	336.0	305.1	281.0	264.8	255.3	250.1	246.7
127.5°	570.6	498.3	437.1	389.9	353.6	323.7	299.5	282.4	271.6	265.4	262.7
130°	563.0	497.7	442.6	398.8	365.3	336.0	311.2	294.8	281.9	275.1	271.6
132.5°	556.1	497.0	447.5	407.8	375.0	345.7	322.2	304.4	292.2	283.3	280.5
135°	545.8	495.9	454.7	419.5	388.5	360.2	337.8	319.8	305.1	296.5	293.1
137.5°	536.8	495.8	459.0	427.7	398.8	372.4	351.0	332.3	318.4	308.9	305.7
140°	532.1	495.1	462.4	433.2	405.7	380.0	359.3	341.2	326.7	317.2	314.6
142.5°	528.0	495.1	465.2	437.3	411.9	386.8	366.9	349.5	335.5	326.8	324.3
145°	520.9	493.4	466.7	441.8	418.6	396.2	377.4	361.0	349.0	340.4	337.8
147.5°	514.5	490.3	467.6	445.7	425.5	404.5	387.4	373.9	361.5	354.0	353.1
150°	509.7	488.2	467.6	447.8	429.0	410.0	393.6	380.8	370.5	363.6	362.7
152.5°	504.2	484.7	466.2	449.2	431.7	414.8	399.8	388.3	378.8	371.9	371.7
155°	495.9	479.7	464.2	450.4	435.8	421.2	408.3	398.8	390.2	385.0	384.2
157.5°	487.5	474.3	461.9	450.4	438.7	426.4	416.2	407.9	401.2	396.4	396.4
160°	481.4	470.2	459.9	450.4	440.1	429.8	420.3	413.5	407.4	404.0	404.0
162.5°	475.9	466.1	457.8	450.4	441.4	431.9	424.5	418.3	412.9	410.2	410.9
165°	466.7	459.9	453.8	448.7	441.8	434.0	429.0	424.6	420.3	418.6	418.6
167.5°	458.5	453.7	449.7	446.6	441.6	435.9	432.0	429.6	426.4	425.5	426.4
170°	453.0	449.5	446.9	445.2	440.9	436.6	434.0	432.4	429.8	429.0	429.8
172.5°	448.2	445.4	444.2	443.8	440.2	437.3	435.4	434.4	432.5	432.4	433.2
175°	442.6	440.9	440.9	441.8	439.2	437.5	437.5	436.6	435.8	435.8	436.6
177.5°	438.9	438.2	438.2	439.5	438.2	437.5	437.5	437.5	436.8	437.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	495.2	496.8	498.9	502.5	503.8	505.4	507.7	507.6	508.2	510.7	515.8
5°	497.0	503.3	509.5	516.8	524.5	529.6	536.5	540.8	545.1	550.6	560.0
7.5°	497.7	507.7	518.9	531.8	543.3	556.5	566.8	576.5	585.3	596.8	608.0
10°	496.6	510.1	524.5	540.8	558.1	572.8	586.1	601.2	614.0	628.0	640.7
12.5°	494.5	510.7	530.0	548.3	568.5	590.2	606.7	622.0	639.0	655.2	674.8
15°	489.7	511.9	534.5	558.5	585.7	610.7	634.6	654.3	672.6	696.9	722.4
17.5°	483.5	507.5	536.1	565.2	593.5	622.1	651.6	681.3	704.5	734.6	754.5
20°	477.9	505.6	534.9	569.6	597.9	633.5	662.9	691.6	723.4	753.4	777.2
22.5°	469.8	500.2	531.3	565.8	603.0	638.8	672.6	703.8	735.6	768.2	797.0
25°	459.7	487.2	524.1	563.2	600.3	639.0	678.0	717.0	751.3	785.7	812.6
27.5°	442.5	477.2	511.5	551.9	593.1	636.9	678.6	719.5	755.4	783.7	800.3
30°	433.6	463.8	501.1	541.7	586.3	633.4	676.7	716.9	750.3	772.9	779.6
32.5°	420.6	451.7	488.2	530.2	577.5	625.9	671.0	708.9	736.8	748.6	740.5
35°	401.2	429.4	466.2	509.2	558.4	609.8	654.5	686.5	700.8	689.6	661.7
37.5°	378.0	405.9	442.9	485.2	536.0	588.4	628.7	651.8	647.0	619.1	577.6
40°	361.7	387.8	423.0	468.6	518.1	570.8	606.2	618.6	605.6	565.7	521.4
42.5°	343.6	369.0	404.4	448.5	500.9	549.4	580.3	581.3	559.5	511.7	467.4
45°	316.1	340.3	373.7	419.6	468.0	513.7	534.1	524.1	483.7	437.7	393.0
47.5°	288.9	309.9	342.9	386.3	432.4	470.8	481.0	463.0	420.0	375.2	333.9
50°	269.0	290.2	321.2	362.7	407.2	440.3	445.2	421.4	379.2	334.2	301.8
52.5°	249.9	271.0	300.7	339.2	379.9	409.8	410.0	382.5	340.4	300.3	270.2
55°	221.9	240.8	267.8	302.2	338.5	361.9	356.2	327.7	291.2	256.3	230.1
57.5°	194.9	211.5	236.2	264.9	296.9	316.2	306.8	279.3	246.8	217.1	197.3
60°	177.5	193.2	214.4	241.5	268.4	283.4	274.5	249.6	219.6	195.8	178.5
62.5°	160.5	173.7	194.2	217.7	242.6	253.7	245.8	221.3	195.4	173.8	159.7
65°	136.6	147.3	163.6	183.8	201.9	211.5	204.8	181.9	162.2	146.7	135.5
67.5°	114.1	122.5	134.9	151.1	166.5	171.7	165.6	149.6	132.9	120.5	112.6
70°	98.6	106.6	116.9	129.4	142.8	148.4	142.2	129.6	116.0	104.5	96.8
72.5°	85.1	91.3	100.0	110.6	121.1	126.7	122.5	110.4	98.8	90.3	83.8
75°	64.8	70.1	76.2	83.8	91.9	95.6	91.9	83.5	75.6	69.3	64.6
77.5°	47.1	49.9	54.7	60.4	65.4	68.2	65.0	59.4	54.5	50.2	47.9
80°	35.9	37.9	41.2	45.6	49.1	51.7	49.7	45.0	41.2	38.3	37.3
82.5°	26.1	27.5	29.6	32.9	35.2	36.6	35.7	32.3	30.7	28.2	27.2
85°	12.8	13.7	15.1	16.1	18.2	18.3	18.5	17.1	15.7	15.1	14.3
87.5°	4.9	5.6	6.3	6.9	7.6	8.8	8.6	9.0	8.6	8.3	7.8
90°	2.6	5.2	6.0	6.9	6.9	12.1	12.1	13.8	15.5	14.6	15.5
92.5°	14.3	22.4	32.8	45.4	63.3	106.9	173.7	238.6	272.7	227.1	168.8
95°	30.9	39.5	50.7	71.4	107.5	182.2	323.2	528.7	700.5	720.3	636.9
97.5°	50.9	58.3	68.6	86.3	116.6	174.2	290.5	494.7	737.8	904.9	941.1
100°	65.3	71.4	81.6	98.0	125.5	176.2	273.4	448.7	691.0	911.1	1036.6
102.5°	80.4	85.8	95.4	111.1	137.2	183.0	268.5	417.8	632.7	859.5	1031.8
105°	103.1	107.5	117.8	133.2	158.2	199.4	270.8	391.1	563.9	765.9	962.7
107.5°	126.1	130.3	141.3	156.1	180.6	218.5	283.4	386.2	525.4	690.2	864.5
110°	141.8	146.1	156.4	171.9	195.1	232.9	293.1	387.6	512.3	652.4	805.4



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	162.0	171.6	187.0	210.3	246.7	303.4	391.8	506.1	631.1	762.1
115°	179.6	185.6	194.2	210.6	233.8	268.2	319.8	399.7	502.8	611.1	718.6
117.5°	202.2	207.5	217.0	232.2	256.3	289.0	336.4	408.1	502.0	602.2	697.2
120°	216.6	222.7	232.0	246.7	270.8	303.4	348.1	414.3	502.0	597.4	687.6
122.5°	230.3	236.3	245.1	261.1	284.5	317.2	359.1	420.5	501.3	591.9	679.4
125°	250.1	255.3	264.8	281.0	305.1	336.0	375.7	429.8	500.2	582.8	665.3
127.5°	265.4	271.6	282.4	299.5	323.7	353.6	389.9	437.1	498.3	570.6	648.1
130°	275.1	281.9	294.8	311.2	336.0	365.3	398.8	442.6	497.7	563.0	634.4
132.5°	283.3	292.2	304.4	322.2	345.7	375.0	407.8	447.5	497.0	556.1	619.9
135°	296.5	305.1	319.8	337.8	360.2	388.5	419.5	454.7	495.9	545.8	599.9
137.5°	308.9	318.4	332.3	351.0	372.4	398.8	427.7	459.0	495.8	536.8	581.9
140°	317.2	326.7	341.2	359.3	380.0	405.7	433.2	462.4	495.1	532.1	571.6
142.5°	326.8	335.5	349.5	366.9	386.8	411.9	437.3	465.2	495.1	528.0	562.0
145°	340.4	349.0	361.0	377.4	396.2	418.6	441.8	466.7	493.4	520.9	548.4
147.5°	354.0	361.5	373.9	387.4	404.5	425.5	445.7	467.6	490.3	514.5	537.2
150°	363.6	370.5	380.8	393.6	410.0	429.0	447.8	467.6	488.2	509.7	530.4
152.5°	371.9	378.8	388.3	399.8	414.8	431.7	449.2	466.2	484.7	504.2	522.8
155°	385.0	390.2	398.8	408.3	421.2	435.8	450.4	464.2	479.7	495.9	511.4
157.5°	396.4	401.2	407.9	416.2	426.4	438.7	450.4	461.9	474.3	487.5	499.2
160°	404.0	407.4	413.5	420.3	429.8	440.1	450.4	459.9	470.2	481.4	491.6
162.5°	410.2	412.9	418.3	424.5	431.9	441.4	450.4	457.8	466.1	475.9	484.1
165°	418.6	420.3	424.6	429.0	434.0	441.8	448.7	453.8	459.9	466.7	473.6
167.5°	425.5	426.4	429.6	432.0	435.9	441.6	446.6	449.7	453.7	458.5	463.5
170°	429.0	429.8	432.4	434.0	436.6	440.9	445.2	446.9	449.5	453.0	457.3
172.5°	432.4	432.5	434.4	435.4	437.3	440.2	443.8	444.2	445.4	448.2	451.8
175°	435.8	435.8	436.6	437.5	437.5	439.2	441.8	440.9	440.9	442.6	444.4
177.5°	437.5	436.8	437.5	437.5	437.5	438.2	439.5	438.2	438.2	438.9	439.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	491.9	491.9	491.9	491.9	491.9	491.9	491.9
2.5°	518.5	518.8	520.3	521.4	521.8	523.4	523.5
5°	564.0	567.5	574.2	574.8	575.8	581.2	577.0
7.5°	617.4	626.2	632.1	637.3	639.1	641.4	641.0
10°	651.7	664.7	671.2	681.7	682.0	684.7	683.0
12.5°	686.0	701.2	713.1	715.1	723.8	725.1	727.4
15°	734.8	750.9	767.4	773.4	785.3	788.2	792.6
17.5°	780.6	797.0	808.7	823.9	828.9	835.4	831.0
20°	805.7	823.6	838.4	850.3	855.4	859.1	858.7
22.5°	820.9	839.0	850.8	860.0	864.7	866.3	866.2
25°	830.3	840.8	844.5	847.9	842.6	840.8	841.5
27.5°	803.9	801.2	791.7	779.1	766.1	755.8	750.1
30°	767.6	751.7	737.3	712.0	699.0	691.2	684.2
32.5°	716.1	690.9	663.1	639.9	625.1	613.6	611.9
35°	627.8	590.0	555.9	527.5	512.9	500.5	497.6
37.5°	533.7	494.4	463.7	438.8	423.0	414.2	406.0
40°	471.3	437.5	407.3	386.2	374.1	367.8	362.7
42.5°	423.3	392.4	362.3	346.2	335.4	331.5	328.5
45°	356.8	328.0	307.3	295.1	288.8	282.2	279.1
47.5°	303.6	280.3	266.6	256.1	249.3	245.5	243.6
50°	273.5	254.3	242.1	234.1	228.0	225.0	223.3
52.5°	246.8	231.0	220.8	214.4	210.3	208.0	207.3
55°	212.5	200.5	194.0	188.5	185.5	183.4	182.6
57.5°	184.8	175.5	170.2	165.7	164.5	162.8	162.2
60°	166.5	159.4	154.9	151.8	150.8	148.8	149.1
62.5°	150.3	144.5	140.7	139.0	137.6	135.9	136.5
65°	127.2	122.9	120.8	119.2	117.6	116.6	117.4
67.5°	106.7	103.8	101.0	100.0	99.3	99.1	98.2
70°	93.3	90.9	88.4	87.8	87.8	87.0	86.8
72.5°	80.4	78.7	77.1	76.5	75.9	76.3	75.4
75°	62.2	60.7	60.1	59.5	59.3	59.3	58.7
77.5°	45.9	44.9	43.9	43.9	43.1	42.9	42.8
80°	34.9	34.4	33.7	33.7	33.2	33.4	33.0
82.5°	26.2	25.7	25.5	25.1	24.5	24.6	24.2
85°	14.0	13.4	13.3	12.7	12.2	12.7	12.2
87.5°	8.2	8.2	8.0	7.8	7.8	7.7	7.2
90°	16.4	17.2	17.2	18.1	18.9	18.1	18.1
92.5°	127.1	101.1	83.9	73.8	69.1	66.2	66.2
95°	503.7	388.5	305.1	263.0	236.3	220.9	209.7
97.5°	891.5	807.4	717.7	656.0	604.2	578.5	560.6
100°	1053.8	1011.7	948.0	873.3	820.9	795.0	788.2
102.5°	1117.1	1129.3	1102.8	1056.9	1018.9	991.8	986.3
105°	1111.4	1196.4	1231.7	1233.5	1226.6	1214.5	1209.4
107.5°	1022.9	1142.7	1219.3	1261.8	1281.4	1290.0	1292.3
110°	954.1	1078.7	1173.3	1234.3	1270.4	1285.9	1293.7



TEST NUMBER: P332519-935

CATALOG NUMBER: S124DIP-S350D1035U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	893.5	1011.3	1105.9	1175.2	1218.8	1240.5	1253.0
115°	824.3	924.9	1007.4	1075.3	1126.9	1154.3	1161.2
117.5°	784.8	863.8	933.8	991.8	1035.1	1062.9	1068.2
120°	767.6	836.4	897.3	946.3	984.2	1006.5	1016.0
122.5°	756.6	819.2	872.6	914.0	946.3	965.3	974.7
125°	739.2	798.5	845.8	880.2	905.1	921.4	926.6
127.5°	718.8	777.9	822.8	857.3	879.5	893.2	898.4
130°	702.2	760.7	806.2	841.5	863.0	876.8	881.9
132.5°	683.7	740.7	786.4	820.9	845.1	858.2	863.3
135°	655.8	708.3	751.2	785.7	809.7	823.5	828.6
137.5°	629.2	673.4	712.2	744.3	768.1	779.5	785.7
140°	612.0	650.7	686.7	716.9	735.8	747.8	754.7
142.5°	597.5	630.8	662.0	688.6	706.2	716.9	721.7
145°	577.6	603.4	627.5	648.9	663.6	672.2	676.5
147.5°	560.4	581.1	599.9	615.8	628.4	634.9	636.4
150°	550.1	567.3	582.8	596.5	607.7	612.9	613.7
152.5°	539.8	555.6	568.3	580.1	589.1	592.2	593.1
155°	525.2	538.0	548.4	557.0	563.9	566.5	566.5
157.5°	510.7	521.6	529.9	536.3	541.5	543.0	543.0
160°	501.1	510.6	517.5	522.6	527.8	528.7	528.7
162.5°	492.1	499.6	505.8	509.5	514.7	515.6	514.9
165°	478.8	484.7	489.0	492.5	495.9	495.1	494.2
167.5°	467.4	472.3	474.8	476.6	478.8	478.6	477.9
170°	459.9	463.3	465.9	467.6	468.5	467.6	467.6
172.5°	453.7	455.7	457.6	458.7	459.5	458.7	457.3
175°	445.2	446.9	446.9	446.9	448.7	446.9	445.2
177.5°	440.2	440.2	440.9	440.2	440.9	439.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5

(END OF REPORT)