

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332974-935

Luminaire Tested: **S124RDIP-S1020D1035U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332974-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6820.6 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	55	52	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	30	26
6	65	53	45	39	60	50	43	37	43	38	34	38	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11926	11926	11926	11926
5°	13834	11962	10573	11962
10°	16365	11910	9437	11910
15°	18904	11800	8109	11800
20°	21047	11649	7332	11649
25°	21727	11500	6807	11500
30°	19020	11320	6492	11320
35°	14807	11052	6300	11052
40°	11102	10745	6198	10745
45°	8766	10255	6142	10255
50°	7401	9688	5966	9688
55°	6450	9064	5645	9064
60°	5804	8418	4997	8418
65°	5117	7721	4298	7721
70°	4607	6996	3878	6996
75°	3862	6201	3306	6201
80°	3268	5286	3096	5286
85°	2760	4131	2760	4131



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.1	2.1
10°-20°	431.8	6.3
20°-30°	675.3	9.9
30°-40°	750.8	11.0
40°-50°	666.1	9.8
50°-60°	519.0	7.6
60°-70°	339.8	5.0
70°-80°	167.1	2.5
80°-90°	44.6	0.7
90°-100°	73.3	1.1
100°-110°	217.1	3.2
110°-120°	368.5	5.4
120°-130°	485.9	7.1
130°-140°	545.7	8.0
140°-150°	536.2	7.9
150°-160°	451.0	6.6
160°-170°	300.1	4.4
170°-180°	105.1	1.5
0°-30°	1250.3	18.3
0°-40°	2001.0	29.3
0°-60°	3186.1	46.7
0°-90°	3737.6	54.8
90°-120°	658.9	9.7
90°-150°	2226.8	32.6
90°-180°	3083.0	45.2
0°-180°	6820.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1477	1477	1477	1477	1477	
5°	1707	1476	1305	1476	1707	173
15°	2262	1412	970	1412	2262	643
25°	2439	1291	764	1291	2439	1082
35°	1502	1121	639	1121	1502	942
45°	768	898	538	898	768	608
55°	458	644	401	644	458	417
65°	268	404	225	404	268	269
75°	124	199	106	199	124	136
85°	30	45	30	45	30	34
90°	26	3	26	3	26	14
95°	68	52	68	52	68	71
105°	210	200	210	200	210	221
115°	371	375	371	375	371	367
125°	541	546	541	546	541	483
135°	705	704	705	704	705	544
145°	856	855	856	855	856	536
155°	979	980	979	980	979	451
165°	1064	1066	1064	1066	1064	300
175°	1104	1110	1104	1110	1104	105
180°	1111	1111	1111	1111	1111	



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1558.2	1562.5	1558.2	1557.8	1553.1	1551.6	1549.7	1543.5	1532.1	1525.4	1526.8
5°	1707.1	1721.9	1713.6	1712.4	1699.4	1686.3	1677.9	1658.9	1638.7	1625.0	1613.6
7.5°	1879.2	1887.7	1882.6	1874.2	1853.0	1841.0	1821.7	1796.6	1760.3	1732.5	1707.2
10°	1996.3	2003.5	2001.1	1985.6	1970.1	1938.6	1920.7	1885.7	1839.8	1803.5	1769.5
12.5°	2111.6	2119.2	2098.3	2098.9	2069.7	2044.8	2016.5	1972.3	1919.3	1872.5	1830.1
15°	2261.8	2252.3	2252.3	2240.4	2207.6	2173.2	2144.0	2097.6	2030.8	1974.9	1916.0
17.5°	2379.5	2382.7	2377.9	2349.8	2324.1	2288.4	2234.9	2180.7	2118.8	2043.8	1983.5
20°	2449.9	2449.9	2444.6	2425.5	2392.2	2354.1	2296.4	2237.4	2158.9	2083.3	2015.4
22.5°	2478.5	2480.4	2474.1	2458.3	2428.4	2391.2	2342.0	2282.2	2201.2	2116.1	2032.0
25°	2439.2	2450.5	2451.7	2447.5	2438.6	2416.0	2373.7	2312.4	2239.8	2147.5	2057.0
27.5°	2239.5	2253.8	2266.2	2286.8	2314.2	2328.5	2330.4	2299.2	2235.8	2147.1	2056.0
30°	2040.4	2052.3	2091.0	2141.6	2180.8	2216.6	2247.6	2255.8	2220.2	2140.4	2044.5
32.5°	1819.5	1835.7	1874.3	1928.7	1994.2	2054.7	2124.2	2159.6	2158.7	2110.8	2022.1
35°	1502.4	1514.2	1550.0	1607.1	1685.7	1775.6	1885.7	1971.3	2029.6	2025.5	1971.3
37.5°	1211.6	1225.0	1261.1	1308.5	1384.7	1496.0	1602.6	1720.6	1828.5	1889.1	1871.0
40°	1053.5	1054.1	1089.3	1138.1	1209.4	1306.5	1422.5	1553.5	1673.7	1771.9	1791.0
42.5°	928.8	928.8	952.1	1004.7	1056.2	1147.5	1258.3	1388.3	1529.0	1642.4	1692.9
45°	767.8	773.2	792.2	823.8	864.3	941.6	1030.3	1151.2	1308.9	1443.4	1527.3
47.5°	650.2	658.1	670.2	695.9	728.1	779.7	853.1	961.7	1089.9	1237.9	1357.4
50°	589.3	590.5	605.9	620.2	648.2	689.2	753.5	844.0	961.8	1104.1	1236.8
52.5°	536.9	536.7	546.0	564.0	586.8	618.8	670.7	753.0	857.6	985.1	1122.1
55°	458.3	461.3	468.5	482.7	500.0	522.6	563.7	625.6	707.7	816.7	941.1
57.5°	398.6	400.1	405.7	411.7	427.6	444.0	474.8	517.8	587.1	676.3	792.2
60°	359.5	360.1	361.9	370.8	383.3	398.8	419.7	455.9	514.3	595.8	687.5
62.5°	321.4	322.4	325.2	331.7	341.4	352.1	373.9	403.1	451.4	521.1	603.6
65°	267.9	268.5	272.6	275.0	282.8	292.2	308.3	328.0	361.3	419.7	482.2
67.5°	223.8	223.8	224.0	227.2	232.6	238.9	248.6	264.2	289.4	325.2	380.3
70°	195.2	195.2	196.4	198.2	201.2	206.6	211.9	223.8	242.3	271.4	313.7
72.5°	168.6	169.0	170.2	170.6	172.1	176.5	180.5	188.1	201.8	223.8	258.0
75°	123.8	125.6	128.5	131.0	133.9	133.4	137.5	142.2	146.5	159.5	179.2
77.5°	92.1	91.2	91.5	93.6	93.9	94.5	97.5	101.2	104.3	110.5	117.5
80°	70.3	70.3	72.0	72.6	72.0	72.6	75.6	77.4	78.6	80.9	87.5
82.5°	53.1	54.1	53.5	54.1	54.4	55.0	57.5	57.9	59.1	60.0	62.8
85°	29.8	30.4	30.9	29.8	29.8	29.8	30.9	31.5	32.7	32.1	33.3
87.5°	15.7	15.1	15.5	15.4	15.8	15.2	15.4	16.2	15.0	15.2	14.9
90°	25.7	25.4	25.1	24.6	24.3	23.5	22.4	21.2	20.1	18.9	17.4
92.5°	38.1	38.0	37.7	37.5	37.3	36.8	36.1	35.4	34.7	34.0	33.0
95°	67.9	67.9	67.9	67.9	67.9	67.6	67.1	66.5	65.9	65.3	64.0
97.5°	106.4	106.4	106.4	106.4	106.4	106.1	105.4	104.7	104.0	103.3	101.8
100°	133.2	133.2	133.2	133.2	133.2	133.0	132.6	132.2	131.9	131.5	129.8
102.5°	163.4	163.3	163.2	163.0	162.8	162.5	162.0	161.4	160.9	160.4	158.8
105°	209.7	209.1	208.5	207.9	207.4	206.8	206.3	205.7	205.1	204.6	203.8
107.5°	254.7	254.8	254.8	254.9	254.9	254.6	254.1	253.6	253.0	252.5	252.4
110°	287.1	286.5	285.9	285.3	284.7	284.6	285.0	285.4	285.8	286.2	286.4



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	320.0	319.9	319.8	319.7	319.6	319.6	319.6	319.7	319.8	319.9	320.2
115°	371.3	371.4	371.6	371.9	372.0	372.2	372.4	372.6	372.8	373.0	373.3
117.5°	420.1	420.4	420.9	421.2	421.6	422.1	422.8	423.4	424.0	424.7	425.0
120°	457.2	456.8	456.4	456.1	455.6	456.0	456.9	457.9	458.8	459.8	460.4
122.5°	488.1	488.8	489.5	490.2	490.9	491.5	492.2	492.8	493.5	494.1	494.4
125°	541.4	541.8	542.2	542.6	542.9	543.3	543.7	544.1	544.5	544.8	545.0
127.5°	590.7	591.1	591.3	591.7	591.9	592.3	592.7	593.1	593.5	593.8	594.2
130°	623.0	623.8	624.6	625.3	626.1	626.7	627.1	627.5	627.8	628.2	628.2
132.5°	657.5	657.7	658.1	658.3	658.7	659.0	659.4	659.8	660.1	660.6	660.6
135°	704.7	705.2	705.8	706.5	707.0	707.5	707.8	708.3	708.6	709.0	709.0
137.5°	754.4	754.2	754.1	754.1	753.9	754.1	754.6	755.1	755.6	756.1	755.8
140°	784.6	784.8	785.0	785.2	785.4	785.6	785.7	786.0	786.2	786.4	786.4
142.5°	814.9	814.9	814.9	815.0	815.0	815.1	815.1	815.1	815.2	815.2	815.4
145°	855.9	856.5	857.1	857.6	858.2	858.6	858.8	859.0	859.2	859.4	859.2
147.5°	897.6	897.8	897.9	898.1	898.3	898.5	898.6	898.8	899.0	899.1	899.2
150°	923.0	923.2	923.3	923.6	923.8	923.9	923.9	923.9	923.9	923.9	923.9
152.5°	946.3	946.8	947.4	947.9	948.4	948.4	947.9	947.4	947.0	946.5	946.4
155°	978.9	979.6	980.4	981.1	981.9	981.9	981.1	980.4	979.6	978.9	979.0
157.5°	1007.9	1008.6	1009.2	1009.9	1010.5	1010.6	1010.0	1009.4	1008.8	1008.2	1008.3
160°	1024.4	1025.4	1026.3	1027.3	1028.2	1028.4	1027.9	1027.3	1026.7	1026.1	1026.3
162.5°	1041.6	1042.6	1043.5	1044.5	1045.4	1045.3	1044.3	1043.3	1042.2	1041.2	1041.5
165°	1063.9	1064.7	1065.5	1066.3	1067.0	1066.8	1065.7	1064.5	1063.3	1062.2	1062.6
167.5°	1080.0	1081.1	1082.3	1083.5	1084.7	1084.7	1083.6	1082.4	1081.2	1080.1	1080.0
170°	1088.8	1090.2	1091.5	1092.9	1094.2	1094.3	1093.1	1092.0	1090.9	1089.7	1089.5
172.5°	1096.4	1097.8	1099.1	1100.4	1101.7	1101.8	1100.4	1099.2	1097.9	1096.6	1096.6
175°	1104.3	1105.7	1107.0	1108.4	1109.7	1109.7	1108.4	1107.0	1105.7	1104.3	1104.5
177.5°	1108.5	1109.7	1110.9	1112.2	1113.4	1113.4	1112.3	1111.3	1110.2	1109.1	1109.1
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1522.1	1515.4	1512.1	1504.4	1495.4	1490.6	1486.3	1480.1	1472.1	1463.5	1457.3
5°	1599.3	1585.0	1567.2	1545.8	1526.7	1508.3	1492.2	1476.1	1457.7	1438.6	1419.6
7.5°	1678.6	1650.5	1620.1	1585.0	1550.9	1519.8	1491.3	1463.9	1432.9	1405.2	1379.9
10°	1733.9	1695.7	1653.5	1608.9	1564.2	1525.5	1487.5	1452.9	1414.8	1380.9	1352.3
12.5°	1778.7	1733.9	1683.0	1627.5	1573.7	1527.0	1483.2	1438.1	1394.8	1358.1	1319.9
15°	1852.9	1791.6	1723.1	1656.5	1586.8	1523.1	1464.2	1411.9	1362.4	1310.7	1274.4
17.5°	1903.9	1831.3	1748.0	1667.9	1585.6	1510.5	1442.5	1380.2	1323.2	1270.3	1227.1
20°	1934.4	1854.1	1761.9	1670.8	1578.5	1498.1	1425.0	1355.9	1297.0	1239.8	1195.2
22.5°	1951.5	1862.7	1761.9	1666.5	1570.9	1483.8	1403.5	1331.6	1267.5	1210.3	1160.9
25°	1957.1	1861.8	1758.9	1649.3	1544.5	1452.3	1369.0	1291.0	1219.6	1162.4	1110.1
27.5°	1949.5	1837.3	1731.8	1619.5	1511.4	1414.1	1326.6	1244.7	1173.2	1111.9	1058.2
30°	1938.0	1817.7	1704.7	1588.0	1478.5	1385.1	1292.8	1214.3	1139.8	1076.2	1022.0
32.5°	1913.2	1794.0	1672.3	1552.8	1441.8	1345.6	1258.0	1179.0	1106.0	1040.9	983.4
35°	1864.2	1743.4	1611.3	1488.7	1379.7	1279.7	1197.6	1121.4	1051.7	982.1	921.4
37.5°	1799.6	1676.1	1544.7	1410.4	1301.4	1206.9	1131.6	1060.1	992.1	928.5	861.3
40°	1738.6	1626.1	1490.4	1357.1	1245.2	1154.1	1084.5	1019.6	951.1	888.0	820.8
42.5°	1664.8	1569.0	1431.8	1298.0	1187.6	1099.8	1034.9	971.5	909.2	848.1	777.9
45°	1541.6	1469.0	1340.4	1211.9	1100.5	1013.7	954.2	898.2	843.4	785.1	719.0
47.5°	1400.4	1351.3	1240.3	1108.6	1005.6	927.5	870.0	824.2	777.9	719.6	661.7
50°	1302.3	1270.7	1163.6	1043.4	945.2	873.1	814.2	771.4	732.7	676.7	625.0
52.5°	1197.6	1180.8	1090.3	975.3	880.5	809.9	759.5	720.9	681.7	635.3	586.9
55°	1038.0	1047.0	970.2	870.8	781.5	722.0	676.1	644.0	610.7	571.4	533.9
57.5°	874.9	907.6	856.0	768.8	685.1	630.1	595.6	568.5	540.5	508.0	476.0
60°	777.3	804.7	775.6	698.8	625.6	574.4	542.3	521.4	493.4	463.6	439.3
62.5°	682.1	711.4	694.1	632.1	564.1	520.1	491.8	472.3	451.5	425.6	400.2
65°	562.5	581.5	573.2	530.4	482.2	444.6	418.4	404.2	385.1	366.1	343.5
67.5°	430.8	467.6	462.7	440.0	398.3	369.0	351.9	339.2	321.9	307.7	292.4
70°	354.1	388.1	387.4	369.0	346.4	319.0	307.1	296.4	280.9	267.3	254.8
72.5°	289.9	321.0	325.5	311.4	295.9	275.3	263.8	256.4	241.4	232.0	221.9
75°	202.9	225.6	231.5	231.5	224.4	213.7	203.5	198.8	188.1	179.8	173.8
77.5°	133.1	147.4	156.7	158.8	159.9	156.3	148.0	144.6	136.4	133.5	127.8
80°	94.0	103.6	114.3	117.9	120.8	119.7	116.1	113.7	106.0	103.0	100.6
82.5°	65.0	70.3	79.0	86.9	86.1	89.2	86.1	84.2	78.4	77.2	74.9
85°	33.9	34.5	35.7	41.1	44.1	45.2	45.8	44.6	42.9	42.9	38.7
87.5°	14.6	13.8	14.5	14.1	14.1	15.7	16.6	16.7	15.7	14.7	13.7
90°	15.8	14.3	12.8	11.0	8.9	6.8	4.6	2.6	4.6	6.8	8.9
92.5°	31.9	30.8	29.8	28.0	25.6	23.2	20.8	18.4	20.8	23.2	25.6
95°	62.7	61.3	59.9	58.5	56.7	55.0	53.3	51.6	53.3	55.0	56.7
97.5°	100.1	98.6	97.0	95.6	94.2	92.8	91.4	90.1	91.4	92.8	94.2
100°	128.0	126.3	124.6	123.4	122.6	121.8	121.1	120.3	121.1	121.8	122.6
102.5°	157.2	155.7	154.1	153.2	152.8	152.6	152.2	152.0	152.2	152.6	152.8
105°	203.0	202.2	201.5	201.0	200.8	200.6	200.4	200.3	200.4	200.6	200.8
107.5°	252.3	252.2	252.0	251.8	251.7	251.4	251.2	251.0	251.2	251.4	251.7
110°	286.5	286.7	287.0	286.9	286.5	286.1	285.7	285.3	285.7	286.1	286.5



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	320.6	320.9	321.2	321.4	321.3	321.2	321.2	321.1	321.2	321.2	321.3
115°	373.8	374.1	374.5	374.7	374.7	374.7	374.7	374.7	374.7	374.7	374.7
117.5°	425.2	425.5	425.8	425.9	425.7	425.5	425.4	425.2	425.4	425.5	425.7
120°	460.9	461.5	462.1	462.0	461.2	460.5	459.7	458.9	459.7	460.5	461.2
122.5°	494.6	495.0	495.2	495.2	494.9	494.6	494.3	494.0	494.3	494.6	494.9
125°	545.3	545.4	545.6	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.7
127.5°	594.4	594.8	595.0	595.0	594.3	593.7	593.2	592.6	593.2	593.7	594.3
130°	628.2	628.2	628.2	627.9	627.3	626.8	626.2	625.6	626.2	626.8	627.3
132.5°	660.8	661.0	661.2	661.0	660.6	660.1	659.8	659.4	659.8	660.1	660.6
135°	709.0	709.0	709.0	708.4	707.3	706.1	705.0	703.9	705.0	706.1	707.3
137.5°	755.5	755.2	754.8	754.5	753.9	753.4	752.9	752.3	752.9	753.4	753.9
140°	786.4	786.4	786.4	786.2	785.7	785.4	785.0	784.6	785.0	785.4	785.7
142.5°	815.5	815.7	815.8	815.7	815.4	814.9	814.6	814.2	814.6	814.9	815.4
145°	859.0	858.8	858.6	858.2	857.4	856.6	855.8	855.1	855.8	856.6	857.4
147.5°	899.4	899.6	899.7	899.3	898.5	897.5	896.6	895.7	896.6	897.5	898.5
150°	923.9	923.9	923.9	923.5	922.7	922.0	921.2	920.4	921.2	922.0	922.7
152.5°	946.2	946.1	945.9	945.6	945.2	944.7	944.3	943.8	944.3	944.7	945.2
155°	979.2	979.4	979.6	979.7	979.7	979.7	979.7	979.7	979.7	979.7	979.7
157.5°	1008.3	1008.3	1008.4	1008.6	1008.9	1009.3	1009.6	1010.0	1009.6	1009.3	1008.9
160°	1026.5	1026.7	1026.9	1027.1	1027.3	1027.4	1027.6	1027.9	1027.6	1027.4	1027.3
162.5°	1041.6	1041.8	1042.0	1042.3	1042.8	1043.4	1043.9	1044.3	1043.9	1043.4	1042.8
165°	1063.0	1063.3	1063.8	1064.2	1064.8	1065.4	1065.9	1066.5	1065.9	1065.4	1064.8
167.5°	1080.0	1080.0	1080.0	1080.3	1081.2	1081.9	1082.7	1083.6	1082.7	1081.9	1081.2
170°	1089.3	1089.2	1088.9	1089.3	1090.3	1091.2	1092.2	1093.1	1092.2	1091.2	1090.3
172.5°	1096.5	1096.5	1096.4	1096.8	1097.6	1098.5	1099.2	1100.0	1099.2	1098.5	1097.6
175°	1104.7	1104.9	1105.1	1105.7	1106.6	1107.6	1108.5	1109.5	1108.5	1107.6	1106.6
177.5°	1109.1	1109.1	1109.1	1109.5	1110.3	1111.0	1111.8	1112.6	1111.8	1111.0	1110.3
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1450.6	1445.9	1439.7	1432.5	1424.0	1416.3	1413.1	1415.9	1417.3	1413.5	1413.1
5°	1406.5	1391.6	1379.7	1361.8	1347.6	1335.7	1327.3	1323.8	1324.9	1315.4	1313.0
7.5°	1356.8	1339.2	1319.7	1298.5	1278.8	1261.3	1252.1	1247.1	1237.0	1232.7	1225.5
10°	1324.9	1301.1	1282.1	1257.1	1234.5	1213.7	1203.5	1195.2	1185.1	1180.3	1170.2
12.5°	1292.1	1264.5	1243.5	1217.5	1194.5	1169.3	1159.7	1144.3	1128.4	1118.4	1105.4
15°	1245.8	1212.5	1186.9	1155.9	1128.5	1099.9	1074.4	1045.8	1035.1	1012.4	999.4
17.5°	1191.6	1157.8	1126.1	1084.6	1042.3	1006.9	979.6	952.2	935.8	921.4	914.7
20°	1155.9	1125.0	1080.9	1032.7	985.7	946.4	924.4	906.5	888.6	878.6	871.4
22.5°	1122.1	1082.5	1031.4	979.4	932.4	901.6	883.0	864.6	850.1	840.4	831.0
25°	1065.4	1013.7	959.5	900.0	867.8	841.0	820.8	805.9	797.0	784.5	779.7
27.5°	1007.2	944.5	884.8	844.7	811.2	786.8	769.1	757.9	746.7	738.7	732.5
30°	962.4	898.8	845.2	807.1	773.2	752.9	738.7	725.6	716.6	710.1	705.3
32.5°	918.2	854.5	809.5	768.5	741.8	722.0	706.8	697.0	690.0	681.5	678.6
35°	854.1	797.5	758.3	721.4	694.1	676.1	664.3	654.1	648.2	645.8	644.0
37.5°	792.6	746.3	704.0	673.8	649.4	635.3	621.3	616.3	612.3	608.0	609.8
40°	753.5	710.1	672.6	640.4	620.8	605.4	597.0	591.1	587.5	587.5	587.5
42.5°	719.7	677.3	640.7	611.9	592.2	579.1	569.9	564.8	563.7	563.2	566.0
45°	667.3	627.9	591.1	567.2	550.6	537.4	532.1	528.0	528.0	530.4	530.9
47.5°	615.2	578.4	548.8	522.1	506.9	498.7	494.0	491.9	492.1	494.5	497.2
50°	583.3	547.0	517.8	494.0	479.7	472.0	467.9	466.7	467.9	467.9	472.0
52.5°	548.5	516.1	487.3	467.4	451.2	443.9	441.6	440.0	440.7	442.6	444.4
55°	497.6	468.5	441.1	422.0	410.1	405.4	400.0	400.5	399.4	400.5	400.5
57.5°	446.5	420.3	394.9	379.8	369.3	362.4	356.5	358.2	356.5	356.2	355.2
60°	413.7	385.1	364.9	351.2	339.2	333.3	328.0	329.2	327.4	326.1	323.8
62.5°	378.0	354.1	334.8	321.7	312.1	305.2	299.9	298.7	294.5	290.5	285.2
65°	326.1	306.5	289.3	276.8	267.9	262.5	258.3	254.8	245.8	236.3	231.5
67.5°	275.9	261.7	245.6	235.0	227.7	220.7	212.8	206.6	198.3	193.1	190.1
70°	243.4	229.7	216.0	206.0	198.2	191.7	182.7	178.6	172.6	170.2	167.3
72.5°	212.5	199.8	187.0	177.9	169.6	164.5	157.5	153.3	150.7	149.7	146.8
75°	165.5	155.3	145.9	137.5	131.0	127.3	124.4	121.4	120.2	114.9	111.9
77.5°	120.7	114.1	108.1	102.1	97.5	95.1	89.4	85.9	83.9	81.5	80.8
80°	94.0	89.3	83.3	79.7	73.2	70.9	68.4	67.8	67.2	66.6	66.0
82.5°	70.7	66.0	60.0	57.9	56.1	54.7	53.2	52.6	52.0	52.3	52.3
85°	35.7	33.3	33.3	32.7	32.1	31.5	30.9	30.9	30.4	30.9	30.4
87.5°	14.1	13.9	14.3	13.6	14.5	14.7	14.5	14.7	15.4	14.7	14.8
90°	11.0	12.8	14.3	15.8	17.4	18.9	20.1	21.2	22.4	23.5	24.3
92.5°	28.0	29.8	30.8	31.9	33.0	34.0	34.7	35.4	36.1	36.8	37.3
95°	58.5	59.9	61.3	62.7	64.0	65.3	65.9	66.5	67.1	67.6	67.9
97.5°	95.6	97.0	98.6	100.1	101.8	103.3	104.0	104.7	105.4	106.1	106.4
100°	123.4	124.6	126.3	128.0	129.8	131.5	131.9	132.2	132.6	133.0	133.2
102.5°	153.2	154.1	155.7	157.2	158.8	160.4	160.9	161.4	162.0	162.5	162.8
105°	201.0	201.5	202.2	203.0	203.8	204.6	205.1	205.7	206.3	206.8	207.4
107.5°	251.8	252.0	252.2	252.3	252.4	252.5	253.0	253.6	254.1	254.6	254.9
110°	286.9	287.0	286.7	286.5	286.4	286.2	285.8	285.4	285.0	284.6	284.7



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	321.4	321.2	320.9	320.6	320.2	319.9	319.8	319.7	319.6	319.6	319.6
115°	374.7	374.5	374.1	373.8	373.3	373.0	372.8	372.6	372.4	372.2	372.0
117.5°	425.9	425.8	425.5	425.2	425.0	424.7	424.0	423.4	422.8	422.1	421.6
120°	462.0	462.1	461.5	460.9	460.4	459.8	458.8	457.9	456.9	456.0	455.6
122.5°	495.2	495.2	495.0	494.6	494.4	494.1	493.5	492.8	492.2	491.5	490.9
125°	545.7	545.6	545.4	545.3	545.0	544.8	544.5	544.1	543.7	543.3	542.9
127.5°	595.0	595.0	594.8	594.4	594.2	593.8	593.5	593.1	592.7	592.3	591.9
130°	627.9	628.2	628.2	628.2	628.2	628.2	627.8	627.5	627.1	626.7	626.1
132.5°	661.0	661.2	661.0	660.8	660.6	660.6	660.1	659.8	659.4	659.0	658.7
135°	708.4	709.0	709.0	709.0	709.0	709.0	708.6	708.3	707.8	707.5	707.0
137.5°	754.5	754.8	755.2	755.5	755.8	756.1	755.6	755.1	754.6	754.1	753.9
140°	786.2	786.4	786.4	786.4	786.4	786.4	786.2	786.0	785.7	785.6	785.4
142.5°	815.7	815.8	815.7	815.5	815.4	815.2	815.2	815.1	815.1	815.1	815.0
145°	858.2	858.6	858.8	859.0	859.2	859.4	859.2	859.0	858.8	858.6	858.2
147.5°	899.3	899.7	899.6	899.4	899.2	899.1	899.0	898.8	898.6	898.5	898.3
150°	923.5	923.9	923.9	923.9	923.9	923.9	923.9	923.9	923.9	923.9	923.8
152.5°	945.6	945.9	946.1	946.2	946.4	946.5	947.0	947.4	947.9	948.4	948.4
155°	979.7	979.6	979.4	979.2	979.0	978.9	979.6	980.4	981.1	981.9	981.9
157.5°	1008.6	1008.4	1008.3	1008.3	1008.3	1008.2	1008.8	1009.4	1010.0	1010.6	1010.5
160°	1027.1	1026.9	1026.7	1026.5	1026.3	1026.1	1026.7	1027.3	1027.9	1028.4	1028.2
162.5°	1042.3	1042.0	1041.8	1041.6	1041.5	1041.2	1042.2	1043.3	1044.3	1045.3	1045.4
165°	1064.2	1063.8	1063.3	1063.0	1062.6	1062.2	1063.3	1064.5	1065.7	1066.8	1067.0
167.5°	1080.3	1080.0	1080.0	1080.0	1080.0	1080.1	1081.2	1082.4	1083.6	1084.7	1084.7
170°	1089.3	1088.9	1089.2	1089.3	1089.5	1089.7	1090.9	1092.0	1093.1	1094.3	1094.2
172.5°	1096.8	1096.4	1096.5	1096.5	1096.6	1096.6	1097.9	1099.2	1100.4	1101.8	1101.7
175°	1105.7	1105.1	1104.9	1104.7	1104.5	1104.3	1105.7	1107.0	1108.4	1109.7	1109.7
177.5°	1109.5	1109.1	1109.1	1109.1	1109.1	1109.1	1110.2	1111.3	1112.3	1113.4	1113.4
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1410.1	1411.1	1407.8	1406.9	1407.8	1411.1	1410.1	1413.1	1413.5	1417.3	1415.9
5°	1308.3	1307.1	1304.1	1304.7	1304.1	1307.1	1308.3	1313.0	1315.4	1324.9	1323.8
7.5°	1221.2	1216.5	1217.8	1213.1	1217.8	1216.5	1221.2	1225.5	1232.7	1237.0	1247.1
10°	1167.8	1161.2	1155.9	1151.2	1155.9	1161.2	1167.8	1170.2	1180.3	1185.1	1195.2
12.5°	1094.9	1089.3	1082.1	1083.6	1082.1	1089.3	1094.9	1105.4	1118.4	1128.4	1144.3
15°	991.6	982.7	968.5	970.2	968.5	982.7	991.6	999.4	1012.4	1035.1	1045.8
17.5°	904.1	904.2	897.7	899.2	897.7	904.2	904.1	914.7	921.4	935.8	952.2
20°	858.9	854.7	855.3	853.5	855.3	854.7	858.9	871.4	878.6	888.6	906.5
22.5°	827.5	822.3	818.2	814.5	818.2	822.3	827.5	831.0	840.4	850.1	864.6
25°	774.4	770.8	765.4	764.2	765.4	770.8	774.4	779.7	784.5	797.0	805.9
27.5°	727.7	727.0	724.9	722.1	724.9	727.0	727.7	732.5	738.7	746.7	757.9
30°	700.6	699.4	698.2	696.4	698.2	699.4	700.6	705.3	710.1	716.6	725.6
32.5°	676.3	675.5	674.3	674.5	674.3	675.5	676.3	678.6	681.5	690.0	697.0
35°	641.6	641.0	639.9	639.3	639.9	641.0	641.6	644.0	645.8	648.2	654.1
37.5°	609.2	610.8	610.1	609.9	610.1	610.8	609.2	609.8	608.0	612.3	616.3
40°	586.9	587.5	588.7	588.1	588.7	587.5	586.9	587.5	587.5	587.5	591.1
42.5°	568.3	568.4	570.1	568.1	570.1	568.4	568.3	566.0	563.2	563.7	564.8
45°	535.1	538.6	538.0	538.0	538.0	538.6	535.1	530.9	530.4	528.0	528.0
47.5°	498.8	501.9	502.7	502.6	502.7	501.9	498.8	497.2	494.5	492.1	491.9
50°	475.0	473.8	475.6	475.0	475.6	473.8	475.0	472.0	467.9	467.9	466.7
52.5°	445.9	446.2	446.1	445.5	446.1	446.2	445.9	444.4	442.6	440.7	440.0
55°	401.1	401.7	400.5	401.1	400.5	401.7	401.1	400.5	400.5	399.4	400.5
57.5°	352.6	349.7	350.9	349.5	350.9	349.7	352.6	355.2	356.2	356.5	358.2
60°	317.9	313.1	311.9	309.5	311.9	313.1	317.9	323.8	326.1	327.4	329.2
62.5°	278.8	275.4	271.4	273.3	271.4	275.4	278.8	285.2	290.5	294.5	298.7
65°	226.8	224.4	222.6	225.0	222.6	224.4	226.8	231.5	236.3	245.8	254.8
67.5°	187.7	186.4	186.4	185.2	186.4	186.4	187.7	190.1	193.1	198.3	206.6
70°	167.3	165.5	165.5	164.3	165.5	165.5	167.3	167.3	170.2	172.6	178.6
72.5°	146.3	144.5	145.0	144.3	145.0	144.5	146.3	146.8	149.7	150.7	153.3
75°	108.3	105.4	105.4	106.0	105.4	105.4	108.3	111.9	114.9	120.2	121.4
77.5°	80.8	80.2	81.1	80.0	81.1	80.2	80.8	80.8	81.5	83.9	85.9
80°	66.0	65.4	64.9	66.6	64.9	65.4	66.0	66.0	66.6	67.2	67.8
82.5°	51.3	51.2	51.1	53.3	51.1	51.2	51.3	52.3	52.3	52.0	52.6
85°	30.9	29.8	30.9	29.8	30.9	29.8	30.9	30.4	30.9	30.4	30.9
87.5°	15.8	15.5	15.1	15.7	15.1	15.5	15.8	14.8	14.7	15.4	14.7
90°	24.6	25.1	25.4	25.7	25.4	25.1	24.6	24.3	23.5	22.4	21.2
92.5°	37.5	37.7	38.0	38.1	38.0	37.7	37.5	37.3	36.8	36.1	35.4
95°	67.9	67.9	67.9	67.9	67.9	67.9	67.9	67.9	67.6	67.1	66.5
97.5°	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.1	105.4	104.7
100°	133.2	133.2	133.2	133.2	133.2	133.2	133.2	133.2	133.0	132.6	132.2
102.5°	163.0	163.2	163.3	163.4	163.3	163.2	163.0	162.8	162.5	162.0	161.4
105°	207.9	208.5	209.1	209.7	209.1	208.5	207.9	207.4	206.8	206.3	205.7
107.5°	254.9	254.8	254.8	254.7	254.8	254.8	254.9	254.9	254.6	254.1	253.6
110°	285.3	285.9	286.5	287.1	286.5	285.9	285.3	284.7	284.6	285.0	285.4



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	319.7	319.8	319.9	320.0	319.9	319.8	319.7	319.6	319.6	319.6	319.7
115°	371.9	371.6	371.4	371.3	371.4	371.6	371.9	372.0	372.2	372.4	372.6
117.5°	421.2	420.9	420.4	420.1	420.4	420.9	421.2	421.6	422.1	422.8	423.4
120°	456.1	456.4	456.8	457.2	456.8	456.4	456.1	455.6	456.0	456.9	457.9
122.5°	490.2	489.5	488.8	488.1	488.8	489.5	490.2	490.9	491.5	492.2	492.8
125°	542.6	542.2	541.8	541.4	541.8	542.2	542.6	542.9	543.3	543.7	544.1
127.5°	591.7	591.3	591.1	590.7	591.1	591.3	591.7	591.9	592.3	592.7	593.1
130°	625.3	624.6	623.8	623.0	623.8	624.6	625.3	626.1	626.7	627.1	627.5
132.5°	658.3	658.1	657.7	657.5	657.7	658.1	658.3	658.7	659.0	659.4	659.8
135°	706.5	705.8	705.2	704.7	705.2	705.8	706.5	707.0	707.5	707.8	708.3
137.5°	754.1	754.1	754.2	754.4	754.2	754.1	754.1	753.9	754.1	754.6	755.1
140°	785.2	785.0	784.8	784.6	784.8	785.0	785.2	785.4	785.6	785.7	786.0
142.5°	815.0	814.9	814.9	814.9	814.9	814.9	815.0	815.0	815.1	815.1	815.1
145°	857.6	857.1	856.5	855.9	856.5	857.1	857.6	858.2	858.6	858.8	859.0
147.5°	898.1	897.9	897.8	897.6	897.8	897.9	898.1	898.3	898.5	898.6	898.8
150°	923.6	923.3	923.2	923.0	923.2	923.3	923.6	923.8	923.9	923.9	923.9
152.5°	947.9	947.4	946.8	946.3	946.8	947.4	947.9	948.4	948.4	947.9	947.4
155°	981.1	980.4	979.6	978.9	979.6	980.4	981.1	981.9	981.9	981.1	980.4
157.5°	1009.9	1009.2	1008.6	1007.9	1008.6	1009.2	1009.9	1010.5	1010.6	1010.0	1009.4
160°	1027.3	1026.3	1025.4	1024.4	1025.4	1026.3	1027.3	1028.2	1028.4	1027.9	1027.3
162.5°	1044.5	1043.5	1042.6	1041.6	1042.6	1043.5	1044.5	1045.4	1045.3	1044.3	1043.3
165°	1066.3	1065.5	1064.7	1063.9	1064.7	1065.5	1066.3	1067.0	1066.8	1065.7	1064.5
167.5°	1083.5	1082.3	1081.1	1080.0	1081.1	1082.3	1083.5	1084.7	1084.7	1083.6	1082.4
170°	1092.9	1091.5	1090.2	1088.8	1090.2	1091.5	1092.9	1094.2	1094.3	1093.1	1092.0
172.5°	1100.4	1099.1	1097.8	1096.4	1097.8	1099.1	1100.4	1101.7	1101.8	1100.4	1099.2
175°	1108.4	1107.0	1105.7	1104.3	1105.7	1107.0	1108.4	1109.7	1109.7	1108.4	1107.0
177.5°	1112.2	1110.9	1109.7	1108.5	1109.7	1110.9	1112.2	1113.4	1113.4	1112.3	1111.3
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1413.1	1416.3	1424.0	1432.5	1439.7	1445.9	1450.6	1457.3	1463.5	1472.1	1480.1
5°	1327.3	1335.7	1347.6	1361.8	1379.7	1391.6	1406.5	1419.6	1438.6	1457.7	1476.1
7.5°	1252.1	1261.3	1278.8	1298.5	1319.7	1339.2	1356.8	1379.9	1405.2	1432.9	1463.9
10°	1203.5	1213.7	1234.5	1257.1	1282.1	1301.1	1324.9	1352.3	1380.9	1414.8	1452.9
12.5°	1159.7	1169.3	1194.5	1217.5	1243.5	1264.5	1292.1	1319.9	1358.1	1394.8	1438.1
15°	1074.4	1099.9	1128.5	1155.9	1186.9	1212.5	1245.8	1274.4	1310.7	1362.4	1411.9
17.5°	979.6	1006.9	1042.3	1084.6	1126.1	1157.8	1191.6	1227.1	1270.3	1323.2	1380.2
20°	924.4	946.4	985.7	1032.7	1080.9	1125.0	1155.9	1195.2	1239.8	1297.0	1355.9
22.5°	883.0	901.6	932.4	979.4	1031.4	1082.5	1122.1	1160.9	1210.3	1267.5	1331.6
25°	820.8	841.0	867.8	900.0	959.5	1013.7	1065.4	1110.1	1162.4	1219.6	1291.0
27.5°	769.1	786.8	811.2	844.7	884.8	944.5	1007.2	1058.2	1111.9	1173.2	1244.7
30°	738.7	752.9	773.2	807.1	845.2	898.8	962.4	1022.0	1076.2	1139.8	1214.3
32.5°	706.8	722.0	741.8	768.5	809.5	854.5	918.2	983.4	1040.9	1106.0	1179.0
35°	664.3	676.1	694.1	721.4	758.3	797.5	854.1	921.4	982.1	1051.7	1121.4
37.5°	621.3	635.3	649.4	673.8	704.0	746.3	792.6	861.3	928.5	992.1	1060.1
40°	597.0	605.4	620.8	640.4	672.6	710.1	753.5	820.8	888.0	951.1	1019.6
42.5°	569.9	579.1	592.2	611.9	640.7	677.3	719.7	777.9	848.1	909.2	971.5
45°	532.1	537.4	550.6	567.2	591.1	627.9	667.3	719.0	785.1	843.4	898.2
47.5°	494.0	498.7	506.9	522.1	548.8	578.4	615.2	661.7	719.6	777.9	824.2
50°	467.9	472.0	479.7	494.0	517.8	547.0	583.3	625.0	676.7	732.7	771.4
52.5°	441.6	443.9	451.2	467.4	487.3	516.1	548.5	586.9	635.3	681.7	720.9
55°	400.0	405.4	410.1	422.0	441.1	468.5	497.6	533.9	571.4	610.7	644.0
57.5°	356.5	362.4	369.3	379.8	394.9	420.3	446.5	476.0	508.0	540.5	568.5
60°	328.0	333.3	339.2	351.2	364.9	385.1	413.7	439.3	463.6	493.4	521.4
62.5°	299.9	305.2	312.1	321.7	334.8	354.1	378.0	400.2	425.6	451.5	472.3
65°	258.3	262.5	267.9	276.8	289.3	306.5	326.1	343.5	366.1	385.1	404.2
67.5°	212.8	220.7	227.7	235.0	245.6	261.7	275.9	292.4	307.7	321.9	339.2
70°	182.7	191.7	198.2	206.0	216.0	229.7	243.4	254.8	267.3	280.9	296.4
72.5°	157.5	164.5	169.6	177.9	187.0	199.8	212.5	221.9	232.0	241.4	256.4
75°	124.4	127.3	131.0	137.5	145.9	155.3	165.5	173.8	179.8	188.1	198.8
77.5°	89.4	95.1	97.5	102.1	108.1	114.1	120.7	127.8	133.5	136.4	144.6
80°	68.4	70.9	73.2	79.7	83.3	89.3	94.0	100.6	103.0	106.0	113.7
82.5°	53.2	54.7	56.1	57.9	60.0	66.0	70.7	74.9	77.2	78.4	84.2
85°	30.9	31.5	32.1	32.7	33.3	33.3	35.7	38.7	42.9	42.9	44.6
87.5°	14.5	14.7	14.5	13.6	14.3	13.9	14.1	13.7	14.7	15.7	16.7
90°	20.1	18.9	17.4	15.8	14.3	12.8	11.0	8.9	6.8	4.6	2.6
92.5°	34.7	34.0	33.0	31.9	30.8	29.8	28.0	25.6	23.2	20.8	18.4
95°	65.9	65.3	64.0	62.7	61.3	59.9	58.5	56.7	55.0	53.3	51.6
97.5°	104.0	103.3	101.8	100.1	98.6	97.0	95.6	94.2	92.8	91.4	90.1
100°	131.9	131.5	129.8	128.0	126.3	124.6	123.4	122.6	121.8	121.1	120.3
102.5°	160.9	160.4	158.8	157.2	155.7	154.1	153.2	152.8	152.6	152.2	152.0
105°	205.1	204.6	203.8	203.0	202.2	201.5	201.0	200.8	200.6	200.4	200.3
107.5°	253.0	252.5	252.4	252.3	252.2	252.0	251.8	251.7	251.4	251.2	251.0
110°	285.8	286.2	286.4	286.5	286.7	287.0	286.9	286.5	286.1	285.7	285.3



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	319.8	319.9	320.2	320.6	320.9	321.2	321.4	321.3	321.2	321.2	321.1
115°	372.8	373.0	373.3	373.8	374.1	374.5	374.7	374.7	374.7	374.7	374.7
117.5°	424.0	424.7	425.0	425.2	425.5	425.8	425.9	425.7	425.5	425.4	425.2
120°	458.8	459.8	460.4	460.9	461.5	462.1	462.0	461.2	460.5	459.7	458.9
122.5°	493.5	494.1	494.4	494.6	495.0	495.2	495.2	494.9	494.6	494.3	494.0
125°	544.5	544.8	545.0	545.3	545.4	545.6	545.7	545.7	545.7	545.7	545.7
127.5°	593.5	593.8	594.2	594.4	594.8	595.0	595.0	594.3	593.7	593.2	592.6
130°	627.8	628.2	628.2	628.2	628.2	628.2	627.9	627.3	626.8	626.2	625.6
132.5°	660.1	660.6	660.6	660.8	661.0	661.2	661.0	660.6	660.1	659.8	659.4
135°	708.6	709.0	709.0	709.0	709.0	709.0	708.4	707.3	706.1	705.0	703.9
137.5°	755.6	756.1	755.8	755.5	755.2	754.8	754.5	753.9	753.4	752.9	752.3
140°	786.2	786.4	786.4	786.4	786.4	786.4	786.2	785.7	785.4	785.0	784.6
142.5°	815.2	815.2	815.4	815.5	815.7	815.8	815.7	815.4	814.9	814.6	814.2
145°	859.2	859.4	859.2	859.0	858.8	858.6	858.2	857.4	856.6	855.8	855.1
147.5°	899.0	899.1	899.2	899.4	899.6	899.7	899.3	898.5	897.5	896.6	895.7
150°	923.9	923.9	923.9	923.9	923.9	923.9	923.5	922.7	922.0	921.2	920.4
152.5°	947.0	946.5	946.4	946.2	946.1	945.9	945.6	945.2	944.7	944.3	943.8
155°	979.6	978.9	979.0	979.2	979.4	979.6	979.7	979.7	979.7	979.7	979.7
157.5°	1008.8	1008.2	1008.3	1008.3	1008.3	1008.4	1008.6	1008.9	1009.3	1009.6	1010.0
160°	1026.7	1026.1	1026.3	1026.5	1026.7	1026.9	1027.1	1027.3	1027.4	1027.6	1027.9
162.5°	1042.2	1041.2	1041.5	1041.6	1041.8	1042.0	1042.3	1042.8	1043.4	1043.9	1044.3
165°	1063.3	1062.2	1062.6	1063.0	1063.3	1063.8	1064.2	1064.8	1065.4	1065.9	1066.5
167.5°	1081.2	1080.1	1080.0	1080.0	1080.0	1080.0	1080.3	1081.2	1081.9	1082.7	1083.6
170°	1090.9	1089.7	1089.5	1089.3	1089.2	1088.9	1089.3	1090.3	1091.2	1092.2	1093.1
172.5°	1097.9	1096.6	1096.6	1096.5	1096.5	1096.4	1096.8	1097.6	1098.5	1099.2	1100.0
175°	1105.7	1104.3	1104.5	1104.7	1104.9	1105.1	1105.7	1106.6	1107.6	1108.5	1109.5
177.5°	1110.2	1109.1	1109.1	1109.1	1109.1	1109.1	1109.5	1110.3	1111.0	1111.8	1112.6
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1486.3	1490.6	1495.4	1504.4	1512.1	1515.4	1522.1	1526.8	1525.4	1532.1	1543.5
5°	1492.2	1508.3	1526.7	1545.8	1567.2	1585.0	1599.3	1613.6	1625.0	1638.7	1658.9
7.5°	1491.3	1519.8	1550.9	1585.0	1620.1	1650.5	1678.6	1707.2	1732.5	1760.3	1796.6
10°	1487.5	1525.5	1564.2	1608.9	1653.5	1695.7	1733.9	1769.5	1803.5	1839.8	1885.7
12.5°	1483.2	1527.0	1573.7	1627.5	1683.0	1733.9	1778.7	1830.1	1872.5	1919.3	1972.3
15°	1464.2	1523.1	1586.8	1656.5	1723.1	1791.6	1852.9	1916.0	1974.9	2030.8	2097.6
17.5°	1442.5	1510.5	1585.6	1667.9	1748.0	1831.3	1903.9	1983.5	2043.8	2118.8	2180.7
20°	1425.0	1498.1	1578.5	1670.8	1761.9	1854.1	1934.4	2015.4	2083.3	2158.9	2237.4
22.5°	1403.5	1483.8	1570.9	1666.5	1761.9	1862.7	1951.5	2032.0	2116.1	2201.2	2282.2
25°	1369.0	1452.3	1544.5	1649.3	1758.9	1861.8	1957.1	2057.0	2147.5	2239.8	2312.4
27.5°	1326.6	1414.1	1511.4	1619.5	1731.8	1837.3	1949.5	2056.0	2147.1	2235.8	2299.2
30°	1292.8	1385.1	1478.5	1588.0	1704.7	1817.7	1938.0	2044.5	2140.4	2220.2	2255.8
32.5°	1258.0	1345.6	1441.8	1552.8	1672.3	1794.0	1913.2	2022.1	2110.8	2158.7	2159.6
35°	1197.6	1279.7	1379.7	1488.7	1611.3	1743.4	1864.2	1971.3	2025.5	2029.6	1971.3
37.5°	1131.6	1206.9	1301.4	1410.4	1544.7	1676.1	1799.6	1871.0	1889.1	1828.5	1720.6
40°	1084.5	1154.1	1245.2	1357.1	1490.4	1626.1	1738.6	1791.0	1771.9	1673.7	1553.5
42.5°	1034.9	1099.8	1187.6	1298.0	1431.8	1569.0	1664.8	1692.9	1642.4	1529.0	1388.3
45°	954.2	1013.7	1100.5	1211.9	1340.4	1469.0	1541.6	1527.3	1443.4	1308.9	1151.2
47.5°	870.0	927.5	1005.6	1108.6	1240.3	1351.3	1400.4	1357.4	1237.9	1089.9	961.7
50°	814.2	873.1	945.2	1043.4	1163.6	1270.7	1302.3	1236.8	1104.1	961.8	844.0
52.5°	759.5	809.9	880.5	975.3	1090.3	1180.8	1197.6	1122.1	985.1	857.6	753.0
55°	676.1	722.0	781.5	870.8	970.2	1047.0	1038.0	941.1	816.7	707.7	625.6
57.5°	595.6	630.1	685.1	768.8	856.0	907.6	874.9	792.2	676.3	587.1	517.8
60°	542.3	574.4	625.6	698.8	775.6	804.7	777.3	687.5	595.8	514.3	455.9
62.5°	491.8	520.1	564.1	632.1	694.1	711.4	682.1	603.6	521.1	451.4	403.1
65°	418.4	444.6	482.2	530.4	573.2	581.5	562.5	482.2	419.7	361.3	328.0
67.5°	351.9	369.0	398.3	440.0	462.7	467.6	430.8	380.3	325.2	289.4	264.2
70°	307.1	319.0	346.4	369.0	387.4	388.1	354.1	313.7	271.4	242.3	223.8
72.5°	263.8	275.3	295.9	311.4	325.5	321.0	289.9	258.0	223.8	201.8	188.1
75°	203.5	213.7	224.4	231.5	231.5	225.6	202.9	179.2	159.5	146.5	142.2
77.5°	148.0	156.3	159.9	158.8	156.7	147.4	133.1	117.5	110.5	104.3	101.2
80°	116.1	119.7	120.8	117.9	114.3	103.6	94.0	87.5	80.9	78.6	77.4
82.5°	86.1	89.2	86.1	86.9	79.0	70.3	65.0	62.8	60.0	59.1	57.9
85°	45.8	45.2	44.1	41.1	35.7	34.5	33.9	33.3	32.1	32.7	31.5
87.5°	16.6	15.7	14.1	14.1	14.5	13.8	14.6	14.9	15.2	15.0	16.2
90°	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1	21.2
92.5°	20.8	23.2	25.6	28.0	29.8	30.8	31.9	33.0	34.0	34.7	35.4
95°	53.3	55.0	56.7	58.5	59.9	61.3	62.7	64.0	65.3	65.9	66.5
97.5°	91.4	92.8	94.2	95.6	97.0	98.6	100.1	101.8	103.3	104.0	104.7
100°	121.1	121.8	122.6	123.4	124.6	126.3	128.0	129.8	131.5	131.9	132.2
102.5°	152.2	152.6	152.8	153.2	154.1	155.7	157.2	158.8	160.4	160.9	161.4
105°	200.4	200.6	200.8	201.0	201.5	202.2	203.0	203.8	204.6	205.1	205.7
107.5°	251.2	251.4	251.7	251.8	252.0	252.2	252.3	252.4	252.5	253.0	253.6
110°	285.7	286.1	286.5	286.9	287.0	286.7	286.5	286.4	286.2	285.8	285.4



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	321.2	321.2	321.3	321.4	321.2	320.9	320.6	320.2	319.9	319.8	319.7
115°	374.7	374.7	374.7	374.7	374.5	374.1	373.8	373.3	373.0	372.8	372.6
117.5°	425.4	425.5	425.7	425.9	425.8	425.5	425.2	425.0	424.7	424.0	423.4
120°	459.7	460.5	461.2	462.0	462.1	461.5	460.9	460.4	459.8	458.8	457.9
122.5°	494.3	494.6	494.9	495.2	495.2	495.0	494.6	494.4	494.1	493.5	492.8
125°	545.7	545.7	545.7	545.7	545.6	545.4	545.3	545.0	544.8	544.5	544.1
127.5°	593.2	593.7	594.3	595.0	595.0	594.8	594.4	594.2	593.8	593.5	593.1
130°	626.2	626.8	627.3	627.9	628.2	628.2	628.2	628.2	628.2	627.8	627.5
132.5°	659.8	660.1	660.6	661.0	661.2	661.0	660.8	660.6	660.6	660.1	659.8
135°	705.0	706.1	707.3	708.4	709.0	709.0	709.0	709.0	709.0	708.6	708.3
137.5°	752.9	753.4	753.9	754.5	754.8	755.2	755.5	755.8	756.1	755.6	755.1
140°	785.0	785.4	785.7	786.2	786.4	786.4	786.4	786.4	786.4	786.2	786.0
142.5°	814.6	814.9	815.4	815.7	815.8	815.7	815.5	815.4	815.2	815.2	815.1
145°	855.8	856.6	857.4	858.2	858.6	858.8	859.0	859.2	859.4	859.2	859.0
147.5°	896.6	897.5	898.5	899.3	899.7	899.6	899.4	899.2	899.1	899.0	898.8
150°	921.2	922.0	922.7	923.5	923.9	923.9	923.9	923.9	923.9	923.9	923.9
152.5°	944.3	944.7	945.2	945.6	945.9	946.1	946.2	946.4	946.5	947.0	947.4
155°	979.7	979.7	979.7	979.7	979.6	979.4	979.2	979.0	978.9	979.6	980.4
157.5°	1009.6	1009.3	1008.9	1008.6	1008.4	1008.3	1008.3	1008.3	1008.2	1008.8	1009.4
160°	1027.6	1027.4	1027.3	1027.1	1026.9	1026.7	1026.5	1026.3	1026.1	1026.7	1027.3
162.5°	1043.9	1043.4	1042.8	1042.3	1042.0	1041.8	1041.6	1041.5	1041.2	1042.2	1043.3
165°	1065.9	1065.4	1064.8	1064.2	1063.8	1063.3	1063.0	1062.6	1062.2	1063.3	1064.5
167.5°	1082.7	1081.9	1081.2	1080.3	1080.0	1080.0	1080.0	1080.0	1080.1	1081.2	1082.4
170°	1092.2	1091.2	1090.3	1089.3	1088.9	1089.2	1089.3	1089.5	1089.7	1090.9	1092.0
172.5°	1099.2	1098.5	1097.6	1096.8	1096.4	1096.5	1096.5	1096.6	1096.6	1097.9	1099.2
175°	1108.5	1107.6	1106.6	1105.7	1105.1	1104.9	1104.7	1104.5	1104.3	1105.7	1107.0
177.5°	1111.8	1111.0	1110.3	1109.5	1109.1	1109.1	1109.1	1109.1	1109.1	1110.2	1111.3
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3	1477.3
2.5°	1549.7	1551.6	1553.1	1557.8	1558.2	1562.5	1558.2
5°	1677.9	1686.3	1699.4	1712.4	1713.6	1721.9	1707.1
7.5°	1821.7	1841.0	1853.0	1874.2	1882.6	1887.7	1879.2
10°	1920.7	1938.6	1970.1	1985.6	2001.1	2003.5	1996.3
12.5°	2016.5	2044.8	2069.7	2098.9	2098.3	2119.2	2111.6
15°	2144.0	2173.2	2207.6	2240.4	2252.3	2252.3	2261.8
17.5°	2234.9	2288.4	2324.1	2349.8	2377.9	2382.7	2379.5
20°	2296.4	2354.1	2392.2	2425.5	2444.6	2449.9	2449.9
22.5°	2342.0	2391.2	2428.4	2458.3	2474.1	2480.4	2478.5
25°	2373.7	2416.0	2438.6	2447.5	2451.7	2450.5	2439.2
27.5°	2330.4	2328.5	2314.2	2286.8	2266.2	2253.8	2239.5
30°	2247.6	2216.6	2180.8	2141.6	2091.0	2052.3	2040.4
32.5°	2124.2	2054.7	1994.2	1928.7	1874.3	1835.7	1819.5
35°	1885.7	1775.6	1685.7	1607.1	1550.0	1514.2	1502.4
37.5°	1602.6	1496.0	1384.7	1308.5	1261.1	1225.0	1211.6
40°	1422.5	1306.5	1209.4	1138.1	1089.3	1054.1	1053.5
42.5°	1258.3	1147.5	1056.2	1004.7	952.1	928.8	928.8
45°	1030.3	941.6	864.3	823.8	792.2	773.2	767.8
47.5°	853.1	779.7	728.1	695.9	670.2	658.1	650.2
50°	753.5	689.2	648.2	620.2	605.9	590.5	589.3
52.5°	670.7	618.8	586.8	564.0	546.0	536.7	536.9
55°	563.7	522.6	500.0	482.7	468.5	461.3	458.3
57.5°	474.8	444.0	427.6	411.7	405.7	400.1	398.6
60°	419.7	398.8	383.3	370.8	361.9	360.1	359.5
62.5°	373.9	352.1	341.4	331.7	325.2	322.4	321.4
65°	308.3	292.2	282.8	275.0	272.6	268.5	267.9
67.5°	248.6	238.9	232.6	227.2	224.0	223.8	223.8
70°	211.9	206.6	201.2	198.2	196.4	195.2	195.2
72.5°	180.5	176.5	172.1	170.6	170.2	169.0	168.6
75°	137.5	133.4	133.9	131.0	128.5	125.6	123.8
77.5°	97.5	94.5	93.9	93.6	91.5	91.2	92.1
80°	75.6	72.6	72.0	72.6	72.0	70.3	70.3
82.5°	57.5	55.0	54.4	54.1	53.5	54.1	53.1
85°	30.9	29.8	29.8	29.8	30.9	30.4	29.8
87.5°	15.4	15.2	15.8	15.4	15.5	15.1	15.7
90°	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	36.1	36.8	37.3	37.5	37.7	38.0	38.1
95°	67.1	67.6	67.9	67.9	67.9	67.9	67.9
97.5°	105.4	106.1	106.4	106.4	106.4	106.4	106.4
100°	132.6	133.0	133.2	133.2	133.2	133.2	133.2
102.5°	162.0	162.5	162.8	163.0	163.2	163.3	163.4
105°	206.3	206.8	207.4	207.9	208.5	209.1	209.7
107.5°	254.1	254.6	254.9	254.9	254.8	254.8	254.7
110°	285.0	284.6	284.7	285.3	285.9	286.5	287.1



TEST NUMBER: P332974-935

CATALOG NUMBER: S124RDIP-S1020D1035U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.6	319.6	319.6	319.7	319.8	319.9	320.0
115°	372.4	372.2	372.0	371.9	371.6	371.4	371.3
117.5°	422.8	422.1	421.6	421.2	420.9	420.4	420.1
120°	456.9	456.0	455.6	456.1	456.4	456.8	457.2
122.5°	492.2	491.5	490.9	490.2	489.5	488.8	488.1
125°	543.7	543.3	542.9	542.6	542.2	541.8	541.4
127.5°	592.7	592.3	591.9	591.7	591.3	591.1	590.7
130°	627.1	626.7	626.1	625.3	624.6	623.8	623.0
132.5°	659.4	659.0	658.7	658.3	658.1	657.7	657.5
135°	707.8	707.5	707.0	706.5	705.8	705.2	704.7
137.5°	754.6	754.1	753.9	754.1	754.1	754.2	754.4
140°	785.7	785.6	785.4	785.2	785.0	784.8	784.6
142.5°	815.1	815.1	815.0	815.0	814.9	814.9	814.9
145°	858.8	858.6	858.2	857.6	857.1	856.5	855.9
147.5°	898.6	898.5	898.3	898.1	897.9	897.8	897.6
150°	923.9	923.9	923.8	923.6	923.3	923.2	923.0
152.5°	947.9	948.4	948.4	947.9	947.4	946.8	946.3
155°	981.1	981.9	981.9	981.1	980.4	979.6	978.9
157.5°	1010.0	1010.6	1010.5	1009.9	1009.2	1008.6	1007.9
160°	1027.9	1028.4	1028.2	1027.3	1026.3	1025.4	1024.4
162.5°	1044.3	1045.3	1045.4	1044.5	1043.5	1042.6	1041.6
165°	1065.7	1066.8	1067.0	1066.3	1065.5	1064.7	1063.9
167.5°	1083.6	1084.7	1084.7	1083.5	1082.3	1081.1	1080.0
170°	1093.1	1094.3	1094.2	1092.9	1091.5	1090.2	1088.8
172.5°	1100.4	1101.8	1101.7	1100.4	1099.1	1097.8	1096.4
175°	1108.4	1109.7	1109.7	1108.4	1107.0	1105.7	1104.3
177.5°	1112.3	1113.4	1113.4	1112.2	1110.9	1109.7	1108.5
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2

(END OF REPORT)