

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332884-935

Luminaire Tested: **S124RDIP-S350D1035U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332884-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D1035U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4364.7 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	33	32	25
2	85	78	72	68	76	70	66	61	56	52	49	42	40	38	30	28	27	22
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23	19
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20	16
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	1.1
10°-20°	147.8	3.4
20°-30°	231.2	5.3
30°-40°	257.0	5.9
40°-50°	228.0	5.2
50°-60°	177.7	4.1
60°-70°	116.3	2.7
70°-80°	57.2	1.3
80°-90°	17.4	0.4
90°-100°	73.3	1.7
100°-110°	217.1	5.0
110°-120°	368.5	8.4
120°-130°	485.9	11.1
130°-140°	545.7	12.5
140°-150°	536.2	12.3
150°-160°	451.0	10.3
160°-170°	300.1	6.9
170°-180°	105.1	2.4
0°-30°	428.0	9.8
0°-40°	685.0	15.7
0°-60°	1090.8	25.0
0°-90°	1281.8	29.4
90°-120°	658.9	15.1
90°-150°	2226.8	51.0
90°-180°	3083.0	70.6
0°-180°	4364.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	26	3	26	3	26	13
95°	68	52	68	52	68	71
105°	210	200	210	200	210	221
115°	371	375	371	375	371	367
125°	541	546	541	546	541	483
135°	705	704	705	704	705	544
145°	856	855	856	855	856	536
155°	979	980	979	980	979	451
165°	1064	1066	1064	1066	1064	300
175°	1104	1110	1104	1110	1104	105
180°	1111	1111	1111	1111	1111	



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	8.8	8.5	8.6	8.5	8.6	8.3	8.2	8.4	7.7	7.7	7.4
90°	25.7	25.4	25.1	24.6	24.3	23.5	22.4	21.2	20.1	18.9	17.4
92.5°	38.1	38.0	37.7	37.5	37.3	36.8	36.1	35.4	34.7	34.0	33.0
95°	67.9	67.9	67.9	67.9	67.9	67.6	67.1	66.5	65.9	65.3	64.0
97.5°	106.4	106.4	106.4	106.4	106.4	106.1	105.4	104.7	104.0	103.3	101.8
100°	133.2	133.2	133.2	133.2	133.2	133.0	132.6	132.2	131.9	131.5	129.8
102.5°	163.4	163.3	163.2	163.0	162.8	162.5	162.0	161.4	160.9	160.4	158.8
105°	209.7	209.1	208.5	207.9	207.4	206.8	206.3	205.7	205.1	204.6	203.8
107.5°	254.7	254.8	254.8	254.9	254.9	254.6	254.1	253.6	253.0	252.5	252.4
110°	287.1	286.5	285.9	285.3	284.7	284.6	285.0	285.4	285.8	286.2	286.4



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	320.0	319.9	319.8	319.7	319.6	319.6	319.6	319.7	319.8	319.9	320.2
115°	371.3	371.4	371.6	371.9	372.0	372.2	372.4	372.6	372.8	373.0	373.3
117.5°	420.1	420.4	420.9	421.2	421.6	422.1	422.8	423.4	424.0	424.7	425.0
120°	457.2	456.8	456.4	456.1	455.6	456.0	456.9	457.9	458.8	459.8	460.4
122.5°	488.1	488.8	489.5	490.2	490.9	491.5	492.2	492.8	493.5	494.1	494.4
125°	541.4	541.8	542.2	542.6	542.9	543.3	543.7	544.1	544.5	544.8	545.0
127.5°	590.7	591.1	591.3	591.7	591.9	592.3	592.7	593.1	593.5	593.8	594.2
130°	623.0	623.8	624.6	625.3	626.1	626.7	627.1	627.5	627.8	628.2	628.2
132.5°	657.5	657.7	658.1	658.3	658.7	659.0	659.4	659.8	660.1	660.6	660.6
135°	704.7	705.2	705.8	706.5	707.0	707.5	707.8	708.3	708.6	709.0	709.0
137.5°	754.4	754.2	754.1	754.1	753.9	754.1	754.6	755.1	755.6	756.1	755.8
140°	784.6	784.8	785.0	785.2	785.4	785.6	785.7	786.0	786.2	786.4	786.4
142.5°	814.9	814.9	814.9	815.0	815.0	815.1	815.1	815.1	815.2	815.2	815.4
145°	855.9	856.5	857.1	857.6	858.2	858.6	858.8	859.0	859.2	859.4	859.2
147.5°	897.6	897.8	897.9	898.1	898.3	898.5	898.6	898.8	899.0	899.1	899.2
150°	923.0	923.2	923.3	923.6	923.8	923.9	923.9	923.9	923.9	923.9	923.9
152.5°	946.3	946.8	947.4	947.9	948.4	948.4	947.9	947.4	947.0	946.5	946.4
155°	978.9	979.6	980.4	981.1	981.9	981.9	981.1	980.4	979.6	978.9	979.0
157.5°	1007.9	1008.6	1009.2	1009.9	1010.5	1010.6	1010.0	1009.4	1008.8	1008.2	1008.3
160°	1024.4	1025.4	1026.3	1027.3	1028.2	1028.4	1027.9	1027.3	1026.7	1026.1	1026.3
162.5°	1041.6	1042.6	1043.5	1044.5	1045.4	1045.3	1044.3	1043.3	1042.2	1041.2	1041.5
165°	1063.9	1064.7	1065.5	1066.3	1067.0	1066.8	1065.7	1064.5	1063.3	1062.2	1062.6
167.5°	1080.0	1081.1	1082.3	1083.5	1084.7	1084.7	1083.6	1082.4	1081.2	1080.1	1080.0
170°	1088.8	1090.2	1091.5	1092.9	1094.2	1094.3	1093.1	1092.0	1090.9	1089.7	1089.5
172.5°	1096.4	1097.8	1099.1	1100.4	1101.7	1101.8	1100.4	1099.2	1097.9	1096.6	1096.6
175°	1104.3	1105.7	1107.0	1108.4	1109.7	1109.7	1108.4	1107.0	1105.7	1104.3	1104.5
177.5°	1108.5	1109.7	1110.9	1112.2	1113.4	1113.4	1112.3	1111.3	1110.2	1109.1	1109.1
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	7.1	6.6	6.6	6.3	6.0	6.3	6.3	6.0	6.0	5.9	5.9
90°	15.8	14.3	12.8	11.0	8.9	6.8	4.6	2.6	4.6	6.8	8.9
92.5°	31.9	30.8	29.8	28.0	25.6	23.2	20.8	18.4	20.8	23.2	25.6
95°	62.7	61.3	59.9	58.5	56.7	55.0	53.3	51.6	53.3	55.0	56.7
97.5°	100.1	98.6	97.0	95.6	94.2	92.8	91.4	90.1	91.4	92.8	94.2
100°	128.0	126.3	124.6	123.4	122.6	121.8	121.1	120.3	121.1	121.8	122.6
102.5°	157.2	155.7	154.1	153.2	152.8	152.6	152.2	152.0	152.2	152.6	152.8
105°	203.0	202.2	201.5	201.0	200.8	200.6	200.4	200.3	200.4	200.6	200.8
107.5°	252.3	252.2	252.0	251.8	251.7	251.4	251.2	251.0	251.2	251.4	251.7
110°	286.5	286.7	287.0	286.9	286.5	286.1	285.7	285.3	285.7	286.1	286.5





TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	320.6	320.9	321.2	321.4	321.3	321.2	321.2	321.1	321.2	321.2	321.3
115°	373.8	374.1	374.5	374.7	374.7	374.7	374.7	374.7	374.7	374.7	374.7
117.5°	425.2	425.5	425.8	425.9	425.7	425.5	425.4	425.2	425.4	425.5	425.7
120°	460.9	461.5	462.1	462.0	461.2	460.5	459.7	458.9	459.7	460.5	461.2
122.5°	494.6	495.0	495.2	495.2	494.9	494.6	494.3	494.0	494.3	494.6	494.9
125°	545.3	545.4	545.6	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.7
127.5°	594.4	594.8	595.0	595.0	594.3	593.7	593.2	592.6	593.2	593.7	594.3
130°	628.2	628.2	628.2	627.9	627.3	626.8	626.2	625.6	626.2	626.8	627.3
132.5°	660.8	661.0	661.2	661.0	660.6	660.1	659.8	659.4	659.8	660.1	660.6
135°	709.0	709.0	709.0	708.4	707.3	706.1	705.0	703.9	705.0	706.1	707.3
137.5°	755.5	755.2	754.8	754.5	753.9	753.4	752.9	752.3	752.9	753.4	753.9
140°	786.4	786.4	786.4	786.2	785.7	785.4	785.0	784.6	785.0	785.4	785.7
142.5°	815.5	815.7	815.8	815.7	815.4	814.9	814.6	814.2	814.6	814.9	815.4
145°	859.0	858.8	858.6	858.2	857.4	856.6	855.8	855.1	855.8	856.6	857.4
147.5°	899.4	899.6	899.7	899.3	898.5	897.5	896.6	895.7	896.6	897.5	898.5
150°	923.9	923.9	923.9	923.5	922.7	922.0	921.2	920.4	921.2	922.0	922.7
152.5°	946.2	946.1	945.9	945.6	945.2	944.7	944.3	943.8	944.3	944.7	945.2
155°	979.2	979.4	979.6	979.7	979.7	979.7	979.7	979.7	979.7	979.7	979.7
157.5°	1008.3	1008.3	1008.4	1008.6	1008.9	1009.3	1009.6	1010.0	1009.6	1009.3	1008.9
160°	1026.5	1026.7	1026.9	1027.1	1027.3	1027.4	1027.6	1027.9	1027.6	1027.4	1027.3
162.5°	1041.6	1041.8	1042.0	1042.3	1042.8	1043.4	1043.9	1044.3	1043.9	1043.4	1042.8
165°	1063.0	1063.3	1063.8	1064.2	1064.8	1065.4	1065.9	1066.5	1065.9	1065.4	1064.8
167.5°	1080.0	1080.0	1080.0	1080.3	1081.2	1081.9	1082.7	1083.6	1082.7	1081.9	1081.2
170°	1089.3	1089.2	1088.9	1089.3	1090.3	1091.2	1092.2	1093.1	1092.2	1091.2	1090.3
172.5°	1096.5	1096.5	1096.4	1096.8	1097.6	1098.5	1099.2	1100.0	1099.2	1098.5	1097.6
175°	1104.7	1104.9	1105.1	1105.7	1106.6	1107.6	1108.5	1109.5	1108.5	1107.6	1106.6
177.5°	1109.1	1109.1	1109.1	1109.5	1110.3	1111.0	1111.8	1112.6	1111.8	1111.0	1110.3
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	6.3	6.5	6.8	6.7	7.2	7.5	7.6	7.8	8.2	8.1	8.3
90°	11.0	12.8	14.3	15.8	17.4	18.9	20.1	21.2	22.4	23.5	24.3
92.5°	28.0	29.8	30.8	31.9	33.0	34.0	34.7	35.4	36.1	36.8	37.3
95°	58.5	59.9	61.3	62.7	64.0	65.3	65.9	66.5	67.1	67.6	67.9
97.5°	95.6	97.0	98.6	100.1	101.8	103.3	104.0	104.7	105.4	106.1	106.4
100°	123.4	124.6	126.3	128.0	129.8	131.5	131.9	132.2	132.6	133.0	133.2
102.5°	153.2	154.1	155.7	157.2	158.8	160.4	160.9	161.4	162.0	162.5	162.8
105°	201.0	201.5	202.2	203.0	203.8	204.6	205.1	205.7	206.3	206.8	207.4
107.5°	251.8	252.0	252.2	252.3	252.4	252.5	253.0	253.6	254.1	254.6	254.9
110°	286.9	287.0	286.7	286.5	286.4	286.2	285.8	285.4	285.0	284.6	284.7



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	321.4	321.2	320.9	320.6	320.2	319.9	319.8	319.7	319.6	319.6	319.6
115°	374.7	374.5	374.1	373.8	373.3	373.0	372.8	372.6	372.4	372.2	372.0
117.5°	425.9	425.8	425.5	425.2	425.0	424.7	424.0	423.4	422.8	422.1	421.6
120°	462.0	462.1	461.5	460.9	460.4	459.8	458.8	457.9	456.9	456.0	455.6
122.5°	495.2	495.2	495.0	494.6	494.4	494.1	493.5	492.8	492.2	491.5	490.9
125°	545.7	545.6	545.4	545.3	545.0	544.8	544.5	544.1	543.7	543.3	542.9
127.5°	595.0	595.0	594.8	594.4	594.2	593.8	593.5	593.1	592.7	592.3	591.9
130°	627.9	628.2	628.2	628.2	628.2	628.2	627.8	627.5	627.1	626.7	626.1
132.5°	661.0	661.2	661.0	660.8	660.6	660.6	660.1	659.8	659.4	659.0	658.7
135°	708.4	709.0	709.0	709.0	709.0	709.0	708.6	708.3	707.8	707.5	707.0
137.5°	754.5	754.8	755.2	755.5	755.8	756.1	755.6	755.1	754.6	754.1	753.9
140°	786.2	786.4	786.4	786.4	786.4	786.4	786.2	786.0	785.7	785.6	785.4
142.5°	815.7	815.8	815.7	815.5	815.4	815.2	815.2	815.1	815.1	815.1	815.0
145°	858.2	858.6	858.8	859.0	859.2	859.4	859.2	859.0	858.8	858.6	858.2
147.5°	899.3	899.7	899.6	899.4	899.2	899.1	899.0	898.8	898.6	898.5	898.3
150°	923.5	923.9	923.9	923.9	923.9	923.9	923.9	923.9	923.9	923.9	923.8
152.5°	945.6	945.9	946.1	946.2	946.4	946.5	947.0	947.4	947.9	948.4	948.4
155°	979.7	979.6	979.4	979.2	979.0	978.9	979.6	980.4	981.1	981.9	981.9
157.5°	1008.6	1008.4	1008.3	1008.3	1008.3	1008.2	1008.8	1009.4	1010.0	1010.6	1010.5
160°	1027.1	1026.9	1026.7	1026.5	1026.3	1026.1	1026.7	1027.3	1027.9	1028.4	1028.2
162.5°	1042.3	1042.0	1041.8	1041.6	1041.5	1041.2	1042.2	1043.3	1044.3	1045.3	1045.4
165°	1064.2	1063.8	1063.3	1063.0	1062.6	1062.2	1063.3	1064.5	1065.7	1066.8	1067.0
167.5°	1080.3	1080.0	1080.0	1080.0	1080.0	1080.1	1081.2	1082.4	1083.6	1084.7	1084.7
170°	1089.3	1088.9	1089.2	1089.3	1089.5	1089.7	1090.9	1092.0	1093.1	1094.3	1094.2
172.5°	1096.8	1096.4	1096.5	1096.5	1096.6	1096.6	1097.9	1099.2	1100.4	1101.8	1101.7
175°	1105.7	1105.1	1104.9	1104.7	1104.5	1104.3	1105.7	1107.0	1108.4	1109.7	1109.7
177.5°	1109.5	1109.1	1109.1	1109.1	1109.1	1109.1	1110.2	1111.3	1112.3	1113.4	1113.4
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	8.7	8.6	8.5	8.8	8.5	8.6	8.7	8.3	8.1	8.2	7.8
90°	24.6	25.1	25.4	25.7	25.4	25.1	24.6	24.3	23.5	22.4	21.2
92.5°	37.5	37.7	38.0	38.1	38.0	37.7	37.5	37.3	36.8	36.1	35.4
95°	67.9	67.9	67.9	67.9	67.9	67.9	67.9	67.9	67.6	67.1	66.5
97.5°	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.1	105.4	104.7
100°	133.2	133.2	133.2	133.2	133.2	133.2	133.2	133.2	133.0	132.6	132.2
102.5°	163.0	163.2	163.3	163.4	163.3	163.2	163.0	162.8	162.5	162.0	161.4
105°	207.9	208.5	209.1	209.7	209.1	208.5	207.9	207.4	206.8	206.3	205.7
107.5°	254.9	254.8	254.8	254.7	254.8	254.8	254.9	254.9	254.6	254.1	253.6
110°	285.3	285.9	286.5	287.1	286.5	285.9	285.3	284.7	284.6	285.0	285.4



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	319.7	319.8	319.9	320.0	319.9	319.8	319.7	319.6	319.6	319.6	319.7
115°	371.9	371.6	371.4	371.3	371.4	371.6	371.9	372.0	372.2	372.4	372.6
117.5°	421.2	420.9	420.4	420.1	420.4	420.9	421.2	421.6	422.1	422.8	423.4
120°	456.1	456.4	456.8	457.2	456.8	456.4	456.1	455.6	456.0	456.9	457.9
122.5°	490.2	489.5	488.8	488.1	488.8	489.5	490.2	490.9	491.5	492.2	492.8
125°	542.6	542.2	541.8	541.4	541.8	542.2	542.6	542.9	543.3	543.7	544.1
127.5°	591.7	591.3	591.1	590.7	591.1	591.3	591.7	591.9	592.3	592.7	593.1
130°	625.3	624.6	623.8	623.0	623.8	624.6	625.3	626.1	626.7	627.1	627.5
132.5°	658.3	658.1	657.7	657.5	657.7	658.1	658.3	658.7	659.0	659.4	659.8
135°	706.5	705.8	705.2	704.7	705.2	705.8	706.5	707.0	707.5	707.8	708.3
137.5°	754.1	754.1	754.2	754.4	754.2	754.1	754.1	753.9	754.1	754.6	755.1
140°	785.2	785.0	784.8	784.6	784.8	785.0	785.2	785.4	785.6	785.7	786.0
142.5°	815.0	814.9	814.9	814.9	814.9	814.9	815.0	815.0	815.1	815.1	815.1
145°	857.6	857.1	856.5	855.9	856.5	857.1	857.6	858.2	858.6	858.8	859.0
147.5°	898.1	897.9	897.8	897.6	897.8	897.9	898.1	898.3	898.5	898.6	898.8
150°	923.6	923.3	923.2	923.0	923.2	923.3	923.6	923.8	923.9	923.9	923.9
152.5°	947.9	947.4	946.8	946.3	946.8	947.4	947.9	948.4	948.4	947.9	947.4
155°	981.1	980.4	979.6	978.9	979.6	980.4	981.1	981.9	981.9	981.1	980.4
157.5°	1009.9	1009.2	1008.6	1007.9	1008.6	1009.2	1009.9	1010.5	1010.6	1010.0	1009.4
160°	1027.3	1026.3	1025.4	1024.4	1025.4	1026.3	1027.3	1028.2	1028.4	1027.9	1027.3
162.5°	1044.5	1043.5	1042.6	1041.6	1042.6	1043.5	1044.5	1045.4	1045.3	1044.3	1043.3
165°	1066.3	1065.5	1064.7	1063.9	1064.7	1065.5	1066.3	1067.0	1066.8	1065.7	1064.5
167.5°	1083.5	1082.3	1081.1	1080.0	1081.1	1082.3	1083.5	1084.7	1084.7	1083.6	1082.4
170°	1092.9	1091.5	1090.2	1088.8	1090.2	1091.5	1092.9	1094.2	1094.3	1093.1	1092.0
172.5°	1100.4	1099.1	1097.8	1096.4	1097.8	1099.1	1100.4	1101.7	1101.8	1100.4	1099.2
175°	1108.4	1107.0	1105.7	1104.3	1105.7	1107.0	1108.4	1109.7	1109.7	1108.4	1107.0
177.5°	1112.2	1110.9	1109.7	1108.5	1109.7	1110.9	1112.2	1113.4	1113.4	1112.3	1111.3
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	7.6	7.5	7.2	6.7	6.8	6.5	6.3	5.9	5.9	6.0	6.0
90°	20.1	18.9	17.4	15.8	14.3	12.8	11.0	8.9	6.8	4.6	2.6
92.5°	34.7	34.0	33.0	31.9	30.8	29.8	28.0	25.6	23.2	20.8	18.4
95°	65.9	65.3	64.0	62.7	61.3	59.9	58.5	56.7	55.0	53.3	51.6
97.5°	104.0	103.3	101.8	100.1	98.6	97.0	95.6	94.2	92.8	91.4	90.1
100°	131.9	131.5	129.8	128.0	126.3	124.6	123.4	122.6	121.8	121.1	120.3
102.5°	160.9	160.4	158.8	157.2	155.7	154.1	153.2	152.8	152.6	152.2	152.0
105°	205.1	204.6	203.8	203.0	202.2	201.5	201.0	200.8	200.6	200.4	200.3
107.5°	253.0	252.5	252.4	252.3	252.2	252.0	251.8	251.7	251.4	251.2	251.0
110°	285.8	286.2	286.4	286.5	286.7	287.0	286.9	286.5	286.1	285.7	285.3



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	319.8	319.9	320.2	320.6	320.9	321.2	321.4	321.3	321.2	321.2	321.1
115°	372.8	373.0	373.3	373.8	374.1	374.5	374.7	374.7	374.7	374.7	374.7
117.5°	424.0	424.7	425.0	425.2	425.5	425.8	425.9	425.7	425.5	425.4	425.2
120°	458.8	459.8	460.4	460.9	461.5	462.1	462.0	461.2	460.5	459.7	458.9
122.5°	493.5	494.1	494.4	494.6	495.0	495.2	495.2	494.9	494.6	494.3	494.0
125°	544.5	544.8	545.0	545.3	545.4	545.6	545.7	545.7	545.7	545.7	545.7
127.5°	593.5	593.8	594.2	594.4	594.8	595.0	595.0	594.3	593.7	593.2	592.6
130°	627.8	628.2	628.2	628.2	628.2	628.2	627.9	627.3	626.8	626.2	625.6
132.5°	660.1	660.6	660.6	660.8	661.0	661.2	661.0	660.6	660.1	659.8	659.4
135°	708.6	709.0	709.0	709.0	709.0	709.0	708.4	707.3	706.1	705.0	703.9
137.5°	755.6	756.1	755.8	755.5	755.2	754.8	754.5	753.9	753.4	752.9	752.3
140°	786.2	786.4	786.4	786.4	786.4	786.4	786.2	785.7	785.4	785.0	784.6
142.5°	815.2	815.2	815.4	815.5	815.7	815.8	815.7	815.4	814.9	814.6	814.2
145°	859.2	859.4	859.2	859.0	858.8	858.6	858.2	857.4	856.6	855.8	855.1
147.5°	899.0	899.1	899.2	899.4	899.6	899.7	899.3	898.5	897.5	896.6	895.7
150°	923.9	923.9	923.9	923.9	923.9	923.9	923.5	922.7	922.0	921.2	920.4
152.5°	947.0	946.5	946.4	946.2	946.1	945.9	945.6	945.2	944.7	944.3	943.8
155°	979.6	978.9	979.0	979.2	979.4	979.6	979.7	979.7	979.7	979.7	979.7
157.5°	1008.8	1008.2	1008.3	1008.3	1008.3	1008.4	1008.6	1008.9	1009.3	1009.6	1010.0
160°	1026.7	1026.1	1026.3	1026.5	1026.7	1026.9	1027.1	1027.3	1027.4	1027.6	1027.9
162.5°	1042.2	1041.2	1041.5	1041.6	1041.8	1042.0	1042.3	1042.8	1043.4	1043.9	1044.3
165°	1063.3	1062.2	1062.6	1063.0	1063.3	1063.8	1064.2	1064.8	1065.4	1065.9	1066.5
167.5°	1081.2	1080.1	1080.0	1080.0	1080.0	1080.0	1080.3	1081.2	1081.9	1082.7	1083.6
170°	1090.9	1089.7	1089.5	1089.3	1089.2	1088.9	1089.3	1090.3	1091.2	1092.2	1093.1
172.5°	1097.9	1096.6	1096.6	1096.5	1096.5	1096.4	1096.8	1097.6	1098.5	1099.2	1100.0
175°	1105.7	1104.3	1104.5	1104.7	1104.9	1105.1	1105.7	1106.6	1107.6	1108.5	1109.5
177.5°	1110.2	1109.1	1109.1	1109.1	1109.1	1109.1	1109.5	1110.3	1111.0	1111.8	1112.6
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.3	6.3	6.0	6.3	6.6	6.6	7.1	7.4	7.7	7.7	8.4
90°	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1	21.2
92.5°	20.8	23.2	25.6	28.0	29.8	30.8	31.9	33.0	34.0	34.7	35.4
95°	53.3	55.0	56.7	58.5	59.9	61.3	62.7	64.0	65.3	65.9	66.5
97.5°	91.4	92.8	94.2	95.6	97.0	98.6	100.1	101.8	103.3	104.0	104.7
100°	121.1	121.8	122.6	123.4	124.6	126.3	128.0	129.8	131.5	131.9	132.2
102.5°	152.2	152.6	152.8	153.2	154.1	155.7	157.2	158.8	160.4	160.9	161.4
105°	200.4	200.6	200.8	201.0	201.5	202.2	203.0	203.8	204.6	205.1	205.7
107.5°	251.2	251.4	251.7	251.8	252.0	252.2	252.3	252.4	252.5	253.0	253.6
110°	285.7	286.1	286.5	286.9	287.0	286.7	286.5	286.4	286.2	285.8	285.4





TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	321.2	321.2	321.3	321.4	321.2	320.9	320.6	320.2	319.9	319.8	319.7
115°	374.7	374.7	374.7	374.7	374.5	374.1	373.8	373.3	373.0	372.8	372.6
117.5°	425.4	425.5	425.7	425.9	425.8	425.5	425.2	425.0	424.7	424.0	423.4
120°	459.7	460.5	461.2	462.0	462.1	461.5	460.9	460.4	459.8	458.8	457.9
122.5°	494.3	494.6	494.9	495.2	495.2	495.0	494.6	494.4	494.1	493.5	492.8
125°	545.7	545.7	545.7	545.7	545.6	545.4	545.3	545.0	544.8	544.5	544.1
127.5°	593.2	593.7	594.3	595.0	595.0	594.8	594.4	594.2	593.8	593.5	593.1
130°	626.2	626.8	627.3	627.9	628.2	628.2	628.2	628.2	628.2	627.8	627.5
132.5°	659.8	660.1	660.6	661.0	661.2	661.0	660.8	660.6	660.6	660.1	659.8
135°	705.0	706.1	707.3	708.4	709.0	709.0	709.0	709.0	709.0	708.6	708.3
137.5°	752.9	753.4	753.9	754.5	754.8	755.2	755.5	755.8	756.1	755.6	755.1
140°	785.0	785.4	785.7	786.2	786.4	786.4	786.4	786.4	786.4	786.2	786.0
142.5°	814.6	814.9	815.4	815.7	815.8	815.7	815.5	815.4	815.2	815.2	815.1
145°	855.8	856.6	857.4	858.2	858.6	858.8	859.0	859.2	859.4	859.2	859.0
147.5°	896.6	897.5	898.5	899.3	899.7	899.6	899.4	899.2	899.1	899.0	898.8
150°	921.2	922.0	922.7	923.5	923.9	923.9	923.9	923.9	923.9	923.9	923.9
152.5°	944.3	944.7	945.2	945.6	945.9	946.1	946.2	946.4	946.5	947.0	947.4
155°	979.7	979.7	979.7	979.7	979.6	979.4	979.2	979.0	978.9	979.6	980.4
157.5°	1009.6	1009.3	1008.9	1008.6	1008.4	1008.3	1008.3	1008.3	1008.2	1008.8	1009.4
160°	1027.6	1027.4	1027.3	1027.1	1026.9	1026.7	1026.5	1026.3	1026.1	1026.7	1027.3
162.5°	1043.9	1043.4	1042.8	1042.3	1042.0	1041.8	1041.6	1041.5	1041.2	1042.2	1043.3
165°	1065.9	1065.4	1064.8	1064.2	1063.8	1063.3	1063.0	1062.6	1062.2	1063.3	1064.5
167.5°	1082.7	1081.9	1081.2	1080.3	1080.0	1080.0	1080.0	1080.0	1080.1	1081.2	1082.4
170°	1092.2	1091.2	1090.3	1089.3	1088.9	1089.2	1089.3	1089.5	1089.7	1090.9	1092.0
172.5°	1099.2	1098.5	1097.6	1096.8	1096.4	1096.5	1096.5	1096.6	1096.6	1097.9	1099.2
175°	1108.5	1107.6	1106.6	1105.7	1105.1	1104.9	1104.7	1104.5	1104.3	1105.7	1107.0
177.5°	1111.8	1111.0	1110.3	1109.5	1109.1	1109.1	1109.1	1109.1	1109.1	1110.2	1111.3
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	8.2	8.3	8.6	8.5	8.6	8.5	8.8
90°	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	36.1	36.8	37.3	37.5	37.7	38.0	38.1
95°	67.1	67.6	67.9	67.9	67.9	67.9	67.9
97.5°	105.4	106.1	106.4	106.4	106.4	106.4	106.4
100°	132.6	133.0	133.2	133.2	133.2	133.2	133.2
102.5°	162.0	162.5	162.8	163.0	163.2	163.3	163.4
105°	206.3	206.8	207.4	207.9	208.5	209.1	209.7
107.5°	254.1	254.6	254.9	254.9	254.8	254.8	254.7
110°	285.0	284.6	284.7	285.3	285.9	286.5	287.1



TEST NUMBER: P332884-935

CATALOG NUMBER: S124RDIP-S350D1035U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.6	319.6	319.6	319.7	319.8	319.9	320.0
115°	372.4	372.2	372.0	371.9	371.6	371.4	371.3
117.5°	422.8	422.1	421.6	421.2	420.9	420.4	420.1
120°	456.9	456.0	455.6	456.1	456.4	456.8	457.2
122.5°	492.2	491.5	490.9	490.2	489.5	488.8	488.1
125°	543.7	543.3	542.9	542.6	542.2	541.8	541.4
127.5°	592.7	592.3	591.9	591.7	591.3	591.1	590.7
130°	627.1	626.7	626.1	625.3	624.6	623.8	623.0
132.5°	659.4	659.0	658.7	658.3	658.1	657.7	657.5
135°	707.8	707.5	707.0	706.5	705.8	705.2	704.7
137.5°	754.6	754.1	753.9	754.1	754.1	754.2	754.4
140°	785.7	785.6	785.4	785.2	785.0	784.8	784.6
142.5°	815.1	815.1	815.0	815.0	814.9	814.9	814.9
145°	858.8	858.6	858.2	857.6	857.1	856.5	855.9
147.5°	898.6	898.5	898.3	898.1	897.9	897.8	897.6
150°	923.9	923.9	923.8	923.6	923.3	923.2	923.0
152.5°	947.9	948.4	948.4	947.9	947.4	946.8	946.3
155°	981.1	981.9	981.9	981.1	980.4	979.6	978.9
157.5°	1010.0	1010.6	1010.5	1009.9	1009.2	1008.6	1007.9
160°	1027.9	1028.4	1028.2	1027.3	1026.3	1025.4	1024.4
162.5°	1044.3	1045.3	1045.4	1044.5	1043.5	1042.6	1041.6
165°	1065.7	1066.8	1067.0	1066.3	1065.5	1064.7	1063.9
167.5°	1083.6	1084.7	1084.7	1083.5	1082.3	1081.1	1080.0
170°	1093.1	1094.3	1094.2	1092.9	1091.5	1090.2	1088.8
172.5°	1100.4	1101.8	1101.7	1100.4	1099.1	1097.8	1096.4
175°	1108.4	1109.7	1109.7	1108.4	1107.0	1105.7	1104.3
177.5°	1112.3	1113.4	1113.4	1112.2	1110.9	1109.7	1108.5
180°	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2	1111.2

(END OF REPORT)