

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332891-935

Luminaire Tested: **S124RDIP-S350D1205U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332891-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D1205U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4984.9 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	22	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	33	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.0
10°-20°	147.8	3.0
20°-30°	231.2	4.6
30°-40°	257.0	5.2
40°-50°	228.0	4.6
50°-60°	177.7	3.6
60°-70°	116.3	2.3
70°-80°	57.2	1.1
80°-90°	16.9	0.3
90°-100°	367.8	7.4
100°-110°	765.5	15.4
110°-120°	685.7	13.8
120°-130°	576.8	11.6
130°-140°	480.9	9.6
140°-150°	367.4	7.4
150°-160°	258.2	5.2
160°-170°	151.9	3.0
170°-180°	49.4	1.0
0°-30°	428.0	8.6
0°-40°	685.0	13.7
0°-60°	1090.8	21.9
0°-90°	1281.2	25.7
90°-120°	1819.0	36.5
90°-150°	3244.1	65.1
90°-180°	3704.0	74.3
0°-180°	4984.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	21	1	21	1	21	17
95°	244	33	244	33	244	379
105°	1408	117	1408	117	1408	1392
115°	1352	206	1352	206	1352	1342
125°	1078	287	1078	287	1078	980
135°	964	341	964	341	964	744
145°	787	393	787	393	787	499
155°	659	447	659	447	659	308
165°	575	487	575	487	575	165
175°	518	508	518	508	518	50
180°	509	509	509	509	509	



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	7.7	7.7	8.0	7.7	7.7	7.6	7.6	7.7	7.1	7.5	7.1
90°	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0	17.0	18.0	16.0
92.5°	77.1	77.1	80.4	85.8	97.6	117.7	147.8	196.5	264.3	317.4	277.8
95°	244.1	257.1	275.2	306.2	355.2	452.2	586.3	741.3	838.4	815.4	615.3
97.5°	652.6	673.3	703.4	763.5	835.4	939.9	1037.7	1095.4	1053.3	858.8	575.8
100°	917.5	925.5	955.5	1016.5	1103.5	1177.6	1226.6	1206.6	1060.5	804.3	522.3
102.5°	1148.0	1154.3	1185.9	1230.2	1283.6	1314.4	1300.2	1201.0	1000.5	736.3	486.2
105°	1407.6	1413.7	1427.7	1435.7	1433.7	1392.7	1293.7	1120.5	891.4	656.3	455.2
107.5°	1504.2	1501.5	1491.5	1468.7	1419.3	1330.1	1190.6	1006.3	803.4	611.5	449.6
110°	1505.7	1496.8	1478.7	1436.7	1365.6	1255.6	1110.5	937.5	759.4	596.3	451.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1458.5	1443.9	1418.7	1367.9	1287.2	1177.2	1040.1	887.0	734.5	589.1	456.0
115°	1351.7	1343.7	1311.6	1251.6	1172.6	1076.5	959.5	836.4	711.4	585.3	465.2
117.5°	1243.4	1237.2	1204.8	1154.3	1086.9	1005.5	913.4	811.6	700.9	584.3	475.0
120°	1182.6	1171.6	1145.6	1101.6	1044.5	973.4	893.5	800.4	695.3	584.3	482.2
122.5°	1134.5	1123.5	1101.6	1063.9	1015.7	953.5	880.6	790.7	689.0	583.5	489.5
125°	1078.5	1072.5	1053.5	1024.5	984.5	929.4	860.4	774.4	678.3	582.3	500.2
127.5°	1045.7	1039.7	1023.7	997.9	957.7	905.4	836.6	754.3	664.1	580.1	508.9
130°	1026.5	1020.5	1004.4	979.5	938.5	885.5	817.4	738.4	655.3	579.3	515.2
132.5°	1004.9	998.8	983.7	955.5	915.2	862.2	795.8	721.5	647.3	578.5	520.8
135°	964.5	958.5	942.5	914.5	874.4	824.4	763.4	698.4	635.3	577.3	529.3
137.5°	914.5	907.2	894.1	866.4	829.0	783.8	732.4	677.3	624.9	577.0	534.3
140°	878.4	870.4	856.4	834.4	799.4	757.3	712.3	665.3	619.3	576.3	538.3
142.5°	840.0	834.4	822.0	801.6	770.6	734.2	695.5	654.1	614.5	576.3	541.5
145°	787.4	782.4	772.4	755.4	730.4	702.3	672.4	638.3	606.3	574.3	543.3
147.5°	740.7	739.0	731.3	716.8	698.4	676.3	652.3	625.3	598.9	570.7	544.2
150°	714.4	713.3	707.3	694.3	678.3	660.3	640.3	617.3	593.3	568.3	544.2
152.5°	690.3	689.3	685.7	675.1	661.5	646.7	628.3	608.5	586.9	564.3	542.7
155°	659.4	659.4	656.3	648.3	638.3	626.3	611.3	595.3	577.3	558.3	540.3
157.5°	632.1	632.1	630.3	624.3	616.7	607.1	594.5	581.1	567.5	552.1	537.7
160°	615.3	615.3	614.3	608.3	602.3	594.3	583.2	572.3	560.3	547.3	535.3
162.5°	599.3	600.1	599.1	593.1	588.7	581.5	572.9	563.4	553.9	542.4	532.9
165°	575.3	576.3	577.3	573.3	569.3	564.3	557.2	551.3	543.3	535.3	528.2
167.5°	556.3	557.1	557.2	554.7	552.7	549.7	544.1	539.5	533.6	528.1	523.5
170°	544.2	544.2	545.3	544.2	542.3	539.2	535.3	532.3	527.3	523.2	520.2
172.5°	532.3	533.8	534.9	533.8	532.6	530.5	528.1	525.8	521.7	518.4	517.0
175°	518.2	520.2	522.3	520.2	520.2	520.2	518.2	517.3	515.2	513.2	513.2
177.5°	510.1	511.6	513.2	512.5	513.2	512.5	512.5	511.6	510.8	510.1	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	6.7	6.5	5.7	5.7	5.6	6.1	5.9	5.8	5.7	5.8	5.5
90°	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0	3.0	6.0	7.0
92.5°	202.1	124.5	73.6	52.9	38.2	26.0	16.6	11.4	16.6	26.0	38.2
95°	376.2	212.1	125.1	83.0	59.1	46.1	36.0	33.0	36.0	46.1	59.1
97.5°	338.2	202.7	135.7	100.5	79.8	67.8	59.2	59.2	59.2	67.8	79.8
100°	318.1	205.1	146.1	114.1	95.1	83.0	76.0	76.0	76.0	83.0	95.1
102.5°	312.5	213.1	159.7	129.2	111.1	99.9	93.7	92.0	93.7	99.9	111.1
105°	315.1	232.1	184.1	155.1	137.1	125.1	120.0	117.1	120.0	125.1	137.1
107.5°	329.9	254.3	210.3	181.7	164.5	151.7	146.6	144.6	146.6	151.7	164.5
110°	341.1	271.1	227.1	200.1	182.1	170.0	165.1	163.1	165.1	170.0	182.1



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	353.2	287.1	244.7	217.7	199.7	188.5	182.7	180.7	182.7	188.5	199.7
115°	372.2	312.1	272.2	245.1	226.1	216.1	209.1	206.1	209.1	216.1	226.1
117.5°	391.6	336.4	298.3	270.4	252.5	241.5	235.3	232.5	235.3	241.5	252.5
120°	405.2	353.2	315.1	287.1	270.1	259.2	252.1	250.1	252.1	259.2	270.1
122.5°	418.0	369.2	331.1	303.9	285.3	275.2	268.1	266.1	268.1	275.2	285.3
125°	437.2	391.2	355.2	327.2	308.2	297.1	291.1	287.1	291.1	297.1	308.2
127.5°	453.8	411.6	376.8	348.5	328.7	316.2	308.9	305.7	308.9	316.2	328.7
130°	464.3	425.2	391.2	362.1	343.2	328.1	320.1	316.2	320.1	328.1	343.2
132.5°	474.7	436.4	402.4	375.0	354.4	340.2	329.8	326.6	329.8	340.2	354.4
135°	488.3	452.2	419.2	393.2	372.2	355.2	345.2	341.1	345.2	355.2	372.2
137.5°	497.8	464.3	433.4	408.6	386.8	370.6	359.6	355.8	359.6	370.6	386.8
140°	504.2	472.3	442.2	418.2	397.2	380.2	369.2	366.2	369.2	380.2	397.2
142.5°	509.0	479.4	450.2	427.0	406.8	390.5	380.4	377.4	380.4	390.5	406.8
145°	514.3	487.2	461.2	439.2	420.2	406.2	396.2	393.2	396.2	406.2	420.2
147.5°	518.8	495.2	470.8	451.0	435.2	420.8	412.0	411.0	412.0	420.8	435.2
150°	521.2	499.2	477.3	458.2	443.2	431.2	423.2	422.2	423.2	431.2	443.2
152.5°	522.9	502.5	482.8	465.5	452.0	440.8	432.8	432.6	432.8	440.8	452.0
155°	524.3	507.2	490.3	475.3	464.3	454.2	448.2	447.2	448.2	454.2	464.3
157.5°	524.3	510.7	496.3	484.4	474.8	467.0	461.4	461.4	461.4	467.0	474.8
160°	524.3	512.2	500.2	489.2	481.2	474.2	470.2	470.2	470.2	474.2	481.2
162.5°	524.3	513.8	502.7	494.0	486.8	480.6	477.4	478.2	477.4	480.6	486.8
165°	522.3	514.3	505.2	499.2	494.2	489.2	487.2	487.2	487.2	489.2	494.2
167.5°	519.9	514.0	507.5	502.8	500.1	496.3	495.2	496.3	495.2	496.3	500.1
170°	518.2	513.2	508.2	505.2	503.3	500.2	499.2	500.2	499.2	500.2	503.3
172.5°	516.7	512.5	509.0	506.9	505.7	503.4	503.3	504.2	503.3	503.4	505.7
175°	514.3	511.3	509.3	509.3	508.2	507.2	507.2	508.2	507.2	507.2	508.2
177.5°	511.6	510.1	509.3	509.3	509.3	508.4	509.3	510.1	509.3	508.4	509.3
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	5.7	5.5	6.7	6.4	7.0	7.3	7.0	7.1	7.6	7.4	7.4
90°	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0	19.0	20.0	20.0
92.5°	52.9	73.6	124.5	202.1	277.8	317.4	264.3	196.5	147.8	117.7	97.6
95°	83.0	125.1	212.1	376.2	615.3	815.4	838.4	741.3	586.3	452.2	355.2
97.5°	100.5	135.7	202.7	338.2	575.8	858.8	1053.3	1095.4	1037.7	939.9	835.4
100°	114.1	146.1	205.1	318.1	522.3	804.3	1060.5	1206.6	1226.6	1177.6	1103.5
102.5°	129.2	159.7	213.1	312.5	486.2	736.3	1000.5	1201.0	1300.2	1314.4	1283.6
105°	155.1	184.1	232.1	315.1	455.2	656.3	891.4	1120.5	1293.7	1392.7	1433.7
107.5°	181.7	210.3	254.3	329.9	449.6	611.5	803.4	1006.3	1190.6	1330.1	1419.3
110°	200.1	227.1	271.1	341.1	451.3	596.3	759.4	937.5	1110.5	1255.6	1365.6



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.7	244.7	287.1	353.2	456.0	589.1	734.5	887.0	1040.1	1177.2	1287.2
115°	245.1	272.2	312.1	372.2	465.2	585.3	711.4	836.4	959.5	1076.5	1172.6
117.5°	270.4	298.3	336.4	391.6	475.0	584.3	700.9	811.6	913.4	1005.5	1086.9
120°	287.1	315.1	353.2	405.2	482.2	584.3	695.3	800.4	893.5	973.4	1044.5
122.5°	303.9	331.1	369.2	418.0	489.5	583.5	689.0	790.7	880.6	953.5	1015.7
125°	327.2	355.2	391.2	437.2	500.2	582.3	678.3	774.4	860.4	929.4	984.5
127.5°	348.5	376.8	411.6	453.8	508.9	580.1	664.1	754.3	836.6	905.4	957.7
130°	362.1	391.2	425.2	464.3	515.2	579.3	655.3	738.4	817.4	885.5	938.5
132.5°	375.0	402.4	436.4	474.7	520.8	578.5	647.3	721.5	795.8	862.2	915.2
135°	393.2	419.2	452.2	488.3	529.3	577.3	635.3	698.4	763.4	824.4	874.4
137.5°	408.6	433.4	464.3	497.8	534.3	577.0	624.9	677.3	732.4	783.8	829.0
140°	418.2	442.2	472.3	504.2	538.3	576.3	619.3	665.3	712.3	757.3	799.4
142.5°	427.0	450.2	479.4	509.0	541.5	576.3	614.5	654.1	695.5	734.2	770.6
145°	439.2	461.2	487.2	514.3	543.3	574.3	606.3	638.3	672.4	702.3	730.4
147.5°	451.0	470.8	495.2	518.8	544.2	570.7	598.9	625.3	652.3	676.3	698.4
150°	458.2	477.3	499.2	521.2	544.2	568.3	593.3	617.3	640.3	660.3	678.3
152.5°	465.5	482.8	502.5	522.9	542.7	564.3	586.9	608.5	628.3	646.7	661.5
155°	475.3	490.3	507.2	524.3	540.3	558.3	577.3	595.3	611.3	626.3	638.3
157.5°	484.4	496.3	510.7	524.3	537.7	552.1	567.5	581.1	594.5	607.1	616.7
160°	489.2	500.2	512.2	524.3	535.3	547.3	560.3	572.3	583.2	594.3	602.3
162.5°	494.0	502.7	513.8	524.3	532.9	542.4	553.9	563.4	572.9	581.5	588.7
165°	499.2	505.2	514.3	522.3	528.2	535.3	543.3	551.3	557.2	564.3	569.3
167.5°	502.8	507.5	514.0	519.9	523.5	528.1	533.6	539.5	544.1	549.7	552.7
170°	505.2	508.2	513.2	518.2	520.2	523.2	527.3	532.3	535.3	539.2	542.3
172.5°	506.9	509.0	512.5	516.7	517.0	518.4	521.7	525.8	528.1	530.5	532.6
175°	509.3	509.3	511.3	514.3	513.2	513.2	515.2	517.3	518.2	520.2	520.2
177.5°	509.3	509.3	510.1	511.6	510.1	510.1	510.8	511.6	512.5	512.5	513.2
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	7.9	8.0	7.7	7.7	7.7	8.0	7.9	7.4	7.4	7.6	7.1
90°	21.0	22.0	21.0	21.0	21.0	22.0	21.0	20.0	20.0	19.0	18.0
92.5°	85.8	80.4	77.1	77.1	77.1	80.4	85.8	97.6	117.7	147.8	196.5
95°	306.2	275.2	257.1	244.1	257.1	275.2	306.2	355.2	452.2	586.3	741.3
97.5°	763.5	703.4	673.3	652.6	673.3	703.4	763.5	835.4	939.9	1037.7	1095.4
100°	1016.5	955.5	925.5	917.5	925.5	955.5	1016.5	1103.5	1177.6	1226.6	1206.6
102.5°	1230.2	1185.9	1154.3	1148.0	1154.3	1185.9	1230.2	1283.6	1314.4	1300.2	1201.0
105°	1435.7	1427.7	1413.7	1407.6	1413.7	1427.7	1435.7	1433.7	1392.7	1293.7	1120.5
107.5°	1468.7	1491.5	1501.5	1504.2	1501.5	1491.5	1468.7	1419.3	1330.1	1190.6	1006.3
110°	1436.7	1478.7	1496.8	1505.7	1496.8	1478.7	1436.7	1365.6	1255.6	1110.5	937.5



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1367.9	1418.7	1443.9	1458.5	1443.9	1418.7	1367.9	1287.2	1177.2	1040.1	887.0
115°	1251.6	1311.6	1343.7	1351.7	1343.7	1311.6	1251.6	1172.6	1076.5	959.5	836.4
117.5°	1154.3	1204.8	1237.2	1243.4	1237.2	1204.8	1154.3	1086.9	1005.5	913.4	811.6
120°	1101.6	1145.6	1171.6	1182.6	1171.6	1145.6	1101.6	1044.5	973.4	893.5	800.4
122.5°	1063.9	1101.6	1123.5	1134.5	1123.5	1101.6	1063.9	1015.7	953.5	880.6	790.7
125°	1024.5	1053.5	1072.5	1078.5	1072.5	1053.5	1024.5	984.5	929.4	860.4	774.4
127.5°	997.9	1023.7	1039.7	1045.7	1039.7	1023.7	997.9	957.7	905.4	836.6	754.3
130°	979.5	1004.4	1020.5	1026.5	1020.5	1004.4	979.5	938.5	885.5	817.4	738.4
132.5°	955.5	983.7	998.8	1004.9	998.8	983.7	955.5	915.2	862.2	795.8	721.5
135°	914.5	942.5	958.5	964.5	958.5	942.5	914.5	874.4	824.4	763.4	698.4
137.5°	866.4	894.1	907.2	914.5	907.2	894.1	866.4	829.0	783.8	732.4	677.3
140°	834.4	856.4	870.4	878.4	870.4	856.4	834.4	799.4	757.3	712.3	665.3
142.5°	801.6	822.0	834.4	840.0	834.4	822.0	801.6	770.6	734.2	695.5	654.1
145°	755.4	772.4	782.4	787.4	782.4	772.4	755.4	730.4	702.3	672.4	638.3
147.5°	716.8	731.3	739.0	740.7	739.0	731.3	716.8	698.4	676.3	652.3	625.3
150°	694.3	707.3	713.3	714.4	713.3	707.3	694.3	678.3	660.3	640.3	617.3
152.5°	675.1	685.7	689.3	690.3	689.3	685.7	675.1	661.5	646.7	628.3	608.5
155°	648.3	656.3	659.4	659.4	659.4	656.3	648.3	638.3	626.3	611.3	595.3
157.5°	624.3	630.3	632.1	632.1	632.1	630.3	624.3	616.7	607.1	594.5	581.1
160°	608.3	614.3	615.3	615.3	615.3	614.3	608.3	602.3	594.3	583.2	572.3
162.5°	593.1	599.1	600.1	599.3	600.1	599.1	593.1	588.7	581.5	572.9	563.4
165°	573.3	577.3	576.3	575.3	576.3	577.3	573.3	569.3	564.3	557.2	551.3
167.5°	554.7	557.2	557.1	556.3	557.1	557.2	554.7	552.7	549.7	544.1	539.5
170°	544.2	545.3	544.2	544.2	544.2	545.3	544.2	542.3	539.2	535.3	532.3
172.5°	533.8	534.9	533.8	532.3	533.8	534.9	533.8	532.6	530.5	528.1	525.8
175°	520.2	522.3	520.2	518.2	520.2	522.3	520.2	520.2	520.2	518.2	517.3
177.5°	512.5	513.2	511.6	510.1	511.6	513.2	512.5	513.2	512.5	512.5	511.6
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	7.0	7.3	7.0	6.4	6.7	5.5	5.7	5.5	5.8	5.7	5.8
90°	17.0	18.0	16.0	14.0	14.0	8.0	8.0	7.0	6.0	3.0	1.0
92.5°	264.3	317.4	277.8	202.1	124.5	73.6	52.9	38.2	26.0	16.6	11.4
95°	838.4	815.4	615.3	376.2	212.1	125.1	83.0	59.1	46.1	36.0	33.0
97.5°	1053.3	858.8	575.8	338.2	202.7	135.7	100.5	79.8	67.8	59.2	59.2
100°	1060.5	804.3	522.3	318.1	205.1	146.1	114.1	95.1	83.0	76.0	76.0
102.5°	1000.5	736.3	486.2	312.5	213.1	159.7	129.2	111.1	99.9	93.7	92.0
105°	891.4	656.3	455.2	315.1	232.1	184.1	155.1	137.1	125.1	120.0	117.1
107.5°	803.4	611.5	449.6	329.9	254.3	210.3	181.7	164.5	151.7	146.6	144.6
110°	759.4	596.3	451.3	341.1	271.1	227.1	200.1	182.1	170.0	165.1	163.1



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	734.5	589.1	456.0	353.2	287.1	244.7	217.7	199.7	188.5	182.7	180.7
115°	711.4	585.3	465.2	372.2	312.1	272.2	245.1	226.1	216.1	209.1	206.1
117.5°	700.9	584.3	475.0	391.6	336.4	298.3	270.4	252.5	241.5	235.3	232.5
120°	695.3	584.3	482.2	405.2	353.2	315.1	287.1	270.1	259.2	252.1	250.1
122.5°	689.0	583.5	489.5	418.0	369.2	331.1	303.9	285.3	275.2	268.1	266.1
125°	678.3	582.3	500.2	437.2	391.2	355.2	327.2	308.2	297.1	291.1	287.1
127.5°	664.1	580.1	508.9	453.8	411.6	376.8	348.5	328.7	316.2	308.9	305.7
130°	655.3	579.3	515.2	464.3	425.2	391.2	362.1	343.2	328.1	320.1	316.2
132.5°	647.3	578.5	520.8	474.7	436.4	402.4	375.0	354.4	340.2	329.8	326.6
135°	635.3	577.3	529.3	488.3	452.2	419.2	393.2	372.2	355.2	345.2	341.1
137.5°	624.9	577.0	534.3	497.8	464.3	433.4	408.6	386.8	370.6	359.6	355.8
140°	619.3	576.3	538.3	504.2	472.3	442.2	418.2	397.2	380.2	369.2	366.2
142.5°	614.5	576.3	541.5	509.0	479.4	450.2	427.0	406.8	390.5	380.4	377.4
145°	606.3	574.3	543.3	514.3	487.2	461.2	439.2	420.2	406.2	396.2	393.2
147.5°	598.9	570.7	544.2	518.8	495.2	470.8	451.0	435.2	420.8	412.0	411.0
150°	593.3	568.3	544.2	521.2	499.2	477.3	458.2	443.2	431.2	423.2	422.2
152.5°	586.9	564.3	542.7	522.9	502.5	482.8	465.5	452.0	440.8	432.8	432.6
155°	577.3	558.3	540.3	524.3	507.2	490.3	475.3	464.3	454.2	448.2	447.2
157.5°	567.5	552.1	537.7	524.3	510.7	496.3	484.4	474.8	467.0	461.4	461.4
160°	560.3	547.3	535.3	524.3	512.2	500.2	489.2	481.2	474.2	470.2	470.2
162.5°	553.9	542.4	532.9	524.3	513.8	502.7	494.0	486.8	480.6	477.4	478.2
165°	543.3	535.3	528.2	522.3	514.3	505.2	499.2	494.2	489.2	487.2	487.2
167.5°	533.6	528.1	523.5	519.9	514.0	507.5	502.8	500.1	496.3	495.2	496.3
170°	527.3	523.2	520.2	518.2	513.2	508.2	505.2	503.3	500.2	499.2	500.2
172.5°	521.7	518.4	517.0	516.7	512.5	509.0	506.9	505.7	503.4	503.3	504.2
175°	515.2	513.2	513.2	514.3	511.3	509.3	509.3	508.2	507.2	507.2	508.2
177.5°	510.8	510.1	510.1	511.6	510.1	509.3	509.3	509.3	508.4	509.3	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	5.9	6.1	5.6	5.7	5.7	6.5	6.7	7.1	7.5	7.1	7.7
90°	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0	18.0
92.5°	16.6	26.0	38.2	52.9	73.6	124.5	202.1	277.8	317.4	264.3	196.5
95°	36.0	46.1	59.1	83.0	125.1	212.1	376.2	615.3	815.4	838.4	741.3
97.5°	59.2	67.8	79.8	100.5	135.7	202.7	338.2	575.8	858.8	1053.3	1095.4
100°	76.0	83.0	95.1	114.1	146.1	205.1	318.1	522.3	804.3	1060.5	1206.6
102.5°	93.7	99.9	111.1	129.2	159.7	213.1	312.5	486.2	736.3	1000.5	1201.0
105°	120.0	125.1	137.1	155.1	184.1	232.1	315.1	455.2	656.3	891.4	1120.5
107.5°	146.6	151.7	164.5	181.7	210.3	254.3	329.9	449.6	611.5	803.4	1006.3
110°	165.1	170.0	182.1	200.1	227.1	271.1	341.1	451.3	596.3	759.4	937.5



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	188.5	199.7	217.7	244.7	287.1	353.2	456.0	589.1	734.5	887.0
115°	209.1	216.1	226.1	245.1	272.2	312.1	372.2	465.2	585.3	711.4	836.4
117.5°	235.3	241.5	252.5	270.4	298.3	336.4	391.6	475.0	584.3	700.9	811.6
120°	252.1	259.2	270.1	287.1	315.1	353.2	405.2	482.2	584.3	695.3	800.4
122.5°	268.1	275.2	285.3	303.9	331.1	369.2	418.0	489.5	583.5	689.0	790.7
125°	291.1	297.1	308.2	327.2	355.2	391.2	437.2	500.2	582.3	678.3	774.4
127.5°	308.9	316.2	328.7	348.5	376.8	411.6	453.8	508.9	580.1	664.1	754.3
130°	320.1	328.1	343.2	362.1	391.2	425.2	464.3	515.2	579.3	655.3	738.4
132.5°	329.8	340.2	354.4	375.0	402.4	436.4	474.7	520.8	578.5	647.3	721.5
135°	345.2	355.2	372.2	393.2	419.2	452.2	488.3	529.3	577.3	635.3	698.4
137.5°	359.6	370.6	386.8	408.6	433.4	464.3	497.8	534.3	577.0	624.9	677.3
140°	369.2	380.2	397.2	418.2	442.2	472.3	504.2	538.3	576.3	619.3	665.3
142.5°	380.4	390.5	406.8	427.0	450.2	479.4	509.0	541.5	576.3	614.5	654.1
145°	396.2	406.2	420.2	439.2	461.2	487.2	514.3	543.3	574.3	606.3	638.3
147.5°	412.0	420.8	435.2	451.0	470.8	495.2	518.8	544.2	570.7	598.9	625.3
150°	423.2	431.2	443.2	458.2	477.3	499.2	521.2	544.2	568.3	593.3	617.3
152.5°	432.8	440.8	452.0	465.5	482.8	502.5	522.9	542.7	564.3	586.9	608.5
155°	448.2	454.2	464.3	475.3	490.3	507.2	524.3	540.3	558.3	577.3	595.3
157.5°	461.4	467.0	474.8	484.4	496.3	510.7	524.3	537.7	552.1	567.5	581.1
160°	470.2	474.2	481.2	489.2	500.2	512.2	524.3	535.3	547.3	560.3	572.3
162.5°	477.4	480.6	486.8	494.0	502.7	513.8	524.3	532.9	542.4	553.9	563.4
165°	487.2	489.2	494.2	499.2	505.2	514.3	522.3	528.2	535.3	543.3	551.3
167.5°	495.2	496.3	500.1	502.8	507.5	514.0	519.9	523.5	528.1	533.6	539.5
170°	499.2	500.2	503.3	505.2	508.2	513.2	518.2	520.2	523.2	527.3	532.3
172.5°	503.3	503.4	505.7	506.9	509.0	512.5	516.7	517.0	518.4	521.7	525.8
175°	507.2	507.2	508.2	509.3	509.3	511.3	514.3	513.2	513.2	515.2	517.3
177.5°	509.3	508.4	509.3	509.3	509.3	510.1	511.6	510.1	510.1	510.8	511.6
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	7.6	7.6	7.7	7.7	8.0	7.7	7.7
90°	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	147.8	117.7	97.6	85.8	80.4	77.1	77.1
95°	586.3	452.2	355.2	306.2	275.2	257.1	244.1
97.5°	1037.7	939.9	835.4	763.5	703.4	673.3	652.6
100°	1226.6	1177.6	1103.5	1016.5	955.5	925.5	917.5
102.5°	1300.2	1314.4	1283.6	1230.2	1185.9	1154.3	1148.0
105°	1293.7	1392.7	1433.7	1435.7	1427.7	1413.7	1407.6
107.5°	1190.6	1330.1	1419.3	1468.7	1491.5	1501.5	1504.2
110°	1110.5	1255.6	1365.6	1436.7	1478.7	1496.8	1505.7



TEST NUMBER: P332891-935

CATALOG NUMBER: S124RDIP-S350D1205U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1040.1	1177.2	1287.2	1367.9	1418.7	1443.9	1458.5
115°	959.5	1076.5	1172.6	1251.6	1311.6	1343.7	1351.7
117.5°	913.4	1005.5	1086.9	1154.3	1204.8	1237.2	1243.4
120°	893.5	973.4	1044.5	1101.6	1145.6	1171.6	1182.6
122.5°	880.6	953.5	1015.7	1063.9	1101.6	1123.5	1134.5
125°	860.4	929.4	984.5	1024.5	1053.5	1072.5	1078.5
127.5°	836.6	905.4	957.7	997.9	1023.7	1039.7	1045.7
130°	817.4	885.5	938.5	979.5	1004.4	1020.5	1026.5
132.5°	795.8	862.2	915.2	955.5	983.7	998.8	1004.9
135°	763.4	824.4	874.4	914.5	942.5	958.5	964.5
137.5°	732.4	783.8	829.0	866.4	894.1	907.2	914.5
140°	712.3	757.3	799.4	834.4	856.4	870.4	878.4
142.5°	695.5	734.2	770.6	801.6	822.0	834.4	840.0
145°	672.4	702.3	730.4	755.4	772.4	782.4	787.4
147.5°	652.3	676.3	698.4	716.8	731.3	739.0	740.7
150°	640.3	660.3	678.3	694.3	707.3	713.3	714.4
152.5°	628.3	646.7	661.5	675.1	685.7	689.3	690.3
155°	611.3	626.3	638.3	648.3	656.3	659.4	659.4
157.5°	594.5	607.1	616.7	624.3	630.3	632.1	632.1
160°	583.2	594.3	602.3	608.3	614.3	615.3	615.3
162.5°	572.9	581.5	588.7	593.1	599.1	600.1	599.3
165°	557.2	564.3	569.3	573.3	577.3	576.3	575.3
167.5°	544.1	549.7	552.7	554.7	557.2	557.1	556.3
170°	535.3	539.2	542.3	544.2	545.3	544.2	544.2
172.5°	528.1	530.5	532.6	533.8	534.9	533.8	532.3
175°	518.2	520.2	520.2	520.2	522.3	520.2	518.2
177.5°	512.5	512.5	513.2	512.5	513.2	511.6	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3

(END OF REPORT)