

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332877-935

Luminaire Tested: **S124RDIP-S350D810U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332877-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D810U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4065.3 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	18	17	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	24	43	33	27	23	27	22	19	21	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.2
10°-20°	147.8	3.6
20°-30°	231.2	5.7
30°-40°	257.0	6.3
40°-50°	228.0	5.6
50°-60°	177.7	4.4
60°-70°	116.3	2.9
70°-80°	57.2	1.4
80°-90°	16.7	0.4
90°-100°	30.8	0.8
100°-110°	196.3	4.8
110°-120°	375.5	9.2
120°-130°	476.7	11.7
130°-140°	510.0	12.5
140°-150°	476.9	11.7
150°-160°	384.6	9.5
160°-170°	248.0	6.1
170°-180°	85.5	2.1
0°-30°	428.0	10.5
0°-40°	685.0	16.9
0°-60°	1090.8	26.8
0°-90°	1281.0	31.5
90°-120°	602.6	14.8
90°-150°	2066.1	50.8
90°-180°	2784.0	68.5
0°-180°	4065.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	20	2	20	2	20	9
95°	20	37	20	37	20	16
105°	192	203	192	203	192	167
115°	381	378	381	378	381	377
125°	536	532	536	532	536	477
135°	664	660	664	660	664	511
145°	765	761	765	761	765	478
155°	833	834	833	834	833	384
165°	876	880	876	880	876	247
175°	895	900	895	900	895	85
180°	900	900	900	900	900	



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	7.7	7.4	7.5	7.4	7.6	7.2	7.2	7.4	6.9	6.9	6.6
90°	20.2	19.9	19.6	19.3	19.0	18.4	17.5	16.6	15.7	14.8	13.6
92.5°	18.6	18.5	18.4	18.4	18.3	17.8	17.0	16.1	15.2	14.3	13.1
95°	19.5	19.4	19.2	19.1	18.9	18.4	17.5	16.6	15.7	14.8	14.6
97.5°	18.9	18.7	18.5	18.4	18.3	18.2	18.1	18.0	17.8	17.7	34.4
100°	18.9	18.7	18.5	18.4	18.3	19.5	22.0	24.5	27.0	29.6	50.3
102.5°	19.4	19.4	19.3	19.3	19.3	33.0	60.4	87.8	115.3	142.8	145.4
105°	191.8	197.3	202.6	208.0	213.4	215.4	214.0	212.8	211.4	210.0	209.3
107.5°	267.4	266.8	266.2	265.7	265.1	264.5	263.8	263.2	262.5	261.9	260.9
110°	300.2	299.8	299.4	298.9	298.4	298.1	297.8	297.5	297.2	296.9	296.0



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.1	332.5	332.0	331.4	330.8	330.5	330.6	330.7	330.8	330.8	330.4
115°	381.1	381.1	381.1	381.1	381.1	380.9	380.6	380.3	380.0	379.7	379.9
117.5°	429.8	429.8	429.9	430.0	430.0	430.1	430.2	430.2	430.2	430.3	430.0
120°	460.5	460.8	461.1	461.4	461.7	461.7	461.4	461.1	460.8	460.5	460.6
122.5°	490.6	490.9	491.2	491.5	491.8	491.9	491.7	491.5	491.4	491.2	490.9
125°	535.9	535.7	535.5	535.5	535.3	534.9	534.5	534.1	533.6	533.2	533.5
127.5°	575.6	575.8	575.8	575.9	576.1	576.2	576.3	576.4	576.4	576.5	575.8
130°	602.5	602.5	602.5	602.5	602.5	602.4	602.3	602.2	602.0	601.8	601.4
132.5°	627.3	627.4	627.5	627.7	627.8	627.8	627.6	627.5	627.3	627.2	626.5
135°	664.4	664.2	663.8	663.6	663.2	663.0	662.6	662.4	662.0	661.8	661.2
137.5°	696.2	696.3	696.4	696.5	696.5	696.5	696.1	695.8	695.5	695.2	694.5
140°	718.3	718.2	718.0	717.9	717.7	717.4	717.0	716.5	716.1	715.6	715.3
142.5°	736.6	736.6	736.6	736.5	736.5	736.3	736.0	735.6	735.4	735.0	734.9
145°	764.7	764.5	764.1	763.9	763.5	763.4	763.2	763.0	762.9	762.8	762.8
147.5°	788.1	787.9	787.7	787.6	787.5	787.3	787.2	787.1	787.0	786.9	787.0
150°	803.1	803.0	802.8	802.7	802.5	802.5	802.5	802.5	802.5	802.5	802.6
152.5°	816.1	816.1	816.2	816.3	816.4	816.3	816.1	815.9	815.6	815.4	815.6
155°	833.4	833.9	834.3	834.7	835.3	835.2	834.6	834.0	833.4	832.8	833.2
157.5°	848.0	848.8	849.5	850.3	851.1	851.1	850.3	849.5	848.8	848.0	848.5
160°	857.6	858.6	859.5	860.4	861.3	861.3	860.4	859.5	858.6	857.6	857.8
162.5°	865.2	866.3	867.2	868.2	869.3	869.4	868.4	867.5	866.7	865.7	865.9
165°	875.8	877.2	878.6	879.9	881.2	881.3	880.1	878.9	877.7	876.5	876.5
167.5°	883.8	885.3	886.7	888.3	889.8	889.8	888.6	887.3	885.9	884.6	884.7
170°	888.6	890.1	891.7	893.1	894.6	894.8	893.5	892.3	891.1	890.0	889.8
172.5°	891.3	892.9	894.6	896.2	897.8	898.0	896.8	895.6	894.4	893.2	893.0
175°	894.7	896.5	898.3	900.1	901.9	902.1	900.8	899.4	898.0	896.7	896.6
177.5°	896.8	898.3	899.7	901.1	902.6	902.8	901.9	901.0	899.9	899.0	898.8
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	6.4	6.0	6.1	5.8	5.6	5.9	6.1	5.9	5.8	5.6	5.4
90°	12.4	11.2	10.0	8.6	7.0	5.3	3.7	2.0	3.7	5.3	7.0
92.5°	11.9	10.7	9.5	8.9	8.8	8.7	8.6	8.5	8.6	8.7	8.8
95°	14.6	14.4	14.2	16.7	21.8	26.9	31.9	37.0	31.9	26.9	21.8
97.5°	51.1	67.8	84.6	91.4	88.2	85.0	81.8	78.6	81.8	85.0	88.2
100°	70.9	91.5	112.2	121.1	118.5	115.8	113.1	110.4	113.1	115.8	118.5
102.5°	148.1	150.8	153.5	153.9	151.9	149.9	147.9	145.9	147.9	149.9	151.9
105°	208.5	207.8	207.1	206.2	205.3	204.4	203.5	202.6	203.5	204.4	205.3
107.5°	259.8	258.8	257.8	257.1	256.7	256.1	255.7	255.3	255.7	256.1	256.7
110°	295.1	294.2	293.3	292.7	292.1	291.7	291.3	290.8	291.3	291.7	292.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	329.9	329.6	329.2	328.6	327.7	326.9	326.1	325.3	326.1	326.9	327.7
115°	380.0	380.1	380.3	380.1	379.7	379.3	378.8	378.3	378.8	379.3	379.7
117.5°	429.6	429.3	429.0	428.5	427.9	427.3	426.7	426.1	426.7	427.3	427.9
120°	460.8	460.9	461.1	460.8	460.3	459.7	459.1	458.5	459.1	459.7	460.3
122.5°	490.8	490.5	490.3	490.1	489.7	489.3	489.0	488.6	489.0	489.3	489.7
125°	533.8	534.1	534.3	534.3	533.6	533.0	532.4	531.8	532.4	533.0	533.6
127.5°	575.1	574.5	573.8	573.3	573.3	573.1	572.9	572.7	572.9	573.1	573.3
130°	601.0	600.5	600.0	599.8	599.6	599.4	599.3	599.2	599.3	599.4	599.6
132.5°	626.0	625.4	624.9	624.5	624.2	624.0	623.6	623.4	623.6	624.0	624.2
135°	660.6	660.0	659.4	659.2	659.3	659.4	659.6	659.8	659.6	659.4	659.3
137.5°	693.9	693.2	692.5	692.2	692.1	692.1	692.0	691.9	692.0	692.1	692.1
140°	715.1	714.7	714.5	714.1	713.9	713.5	713.3	712.9	713.3	713.5	713.9
142.5°	734.7	734.4	734.3	733.9	733.4	732.9	732.3	731.8	732.3	732.9	733.4
145°	762.8	762.8	762.8	762.5	762.1	761.6	761.2	760.7	761.2	761.6	762.1
147.5°	787.1	787.3	787.5	787.1	786.3	785.4	784.6	783.8	784.6	785.4	786.3
150°	802.8	802.9	803.1	802.8	802.3	801.7	801.1	800.5	801.1	801.7	802.3
152.5°	816.0	816.2	816.5	816.4	815.9	815.4	814.9	814.4	814.9	815.4	815.9
155°	833.6	834.1	834.6	834.7	834.6	834.4	834.2	834.1	834.2	834.4	834.6
157.5°	849.0	849.5	850.0	850.3	850.4	850.5	850.6	850.7	850.6	850.5	850.4
160°	858.0	858.2	858.2	858.6	859.0	859.5	859.9	860.4	859.9	859.5	859.0
162.5°	866.1	866.2	866.3	866.7	867.3	867.8	868.4	869.0	868.4	867.8	867.3
165°	876.5	876.5	876.5	876.9	877.6	878.4	879.2	879.9	879.2	878.4	877.6
167.5°	884.8	884.8	884.9	885.4	886.1	886.9	887.7	888.5	887.7	886.9	886.1
170°	889.7	889.5	889.4	889.8	890.6	891.6	892.4	893.4	892.4	891.6	890.6
172.5°	892.9	892.8	892.6	893.0	893.9	894.8	895.7	896.6	895.7	894.8	893.9
175°	896.4	896.3	896.1	896.5	897.4	898.3	899.1	900.1	899.1	898.3	897.4
177.5°	898.5	898.3	898.0	898.4	899.1	900.0	900.9	901.7	900.9	900.0	899.1
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	5.8	5.9	6.2	6.0	6.5	6.7	6.7	6.9	7.2	7.1	7.2
90°	8.6	10.0	11.2	12.4	13.6	14.8	15.7	16.6	17.5	18.4	19.0
92.5°	8.9	9.5	10.7	11.9	13.1	14.3	15.2	16.1	17.0	17.8	18.3
95°	16.7	14.2	14.4	14.6	14.6	14.8	15.7	16.6	17.5	18.4	18.9
97.5°	91.4	84.6	67.8	51.1	34.4	17.7	17.8	18.0	18.1	18.2	18.3
100°	121.1	112.2	91.5	70.9	50.3	29.6	27.0	24.5	22.0	19.5	18.3
102.5°	153.9	153.5	150.8	148.1	145.4	142.8	115.3	87.8	60.4	33.0	19.3
105°	206.2	207.1	207.8	208.5	209.3	210.0	211.4	212.8	214.0	215.4	213.4
107.5°	257.1	257.8	258.8	259.8	260.9	261.9	262.5	263.2	263.8	264.5	265.1
110°	292.7	293.3	294.2	295.1	296.0	296.9	297.2	297.5	297.8	298.1	298.4



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	328.6	329.2	329.6	329.9	330.4	330.8	330.8	330.7	330.6	330.5	330.8
115°	380.1	380.3	380.1	380.0	379.9	379.7	380.0	380.3	380.6	380.9	381.1
117.5°	428.5	429.0	429.3	429.6	430.0	430.3	430.2	430.2	430.2	430.1	430.0
120°	460.8	461.1	460.9	460.8	460.6	460.5	460.8	461.1	461.4	461.7	461.7
122.5°	490.1	490.3	490.5	490.8	490.9	491.2	491.4	491.5	491.7	491.9	491.8
125°	534.3	534.3	534.1	533.8	533.5	533.2	533.6	534.1	534.5	534.9	535.3
127.5°	573.3	573.8	574.5	575.1	575.8	576.5	576.4	576.4	576.3	576.2	576.1
130°	599.8	600.0	600.5	601.0	601.4	601.8	602.0	602.2	602.3	602.4	602.5
132.5°	624.5	624.9	625.4	626.0	626.5	627.2	627.3	627.5	627.6	627.8	627.8
135°	659.2	659.4	660.0	660.6	661.2	661.8	662.0	662.4	662.6	663.0	663.2
137.5°	692.2	692.5	693.2	693.9	694.5	695.2	695.5	695.8	696.1	696.5	696.5
140°	714.1	714.5	714.7	715.1	715.3	715.6	716.1	716.5	717.0	717.4	717.7
142.5°	733.9	734.3	734.4	734.7	734.9	735.0	735.4	735.6	736.0	736.3	736.5
145°	762.5	762.8	762.8	762.8	762.8	762.8	762.9	763.0	763.2	763.4	763.5
147.5°	787.1	787.5	787.3	787.1	787.0	786.9	787.0	787.1	787.2	787.3	787.5
150°	802.8	803.1	802.9	802.8	802.6	802.5	802.5	802.5	802.5	802.5	802.5
152.5°	816.4	816.5	816.2	816.0	815.6	815.4	815.6	815.9	816.1	816.3	816.4
155°	834.7	834.6	834.1	833.6	833.2	832.8	833.4	834.0	834.6	835.2	835.3
157.5°	850.3	850.0	849.5	849.0	848.5	848.0	848.8	849.5	850.3	851.1	851.1
160°	858.6	858.2	858.2	858.0	857.8	857.6	858.6	859.5	860.4	861.3	861.3
162.5°	866.7	866.3	866.2	866.1	865.9	865.7	866.7	867.5	868.4	869.4	869.3
165°	876.9	876.5	876.5	876.5	876.5	876.5	877.7	878.9	880.1	881.3	881.2
167.5°	885.4	884.9	884.8	884.8	884.7	884.6	885.9	887.3	888.6	889.8	889.8
170°	889.8	889.4	889.5	889.7	889.8	890.0	891.1	892.3	893.5	894.8	894.6
172.5°	893.0	892.6	892.8	892.9	893.0	893.2	894.4	895.6	896.8	898.0	897.8
175°	896.5	896.1	896.3	896.4	896.6	896.7	898.0	899.4	900.8	902.1	901.9
177.5°	898.4	898.0	898.3	898.5	898.8	899.0	899.9	901.0	901.9	902.8	902.6
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	7.6	7.5	7.4	7.7	7.4	7.5	7.6	7.2	7.1	7.2	6.9
90°	19.3	19.6	19.9	20.2	19.9	19.6	19.3	19.0	18.4	17.5	16.6
92.5°	18.4	18.4	18.5	18.6	18.5	18.4	18.4	18.3	17.8	17.0	16.1
95°	19.1	19.2	19.4	19.5	19.4	19.2	19.1	18.9	18.4	17.5	16.6
97.5°	18.4	18.5	18.7	18.9	18.7	18.5	18.4	18.3	18.2	18.1	18.0
100°	18.4	18.5	18.7	18.9	18.7	18.5	18.4	18.3	19.5	22.0	24.5
102.5°	19.3	19.3	19.4	19.4	19.4	19.3	19.3	19.3	33.0	60.4	87.8
105°	208.0	202.6	197.3	191.8	197.3	202.6	208.0	213.4	215.4	214.0	212.8
107.5°	265.7	266.2	266.8	267.4	266.8	266.2	265.7	265.1	264.5	263.8	263.2
110°	298.9	299.4	299.8	300.2	299.8	299.4	298.9	298.4	298.1	297.8	297.5



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	331.4	332.0	332.5	333.1	332.5	332.0	331.4	330.8	330.5	330.6	330.7
115°	381.1	381.1	381.1	381.1	381.1	381.1	381.1	381.1	380.9	380.6	380.3
117.5°	430.0	429.9	429.8	429.8	429.8	429.9	430.0	430.0	430.1	430.2	430.2
120°	461.4	461.1	460.8	460.5	460.8	461.1	461.4	461.7	461.7	461.4	461.1
122.5°	491.5	491.2	490.9	490.6	490.9	491.2	491.5	491.8	491.9	491.7	491.5
125°	535.5	535.5	535.7	535.9	535.7	535.5	535.5	535.3	534.9	534.5	534.1
127.5°	575.9	575.8	575.8	575.6	575.8	575.8	575.9	576.1	576.2	576.3	576.4
130°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.4	602.3	602.2
132.5°	627.7	627.5	627.4	627.3	627.4	627.5	627.7	627.8	627.8	627.6	627.5
135°	663.6	663.8	664.2	664.4	664.2	663.8	663.6	663.2	663.0	662.6	662.4
137.5°	696.5	696.4	696.3	696.2	696.3	696.4	696.5	696.5	696.5	696.1	695.8
140°	717.9	718.0	718.2	718.3	718.2	718.0	717.9	717.7	717.4	717.0	716.5
142.5°	736.5	736.6	736.6	736.6	736.6	736.6	736.5	736.5	736.3	736.0	735.6
145°	763.9	764.1	764.5	764.7	764.5	764.1	763.9	763.5	763.4	763.2	763.0
147.5°	787.6	787.7	787.9	788.1	787.9	787.7	787.6	787.5	787.3	787.2	787.1
150°	802.7	802.8	803.0	803.1	803.0	802.8	802.7	802.5	802.5	802.5	802.5
152.5°	816.3	816.2	816.1	816.1	816.1	816.2	816.3	816.4	816.3	816.1	815.9
155°	834.7	834.3	833.9	833.4	833.9	834.3	834.7	835.3	835.2	834.6	834.0
157.5°	850.3	849.5	848.8	848.0	848.8	849.5	850.3	851.1	851.1	850.3	849.5
160°	860.4	859.5	858.6	857.6	858.6	859.5	860.4	861.3	861.3	860.4	859.5
162.5°	868.2	867.2	866.3	865.2	866.3	867.2	868.2	869.3	869.4	868.4	867.5
165°	879.9	878.6	877.2	875.8	877.2	878.6	879.9	881.2	881.3	880.1	878.9
167.5°	888.3	886.7	885.3	883.8	885.3	886.7	888.3	889.8	889.8	888.6	887.3
170°	893.1	891.7	890.1	888.6	890.1	891.7	893.1	894.6	894.8	893.5	892.3
172.5°	896.2	894.6	892.9	891.3	892.9	894.6	896.2	897.8	898.0	896.8	895.6
175°	900.1	898.3	896.5	894.7	896.5	898.3	900.1	901.9	902.1	900.8	899.4
177.5°	901.1	899.7	898.3	896.8	898.3	899.7	901.1	902.6	902.8	901.9	901.0
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	6.7	6.7	6.5	6.0	6.2	5.9	5.8	5.4	5.6	5.8	5.9
90°	15.7	14.8	13.6	12.4	11.2	10.0	8.6	7.0	5.3	3.7	2.0
92.5°	15.2	14.3	13.1	11.9	10.7	9.5	8.9	8.8	8.7	8.6	8.5
95°	15.7	14.8	14.6	14.6	14.4	14.2	16.7	21.8	26.9	31.9	37.0
97.5°	17.8	17.7	34.4	51.1	67.8	84.6	91.4	88.2	85.0	81.8	78.6
100°	27.0	29.6	50.3	70.9	91.5	112.2	121.1	118.5	115.8	113.1	110.4
102.5°	115.3	142.8	145.4	148.1	150.8	153.5	153.9	151.9	149.9	147.9	145.9
105°	211.4	210.0	209.3	208.5	207.8	207.1	206.2	205.3	204.4	203.5	202.6
107.5°	262.5	261.9	260.9	259.8	258.8	257.8	257.1	256.7	256.1	255.7	255.3
110°	297.2	296.9	296.0	295.1	294.2	293.3	292.7	292.1	291.7	291.3	290.8



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	330.8	330.8	330.4	329.9	329.6	329.2	328.6	327.7	326.9	326.1	325.3
115°	380.0	379.7	379.9	380.0	380.1	380.3	380.1	379.7	379.3	378.8	378.3
117.5°	430.2	430.3	430.0	429.6	429.3	429.0	428.5	427.9	427.3	426.7	426.1
120°	460.8	460.5	460.6	460.8	460.9	461.1	460.8	460.3	459.7	459.1	458.5
122.5°	491.4	491.2	490.9	490.8	490.5	490.3	490.1	489.7	489.3	489.0	488.6
125°	533.6	533.2	533.5	533.8	534.1	534.3	534.3	533.6	533.0	532.4	531.8
127.5°	576.4	576.5	575.8	575.1	574.5	573.8	573.3	573.3	573.1	572.9	572.7
130°	602.0	601.8	601.4	601.0	600.5	600.0	599.8	599.6	599.4	599.3	599.2
132.5°	627.3	627.2	626.5	626.0	625.4	624.9	624.5	624.2	624.0	623.6	623.4
135°	662.0	661.8	661.2	660.6	660.0	659.4	659.2	659.3	659.4	659.6	659.8
137.5°	695.5	695.2	694.5	693.9	693.2	692.5	692.2	692.1	692.1	692.0	691.9
140°	716.1	715.6	715.3	715.1	714.7	714.5	714.1	713.9	713.5	713.3	712.9
142.5°	735.4	735.0	734.9	734.7	734.4	734.3	733.9	733.4	732.9	732.3	731.8
145°	762.9	762.8	762.8	762.8	762.8	762.8	762.5	762.1	761.6	761.2	760.7
147.5°	787.0	786.9	787.0	787.1	787.3	787.5	787.1	786.3	785.4	784.6	783.8
150°	802.5	802.5	802.6	802.8	802.9	803.1	802.8	802.3	801.7	801.1	800.5
152.5°	815.6	815.4	815.6	816.0	816.2	816.5	816.4	815.9	815.4	814.9	814.4
155°	833.4	832.8	833.2	833.6	834.1	834.6	834.7	834.6	834.4	834.2	834.1
157.5°	848.8	848.0	848.5	849.0	849.5	850.0	850.3	850.4	850.5	850.6	850.7
160°	858.6	857.6	857.8	858.0	858.2	858.2	858.6	859.0	859.5	859.9	860.4
162.5°	866.7	865.7	865.9	866.1	866.2	866.3	866.7	867.3	867.8	868.4	869.0
165°	877.7	876.5	876.5	876.5	876.5	876.5	876.9	877.6	878.4	879.2	879.9
167.5°	885.9	884.6	884.7	884.8	884.8	884.9	885.4	886.1	886.9	887.7	888.5
170°	891.1	890.0	889.8	889.7	889.5	889.4	889.8	890.6	891.6	892.4	893.4
172.5°	894.4	893.2	893.0	892.9	892.8	892.6	893.0	893.9	894.8	895.7	896.6
175°	898.0	896.7	896.6	896.4	896.3	896.1	896.5	897.4	898.3	899.1	900.1
177.5°	899.9	899.0	898.8	898.5	898.3	898.0	898.4	899.1	900.0	900.9	901.7
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.1	5.9	5.6	5.8	6.1	6.0	6.4	6.6	6.9	6.9	7.4
90°	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7	16.6
92.5°	8.6	8.7	8.8	8.9	9.5	10.7	11.9	13.1	14.3	15.2	16.1
95°	31.9	26.9	21.8	16.7	14.2	14.4	14.6	14.6	14.8	15.7	16.6
97.5°	81.8	85.0	88.2	91.4	84.6	67.8	51.1	34.4	17.7	17.8	18.0
100°	113.1	115.8	118.5	121.1	112.2	91.5	70.9	50.3	29.6	27.0	24.5
102.5°	147.9	149.9	151.9	153.9	153.5	150.8	148.1	145.4	142.8	115.3	87.8
105°	203.5	204.4	205.3	206.2	207.1	207.8	208.5	209.3	210.0	211.4	212.8
107.5°	255.7	256.1	256.7	257.1	257.8	258.8	259.8	260.9	261.9	262.5	263.2
110°	291.3	291.7	292.1	292.7	293.3	294.2	295.1	296.0	296.9	297.2	297.5



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.1	326.9	327.7	328.6	329.2	329.6	329.9	330.4	330.8	330.8	330.7
115°	378.8	379.3	379.7	380.1	380.3	380.1	380.0	379.9	379.7	380.0	380.3
117.5°	426.7	427.3	427.9	428.5	429.0	429.3	429.6	430.0	430.3	430.2	430.2
120°	459.1	459.7	460.3	460.8	461.1	460.9	460.8	460.6	460.5	460.8	461.1
122.5°	489.0	489.3	489.7	490.1	490.3	490.5	490.8	490.9	491.2	491.4	491.5
125°	532.4	533.0	533.6	534.3	534.3	534.1	533.8	533.5	533.2	533.6	534.1
127.5°	572.9	573.1	573.3	573.3	573.8	574.5	575.1	575.8	576.5	576.4	576.4
130°	599.3	599.4	599.6	599.8	600.0	600.5	601.0	601.4	601.8	602.0	602.2
132.5°	623.6	624.0	624.2	624.5	624.9	625.4	626.0	626.5	627.2	627.3	627.5
135°	659.6	659.4	659.3	659.2	659.4	660.0	660.6	661.2	661.8	662.0	662.4
137.5°	692.0	692.1	692.1	692.2	692.5	693.2	693.9	694.5	695.2	695.5	695.8
140°	713.3	713.5	713.9	714.1	714.5	714.7	715.1	715.3	715.6	716.1	716.5
142.5°	732.3	732.9	733.4	733.9	734.3	734.4	734.7	734.9	735.0	735.4	735.6
145°	761.2	761.6	762.1	762.5	762.8	762.8	762.8	762.8	762.8	762.9	763.0
147.5°	784.6	785.4	786.3	787.1	787.5	787.3	787.1	787.0	786.9	787.0	787.1
150°	801.1	801.7	802.3	802.8	803.1	802.9	802.8	802.6	802.5	802.5	802.5
152.5°	814.9	815.4	815.9	816.4	816.5	816.2	816.0	815.6	815.4	815.6	815.9
155°	834.2	834.4	834.6	834.7	834.6	834.1	833.6	833.2	832.8	833.4	834.0
157.5°	850.6	850.5	850.4	850.3	850.0	849.5	849.0	848.5	848.0	848.8	849.5
160°	859.9	859.5	859.0	858.6	858.2	858.2	858.0	857.8	857.6	858.6	859.5
162.5°	868.4	867.8	867.3	866.7	866.3	866.2	866.1	865.9	865.7	866.7	867.5
165°	879.2	878.4	877.6	876.9	876.5	876.5	876.5	876.5	876.5	877.7	878.9
167.5°	887.7	886.9	886.1	885.4	884.9	884.8	884.8	884.7	884.6	885.9	887.3
170°	892.4	891.6	890.6	889.8	889.4	889.5	889.7	889.8	890.0	891.1	892.3
172.5°	895.7	894.8	893.9	893.0	892.6	892.8	892.9	893.0	893.2	894.4	895.6
175°	899.1	898.3	897.4	896.5	896.1	896.3	896.4	896.6	896.7	898.0	899.4
177.5°	900.9	900.0	899.1	898.4	898.0	898.3	898.5	898.8	899.0	899.9	901.0
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	7.2	7.2	7.6	7.4	7.5	7.4	7.7
90°	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	17.0	17.8	18.3	18.4	18.4	18.5	18.6
95°	17.5	18.4	18.9	19.1	19.2	19.4	19.5
97.5°	18.1	18.2	18.3	18.4	18.5	18.7	18.9
100°	22.0	19.5	18.3	18.4	18.5	18.7	18.9
102.5°	60.4	33.0	19.3	19.3	19.3	19.4	19.4
105°	214.0	215.4	213.4	208.0	202.6	197.3	191.8
107.5°	263.8	264.5	265.1	265.7	266.2	266.8	267.4
110°	297.8	298.1	298.4	298.9	299.4	299.8	300.2



TEST NUMBER: P332877-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	330.6	330.5	330.8	331.4	332.0	332.5	333.1
115°	380.6	380.9	381.1	381.1	381.1	381.1	381.1
117.5°	430.2	430.1	430.0	430.0	429.9	429.8	429.8
120°	461.4	461.7	461.7	461.4	461.1	460.8	460.5
122.5°	491.7	491.9	491.8	491.5	491.2	490.9	490.6
125°	534.5	534.9	535.3	535.5	535.5	535.7	535.9
127.5°	576.3	576.2	576.1	575.9	575.8	575.8	575.6
130°	602.3	602.4	602.5	602.5	602.5	602.5	602.5
132.5°	627.6	627.8	627.8	627.7	627.5	627.4	627.3
135°	662.6	663.0	663.2	663.6	663.8	664.2	664.4
137.5°	696.1	696.5	696.5	696.5	696.4	696.3	696.2
140°	717.0	717.4	717.7	717.9	718.0	718.2	718.3
142.5°	736.0	736.3	736.5	736.5	736.6	736.6	736.6
145°	763.2	763.4	763.5	763.9	764.1	764.5	764.7
147.5°	787.2	787.3	787.5	787.6	787.7	787.9	788.1
150°	802.5	802.5	802.5	802.7	802.8	803.0	803.1
152.5°	816.1	816.3	816.4	816.3	816.2	816.1	816.1
155°	834.6	835.2	835.3	834.7	834.3	833.9	833.4
157.5°	850.3	851.1	851.1	850.3	849.5	848.8	848.0
160°	860.4	861.3	861.3	860.4	859.5	858.6	857.6
162.5°	868.4	869.4	869.3	868.2	867.2	866.3	865.2
165°	880.1	881.3	881.2	879.9	878.6	877.2	875.8
167.5°	888.6	889.8	889.8	888.3	886.7	885.3	883.8
170°	893.5	894.8	894.6	893.1	891.7	890.1	888.6
172.5°	896.8	898.0	897.8	896.2	894.6	892.9	891.3
175°	900.8	902.1	901.9	900.1	898.3	896.5	894.7
177.5°	901.9	902.8	902.6	901.1	899.7	898.3	896.8
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1

(END OF REPORT)