

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332879-935

Luminaire Tested: **S124RDIP-S350D810U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332879-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D810U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3772.6 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.3
10°-20°	147.8	3.9
20°-30°	231.2	6.1
30°-40°	257.0	6.8
40°-50°	228.0	6.0
50°-60°	177.7	4.7
60°-70°	116.3	3.1
70°-80°	57.2	1.5
80°-90°	16.0	0.4
90°-100°	247.5	6.6
100°-110°	515.1	13.7
110°-120°	461.4	12.2
120°-130°	388.1	10.3
130°-140°	323.6	8.6
140°-150°	247.2	6.6
150°-160°	173.8	4.6
160°-170°	102.2	2.7
170°-180°	33.3	0.9
0°-30°	428.0	11.3
0°-40°	685.0	18.2
0°-60°	1090.8	28.9
0°-90°	1280.3	33.9
90°-120°	1224.0	32.4
90°-150°	2183.0	57.9
90°-180°	2492.0	66.1
0°-180°	3772.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	14	1	14	1	14	12
95°	164	22	164	22	164	255
105°	947	79	947	79	947	937
115°	910	139	910	139	910	903
125°	726	193	726	193	726	659
135°	649	230	649	230	649	501
145°	530	265	530	265	530	336
155°	444	301	444	301	444	207
165°	387	328	387	328	387	111
175°	349	342	349	342	349	34
180°	343	343	343	343	343	



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	6.4	6.3	6.5	6.4	6.5	6.3	6.3	6.5	6.0	6.4	6.0
90°	14.1	14.1	14.8	14.1	13.4	13.4	12.8	12.1	11.5	12.1	10.8
92.5°	51.8	51.8	54.2	57.8	65.7	79.2	99.5	132.2	177.9	213.5	186.9
95°	164.3	173.1	185.1	206.0	239.0	304.3	394.5	498.9	564.2	548.7	414.1
97.5°	439.1	453.1	473.3	513.8	562.1	632.4	698.3	737.0	708.8	577.9	387.5
100°	617.3	622.8	642.9	684.0	742.6	792.4	825.4	811.9	713.6	541.3	351.5
102.5°	772.5	776.8	798.1	827.9	863.8	884.5	874.9	808.1	673.2	495.5	327.2
105°	947.3	951.3	960.7	966.1	964.8	937.1	870.5	754.1	599.9	441.6	306.3
107.5°	1012.1	1010.4	1003.7	988.3	955.0	895.0	801.2	677.2	540.6	411.5	302.6
110°	1013.2	1007.2	995.1	966.7	918.9	844.9	747.3	630.9	511.0	401.2	303.6



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	981.5	971.6	954.7	920.4	866.2	792.1	699.9	596.9	494.3	396.4	306.9
115°	909.6	904.1	882.6	842.2	789.0	724.4	645.7	562.8	478.6	393.8	313.1
117.5°	836.7	832.5	810.7	776.8	731.4	676.6	614.7	546.1	471.7	393.1	319.7
120°	795.7	788.3	770.9	741.2	702.8	655.0	601.2	538.6	467.9	393.1	324.5
122.5°	763.4	756.0	741.2	715.9	683.5	641.6	592.5	532.1	463.6	392.6	329.3
125°	725.7	721.7	708.9	689.4	662.5	625.4	579.0	521.1	456.4	391.8	336.7
127.5°	703.7	699.6	688.9	671.5	644.5	609.2	562.9	507.6	446.9	390.4	342.4
130°	690.8	686.7	676.0	659.1	631.5	595.8	550.0	496.9	441.0	389.8	346.7
132.5°	676.2	672.2	661.9	642.9	615.9	580.2	535.5	485.5	435.6	389.3	350.5
135°	649.0	645.0	634.2	615.4	588.4	554.7	513.7	469.9	427.5	388.5	356.1
137.5°	615.4	610.4	601.6	583.0	557.8	527.4	492.8	455.8	420.5	388.3	359.5
140°	591.1	585.7	576.3	561.5	538.0	509.6	479.3	447.7	416.7	387.8	362.2
142.5°	565.2	561.5	553.1	539.4	518.5	494.0	468.0	440.1	413.5	387.8	364.4
145°	529.9	526.5	519.7	508.3	491.5	472.6	452.5	429.6	407.9	386.4	365.6
147.5°	498.4	497.2	492.1	482.3	469.9	455.1	438.9	420.8	403.0	384.0	366.3
150°	480.7	480.0	476.0	467.3	456.4	444.4	430.8	415.3	399.2	382.4	366.3
152.5°	464.5	463.8	461.4	454.3	445.1	435.1	422.8	409.5	394.9	379.7	365.2
155°	443.7	443.7	441.6	436.3	429.6	421.5	411.4	400.5	388.5	375.7	363.5
157.5°	425.3	425.3	424.1	420.1	415.0	408.5	400.0	391.0	381.9	371.5	361.8
160°	414.1	414.1	413.4	409.3	405.3	399.9	392.5	385.1	377.0	368.2	360.2
162.5°	403.3	403.8	403.1	399.1	396.1	391.3	385.5	379.2	372.7	365.1	358.6
165°	387.1	387.8	388.5	385.7	383.1	379.7	375.0	370.9	365.6	360.2	355.5
167.5°	374.3	374.9	375.0	373.2	371.9	369.9	366.1	363.0	359.1	355.3	352.2
170°	366.3	366.3	366.9	366.3	364.9	362.9	360.2	358.2	354.8	352.1	350.1
172.5°	358.2	359.2	359.9	359.2	358.4	357.0	355.3	353.9	351.0	348.9	347.9
175°	348.7	350.1	351.5	350.1	350.1	350.1	348.7	348.1	346.7	345.3	345.3
177.5°	343.2	344.3	345.3	344.8	345.3	344.8	344.8	344.3	343.7	343.2	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	5.8	5.6	5.2	5.2	5.2	5.7	5.8	5.7	5.4	5.3	5.0
90°	9.4	9.4	5.4	5.4	4.7	4.0	2.0	0.7	2.0	4.0	4.7
92.5°	136.0	83.8	49.5	35.6	25.7	17.5	11.2	7.7	11.2	17.5	25.7
95°	253.1	142.8	84.1	55.9	39.7	31.0	24.2	22.2	24.2	31.0	39.7
97.5°	227.6	136.4	91.3	67.6	53.7	45.6	39.9	39.9	39.9	45.6	53.7
100°	214.1	138.0	98.3	76.7	64.0	55.9	51.1	51.1	51.1	55.9	64.0
102.5°	210.3	143.4	107.5	87.0	74.7	67.2	63.0	61.9	63.0	67.2	74.7
105°	212.1	156.2	123.9	104.4	92.2	84.1	80.8	78.8	80.8	84.1	92.2
107.5°	222.1	171.2	141.5	122.3	110.6	102.0	98.7	97.4	98.7	102.0	110.6
110°	229.5	182.4	152.8	134.7	122.5	114.4	111.1	109.8	111.1	114.4	122.5



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	237.6	193.2	164.7	146.5	134.4	126.8	123.0	121.6	123.0	126.8	134.4
115°	250.5	210.1	183.1	165.0	152.1	145.4	140.7	138.7	140.7	145.4	152.1
117.5°	263.5	226.4	200.8	181.9	170.0	162.6	158.3	156.4	158.3	162.6	170.0
120°	272.7	237.6	212.1	193.2	181.8	174.4	169.6	168.3	169.6	174.4	181.8
122.5°	281.3	248.4	222.8	204.5	192.0	185.1	180.5	179.1	180.5	185.1	192.0
125°	294.2	263.2	239.0	220.2	207.3	199.9	195.9	193.2	195.9	199.9	207.3
127.5°	305.4	277.0	253.6	234.5	221.2	212.8	207.9	205.8	207.9	212.8	221.2
130°	312.4	286.1	263.2	243.7	230.9	220.8	215.4	212.8	215.4	220.8	230.9
132.5°	319.3	293.7	270.8	252.4	238.5	228.9	221.9	219.7	221.9	228.9	238.5
135°	328.6	304.3	282.1	264.6	250.5	239.0	232.3	229.5	232.3	239.0	250.5
137.5°	335.0	312.4	291.6	274.9	260.3	249.3	241.9	239.4	241.9	249.3	260.3
140°	339.3	317.8	297.6	281.4	267.3	255.8	248.4	246.4	248.4	255.8	267.3
142.5°	342.5	322.6	303.0	287.3	273.7	262.9	256.0	253.9	256.0	262.9	273.7
145°	346.0	327.9	310.4	295.6	282.8	273.4	266.6	264.6	266.6	273.4	282.8
147.5°	349.1	333.3	316.8	303.5	292.8	283.2	277.2	276.6	277.2	283.2	292.8
150°	350.8	336.0	321.2	308.3	298.3	290.2	284.8	284.1	284.8	290.2	298.3
152.5°	351.8	338.1	324.9	313.2	304.2	296.6	291.3	291.1	291.3	296.6	304.2
155°	352.8	341.3	329.8	319.8	312.4	305.7	301.6	300.9	301.6	305.7	312.4
157.5°	352.8	343.6	333.9	326.0	319.5	314.3	310.5	310.5	310.5	314.3	319.5
160°	352.8	344.7	336.7	329.2	323.8	319.1	316.4	316.4	316.4	319.1	323.8
162.5°	352.8	345.8	338.2	332.4	327.6	323.4	321.2	321.8	321.2	323.4	327.6
165°	351.5	346.0	340.0	336.0	332.6	329.2	327.9	327.9	327.9	329.2	332.6
167.5°	349.8	345.9	341.5	338.4	336.5	333.9	333.3	333.9	333.3	333.9	336.5
170°	348.7	345.3	342.0	340.0	338.6	336.7	336.0	336.7	336.0	336.7	338.6
172.5°	347.7	344.8	342.5	341.0	340.3	338.8	338.6	339.3	338.6	338.8	340.3
175°	346.0	344.1	342.7	342.7	342.0	341.3	341.3	342.0	341.3	341.3	342.0
177.5°	344.3	343.2	342.7	342.7	342.7	342.2	342.7	343.2	342.7	342.2	342.7
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	5.2	5.0	5.8	5.5	5.9	6.2	5.9	6.0	6.3	6.1	6.1
90°	5.4	5.4	9.4	9.4	10.8	12.1	11.5	12.1	12.8	13.4	13.4
92.5°	35.6	49.5	83.8	136.0	186.9	213.5	177.9	132.2	99.5	79.2	65.7
95°	55.9	84.1	142.8	253.1	414.1	548.7	564.2	498.9	394.5	304.3	239.0
97.5°	67.6	91.3	136.4	227.6	387.5	577.9	708.8	737.0	698.3	632.4	562.1
100°	76.7	98.3	138.0	214.1	351.5	541.3	713.6	811.9	825.4	792.4	742.6
102.5°	87.0	107.5	143.4	210.3	327.2	495.5	673.2	808.1	874.9	884.5	863.8
105°	104.4	123.9	156.2	212.1	306.3	441.6	599.9	754.1	870.5	937.1	964.8
107.5°	122.3	141.5	171.2	222.1	302.6	411.5	540.6	677.2	801.2	895.0	955.0
110°	134.7	152.8	182.4	229.5	303.6	401.2	511.0	630.9	747.3	844.9	918.9



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	146.5	164.7	193.2	237.6	306.9	396.4	494.3	596.9	699.9	792.1	866.2
115°	165.0	183.1	210.1	250.5	313.1	393.8	478.6	562.8	645.7	724.4	789.0
117.5°	181.9	200.8	226.4	263.5	319.7	393.1	471.7	546.1	614.7	676.6	731.4
120°	193.2	212.1	237.6	272.7	324.5	393.1	467.9	538.6	601.2	655.0	702.8
122.5°	204.5	222.8	248.4	281.3	329.3	392.6	463.6	532.1	592.5	641.6	683.5
125°	220.2	239.0	263.2	294.2	336.7	391.8	456.4	521.1	579.0	625.4	662.5
127.5°	234.5	253.6	277.0	305.4	342.4	390.4	446.9	507.6	562.9	609.2	644.5
130°	243.7	263.2	286.1	312.4	346.7	389.8	441.0	496.9	550.0	595.8	631.5
132.5°	252.4	270.8	293.7	319.3	350.5	389.3	435.6	485.5	535.5	580.2	615.9
135°	264.6	282.1	304.3	328.6	356.1	388.5	427.5	469.9	513.7	554.7	588.4
137.5°	274.9	291.6	312.4	335.0	359.5	388.3	420.5	455.8	492.8	527.4	557.8
140°	281.4	297.6	317.8	339.3	362.2	387.8	416.7	447.7	479.3	509.6	538.0
142.5°	287.3	303.0	322.6	342.5	364.4	387.8	413.5	440.1	468.0	494.0	518.5
145°	295.6	310.4	327.9	346.0	365.6	386.4	407.9	429.6	452.5	472.6	491.5
147.5°	303.5	316.8	333.3	349.1	366.3	384.0	403.0	420.8	438.9	455.1	469.9
150°	308.3	321.2	336.0	350.8	366.3	382.4	399.2	415.3	430.8	444.4	456.4
152.5°	313.2	324.9	338.1	351.8	365.2	379.7	394.9	409.5	422.8	435.1	445.1
155°	319.8	329.8	341.3	352.8	363.5	375.7	388.5	400.5	411.4	421.5	429.6
157.5°	326.0	333.9	343.6	352.8	361.8	371.5	381.9	391.0	400.0	408.5	415.0
160°	329.2	336.7	344.7	352.8	360.2	368.2	377.0	385.1	392.5	399.9	405.3
162.5°	332.4	338.2	345.8	352.8	358.6	365.1	372.7	379.2	385.5	391.3	396.1
165°	336.0	340.0	346.0	351.5	355.5	360.2	365.6	370.9	375.0	379.7	383.1
167.5°	338.4	341.5	345.9	349.8	352.2	355.3	359.1	363.0	366.1	369.9	371.9
170°	340.0	342.0	345.3	348.7	350.1	352.1	354.8	358.2	360.2	362.9	364.9
172.5°	341.0	342.5	344.8	347.7	347.9	348.9	351.0	353.9	355.3	357.0	358.4
175°	342.7	342.7	344.1	346.0	345.3	345.3	346.7	348.1	348.7	350.1	350.1
177.5°	342.7	342.7	343.2	344.3	343.2	343.2	343.7	344.3	344.8	344.8	345.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	6.5	6.5	6.3	6.4	6.3	6.5	6.5	6.1	6.1	6.3	6.0
90°	14.1	14.8	14.1	14.1	14.1	14.8	14.1	13.4	13.4	12.8	12.1
92.5°	57.8	54.2	51.8	51.8	51.8	54.2	57.8	65.7	79.2	99.5	132.2
95°	206.0	185.1	173.1	164.3	173.1	185.1	206.0	239.0	304.3	394.5	498.9
97.5°	513.8	473.3	453.1	439.1	453.1	473.3	513.8	562.1	632.4	698.3	737.0
100°	684.0	642.9	622.8	617.3	622.8	642.9	684.0	742.6	792.4	825.4	811.9
102.5°	827.9	798.1	776.8	772.5	776.8	798.1	827.9	863.8	884.5	874.9	808.1
105°	966.1	960.7	951.3	947.3	951.3	960.7	966.1	964.8	937.1	870.5	754.1
107.5°	988.3	1003.7	1010.4	1012.1	1010.4	1003.7	988.3	955.0	895.0	801.2	677.2
110°	966.7	995.1	1007.2	1013.2	1007.2	995.1	966.7	918.9	844.9	747.3	630.9



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	920.4	954.7	971.6	981.5	971.6	954.7	920.4	866.2	792.1	699.9	596.9
115°	842.2	882.6	904.1	909.6	904.1	882.6	842.2	789.0	724.4	645.7	562.8
117.5°	776.8	810.7	832.5	836.7	832.5	810.7	776.8	731.4	676.6	614.7	546.1
120°	741.2	770.9	788.3	795.7	788.3	770.9	741.2	702.8	655.0	601.2	538.6
122.5°	715.9	741.2	756.0	763.4	756.0	741.2	715.9	683.5	641.6	592.5	532.1
125°	689.4	708.9	721.7	725.7	721.7	708.9	689.4	662.5	625.4	579.0	521.1
127.5°	671.5	688.9	699.6	703.7	699.6	688.9	671.5	644.5	609.2	562.9	507.6
130°	659.1	676.0	686.7	690.8	686.7	676.0	659.1	631.5	595.8	550.0	496.9
132.5°	642.9	661.9	672.2	676.2	672.2	661.9	642.9	615.9	580.2	535.5	485.5
135°	615.4	634.2	645.0	649.0	645.0	634.2	615.4	588.4	554.7	513.7	469.9
137.5°	583.0	601.6	610.4	615.4	610.4	601.6	583.0	557.8	527.4	492.8	455.8
140°	561.5	576.3	585.7	591.1	585.7	576.3	561.5	538.0	509.6	479.3	447.7
142.5°	539.4	553.1	561.5	565.2	561.5	553.1	539.4	518.5	494.0	468.0	440.1
145°	508.3	519.7	526.5	529.9	526.5	519.7	508.3	491.5	472.6	452.5	429.6
147.5°	482.3	492.1	497.2	498.4	497.2	492.1	482.3	469.9	455.1	438.9	420.8
150°	467.3	476.0	480.0	480.7	480.0	476.0	467.3	456.4	444.4	430.8	415.3
152.5°	454.3	461.4	463.8	464.5	463.8	461.4	454.3	445.1	435.1	422.8	409.5
155°	436.3	441.6	443.7	443.7	443.7	441.6	436.3	429.6	421.5	411.4	400.5
157.5°	420.1	424.1	425.3	425.3	425.3	424.1	420.1	415.0	408.5	400.0	391.0
160°	409.3	413.4	414.1	414.1	414.1	413.4	409.3	405.3	399.9	392.5	385.1
162.5°	399.1	403.1	403.8	403.3	403.8	403.1	399.1	396.1	391.3	385.5	379.2
165°	385.7	388.5	387.8	387.1	387.8	388.5	385.7	383.1	379.7	375.0	370.9
167.5°	373.2	375.0	374.9	374.3	374.9	375.0	373.2	371.9	369.9	366.1	363.0
170°	366.3	366.9	366.3	366.3	366.3	366.9	366.3	364.9	362.9	360.2	358.2
172.5°	359.2	359.9	359.2	358.2	359.2	359.9	359.2	358.4	357.0	355.3	353.9
175°	350.1	351.5	350.1	348.7	350.1	351.5	350.1	350.1	350.1	348.7	348.1
177.5°	344.8	345.3	344.3	343.2	344.3	345.3	344.8	345.3	344.8	344.8	344.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	5.9	6.2	5.9	5.5	5.8	5.0	5.2	5.0	5.3	5.4	5.7
90°	11.5	12.1	10.8	9.4	9.4	5.4	5.4	4.7	4.0	2.0	0.7
92.5°	177.9	213.5	186.9	136.0	83.8	49.5	35.6	25.7	17.5	11.2	7.7
95°	564.2	548.7	414.1	253.1	142.8	84.1	55.9	39.7	31.0	24.2	22.2
97.5°	708.8	577.9	387.5	227.6	136.4	91.3	67.6	53.7	45.6	39.9	39.9
100°	713.6	541.3	351.5	214.1	138.0	98.3	76.7	64.0	55.9	51.1	51.1
102.5°	673.2	495.5	327.2	210.3	143.4	107.5	87.0	74.7	67.2	63.0	61.9
105°	599.9	441.6	306.3	212.1	156.2	123.9	104.4	92.2	84.1	80.8	78.8
107.5°	540.6	411.5	302.6	222.1	171.2	141.5	122.3	110.6	102.0	98.7	97.4
110°	511.0	401.2	303.6	229.5	182.4	152.8	134.7	122.5	114.4	111.1	109.8



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.3	396.4	306.9	237.6	193.2	164.7	146.5	134.4	126.8	123.0	121.6
115°	478.6	393.8	313.1	250.5	210.1	183.1	165.0	152.1	145.4	140.7	138.7
117.5°	471.7	393.1	319.7	263.5	226.4	200.8	181.9	170.0	162.6	158.3	156.4
120°	467.9	393.1	324.5	272.7	237.6	212.1	193.2	181.8	174.4	169.6	168.3
122.5°	463.6	392.6	329.3	281.3	248.4	222.8	204.5	192.0	185.1	180.5	179.1
125°	456.4	391.8	336.7	294.2	263.2	239.0	220.2	207.3	199.9	195.9	193.2
127.5°	446.9	390.4	342.4	305.4	277.0	253.6	234.5	221.2	212.8	207.9	205.8
130°	441.0	389.8	346.7	312.4	286.1	263.2	243.7	230.9	220.8	215.4	212.8
132.5°	435.6	389.3	350.5	319.3	293.7	270.8	252.4	238.5	228.9	221.9	219.7
135°	427.5	388.5	356.1	328.6	304.3	282.1	264.6	250.5	239.0	232.3	229.5
137.5°	420.5	388.3	359.5	335.0	312.4	291.6	274.9	260.3	249.3	241.9	239.4
140°	416.7	387.8	362.2	339.3	317.8	297.6	281.4	267.3	255.8	248.4	246.4
142.5°	413.5	387.8	364.4	342.5	322.6	303.0	287.3	273.7	262.9	256.0	253.9
145°	407.9	386.4	365.6	346.0	327.9	310.4	295.6	282.8	273.4	266.6	264.6
147.5°	403.0	384.0	366.3	349.1	333.3	316.8	303.5	292.8	283.2	277.2	276.6
150°	399.2	382.4	366.3	350.8	336.0	321.2	308.3	298.3	290.2	284.8	284.1
152.5°	394.9	379.7	365.2	351.8	338.1	324.9	313.2	304.2	296.6	291.3	291.1
155°	388.5	375.7	363.5	352.8	341.3	329.8	319.8	312.4	305.7	301.6	300.9
157.5°	381.9	371.5	361.8	352.8	343.6	333.9	326.0	319.5	314.3	310.5	310.5
160°	377.0	368.2	360.2	352.8	344.7	336.7	329.2	323.8	319.1	316.4	316.4
162.5°	372.7	365.1	358.6	352.8	345.8	338.2	332.4	327.6	323.4	321.2	321.8
165°	365.6	360.2	355.5	351.5	346.0	340.0	336.0	332.6	329.2	327.9	327.9
167.5°	359.1	355.3	352.2	349.8	345.9	341.5	338.4	336.5	333.9	333.3	333.9
170°	354.8	352.1	350.1	348.7	345.3	342.0	340.0	338.6	336.7	336.0	336.7
172.5°	351.0	348.9	347.9	347.7	344.8	342.5	341.0	340.3	338.8	338.6	339.3
175°	346.7	345.3	345.3	346.0	344.1	342.7	342.7	342.0	341.3	341.3	342.0
177.5°	343.7	343.2	343.2	344.3	343.2	342.7	342.7	342.7	342.2	342.7	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	5.8	5.7	5.2	5.2	5.2	5.6	5.8	6.0	6.4	6.0	6.5
90°	2.0	4.0	4.7	5.4	5.4	9.4	9.4	10.8	12.1	11.5	12.1
92.5°	11.2	17.5	25.7	35.6	49.5	83.8	136.0	186.9	213.5	177.9	132.2
95°	24.2	31.0	39.7	55.9	84.1	142.8	253.1	414.1	548.7	564.2	498.9
97.5°	39.9	45.6	53.7	67.6	91.3	136.4	227.6	387.5	577.9	708.8	737.0
100°	51.1	55.9	64.0	76.7	98.3	138.0	214.1	351.5	541.3	713.6	811.9
102.5°	63.0	67.2	74.7	87.0	107.5	143.4	210.3	327.2	495.5	673.2	808.1
105°	80.8	84.1	92.2	104.4	123.9	156.2	212.1	306.3	441.6	599.9	754.1
107.5°	98.7	102.0	110.6	122.3	141.5	171.2	222.1	302.6	411.5	540.6	677.2
110°	111.1	114.4	122.5	134.7	152.8	182.4	229.5	303.6	401.2	511.0	630.9



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.8	134.4	146.5	164.7	193.2	237.6	306.9	396.4	494.3	596.9
115°	140.7	145.4	152.1	165.0	183.1	210.1	250.5	313.1	393.8	478.6	562.8
117.5°	158.3	162.6	170.0	181.9	200.8	226.4	263.5	319.7	393.1	471.7	546.1
120°	169.6	174.4	181.8	193.2	212.1	237.6	272.7	324.5	393.1	467.9	538.6
122.5°	180.5	185.1	192.0	204.5	222.8	248.4	281.3	329.3	392.6	463.6	532.1
125°	195.9	199.9	207.3	220.2	239.0	263.2	294.2	336.7	391.8	456.4	521.1
127.5°	207.9	212.8	221.2	234.5	253.6	277.0	305.4	342.4	390.4	446.9	507.6
130°	215.4	220.8	230.9	243.7	263.2	286.1	312.4	346.7	389.8	441.0	496.9
132.5°	221.9	228.9	238.5	252.4	270.8	293.7	319.3	350.5	389.3	435.6	485.5
135°	232.3	239.0	250.5	264.6	282.1	304.3	328.6	356.1	388.5	427.5	469.9
137.5°	241.9	249.3	260.3	274.9	291.6	312.4	335.0	359.5	388.3	420.5	455.8
140°	248.4	255.8	267.3	281.4	297.6	317.8	339.3	362.2	387.8	416.7	447.7
142.5°	256.0	262.9	273.7	287.3	303.0	322.6	342.5	364.4	387.8	413.5	440.1
145°	266.6	273.4	282.8	295.6	310.4	327.9	346.0	365.6	386.4	407.9	429.6
147.5°	277.2	283.2	292.8	303.5	316.8	333.3	349.1	366.3	384.0	403.0	420.8
150°	284.8	290.2	298.3	308.3	321.2	336.0	350.8	366.3	382.4	399.2	415.3
152.5°	291.3	296.6	304.2	313.2	324.9	338.1	351.8	365.2	379.7	394.9	409.5
155°	301.6	305.7	312.4	319.8	329.8	341.3	352.8	363.5	375.7	388.5	400.5
157.5°	310.5	314.3	319.5	326.0	333.9	343.6	352.8	361.8	371.5	381.9	391.0
160°	316.4	319.1	323.8	329.2	336.7	344.7	352.8	360.2	368.2	377.0	385.1
162.5°	321.2	323.4	327.6	332.4	338.2	345.8	352.8	358.6	365.1	372.7	379.2
165°	327.9	329.2	332.6	336.0	340.0	346.0	351.5	355.5	360.2	365.6	370.9
167.5°	333.3	333.9	336.5	338.4	341.5	345.9	349.8	352.2	355.3	359.1	363.0
170°	336.0	336.7	338.6	340.0	342.0	345.3	348.7	350.1	352.1	354.8	358.2
172.5°	338.6	338.8	340.3	341.0	342.5	344.8	347.7	347.9	348.9	351.0	353.9
175°	341.3	341.3	342.0	342.7	342.7	344.1	346.0	345.3	345.3	346.7	348.1
177.5°	342.7	342.2	342.7	342.7	342.7	343.2	344.3	343.2	343.2	343.7	344.3
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	6.3	6.3	6.5	6.4	6.5	6.3	6.4
90°	12.8	13.4	13.4	14.1	14.8	14.1	14.1
92.5°	99.5	79.2	65.7	57.8	54.2	51.8	51.8
95°	394.5	304.3	239.0	206.0	185.1	173.1	164.3
97.5°	698.3	632.4	562.1	513.8	473.3	453.1	439.1
100°	825.4	792.4	742.6	684.0	642.9	622.8	617.3
102.5°	874.9	884.5	863.8	827.9	798.1	776.8	772.5
105°	870.5	937.1	964.8	966.1	960.7	951.3	947.3
107.5°	801.2	895.0	955.0	988.3	1003.7	1010.4	1012.1
110°	747.3	844.9	918.9	966.7	995.1	1007.2	1013.2



TEST NUMBER: P332879-935

CATALOG NUMBER: S124RDIP-S350D810U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	699.9	792.1	866.2	920.4	954.7	971.6	981.5
115°	645.7	724.4	789.0	842.2	882.6	904.1	909.6
117.5°	614.7	676.6	731.4	776.8	810.7	832.5	836.7
120°	601.2	655.0	702.8	741.2	770.9	788.3	795.7
122.5°	592.5	641.6	683.5	715.9	741.2	756.0	763.4
125°	579.0	625.4	662.5	689.4	708.9	721.7	725.7
127.5°	562.9	609.2	644.5	671.5	688.9	699.6	703.7
130°	550.0	595.8	631.5	659.1	676.0	686.7	690.8
132.5°	535.5	580.2	615.9	642.9	661.9	672.2	676.2
135°	513.7	554.7	588.4	615.4	634.2	645.0	649.0
137.5°	492.8	527.4	557.8	583.0	601.6	610.4	615.4
140°	479.3	509.6	538.0	561.5	576.3	585.7	591.1
142.5°	468.0	494.0	518.5	539.4	553.1	561.5	565.2
145°	452.5	472.6	491.5	508.3	519.7	526.5	529.9
147.5°	438.9	455.1	469.9	482.3	492.1	497.2	498.4
150°	430.8	444.4	456.4	467.3	476.0	480.0	480.7
152.5°	422.8	435.1	445.1	454.3	461.4	463.8	464.5
155°	411.4	421.5	429.6	436.3	441.6	443.7	443.7
157.5°	400.0	408.5	415.0	420.1	424.1	425.3	425.3
160°	392.5	399.9	405.3	409.3	413.4	414.1	414.1
162.5°	385.5	391.3	396.1	399.1	403.1	403.8	403.3
165°	375.0	379.7	383.1	385.7	388.5	387.8	387.1
167.5°	366.1	369.9	371.9	373.2	375.0	374.9	374.3
170°	360.2	362.9	364.9	366.3	366.9	366.3	366.3
172.5°	355.3	357.0	358.4	359.2	359.9	359.2	358.2
175°	348.7	350.1	350.1	350.1	351.5	350.1	348.7
177.5°	344.8	344.8	345.3	344.8	345.3	344.3	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7

(END OF REPORT)