

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332908-935

Luminaire Tested: **S124RDIP-S575D810U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332908-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D810U935-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4519.1 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	81	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	26
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	32	37	32	28	31	27	24	26	23	20	18
8	54	42	35	30	50	39	33	28	34	29	25	29	24	22	24	21	18	16
9	51	39	31	26	47	36	30	25	31	26	22	26	22	19	22	19	17	14
10	47	36	28	24	44	33	27	22	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6713	6713	6713	6713
5°	7786	6733	5951	6733
10°	9211	6703	5311	6703
15°	10639	6641	4563	6641
20°	11846	6556	4127	6556
25°	12229	6472	3832	6472
30°	10705	6371	3653	6371
35°	8333	6220	3546	6220
40°	6249	6048	3488	6048
45°	4933	5771	3457	5771
50°	4166	5452	3357	5452
55°	3631	5102	3178	5102
60°	3266	4737	2813	4737
65°	2881	4346	2420	4346
70°	2594	3939	2183	3939
75°	2174	3490	1862	3490
80°	1836	2975	1743	2975
85°	1556	2325	1556	2325



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.6	1.8
10°-20°	243.0	5.4
20°-30°	380.1	8.4
30°-40°	422.5	9.4
40°-50°	374.9	8.3
50°-60°	292.1	6.5
60°-70°	191.3	4.2
70°-80°	94.1	2.1
80°-90°	25.8	0.6
90°-100°	57.4	1.3
100°-110°	170.1	3.8
110°-120°	288.6	6.4
120°-130°	380.6	8.4
130°-140°	427.4	9.5
140°-150°	420.0	9.3
150°-160°	353.3	7.8
160°-170°	235.0	5.2
170°-180°	82.3	1.8
0°-30°	703.7	15.6
0°-40°	1126.2	24.9
0°-60°	1793.2	39.7
0°-90°	2104.4	46.6
90°-120°	516.1	11.4
90°-150°	1744.1	38.6
90°-180°	2415.0	53.4
0°-180°	4519.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	832	832	832	832	832	
5°	961	831	734	831	961	97
15°	1273	795	546	795	1273	362
25°	1373	727	430	727	1373	609
35°	846	631	360	631	846	530
45°	432	506	303	506	432	342
55°	258	362	226	362	258	235
65°	151	228	127	228	151	152
75°	70	112	60	112	70	77
85°	17	25	17	25	17	19
90°	20	2	20	2	20	11
95°	53	40	53	40	53	55
105°	164	157	164	157	164	173
115°	291	294	291	294	291	287
125°	424	427	424	427	424	378
135°	552	551	552	551	552	426
145°	670	670	670	670	670	420
155°	767	767	767	767	767	353
165°	833	835	833	835	833	235
175°	865	869	865	869	865	82
180°	870	870	870	870	870	



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	877.0	879.4	877.0	876.8	874.1	873.3	872.2	868.7	862.3	858.5	859.4
5°	960.8	969.1	964.5	963.8	956.4	949.1	944.3	933.7	922.2	914.6	908.2
7.5°	1057.7	1062.5	1059.5	1054.8	1042.9	1036.1	1025.3	1011.2	990.8	975.1	960.9
10°	1123.6	1127.6	1126.3	1117.6	1108.9	1091.1	1081.1	1061.3	1035.4	1015.0	995.9
12.5°	1188.4	1192.7	1180.9	1181.4	1164.8	1150.8	1134.9	1110.1	1080.2	1053.9	1030.0
15°	1273.0	1267.7	1267.7	1260.9	1242.5	1223.1	1206.7	1180.5	1143.0	1111.6	1078.4
17.5°	1339.2	1341.1	1338.3	1322.5	1308.0	1288.0	1257.8	1227.4	1192.5	1150.2	1116.4
20°	1378.9	1378.9	1375.9	1365.1	1346.3	1324.9	1292.4	1259.3	1215.0	1172.5	1134.3
22.5°	1394.9	1396.0	1392.5	1383.6	1366.8	1345.8	1318.2	1284.4	1238.9	1191.0	1143.7
25°	1372.9	1379.1	1379.8	1377.5	1372.5	1359.8	1336.0	1301.5	1260.6	1208.7	1157.8
27.5°	1260.4	1268.4	1275.5	1287.0	1302.4	1310.5	1311.6	1294.0	1258.4	1208.4	1157.2
30°	1148.4	1155.0	1176.8	1205.3	1227.4	1247.5	1265.0	1269.6	1249.6	1204.6	1150.7
32.5°	1024.0	1033.1	1054.9	1085.5	1122.4	1156.4	1195.6	1215.5	1215.0	1188.0	1138.2
35°	845.5	852.2	872.4	904.5	948.7	999.3	1061.3	1109.5	1142.4	1140.0	1109.5
37.5°	681.9	689.5	709.8	736.5	779.4	842.0	902.0	968.5	1029.2	1063.2	1053.0
40°	593.0	593.3	613.0	640.5	680.7	735.3	800.6	874.3	942.0	997.3	1008.0
42.5°	522.7	522.8	535.9	565.5	594.4	645.8	708.2	781.4	860.6	924.4	952.8
45°	432.1	435.1	445.9	463.6	486.4	529.9	579.9	647.9	736.7	812.4	859.6
47.5°	365.9	370.4	377.2	391.7	409.8	438.9	480.1	541.2	613.5	696.7	764.0
50°	331.7	332.3	341.0	349.0	364.8	388.0	424.1	475.0	541.4	621.4	696.1
52.5°	302.2	302.0	307.3	317.5	330.3	348.3	377.5	423.9	482.7	554.4	631.5
55°	258.0	259.6	263.6	271.6	281.4	294.1	317.3	352.1	398.3	459.6	529.6
57.5°	224.3	225.2	228.3	231.8	240.6	249.9	267.3	291.4	330.5	380.6	445.9
60°	202.3	202.7	203.7	208.7	215.8	224.5	236.2	256.6	289.5	335.4	386.9
62.5°	180.9	181.5	183.0	186.8	192.2	198.2	210.4	226.9	254.1	293.3	339.8
65°	150.8	151.1	153.4	154.8	159.1	164.5	173.5	184.6	203.4	236.2	271.4
67.5°	126.0	126.0	126.1	127.9	131.0	134.5	139.9	148.8	162.9	183.0	214.0
70°	109.9	109.9	110.6	111.6	113.2	116.2	119.2	126.0	136.4	152.7	176.5
72.5°	94.9	95.1	95.8	96.0	96.9	99.4	101.6	105.8	113.6	126.0	145.2
75°	69.7	70.7	72.3	73.7	75.3	75.1	77.4	80.1	82.4	89.8	100.8
77.5°	51.8	51.3	51.5	52.7	52.9	53.2	54.8	56.9	58.7	62.2	66.1
80°	39.5	39.5	40.6	40.9	40.6	40.9	42.5	43.6	44.3	45.5	49.2
82.5°	29.9	30.4	30.0	30.4	30.7	31.0	32.4	32.5	33.2	33.8	35.3
85°	16.8	17.0	17.4	16.8	16.8	16.8	17.4	17.7	18.4	18.1	18.8
87.5°	9.9	9.6	9.8	9.7	10.0	9.6	9.6	10.0	9.3	9.4	9.1
90°	20.2	19.9	19.6	19.3	19.0	18.4	17.5	16.6	15.7	14.8	13.6
92.5°	29.9	29.7	29.5	29.4	29.2	28.8	28.2	27.7	27.2	26.7	25.8
95°	53.2	53.2	53.2	53.2	53.2	53.0	52.5	52.1	51.6	51.1	50.1
97.5°	83.3	83.3	83.3	83.3	83.3	83.1	82.5	82.0	81.5	80.9	79.6
100°	104.4	104.4	104.4	104.4	104.4	104.2	103.9	103.6	103.3	103.0	101.6
102.5°	128.0	127.9	127.8	127.7	127.5	127.3	126.8	126.5	126.1	125.6	124.4
105°	164.3	163.8	163.3	162.9	162.5	162.0	161.5	161.1	160.7	160.2	159.6
107.5°	199.5	199.6	199.6	199.6	199.7	199.4	199.0	198.6	198.2	197.8	197.7
110°	224.8	224.4	223.9	223.5	223.0	222.9	223.3	223.5	223.9	224.1	224.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	250.6	250.6	250.5	250.4	250.3	250.3	250.4	250.4	250.5	250.6	250.8
115°	290.8	290.9	291.1	291.3	291.4	291.5	291.7	291.8	292.0	292.1	292.4
117.5°	329.0	329.3	329.6	329.9	330.2	330.6	331.1	331.7	332.2	332.7	332.9
120°	358.1	357.8	357.5	357.2	356.9	357.1	357.8	358.6	359.4	360.2	360.6
122.5°	382.4	382.9	383.4	383.9	384.5	385.0	385.6	386.0	386.5	387.0	387.3
125°	424.0	424.4	424.6	425.0	425.2	425.6	425.9	426.2	426.5	426.8	426.9
127.5°	462.7	463.0	463.2	463.4	463.6	463.9	464.3	464.5	464.9	465.1	465.4
130°	488.0	488.6	489.2	489.8	490.4	490.9	491.1	491.5	491.7	492.1	492.1
132.5°	515.0	515.1	515.4	515.7	515.9	516.2	516.4	516.8	517.0	517.4	517.5
135°	552.0	552.4	552.8	553.3	553.7	554.1	554.4	554.7	555.0	555.3	555.3
137.5°	590.9	590.7	590.6	590.6	590.5	590.6	591.1	591.4	591.9	592.2	591.9
140°	614.6	614.7	614.8	615.0	615.2	615.3	615.4	615.6	615.8	615.9	615.9
142.5°	638.3	638.3	638.3	638.3	638.3	638.4	638.4	638.4	638.5	638.5	638.6
145°	670.5	670.9	671.3	671.8	672.2	672.5	672.7	672.8	673.0	673.1	673.0
147.5°	703.0	703.2	703.3	703.4	703.6	703.7	703.9	704.0	704.1	704.2	704.3
150°	722.9	723.1	723.2	723.4	723.5	723.6	723.6	723.6	723.6	723.6	723.6
152.5°	741.2	741.7	742.0	742.4	742.8	742.8	742.4	742.1	741.8	741.4	741.2
155°	766.7	767.2	767.8	768.4	769.0	769.0	768.4	767.8	767.2	766.7	766.8
157.5°	789.5	790.0	790.5	791.0	791.4	791.5	791.1	790.6	790.1	789.7	789.7
160°	802.4	803.1	803.8	804.6	805.4	805.5	805.0	804.6	804.2	803.7	803.8
162.5°	815.8	816.6	817.3	818.0	818.8	818.8	817.9	817.2	816.4	815.5	815.7
165°	833.4	833.9	834.5	835.1	835.7	835.6	834.7	833.8	832.8	832.0	832.2
167.5°	845.8	846.8	847.7	848.6	849.5	849.5	848.7	847.7	846.9	845.9	845.9
170°	852.8	853.9	855.0	856.0	857.0	857.1	856.2	855.3	854.4	853.5	853.3
172.5°	858.8	859.8	860.8	861.9	863.0	863.0	861.9	860.9	859.9	858.9	858.8
175°	865.0	866.0	867.0	868.1	869.2	869.2	868.1	867.0	866.0	865.0	865.1
177.5°	868.1	869.2	870.1	871.1	872.0	872.1	871.2	870.4	869.5	868.7	868.7
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	856.7	852.9	851.0	846.7	841.6	839.0	836.5	833.1	828.5	823.7	820.2
5°	900.2	892.1	882.0	870.0	859.3	848.9	839.8	830.8	820.4	809.7	799.0
7.5°	944.8	928.9	911.9	892.1	872.9	855.4	839.3	823.9	806.5	790.8	776.6
10°	975.9	954.4	930.7	905.5	880.4	858.6	837.2	817.7	796.3	777.2	761.1
12.5°	1001.1	975.9	947.3	915.9	885.7	859.4	834.7	809.4	785.1	764.3	742.9
15°	1042.8	1008.3	969.8	932.3	893.1	857.3	824.1	794.6	766.8	737.7	717.2
17.5°	1071.6	1030.6	983.9	938.7	892.4	850.2	811.9	776.8	744.7	715.0	690.6
20°	1088.7	1043.5	991.6	940.3	888.4	843.2	802.0	763.1	730.0	697.8	672.7
22.5°	1098.4	1048.4	991.6	937.9	884.2	835.2	790.0	749.5	713.3	681.2	653.4
25°	1101.5	1047.8	989.9	928.2	869.4	817.4	770.5	726.6	686.4	654.3	624.7
27.5°	1097.2	1034.1	974.7	911.5	850.7	795.9	746.7	700.5	660.3	625.8	595.6
30°	1090.7	1023.1	959.4	893.8	832.2	779.5	727.6	683.4	641.5	605.7	575.2
32.5°	1076.9	1009.7	941.2	873.9	811.5	757.3	708.1	663.6	622.5	585.8	553.5
35°	1049.2	981.2	906.8	837.8	776.5	720.2	674.0	631.1	591.9	552.8	518.6
37.5°	1012.8	943.4	869.4	793.8	732.5	679.3	636.9	596.7	558.4	522.6	484.7
40°	978.5	915.2	838.9	763.8	700.9	649.5	610.4	573.9	535.4	499.8	461.9
42.5°	937.0	883.0	805.9	730.6	668.4	619.0	582.5	546.8	511.8	477.3	437.8
45°	867.6	826.8	754.4	682.1	619.4	570.5	537.0	505.5	474.7	441.9	404.7
47.5°	788.2	760.5	698.1	624.0	566.0	522.0	489.7	463.9	437.8	405.0	372.4
50°	733.0	715.2	655.0	587.3	532.0	491.5	458.3	434.1	412.4	380.9	351.7
52.5°	674.0	664.6	613.6	548.9	495.5	455.8	427.5	405.8	383.7	357.6	330.3
55°	584.3	589.3	546.0	490.1	439.9	406.4	380.6	362.5	343.7	321.6	300.5
57.5°	492.4	510.8	481.8	432.7	385.6	354.6	335.2	319.9	304.3	285.9	267.9
60°	437.5	452.9	436.5	393.3	352.1	323.3	305.2	293.4	277.7	261.0	247.2
62.5°	383.9	400.4	390.6	355.8	317.5	292.7	276.8	265.9	254.2	239.5	225.2
65°	316.6	327.3	322.6	298.5	271.4	250.2	235.5	227.5	216.7	206.0	193.3
67.5°	242.5	263.2	260.5	247.6	224.2	207.7	198.0	191.0	181.2	173.2	164.5
70°	199.3	218.4	218.1	207.7	194.9	179.5	172.9	166.9	158.1	150.4	143.4
72.5°	163.2	180.6	183.2	175.3	166.6	154.9	148.4	144.3	135.9	130.6	124.8
75°	114.3	127.0	130.4	130.4	126.3	120.3	114.6	111.9	105.8	101.2	97.8
77.5°	74.9	82.9	88.2	89.4	90.0	88.0	83.3	81.4	76.8	75.1	71.9
80°	53.0	58.3	64.3	66.3	68.0	67.3	65.3	64.0	59.7	57.9	56.7
82.5°	36.6	39.5	44.5	48.9	48.5	50.2	48.5	47.4	44.1	43.5	42.1
85°	19.1	19.5	20.1	23.1	24.8	25.5	25.8	25.1	24.1	24.1	21.8
87.5°	9.0	8.4	8.7	8.4	8.4	9.1	9.6	9.6	9.0	8.5	8.1
90°	12.4	11.2	10.0	8.6	7.0	5.3	3.7	2.0	3.7	5.3	7.0
92.5°	25.0	24.1	23.3	22.0	20.1	18.2	16.3	14.4	16.3	18.2	20.1
95°	49.1	48.0	47.0	45.8	44.4	43.0	41.8	40.4	41.8	43.0	44.4
97.5°	78.4	77.2	76.0	74.8	73.8	72.7	71.6	70.5	71.6	72.7	73.8
100°	100.3	98.9	97.6	96.6	96.0	95.4	94.8	94.3	94.8	95.4	96.0
102.5°	123.1	121.9	120.7	119.9	119.8	119.5	119.2	119.0	119.2	119.5	119.8
105°	159.0	158.4	157.8	157.5	157.3	157.1	157.0	156.9	157.0	157.1	157.3
107.5°	197.6	197.5	197.4	197.3	197.1	196.9	196.7	196.6	196.7	196.9	197.1
110°	224.5	224.6	224.7	224.6	224.4	224.0	223.8	223.5	223.8	224.0	224.4



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	251.1	251.3	251.6	251.8	251.7	251.6	251.5	251.5	251.5	251.6	251.7
115°	292.7	293.0	293.3	293.5	293.5	293.5	293.5	293.5	293.5	293.5	293.5
117.5°	333.0	333.3	333.5	333.6	333.4	333.3	333.2	333.0	333.2	333.3	333.4
120°	361.0	361.4	361.9	361.9	361.3	360.7	360.1	359.5	360.1	360.7	361.3
122.5°	387.4	387.7	387.9	387.9	387.6	387.4	387.1	386.9	387.1	387.4	387.6
125°	427.1	427.2	427.3	427.4	427.4	427.4	427.4	427.4	427.4	427.4	427.4
127.5°	465.6	465.8	466.1	466.0	465.5	465.1	464.6	464.2	464.6	465.1	465.5
130°	492.1	492.1	492.1	491.8	491.4	490.9	490.5	490.0	490.5	490.9	491.4
132.5°	517.6	517.7	517.8	517.7	517.4	517.1	516.8	516.4	516.8	517.1	517.4
135°	555.3	555.3	555.3	554.9	554.0	553.1	552.2	551.3	552.2	553.1	554.0
137.5°	591.8	591.5	591.2	590.9	590.5	590.0	589.7	589.3	589.7	590.0	590.5
140°	615.9	615.9	615.9	615.8	615.4	615.2	614.8	614.6	614.8	615.2	615.4
142.5°	638.8	638.9	639.0	638.9	638.6	638.3	638.0	637.7	638.0	638.3	638.6
145°	672.8	672.7	672.5	672.2	671.6	671.0	670.4	669.8	670.4	671.0	671.6
147.5°	704.5	704.6	704.7	704.4	703.7	702.9	702.2	701.5	702.2	702.9	703.7
150°	723.6	723.6	723.6	723.3	722.7	722.1	721.5	720.9	721.5	722.1	722.7
152.5°	741.1	741.0	740.9	740.6	740.3	739.9	739.6	739.3	739.6	739.9	740.3
155°	767.0	767.2	767.2	767.3	767.3	767.3	767.3	767.3	767.3	767.3	767.3
157.5°	789.8	789.8	789.8	790.0	790.2	790.5	790.7	791.1	790.7	790.5	790.2
160°	804.0	804.2	804.3	804.4	804.6	804.8	804.9	805.0	804.9	804.8	804.6
162.5°	815.9	816.0	816.1	816.4	816.8	817.2	817.6	817.9	817.6	817.2	816.8
165°	832.6	832.8	833.2	833.5	834.0	834.5	834.9	835.3	834.9	834.5	834.0
167.5°	845.9	845.8	845.8	846.2	846.8	847.4	848.0	848.7	848.0	847.4	846.8
170°	853.3	853.1	852.9	853.3	853.9	854.7	855.5	856.2	855.5	854.7	853.9
172.5°	858.8	858.8	858.8	859.1	859.7	860.3	861.0	861.6	861.0	860.3	859.7
175°	865.2	865.4	865.6	866.0	866.8	867.5	868.2	869.0	868.2	867.5	866.8
177.5°	868.7	868.7	868.7	869.0	869.6	870.2	870.8	871.4	870.8	870.2	869.6
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	816.5	813.8	810.3	806.2	801.4	797.2	795.3	796.9	797.7	795.6	795.3
5°	791.6	783.3	776.5	766.5	758.5	751.7	747.0	745.0	745.7	740.4	739.0
7.5°	763.6	753.7	742.8	730.8	719.7	709.9	704.7	701.9	696.2	693.8	689.7
10°	745.7	732.3	721.6	707.5	694.8	683.0	677.3	672.7	667.0	664.3	658.6
12.5°	727.2	711.7	699.9	685.3	672.3	658.1	652.7	644.0	635.1	629.5	622.2
15°	701.1	682.4	668.0	650.6	635.2	619.1	604.7	588.6	582.6	569.8	562.5
17.5°	670.6	651.6	633.8	610.4	586.7	566.7	551.3	536.0	526.7	518.6	514.8
20°	650.6	633.2	608.4	581.3	554.7	532.6	520.2	510.2	500.2	494.5	490.4
22.5°	631.5	609.3	580.5	551.2	524.8	507.5	497.0	486.6	478.5	473.0	467.7
25°	599.7	570.5	540.0	506.5	488.4	473.4	461.9	453.6	448.6	441.5	438.9
27.5°	566.9	531.6	497.9	475.4	456.6	442.8	432.9	426.6	420.3	415.7	412.2
30°	541.7	505.8	475.7	454.3	435.1	423.8	415.7	408.4	403.4	399.7	397.0
32.5°	516.8	481.0	455.6	432.6	417.5	406.4	397.8	392.3	388.3	383.6	381.9
35°	480.7	448.9	426.8	406.0	390.6	380.6	373.8	368.2	364.8	363.5	362.5
37.5°	446.1	420.0	396.2	379.2	365.5	357.6	349.7	346.9	344.6	342.2	343.3
40°	424.1	399.7	378.6	360.5	349.4	340.7	336.0	332.7	330.6	330.6	330.6
42.5°	405.1	381.2	360.6	344.4	333.3	326.0	320.7	317.9	317.3	316.9	318.6
45°	375.6	353.4	332.7	319.3	309.9	302.5	299.5	297.1	297.1	298.5	298.9
47.5°	346.3	325.5	308.8	293.9	285.2	280.7	278.0	276.8	277.0	278.3	279.8
50°	328.3	307.9	291.4	278.0	270.0	265.6	263.3	262.6	263.3	263.3	265.6
52.5°	308.8	290.4	274.3	263.0	253.9	249.9	248.6	247.6	248.1	249.1	250.1
55°	280.1	263.6	248.2	237.5	230.8	228.2	225.2	225.5	224.8	225.5	225.5
57.5°	251.3	236.6	222.2	213.7	207.8	204.0	200.7	201.6	200.6	200.4	199.9
60°	232.8	216.7	205.3	197.7	191.0	187.6	184.6	185.3	184.3	183.6	182.3
62.5°	212.8	199.3	188.5	181.1	175.6	171.8	168.8	168.1	165.7	163.5	160.5
65°	183.6	172.5	162.8	155.8	150.8	147.7	145.4	143.4	138.4	133.0	130.4
67.5°	155.2	147.2	138.2	132.2	128.2	124.2	119.8	116.3	111.6	108.7	107.0
70°	137.0	129.3	121.6	115.9	111.6	107.9	102.8	100.5	97.1	95.8	94.1
72.5°	119.6	112.4	105.2	100.1	95.5	92.6	88.7	86.3	84.8	84.3	82.6
75°	93.2	87.5	82.1	77.4	73.7	71.7	70.0	68.4	67.7	64.7	62.9
77.5°	67.9	64.1	60.9	57.5	54.8	53.6	50.3	48.4	47.3	45.8	45.5
80°	53.0	50.3	46.9	44.9	41.2	39.9	38.5	38.2	37.9	37.5	37.2
82.5°	39.8	37.1	33.8	32.5	31.6	30.7	30.0	29.6	29.3	29.4	29.4
85°	20.1	18.8	18.8	18.4	18.1	17.7	17.4	17.4	17.0	17.4	17.0
87.5°	8.4	8.4	8.7	8.4	8.9	9.1	9.0	9.2	9.6	9.3	9.4
90°	8.6	10.0	11.2	12.4	13.6	14.8	15.7	16.6	17.5	18.4	19.0
92.5°	22.0	23.3	24.1	25.0	25.8	26.7	27.2	27.7	28.2	28.8	29.2
95°	45.8	47.0	48.0	49.1	50.1	51.1	51.6	52.1	52.5	53.0	53.2
97.5°	74.8	76.0	77.2	78.4	79.6	80.9	81.5	82.0	82.5	83.1	83.3
100°	96.6	97.6	98.9	100.3	101.6	103.0	103.3	103.6	103.9	104.2	104.4
102.5°	119.9	120.7	121.9	123.1	124.4	125.6	126.1	126.5	126.8	127.3	127.5
105°	157.5	157.8	158.4	159.0	159.6	160.2	160.7	161.1	161.5	162.0	162.5
107.5°	197.3	197.4	197.5	197.6	197.7	197.8	198.2	198.6	199.0	199.4	199.7
110°	224.6	224.7	224.6	224.5	224.3	224.1	223.9	223.5	223.3	222.9	223.0



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	251.8	251.6	251.3	251.1	250.8	250.6	250.5	250.4	250.4	250.3	250.3
115°	293.5	293.3	293.0	292.7	292.4	292.1	292.0	291.8	291.7	291.5	291.4
117.5°	333.6	333.5	333.3	333.0	332.9	332.7	332.2	331.7	331.1	330.6	330.2
120°	361.9	361.9	361.4	361.0	360.6	360.2	359.4	358.6	357.8	357.1	356.9
122.5°	387.9	387.9	387.7	387.4	387.3	387.0	386.5	386.0	385.6	385.0	384.5
125°	427.4	427.3	427.2	427.1	426.9	426.8	426.5	426.2	425.9	425.6	425.2
127.5°	466.0	466.1	465.8	465.6	465.4	465.1	464.9	464.5	464.3	463.9	463.6
130°	491.8	492.1	492.1	492.1	492.1	492.1	491.7	491.5	491.1	490.9	490.4
132.5°	517.7	517.8	517.7	517.6	517.5	517.4	517.0	516.8	516.4	516.2	515.9
135°	554.9	555.3	555.3	555.3	555.3	555.3	555.0	554.7	554.4	554.1	553.7
137.5°	590.9	591.2	591.5	591.8	591.9	592.2	591.9	591.4	591.1	590.6	590.5
140°	615.8	615.9	615.9	615.9	615.9	615.9	615.8	615.6	615.4	615.3	615.2
142.5°	638.9	639.0	638.9	638.8	638.6	638.5	638.5	638.4	638.4	638.4	638.3
145°	672.2	672.5	672.7	672.8	673.0	673.1	673.0	672.8	672.7	672.5	672.2
147.5°	704.4	704.7	704.6	704.5	704.3	704.2	704.1	704.0	703.9	703.7	703.6
150°	723.3	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.5
152.5°	740.6	740.9	741.0	741.1	741.2	741.4	741.8	742.1	742.4	742.8	742.8
155°	767.3	767.2	767.2	767.0	766.8	766.7	767.2	767.8	768.4	769.0	769.0
157.5°	790.0	789.8	789.8	789.8	789.7	789.7	790.1	790.6	791.1	791.5	791.4
160°	804.4	804.3	804.2	804.0	803.8	803.7	804.2	804.6	805.0	805.5	805.4
162.5°	816.4	816.1	816.0	815.9	815.7	815.5	816.4	817.2	817.9	818.8	818.8
165°	833.5	833.2	832.8	832.6	832.2	832.0	832.8	833.8	834.7	835.6	835.7
167.5°	846.2	845.8	845.8	845.9	845.9	845.9	846.9	847.7	848.7	849.5	849.5
170°	853.3	852.9	853.1	853.3	853.3	853.5	854.4	855.3	856.2	857.1	857.0
172.5°	859.1	858.8	858.8	858.8	858.8	858.9	859.9	860.9	861.9	863.0	863.0
175°	866.0	865.6	865.4	865.2	865.1	865.0	866.0	867.0	868.1	869.2	869.2
177.5°	869.0	868.7	868.7	868.7	868.7	868.7	869.5	870.4	871.2	872.1	872.0
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	793.7	794.2	792.4	791.8	792.4	794.2	793.7	795.3	795.6	797.7	796.9
5°	736.3	735.6	734.0	734.3	734.0	735.6	736.3	739.0	740.4	745.7	745.0
7.5°	687.3	684.7	685.4	682.7	685.4	684.7	687.3	689.7	693.8	696.2	701.9
10°	657.3	653.6	650.6	647.9	650.6	653.6	657.3	658.6	664.3	667.0	672.7
12.5°	616.3	613.1	609.0	609.8	609.0	613.1	616.3	622.2	629.5	635.1	644.0
15°	558.1	553.1	545.0	546.0	545.0	553.1	558.1	562.5	569.8	582.6	588.6
17.5°	508.9	508.9	505.2	506.1	505.2	508.9	508.9	514.8	518.6	526.7	536.0
20°	483.4	481.0	481.4	480.4	481.4	481.0	483.4	490.4	494.5	500.2	510.2
22.5°	465.7	462.9	460.5	458.4	460.5	462.9	465.7	467.7	473.0	478.5	486.6
25°	435.8	433.9	430.8	430.2	430.8	433.9	435.8	438.9	441.5	448.6	453.6
27.5°	409.6	409.1	407.9	406.4	407.9	409.1	409.6	412.2	415.7	420.3	426.6
30°	394.3	393.6	393.0	391.9	393.0	393.6	394.3	397.0	399.7	403.4	408.4
32.5°	380.6	380.2	379.5	379.6	379.5	380.2	380.6	381.9	383.6	388.3	392.3
35°	361.1	360.8	360.2	359.8	360.2	360.8	361.1	362.5	363.5	364.8	368.2
37.5°	342.9	343.8	343.4	343.3	343.4	343.8	342.9	343.3	342.2	344.6	346.9
40°	330.3	330.6	331.3	331.0	331.3	330.6	330.3	330.6	330.6	330.6	332.7
42.5°	319.9	319.9	320.9	319.7	320.9	319.9	319.9	318.6	316.9	317.3	317.9
45°	301.2	303.2	302.8	302.8	302.8	303.2	301.2	298.9	298.5	297.1	297.1
47.5°	280.7	282.5	282.9	282.8	282.9	282.5	280.7	279.8	278.3	277.0	276.8
50°	267.3	266.7	267.7	267.3	267.7	266.7	267.3	265.6	263.3	263.3	262.6
52.5°	251.0	251.2	251.1	250.7	251.1	251.2	251.0	250.1	249.1	248.1	247.6
55°	225.8	226.1	225.5	225.8	225.5	226.1	225.8	225.5	225.5	224.8	225.5
57.5°	198.5	196.8	197.5	196.7	197.5	196.8	198.5	199.9	200.4	200.6	201.6
60°	178.9	176.2	175.6	174.2	175.6	176.2	178.9	182.3	183.6	184.3	185.3
62.5°	156.9	155.1	152.7	153.9	152.7	155.1	156.9	160.5	163.5	165.7	168.1
65°	127.6	126.3	125.3	126.7	125.3	126.3	127.6	130.4	133.0	138.4	143.4
67.5°	105.6	105.0	105.0	104.3	105.0	105.0	105.6	107.0	108.7	111.6	116.3
70°	94.1	93.2	93.2	92.5	93.2	93.2	94.1	94.1	95.8	97.1	100.5
72.5°	82.3	81.4	81.6	81.2	81.6	81.4	82.3	82.6	84.3	84.8	86.3
75°	61.0	59.3	59.3	59.7	59.3	59.3	61.0	62.9	64.7	67.7	68.4
77.5°	45.5	45.1	45.6	45.0	45.6	45.1	45.5	45.5	45.8	47.3	48.4
80°	37.2	36.9	36.5	37.5	36.5	36.9	37.2	37.2	37.5	37.9	38.2
82.5°	28.8	28.8	28.8	30.0	28.8	28.8	28.8	29.4	29.4	29.3	29.6
85°	17.4	16.8	17.4	16.8	17.4	16.8	17.4	17.0	17.4	17.0	17.4
87.5°	10.0	9.8	9.6	9.9	9.6	9.8	10.0	9.4	9.3	9.6	9.2
90°	19.3	19.6	19.9	20.2	19.9	19.6	19.3	19.0	18.4	17.5	16.6
92.5°	29.4	29.5	29.7	29.9	29.7	29.5	29.4	29.2	28.8	28.2	27.7
95°	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.0	52.5	52.1
97.5°	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.3	83.1	82.5	82.0
100°	104.4	104.4	104.4	104.4	104.4	104.4	104.4	104.4	104.2	103.9	103.6
102.5°	127.7	127.8	127.9	128.0	127.9	127.8	127.7	127.5	127.3	126.8	126.5
105°	162.9	163.3	163.8	164.3	163.8	163.3	162.9	162.5	162.0	161.5	161.1
107.5°	199.6	199.6	199.6	199.5	199.6	199.6	199.6	199.7	199.4	199.0	198.6
110°	223.5	223.9	224.4	224.8	224.4	223.9	223.5	223.0	222.9	223.3	223.5



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	250.4	250.5	250.6	250.6	250.6	250.5	250.4	250.3	250.3	250.4	250.4
115°	291.3	291.1	290.9	290.8	290.9	291.1	291.3	291.4	291.5	291.7	291.8
117.5°	329.9	329.6	329.3	329.0	329.3	329.6	329.9	330.2	330.6	331.1	331.7
120°	357.2	357.5	357.8	358.1	357.8	357.5	357.2	356.9	357.1	357.8	358.6
122.5°	383.9	383.4	382.9	382.4	382.9	383.4	383.9	384.5	385.0	385.6	386.0
125°	425.0	424.6	424.4	424.0	424.4	424.6	425.0	425.2	425.6	425.9	426.2
127.5°	463.4	463.2	463.0	462.7	463.0	463.2	463.4	463.6	463.9	464.3	464.5
130°	489.8	489.2	488.6	488.0	488.6	489.2	489.8	490.4	490.9	491.1	491.5
132.5°	515.7	515.4	515.1	515.0	515.1	515.4	515.7	515.9	516.2	516.4	516.8
135°	553.3	552.8	552.4	552.0	552.4	552.8	553.3	553.7	554.1	554.4	554.7
137.5°	590.6	590.6	590.7	590.9	590.7	590.6	590.6	590.5	590.6	591.1	591.4
140°	615.0	614.8	614.7	614.6	614.7	614.8	615.0	615.2	615.3	615.4	615.6
142.5°	638.3	638.3	638.3	638.3	638.3	638.3	638.3	638.3	638.4	638.4	638.4
145°	671.8	671.3	670.9	670.5	670.9	671.3	671.8	672.2	672.5	672.7	672.8
147.5°	703.4	703.3	703.2	703.0	703.2	703.3	703.4	703.6	703.7	703.9	704.0
150°	723.4	723.2	723.1	722.9	723.1	723.2	723.4	723.5	723.6	723.6	723.6
152.5°	742.4	742.0	741.7	741.2	741.7	742.0	742.4	742.8	742.8	742.4	742.1
155°	768.4	767.8	767.2	766.7	767.2	767.8	768.4	769.0	769.0	768.4	767.8
157.5°	791.0	790.5	790.0	789.5	790.0	790.5	791.0	791.4	791.5	791.1	790.6
160°	804.6	803.8	803.1	802.4	803.1	803.8	804.6	805.4	805.5	805.0	804.6
162.5°	818.0	817.3	816.6	815.8	816.6	817.3	818.0	818.8	818.8	817.9	817.2
165°	835.1	834.5	833.9	833.4	833.9	834.5	835.1	835.7	835.6	834.7	833.8
167.5°	848.6	847.7	846.8	845.8	846.8	847.7	848.6	849.5	849.5	848.7	847.7
170°	856.0	855.0	853.9	852.8	853.9	855.0	856.0	857.0	857.1	856.2	855.3
172.5°	861.9	860.8	859.8	858.8	859.8	860.8	861.9	863.0	863.0	861.9	860.9
175°	868.1	867.0	866.0	865.0	866.0	867.0	868.1	869.2	869.2	868.1	867.0
177.5°	871.1	870.1	869.2	868.1	869.2	870.1	871.1	872.0	872.1	871.2	870.4
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	795.3	797.2	801.4	806.2	810.3	813.8	816.5	820.2	823.7	828.5	833.1
5°	747.0	751.7	758.5	766.5	776.5	783.3	791.6	799.0	809.7	820.4	830.8
7.5°	704.7	709.9	719.7	730.8	742.8	753.7	763.6	776.6	790.8	806.5	823.9
10°	677.3	683.0	694.8	707.5	721.6	732.3	745.7	761.1	777.2	796.3	817.7
12.5°	652.7	658.1	672.3	685.3	699.9	711.7	727.2	742.9	764.3	785.1	809.4
15°	604.7	619.1	635.2	650.6	668.0	682.4	701.1	717.2	737.7	766.8	794.6
17.5°	551.3	566.7	586.7	610.4	633.8	651.6	670.6	690.6	715.0	744.7	776.8
20°	520.2	532.6	554.7	581.3	608.4	633.2	650.6	672.7	697.8	730.0	763.1
22.5°	497.0	507.5	524.8	551.2	580.5	609.3	631.5	653.4	681.2	713.3	749.5
25°	461.9	473.4	488.4	506.5	540.0	570.5	599.7	624.7	654.3	686.4	726.6
27.5°	432.9	442.8	456.6	475.4	497.9	531.6	566.9	595.6	625.8	660.3	700.5
30°	415.7	423.8	435.1	454.3	475.7	505.8	541.7	575.2	605.7	641.5	683.4
32.5°	397.8	406.4	417.5	432.6	455.6	481.0	516.8	553.5	585.8	622.5	663.6
35°	373.8	380.6	390.6	406.0	426.8	448.9	480.7	518.6	552.8	591.9	631.1
37.5°	349.7	357.6	365.5	379.2	396.2	420.0	446.1	484.7	522.6	558.4	596.7
40°	336.0	340.7	349.4	360.5	378.6	399.7	424.1	461.9	499.8	535.4	573.9
42.5°	320.7	326.0	333.3	344.4	360.6	381.2	405.1	437.8	477.3	511.8	546.8
45°	299.5	302.5	309.9	319.3	332.7	353.4	375.6	404.7	441.9	474.7	505.5
47.5°	278.0	280.7	285.2	293.9	308.8	325.5	346.3	372.4	405.0	437.8	463.9
50°	263.3	265.6	270.0	278.0	291.4	307.9	328.3	351.7	380.9	412.4	434.1
52.5°	248.6	249.9	253.9	263.0	274.3	290.4	308.8	330.3	357.6	383.7	405.8
55°	225.2	228.2	230.8	237.5	248.2	263.6	280.1	300.5	321.6	343.7	362.5
57.5°	200.7	204.0	207.8	213.7	222.2	236.6	251.3	267.9	285.9	304.3	319.9
60°	184.6	187.6	191.0	197.7	205.3	216.7	232.8	247.2	261.0	277.7	293.4
62.5°	168.8	171.8	175.6	181.1	188.5	199.3	212.8	225.2	239.5	254.2	265.9
65°	145.4	147.7	150.8	155.8	162.8	172.5	183.6	193.3	206.0	216.7	227.5
67.5°	119.8	124.2	128.2	132.2	138.2	147.2	155.2	164.5	173.2	181.2	191.0
70°	102.8	107.9	111.6	115.9	121.6	129.3	137.0	143.4	150.4	158.1	166.9
72.5°	88.7	92.6	95.5	100.1	105.2	112.4	119.6	124.8	130.6	135.9	144.3
75°	70.0	71.7	73.7	77.4	82.1	87.5	93.2	97.8	101.2	105.8	111.9
77.5°	50.3	53.6	54.8	57.5	60.9	64.1	67.9	71.9	75.1	76.8	81.4
80°	38.5	39.9	41.2	44.9	46.9	50.3	53.0	56.7	57.9	59.7	64.0
82.5°	30.0	30.7	31.6	32.5	33.8	37.1	39.8	42.1	43.5	44.1	47.4
85°	17.4	17.7	18.1	18.4	18.8	18.8	20.1	21.8	24.1	24.1	25.1
87.5°	9.0	9.1	8.9	8.4	8.7	8.4	8.4	8.1	8.5	9.0	9.6
90°	15.7	14.8	13.6	12.4	11.2	10.0	8.6	7.0	5.3	3.7	2.0
92.5°	27.2	26.7	25.8	25.0	24.1	23.3	22.0	20.1	18.2	16.3	14.4
95°	51.6	51.1	50.1	49.1	48.0	47.0	45.8	44.4	43.0	41.8	40.4
97.5°	81.5	80.9	79.6	78.4	77.2	76.0	74.8	73.8	72.7	71.6	70.5
100°	103.3	103.0	101.6	100.3	98.9	97.6	96.6	96.0	95.4	94.8	94.3
102.5°	126.1	125.6	124.4	123.1	121.9	120.7	119.9	119.8	119.5	119.2	119.0
105°	160.7	160.2	159.6	159.0	158.4	157.8	157.5	157.3	157.1	157.0	156.9
107.5°	198.2	197.8	197.7	197.6	197.5	197.4	197.3	197.1	196.9	196.7	196.6
110°	223.9	224.1	224.3	224.5	224.6	224.7	224.6	224.4	224.0	223.8	223.5



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	250.5	250.6	250.8	251.1	251.3	251.6	251.8	251.7	251.6	251.5	251.5
115°	292.0	292.1	292.4	292.7	293.0	293.3	293.5	293.5	293.5	293.5	293.5
117.5°	332.2	332.7	332.9	333.0	333.3	333.5	333.6	333.4	333.3	333.2	333.0
120°	359.4	360.2	360.6	361.0	361.4	361.9	361.9	361.3	360.7	360.1	359.5
122.5°	386.5	387.0	387.3	387.4	387.7	387.9	387.9	387.6	387.4	387.1	386.9
125°	426.5	426.8	426.9	427.1	427.2	427.3	427.4	427.4	427.4	427.4	427.4
127.5°	464.9	465.1	465.4	465.6	465.8	466.1	466.0	465.5	465.1	464.6	464.2
130°	491.7	492.1	492.1	492.1	492.1	492.1	491.8	491.4	490.9	490.5	490.0
132.5°	517.0	517.4	517.5	517.6	517.7	517.8	517.7	517.4	517.1	516.8	516.4
135°	555.0	555.3	555.3	555.3	555.3	555.3	554.9	554.0	553.1	552.2	551.3
137.5°	591.9	592.2	591.9	591.8	591.5	591.2	590.9	590.5	590.0	589.7	589.3
140°	615.8	615.9	615.9	615.9	615.9	615.9	615.8	615.4	615.2	614.8	614.6
142.5°	638.5	638.5	638.6	638.8	638.9	639.0	638.9	638.6	638.3	638.0	637.7
145°	673.0	673.1	673.0	672.8	672.7	672.5	672.2	671.6	671.0	670.4	669.8
147.5°	704.1	704.2	704.3	704.5	704.6	704.7	704.4	703.7	702.9	702.2	701.5
150°	723.6	723.6	723.6	723.6	723.6	723.6	723.3	722.7	722.1	721.5	720.9
152.5°	741.8	741.4	741.2	741.1	741.0	740.9	740.6	740.3	739.9	739.6	739.3
155°	767.2	766.7	766.8	767.0	767.2	767.2	767.3	767.3	767.3	767.3	767.3
157.5°	790.1	789.7	789.7	789.8	789.8	789.8	790.0	790.2	790.5	790.7	791.1
160°	804.2	803.7	803.8	804.0	804.2	804.3	804.4	804.6	804.8	804.9	805.0
162.5°	816.4	815.5	815.7	815.9	816.0	816.1	816.4	816.8	817.2	817.6	817.9
165°	832.8	832.0	832.2	832.6	832.8	833.2	833.5	834.0	834.5	834.9	835.3
167.5°	846.9	845.9	845.9	845.9	845.8	845.8	846.2	846.8	847.4	848.0	848.7
170°	854.4	853.5	853.3	853.3	853.1	852.9	853.3	853.9	854.7	855.5	856.2
172.5°	859.9	858.9	858.8	858.8	858.8	858.8	859.1	859.7	860.3	861.0	861.6
175°	866.0	865.0	865.1	865.2	865.4	865.6	866.0	866.8	867.5	868.2	869.0
177.5°	869.5	868.7	868.7	868.7	868.7	868.7	869.0	869.6	870.2	870.8	871.4
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	836.5	839.0	841.6	846.7	851.0	852.9	856.7	859.4	858.5	862.3	868.7
5°	839.8	848.9	859.3	870.0	882.0	892.1	900.2	908.2	914.6	922.2	933.7
7.5°	839.3	855.4	872.9	892.1	911.9	928.9	944.8	960.9	975.1	990.8	1011.2
10°	837.2	858.6	880.4	905.5	930.7	954.4	975.9	995.9	1015.0	1035.4	1061.3
12.5°	834.7	859.4	885.7	915.9	947.3	975.9	1001.1	1030.0	1053.9	1080.2	1110.1
15°	824.1	857.3	893.1	932.3	969.8	1008.3	1042.8	1078.4	1111.6	1143.0	1180.5
17.5°	811.9	850.2	892.4	938.7	983.9	1030.6	1071.6	1116.4	1150.2	1192.5	1227.4
20°	802.0	843.2	888.4	940.3	991.6	1043.5	1088.7	1134.3	1172.5	1215.0	1259.3
22.5°	790.0	835.2	884.2	937.9	991.6	1048.4	1098.4	1143.7	1191.0	1238.9	1284.4
25°	770.5	817.4	869.4	928.2	989.9	1047.8	1101.5	1157.8	1208.7	1260.6	1301.5
27.5°	746.7	795.9	850.7	911.5	974.7	1034.1	1097.2	1157.2	1208.4	1258.4	1294.0
30°	727.6	779.5	832.2	893.8	959.4	1023.1	1090.7	1150.7	1204.6	1249.6	1269.6
32.5°	708.1	757.3	811.5	873.9	941.2	1009.7	1076.9	1138.2	1188.0	1215.0	1215.5
35°	674.0	720.2	776.5	837.8	906.8	981.2	1049.2	1109.5	1140.0	1142.4	1109.5
37.5°	636.9	679.3	732.5	793.8	869.4	943.4	1012.8	1053.0	1063.2	1029.2	968.5
40°	610.4	649.5	700.9	763.8	838.9	915.2	978.5	1008.0	997.3	942.0	874.3
42.5°	582.5	619.0	668.4	730.6	805.9	883.0	937.0	952.8	924.4	860.6	781.4
45°	537.0	570.5	619.4	682.1	754.4	826.8	867.6	859.6	812.4	736.7	647.9
47.5°	489.7	522.0	566.0	624.0	698.1	760.5	788.2	764.0	696.7	613.5	541.2
50°	458.3	491.5	532.0	587.3	655.0	715.2	733.0	696.1	621.4	541.4	475.0
52.5°	427.5	455.8	495.5	548.9	613.6	664.6	674.0	631.5	554.4	482.7	423.9
55°	380.6	406.4	439.9	490.1	546.0	589.3	584.3	529.6	459.6	398.3	352.1
57.5°	335.2	354.6	385.6	432.7	481.8	510.8	492.4	445.9	380.6	330.5	291.4
60°	305.2	323.3	352.1	393.3	436.5	452.9	437.5	386.9	335.4	289.5	256.6
62.5°	276.8	292.7	317.5	355.8	390.6	400.4	383.9	339.8	293.3	254.1	226.9
65°	235.5	250.2	271.4	298.5	322.6	327.3	316.6	271.4	236.2	203.4	184.6
67.5°	198.0	207.7	224.2	247.6	260.5	263.2	242.5	214.0	183.0	162.9	148.8
70°	172.9	179.5	194.9	207.7	218.1	218.4	199.3	176.5	152.7	136.4	126.0
72.5°	148.4	154.9	166.6	175.3	183.2	180.6	163.2	145.2	126.0	113.6	105.8
75°	114.6	120.3	126.3	130.4	130.4	127.0	114.3	100.8	89.8	82.4	80.1
77.5°	83.3	88.0	90.0	89.4	88.2	82.9	74.9	66.1	62.2	58.7	56.9
80°	65.3	67.3	68.0	66.3	64.3	58.3	53.0	49.2	45.5	44.3	43.6
82.5°	48.5	50.2	48.5	48.9	44.5	39.5	36.6	35.3	33.8	33.2	32.5
85°	25.8	25.5	24.8	23.1	20.1	19.5	19.1	18.8	18.1	18.4	17.7
87.5°	9.6	9.1	8.4	8.4	8.7	8.4	9.0	9.1	9.4	9.3	10.0
90°	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7	16.6
92.5°	16.3	18.2	20.1	22.0	23.3	24.1	25.0	25.8	26.7	27.2	27.7
95°	41.8	43.0	44.4	45.8	47.0	48.0	49.1	50.1	51.1	51.6	52.1
97.5°	71.6	72.7	73.8	74.8	76.0	77.2	78.4	79.6	80.9	81.5	82.0
100°	94.8	95.4	96.0	96.6	97.6	98.9	100.3	101.6	103.0	103.3	103.6
102.5°	119.2	119.5	119.8	119.9	120.7	121.9	123.1	124.4	125.6	126.1	126.5
105°	157.0	157.1	157.3	157.5	157.8	158.4	159.0	159.6	160.2	160.7	161.1
107.5°	196.7	196.9	197.1	197.3	197.4	197.5	197.6	197.7	197.8	198.2	198.6
110°	223.8	224.0	224.4	224.6	224.7	224.6	224.5	224.3	224.1	223.9	223.5



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	251.5	251.6	251.7	251.8	251.6	251.3	251.1	250.8	250.6	250.5	250.4
115°	293.5	293.5	293.5	293.5	293.3	293.0	292.7	292.4	292.1	292.0	291.8
117.5°	333.2	333.3	333.4	333.6	333.5	333.3	333.0	332.9	332.7	332.2	331.7
120°	360.1	360.7	361.3	361.9	361.9	361.4	361.0	360.6	360.2	359.4	358.6
122.5°	387.1	387.4	387.6	387.9	387.9	387.7	387.4	387.3	387.0	386.5	386.0
125°	427.4	427.4	427.4	427.4	427.3	427.2	427.1	426.9	426.8	426.5	426.2
127.5°	464.6	465.1	465.5	466.0	466.1	465.8	465.6	465.4	465.1	464.9	464.5
130°	490.5	490.9	491.4	491.8	492.1	492.1	492.1	492.1	492.1	491.7	491.5
132.5°	516.8	517.1	517.4	517.7	517.8	517.7	517.6	517.5	517.4	517.0	516.8
135°	552.2	553.1	554.0	554.9	555.3	555.3	555.3	555.3	555.3	555.0	554.7
137.5°	589.7	590.0	590.5	590.9	591.2	591.5	591.8	591.9	592.2	591.9	591.4
140°	614.8	615.2	615.4	615.8	615.9	615.9	615.9	615.9	615.9	615.8	615.6
142.5°	638.0	638.3	638.6	638.9	639.0	638.9	638.8	638.6	638.5	638.5	638.4
145°	670.4	671.0	671.6	672.2	672.5	672.7	672.8	673.0	673.1	673.0	672.8
147.5°	702.2	702.9	703.7	704.4	704.7	704.6	704.5	704.3	704.2	704.1	704.0
150°	721.5	722.1	722.7	723.3	723.6	723.6	723.6	723.6	723.6	723.6	723.6
152.5°	739.6	739.9	740.3	740.6	740.9	741.0	741.1	741.2	741.4	741.8	742.1
155°	767.3	767.3	767.3	767.3	767.2	767.2	767.0	766.8	766.7	767.2	767.8
157.5°	790.7	790.5	790.2	790.0	789.8	789.8	789.8	789.7	789.7	790.1	790.6
160°	804.9	804.8	804.6	804.4	804.3	804.2	804.0	803.8	803.7	804.2	804.6
162.5°	817.6	817.2	816.8	816.4	816.1	816.0	815.9	815.7	815.5	816.4	817.2
165°	834.9	834.5	834.0	833.5	833.2	832.8	832.6	832.2	832.0	832.8	833.8
167.5°	848.0	847.4	846.8	846.2	845.8	845.8	845.9	845.9	845.9	846.9	847.7
170°	855.5	854.7	853.9	853.3	852.9	853.1	853.3	853.3	853.5	854.4	855.3
172.5°	861.0	860.3	859.7	859.1	858.8	858.8	858.8	858.8	858.9	859.9	860.9
175°	868.2	867.5	866.8	866.0	865.6	865.4	865.2	865.1	865.0	866.0	867.0
177.5°	870.8	870.2	869.6	869.0	868.7	868.7	868.7	868.7	868.7	869.5	870.4
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	831.5	831.5	831.5	831.5	831.5	831.5	831.5
2.5°	872.2	873.3	874.1	876.8	877.0	879.4	877.0
5°	944.3	949.1	956.4	963.8	964.5	969.1	960.8
7.5°	1025.3	1036.1	1042.9	1054.8	1059.5	1062.5	1057.7
10°	1081.1	1091.1	1108.9	1117.6	1126.3	1127.6	1123.6
12.5°	1134.9	1150.8	1164.8	1181.4	1180.9	1192.7	1188.4
15°	1206.7	1223.1	1242.5	1260.9	1267.7	1267.7	1273.0
17.5°	1257.8	1288.0	1308.0	1322.5	1338.3	1341.1	1339.2
20°	1292.4	1324.9	1346.3	1365.1	1375.9	1378.9	1378.9
22.5°	1318.2	1345.8	1366.8	1383.6	1392.5	1396.0	1394.9
25°	1336.0	1359.8	1372.5	1377.5	1379.8	1379.1	1372.9
27.5°	1311.6	1310.5	1302.4	1287.0	1275.5	1268.4	1260.4
30°	1265.0	1247.5	1227.4	1205.3	1176.8	1155.0	1148.4
32.5°	1195.6	1156.4	1122.4	1085.5	1054.9	1033.1	1024.0
35°	1061.3	999.3	948.7	904.5	872.4	852.2	845.5
37.5°	902.0	842.0	779.4	736.5	709.8	689.5	681.9
40°	800.6	735.3	680.7	640.5	613.0	593.3	593.0
42.5°	708.2	645.8	594.4	565.5	535.9	522.8	522.7
45°	579.9	529.9	486.4	463.6	445.9	435.1	432.1
47.5°	480.1	438.9	409.8	391.7	377.2	370.4	365.9
50°	424.1	388.0	364.8	349.0	341.0	332.3	331.7
52.5°	377.5	348.3	330.3	317.5	307.3	302.0	302.2
55°	317.3	294.1	281.4	271.6	263.6	259.6	258.0
57.5°	267.3	249.9	240.6	231.8	228.3	225.2	224.3
60°	236.2	224.5	215.8	208.7	203.7	202.7	202.3
62.5°	210.4	198.2	192.2	186.8	183.0	181.5	180.9
65°	173.5	164.5	159.1	154.8	153.4	151.1	150.8
67.5°	139.9	134.5	131.0	127.9	126.1	126.0	126.0
70°	119.2	116.2	113.2	111.6	110.6	109.9	109.9
72.5°	101.6	99.4	96.9	96.0	95.8	95.1	94.9
75°	77.4	75.1	75.3	73.7	72.3	70.7	69.7
77.5°	54.8	53.2	52.9	52.7	51.5	51.3	51.8
80°	42.5	40.9	40.6	40.9	40.6	39.5	39.5
82.5°	32.4	31.0	30.7	30.4	30.0	30.4	29.9
85°	17.4	16.8	16.8	16.8	17.4	17.0	16.8
87.5°	9.6	9.6	10.0	9.7	9.8	9.6	9.9
90°	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	28.2	28.8	29.2	29.4	29.5	29.7	29.9
95°	52.5	53.0	53.2	53.2	53.2	53.2	53.2
97.5°	82.5	83.1	83.3	83.3	83.3	83.3	83.3
100°	103.9	104.2	104.4	104.4	104.4	104.4	104.4
102.5°	126.8	127.3	127.5	127.7	127.8	127.9	128.0
105°	161.5	162.0	162.5	162.9	163.3	163.8	164.3
107.5°	199.0	199.4	199.7	199.6	199.6	199.6	199.5
110°	223.3	222.9	223.0	223.5	223.9	224.4	224.8



TEST NUMBER: P332908-935

CATALOG NUMBER: S124RDIP-S575D810U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	250.4	250.3	250.3	250.4	250.5	250.6	250.6
115°	291.7	291.5	291.4	291.3	291.1	290.9	290.8
117.5°	331.1	330.6	330.2	329.9	329.6	329.3	329.0
120°	357.8	357.1	356.9	357.2	357.5	357.8	358.1
122.5°	385.6	385.0	384.5	383.9	383.4	382.9	382.4
125°	425.9	425.6	425.2	425.0	424.6	424.4	424.0
127.5°	464.3	463.9	463.6	463.4	463.2	463.0	462.7
130°	491.1	490.9	490.4	489.8	489.2	488.6	488.0
132.5°	516.4	516.2	515.9	515.7	515.4	515.1	515.0
135°	554.4	554.1	553.7	553.3	552.8	552.4	552.0
137.5°	591.1	590.6	590.5	590.6	590.6	590.7	590.9
140°	615.4	615.3	615.2	615.0	614.8	614.7	614.6
142.5°	638.4	638.4	638.3	638.3	638.3	638.3	638.3
145°	672.7	672.5	672.2	671.8	671.3	670.9	670.5
147.5°	703.9	703.7	703.6	703.4	703.3	703.2	703.0
150°	723.6	723.6	723.5	723.4	723.2	723.1	722.9
152.5°	742.4	742.8	742.8	742.4	742.0	741.7	741.2
155°	768.4	769.0	769.0	768.4	767.8	767.2	766.7
157.5°	791.1	791.5	791.4	791.0	790.5	790.0	789.5
160°	805.0	805.5	805.4	804.6	803.8	803.1	802.4
162.5°	817.9	818.8	818.8	818.0	817.3	816.6	815.8
165°	834.7	835.6	835.7	835.1	834.5	833.9	833.4
167.5°	848.7	849.5	849.5	848.6	847.7	846.8	845.8
170°	856.2	857.1	857.0	856.0	855.0	853.9	852.8
172.5°	861.9	863.0	863.0	861.9	860.8	859.8	858.8
175°	868.1	869.2	869.2	868.1	867.0	866.0	865.0
177.5°	871.2	872.1	872.0	871.1	870.1	869.2	868.1
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3

(END OF REPORT)