

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332492-840

Luminaire Tested: **S124DIP-S350D365U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332492-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D365U840-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2914.1 lumens  
Efficiency: N/A  
Efficacy: 143.6 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4657	4657	4657	4657
5°	5485	4669	4122	4669
10°	6567	4649	3710	4649
15°	7770	4603	3408	4603
20°	8652	4554	3137	4554
25°	8792	4483	2950	4483
30°	7481	4416	2892	4416
35°	5752	4306	2893	4306
40°	4484	4176	2947	4176
45°	3738	3981	2997	3981
50°	3291	3743	3097	3743
55°	3015	3458	3222	3458
60°	2824	3202	3371	3202
65°	2628	2917	3498	2917
70°	2403	2634	3576	2634
75°	2149	2318	3534	2318
80°	1799	1901	3422	1901
85°	1325	1371	3270	1371



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.2	1.9
10°-20°	173.3	5.9
20°-30°	274.7	9.4
30°-40°	305.7	10.5
40°-50°	278.3	9.6
50°-60°	227.4	7.8
60°-70°	162.4	5.6
70°-80°	89.4	3.1
80°-90°	25.4	0.9
90°-100°	131.2	4.5
100°-110°	273.1	9.4
110°-120°	244.6	8.4
120°-130°	205.8	7.1
130°-140°	171.6	5.9
140°-150°	131.1	4.5
150°-160°	92.1	3.2
160°-170°	54.2	1.9
170°-180°	17.6	0.6
0°-30°	504.2	17.3
0°-40°	809.9	27.8
0°-60°	1315.6	45.1
0°-90°	1592.8	54.7
90°-120°	648.9	22.3
90°-150°	1157.3	39.7
90°-180°	1321.0	45.3
0°-180°	2914.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	577	577	577	577	577	
5°	677	576	509	576	677	69
15°	930	551	408	551	930	263
25°	987	503	331	503	987	435
35°	584	437	294	437	584	370
45°	327	349	262	349	327	258
55°	214	246	229	246	214	193
65°	138	153	183	153	138	136
75°	69	74	113	74	69	73
85°	14	15	35	15	14	18
90°	8	0	8	0	8	7
95°	87	12	87	12	87	135
105°	502	42	502	42	502	496
115°	482	74	482	74	482	479
125°	385	102	385	102	385	350
135°	344	122	344	122	344	266
145°	281	140	281	140	281	178
155°	235	160	235	160	235	110
165°	205	174	205	174	205	59
175°	185	181	185	181	185	18
180°	182	182	182	182	182	



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	614.0	613.9	612.0	611.6	610.3	608.5	608.1	605.0	599.0	596.0	595.3
5°	676.8	681.7	675.4	674.2	673.5	665.6	661.6	656.8	645.8	639.3	634.3
7.5°	751.8	752.3	749.6	747.5	741.3	734.5	724.2	713.2	700.0	686.5	676.2
10°	801.1	803.0	799.9	799.5	787.3	779.6	764.4	751.4	736.6	720.1	705.1
12.5°	853.1	850.5	848.9	838.7	836.4	822.4	804.7	791.4	768.5	749.5	729.5
15°	929.7	924.4	921.1	907.1	900.1	880.7	861.8	847.3	817.4	788.9	767.4
17.5°	974.6	979.9	972.2	966.3	948.5	934.8	915.5	884.9	861.6	826.3	799.1
20°	1007.1	1007.6	1003.3	997.3	983.3	966.0	945.0	911.6	883.6	848.5	811.1
22.5°	1015.9	1016.0	1014.2	1008.7	997.9	984.0	962.8	934.8	901.0	862.8	825.5
25°	987.0	986.1	988.3	994.5	990.5	986.1	973.9	953.1	921.6	881.2	841.0
27.5°	879.8	886.5	898.6	913.8	928.6	939.8	942.9	938.7	919.2	886.0	843.8
30°	802.5	810.7	819.8	835.1	864.7	881.7	900.3	914.4	906.6	880.0	840.8
32.5°	717.7	719.7	733.2	750.5	777.7	810.3	839.9	868.6	878.1	864.1	831.4
35°	583.6	587.0	601.6	618.7	652.0	692.0	736.4	776.1	808.8	821.9	805.2
37.5°	476.3	485.8	496.1	514.6	543.9	579.9	626.0	677.4	726.2	758.9	764.5
40°	425.5	431.4	438.8	452.9	477.8	513.1	552.8	611.6	663.5	710.3	725.6
42.5°	385.3	388.8	393.3	406.1	425.0	460.2	496.4	548.2	600.2	656.2	681.9
45°	327.4	331.0	338.7	346.1	360.4	384.8	418.5	461.0	513.4	567.3	614.7
47.5°	285.7	287.9	292.5	300.4	312.7	328.7	356.1	391.6	440.1	492.6	543.0
50°	262.0	263.9	267.4	274.6	284.0	298.3	320.7	354.0	391.9	444.7	494.2
52.5°	243.2	244.0	246.6	251.5	258.9	270.9	289.4	316.9	352.2	399.3	448.6
55°	214.2	215.1	217.5	221.1	227.5	235.2	249.2	269.8	300.6	341.5	384.4
57.5°	190.3	191.0	192.9	194.3	199.7	205.8	216.7	231.4	254.7	289.4	327.6
60°	174.9	174.5	176.8	178.0	181.7	186.9	195.3	209.3	229.6	257.6	292.8
62.5°	160.1	159.4	161.4	163.0	165.0	169.5	176.3	187.3	203.9	229.1	259.5
65°	137.6	136.7	137.9	139.9	141.7	144.1	149.2	159.0	172.1	190.3	213.4
67.5°	115.2	116.2	116.4	117.3	118.5	121.7	125.1	132.1	141.4	155.9	175.5
70°	101.8	102.1	103.0	103.0	103.7	106.6	109.5	113.5	122.6	136.0	152.0
72.5°	88.5	89.5	89.1	89.8	90.4	92.3	94.3	98.3	105.9	115.9	129.5
75°	68.9	69.6	69.6	69.8	70.5	71.2	72.9	75.7	81.3	88.7	98.0
77.5°	50.2	50.3	50.6	51.5	51.5	52.6	53.8	56.1	58.9	63.9	69.7
80°	38.7	39.2	39.0	39.5	39.5	40.4	40.9	43.7	44.9	48.3	52.8
82.5°	28.4	28.9	28.8	29.5	29.9	30.1	30.7	31.9	33.1	36.1	37.9
85°	14.3	14.8	14.3	14.8	15.6	15.8	16.5	16.8	17.7	18.4	20.1
87.5°	5.7	6.3	6.4	6.5	6.8	7.0	7.1	6.9	7.5	7.8	8.4
90°	7.5	7.5	7.9	7.5	7.2	7.2	6.8	6.5	6.1	6.5	5.8
92.5°	27.5	27.5	28.7	30.6	34.8	42.0	52.7	70.1	94.3	113.2	99.1
95°	87.1	91.7	98.2	109.2	126.7	161.3	209.1	264.5	299.1	290.8	219.5
97.5°	232.8	240.2	251.0	272.4	298.0	335.3	370.2	390.7	375.8	306.4	205.4
100°	327.3	330.1	340.8	362.6	393.6	420.1	437.6	430.4	378.3	287.0	186.3
102.5°	409.5	411.8	423.1	438.9	457.9	468.9	463.8	428.5	356.9	262.7	173.5
105°	502.2	504.3	509.3	512.2	511.5	496.9	461.5	399.7	318.0	234.1	162.4
107.5°	536.5	535.6	532.1	523.9	506.3	474.4	424.7	359.0	286.6	218.1	160.4
110°	537.1	533.9	527.6	512.5	487.2	448.0	396.2	334.5	270.9	212.7	161.0



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	520.3	515.1	506.1	488.0	459.2	419.9	371.0	316.4	262.1	210.2	162.7
115°	482.2	479.4	467.9	446.5	418.3	384.1	342.2	298.4	253.8	208.8	165.9
117.5°	443.5	441.3	429.8	411.8	387.8	358.7	325.9	289.5	250.0	208.4	169.5
120°	421.9	418.0	408.7	392.9	372.6	347.3	318.7	285.5	248.0	208.4	172.1
122.5°	404.8	400.8	392.9	379.5	362.3	340.1	314.2	282.1	245.8	208.1	174.6
125°	384.8	382.6	375.9	365.5	351.2	331.5	306.9	276.3	242.0	207.7	178.4
127.5°	373.0	370.9	365.2	356.0	341.6	323.1	298.4	269.1	236.9	206.9	181.6
130°	366.2	364.1	358.3	349.4	334.8	315.9	291.6	263.4	233.8	206.6	183.8
132.5°	358.5	356.4	350.9	340.8	326.5	307.6	283.9	257.4	231.0	206.4	185.8
135°	344.1	341.9	336.2	326.2	311.9	294.1	272.4	249.1	226.6	205.9	188.8
137.5°	326.2	323.7	318.9	309.1	295.7	279.6	261.3	241.7	223.0	205.9	190.6
140°	313.4	310.5	305.5	297.7	285.2	270.1	254.1	237.3	221.0	205.6	192.0
142.5°	299.6	297.7	293.3	286.0	274.9	261.9	248.1	233.4	219.2	205.6	193.2
145°	280.8	279.1	275.5	269.4	260.5	250.5	239.8	227.7	216.3	204.9	193.8
147.5°	264.3	263.6	260.9	255.7	249.1	241.3	232.7	223.1	213.7	203.6	194.2
150°	254.8	254.5	252.4	247.7	242.0	235.6	228.4	220.3	211.7	202.7	194.2
152.5°	246.3	245.9	244.6	240.9	236.0	230.8	224.2	217.1	209.3	201.3	193.6
155°	235.2	235.2	234.1	231.3	227.7	223.4	218.0	212.4	205.9	199.1	192.8
157.5°	225.5	225.5	224.9	222.7	220.0	216.6	212.1	207.3	202.5	196.9	191.8
160°	219.5	219.5	219.1	217.0	214.9	212.0	208.0	204.2	199.9	195.2	191.0
162.5°	213.8	214.1	213.7	211.6	210.1	207.4	204.4	201.1	197.6	193.5	190.1
165°	205.2	205.6	205.9	204.5	203.1	201.3	198.8	196.6	193.8	191.0	188.4
167.5°	198.4	198.7	198.8	197.8	197.1	196.1	194.1	192.5	190.4	188.3	186.7
170°	194.2	194.2	194.5	194.2	193.5	192.4	191.0	189.9	188.1	186.6	185.6
172.5°	189.9	190.5	190.8	190.5	190.1	189.2	188.3	187.6	186.1	184.9	184.5
175°	184.9	185.6	186.3	185.6	185.6	185.6	184.9	184.5	183.8	183.1	183.1
177.5°	182.0	182.5	183.1	182.8	183.1	182.8	182.8	182.5	182.3	182.0	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	595.5	592.8	590.9	589.4	585.2	582.7	580.8	578.1	575.0	571.8	567.7
5°	629.2	621.2	615.2	606.1	597.5	590.4	582.9	576.2	568.2	559.3	552.8
7.5°	664.8	652.7	637.2	623.8	608.6	595.5	583.8	571.8	559.3	547.0	535.9
10°	687.4	671.9	654.6	634.3	615.2	598.2	582.5	567.1	552.3	537.6	524.8
12.5°	711.7	692.3	666.8	643.1	621.7	599.0	580.0	561.2	543.3	527.8	513.0
15°	744.3	716.3	686.9	655.1	626.9	600.4	574.3	550.7	530.6	510.0	495.6
17.5°	764.3	729.6	696.1	662.9	628.7	595.2	567.1	539.9	514.7	494.3	476.3
20°	777.5	743.1	701.3	668.0	627.4	593.0	560.5	530.1	503.8	482.1	463.4
22.5°	788.9	749.2	707.3	663.6	623.2	586.6	551.1	520.6	493.7	470.8	452.9
25°	795.2	749.5	704.1	660.6	614.7	571.5	539.2	503.3	474.6	450.5	431.4
27.5°	795.9	747.0	695.6	647.3	600.0	559.7	519.0	486.9	457.2	431.6	413.2
30°	793.8	742.9	687.6	635.3	587.7	544.0	508.6	473.7	443.3	418.0	398.9
32.5°	787.0	734.1	677.3	621.9	572.6	529.8	493.3	460.1	430.5	405.6	385.5
35°	767.7	715.3	654.9	597.2	546.8	503.6	470.6	436.9	407.3	383.6	364.3
37.5°	737.4	690.1	628.6	569.1	519.5	476.1	443.3	412.9	386.2	362.1	342.3
40°	711.0	669.4	607.7	549.7	496.1	454.8	424.2	396.3	369.7	347.0	328.1
42.5°	680.6	644.4	587.5	526.0	474.3	432.8	403.0	377.9	352.9	331.9	313.1
45°	626.4	602.5	549.0	492.1	438.3	399.1	370.7	348.7	327.7	307.1	291.3
47.5°	564.1	552.2	507.2	453.1	402.1	363.5	338.8	318.5	300.0	282.7	268.7
50°	522.2	516.4	477.6	425.5	376.7	340.3	315.5	298.0	282.3	267.0	253.8
52.5°	480.9	480.7	445.6	397.9	352.7	317.8	293.1	276.8	263.2	250.7	238.9
55°	417.8	424.4	397.0	354.5	314.1	282.5	260.2	245.7	236.1	225.9	217.0
57.5°	359.8	370.9	348.2	310.7	277.0	248.0	228.6	217.7	207.5	201.3	194.8
60°	321.9	332.4	314.8	283.3	251.5	226.6	208.1	198.3	189.6	185.2	180.7
62.5°	288.3	297.6	284.6	255.3	227.7	203.8	188.2	178.8	172.9	168.2	165.2
65°	240.2	248.1	236.8	215.6	191.9	172.8	160.2	152.7	147.0	145.1	141.7
67.5°	194.2	201.4	195.3	177.2	158.2	143.7	133.8	126.7	123.3	121.7	119.3
70°	166.8	174.0	167.5	151.8	137.1	125.0	115.6	111.6	108.1	107.3	104.0
72.5°	143.7	148.6	142.1	129.8	117.3	107.0	99.8	95.5	93.7	92.4	90.6
75°	107.8	112.1	107.8	98.3	89.4	82.2	76.0	74.3	72.2	71.5	70.3
77.5°	76.2	80.0	76.7	70.8	64.1	58.6	55.2	53.1	52.6	51.4	52.0
80°	58.3	60.7	57.6	53.5	48.3	44.4	42.1	40.9	39.5	39.0	39.9
82.5°	41.9	42.9	41.3	38.6	34.7	32.2	30.6	29.2	28.9	29.0	29.0
85°	21.7	21.5	21.3	18.9	17.7	16.1	15.0	14.8	14.5	15.0	15.6
87.5°	8.3	8.5	7.9	7.1	6.5	5.8	5.4	5.0	5.4	5.8	6.1
90°	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	72.1	44.4	26.3	18.9	13.6	9.3	6.0	4.0	6.0	9.3	13.6
95°	134.2	75.6	44.6	29.6	21.1	16.5	12.8	11.8	12.8	16.5	21.1
97.5°	120.7	72.3	48.4	35.9	28.5	24.2	21.1	21.1	21.1	24.2	28.5
100°	113.5	73.2	52.1	40.7	33.9	29.6	27.2	27.2	27.2	29.6	33.9
102.5°	111.5	76.0	57.0	46.2	39.6	35.6	33.4	32.8	33.4	35.6	39.6
105°	112.4	82.8	65.6	55.3	48.9	44.6	42.8	41.8	42.8	44.6	48.9
107.5°	117.8	90.7	75.0	64.8	58.7	54.1	52.3	51.6	52.3	54.1	58.7
110°	121.7	96.7	81.0	71.4	64.9	60.7	58.9	58.2	58.9	60.7	64.9





TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	126.0	102.4	87.3	77.7	71.2	67.3	65.1	64.4	65.1	67.3	71.2
115°	132.8	111.4	97.0	87.5	80.7	77.1	74.6	73.5	74.6	77.1	80.7
117.5°	139.7	120.0	106.4	96.4	90.1	86.1	83.9	82.9	83.9	86.1	90.1
120°	144.5	126.0	112.4	102.4	96.3	92.4	90.0	89.3	90.0	92.4	96.3
122.5°	149.2	131.7	118.2	108.5	101.8	98.2	95.6	94.9	95.6	98.2	101.8
125°	155.9	139.6	126.7	116.7	110.0	106.0	103.8	102.4	103.8	106.0	110.0
127.5°	161.9	146.8	134.4	124.3	117.2	112.8	110.2	109.1	110.2	112.8	117.2
130°	165.6	151.7	139.6	129.2	122.4	117.0	114.2	112.8	114.2	117.0	122.4
132.5°	169.4	155.7	143.5	133.8	126.4	121.4	117.6	116.5	117.6	121.4	126.4
135°	174.2	161.3	149.6	140.3	132.8	126.7	123.1	121.7	123.1	126.7	132.8
137.5°	177.6	165.6	154.6	145.7	137.9	132.2	128.3	126.9	128.3	132.2	137.9
140°	179.9	168.4	157.7	149.2	141.7	135.6	131.7	130.7	131.7	135.6	141.7
142.5°	181.6	171.1	160.6	152.3	145.1	139.4	135.7	134.6	135.7	139.4	145.1
145°	183.5	173.8	164.5	156.7	149.9	144.9	141.4	140.3	141.4	144.9	149.9
147.5°	185.1	176.6	167.9	160.9	155.2	150.2	146.9	146.6	146.9	150.2	155.2
150°	185.9	178.1	170.3	163.5	158.1	153.8	151.0	150.6	151.0	153.8	158.1
152.5°	186.5	179.3	172.3	166.0	161.3	157.2	154.4	154.3	154.4	157.2	161.3
155°	187.0	181.0	174.9	169.6	165.6	162.1	159.9	159.6	159.9	162.1	165.6
157.5°	187.0	182.2	177.0	172.8	169.4	166.6	164.6	164.6	164.6	166.6	169.4
160°	187.0	182.8	178.4	174.5	171.7	169.2	167.7	167.7	167.7	169.2	171.7
162.5°	187.0	183.3	179.4	176.2	173.7	171.5	170.4	170.6	170.4	171.5	173.7
165°	186.3	183.5	180.3	178.1	176.3	174.5	173.8	173.8	173.8	174.5	176.3
167.5°	185.4	183.4	181.1	179.4	178.3	177.0	176.6	177.0	176.6	177.0	178.3
170°	184.9	183.1	181.3	180.3	179.6	178.4	178.1	178.4	178.1	178.4	179.6
172.5°	184.3	182.8	181.6	180.8	180.4	179.6	179.6	179.9	179.6	179.6	180.4
175°	183.5	182.4	181.7	181.7	181.3	181.0	181.0	181.3	181.0	181.0	181.3
177.5°	182.5	182.0	181.7	181.7	181.7	181.4	181.7	182.0	181.7	181.4	181.7
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	565.8	564.1	561.7	558.3	555.3	552.3	551.5	550.4	552.7	550.8	550.2
5°	547.3	542.3	535.8	528.5	524.1	518.0	516.7	514.3	511.9	511.7	509.3
7.5°	527.7	520.3	511.8	504.3	497.4	490.5	486.0	485.1	481.6	479.5	477.2
10°	515.0	505.9	496.1	489.0	480.9	473.7	468.7	465.9	463.4	460.8	458.4
12.5°	500.2	490.5	482.4	474.6	465.0	459.6	451.3	446.4	445.9	445.9	439.7
15°	482.8	473.2	460.8	449.8	444.5	434.0	429.5	423.7	420.2	416.6	413.7
17.5°	462.9	451.0	441.3	428.7	418.7	410.3	404.3	400.9	395.5	390.4	386.8
20°	450.5	437.9	427.6	414.1	403.2	392.9	387.9	383.1	379.1	374.8	370.7
22.5°	437.9	424.6	412.1	399.1	388.9	378.0	373.1	366.7	362.8	360.4	356.4
25°	418.0	403.6	389.3	376.9	366.4	356.8	350.4	345.4	341.0	339.1	336.5
27.5°	396.4	382.1	368.3	354.2	342.2	335.3	330.1	326.4	323.9	321.3	320.1
30°	382.6	367.8	353.0	339.8	328.9	321.9	317.2	314.6	312.7	311.4	310.2
32.5°	368.7	354.1	338.5	326.5	316.6	310.4	306.8	304.2	303.3	302.9	302.4
35°	346.3	331.5	317.2	306.4	297.1	294.7	291.5	290.1	289.6	291.3	292.1
37.5°	324.7	310.9	297.7	287.3	281.1	277.7	276.6	276.7	278.4	279.8	281.6
40°	310.7	297.3	284.9	275.8	270.0	267.9	267.4	268.6	270.5	272.3	274.2
42.5°	297.1	284.0	272.7	264.2	260.1	258.1	258.4	259.6	262.4	264.4	267.2
45°	276.1	265.1	254.1	247.1	243.8	244.3	244.3	246.4	249.0	252.2	255.3
47.5°	256.2	245.1	236.1	230.2	228.5	228.1	229.4	232.3	236.0	239.8	244.2
50°	242.9	232.3	224.4	219.1	217.2	217.9	219.8	222.5	227.0	231.9	236.4
52.5°	229.2	219.6	212.4	207.5	206.1	207.4	209.3	213.5	217.5	222.7	228.1
55°	208.1	200.1	194.3	190.8	190.3	191.0	193.1	197.6	203.4	209.8	215.1
57.5°	187.2	180.4	175.1	172.7	172.9	173.6	177.1	182.5	188.6	195.5	202.3
60°	173.0	166.8	162.5	160.6	160.9	162.3	166.6	171.6	179.3	185.9	193.1
62.5°	159.7	154.2	150.1	148.3	148.0	151.2	155.3	160.5	168.1	175.6	183.4
65°	138.1	133.8	130.5	129.6	130.3	132.7	137.9	144.8	151.3	159.2	167.3
67.5°	117.1	113.6	111.3	111.7	112.6	116.1	120.5	126.4	133.8	142.0	150.0
70°	103.7	100.4	98.5	98.7	100.2	104.4	108.3	114.2	122.1	130.5	137.1
72.5°	90.0	87.8	86.0	87.1	88.5	91.4	96.2	102.2	109.2	116.9	124.0
75°	69.1	69.1	68.2	68.9	71.0	73.8	77.5	83.6	90.6	96.8	102.5
77.5°	51.2	50.7	51.3	52.2	53.4	56.9	61.0	65.4	70.6	76.9	81.6
80°	39.2	39.5	40.6	42.1	42.5	45.1	49.5	53.5	57.6	62.8	67.4
82.5°	29.5	29.7	30.3	32.1	32.6	35.4	38.2	42.2	45.9	49.5	53.2
85°	16.1	16.1	17.2	18.0	19.1	21.0	22.7	25.1	28.5	30.8	34.4
87.5°	6.7	6.7	7.9	8.3	9.0	10.1	10.4	12.5	13.4	14.4	16.2
90°	2.8	2.8	4.9	4.9	5.8	6.5	6.1	6.5	6.8	7.2	7.2
92.5°	18.9	26.3	44.4	72.1	99.1	113.2	94.3	70.1	52.7	42.0	34.8
95°	29.6	44.6	75.6	134.2	219.5	290.8	299.1	264.5	209.1	161.3	126.7
97.5°	35.9	48.4	72.3	120.7	205.4	306.4	375.8	390.7	370.2	335.3	298.0
100°	40.7	52.1	73.2	113.5	186.3	287.0	378.3	430.4	437.6	420.1	393.6
102.5°	46.2	57.0	76.0	111.5	173.5	262.7	356.9	428.5	463.8	468.9	457.9
105°	55.3	65.6	82.8	112.4	162.4	234.1	318.0	399.7	461.5	496.9	511.5
107.5°	64.8	75.0	90.7	117.8	160.4	218.1	286.6	359.0	424.7	474.4	506.3
110°	71.4	81.0	96.7	121.7	161.0	212.7	270.9	334.5	396.2	448.0	487.2



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	77.7	87.3	102.4	126.0	162.7	210.2	262.1	316.4	371.0	419.9	459.2
115°	87.5	97.0	111.4	132.8	165.9	208.8	253.8	298.4	342.2	384.1	418.3
117.5°	96.4	106.4	120.0	139.7	169.5	208.4	250.0	289.5	325.9	358.7	387.8
120°	102.4	112.4	126.0	144.5	172.1	208.4	248.0	285.5	318.7	347.3	372.6
122.5°	108.5	118.2	131.7	149.2	174.6	208.1	245.8	282.1	314.2	340.1	362.3
125°	116.7	126.7	139.6	155.9	178.4	207.7	242.0	276.3	306.9	331.5	351.2
127.5°	124.3	134.4	146.8	161.9	181.6	206.9	236.9	269.1	298.4	323.1	341.6
130°	129.2	139.6	151.7	165.6	183.8	206.6	233.8	263.4	291.6	315.9	334.8
132.5°	133.8	143.5	155.7	169.4	185.8	206.4	231.0	257.4	283.9	307.6	326.5
135°	140.3	149.6	161.3	174.2	188.8	205.9	226.6	249.1	272.4	294.1	311.9
137.5°	145.7	154.6	165.6	177.6	190.6	205.9	223.0	241.7	261.3	279.6	295.7
140°	149.2	157.7	168.4	179.9	192.0	205.6	221.0	237.3	254.1	270.1	285.2
142.5°	152.3	160.6	171.1	181.6	193.2	205.6	219.2	233.4	248.1	261.9	274.9
145°	156.7	164.5	173.8	183.5	193.8	204.9	216.3	227.7	239.8	250.5	260.5
147.5°	160.9	167.9	176.6	185.1	194.2	203.6	213.7	223.1	232.7	241.3	249.1
150°	163.5	170.3	178.1	185.9	194.2	202.7	211.7	220.3	228.4	235.6	242.0
152.5°	166.0	172.3	179.3	186.5	193.6	201.3	209.3	217.1	224.2	230.8	236.0
155°	169.6	174.9	181.0	187.0	192.8	199.1	205.9	212.4	218.0	223.4	227.7
157.5°	172.8	177.0	182.2	187.0	191.8	196.9	202.5	207.3	212.1	216.6	220.0
160°	174.5	178.4	182.8	187.0	191.0	195.2	199.9	204.2	208.0	212.0	214.9
162.5°	176.2	179.4	183.3	187.0	190.1	193.5	197.6	201.1	204.4	207.4	210.1
165°	178.1	180.3	183.5	186.3	188.4	191.0	193.8	196.6	198.8	201.3	203.1
167.5°	179.4	181.1	183.4	185.4	186.7	188.3	190.4	192.5	194.1	196.1	197.1
170°	180.3	181.3	183.1	184.9	185.6	186.6	188.1	189.9	191.0	192.4	193.5
172.5°	180.8	181.6	182.8	184.3	184.5	184.9	186.1	187.6	188.3	189.2	190.1
175°	181.7	181.7	182.4	183.5	183.1	183.1	183.8	184.5	184.9	185.6	185.6
177.5°	181.7	181.7	182.0	182.5	182.0	182.0	182.3	182.5	182.8	182.8	183.1
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	549.8	549.5	548.1	547.9	548.1	549.5	549.8	550.2	550.8	552.7	550.4
5°	507.9	506.6	505.9	508.6	505.9	506.6	507.9	509.3	511.7	511.9	514.3
7.5°	476.3	475.3	473.2	472.5	473.2	475.3	476.3	477.2	479.5	481.6	485.1
10°	456.1	455.0	453.1	452.6	453.1	455.0	456.1	458.4	460.8	463.4	465.9
12.5°	436.5	434.6	434.2	434.7	434.2	434.6	436.5	439.7	445.9	445.9	446.4
15°	410.6	409.6	407.0	407.8	407.0	409.6	410.6	413.7	416.6	420.2	423.7
17.5°	385.1	384.0	380.7	383.5	380.7	384.0	385.1	386.8	390.4	395.5	400.9
20°	369.0	367.1	365.5	365.2	365.5	367.1	369.0	370.7	374.8	379.1	383.1
22.5°	353.8	352.0	351.8	350.3	351.8	352.0	353.8	356.4	360.4	362.8	366.7
25°	334.6	333.0	332.4	331.2	332.4	333.0	334.6	336.5	339.1	341.0	345.4
27.5°	319.9	319.1	318.2	318.6	318.2	319.1	319.9	320.1	321.3	323.9	326.4
30°	310.9	310.7	310.2	310.2	310.2	310.7	310.9	310.2	311.4	312.7	314.6
32.5°	303.5	303.5	303.8	303.8	303.8	303.5	303.5	302.4	302.9	303.3	304.2
35°	293.1	293.8	294.2	293.5	294.2	293.8	293.1	292.1	291.3	289.6	290.1
37.5°	283.6	284.3	285.0	285.8	285.0	284.3	283.6	281.6	279.8	278.4	276.7
40°	276.3	277.9	278.4	279.6	278.4	277.9	276.3	274.2	272.3	270.5	268.6
42.5°	269.4	271.2	272.5	272.8	272.5	271.2	269.4	267.2	264.4	262.4	259.6
45°	258.8	260.7	262.5	262.5	262.5	260.7	258.8	255.3	252.2	249.0	246.4
47.5°	247.9	250.6	252.4	252.8	252.4	250.6	247.9	244.2	239.8	236.0	232.3
50°	240.4	243.8	245.5	246.6	245.5	243.8	240.4	236.4	231.9	227.0	222.5
52.5°	233.2	236.5	238.7	239.3	238.7	236.5	233.2	228.1	222.7	217.5	213.5
55°	220.6	225.4	228.0	228.9	228.0	225.4	220.6	215.1	209.8	203.4	197.6
57.5°	208.7	213.2	216.2	216.9	216.2	213.2	208.7	202.3	195.5	188.6	182.5
60°	199.5	204.4	208.1	208.8	208.1	204.4	199.5	193.1	185.9	179.3	171.6
62.5°	190.2	195.2	198.6	200.5	198.6	195.2	190.2	183.4	175.6	168.1	160.5
65°	174.0	179.0	182.4	183.1	182.4	179.0	174.0	167.3	159.2	151.3	144.8
67.5°	156.3	161.4	163.5	164.9	163.5	161.4	156.3	150.0	142.0	133.8	126.4
70°	143.9	147.9	150.4	151.5	150.4	147.9	143.9	137.1	130.5	122.1	114.2
72.5°	129.8	134.0	136.7	137.0	136.7	134.0	129.8	124.0	116.9	109.2	102.2
75°	108.1	111.9	113.3	113.3	113.3	111.9	108.1	102.5	96.8	90.6	83.6
77.5°	85.5	87.5	89.3	89.7	89.3	87.5	85.5	81.6	76.9	70.6	65.4
80°	71.0	72.2	73.6	73.6	73.6	72.2	71.0	67.4	62.8	57.6	53.5
82.5°	56.0	57.1	58.5	58.3	58.5	57.1	56.0	53.2	49.5	45.9	42.2
85°	33.9	36.1	35.9	35.3	35.9	36.1	33.9	34.4	30.8	28.5	25.1
87.5°	16.8	17.1	17.6	18.0	17.6	17.1	16.8	16.2	14.4	13.4	12.5
90°	7.5	7.9	7.5	7.5	7.5	7.9	7.5	7.2	7.2	6.8	6.5
92.5°	30.6	28.7	27.5	27.5	27.5	28.7	30.6	34.8	42.0	52.7	70.1
95°	109.2	98.2	91.7	87.1	91.7	98.2	109.2	126.7	161.3	209.1	264.5
97.5°	272.4	251.0	240.2	232.8	240.2	251.0	272.4	298.0	335.3	370.2	390.7
100°	362.6	340.8	330.1	327.3	330.1	340.8	362.6	393.6	420.1	437.6	430.4
102.5°	438.9	423.1	411.8	409.5	411.8	423.1	438.9	457.9	468.9	463.8	428.5
105°	512.2	509.3	504.3	502.2	504.3	509.3	512.2	511.5	496.9	461.5	399.7
107.5°	523.9	532.1	535.6	536.5	535.6	532.1	523.9	506.3	474.4	424.7	359.0
110°	512.5	527.6	533.9	537.1	533.9	527.6	512.5	487.2	448.0	396.2	334.5



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	488.0	506.1	515.1	520.3	515.1	506.1	488.0	459.2	419.9	371.0	316.4
115°	446.5	467.9	479.4	482.2	479.4	467.9	446.5	418.3	384.1	342.2	298.4
117.5°	411.8	429.8	441.3	443.5	441.3	429.8	411.8	387.8	358.7	325.9	289.5
120°	392.9	408.7	418.0	421.9	418.0	408.7	392.9	372.6	347.3	318.7	285.5
122.5°	379.5	392.9	400.8	404.8	400.8	392.9	379.5	362.3	340.1	314.2	282.1
125°	365.5	375.9	382.6	384.8	382.6	375.9	365.5	351.2	331.5	306.9	276.3
127.5°	356.0	365.2	370.9	373.0	370.9	365.2	356.0	341.6	323.1	298.4	269.1
130°	349.4	358.3	364.1	366.2	364.1	358.3	349.4	334.8	315.9	291.6	263.4
132.5°	340.8	350.9	356.4	358.5	356.4	350.9	340.8	326.5	307.6	283.9	257.4
135°	326.2	336.2	341.9	344.1	341.9	336.2	326.2	311.9	294.1	272.4	249.1
137.5°	309.1	318.9	323.7	326.2	323.7	318.9	309.1	295.7	279.6	261.3	241.7
140°	297.7	305.5	310.5	313.4	310.5	305.5	297.7	285.2	270.1	254.1	237.3
142.5°	286.0	293.3	297.7	299.6	297.7	293.3	286.0	274.9	261.9	248.1	233.4
145°	269.4	275.5	279.1	280.8	279.1	275.5	269.4	260.5	250.5	239.8	227.7
147.5°	255.7	260.9	263.6	264.3	263.6	260.9	255.7	249.1	241.3	232.7	223.1
150°	247.7	252.4	254.5	254.8	254.5	252.4	247.7	242.0	235.6	228.4	220.3
152.5°	240.9	244.6	245.9	246.3	245.9	244.6	240.9	236.0	230.8	224.2	217.1
155°	231.3	234.1	235.2	235.2	235.2	234.1	231.3	227.7	223.4	218.0	212.4
157.5°	222.7	224.9	225.5	225.5	225.5	224.9	222.7	220.0	216.6	212.1	207.3
160°	217.0	219.1	219.5	219.5	219.5	219.1	217.0	214.9	212.0	208.0	204.2
162.5°	211.6	213.7	214.1	213.8	214.1	213.7	211.6	210.1	207.4	204.4	201.1
165°	204.5	205.9	205.6	205.2	205.6	205.9	204.5	203.1	201.3	198.8	196.6
167.5°	197.8	198.8	198.7	198.4	198.7	198.8	197.8	197.1	196.1	194.1	192.5
170°	194.2	194.5	194.2	194.2	194.2	194.5	194.2	193.5	192.4	191.0	189.9
172.5°	190.5	190.8	190.5	189.9	190.5	190.8	190.5	190.1	189.2	188.3	187.6
175°	185.6	186.3	185.6	184.9	185.6	186.3	185.6	185.6	185.6	184.9	184.5
177.5°	182.8	183.1	182.5	182.0	182.5	183.1	182.8	183.1	182.8	182.8	182.5
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	551.5	552.3	555.3	558.3	561.7	564.1	565.8	567.7	571.8	575.0	578.1
5°	516.7	518.0	524.1	528.5	535.8	542.3	547.3	552.8	559.3	568.2	576.2
7.5°	486.0	490.5	497.4	504.3	511.8	520.3	527.7	535.9	547.0	559.3	571.8
10°	468.7	473.7	480.9	489.0	496.1	505.9	515.0	524.8	537.6	552.3	567.1
12.5°	451.3	459.6	465.0	474.6	482.4	490.5	500.2	513.0	527.8	543.3	561.2
15°	429.5	434.0	444.5	449.8	460.8	473.2	482.8	495.6	510.0	530.6	550.7
17.5°	404.3	410.3	418.7	428.7	441.3	451.0	462.9	476.3	494.3	514.7	539.9
20°	387.9	392.9	403.2	414.1	427.6	437.9	450.5	463.4	482.1	503.8	530.1
22.5°	373.1	378.0	388.9	399.1	412.1	424.6	437.9	452.9	470.8	493.7	520.6
25°	350.4	356.8	366.4	376.9	389.3	403.6	418.0	431.4	450.5	474.6	503.3
27.5°	330.1	335.3	342.2	354.2	368.3	382.1	396.4	413.2	431.6	457.2	486.9
30°	317.2	321.9	328.9	339.8	353.0	367.8	382.6	398.9	418.0	443.3	473.7
32.5°	306.8	310.4	316.6	326.5	338.5	354.1	368.7	385.5	405.6	430.5	460.1
35°	291.5	294.7	297.1	306.4	317.2	331.5	346.3	364.3	383.6	407.3	436.9
37.5°	276.6	277.7	281.1	287.3	297.7	310.9	324.7	342.3	362.1	386.2	412.9
40°	267.4	267.9	270.0	275.8	284.9	297.3	310.7	328.1	347.0	369.7	396.3
42.5°	258.4	258.1	260.1	264.2	272.7	284.0	297.1	313.1	331.9	352.9	377.9
45°	244.3	244.3	243.8	247.1	254.1	265.1	276.1	291.3	307.1	327.7	348.7
47.5°	229.4	228.1	228.5	230.2	236.1	245.1	256.2	268.7	282.7	300.0	318.5
50°	219.8	217.9	217.2	219.1	224.4	232.3	242.9	253.8	267.0	282.3	298.0
52.5°	209.3	207.4	206.1	207.5	212.4	219.6	229.2	238.9	250.7	263.2	276.8
55°	193.1	191.0	190.3	190.8	194.3	200.1	208.1	217.0	225.9	236.1	245.7
57.5°	177.1	173.6	172.9	172.7	175.1	180.4	187.2	194.8	201.3	207.5	217.7
60°	166.6	162.3	160.9	160.6	162.5	166.8	173.0	180.7	185.2	189.6	198.3
62.5°	155.3	151.2	148.0	148.3	150.1	154.2	159.7	165.2	168.2	172.9	178.8
65°	137.9	132.7	130.3	129.6	130.5	133.8	138.1	141.7	145.1	147.0	152.7
67.5°	120.5	116.1	112.6	111.7	111.3	113.6	117.1	119.3	121.7	123.3	126.7
70°	108.3	104.4	100.2	98.7	98.5	100.4	103.7	104.0	107.3	108.1	111.6
72.5°	96.2	91.4	88.5	87.1	86.0	87.8	90.0	90.6	92.4	93.7	95.5
75°	77.5	73.8	71.0	68.9	68.2	69.1	69.1	70.3	71.5	72.2	74.3
77.5°	61.0	56.9	53.4	52.2	51.3	50.7	51.2	52.0	51.4	52.6	53.1
80°	49.5	45.1	42.5	42.1	40.6	39.5	39.2	39.9	39.0	39.5	40.9
82.5°	38.2	35.4	32.6	32.1	30.3	29.7	29.5	29.0	29.0	28.9	29.2
85°	22.7	21.0	19.1	18.0	17.2	16.1	16.1	15.6	15.0	14.5	14.8
87.5°	10.4	10.1	9.0	8.3	7.9	6.7	6.7	6.1	5.8	5.4	5.0
90°	6.1	6.5	5.8	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4
92.5°	94.3	113.2	99.1	72.1	44.4	26.3	18.9	13.6	9.3	6.0	4.0
95°	299.1	290.8	219.5	134.2	75.6	44.6	29.6	21.1	16.5	12.8	11.8
97.5°	375.8	306.4	205.4	120.7	72.3	48.4	35.9	28.5	24.2	21.1	21.1
100°	378.3	287.0	186.3	113.5	73.2	52.1	40.7	33.9	29.6	27.2	27.2
102.5°	356.9	262.7	173.5	111.5	76.0	57.0	46.2	39.6	35.6	33.4	32.8
105°	318.0	234.1	162.4	112.4	82.8	65.6	55.3	48.9	44.6	42.8	41.8
107.5°	286.6	218.1	160.4	117.8	90.7	75.0	64.8	58.7	54.1	52.3	51.6
110°	270.9	212.7	161.0	121.7	96.7	81.0	71.4	64.9	60.7	58.9	58.2



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	262.1	210.2	162.7	126.0	102.4	87.3	77.7	71.2	67.3	65.1	64.4
115°	253.8	208.8	165.9	132.8	111.4	97.0	87.5	80.7	77.1	74.6	73.5
117.5°	250.0	208.4	169.5	139.7	120.0	106.4	96.4	90.1	86.1	83.9	82.9
120°	248.0	208.4	172.1	144.5	126.0	112.4	102.4	96.3	92.4	90.0	89.3
122.5°	245.8	208.1	174.6	149.2	131.7	118.2	108.5	101.8	98.2	95.6	94.9
125°	242.0	207.7	178.4	155.9	139.6	126.7	116.7	110.0	106.0	103.8	102.4
127.5°	236.9	206.9	181.6	161.9	146.8	134.4	124.3	117.2	112.8	110.2	109.1
130°	233.8	206.6	183.8	165.6	151.7	139.6	129.2	122.4	117.0	114.2	112.8
132.5°	231.0	206.4	185.8	169.4	155.7	143.5	133.8	126.4	121.4	117.6	116.5
135°	226.6	205.9	188.8	174.2	161.3	149.6	140.3	132.8	126.7	123.1	121.7
137.5°	223.0	205.9	190.6	177.6	165.6	154.6	145.7	137.9	132.2	128.3	126.9
140°	221.0	205.6	192.0	179.9	168.4	157.7	149.2	141.7	135.6	131.7	130.7
142.5°	219.2	205.6	193.2	181.6	171.1	160.6	152.3	145.1	139.4	135.7	134.6
145°	216.3	204.9	193.8	183.5	173.8	164.5	156.7	149.9	144.9	141.4	140.3
147.5°	213.7	203.6	194.2	185.1	176.6	167.9	160.9	155.2	150.2	146.9	146.6
150°	211.7	202.7	194.2	185.9	178.1	170.3	163.5	158.1	153.8	151.0	150.6
152.5°	209.3	201.3	193.6	186.5	179.3	172.3	166.0	161.3	157.2	154.4	154.3
155°	205.9	199.1	192.8	187.0	181.0	174.9	169.6	165.6	162.1	159.9	159.6
157.5°	202.5	196.9	191.8	187.0	182.2	177.0	172.8	169.4	166.6	164.6	164.6
160°	199.9	195.2	191.0	187.0	182.8	178.4	174.5	171.7	169.2	167.7	167.7
162.5°	197.6	193.5	190.1	187.0	183.3	179.4	176.2	173.7	171.5	170.4	170.6
165°	193.8	191.0	188.4	186.3	183.5	180.3	178.1	176.3	174.5	173.8	173.8
167.5°	190.4	188.3	186.7	185.4	183.4	181.1	179.4	178.3	177.0	176.6	177.0
170°	188.1	186.6	185.6	184.9	183.1	181.3	180.3	179.6	178.4	178.1	178.4
172.5°	186.1	184.9	184.5	184.3	182.8	181.6	180.8	180.4	179.6	179.6	179.9
175°	183.8	183.1	183.1	183.5	182.4	181.7	181.7	181.3	181.0	181.0	181.3
177.5°	182.3	182.0	182.0	182.5	182.0	181.7	181.7	181.7	181.4	181.7	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	580.8	582.7	585.2	589.4	590.9	592.8	595.5	595.3	596.0	599.0	605.0
5°	582.9	590.4	597.5	606.1	615.2	621.2	629.2	634.3	639.3	645.8	656.8
7.5°	583.8	595.5	608.6	623.8	637.2	652.7	664.8	676.2	686.5	700.0	713.2
10°	582.5	598.2	615.2	634.3	654.6	671.9	687.4	705.1	720.1	736.6	751.4
12.5°	580.0	599.0	621.7	643.1	666.8	692.3	711.7	729.5	749.5	768.5	791.4
15°	574.3	600.4	626.9	655.1	686.9	716.3	744.3	767.4	788.9	817.4	847.3
17.5°	567.1	595.2	628.7	662.9	696.1	729.6	764.3	799.1	826.3	861.6	884.9
20°	560.5	593.0	627.4	668.0	701.3	743.1	777.5	811.1	848.5	883.6	911.6
22.5°	551.1	586.6	623.2	663.6	707.3	749.2	788.9	825.5	862.8	901.0	934.8
25°	539.2	571.5	614.7	660.6	704.1	749.5	795.2	841.0	881.2	921.6	953.1
27.5°	519.0	559.7	600.0	647.3	695.6	747.0	795.9	843.8	886.0	919.2	938.7
30°	508.6	544.0	587.7	635.3	687.6	742.9	793.8	840.8	880.0	906.6	914.4
32.5°	493.3	529.8	572.6	621.9	677.3	734.1	787.0	831.4	864.1	878.1	868.6
35°	470.6	503.6	546.8	597.2	654.9	715.3	767.7	805.2	821.9	808.8	776.1
37.5°	443.3	476.1	519.5	569.1	628.6	690.1	737.4	764.5	758.9	726.2	677.4
40°	424.2	454.8	496.1	549.7	607.7	669.4	711.0	725.6	710.3	663.5	611.6
42.5°	403.0	432.8	474.3	526.0	587.5	644.4	680.6	681.9	656.2	600.2	548.2
45°	370.7	399.1	438.3	492.1	549.0	602.5	626.4	614.7	567.3	513.4	461.0
47.5°	338.8	363.5	402.1	453.1	507.2	552.2	564.1	543.0	492.6	440.1	391.6
50°	315.5	340.3	376.7	425.5	477.6	516.4	522.2	494.2	444.7	391.9	354.0
52.5°	293.1	317.8	352.7	397.9	445.6	480.7	480.9	448.6	399.3	352.2	316.9
55°	260.2	282.5	314.1	354.5	397.0	424.4	417.8	384.4	341.5	300.6	269.8
57.5°	228.6	248.0	277.0	310.7	348.2	370.9	359.8	327.6	289.4	254.7	231.4
60°	208.1	226.6	251.5	283.3	314.8	332.4	321.9	292.8	257.6	229.6	209.3
62.5°	188.2	203.8	227.7	255.3	284.6	297.6	288.3	259.5	229.1	203.9	187.3
65°	160.2	172.8	191.9	215.6	236.8	248.1	240.2	213.4	190.3	172.1	159.0
67.5°	133.8	143.7	158.2	177.2	195.3	201.4	194.2	175.5	155.9	141.4	132.1
70°	115.6	125.0	137.1	151.8	167.5	174.0	166.8	152.0	136.0	122.6	113.5
72.5°	99.8	107.0	117.3	129.8	142.1	148.6	143.7	129.5	115.9	105.9	98.3
75°	76.0	82.2	89.4	98.3	107.8	112.1	107.8	98.0	88.7	81.3	75.7
77.5°	55.2	58.6	64.1	70.8	76.7	80.0	76.2	69.7	63.9	58.9	56.1
80°	42.1	44.4	48.3	53.5	57.6	60.7	58.3	52.8	48.3	44.9	43.7
82.5°	30.6	32.2	34.7	38.6	41.3	42.9	41.9	37.9	36.1	33.1	31.9
85°	15.0	16.1	17.7	18.9	21.3	21.5	21.7	20.1	18.4	17.7	16.8
87.5°	5.4	5.8	6.5	7.1	7.9	8.5	8.3	8.4	7.8	7.5	6.9
90°	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.8	6.5	6.1	6.5
92.5°	6.0	9.3	13.6	18.9	26.3	44.4	72.1	99.1	113.2	94.3	70.1
95°	12.8	16.5	21.1	29.6	44.6	75.6	134.2	219.5	290.8	299.1	264.5
97.5°	21.1	24.2	28.5	35.9	48.4	72.3	120.7	205.4	306.4	375.8	390.7
100°	27.2	29.6	33.9	40.7	52.1	73.2	113.5	186.3	287.0	378.3	430.4
102.5°	33.4	35.6	39.6	46.2	57.0	76.0	111.5	173.5	262.7	356.9	428.5
105°	42.8	44.6	48.9	55.3	65.6	82.8	112.4	162.4	234.1	318.0	399.7
107.5°	52.3	54.1	58.7	64.8	75.0	90.7	117.8	160.4	218.1	286.6	359.0
110°	58.9	60.7	64.9	71.4	81.0	96.7	121.7	161.0	212.7	270.9	334.5





TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	65.1	67.3	71.2	77.7	87.3	102.4	126.0	162.7	210.2	262.1	316.4
115°	74.6	77.1	80.7	87.5	97.0	111.4	132.8	165.9	208.8	253.8	298.4
117.5°	83.9	86.1	90.1	96.4	106.4	120.0	139.7	169.5	208.4	250.0	289.5
120°	90.0	92.4	96.3	102.4	112.4	126.0	144.5	172.1	208.4	248.0	285.5
122.5°	95.6	98.2	101.8	108.5	118.2	131.7	149.2	174.6	208.1	245.8	282.1
125°	103.8	106.0	110.0	116.7	126.7	139.6	155.9	178.4	207.7	242.0	276.3
127.5°	110.2	112.8	117.2	124.3	134.4	146.8	161.9	181.6	206.9	236.9	269.1
130°	114.2	117.0	122.4	129.2	139.6	151.7	165.6	183.8	206.6	233.8	263.4
132.5°	117.6	121.4	126.4	133.8	143.5	155.7	169.4	185.8	206.4	231.0	257.4
135°	123.1	126.7	132.8	140.3	149.6	161.3	174.2	188.8	205.9	226.6	249.1
137.5°	128.3	132.2	137.9	145.7	154.6	165.6	177.6	190.6	205.9	223.0	241.7
140°	131.7	135.6	141.7	149.2	157.7	168.4	179.9	192.0	205.6	221.0	237.3
142.5°	135.7	139.4	145.1	152.3	160.6	171.1	181.6	193.2	205.6	219.2	233.4
145°	141.4	144.9	149.9	156.7	164.5	173.8	183.5	193.8	204.9	216.3	227.7
147.5°	146.9	150.2	155.2	160.9	167.9	176.6	185.1	194.2	203.6	213.7	223.1
150°	151.0	153.8	158.1	163.5	170.3	178.1	185.9	194.2	202.7	211.7	220.3
152.5°	154.4	157.2	161.3	166.0	172.3	179.3	186.5	193.6	201.3	209.3	217.1
155°	159.9	162.1	165.6	169.6	174.9	181.0	187.0	192.8	199.1	205.9	212.4
157.5°	164.6	166.6	169.4	172.8	177.0	182.2	187.0	191.8	196.9	202.5	207.3
160°	167.7	169.2	171.7	174.5	178.4	182.8	187.0	191.0	195.2	199.9	204.2
162.5°	170.4	171.5	173.7	176.2	179.4	183.3	187.0	190.1	193.5	197.6	201.1
165°	173.8	174.5	176.3	178.1	180.3	183.5	186.3	188.4	191.0	193.8	196.6
167.5°	176.6	177.0	178.3	179.4	181.1	183.4	185.4	186.7	188.3	190.4	192.5
170°	178.1	178.4	179.6	180.3	181.3	183.1	184.9	185.6	186.6	188.1	189.9
172.5°	179.6	179.6	180.4	180.8	181.6	182.8	184.3	184.5	184.9	186.1	187.6
175°	181.0	181.0	181.3	181.7	181.7	182.4	183.5	183.1	183.1	183.8	184.5
177.5°	181.7	181.4	181.7	181.7	181.7	182.0	182.5	182.0	182.0	182.3	182.5
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	576.9	576.9	576.9	576.9	576.9	576.9	576.9
2.5°	608.1	608.5	610.3	611.6	612.0	613.9	614.0
5°	661.6	665.6	673.5	674.2	675.4	681.7	676.8
7.5°	724.2	734.5	741.3	747.5	749.6	752.3	751.8
10°	764.4	779.6	787.3	799.5	799.9	803.0	801.1
12.5°	804.7	822.4	836.4	838.7	848.9	850.5	853.1
15°	861.8	880.7	900.1	907.1	921.1	924.4	929.7
17.5°	915.5	934.8	948.5	966.3	972.2	979.9	974.6
20°	945.0	966.0	983.3	997.3	1003.3	1007.6	1007.1
22.5°	962.8	984.0	997.9	1008.7	1014.2	1016.0	1015.9
25°	973.9	986.1	990.5	994.5	988.3	986.1	987.0
27.5°	942.9	939.8	928.6	913.8	898.6	886.5	879.8
30°	900.3	881.7	864.7	835.1	819.8	810.7	802.5
32.5°	839.9	810.3	777.7	750.5	733.2	719.7	717.7
35°	736.4	692.0	652.0	618.7	601.6	587.0	583.6
37.5°	626.0	579.9	543.9	514.6	496.1	485.8	476.3
40°	552.8	513.1	477.8	452.9	438.8	431.4	425.5
42.5°	496.4	460.2	425.0	406.1	393.3	388.8	385.3
45°	418.5	384.8	360.4	346.1	338.7	331.0	327.4
47.5°	356.1	328.7	312.7	300.4	292.5	287.9	285.7
50°	320.7	298.3	284.0	274.6	267.4	263.9	262.0
52.5°	289.4	270.9	258.9	251.5	246.6	244.0	243.2
55°	249.2	235.2	227.5	221.1	217.5	215.1	214.2
57.5°	216.7	205.8	199.7	194.3	192.9	191.0	190.3
60°	195.3	186.9	181.7	178.0	176.8	174.5	174.9
62.5°	176.3	169.5	165.0	163.0	161.4	159.4	160.1
65°	149.2	144.1	141.7	139.9	137.9	136.7	137.6
67.5°	125.1	121.7	118.5	117.3	116.4	116.2	115.2
70°	109.5	106.6	103.7	103.0	103.0	102.1	101.8
72.5°	94.3	92.3	90.4	89.8	89.1	89.5	88.5
75°	72.9	71.2	70.5	69.8	69.6	69.6	68.9
77.5°	53.8	52.6	51.5	51.5	50.6	50.3	50.2
80°	40.9	40.4	39.5	39.5	39.0	39.2	38.7
82.5°	30.7	30.1	29.9	29.5	28.8	28.9	28.4
85°	16.5	15.8	15.6	14.8	14.3	14.8	14.3
87.5°	7.1	7.0	6.8	6.5	6.4	6.3	5.7
90°	6.8	7.2	7.2	7.5	7.9	7.5	7.5
92.5°	52.7	42.0	34.8	30.6	28.7	27.5	27.5
95°	209.1	161.3	126.7	109.2	98.2	91.7	87.1
97.5°	370.2	335.3	298.0	272.4	251.0	240.2	232.8
100°	437.6	420.1	393.6	362.6	340.8	330.1	327.3
102.5°	463.8	468.9	457.9	438.9	423.1	411.8	409.5
105°	461.5	496.9	511.5	512.2	509.3	504.3	502.2
107.5°	424.7	474.4	506.3	523.9	532.1	535.6	536.5
110°	396.2	448.0	487.2	512.5	527.6	533.9	537.1



TEST NUMBER: P332492-840

CATALOG NUMBER: S124DIP-S350D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	371.0	419.9	459.2	488.0	506.1	515.1	520.3
115°	342.2	384.1	418.3	446.5	467.9	479.4	482.2
117.5°	325.9	358.7	387.8	411.8	429.8	441.3	443.5
120°	318.7	347.3	372.6	392.9	408.7	418.0	421.9
122.5°	314.2	340.1	362.3	379.5	392.9	400.8	404.8
125°	306.9	331.5	351.2	365.5	375.9	382.6	384.8
127.5°	298.4	323.1	341.6	356.0	365.2	370.9	373.0
130°	291.6	315.9	334.8	349.4	358.3	364.1	366.2
132.5°	283.9	307.6	326.5	340.8	350.9	356.4	358.5
135°	272.4	294.1	311.9	326.2	336.2	341.9	344.1
137.5°	261.3	279.6	295.7	309.1	318.9	323.7	326.2
140°	254.1	270.1	285.2	297.7	305.5	310.5	313.4
142.5°	248.1	261.9	274.9	286.0	293.3	297.7	299.6
145°	239.8	250.5	260.5	269.4	275.5	279.1	280.8
147.5°	232.7	241.3	249.1	255.7	260.9	263.6	264.3
150°	228.4	235.6	242.0	247.7	252.4	254.5	254.8
152.5°	224.2	230.8	236.0	240.9	244.6	245.9	246.3
155°	218.0	223.4	227.7	231.3	234.1	235.2	235.2
157.5°	212.1	216.6	220.0	222.7	224.9	225.5	225.5
160°	208.0	212.0	214.9	217.0	219.1	219.5	219.5
162.5°	204.4	207.4	210.1	211.6	213.7	214.1	213.8
165°	198.8	201.3	203.1	204.5	205.9	205.6	205.2
167.5°	194.1	196.1	197.1	197.8	198.8	198.7	198.4
170°	191.0	192.4	193.5	194.2	194.5	194.2	194.2
172.5°	188.3	189.2	190.1	190.5	190.8	190.5	189.9
175°	184.9	185.6	185.6	185.6	186.3	185.6	184.9
177.5°	182.8	182.8	183.1	182.8	183.1	182.5	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7

(END OF REPORT)