

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332873-840

Luminaire Tested: **S124RDIP-S350D590U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332873-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D590U840-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3633.7 lumens
Efficiency: N/A
Efficacy: 141.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41								
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36								
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30								
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	31	26								
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	29	27	23								
5	68	56	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20								
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18								
7	58	46	38	33	53	42	35	31	36	30	27	29	25	22	23	21	18	16								
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	19	17	14								
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15	13								
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4789	4789	4789	4789
5°	5555	4803	4246	4803
10°	6571	4782	3789	4782
15°	7590	4738	3256	4738
20°	8451	4677	2944	4677
25°	8725	4618	2734	4618
30°	7637	4545	2606	4545
35°	5945	4438	2530	4438
40°	4458	4314	2488	4314
45°	3520	4117	2466	4117
50°	2972	3890	2396	3890
55°	2590	3640	2267	3640
60°	2330	3379	2007	3379
65°	2055	3100	1727	3100
70°	1851	2811	1555	2811
75°	1550	2489	1326	2489
80°	1311	2120	1246	2120
85°	1102	1667	1102	1667



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.6
10°-20°	173.4	4.8
20°-30°	271.2	7.5
30°-40°	301.5	8.3
40°-50°	267.5	7.4
50°-60°	208.4	5.7
60°-70°	136.5	3.8
70°-80°	67.1	1.8
80°-90°	18.2	0.5
90°-100°	211.8	5.8
100°-110°	440.8	12.1
110°-120°	394.8	10.9
120°-130°	332.1	9.1
130°-140°	276.9	7.6
140°-150°	211.5	5.8
150°-160°	148.7	4.1
160°-170°	87.5	2.4
170°-180°	28.5	0.8
0°-30°	502.0	13.8
0°-40°	803.5	22.1
0°-60°	1279.4	35.2
0°-90°	1501.1	41.3
90°-120°	1047.4	28.8
90°-150°	1868.0	51.4
90°-180°	2133.0	58.7
0°-180°	3633.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	593	593	593	593	593	
5°	686	593	524	593	686	69
15°	908	567	390	567	908	258
25°	980	518	307	518	980	435
35°	603	450	257	450	603	378
45°	308	361	216	361	308	244
55°	184	259	161	259	184	167
65°	108	162	90	162	108	108
75°	50	80	42	80	50	55
85°	12	18	12	18	12	14
90°	12	1	12	1	12	10
95°	141	19	141	19	141	218
105°	810	67	810	67	810	801
115°	778	119	778	119	778	773
125°	621	165	621	165	621	564
135°	555	196	555	196	555	429
145°	453	226	453	226	453	287
155°	380	258	380	258	380	177
165°	331	280	331	280	331	95
175°	298	293	298	293	298	29
180°	293	293	293	293	293	



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	625.7	627.4	625.7	625.5	623.6	623.0	622.3	619.8	615.2	612.5	613.1
5°	685.5	691.5	688.1	687.6	682.4	677.1	673.8	666.1	657.9	652.5	647.9
7.5°	754.6	758.0	755.9	752.6	744.1	739.2	731.4	721.4	706.8	695.7	685.5
10°	801.6	804.5	803.5	797.3	791.1	778.4	771.2	757.2	738.7	724.2	710.5
12.5°	847.9	850.9	842.5	842.8	831.0	821.0	809.7	791.9	770.7	751.9	734.9
15°	908.2	904.3	904.3	899.6	886.5	872.6	860.9	842.2	815.5	793.0	769.3
17.5°	955.4	956.7	954.8	943.5	933.2	918.9	897.4	875.7	850.8	820.6	796.5
20°	983.7	983.7	981.6	973.9	960.6	945.2	922.1	898.4	866.9	836.5	809.3
22.5°	995.2	995.9	993.4	987.1	975.1	960.2	940.4	916.4	883.8	849.7	816.0
25°	979.5	984.0	984.4	982.8	979.2	970.1	953.1	928.6	899.4	862.3	826.0
27.5°	899.2	904.9	910.0	918.3	929.3	934.9	935.7	923.2	897.8	862.1	825.6
30°	819.3	824.0	839.6	859.9	875.7	890.0	902.5	905.8	891.5	859.5	821.0
32.5°	730.5	737.1	752.7	774.5	800.7	825.1	852.9	867.2	866.8	847.6	812.0
35°	603.2	608.0	622.4	645.3	676.8	713.0	757.2	791.5	815.0	813.3	791.5
37.5°	486.6	491.9	506.3	525.4	556.0	600.7	643.5	690.9	734.2	758.5	751.2
40°	423.0	423.2	437.4	457.0	485.6	524.6	571.2	623.8	672.1	711.6	719.1
42.5°	372.9	372.9	382.3	403.4	424.0	460.7	505.2	557.4	614.0	659.5	679.7
45°	308.3	310.4	318.1	330.7	347.0	378.1	413.7	462.2	525.5	579.6	613.3
47.5°	261.1	264.3	269.1	279.4	292.4	313.1	342.5	386.2	437.7	497.1	545.0
50°	236.6	237.1	243.3	249.0	260.2	276.8	302.6	338.9	386.3	443.3	496.7
52.5°	215.6	215.5	219.2	226.5	235.6	248.4	269.3	302.4	344.4	395.6	450.6
55°	184.0	185.2	188.1	193.8	200.8	209.8	226.3	251.2	284.2	327.9	377.9
57.5°	160.1	160.7	162.9	165.3	171.7	178.3	190.7	207.9	235.7	271.6	318.1
60°	144.3	144.6	145.3	148.9	153.9	160.2	168.5	183.1	206.5	239.2	276.1
62.5°	129.1	129.5	130.6	133.2	137.1	141.4	150.2	161.9	181.3	209.2	242.4
65°	107.6	107.8	109.5	110.4	113.5	117.3	123.8	131.7	145.1	168.5	193.6
67.5°	89.9	89.9	90.0	91.3	93.4	95.9	99.8	106.1	116.2	130.6	152.7
70°	78.4	78.4	78.9	79.6	80.8	82.9	85.1	89.9	97.3	109.0	125.9
72.5°	67.7	67.9	68.4	68.5	69.1	70.9	72.5	75.5	81.0	89.9	103.6
75°	49.7	50.4	51.6	52.6	53.8	53.5	55.2	57.2	58.8	64.0	71.9
77.5°	37.0	36.7	36.8	37.6	37.7	38.0	39.2	40.6	41.9	44.3	47.2
80°	28.2	28.2	28.9	29.2	28.9	29.2	30.4	31.1	31.5	32.5	35.1
82.5°	21.3	21.7	21.5	21.7	21.8	22.1	23.1	23.2	23.7	24.1	25.1
85°	11.9	12.2	12.4	11.9	11.9	11.9	12.4	12.6	13.1	12.9	13.4
87.5°	6.7	6.5	6.8	6.7	6.7	6.5	6.6	6.9	6.4	6.7	6.5
90°	12.1	12.1	12.6	12.1	11.5	11.5	10.9	10.4	9.8	10.4	9.2
92.5°	44.3	44.3	46.4	49.4	56.2	67.8	85.1	113.1	152.2	182.7	160.0
95°	140.6	148.0	158.4	176.3	204.5	260.3	337.6	426.9	482.7	469.5	354.3
97.5°	375.7	387.7	405.0	439.7	481.0	541.2	597.5	630.7	606.5	494.5	331.6
100°	528.3	532.9	550.2	585.3	635.4	678.0	706.3	694.8	610.7	463.1	300.7
102.5°	661.0	664.7	682.9	708.3	739.1	756.9	748.7	691.6	576.0	424.0	279.9
105°	810.5	814.0	822.0	826.7	825.6	801.9	744.9	645.2	513.3	377.9	262.2
107.5°	866.1	864.5	858.8	845.7	817.2	765.9	685.5	579.5	462.6	352.1	258.9
110°	867.0	861.8	851.4	827.3	786.4	723.0	639.4	539.8	437.3	343.4	259.8



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	839.8	831.4	816.9	787.6	741.1	677.8	598.8	510.8	422.9	339.2	262.6
115°	778.3	773.7	755.3	720.6	675.2	619.9	552.5	481.6	409.6	337.0	267.9
117.5°	716.0	712.4	693.7	664.7	625.8	579.0	525.9	467.3	403.6	336.4	273.5
120°	681.0	674.6	659.6	634.3	601.4	560.5	514.4	460.9	400.4	336.4	277.7
122.5°	653.3	646.9	634.3	612.6	584.8	549.0	507.1	455.3	396.7	336.0	281.9
125°	621.0	617.5	606.6	589.9	566.8	535.1	495.4	445.9	390.6	335.3	288.0
127.5°	602.1	598.6	589.5	574.6	551.4	521.4	481.7	434.3	382.4	334.0	293.0
130°	591.1	587.6	578.3	564.0	540.4	509.8	470.7	425.2	377.3	333.6	296.7
132.5°	578.7	575.1	566.4	550.2	526.9	496.4	458.2	415.5	372.7	333.1	299.9
135°	555.3	551.9	542.7	526.5	503.5	474.6	439.6	402.1	365.8	332.3	304.8
137.5°	526.5	522.4	514.8	498.9	477.4	451.3	421.7	390.0	359.8	332.2	307.6
140°	505.8	501.2	493.1	480.5	460.3	436.1	410.2	383.0	356.6	331.8	309.9
142.5°	483.6	480.5	473.3	461.5	443.7	422.7	400.5	376.7	353.9	331.8	311.7
145°	453.3	450.5	444.7	434.9	420.5	404.5	387.1	367.5	349.1	330.6	312.9
147.5°	426.6	425.5	421.1	412.7	402.1	389.4	375.6	360.0	344.9	328.6	313.4
150°	411.3	410.7	407.3	399.8	390.6	380.2	368.7	355.5	341.6	327.2	313.4
152.5°	397.5	396.9	394.9	388.7	380.9	372.3	361.7	350.3	337.9	324.9	312.5
155°	379.6	379.6	377.9	373.3	367.5	360.6	351.9	342.7	332.3	321.4	311.0
157.5°	364.0	364.0	362.9	359.5	355.1	349.5	342.3	334.6	326.8	317.9	309.6
160°	354.3	354.3	353.8	350.2	346.8	342.1	335.9	329.5	322.7	315.1	308.2
162.5°	345.1	345.6	345.0	341.5	339.0	334.8	329.8	324.5	318.9	312.4	306.8
165°	331.2	331.8	332.3	330.1	327.8	324.9	320.8	317.4	312.9	308.2	304.2
167.5°	320.3	320.7	320.8	319.4	318.2	316.5	313.3	310.6	307.3	304.1	301.4
170°	313.4	313.4	314.0	313.4	312.3	310.5	308.2	306.5	303.6	301.2	299.5
172.5°	306.5	307.4	308.0	307.4	306.7	305.5	304.1	302.8	300.3	298.5	297.7
175°	298.4	299.5	300.7	299.5	299.5	299.5	298.4	297.8	296.7	295.5	295.5
177.5°	293.7	294.6	295.5	295.1	295.5	295.1	295.1	294.6	294.2	293.7	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	611.2	608.5	607.1	604.1	600.5	598.5	596.8	594.3	591.1	587.6	585.2
5°	642.2	636.4	629.2	620.7	613.1	605.6	599.2	592.7	585.3	577.6	570.1
7.5°	674.0	662.8	650.6	636.4	622.8	610.3	598.7	587.8	575.4	564.2	554.1
10°	696.2	681.0	664.0	646.0	628.1	612.6	597.2	583.4	568.2	554.5	543.0
12.5°	714.2	696.2	675.8	653.5	631.9	613.1	595.5	577.4	560.1	545.3	530.0
15°	744.0	719.4	692.0	665.1	637.2	611.6	587.9	566.9	547.0	526.2	511.7
17.5°	764.6	735.3	701.9	669.7	636.7	606.5	579.3	554.2	531.3	510.1	492.7
20°	776.8	744.5	707.4	670.9	633.8	601.6	572.2	544.4	520.8	497.9	479.9
22.5°	783.7	747.9	707.4	669.1	630.8	595.8	563.6	534.7	509.0	485.9	466.2
25°	785.9	747.6	706.3	662.3	620.3	583.2	549.7	518.4	489.7	466.8	445.8
27.5°	782.7	737.7	695.4	650.3	606.8	567.8	532.7	499.8	471.1	446.5	424.9
30°	778.2	729.9	684.5	637.6	593.7	556.1	519.1	487.6	457.7	432.1	410.4
32.5°	768.2	720.3	671.5	623.5	579.0	540.3	505.1	473.4	444.1	418.0	394.9
35°	748.5	700.0	647.0	597.7	554.0	513.8	480.9	450.3	422.3	394.4	370.0
37.5°	722.6	673.1	620.3	566.3	522.5	484.6	454.4	425.7	398.4	372.8	345.9
40°	698.1	653.0	598.4	544.9	500.0	463.4	435.5	409.4	381.9	356.6	329.6
42.5°	668.5	630.1	574.9	521.2	476.9	441.6	415.6	390.1	365.1	340.5	312.4
45°	619.0	589.9	538.3	486.7	441.9	407.0	383.1	360.6	338.7	315.3	288.7
47.5°	562.3	542.6	498.1	445.1	403.8	372.4	349.3	330.9	312.4	288.9	265.7
50°	522.9	510.3	467.3	419.0	379.5	350.6	327.0	309.7	294.2	271.8	251.0
52.5°	480.9	474.1	437.8	391.6	353.6	325.2	305.0	289.5	273.8	255.1	235.7
55°	416.8	420.4	389.6	349.6	313.8	289.9	271.6	258.6	245.2	229.4	214.4
57.5°	351.3	364.5	343.8	308.7	275.1	253.0	239.1	228.3	217.0	204.0	191.1
60°	312.1	323.2	311.4	280.5	251.2	230.7	217.7	209.3	198.1	186.2	176.4
62.5°	273.9	285.7	278.7	253.8	226.5	208.8	197.4	189.7	181.3	170.9	160.7
65°	225.9	233.5	230.1	213.0	193.6	178.5	168.0	162.3	154.6	147.0	137.9
67.5°	173.0	187.7	185.8	176.6	160.0	148.1	141.3	136.2	129.3	123.6	117.4
70°	142.2	155.8	155.6	148.1	139.1	128.2	123.3	119.1	112.8	107.3	102.3
72.5°	116.4	128.9	130.8	125.0	118.9	110.5	105.9	103.0	96.9	93.2	89.1
75°	81.5	90.6	93.0	93.0	90.1	85.8	81.7	79.8	75.5	72.2	69.8
77.5°	53.4	59.2	62.9	63.7	64.2	62.7	59.4	58.1	54.7	53.6	51.3
80°	37.8	41.6	45.8	47.4	48.5	48.1	46.7	45.6	42.5	41.3	40.4
82.5°	26.1	28.2	31.7	34.9	34.5	35.9	34.5	33.8	31.4	31.0	30.1
85°	13.6	13.8	14.3	16.5	17.7	18.2	18.4	18.0	17.2	17.2	15.6
87.5°	6.2	6.1	5.7	5.7	5.8	6.5	6.7	6.7	6.3	6.1	5.6
90°	8.1	8.1	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	116.3	71.7	42.4	30.4	22.0	14.9	9.6	6.6	9.6	14.9	22.0
95°	216.6	122.1	72.0	47.8	34.0	26.5	20.7	19.0	20.7	26.5	34.0
97.5°	194.7	116.7	78.2	57.9	45.9	39.1	34.1	34.1	34.1	39.1	45.9
100°	183.2	118.1	84.1	65.6	54.7	47.8	43.8	43.8	43.8	47.8	54.7
102.5°	180.0	122.7	91.9	74.4	63.9	57.5	53.9	53.0	53.9	57.5	63.9
105°	181.5	133.6	106.0	89.3	79.0	72.0	69.2	67.4	69.2	72.0	79.0
107.5°	190.0	146.4	121.1	104.6	94.7	87.4	84.4	83.3	84.4	87.4	94.7
110°	196.4	156.1	130.8	115.2	104.8	98.0	95.0	93.9	95.0	98.0	104.8



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	203.4	165.3	140.9	125.3	115.0	108.6	105.2	104.0	105.2	108.6	115.0
115°	214.3	179.8	156.7	141.2	130.2	124.4	120.4	118.7	120.4	124.4	130.2
117.5°	225.5	193.7	171.8	155.6	145.4	139.1	135.5	133.9	135.5	139.1	145.4
120°	233.3	203.4	181.5	165.3	155.5	149.2	145.2	144.0	145.2	149.2	155.5
122.5°	240.7	212.6	190.7	175.0	164.3	158.4	154.4	153.2	154.4	158.4	164.3
125°	251.8	225.2	204.5	188.3	177.4	171.1	167.6	165.3	167.6	171.1	177.4
127.5°	261.4	237.0	216.9	200.7	189.2	182.1	177.9	176.0	177.9	182.1	189.2
130°	267.3	244.8	225.2	208.5	197.6	188.9	184.3	182.1	184.3	188.9	197.6
132.5°	273.3	251.3	231.7	215.9	204.1	195.9	189.9	188.0	189.9	195.9	204.1
135°	281.1	260.3	241.4	226.4	214.3	204.5	198.7	196.4	198.7	204.5	214.3
137.5°	286.7	267.3	249.5	235.3	222.7	213.4	207.0	204.9	207.0	213.4	222.7
140°	290.3	272.0	254.6	240.8	228.7	218.9	212.6	210.9	212.6	218.9	228.7
142.5°	293.1	276.1	259.2	245.9	234.2	224.9	219.0	217.3	219.0	224.9	234.2
145°	296.1	280.5	265.6	252.9	242.0	233.9	228.1	226.4	228.1	233.9	242.0
147.5°	298.7	285.2	271.1	259.7	250.5	242.3	237.2	236.6	237.2	242.3	250.5
150°	300.1	287.5	274.8	263.9	255.2	248.3	243.7	243.1	243.7	248.3	255.2
152.5°	301.0	289.3	278.0	268.0	260.2	253.8	249.2	249.1	249.2	253.8	260.2
155°	301.8	292.1	282.3	273.7	267.3	261.6	258.1	257.5	258.1	261.6	267.3
157.5°	301.8	294.1	285.7	278.9	273.4	268.9	265.7	265.7	265.7	268.9	273.4
160°	301.8	295.0	288.0	281.7	277.1	273.1	270.7	270.7	270.7	273.1	277.1
162.5°	301.8	295.9	289.4	284.5	280.3	276.7	274.9	275.4	274.9	276.7	280.3
165°	300.7	296.1	290.9	287.5	284.6	281.7	280.5	280.5	280.5	281.7	284.6
167.5°	299.3	296.0	292.2	289.5	287.9	285.7	285.2	285.7	285.2	285.7	287.9
170°	298.4	295.5	292.7	290.9	289.7	288.0	287.5	288.0	287.5	288.0	289.7
172.5°	297.5	295.1	293.1	291.9	291.1	289.8	289.7	290.3	289.7	289.8	291.1
175°	296.1	294.4	293.3	293.3	292.7	292.1	292.1	292.7	292.1	292.1	292.7
177.5°	294.6	293.7	293.3	293.3	293.3	292.8	293.3	293.7	293.3	292.8	293.3
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	582.5	580.6	578.1	575.2	571.8	568.8	567.3	568.6	569.2	567.5	567.3
5°	564.7	558.8	554.0	546.8	541.1	536.3	533.0	531.5	532.0	528.2	527.3
7.5°	544.8	537.8	529.9	521.4	513.5	506.4	502.8	500.8	496.7	494.9	492.0
10°	532.0	522.5	514.8	504.7	495.6	487.4	483.2	479.9	475.8	473.9	469.9
12.5°	518.9	507.8	499.3	488.9	479.6	469.6	465.6	459.5	453.1	449.1	443.8
15°	500.2	486.9	476.6	464.1	453.1	441.7	431.4	419.9	415.7	406.6	401.3
17.5°	478.5	464.9	452.2	435.6	418.6	404.2	393.3	382.3	375.8	370.0	367.3
20°	464.1	451.7	434.0	414.7	395.8	380.0	371.1	364.0	356.8	352.7	349.9
22.5°	450.6	434.6	414.1	393.2	374.4	362.0	354.6	347.2	341.3	337.5	333.7
25°	427.8	407.0	385.3	361.3	348.5	337.7	329.6	323.6	320.0	315.0	313.1
27.5°	404.5	379.2	355.3	339.2	325.8	315.9	308.8	304.4	299.8	296.6	294.1
30°	386.5	360.9	339.4	324.1	310.4	302.4	296.6	291.3	287.7	285.1	283.3
32.5°	368.7	343.2	325.1	308.6	297.8	289.9	283.8	279.8	277.0	273.7	272.5
35°	343.0	320.2	304.5	289.6	278.7	271.6	266.7	262.7	260.2	259.3	258.6
37.5°	318.2	299.6	282.7	270.5	260.7	255.1	249.4	247.4	245.8	244.1	244.9
40°	302.6	285.1	270.0	257.2	249.2	243.1	239.7	237.3	235.9	235.9	235.9
42.5°	289.0	272.0	257.2	245.7	237.8	232.6	228.8	226.8	226.3	226.1	227.3
45°	267.9	252.2	237.3	227.7	221.1	215.8	213.7	212.0	212.0	213.0	213.2
47.5°	247.0	232.3	220.4	209.6	203.5	200.3	198.3	197.5	197.6	198.5	199.7
50°	234.2	219.6	207.9	198.3	192.7	189.6	187.8	187.3	187.8	187.8	189.6
52.5°	220.3	207.2	195.7	187.6	181.2	178.2	177.3	176.6	176.9	177.7	178.4
55°	199.9	188.1	177.1	169.5	164.7	162.8	160.6	160.9	160.4	160.9	160.9
57.5°	179.3	168.7	158.5	152.5	148.2	145.5	143.2	143.8	143.1	143.0	142.6
60°	166.1	154.6	146.5	141.0	136.2	133.8	131.7	132.2	131.5	131.0	130.0
62.5°	151.8	142.2	134.4	129.2	125.3	122.6	120.4	120.0	118.3	116.6	114.5
65°	131.0	123.1	116.1	111.2	107.6	105.4	103.7	102.3	98.7	94.9	93.0
67.5°	110.8	105.0	98.6	94.3	91.4	88.7	85.4	83.0	79.7	77.6	76.3
70°	97.8	92.3	86.7	82.7	79.6	77.0	73.4	71.7	69.3	68.4	67.2
72.5°	85.3	80.2	75.1	71.4	68.2	66.0	63.2	61.6	60.5	60.1	59.0
75°	66.4	62.4	58.6	55.2	52.6	51.1	50.0	48.8	48.3	46.2	44.9
77.5°	48.5	45.7	43.4	41.0	39.2	38.2	35.9	34.5	33.7	32.7	32.4
80°	37.8	35.9	33.4	32.0	29.4	28.5	27.5	27.3	27.0	26.8	26.6
82.5°	28.4	26.5	24.1	23.2	22.5	21.9	21.4	21.1	20.9	21.0	21.0
85°	14.3	13.4	13.4	13.1	12.9	12.6	12.4	12.4	12.2	12.4	12.2
87.5°	5.7	5.6	6.2	5.9	6.3	6.5	6.2	6.3	6.6	6.4	6.4
90°	4.6	4.6	8.1	8.1	9.2	10.4	9.8	10.4	10.9	11.5	11.5
92.5°	30.4	42.4	71.7	116.3	160.0	182.7	152.2	113.1	85.1	67.8	56.2
95°	47.8	72.0	122.1	216.6	354.3	469.5	482.7	426.9	337.6	260.3	204.5
97.5°	57.9	78.2	116.7	194.7	331.6	494.5	606.5	630.7	597.5	541.2	481.0
100°	65.6	84.1	118.1	183.2	300.7	463.1	610.7	694.8	706.3	678.0	635.4
102.5°	74.4	91.9	122.7	180.0	279.9	424.0	576.0	691.6	748.7	756.9	739.1
105°	89.3	106.0	133.6	181.5	262.2	377.9	513.3	645.2	744.9	801.9	825.6
107.5°	104.6	121.1	146.4	190.0	258.9	352.1	462.6	579.5	685.5	765.9	817.2
110°	115.2	130.8	156.1	196.4	259.8	343.4	437.3	539.8	639.4	723.0	786.4



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	125.3	140.9	165.3	203.4	262.6	339.2	422.9	510.8	598.8	677.8	741.1
115°	141.2	156.7	179.8	214.3	267.9	337.0	409.6	481.6	552.5	619.9	675.2
117.5°	155.6	171.8	193.7	225.5	273.5	336.4	403.6	467.3	525.9	579.0	625.8
120°	165.3	181.5	203.4	233.3	277.7	336.4	400.4	460.9	514.4	560.5	601.4
122.5°	175.0	190.7	212.6	240.7	281.9	336.0	396.7	455.3	507.1	549.0	584.8
125°	188.3	204.5	225.2	251.8	288.0	335.3	390.6	445.9	495.4	535.1	566.8
127.5°	200.7	216.9	237.0	261.4	293.0	334.0	382.4	434.3	481.7	521.4	551.4
130°	208.5	225.2	244.8	267.3	296.7	333.6	377.3	425.2	470.7	509.8	540.4
132.5°	215.9	231.7	251.3	273.3	299.9	333.1	372.7	415.5	458.2	496.4	526.9
135°	226.4	241.4	260.3	281.1	304.8	332.3	365.8	402.1	439.6	474.6	503.5
137.5°	235.3	249.5	267.3	286.7	307.6	332.2	359.8	390.0	421.7	451.3	477.4
140°	240.8	254.6	272.0	290.3	309.9	331.8	356.6	383.0	410.2	436.1	460.3
142.5°	245.9	259.2	276.1	293.1	311.7	331.8	353.9	376.7	400.5	422.7	443.7
145°	252.9	265.6	280.5	296.1	312.9	330.6	349.1	367.5	387.1	404.5	420.5
147.5°	259.7	271.1	285.2	298.7	313.4	328.6	344.9	360.0	375.6	389.4	402.1
150°	263.9	274.8	287.5	300.1	313.4	327.2	341.6	355.5	368.7	380.2	390.6
152.5°	268.0	278.0	289.3	301.0	312.5	324.9	337.9	350.3	361.7	372.3	380.9
155°	273.7	282.3	292.1	301.8	311.0	321.4	332.3	342.7	351.9	360.6	367.5
157.5°	278.9	285.7	294.1	301.8	309.6	317.9	326.8	334.6	342.3	349.5	355.1
160°	281.7	288.0	295.0	301.8	308.2	315.1	322.7	329.5	335.9	342.1	346.8
162.5°	284.5	289.4	295.9	301.8	306.8	312.4	318.9	324.5	329.8	334.8	339.0
165°	287.5	290.9	296.1	300.7	304.2	308.2	312.9	317.4	320.8	324.9	327.8
167.5°	289.5	292.2	296.0	299.3	301.4	304.1	307.3	310.6	313.3	316.5	318.2
170°	290.9	292.7	295.5	298.4	299.5	301.2	303.6	306.5	308.2	310.5	312.3
172.5°	291.9	293.1	295.1	297.5	297.7	298.5	300.3	302.8	304.1	305.5	306.7
175°	293.3	293.3	294.4	296.1	295.5	295.5	296.7	297.8	298.4	299.5	299.5
177.5°	293.3	293.3	293.7	294.6	293.7	293.7	294.2	294.6	295.1	295.1	295.5
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	566.2	566.6	565.3	564.9	565.3	566.6	566.2	567.3	567.5	569.2	568.6
5°	525.3	524.8	523.6	523.9	523.6	524.8	525.3	527.3	528.2	532.0	531.5
7.5°	490.3	488.5	489.0	487.1	489.0	488.5	490.3	492.0	494.9	496.7	500.8
10°	468.9	466.3	464.1	462.2	464.1	466.3	468.9	469.9	473.9	475.8	479.9
12.5°	439.7	437.4	434.5	435.0	434.5	437.4	439.7	443.8	449.1	453.1	459.5
15°	398.2	394.6	388.9	389.6	388.9	394.6	398.2	401.3	406.6	415.7	419.9
17.5°	363.0	363.0	360.4	361.1	360.4	363.0	363.0	367.3	370.0	375.8	382.3
20°	344.9	343.3	343.5	342.7	343.5	343.3	344.9	349.9	352.7	356.8	364.0
22.5°	332.2	330.2	328.5	327.1	328.5	330.2	332.2	333.7	337.5	341.3	347.2
25°	310.9	309.5	307.4	306.9	307.4	309.5	310.9	313.1	315.0	320.0	323.6
27.5°	292.2	292.0	291.0	289.9	291.0	292.0	292.2	294.1	296.6	299.8	304.4
30°	281.3	280.8	280.3	279.6	280.3	280.8	281.3	283.3	285.1	287.7	291.3
32.5°	271.6	271.2	270.7	270.8	270.7	271.2	271.6	272.5	273.7	277.0	279.8
35°	257.6	257.4	256.9	256.7	256.9	257.4	257.6	258.6	259.3	260.2	262.7
37.5°	244.7	245.3	245.0	244.9	245.0	245.3	244.7	244.9	244.1	245.8	247.4
40°	235.7	235.9	236.4	236.1	236.4	235.9	235.7	235.9	235.9	235.9	237.3
42.5°	228.2	228.2	228.9	228.1	228.9	228.2	228.2	227.3	226.1	226.3	226.8
45°	214.9	216.3	216.0	216.0	216.0	216.3	214.9	213.2	213.0	212.0	212.0
47.5°	200.3	201.6	201.9	201.8	201.9	201.6	200.3	199.7	198.5	197.6	197.5
50°	190.8	190.3	191.0	190.8	191.0	190.3	190.8	189.6	187.8	187.8	187.3
52.5°	179.0	179.2	179.2	178.8	179.2	179.2	179.0	178.4	177.7	176.9	176.6
55°	161.1	161.4	160.9	161.1	160.9	161.4	161.1	160.9	160.9	160.4	160.9
57.5°	141.6	140.5	140.9	140.4	140.9	140.5	141.6	142.6	143.0	143.1	143.8
60°	127.6	125.7	125.2	124.3	125.2	125.7	127.6	130.0	131.0	131.5	132.2
62.5°	112.0	110.6	109.0	109.8	109.0	110.6	112.0	114.5	116.6	118.3	120.0
65°	91.1	90.1	89.4	90.4	89.4	90.1	91.1	93.0	94.9	98.7	102.3
67.5°	75.3	74.8	74.8	74.4	74.8	74.8	75.3	76.3	77.6	79.7	83.0
70°	67.2	66.4	66.4	65.9	66.4	66.4	67.2	67.2	68.4	69.3	71.7
72.5°	58.8	58.1	58.3	58.0	58.3	58.1	58.8	59.0	60.1	60.5	61.6
75°	43.5	42.3	42.3	42.5	42.3	42.3	43.5	44.9	46.2	48.3	48.8
77.5°	32.4	32.2	32.5	32.1	32.5	32.2	32.4	32.4	32.7	33.7	34.5
80°	26.6	26.3	26.1	26.8	26.1	26.3	26.6	26.6	26.8	27.0	27.3
82.5°	20.6	20.6	20.5	21.4	20.5	20.6	20.6	21.0	21.0	20.9	21.1
85°	12.4	11.9	12.4	11.9	12.4	11.9	12.4	12.2	12.4	12.2	12.4
87.5°	6.9	6.8	6.5	6.7	6.5	6.8	6.9	6.4	6.4	6.6	6.3
90°	12.1	12.6	12.1	12.1	12.1	12.6	12.1	11.5	11.5	10.9	10.4
92.5°	49.4	46.4	44.3	44.3	44.3	46.4	49.4	56.2	67.8	85.1	113.1
95°	176.3	158.4	148.0	140.6	148.0	158.4	176.3	204.5	260.3	337.6	426.9
97.5°	439.7	405.0	387.7	375.7	387.7	405.0	439.7	481.0	541.2	597.5	630.7
100°	585.3	550.2	532.9	528.3	532.9	550.2	585.3	635.4	678.0	706.3	694.8
102.5°	708.3	682.9	664.7	661.0	664.7	682.9	708.3	739.1	756.9	748.7	691.6
105°	826.7	822.0	814.0	810.5	814.0	822.0	826.7	825.6	801.9	744.9	645.2
107.5°	845.7	858.8	864.5	866.1	864.5	858.8	845.7	817.2	765.9	685.5	579.5
110°	827.3	851.4	861.8	867.0	861.8	851.4	827.3	786.4	723.0	639.4	539.8



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	787.6	816.9	831.4	839.8	831.4	816.9	787.6	741.1	677.8	598.8	510.8
115°	720.6	755.3	773.7	778.3	773.7	755.3	720.6	675.2	619.9	552.5	481.6
117.5°	664.7	693.7	712.4	716.0	712.4	693.7	664.7	625.8	579.0	525.9	467.3
120°	634.3	659.6	674.6	681.0	674.6	659.6	634.3	601.4	560.5	514.4	460.9
122.5°	612.6	634.3	646.9	653.3	646.9	634.3	612.6	584.8	549.0	507.1	455.3
125°	589.9	606.6	617.5	621.0	617.5	606.6	589.9	566.8	535.1	495.4	445.9
127.5°	574.6	589.5	598.6	602.1	598.6	589.5	574.6	551.4	521.4	481.7	434.3
130°	564.0	578.3	587.6	591.1	587.6	578.3	564.0	540.4	509.8	470.7	425.2
132.5°	550.2	566.4	575.1	578.7	575.1	566.4	550.2	526.9	496.4	458.2	415.5
135°	526.5	542.7	551.9	555.3	551.9	542.7	526.5	503.5	474.6	439.6	402.1
137.5°	498.9	514.8	522.4	526.5	522.4	514.8	498.9	477.4	451.3	421.7	390.0
140°	480.5	493.1	501.2	505.8	501.2	493.1	480.5	460.3	436.1	410.2	383.0
142.5°	461.5	473.3	480.5	483.6	480.5	473.3	461.5	443.7	422.7	400.5	376.7
145°	434.9	444.7	450.5	453.3	450.5	444.7	434.9	420.5	404.5	387.1	367.5
147.5°	412.7	421.1	425.5	426.6	425.5	421.1	412.7	402.1	389.4	375.6	360.0
150°	399.8	407.3	410.7	411.3	410.7	407.3	399.8	390.6	380.2	368.7	355.5
152.5°	388.7	394.9	396.9	397.5	396.9	394.9	388.7	380.9	372.3	361.7	350.3
155°	373.3	377.9	379.6	379.6	379.6	377.9	373.3	367.5	360.6	351.9	342.7
157.5°	359.5	362.9	364.0	364.0	364.0	362.9	359.5	355.1	349.5	342.3	334.6
160°	350.2	353.8	354.3	354.3	354.3	353.8	350.2	346.8	342.1	335.9	329.5
162.5°	341.5	345.0	345.6	345.1	345.6	345.0	341.5	339.0	334.8	329.8	324.5
165°	330.1	332.3	331.8	331.2	331.8	332.3	330.1	327.8	324.9	320.8	317.4
167.5°	319.4	320.8	320.7	320.3	320.7	320.8	319.4	318.2	316.5	313.3	310.6
170°	313.4	314.0	313.4	313.4	313.4	314.0	313.4	312.3	310.5	308.2	306.5
172.5°	307.4	308.0	307.4	306.5	307.4	308.0	307.4	306.7	305.5	304.1	302.8
175°	299.5	300.7	299.5	298.4	299.5	300.7	299.5	299.5	299.5	298.4	297.8
177.5°	295.1	295.5	294.6	293.7	294.6	295.5	295.1	295.5	295.1	295.1	294.6
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	567.3	568.8	571.8	575.2	578.1	580.6	582.5	585.2	587.6	591.1	594.3
5°	533.0	536.3	541.1	546.8	554.0	558.8	564.7	570.1	577.6	585.3	592.7
7.5°	502.8	506.4	513.5	521.4	529.9	537.8	544.8	554.1	564.2	575.4	587.8
10°	483.2	487.4	495.6	504.7	514.8	522.5	532.0	543.0	554.5	568.2	583.4
12.5°	465.6	469.6	479.6	488.9	499.3	507.8	518.9	530.0	545.3	560.1	577.4
15°	431.4	441.7	453.1	464.1	476.6	486.9	500.2	511.7	526.2	547.0	566.9
17.5°	393.3	404.2	418.6	435.6	452.2	464.9	478.5	492.7	510.1	531.3	554.2
20°	371.1	380.0	395.8	414.7	434.0	451.7	464.1	479.9	497.9	520.8	544.4
22.5°	354.6	362.0	374.4	393.2	414.1	434.6	450.6	466.2	485.9	509.0	534.7
25°	329.6	337.7	348.5	361.3	385.3	407.0	427.8	445.8	466.8	489.7	518.4
27.5°	308.8	315.9	325.8	339.2	355.3	379.2	404.5	424.9	446.5	471.1	499.8
30°	296.6	302.4	310.4	324.1	339.4	360.9	386.5	410.4	432.1	457.7	487.6
32.5°	283.8	289.9	297.8	308.6	325.1	343.2	368.7	394.9	418.0	444.1	473.4
35°	266.7	271.6	278.7	289.6	304.5	320.2	343.0	370.0	394.4	422.3	450.3
37.5°	249.4	255.1	260.7	270.5	282.7	299.6	318.2	345.9	372.8	398.4	425.7
40°	239.7	243.1	249.2	257.2	270.0	285.1	302.6	329.6	356.6	381.9	409.4
42.5°	228.8	232.6	237.8	245.7	257.2	272.0	289.0	312.4	340.5	365.1	390.1
45°	213.7	215.8	221.1	227.7	237.3	252.2	267.9	288.7	315.3	338.7	360.6
47.5°	198.3	200.3	203.5	209.6	220.4	232.3	247.0	265.7	288.9	312.4	330.9
50°	187.8	189.6	192.7	198.3	207.9	219.6	234.2	251.0	271.8	294.2	309.7
52.5°	177.3	178.2	181.2	187.6	195.7	207.2	220.3	235.7	255.1	273.8	289.5
55°	160.6	162.8	164.7	169.5	177.1	188.1	199.9	214.4	229.4	245.2	258.6
57.5°	143.2	145.5	148.2	152.5	158.5	168.7	179.3	191.1	204.0	217.0	228.3
60°	131.7	133.8	136.2	141.0	146.5	154.6	166.1	176.4	186.2	198.1	209.3
62.5°	120.4	122.6	125.3	129.2	134.4	142.2	151.8	160.7	170.9	181.3	189.7
65°	103.7	105.4	107.6	111.2	116.1	123.1	131.0	137.9	147.0	154.6	162.3
67.5°	85.4	88.7	91.4	94.3	98.6	105.0	110.8	117.4	123.6	129.3	136.2
70°	73.4	77.0	79.6	82.7	86.7	92.3	97.8	102.3	107.3	112.8	119.1
72.5°	63.2	66.0	68.2	71.4	75.1	80.2	85.3	89.1	93.2	96.9	103.0
75°	50.0	51.1	52.6	55.2	58.6	62.4	66.4	69.8	72.2	75.5	79.8
77.5°	35.9	38.2	39.2	41.0	43.4	45.7	48.5	51.3	53.6	54.7	58.1
80°	27.5	28.5	29.4	32.0	33.4	35.9	37.8	40.4	41.3	42.5	45.6
82.5°	21.4	21.9	22.5	23.2	24.1	26.5	28.4	30.1	31.0	31.4	33.8
85°	12.4	12.6	12.9	13.1	13.4	13.4	14.3	15.6	17.2	17.2	18.0
87.5°	6.2	6.5	6.3	5.9	6.2	5.6	5.7	5.6	6.1	6.3	6.7
90°	9.8	10.4	9.2	8.1	8.1	4.6	4.6	4.0	3.4	1.7	0.6
92.5°	152.2	182.7	160.0	116.3	71.7	42.4	30.4	22.0	14.9	9.6	6.6
95°	482.7	469.5	354.3	216.6	122.1	72.0	47.8	34.0	26.5	20.7	19.0
97.5°	606.5	494.5	331.6	194.7	116.7	78.2	57.9	45.9	39.1	34.1	34.1
100°	610.7	463.1	300.7	183.2	118.1	84.1	65.6	54.7	47.8	43.8	43.8
102.5°	576.0	424.0	279.9	180.0	122.7	91.9	74.4	63.9	57.5	53.9	53.0
105°	513.3	377.9	262.2	181.5	133.6	106.0	89.3	79.0	72.0	69.2	67.4
107.5°	462.6	352.1	258.9	190.0	146.4	121.1	104.6	94.7	87.4	84.4	83.3
110°	437.3	343.4	259.8	196.4	156.1	130.8	115.2	104.8	98.0	95.0	93.9



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	422.9	339.2	262.6	203.4	165.3	140.9	125.3	115.0	108.6	105.2	104.0
115°	409.6	337.0	267.9	214.3	179.8	156.7	141.2	130.2	124.4	120.4	118.7
117.5°	403.6	336.4	273.5	225.5	193.7	171.8	155.6	145.4	139.1	135.5	133.9
120°	400.4	336.4	277.7	233.3	203.4	181.5	165.3	155.5	149.2	145.2	144.0
122.5°	396.7	336.0	281.9	240.7	212.6	190.7	175.0	164.3	158.4	154.4	153.2
125°	390.6	335.3	288.0	251.8	225.2	204.5	188.3	177.4	171.1	167.6	165.3
127.5°	382.4	334.0	293.0	261.4	237.0	216.9	200.7	189.2	182.1	177.9	176.0
130°	377.3	333.6	296.7	267.3	244.8	225.2	208.5	197.6	188.9	184.3	182.1
132.5°	372.7	333.1	299.9	273.3	251.3	231.7	215.9	204.1	195.9	189.9	188.0
135°	365.8	332.3	304.8	281.1	260.3	241.4	226.4	214.3	204.5	198.7	196.4
137.5°	359.8	332.2	307.6	286.7	267.3	249.5	235.3	222.7	213.4	207.0	204.9
140°	356.6	331.8	309.9	290.3	272.0	254.6	240.8	228.7	218.9	212.6	210.9
142.5°	353.9	331.8	311.7	293.1	276.1	259.2	245.9	234.2	224.9	219.0	217.3
145°	349.1	330.6	312.9	296.1	280.5	265.6	252.9	242.0	233.9	228.1	226.4
147.5°	344.9	328.6	313.4	298.7	285.2	271.1	259.7	250.5	242.3	237.2	236.6
150°	341.6	327.2	313.4	300.1	287.5	274.8	263.9	255.2	248.3	243.7	243.1
152.5°	337.9	324.9	312.5	301.0	289.3	278.0	268.0	260.2	253.8	249.2	249.1
155°	332.3	321.4	311.0	301.8	292.1	282.3	273.7	267.3	261.6	258.1	257.5
157.5°	326.8	317.9	309.6	301.8	294.1	285.7	278.9	273.4	268.9	265.7	265.7
160°	322.7	315.1	308.2	301.8	295.0	288.0	281.7	277.1	273.1	270.7	270.7
162.5°	318.9	312.4	306.8	301.8	295.9	289.4	284.5	280.3	276.7	274.9	275.4
165°	312.9	308.2	304.2	300.7	296.1	290.9	287.5	284.6	281.7	280.5	280.5
167.5°	307.3	304.1	301.4	299.3	296.0	292.2	289.5	287.9	285.7	285.2	285.7
170°	303.6	301.2	299.5	298.4	295.5	292.7	290.9	289.7	288.0	287.5	288.0
172.5°	300.3	298.5	297.7	297.5	295.1	293.1	291.9	291.1	289.8	289.7	290.3
175°	296.7	295.5	295.5	296.1	294.4	293.3	293.3	292.7	292.1	292.1	292.7
177.5°	294.2	293.7	293.7	294.6	293.7	293.3	293.3	293.3	292.8	293.3	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	596.8	598.5	600.5	604.1	607.1	608.5	611.2	613.1	612.5	615.2	619.8
5°	599.2	605.6	613.1	620.7	629.2	636.4	642.2	647.9	652.5	657.9	666.1
7.5°	598.7	610.3	622.8	636.4	650.6	662.8	674.0	685.5	695.7	706.8	721.4
10°	597.2	612.6	628.1	646.0	664.0	681.0	696.2	710.5	724.2	738.7	757.2
12.5°	595.5	613.1	631.9	653.5	675.8	696.2	714.2	734.9	751.9	770.7	791.9
15°	587.9	611.6	637.2	665.1	692.0	719.4	744.0	769.3	793.0	815.5	842.2
17.5°	579.3	606.5	636.7	669.7	701.9	735.3	764.6	796.5	820.6	850.8	875.7
20°	572.2	601.6	633.8	670.9	707.4	744.5	776.8	809.3	836.5	866.9	898.4
22.5°	563.6	595.8	630.8	669.1	707.4	747.9	783.7	816.0	849.7	883.8	916.4
25°	549.7	583.2	620.3	662.3	706.3	747.6	785.9	826.0	862.3	899.4	928.6
27.5°	532.7	567.8	606.8	650.3	695.4	737.7	782.7	825.6	862.1	897.8	923.2
30°	519.1	556.1	593.7	637.6	684.5	729.9	778.2	821.0	859.5	891.5	905.8
32.5°	505.1	540.3	579.0	623.5	671.5	720.3	768.2	812.0	847.6	866.8	867.2
35°	480.9	513.8	554.0	597.7	647.0	700.0	748.5	791.5	813.3	815.0	791.5
37.5°	454.4	484.6	522.5	566.3	620.3	673.1	722.6	751.2	758.5	734.2	690.9
40°	435.5	463.4	500.0	544.9	598.4	653.0	698.1	719.1	711.6	672.1	623.8
42.5°	415.6	441.6	476.9	521.2	574.9	630.1	668.5	679.7	659.5	614.0	557.4
45°	383.1	407.0	441.9	486.7	538.3	589.9	619.0	613.3	579.6	525.5	462.2
47.5°	349.3	372.4	403.8	445.1	498.1	542.6	562.3	545.0	497.1	437.7	386.2
50°	327.0	350.6	379.5	419.0	467.3	510.3	522.9	496.7	443.3	386.3	338.9
52.5°	305.0	325.2	353.6	391.6	437.8	474.1	480.9	450.6	395.6	344.4	302.4
55°	271.6	289.9	313.8	349.6	389.6	420.4	416.8	377.9	327.9	284.2	251.2
57.5°	239.1	253.0	275.1	308.7	343.8	364.5	351.3	318.1	271.6	235.7	207.9
60°	217.7	230.7	251.2	280.5	311.4	323.2	312.1	276.1	239.2	206.5	183.1
62.5°	197.4	208.8	226.5	253.8	278.7	285.7	273.9	242.4	209.2	181.3	161.9
65°	168.0	178.5	193.6	213.0	230.1	233.5	225.9	193.6	168.5	145.1	131.7
67.5°	141.3	148.1	160.0	176.6	185.8	187.7	173.0	152.7	130.6	116.2	106.1
70°	123.3	128.2	139.1	148.1	155.6	155.8	142.2	125.9	109.0	97.3	89.9
72.5°	105.9	110.5	118.9	125.0	130.8	128.9	116.4	103.6	89.9	81.0	75.5
75°	81.7	85.8	90.1	93.0	93.0	90.6	81.5	71.9	64.0	58.8	57.2
77.5°	59.4	62.7	64.2	63.7	62.9	59.2	53.4	47.2	44.3	41.9	40.6
80°	46.7	48.1	48.5	47.4	45.8	41.6	37.8	35.1	32.5	31.5	31.1
82.5°	34.5	35.9	34.5	34.9	31.7	28.2	26.1	25.1	24.1	23.7	23.2
85°	18.4	18.2	17.7	16.5	14.3	13.8	13.6	13.4	12.9	13.1	12.6
87.5°	6.7	6.5	5.8	5.7	5.7	6.1	6.2	6.5	6.7	6.4	6.9
90°	1.7	3.4	4.0	4.6	4.6	8.1	8.1	9.2	10.4	9.8	10.4
92.5°	9.6	14.9	22.0	30.4	42.4	71.7	116.3	160.0	182.7	152.2	113.1
95°	20.7	26.5	34.0	47.8	72.0	122.1	216.6	354.3	469.5	482.7	426.9
97.5°	34.1	39.1	45.9	57.9	78.2	116.7	194.7	331.6	494.5	606.5	630.7
100°	43.8	47.8	54.7	65.6	84.1	118.1	183.2	300.7	463.1	610.7	694.8
102.5°	53.9	57.5	63.9	74.4	91.9	122.7	180.0	279.9	424.0	576.0	691.6
105°	69.2	72.0	79.0	89.3	106.0	133.6	181.5	262.2	377.9	513.3	645.2
107.5°	84.4	87.4	94.7	104.6	121.1	146.4	190.0	258.9	352.1	462.6	579.5
110°	95.0	98.0	104.8	115.2	130.8	156.1	196.4	259.8	343.4	437.3	539.8



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	105.2	108.6	115.0	125.3	140.9	165.3	203.4	262.6	339.2	422.9	510.8
115°	120.4	124.4	130.2	141.2	156.7	179.8	214.3	267.9	337.0	409.6	481.6
117.5°	135.5	139.1	145.4	155.6	171.8	193.7	225.5	273.5	336.4	403.6	467.3
120°	145.2	149.2	155.5	165.3	181.5	203.4	233.3	277.7	336.4	400.4	460.9
122.5°	154.4	158.4	164.3	175.0	190.7	212.6	240.7	281.9	336.0	396.7	455.3
125°	167.6	171.1	177.4	188.3	204.5	225.2	251.8	288.0	335.3	390.6	445.9
127.5°	177.9	182.1	189.2	200.7	216.9	237.0	261.4	293.0	334.0	382.4	434.3
130°	184.3	188.9	197.6	208.5	225.2	244.8	267.3	296.7	333.6	377.3	425.2
132.5°	189.9	195.9	204.1	215.9	231.7	251.3	273.3	299.9	333.1	372.7	415.5
135°	198.7	204.5	214.3	226.4	241.4	260.3	281.1	304.8	332.3	365.8	402.1
137.5°	207.0	213.4	222.7	235.3	249.5	267.3	286.7	307.6	332.2	359.8	390.0
140°	212.6	218.9	228.7	240.8	254.6	272.0	290.3	309.9	331.8	356.6	383.0
142.5°	219.0	224.9	234.2	245.9	259.2	276.1	293.1	311.7	331.8	353.9	376.7
145°	228.1	233.9	242.0	252.9	265.6	280.5	296.1	312.9	330.6	349.1	367.5
147.5°	237.2	242.3	250.5	259.7	271.1	285.2	298.7	313.4	328.6	344.9	360.0
150°	243.7	248.3	255.2	263.9	274.8	287.5	300.1	313.4	327.2	341.6	355.5
152.5°	249.2	253.8	260.2	268.0	278.0	289.3	301.0	312.5	324.9	337.9	350.3
155°	258.1	261.6	267.3	273.7	282.3	292.1	301.8	311.0	321.4	332.3	342.7
157.5°	265.7	268.9	273.4	278.9	285.7	294.1	301.8	309.6	317.9	326.8	334.6
160°	270.7	273.1	277.1	281.7	288.0	295.0	301.8	308.2	315.1	322.7	329.5
162.5°	274.9	276.7	280.3	284.5	289.4	295.9	301.8	306.8	312.4	318.9	324.5
165°	280.5	281.7	284.6	287.5	290.9	296.1	300.7	304.2	308.2	312.9	317.4
167.5°	285.2	285.7	287.9	289.5	292.2	296.0	299.3	301.4	304.1	307.3	310.6
170°	287.5	288.0	289.7	290.9	292.7	295.5	298.4	299.5	301.2	303.6	306.5
172.5°	289.7	289.8	291.1	291.9	293.1	295.1	297.5	297.7	298.5	300.3	302.8
175°	292.1	292.1	292.7	293.3	293.3	294.4	296.1	295.5	295.5	296.7	297.8
177.5°	293.3	292.8	293.3	293.3	293.3	293.7	294.6	293.7	293.7	294.2	294.6
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	593.2	593.2	593.2	593.2	593.2	593.2	593.2
2.5°	622.3	623.0	623.6	625.5	625.7	627.4	625.7
5°	673.8	677.1	682.4	687.6	688.1	691.5	685.5
7.5°	731.4	739.2	744.1	752.6	755.9	758.0	754.6
10°	771.2	778.4	791.1	797.3	803.5	804.5	801.6
12.5°	809.7	821.0	831.0	842.8	842.5	850.9	847.9
15°	860.9	872.6	886.5	899.6	904.3	904.3	908.2
17.5°	897.4	918.9	933.2	943.5	954.8	956.7	955.4
20°	922.1	945.2	960.6	973.9	981.6	983.7	983.7
22.5°	940.4	960.2	975.1	987.1	993.4	995.9	995.2
25°	953.1	970.1	979.2	982.8	984.4	984.0	979.5
27.5°	935.7	934.9	929.3	918.3	910.0	904.9	899.2
30°	902.5	890.0	875.7	859.9	839.6	824.0	819.3
32.5°	852.9	825.1	800.7	774.5	752.7	737.1	730.5
35°	757.2	713.0	676.8	645.3	622.4	608.0	603.2
37.5°	643.5	600.7	556.0	525.4	506.3	491.9	486.6
40°	571.2	524.6	485.6	457.0	437.4	423.2	423.0
42.5°	505.2	460.7	424.0	403.4	382.3	372.9	372.9
45°	413.7	378.1	347.0	330.7	318.1	310.4	308.3
47.5°	342.5	313.1	292.4	279.4	269.1	264.3	261.1
50°	302.6	276.8	260.2	249.0	243.3	237.1	236.6
52.5°	269.3	248.4	235.6	226.5	219.2	215.5	215.6
55°	226.3	209.8	200.8	193.8	188.1	185.2	184.0
57.5°	190.7	178.3	171.7	165.3	162.9	160.7	160.1
60°	168.5	160.2	153.9	148.9	145.3	144.6	144.3
62.5°	150.2	141.4	137.1	133.2	130.6	129.5	129.1
65°	123.8	117.3	113.5	110.4	109.5	107.8	107.6
67.5°	99.8	95.9	93.4	91.3	90.0	89.9	89.9
70°	85.1	82.9	80.8	79.6	78.9	78.4	78.4
72.5°	72.5	70.9	69.1	68.5	68.4	67.9	67.7
75°	55.2	53.5	53.8	52.6	51.6	50.4	49.7
77.5°	39.2	38.0	37.7	37.6	36.8	36.7	37.0
80°	30.4	29.2	28.9	29.2	28.9	28.2	28.2
82.5°	23.1	22.1	21.8	21.7	21.5	21.7	21.3
85°	12.4	11.9	11.9	11.9	12.4	12.2	11.9
87.5°	6.6	6.5	6.7	6.7	6.8	6.5	6.7
90°	10.9	11.5	11.5	12.1	12.6	12.1	12.1
92.5°	85.1	67.8	56.2	49.4	46.4	44.3	44.3
95°	337.6	260.3	204.5	176.3	158.4	148.0	140.6
97.5°	597.5	541.2	481.0	439.7	405.0	387.7	375.7
100°	706.3	678.0	635.4	585.3	550.2	532.9	528.3
102.5°	748.7	756.9	739.1	708.3	682.9	664.7	661.0
105°	744.9	801.9	825.6	826.7	822.0	814.0	810.5
107.5°	685.5	765.9	817.2	845.7	858.8	864.5	866.1
110°	639.4	723.0	786.4	827.3	851.4	861.8	867.0



TEST NUMBER: P332873-840

CATALOG NUMBER: S124RDIP-S350D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	598.8	677.8	741.1	787.6	816.9	831.4	839.8
115°	552.5	619.9	675.2	720.6	755.3	773.7	778.3
117.5°	525.9	579.0	625.8	664.7	693.7	712.4	716.0
120°	514.4	560.5	601.4	634.3	659.6	674.6	681.0
122.5°	507.1	549.0	584.8	612.6	634.3	646.9	653.3
125°	495.4	535.1	566.8	589.9	606.6	617.5	621.0
127.5°	481.7	521.4	551.4	574.6	589.5	598.6	602.1
130°	470.7	509.8	540.4	564.0	578.3	587.6	591.1
132.5°	458.2	496.4	526.9	550.2	566.4	575.1	578.7
135°	439.6	474.6	503.5	526.5	542.7	551.9	555.3
137.5°	421.7	451.3	477.4	498.9	514.8	522.4	526.5
140°	410.2	436.1	460.3	480.5	493.1	501.2	505.8
142.5°	400.5	422.7	443.7	461.5	473.3	480.5	483.6
145°	387.1	404.5	420.5	434.9	444.7	450.5	453.3
147.5°	375.6	389.4	402.1	412.7	421.1	425.5	426.6
150°	368.7	380.2	390.6	399.8	407.3	410.7	411.3
152.5°	361.7	372.3	380.9	388.7	394.9	396.9	397.5
155°	351.9	360.6	367.5	373.3	377.9	379.6	379.6
157.5°	342.3	349.5	355.1	359.5	362.9	364.0	364.0
160°	335.9	342.1	346.8	350.2	353.8	354.3	354.3
162.5°	329.8	334.8	339.0	341.5	345.0	345.6	345.1
165°	320.8	324.9	327.8	330.1	332.3	331.8	331.2
167.5°	313.3	316.5	318.2	319.4	320.8	320.7	320.3
170°	308.2	310.5	312.3	313.4	314.0	313.4	313.4
172.5°	304.1	305.5	306.7	307.4	308.0	307.4	306.5
175°	298.4	299.5	299.5	299.5	300.7	299.5	298.4
177.5°	295.1	295.1	295.5	295.1	295.5	294.6	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3

(END OF REPORT)