

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332920-840

Luminaire Tested: **S124RDIP-S575D1205U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332920-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D1205U840-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6678.6 lumens
Efficiency: N/A
Efficacy: 135.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27				
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	31	30	28	23				
4	73	62	55	49	66	57	51	45	47	42	38	37	34	31	28	26	24	20				
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18				
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14				
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13				
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	11				
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7873	7873	7873	7873
5°	9132	7896	6980	7896
10°	10803	7862	6229	7862
15°	12479	7789	5353	7789
20°	13894	7689	4840	7689
25°	14343	7591	4494	7591
30°	12557	7471	4285	7471
35°	9773	7295	4159	7295
40°	7330	7093	4091	7093
45°	5787	6769	4055	6769
50°	4886	6395	3939	6395
55°	4259	5985	3727	5985
60°	3831	5557	3299	5557
65°	3377	5096	2839	5096
70°	3043	4619	2561	4619
75°	2548	4095	2183	4095
80°	2157	3487	2046	3487
85°	1825	2732	1825	2732



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.5	1.4
10°-20°	285.0	4.3
20°-30°	445.8	6.7
30°-40°	495.6	7.4
40°-50°	439.7	6.6
50°-60°	342.6	5.1
60°-70°	224.3	3.4
70°-80°	110.3	1.7
80°-90°	31.7	0.5
90°-100°	100.1	1.5
100°-110°	296.4	4.4
110°-120°	503.1	7.5
120°-130°	663.4	9.9
130°-140°	745.0	11.2
140°-150°	732.1	11.0
150°-160°	615.7	9.2
160°-170°	409.7	6.1
170°-180°	143.5	2.1
0°-30°	825.3	12.4
0°-40°	1320.9	19.8
0°-60°	2103.3	31.5
0°-90°	2469.7	37.0
90°-120°	899.6	13.5
90°-150°	3040.1	45.5
90°-180°	4209.0	63.0
0°-180°	6678.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	975	975	975	975	975	
5°	1127	974	861	974	1127	114
15°	1493	932	640	932	1493	425
25°	1610	852	504	852	1610	714
35°	992	740	422	740	992	622
45°	507	593	355	593	507	401
55°	303	425	265	425	303	275
65°	177	267	149	267	177	178
75°	82	131	70	131	82	90
85°	20	30	20	30	20	23
90°	35	4	35	4	35	19
95°	93	70	93	70	93	97
105°	286	273	286	273	286	302
115°	507	512	507	512	507	501
125°	739	745	739	745	739	659
135°	962	961	962	961	962	743
145°	1169	1167	1169	1167	1169	731
155°	1336	1338	1336	1338	1336	615
165°	1452	1456	1452	1456	1452	409
175°	1508	1515	1508	1515	1508	143
180°	1517	1517	1517	1517	1517	



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1028.6	1031.5	1028.6	1028.3	1025.2	1024.3	1023.0	1019.0	1011.4	1006.9	1007.9
5°	1126.9	1136.7	1131.3	1130.4	1121.8	1113.2	1107.6	1095.1	1081.7	1072.7	1065.2
7.5°	1240.5	1246.2	1242.7	1237.2	1223.2	1215.3	1202.5	1186.0	1162.1	1143.7	1127.0
10°	1317.9	1322.5	1321.0	1310.8	1300.6	1279.7	1268.0	1244.8	1214.5	1190.5	1168.1
12.5°	1393.9	1399.0	1385.1	1385.6	1366.2	1349.8	1331.1	1302.0	1267.0	1236.1	1208.1
15°	1493.1	1486.8	1486.8	1478.9	1457.3	1434.5	1415.3	1384.6	1340.6	1303.7	1264.9
17.5°	1570.7	1573.0	1569.7	1551.2	1534.2	1510.7	1475.3	1439.6	1398.7	1349.1	1309.4
20°	1617.3	1617.3	1613.8	1601.1	1579.1	1554.0	1515.9	1477.0	1425.1	1375.2	1330.4
22.5°	1636.1	1637.4	1633.3	1622.9	1603.1	1578.5	1546.1	1506.5	1453.1	1396.9	1341.4
25°	1610.2	1617.6	1618.4	1615.7	1609.8	1594.9	1567.0	1526.5	1478.5	1417.6	1358.0
27.5°	1478.3	1487.7	1496.0	1509.5	1527.6	1537.1	1538.3	1517.7	1475.9	1417.3	1357.3
30°	1347.0	1354.7	1380.3	1413.7	1439.7	1463.2	1483.7	1489.1	1465.6	1412.9	1349.7
32.5°	1201.0	1211.7	1237.3	1273.2	1316.5	1356.3	1402.3	1425.6	1425.0	1393.4	1334.9
35°	991.7	999.6	1023.2	1060.9	1112.8	1172.0	1244.8	1301.3	1339.9	1337.1	1301.3
37.5°	799.8	808.7	832.5	863.8	914.1	987.5	1057.9	1135.9	1207.1	1247.1	1235.1
40°	695.5	695.9	719.0	751.2	798.4	862.4	939.1	1025.5	1104.9	1169.7	1182.2
42.5°	613.1	613.2	628.5	663.3	697.2	757.5	830.6	916.5	1009.4	1084.2	1117.5
45°	506.9	510.4	523.0	543.8	570.5	621.6	680.1	759.9	864.0	952.8	1008.2
47.5°	429.2	434.4	442.4	459.4	480.7	514.7	563.1	634.8	719.5	817.2	896.1
50°	389.0	389.8	400.0	409.4	427.9	455.0	497.5	557.1	635.0	728.8	816.5
52.5°	354.5	354.3	360.4	372.3	387.4	408.5	442.7	497.2	566.1	650.3	740.7
55°	302.6	304.5	309.2	318.6	330.0	345.0	372.1	412.9	467.2	539.1	621.2
57.5°	263.1	264.1	267.8	271.9	282.3	293.2	313.5	341.8	387.6	446.5	523.0
60°	237.3	237.7	238.9	244.8	253.1	263.3	277.0	300.9	339.5	393.3	453.8
62.5°	212.2	212.9	214.7	219.0	225.4	232.5	246.8	266.1	298.0	344.0	398.5
65°	176.8	177.2	180.0	181.6	186.6	192.9	203.5	216.5	238.5	277.0	318.3
67.5°	147.7	147.7	147.8	150.1	153.6	157.7	164.1	174.5	191.1	214.7	251.1
70°	128.9	128.9	129.7	130.9	132.8	136.3	139.9	147.7	160.0	179.2	207.0
72.5°	111.3	111.6	112.4	112.6	113.6	116.5	119.2	124.1	133.2	147.7	170.3
75°	81.7	82.9	84.8	86.4	88.4	88.1	90.8	93.9	96.6	105.3	118.3
77.5°	60.8	60.2	60.4	61.8	62.0	62.4	64.3	66.8	68.9	72.9	77.6
80°	46.4	46.4	47.6	48.0	47.6	48.0	49.9	51.1	51.9	53.4	57.8
82.5°	35.0	35.6	35.2	35.6	36.0	36.4	38.0	38.2	39.0	39.6	41.4
85°	19.7	20.0	20.4	19.7	19.7	19.7	20.4	20.8	21.6	21.2	22.0
87.5°	13.9	13.5	13.7	13.6	13.8	13.3	13.3	13.6	12.7	12.7	12.3
90°	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0	27.4	25.9	23.7
92.5°	52.1	51.8	51.5	51.2	50.8	50.2	49.3	48.4	47.4	46.5	45.0
95°	92.7	92.7	92.7	92.7	92.7	92.3	91.5	90.7	90.0	89.2	87.4
97.5°	145.2	145.2	145.2	145.2	145.2	144.8	143.8	142.9	142.0	141.0	138.9
100°	181.9	181.9	181.9	181.9	181.9	181.6	181.1	180.6	180.1	179.6	177.1
102.5°	223.2	223.0	222.8	222.6	222.3	221.9	221.2	220.4	219.6	218.9	216.8
105°	286.3	285.5	284.7	284.0	283.2	282.4	281.6	280.8	280.0	279.2	278.2
107.5°	347.8	347.8	347.9	347.9	348.0	347.6	346.9	346.2	345.5	344.7	344.6
110°	391.8	391.1	390.3	389.5	388.7	388.6	389.1	389.6	390.2	390.7	390.9



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	437.0	436.8	436.6	436.5	436.3	436.3	436.4	436.5	436.6	436.7	437.2
115°	506.9	507.2	507.4	507.7	507.9	508.2	508.4	508.7	509.0	509.2	509.7
117.5°	573.5	574.0	574.5	575.0	575.6	576.2	577.1	578.0	579.0	579.9	580.2
120°	624.2	623.7	623.1	622.6	622.1	622.5	623.8	625.1	626.4	627.7	628.4
122.5°	666.4	667.3	668.3	669.2	670.1	671.1	672.0	672.9	673.8	674.6	675.0
125°	739.1	739.6	740.2	740.7	741.2	741.7	742.3	742.8	743.4	743.9	744.1
127.5°	806.5	806.9	807.3	807.8	808.2	808.6	809.2	809.7	810.2	810.7	811.1
130°	850.6	851.6	852.7	853.7	854.7	855.6	856.1	856.6	857.2	857.7	857.7
132.5°	897.6	898.0	898.4	898.8	899.2	899.7	900.2	900.7	901.2	901.8	902.0
135°	962.1	962.8	963.6	964.4	965.2	965.8	966.3	966.9	967.5	968.0	968.0
137.5°	1029.9	1029.8	1029.6	1029.5	1029.3	1029.6	1030.2	1030.9	1031.6	1032.2	1031.8
140°	1071.2	1071.5	1071.7	1072.0	1072.3	1072.5	1072.8	1073.0	1073.3	1073.5	1073.5
142.5°	1112.5	1112.6	1112.6	1112.7	1112.7	1112.8	1112.8	1112.9	1112.9	1113.0	1113.2
145°	1168.6	1169.3	1170.1	1170.9	1171.6	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0
147.5°	1225.4	1225.6	1225.9	1226.2	1226.4	1226.6	1226.9	1227.1	1227.3	1227.5	1227.7
150°	1260.1	1260.3	1260.6	1260.8	1261.1	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1292.0	1292.6	1293.3	1294.0	1294.7	1294.7	1294.1	1293.4	1292.8	1292.2	1292.0
155°	1336.4	1337.4	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4	1336.6
157.5°	1376.0	1376.8	1377.8	1378.7	1379.6	1379.6	1378.8	1378.1	1377.3	1376.4	1376.5
160°	1398.6	1399.9	1401.1	1402.4	1403.7	1404.0	1403.2	1402.4	1401.7	1400.9	1401.1
162.5°	1422.0	1423.3	1424.6	1425.9	1427.2	1427.1	1425.7	1424.3	1422.9	1421.5	1421.8
165°	1452.5	1453.5	1454.6	1455.6	1456.6	1456.4	1454.8	1453.3	1451.7	1450.2	1450.7
167.5°	1474.3	1475.9	1477.5	1479.1	1480.8	1480.8	1479.3	1477.6	1476.1	1474.5	1474.5
170°	1486.5	1488.3	1490.2	1492.0	1493.8	1494.0	1492.4	1490.9	1489.2	1487.7	1487.4
172.5°	1496.8	1498.6	1500.5	1502.3	1504.2	1504.2	1502.4	1500.7	1498.8	1497.1	1497.0
175°	1507.6	1509.4	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6	1507.9
177.5°	1513.3	1514.9	1516.6	1518.2	1519.9	1520.0	1518.6	1517.1	1515.7	1514.2	1514.2
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1004.8	1000.4	998.2	993.1	987.1	984.0	981.2	977.1	971.8	966.1	962.0
5°	1055.8	1046.3	1034.5	1020.4	1007.8	995.6	985.0	974.4	962.3	949.7	937.2
7.5°	1108.1	1089.5	1069.5	1046.3	1023.8	1003.3	984.4	966.3	945.9	927.6	910.9
10°	1144.6	1119.4	1091.6	1062.1	1032.6	1007.0	981.9	959.1	933.9	911.6	892.7
12.5°	1174.2	1144.6	1111.1	1074.3	1038.8	1007.9	979.1	949.4	920.8	896.5	871.3
15°	1223.1	1182.7	1137.5	1093.5	1047.5	1005.5	966.5	932.0	899.4	865.3	841.2
17.5°	1256.9	1208.8	1154.0	1101.1	1046.7	997.1	952.3	911.1	873.4	838.6	810.0
20°	1277.0	1224.0	1163.1	1102.9	1042.0	989.0	940.7	895.0	856.2	818.5	789.0
22.5°	1288.3	1229.6	1163.1	1100.0	1037.0	979.6	926.6	879.1	836.7	799.0	766.4
25°	1291.9	1229.0	1161.0	1088.7	1019.7	958.8	903.7	852.2	805.1	767.4	732.8
27.5°	1286.9	1212.8	1143.3	1069.0	997.7	933.5	875.8	821.6	774.5	734.0	698.5
30°	1279.3	1200.0	1125.3	1048.3	976.0	914.3	853.4	801.5	752.5	710.4	674.7
32.5°	1263.0	1184.3	1104.0	1025.0	951.8	888.3	830.5	778.3	730.1	687.1	649.1
35°	1230.6	1150.8	1063.6	982.7	910.8	844.8	790.5	740.2	694.3	648.3	608.2
37.5°	1187.9	1106.5	1019.7	931.1	859.1	796.8	747.0	699.8	654.9	613.0	568.6
40°	1147.7	1073.5	983.9	895.9	822.0	761.8	715.9	673.1	627.9	586.2	541.8
42.5°	1099.0	1035.7	945.2	856.9	784.0	726.0	683.2	641.4	600.3	559.9	513.5
45°	1017.6	969.8	884.8	800.0	726.5	669.1	629.9	592.9	556.7	518.3	474.6
47.5°	924.4	892.0	818.8	731.8	663.9	612.3	574.3	544.1	513.5	475.0	436.8
50°	859.7	838.9	768.2	688.8	624.0	576.4	537.6	509.2	483.7	446.8	412.5
52.5°	790.5	779.5	719.7	643.8	581.2	534.6	501.4	475.9	450.1	419.4	387.4
55°	685.3	691.2	640.5	574.8	515.9	476.7	446.4	425.2	403.1	377.2	352.4
57.5°	577.5	599.2	565.1	507.5	452.2	416.0	393.1	375.3	356.9	335.3	314.2
60°	513.1	531.2	512.0	461.3	412.9	379.2	358.0	344.2	325.7	306.1	289.9
62.5°	450.3	469.6	458.2	417.3	372.4	343.4	324.7	311.8	298.1	280.9	264.2
65°	371.3	383.8	378.4	350.1	318.3	293.5	276.2	266.8	254.2	241.7	226.7
67.5°	284.4	308.7	305.5	290.4	263.0	243.6	232.3	224.0	212.5	203.2	193.0
70°	233.8	256.2	255.8	243.6	228.6	210.6	202.8	195.7	185.4	176.4	168.1
72.5°	191.4	211.9	214.9	205.6	195.4	181.7	174.1	169.3	159.4	153.2	146.4
75°	134.0	149.0	152.9	152.9	148.1	141.1	134.4	131.3	124.1	118.7	114.7
77.5°	87.9	97.3	103.4	104.8	105.5	103.2	97.7	95.4	90.1	88.1	84.3
80°	62.1	68.4	75.4	77.8	79.8	79.0	76.6	75.0	70.0	68.0	66.4
82.5°	42.9	46.4	52.2	57.4	56.9	58.9	56.9	55.5	51.7	51.0	49.4
85°	22.4	22.8	23.5	27.1	29.1	29.9	30.3	29.5	28.3	28.3	25.5
87.5°	11.9	11.1	11.3	10.9	10.6	11.3	11.6	11.4	11.0	10.6	10.3
90°	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5	6.4	9.3	12.1
92.5°	43.5	42.1	40.6	38.3	34.9	31.7	28.4	25.1	28.4	31.7	34.9
95°	85.5	83.7	81.9	79.8	77.5	75.1	72.7	70.4	72.7	75.1	77.5
97.5°	136.7	134.6	132.5	130.5	128.6	126.7	124.8	123.0	124.8	126.7	128.6
100°	174.8	172.5	170.2	168.4	167.3	166.3	165.3	164.3	165.3	166.3	167.3
102.5°	214.7	212.5	210.4	209.1	208.6	208.2	207.8	207.4	207.8	208.2	208.6
105°	277.1	276.1	275.1	274.4	274.2	273.9	273.7	273.4	273.7	273.9	274.2
107.5°	344.4	344.3	344.1	343.9	343.6	343.3	343.0	342.5	343.0	343.3	343.6
110°	391.2	391.5	391.7	391.6	391.1	390.5	390.0	389.5	390.0	390.5	391.1



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	438.1	438.6	438.8	438.7	438.6	438.5	438.3	438.5	438.6	438.7
115°	510.3	510.8	511.3	511.5	511.5	511.5	511.5	511.5	511.5	511.5	511.5
117.5°	580.6	580.9	581.3	581.4	581.2	581.0	580.8	580.6	580.8	581.0	581.2
120°	629.2	630.1	630.9	630.7	629.7	628.6	627.5	626.5	627.5	628.6	629.7
122.5°	675.4	675.7	676.1	676.1	675.6	675.2	674.8	674.4	674.8	675.2	675.6
125°	744.4	744.7	744.9	745.0	745.0	745.0	745.0	745.0	745.0	745.0	745.0
127.5°	811.5	811.9	812.4	812.2	811.4	810.6	809.9	809.1	809.9	810.6	811.4
130°	857.7	857.7	857.7	857.3	856.5	855.7	855.0	854.1	855.0	855.7	856.5
132.5°	902.2	902.4	902.6	902.4	901.8	901.3	900.7	900.1	900.7	901.3	901.8
135°	968.0	968.0	968.0	967.1	965.6	964.0	962.5	960.9	962.5	964.0	965.6
137.5°	1031.4	1031.0	1030.6	1030.0	1029.3	1028.5	1027.8	1027.0	1027.8	1028.5	1029.3
140°	1073.5	1073.5	1073.5	1073.3	1072.8	1072.3	1071.7	1071.2	1071.7	1072.3	1072.8
142.5°	1113.4	1113.6	1113.8	1113.7	1113.1	1112.6	1112.1	1111.6	1112.1	1112.6	1113.1
145°	1172.8	1172.5	1172.3	1171.5	1170.5	1169.5	1168.4	1167.4	1168.4	1169.5	1170.5
147.5°	1227.9	1228.1	1228.3	1227.8	1226.5	1225.3	1224.1	1222.7	1224.1	1225.3	1226.5
150°	1261.2	1261.2	1261.2	1260.7	1259.7	1258.7	1257.6	1256.6	1257.6	1258.7	1259.7
152.5°	1291.8	1291.6	1291.4	1291.0	1290.3	1289.7	1289.1	1288.5	1289.1	1289.7	1290.3
155°	1336.9	1337.2	1337.4	1337.5	1337.5	1337.5	1337.5	1337.5	1337.5	1337.5	1337.5
157.5°	1376.5	1376.6	1376.6	1377.0	1377.5	1377.9	1378.4	1378.8	1378.4	1377.9	1377.5
160°	1401.4	1401.7	1401.9	1402.2	1402.4	1402.7	1403.0	1403.2	1403.0	1402.7	1402.4
162.5°	1422.1	1422.3	1422.6	1423.0	1423.7	1424.4	1425.0	1425.7	1425.0	1424.4	1423.7
165°	1451.2	1451.7	1452.2	1452.9	1453.7	1454.4	1455.2	1456.0	1455.2	1454.4	1453.7
167.5°	1474.4	1474.4	1474.3	1474.9	1475.9	1477.0	1478.1	1479.3	1478.1	1477.0	1475.9
170°	1487.1	1486.9	1486.6	1487.1	1488.4	1489.8	1491.1	1492.4	1491.1	1489.8	1488.4
172.5°	1497.0	1496.9	1496.8	1497.4	1498.4	1499.5	1500.7	1501.8	1500.7	1499.5	1498.4
175°	1508.1	1508.4	1508.6	1509.4	1510.8	1512.1	1513.4	1514.7	1513.4	1512.1	1510.8
177.5°	1514.2	1514.2	1514.2	1514.7	1515.8	1516.8	1517.8	1518.9	1517.8	1516.8	1515.8
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	957.7	954.5	950.4	945.6	940.0	935.0	932.8	934.6	935.6	933.1	932.8
5°	928.5	918.7	910.8	899.0	889.6	881.7	876.2	873.8	874.6	868.4	866.8
7.5°	895.6	884.0	871.2	857.2	844.1	832.6	826.6	823.2	816.6	813.7	808.9
10°	874.6	858.9	846.4	829.8	815.0	801.1	794.5	789.0	782.3	779.1	772.4
12.5°	852.9	834.8	820.9	803.8	788.5	771.9	765.6	755.4	744.9	738.3	729.7
15°	822.3	800.4	783.5	763.1	745.0	726.1	709.2	690.3	683.3	668.3	659.7
17.5°	786.6	764.3	743.4	716.0	688.1	664.7	646.6	628.6	617.7	608.2	603.8
20°	763.1	742.7	713.6	681.8	650.7	624.7	610.2	598.4	586.6	580.0	575.2
22.5°	740.7	714.7	680.9	646.5	615.5	595.2	582.9	570.8	561.2	554.8	548.6
25°	703.4	669.1	633.4	594.1	572.9	555.2	541.8	532.0	526.1	517.9	514.7
27.5°	664.9	623.5	584.0	557.6	535.5	519.4	507.8	500.4	492.9	487.6	483.5
30°	635.3	593.3	558.0	532.8	510.4	497.1	487.6	479.0	473.1	468.8	465.6
32.5°	606.1	564.1	534.3	507.4	489.7	476.7	466.6	460.1	455.4	449.9	448.0
35°	563.8	526.5	500.6	476.3	458.2	446.4	438.5	431.8	427.9	426.4	425.2
37.5°	523.2	492.6	464.7	444.7	428.7	419.4	410.1	406.9	404.1	401.3	402.6
40°	497.5	468.8	444.0	422.8	409.8	399.6	394.0	390.2	387.8	387.8	387.8
42.5°	475.1	447.1	422.9	403.9	390.9	382.3	376.2	372.8	372.1	371.7	373.7
45°	440.5	414.5	390.2	374.5	363.5	354.8	351.2	348.5	348.5	350.1	350.5
47.5°	406.2	381.8	362.2	344.7	334.6	329.2	326.1	324.7	324.9	326.4	328.2
50°	385.1	361.1	341.8	326.1	316.7	311.5	308.8	308.0	308.8	308.8	311.5
52.5°	362.1	340.6	321.7	308.5	297.8	293.1	291.5	290.4	290.9	292.2	293.4
55°	328.5	309.2	291.1	278.6	270.7	267.6	264.1	264.5	263.7	264.5	264.5
57.5°	294.8	277.5	260.6	250.6	243.8	239.2	235.4	236.4	235.3	235.1	234.5
60°	273.1	254.2	240.9	231.9	224.0	220.0	216.5	217.3	216.1	215.3	213.8
62.5°	249.5	233.8	221.1	212.4	206.0	201.5	197.9	197.1	194.4	191.8	188.2
65°	215.3	202.4	191.0	182.7	176.8	173.3	170.6	168.1	162.3	156.0	152.9
67.5°	182.1	172.7	162.1	155.1	150.4	145.7	140.5	136.4	130.9	127.4	125.5
70°	160.7	151.7	142.6	135.9	130.9	126.5	120.6	117.9	113.9	112.4	110.4
72.5°	140.3	131.9	123.4	117.4	112.0	108.6	104.0	101.2	99.5	98.9	96.8
75°	109.3	102.6	96.2	90.8	86.4	84.1	82.1	80.2	79.4	75.8	73.8
77.5°	79.7	75.2	71.4	67.5	64.3	62.8	59.0	56.8	55.4	53.7	53.3
80°	62.1	59.0	55.0	52.6	48.4	46.8	45.1	44.8	44.4	44.0	43.6
82.5°	46.7	43.5	39.6	38.2	37.1	36.1	35.1	34.7	34.3	34.5	34.5
85°	23.5	22.0	22.0	21.6	21.2	20.8	20.4	20.4	20.0	20.4	20.0
87.5°	10.9	11.0	11.4	11.2	12.0	12.4	12.4	12.7	13.3	13.0	13.2
90°	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0	30.5	32.1	33.1
92.5°	38.3	40.6	42.1	43.5	45.0	46.5	47.4	48.4	49.3	50.2	50.8
95°	79.8	81.9	83.7	85.5	87.4	89.2	90.0	90.7	91.5	92.3	92.7
97.5°	130.5	132.5	134.6	136.7	138.9	141.0	142.0	142.9	143.8	144.8	145.2
100°	168.4	170.2	172.5	174.8	177.1	179.6	180.1	180.6	181.1	181.6	181.9
102.5°	209.1	210.4	212.5	214.7	216.8	218.9	219.6	220.4	221.2	221.9	222.3
105°	274.4	275.1	276.1	277.1	278.2	279.2	280.0	280.8	281.6	282.4	283.2
107.5°	343.9	344.1	344.3	344.4	344.6	344.7	345.5	346.2	346.9	347.6	348.0
110°	391.6	391.7	391.5	391.2	390.9	390.7	390.2	389.6	389.1	388.6	388.7



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	438.8	438.6	438.1	437.7	437.2	436.7	436.6	436.5	436.4	436.3	436.3
115°	511.5	511.3	510.8	510.3	509.7	509.2	509.0	508.7	508.4	508.2	507.9
117.5°	581.4	581.3	580.9	580.6	580.2	579.9	579.0	578.0	577.1	576.2	575.6
120°	630.7	630.9	630.1	629.2	628.4	627.7	626.4	625.1	623.8	622.5	622.1
122.5°	676.1	676.1	675.7	675.4	675.0	674.6	673.8	672.9	672.0	671.1	670.1
125°	745.0	744.9	744.7	744.4	744.1	743.9	743.4	742.8	742.3	741.7	741.2
127.5°	812.2	812.4	811.9	811.5	811.1	810.7	810.2	809.7	809.2	808.6	808.2
130°	857.3	857.7	857.7	857.7	857.7	857.7	857.2	856.6	856.1	855.6	854.7
132.5°	902.4	902.6	902.4	902.2	902.0	901.8	901.2	900.7	900.2	899.7	899.2
135°	967.1	968.0	968.0	968.0	968.0	968.0	967.5	966.9	966.3	965.8	965.2
137.5°	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6	1030.9	1030.2	1029.6	1029.3
140°	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3	1073.0	1072.8	1072.5	1072.3
142.5°	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9	1112.9	1112.8	1112.8	1112.7
145°	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0	1172.8	1172.5	1172.3	1171.6
147.5°	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3	1227.1	1226.9	1226.6	1226.4
150°	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.1
152.5°	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8	1293.4	1294.1	1294.7	1294.7
155°	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4	1338.5	1339.5	1340.5	1340.5
157.5°	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3	1378.1	1378.8	1379.6	1379.6
160°	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7	1402.4	1403.2	1404.0	1403.7
162.5°	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9	1424.3	1425.7	1427.1	1427.2
165°	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7	1453.3	1454.8	1456.4	1456.6
167.5°	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1	1477.6	1479.3	1480.8	1480.8
170°	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2	1490.9	1492.4	1494.0	1493.8
172.5°	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8	1500.7	1502.4	1504.2	1504.2
175°	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4	1511.3	1513.1	1514.9	1514.9
177.5°	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7	1517.1	1518.6	1520.0	1519.9
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	930.9	931.5	929.4	928.7	929.4	931.5	930.9	932.8	933.1	935.6	934.6
5°	863.6	862.8	860.9	861.3	860.9	862.8	863.6	866.8	868.4	874.6	873.8
7.5°	806.1	803.0	804.0	800.7	804.0	803.0	806.1	808.9	813.7	816.6	823.2
10°	770.9	766.6	763.1	759.9	763.1	766.6	770.9	772.4	779.1	782.3	789.0
12.5°	722.9	719.1	714.3	715.3	714.3	719.1	722.9	729.7	738.3	744.9	755.4
15°	654.6	648.7	639.2	640.5	639.2	648.7	654.6	659.7	668.3	683.3	690.3
17.5°	596.8	596.9	592.6	593.6	592.6	596.9	596.8	603.8	608.2	617.7	628.6
20°	566.9	564.2	564.6	563.4	564.6	564.2	566.9	575.2	580.0	586.6	598.4
22.5°	546.2	542.9	540.1	537.7	540.1	542.9	546.2	548.6	554.8	561.2	570.8
25°	511.2	508.9	505.3	504.5	505.3	508.9	511.2	514.7	517.9	526.1	532.0
27.5°	480.4	479.9	478.5	476.7	478.5	479.9	480.4	483.5	487.6	492.9	500.4
30°	462.4	461.7	460.9	459.7	460.9	461.7	462.4	465.6	468.8	473.1	479.0
32.5°	446.5	446.0	445.1	445.2	445.1	446.0	446.5	448.0	449.9	455.4	460.1
35°	423.5	423.1	422.4	422.0	422.4	423.1	423.5	425.2	426.4	427.9	431.8
37.5°	402.2	403.2	402.7	402.6	402.7	403.2	402.2	402.6	401.3	404.1	406.9
40°	387.4	387.8	388.6	388.2	388.6	387.8	387.4	387.8	387.8	387.8	390.2
42.5°	375.2	375.3	376.4	375.0	376.4	375.3	375.2	373.7	371.7	372.1	372.8
45°	353.3	355.6	355.2	355.2	355.2	355.6	353.3	350.5	350.1	348.5	348.5
47.5°	329.2	331.3	331.8	331.7	331.8	331.3	329.2	328.2	326.4	324.9	324.7
50°	313.6	312.8	314.0	313.6	314.0	312.8	313.6	311.5	308.8	308.8	308.0
52.5°	294.4	294.6	294.5	294.1	294.5	294.6	294.4	293.4	292.2	290.9	290.4
55°	264.8	265.2	264.5	264.8	264.5	265.2	264.8	264.5	264.5	263.7	264.5
57.5°	232.8	230.9	231.7	230.8	231.7	230.9	232.8	234.5	235.1	235.3	236.4
60°	209.8	206.7	205.9	204.3	205.9	206.7	209.8	213.8	215.3	216.1	217.3
62.5°	184.0	181.9	179.2	180.5	179.2	181.9	184.0	188.2	191.8	194.4	197.1
65°	149.7	148.1	146.9	148.6	146.9	148.1	149.7	152.9	156.0	162.3	168.1
67.5°	123.9	123.1	123.1	122.3	123.1	123.1	123.9	125.5	127.4	130.9	136.4
70°	110.4	109.3	109.3	108.5	109.3	109.3	110.4	110.4	112.4	113.9	117.9
72.5°	96.5	95.4	95.7	95.2	95.7	95.4	96.5	96.8	98.9	99.5	101.2
75°	71.5	69.6	69.6	70.0	69.6	69.6	71.5	73.8	75.8	79.4	80.2
77.5°	53.3	52.9	53.5	52.8	53.5	52.9	53.3	53.3	53.7	55.4	56.8
80°	43.6	43.2	42.8	44.0	42.8	43.2	43.6	43.6	44.0	44.4	44.8
82.5°	33.8	33.8	33.7	35.2	33.7	33.8	33.8	34.5	34.5	34.3	34.7
85°	20.4	19.7	20.4	19.7	20.4	19.7	20.4	20.0	20.4	20.0	20.4
87.5°	13.9	13.7	13.5	13.9	13.5	13.7	13.9	13.2	13.0	13.3	12.7
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.1	30.5	29.0
92.5°	51.2	51.5	51.8	52.1	51.8	51.5	51.2	50.8	50.2	49.3	48.4
95°	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.7	92.3	91.5	90.7
97.5°	145.2	145.2	145.2	145.2	145.2	145.2	145.2	145.2	144.8	143.8	142.9
100°	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.9	181.6	181.1	180.6
102.5°	222.6	222.8	223.0	223.2	223.0	222.8	222.6	222.3	221.9	221.2	220.4
105°	284.0	284.7	285.5	286.3	285.5	284.7	284.0	283.2	282.4	281.6	280.8
107.5°	347.9	347.9	347.8	347.8	347.8	347.9	347.9	348.0	347.6	346.9	346.2
110°	389.5	390.3	391.1	391.8	391.1	390.3	389.5	388.7	388.6	389.1	389.6



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	436.5	436.6	436.8	437.0	436.8	436.6	436.5	436.3	436.3	436.4	436.5
115°	507.7	507.4	507.2	506.9	507.2	507.4	507.7	507.9	508.2	508.4	508.7
117.5°	575.0	574.5	574.0	573.5	574.0	574.5	575.0	575.6	576.2	577.1	578.0
120°	622.6	623.1	623.7	624.2	623.7	623.1	622.6	622.1	622.5	623.8	625.1
122.5°	669.2	668.3	667.3	666.4	667.3	668.3	669.2	670.1	671.1	672.0	672.9
125°	740.7	740.2	739.6	739.1	739.6	740.2	740.7	741.2	741.7	742.3	742.8
127.5°	807.8	807.3	806.9	806.5	806.9	807.3	807.8	808.2	808.6	809.2	809.7
130°	853.7	852.7	851.6	850.6	851.6	852.7	853.7	854.7	855.6	856.1	856.6
132.5°	898.8	898.4	898.0	897.6	898.0	898.4	898.8	899.2	899.7	900.2	900.7
135°	964.4	963.6	962.8	962.1	962.8	963.6	964.4	965.2	965.8	966.3	966.9
137.5°	1029.5	1029.6	1029.8	1029.9	1029.8	1029.6	1029.5	1029.3	1029.6	1030.2	1030.9
140°	1072.0	1071.7	1071.5	1071.2	1071.5	1071.7	1072.0	1072.3	1072.5	1072.8	1073.0
142.5°	1112.7	1112.6	1112.6	1112.5	1112.6	1112.6	1112.7	1112.7	1112.8	1112.8	1112.9
145°	1170.9	1170.1	1169.3	1168.6	1169.3	1170.1	1170.9	1171.6	1172.3	1172.5	1172.8
147.5°	1226.2	1225.9	1225.6	1225.4	1225.6	1225.9	1226.2	1226.4	1226.6	1226.9	1227.1
150°	1260.8	1260.6	1260.3	1260.1	1260.3	1260.6	1260.8	1261.1	1261.2	1261.2	1261.2
152.5°	1294.0	1293.3	1292.6	1292.0	1292.6	1293.3	1294.0	1294.7	1294.7	1294.1	1293.4
155°	1339.5	1338.5	1337.4	1336.4	1337.4	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5
157.5°	1378.7	1377.8	1376.8	1376.0	1376.8	1377.8	1378.7	1379.6	1379.6	1378.8	1378.1
160°	1402.4	1401.1	1399.9	1398.6	1399.9	1401.1	1402.4	1403.7	1404.0	1403.2	1402.4
162.5°	1425.9	1424.6	1423.3	1422.0	1423.3	1424.6	1425.9	1427.2	1427.1	1425.7	1424.3
165°	1455.6	1454.6	1453.5	1452.5	1453.5	1454.6	1455.6	1456.6	1456.4	1454.8	1453.3
167.5°	1479.1	1477.5	1475.9	1474.3	1475.9	1477.5	1479.1	1480.8	1480.8	1479.3	1477.6
170°	1492.0	1490.2	1488.3	1486.5	1488.3	1490.2	1492.0	1493.8	1494.0	1492.4	1490.9
172.5°	1502.3	1500.5	1498.6	1496.8	1498.6	1500.5	1502.3	1504.2	1504.2	1502.4	1500.7
175°	1513.1	1511.3	1509.4	1507.6	1509.4	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3
177.5°	1518.2	1516.6	1514.9	1513.3	1514.9	1516.6	1518.2	1519.9	1520.0	1518.6	1517.1
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	932.8	935.0	940.0	945.6	950.4	954.5	957.7	962.0	966.1	971.8	977.1
5°	876.2	881.7	889.6	899.0	910.8	918.7	928.5	937.2	949.7	962.3	974.4
7.5°	826.6	832.6	844.1	857.2	871.2	884.0	895.6	910.9	927.6	945.9	966.3
10°	794.5	801.1	815.0	829.8	846.4	858.9	874.6	892.7	911.6	933.9	959.1
12.5°	765.6	771.9	788.5	803.8	820.9	834.8	852.9	871.3	896.5	920.8	949.4
15°	709.2	726.1	745.0	763.1	783.5	800.4	822.3	841.2	865.3	899.4	932.0
17.5°	646.6	664.7	688.1	716.0	743.4	764.3	786.6	810.0	838.6	873.4	911.1
20°	610.2	624.7	650.7	681.8	713.6	742.7	763.1	789.0	818.5	856.2	895.0
22.5°	582.9	595.2	615.5	646.5	680.9	714.7	740.7	766.4	799.0	836.7	879.1
25°	541.8	555.2	572.9	594.1	633.4	669.1	703.4	732.8	767.4	805.1	852.2
27.5°	507.8	519.4	535.5	557.6	584.0	623.5	664.9	698.5	734.0	774.5	821.6
30°	487.6	497.1	510.4	532.8	558.0	593.3	635.3	674.7	710.4	752.5	801.5
32.5°	466.6	476.7	489.7	507.4	534.3	564.1	606.1	649.1	687.1	730.1	778.3
35°	438.5	446.4	458.2	476.3	500.6	526.5	563.8	608.2	648.3	694.3	740.2
37.5°	410.1	419.4	428.7	444.7	464.7	492.6	523.2	568.6	613.0	654.9	699.8
40°	394.0	399.6	409.8	422.8	444.0	468.8	497.5	541.8	586.2	627.9	673.1
42.5°	376.2	382.3	390.9	403.9	422.9	447.1	475.1	513.5	559.9	600.3	641.4
45°	351.2	354.8	363.5	374.5	390.2	414.5	440.5	474.6	518.3	556.7	592.9
47.5°	326.1	329.2	334.6	344.7	362.2	381.8	406.2	436.8	475.0	513.5	544.1
50°	308.8	311.5	316.7	326.1	341.8	361.1	385.1	412.5	446.8	483.7	509.2
52.5°	291.5	293.1	297.8	308.5	321.7	340.6	362.1	387.4	419.4	450.1	475.9
55°	264.1	267.6	270.7	278.6	291.1	309.2	328.5	352.4	377.2	403.1	425.2
57.5°	235.4	239.2	243.8	250.6	260.6	277.5	294.8	314.2	335.3	356.9	375.3
60°	216.5	220.0	224.0	231.9	240.9	254.2	273.1	289.9	306.1	325.7	344.2
62.5°	197.9	201.5	206.0	212.4	221.1	233.8	249.5	264.2	280.9	298.1	311.8
65°	170.6	173.3	176.8	182.7	191.0	202.4	215.3	226.7	241.7	254.2	266.8
67.5°	140.5	145.7	150.4	155.1	162.1	172.7	182.1	193.0	203.2	212.5	224.0
70°	120.6	126.5	130.9	135.9	142.6	151.7	160.7	168.1	176.4	185.4	195.7
72.5°	104.0	108.6	112.0	117.4	123.4	131.9	140.3	146.4	153.2	159.4	169.3
75°	82.1	84.1	86.4	90.8	96.2	102.6	109.3	114.7	118.7	124.1	131.3
77.5°	59.0	62.8	64.3	67.5	71.4	75.2	79.7	84.3	88.1	90.1	95.4
80°	45.1	46.8	48.4	52.6	55.0	59.0	62.1	66.4	68.0	70.0	75.0
82.5°	35.1	36.1	37.1	38.2	39.6	43.5	46.7	49.4	51.0	51.7	55.5
85°	20.4	20.8	21.2	21.6	22.0	22.0	23.5	25.5	28.3	28.3	29.5
87.5°	12.4	12.4	12.0	11.2	11.4	11.0	10.9	10.3	10.6	11.0	11.4
90°	27.4	25.9	23.7	21.6	19.6	17.5	14.9	12.1	9.3	6.4	3.5
92.5°	47.4	46.5	45.0	43.5	42.1	40.6	38.3	34.9	31.7	28.4	25.1
95°	90.0	89.2	87.4	85.5	83.7	81.9	79.8	77.5	75.1	72.7	70.4
97.5°	142.0	141.0	138.9	136.7	134.6	132.5	130.5	128.6	126.7	124.8	123.0
100°	180.1	179.6	177.1	174.8	172.5	170.2	168.4	167.3	166.3	165.3	164.3
102.5°	219.6	218.9	216.8	214.7	212.5	210.4	209.1	208.6	208.2	207.8	207.4
105°	280.0	279.2	278.2	277.1	276.1	275.1	274.4	274.2	273.9	273.7	273.4
107.5°	345.5	344.7	344.6	344.4	344.3	344.1	343.9	343.6	343.3	343.0	342.5
110°	390.2	390.7	390.9	391.2	391.5	391.7	391.6	391.1	390.5	390.0	389.5



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	436.6	436.7	437.2	437.7	438.1	438.6	438.8	438.7	438.6	438.5	438.3
115°	509.0	509.2	509.7	510.3	510.8	511.3	511.5	511.5	511.5	511.5	511.5
117.5°	579.0	579.9	580.2	580.6	580.9	581.3	581.4	581.2	581.0	580.8	580.6
120°	626.4	627.7	628.4	629.2	630.1	630.9	630.7	629.7	628.6	627.5	626.5
122.5°	673.8	674.6	675.0	675.4	675.7	676.1	676.1	675.6	675.2	674.8	674.4
125°	743.4	743.9	744.1	744.4	744.7	744.9	745.0	745.0	745.0	745.0	745.0
127.5°	810.2	810.7	811.1	811.5	811.9	812.4	812.2	811.4	810.6	809.9	809.1
130°	857.2	857.7	857.7	857.7	857.7	857.7	857.3	856.5	855.7	855.0	854.1
132.5°	901.2	901.8	902.0	902.2	902.4	902.6	902.4	901.8	901.3	900.7	900.1
135°	967.5	968.0	968.0	968.0	968.0	968.0	967.1	965.6	964.0	962.5	960.9
137.5°	1031.6	1032.2	1031.8	1031.4	1031.0	1030.6	1030.0	1029.3	1028.5	1027.8	1027.0
140°	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3	1072.8	1072.3	1071.7	1071.2
142.5°	1112.9	1113.0	1113.2	1113.4	1113.6	1113.8	1113.7	1113.1	1112.6	1112.1	1111.6
145°	1173.0	1173.3	1173.0	1172.8	1172.5	1172.3	1171.5	1170.5	1169.5	1168.4	1167.4
147.5°	1227.3	1227.5	1227.7	1227.9	1228.1	1228.3	1227.8	1226.5	1225.3	1224.1	1222.7
150°	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1260.7	1259.7	1258.7	1257.6	1256.6
152.5°	1292.8	1292.2	1292.0	1291.8	1291.6	1291.4	1291.0	1290.3	1289.7	1289.1	1288.5
155°	1337.4	1336.4	1336.6	1336.9	1337.2	1337.4	1337.5	1337.5	1337.5	1337.5	1337.5
157.5°	1377.3	1376.4	1376.5	1376.5	1376.6	1376.6	1377.0	1377.5	1377.9	1378.4	1378.8
160°	1401.7	1400.9	1401.1	1401.4	1401.7	1401.9	1402.2	1402.4	1402.7	1403.0	1403.2
162.5°	1422.9	1421.5	1421.8	1422.1	1422.3	1422.6	1423.0	1423.7	1424.4	1425.0	1425.7
165°	1451.7	1450.2	1450.7	1451.2	1451.7	1452.2	1452.9	1453.7	1454.4	1455.2	1456.0
167.5°	1476.1	1474.5	1474.5	1474.4	1474.4	1474.3	1474.9	1475.9	1477.0	1478.1	1479.3
170°	1489.2	1487.7	1487.4	1487.1	1486.9	1486.6	1487.1	1488.4	1489.8	1491.1	1492.4
172.5°	1498.8	1497.1	1497.0	1497.0	1496.9	1496.8	1497.4	1498.4	1499.5	1500.7	1501.8
175°	1509.4	1507.6	1507.9	1508.1	1508.4	1508.6	1509.4	1510.8	1512.1	1513.4	1514.7
177.5°	1515.7	1514.2	1514.2	1514.2	1514.2	1514.2	1514.7	1515.8	1516.8	1517.8	1518.9
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	981.2	984.0	987.1	993.1	998.2	1000.4	1004.8	1007.9	1006.9	1011.4	1019.0
5°	985.0	995.6	1007.8	1020.4	1034.5	1046.3	1055.8	1065.2	1072.7	1081.7	1095.1
7.5°	984.4	1003.3	1023.8	1046.3	1069.5	1089.5	1108.1	1127.0	1143.7	1162.1	1186.0
10°	981.9	1007.0	1032.6	1062.1	1091.6	1119.4	1144.6	1168.1	1190.5	1214.5	1244.8
12.5°	979.1	1007.9	1038.8	1074.3	1111.1	1144.6	1174.2	1208.1	1236.1	1267.0	1302.0
15°	966.5	1005.5	1047.5	1093.5	1137.5	1182.7	1223.1	1264.9	1303.7	1340.6	1384.6
17.5°	952.3	997.1	1046.7	1101.1	1154.0	1208.8	1256.9	1309.4	1349.1	1398.7	1439.6
20°	940.7	989.0	1042.0	1102.9	1163.1	1224.0	1277.0	1330.4	1375.2	1425.1	1477.0
22.5°	926.6	979.6	1037.0	1100.0	1163.1	1229.6	1288.3	1341.4	1396.9	1453.1	1506.5
25°	903.7	958.8	1019.7	1088.7	1161.0	1229.0	1291.9	1358.0	1417.6	1478.5	1526.5
27.5°	875.8	933.5	997.7	1069.0	1143.3	1212.8	1286.9	1357.3	1417.3	1475.9	1517.7
30°	853.4	914.3	976.0	1048.3	1125.3	1200.0	1279.3	1349.7	1412.9	1465.6	1489.1
32.5°	830.5	888.3	951.8	1025.0	1104.0	1184.3	1263.0	1334.9	1393.4	1425.0	1425.6
35°	790.5	844.8	910.8	982.7	1063.6	1150.8	1230.6	1301.3	1337.1	1339.9	1301.3
37.5°	747.0	796.8	859.1	931.1	1019.7	1106.5	1187.9	1235.1	1247.1	1207.1	1135.9
40°	715.9	761.8	822.0	895.9	983.9	1073.5	1147.7	1182.2	1169.7	1104.9	1025.5
42.5°	683.2	726.0	784.0	856.9	945.2	1035.7	1099.0	1117.5	1084.2	1009.4	916.5
45°	629.9	669.1	726.5	800.0	884.8	969.8	1017.6	1008.2	952.8	864.0	759.9
47.5°	574.3	612.3	663.9	731.8	818.8	892.0	924.4	896.1	817.2	719.5	634.8
50°	537.6	576.4	624.0	688.8	768.2	838.9	859.7	816.5	728.8	635.0	557.1
52.5°	501.4	534.6	581.2	643.8	719.7	779.5	790.5	740.7	650.3	566.1	497.2
55°	446.4	476.7	515.9	574.8	640.5	691.2	685.3	621.2	539.1	467.2	412.9
57.5°	393.1	416.0	452.2	507.5	565.1	599.2	577.5	523.0	446.5	387.6	341.8
60°	358.0	379.2	412.9	461.3	512.0	531.2	513.1	453.8	393.3	339.5	300.9
62.5°	324.7	343.4	372.4	417.3	458.2	469.6	450.3	398.5	344.0	298.0	266.1
65°	276.2	293.5	318.3	350.1	378.4	383.8	371.3	318.3	277.0	238.5	216.5
67.5°	232.3	243.6	263.0	290.4	305.5	308.7	284.4	251.1	214.7	191.1	174.5
70°	202.8	210.6	228.6	243.6	255.8	256.2	233.8	207.0	179.2	160.0	147.7
72.5°	174.1	181.7	195.4	205.6	214.9	211.9	191.4	170.3	147.7	133.2	124.1
75°	134.4	141.1	148.1	152.9	152.9	149.0	134.0	118.3	105.3	96.6	93.9
77.5°	97.7	103.2	105.5	104.8	103.4	97.3	87.9	77.6	72.9	68.9	66.8
80°	76.6	79.0	79.8	77.8	75.4	68.4	62.1	57.8	53.4	51.9	51.1
82.5°	56.9	58.9	56.9	57.4	52.2	46.4	42.9	41.4	39.6	39.0	38.2
85°	30.3	29.9	29.1	27.1	23.5	22.8	22.4	22.0	21.2	21.6	20.8
87.5°	11.6	11.3	10.6	10.9	11.3	11.1	11.9	12.3	12.7	12.7	13.6
90°	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4	29.0
92.5°	28.4	31.7	34.9	38.3	40.6	42.1	43.5	45.0	46.5	47.4	48.4
95°	72.7	75.1	77.5	79.8	81.9	83.7	85.5	87.4	89.2	90.0	90.7
97.5°	124.8	126.7	128.6	130.5	132.5	134.6	136.7	138.9	141.0	142.0	142.9
100°	165.3	166.3	167.3	168.4	170.2	172.5	174.8	177.1	179.6	180.1	180.6
102.5°	207.8	208.2	208.6	209.1	210.4	212.5	214.7	216.8	218.9	219.6	220.4
105°	273.7	273.9	274.2	274.4	275.1	276.1	277.1	278.2	279.2	280.0	280.8
107.5°	343.0	343.3	343.6	343.9	344.1	344.3	344.4	344.6	344.7	345.5	346.2
110°	390.0	390.5	391.1	391.6	391.7	391.5	391.2	390.9	390.7	390.2	389.6



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	438.5	438.6	438.7	438.8	438.6	438.1	437.7	437.2	436.7	436.6	436.5
115°	511.5	511.5	511.5	511.5	511.3	510.8	510.3	509.7	509.2	509.0	508.7
117.5°	580.8	581.0	581.2	581.4	581.3	580.9	580.6	580.2	579.9	579.0	578.0
120°	627.5	628.6	629.7	630.7	630.9	630.1	629.2	628.4	627.7	626.4	625.1
122.5°	674.8	675.2	675.6	676.1	676.1	675.7	675.4	675.0	674.6	673.8	672.9
125°	745.0	745.0	745.0	745.0	744.9	744.7	744.4	744.1	743.9	743.4	742.8
127.5°	809.9	810.6	811.4	812.2	812.4	811.9	811.5	811.1	810.7	810.2	809.7
130°	855.0	855.7	856.5	857.3	857.7	857.7	857.7	857.7	857.7	857.2	856.6
132.5°	900.7	901.3	901.8	902.4	902.6	902.4	902.2	902.0	901.8	901.2	900.7
135°	962.5	964.0	965.6	967.1	968.0	968.0	968.0	968.0	968.0	967.5	966.9
137.5°	1027.8	1028.5	1029.3	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6	1030.9
140°	1071.7	1072.3	1072.8	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3	1073.0
142.5°	1112.1	1112.6	1113.1	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9	1112.9
145°	1168.4	1169.5	1170.5	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0	1172.8
147.5°	1224.1	1225.3	1226.5	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3	1227.1
150°	1257.6	1258.7	1259.7	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1289.1	1289.7	1290.3	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8	1293.4
155°	1337.5	1337.5	1337.5	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4	1338.5
157.5°	1378.4	1377.9	1377.5	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3	1378.1
160°	1403.0	1402.7	1402.4	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7	1402.4
162.5°	1425.0	1424.4	1423.7	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9	1424.3
165°	1455.2	1454.4	1453.7	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7	1453.3
167.5°	1478.1	1477.0	1475.9	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1	1477.6
170°	1491.1	1489.8	1488.4	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2	1490.9
172.5°	1500.7	1499.5	1498.4	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8	1500.7
175°	1513.4	1512.1	1510.8	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4	1511.3
177.5°	1517.8	1516.8	1515.8	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7	1517.1
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1023.0	1024.3	1025.2	1028.3	1028.6	1031.5	1028.6
5°	1107.6	1113.2	1121.8	1130.4	1131.3	1136.7	1126.9
7.5°	1202.5	1215.3	1223.2	1237.2	1242.7	1246.2	1240.5
10°	1268.0	1279.7	1300.6	1310.8	1321.0	1322.5	1317.9
12.5°	1331.1	1349.8	1366.2	1385.6	1385.1	1399.0	1393.9
15°	1415.3	1434.5	1457.3	1478.9	1486.8	1486.8	1493.1
17.5°	1475.3	1510.7	1534.2	1551.2	1569.7	1573.0	1570.7
20°	1515.9	1554.0	1579.1	1601.1	1613.8	1617.3	1617.3
22.5°	1546.1	1578.5	1603.1	1622.9	1633.3	1637.4	1636.1
25°	1567.0	1594.9	1609.8	1615.7	1618.4	1617.6	1610.2
27.5°	1538.3	1537.1	1527.6	1509.5	1496.0	1487.7	1478.3
30°	1483.7	1463.2	1439.7	1413.7	1380.3	1354.7	1347.0
32.5°	1402.3	1356.3	1316.5	1273.2	1237.3	1211.7	1201.0
35°	1244.8	1172.0	1112.8	1060.9	1023.2	999.6	991.7
37.5°	1057.9	987.5	914.1	863.8	832.5	808.7	799.8
40°	939.1	862.4	798.4	751.2	719.0	695.9	695.5
42.5°	830.6	757.5	697.2	663.3	628.5	613.2	613.1
45°	680.1	621.6	570.5	543.8	523.0	510.4	506.9
47.5°	563.1	514.7	480.7	459.4	442.4	434.4	429.2
50°	497.5	455.0	427.9	409.4	400.0	389.8	389.0
52.5°	442.7	408.5	387.4	372.3	360.4	354.3	354.5
55°	372.1	345.0	330.0	318.6	309.2	304.5	302.6
57.5°	313.5	293.2	282.3	271.9	267.8	264.1	263.1
60°	277.0	263.3	253.1	244.8	238.9	237.7	237.3
62.5°	246.8	232.5	225.4	219.0	214.7	212.9	212.2
65°	203.5	192.9	186.6	181.6	180.0	177.2	176.8
67.5°	164.1	157.7	153.6	150.1	147.8	147.7	147.7
70°	139.9	136.3	132.8	130.9	129.7	128.9	128.9
72.5°	119.2	116.5	113.6	112.6	112.4	111.6	111.3
75°	90.8	88.1	88.4	86.4	84.8	82.9	81.7
77.5°	64.3	62.4	62.0	61.8	60.4	60.2	60.8
80°	49.9	48.0	47.6	48.0	47.6	46.4	46.4
82.5°	38.0	36.4	36.0	35.6	35.2	35.6	35.0
85°	20.4	19.7	19.7	19.7	20.4	20.0	19.7
87.5°	13.3	13.3	13.8	13.6	13.7	13.5	13.9
90°	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	49.3	50.2	50.8	51.2	51.5	51.8	52.1
95°	91.5	92.3	92.7	92.7	92.7	92.7	92.7
97.5°	143.8	144.8	145.2	145.2	145.2	145.2	145.2
100°	181.1	181.6	181.9	181.9	181.9	181.9	181.9
102.5°	221.2	221.9	222.3	222.6	222.8	223.0	223.2
105°	281.6	282.4	283.2	284.0	284.7	285.5	286.3
107.5°	346.9	347.6	348.0	347.9	347.9	347.8	347.8
110°	389.1	388.6	388.7	389.5	390.3	391.1	391.8



TEST NUMBER: P332920-840

CATALOG NUMBER: S124RDIP-S575D1205U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	436.4	436.3	436.3	436.5	436.6	436.8	437.0
115°	508.4	508.2	507.9	507.7	507.4	507.2	506.9
117.5°	577.1	576.2	575.6	575.0	574.5	574.0	573.5
120°	623.8	622.5	622.1	622.6	623.1	623.7	624.2
122.5°	672.0	671.1	670.1	669.2	668.3	667.3	666.4
125°	742.3	741.7	741.2	740.7	740.2	739.6	739.1
127.5°	809.2	808.6	808.2	807.8	807.3	806.9	806.5
130°	856.1	855.6	854.7	853.7	852.7	851.6	850.6
132.5°	900.2	899.7	899.2	898.8	898.4	898.0	897.6
135°	966.3	965.8	965.2	964.4	963.6	962.8	962.1
137.5°	1030.2	1029.6	1029.3	1029.5	1029.6	1029.8	1029.9
140°	1072.8	1072.5	1072.3	1072.0	1071.7	1071.5	1071.2
142.5°	1112.8	1112.8	1112.7	1112.7	1112.6	1112.6	1112.5
145°	1172.5	1172.3	1171.6	1170.9	1170.1	1169.3	1168.6
147.5°	1226.9	1226.6	1226.4	1226.2	1225.9	1225.6	1225.4
150°	1261.2	1261.2	1261.1	1260.8	1260.6	1260.3	1260.1
152.5°	1294.1	1294.7	1294.7	1294.0	1293.3	1292.6	1292.0
155°	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4
157.5°	1378.8	1379.6	1379.6	1378.7	1377.8	1376.8	1376.0
160°	1403.2	1404.0	1403.7	1402.4	1401.1	1399.9	1398.6
162.5°	1425.7	1427.1	1427.2	1425.9	1424.6	1423.3	1422.0
165°	1454.8	1456.4	1456.6	1455.6	1454.6	1453.5	1452.5
167.5°	1479.3	1480.8	1480.8	1479.1	1477.5	1475.9	1474.3
170°	1492.4	1494.0	1493.8	1492.0	1490.2	1488.3	1486.5
172.5°	1502.4	1504.2	1504.2	1502.3	1500.5	1498.6	1496.8
175°	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6
177.5°	1518.6	1520.0	1519.9	1518.2	1516.6	1514.9	1513.3
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0

(END OF REPORT)