

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332895-840

Luminaire Tested: **S124RDIP-S575D365U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332895-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D365U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3942.6 lumens  
Efficiency: N/A  
Efficacy: 143.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	59	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50	46
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43	40
4	78	67	59	54	73	63	57	51	56	51	47	50	45	42	44	40	38	34
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	39	46	40	36	41	36	32	36	32	29	27
7	61	49	41	36	58	47	39	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	27	24	21
9	53	41	34	29	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	38	31	26	47	36	29	25	33	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7873	7873	7873	7873
5°	9132	7896	6980	7896
10°	10803	7862	6229	7862
15°	12479	7789	5353	7789
20°	13894	7689	4840	7689
25°	14343	7591	4494	7591
30°	12557	7471	4285	7471
35°	9773	7295	4159	7295
40°	7330	7093	4091	7093
45°	5787	6769	4055	6769
50°	4886	6395	3939	6395
55°	4259	5985	3727	5985
60°	3831	5557	3299	5557
65°	3377	5096	2839	5096
70°	3043	4619	2561	4619
75°	2548	4095	2183	4095
80°	2157	3487	2046	3487
85°	1825	2732	1825	2732



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.5	2.4
10°-20°	285.0	7.2
20°-30°	445.8	11.3
30°-40°	495.6	12.6
40°-50°	439.7	11.2
50°-60°	342.6	8.7
60°-70°	224.3	5.7
70°-80°	110.3	2.8
80°-90°	28.6	0.7
90°-100°	16.3	0.4
100°-110°	104.1	2.6
110°-120°	199.1	5.0
120°-130°	252.7	6.4
130°-140°	270.4	6.9
140°-150°	252.8	6.4
150°-160°	203.9	5.2
160°-170°	131.5	3.3
170°-180°	45.3	1.1
0°-30°	825.3	20.9
0°-40°	1320.9	33.5
0°-60°	2103.3	53.3
0°-90°	2466.5	62.6
90°-120°	319.5	8.1
90°-150°	1095.3	27.8
90°-180°	1476.0	37.4
0°-180°	3942.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	975	975	975	975	975	
5°	1127	974	861	974	1127	114
15°	1493	932	640	932	1493	425
25°	1610	852	504	852	1610	714
35°	992	740	422	740	992	622
45°	507	593	355	593	507	401
55°	303	425	265	425	303	275
65°	177	267	149	267	177	178
75°	82	131	70	131	82	90
85°	20	30	20	30	20	22
90°	11	1	11	1	11	6
95°	10	20	10	20	10	8
105°	102	107	102	107	102	89
115°	202	201	202	201	202	200
125°	284	282	284	282	284	253
135°	352	350	352	350	352	271
145°	406	403	406	403	406	253
155°	442	442	442	442	442	204
165°	464	466	464	466	464	131
175°	474	477	474	477	474	45
180°	477	477	477	477	477	



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1028.6	1031.5	1028.6	1028.3	1025.2	1024.3	1023.0	1019.0	1011.4	1006.9	1007.9
5°	1126.9	1136.7	1131.3	1130.4	1121.8	1113.2	1107.6	1095.1	1081.7	1072.7	1065.2
7.5°	1240.5	1246.2	1242.7	1237.2	1223.2	1215.3	1202.5	1186.0	1162.1	1143.7	1127.0
10°	1317.9	1322.5	1321.0	1310.8	1300.6	1279.7	1268.0	1244.8	1214.5	1190.5	1168.1
12.5°	1393.9	1399.0	1385.1	1385.6	1366.2	1349.8	1331.1	1302.0	1267.0	1236.1	1208.1
15°	1493.1	1486.8	1486.8	1478.9	1457.3	1434.5	1415.3	1384.6	1340.6	1303.7	1264.9
17.5°	1570.7	1573.0	1569.7	1551.2	1534.2	1510.7	1475.3	1439.6	1398.7	1349.1	1309.4
20°	1617.3	1617.3	1613.8	1601.1	1579.1	1554.0	1515.9	1477.0	1425.1	1375.2	1330.4
22.5°	1636.1	1637.4	1633.3	1622.9	1603.1	1578.5	1546.1	1506.5	1453.1	1396.9	1341.4
25°	1610.2	1617.6	1618.4	1615.7	1609.8	1594.9	1567.0	1526.5	1478.5	1417.6	1358.0
27.5°	1478.3	1487.7	1496.0	1509.5	1527.6	1537.1	1538.3	1517.7	1475.9	1417.3	1357.3
30°	1347.0	1354.7	1380.3	1413.7	1439.7	1463.2	1483.7	1489.1	1465.6	1412.9	1349.7
32.5°	1201.0	1211.7	1237.3	1273.2	1316.5	1356.3	1402.3	1425.6	1425.0	1393.4	1334.9
35°	991.7	999.6	1023.2	1060.9	1112.8	1172.0	1244.8	1301.3	1339.9	1337.1	1301.3
37.5°	799.8	808.7	832.5	863.8	914.1	987.5	1057.9	1135.9	1207.1	1247.1	1235.1
40°	695.5	695.9	719.0	751.2	798.4	862.4	939.1	1025.5	1104.9	1169.7	1182.2
42.5°	613.1	613.2	628.5	663.3	697.2	757.5	830.6	916.5	1009.4	1084.2	1117.5
45°	506.9	510.4	523.0	543.8	570.5	621.6	680.1	759.9	864.0	952.8	1008.2
47.5°	429.2	434.4	442.4	459.4	480.7	514.7	563.1	634.8	719.5	817.2	896.1
50°	389.0	389.8	400.0	409.4	427.9	455.0	497.5	557.1	635.0	728.8	816.5
52.5°	354.5	354.3	360.4	372.3	387.4	408.5	442.7	497.2	566.1	650.3	740.7
55°	302.6	304.5	309.2	318.6	330.0	345.0	372.1	412.9	467.2	539.1	621.2
57.5°	263.1	264.1	267.8	271.9	282.3	293.2	313.5	341.8	387.6	446.5	523.0
60°	237.3	237.7	238.9	244.8	253.1	263.3	277.0	300.9	339.5	393.3	453.8
62.5°	212.2	212.9	214.7	219.0	225.4	232.5	246.8	266.1	298.0	344.0	398.5
65°	176.8	177.2	180.0	181.6	186.6	192.9	203.5	216.5	238.5	277.0	318.3
67.5°	147.7	147.7	147.8	150.1	153.6	157.7	164.1	174.5	191.1	214.7	251.1
70°	128.9	128.9	129.7	130.9	132.8	136.3	139.9	147.7	160.0	179.2	207.0
72.5°	111.3	111.6	112.4	112.6	113.6	116.5	119.2	124.1	133.2	147.7	170.3
75°	81.7	82.9	84.8	86.4	88.4	88.1	90.8	93.9	96.6	105.3	118.3
77.5°	60.8	60.2	60.4	61.8	62.0	62.4	64.3	66.8	68.9	72.9	77.6
80°	46.4	46.4	47.6	48.0	47.6	48.0	49.9	51.1	51.9	53.4	57.8
82.5°	35.0	35.6	35.2	35.6	36.0	36.4	38.0	38.2	39.0	39.6	41.4
85°	19.7	20.0	20.4	19.7	19.7	19.7	20.4	20.8	21.6	21.2	22.0
87.5°	9.1	8.7	9.0	9.0	9.3	8.9	9.1	9.6	8.9	9.1	9.0
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.3	8.8	8.3	7.9	7.2
92.5°	9.9	9.8	9.8	9.8	9.7	9.5	9.0	8.5	8.1	7.6	7.0
95°	10.3	10.3	10.2	10.1	10.0	9.8	9.3	8.8	8.3	7.9	7.8
97.5°	10.0	9.9	9.8	9.8	9.7	9.6	9.6	9.5	9.5	9.4	18.3
100°	10.0	9.9	9.8	9.8	9.7	10.3	11.6	13.0	14.3	15.8	26.7
102.5°	10.3	10.3	10.2	10.2	10.2	17.5	32.0	46.6	61.1	75.6	77.1
105°	101.7	104.5	107.4	110.3	113.1	114.2	113.5	112.8	112.1	111.4	111.0
107.5°	141.8	141.5	141.2	140.9	140.6	140.3	139.9	139.6	139.2	138.9	138.3
110°	159.2	159.0	158.8	158.4	158.2	158.0	157.8	157.7	157.5	157.4	156.9



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.6	176.3	176.0	175.7	175.4	175.2	175.3	175.3	175.3	175.4	175.1
115°	202.0	202.0	202.0	202.0	202.0	202.0	201.8	201.6	201.5	201.3	201.4
117.5°	227.8	227.9	227.9	227.9	227.9	228.0	228.0	228.0	228.1	228.1	227.9
120°	244.1	244.3	244.4	244.6	244.8	244.8	244.6	244.4	244.3	244.1	244.2
122.5°	260.1	260.2	260.4	260.5	260.7	260.7	260.6	260.5	260.4	260.4	260.2
125°	284.1	284.0	284.0	283.9	283.8	283.6	283.4	283.2	282.9	282.7	282.9
127.5°	305.2	305.2	305.3	305.4	305.4	305.5	305.5	305.6	305.6	305.7	305.3
130°	319.4	319.4	319.4	319.4	319.4	319.4	319.3	319.2	319.1	319.1	318.8
132.5°	332.5	332.6	332.6	332.8	332.9	332.9	332.8	332.6	332.5	332.4	332.1
135°	352.2	352.1	351.9	351.7	351.6	351.4	351.3	351.1	351.0	350.8	350.5
137.5°	369.1	369.1	369.2	369.2	369.3	369.2	369.1	368.9	368.7	368.5	368.2
140°	380.8	380.7	380.6	380.6	380.5	380.3	380.1	379.8	379.6	379.4	379.2
142.5°	390.5	390.5	390.5	390.5	390.4	390.3	390.2	390.0	389.8	389.7	389.6
145°	405.5	405.3	405.2	405.0	404.8	404.7	404.7	404.6	404.5	404.3	404.3
147.5°	417.8	417.7	417.6	417.6	417.5	417.4	417.4	417.3	417.2	417.2	417.2
150°	425.8	425.7	425.7	425.6	425.5	425.5	425.5	425.5	425.5	425.5	425.5
152.5°	432.6	432.7	432.7	432.7	432.8	432.8	432.6	432.5	432.4	432.3	432.4
155°	441.8	442.1	442.3	442.5	442.8	442.7	442.4	442.1	441.8	441.5	441.7
157.5°	449.6	450.0	450.4	450.8	451.2	451.2	450.8	450.4	450.0	449.6	449.8
160°	454.6	455.1	455.7	456.2	456.6	456.6	456.2	455.7	455.1	454.6	454.7
162.5°	458.7	459.2	459.8	460.3	460.8	460.9	460.4	459.9	459.5	459.0	459.1
165°	464.3	465.0	465.7	466.5	467.2	467.3	466.6	466.0	465.3	464.6	464.6
167.5°	468.6	469.3	470.1	470.9	471.7	471.7	471.1	470.4	469.7	469.0	469.0
170°	471.1	471.9	472.7	473.5	474.2	474.3	473.7	473.1	472.4	471.8	471.7
172.5°	472.5	473.4	474.2	475.1	475.9	476.1	475.4	474.8	474.1	473.5	473.4
175°	474.3	475.2	476.3	477.2	478.2	478.3	477.6	476.9	476.2	475.3	475.3
177.5°	475.4	476.3	477.0	477.8	478.5	478.7	478.2	477.7	477.2	476.6	476.5
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1004.8	1000.4	998.2	993.1	987.1	984.0	981.2	977.1	971.8	966.1	962.0
5°	1055.8	1046.3	1034.5	1020.4	1007.8	995.6	985.0	974.4	962.3	949.7	937.2
7.5°	1108.1	1089.5	1069.5	1046.3	1023.8	1003.3	984.4	966.3	945.9	927.6	910.9
10°	1144.6	1119.4	1091.6	1062.1	1032.6	1007.0	981.9	959.1	933.9	911.6	892.7
12.5°	1174.2	1144.6	1111.1	1074.3	1038.8	1007.9	979.1	949.4	920.8	896.5	871.3
15°	1223.1	1182.7	1137.5	1093.5	1047.5	1005.5	966.5	932.0	899.4	865.3	841.2
17.5°	1256.9	1208.8	1154.0	1101.1	1046.7	997.1	952.3	911.1	873.4	838.6	810.0
20°	1277.0	1224.0	1163.1	1102.9	1042.0	989.0	940.7	895.0	856.2	818.5	789.0
22.5°	1288.3	1229.6	1163.1	1100.0	1037.0	979.6	926.6	879.1	836.7	799.0	766.4
25°	1291.9	1229.0	1161.0	1088.7	1019.7	958.8	903.7	852.2	805.1	767.4	732.8
27.5°	1286.9	1212.8	1143.3	1069.0	997.7	933.5	875.8	821.6	774.5	734.0	698.5
30°	1279.3	1200.0	1125.3	1048.3	976.0	914.3	853.4	801.5	752.5	710.4	674.7
32.5°	1263.0	1184.3	1104.0	1025.0	951.8	888.3	830.5	778.3	730.1	687.1	649.1
35°	1230.6	1150.8	1063.6	982.7	910.8	844.8	790.5	740.2	694.3	648.3	608.2
37.5°	1187.9	1106.5	1019.7	931.1	859.1	796.8	747.0	699.8	654.9	613.0	568.6
40°	1147.7	1073.5	983.9	895.9	822.0	761.8	715.9	673.1	627.9	586.2	541.8
42.5°	1099.0	1035.7	945.2	856.9	784.0	726.0	683.2	641.4	600.3	559.9	513.5
45°	1017.6	969.8	884.8	800.0	726.5	669.1	629.9	592.9	556.7	518.3	474.6
47.5°	924.4	892.0	818.8	731.8	663.9	612.3	574.3	544.1	513.5	475.0	436.8
50°	859.7	838.9	768.2	688.8	624.0	576.4	537.6	509.2	483.7	446.8	412.5
52.5°	790.5	779.5	719.7	643.8	581.2	534.6	501.4	475.9	450.1	419.4	387.4
55°	685.3	691.2	640.5	574.8	515.9	476.7	446.4	425.2	403.1	377.2	352.4
57.5°	577.5	599.2	565.1	507.5	452.2	416.0	393.1	375.3	356.9	335.3	314.2
60°	513.1	531.2	512.0	461.3	412.9	379.2	358.0	344.2	325.7	306.1	289.9
62.5°	450.3	469.6	458.2	417.3	372.4	343.4	324.7	311.8	298.1	280.9	264.2
65°	371.3	383.8	378.4	350.1	318.3	293.5	276.2	266.8	254.2	241.7	226.7
67.5°	284.4	308.7	305.5	290.4	263.0	243.6	232.3	224.0	212.5	203.2	193.0
70°	233.8	256.2	255.8	243.6	228.6	210.6	202.8	195.7	185.4	176.4	168.1
72.5°	191.4	211.9	214.9	205.6	195.4	181.7	174.1	169.3	159.4	153.2	146.4
75°	134.0	149.0	152.9	152.9	148.1	141.1	134.4	131.3	124.1	118.7	114.7
77.5°	87.9	97.3	103.4	104.8	105.5	103.2	97.7	95.4	90.1	88.1	84.3
80°	62.1	68.4	75.4	77.8	79.8	79.0	76.6	75.0	70.0	68.0	66.4
82.5°	42.9	46.4	52.2	57.4	56.9	58.9	56.9	55.5	51.7	51.0	49.4
85°	22.4	22.8	23.5	27.1	29.1	29.9	30.3	29.5	28.3	28.3	25.5
87.5°	8.9	8.4	8.9	8.8	8.9	10.0	10.8	10.9	10.1	9.4	8.6
90°	6.6	6.0	5.4	4.5	3.7	2.8	1.9	1.1	1.9	2.8	3.7
92.5°	6.3	5.7	5.0	4.6	4.6	4.5	4.5	4.5	4.5	4.5	4.6
95°	7.7	7.6	7.6	8.9	11.5	14.2	17.0	19.6	17.0	14.2	11.5
97.5°	27.2	36.0	44.8	48.4	46.8	45.0	43.3	41.7	43.3	45.0	46.8
100°	37.6	48.6	59.5	64.2	62.8	61.4	60.0	58.6	60.0	61.4	62.8
102.5°	78.6	80.0	81.4	81.6	80.5	79.5	78.5	77.4	78.5	79.5	80.5
105°	110.6	110.2	109.8	109.4	108.9	108.4	107.9	107.4	107.9	108.4	108.9
107.5°	137.7	137.2	136.6	136.3	136.0	135.8	135.5	135.3	135.5	135.8	136.0
110°	156.4	155.9	155.5	155.1	154.9	154.6	154.4	154.2	154.4	154.6	154.9





TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.9	174.7	174.5	174.2	173.7	173.3	172.9	172.5	172.9	173.3	173.7
115°	201.5	201.6	201.6	201.6	201.3	201.1	200.9	200.6	200.9	201.1	201.3
117.5°	227.8	227.6	227.4	227.2	226.9	226.5	226.2	225.9	226.2	226.5	226.9
120°	244.3	244.4	244.4	244.3	244.0	243.7	243.4	243.1	243.4	243.7	244.0
122.5°	260.1	260.0	259.9	259.8	259.6	259.4	259.2	259.0	259.2	259.4	259.6
125°	283.0	283.2	283.3	283.3	282.9	282.6	282.3	282.0	282.3	282.6	282.9
127.5°	304.9	304.6	304.2	304.0	303.9	303.8	303.8	303.7	303.8	303.8	303.9
130°	318.6	318.3	318.1	318.0	317.9	317.8	317.7	317.6	317.7	317.8	317.9
132.5°	331.8	331.5	331.2	331.0	330.9	330.7	330.6	330.5	330.6	330.7	330.9
135°	350.2	349.9	349.5	349.4	349.5	349.6	349.7	349.7	349.7	349.6	349.5
137.5°	367.8	367.5	367.2	367.0	366.9	366.9	366.9	366.8	366.9	366.9	366.9
140°	379.1	378.9	378.7	378.6	378.4	378.3	378.1	378.0	378.1	378.3	378.4
142.5°	389.5	389.4	389.3	389.1	388.8	388.5	388.2	388.0	388.2	388.5	388.8
145°	404.3	404.3	404.3	404.2	404.0	403.7	403.5	403.3	403.5	403.7	404.0
147.5°	417.3	417.4	417.5	417.3	416.9	416.4	416.0	415.5	416.0	416.4	416.9
150°	425.6	425.7	425.8	425.7	425.4	425.0	424.6	424.3	424.6	425.0	425.4
152.5°	432.5	432.7	432.8	432.8	432.5	432.3	432.0	431.8	432.0	432.3	432.5
155°	441.9	442.2	442.4	442.5	442.4	442.3	442.3	442.2	442.3	442.3	442.4
157.5°	450.1	450.4	450.6	450.8	450.8	450.9	450.9	451.0	450.9	450.9	450.8
160°	454.8	454.9	455.0	455.1	455.4	455.7	455.9	456.2	455.9	455.7	455.4
162.5°	459.1	459.2	459.3	459.5	459.8	460.1	460.4	460.7	460.4	460.1	459.8
165°	464.6	464.6	464.6	464.8	465.2	465.6	466.1	466.5	466.1	465.6	465.2
167.5°	469.1	469.1	469.2	469.4	469.8	470.2	470.6	471.0	470.6	470.2	469.8
170°	471.7	471.6	471.5	471.7	472.2	472.6	473.1	473.6	473.1	472.6	472.2
172.5°	473.4	473.3	473.2	473.4	473.9	474.3	474.8	475.3	474.8	474.3	473.9
175°	475.2	475.1	475.0	475.2	475.7	476.3	476.7	477.2	476.7	476.3	475.7
177.5°	476.4	476.3	476.1	476.3	476.7	477.2	477.6	478.1	477.6	477.2	476.7
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	957.7	954.5	950.4	945.6	940.0	935.0	932.8	934.6	935.6	933.1	932.8
5°	928.5	918.7	910.8	899.0	889.6	881.7	876.2	873.8	874.6	868.4	866.8
7.5°	895.6	884.0	871.2	857.2	844.1	832.6	826.6	823.2	816.6	813.7	808.9
10°	874.6	858.9	846.4	829.8	815.0	801.1	794.5	789.0	782.3	779.1	772.4
12.5°	852.9	834.8	820.9	803.8	788.5	771.9	765.6	755.4	744.9	738.3	729.7
15°	822.3	800.4	783.5	763.1	745.0	726.1	709.2	690.3	683.3	668.3	659.7
17.5°	786.6	764.3	743.4	716.0	688.1	664.7	646.6	628.6	617.7	608.2	603.8
20°	763.1	742.7	713.6	681.8	650.7	624.7	610.2	598.4	586.6	580.0	575.2
22.5°	740.7	714.7	680.9	646.5	615.5	595.2	582.9	570.8	561.2	554.8	548.6
25°	703.4	669.1	633.4	594.1	572.9	555.2	541.8	532.0	526.1	517.9	514.7
27.5°	664.9	623.5	584.0	557.6	535.5	519.4	507.8	500.4	492.9	487.6	483.5
30°	635.3	593.3	558.0	532.8	510.4	497.1	487.6	479.0	473.1	468.8	465.6
32.5°	606.1	564.1	534.3	507.4	489.7	476.7	466.6	460.1	455.4	449.9	448.0
35°	563.8	526.5	500.6	476.3	458.2	446.4	438.5	431.8	427.9	426.4	425.2
37.5°	523.2	492.6	464.7	444.7	428.7	419.4	410.1	406.9	404.1	401.3	402.6
40°	497.5	468.8	444.0	422.8	409.8	399.6	394.0	390.2	387.8	387.8	387.8
42.5°	475.1	447.1	422.9	403.9	390.9	382.3	376.2	372.8	372.1	371.7	373.7
45°	440.5	414.5	390.2	374.5	363.5	354.8	351.2	348.5	348.5	350.1	350.5
47.5°	406.2	381.8	362.2	344.7	334.6	329.2	326.1	324.7	324.9	326.4	328.2
50°	385.1	361.1	341.8	326.1	316.7	311.5	308.8	308.0	308.8	308.8	311.5
52.5°	362.1	340.6	321.7	308.5	297.8	293.1	291.5	290.4	290.9	292.2	293.4
55°	328.5	309.2	291.1	278.6	270.7	267.6	264.1	264.5	263.7	264.5	264.5
57.5°	294.8	277.5	260.6	250.6	243.8	239.2	235.4	236.4	235.3	235.1	234.5
60°	273.1	254.2	240.9	231.9	224.0	220.0	216.5	217.3	216.1	215.3	213.8
62.5°	249.5	233.8	221.1	212.4	206.0	201.5	197.9	197.1	194.4	191.8	188.2
65°	215.3	202.4	191.0	182.7	176.8	173.3	170.6	168.1	162.3	156.0	152.9
67.5°	182.1	172.7	162.1	155.1	150.4	145.7	140.5	136.4	130.9	127.4	125.5
70°	160.7	151.7	142.6	135.9	130.9	126.5	120.6	117.9	113.9	112.4	110.4
72.5°	140.3	131.9	123.4	117.4	112.0	108.6	104.0	101.2	99.5	98.9	96.8
75°	109.3	102.6	96.2	90.8	86.4	84.1	82.1	80.2	79.4	75.8	73.8
77.5°	79.7	75.2	71.4	67.5	64.3	62.8	59.0	56.8	55.4	53.7	53.3
80°	62.1	59.0	55.0	52.6	48.4	46.8	45.1	44.8	44.4	44.0	43.6
82.5°	46.7	43.5	39.6	38.2	37.1	36.1	35.1	34.7	34.3	34.5	34.5
85°	23.5	22.0	22.0	21.6	21.2	20.8	20.4	20.4	20.0	20.4	20.0
87.5°	8.8	8.6	8.7	8.3	8.7	8.8	8.6	8.7	9.1	8.6	8.6
90°	4.5	5.4	6.0	6.6	7.2	7.9	8.3	8.8	9.3	9.8	10.1
92.5°	4.6	5.0	5.7	6.3	7.0	7.6	8.1	8.5	9.0	9.5	9.7
95°	8.9	7.6	7.6	7.7	7.8	7.9	8.3	8.8	9.3	9.8	10.0
97.5°	48.4	44.8	36.0	27.2	18.3	9.4	9.5	9.5	9.6	9.6	9.7
100°	64.2	59.5	48.6	37.6	26.7	15.8	14.3	13.0	11.6	10.3	9.7
102.5°	81.6	81.4	80.0	78.6	77.1	75.6	61.1	46.6	32.0	17.5	10.2
105°	109.4	109.8	110.2	110.6	111.0	111.4	112.1	112.8	113.5	114.2	113.1
107.5°	136.3	136.6	137.2	137.7	138.3	138.9	139.2	139.6	139.9	140.3	140.6
110°	155.1	155.5	155.9	156.4	156.9	157.4	157.5	157.7	157.8	158.0	158.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.2	174.5	174.7	174.9	175.1	175.4	175.3	175.3	175.3	175.2	175.4
115°	201.6	201.6	201.6	201.5	201.4	201.3	201.5	201.6	201.8	202.0	202.0
117.5°	227.2	227.4	227.6	227.8	227.9	228.1	228.1	228.0	228.0	228.0	227.9
120°	244.3	244.4	244.4	244.3	244.2	244.1	244.3	244.4	244.6	244.8	244.8
122.5°	259.8	259.9	260.0	260.1	260.2	260.4	260.4	260.5	260.6	260.7	260.7
125°	283.3	283.3	283.2	283.0	282.9	282.7	282.9	283.2	283.4	283.6	283.8
127.5°	304.0	304.2	304.6	304.9	305.3	305.7	305.6	305.6	305.5	305.5	305.4
130°	318.0	318.1	318.3	318.6	318.8	319.1	319.1	319.2	319.3	319.4	319.4
132.5°	331.0	331.2	331.5	331.8	332.1	332.4	332.5	332.6	332.8	332.9	332.9
135°	349.4	349.5	349.9	350.2	350.5	350.8	351.0	351.1	351.3	351.4	351.6
137.5°	367.0	367.2	367.5	367.8	368.2	368.5	368.7	368.9	369.1	369.2	369.3
140°	378.6	378.7	378.9	379.1	379.2	379.4	379.6	379.8	380.1	380.3	380.5
142.5°	389.1	389.3	389.4	389.5	389.6	389.7	389.8	390.0	390.2	390.3	390.4
145°	404.2	404.3	404.3	404.3	404.3	404.3	404.5	404.6	404.7	404.7	404.8
147.5°	417.3	417.5	417.4	417.3	417.2	417.2	417.2	417.3	417.4	417.4	417.5
150°	425.7	425.8	425.7	425.6	425.5	425.5	425.5	425.5	425.5	425.5	425.5
152.5°	432.8	432.8	432.7	432.5	432.4	432.3	432.4	432.5	432.6	432.8	432.8
155°	442.5	442.4	442.2	441.9	441.7	441.5	441.8	442.1	442.4	442.7	442.8
157.5°	450.8	450.6	450.4	450.1	449.8	449.6	450.0	450.4	450.8	451.2	451.2
160°	455.1	455.0	454.9	454.8	454.7	454.6	455.1	455.7	456.2	456.6	456.6
162.5°	459.5	459.3	459.2	459.1	459.1	459.0	459.5	459.9	460.4	460.9	460.8
165°	464.8	464.6	464.6	464.6	464.6	464.6	465.3	466.0	466.6	467.3	467.2
167.5°	469.4	469.2	469.1	469.1	469.0	469.0	469.7	470.4	471.1	471.7	471.7
170°	471.7	471.5	471.6	471.7	471.7	471.8	472.4	473.1	473.7	474.3	474.2
172.5°	473.4	473.2	473.3	473.4	473.4	473.5	474.1	474.8	475.4	476.1	475.9
175°	475.2	475.0	475.1	475.2	475.3	475.3	476.2	476.9	477.6	478.3	478.2
177.5°	476.3	476.1	476.3	476.4	476.5	476.6	477.2	477.7	478.2	478.7	478.5
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	930.9	931.5	929.4	928.7	929.4	931.5	930.9	932.8	933.1	935.6	934.6
5°	863.6	862.8	860.9	861.3	860.9	862.8	863.6	866.8	868.4	874.6	873.8
7.5°	806.1	803.0	804.0	800.7	804.0	803.0	806.1	808.9	813.7	816.6	823.2
10°	770.9	766.6	763.1	759.9	763.1	766.6	770.9	772.4	779.1	782.3	789.0
12.5°	722.9	719.1	714.3	715.3	714.3	719.1	722.9	729.7	738.3	744.9	755.4
15°	654.6	648.7	639.2	640.5	639.2	648.7	654.6	659.7	668.3	683.3	690.3
17.5°	596.8	596.9	592.6	593.6	592.6	596.9	596.8	603.8	608.2	617.7	628.6
20°	566.9	564.2	564.6	563.4	564.6	564.2	566.9	575.2	580.0	586.6	598.4
22.5°	546.2	542.9	540.1	537.7	540.1	542.9	546.2	548.6	554.8	561.2	570.8
25°	511.2	508.9	505.3	504.5	505.3	508.9	511.2	514.7	517.9	526.1	532.0
27.5°	480.4	479.9	478.5	476.7	478.5	479.9	480.4	483.5	487.6	492.9	500.4
30°	462.4	461.7	460.9	459.7	460.9	461.7	462.4	465.6	468.8	473.1	479.0
32.5°	446.5	446.0	445.1	445.2	445.1	446.0	446.5	448.0	449.9	455.4	460.1
35°	423.5	423.1	422.4	422.0	422.4	423.1	423.5	425.2	426.4	427.9	431.8
37.5°	402.2	403.2	402.7	402.6	402.7	403.2	402.2	402.6	401.3	404.1	406.9
40°	387.4	387.8	388.6	388.2	388.6	387.8	387.4	387.8	387.8	387.8	390.2
42.5°	375.2	375.3	376.4	375.0	376.4	375.3	375.2	373.7	371.7	372.1	372.8
45°	353.3	355.6	355.2	355.2	355.2	355.6	353.3	350.5	350.1	348.5	348.5
47.5°	329.2	331.3	331.8	331.7	331.8	331.3	329.2	328.2	326.4	324.9	324.7
50°	313.6	312.8	314.0	313.6	314.0	312.8	313.6	311.5	308.8	308.8	308.0
52.5°	294.4	294.6	294.5	294.1	294.5	294.6	294.4	293.4	292.2	290.9	290.4
55°	264.8	265.2	264.5	264.8	264.5	265.2	264.8	264.5	264.5	263.7	264.5
57.5°	232.8	230.9	231.7	230.8	231.7	230.9	232.8	234.5	235.1	235.3	236.4
60°	209.8	206.7	205.9	204.3	205.9	206.7	209.8	213.8	215.3	216.1	217.3
62.5°	184.0	181.9	179.2	180.5	179.2	181.9	184.0	188.2	191.8	194.4	197.1
65°	149.7	148.1	146.9	148.6	146.9	148.1	149.7	152.9	156.0	162.3	168.1
67.5°	123.9	123.1	123.1	122.3	123.1	123.1	123.9	125.5	127.4	130.9	136.4
70°	110.4	109.3	109.3	108.5	109.3	109.3	110.4	110.4	112.4	113.9	117.9
72.5°	96.5	95.4	95.7	95.2	95.7	95.4	96.5	96.8	98.9	99.5	101.2
75°	71.5	69.6	69.6	70.0	69.6	69.6	71.5	73.8	75.8	79.4	80.2
77.5°	53.3	52.9	53.5	52.8	53.5	52.9	53.3	53.3	53.7	55.4	56.8
80°	43.6	43.2	42.8	44.0	42.8	43.2	43.6	43.6	44.0	44.4	44.8
82.5°	33.8	33.8	33.7	35.2	33.7	33.8	33.8	34.5	34.5	34.3	34.7
85°	20.4	19.7	20.4	19.7	20.4	19.7	20.4	20.0	20.4	20.0	20.4
87.5°	9.3	9.0	8.7	9.1	8.7	9.0	9.3	8.6	8.6	9.1	8.7
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.3	8.8
92.5°	9.8	9.8	9.8	9.9	9.8	9.8	9.8	9.7	9.5	9.0	8.5
95°	10.1	10.2	10.3	10.3	10.3	10.2	10.1	10.0	9.8	9.3	8.8
97.5°	9.8	9.8	9.9	10.0	9.9	9.8	9.8	9.7	9.6	9.6	9.5
100°	9.8	9.8	9.9	10.0	9.9	9.8	9.8	9.7	10.3	11.6	13.0
102.5°	10.2	10.2	10.3	10.3	10.3	10.2	10.2	10.2	17.5	32.0	46.6
105°	110.3	107.4	104.5	101.7	104.5	107.4	110.3	113.1	114.2	113.5	112.8
107.5°	140.9	141.2	141.5	141.8	141.5	141.2	140.9	140.6	140.3	139.9	139.6
110°	158.4	158.8	159.0	159.2	159.0	158.8	158.4	158.2	158.0	157.8	157.7



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.7	176.0	176.3	176.6	176.3	176.0	175.7	175.4	175.2	175.3	175.3
115°	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0	201.8	201.6
117.5°	227.9	227.9	227.9	227.8	227.9	227.9	227.9	227.9	228.0	228.0	228.0
120°	244.6	244.4	244.3	244.1	244.3	244.4	244.6	244.8	244.8	244.6	244.4
122.5°	260.5	260.4	260.2	260.1	260.2	260.4	260.5	260.7	260.7	260.6	260.5
125°	283.9	284.0	284.0	284.1	284.0	284.0	283.9	283.8	283.6	283.4	283.2
127.5°	305.4	305.3	305.2	305.2	305.2	305.3	305.4	305.4	305.5	305.5	305.6
130°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.3	319.2
132.5°	332.8	332.6	332.6	332.5	332.6	332.6	332.8	332.9	332.9	332.8	332.6
135°	351.7	351.9	352.1	352.2	352.1	351.9	351.7	351.6	351.4	351.3	351.1
137.5°	369.2	369.2	369.1	369.1	369.1	369.2	369.2	369.3	369.2	369.1	368.9
140°	380.6	380.6	380.7	380.8	380.7	380.6	380.6	380.5	380.3	380.1	379.8
142.5°	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.4	390.3	390.2	390.0
145°	405.0	405.2	405.3	405.5	405.3	405.2	405.0	404.8	404.7	404.7	404.6
147.5°	417.6	417.6	417.7	417.8	417.7	417.6	417.6	417.5	417.4	417.4	417.3
150°	425.6	425.7	425.7	425.8	425.7	425.7	425.6	425.5	425.5	425.5	425.5
152.5°	432.7	432.7	432.7	432.6	432.7	432.7	432.7	432.8	432.8	432.6	432.5
155°	442.5	442.3	442.1	441.8	442.1	442.3	442.5	442.8	442.7	442.4	442.1
157.5°	450.8	450.4	450.0	449.6	450.0	450.4	450.8	451.2	451.2	450.8	450.4
160°	456.2	455.7	455.1	454.6	455.1	455.7	456.2	456.6	456.6	456.2	455.7
162.5°	460.3	459.8	459.2	458.7	459.2	459.8	460.3	460.8	460.9	460.4	459.9
165°	466.5	465.7	465.0	464.3	465.0	465.7	466.5	467.2	467.3	466.6	466.0
167.5°	470.9	470.1	469.3	468.6	469.3	470.1	470.9	471.7	471.7	471.1	470.4
170°	473.5	472.7	471.9	471.1	471.9	472.7	473.5	474.2	474.3	473.7	473.1
172.5°	475.1	474.2	473.4	472.5	473.4	474.2	475.1	475.9	476.1	475.4	474.8
175°	477.2	476.3	475.2	474.3	475.2	476.3	477.2	478.2	478.3	477.6	476.9
177.5°	477.8	477.0	476.3	475.4	476.3	477.0	477.8	478.5	478.7	478.2	477.7
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	932.8	935.0	940.0	945.6	950.4	954.5	957.7	962.0	966.1	971.8	977.1
5°	876.2	881.7	889.6	899.0	910.8	918.7	928.5	937.2	949.7	962.3	974.4
7.5°	826.6	832.6	844.1	857.2	871.2	884.0	895.6	910.9	927.6	945.9	966.3
10°	794.5	801.1	815.0	829.8	846.4	858.9	874.6	892.7	911.6	933.9	959.1
12.5°	765.6	771.9	788.5	803.8	820.9	834.8	852.9	871.3	896.5	920.8	949.4
15°	709.2	726.1	745.0	763.1	783.5	800.4	822.3	841.2	865.3	899.4	932.0
17.5°	646.6	664.7	688.1	716.0	743.4	764.3	786.6	810.0	838.6	873.4	911.1
20°	610.2	624.7	650.7	681.8	713.6	742.7	763.1	789.0	818.5	856.2	895.0
22.5°	582.9	595.2	615.5	646.5	680.9	714.7	740.7	766.4	799.0	836.7	879.1
25°	541.8	555.2	572.9	594.1	633.4	669.1	703.4	732.8	767.4	805.1	852.2
27.5°	507.8	519.4	535.5	557.6	584.0	623.5	664.9	698.5	734.0	774.5	821.6
30°	487.6	497.1	510.4	532.8	558.0	593.3	635.3	674.7	710.4	752.5	801.5
32.5°	466.6	476.7	489.7	507.4	534.3	564.1	606.1	649.1	687.1	730.1	778.3
35°	438.5	446.4	458.2	476.3	500.6	526.5	563.8	608.2	648.3	694.3	740.2
37.5°	410.1	419.4	428.7	444.7	464.7	492.6	523.2	568.6	613.0	654.9	699.8
40°	394.0	399.6	409.8	422.8	444.0	468.8	497.5	541.8	586.2	627.9	673.1
42.5°	376.2	382.3	390.9	403.9	422.9	447.1	475.1	513.5	559.9	600.3	641.4
45°	351.2	354.8	363.5	374.5	390.2	414.5	440.5	474.6	518.3	556.7	592.9
47.5°	326.1	329.2	334.6	344.7	362.2	381.8	406.2	436.8	475.0	513.5	544.1
50°	308.8	311.5	316.7	326.1	341.8	361.1	385.1	412.5	446.8	483.7	509.2
52.5°	291.5	293.1	297.8	308.5	321.7	340.6	362.1	387.4	419.4	450.1	475.9
55°	264.1	267.6	270.7	278.6	291.1	309.2	328.5	352.4	377.2	403.1	425.2
57.5°	235.4	239.2	243.8	250.6	260.6	277.5	294.8	314.2	335.3	356.9	375.3
60°	216.5	220.0	224.0	231.9	240.9	254.2	273.1	289.9	306.1	325.7	344.2
62.5°	197.9	201.5	206.0	212.4	221.1	233.8	249.5	264.2	280.9	298.1	311.8
65°	170.6	173.3	176.8	182.7	191.0	202.4	215.3	226.7	241.7	254.2	266.8
67.5°	140.5	145.7	150.4	155.1	162.1	172.7	182.1	193.0	203.2	212.5	224.0
70°	120.6	126.5	130.9	135.9	142.6	151.7	160.7	168.1	176.4	185.4	195.7
72.5°	104.0	108.6	112.0	117.4	123.4	131.9	140.3	146.4	153.2	159.4	169.3
75°	82.1	84.1	86.4	90.8	96.2	102.6	109.3	114.7	118.7	124.1	131.3
77.5°	59.0	62.8	64.3	67.5	71.4	75.2	79.7	84.3	88.1	90.1	95.4
80°	45.1	46.8	48.4	52.6	55.0	59.0	62.1	66.4	68.0	70.0	75.0
82.5°	35.1	36.1	37.1	38.2	39.6	43.5	46.7	49.4	51.0	51.7	55.5
85°	20.4	20.8	21.2	21.6	22.0	22.0	23.5	25.5	28.3	28.3	29.5
87.5°	8.6	8.8	8.7	8.3	8.7	8.6	8.8	8.6	9.4	10.1	10.9
90°	8.3	7.9	7.2	6.6	6.0	5.4	4.5	3.7	2.8	1.9	1.1
92.5°	8.1	7.6	7.0	6.3	5.7	5.0	4.6	4.6	4.5	4.5	4.5
95°	8.3	7.9	7.8	7.7	7.6	7.6	8.9	11.5	14.2	17.0	19.6
97.5°	9.5	9.4	18.3	27.2	36.0	44.8	48.4	46.8	45.0	43.3	41.7
100°	14.3	15.8	26.7	37.6	48.6	59.5	64.2	62.8	61.4	60.0	58.6
102.5°	61.1	75.6	77.1	78.6	80.0	81.4	81.6	80.5	79.5	78.5	77.4
105°	112.1	111.4	111.0	110.6	110.2	109.8	109.4	108.9	108.4	107.9	107.4
107.5°	139.2	138.9	138.3	137.7	137.2	136.6	136.3	136.0	135.8	135.5	135.3
110°	157.5	157.4	156.9	156.4	155.9	155.5	155.1	154.9	154.6	154.4	154.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	175.3	175.4	175.1	174.9	174.7	174.5	174.2	173.7	173.3	172.9	172.5
115°	201.5	201.3	201.4	201.5	201.6	201.6	201.6	201.3	201.1	200.9	200.6
117.5°	228.1	228.1	227.9	227.8	227.6	227.4	227.2	226.9	226.5	226.2	225.9
120°	244.3	244.1	244.2	244.3	244.4	244.4	244.3	244.0	243.7	243.4	243.1
122.5°	260.4	260.4	260.2	260.1	260.0	259.9	259.8	259.6	259.4	259.2	259.0
125°	282.9	282.7	282.9	283.0	283.2	283.3	283.3	282.9	282.6	282.3	282.0
127.5°	305.6	305.7	305.3	304.9	304.6	304.2	304.0	303.9	303.8	303.8	303.7
130°	319.1	319.1	318.8	318.6	318.3	318.1	318.0	317.9	317.8	317.7	317.6
132.5°	332.5	332.4	332.1	331.8	331.5	331.2	331.0	330.9	330.7	330.6	330.5
135°	351.0	350.8	350.5	350.2	349.9	349.5	349.4	349.5	349.6	349.7	349.7
137.5°	368.7	368.5	368.2	367.8	367.5	367.2	367.0	366.9	366.9	366.9	366.8
140°	379.6	379.4	379.2	379.1	378.9	378.7	378.6	378.4	378.3	378.1	378.0
142.5°	389.8	389.7	389.6	389.5	389.4	389.3	389.1	388.8	388.5	388.2	388.0
145°	404.5	404.3	404.3	404.3	404.3	404.3	404.2	404.0	403.7	403.5	403.3
147.5°	417.2	417.2	417.2	417.3	417.4	417.5	417.3	416.9	416.4	416.0	415.5
150°	425.5	425.5	425.5	425.6	425.7	425.8	425.7	425.4	425.0	424.6	424.3
152.5°	432.4	432.3	432.4	432.5	432.7	432.8	432.8	432.5	432.3	432.0	431.8
155°	441.8	441.5	441.7	441.9	442.2	442.4	442.5	442.4	442.3	442.3	442.2
157.5°	450.0	449.6	449.8	450.1	450.4	450.6	450.8	450.8	450.9	450.9	451.0
160°	455.1	454.6	454.7	454.8	454.9	455.0	455.1	455.4	455.7	455.9	456.2
162.5°	459.5	459.0	459.1	459.1	459.2	459.3	459.5	459.8	460.1	460.4	460.7
165°	465.3	464.6	464.6	464.6	464.6	464.6	464.8	465.2	465.6	466.1	466.5
167.5°	469.7	469.0	469.0	469.1	469.1	469.2	469.4	469.8	470.2	470.6	471.0
170°	472.4	471.8	471.7	471.7	471.6	471.5	471.7	472.2	472.6	473.1	473.6
172.5°	474.1	473.5	473.4	473.4	473.3	473.2	473.4	473.9	474.3	474.8	475.3
175°	476.2	475.3	475.3	475.2	475.1	475.0	475.2	475.7	476.3	476.7	477.2
177.5°	477.2	476.6	476.5	476.4	476.3	476.1	476.3	476.7	477.2	477.6	478.1
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	981.2	984.0	987.1	993.1	998.2	1000.4	1004.8	1007.9	1006.9	1011.4	1019.0
5°	985.0	995.6	1007.8	1020.4	1034.5	1046.3	1055.8	1065.2	1072.7	1081.7	1095.1
7.5°	984.4	1003.3	1023.8	1046.3	1069.5	1089.5	1108.1	1127.0	1143.7	1162.1	1186.0
10°	981.9	1007.0	1032.6	1062.1	1091.6	1119.4	1144.6	1168.1	1190.5	1214.5	1244.8
12.5°	979.1	1007.9	1038.8	1074.3	1111.1	1144.6	1174.2	1208.1	1236.1	1267.0	1302.0
15°	966.5	1005.5	1047.5	1093.5	1137.5	1182.7	1223.1	1264.9	1303.7	1340.6	1384.6
17.5°	952.3	997.1	1046.7	1101.1	1154.0	1208.8	1256.9	1309.4	1349.1	1398.7	1439.6
20°	940.7	989.0	1042.0	1102.9	1163.1	1224.0	1277.0	1330.4	1375.2	1425.1	1477.0
22.5°	926.6	979.6	1037.0	1100.0	1163.1	1229.6	1288.3	1341.4	1396.9	1453.1	1506.5
25°	903.7	958.8	1019.7	1088.7	1161.0	1229.0	1291.9	1358.0	1417.6	1478.5	1526.5
27.5°	875.8	933.5	997.7	1069.0	1143.3	1212.8	1286.9	1357.3	1417.3	1475.9	1517.7
30°	853.4	914.3	976.0	1048.3	1125.3	1200.0	1279.3	1349.7	1412.9	1465.6	1489.1
32.5°	830.5	888.3	951.8	1025.0	1104.0	1184.3	1263.0	1334.9	1393.4	1425.0	1425.6
35°	790.5	844.8	910.8	982.7	1063.6	1150.8	1230.6	1301.3	1337.1	1339.9	1301.3
37.5°	747.0	796.8	859.1	931.1	1019.7	1106.5	1187.9	1235.1	1247.1	1207.1	1135.9
40°	715.9	761.8	822.0	895.9	983.9	1073.5	1147.7	1182.2	1169.7	1104.9	1025.5
42.5°	683.2	726.0	784.0	856.9	945.2	1035.7	1099.0	1117.5	1084.2	1009.4	916.5
45°	629.9	669.1	726.5	800.0	884.8	969.8	1017.6	1008.2	952.8	864.0	759.9
47.5°	574.3	612.3	663.9	731.8	818.8	892.0	924.4	896.1	817.2	719.5	634.8
50°	537.6	576.4	624.0	688.8	768.2	838.9	859.7	816.5	728.8	635.0	557.1
52.5°	501.4	534.6	581.2	643.8	719.7	779.5	790.5	740.7	650.3	566.1	497.2
55°	446.4	476.7	515.9	574.8	640.5	691.2	685.3	621.2	539.1	467.2	412.9
57.5°	393.1	416.0	452.2	507.5	565.1	599.2	577.5	523.0	446.5	387.6	341.8
60°	358.0	379.2	412.9	461.3	512.0	531.2	513.1	453.8	393.3	339.5	300.9
62.5°	324.7	343.4	372.4	417.3	458.2	469.6	450.3	398.5	344.0	298.0	266.1
65°	276.2	293.5	318.3	350.1	378.4	383.8	371.3	318.3	277.0	238.5	216.5
67.5°	232.3	243.6	263.0	290.4	305.5	308.7	284.4	251.1	214.7	191.1	174.5
70°	202.8	210.6	228.6	243.6	255.8	256.2	233.8	207.0	179.2	160.0	147.7
72.5°	174.1	181.7	195.4	205.6	214.9	211.9	191.4	170.3	147.7	133.2	124.1
75°	134.4	141.1	148.1	152.9	152.9	149.0	134.0	118.3	105.3	96.6	93.9
77.5°	97.7	103.2	105.5	104.8	103.4	97.3	87.9	77.6	72.9	68.9	66.8
80°	76.6	79.0	79.8	77.8	75.4	68.4	62.1	57.8	53.4	51.9	51.1
82.5°	56.9	58.9	56.9	57.4	52.2	46.4	42.9	41.4	39.6	39.0	38.2
85°	30.3	29.9	29.1	27.1	23.5	22.8	22.4	22.0	21.2	21.6	20.8
87.5°	10.8	10.0	8.9	8.8	8.9	8.4	8.9	9.0	9.1	8.9	9.6
90°	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3	8.8
92.5°	4.5	4.5	4.6	4.6	5.0	5.7	6.3	7.0	7.6	8.1	8.5
95°	17.0	14.2	11.5	8.9	7.6	7.6	7.7	7.8	7.9	8.3	8.8
97.5°	43.3	45.0	46.8	48.4	44.8	36.0	27.2	18.3	9.4	9.5	9.5
100°	60.0	61.4	62.8	64.2	59.5	48.6	37.6	26.7	15.8	14.3	13.0
102.5°	78.5	79.5	80.5	81.6	81.4	80.0	78.6	77.1	75.6	61.1	46.6
105°	107.9	108.4	108.9	109.4	109.8	110.2	110.6	111.0	111.4	112.1	112.8
107.5°	135.5	135.8	136.0	136.3	136.6	137.2	137.7	138.3	138.9	139.2	139.6
110°	154.4	154.6	154.9	155.1	155.5	155.9	156.4	156.9	157.4	157.5	157.7





TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	172.9	173.3	173.7	174.2	174.5	174.7	174.9	175.1	175.4	175.3	175.3
115°	200.9	201.1	201.3	201.6	201.6	201.6	201.5	201.4	201.3	201.5	201.6
117.5°	226.2	226.5	226.9	227.2	227.4	227.6	227.8	227.9	228.1	228.1	228.0
120°	243.4	243.7	244.0	244.3	244.4	244.4	244.3	244.2	244.1	244.3	244.4
122.5°	259.2	259.4	259.6	259.8	259.9	260.0	260.1	260.2	260.4	260.4	260.5
125°	282.3	282.6	282.9	283.3	283.3	283.2	283.0	282.9	282.7	282.9	283.2
127.5°	303.8	303.8	303.9	304.0	304.2	304.6	304.9	305.3	305.7	305.6	305.6
130°	317.7	317.8	317.9	318.0	318.1	318.3	318.6	318.8	319.1	319.1	319.2
132.5°	330.6	330.7	330.9	331.0	331.2	331.5	331.8	332.1	332.4	332.5	332.6
135°	349.7	349.6	349.5	349.4	349.5	349.9	350.2	350.5	350.8	351.0	351.1
137.5°	366.9	366.9	366.9	367.0	367.2	367.5	367.8	368.2	368.5	368.7	368.9
140°	378.1	378.3	378.4	378.6	378.7	378.9	379.1	379.2	379.4	379.6	379.8
142.5°	388.2	388.5	388.8	389.1	389.3	389.4	389.5	389.6	389.7	389.8	390.0
145°	403.5	403.7	404.0	404.2	404.3	404.3	404.3	404.3	404.3	404.5	404.6
147.5°	416.0	416.4	416.9	417.3	417.5	417.4	417.3	417.2	417.2	417.2	417.3
150°	424.6	425.0	425.4	425.7	425.8	425.7	425.6	425.5	425.5	425.5	425.5
152.5°	432.0	432.3	432.5	432.8	432.8	432.7	432.5	432.4	432.3	432.4	432.5
155°	442.3	442.3	442.4	442.5	442.4	442.2	441.9	441.7	441.5	441.8	442.1
157.5°	450.9	450.9	450.8	450.8	450.6	450.4	450.1	449.8	449.6	450.0	450.4
160°	455.9	455.7	455.4	455.1	455.0	454.9	454.8	454.7	454.6	455.1	455.7
162.5°	460.4	460.1	459.8	459.5	459.3	459.2	459.1	459.1	459.0	459.5	459.9
165°	466.1	465.6	465.2	464.8	464.6	464.6	464.6	464.6	464.6	465.3	466.0
167.5°	470.6	470.2	469.8	469.4	469.2	469.1	469.1	469.0	469.0	469.7	470.4
170°	473.1	472.6	472.2	471.7	471.5	471.6	471.7	471.7	471.8	472.4	473.1
172.5°	474.8	474.3	473.9	473.4	473.2	473.3	473.4	473.4	473.5	474.1	474.8
175°	476.7	476.3	475.7	475.2	475.0	475.1	475.2	475.3	475.3	476.2	476.9
177.5°	477.6	477.2	476.7	476.3	476.1	476.3	476.4	476.5	476.6	477.2	477.7
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1023.0	1024.3	1025.2	1028.3	1028.6	1031.5	1028.6
5°	1107.6	1113.2	1121.8	1130.4	1131.3	1136.7	1126.9
7.5°	1202.5	1215.3	1223.2	1237.2	1242.7	1246.2	1240.5
10°	1268.0	1279.7	1300.6	1310.8	1321.0	1322.5	1317.9
12.5°	1331.1	1349.8	1366.2	1385.6	1385.1	1399.0	1393.9
15°	1415.3	1434.5	1457.3	1478.9	1486.8	1486.8	1493.1
17.5°	1475.3	1510.7	1534.2	1551.2	1569.7	1573.0	1570.7
20°	1515.9	1554.0	1579.1	1601.1	1613.8	1617.3	1617.3
22.5°	1546.1	1578.5	1603.1	1622.9	1633.3	1637.4	1636.1
25°	1567.0	1594.9	1609.8	1615.7	1618.4	1617.6	1610.2
27.5°	1538.3	1537.1	1527.6	1509.5	1496.0	1487.7	1478.3
30°	1483.7	1463.2	1439.7	1413.7	1380.3	1354.7	1347.0
32.5°	1402.3	1356.3	1316.5	1273.2	1237.3	1211.7	1201.0
35°	1244.8	1172.0	1112.8	1060.9	1023.2	999.6	991.7
37.5°	1057.9	987.5	914.1	863.8	832.5	808.7	799.8
40°	939.1	862.4	798.4	751.2	719.0	695.9	695.5
42.5°	830.6	757.5	697.2	663.3	628.5	613.2	613.1
45°	680.1	621.6	570.5	543.8	523.0	510.4	506.9
47.5°	563.1	514.7	480.7	459.4	442.4	434.4	429.2
50°	497.5	455.0	427.9	409.4	400.0	389.8	389.0
52.5°	442.7	408.5	387.4	372.3	360.4	354.3	354.5
55°	372.1	345.0	330.0	318.6	309.2	304.5	302.6
57.5°	313.5	293.2	282.3	271.9	267.8	264.1	263.1
60°	277.0	263.3	253.1	244.8	238.9	237.7	237.3
62.5°	246.8	232.5	225.4	219.0	214.7	212.9	212.2
65°	203.5	192.9	186.6	181.6	180.0	177.2	176.8
67.5°	164.1	157.7	153.6	150.1	147.8	147.7	147.7
70°	139.9	136.3	132.8	130.9	129.7	128.9	128.9
72.5°	119.2	116.5	113.6	112.6	112.4	111.6	111.3
75°	90.8	88.1	88.4	86.4	84.8	82.9	81.7
77.5°	64.3	62.4	62.0	61.8	60.4	60.2	60.8
80°	49.9	48.0	47.6	48.0	47.6	46.4	46.4
82.5°	38.0	36.4	36.0	35.6	35.2	35.6	35.0
85°	20.4	19.7	19.7	19.7	20.4	20.0	19.7
87.5°	9.1	8.9	9.3	9.0	9.0	8.7	9.1
90°	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	9.0	9.5	9.7	9.8	9.8	9.8	9.9
95°	9.3	9.8	10.0	10.1	10.2	10.3	10.3
97.5°	9.6	9.6	9.7	9.8	9.8	9.9	10.0
100°	11.6	10.3	9.7	9.8	9.8	9.9	10.0
102.5°	32.0	17.5	10.2	10.2	10.2	10.3	10.3
105°	113.5	114.2	113.1	110.3	107.4	104.5	101.7
107.5°	139.9	140.3	140.6	140.9	141.2	141.5	141.8
110°	157.8	158.0	158.2	158.4	158.8	159.0	159.2



TEST NUMBER: P332895-840

CATALOG NUMBER: S124RDIP-S575D365U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	175.3	175.2	175.4	175.7	176.0	176.3	176.6
115°	201.8	202.0	202.0	202.0	202.0	202.0	202.0
117.5°	228.0	228.0	227.9	227.9	227.9	227.9	227.8
120°	244.6	244.8	244.8	244.6	244.4	244.3	244.1
122.5°	260.6	260.7	260.7	260.5	260.4	260.2	260.1
125°	283.4	283.6	283.8	283.9	284.0	284.0	284.1
127.5°	305.5	305.5	305.4	305.4	305.3	305.2	305.2
130°	319.3	319.4	319.4	319.4	319.4	319.4	319.4
132.5°	332.8	332.9	332.9	332.8	332.6	332.6	332.5
135°	351.3	351.4	351.6	351.7	351.9	352.1	352.2
137.5°	369.1	369.2	369.3	369.2	369.2	369.1	369.1
140°	380.1	380.3	380.5	380.6	380.6	380.7	380.8
142.5°	390.2	390.3	390.4	390.5	390.5	390.5	390.5
145°	404.7	404.7	404.8	405.0	405.2	405.3	405.5
147.5°	417.4	417.4	417.5	417.6	417.6	417.7	417.8
150°	425.5	425.5	425.5	425.6	425.7	425.7	425.8
152.5°	432.6	432.8	432.8	432.7	432.7	432.7	432.6
155°	442.4	442.7	442.8	442.5	442.3	442.1	441.8
157.5°	450.8	451.2	451.2	450.8	450.4	450.0	449.6
160°	456.2	456.6	456.6	456.2	455.7	455.1	454.6
162.5°	460.4	460.9	460.8	460.3	459.8	459.2	458.7
165°	466.6	467.3	467.2	466.5	465.7	465.0	464.3
167.5°	471.1	471.7	471.7	470.9	470.1	469.3	468.6
170°	473.7	474.3	474.2	473.5	472.7	471.9	471.1
172.5°	475.4	476.1	475.9	475.1	474.2	473.4	472.5
175°	477.6	478.3	478.2	477.2	476.3	475.2	474.3
177.5°	478.2	478.7	478.5	477.8	477.0	476.3	475.4
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2

(END OF REPORT)