

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332903-840

Luminaire Tested: **S124RDIP-S575D590U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332903-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D590U840-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4599.3 lumens  
Efficiency: N/A  
Efficacy: 140.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	34	29	34	29	26	29	26	23	20
8	56	43	36	31	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7873	7873	7873	7873
5°	9132	7896	6980	7896
10°	10803	7862	6229	7862
15°	12479	7789	5353	7789
20°	13894	7689	4840	7689
25°	14343	7591	4494	7591
30°	12557	7471	4285	7471
35°	9773	7295	4159	7295
40°	7330	7093	4091	7093
45°	5787	6769	4055	6769
50°	4886	6395	3939	6395
55°	4259	5985	3727	5985
60°	3831	5557	3299	5557
65°	3377	5096	2839	5096
70°	3043	4619	2561	4619
75°	2548	4095	2183	4095
80°	2157	3487	2046	3487
85°	1825	2732	1825	2732



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.5	2.1
10°-20°	285.0	6.2
20°-30°	445.8	9.7
30°-40°	495.6	10.8
40°-50°	439.7	9.6
50°-60°	342.6	7.4
60°-70°	224.3	4.9
70°-80°	110.3	2.4
80°-90°	28.8	0.6
90°-100°	211.8	4.6
100°-110°	440.8	9.6
110°-120°	394.8	8.6
120°-130°	332.1	7.2
130°-140°	276.9	6.0
140°-150°	211.5	4.6
150°-160°	148.7	3.2
160°-170°	87.5	1.9
170°-180°	28.5	0.6
0°-30°	825.3	17.9
0°-40°	1320.9	28.7
0°-60°	2103.3	45.7
0°-90°	2466.8	53.6
90°-120°	1047.4	22.8
90°-150°	1868.0	40.6
90°-180°	2133.0	46.4
0°-180°	4599.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	975	975	975	975	975	
5°	1127	974	861	974	1127	114
15°	1493	932	640	932	1493	425
25°	1610	852	504	852	1610	714
35°	992	740	422	740	992	622
45°	507	593	355	593	507	401
55°	303	425	265	425	303	275
65°	177	267	149	267	177	178
75°	82	131	70	131	82	90
85°	20	30	20	30	20	22
90°	12	1	12	1	12	11
95°	141	19	141	19	141	218
105°	810	67	810	67	810	801
115°	778	119	778	119	778	773
125°	621	165	621	165	621	564
135°	555	196	555	196	555	429
145°	453	226	453	226	453	287
155°	380	258	380	258	380	177
165°	331	280	331	280	331	95
175°	298	293	298	293	298	29
180°	293	293	293	293	293	



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1028.6	1031.5	1028.6	1028.3	1025.2	1024.3	1023.0	1019.0	1011.4	1006.9	1007.9
5°	1126.9	1136.7	1131.3	1130.4	1121.8	1113.2	1107.6	1095.1	1081.7	1072.7	1065.2
7.5°	1240.5	1246.2	1242.7	1237.2	1223.2	1215.3	1202.5	1186.0	1162.1	1143.7	1127.0
10°	1317.9	1322.5	1321.0	1310.8	1300.6	1279.7	1268.0	1244.8	1214.5	1190.5	1168.1
12.5°	1393.9	1399.0	1385.1	1385.6	1366.2	1349.8	1331.1	1302.0	1267.0	1236.1	1208.1
15°	1493.1	1486.8	1486.8	1478.9	1457.3	1434.5	1415.3	1384.6	1340.6	1303.7	1264.9
17.5°	1570.7	1573.0	1569.7	1551.2	1534.2	1510.7	1475.3	1439.6	1398.7	1349.1	1309.4
20°	1617.3	1617.3	1613.8	1601.1	1579.1	1554.0	1515.9	1477.0	1425.1	1375.2	1330.4
22.5°	1636.1	1637.4	1633.3	1622.9	1603.1	1578.5	1546.1	1506.5	1453.1	1396.9	1341.4
25°	1610.2	1617.6	1618.4	1615.7	1609.8	1594.9	1567.0	1526.5	1478.5	1417.6	1358.0
27.5°	1478.3	1487.7	1496.0	1509.5	1527.6	1537.1	1538.3	1517.7	1475.9	1417.3	1357.3
30°	1347.0	1354.7	1380.3	1413.7	1439.7	1463.2	1483.7	1489.1	1465.6	1412.9	1349.7
32.5°	1201.0	1211.7	1237.3	1273.2	1316.5	1356.3	1402.3	1425.6	1425.0	1393.4	1334.9
35°	991.7	999.6	1023.2	1060.9	1112.8	1172.0	1244.8	1301.3	1339.9	1337.1	1301.3
37.5°	799.8	808.7	832.5	863.8	914.1	987.5	1057.9	1135.9	1207.1	1247.1	1235.1
40°	695.5	695.9	719.0	751.2	798.4	862.4	939.1	1025.5	1104.9	1169.7	1182.2
42.5°	613.1	613.2	628.5	663.3	697.2	757.5	830.6	916.5	1009.4	1084.2	1117.5
45°	506.9	510.4	523.0	543.8	570.5	621.6	680.1	759.9	864.0	952.8	1008.2
47.5°	429.2	434.4	442.4	459.4	480.7	514.7	563.1	634.8	719.5	817.2	896.1
50°	389.0	389.8	400.0	409.4	427.9	455.0	497.5	557.1	635.0	728.8	816.5
52.5°	354.5	354.3	360.4	372.3	387.4	408.5	442.7	497.2	566.1	650.3	740.7
55°	302.6	304.5	309.2	318.6	330.0	345.0	372.1	412.9	467.2	539.1	621.2
57.5°	263.1	264.1	267.8	271.9	282.3	293.2	313.5	341.8	387.6	446.5	523.0
60°	237.3	237.7	238.9	244.8	253.1	263.3	277.0	300.9	339.5	393.3	453.8
62.5°	212.2	212.9	214.7	219.0	225.4	232.5	246.8	266.1	298.0	344.0	398.5
65°	176.8	177.2	180.0	181.6	186.6	192.9	203.5	216.5	238.5	277.0	318.3
67.5°	147.7	147.7	147.8	150.1	153.6	157.7	164.1	174.5	191.1	214.7	251.1
70°	128.9	128.9	129.7	130.9	132.8	136.3	139.9	147.7	160.0	179.2	207.0
72.5°	111.3	111.6	112.4	112.6	113.6	116.5	119.2	124.1	133.2	147.7	170.3
75°	81.7	82.9	84.8	86.4	88.4	88.1	90.8	93.9	96.6	105.3	118.3
77.5°	60.8	60.2	60.4	61.8	62.0	62.4	64.3	66.8	68.9	72.9	77.6
80°	46.4	46.4	47.6	48.0	47.6	48.0	49.9	51.1	51.9	53.4	57.8
82.5°	35.0	35.6	35.2	35.6	36.0	36.4	38.0	38.2	39.0	39.6	41.4
85°	19.7	20.0	20.4	19.7	19.7	19.7	20.4	20.8	21.6	21.2	22.0
87.5°	9.3	9.0	9.5	9.3	9.5	9.2	9.4	9.9	9.2	9.6	9.4
90°	12.1	12.1	12.6	12.1	11.5	11.5	10.9	10.4	9.8	10.4	9.2
92.5°	44.3	44.3	46.4	49.4	56.2	67.8	85.1	113.1	152.2	182.7	160.0
95°	140.6	148.0	158.4	176.3	204.5	260.3	337.6	426.9	482.7	469.5	354.3
97.5°	375.7	387.7	405.0	439.7	481.0	541.2	597.5	630.7	606.5	494.5	331.6
100°	528.3	532.9	550.2	585.3	635.4	678.0	706.3	694.8	610.7	463.1	300.7
102.5°	661.0	664.7	682.9	708.3	739.1	756.9	748.7	691.6	576.0	424.0	279.9
105°	810.5	814.0	822.0	826.7	825.6	801.9	744.9	645.2	513.3	377.9	262.2
107.5°	866.1	864.5	858.8	845.7	817.2	765.9	685.5	579.5	462.6	352.1	258.9
110°	867.0	861.8	851.4	827.3	786.4	723.0	639.4	539.8	437.3	343.4	259.8



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	839.8	831.4	816.9	787.6	741.1	677.8	598.8	510.8	422.9	339.2	262.6
115°	778.3	773.7	755.3	720.6	675.2	619.9	552.5	481.6	409.6	337.0	267.9
117.5°	716.0	712.4	693.7	664.7	625.8	579.0	525.9	467.3	403.6	336.4	273.5
120°	681.0	674.6	659.6	634.3	601.4	560.5	514.4	460.9	400.4	336.4	277.7
122.5°	653.3	646.9	634.3	612.6	584.8	549.0	507.1	455.3	396.7	336.0	281.9
125°	621.0	617.5	606.6	589.9	566.8	535.1	495.4	445.9	390.6	335.3	288.0
127.5°	602.1	598.6	589.5	574.6	551.4	521.4	481.7	434.3	382.4	334.0	293.0
130°	591.1	587.6	578.3	564.0	540.4	509.8	470.7	425.2	377.3	333.6	296.7
132.5°	578.7	575.1	566.4	550.2	526.9	496.4	458.2	415.5	372.7	333.1	299.9
135°	555.3	551.9	542.7	526.5	503.5	474.6	439.6	402.1	365.8	332.3	304.8
137.5°	526.5	522.4	514.8	498.9	477.4	451.3	421.7	390.0	359.8	332.2	307.6
140°	505.8	501.2	493.1	480.5	460.3	436.1	410.2	383.0	356.6	331.8	309.9
142.5°	483.6	480.5	473.3	461.5	443.7	422.7	400.5	376.7	353.9	331.8	311.7
145°	453.3	450.5	444.7	434.9	420.5	404.5	387.1	367.5	349.1	330.6	312.9
147.5°	426.6	425.5	421.1	412.7	402.1	389.4	375.6	360.0	344.9	328.6	313.4
150°	411.3	410.7	407.3	399.8	390.6	380.2	368.7	355.5	341.6	327.2	313.4
152.5°	397.5	396.9	394.9	388.7	380.9	372.3	361.7	350.3	337.9	324.9	312.5
155°	379.6	379.6	377.9	373.3	367.5	360.6	351.9	342.7	332.3	321.4	311.0
157.5°	364.0	364.0	362.9	359.5	355.1	349.5	342.3	334.6	326.8	317.9	309.6
160°	354.3	354.3	353.8	350.2	346.8	342.1	335.9	329.5	322.7	315.1	308.2
162.5°	345.1	345.6	345.0	341.5	339.0	334.8	329.8	324.5	318.9	312.4	306.8
165°	331.2	331.8	332.3	330.1	327.8	324.9	320.8	317.4	312.9	308.2	304.2
167.5°	320.3	320.7	320.8	319.4	318.2	316.5	313.3	310.6	307.3	304.1	301.4
170°	313.4	313.4	314.0	313.4	312.3	310.5	308.2	306.5	303.6	301.2	299.5
172.5°	306.5	307.4	308.0	307.4	306.7	305.5	304.1	302.8	300.3	298.5	297.7
175°	298.4	299.5	300.7	299.5	299.5	299.5	298.4	297.8	296.7	295.5	295.5
177.5°	293.7	294.6	295.5	295.1	295.5	295.1	295.1	294.6	294.2	293.7	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1004.8	1000.4	998.2	993.1	987.1	984.0	981.2	977.1	971.8	966.1	962.0
5°	1055.8	1046.3	1034.5	1020.4	1007.8	995.6	985.0	974.4	962.3	949.7	937.2
7.5°	1108.1	1089.5	1069.5	1046.3	1023.8	1003.3	984.4	966.3	945.9	927.6	910.9
10°	1144.6	1119.4	1091.6	1062.1	1032.6	1007.0	981.9	959.1	933.9	911.6	892.7
12.5°	1174.2	1144.6	1111.1	1074.3	1038.8	1007.9	979.1	949.4	920.8	896.5	871.3
15°	1223.1	1182.7	1137.5	1093.5	1047.5	1005.5	966.5	932.0	899.4	865.3	841.2
17.5°	1256.9	1208.8	1154.0	1101.1	1046.7	997.1	952.3	911.1	873.4	838.6	810.0
20°	1277.0	1224.0	1163.1	1102.9	1042.0	989.0	940.7	895.0	856.2	818.5	789.0
22.5°	1288.3	1229.6	1163.1	1100.0	1037.0	979.6	926.6	879.1	836.7	799.0	766.4
25°	1291.9	1229.0	1161.0	1088.7	1019.7	958.8	903.7	852.2	805.1	767.4	732.8
27.5°	1286.9	1212.8	1143.3	1069.0	997.7	933.5	875.8	821.6	774.5	734.0	698.5
30°	1279.3	1200.0	1125.3	1048.3	976.0	914.3	853.4	801.5	752.5	710.4	674.7
32.5°	1263.0	1184.3	1104.0	1025.0	951.8	888.3	830.5	778.3	730.1	687.1	649.1
35°	1230.6	1150.8	1063.6	982.7	910.8	844.8	790.5	740.2	694.3	648.3	608.2
37.5°	1187.9	1106.5	1019.7	931.1	859.1	796.8	747.0	699.8	654.9	613.0	568.6
40°	1147.7	1073.5	983.9	895.9	822.0	761.8	715.9	673.1	627.9	586.2	541.8
42.5°	1099.0	1035.7	945.2	856.9	784.0	726.0	683.2	641.4	600.3	559.9	513.5
45°	1017.6	969.8	884.8	800.0	726.5	669.1	629.9	592.9	556.7	518.3	474.6
47.5°	924.4	892.0	818.8	731.8	663.9	612.3	574.3	544.1	513.5	475.0	436.8
50°	859.7	838.9	768.2	688.8	624.0	576.4	537.6	509.2	483.7	446.8	412.5
52.5°	790.5	779.5	719.7	643.8	581.2	534.6	501.4	475.9	450.1	419.4	387.4
55°	685.3	691.2	640.5	574.8	515.9	476.7	446.4	425.2	403.1	377.2	352.4
57.5°	577.5	599.2	565.1	507.5	452.2	416.0	393.1	375.3	356.9	335.3	314.2
60°	513.1	531.2	512.0	461.3	412.9	379.2	358.0	344.2	325.7	306.1	289.9
62.5°	450.3	469.6	458.2	417.3	372.4	343.4	324.7	311.8	298.1	280.9	264.2
65°	371.3	383.8	378.4	350.1	318.3	293.5	276.2	266.8	254.2	241.7	226.7
67.5°	284.4	308.7	305.5	290.4	263.0	243.6	232.3	224.0	212.5	203.2	193.0
70°	233.8	256.2	255.8	243.6	228.6	210.6	202.8	195.7	185.4	176.4	168.1
72.5°	191.4	211.9	214.9	205.6	195.4	181.7	174.1	169.3	159.4	153.2	146.4
75°	134.0	149.0	152.9	152.9	148.1	141.1	134.4	131.3	124.1	118.7	114.7
77.5°	87.9	97.3	103.4	104.8	105.5	103.2	97.7	95.4	90.1	88.1	84.3
80°	62.1	68.4	75.4	77.8	79.8	79.0	76.6	75.0	70.0	68.0	66.4
82.5°	42.9	46.4	52.2	57.4	56.9	58.9	56.9	55.5	51.7	51.0	49.4
85°	22.4	22.8	23.5	27.1	29.1	29.9	30.3	29.5	28.3	28.3	25.5
87.5°	9.2	8.9	8.8	8.8	9.0	10.1	10.7	10.8	10.1	9.5	8.7
90°	8.1	8.1	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	116.3	71.7	42.4	30.4	22.0	14.9	9.6	6.6	9.6	14.9	22.0
95°	216.6	122.1	72.0	47.8	34.0	26.5	20.7	19.0	20.7	26.5	34.0
97.5°	194.7	116.7	78.2	57.9	45.9	39.1	34.1	34.1	34.1	39.1	45.9
100°	183.2	118.1	84.1	65.6	54.7	47.8	43.8	43.8	43.8	47.8	54.7
102.5°	180.0	122.7	91.9	74.4	63.9	57.5	53.9	53.0	53.9	57.5	63.9
105°	181.5	133.6	106.0	89.3	79.0	72.0	69.2	67.4	69.2	72.0	79.0
107.5°	190.0	146.4	121.1	104.6	94.7	87.4	84.4	83.3	84.4	87.4	94.7
110°	196.4	156.1	130.8	115.2	104.8	98.0	95.0	93.9	95.0	98.0	104.8





TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	203.4	165.3	140.9	125.3	115.0	108.6	105.2	104.0	105.2	108.6	115.0
115°	214.3	179.8	156.7	141.2	130.2	124.4	120.4	118.7	120.4	124.4	130.2
117.5°	225.5	193.7	171.8	155.6	145.4	139.1	135.5	133.9	135.5	139.1	145.4
120°	233.3	203.4	181.5	165.3	155.5	149.2	145.2	144.0	145.2	149.2	155.5
122.5°	240.7	212.6	190.7	175.0	164.3	158.4	154.4	153.2	154.4	158.4	164.3
125°	251.8	225.2	204.5	188.3	177.4	171.1	167.6	165.3	167.6	171.1	177.4
127.5°	261.4	237.0	216.9	200.7	189.2	182.1	177.9	176.0	177.9	182.1	189.2
130°	267.3	244.8	225.2	208.5	197.6	188.9	184.3	182.1	184.3	188.9	197.6
132.5°	273.3	251.3	231.7	215.9	204.1	195.9	189.9	188.0	189.9	195.9	204.1
135°	281.1	260.3	241.4	226.4	214.3	204.5	198.7	196.4	198.7	204.5	214.3
137.5°	286.7	267.3	249.5	235.3	222.7	213.4	207.0	204.9	207.0	213.4	222.7
140°	290.3	272.0	254.6	240.8	228.7	218.9	212.6	210.9	212.6	218.9	228.7
142.5°	293.1	276.1	259.2	245.9	234.2	224.9	219.0	217.3	219.0	224.9	234.2
145°	296.1	280.5	265.6	252.9	242.0	233.9	228.1	226.4	228.1	233.9	242.0
147.5°	298.7	285.2	271.1	259.7	250.5	242.3	237.2	236.6	237.2	242.3	250.5
150°	300.1	287.5	274.8	263.9	255.2	248.3	243.7	243.1	243.7	248.3	255.2
152.5°	301.0	289.3	278.0	268.0	260.2	253.8	249.2	249.1	249.2	253.8	260.2
155°	301.8	292.1	282.3	273.7	267.3	261.6	258.1	257.5	258.1	261.6	267.3
157.5°	301.8	294.1	285.7	278.9	273.4	268.9	265.7	265.7	265.7	268.9	273.4
160°	301.8	295.0	288.0	281.7	277.1	273.1	270.7	270.7	270.7	273.1	277.1
162.5°	301.8	295.9	289.4	284.5	280.3	276.7	274.9	275.4	274.9	276.7	280.3
165°	300.7	296.1	290.9	287.5	284.6	281.7	280.5	280.5	280.5	281.7	284.6
167.5°	299.3	296.0	292.2	289.5	287.9	285.7	285.2	285.7	285.2	285.7	287.9
170°	298.4	295.5	292.7	290.9	289.7	288.0	287.5	288.0	287.5	288.0	289.7
172.5°	297.5	295.1	293.1	291.9	291.1	289.8	289.7	290.3	289.7	289.8	291.1
175°	296.1	294.4	293.3	293.3	292.7	292.1	292.1	292.7	292.1	292.1	292.7
177.5°	294.6	293.7	293.3	293.3	293.3	292.8	293.3	293.7	293.3	292.8	293.3
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	957.7	954.5	950.4	945.6	940.0	935.0	932.8	934.6	935.6	933.1	932.8
5°	928.5	918.7	910.8	899.0	889.6	881.7	876.2	873.8	874.6	868.4	866.8
7.5°	895.6	884.0	871.2	857.2	844.1	832.6	826.6	823.2	816.6	813.7	808.9
10°	874.6	858.9	846.4	829.8	815.0	801.1	794.5	789.0	782.3	779.1	772.4
12.5°	852.9	834.8	820.9	803.8	788.5	771.9	765.6	755.4	744.9	738.3	729.7
15°	822.3	800.4	783.5	763.1	745.0	726.1	709.2	690.3	683.3	668.3	659.7
17.5°	786.6	764.3	743.4	716.0	688.1	664.7	646.6	628.6	617.7	608.2	603.8
20°	763.1	742.7	713.6	681.8	650.7	624.7	610.2	598.4	586.6	580.0	575.2
22.5°	740.7	714.7	680.9	646.5	615.5	595.2	582.9	570.8	561.2	554.8	548.6
25°	703.4	669.1	633.4	594.1	572.9	555.2	541.8	532.0	526.1	517.9	514.7
27.5°	664.9	623.5	584.0	557.6	535.5	519.4	507.8	500.4	492.9	487.6	483.5
30°	635.3	593.3	558.0	532.8	510.4	497.1	487.6	479.0	473.1	468.8	465.6
32.5°	606.1	564.1	534.3	507.4	489.7	476.7	466.6	460.1	455.4	449.9	448.0
35°	563.8	526.5	500.6	476.3	458.2	446.4	438.5	431.8	427.9	426.4	425.2
37.5°	523.2	492.6	464.7	444.7	428.7	419.4	410.1	406.9	404.1	401.3	402.6
40°	497.5	468.8	444.0	422.8	409.8	399.6	394.0	390.2	387.8	387.8	387.8
42.5°	475.1	447.1	422.9	403.9	390.9	382.3	376.2	372.8	372.1	371.7	373.7
45°	440.5	414.5	390.2	374.5	363.5	354.8	351.2	348.5	348.5	350.1	350.5
47.5°	406.2	381.8	362.2	344.7	334.6	329.2	326.1	324.7	324.9	326.4	328.2
50°	385.1	361.1	341.8	326.1	316.7	311.5	308.8	308.0	308.8	308.8	311.5
52.5°	362.1	340.6	321.7	308.5	297.8	293.1	291.5	290.4	290.9	292.2	293.4
55°	328.5	309.2	291.1	278.6	270.7	267.6	264.1	264.5	263.7	264.5	264.5
57.5°	294.8	277.5	260.6	250.6	243.8	239.2	235.4	236.4	235.3	235.1	234.5
60°	273.1	254.2	240.9	231.9	224.0	220.0	216.5	217.3	216.1	215.3	213.8
62.5°	249.5	233.8	221.1	212.4	206.0	201.5	197.9	197.1	194.4	191.8	188.2
65°	215.3	202.4	191.0	182.7	176.8	173.3	170.6	168.1	162.3	156.0	152.9
67.5°	182.1	172.7	162.1	155.1	150.4	145.7	140.5	136.4	130.9	127.4	125.5
70°	160.7	151.7	142.6	135.9	130.9	126.5	120.6	117.9	113.9	112.4	110.4
72.5°	140.3	131.9	123.4	117.4	112.0	108.6	104.0	101.2	99.5	98.9	96.8
75°	109.3	102.6	96.2	90.8	86.4	84.1	82.1	80.2	79.4	75.8	73.8
77.5°	79.7	75.2	71.4	67.5	64.3	62.8	59.0	56.8	55.4	53.7	53.3
80°	62.1	59.0	55.0	52.6	48.4	46.8	45.1	44.8	44.4	44.0	43.6
82.5°	46.7	43.5	39.6	38.2	37.1	36.1	35.1	34.7	34.3	34.5	34.5
85°	23.5	22.0	22.0	21.6	21.2	20.8	20.4	20.4	20.0	20.4	20.0
87.5°	8.8	8.5	9.2	8.5	9.1	9.3	8.9	9.0	9.4	8.9	8.9
90°	4.6	4.6	8.1	8.1	9.2	10.4	9.8	10.4	10.9	11.5	11.5
92.5°	30.4	42.4	71.7	116.3	160.0	182.7	152.2	113.1	85.1	67.8	56.2
95°	47.8	72.0	122.1	216.6	354.3	469.5	482.7	426.9	337.6	260.3	204.5
97.5°	57.9	78.2	116.7	194.7	331.6	494.5	606.5	630.7	597.5	541.2	481.0
100°	65.6	84.1	118.1	183.2	300.7	463.1	610.7	694.8	706.3	678.0	635.4
102.5°	74.4	91.9	122.7	180.0	279.9	424.0	576.0	691.6	748.7	756.9	739.1
105°	89.3	106.0	133.6	181.5	262.2	377.9	513.3	645.2	744.9	801.9	825.6
107.5°	104.6	121.1	146.4	190.0	258.9	352.1	462.6	579.5	685.5	765.9	817.2
110°	115.2	130.8	156.1	196.4	259.8	343.4	437.3	539.8	639.4	723.0	786.4



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	125.3	140.9	165.3	203.4	262.6	339.2	422.9	510.8	598.8	677.8	741.1
115°	141.2	156.7	179.8	214.3	267.9	337.0	409.6	481.6	552.5	619.9	675.2
117.5°	155.6	171.8	193.7	225.5	273.5	336.4	403.6	467.3	525.9	579.0	625.8
120°	165.3	181.5	203.4	233.3	277.7	336.4	400.4	460.9	514.4	560.5	601.4
122.5°	175.0	190.7	212.6	240.7	281.9	336.0	396.7	455.3	507.1	549.0	584.8
125°	188.3	204.5	225.2	251.8	288.0	335.3	390.6	445.9	495.4	535.1	566.8
127.5°	200.7	216.9	237.0	261.4	293.0	334.0	382.4	434.3	481.7	521.4	551.4
130°	208.5	225.2	244.8	267.3	296.7	333.6	377.3	425.2	470.7	509.8	540.4
132.5°	215.9	231.7	251.3	273.3	299.9	333.1	372.7	415.5	458.2	496.4	526.9
135°	226.4	241.4	260.3	281.1	304.8	332.3	365.8	402.1	439.6	474.6	503.5
137.5°	235.3	249.5	267.3	286.7	307.6	332.2	359.8	390.0	421.7	451.3	477.4
140°	240.8	254.6	272.0	290.3	309.9	331.8	356.6	383.0	410.2	436.1	460.3
142.5°	245.9	259.2	276.1	293.1	311.7	331.8	353.9	376.7	400.5	422.7	443.7
145°	252.9	265.6	280.5	296.1	312.9	330.6	349.1	367.5	387.1	404.5	420.5
147.5°	259.7	271.1	285.2	298.7	313.4	328.6	344.9	360.0	375.6	389.4	402.1
150°	263.9	274.8	287.5	300.1	313.4	327.2	341.6	355.5	368.7	380.2	390.6
152.5°	268.0	278.0	289.3	301.0	312.5	324.9	337.9	350.3	361.7	372.3	380.9
155°	273.7	282.3	292.1	301.8	311.0	321.4	332.3	342.7	351.9	360.6	367.5
157.5°	278.9	285.7	294.1	301.8	309.6	317.9	326.8	334.6	342.3	349.5	355.1
160°	281.7	288.0	295.0	301.8	308.2	315.1	322.7	329.5	335.9	342.1	346.8
162.5°	284.5	289.4	295.9	301.8	306.8	312.4	318.9	324.5	329.8	334.8	339.0
165°	287.5	290.9	296.1	300.7	304.2	308.2	312.9	317.4	320.8	324.9	327.8
167.5°	289.5	292.2	296.0	299.3	301.4	304.1	307.3	310.6	313.3	316.5	318.2
170°	290.9	292.7	295.5	298.4	299.5	301.2	303.6	306.5	308.2	310.5	312.3
172.5°	291.9	293.1	295.1	297.5	297.7	298.5	300.3	302.8	304.1	305.5	306.7
175°	293.3	293.3	294.4	296.1	295.5	295.5	296.7	297.8	298.4	299.5	299.5
177.5°	293.3	293.3	293.7	294.6	293.7	293.7	294.2	294.6	295.1	295.1	295.5
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	930.9	931.5	929.4	928.7	929.4	931.5	930.9	932.8	933.1	935.6	934.6
5°	863.6	862.8	860.9	861.3	860.9	862.8	863.6	866.8	868.4	874.6	873.8
7.5°	806.1	803.0	804.0	800.7	804.0	803.0	806.1	808.9	813.7	816.6	823.2
10°	770.9	766.6	763.1	759.9	763.1	766.6	770.9	772.4	779.1	782.3	789.0
12.5°	722.9	719.1	714.3	715.3	714.3	719.1	722.9	729.7	738.3	744.9	755.4
15°	654.6	648.7	639.2	640.5	639.2	648.7	654.6	659.7	668.3	683.3	690.3
17.5°	596.8	596.9	592.6	593.6	592.6	596.9	596.8	603.8	608.2	617.7	628.6
20°	566.9	564.2	564.6	563.4	564.6	564.2	566.9	575.2	580.0	586.6	598.4
22.5°	546.2	542.9	540.1	537.7	540.1	542.9	546.2	548.6	554.8	561.2	570.8
25°	511.2	508.9	505.3	504.5	505.3	508.9	511.2	514.7	517.9	526.1	532.0
27.5°	480.4	479.9	478.5	476.7	478.5	479.9	480.4	483.5	487.6	492.9	500.4
30°	462.4	461.7	460.9	459.7	460.9	461.7	462.4	465.6	468.8	473.1	479.0
32.5°	446.5	446.0	445.1	445.2	445.1	446.0	446.5	448.0	449.9	455.4	460.1
35°	423.5	423.1	422.4	422.0	422.4	423.1	423.5	425.2	426.4	427.9	431.8
37.5°	402.2	403.2	402.7	402.6	402.7	403.2	402.2	402.6	401.3	404.1	406.9
40°	387.4	387.8	388.6	388.2	388.6	387.8	387.4	387.8	387.8	387.8	390.2
42.5°	375.2	375.3	376.4	375.0	376.4	375.3	375.2	373.7	371.7	372.1	372.8
45°	353.3	355.6	355.2	355.2	355.2	355.6	353.3	350.5	350.1	348.5	348.5
47.5°	329.2	331.3	331.8	331.7	331.8	331.3	329.2	328.2	326.4	324.9	324.7
50°	313.6	312.8	314.0	313.6	314.0	312.8	313.6	311.5	308.8	308.8	308.0
52.5°	294.4	294.6	294.5	294.1	294.5	294.6	294.4	293.4	292.2	290.9	290.4
55°	264.8	265.2	264.5	264.8	264.5	265.2	264.8	264.5	264.5	263.7	264.5
57.5°	232.8	230.9	231.7	230.8	231.7	230.9	232.8	234.5	235.1	235.3	236.4
60°	209.8	206.7	205.9	204.3	205.9	206.7	209.8	213.8	215.3	216.1	217.3
62.5°	184.0	181.9	179.2	180.5	179.2	181.9	184.0	188.2	191.8	194.4	197.1
65°	149.7	148.1	146.9	148.6	146.9	148.1	149.7	152.9	156.0	162.3	168.1
67.5°	123.9	123.1	123.1	122.3	123.1	123.1	123.9	125.5	127.4	130.9	136.4
70°	110.4	109.3	109.3	108.5	109.3	109.3	110.4	110.4	112.4	113.9	117.9
72.5°	96.5	95.4	95.7	95.2	95.7	95.4	96.5	96.8	98.9	99.5	101.2
75°	71.5	69.6	69.6	70.0	69.6	69.6	71.5	73.8	75.8	79.4	80.2
77.5°	53.3	52.9	53.5	52.8	53.5	52.9	53.3	53.3	53.7	55.4	56.8
80°	43.6	43.2	42.8	44.0	42.8	43.2	43.6	43.6	44.0	44.4	44.8
82.5°	33.8	33.8	33.7	35.2	33.7	33.8	33.8	34.5	34.5	34.3	34.7
85°	20.4	19.7	20.4	19.7	20.4	19.7	20.4	20.0	20.4	20.0	20.4
87.5°	9.7	9.5	9.0	9.3	9.0	9.5	9.7	8.9	8.9	9.4	9.0
90°	12.1	12.6	12.1	12.1	12.1	12.6	12.1	11.5	11.5	10.9	10.4
92.5°	49.4	46.4	44.3	44.3	44.3	46.4	49.4	56.2	67.8	85.1	113.1
95°	176.3	158.4	148.0	140.6	148.0	158.4	176.3	204.5	260.3	337.6	426.9
97.5°	439.7	405.0	387.7	375.7	387.7	405.0	439.7	481.0	541.2	597.5	630.7
100°	585.3	550.2	532.9	528.3	532.9	550.2	585.3	635.4	678.0	706.3	694.8
102.5°	708.3	682.9	664.7	661.0	664.7	682.9	708.3	739.1	756.9	748.7	691.6
105°	826.7	822.0	814.0	810.5	814.0	822.0	826.7	825.6	801.9	744.9	645.2
107.5°	845.7	858.8	864.5	866.1	864.5	858.8	845.7	817.2	765.9	685.5	579.5
110°	827.3	851.4	861.8	867.0	861.8	851.4	827.3	786.4	723.0	639.4	539.8



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	787.6	816.9	831.4	839.8	831.4	816.9	787.6	741.1	677.8	598.8	510.8
115°	720.6	755.3	773.7	778.3	773.7	755.3	720.6	675.2	619.9	552.5	481.6
117.5°	664.7	693.7	712.4	716.0	712.4	693.7	664.7	625.8	579.0	525.9	467.3
120°	634.3	659.6	674.6	681.0	674.6	659.6	634.3	601.4	560.5	514.4	460.9
122.5°	612.6	634.3	646.9	653.3	646.9	634.3	612.6	584.8	549.0	507.1	455.3
125°	589.9	606.6	617.5	621.0	617.5	606.6	589.9	566.8	535.1	495.4	445.9
127.5°	574.6	589.5	598.6	602.1	598.6	589.5	574.6	551.4	521.4	481.7	434.3
130°	564.0	578.3	587.6	591.1	587.6	578.3	564.0	540.4	509.8	470.7	425.2
132.5°	550.2	566.4	575.1	578.7	575.1	566.4	550.2	526.9	496.4	458.2	415.5
135°	526.5	542.7	551.9	555.3	551.9	542.7	526.5	503.5	474.6	439.6	402.1
137.5°	498.9	514.8	522.4	526.5	522.4	514.8	498.9	477.4	451.3	421.7	390.0
140°	480.5	493.1	501.2	505.8	501.2	493.1	480.5	460.3	436.1	410.2	383.0
142.5°	461.5	473.3	480.5	483.6	480.5	473.3	461.5	443.7	422.7	400.5	376.7
145°	434.9	444.7	450.5	453.3	450.5	444.7	434.9	420.5	404.5	387.1	367.5
147.5°	412.7	421.1	425.5	426.6	425.5	421.1	412.7	402.1	389.4	375.6	360.0
150°	399.8	407.3	410.7	411.3	410.7	407.3	399.8	390.6	380.2	368.7	355.5
152.5°	388.7	394.9	396.9	397.5	396.9	394.9	388.7	380.9	372.3	361.7	350.3
155°	373.3	377.9	379.6	379.6	379.6	377.9	373.3	367.5	360.6	351.9	342.7
157.5°	359.5	362.9	364.0	364.0	364.0	362.9	359.5	355.1	349.5	342.3	334.6
160°	350.2	353.8	354.3	354.3	354.3	353.8	350.2	346.8	342.1	335.9	329.5
162.5°	341.5	345.0	345.6	345.1	345.6	345.0	341.5	339.0	334.8	329.8	324.5
165°	330.1	332.3	331.8	331.2	331.8	332.3	330.1	327.8	324.9	320.8	317.4
167.5°	319.4	320.8	320.7	320.3	320.7	320.8	319.4	318.2	316.5	313.3	310.6
170°	313.4	314.0	313.4	313.4	313.4	314.0	313.4	312.3	310.5	308.2	306.5
172.5°	307.4	308.0	307.4	306.5	307.4	308.0	307.4	306.7	305.5	304.1	302.8
175°	299.5	300.7	299.5	298.4	299.5	300.7	299.5	299.5	299.5	298.4	297.8
177.5°	295.1	295.5	294.6	293.7	294.6	295.5	295.1	295.5	295.1	295.1	294.6
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	932.8	935.0	940.0	945.6	950.4	954.5	957.7	962.0	966.1	971.8	977.1
5°	876.2	881.7	889.6	899.0	910.8	918.7	928.5	937.2	949.7	962.3	974.4
7.5°	826.6	832.6	844.1	857.2	871.2	884.0	895.6	910.9	927.6	945.9	966.3
10°	794.5	801.1	815.0	829.8	846.4	858.9	874.6	892.7	911.6	933.9	959.1
12.5°	765.6	771.9	788.5	803.8	820.9	834.8	852.9	871.3	896.5	920.8	949.4
15°	709.2	726.1	745.0	763.1	783.5	800.4	822.3	841.2	865.3	899.4	932.0
17.5°	646.6	664.7	688.1	716.0	743.4	764.3	786.6	810.0	838.6	873.4	911.1
20°	610.2	624.7	650.7	681.8	713.6	742.7	763.1	789.0	818.5	856.2	895.0
22.5°	582.9	595.2	615.5	646.5	680.9	714.7	740.7	766.4	799.0	836.7	879.1
25°	541.8	555.2	572.9	594.1	633.4	669.1	703.4	732.8	767.4	805.1	852.2
27.5°	507.8	519.4	535.5	557.6	584.0	623.5	664.9	698.5	734.0	774.5	821.6
30°	487.6	497.1	510.4	532.8	558.0	593.3	635.3	674.7	710.4	752.5	801.5
32.5°	466.6	476.7	489.7	507.4	534.3	564.1	606.1	649.1	687.1	730.1	778.3
35°	438.5	446.4	458.2	476.3	500.6	526.5	563.8	608.2	648.3	694.3	740.2
37.5°	410.1	419.4	428.7	444.7	464.7	492.6	523.2	568.6	613.0	654.9	699.8
40°	394.0	399.6	409.8	422.8	444.0	468.8	497.5	541.8	586.2	627.9	673.1
42.5°	376.2	382.3	390.9	403.9	422.9	447.1	475.1	513.5	559.9	600.3	641.4
45°	351.2	354.8	363.5	374.5	390.2	414.5	440.5	474.6	518.3	556.7	592.9
47.5°	326.1	329.2	334.6	344.7	362.2	381.8	406.2	436.8	475.0	513.5	544.1
50°	308.8	311.5	316.7	326.1	341.8	361.1	385.1	412.5	446.8	483.7	509.2
52.5°	291.5	293.1	297.8	308.5	321.7	340.6	362.1	387.4	419.4	450.1	475.9
55°	264.1	267.6	270.7	278.6	291.1	309.2	328.5	352.4	377.2	403.1	425.2
57.5°	235.4	239.2	243.8	250.6	260.6	277.5	294.8	314.2	335.3	356.9	375.3
60°	216.5	220.0	224.0	231.9	240.9	254.2	273.1	289.9	306.1	325.7	344.2
62.5°	197.9	201.5	206.0	212.4	221.1	233.8	249.5	264.2	280.9	298.1	311.8
65°	170.6	173.3	176.8	182.7	191.0	202.4	215.3	226.7	241.7	254.2	266.8
67.5°	140.5	145.7	150.4	155.1	162.1	172.7	182.1	193.0	203.2	212.5	224.0
70°	120.6	126.5	130.9	135.9	142.6	151.7	160.7	168.1	176.4	185.4	195.7
72.5°	104.0	108.6	112.0	117.4	123.4	131.9	140.3	146.4	153.2	159.4	169.3
75°	82.1	84.1	86.4	90.8	96.2	102.6	109.3	114.7	118.7	124.1	131.3
77.5°	59.0	62.8	64.3	67.5	71.4	75.2	79.7	84.3	88.1	90.1	95.4
80°	45.1	46.8	48.4	52.6	55.0	59.0	62.1	66.4	68.0	70.0	75.0
82.5°	35.1	36.1	37.1	38.2	39.6	43.5	46.7	49.4	51.0	51.7	55.5
85°	20.4	20.8	21.2	21.6	22.0	22.0	23.5	25.5	28.3	28.3	29.5
87.5°	8.9	9.3	9.1	8.5	9.2	8.5	8.8	8.7	9.5	10.1	10.8
90°	9.8	10.4	9.2	8.1	8.1	4.6	4.6	4.0	3.4	1.7	0.6
92.5°	152.2	182.7	160.0	116.3	71.7	42.4	30.4	22.0	14.9	9.6	6.6
95°	482.7	469.5	354.3	216.6	122.1	72.0	47.8	34.0	26.5	20.7	19.0
97.5°	606.5	494.5	331.6	194.7	116.7	78.2	57.9	45.9	39.1	34.1	34.1
100°	610.7	463.1	300.7	183.2	118.1	84.1	65.6	54.7	47.8	43.8	43.8
102.5°	576.0	424.0	279.9	180.0	122.7	91.9	74.4	63.9	57.5	53.9	53.0
105°	513.3	377.9	262.2	181.5	133.6	106.0	89.3	79.0	72.0	69.2	67.4
107.5°	462.6	352.1	258.9	190.0	146.4	121.1	104.6	94.7	87.4	84.4	83.3
110°	437.3	343.4	259.8	196.4	156.1	130.8	115.2	104.8	98.0	95.0	93.9



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	422.9	339.2	262.6	203.4	165.3	140.9	125.3	115.0	108.6	105.2	104.0
115°	409.6	337.0	267.9	214.3	179.8	156.7	141.2	130.2	124.4	120.4	118.7
117.5°	403.6	336.4	273.5	225.5	193.7	171.8	155.6	145.4	139.1	135.5	133.9
120°	400.4	336.4	277.7	233.3	203.4	181.5	165.3	155.5	149.2	145.2	144.0
122.5°	396.7	336.0	281.9	240.7	212.6	190.7	175.0	164.3	158.4	154.4	153.2
125°	390.6	335.3	288.0	251.8	225.2	204.5	188.3	177.4	171.1	167.6	165.3
127.5°	382.4	334.0	293.0	261.4	237.0	216.9	200.7	189.2	182.1	177.9	176.0
130°	377.3	333.6	296.7	267.3	244.8	225.2	208.5	197.6	188.9	184.3	182.1
132.5°	372.7	333.1	299.9	273.3	251.3	231.7	215.9	204.1	195.9	189.9	188.0
135°	365.8	332.3	304.8	281.1	260.3	241.4	226.4	214.3	204.5	198.7	196.4
137.5°	359.8	332.2	307.6	286.7	267.3	249.5	235.3	222.7	213.4	207.0	204.9
140°	356.6	331.8	309.9	290.3	272.0	254.6	240.8	228.7	218.9	212.6	210.9
142.5°	353.9	331.8	311.7	293.1	276.1	259.2	245.9	234.2	224.9	219.0	217.3
145°	349.1	330.6	312.9	296.1	280.5	265.6	252.9	242.0	233.9	228.1	226.4
147.5°	344.9	328.6	313.4	298.7	285.2	271.1	259.7	250.5	242.3	237.2	236.6
150°	341.6	327.2	313.4	300.1	287.5	274.8	263.9	255.2	248.3	243.7	243.1
152.5°	337.9	324.9	312.5	301.0	289.3	278.0	268.0	260.2	253.8	249.2	249.1
155°	332.3	321.4	311.0	301.8	292.1	282.3	273.7	267.3	261.6	258.1	257.5
157.5°	326.8	317.9	309.6	301.8	294.1	285.7	278.9	273.4	268.9	265.7	265.7
160°	322.7	315.1	308.2	301.8	295.0	288.0	281.7	277.1	273.1	270.7	270.7
162.5°	318.9	312.4	306.8	301.8	295.9	289.4	284.5	280.3	276.7	274.9	275.4
165°	312.9	308.2	304.2	300.7	296.1	290.9	287.5	284.6	281.7	280.5	280.5
167.5°	307.3	304.1	301.4	299.3	296.0	292.2	289.5	287.9	285.7	285.2	285.7
170°	303.6	301.2	299.5	298.4	295.5	292.7	290.9	289.7	288.0	287.5	288.0
172.5°	300.3	298.5	297.7	297.5	295.1	293.1	291.9	291.1	289.8	289.7	290.3
175°	296.7	295.5	295.5	296.1	294.4	293.3	293.3	292.7	292.1	292.1	292.7
177.5°	294.2	293.7	293.7	294.6	293.7	293.3	293.3	293.3	292.8	293.3	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	981.2	984.0	987.1	993.1	998.2	1000.4	1004.8	1007.9	1006.9	1011.4	1019.0
5°	985.0	995.6	1007.8	1020.4	1034.5	1046.3	1055.8	1065.2	1072.7	1081.7	1095.1
7.5°	984.4	1003.3	1023.8	1046.3	1069.5	1089.5	1108.1	1127.0	1143.7	1162.1	1186.0
10°	981.9	1007.0	1032.6	1062.1	1091.6	1119.4	1144.6	1168.1	1190.5	1214.5	1244.8
12.5°	979.1	1007.9	1038.8	1074.3	1111.1	1144.6	1174.2	1208.1	1236.1	1267.0	1302.0
15°	966.5	1005.5	1047.5	1093.5	1137.5	1182.7	1223.1	1264.9	1303.7	1340.6	1384.6
17.5°	952.3	997.1	1046.7	1101.1	1154.0	1208.8	1256.9	1309.4	1349.1	1398.7	1439.6
20°	940.7	989.0	1042.0	1102.9	1163.1	1224.0	1277.0	1330.4	1375.2	1425.1	1477.0
22.5°	926.6	979.6	1037.0	1100.0	1163.1	1229.6	1288.3	1341.4	1396.9	1453.1	1506.5
25°	903.7	958.8	1019.7	1088.7	1161.0	1229.0	1291.9	1358.0	1417.6	1478.5	1526.5
27.5°	875.8	933.5	997.7	1069.0	1143.3	1212.8	1286.9	1357.3	1417.3	1475.9	1517.7
30°	853.4	914.3	976.0	1048.3	1125.3	1200.0	1279.3	1349.7	1412.9	1465.6	1489.1
32.5°	830.5	888.3	951.8	1025.0	1104.0	1184.3	1263.0	1334.9	1393.4	1425.0	1425.6
35°	790.5	844.8	910.8	982.7	1063.6	1150.8	1230.6	1301.3	1337.1	1339.9	1301.3
37.5°	747.0	796.8	859.1	931.1	1019.7	1106.5	1187.9	1235.1	1247.1	1207.1	1135.9
40°	715.9	761.8	822.0	895.9	983.9	1073.5	1147.7	1182.2	1169.7	1104.9	1025.5
42.5°	683.2	726.0	784.0	856.9	945.2	1035.7	1099.0	1117.5	1084.2	1009.4	916.5
45°	629.9	669.1	726.5	800.0	884.8	969.8	1017.6	1008.2	952.8	864.0	759.9
47.5°	574.3	612.3	663.9	731.8	818.8	892.0	924.4	896.1	817.2	719.5	634.8
50°	537.6	576.4	624.0	688.8	768.2	838.9	859.7	816.5	728.8	635.0	557.1
52.5°	501.4	534.6	581.2	643.8	719.7	779.5	790.5	740.7	650.3	566.1	497.2
55°	446.4	476.7	515.9	574.8	640.5	691.2	685.3	621.2	539.1	467.2	412.9
57.5°	393.1	416.0	452.2	507.5	565.1	599.2	577.5	523.0	446.5	387.6	341.8
60°	358.0	379.2	412.9	461.3	512.0	531.2	513.1	453.8	393.3	339.5	300.9
62.5°	324.7	343.4	372.4	417.3	458.2	469.6	450.3	398.5	344.0	298.0	266.1
65°	276.2	293.5	318.3	350.1	378.4	383.8	371.3	318.3	277.0	238.5	216.5
67.5°	232.3	243.6	263.0	290.4	305.5	308.7	284.4	251.1	214.7	191.1	174.5
70°	202.8	210.6	228.6	243.6	255.8	256.2	233.8	207.0	179.2	160.0	147.7
72.5°	174.1	181.7	195.4	205.6	214.9	211.9	191.4	170.3	147.7	133.2	124.1
75°	134.4	141.1	148.1	152.9	152.9	149.0	134.0	118.3	105.3	96.6	93.9
77.5°	97.7	103.2	105.5	104.8	103.4	97.3	87.9	77.6	72.9	68.9	66.8
80°	76.6	79.0	79.8	77.8	75.4	68.4	62.1	57.8	53.4	51.9	51.1
82.5°	56.9	58.9	56.9	57.4	52.2	46.4	42.9	41.4	39.6	39.0	38.2
85°	30.3	29.9	29.1	27.1	23.5	22.8	22.4	22.0	21.2	21.6	20.8
87.5°	10.7	10.1	9.0	8.8	8.8	8.9	9.2	9.4	9.6	9.2	9.9
90°	1.7	3.4	4.0	4.6	4.6	8.1	8.1	9.2	10.4	9.8	10.4
92.5°	9.6	14.9	22.0	30.4	42.4	71.7	116.3	160.0	182.7	152.2	113.1
95°	20.7	26.5	34.0	47.8	72.0	122.1	216.6	354.3	469.5	482.7	426.9
97.5°	34.1	39.1	45.9	57.9	78.2	116.7	194.7	331.6	494.5	606.5	630.7
100°	43.8	47.8	54.7	65.6	84.1	118.1	183.2	300.7	463.1	610.7	694.8
102.5°	53.9	57.5	63.9	74.4	91.9	122.7	180.0	279.9	424.0	576.0	691.6
105°	69.2	72.0	79.0	89.3	106.0	133.6	181.5	262.2	377.9	513.3	645.2
107.5°	84.4	87.4	94.7	104.6	121.1	146.4	190.0	258.9	352.1	462.6	579.5
110°	95.0	98.0	104.8	115.2	130.8	156.1	196.4	259.8	343.4	437.3	539.8





TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	105.2	108.6	115.0	125.3	140.9	165.3	203.4	262.6	339.2	422.9	510.8
115°	120.4	124.4	130.2	141.2	156.7	179.8	214.3	267.9	337.0	409.6	481.6
117.5°	135.5	139.1	145.4	155.6	171.8	193.7	225.5	273.5	336.4	403.6	467.3
120°	145.2	149.2	155.5	165.3	181.5	203.4	233.3	277.7	336.4	400.4	460.9
122.5°	154.4	158.4	164.3	175.0	190.7	212.6	240.7	281.9	336.0	396.7	455.3
125°	167.6	171.1	177.4	188.3	204.5	225.2	251.8	288.0	335.3	390.6	445.9
127.5°	177.9	182.1	189.2	200.7	216.9	237.0	261.4	293.0	334.0	382.4	434.3
130°	184.3	188.9	197.6	208.5	225.2	244.8	267.3	296.7	333.6	377.3	425.2
132.5°	189.9	195.9	204.1	215.9	231.7	251.3	273.3	299.9	333.1	372.7	415.5
135°	198.7	204.5	214.3	226.4	241.4	260.3	281.1	304.8	332.3	365.8	402.1
137.5°	207.0	213.4	222.7	235.3	249.5	267.3	286.7	307.6	332.2	359.8	390.0
140°	212.6	218.9	228.7	240.8	254.6	272.0	290.3	309.9	331.8	356.6	383.0
142.5°	219.0	224.9	234.2	245.9	259.2	276.1	293.1	311.7	331.8	353.9	376.7
145°	228.1	233.9	242.0	252.9	265.6	280.5	296.1	312.9	330.6	349.1	367.5
147.5°	237.2	242.3	250.5	259.7	271.1	285.2	298.7	313.4	328.6	344.9	360.0
150°	243.7	248.3	255.2	263.9	274.8	287.5	300.1	313.4	327.2	341.6	355.5
152.5°	249.2	253.8	260.2	268.0	278.0	289.3	301.0	312.5	324.9	337.9	350.3
155°	258.1	261.6	267.3	273.7	282.3	292.1	301.8	311.0	321.4	332.3	342.7
157.5°	265.7	268.9	273.4	278.9	285.7	294.1	301.8	309.6	317.9	326.8	334.6
160°	270.7	273.1	277.1	281.7	288.0	295.0	301.8	308.2	315.1	322.7	329.5
162.5°	274.9	276.7	280.3	284.5	289.4	295.9	301.8	306.8	312.4	318.9	324.5
165°	280.5	281.7	284.6	287.5	290.9	296.1	300.7	304.2	308.2	312.9	317.4
167.5°	285.2	285.7	287.9	289.5	292.2	296.0	299.3	301.4	304.1	307.3	310.6
170°	287.5	288.0	289.7	290.9	292.7	295.5	298.4	299.5	301.2	303.6	306.5
172.5°	289.7	289.8	291.1	291.9	293.1	295.1	297.5	297.7	298.5	300.3	302.8
175°	292.1	292.1	292.7	293.3	293.3	294.4	296.1	295.5	295.5	296.7	297.8
177.5°	293.3	292.8	293.3	293.3	293.3	293.7	294.6	293.7	293.7	294.2	294.6
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	975.2	975.2	975.2	975.2	975.2	975.2	975.2
2.5°	1023.0	1024.3	1025.2	1028.3	1028.6	1031.5	1028.6
5°	1107.6	1113.2	1121.8	1130.4	1131.3	1136.7	1126.9
7.5°	1202.5	1215.3	1223.2	1237.2	1242.7	1246.2	1240.5
10°	1268.0	1279.7	1300.6	1310.8	1321.0	1322.5	1317.9
12.5°	1331.1	1349.8	1366.2	1385.6	1385.1	1399.0	1393.9
15°	1415.3	1434.5	1457.3	1478.9	1486.8	1486.8	1493.1
17.5°	1475.3	1510.7	1534.2	1551.2	1569.7	1573.0	1570.7
20°	1515.9	1554.0	1579.1	1601.1	1613.8	1617.3	1617.3
22.5°	1546.1	1578.5	1603.1	1622.9	1633.3	1637.4	1636.1
25°	1567.0	1594.9	1609.8	1615.7	1618.4	1617.6	1610.2
27.5°	1538.3	1537.1	1527.6	1509.5	1496.0	1487.7	1478.3
30°	1483.7	1463.2	1439.7	1413.7	1380.3	1354.7	1347.0
32.5°	1402.3	1356.3	1316.5	1273.2	1237.3	1211.7	1201.0
35°	1244.8	1172.0	1112.8	1060.9	1023.2	999.6	991.7
37.5°	1057.9	987.5	914.1	863.8	832.5	808.7	799.8
40°	939.1	862.4	798.4	751.2	719.0	695.9	695.5
42.5°	830.6	757.5	697.2	663.3	628.5	613.2	613.1
45°	680.1	621.6	570.5	543.8	523.0	510.4	506.9
47.5°	563.1	514.7	480.7	459.4	442.4	434.4	429.2
50°	497.5	455.0	427.9	409.4	400.0	389.8	389.0
52.5°	442.7	408.5	387.4	372.3	360.4	354.3	354.5
55°	372.1	345.0	330.0	318.6	309.2	304.5	302.6
57.5°	313.5	293.2	282.3	271.9	267.8	264.1	263.1
60°	277.0	263.3	253.1	244.8	238.9	237.7	237.3
62.5°	246.8	232.5	225.4	219.0	214.7	212.9	212.2
65°	203.5	192.9	186.6	181.6	180.0	177.2	176.8
67.5°	164.1	157.7	153.6	150.1	147.8	147.7	147.7
70°	139.9	136.3	132.8	130.9	129.7	128.9	128.9
72.5°	119.2	116.5	113.6	112.6	112.4	111.6	111.3
75°	90.8	88.1	88.4	86.4	84.8	82.9	81.7
77.5°	64.3	62.4	62.0	61.8	60.4	60.2	60.8
80°	49.9	48.0	47.6	48.0	47.6	46.4	46.4
82.5°	38.0	36.4	36.0	35.6	35.2	35.6	35.0
85°	20.4	19.7	19.7	19.7	20.4	20.0	19.7
87.5°	9.4	9.2	9.5	9.3	9.5	9.0	9.3
90°	10.9	11.5	11.5	12.1	12.6	12.1	12.1
92.5°	85.1	67.8	56.2	49.4	46.4	44.3	44.3
95°	337.6	260.3	204.5	176.3	158.4	148.0	140.6
97.5°	597.5	541.2	481.0	439.7	405.0	387.7	375.7
100°	706.3	678.0	635.4	585.3	550.2	532.9	528.3
102.5°	748.7	756.9	739.1	708.3	682.9	664.7	661.0
105°	744.9	801.9	825.6	826.7	822.0	814.0	810.5
107.5°	685.5	765.9	817.2	845.7	858.8	864.5	866.1
110°	639.4	723.0	786.4	827.3	851.4	861.8	867.0



TEST NUMBER: P332903-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	598.8	677.8	741.1	787.6	816.9	831.4	839.8
115°	552.5	619.9	675.2	720.6	755.3	773.7	778.3
117.5°	525.9	579.0	625.8	664.7	693.7	712.4	716.0
120°	514.4	560.5	601.4	634.3	659.6	674.6	681.0
122.5°	507.1	549.0	584.8	612.6	634.3	646.9	653.3
125°	495.4	535.1	566.8	589.9	606.6	617.5	621.0
127.5°	481.7	521.4	551.4	574.6	589.5	598.6	602.1
130°	470.7	509.8	540.4	564.0	578.3	587.6	591.1
132.5°	458.2	496.4	526.9	550.2	566.4	575.1	578.7
135°	439.6	474.6	503.5	526.5	542.7	551.9	555.3
137.5°	421.7	451.3	477.4	498.9	514.8	522.4	526.5
140°	410.2	436.1	460.3	480.5	493.1	501.2	505.8
142.5°	400.5	422.7	443.7	461.5	473.3	480.5	483.6
145°	387.1	404.5	420.5	434.9	444.7	450.5	453.3
147.5°	375.6	389.4	402.1	412.7	421.1	425.5	426.6
150°	368.7	380.2	390.6	399.8	407.3	410.7	411.3
152.5°	361.7	372.3	380.9	388.7	394.9	396.9	397.5
155°	351.9	360.6	367.5	373.3	377.9	379.6	379.6
157.5°	342.3	349.5	355.1	359.5	362.9	364.0	364.0
160°	335.9	342.1	346.8	350.2	353.8	354.3	354.3
162.5°	329.8	334.8	339.0	341.5	345.0	345.6	345.1
165°	320.8	324.9	327.8	330.1	332.3	331.8	331.2
167.5°	313.3	316.5	318.2	319.4	320.8	320.7	320.3
170°	308.2	310.5	312.3	313.4	314.0	313.4	313.4
172.5°	304.1	305.5	306.7	307.4	308.0	307.4	306.5
175°	298.4	299.5	299.5	299.5	300.7	299.5	298.4
177.5°	295.1	295.1	295.5	295.1	295.5	294.6	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3

(END OF REPORT)