

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332905-840

Luminaire Tested: **S124RDIP-S575D590U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332905-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D590U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4439.6 lumens  
Efficiency: N/A  
Efficacy: 135.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85		72	72	72		59	59	59	53
1	99	95	91	87	91	88	85	82	75	73	71		64	62	60		53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59		56	53	51		47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50		50	46	43		42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43		45	41	37		37	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37		40	36	33		34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32		36	32	29		31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29		33	29	25		28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26		30	26	23		26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23		28	24	21		24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21		26	22	19		22	19	16	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8285	8285	8285
5°	8304	8203	8253
10°	8252	8104	8104
15°	8157	7934	7875
20°	8027	7710	7568
25°	7861	7448	7259
30°	7699	7171	6871
35°	7521	6885	6482
40°	7304	6559	6062
45°	7106	6235	5634
50°	6880	5863	5181
55°	6636	5475	4690
60°	6370	5050	4187
65°	6124	4518	3692
70°	5769	3932	3135
75°	5321	3260	2548
80°	4640	2483	2338
85°	3927	2251	2112



TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.4	2.2
10°-20°	268.8	6.1
20°-30°	388.2	8.7
30°-40°	440.0	9.9
40°-50°	424.9	9.6
50°-60°	353.4	8.0
60°-70°	244.0	5.5
70°-80°	123.7	2.8
80°-90°	34.0	0.8
90°-100°	49.1	1.1
100°-110°	145.5	3.3
110°-120°	247.0	5.6
120°-130°	325.7	7.3
130°-140°	365.7	8.2
140°-150°	359.4	8.1
150°-160°	302.3	6.8
160°-170°	201.1	4.5
170°-180°	70.4	1.6
0°-30°	753.5	17.0
0°-40°	1193.5	26.9
0°-60°	1971.8	44.4
0°-90°	2373.4	53.5
90°-120°	441.6	9.9
90°-150°	1492.4	33.6
90°-180°	2066.0	46.5
0°-180°	4439.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1025	1021	1012	1020	1018	97
15°	976	968	949	948	942	275
25°	882	867	836	823	815	406
35°	763	737	699	673	658	477
45°	622	592	546	509	494	480
55°	472	439	389	350	333	422
65°	321	286	236	204	193	317
75°	171	141	104	87	82	180
85°	42	28	24	23	23	48
90°	2	8	13	16	17	4
95°	34	40	44	45	46	38
105°	134	135	137	139	141	142
115°	251	251	250	249	249	248
125°	366	366	365	364	363	326
135°	472	475	475	474	472	365
145°	573	575	576	575	574	358
155°	657	657	656	658	656	302
165°	715	713	712	715	713	201
175°	744	741	740	744	740	71
180°	745	745	745	745	745	



TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1028.9	1028.2	1027.7	1027.1	1026.6	1025.5	1024.0	1022.5	1020.9	1019.4	1020.9
5°	1024.7	1024.0	1023.3	1022.6	1022.0	1020.6	1018.4	1016.3	1014.2	1012.2	1013.9
7.5°	1015.4	1014.7	1014.0	1013.3	1012.5	1010.8	1008.0	1005.3	1002.6	999.9	1001.0
10°	1006.6	1005.8	1004.9	1004.0	1003.2	1001.2	998.0	994.8	991.7	988.6	989.3
12.5°	995.3	994.3	993.3	992.3	991.3	989.0	985.2	981.5	977.9	974.1	974.5
15°	976.0	974.4	972.9	971.3	969.7	966.7	962.4	958.1	953.6	949.3	949.0
17.5°	952.6	950.3	948.1	945.7	943.5	939.8	934.5	929.3	924.0	918.8	917.9
20°	934.3	932.1	929.8	927.6	925.2	921.2	915.2	909.3	903.3	897.5	896.1
22.5°	914.2	911.7	909.2	906.6	904.0	899.6	893.2	886.9	880.5	874.1	872.0
25°	882.5	879.4	876.2	873.0	869.9	864.7	857.6	850.4	843.2	836.2	833.1
27.5°	849.2	845.3	841.3	837.4	833.3	827.6	819.9	812.3	804.7	797.0	793.3
30°	825.9	821.5	817.2	812.8	808.5	802.1	794.0	785.8	777.5	769.3	765.0
32.5°	801.4	796.5	791.5	786.6	781.7	775.0	766.5	758.0	749.5	741.0	736.0
35°	763.1	757.5	751.8	746.3	740.7	733.6	724.8	716.1	707.3	698.6	692.7
37.5°	722.1	716.3	710.5	704.8	698.9	691.3	681.6	671.9	662.3	652.6	645.9
40°	693.1	687.3	681.6	675.8	670.0	662.2	652.3	642.3	632.4	622.4	615.0
42.5°	665.4	659.4	653.4	647.3	641.3	633.1	622.7	612.3	602.0	591.6	584.1
45°	622.4	615.9	609.5	603.0	596.5	588.0	577.5	567.1	556.6	546.1	537.6
47.5°	577.9	571.3	564.5	557.8	551.2	542.4	531.5	520.7	509.8	498.9	490.0
50°	547.8	540.9	534.1	527.3	520.5	511.5	500.3	489.2	478.0	466.8	458.1
52.5°	516.9	510.3	503.6	497.0	490.2	481.2	469.7	458.3	446.8	435.4	426.5
55°	471.5	464.5	457.6	450.5	443.5	434.3	423.0	411.7	400.3	389.0	379.9
57.5°	426.6	419.3	412.0	404.8	397.5	388.3	377.1	365.9	354.8	343.6	334.4
60°	394.5	387.5	380.5	373.5	366.6	357.5	346.3	335.1	324.0	312.8	303.7
62.5°	365.6	358.3	351.0	343.8	336.5	327.2	315.7	304.3	292.8	281.3	273.0
65°	320.6	313.2	305.6	298.1	290.5	281.2	270.0	258.9	247.7	236.5	229.0
67.5°	274.0	266.7	259.5	252.4	245.2	236.4	226.0	215.6	205.3	194.9	188.4
70°	244.4	237.0	229.7	222.4	215.1	206.4	196.4	186.5	176.5	166.6	160.9
72.5°	213.0	206.3	199.7	193.1	186.4	178.4	169.1	159.7	150.2	140.8	135.9
75°	170.6	164.1	157.6	151.2	144.7	137.3	129.2	120.9	112.7	104.5	100.5
77.5°	127.4	122.0	116.5	111.0	105.5	99.5	92.8	86.2	79.6	72.9	70.6
80°	99.8	94.7	89.7	84.6	79.6	74.4	69.2	63.9	58.7	53.4	52.9
82.5°	75.9	71.3	66.7	62.0	57.4	53.5	50.5	47.5	44.5	41.5	41.1
85°	42.4	39.0	35.4	31.9	28.5	26.5	26.0	25.4	24.8	24.3	24.0
87.5°	14.8	13.9	13.1	12.3	11.4	11.1	11.1	11.2	11.3	11.3	11.3
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	12.3	13.9	15.6	17.2	18.8	19.9	20.7	21.4	22.1	22.8	23.2
95°	34.5	35.7	36.9	38.0	39.2	40.2	41.1	42.0	42.9	43.7	44.1
97.5°	60.4	61.3	62.2	63.1	64.0	65.0	66.0	67.2	68.2	69.3	69.7
100°	80.6	81.2	81.7	82.2	82.7	83.5	84.6	85.8	86.9	88.2	88.4
102.5°	101.8	102.0	102.2	102.4	102.6	103.3	104.3	105.3	106.4	107.4	107.9
105°	134.2	134.3	134.4	134.6	134.7	135.0	135.5	136.0	136.5	137.0	137.4
107.5°	168.1	168.3	168.4	168.6	168.8	169.0	169.0	169.1	169.2	169.3	169.6
110°	191.3	191.5	191.8	192.0	192.3	192.3	192.2	192.1	192.0	191.8	191.6



TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.2	215.2	215.3	215.3	215.4	215.3	215.1	214.8	214.6	214.4	214.3
115°	251.2	251.2	251.2	251.2	251.2	251.0	250.7	250.4	250.2	249.9	249.8
117.5°	285.0	285.1	285.2	285.3	285.4	285.4	285.2	285.0	284.8	284.7	284.2
120°	307.6	308.1	308.6	309.1	309.6	309.7	309.3	308.9	308.5	308.1	307.5
122.5°	331.0	331.2	331.4	331.6	331.8	331.9	331.7	331.5	331.3	331.2	330.7
125°	365.8	365.8	365.8	365.8	365.8	365.7	365.6	365.5	365.3	365.2	364.9
127.5°	397.2	397.6	398.0	398.4	398.7	398.8	398.6	398.4	398.2	398.0	397.8
130°	419.3	419.7	420.1	420.5	420.8	421.0	421.0	421.0	421.0	421.0	420.8
132.5°	441.9	442.2	442.4	442.7	443.0	443.1	443.0	442.9	442.8	442.7	442.4
135°	471.7	472.5	473.2	474.0	474.8	475.1	475.1	475.1	475.1	475.1	474.9
137.5°	504.2	504.5	504.9	505.2	505.6	505.9	506.1	506.3	506.5	506.8	506.4
140°	525.8	526.1	526.3	526.6	526.8	527.0	527.0	527.0	527.0	527.0	526.8
142.5°	545.6	545.9	546.2	546.4	546.7	546.7	546.6	546.5	546.4	546.3	546.3
145°	573.1	573.6	574.1	574.6	575.1	575.4	575.6	575.7	575.8	575.9	575.8
147.5°	600.3	600.9	601.5	602.1	602.8	603.0	602.9	602.8	602.7	602.6	602.5
150°	616.8	617.4	617.9	618.4	618.9	619.1	619.1	619.1	619.1	619.1	619.1
152.5°	632.6	632.9	633.2	633.5	633.8	634.0	634.1	634.2	634.3	634.4	634.7
155°	656.6	656.6	656.6	656.6	656.6	656.5	656.4	656.3	656.2	656.0	656.5
157.5°	676.9	676.6	676.4	676.2	676.0	675.8	675.8	675.8	675.8	675.7	676.1
160°	688.8	688.7	688.6	688.5	688.3	688.2	688.1	688.0	687.8	687.7	688.1
162.5°	699.9	699.6	699.2	698.9	698.6	698.3	698.2	698.1	698.0	697.8	698.5
165°	714.8	714.4	714.0	713.7	713.3	713.0	712.7	712.5	712.2	712.0	712.7
167.5°	726.2	725.7	725.1	724.6	724.1	723.8	723.8	723.9	723.9	723.9	724.7
170°	732.7	732.1	731.3	730.7	730.0	729.8	729.9	730.0	730.2	730.3	731.1
172.5°	737.2	736.7	736.2	735.7	735.1	734.9	734.9	734.9	734.9	735.0	735.8
175°	743.6	743.0	742.4	741.6	741.0	740.6	740.5	740.4	740.2	740.1	741.0
177.5°	745.7	745.2	744.7	744.2	743.6	743.4	743.4	743.4	743.4	743.4	744.1
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8



TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1022.5	1024.0	1025.5	1026.2	1026.1	1025.9	1025.8	1025.7
5°	1015.6	1017.4	1019.2	1019.9	1019.5	1019.2	1018.8	1018.4
7.5°	1002.1	1003.2	1004.4	1004.6	1004.1	1003.5	1003.0	1002.4
10°	990.0	990.7	991.4	991.4	990.7	990.0	989.3	988.6
12.5°	974.9	975.3	975.8	975.5	974.5	973.6	972.6	971.6
15°	948.6	948.3	947.9	947.2	945.8	944.6	943.4	942.2
17.5°	916.9	915.8	914.8	913.4	911.6	909.8	907.9	906.1
20°	894.6	893.2	891.8	890.0	887.8	885.4	883.2	880.9
22.5°	870.0	867.9	865.8	863.8	861.9	860.1	858.3	856.4
25°	830.2	827.2	824.3	821.9	820.1	818.4	816.7	814.9
27.5°	789.6	786.0	782.3	779.2	776.7	774.2	771.7	769.2
30°	760.6	756.2	751.8	748.3	745.5	742.7	739.9	737.1
32.5°	730.9	725.9	720.7	716.9	714.3	711.7	708.9	706.3
35°	686.7	680.8	674.9	670.3	667.2	664.0	660.9	657.7
37.5°	639.2	632.7	626.0	621.2	617.9	614.8	611.7	608.5
40°	607.7	600.4	593.0	587.8	584.6	581.5	578.3	575.2
42.5°	576.6	569.2	561.7	556.3	553.0	549.8	546.4	543.2
45°	529.1	520.5	511.9	506.0	502.9	499.8	496.7	493.5
47.5°	481.1	472.2	463.3	457.2	453.7	450.3	446.9	443.3
50°	449.3	440.6	431.8	425.9	422.5	419.2	415.9	412.5
52.5°	417.6	408.7	399.9	393.7	390.2	386.8	383.3	379.9
55°	370.8	361.7	352.6	346.5	343.2	339.8	336.5	333.2
57.5°	325.1	315.9	306.7	300.8	298.3	295.8	293.3	290.7
60°	294.6	285.5	276.4	270.5	267.7	264.9	262.2	259.3
62.5°	264.6	256.2	247.8	242.5	240.2	238.0	235.8	233.6
65°	221.6	214.0	206.5	201.7	199.7	197.5	195.4	193.3
67.5°	182.0	175.5	169.1	164.7	162.4	160.1	157.7	155.4
70°	155.1	149.4	143.5	139.8	138.0	136.3	134.5	132.8
72.5°	131.0	126.0	121.1	117.9	116.2	114.6	113.0	111.4
75°	96.4	92.5	88.5	85.9	84.8	83.8	82.8	81.7
77.5°	68.3	65.9	63.5	62.2	61.9	61.6	61.3	61.0
80°	52.4	51.9	51.3	51.0	50.8	50.6	50.5	50.3
82.5°	40.7	40.3	40.0	39.7	39.5	39.3	39.2	39.0
85°	23.6	23.3	22.9	22.8	22.8	22.8	22.8	22.8
87.5°	11.4	11.4	11.4	11.5	11.7	11.9	12.0	12.2
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	23.7	24.2	24.6	24.9	25.1	25.2	25.4	25.5
95°	44.5	44.9	45.3	45.5	45.5	45.5	45.5	45.5
97.5°	70.2	70.6	71.1	71.3	71.3	71.3	71.3	71.3
100°	88.7	88.9	89.2	89.3	89.3	89.3	89.3	89.3
102.5°	108.2	108.6	108.9	109.2	109.3	109.4	109.5	109.6
105°	137.8	138.3	138.7	139.0	139.4	139.8	140.2	140.6
107.5°	170.0	170.3	170.7	170.9	170.8	170.8	170.8	170.8
110°	191.3	191.1	190.8	190.9	191.3	191.6	192.0	192.4





TEST NUMBER: P332905-840

CATALOG NUMBER: S124RDIP-S575D590U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.3	214.2	214.2	214.2	214.3	214.3	214.4	214.5
115°	249.7	249.6	249.4	249.3	249.2	249.0	248.9	248.8
117.5°	283.8	283.4	282.9	282.6	282.3	282.1	281.8	281.6
120°	306.9	306.2	305.6	305.4	305.7	305.9	306.2	306.4
122.5°	330.3	329.9	329.4	329.0	328.5	328.1	327.6	327.2
125°	364.7	364.4	364.2	363.9	363.7	363.3	363.1	362.8
127.5°	397.5	397.3	397.0	396.8	396.6	396.4	396.2	396.0
130°	420.5	420.3	420.0	419.6	419.1	418.6	418.1	417.6
132.5°	442.2	441.9	441.7	441.4	441.2	441.0	440.8	440.6
135°	474.6	474.4	474.1	473.8	473.4	473.0	472.7	472.3
137.5°	506.0	505.7	505.4	505.2	505.3	505.4	505.5	505.6
140°	526.7	526.6	526.5	526.3	526.2	526.1	526.0	525.8
142.5°	546.3	546.3	546.2	546.2	546.2	546.2	546.1	546.1
145°	575.7	575.6	575.4	575.2	574.8	574.4	574.0	573.7
147.5°	602.4	602.3	602.2	602.1	602.0	601.8	601.7	601.6
150°	619.1	619.1	619.1	619.1	618.9	618.8	618.7	618.6
152.5°	635.0	635.3	635.6	635.6	635.3	634.9	634.6	634.3
155°	657.0	657.5	658.1	658.1	657.5	657.0	656.5	656.0
157.5°	676.5	676.9	677.3	677.2	676.8	676.4	675.9	675.5
160°	688.5	688.8	689.2	689.1	688.5	687.8	687.2	686.6
162.5°	699.2	699.9	700.6	700.6	700.0	699.3	698.7	698.1
165°	713.5	714.2	715.0	715.1	714.6	714.1	713.6	713.1
167.5°	725.4	726.2	727.0	726.9	726.2	725.4	724.6	723.8
170°	731.8	732.7	733.4	733.4	732.5	731.5	730.6	729.7
172.5°	736.7	737.6	738.4	738.4	737.5	736.6	735.7	734.9
175°	741.9	742.9	743.7	743.7	742.9	741.9	741.0	740.1
177.5°	744.8	745.5	746.2	746.2	745.4	744.6	743.7	742.9
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8

(END OF REPORT)