

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332928-840

Luminaire Tested: **S124RDIP-S795D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332928-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D365U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4718.6 lumens  
Efficiency: N/A  
Efficacy: 134.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63	59
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	53	50
3	86	76	69	63	81	72	66	60	65	60	55	58	54	50	52	49	46	42
4	79	68	60	53	74	64	57	51	58	52	47	52	47	44	46	43	40	37
5	72	60	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31	28
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28	25
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	41	34	29	51	40	32	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	33	28	24	30	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11326	11326	11326
5°	11351	11212	11281
10°	11280	11077	11077
15°	11150	10845	10764
20°	10972	10539	10345
25°	10745	10180	9922
30°	10523	9803	9392
35°	10279	9411	8861
40°	9985	8965	8286
45°	9712	8524	7702
50°	9403	8013	7082
55°	9071	7484	6410
60°	8707	6902	5724
65°	8373	6178	5049
70°	7886	5375	4286
75°	7271	4457	3484
80°	6341	3394	3199
85°	5372	3084	2881



TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.8	2.8
10°-20°	367.5	7.8
20°-30°	530.6	11.2
30°-40°	601.5	12.7
40°-50°	580.8	12.3
50°-60°	483.0	10.2
60°-70°	333.5	7.1
70°-80°	169.1	3.6
80°-90°	44.7	0.9
90°-100°	16.3	0.3
100°-110°	104.1	2.2
110°-120°	199.1	4.2
120°-130°	252.7	5.4
130°-140°	270.4	5.7
140°-150°	252.8	5.4
150°-160°	203.9	4.3
160°-170°	131.5	2.8
170°-180°	45.3	1.0
0°-30°	1029.9	21.8
0°-40°	1631.4	34.6
0°-60°	2695.2	57.1
0°-90°	3242.6	68.7
90°-120°	319.5	6.8
90°-150°	1095.3	23.2
90°-180°	1476.0	31.3
0°-180°	4718.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1401	1396	1384	1394	1392	133
15°	1334	1324	1298	1295	1288	376
25°	1206	1186	1143	1125	1114	556
35°	1043	1008	955	919	899	651
45°	851	810	747	696	675	656
55°	644	600	532	478	455	576
65°	438	391	323	279	264	433
75°	233	193	143	119	112	246
85°	58	38	33	31	31	65
90°	1	5	8	10	11	4
95°	20	8	8	10	10	25
105°	107	110	111	114	102	112
115°	201	202	201	202	202	197
125°	282	283	283	284	284	252
135°	350	349	351	352	352	269
145°	403	404	404	405	406	252
155°	442	442	442	443	442	204
165°	466	465	465	467	464	132
175°	477	475	475	478	474	45
180°	477	477	477	477	477	



TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1406.3	1405.5	1404.7	1404.0	1403.2	1401.8	1399.7	1397.7	1395.5	1393.4	1395.5
5°	1400.7	1399.8	1398.8	1397.9	1396.8	1395.0	1392.1	1389.3	1386.3	1383.5	1385.9
7.5°	1388.1	1387.0	1386.0	1385.0	1384.0	1381.7	1378.0	1374.2	1370.5	1366.8	1368.3
10°	1376.0	1374.8	1373.6	1372.4	1371.2	1368.5	1364.2	1359.9	1355.6	1351.3	1352.2
12.5°	1360.5	1359.2	1357.8	1356.3	1355.0	1351.8	1346.8	1341.6	1336.6	1331.5	1332.1
15°	1334.1	1332.0	1329.8	1327.7	1325.5	1321.5	1315.5	1309.5	1303.5	1297.6	1297.1
17.5°	1302.1	1299.0	1295.9	1292.8	1289.7	1284.5	1277.4	1270.2	1263.0	1255.9	1254.6
20°	1277.2	1274.0	1271.0	1267.9	1264.8	1259.2	1251.0	1242.9	1234.8	1226.7	1224.8
22.5°	1249.7	1246.2	1242.7	1239.2	1235.8	1229.6	1220.9	1212.2	1203.6	1194.9	1192.0
25°	1206.3	1201.9	1197.7	1193.4	1189.1	1182.0	1172.3	1162.5	1152.7	1142.9	1138.8
27.5°	1160.7	1155.4	1149.9	1144.6	1139.1	1131.3	1120.7	1110.3	1099.8	1089.4	1084.4
30°	1128.9	1123.0	1117.0	1111.1	1105.1	1096.5	1085.3	1074.1	1062.8	1051.6	1045.6
32.5°	1095.4	1088.7	1082.0	1075.2	1068.5	1059.3	1047.7	1036.1	1024.5	1012.9	1006.0
35°	1043.0	1035.4	1027.7	1020.1	1012.5	1002.7	990.8	978.8	966.8	954.9	946.8
37.5°	986.9	979.1	971.2	963.3	955.4	944.9	931.7	918.5	905.2	892.0	882.9
40°	947.5	939.6	931.7	923.8	915.9	905.1	891.5	878.0	864.3	850.7	840.7
42.5°	909.6	901.3	893.1	884.8	876.6	865.4	851.2	837.0	822.8	808.6	798.4
45°	850.7	841.9	833.0	824.3	815.4	803.9	789.5	775.2	760.8	746.6	734.9
47.5°	789.9	780.8	771.7	762.5	753.5	741.4	726.6	711.7	696.8	681.9	669.7
50°	748.7	739.4	730.0	720.7	711.4	699.1	683.9	668.6	653.3	638.0	626.1
52.5°	706.6	697.5	688.3	679.2	670.1	657.7	642.1	626.4	610.8	595.1	583.0
55°	644.5	634.9	625.4	615.8	606.3	593.8	578.2	562.7	547.2	531.7	519.3
57.5°	583.1	573.1	563.2	553.3	543.3	530.7	515.4	500.2	484.9	469.6	457.1
60°	539.3	529.7	520.2	510.6	501.0	488.7	473.3	458.1	442.8	427.5	415.1
62.5°	499.7	489.8	479.9	469.9	460.0	447.2	431.5	415.9	400.2	384.6	373.0
65°	438.3	428.0	417.7	407.5	397.2	384.5	369.1	353.9	338.6	323.4	313.1
67.5°	374.5	364.7	354.8	345.0	335.1	323.2	308.9	294.8	280.5	266.4	257.5
70°	334.1	324.1	314.0	304.0	294.0	282.2	268.5	254.9	241.4	227.7	219.8
72.5°	291.1	282.1	273.0	263.9	254.8	243.9	231.1	218.1	205.3	192.5	185.7
75°	233.1	224.3	215.4	206.6	197.7	187.7	176.5	165.3	154.1	142.9	137.3
77.5°	174.2	166.7	159.3	151.8	144.2	135.9	126.9	117.9	108.8	99.7	96.4
80°	136.4	129.5	122.6	115.6	108.8	101.7	94.5	87.4	80.2	73.0	72.3
82.5°	103.8	97.5	91.1	84.7	78.4	73.1	69.1	64.9	60.8	56.8	56.1
85°	58.0	53.2	48.5	43.7	38.9	36.2	35.4	34.7	34.0	33.3	32.8
87.5°	20.0	18.6	17.3	16.0	14.5	13.8	13.8	13.7	13.6	13.6	13.5
90°	1.1	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.7	6.3	7.0	7.6	8.1
95°	19.6	17.0	14.2	11.5	8.9	7.6	7.6	7.7	7.8	7.9	8.3
97.5°	41.7	43.3	45.0	46.8	48.4	44.8	36.0	27.2	18.3	9.4	9.5
100°	58.6	60.0	61.4	62.8	64.2	59.5	48.6	37.6	26.7	15.8	14.3
102.5°	77.4	78.5	79.5	80.5	81.6	81.4	80.0	78.6	77.1	75.6	61.1
105°	107.4	107.9	108.4	108.9	109.4	109.8	110.2	110.6	111.0	111.4	112.1
107.5°	135.3	135.5	135.8	136.0	136.3	136.6	137.2	137.7	138.3	138.9	139.2
110°	154.2	154.4	154.6	154.9	155.1	155.5	155.9	156.4	156.9	157.4	157.5



TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.5	172.9	173.3	173.7	174.2	174.5	174.7	174.9	175.1	175.4	175.3
115°	200.6	200.9	201.1	201.3	201.6	201.6	201.6	201.5	201.4	201.3	201.5
117.5°	225.9	226.2	226.5	226.9	227.2	227.4	227.6	227.8	227.9	228.1	228.1
120°	243.1	243.4	243.7	244.0	244.3	244.4	244.4	244.3	244.2	244.1	244.3
122.5°	259.0	259.2	259.4	259.6	259.8	259.9	260.0	260.1	260.2	260.4	260.4
125°	282.0	282.3	282.6	282.9	283.3	283.3	283.2	283.0	282.9	282.7	282.9
127.5°	303.7	303.8	303.8	303.9	304.0	304.2	304.6	304.9	305.3	305.7	305.6
130°	317.6	317.7	317.8	317.9	318.0	318.1	318.3	318.6	318.8	319.1	319.1
132.5°	330.5	330.6	330.7	330.9	331.0	331.2	331.5	331.8	332.1	332.4	332.5
135°	349.7	349.7	349.6	349.5	349.4	349.5	349.9	350.2	350.5	350.8	351.0
137.5°	366.8	366.9	366.9	366.9	367.0	367.2	367.5	367.8	368.2	368.5	368.7
140°	378.0	378.1	378.3	378.4	378.6	378.7	378.9	379.1	379.2	379.4	379.6
142.5°	388.0	388.2	388.5	388.8	389.1	389.3	389.4	389.5	389.6	389.7	389.8
145°	403.3	403.5	403.7	404.0	404.2	404.3	404.3	404.3	404.3	404.3	404.5
147.5°	415.5	416.0	416.4	416.9	417.3	417.5	417.4	417.3	417.2	417.2	417.2
150°	424.3	424.6	425.0	425.4	425.7	425.8	425.7	425.6	425.5	425.5	425.5
152.5°	431.8	432.0	432.3	432.5	432.8	432.8	432.7	432.5	432.4	432.3	432.4
155°	442.2	442.3	442.3	442.4	442.5	442.4	442.2	441.9	441.7	441.5	441.8
157.5°	451.0	450.9	450.9	450.8	450.8	450.6	450.4	450.1	449.8	449.6	450.0
160°	456.2	455.9	455.7	455.4	455.1	455.0	454.9	454.8	454.7	454.6	455.1
162.5°	460.7	460.4	460.1	459.8	459.5	459.3	459.2	459.1	459.1	459.0	459.5
165°	466.5	466.1	465.6	465.2	464.8	464.6	464.6	464.6	464.6	464.6	465.3
167.5°	471.0	470.6	470.2	469.8	469.4	469.2	469.1	469.1	469.0	469.0	469.7
170°	473.6	473.1	472.6	472.2	471.7	471.5	471.6	471.7	471.7	471.8	472.4
172.5°	475.3	474.8	474.3	473.9	473.4	473.2	473.3	473.4	473.4	473.5	474.1
175°	477.2	476.7	476.3	475.7	475.2	475.0	475.1	475.2	475.3	475.3	476.2
177.5°	478.1	477.6	477.2	476.7	476.3	476.1	476.3	476.4	476.5	476.6	477.2
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9	1402.9
2.5°	1397.7	1399.7	1401.8	1402.8	1402.6	1402.4	1402.2	1402.0
5°	1388.3	1390.7	1393.1	1394.0	1393.5	1393.1	1392.6	1392.1
7.5°	1369.8	1371.4	1372.9	1373.2	1372.5	1371.7	1371.0	1370.2
10°	1353.2	1354.1	1355.1	1355.1	1354.1	1353.2	1352.2	1351.3
12.5°	1332.7	1333.2	1333.8	1333.4	1332.1	1330.8	1329.4	1328.1
15°	1296.7	1296.2	1295.7	1294.6	1292.9	1291.2	1289.6	1287.9
17.5°	1253.2	1251.9	1250.5	1248.6	1246.1	1243.5	1241.0	1238.5
20°	1222.8	1220.9	1219.0	1216.6	1213.5	1210.3	1207.2	1204.2
22.5°	1189.2	1186.3	1183.5	1180.7	1178.2	1175.7	1173.2	1170.6
25°	1134.8	1130.7	1126.7	1123.5	1121.1	1118.7	1116.3	1113.9
27.5°	1079.3	1074.4	1069.3	1065.1	1061.7	1058.2	1054.8	1051.4
30°	1039.7	1033.7	1027.7	1022.8	1019.1	1015.2	1011.4	1007.5
32.5°	999.1	992.2	985.2	980.0	976.3	972.7	969.1	965.4
35°	938.7	930.6	922.5	916.3	912.0	907.7	903.3	899.1
37.5°	873.8	864.7	855.7	849.0	844.8	840.4	836.2	831.8
40°	830.7	820.6	810.6	803.4	799.2	794.9	790.6	786.3
42.5°	788.2	778.0	767.8	760.4	755.9	751.4	747.0	742.5
45°	723.2	711.4	699.7	691.8	687.4	683.2	678.8	674.6
47.5°	657.6	645.5	633.4	624.9	620.3	615.5	610.8	606.0
50°	614.2	602.3	590.3	582.1	577.5	573.0	568.5	563.9
52.5°	570.9	558.8	546.5	538.2	533.4	528.7	524.0	519.3
55°	506.9	494.4	482.1	473.6	469.1	464.5	460.0	455.4
57.5°	444.4	431.8	419.2	411.2	407.8	404.3	400.9	397.5
60°	402.7	390.3	377.9	369.7	366.0	362.1	358.3	354.5
62.5°	361.6	350.2	338.7	331.4	328.4	325.4	322.2	319.2
65°	302.8	292.6	282.3	275.7	272.9	269.9	267.1	264.3
67.5°	248.7	239.9	231.1	225.1	222.0	218.7	215.6	212.5
70°	212.0	204.1	196.2	191.1	188.7	186.3	183.9	181.6
72.5°	179.0	172.3	165.5	161.1	159.0	156.7	154.5	152.3
75°	131.9	126.4	120.9	117.4	116.0	114.6	113.1	111.7
77.5°	93.3	90.1	86.8	85.0	84.6	84.2	83.8	83.3
80°	71.6	70.9	70.2	69.7	69.5	69.2	69.0	68.8
82.5°	55.6	55.1	54.6	54.2	54.0	53.7	53.5	53.3
85°	32.3	31.9	31.4	31.1	31.1	31.1	31.1	31.1
87.5°	13.4	13.3	13.2	13.3	13.5	13.7	13.9	14.1
90°	8.8	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	8.5	9.0	9.5	9.7	9.8	9.8	9.8	9.9
95°	8.8	9.3	9.8	10.0	10.1	10.2	10.3	10.3
97.5°	9.5	9.6	9.6	9.7	9.8	9.8	9.9	10.0
100°	13.0	11.6	10.3	9.7	9.8	9.8	9.9	10.0
102.5°	46.6	32.0	17.5	10.2	10.2	10.2	10.3	10.3
105°	112.8	113.5	114.2	113.1	110.3	107.4	104.5	101.7
107.5°	139.6	139.9	140.3	140.6	140.9	141.2	141.5	141.8
110°	157.7	157.8	158.0	158.2	158.4	158.8	159.0	159.2





TEST NUMBER: P332928-840

CATALOG NUMBER: S124RDIP-S795D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	175.3	175.3	175.2	175.4	175.7	176.0	176.3	176.6
115°	201.6	201.8	202.0	202.0	202.0	202.0	202.0	202.0
117.5°	228.0	228.0	228.0	227.9	227.9	227.9	227.9	227.8
120°	244.4	244.6	244.8	244.8	244.6	244.4	244.3	244.1
122.5°	260.5	260.6	260.7	260.7	260.5	260.4	260.2	260.1
125°	283.2	283.4	283.6	283.8	283.9	284.0	284.0	284.1
127.5°	305.6	305.5	305.5	305.4	305.4	305.3	305.2	305.2
130°	319.2	319.3	319.4	319.4	319.4	319.4	319.4	319.4
132.5°	332.6	332.8	332.9	332.9	332.8	332.6	332.6	332.5
135°	351.1	351.3	351.4	351.6	351.7	351.9	352.1	352.2
137.5°	368.9	369.1	369.2	369.3	369.2	369.2	369.1	369.1
140°	379.8	380.1	380.3	380.5	380.6	380.6	380.7	380.8
142.5°	390.0	390.2	390.3	390.4	390.5	390.5	390.5	390.5
145°	404.6	404.7	404.7	404.8	405.0	405.2	405.3	405.5
147.5°	417.3	417.4	417.4	417.5	417.6	417.6	417.7	417.8
150°	425.5	425.5	425.5	425.5	425.6	425.7	425.7	425.8
152.5°	432.5	432.6	432.8	432.8	432.7	432.7	432.7	432.6
155°	442.1	442.4	442.7	442.8	442.5	442.3	442.1	441.8
157.5°	450.4	450.8	451.2	451.2	450.8	450.4	450.0	449.6
160°	455.7	456.2	456.6	456.6	456.2	455.7	455.1	454.6
162.5°	459.9	460.4	460.9	460.8	460.3	459.8	459.2	458.7
165°	466.0	466.6	467.3	467.2	466.5	465.7	465.0	464.3
167.5°	470.4	471.1	471.7	471.7	470.9	470.1	469.3	468.6
170°	473.1	473.7	474.3	474.2	473.5	472.7	471.9	471.1
172.5°	474.8	475.4	476.1	475.9	475.1	474.2	473.4	472.5
175°	476.9	477.6	478.3	478.2	477.2	476.3	475.2	474.3
177.5°	477.7	478.2	478.7	478.5	477.8	477.0	476.3	475.4
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2

(END OF REPORT)