

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332528-940

Luminaire Tested: **S124DIP-S350D1205U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332528-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1205U940-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5244.3 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4112	4112	4112	4112
5°	4843	4123	3639	4123
10°	5799	4105	3277	4105
15°	6861	4064	3010	4064
20°	7640	4021	2770	4021
25°	7764	3958	2605	3958
30°	6605	3899	2553	3899
35°	5078	3802	2553	3802
40°	3959	3687	2602	3687
45°	3301	3515	2646	3515
50°	2905	3304	2735	3304
55°	2662	3054	2846	3054
60°	2493	2827	2977	2827
65°	2321	2575	3089	2575
70°	2122	2325	3158	2325
75°	1896	2046	3119	2046
80°	1590	1678	3022	1678
85°	1176	1213	2890	1213



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	0.9
10°-20°	153.0	2.9
20°-30°	242.6	4.6
30°-40°	270.0	5.1
40°-50°	245.7	4.7
50°-60°	200.8	3.8
60°-70°	143.4	2.7
70°-80°	78.9	1.5
80°-90°	24.5	0.5
90°-100°	380.9	7.3
100°-110°	792.8	15.1
110°-120°	710.1	13.5
120°-130°	597.3	11.4
130°-140°	498.1	9.5
140°-150°	380.5	7.3
150°-160°	267.5	5.1
160°-170°	157.3	3.0
170°-180°	51.2	1.0
0°-30°	445.2	8.5
0°-40°	715.2	13.6
0°-60°	1161.7	22.2
0°-90°	1408.5	26.9
90°-120°	1883.9	35.9
90°-150°	3359.8	64.1
90°-180°	3836.0	73.1
0°-180°	5244.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	598	509	449	509	598	61
15°	821	486	360	486	821	232
25°	872	444	292	444	872	384
35°	515	386	259	386	515	327
45°	289	308	232	308	289	228
55°	189	217	202	217	189	171
65°	122	135	162	135	122	120
75°	61	66	100	66	61	65
85°	13	13	31	13	13	16
90°	22	1	22	1	22	18
95°	253	34	253	34	253	392
105°	1458	121	1458	121	1458	1441
115°	1400	214	1400	214	1400	1390
125°	1117	297	1117	297	1117	1015
135°	999	353	999	353	999	771
145°	816	407	816	407	816	517
155°	683	463	683	463	683	319
165°	596	505	596	505	596	171
175°	537	526	537	526	537	52
180°	527	527	527	527	527	



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	542.2	542.1	540.4	540.0	538.9	537.3	537.0	534.2	528.9	526.3	525.7
5°	597.6	601.9	596.4	595.3	594.7	587.7	584.2	580.0	570.2	564.5	560.1
7.5°	663.9	664.3	661.9	660.0	654.6	648.5	639.4	629.7	618.1	606.2	597.1
10°	707.4	709.1	706.3	706.0	695.2	688.4	674.9	663.5	650.4	635.9	622.6
12.5°	753.3	751.0	749.6	740.6	738.5	726.2	710.5	698.8	678.6	661.8	644.2
15°	820.9	816.3	813.3	800.9	794.8	777.7	761.0	748.1	721.8	696.6	677.6
17.5°	860.6	865.2	858.4	853.3	837.5	825.5	808.4	781.4	760.8	729.6	705.6
20°	889.3	889.7	885.9	880.7	868.3	853.0	834.5	804.9	780.2	749.2	716.2
22.5°	897.1	897.2	895.5	890.6	881.2	868.9	850.2	825.5	795.6	761.9	728.9
25°	871.6	870.8	872.6	878.2	874.6	870.8	860.0	841.6	813.8	778.1	742.6
27.5°	776.9	782.7	793.4	806.9	819.9	829.8	832.6	828.8	811.6	782.3	745.1
30°	708.6	715.9	723.9	737.4	763.6	778.6	795.0	807.4	800.5	777.0	742.4
32.5°	633.7	635.5	647.4	662.7	686.7	715.5	741.6	767.0	775.3	763.0	734.1
35°	515.3	518.4	531.2	546.4	575.7	611.0	650.2	685.3	714.2	725.8	711.0
37.5°	420.5	429.0	438.1	454.4	480.3	512.0	552.8	598.2	641.2	670.1	675.0
40°	375.7	380.9	387.4	399.9	421.9	453.1	488.1	540.0	585.9	627.2	640.7
42.5°	340.2	343.3	347.3	358.6	375.2	406.4	438.4	484.0	529.9	579.4	602.1
45°	289.1	292.3	299.1	305.6	318.3	339.7	369.5	407.1	453.3	501.0	542.8
47.5°	252.3	254.2	258.2	265.3	276.1	290.3	314.4	345.8	388.6	435.0	479.5
50°	231.3	233.0	236.1	242.5	250.7	263.4	283.2	312.5	346.1	392.7	436.4
52.5°	214.7	215.4	217.8	222.0	228.6	239.2	255.6	279.8	311.0	352.6	396.1
55°	189.1	189.9	192.1	195.2	200.9	207.7	220.1	238.3	265.5	301.6	339.4
57.5°	168.0	168.6	170.3	171.6	176.3	181.7	191.4	204.3	224.9	255.6	289.3
60°	154.4	154.1	156.1	157.2	160.4	165.1	172.5	184.9	202.8	227.5	258.5
62.5°	141.3	140.7	142.5	143.9	145.7	149.6	155.7	165.4	180.0	202.3	229.2
65°	121.5	120.7	121.8	123.5	125.1	127.2	131.7	140.4	151.9	168.0	188.4
67.5°	101.7	102.6	102.8	103.6	104.6	107.5	110.5	116.6	124.8	137.7	155.0
70°	89.9	90.2	91.0	91.0	91.6	94.2	96.7	100.2	108.3	120.1	134.2
72.5°	78.1	79.0	78.6	79.3	79.8	81.5	83.3	86.8	93.5	102.4	114.3
75°	60.8	61.4	61.4	61.6	62.2	62.9	64.4	66.9	71.8	78.3	86.5
77.5°	44.3	44.4	44.7	45.5	45.5	46.5	47.5	49.6	52.0	56.4	61.5
80°	34.2	34.6	34.4	34.9	34.9	35.7	36.1	38.6	39.7	42.6	46.6
82.5°	25.1	25.5	25.4	26.0	26.4	26.6	27.1	28.2	29.2	31.8	33.4
85°	12.7	13.1	12.7	13.1	13.7	13.9	14.5	14.8	15.6	16.2	17.7
87.5°	8.0	8.6	8.7	8.7	8.8	9.0	9.0	8.6	9.1	9.5	9.7
90°	21.8	21.8	22.8	21.8	20.7	20.7	19.7	18.6	17.7	18.6	16.6
92.5°	79.8	79.8	83.3	88.9	101.1	121.9	153.1	203.5	273.8	328.7	287.7
95°	252.8	266.3	285.0	317.1	367.8	468.3	607.2	767.8	868.3	844.5	637.2
97.5°	675.8	697.3	728.4	790.8	865.2	973.4	1074.7	1134.4	1090.9	889.5	596.4
100°	950.2	958.5	989.5	1052.8	1142.9	1219.6	1270.3	1249.6	1098.3	833.0	540.9
102.5°	1188.9	1195.5	1228.2	1274.1	1329.4	1361.3	1346.6	1243.8	1036.2	762.6	503.5
105°	1457.9	1464.1	1478.6	1486.9	1484.8	1442.3	1339.8	1160.5	923.2	679.8	471.4
107.5°	1557.8	1555.1	1544.7	1521.1	1469.9	1377.5	1233.1	1042.1	832.1	633.3	465.7
110°	1559.4	1550.2	1531.4	1487.9	1414.3	1300.4	1150.1	970.9	786.5	617.6	467.3



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1510.6	1495.4	1469.3	1416.7	1333.1	1219.1	1077.2	918.6	760.7	610.1	472.3
115°	1399.9	1391.6	1358.4	1296.3	1214.4	1114.9	993.7	866.2	736.7	606.2	481.8
117.5°	1287.7	1281.3	1247.8	1195.5	1125.7	1041.3	946.0	840.5	725.9	605.1	492.0
120°	1224.8	1213.4	1186.4	1140.9	1081.7	1008.2	925.3	828.9	720.1	605.1	499.4
122.5°	1175.0	1163.6	1140.9	1101.9	1052.0	987.5	912.0	818.9	713.5	604.3	506.9
125°	1117.0	1110.8	1091.1	1061.0	1019.6	962.6	891.1	802.0	702.5	603.1	518.1
127.5°	1083.0	1076.8	1060.2	1033.5	991.8	937.7	866.5	781.2	687.8	600.7	527.0
130°	1063.1	1056.9	1040.3	1014.4	972.0	917.0	846.6	764.7	678.7	599.9	533.6
132.5°	1040.7	1034.5	1018.8	989.5	947.9	893.0	824.2	747.3	670.4	599.1	539.4
135°	998.9	992.7	976.1	947.1	905.6	853.8	790.6	723.3	658.0	597.9	548.1
137.5°	947.1	939.6	926.0	897.3	858.5	811.7	758.5	701.5	647.2	597.6	553.3
140°	909.7	901.4	887.0	864.2	827.9	784.3	737.7	689.0	641.4	596.8	557.5
142.5°	870.0	864.2	851.3	830.2	798.1	760.4	720.3	677.4	636.4	596.8	560.8
145°	815.5	810.3	800.0	782.3	756.4	727.4	696.3	661.1	627.9	594.8	562.7
147.5°	767.1	765.4	757.4	742.3	723.3	700.4	675.6	647.6	620.3	591.0	563.7
150°	739.9	738.8	732.5	719.1	702.5	683.9	663.2	639.4	614.5	588.5	563.7
152.5°	715.0	713.9	710.2	699.2	685.1	669.8	650.7	630.2	607.8	584.4	562.0
155°	682.9	682.9	679.8	671.5	661.1	648.6	633.1	616.5	597.9	578.2	559.5
157.5°	654.7	654.7	652.8	646.6	638.7	628.7	615.7	601.8	587.7	571.8	556.9
160°	637.2	637.2	636.2	630.0	623.8	615.5	604.0	592.7	580.2	566.8	554.4
162.5°	620.6	621.5	620.5	614.2	609.7	602.3	593.3	583.5	573.6	561.8	551.9
165°	595.8	596.8	597.9	593.7	589.6	584.4	577.1	571.0	562.7	554.4	547.1
167.5°	576.1	576.9	577.1	574.4	572.4	569.3	563.5	558.7	552.7	546.9	542.2
170°	563.7	563.7	564.7	563.7	561.6	558.5	554.4	551.3	546.1	541.9	538.8
172.5°	551.3	552.9	553.9	552.9	551.6	549.4	546.9	544.6	540.3	536.9	535.5
175°	536.7	538.8	540.9	538.8	538.8	538.8	536.7	535.7	533.6	531.5	531.5
177.5°	528.2	529.9	531.5	530.7	531.5	530.7	530.7	529.9	529.1	528.2	528.2
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	525.8	523.4	521.7	520.4	516.7	514.5	512.8	510.5	507.7	504.9	501.3
5°	555.6	548.5	543.2	535.2	527.6	521.3	514.7	508.8	501.7	493.8	488.1
7.5°	587.0	576.3	562.7	550.8	537.4	525.8	515.5	504.9	493.8	483.0	473.2
10°	607.0	593.3	578.0	560.1	543.2	528.2	514.3	500.8	487.7	474.7	463.4
12.5°	628.4	611.3	588.8	567.8	548.9	528.9	512.1	495.5	479.7	466.0	453.0
15°	657.2	632.5	606.5	578.5	553.6	530.1	507.1	486.2	468.5	450.3	437.7
17.5°	674.8	644.3	614.7	585.3	555.2	525.6	500.8	476.7	454.5	436.5	420.5
20°	686.5	656.1	619.2	589.9	554.0	523.6	494.9	468.1	444.9	425.7	409.2
22.5°	696.6	661.6	624.6	585.9	550.3	518.0	486.6	459.7	436.0	415.7	399.9
25°	702.1	661.8	621.7	583.3	542.8	504.6	476.1	444.4	419.1	397.8	380.9
27.5°	702.8	659.6	614.2	571.6	529.8	494.2	458.3	429.9	403.7	381.1	364.9
30°	700.9	655.9	607.2	561.0	519.0	480.4	449.1	418.3	391.5	369.1	352.2
32.5°	694.9	648.2	598.1	549.1	505.6	467.8	435.6	406.3	380.1	358.1	340.4
35°	677.9	631.6	578.3	527.4	482.9	444.7	415.5	385.8	359.6	338.8	321.6
37.5°	651.1	609.4	555.1	502.5	458.7	420.4	391.5	364.6	341.0	319.8	302.3
40°	627.9	591.1	536.6	485.4	438.1	401.6	374.6	349.9	326.5	306.4	289.7
42.5°	601.0	569.0	518.8	464.5	418.8	382.2	355.9	333.7	311.7	293.1	276.4
45°	553.1	532.0	484.7	434.5	387.0	352.4	327.3	307.9	289.4	271.2	257.3
47.5°	498.1	487.6	447.8	400.1	355.1	320.9	299.2	281.2	264.9	249.6	237.3
50°	461.1	456.0	421.7	375.7	332.6	300.5	278.6	263.1	249.2	235.8	224.1
52.5°	424.6	424.5	393.4	351.3	311.5	280.6	258.8	244.4	232.4	221.4	211.0
55°	368.9	374.8	350.5	313.0	277.3	249.4	229.8	217.0	208.5	199.5	191.6
57.5°	317.7	327.5	307.5	274.4	244.6	219.0	201.9	192.3	183.2	177.7	172.0
60°	284.3	293.6	277.9	250.1	222.0	200.1	183.8	175.1	167.4	163.5	159.5
62.5°	254.6	262.8	251.3	225.4	201.1	179.9	166.2	157.9	152.7	148.6	145.9
65°	212.1	219.1	209.1	190.4	169.4	152.6	141.4	134.8	129.8	128.1	125.1
67.5°	171.5	177.8	172.5	156.5	139.7	126.9	118.2	111.9	108.9	107.5	105.3
70°	147.3	153.6	147.9	134.0	121.1	110.4	102.1	98.5	95.4	94.8	91.8
72.5°	126.9	131.2	125.5	114.6	103.6	94.5	88.1	84.4	82.8	81.6	80.0
75°	95.1	99.0	95.1	86.8	78.9	72.6	67.1	65.6	63.8	63.1	62.1
77.5°	67.3	70.6	67.8	62.5	56.6	51.7	48.8	46.9	46.5	45.4	45.9
80°	51.5	53.6	50.8	47.3	42.6	39.2	37.2	36.1	34.9	34.4	35.2
82.5°	37.0	37.9	36.5	34.1	30.7	28.4	27.0	25.8	25.5	25.6	25.6
85°	19.2	19.0	18.8	16.7	15.6	14.2	13.3	13.1	12.8	13.3	13.7
87.5°	9.3	9.5	8.1	7.4	6.7	6.0	5.2	4.6	5.2	6.0	6.3
90°	14.5	14.5	8.3	8.3	7.2	6.2	3.1	1.1	3.1	6.2	7.2
92.5°	209.3	128.9	76.2	54.8	39.6	26.9	17.2	11.8	17.2	26.9	39.6
95°	389.6	219.6	129.6	86.0	61.2	47.7	37.3	34.2	37.3	47.7	61.2
97.5°	350.3	209.9	140.5	104.1	82.7	70.3	61.3	61.3	61.3	70.3	82.7
100°	329.5	212.4	151.3	118.2	98.4	86.0	78.7	78.7	78.7	86.0	98.4
102.5°	323.7	220.7	165.4	133.8	115.0	103.4	97.0	95.3	97.0	103.4	115.0
105°	326.4	240.4	190.6	160.6	142.0	129.6	124.3	121.3	124.3	129.6	142.0
107.5°	341.7	263.4	217.8	188.2	170.3	157.1	151.9	149.8	151.9	157.1	170.3
110°	353.3	280.8	235.2	207.2	188.6	176.1	170.9	168.9	170.9	176.1	188.6



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	365.8	297.4	253.4	225.5	206.8	195.2	189.2	187.2	189.2	195.2	206.8
115°	385.5	323.2	281.9	253.9	234.2	223.8	216.6	213.5	216.6	223.8	234.2
117.5°	405.6	348.4	309.0	280.0	261.5	250.1	243.7	240.8	243.7	250.1	261.5
120°	419.6	365.8	326.4	297.4	279.7	268.4	261.1	259.0	261.1	268.4	279.7
122.5°	432.9	382.4	343.0	314.8	295.5	285.0	277.7	275.6	277.7	285.0	295.5
125°	452.8	405.1	367.8	338.9	319.1	307.7	301.5	297.4	301.5	307.7	319.1
127.5°	470.0	426.2	390.2	361.0	340.5	327.4	319.9	316.6	319.9	327.4	340.5
130°	480.8	440.4	405.1	375.1	355.4	339.8	331.5	327.4	331.5	339.8	355.4
132.5°	491.6	452.0	416.8	388.3	367.0	352.3	341.5	338.2	341.5	352.3	367.0
135°	505.7	468.3	434.2	407.2	385.5	367.8	357.5	353.3	357.5	367.8	385.5
137.5°	515.6	480.8	448.9	423.2	400.6	383.8	372.4	368.5	372.4	383.8	400.6
140°	522.2	489.1	458.0	433.1	411.3	393.8	382.4	379.2	382.4	393.8	411.3
142.5°	527.2	496.5	466.3	442.2	421.3	404.5	394.0	390.8	394.0	404.5	421.3
145°	532.6	504.6	477.7	454.9	435.2	420.7	410.4	407.2	410.4	420.7	435.2
147.5°	537.3	512.9	487.6	467.1	450.8	435.8	426.7	425.6	426.7	435.8	450.8
150°	539.8	517.0	494.3	474.6	459.1	446.6	438.3	437.3	438.3	446.6	459.1
152.5°	541.5	520.4	500.1	482.1	468.1	456.6	448.3	448.0	448.3	456.6	468.1
155°	543.0	525.3	507.7	492.2	480.8	470.4	464.2	463.2	464.2	470.4	480.8
157.5°	543.0	528.9	514.0	501.7	491.8	483.7	477.9	477.9	477.9	483.7	491.8
160°	543.0	530.5	518.1	506.7	498.4	491.2	487.0	487.0	487.0	491.2	498.4
162.5°	543.0	532.2	520.6	511.7	504.2	497.8	494.5	495.3	494.5	497.8	504.2
165°	540.9	532.6	523.3	517.0	511.8	506.7	504.6	504.6	504.6	506.7	511.8
167.5°	538.4	532.4	525.6	520.8	517.9	514.0	512.9	514.0	512.9	514.0	517.9
170°	536.7	531.5	526.4	523.3	521.2	518.1	517.0	518.1	517.0	518.1	521.2
172.5°	535.1	530.7	527.2	525.0	523.7	521.4	521.2	522.2	521.2	521.4	523.7
175°	532.6	529.5	527.4	527.4	526.4	525.3	525.3	526.4	525.3	525.3	526.4
177.5°	529.9	528.2	527.4	527.4	527.4	526.6	527.4	528.2	527.4	526.6	527.4
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	499.6	498.1	496.0	492.9	490.4	487.7	487.0	486.0	488.0	486.3	485.8
5°	483.3	478.8	473.1	466.6	462.8	457.4	456.3	454.1	452.0	451.8	449.7
7.5°	465.9	459.4	451.9	445.3	439.2	433.1	429.2	428.4	425.3	423.4	421.3
10°	454.8	446.7	438.1	431.8	424.6	418.3	413.8	411.3	409.2	406.9	404.7
12.5°	441.7	433.1	426.0	419.1	410.6	405.8	398.5	394.1	393.7	393.7	388.3
15°	426.3	417.9	406.9	397.2	392.5	383.3	379.2	374.2	371.0	367.8	365.3
17.5°	408.8	398.2	389.7	378.5	369.7	362.3	357.0	354.0	349.2	344.7	341.5
20°	397.8	386.6	377.6	365.7	356.1	347.0	342.5	338.3	334.7	330.9	327.3
22.5°	386.6	375.0	363.9	352.4	343.4	333.8	329.5	323.8	320.4	318.3	314.7
25°	369.1	356.4	343.8	332.8	323.5	315.0	309.4	305.0	301.1	299.4	297.1
27.5°	350.0	337.4	325.2	312.7	302.2	296.0	291.5	288.2	286.0	283.7	282.7
30°	337.9	324.8	311.7	300.1	290.4	284.3	280.1	277.8	276.1	275.0	273.9
32.5°	325.6	312.6	298.9	288.3	279.6	274.1	270.9	268.6	267.8	267.4	267.0
35°	305.8	292.7	280.1	270.5	262.3	260.2	257.4	256.2	255.7	257.3	257.9
37.5°	286.7	274.6	262.9	253.7	248.3	245.2	244.2	244.3	245.8	247.1	248.6
40°	274.4	262.5	251.6	243.5	238.4	236.6	236.1	237.2	238.9	240.4	242.1
42.5°	262.3	250.7	240.8	233.3	229.7	227.9	228.2	229.3	231.7	233.4	235.9
45°	243.8	234.1	224.4	218.2	215.3	215.7	215.7	217.6	219.9	222.7	225.4
47.5°	226.2	216.4	208.5	203.3	201.8	201.4	202.6	205.1	208.4	211.8	215.6
50°	214.5	205.1	198.1	193.5	191.8	192.4	194.1	196.4	200.5	204.7	208.7
52.5°	202.4	193.9	187.5	183.2	182.0	183.2	184.9	188.5	192.1	196.6	201.4
55°	183.8	176.6	171.6	168.4	168.0	168.6	170.5	174.5	179.6	185.3	189.9
57.5°	165.3	159.3	154.6	152.5	152.7	153.3	156.4	161.1	166.6	172.6	178.6
60°	152.8	147.3	143.5	141.8	142.0	143.3	147.1	151.5	158.3	164.2	170.5
62.5°	141.0	136.2	132.5	131.0	130.7	133.5	137.1	141.7	148.5	155.1	161.9
65°	122.0	118.2	115.2	114.4	115.0	117.2	121.8	127.9	133.6	140.5	147.8
67.5°	103.4	100.3	98.3	98.6	99.4	102.5	106.4	111.6	118.2	125.4	132.4
70°	91.6	88.6	86.9	87.1	88.5	92.2	95.6	100.9	107.8	115.2	121.1
72.5°	79.5	77.5	76.0	76.9	78.1	80.7	85.0	90.2	96.4	103.3	109.5
75°	61.0	61.0	60.2	60.8	62.7	65.2	68.4	73.8	80.0	85.5	90.5
77.5°	45.2	44.8	45.3	46.1	47.2	50.2	53.9	57.8	62.3	67.9	72.1
80°	34.6	34.9	35.8	37.2	37.5	39.9	43.7	47.3	50.8	55.5	59.5
82.5°	26.0	26.2	26.8	28.4	28.8	31.3	33.7	37.3	40.6	43.7	47.0
85°	14.2	14.2	15.2	15.9	16.9	18.5	20.1	22.2	25.1	27.2	30.4
87.5°	7.0	7.0	9.0	9.3	10.3	11.5	11.6	13.7	14.5	15.6	17.1
90°	8.3	8.3	14.5	14.5	16.6	18.6	17.7	18.6	19.7	20.7	20.7
92.5°	54.8	76.2	128.9	209.3	287.7	328.7	273.8	203.5	153.1	121.9	101.1
95°	86.0	129.6	219.6	389.6	637.2	844.5	868.3	767.8	607.2	468.3	367.8
97.5°	104.1	140.5	209.9	350.3	596.4	889.5	1090.9	1134.4	1074.7	973.4	865.2
100°	118.2	151.3	212.4	329.5	540.9	833.0	1098.3	1249.6	1270.3	1219.6	1142.9
102.5°	133.8	165.4	220.7	323.7	503.5	762.6	1036.2	1243.8	1346.6	1361.3	1329.4
105°	160.6	190.6	240.4	326.4	471.4	679.8	923.2	1160.5	1339.8	1442.3	1484.8
107.5°	188.2	217.8	263.4	341.7	465.7	633.3	832.1	1042.1	1233.1	1377.5	1469.9
110°	207.2	235.2	280.8	353.3	467.3	617.6	786.5	970.9	1150.1	1300.4	1414.3



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	225.5	253.4	297.4	365.8	472.3	610.1	760.7	918.6	1077.2	1219.1	1333.1
115°	253.9	281.9	323.2	385.5	481.8	606.2	736.7	866.2	993.7	1114.9	1214.4
117.5°	280.0	309.0	348.4	405.6	492.0	605.1	725.9	840.5	946.0	1041.3	1125.7
120°	297.4	326.4	365.8	419.6	499.4	605.1	720.1	828.9	925.3	1008.2	1081.7
122.5°	314.8	343.0	382.4	432.9	506.9	604.3	713.5	818.9	912.0	987.5	1052.0
125°	338.9	367.8	405.1	452.8	518.1	603.1	702.5	802.0	891.1	962.6	1019.6
127.5°	361.0	390.2	426.2	470.0	527.0	600.7	687.8	781.2	866.5	937.7	991.8
130°	375.1	405.1	440.4	480.8	533.6	599.9	678.7	764.7	846.6	917.0	972.0
132.5°	388.3	416.8	452.0	491.6	539.4	599.1	670.4	747.3	824.2	893.0	947.9
135°	407.2	434.2	468.3	505.7	548.1	597.9	658.0	723.3	790.6	853.8	905.6
137.5°	423.2	448.9	480.8	515.6	553.3	597.6	647.2	701.5	758.5	811.7	858.5
140°	433.1	458.0	489.1	522.2	557.5	596.8	641.4	689.0	737.7	784.3	827.9
142.5°	442.2	466.3	496.5	527.2	560.8	596.8	636.4	677.4	720.3	760.4	798.1
145°	454.9	477.7	504.6	532.6	562.7	594.8	627.9	661.1	696.3	727.4	756.4
147.5°	467.1	487.6	512.9	537.3	563.7	591.0	620.3	647.6	675.6	700.4	723.3
150°	474.6	494.3	517.0	539.8	563.7	588.5	614.5	639.4	663.2	683.9	702.5
152.5°	482.1	500.1	520.4	541.5	562.0	584.4	607.8	630.2	650.7	669.8	685.1
155°	492.2	507.7	525.3	543.0	559.5	578.2	597.9	616.5	633.1	648.6	661.1
157.5°	501.7	514.0	528.9	543.0	556.9	571.8	587.7	601.8	615.7	628.7	638.7
160°	506.7	518.1	530.5	543.0	554.4	566.8	580.2	592.7	604.0	615.5	623.8
162.5°	511.7	520.6	532.2	543.0	551.9	561.8	573.6	583.5	593.3	602.3	609.7
165°	517.0	523.3	532.6	540.9	547.1	554.4	562.7	571.0	577.1	584.4	589.6
167.5°	520.8	525.6	532.4	538.4	542.2	546.9	552.7	558.7	563.5	569.3	572.4
170°	523.3	526.4	531.5	536.7	538.8	541.9	546.1	551.3	554.4	558.5	561.6
172.5°	525.0	527.2	530.7	535.1	535.5	536.9	540.3	544.6	546.9	549.4	551.6
175°	527.4	527.4	529.5	532.6	531.5	531.5	533.6	535.7	536.7	538.8	538.8
177.5°	527.4	527.4	528.2	529.9	528.2	528.2	529.1	529.9	530.7	530.7	531.5
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	485.4	485.2	483.9	483.8	483.9	485.2	485.4	485.8	486.3	488.0	486.0
5°	448.4	447.4	446.7	449.1	446.7	447.4	448.4	449.7	451.8	452.0	454.1
7.5°	420.5	419.7	417.9	417.2	417.9	419.7	420.5	421.3	423.4	425.3	428.4
10°	402.7	401.8	400.1	399.7	400.1	401.8	402.7	404.7	406.9	409.2	411.3
12.5°	385.4	383.8	383.4	383.9	383.4	383.8	385.4	388.3	393.7	393.7	394.1
15°	362.6	361.7	359.4	360.1	359.4	361.7	362.6	365.3	367.8	371.0	374.2
17.5°	340.0	339.0	336.2	338.7	336.2	339.0	340.0	341.5	344.7	349.2	354.0
20°	325.8	324.1	322.7	322.4	322.7	324.1	325.8	327.3	330.9	334.7	338.3
22.5°	312.4	310.9	310.7	309.3	310.7	310.9	312.4	314.7	318.3	320.4	323.8
25°	295.4	294.0	293.6	292.5	293.6	294.0	295.4	297.1	299.4	301.1	305.0
27.5°	282.5	281.8	281.0	281.3	281.0	281.8	282.5	282.7	283.7	286.0	288.2
30°	274.6	274.4	273.9	273.9	273.9	274.4	274.6	273.9	275.0	276.1	277.8
32.5°	268.0	268.0	268.2	268.2	268.2	268.0	268.0	267.0	267.4	267.8	268.6
35°	258.8	259.4	259.8	259.1	259.8	259.4	258.8	257.9	257.3	255.7	256.2
37.5°	250.4	251.0	251.6	252.4	251.6	251.0	250.4	248.6	247.1	245.8	244.3
40°	244.0	245.4	245.8	246.9	245.8	245.4	244.0	242.1	240.4	238.9	237.2
42.5°	237.9	239.5	240.6	240.9	240.6	239.5	237.9	235.9	233.4	231.7	229.3
45°	228.5	230.2	231.8	231.8	231.8	230.2	228.5	225.4	222.7	219.9	217.6
47.5°	218.9	221.3	222.8	223.2	222.8	221.3	218.9	215.6	211.8	208.4	205.1
50°	212.3	215.3	216.8	217.8	216.8	215.3	212.3	208.7	204.7	200.5	196.4
52.5°	205.9	208.8	210.8	211.3	210.8	208.8	205.9	201.4	196.6	192.1	188.5
55°	194.7	199.0	201.3	202.2	201.3	199.0	194.7	189.9	185.3	179.6	174.5
57.5°	184.3	188.2	190.9	191.5	190.9	188.2	184.3	178.6	172.6	166.6	161.1
60°	176.2	180.5	183.8	184.4	183.8	180.5	176.2	170.5	164.2	158.3	151.5
62.5°	167.9	172.4	175.4	177.0	175.4	172.4	167.9	161.9	155.1	148.5	141.7
65°	153.6	158.1	161.0	161.7	161.0	158.1	153.6	147.8	140.5	133.6	127.9
67.5°	138.0	142.5	144.4	145.6	144.4	142.5	138.0	132.4	125.4	118.2	111.6
70°	127.1	130.6	132.8	133.8	132.8	130.6	127.1	121.1	115.2	107.8	100.9
72.5°	114.6	118.3	120.7	121.0	120.7	118.3	114.6	109.5	103.3	96.4	90.2
75°	95.4	98.8	100.0	100.0	100.0	98.8	95.4	90.5	85.5	80.0	73.8
77.5°	75.5	77.2	78.8	79.2	78.8	77.2	75.5	72.1	67.9	62.3	57.8
80°	62.7	63.8	65.0	65.0	65.0	63.8	62.7	59.5	55.5	50.8	47.3
82.5°	49.5	50.4	51.6	51.5	51.6	50.4	49.5	47.0	43.7	40.6	37.3
85°	30.0	31.8	31.7	31.2	31.7	31.8	30.0	30.4	27.2	25.1	22.2
87.5°	17.8	18.2	18.5	18.9	18.5	18.2	17.8	17.1	15.6	14.5	13.7
90°	21.8	22.8	21.8	21.8	21.8	22.8	21.8	20.7	20.7	19.7	18.6
92.5°	88.9	83.3	79.8	79.8	79.8	83.3	88.9	101.1	121.9	153.1	203.5
95°	317.1	285.0	266.3	252.8	266.3	285.0	317.1	367.8	468.3	607.2	767.8
97.5°	790.8	728.4	697.3	675.8	697.3	728.4	790.8	865.2	973.4	1074.7	1134.4
100°	1052.8	989.5	958.5	950.2	958.5	989.5	1052.8	1142.9	1219.6	1270.3	1249.6
102.5°	1274.1	1228.2	1195.5	1188.9	1195.5	1228.2	1274.1	1329.4	1361.3	1346.6	1243.8
105°	1486.9	1478.6	1464.1	1457.9	1464.1	1478.6	1486.9	1484.8	1442.3	1339.8	1160.5
107.5°	1521.1	1544.7	1555.1	1557.8	1555.1	1544.7	1521.1	1469.9	1377.5	1233.1	1042.1
110°	1487.9	1531.4	1550.2	1559.4	1550.2	1531.4	1487.9	1414.3	1300.4	1150.1	970.9



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1416.7	1469.3	1495.4	1510.6	1495.4	1469.3	1416.7	1333.1	1219.1	1077.2	918.6
115°	1296.3	1358.4	1391.6	1399.9	1391.6	1358.4	1296.3	1214.4	1114.9	993.7	866.2
117.5°	1195.5	1247.8	1281.3	1287.7	1281.3	1247.8	1195.5	1125.7	1041.3	946.0	840.5
120°	1140.9	1186.4	1213.4	1224.8	1213.4	1186.4	1140.9	1081.7	1008.2	925.3	828.9
122.5°	1101.9	1140.9	1163.6	1175.0	1163.6	1140.9	1101.9	1052.0	987.5	912.0	818.9
125°	1061.0	1091.1	1110.8	1117.0	1110.8	1091.1	1061.0	1019.6	962.6	891.1	802.0
127.5°	1033.5	1060.2	1076.8	1083.0	1076.8	1060.2	1033.5	991.8	937.7	866.5	781.2
130°	1014.4	1040.3	1056.9	1063.1	1056.9	1040.3	1014.4	972.0	917.0	846.6	764.7
132.5°	989.5	1018.8	1034.5	1040.7	1034.5	1018.8	989.5	947.9	893.0	824.2	747.3
135°	947.1	976.1	992.7	998.9	992.7	976.1	947.1	905.6	853.8	790.6	723.3
137.5°	897.3	926.0	939.6	947.1	939.6	926.0	897.3	858.5	811.7	758.5	701.5
140°	864.2	887.0	901.4	909.7	901.4	887.0	864.2	827.9	784.3	737.7	689.0
142.5°	830.2	851.3	864.2	870.0	864.2	851.3	830.2	798.1	760.4	720.3	677.4
145°	782.3	800.0	810.3	815.5	810.3	800.0	782.3	756.4	727.4	696.3	661.1
147.5°	742.3	757.4	765.4	767.1	765.4	757.4	742.3	723.3	700.4	675.6	647.6
150°	719.1	732.5	738.8	739.9	738.8	732.5	719.1	702.5	683.9	663.2	639.4
152.5°	699.2	710.2	713.9	715.0	713.9	710.2	699.2	685.1	669.8	650.7	630.2
155°	671.5	679.8	682.9	682.9	682.9	679.8	671.5	661.1	648.6	633.1	616.5
157.5°	646.6	652.8	654.7	654.7	654.7	652.8	646.6	638.7	628.7	615.7	601.8
160°	630.0	636.2	637.2	637.2	637.2	636.2	630.0	623.8	615.5	604.0	592.7
162.5°	614.2	620.5	621.5	620.6	621.5	620.5	614.2	609.7	602.3	593.3	583.5
165°	593.7	597.9	596.8	595.8	596.8	597.9	593.7	589.6	584.4	577.1	571.0
167.5°	574.4	577.1	576.9	576.1	576.9	577.1	574.4	572.4	569.3	563.5	558.7
170°	563.7	564.7	563.7	563.7	563.7	564.7	563.7	561.6	558.5	554.4	551.3
172.5°	552.9	553.9	552.9	551.3	552.9	553.9	552.9	551.6	549.4	546.9	544.6
175°	538.8	540.9	538.8	536.7	538.8	540.9	538.8	538.8	538.8	536.7	535.7
177.5°	530.7	531.5	529.9	528.2	529.9	531.5	530.7	531.5	530.7	530.7	529.9
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	487.0	487.7	490.4	492.9	496.0	498.1	499.6	501.3	504.9	507.7	510.5
5°	456.3	457.4	462.8	466.6	473.1	478.8	483.3	488.1	493.8	501.7	508.8
7.5°	429.2	433.1	439.2	445.3	451.9	459.4	465.9	473.2	483.0	493.8	504.9
10°	413.8	418.3	424.6	431.8	438.1	446.7	454.8	463.4	474.7	487.7	500.8
12.5°	398.5	405.8	410.6	419.1	426.0	433.1	441.7	453.0	466.0	479.7	495.5
15°	379.2	383.3	392.5	397.2	406.9	417.9	426.3	437.7	450.3	468.5	486.2
17.5°	357.0	362.3	369.7	378.5	389.7	398.2	408.8	420.5	436.5	454.5	476.7
20°	342.5	347.0	356.1	365.7	377.6	386.6	397.8	409.2	425.7	444.9	468.1
22.5°	329.5	333.8	343.4	352.4	363.9	375.0	386.6	399.9	415.7	436.0	459.7
25°	309.4	315.0	323.5	332.8	343.8	356.4	369.1	380.9	397.8	419.1	444.4
27.5°	291.5	296.0	302.2	312.7	325.2	337.4	350.0	364.9	381.1	403.7	429.9
30°	280.1	284.3	290.4	300.1	311.7	324.8	337.9	352.2	369.1	391.5	418.3
32.5°	270.9	274.1	279.6	288.3	298.9	312.6	325.6	340.4	358.1	380.1	406.3
35°	257.4	260.2	262.3	270.5	280.1	292.7	305.8	321.6	338.8	359.6	385.8
37.5°	244.2	245.2	248.3	253.7	262.9	274.6	286.7	302.3	319.8	341.0	364.6
40°	236.1	236.6	238.4	243.5	251.6	262.5	274.4	289.7	306.4	326.5	349.9
42.5°	228.2	227.9	229.7	233.3	240.8	250.7	262.3	276.4	293.1	311.7	333.7
45°	215.7	215.7	215.3	218.2	224.4	234.1	243.8	257.3	271.2	289.4	307.9
47.5°	202.6	201.4	201.8	203.3	208.5	216.4	226.2	237.3	249.6	264.9	281.2
50°	194.1	192.4	191.8	193.5	198.1	205.1	214.5	224.1	235.8	249.2	263.1
52.5°	184.9	183.2	182.0	183.2	187.5	193.9	202.4	211.0	221.4	232.4	244.4
55°	170.5	168.6	168.0	168.4	171.6	176.6	183.8	191.6	199.5	208.5	217.0
57.5°	156.4	153.3	152.7	152.5	154.6	159.3	165.3	172.0	177.7	183.2	192.3
60°	147.1	143.3	142.0	141.8	143.5	147.3	152.8	159.5	163.5	167.4	175.1
62.5°	137.1	133.5	130.7	131.0	132.5	136.2	141.0	145.9	148.6	152.7	157.9
65°	121.8	117.2	115.0	114.4	115.2	118.2	122.0	125.1	128.1	129.8	134.8
67.5°	106.4	102.5	99.4	98.6	98.3	100.3	103.4	105.3	107.5	108.9	111.9
70°	95.6	92.2	88.5	87.1	86.9	88.6	91.6	91.8	94.8	95.4	98.5
72.5°	85.0	80.7	78.1	76.9	76.0	77.5	79.5	80.0	81.6	82.8	84.4
75°	68.4	65.2	62.7	60.8	60.2	61.0	61.0	62.1	63.1	63.8	65.6
77.5°	53.9	50.2	47.2	46.1	45.3	44.8	45.2	45.9	45.4	46.5	46.9
80°	43.7	39.9	37.5	37.2	35.8	34.9	34.6	35.2	34.4	34.9	36.1
82.5°	33.7	31.3	28.8	28.4	26.8	26.2	26.0	25.6	25.6	25.5	25.8
85°	20.1	18.5	16.9	15.9	15.2	14.2	14.2	13.7	13.3	12.8	13.1
87.5°	11.6	11.5	10.3	9.3	9.0	7.0	7.0	6.3	6.0	5.2	4.6
90°	17.7	18.6	16.6	14.5	14.5	8.3	8.3	7.2	6.2	3.1	1.1
92.5°	273.8	328.7	287.7	209.3	128.9	76.2	54.8	39.6	26.9	17.2	11.8
95°	868.3	844.5	637.2	389.6	219.6	129.6	86.0	61.2	47.7	37.3	34.2
97.5°	1090.9	889.5	596.4	350.3	209.9	140.5	104.1	82.7	70.3	61.3	61.3
100°	1098.3	833.0	540.9	329.5	212.4	151.3	118.2	98.4	86.0	78.7	78.7
102.5°	1036.2	762.6	503.5	323.7	220.7	165.4	133.8	115.0	103.4	97.0	95.3
105°	923.2	679.8	471.4	326.4	240.4	190.6	160.6	142.0	129.6	124.3	121.3
107.5°	832.1	633.3	465.7	341.7	263.4	217.8	188.2	170.3	157.1	151.9	149.8
110°	786.5	617.6	467.3	353.3	280.8	235.2	207.2	188.6	176.1	170.9	168.9



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	760.7	610.1	472.3	365.8	297.4	253.4	225.5	206.8	195.2	189.2	187.2
115°	736.7	606.2	481.8	385.5	323.2	281.9	253.9	234.2	223.8	216.6	213.5
117.5°	725.9	605.1	492.0	405.6	348.4	309.0	280.0	261.5	250.1	243.7	240.8
120°	720.1	605.1	499.4	419.6	365.8	326.4	297.4	279.7	268.4	261.1	259.0
122.5°	713.5	604.3	506.9	432.9	382.4	343.0	314.8	295.5	285.0	277.7	275.6
125°	702.5	603.1	518.1	452.8	405.1	367.8	338.9	319.1	307.7	301.5	297.4
127.5°	687.8	600.7	527.0	470.0	426.2	390.2	361.0	340.5	327.4	319.9	316.6
130°	678.7	599.9	533.6	480.8	440.4	405.1	375.1	355.4	339.8	331.5	327.4
132.5°	670.4	599.1	539.4	491.6	452.0	416.8	388.3	367.0	352.3	341.5	338.2
135°	658.0	597.9	548.1	505.7	468.3	434.2	407.2	385.5	367.8	357.5	353.3
137.5°	647.2	597.6	553.3	515.6	480.8	448.9	423.2	400.6	383.8	372.4	368.5
140°	641.4	596.8	557.5	522.2	489.1	458.0	433.1	411.3	393.8	382.4	379.2
142.5°	636.4	596.8	560.8	527.2	496.5	466.3	442.2	421.3	404.5	394.0	390.8
145°	627.9	594.8	562.7	532.6	504.6	477.7	454.9	435.2	420.7	410.4	407.2
147.5°	620.3	591.0	563.7	537.3	512.9	487.6	467.1	450.8	435.8	426.7	425.6
150°	614.5	588.5	563.7	539.8	517.0	494.3	474.6	459.1	446.6	438.3	437.3
152.5°	607.8	584.4	562.0	541.5	520.4	500.1	482.1	468.1	456.6	448.3	448.0
155°	597.9	578.2	559.5	543.0	525.3	507.7	492.2	480.8	470.4	464.2	463.2
157.5°	587.7	571.8	556.9	543.0	528.9	514.0	501.7	491.8	483.7	477.9	477.9
160°	580.2	566.8	554.4	543.0	530.5	518.1	506.7	498.4	491.2	487.0	487.0
162.5°	573.6	561.8	551.9	543.0	532.2	520.6	511.7	504.2	497.8	494.5	495.3
165°	562.7	554.4	547.1	540.9	532.6	523.3	517.0	511.8	506.7	504.6	504.6
167.5°	552.7	546.9	542.2	538.4	532.4	525.6	520.8	517.9	514.0	512.9	514.0
170°	546.1	541.9	538.8	536.7	531.5	526.4	523.3	521.2	518.1	517.0	518.1
172.5°	540.3	536.9	535.5	535.1	530.7	527.2	525.0	523.7	521.4	521.2	522.2
175°	533.6	531.5	531.5	532.6	529.5	527.4	527.4	526.4	525.3	525.3	526.4
177.5°	529.1	528.2	528.2	529.9	528.2	527.4	527.4	527.4	526.6	527.4	528.2
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	512.8	514.5	516.7	520.4	521.7	523.4	525.8	525.7	526.3	528.9	534.2
5°	514.7	521.3	527.6	535.2	543.2	548.5	555.6	560.1	564.5	570.2	580.0
7.5°	515.5	525.8	537.4	550.8	562.7	576.3	587.0	597.1	606.2	618.1	629.7
10°	514.3	528.2	543.2	560.1	578.0	593.3	607.0	622.6	635.9	650.4	663.5
12.5°	512.1	528.9	548.9	567.8	588.8	611.3	628.4	644.2	661.8	678.6	698.8
15°	507.1	530.1	553.6	578.5	606.5	632.5	657.2	677.6	696.6	721.8	748.1
17.5°	500.8	525.6	555.2	585.3	614.7	644.3	674.8	705.6	729.6	760.8	781.4
20°	494.9	523.6	554.0	589.9	619.2	656.1	686.5	716.2	749.2	780.2	804.9
22.5°	486.6	518.0	550.3	585.9	624.6	661.6	696.6	728.9	761.9	795.6	825.5
25°	476.1	504.6	542.8	583.3	621.7	661.8	702.1	742.6	778.1	813.8	841.6
27.5°	458.3	494.2	529.8	571.6	614.2	659.6	702.8	745.1	782.3	811.6	828.8
30°	449.1	480.4	519.0	561.0	607.2	655.9	700.9	742.4	777.0	800.5	807.4
32.5°	435.6	467.8	505.6	549.1	598.1	648.2	694.9	734.1	763.0	775.3	767.0
35°	415.5	444.7	482.9	527.4	578.3	631.6	677.9	711.0	725.8	714.2	685.3
37.5°	391.5	420.4	458.7	502.5	555.1	609.4	651.1	675.0	670.1	641.2	598.2
40°	374.6	401.6	438.1	485.4	536.6	591.1	627.9	640.7	627.2	585.9	540.0
42.5°	355.9	382.2	418.8	464.5	518.8	569.0	601.0	602.1	579.4	529.9	484.0
45°	327.3	352.4	387.0	434.5	484.7	532.0	553.1	542.8	501.0	453.3	407.1
47.5°	299.2	320.9	355.1	400.1	447.8	487.6	498.1	479.5	435.0	388.6	345.8
50°	278.6	300.5	332.6	375.7	421.7	456.0	461.1	436.4	392.7	346.1	312.5
52.5°	258.8	280.6	311.5	351.3	393.4	424.5	424.6	396.1	352.6	311.0	279.8
55°	229.8	249.4	277.3	313.0	350.5	374.8	368.9	339.4	301.6	265.5	238.3
57.5°	201.9	219.0	244.6	274.4	307.5	327.5	317.7	289.3	255.6	224.9	204.3
60°	183.8	200.1	222.0	250.1	277.9	293.6	284.3	258.5	227.5	202.8	184.9
62.5°	166.2	179.9	201.1	225.4	251.3	262.8	254.6	229.2	202.3	180.0	165.4
65°	141.4	152.6	169.4	190.4	209.1	219.1	212.1	188.4	168.0	151.9	140.4
67.5°	118.2	126.9	139.7	156.5	172.5	177.8	171.5	155.0	137.7	124.8	116.6
70°	102.1	110.4	121.1	134.0	147.9	153.6	147.3	134.2	120.1	108.3	100.2
72.5°	88.1	94.5	103.6	114.6	125.5	131.2	126.9	114.3	102.4	93.5	86.8
75°	67.1	72.6	78.9	86.8	95.1	99.0	95.1	86.5	78.3	71.8	66.9
77.5°	48.8	51.7	56.6	62.5	67.8	70.6	67.3	61.5	56.4	52.0	49.6
80°	37.2	39.2	42.6	47.3	50.8	53.6	51.5	46.6	42.6	39.7	38.6
82.5°	27.0	28.4	30.7	34.1	36.5	37.9	37.0	33.4	31.8	29.2	28.2
85°	13.3	14.2	15.6	16.7	18.8	19.0	19.2	17.7	16.2	15.6	14.8
87.5°	5.2	6.0	6.7	7.4	8.1	9.5	9.3	9.7	9.5	9.1	8.6
90°	3.1	6.2	7.2	8.3	8.3	14.5	14.5	16.6	18.6	17.7	18.6
92.5°	17.2	26.9	39.6	54.8	76.2	128.9	209.3	287.7	328.7	273.8	203.5
95°	37.3	47.7	61.2	86.0	129.6	219.6	389.6	637.2	844.5	868.3	767.8
97.5°	61.3	70.3	82.7	104.1	140.5	209.9	350.3	596.4	889.5	1090.9	1134.4
100°	78.7	86.0	98.4	118.2	151.3	212.4	329.5	540.9	833.0	1098.3	1249.6
102.5°	97.0	103.4	115.0	133.8	165.4	220.7	323.7	503.5	762.6	1036.2	1243.8
105°	124.3	129.6	142.0	160.6	190.6	240.4	326.4	471.4	679.8	923.2	1160.5
107.5°	151.9	157.1	170.3	188.2	217.8	263.4	341.7	465.7	633.3	832.1	1042.1
110°	170.9	176.1	188.6	207.2	235.2	280.8	353.3	467.3	617.6	786.5	970.9



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.2	195.2	206.8	225.5	253.4	297.4	365.8	472.3	610.1	760.7	918.6
115°	216.6	223.8	234.2	253.9	281.9	323.2	385.5	481.8	606.2	736.7	866.2
117.5°	243.7	250.1	261.5	280.0	309.0	348.4	405.6	492.0	605.1	725.9	840.5
120°	261.1	268.4	279.7	297.4	326.4	365.8	419.6	499.4	605.1	720.1	828.9
122.5°	277.7	285.0	295.5	314.8	343.0	382.4	432.9	506.9	604.3	713.5	818.9
125°	301.5	307.7	319.1	338.9	367.8	405.1	452.8	518.1	603.1	702.5	802.0
127.5°	319.9	327.4	340.5	361.0	390.2	426.2	470.0	527.0	600.7	687.8	781.2
130°	331.5	339.8	355.4	375.1	405.1	440.4	480.8	533.6	599.9	678.7	764.7
132.5°	341.5	352.3	367.0	388.3	416.8	452.0	491.6	539.4	599.1	670.4	747.3
135°	357.5	367.8	385.5	407.2	434.2	468.3	505.7	548.1	597.9	658.0	723.3
137.5°	372.4	383.8	400.6	423.2	448.9	480.8	515.6	553.3	597.6	647.2	701.5
140°	382.4	393.8	411.3	433.1	458.0	489.1	522.2	557.5	596.8	641.4	689.0
142.5°	394.0	404.5	421.3	442.2	466.3	496.5	527.2	560.8	596.8	636.4	677.4
145°	410.4	420.7	435.2	454.9	477.7	504.6	532.6	562.7	594.8	627.9	661.1
147.5°	426.7	435.8	450.8	467.1	487.6	512.9	537.3	563.7	591.0	620.3	647.6
150°	438.3	446.6	459.1	474.6	494.3	517.0	539.8	563.7	588.5	614.5	639.4
152.5°	448.3	456.6	468.1	482.1	500.1	520.4	541.5	562.0	584.4	607.8	630.2
155°	464.2	470.4	480.8	492.2	507.7	525.3	543.0	559.5	578.2	597.9	616.5
157.5°	477.9	483.7	491.8	501.7	514.0	528.9	543.0	556.9	571.8	587.7	601.8
160°	487.0	491.2	498.4	506.7	518.1	530.5	543.0	554.4	566.8	580.2	592.7
162.5°	494.5	497.8	504.2	511.7	520.6	532.2	543.0	551.9	561.8	573.6	583.5
165°	504.6	506.7	511.8	517.0	523.3	532.6	540.9	547.1	554.4	562.7	571.0
167.5°	512.9	514.0	517.9	520.8	525.6	532.4	538.4	542.2	546.9	552.7	558.7
170°	517.0	518.1	521.2	523.3	526.4	531.5	536.7	538.8	541.9	546.1	551.3
172.5°	521.2	521.4	523.7	525.0	527.2	530.7	535.1	535.5	536.9	540.3	544.6
175°	525.3	525.3	526.4	527.4	527.4	529.5	532.6	531.5	531.5	533.6	535.7
177.5°	527.4	526.6	527.4	527.4	527.4	528.2	529.9	528.2	528.2	529.1	529.9
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	537.0	537.3	538.9	540.0	540.4	542.1	542.2
5°	584.2	587.7	594.7	595.3	596.4	601.9	597.6
7.5°	639.4	648.5	654.6	660.0	661.9	664.3	663.9
10°	674.9	688.4	695.2	706.0	706.3	709.1	707.4
12.5°	710.5	726.2	738.5	740.6	749.6	751.0	753.3
15°	761.0	777.7	794.8	800.9	813.3	816.3	820.9
17.5°	808.4	825.5	837.5	853.3	858.4	865.2	860.6
20°	834.5	853.0	868.3	880.7	885.9	889.7	889.3
22.5°	850.2	868.9	881.2	890.6	895.5	897.2	897.1
25°	860.0	870.8	874.6	878.2	872.6	870.8	871.6
27.5°	832.6	829.8	819.9	806.9	793.4	782.7	776.9
30°	795.0	778.6	763.6	737.4	723.9	715.9	708.6
32.5°	741.6	715.5	686.7	662.7	647.4	635.5	633.7
35°	650.2	611.0	575.7	546.4	531.2	518.4	515.3
37.5°	552.8	512.0	480.3	454.4	438.1	429.0	420.5
40°	488.1	453.1	421.9	399.9	387.4	380.9	375.7
42.5°	438.4	406.4	375.2	358.6	347.3	343.3	340.2
45°	369.5	339.7	318.3	305.6	299.1	292.3	289.1
47.5°	314.4	290.3	276.1	265.3	258.2	254.2	252.3
50°	283.2	263.4	250.7	242.5	236.1	233.0	231.3
52.5°	255.6	239.2	228.6	222.0	217.8	215.4	214.7
55°	220.1	207.7	200.9	195.2	192.1	189.9	189.1
57.5°	191.4	181.7	176.3	171.6	170.3	168.6	168.0
60°	172.5	165.1	160.4	157.2	156.1	154.1	154.4
62.5°	155.7	149.6	145.7	143.9	142.5	140.7	141.3
65°	131.7	127.2	125.1	123.5	121.8	120.7	121.5
67.5°	110.5	107.5	104.6	103.6	102.8	102.6	101.7
70°	96.7	94.2	91.6	91.0	91.0	90.2	89.9
72.5°	83.3	81.5	79.8	79.3	78.6	79.0	78.1
75°	64.4	62.9	62.2	61.6	61.4	61.4	60.8
77.5°	47.5	46.5	45.5	45.5	44.7	44.4	44.3
80°	36.1	35.7	34.9	34.9	34.4	34.6	34.2
82.5°	27.1	26.6	26.4	26.0	25.4	25.5	25.1
85°	14.5	13.9	13.7	13.1	12.7	13.1	12.7
87.5°	9.0	9.0	8.8	8.7	8.7	8.6	8.0
90°	19.7	20.7	20.7	21.8	22.8	21.8	21.8
92.5°	153.1	121.9	101.1	88.9	83.3	79.8	79.8
95°	607.2	468.3	367.8	317.1	285.0	266.3	252.8
97.5°	1074.7	973.4	865.2	790.8	728.4	697.3	675.8
100°	1270.3	1219.6	1142.9	1052.8	989.5	958.5	950.2
102.5°	1346.6	1361.3	1329.4	1274.1	1228.2	1195.5	1188.9
105°	1339.8	1442.3	1484.8	1486.9	1478.6	1464.1	1457.9
107.5°	1233.1	1377.5	1469.9	1521.1	1544.7	1555.1	1557.8
110°	1150.1	1300.4	1414.3	1487.9	1531.4	1550.2	1559.4



TEST NUMBER: P332528-940

CATALOG NUMBER: S124DIP-S350D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1077.2	1219.1	1333.1	1416.7	1469.3	1495.4	1510.6
115°	993.7	1114.9	1214.4	1296.3	1358.4	1391.6	1399.9
117.5°	946.0	1041.3	1125.7	1195.5	1247.8	1281.3	1287.7
120°	925.3	1008.2	1081.7	1140.9	1186.4	1213.4	1224.8
122.5°	912.0	987.5	1052.0	1101.9	1140.9	1163.6	1175.0
125°	891.1	962.6	1019.6	1061.0	1091.1	1110.8	1117.0
127.5°	866.5	937.7	991.8	1033.5	1060.2	1076.8	1083.0
130°	846.6	917.0	972.0	1014.4	1040.3	1056.9	1063.1
132.5°	824.2	893.0	947.9	989.5	1018.8	1034.5	1040.7
135°	790.6	853.8	905.6	947.1	976.1	992.7	998.9
137.5°	758.5	811.7	858.5	897.3	926.0	939.6	947.1
140°	737.7	784.3	827.9	864.2	887.0	901.4	909.7
142.5°	720.3	760.4	798.1	830.2	851.3	864.2	870.0
145°	696.3	727.4	756.4	782.3	800.0	810.3	815.5
147.5°	675.6	700.4	723.3	742.3	757.4	765.4	767.1
150°	663.2	683.9	702.5	719.1	732.5	738.8	739.9
152.5°	650.7	669.8	685.1	699.2	710.2	713.9	715.0
155°	633.1	648.6	661.1	671.5	679.8	682.9	682.9
157.5°	615.7	628.7	638.7	646.6	652.8	654.7	654.7
160°	604.0	615.5	623.8	630.0	636.2	637.2	637.2
162.5°	593.3	602.3	609.7	614.2	620.5	621.5	620.6
165°	577.1	584.4	589.6	593.7	597.9	596.8	595.8
167.5°	563.5	569.3	572.4	574.4	577.1	576.9	576.1
170°	554.4	558.5	561.6	563.7	564.7	563.7	563.7
172.5°	546.9	549.4	551.6	552.9	553.9	552.9	551.3
175°	536.7	538.8	538.8	538.8	540.9	538.8	536.7
177.5°	530.7	530.7	531.5	530.7	531.5	529.9	528.2
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4

(END OF REPORT)