

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332510-940

Luminaire Tested: **S124DIP-S350D810U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332510-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D810U940-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3988.7 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	50	44	46	41	37	36	32	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4112	4112	4112	4112
5°	4843	4123	3639	4123
10°	5799	4105	3277	4105
15°	6861	4064	3010	4064
20°	7640	4021	2770	4021
25°	7764	3958	2605	3958
30°	6605	3899	2553	3899
35°	5078	3802	2553	3802
40°	3959	3687	2602	3687
45°	3301	3515	2646	3515
50°	2905	3304	2735	3304
55°	2662	3054	2846	3054
60°	2493	2827	2977	2827
65°	2321	2575	3089	2575
70°	2122	2325	3158	2325
75°	1896	2046	3119	2046
80°	1590	1678	3022	1678
85°	1176	1213	2890	1213



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	1.2
10°-20°	153.0	3.8
20°-30°	242.6	6.1
30°-40°	270.0	6.8
40°-50°	245.7	6.2
50°-60°	200.8	5.0
60°-70°	143.4	3.6
70°-80°	78.9	2.0
80°-90°	23.5	0.6
90°-100°	256.3	6.4
100°-110°	533.5	13.4
110°-120°	477.9	12.0
120°-130°	402.0	10.1
130°-140°	335.1	8.4
140°-150°	256.1	6.4
150°-160°	180.0	4.5
160°-170°	105.9	2.7
170°-180°	34.4	0.9
0°-30°	445.2	11.2
0°-40°	715.2	17.9
0°-60°	1161.7	29.1
0°-90°	1407.5	35.3
90°-120°	1267.7	31.8
90°-150°	2260.9	56.7
90°-180°	2581.0	64.7
0°-180°	3988.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	598	509	449	509	598	61
15°	821	486	360	486	821	232
25°	872	444	292	444	872	384
35°	515	386	259	386	515	327
45°	289	308	232	308	289	228
55°	189	217	202	217	189	171
65°	122	135	162	135	122	120
75°	61	66	100	66	61	65
85°	13	13	31	13	13	16
90°	15	1	15	1	15	12
95°	170	23	170	23	170	264
105°	981	82	981	82	981	970
115°	942	144	942	144	942	935
125°	752	200	752	200	752	683
135°	672	238	672	238	672	519
145°	549	274	549	274	549	348
155°	460	312	460	312	460	214
165°	401	340	401	340	401	115
175°	361	354	361	354	361	35
180°	355	355	355	355	355	



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	542.2	542.1	540.4	540.0	538.9	537.3	537.0	534.2	528.9	526.3	525.7
5°	597.6	601.9	596.4	595.3	594.7	587.7	584.2	580.0	570.2	564.5	560.1
7.5°	663.9	664.3	661.9	660.0	654.6	648.5	639.4	629.7	618.1	606.2	597.1
10°	707.4	709.1	706.3	706.0	695.2	688.4	674.9	663.5	650.4	635.9	622.6
12.5°	753.3	751.0	749.6	740.6	738.5	726.2	710.5	698.8	678.6	661.8	644.2
15°	820.9	816.3	813.3	800.9	794.8	777.7	761.0	748.1	721.8	696.6	677.6
17.5°	860.6	865.2	858.4	853.3	837.5	825.5	808.4	781.4	760.8	729.6	705.6
20°	889.3	889.7	885.9	880.7	868.3	853.0	834.5	804.9	780.2	749.2	716.2
22.5°	897.1	897.2	895.5	890.6	881.2	868.9	850.2	825.5	795.6	761.9	728.9
25°	871.6	870.8	872.6	878.2	874.6	870.8	860.0	841.6	813.8	778.1	742.6
27.5°	776.9	782.7	793.4	806.9	819.9	829.8	832.6	828.8	811.6	782.3	745.1
30°	708.6	715.9	723.9	737.4	763.6	778.6	795.0	807.4	800.5	777.0	742.4
32.5°	633.7	635.5	647.4	662.7	686.7	715.5	741.6	767.0	775.3	763.0	734.1
35°	515.3	518.4	531.2	546.4	575.7	611.0	650.2	685.3	714.2	725.8	711.0
37.5°	420.5	429.0	438.1	454.4	480.3	512.0	552.8	598.2	641.2	670.1	675.0
40°	375.7	380.9	387.4	399.9	421.9	453.1	488.1	540.0	585.9	627.2	640.7
42.5°	340.2	343.3	347.3	358.6	375.2	406.4	438.4	484.0	529.9	579.4	602.1
45°	289.1	292.3	299.1	305.6	318.3	339.7	369.5	407.1	453.3	501.0	542.8
47.5°	252.3	254.2	258.2	265.3	276.1	290.3	314.4	345.8	388.6	435.0	479.5
50°	231.3	233.0	236.1	242.5	250.7	263.4	283.2	312.5	346.1	392.7	436.4
52.5°	214.7	215.4	217.8	222.0	228.6	239.2	255.6	279.8	311.0	352.6	396.1
55°	189.1	189.9	192.1	195.2	200.9	207.7	220.1	238.3	265.5	301.6	339.4
57.5°	168.0	168.6	170.3	171.6	176.3	181.7	191.4	204.3	224.9	255.6	289.3
60°	154.4	154.1	156.1	157.2	160.4	165.1	172.5	184.9	202.8	227.5	258.5
62.5°	141.3	140.7	142.5	143.9	145.7	149.6	155.7	165.4	180.0	202.3	229.2
65°	121.5	120.7	121.8	123.5	125.1	127.2	131.7	140.4	151.9	168.0	188.4
67.5°	101.7	102.6	102.8	103.6	104.6	107.5	110.5	116.6	124.8	137.7	155.0
70°	89.9	90.2	91.0	91.0	91.6	94.2	96.7	100.2	108.3	120.1	134.2
72.5°	78.1	79.0	78.6	79.3	79.8	81.5	83.3	86.8	93.5	102.4	114.3
75°	60.8	61.4	61.4	61.6	62.2	62.9	64.4	66.9	71.8	78.3	86.5
77.5°	44.3	44.4	44.7	45.5	45.5	46.5	47.5	49.6	52.0	56.4	61.5
80°	34.2	34.6	34.4	34.9	34.9	35.7	36.1	38.6	39.7	42.6	46.6
82.5°	25.1	25.5	25.4	26.0	26.4	26.6	27.1	28.2	29.2	31.8	33.4
85°	12.7	13.1	12.7	13.1	13.7	13.9	14.5	14.8	15.6	16.2	17.7
87.5°	6.6	7.1	7.3	7.3	7.5	7.7	7.8	7.4	7.9	8.3	8.6
90°	14.6	14.6	15.3	14.6	13.9	13.9	13.3	12.6	11.9	12.6	11.1
92.5°	53.7	53.7	56.1	59.8	68.0	82.0	103.1	137.0	184.2	221.1	193.6
95°	170.1	179.2	191.7	213.4	247.5	315.1	408.6	516.7	584.3	568.3	428.8
97.5°	454.8	469.2	490.2	532.2	582.2	655.0	723.2	763.3	734.1	598.5	401.4
100°	639.4	645.0	665.8	708.4	769.1	820.6	854.8	840.9	739.0	560.6	364.0
102.5°	800.0	804.5	826.5	857.4	894.6	916.1	906.2	837.0	697.2	513.2	338.9
105°	981.1	985.3	995.0	1000.6	999.2	970.5	901.5	781.0	621.3	457.4	317.3
107.5°	1048.2	1046.4	1039.5	1023.6	989.1	926.9	829.7	701.3	559.9	426.1	313.3
110°	1049.4	1043.1	1030.6	1001.2	951.7	875.0	773.9	653.4	529.2	415.5	314.4



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1016.5	1006.3	988.7	953.2	897.1	820.4	724.9	618.2	511.9	410.5	317.8
115°	942.0	936.4	914.1	872.3	817.2	750.2	668.7	582.9	495.7	407.9	324.2
117.5°	866.6	862.2	839.6	804.5	757.5	700.7	636.6	565.6	488.5	407.2	331.1
120°	824.1	816.5	798.3	767.7	727.9	678.4	622.7	557.8	484.6	407.2	336.1
122.5°	790.7	783.0	767.7	741.5	707.8	664.5	613.7	551.1	480.1	406.6	341.1
125°	751.6	747.4	734.2	714.0	686.1	647.7	599.7	539.7	472.7	405.8	348.7
127.5°	728.8	724.6	713.5	695.4	667.4	631.0	583.0	525.8	462.8	404.3	354.6
130°	715.4	711.2	700.1	682.6	654.0	617.1	569.6	514.6	456.7	403.7	359.1
132.5°	700.3	696.2	685.5	665.8	637.8	600.9	554.6	502.8	451.1	403.1	363.0
135°	672.2	668.0	656.8	637.3	609.4	574.5	532.0	486.7	442.7	402.3	368.8
137.5°	637.3	632.2	623.0	603.8	577.7	546.3	510.4	472.1	435.5	402.2	372.3
140°	612.2	606.6	596.8	581.5	557.1	527.8	496.4	463.7	431.6	401.6	375.1
142.5°	585.4	581.5	572.8	558.7	537.0	511.7	484.7	455.8	428.3	401.6	377.4
145°	548.8	545.3	538.2	526.5	509.0	489.5	468.6	444.9	422.5	400.2	378.6
147.5°	516.2	515.0	509.7	499.5	486.7	471.4	454.6	435.8	417.4	397.7	379.3
150°	497.8	497.1	492.9	483.9	472.7	460.2	446.2	430.2	413.5	396.0	379.3
152.5°	481.1	480.4	477.9	470.5	461.0	450.7	437.8	424.1	409.0	393.2	378.2
155°	459.5	459.5	457.4	451.8	444.9	436.5	426.1	414.8	402.3	389.1	376.5
157.5°	440.5	440.5	439.3	435.1	429.8	423.1	414.3	404.9	395.5	384.8	374.7
160°	428.8	428.8	428.1	423.9	419.7	414.2	406.5	398.9	390.5	381.4	373.0
162.5°	417.7	418.2	417.5	413.3	410.3	405.3	399.2	392.7	386.0	378.1	371.4
165°	400.9	401.6	402.3	399.5	396.7	393.2	388.3	384.1	378.6	373.0	368.2
167.5°	387.6	388.3	388.3	386.6	385.1	383.1	379.2	375.9	371.9	368.0	364.8
170°	379.3	379.3	380.0	379.3	377.9	375.9	373.0	371.0	367.5	364.6	362.6
172.5°	371.0	372.0	372.7	372.0	371.2	369.7	368.0	366.5	363.6	361.3	360.3
175°	361.1	362.6	364.0	362.6	362.6	362.6	361.1	360.5	359.1	357.7	357.7
177.5°	355.4	356.6	357.7	357.1	357.7	357.1	357.1	356.6	356.0	355.4	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	525.8	523.4	521.7	520.4	516.7	514.5	512.8	510.5	507.7	504.9	501.3
5°	555.6	548.5	543.2	535.2	527.6	521.3	514.7	508.8	501.7	493.8	488.1
7.5°	587.0	576.3	562.7	550.8	537.4	525.8	515.5	504.9	493.8	483.0	473.2
10°	607.0	593.3	578.0	560.1	543.2	528.2	514.3	500.8	487.7	474.7	463.4
12.5°	628.4	611.3	588.8	567.8	548.9	528.9	512.1	495.5	479.7	466.0	453.0
15°	657.2	632.5	606.5	578.5	553.6	530.1	507.1	486.2	468.5	450.3	437.7
17.5°	674.8	644.3	614.7	585.3	555.2	525.6	500.8	476.7	454.5	436.5	420.5
20°	686.5	656.1	619.2	589.9	554.0	523.6	494.9	468.1	444.9	425.7	409.2
22.5°	696.6	661.6	624.6	585.9	550.3	518.0	486.6	459.7	436.0	415.7	399.9
25°	702.1	661.8	621.7	583.3	542.8	504.6	476.1	444.4	419.1	397.8	380.9
27.5°	702.8	659.6	614.2	571.6	529.8	494.2	458.3	429.9	403.7	381.1	364.9
30°	700.9	655.9	607.2	561.0	519.0	480.4	449.1	418.3	391.5	369.1	352.2
32.5°	694.9	648.2	598.1	549.1	505.6	467.8	435.6	406.3	380.1	358.1	340.4
35°	677.9	631.6	578.3	527.4	482.9	444.7	415.5	385.8	359.6	338.8	321.6
37.5°	651.1	609.4	555.1	502.5	458.7	420.4	391.5	364.6	341.0	319.8	302.3
40°	627.9	591.1	536.6	485.4	438.1	401.6	374.6	349.9	326.5	306.4	289.7
42.5°	601.0	569.0	518.8	464.5	418.8	382.2	355.9	333.7	311.7	293.1	276.4
45°	553.1	532.0	484.7	434.5	387.0	352.4	327.3	307.9	289.4	271.2	257.3
47.5°	498.1	487.6	447.8	400.1	355.1	320.9	299.2	281.2	264.9	249.6	237.3
50°	461.1	456.0	421.7	375.7	332.6	300.5	278.6	263.1	249.2	235.8	224.1
52.5°	424.6	424.5	393.4	351.3	311.5	280.6	258.8	244.4	232.4	221.4	211.0
55°	368.9	374.8	350.5	313.0	277.3	249.4	229.8	217.0	208.5	199.5	191.6
57.5°	317.7	327.5	307.5	274.4	244.6	219.0	201.9	192.3	183.2	177.7	172.0
60°	284.3	293.6	277.9	250.1	222.0	200.1	183.8	175.1	167.4	163.5	159.5
62.5°	254.6	262.8	251.3	225.4	201.1	179.9	166.2	157.9	152.7	148.6	145.9
65°	212.1	219.1	209.1	190.4	169.4	152.6	141.4	134.8	129.8	128.1	125.1
67.5°	171.5	177.8	172.5	156.5	139.7	126.9	118.2	111.9	108.9	107.5	105.3
70°	147.3	153.6	147.9	134.0	121.1	110.4	102.1	98.5	95.4	94.8	91.8
72.5°	126.9	131.2	125.5	114.6	103.6	94.5	88.1	84.4	82.8	81.6	80.0
75°	95.1	99.0	95.1	86.8	78.9	72.6	67.1	65.6	63.8	63.1	62.1
77.5°	67.3	70.6	67.8	62.5	56.6	51.7	48.8	46.9	46.5	45.4	45.9
80°	51.5	53.6	50.8	47.3	42.6	39.2	37.2	36.1	34.9	34.4	35.2
82.5°	37.0	37.9	36.5	34.1	30.7	28.4	27.0	25.8	25.5	25.6	25.6
85°	19.2	19.0	18.8	16.7	15.6	14.2	13.3	13.1	12.8	13.3	13.7
87.5°	8.4	8.6	7.5	6.9	6.2	5.5	5.0	4.5	5.0	5.5	5.9
90°	9.7	9.7	5.6	5.6	4.9	4.2	2.1	0.7	2.1	4.2	4.9
92.5°	140.8	86.8	51.3	36.8	26.7	18.1	11.6	7.9	11.6	18.1	26.7
95°	262.2	147.8	87.1	57.9	41.1	32.1	25.1	23.0	25.1	32.1	41.1
97.5°	235.7	141.2	94.5	70.0	55.6	47.3	41.3	41.3	41.3	47.3	55.6
100°	221.8	142.9	101.8	79.5	66.3	57.9	53.0	53.0	53.0	57.9	66.3
102.5°	217.8	148.5	111.3	90.1	77.4	69.6	65.3	64.1	65.3	69.6	77.4
105°	219.6	161.8	128.3	108.1	95.5	87.1	83.6	81.6	83.6	87.1	95.5
107.5°	230.0	177.3	146.6	126.6	114.6	105.7	102.2	100.9	102.2	105.7	114.6
110°	237.7	189.0	158.3	139.5	126.9	118.5	115.0	113.7	115.0	118.5	126.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.1	200.1	170.6	151.7	139.2	131.3	127.3	125.9	127.3	131.3	139.2
115°	259.4	217.6	189.7	170.9	157.6	150.6	145.7	143.7	145.7	150.6	157.6
117.5°	272.9	234.4	207.9	188.4	176.0	168.4	164.0	162.0	164.0	168.4	176.0
120°	282.4	246.1	219.6	200.1	188.2	180.6	175.7	174.3	175.7	180.6	188.2
122.5°	291.3	257.3	230.8	211.8	198.9	191.7	186.9	185.5	186.9	191.7	198.9
125°	304.7	272.6	247.5	228.0	214.7	207.1	202.9	200.1	202.9	207.1	214.7
127.5°	316.3	286.9	262.6	242.9	229.1	220.3	215.3	213.1	215.3	220.3	229.1
130°	323.5	296.3	272.6	252.4	239.2	228.7	223.1	220.3	223.1	228.7	239.2
132.5°	330.7	304.2	280.4	261.4	247.0	237.1	229.8	227.6	229.8	237.1	247.0
135°	340.3	315.1	292.1	274.0	259.4	247.5	240.6	237.7	240.6	247.5	259.4
137.5°	347.0	323.5	302.0	284.7	269.6	258.2	250.6	248.0	250.6	258.2	269.6
140°	351.4	329.1	308.2	291.4	276.8	264.9	257.3	255.2	257.3	264.9	276.8
142.5°	354.7	334.1	313.8	297.6	283.5	272.2	265.1	263.0	265.1	272.2	283.5
145°	358.4	339.6	321.5	306.1	292.8	283.1	276.1	274.0	276.1	283.1	292.8
147.5°	361.6	345.2	328.1	314.3	303.3	293.3	287.1	286.4	287.1	293.3	303.3
150°	363.3	347.9	332.6	319.3	308.9	300.5	295.0	294.3	295.0	300.5	308.9
152.5°	364.4	350.2	336.5	324.4	315.0	307.2	301.7	301.5	301.7	307.2	315.0
155°	365.3	353.5	341.6	331.2	323.5	316.6	312.4	311.7	312.4	316.6	323.5
157.5°	365.3	355.9	345.8	337.6	330.9	325.5	321.6	321.6	321.6	325.5	330.9
160°	365.3	357.0	348.7	341.0	335.4	330.5	327.7	327.7	327.7	330.5	335.4
162.5°	365.3	358.1	350.3	344.3	339.3	334.9	332.7	333.3	332.7	334.9	339.3
165°	364.0	358.4	352.1	347.9	344.5	341.0	339.6	339.6	339.6	341.0	344.5
167.5°	362.3	358.3	353.7	350.4	348.5	345.8	345.2	345.8	345.2	345.8	348.5
170°	361.1	357.7	354.2	352.1	350.7	348.7	347.9	348.7	347.9	348.7	350.7
172.5°	360.1	357.1	354.7	353.2	352.4	350.9	350.7	351.4	350.7	350.9	352.4
175°	358.4	356.3	354.9	354.9	354.2	353.5	353.5	354.2	353.5	353.5	354.2
177.5°	356.6	355.4	354.9	354.9	354.9	354.4	354.9	355.4	354.9	354.4	354.9
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	499.6	498.1	496.0	492.9	490.4	487.7	487.0	486.0	488.0	486.3	485.8
5°	483.3	478.8	473.1	466.6	462.8	457.4	456.3	454.1	452.0	451.8	449.7
7.5°	465.9	459.4	451.9	445.3	439.2	433.1	429.2	428.4	425.3	423.4	421.3
10°	454.8	446.7	438.1	431.8	424.6	418.3	413.8	411.3	409.2	406.9	404.7
12.5°	441.7	433.1	426.0	419.1	410.6	405.8	398.5	394.1	393.7	393.7	388.3
15°	426.3	417.9	406.9	397.2	392.5	383.3	379.2	374.2	371.0	367.8	365.3
17.5°	408.8	398.2	389.7	378.5	369.7	362.3	357.0	354.0	349.2	344.7	341.5
20°	397.8	386.6	377.6	365.7	356.1	347.0	342.5	338.3	334.7	330.9	327.3
22.5°	386.6	375.0	363.9	352.4	343.4	333.8	329.5	323.8	320.4	318.3	314.7
25°	369.1	356.4	343.8	332.8	323.5	315.0	309.4	305.0	301.1	299.4	297.1
27.5°	350.0	337.4	325.2	312.7	302.2	296.0	291.5	288.2	286.0	283.7	282.7
30°	337.9	324.8	311.7	300.1	290.4	284.3	280.1	277.8	276.1	275.0	273.9
32.5°	325.6	312.6	298.9	288.3	279.6	274.1	270.9	268.6	267.8	267.4	267.0
35°	305.8	292.7	280.1	270.5	262.3	260.2	257.4	256.2	255.7	257.3	257.9
37.5°	286.7	274.6	262.9	253.7	248.3	245.2	244.2	244.3	245.8	247.1	248.6
40°	274.4	262.5	251.6	243.5	238.4	236.6	236.1	237.2	238.9	240.4	242.1
42.5°	262.3	250.7	240.8	233.3	229.7	227.9	228.2	229.3	231.7	233.4	235.9
45°	243.8	234.1	224.4	218.2	215.3	215.7	215.7	217.6	219.9	222.7	225.4
47.5°	226.2	216.4	208.5	203.3	201.8	201.4	202.6	205.1	208.4	211.8	215.6
50°	214.5	205.1	198.1	193.5	191.8	192.4	194.1	196.4	200.5	204.7	208.7
52.5°	202.4	193.9	187.5	183.2	182.0	183.2	184.9	188.5	192.1	196.6	201.4
55°	183.8	176.6	171.6	168.4	168.0	168.6	170.5	174.5	179.6	185.3	189.9
57.5°	165.3	159.3	154.6	152.5	152.7	153.3	156.4	161.1	166.6	172.6	178.6
60°	152.8	147.3	143.5	141.8	142.0	143.3	147.1	151.5	158.3	164.2	170.5
62.5°	141.0	136.2	132.5	131.0	130.7	133.5	137.1	141.7	148.5	155.1	161.9
65°	122.0	118.2	115.2	114.4	115.0	117.2	121.8	127.9	133.6	140.5	147.8
67.5°	103.4	100.3	98.3	98.6	99.4	102.5	106.4	111.6	118.2	125.4	132.4
70°	91.6	88.6	86.9	87.1	88.5	92.2	95.6	100.9	107.8	115.2	121.1
72.5°	79.5	77.5	76.0	76.9	78.1	80.7	85.0	90.2	96.4	103.3	109.5
75°	61.0	61.0	60.2	60.8	62.7	65.2	68.4	73.8	80.0	85.5	90.5
77.5°	45.2	44.8	45.3	46.1	47.2	50.2	53.9	57.8	62.3	67.9	72.1
80°	34.6	34.9	35.8	37.2	37.5	39.9	43.7	47.3	50.8	55.5	59.5
82.5°	26.0	26.2	26.8	28.4	28.8	31.3	33.7	37.3	40.6	43.7	47.0
85°	14.2	14.2	15.2	15.9	16.9	18.5	20.1	22.2	25.1	27.2	30.4
87.5°	6.5	6.5	8.0	8.4	9.2	10.3	10.4	12.5	13.3	14.3	15.8
90°	5.6	5.6	9.7	9.7	11.1	12.6	11.9	12.6	13.3	13.9	13.9
92.5°	36.8	51.3	86.8	140.8	193.6	221.1	184.2	137.0	103.1	82.0	68.0
95°	57.9	87.1	147.8	262.2	428.8	568.3	584.3	516.7	408.6	315.1	247.5
97.5°	70.0	94.5	141.2	235.7	401.4	598.5	734.1	763.3	723.2	655.0	582.2
100°	79.5	101.8	142.9	221.8	364.0	560.6	739.0	840.9	854.8	820.6	769.1
102.5°	90.1	111.3	148.5	217.8	338.9	513.2	697.2	837.0	906.2	916.1	894.6
105°	108.1	128.3	161.8	219.6	317.3	457.4	621.3	781.0	901.5	970.5	999.2
107.5°	126.6	146.6	177.3	230.0	313.3	426.1	559.9	701.3	829.7	926.9	989.1
110°	139.5	158.3	189.0	237.7	314.4	415.5	529.2	653.4	773.9	875.0	951.7



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	151.7	170.6	200.1	246.1	317.8	410.5	511.9	618.2	724.9	820.4	897.1
115°	170.9	189.7	217.6	259.4	324.2	407.9	495.7	582.9	668.7	750.2	817.2
117.5°	188.4	207.9	234.4	272.9	331.1	407.2	488.5	565.6	636.6	700.7	757.5
120°	200.1	219.6	246.1	282.4	336.1	407.2	484.6	557.8	622.7	678.4	727.9
122.5°	211.8	230.8	257.3	291.3	341.1	406.6	480.1	551.1	613.7	664.5	707.8
125°	228.0	247.5	272.6	304.7	348.7	405.8	472.7	539.7	599.7	647.7	686.1
127.5°	242.9	262.6	286.9	316.3	354.6	404.3	462.8	525.8	583.0	631.0	667.4
130°	252.4	272.6	296.3	323.5	359.1	403.7	456.7	514.6	569.6	617.1	654.0
132.5°	261.4	280.4	304.2	330.7	363.0	403.1	451.1	502.8	554.6	600.9	637.8
135°	274.0	292.1	315.1	340.3	368.8	402.3	442.7	486.7	532.0	574.5	609.4
137.5°	284.7	302.0	323.5	347.0	372.3	402.2	435.5	472.1	510.4	546.3	577.7
140°	291.4	308.2	329.1	351.4	375.1	401.6	431.6	463.7	496.4	527.8	557.1
142.5°	297.6	313.8	334.1	354.7	377.4	401.6	428.3	455.8	484.7	511.7	537.0
145°	306.1	321.5	339.6	358.4	378.6	400.2	422.5	444.9	468.6	489.5	509.0
147.5°	314.3	328.1	345.2	361.6	379.3	397.7	417.4	435.8	454.6	471.4	486.7
150°	319.3	332.6	347.9	363.3	379.3	396.0	413.5	430.2	446.2	460.2	472.7
152.5°	324.4	336.5	350.2	364.4	378.2	393.2	409.0	424.1	437.8	450.7	461.0
155°	331.2	341.6	353.5	365.3	376.5	389.1	402.3	414.8	426.1	436.5	444.9
157.5°	337.6	345.8	355.9	365.3	374.7	384.8	395.5	404.9	414.3	423.1	429.8
160°	341.0	348.7	357.0	365.3	373.0	381.4	390.5	398.9	406.5	414.2	419.7
162.5°	344.3	350.3	358.1	365.3	371.4	378.1	386.0	392.7	399.2	405.3	410.3
165°	347.9	352.1	358.4	364.0	368.2	373.0	378.6	384.1	388.3	393.2	396.7
167.5°	350.4	353.7	358.3	362.3	364.8	368.0	371.9	375.9	379.2	383.1	385.1
170°	352.1	354.2	357.7	361.1	362.6	364.6	367.5	371.0	373.0	375.9	377.9
172.5°	353.2	354.7	357.1	360.1	360.3	361.3	363.6	366.5	368.0	369.7	371.2
175°	354.9	354.9	356.3	358.4	357.7	357.7	359.1	360.5	361.1	362.6	362.6
177.5°	354.9	354.9	355.4	356.6	355.4	355.4	356.0	356.6	357.1	357.1	357.7
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	485.4	485.2	483.9	483.8	483.9	485.2	485.4	485.8	486.3	488.0	486.0
5°	448.4	447.4	446.7	449.1	446.7	447.4	448.4	449.7	451.8	452.0	454.1
7.5°	420.5	419.7	417.9	417.2	417.9	419.7	420.5	421.3	423.4	425.3	428.4
10°	402.7	401.8	400.1	399.7	400.1	401.8	402.7	404.7	406.9	409.2	411.3
12.5°	385.4	383.8	383.4	383.9	383.4	383.8	385.4	388.3	393.7	393.7	394.1
15°	362.6	361.7	359.4	360.1	359.4	361.7	362.6	365.3	367.8	371.0	374.2
17.5°	340.0	339.0	336.2	338.7	336.2	339.0	340.0	341.5	344.7	349.2	354.0
20°	325.8	324.1	322.7	322.4	322.7	324.1	325.8	327.3	330.9	334.7	338.3
22.5°	312.4	310.9	310.7	309.3	310.7	310.9	312.4	314.7	318.3	320.4	323.8
25°	295.4	294.0	293.6	292.5	293.6	294.0	295.4	297.1	299.4	301.1	305.0
27.5°	282.5	281.8	281.0	281.3	281.0	281.8	282.5	282.7	283.7	286.0	288.2
30°	274.6	274.4	273.9	273.9	273.9	274.4	274.6	273.9	275.0	276.1	277.8
32.5°	268.0	268.0	268.2	268.2	268.2	268.0	268.0	267.0	267.4	267.8	268.6
35°	258.8	259.4	259.8	259.1	259.8	259.4	258.8	257.9	257.3	255.7	256.2
37.5°	250.4	251.0	251.6	252.4	251.6	251.0	250.4	248.6	247.1	245.8	244.3
40°	244.0	245.4	245.8	246.9	245.8	245.4	244.0	242.1	240.4	238.9	237.2
42.5°	237.9	239.5	240.6	240.9	240.6	239.5	237.9	235.9	233.4	231.7	229.3
45°	228.5	230.2	231.8	231.8	231.8	230.2	228.5	225.4	222.7	219.9	217.6
47.5°	218.9	221.3	222.8	223.2	222.8	221.3	218.9	215.6	211.8	208.4	205.1
50°	212.3	215.3	216.8	217.8	216.8	215.3	212.3	208.7	204.7	200.5	196.4
52.5°	205.9	208.8	210.8	211.3	210.8	208.8	205.9	201.4	196.6	192.1	188.5
55°	194.7	199.0	201.3	202.2	201.3	199.0	194.7	189.9	185.3	179.6	174.5
57.5°	184.3	188.2	190.9	191.5	190.9	188.2	184.3	178.6	172.6	166.6	161.1
60°	176.2	180.5	183.8	184.4	183.8	180.5	176.2	170.5	164.2	158.3	151.5
62.5°	167.9	172.4	175.4	177.0	175.4	172.4	167.9	161.9	155.1	148.5	141.7
65°	153.6	158.1	161.0	161.7	161.0	158.1	153.6	147.8	140.5	133.6	127.9
67.5°	138.0	142.5	144.4	145.6	144.4	142.5	138.0	132.4	125.4	118.2	111.6
70°	127.1	130.6	132.8	133.8	132.8	130.6	127.1	121.1	115.2	107.8	100.9
72.5°	114.6	118.3	120.7	121.0	120.7	118.3	114.6	109.5	103.3	96.4	90.2
75°	95.4	98.8	100.0	100.0	100.0	98.8	95.4	90.5	85.5	80.0	73.8
77.5°	75.5	77.2	78.8	79.2	78.8	77.2	75.5	72.1	67.9	62.3	57.8
80°	62.7	63.8	65.0	65.0	65.0	63.8	62.7	59.5	55.5	50.8	47.3
82.5°	49.5	50.4	51.6	51.5	51.6	50.4	49.5	47.0	43.7	40.6	37.3
85°	30.0	31.8	31.7	31.2	31.7	31.8	30.0	30.4	27.2	25.1	22.2
87.5°	16.4	16.8	17.1	17.5	17.1	16.8	16.4	15.8	14.3	13.3	12.5
90°	14.6	15.3	14.6	14.6	14.6	15.3	14.6	13.9	13.9	13.3	12.6
92.5°	59.8	56.1	53.7	53.7	53.7	56.1	59.8	68.0	82.0	103.1	137.0
95°	213.4	191.7	179.2	170.1	179.2	191.7	213.4	247.5	315.1	408.6	516.7
97.5°	532.2	490.2	469.2	454.8	469.2	490.2	532.2	582.2	655.0	723.2	763.3
100°	708.4	665.8	645.0	639.4	645.0	665.8	708.4	769.1	820.6	854.8	840.9
102.5°	857.4	826.5	804.5	800.0	804.5	826.5	857.4	894.6	916.1	906.2	837.0
105°	1000.6	995.0	985.3	981.1	985.3	995.0	1000.6	999.2	970.5	901.5	781.0
107.5°	1023.6	1039.5	1046.4	1048.2	1046.4	1039.5	1023.6	989.1	926.9	829.7	701.3
110°	1001.2	1030.6	1043.1	1049.4	1043.1	1030.6	1001.2	951.7	875.0	773.9	653.4



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	953.2	988.7	1006.3	1016.5	1006.3	988.7	953.2	897.1	820.4	724.9	618.2
115°	872.3	914.1	936.4	942.0	936.4	914.1	872.3	817.2	750.2	668.7	582.9
117.5°	804.5	839.6	862.2	866.6	862.2	839.6	804.5	757.5	700.7	636.6	565.6
120°	767.7	798.3	816.5	824.1	816.5	798.3	767.7	727.9	678.4	622.7	557.8
122.5°	741.5	767.7	783.0	790.7	783.0	767.7	741.5	707.8	664.5	613.7	551.1
125°	714.0	734.2	747.4	751.6	747.4	734.2	714.0	686.1	647.7	599.7	539.7
127.5°	695.4	713.5	724.6	728.8	724.6	713.5	695.4	667.4	631.0	583.0	525.8
130°	682.6	700.1	711.2	715.4	711.2	700.1	682.6	654.0	617.1	569.6	514.6
132.5°	665.8	685.5	696.2	700.3	696.2	685.5	665.8	637.8	600.9	554.6	502.8
135°	637.3	656.8	668.0	672.2	668.0	656.8	637.3	609.4	574.5	532.0	486.7
137.5°	603.8	623.0	632.2	637.3	632.2	623.0	603.8	577.7	546.3	510.4	472.1
140°	581.5	596.8	606.6	612.2	606.6	596.8	581.5	557.1	527.8	496.4	463.7
142.5°	558.7	572.8	581.5	585.4	581.5	572.8	558.7	537.0	511.7	484.7	455.8
145°	526.5	538.2	545.3	548.8	545.3	538.2	526.5	509.0	489.5	468.6	444.9
147.5°	499.5	509.7	515.0	516.2	515.0	509.7	499.5	486.7	471.4	454.6	435.8
150°	483.9	492.9	497.1	497.8	497.1	492.9	483.9	472.7	460.2	446.2	430.2
152.5°	470.5	477.9	480.4	481.1	480.4	477.9	470.5	461.0	450.7	437.8	424.1
155°	451.8	457.4	459.5	459.5	459.5	457.4	451.8	444.9	436.5	426.1	414.8
157.5°	435.1	439.3	440.5	440.5	440.5	439.3	435.1	429.8	423.1	414.3	404.9
160°	423.9	428.1	428.8	428.8	428.8	428.1	423.9	419.7	414.2	406.5	398.9
162.5°	413.3	417.5	418.2	417.7	418.2	417.5	413.3	410.3	405.3	399.2	392.7
165°	399.5	402.3	401.6	400.9	401.6	402.3	399.5	396.7	393.2	388.3	384.1
167.5°	386.6	388.3	388.3	387.6	388.3	388.3	386.6	385.1	383.1	379.2	375.9
170°	379.3	380.0	379.3	379.3	379.3	380.0	379.3	377.9	375.9	373.0	371.0
172.5°	372.0	372.7	372.0	371.0	372.0	372.7	372.0	371.2	369.7	368.0	366.5
175°	362.6	364.0	362.6	361.1	362.6	364.0	362.6	362.6	362.6	361.1	360.5
177.5°	357.1	357.7	356.6	355.4	356.6	357.7	357.1	357.7	357.1	357.1	356.6
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	487.0	487.7	490.4	492.9	496.0	498.1	499.6	501.3	504.9	507.7	510.5
5°	456.3	457.4	462.8	466.6	473.1	478.8	483.3	488.1	493.8	501.7	508.8
7.5°	429.2	433.1	439.2	445.3	451.9	459.4	465.9	473.2	483.0	493.8	504.9
10°	413.8	418.3	424.6	431.8	438.1	446.7	454.8	463.4	474.7	487.7	500.8
12.5°	398.5	405.8	410.6	419.1	426.0	433.1	441.7	453.0	466.0	479.7	495.5
15°	379.2	383.3	392.5	397.2	406.9	417.9	426.3	437.7	450.3	468.5	486.2
17.5°	357.0	362.3	369.7	378.5	389.7	398.2	408.8	420.5	436.5	454.5	476.7
20°	342.5	347.0	356.1	365.7	377.6	386.6	397.8	409.2	425.7	444.9	468.1
22.5°	329.5	333.8	343.4	352.4	363.9	375.0	386.6	399.9	415.7	436.0	459.7
25°	309.4	315.0	323.5	332.8	343.8	356.4	369.1	380.9	397.8	419.1	444.4
27.5°	291.5	296.0	302.2	312.7	325.2	337.4	350.0	364.9	381.1	403.7	429.9
30°	280.1	284.3	290.4	300.1	311.7	324.8	337.9	352.2	369.1	391.5	418.3
32.5°	270.9	274.1	279.6	288.3	298.9	312.6	325.6	340.4	358.1	380.1	406.3
35°	257.4	260.2	262.3	270.5	280.1	292.7	305.8	321.6	338.8	359.6	385.8
37.5°	244.2	245.2	248.3	253.7	262.9	274.6	286.7	302.3	319.8	341.0	364.6
40°	236.1	236.6	238.4	243.5	251.6	262.5	274.4	289.7	306.4	326.5	349.9
42.5°	228.2	227.9	229.7	233.3	240.8	250.7	262.3	276.4	293.1	311.7	333.7
45°	215.7	215.7	215.3	218.2	224.4	234.1	243.8	257.3	271.2	289.4	307.9
47.5°	202.6	201.4	201.8	203.3	208.5	216.4	226.2	237.3	249.6	264.9	281.2
50°	194.1	192.4	191.8	193.5	198.1	205.1	214.5	224.1	235.8	249.2	263.1
52.5°	184.9	183.2	182.0	183.2	187.5	193.9	202.4	211.0	221.4	232.4	244.4
55°	170.5	168.6	168.0	168.4	171.6	176.6	183.8	191.6	199.5	208.5	217.0
57.5°	156.4	153.3	152.7	152.5	154.6	159.3	165.3	172.0	177.7	183.2	192.3
60°	147.1	143.3	142.0	141.8	143.5	147.3	152.8	159.5	163.5	167.4	175.1
62.5°	137.1	133.5	130.7	131.0	132.5	136.2	141.0	145.9	148.6	152.7	157.9
65°	121.8	117.2	115.0	114.4	115.2	118.2	122.0	125.1	128.1	129.8	134.8
67.5°	106.4	102.5	99.4	98.6	98.3	100.3	103.4	105.3	107.5	108.9	111.9
70°	95.6	92.2	88.5	87.1	86.9	88.6	91.6	91.8	94.8	95.4	98.5
72.5°	85.0	80.7	78.1	76.9	76.0	77.5	79.5	80.0	81.6	82.8	84.4
75°	68.4	65.2	62.7	60.8	60.2	61.0	61.0	62.1	63.1	63.8	65.6
77.5°	53.9	50.2	47.2	46.1	45.3	44.8	45.2	45.9	45.4	46.5	46.9
80°	43.7	39.9	37.5	37.2	35.8	34.9	34.6	35.2	34.4	34.9	36.1
82.5°	33.7	31.3	28.8	28.4	26.8	26.2	26.0	25.6	25.6	25.5	25.8
85°	20.1	18.5	16.9	15.9	15.2	14.2	14.2	13.7	13.3	12.8	13.1
87.5°	10.4	10.3	9.2	8.4	8.0	6.5	6.5	5.9	5.5	5.0	4.5
90°	11.9	12.6	11.1	9.7	9.7	5.6	5.6	4.9	4.2	2.1	0.7
92.5°	184.2	221.1	193.6	140.8	86.8	51.3	36.8	26.7	18.1	11.6	7.9
95°	584.3	568.3	428.8	262.2	147.8	87.1	57.9	41.1	32.1	25.1	23.0
97.5°	734.1	598.5	401.4	235.7	141.2	94.5	70.0	55.6	47.3	41.3	41.3
100°	739.0	560.6	364.0	221.8	142.9	101.8	79.5	66.3	57.9	53.0	53.0
102.5°	697.2	513.2	338.9	217.8	148.5	111.3	90.1	77.4	69.6	65.3	64.1
105°	621.3	457.4	317.3	219.6	161.8	128.3	108.1	95.5	87.1	83.6	81.6
107.5°	559.9	426.1	313.3	230.0	177.3	146.6	126.6	114.6	105.7	102.2	100.9
110°	529.2	415.5	314.4	237.7	189.0	158.3	139.5	126.9	118.5	115.0	113.7



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	511.9	410.5	317.8	246.1	200.1	170.6	151.7	139.2	131.3	127.3	125.9
115°	495.7	407.9	324.2	259.4	217.6	189.7	170.9	157.6	150.6	145.7	143.7
117.5°	488.5	407.2	331.1	272.9	234.4	207.9	188.4	176.0	168.4	164.0	162.0
120°	484.6	407.2	336.1	282.4	246.1	219.6	200.1	188.2	180.6	175.7	174.3
122.5°	480.1	406.6	341.1	291.3	257.3	230.8	211.8	198.9	191.7	186.9	185.5
125°	472.7	405.8	348.7	304.7	272.6	247.5	228.0	214.7	207.1	202.9	200.1
127.5°	462.8	404.3	354.6	316.3	286.9	262.6	242.9	229.1	220.3	215.3	213.1
130°	456.7	403.7	359.1	323.5	296.3	272.6	252.4	239.2	228.7	223.1	220.3
132.5°	451.1	403.1	363.0	330.7	304.2	280.4	261.4	247.0	237.1	229.8	227.6
135°	442.7	402.3	368.8	340.3	315.1	292.1	274.0	259.4	247.5	240.6	237.7
137.5°	435.5	402.2	372.3	347.0	323.5	302.0	284.7	269.6	258.2	250.6	248.0
140°	431.6	401.6	375.1	351.4	329.1	308.2	291.4	276.8	264.9	257.3	255.2
142.5°	428.3	401.6	377.4	354.7	334.1	313.8	297.6	283.5	272.2	265.1	263.0
145°	422.5	400.2	378.6	358.4	339.6	321.5	306.1	292.8	283.1	276.1	274.0
147.5°	417.4	397.7	379.3	361.6	345.2	328.1	314.3	303.3	293.3	287.1	286.4
150°	413.5	396.0	379.3	363.3	347.9	332.6	319.3	308.9	300.5	295.0	294.3
152.5°	409.0	393.2	378.2	364.4	350.2	336.5	324.4	315.0	307.2	301.7	301.5
155°	402.3	389.1	376.5	365.3	353.5	341.6	331.2	323.5	316.6	312.4	311.7
157.5°	395.5	384.8	374.7	365.3	355.9	345.8	337.6	330.9	325.5	321.6	321.6
160°	390.5	381.4	373.0	365.3	357.0	348.7	341.0	335.4	330.5	327.7	327.7
162.5°	386.0	378.1	371.4	365.3	358.1	350.3	344.3	339.3	334.9	332.7	333.3
165°	378.6	373.0	368.2	364.0	358.4	352.1	347.9	344.5	341.0	339.6	339.6
167.5°	371.9	368.0	364.8	362.3	358.3	353.7	350.4	348.5	345.8	345.2	345.8
170°	367.5	364.6	362.6	361.1	357.7	354.2	352.1	350.7	348.7	347.9	348.7
172.5°	363.6	361.3	360.3	360.1	357.1	354.7	353.2	352.4	350.9	350.7	351.4
175°	359.1	357.7	357.7	358.4	356.3	354.9	354.9	354.2	353.5	353.5	354.2
177.5°	356.0	355.4	355.4	356.6	355.4	354.9	354.9	354.9	354.4	354.9	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	512.8	514.5	516.7	520.4	521.7	523.4	525.8	525.7	526.3	528.9	534.2
5°	514.7	521.3	527.6	535.2	543.2	548.5	555.6	560.1	564.5	570.2	580.0
7.5°	515.5	525.8	537.4	550.8	562.7	576.3	587.0	597.1	606.2	618.1	629.7
10°	514.3	528.2	543.2	560.1	578.0	593.3	607.0	622.6	635.9	650.4	663.5
12.5°	512.1	528.9	548.9	567.8	588.8	611.3	628.4	644.2	661.8	678.6	698.8
15°	507.1	530.1	553.6	578.5	606.5	632.5	657.2	677.6	696.6	721.8	748.1
17.5°	500.8	525.6	555.2	585.3	614.7	644.3	674.8	705.6	729.6	760.8	781.4
20°	494.9	523.6	554.0	589.9	619.2	656.1	686.5	716.2	749.2	780.2	804.9
22.5°	486.6	518.0	550.3	585.9	624.6	661.6	696.6	728.9	761.9	795.6	825.5
25°	476.1	504.6	542.8	583.3	621.7	661.8	702.1	742.6	778.1	813.8	841.6
27.5°	458.3	494.2	529.8	571.6	614.2	659.6	702.8	745.1	782.3	811.6	828.8
30°	449.1	480.4	519.0	561.0	607.2	655.9	700.9	742.4	777.0	800.5	807.4
32.5°	435.6	467.8	505.6	549.1	598.1	648.2	694.9	734.1	763.0	775.3	767.0
35°	415.5	444.7	482.9	527.4	578.3	631.6	677.9	711.0	725.8	714.2	685.3
37.5°	391.5	420.4	458.7	502.5	555.1	609.4	651.1	675.0	670.1	641.2	598.2
40°	374.6	401.6	438.1	485.4	536.6	591.1	627.9	640.7	627.2	585.9	540.0
42.5°	355.9	382.2	418.8	464.5	518.8	569.0	601.0	602.1	579.4	529.9	484.0
45°	327.3	352.4	387.0	434.5	484.7	532.0	553.1	542.8	501.0	453.3	407.1
47.5°	299.2	320.9	355.1	400.1	447.8	487.6	498.1	479.5	435.0	388.6	345.8
50°	278.6	300.5	332.6	375.7	421.7	456.0	461.1	436.4	392.7	346.1	312.5
52.5°	258.8	280.6	311.5	351.3	393.4	424.5	424.6	396.1	352.6	311.0	279.8
55°	229.8	249.4	277.3	313.0	350.5	374.8	368.9	339.4	301.6	265.5	238.3
57.5°	201.9	219.0	244.6	274.4	307.5	327.5	317.7	289.3	255.6	224.9	204.3
60°	183.8	200.1	222.0	250.1	277.9	293.6	284.3	258.5	227.5	202.8	184.9
62.5°	166.2	179.9	201.1	225.4	251.3	262.8	254.6	229.2	202.3	180.0	165.4
65°	141.4	152.6	169.4	190.4	209.1	219.1	212.1	188.4	168.0	151.9	140.4
67.5°	118.2	126.9	139.7	156.5	172.5	177.8	171.5	155.0	137.7	124.8	116.6
70°	102.1	110.4	121.1	134.0	147.9	153.6	147.3	134.2	120.1	108.3	100.2
72.5°	88.1	94.5	103.6	114.6	125.5	131.2	126.9	114.3	102.4	93.5	86.8
75°	67.1	72.6	78.9	86.8	95.1	99.0	95.1	86.5	78.3	71.8	66.9
77.5°	48.8	51.7	56.6	62.5	67.8	70.6	67.3	61.5	56.4	52.0	49.6
80°	37.2	39.2	42.6	47.3	50.8	53.6	51.5	46.6	42.6	39.7	38.6
82.5°	27.0	28.4	30.7	34.1	36.5	37.9	37.0	33.4	31.8	29.2	28.2
85°	13.3	14.2	15.6	16.7	18.8	19.0	19.2	17.7	16.2	15.6	14.8
87.5°	5.0	5.5	6.2	6.9	7.5	8.6	8.4	8.6	8.3	7.9	7.4
90°	2.1	4.2	4.9	5.6	5.6	9.7	9.7	11.1	12.6	11.9	12.6
92.5°	11.6	18.1	26.7	36.8	51.3	86.8	140.8	193.6	221.1	184.2	137.0
95°	25.1	32.1	41.1	57.9	87.1	147.8	262.2	428.8	568.3	584.3	516.7
97.5°	41.3	47.3	55.6	70.0	94.5	141.2	235.7	401.4	598.5	734.1	763.3
100°	53.0	57.9	66.3	79.5	101.8	142.9	221.8	364.0	560.6	739.0	840.9
102.5°	65.3	69.6	77.4	90.1	111.3	148.5	217.8	338.9	513.2	697.2	837.0
105°	83.6	87.1	95.5	108.1	128.3	161.8	219.6	317.3	457.4	621.3	781.0
107.5°	102.2	105.7	114.6	126.6	146.6	177.3	230.0	313.3	426.1	559.9	701.3
110°	115.0	118.5	126.9	139.5	158.3	189.0	237.7	314.4	415.5	529.2	653.4



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	131.3	139.2	151.7	170.6	200.1	246.1	317.8	410.5	511.9	618.2
115°	145.7	150.6	157.6	170.9	189.7	217.6	259.4	324.2	407.9	495.7	582.9
117.5°	164.0	168.4	176.0	188.4	207.9	234.4	272.9	331.1	407.2	488.5	565.6
120°	175.7	180.6	188.2	200.1	219.6	246.1	282.4	336.1	407.2	484.6	557.8
122.5°	186.9	191.7	198.9	211.8	230.8	257.3	291.3	341.1	406.6	480.1	551.1
125°	202.9	207.1	214.7	228.0	247.5	272.6	304.7	348.7	405.8	472.7	539.7
127.5°	215.3	220.3	229.1	242.9	262.6	286.9	316.3	354.6	404.3	462.8	525.8
130°	223.1	228.7	239.2	252.4	272.6	296.3	323.5	359.1	403.7	456.7	514.6
132.5°	229.8	237.1	247.0	261.4	280.4	304.2	330.7	363.0	403.1	451.1	502.8
135°	240.6	247.5	259.4	274.0	292.1	315.1	340.3	368.8	402.3	442.7	486.7
137.5°	250.6	258.2	269.6	284.7	302.0	323.5	347.0	372.3	402.2	435.5	472.1
140°	257.3	264.9	276.8	291.4	308.2	329.1	351.4	375.1	401.6	431.6	463.7
142.5°	265.1	272.2	283.5	297.6	313.8	334.1	354.7	377.4	401.6	428.3	455.8
145°	276.1	283.1	292.8	306.1	321.5	339.6	358.4	378.6	400.2	422.5	444.9
147.5°	287.1	293.3	303.3	314.3	328.1	345.2	361.6	379.3	397.7	417.4	435.8
150°	295.0	300.5	308.9	319.3	332.6	347.9	363.3	379.3	396.0	413.5	430.2
152.5°	301.7	307.2	315.0	324.4	336.5	350.2	364.4	378.2	393.2	409.0	424.1
155°	312.4	316.6	323.5	331.2	341.6	353.5	365.3	376.5	389.1	402.3	414.8
157.5°	321.6	325.5	330.9	337.6	345.8	355.9	365.3	374.7	384.8	395.5	404.9
160°	327.7	330.5	335.4	341.0	348.7	357.0	365.3	373.0	381.4	390.5	398.9
162.5°	332.7	334.9	339.3	344.3	350.3	358.1	365.3	371.4	378.1	386.0	392.7
165°	339.6	341.0	344.5	347.9	352.1	358.4	364.0	368.2	373.0	378.6	384.1
167.5°	345.2	345.8	348.5	350.4	353.7	358.3	362.3	364.8	368.0	371.9	375.9
170°	347.9	348.7	350.7	352.1	354.2	357.7	361.1	362.6	364.6	367.5	371.0
172.5°	350.7	350.9	352.4	353.2	354.7	357.1	360.1	360.3	361.3	363.6	366.5
175°	353.5	353.5	354.2	354.9	354.9	356.3	358.4	357.7	357.7	359.1	360.5
177.5°	354.9	354.4	354.9	354.9	354.9	355.4	356.6	355.4	355.4	356.0	356.6
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	509.4	509.4	509.4	509.4	509.4	509.4	509.4
2.5°	537.0	537.3	538.9	540.0	540.4	542.1	542.2
5°	584.2	587.7	594.7	595.3	596.4	601.9	597.6
7.5°	639.4	648.5	654.6	660.0	661.9	664.3	663.9
10°	674.9	688.4	695.2	706.0	706.3	709.1	707.4
12.5°	710.5	726.2	738.5	740.6	749.6	751.0	753.3
15°	761.0	777.7	794.8	800.9	813.3	816.3	820.9
17.5°	808.4	825.5	837.5	853.3	858.4	865.2	860.6
20°	834.5	853.0	868.3	880.7	885.9	889.7	889.3
22.5°	850.2	868.9	881.2	890.6	895.5	897.2	897.1
25°	860.0	870.8	874.6	878.2	872.6	870.8	871.6
27.5°	832.6	829.8	819.9	806.9	793.4	782.7	776.9
30°	795.0	778.6	763.6	737.4	723.9	715.9	708.6
32.5°	741.6	715.5	686.7	662.7	647.4	635.5	633.7
35°	650.2	611.0	575.7	546.4	531.2	518.4	515.3
37.5°	552.8	512.0	480.3	454.4	438.1	429.0	420.5
40°	488.1	453.1	421.9	399.9	387.4	380.9	375.7
42.5°	438.4	406.4	375.2	358.6	347.3	343.3	340.2
45°	369.5	339.7	318.3	305.6	299.1	292.3	289.1
47.5°	314.4	290.3	276.1	265.3	258.2	254.2	252.3
50°	283.2	263.4	250.7	242.5	236.1	233.0	231.3
52.5°	255.6	239.2	228.6	222.0	217.8	215.4	214.7
55°	220.1	207.7	200.9	195.2	192.1	189.9	189.1
57.5°	191.4	181.7	176.3	171.6	170.3	168.6	168.0
60°	172.5	165.1	160.4	157.2	156.1	154.1	154.4
62.5°	155.7	149.6	145.7	143.9	142.5	140.7	141.3
65°	131.7	127.2	125.1	123.5	121.8	120.7	121.5
67.5°	110.5	107.5	104.6	103.6	102.8	102.6	101.7
70°	96.7	94.2	91.6	91.0	91.0	90.2	89.9
72.5°	83.3	81.5	79.8	79.3	78.6	79.0	78.1
75°	64.4	62.9	62.2	61.6	61.4	61.4	60.8
77.5°	47.5	46.5	45.5	45.5	44.7	44.4	44.3
80°	36.1	35.7	34.9	34.9	34.4	34.6	34.2
82.5°	27.1	26.6	26.4	26.0	25.4	25.5	25.1
85°	14.5	13.9	13.7	13.1	12.7	13.1	12.7
87.5°	7.8	7.7	7.5	7.3	7.3	7.1	6.6
90°	13.3	13.9	13.9	14.6	15.3	14.6	14.6
92.5°	103.1	82.0	68.0	59.8	56.1	53.7	53.7
95°	408.6	315.1	247.5	213.4	191.7	179.2	170.1
97.5°	723.2	655.0	582.2	532.2	490.2	469.2	454.8
100°	854.8	820.6	769.1	708.4	665.8	645.0	639.4
102.5°	906.2	916.1	894.6	857.4	826.5	804.5	800.0
105°	901.5	970.5	999.2	1000.6	995.0	985.3	981.1
107.5°	829.7	926.9	989.1	1023.6	1039.5	1046.4	1048.2
110°	773.9	875.0	951.7	1001.2	1030.6	1043.1	1049.4



TEST NUMBER: P332510-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	724.9	820.4	897.1	953.2	988.7	1006.3	1016.5
115°	668.7	750.2	817.2	872.3	914.1	936.4	942.0
117.5°	636.6	700.7	757.5	804.5	839.6	862.2	866.6
120°	622.7	678.4	727.9	767.7	798.3	816.5	824.1
122.5°	613.7	664.5	707.8	741.5	767.7	783.0	790.7
125°	599.7	647.7	686.1	714.0	734.2	747.4	751.6
127.5°	583.0	631.0	667.4	695.4	713.5	724.6	728.8
130°	569.6	617.1	654.0	682.6	700.1	711.2	715.4
132.5°	554.6	600.9	637.8	665.8	685.5	696.2	700.3
135°	532.0	574.5	609.4	637.3	656.8	668.0	672.2
137.5°	510.4	546.3	577.7	603.8	623.0	632.2	637.3
140°	496.4	527.8	557.1	581.5	596.8	606.6	612.2
142.5°	484.7	511.7	537.0	558.7	572.8	581.5	585.4
145°	468.6	489.5	509.0	526.5	538.2	545.3	548.8
147.5°	454.6	471.4	486.7	499.5	509.7	515.0	516.2
150°	446.2	460.2	472.7	483.9	492.9	497.1	497.8
152.5°	437.8	450.7	461.0	470.5	477.9	480.4	481.1
155°	426.1	436.5	444.9	451.8	457.4	459.5	459.5
157.5°	414.3	423.1	429.8	435.1	439.3	440.5	440.5
160°	406.5	414.2	419.7	423.9	428.1	428.8	428.8
162.5°	399.2	405.3	410.3	413.3	417.5	418.2	417.7
165°	388.3	393.2	396.7	399.5	402.3	401.6	400.9
167.5°	379.2	383.1	385.1	386.6	388.3	388.3	387.6
170°	373.0	375.9	377.9	379.3	380.0	379.3	379.3
172.5°	368.0	369.7	371.2	372.0	372.7	372.0	371.0
175°	361.1	362.6	362.6	362.6	364.0	362.6	361.1
177.5°	357.1	357.1	357.7	357.1	357.7	356.6	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9

(END OF REPORT)