

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332536-940

Luminaire Tested: **S124DIP-S575D365U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332536-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S575D365U940-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3442.4 lumens  
Efficiency: N/A  
Efficacy: 125.2 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	79	77	73	71	69	64	63	61	57
2	93	86	79	74	87	81	75	71	72	68	64	64	61	58	57	54	52	48
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	39	46	40	36	42	37	33	37	33	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6761	6761	6761	6761
5°	7963	6779	5983	6779
10°	9534	6749	5387	6749
15°	11280	6680	4947	6680
20°	12560	6611	4554	6611
25°	12764	6509	4284	6509
30°	10860	6411	4198	6411
35°	8349	6250	4199	6250
40°	6509	6062	4278	6062
45°	5426	5779	4349	5779
50°	4775	5434	4496	5434
55°	4376	5020	4677	5020
60°	4101	4648	4897	4648
65°	3817	4235	5075	4235
70°	3489	3824	5193	3824
75°	3119	3366	5128	3366
80°	2613	2757	4965	2757
85°	1927	1991	4761	1991



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.6	2.4
10°-20°	251.5	7.3
20°-30°	398.8	11.6
30°-40°	443.8	12.9
40°-50°	404.0	11.7
50°-60°	330.1	9.6
60°-70°	235.7	6.8
70°-80°	129.8	3.8
80°-90°	36.7	1.1
90°-100°	26.9	0.8
100°-110°	79.6	2.3
110°-120°	135.1	3.9
120°-130°	178.2	5.2
130°-140°	200.1	5.8
140°-150°	196.6	5.7
150°-160°	165.4	4.8
160°-170°	110.0	3.2
170°-180°	38.5	1.1
0°-30°	731.9	21.3
0°-40°	1175.7	34.2
0°-60°	1909.9	55.5
0°-90°	2312.0	67.2
90°-120°	241.6	7.0
90°-150°	816.5	23.7
90°-180°	1130.0	32.8
0°-180°	3442.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	838	838	838	838	838	
5°	983	836	738	836	983	100
15°	1350	799	592	799	1350	381
25°	1433	731	481	731	1433	632
35°	847	634	426	634	847	538
45°	475	506	381	506	475	374
55°	311	357	332	357	311	281
65°	200	222	266	222	200	198
75°	100	108	164	108	100	106
85°	21	22	51	22	21	26
90°	10	1	10	1	10	6
95°	25	19	25	19	25	26
105°	77	73	77	73	77	81
115°	136	137	136	137	136	135
125°	198	200	198	200	198	177
135°	258	258	258	258	258	200
145°	314	314	314	314	314	196
155°	359	359	359	359	359	165
165°	390	391	390	391	390	110
175°	405	407	405	407	405	38
180°	407	407	407	407	407	



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	891.4	891.1	888.3	887.8	885.8	883.3	882.8	878.3	869.4	865.3	864.2
5°	982.6	989.5	980.4	978.7	977.7	966.3	960.4	953.4	937.5	928.1	920.8
7.5°	1091.4	1092.2	1088.2	1085.0	1076.2	1066.2	1051.2	1035.3	1016.3	996.5	981.6
10°	1163.0	1165.7	1161.3	1160.6	1142.8	1131.8	1109.6	1090.8	1069.3	1045.4	1023.5
12.5°	1238.5	1234.6	1232.3	1217.5	1214.2	1193.9	1168.1	1148.8	1115.6	1088.1	1059.0
15°	1349.6	1342.0	1337.1	1316.7	1306.6	1278.5	1251.1	1229.9	1186.6	1145.3	1114.0
17.5°	1414.9	1422.5	1411.2	1402.8	1376.8	1357.1	1329.1	1284.7	1250.7	1199.4	1160.0
20°	1462.0	1462.8	1456.5	1447.8	1427.4	1402.4	1371.8	1323.3	1282.6	1231.6	1177.5
22.5°	1474.8	1475.0	1472.3	1464.2	1448.7	1428.4	1397.7	1357.1	1308.0	1252.5	1198.4
25°	1432.9	1431.6	1434.7	1443.7	1437.8	1431.6	1413.8	1383.7	1337.8	1279.2	1220.9
27.5°	1277.2	1286.7	1304.4	1326.6	1348.0	1364.2	1368.9	1362.7	1334.3	1286.0	1225.0
30°	1165.0	1176.9	1190.0	1212.3	1255.3	1279.9	1307.0	1327.4	1316.0	1277.5	1220.6
32.5°	1041.8	1044.7	1064.3	1089.6	1129.0	1176.3	1219.2	1260.8	1274.6	1254.5	1206.9
35°	847.2	852.1	873.3	898.2	946.5	1004.4	1069.0	1126.5	1174.1	1193.2	1168.9
37.5°	691.4	705.3	720.2	747.1	789.6	841.8	908.8	983.3	1054.2	1101.6	1109.6
40°	617.6	626.2	637.0	657.5	693.6	744.9	802.5	887.9	963.1	1031.2	1053.4
42.5°	559.3	564.4	571.0	589.4	617.0	668.0	720.6	795.7	871.3	952.6	989.8
45°	475.3	480.5	491.6	502.4	523.2	558.6	607.5	669.2	745.2	823.7	892.3
47.5°	414.6	418.0	424.6	436.1	453.8	477.2	516.9	568.5	638.9	715.1	788.3
50°	380.2	383.0	388.3	398.7	412.1	433.0	465.6	513.8	569.0	645.7	717.5
52.5°	353.0	354.2	358.0	365.1	375.9	393.3	420.1	459.9	511.3	579.6	651.1
55°	310.9	312.3	315.8	320.9	330.3	341.4	361.9	391.7	436.5	495.8	557.9
57.5°	276.2	277.1	280.1	282.0	289.8	298.8	314.5	335.8	369.8	420.1	475.5
60°	254.0	253.2	256.7	258.5	263.7	271.3	283.5	303.9	333.4	374.0	425.0
62.5°	232.3	231.3	234.3	236.6	239.5	246.0	256.0	272.0	296.0	332.7	376.7
65°	199.8	198.5	200.2	203.0	205.7	209.2	216.5	230.7	249.8	276.2	309.8
67.5°	167.2	168.7	169.0	170.3	171.9	176.6	181.6	191.7	205.2	226.3	254.8
70°	147.8	148.1	149.5	149.5	150.6	154.7	158.9	164.8	178.0	197.4	220.7
72.5°	128.4	129.8	129.3	130.4	131.2	133.9	137.0	142.6	153.8	168.3	187.9
75°	100.0	100.9	100.9	101.3	102.4	103.3	105.8	109.9	118.0	128.7	142.2
77.5°	72.9	73.0	73.5	74.7	74.7	76.4	78.2	81.5	85.5	92.8	101.1
80°	56.2	56.9	56.5	57.2	57.2	58.7	59.3	63.5	65.2	70.1	76.7
82.5°	41.2	41.9	41.8	42.8	43.3	43.6	44.6	46.3	48.0	52.3	55.0
85°	20.8	21.5	20.8	21.5	22.6	22.9	23.9	24.3	25.7	26.8	29.2
87.5°	8.0	8.8	8.7	9.0	9.5	9.8	10.0	9.6	10.6	10.8	11.9
90°	9.5	9.3	9.2	9.0	8.9	8.6	8.2	7.8	7.3	7.0	6.3
92.5°	14.0	13.9	13.8	13.7	13.6	13.5	13.2	13.0	12.8	12.5	12.1
95°	24.9	24.9	24.9	24.9	24.9	24.8	24.6	24.3	24.2	24.0	23.5
97.5°	39.0	39.0	39.0	39.0	39.0	38.9	38.6	38.3	38.2	37.9	37.3
100°	48.9	48.9	48.9	48.9	48.9	48.8	48.6	48.5	48.3	48.2	47.6
102.5°	59.9	59.8	59.8	59.7	59.7	59.6	59.4	59.2	59.0	58.8	58.2
105°	76.9	76.7	76.5	76.2	76.1	75.8	75.6	75.4	75.2	75.0	74.7
107.5°	93.4	93.5	93.5	93.5	93.5	93.4	93.2	93.0	92.7	92.6	92.6
110°	105.2	105.0	104.9	104.6	104.4	104.3	104.5	104.7	104.8	105.0	105.0



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	117.3	117.3	117.3	117.3	117.2	117.2	117.2	117.3	117.3	117.3	117.4
115°	136.2	136.2	136.3	136.3	136.4	136.4	136.5	136.6	136.7	136.8	136.9
117.5°	154.0	154.2	154.3	154.4	154.6	154.8	155.0	155.2	155.5	155.7	155.8
120°	167.6	167.5	167.4	167.2	167.1	167.2	167.6	167.9	168.3	168.6	168.8
122.5°	179.0	179.2	179.5	179.8	179.9	180.2	180.5	180.7	180.9	181.2	181.3
125°	198.5	198.7	198.8	198.9	199.0	199.2	199.4	199.5	199.7	199.7	199.8
127.5°	216.6	216.7	216.9	217.0	217.0	217.1	217.3	217.5	217.6	217.8	217.8
130°	228.5	228.7	229.0	229.3	229.5	229.8	229.9	230.1	230.2	230.3	230.3
132.5°	241.0	241.2	241.3	241.4	241.5	241.7	241.7	241.9	242.0	242.2	242.3
135°	258.4	258.6	258.8	259.0	259.2	259.4	259.6	259.7	259.8	259.9	259.9
137.5°	276.6	276.5	276.5	276.4	276.4	276.5	276.7	276.9	277.1	277.2	277.1
140°	287.7	287.8	287.8	287.9	287.9	288.0	288.1	288.2	288.3	288.3	288.3
142.5°	298.8	298.8	298.8	298.8	298.8	298.8	298.9	298.9	298.9	298.9	299.0
145°	313.9	314.1	314.2	314.5	314.7	314.9	314.9	315.0	315.0	315.1	315.0
147.5°	329.1	329.1	329.2	329.3	329.4	329.4	329.5	329.6	329.6	329.7	329.8
150°	338.4	338.5	338.6	338.7	338.7	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	347.0	347.1	347.3	347.5	347.7	347.8	347.6	347.4	347.2	347.1	347.0
155°	358.9	359.2	359.4	359.7	360.0	360.0	359.7	359.4	359.2	358.9	359.0
157.5°	369.5	369.8	370.1	370.2	370.5	370.5	370.3	370.1	369.9	369.7	369.7
160°	375.6	375.9	376.3	376.7	377.0	377.1	376.8	376.7	376.5	376.2	376.3
162.5°	381.9	382.3	382.6	383.0	383.3	383.3	382.9	382.5	382.2	381.7	381.8
165°	390.1	390.4	390.7	390.9	391.2	391.1	390.7	390.3	389.9	389.5	389.6
167.5°	395.9	396.4	396.8	397.3	397.7	397.7	397.3	396.9	396.5	396.0	396.0
170°	399.2	399.8	400.2	400.7	401.2	401.3	400.8	400.4	399.9	399.6	399.5
172.5°	402.0	402.5	403.0	403.5	403.9	403.9	403.5	403.1	402.5	402.1	402.1
175°	404.9	405.4	405.9	406.4	406.9	406.9	406.4	405.9	405.4	404.9	405.0
177.5°	406.4	406.9	407.3	407.8	408.2	408.2	407.9	407.4	407.1	406.7	406.7
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	864.4	860.6	857.8	855.6	849.4	845.9	843.1	839.2	834.7	830.0	824.2
5°	913.6	901.7	893.0	879.9	867.4	856.9	846.2	836.5	824.7	811.9	802.5
7.5°	965.1	947.5	925.1	905.5	883.6	864.5	847.5	830.0	811.8	794.2	778.0
10°	997.8	975.3	950.3	920.8	893.0	868.4	845.5	823.3	801.8	780.2	761.9
12.5°	1033.0	1005.0	968.0	933.5	902.5	869.5	841.9	814.7	788.7	766.2	744.7
15°	1080.4	1039.8	997.1	951.0	910.1	871.6	833.7	799.3	770.3	740.4	719.6
17.5°	1109.5	1059.3	1010.5	962.2	912.7	864.1	823.3	783.7	747.2	717.6	691.3
20°	1128.6	1078.7	1018.0	969.7	910.7	860.8	813.6	769.5	731.4	699.8	672.7
22.5°	1145.3	1087.5	1026.8	963.3	904.6	851.6	800.0	755.6	716.7	683.4	657.5
25°	1154.3	1088.1	1022.1	958.9	892.3	829.6	782.7	730.7	689.0	654.0	626.2
27.5°	1155.3	1084.4	1009.9	939.7	870.9	812.4	753.3	706.8	663.6	626.5	599.9
30°	1152.2	1078.3	998.2	922.2	853.2	789.6	738.3	687.7	643.5	606.8	579.1
32.5°	1142.5	1065.5	983.2	902.8	831.3	769.1	716.1	668.0	625.0	588.8	559.6
35°	1114.4	1038.4	950.7	867.0	793.8	731.0	683.1	634.2	591.2	556.9	528.8
37.5°	1070.5	1001.7	912.6	826.0	754.1	691.1	643.5	599.4	560.6	525.7	496.9
40°	1032.2	971.8	882.3	798.0	720.2	660.2	615.8	575.2	536.7	503.7	476.4
42.5°	988.0	935.4	852.8	763.6	688.6	628.3	585.1	548.6	512.3	481.9	454.4
45°	909.4	874.7	796.9	714.3	636.3	579.4	538.1	506.2	475.6	445.9	422.9
47.5°	818.9	801.6	736.2	657.8	583.7	527.6	491.9	462.4	435.6	410.3	390.1
50°	758.0	749.8	693.2	617.6	546.8	494.1	458.0	432.7	409.7	387.5	368.5
52.5°	698.1	697.9	646.8	577.6	512.1	461.3	425.5	401.8	382.0	363.9	346.8
55°	606.5	616.2	576.3	514.5	455.9	410.1	377.8	356.7	342.8	327.9	315.0
57.5°	522.3	538.4	505.5	451.1	402.2	360.0	331.9	316.0	301.2	292.2	282.9
60°	467.3	482.6	456.9	411.2	365.0	328.9	302.2	287.9	275.1	268.9	262.3
62.5°	418.5	432.1	413.0	370.6	330.6	295.9	273.3	259.7	251.0	244.2	239.8
65°	348.7	360.2	343.8	313.0	278.6	250.8	232.5	221.7	213.4	210.6	205.7
67.5°	281.9	292.3	283.5	257.3	229.7	208.7	194.3	184.0	179.1	176.6	173.2
70°	242.2	252.6	243.2	220.3	199.1	181.5	167.9	162.0	156.9	155.8	151.0
72.5°	208.6	215.7	206.3	188.4	170.3	155.3	144.9	138.8	136.0	134.1	131.5
75°	156.5	162.7	156.5	142.6	129.7	119.3	110.3	107.9	104.8	103.7	102.0
77.5°	110.8	116.2	111.4	102.7	93.1	85.1	80.3	77.1	76.4	74.6	75.4
80°	84.6	88.1	83.6	77.8	70.1	64.6	61.1	59.3	57.2	56.5	58.0
82.5°	60.8	62.3	60.0	56.1	50.4	46.7	44.4	42.4	42.0	42.1	42.1
85°	31.6	31.2	30.9	27.4	25.7	23.3	21.8	21.5	21.1	21.8	22.6
87.5°	11.7	11.9	11.5	10.3	9.3	8.3	7.8	7.4	7.8	8.3	8.7
90°	5.8	5.3	4.7	4.0	3.3	2.5	1.7	1.0	1.7	2.5	3.3
92.5°	11.7	11.3	10.9	10.3	9.4	8.5	7.7	6.8	7.7	8.5	9.4
95°	23.0	22.5	22.0	21.4	20.8	20.2	19.5	18.9	19.5	20.2	20.8
97.5°	36.7	36.1	35.6	35.0	34.5	34.1	33.5	33.0	33.5	34.1	34.5
100°	47.0	46.3	45.7	45.2	44.9	44.7	44.4	44.1	44.4	44.7	44.9
102.5°	57.7	57.1	56.5	56.2	56.1	55.9	55.8	55.7	55.8	55.9	56.1
105°	74.5	74.2	73.8	73.7	73.7	73.6	73.5	73.4	73.5	73.6	73.7
107.5°	92.5	92.5	92.4	92.4	92.3	92.2	92.1	92.0	92.1	92.2	92.3
110°	105.0	105.1	105.2	105.1	105.0	104.9	104.8	104.6	104.8	104.9	105.0





TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	117.5	117.6	117.8	117.8	117.8	117.8	117.7	117.7	117.7	117.8	117.8
115°	137.1	137.1	137.3	137.4	137.4	137.4	137.4	137.4	137.4	137.4	137.4
117.5°	156.0	156.0	156.1	156.1	156.0	156.0	156.0	155.9	156.0	156.0	156.0
120°	169.0	169.2	169.4	169.4	169.1	168.8	168.5	168.3	168.5	168.8	169.1
122.5°	181.4	181.5	181.6	181.6	181.5	181.4	181.2	181.1	181.2	181.4	181.5
125°	199.9	200.0	200.0	200.1	200.1	200.1	200.1	200.1	200.1	200.1	200.1
127.5°	217.9	218.1	218.2	218.1	217.9	217.8	217.5	217.3	217.5	217.8	217.9
130°	230.3	230.3	230.3	230.2	230.1	229.8	229.6	229.4	229.6	229.8	230.1
132.5°	242.3	242.4	242.4	242.4	242.2	242.0	241.9	241.7	241.9	242.0	242.2
135°	259.9	259.9	259.9	259.8	259.3	258.9	258.5	258.1	258.5	258.9	259.3
137.5°	277.0	276.9	276.8	276.6	276.4	276.3	276.1	275.8	276.1	276.3	276.4
140°	288.3	288.3	288.3	288.3	288.1	287.9	287.8	287.7	287.8	287.9	288.1
142.5°	299.0	299.1	299.2	299.1	298.9	298.8	298.6	298.5	298.6	298.8	298.9
145°	315.0	314.9	314.9	314.7	314.3	314.1	313.8	313.5	313.8	314.1	314.3
147.5°	329.8	329.8	329.8	329.8	329.4	329.0	328.8	328.4	328.8	329.0	329.4
150°	338.8	338.8	338.8	338.6	338.3	338.0	337.8	337.5	337.8	338.0	338.3
152.5°	347.0	346.9	346.8	346.7	346.5	346.3	346.3	346.1	346.3	346.3	346.5
155°	359.0	359.1	359.2	359.2	359.2	359.2	359.2	359.2	359.2	359.2	359.2
157.5°	369.7	369.7	369.7	369.8	370.0	370.1	370.1	370.3	370.1	370.1	370.0
160°	376.4	376.5	376.5	376.6	376.7	376.7	376.7	376.8	376.7	376.7	376.7
162.5°	381.9	382.0	382.1	382.2	382.4	382.5	382.7	382.9	382.7	382.5	382.4
165°	389.8	389.9	390.0	390.2	390.4	390.7	390.8	391.0	390.8	390.7	390.4
167.5°	396.0	396.0	395.9	396.1	396.4	396.7	397.0	397.3	397.0	396.7	396.4
170°	399.4	399.3	399.3	399.4	399.8	400.1	400.5	400.8	400.5	400.1	399.8
172.5°	402.1	402.0	402.0	402.2	402.4	402.7	403.1	403.3	403.1	402.7	402.4
175°	405.0	405.1	405.2	405.4	405.7	406.1	406.4	406.8	406.4	406.1	405.7
177.5°	406.7	406.7	406.7	406.8	407.1	407.3	407.7	408.0	407.7	407.3	407.1
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	821.4	818.9	815.3	810.3	806.2	801.7	800.6	799.0	802.3	799.5	798.7
5°	794.5	787.2	777.8	767.1	760.9	751.8	750.1	746.6	743.2	742.8	739.3
7.5°	766.0	755.3	743.1	732.1	721.9	712.1	705.6	704.3	699.1	696.2	692.7
10°	747.7	734.5	720.2	709.9	698.0	687.7	680.4	676.2	672.7	668.9	665.5
12.5°	726.0	712.0	700.3	689.0	675.0	667.1	655.1	647.9	647.2	647.3	638.3
15°	700.8	687.0	668.9	653.0	645.3	630.1	623.5	615.1	609.9	604.8	600.6
17.5°	672.1	654.8	640.7	622.3	607.8	595.7	586.9	581.9	574.2	566.8	561.4
20°	654.0	635.6	620.7	601.3	585.3	570.4	563.1	556.2	550.3	544.0	538.1
22.5°	635.7	616.4	598.2	579.3	564.5	548.8	541.7	532.3	526.6	523.2	517.3
25°	606.8	586.0	565.2	547.2	531.9	518.0	508.6	501.3	495.1	492.3	488.5
27.5°	575.4	554.7	534.7	514.2	496.9	486.8	479.3	473.8	470.2	466.5	464.8
30°	555.4	534.0	512.5	493.4	477.4	467.3	460.4	456.6	453.8	452.1	450.3
32.5°	535.2	514.0	491.3	473.9	459.7	450.7	445.4	441.6	440.2	439.6	439.0
35°	502.7	481.3	460.4	444.8	431.2	427.8	423.3	421.2	420.5	422.9	424.0
37.5°	471.3	451.3	432.1	417.1	408.1	403.1	401.5	401.6	404.1	406.3	408.8
40°	451.0	431.6	413.6	400.4	392.1	389.0	388.3	389.9	392.7	395.2	398.0
42.5°	431.3	412.1	395.8	383.4	377.6	374.8	375.2	376.9	380.8	383.8	388.0
45°	400.7	384.8	368.8	358.7	353.9	354.5	354.5	357.7	361.5	366.0	370.5
47.5°	371.9	355.8	342.7	334.2	331.7	331.1	333.1	337.2	342.7	348.2	354.5
50°	352.5	337.2	325.7	318.2	315.4	316.4	319.2	323.0	329.6	336.5	343.1
52.5°	332.8	318.9	308.3	301.2	299.3	301.1	303.9	310.0	315.8	323.2	331.2
55°	302.2	290.4	282.0	276.9	276.2	277.2	280.4	287.0	295.2	304.6	312.3
57.5°	271.7	261.9	254.2	250.7	251.0	252.0	257.1	264.9	273.8	283.8	293.6
60°	251.2	242.2	235.9	233.2	233.5	235.6	241.8	249.1	260.2	269.9	280.4
62.5°	231.8	223.8	217.8	215.3	214.9	219.5	225.4	233.0	244.2	254.9	266.2
65°	200.5	194.3	189.4	188.1	189.0	192.5	200.2	210.3	219.6	231.0	242.9
67.5°	170.0	164.9	161.6	162.2	163.5	168.5	175.0	183.6	194.2	206.1	217.8
70°	150.6	145.7	142.9	143.3	145.3	151.6	157.2	165.9	177.3	189.4	199.1
72.5°	130.6	127.4	124.9	126.4	128.4	132.8	139.6	148.4	158.5	169.7	180.0
75°	100.2	100.2	98.9	100.0	103.1	107.2	112.4	121.5	131.5	140.5	148.8
77.5°	74.4	73.7	74.5	75.8	77.6	82.5	88.5	95.0	102.5	111.6	118.4
80°	56.9	57.2	58.9	61.1	61.8	65.5	71.8	77.8	83.6	91.2	97.8
82.5°	42.7	43.1	44.0	46.6	47.3	51.5	55.5	61.3	66.7	71.8	77.3
85°	23.3	23.3	25.0	26.0	27.7	30.5	33.0	36.5	41.3	44.8	49.9
87.5°	9.7	9.8	11.1	11.7	12.7	14.2	14.8	17.9	19.1	20.6	23.2
90°	4.0	4.7	5.3	5.8	6.3	7.0	7.3	7.8	8.2	8.6	8.9
92.5°	10.3	10.9	11.3	11.7	12.1	12.5	12.8	13.0	13.2	13.5	13.6
95°	21.4	22.0	22.5	23.0	23.5	24.0	24.2	24.3	24.6	24.8	24.9
97.5°	35.0	35.6	36.1	36.7	37.3	37.9	38.2	38.3	38.6	38.9	39.0
100°	45.2	45.7	46.3	47.0	47.6	48.2	48.3	48.5	48.6	48.8	48.9
102.5°	56.2	56.5	57.1	57.7	58.2	58.8	59.0	59.2	59.4	59.6	59.7
105°	73.7	73.8	74.2	74.5	74.7	75.0	75.2	75.4	75.6	75.8	76.1
107.5°	92.4	92.4	92.5	92.5	92.6	92.6	92.7	93.0	93.2	93.4	93.5
110°	105.1	105.2	105.1	105.0	105.0	105.0	104.8	104.7	104.5	104.3	104.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.8	117.8	117.6	117.5	117.4	117.3	117.3	117.3	117.2	117.2	117.2
115°	137.4	137.3	137.1	137.1	136.9	136.8	136.7	136.6	136.5	136.4	136.4
117.5°	156.1	156.1	156.0	156.0	155.8	155.7	155.5	155.2	155.0	154.8	154.6
120°	169.4	169.4	169.2	169.0	168.8	168.6	168.3	167.9	167.6	167.2	167.1
122.5°	181.6	181.6	181.5	181.4	181.3	181.2	180.9	180.7	180.5	180.2	179.9
125°	200.1	200.0	200.0	199.9	199.8	199.7	199.7	199.5	199.4	199.2	199.0
127.5°	218.1	218.2	218.1	217.9	217.8	217.8	217.6	217.5	217.3	217.1	217.0
130°	230.2	230.3	230.3	230.3	230.3	230.3	230.2	230.1	229.9	229.8	229.5
132.5°	242.4	242.4	242.4	242.3	242.3	242.2	242.0	241.9	241.7	241.7	241.5
135°	259.8	259.9	259.9	259.9	259.9	259.9	259.8	259.7	259.6	259.4	259.2
137.5°	276.6	276.8	276.9	277.0	277.1	277.2	277.1	276.9	276.7	276.5	276.4
140°	288.3	288.3	288.3	288.3	288.3	288.3	288.3	288.2	288.1	288.0	287.9
142.5°	299.1	299.2	299.1	299.0	299.0	298.9	298.9	298.9	298.9	298.8	298.8
145°	314.7	314.9	314.9	315.0	315.0	315.1	315.0	315.0	314.9	314.9	314.7
147.5°	329.8	329.8	329.8	329.8	329.8	329.7	329.6	329.6	329.5	329.4	329.4
150°	338.6	338.8	338.8	338.8	338.8	338.8	338.8	338.8	338.8	338.8	338.7
152.5°	346.7	346.8	346.9	347.0	347.0	347.1	347.2	347.4	347.6	347.8	347.7
155°	359.2	359.2	359.1	359.0	359.0	358.9	359.2	359.4	359.7	360.0	360.0
157.5°	369.8	369.7	369.7	369.7	369.7	369.7	369.9	370.1	370.3	370.5	370.5
160°	376.6	376.5	376.5	376.4	376.3	376.2	376.5	376.7	376.8	377.1	377.0
162.5°	382.2	382.1	382.0	381.9	381.8	381.7	382.2	382.5	382.9	383.3	383.3
165°	390.2	390.0	389.9	389.8	389.6	389.5	389.9	390.3	390.7	391.1	391.2
167.5°	396.1	395.9	396.0	396.0	396.0	396.0	396.5	396.9	397.3	397.7	397.7
170°	399.4	399.3	399.3	399.4	399.5	399.6	399.9	400.4	400.8	401.3	401.2
172.5°	402.2	402.0	402.0	402.1	402.1	402.1	402.5	403.1	403.5	403.9	403.9
175°	405.4	405.2	405.1	405.0	405.0	404.9	405.4	405.9	406.4	406.9	406.9
177.5°	406.8	406.7	406.7	406.7	406.7	406.7	407.1	407.4	407.9	408.2	408.2
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	798.1	797.5	795.6	795.3	795.6	797.5	798.1	798.7	799.5	802.3	799.0
5°	737.3	735.6	734.5	738.3	734.5	735.6	737.3	739.3	742.8	743.2	746.6
7.5°	691.4	690.0	687.0	686.0	687.0	690.0	691.4	692.7	696.2	699.1	704.3
10°	662.0	660.6	657.8	657.1	657.8	660.6	662.0	665.5	668.9	672.7	676.2
12.5°	633.6	630.9	630.4	631.1	630.4	630.9	633.6	638.3	647.3	647.2	647.9
15°	596.0	594.7	590.8	591.9	590.8	594.7	596.0	600.6	604.8	609.9	615.1
17.5°	559.0	557.3	552.7	556.8	552.7	557.3	559.0	561.4	566.8	574.2	581.9
20°	535.7	532.9	530.5	530.1	530.5	532.9	535.7	538.1	544.0	550.3	556.2
22.5°	513.4	511.0	510.8	508.5	510.8	511.0	513.4	517.3	523.2	526.6	532.3
25°	485.7	483.3	482.6	480.9	482.6	483.3	485.7	488.5	492.3	495.1	501.3
27.5°	464.4	463.2	462.0	462.5	462.0	463.2	464.4	464.8	466.5	470.2	473.8
30°	451.4	451.0	450.3	450.3	450.3	451.0	451.4	450.3	452.1	453.8	456.6
32.5°	440.6	440.5	440.9	440.9	440.9	440.5	440.6	439.0	439.6	440.2	441.6
35°	425.3	426.4	427.1	426.1	427.1	426.4	425.3	424.0	422.9	420.5	421.2
37.5°	411.6	412.7	413.7	414.8	413.7	412.7	411.6	408.8	406.3	404.1	401.6
40°	401.1	403.5	404.2	405.9	404.2	403.5	401.1	398.0	395.2	392.7	389.9
42.5°	391.1	393.8	395.6	395.9	395.6	393.8	391.1	388.0	383.8	380.8	376.9
45°	375.8	378.5	380.9	380.9	380.9	378.5	375.8	370.5	366.0	361.5	357.7
47.5°	359.9	363.9	366.3	366.9	366.3	363.9	359.9	354.5	348.2	342.7	337.2
50°	349.0	353.9	356.3	358.0	356.3	353.9	349.0	343.1	336.5	329.6	323.0
52.5°	338.5	343.3	346.6	347.5	346.6	343.3	338.5	331.2	323.2	315.8	310.0
55°	320.2	327.2	331.0	332.3	331.0	327.2	320.2	312.3	304.6	295.2	287.0
57.5°	303.0	309.4	313.9	314.9	313.9	309.4	303.0	293.6	283.8	273.8	264.9
60°	289.7	296.7	302.2	303.3	302.2	296.7	289.7	280.4	269.9	260.2	249.1
62.5°	276.1	283.3	288.3	291.1	288.3	283.3	276.1	266.2	254.9	244.2	233.0
65°	252.6	259.8	264.7	265.7	264.7	259.8	252.6	242.9	231.0	219.6	210.3
67.5°	226.9	234.2	237.4	239.4	237.4	234.2	226.9	217.8	206.1	194.2	183.6
70°	208.8	214.7	218.2	220.0	218.2	214.7	208.8	199.1	189.4	177.3	165.9
72.5°	188.3	194.5	198.5	198.9	198.5	194.5	188.3	180.0	169.7	158.5	148.4
75°	156.9	162.4	164.4	164.4	164.4	162.4	156.9	148.8	140.5	131.5	121.5
77.5°	124.1	127.0	129.7	130.2	129.7	127.0	124.1	118.4	111.6	102.5	95.0
80°	103.1	104.8	106.8	106.8	106.8	104.8	103.1	97.8	91.2	83.6	77.8
82.5°	81.4	82.8	84.9	84.6	84.9	82.8	81.4	77.3	71.8	66.7	61.3
85°	49.2	52.4	52.1	51.4	52.1	52.4	49.2	49.9	44.8	41.3	36.5
87.5°	24.0	24.3	25.1	25.8	25.1	24.3	24.0	23.2	20.6	19.1	17.9
90°	9.0	9.2	9.3	9.5	9.3	9.2	9.0	8.9	8.6	8.2	7.8
92.5°	13.7	13.8	13.9	14.0	13.9	13.8	13.7	13.6	13.5	13.2	13.0
95°	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.8	24.6	24.3
97.5°	39.0	39.0	39.0	39.0	39.0	39.0	39.0	39.0	38.9	38.6	38.3
100°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.8	48.6	48.5
102.5°	59.7	59.8	59.8	59.9	59.8	59.8	59.7	59.7	59.6	59.4	59.2
105°	76.2	76.5	76.7	76.9	76.7	76.5	76.2	76.1	75.8	75.6	75.4
107.5°	93.5	93.5	93.5	93.4	93.5	93.5	93.5	93.5	93.4	93.2	93.0
110°	104.6	104.9	105.0	105.2	105.0	104.9	104.6	104.4	104.3	104.5	104.7



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	117.3	117.3	117.3	117.3	117.3	117.3	117.3	117.2	117.2	117.2	117.3
115°	136.3	136.3	136.2	136.2	136.2	136.3	136.3	136.4	136.4	136.5	136.6
117.5°	154.4	154.3	154.2	154.0	154.2	154.3	154.4	154.6	154.8	155.0	155.2
120°	167.2	167.4	167.5	167.6	167.5	167.4	167.2	167.1	167.2	167.6	167.9
122.5°	179.8	179.5	179.2	179.0	179.2	179.5	179.8	179.9	180.2	180.5	180.7
125°	198.9	198.8	198.7	198.5	198.7	198.8	198.9	199.0	199.2	199.4	199.5
127.5°	217.0	216.9	216.7	216.6	216.7	216.9	217.0	217.0	217.1	217.3	217.5
130°	229.3	229.0	228.7	228.5	228.7	229.0	229.3	229.5	229.8	229.9	230.1
132.5°	241.4	241.3	241.2	241.0	241.2	241.3	241.4	241.5	241.7	241.7	241.9
135°	259.0	258.8	258.6	258.4	258.6	258.8	259.0	259.2	259.4	259.6	259.7
137.5°	276.4	276.5	276.5	276.6	276.5	276.5	276.4	276.4	276.5	276.7	276.9
140°	287.9	287.8	287.8	287.7	287.8	287.8	287.9	287.9	288.0	288.1	288.2
142.5°	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.9	298.9
145°	314.5	314.2	314.1	313.9	314.1	314.2	314.5	314.7	314.9	314.9	315.0
147.5°	329.3	329.2	329.1	329.1	329.1	329.2	329.3	329.4	329.4	329.5	329.6
150°	338.7	338.6	338.5	338.4	338.5	338.6	338.7	338.7	338.8	338.8	338.8
152.5°	347.5	347.3	347.1	347.0	347.1	347.3	347.5	347.7	347.8	347.6	347.4
155°	359.7	359.4	359.2	358.9	359.2	359.4	359.7	360.0	360.0	359.7	359.4
157.5°	370.2	370.1	369.8	369.5	369.8	370.1	370.2	370.5	370.5	370.3	370.1
160°	376.7	376.3	375.9	375.6	375.9	376.3	376.7	377.0	377.1	376.8	376.7
162.5°	383.0	382.6	382.3	381.9	382.3	382.6	383.0	383.3	383.3	382.9	382.5
165°	390.9	390.7	390.4	390.1	390.4	390.7	390.9	391.2	391.1	390.7	390.3
167.5°	397.3	396.8	396.4	395.9	396.4	396.8	397.3	397.7	397.7	397.3	396.9
170°	400.7	400.2	399.8	399.2	399.8	400.2	400.7	401.2	401.3	400.8	400.4
172.5°	403.5	403.0	402.5	402.0	402.5	403.0	403.5	403.9	403.9	403.5	403.1
175°	406.4	405.9	405.4	404.9	405.4	405.9	406.4	406.9	406.9	406.4	405.9
177.5°	407.8	407.3	406.9	406.4	406.9	407.3	407.8	408.2	408.2	407.9	407.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	800.6	801.7	806.2	810.3	815.3	818.9	821.4	824.2	830.0	834.7	839.2
5°	750.1	751.8	760.9	767.1	777.8	787.2	794.5	802.5	811.9	824.7	836.5
7.5°	705.6	712.1	721.9	732.1	743.1	755.3	766.0	778.0	794.2	811.8	830.0
10°	680.4	687.7	698.0	709.9	720.2	734.5	747.7	761.9	780.2	801.8	823.3
12.5°	655.1	667.1	675.0	689.0	700.3	712.0	726.0	744.7	766.2	788.7	814.7
15°	623.5	630.1	645.3	653.0	668.9	687.0	700.8	719.6	740.4	770.3	799.3
17.5°	586.9	595.7	607.8	622.3	640.7	654.8	672.1	691.3	717.6	747.2	783.7
20°	563.1	570.4	585.3	601.3	620.7	635.6	654.0	672.7	699.8	731.4	769.5
22.5°	541.7	548.8	564.5	579.3	598.2	616.4	635.7	657.5	683.4	716.7	755.6
25°	508.6	518.0	531.9	547.2	565.2	586.0	606.8	626.2	654.0	689.0	730.7
27.5°	479.3	486.8	496.9	514.2	534.7	554.7	575.4	599.9	626.5	663.6	706.8
30°	460.4	467.3	477.4	493.4	512.5	534.0	555.4	579.1	606.8	643.5	687.7
32.5°	445.4	450.7	459.7	473.9	491.3	514.0	535.2	559.6	588.8	625.0	668.0
35°	423.3	427.8	431.2	444.8	460.4	481.3	502.7	528.8	556.9	591.2	634.2
37.5°	401.5	403.1	408.1	417.1	432.1	451.3	471.3	496.9	525.7	560.6	599.4
40°	388.3	389.0	392.1	400.4	413.6	431.6	451.0	476.4	503.7	536.7	575.2
42.5°	375.2	374.8	377.6	383.4	395.8	412.1	431.3	454.4	481.9	512.3	548.6
45°	354.5	354.5	353.9	358.7	368.8	384.8	400.7	422.9	445.9	475.6	506.2
47.5°	333.1	331.1	331.7	334.2	342.7	355.8	371.9	390.1	410.3	435.6	462.4
50°	319.2	316.4	315.4	318.2	325.7	337.2	352.5	368.5	387.5	409.7	432.7
52.5°	303.9	301.1	299.3	301.2	308.3	318.9	332.8	346.8	363.9	382.0	401.8
55°	280.4	277.2	276.2	276.9	282.0	290.4	302.2	315.0	327.9	342.8	356.7
57.5°	257.1	252.0	251.0	250.7	254.2	261.9	271.7	282.9	292.2	301.2	316.0
60°	241.8	235.6	233.5	233.2	235.9	242.2	251.2	262.3	268.9	275.1	287.9
62.5°	225.4	219.5	214.9	215.3	217.8	223.8	231.8	239.8	244.2	251.0	259.7
65°	200.2	192.5	189.0	188.1	189.4	194.3	200.5	205.7	210.6	213.4	221.7
67.5°	175.0	168.5	163.5	162.2	161.6	164.9	170.0	173.2	176.6	179.1	184.0
70°	157.2	151.6	145.3	143.3	142.9	145.7	150.6	151.0	155.8	156.9	162.0
72.5°	139.6	132.8	128.4	126.4	124.9	127.4	130.6	131.5	134.1	136.0	138.8
75°	112.4	107.2	103.1	100.0	98.9	100.2	100.2	102.0	103.7	104.8	107.9
77.5°	88.5	82.5	77.6	75.8	74.5	73.7	74.4	75.4	74.6	76.4	77.1
80°	71.8	65.5	61.8	61.1	58.9	57.2	56.9	58.0	56.5	57.2	59.3
82.5°	55.5	51.5	47.3	46.6	44.0	43.1	42.7	42.1	42.1	42.0	42.4
85°	33.0	30.5	27.7	26.0	25.0	23.3	23.3	22.6	21.8	21.1	21.5
87.5°	14.8	14.2	12.7	11.7	11.1	9.8	9.7	8.7	8.3	7.8	7.4
90°	7.3	7.0	6.3	5.8	5.3	4.7	4.0	3.3	2.5	1.7	1.0
92.5°	12.8	12.5	12.1	11.7	11.3	10.9	10.3	9.4	8.5	7.7	6.8
95°	24.2	24.0	23.5	23.0	22.5	22.0	21.4	20.8	20.2	19.5	18.9
97.5°	38.2	37.9	37.3	36.7	36.1	35.6	35.0	34.5	34.1	33.5	33.0
100°	48.3	48.2	47.6	47.0	46.3	45.7	45.2	44.9	44.7	44.4	44.1
102.5°	59.0	58.8	58.2	57.7	57.1	56.5	56.2	56.1	55.9	55.8	55.7
105°	75.2	75.0	74.7	74.5	74.2	73.8	73.7	73.7	73.6	73.5	73.4
107.5°	92.7	92.6	92.6	92.5	92.5	92.4	92.4	92.3	92.2	92.1	92.0
110°	104.8	105.0	105.0	105.0	105.1	105.2	105.1	105.0	104.9	104.8	104.6



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	117.3	117.3	117.4	117.5	117.6	117.8	117.8	117.8	117.8	117.7	117.7
115°	136.7	136.8	136.9	137.1	137.1	137.3	137.4	137.4	137.4	137.4	137.4
117.5°	155.5	155.7	155.8	156.0	156.0	156.1	156.1	156.0	156.0	156.0	155.9
120°	168.3	168.6	168.8	169.0	169.2	169.4	169.4	169.1	168.8	168.5	168.3
122.5°	180.9	181.2	181.3	181.4	181.5	181.6	181.6	181.5	181.4	181.2	181.1
125°	199.7	199.7	199.8	199.9	200.0	200.0	200.1	200.1	200.1	200.1	200.1
127.5°	217.6	217.8	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.5	217.3
130°	230.2	230.3	230.3	230.3	230.3	230.3	230.2	230.1	229.8	229.6	229.4
132.5°	242.0	242.2	242.3	242.3	242.4	242.4	242.4	242.2	242.0	241.9	241.7
135°	259.8	259.9	259.9	259.9	259.9	259.9	259.8	259.3	258.9	258.5	258.1
137.5°	277.1	277.2	277.1	277.0	276.9	276.8	276.6	276.4	276.3	276.1	275.8
140°	288.3	288.3	288.3	288.3	288.3	288.3	288.3	288.1	287.9	287.8	287.7
142.5°	298.9	298.9	299.0	299.0	299.1	299.2	299.1	298.9	298.8	298.6	298.5
145°	315.0	315.1	315.0	315.0	314.9	314.9	314.7	314.3	314.1	313.8	313.5
147.5°	329.6	329.7	329.8	329.8	329.8	329.8	329.8	329.4	329.0	328.8	328.4
150°	338.8	338.8	338.8	338.8	338.8	338.8	338.6	338.3	338.0	337.8	337.5
152.5°	347.2	347.1	347.0	347.0	346.9	346.8	346.7	346.5	346.3	346.3	346.1
155°	359.2	358.9	359.0	359.0	359.1	359.2	359.2	359.2	359.2	359.2	359.2
157.5°	369.9	369.7	369.7	369.7	369.7	369.7	369.8	370.0	370.1	370.1	370.3
160°	376.5	376.2	376.3	376.4	376.5	376.5	376.6	376.7	376.7	376.7	376.8
162.5°	382.2	381.7	381.8	381.9	382.0	382.1	382.2	382.4	382.5	382.7	382.9
165°	389.9	389.5	389.6	389.8	389.9	390.0	390.2	390.4	390.7	390.8	391.0
167.5°	396.5	396.0	396.0	396.0	396.0	395.9	396.1	396.4	396.7	397.0	397.3
170°	399.9	399.6	399.5	399.4	399.3	399.3	399.4	399.8	400.1	400.5	400.8
172.5°	402.5	402.1	402.1	402.1	402.0	402.0	402.2	402.4	402.7	403.1	403.3
175°	405.4	404.9	405.0	405.0	405.1	405.2	405.4	405.7	406.1	406.4	406.8
177.5°	407.1	406.7	406.7	406.7	406.7	406.7	406.8	407.1	407.3	407.7	408.0
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	843.1	845.9	849.4	855.6	857.8	860.6	864.4	864.2	865.3	869.4	878.3
5°	846.2	856.9	867.4	879.9	893.0	901.7	913.6	920.8	928.1	937.5	953.4
7.5°	847.5	864.5	883.6	905.5	925.1	947.5	965.1	981.6	996.5	1016.3	1035.3
10°	845.5	868.4	893.0	920.8	950.3	975.3	997.8	1023.5	1045.4	1069.3	1090.8
12.5°	841.9	869.5	902.5	933.5	968.0	1005.0	1033.0	1059.0	1088.1	1115.6	1148.8
15°	833.7	871.6	910.1	951.0	997.1	1039.8	1080.4	1114.0	1145.3	1186.6	1229.9
17.5°	823.3	864.1	912.7	962.2	1010.5	1059.3	1109.5	1160.0	1199.4	1250.7	1284.7
20°	813.6	860.8	910.7	969.7	1018.0	1078.7	1128.6	1177.5	1231.6	1282.6	1323.3
22.5°	800.0	851.6	904.6	963.3	1026.8	1087.5	1145.3	1198.4	1252.5	1308.0	1357.1
25°	782.7	829.6	892.3	958.9	1022.1	1088.1	1154.3	1220.9	1279.2	1337.8	1383.7
27.5°	753.3	812.4	870.9	939.7	1009.9	1084.4	1155.3	1225.0	1286.0	1334.3	1362.7
30°	738.3	789.6	853.2	922.2	998.2	1078.3	1152.2	1220.6	1277.5	1316.0	1327.4
32.5°	716.1	769.1	831.3	902.8	983.2	1065.5	1142.5	1206.9	1254.5	1274.6	1260.8
35°	683.1	731.0	793.8	867.0	950.7	1038.4	1114.4	1168.9	1193.2	1174.1	1126.5
37.5°	643.5	691.1	754.1	826.0	912.6	1001.7	1070.5	1109.6	1101.6	1054.2	983.3
40°	615.8	660.2	720.2	798.0	882.3	971.8	1032.2	1053.4	1031.2	963.1	887.9
42.5°	585.1	628.3	688.6	763.6	852.8	935.4	988.0	989.8	952.6	871.3	795.7
45°	538.1	579.4	636.3	714.3	796.9	874.7	909.4	892.3	823.7	745.2	669.2
47.5°	491.9	527.6	583.7	657.8	736.2	801.6	818.9	788.3	715.1	638.9	568.5
50°	458.0	494.1	546.8	617.6	693.2	749.8	758.0	717.5	645.7	569.0	513.8
52.5°	425.5	461.3	512.1	577.6	646.8	697.9	698.1	651.1	579.6	511.3	459.9
55°	377.8	410.1	455.9	514.5	576.3	616.2	606.5	557.9	495.8	436.5	391.7
57.5°	331.9	360.0	402.2	451.1	505.5	538.4	522.3	475.5	420.1	369.8	335.8
60°	302.2	328.9	365.0	411.2	456.9	482.6	467.3	425.0	374.0	333.4	303.9
62.5°	273.3	295.9	330.6	370.6	413.0	432.1	418.5	376.7	332.7	296.0	272.0
65°	232.5	250.8	278.6	313.0	343.8	360.2	348.7	309.8	276.2	249.8	230.7
67.5°	194.3	208.7	229.7	257.3	283.5	292.3	281.9	254.8	226.3	205.2	191.7
70°	167.9	181.5	199.1	220.3	243.2	252.6	242.2	220.7	197.4	178.0	164.8
72.5°	144.9	155.3	170.3	188.4	206.3	215.7	208.6	187.9	168.3	153.8	142.6
75°	110.3	119.3	129.7	142.6	156.5	162.7	156.5	142.2	128.7	118.0	109.9
77.5°	80.3	85.1	93.1	102.7	111.4	116.2	110.8	101.1	92.8	85.5	81.5
80°	61.1	64.6	70.1	77.8	83.6	88.1	84.6	76.7	70.1	65.2	63.5
82.5°	44.4	46.7	50.4	56.1	60.0	62.3	60.8	55.0	52.3	48.0	46.3
85°	21.8	23.3	25.7	27.4	30.9	31.2	31.6	29.2	26.8	25.7	24.3
87.5°	7.8	8.3	9.3	10.3	11.5	11.9	11.7	11.9	10.8	10.6	9.6
90°	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3	7.8
92.5°	7.7	8.5	9.4	10.3	10.9	11.3	11.7	12.1	12.5	12.8	13.0
95°	19.5	20.2	20.8	21.4	22.0	22.5	23.0	23.5	24.0	24.2	24.3
97.5°	33.5	34.1	34.5	35.0	35.6	36.1	36.7	37.3	37.9	38.2	38.3
100°	44.4	44.7	44.9	45.2	45.7	46.3	47.0	47.6	48.2	48.3	48.5
102.5°	55.8	55.9	56.1	56.2	56.5	57.1	57.7	58.2	58.8	59.0	59.2
105°	73.5	73.6	73.7	73.7	73.8	74.2	74.5	74.7	75.0	75.2	75.4
107.5°	92.1	92.2	92.3	92.4	92.4	92.5	92.5	92.6	92.6	92.7	93.0
110°	104.8	104.9	105.0	105.1	105.2	105.1	105.0	105.0	105.0	104.8	104.7





TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	117.7	117.8	117.8	117.8	117.8	117.6	117.5	117.4	117.3	117.3	117.3
115°	137.4	137.4	137.4	137.4	137.3	137.1	137.1	136.9	136.8	136.7	136.6
117.5°	156.0	156.0	156.0	156.1	156.1	156.0	156.0	155.8	155.7	155.5	155.2
120°	168.5	168.8	169.1	169.4	169.4	169.2	169.0	168.8	168.6	168.3	167.9
122.5°	181.2	181.4	181.5	181.6	181.6	181.5	181.4	181.3	181.2	180.9	180.7
125°	200.1	200.1	200.1	200.1	200.0	200.0	199.9	199.8	199.7	199.7	199.5
127.5°	217.5	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.8	217.6	217.5
130°	229.6	229.8	230.1	230.2	230.3	230.3	230.3	230.3	230.3	230.2	230.1
132.5°	241.9	242.0	242.2	242.4	242.4	242.4	242.3	242.3	242.2	242.0	241.9
135°	258.5	258.9	259.3	259.8	259.9	259.9	259.9	259.9	259.9	259.8	259.7
137.5°	276.1	276.3	276.4	276.6	276.8	276.9	277.0	277.1	277.2	277.1	276.9
140°	287.8	287.9	288.1	288.3	288.3	288.3	288.3	288.3	288.3	288.3	288.2
142.5°	298.6	298.8	298.9	299.1	299.2	299.1	299.0	299.0	298.9	298.9	298.9
145°	313.8	314.1	314.3	314.7	314.9	314.9	315.0	315.0	315.1	315.0	315.0
147.5°	328.8	329.0	329.4	329.8	329.8	329.8	329.8	329.8	329.7	329.6	329.6
150°	337.8	338.0	338.3	338.6	338.8	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	346.3	346.3	346.5	346.7	346.8	346.9	347.0	347.0	347.1	347.2	347.4
155°	359.2	359.2	359.2	359.2	359.2	359.1	359.0	359.0	358.9	359.2	359.4
157.5°	370.1	370.1	370.0	369.8	369.7	369.7	369.7	369.7	369.7	369.9	370.1
160°	376.7	376.7	376.7	376.6	376.5	376.5	376.4	376.3	376.2	376.5	376.7
162.5°	382.7	382.5	382.4	382.2	382.1	382.0	381.9	381.8	381.7	382.2	382.5
165°	390.8	390.7	390.4	390.2	390.0	389.9	389.8	389.6	389.5	389.9	390.3
167.5°	397.0	396.7	396.4	396.1	395.9	396.0	396.0	396.0	396.0	396.5	396.9
170°	400.5	400.1	399.8	399.4	399.3	399.3	399.4	399.5	399.6	399.9	400.4
172.5°	403.1	402.7	402.4	402.2	402.0	402.0	402.1	402.1	402.1	402.5	403.1
175°	406.4	406.1	405.7	405.4	405.2	405.1	405.0	405.0	404.9	405.4	405.9
177.5°	407.7	407.3	407.1	406.8	406.7	406.7	406.7	406.7	406.7	407.1	407.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	837.5	837.5	837.5	837.5	837.5	837.5	837.5
2.5°	882.8	883.3	885.8	887.8	888.3	891.1	891.4
5°	960.4	966.3	977.7	978.7	980.4	989.5	982.6
7.5°	1051.2	1066.2	1076.2	1085.0	1088.2	1092.2	1091.4
10°	1109.6	1131.8	1142.8	1160.6	1161.3	1165.7	1163.0
12.5°	1168.1	1193.9	1214.2	1217.5	1232.3	1234.6	1238.5
15°	1251.1	1278.5	1306.6	1316.7	1337.1	1342.0	1349.6
17.5°	1329.1	1357.1	1376.8	1402.8	1411.2	1422.5	1414.9
20°	1371.8	1402.4	1427.4	1447.8	1456.5	1462.8	1462.0
22.5°	1397.7	1428.4	1448.7	1464.2	1472.3	1475.0	1474.8
25°	1413.8	1431.6	1437.8	1443.7	1434.7	1431.6	1432.9
27.5°	1368.9	1364.2	1348.0	1326.6	1304.4	1286.7	1277.2
30°	1307.0	1279.9	1255.3	1212.3	1190.0	1176.9	1165.0
32.5°	1219.2	1176.3	1129.0	1089.6	1064.3	1044.7	1041.8
35°	1069.0	1004.4	946.5	898.2	873.3	852.1	847.2
37.5°	908.8	841.8	789.6	747.1	720.2	705.3	691.4
40°	802.5	744.9	693.6	657.5	637.0	626.2	617.6
42.5°	720.6	668.0	617.0	589.4	571.0	564.4	559.3
45°	607.5	558.6	523.2	502.4	491.6	480.5	475.3
47.5°	516.9	477.2	453.8	436.1	424.6	418.0	414.6
50°	465.6	433.0	412.1	398.7	388.3	383.0	380.2
52.5°	420.1	393.3	375.9	365.1	358.0	354.2	353.0
55°	361.9	341.4	330.3	320.9	315.8	312.3	310.9
57.5°	314.5	298.8	289.8	282.0	280.1	277.1	276.2
60°	283.5	271.3	263.7	258.5	256.7	253.2	254.0
62.5°	256.0	246.0	239.5	236.6	234.3	231.3	232.3
65°	216.5	209.2	205.7	203.0	200.2	198.5	199.8
67.5°	181.6	176.6	171.9	170.3	169.0	168.7	167.2
70°	158.9	154.7	150.6	149.5	149.5	148.1	147.8
72.5°	137.0	133.9	131.2	130.4	129.3	129.8	128.4
75°	105.8	103.3	102.4	101.3	100.9	100.9	100.0
77.5°	78.2	76.4	74.7	74.7	73.5	73.0	72.9
80°	59.3	58.7	57.2	57.2	56.5	56.9	56.2
82.5°	44.6	43.6	43.3	42.8	41.8	41.9	41.2
85°	23.9	22.9	22.6	21.5	20.8	21.5	20.8
87.5°	10.0	9.8	9.5	9.0	8.7	8.8	8.0
90°	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	13.2	13.5	13.6	13.7	13.8	13.9	14.0
95°	24.6	24.8	24.9	24.9	24.9	24.9	24.9
97.5°	38.6	38.9	39.0	39.0	39.0	39.0	39.0
100°	48.6	48.8	48.9	48.9	48.9	48.9	48.9
102.5°	59.4	59.6	59.7	59.7	59.8	59.8	59.9
105°	75.6	75.8	76.1	76.2	76.5	76.7	76.9
107.5°	93.2	93.4	93.5	93.5	93.5	93.5	93.4
110°	104.5	104.3	104.4	104.6	104.9	105.0	105.2



TEST NUMBER: P332536-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	117.2	117.2	117.2	117.3	117.3	117.3	117.3
115°	136.5	136.4	136.4	136.3	136.3	136.2	136.2
117.5°	155.0	154.8	154.6	154.4	154.3	154.2	154.0
120°	167.6	167.2	167.1	167.2	167.4	167.5	167.6
122.5°	180.5	180.2	179.9	179.8	179.5	179.2	179.0
125°	199.4	199.2	199.0	198.9	198.8	198.7	198.5
127.5°	217.3	217.1	217.0	217.0	216.9	216.7	216.6
130°	229.9	229.8	229.5	229.3	229.0	228.7	228.5
132.5°	241.7	241.7	241.5	241.4	241.3	241.2	241.0
135°	259.6	259.4	259.2	259.0	258.8	258.6	258.4
137.5°	276.7	276.5	276.4	276.4	276.5	276.5	276.6
140°	288.1	288.0	287.9	287.9	287.8	287.8	287.7
142.5°	298.9	298.8	298.8	298.8	298.8	298.8	298.8
145°	314.9	314.9	314.7	314.5	314.2	314.1	313.9
147.5°	329.5	329.4	329.4	329.3	329.2	329.1	329.1
150°	338.8	338.8	338.7	338.7	338.6	338.5	338.4
152.5°	347.6	347.8	347.7	347.5	347.3	347.1	347.0
155°	359.7	360.0	360.0	359.7	359.4	359.2	358.9
157.5°	370.3	370.5	370.5	370.2	370.1	369.8	369.5
160°	376.8	377.1	377.0	376.7	376.3	375.9	375.6
162.5°	382.9	383.3	383.3	383.0	382.6	382.3	381.9
165°	390.7	391.1	391.2	390.9	390.7	390.4	390.1
167.5°	397.3	397.7	397.7	397.3	396.8	396.4	395.9
170°	400.8	401.3	401.2	400.7	400.2	399.8	399.2
172.5°	403.5	403.9	403.9	403.5	403.0	402.5	402.0
175°	406.4	406.9	406.9	406.4	405.9	405.4	404.9
177.5°	407.9	408.2	408.2	407.8	407.3	406.9	406.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4

(END OF REPORT)