

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332989-940

Luminaire Tested: **S124RDIP-S1195D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332989-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D365U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5428.1 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	105	100	97	93	100	96	93	90	88	85	83	81	79	77	74	72	71	68
2	96	88	82	77	91	85	79	74	78	73	69	71	68	65	66	63	60	57
3	88	78	70	64	84	75	68	63	69	63	59	64	59	55	59	55	52	49
4	80	69	61	55	77	67	59	54	62	56	51	57	52	48	53	48	45	42
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	48	43	40	37
6	69	56	48	42	65	54	46	41	50	44	39	47	41	37	43	39	35	33
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	3.2
10°-20°	487.1	9.0
20°-30°	703.4	13.0
30°-40°	797.3	14.7
40°-50°	770.0	14.2
50°-60°	640.3	11.8
60°-70°	442.1	8.1
70°-80°	224.1	4.1
80°-90°	58.7	1.1
90°-100°	26.9	0.5
100°-110°	79.6	1.5
110°-120°	135.1	2.5
120°-130°	178.2	3.3
130°-140°	200.1	3.7
140°-150°	196.6	3.6
150°-160°	165.4	3.0
160°-170°	110.0	2.0
170°-180°	38.5	0.7
0°-30°	1365.2	25.2
0°-40°	2162.6	39.8
0°-60°	3572.8	65.8
0°-90°	4297.7	79.2
90°-120°	241.6	4.5
90°-150°	816.5	15.0
90°-180°	1130.0	20.8
0°-180°	5428.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	86
90°	1	4	7	9	10	5
95°	19	22	24	25	25	21
105°	73	74	75	76	77	78
115°	137	137	137	136	136	135
125°	200	200	200	199	198	178
135°	258	260	260	259	258	200
145°	314	315	315	315	314	196
155°	359	359	359	360	359	165
165°	391	390	390	391	390	110
175°	407	405	405	407	405	39
180°	407	407	407	407	407	



TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.4	24.5	22.6	20.8	18.9	17.9	17.7	17.7	17.5	17.3	17.1
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	6.8	7.7	8.5	9.4	10.3	10.9	11.3	11.7	12.1	12.5	12.8
95°	18.9	19.5	20.2	20.8	21.4	22.0	22.5	23.0	23.5	24.0	24.2
97.5°	33.0	33.5	34.1	34.5	35.0	35.6	36.1	36.7	37.3	37.9	38.2
100°	44.1	44.4	44.7	44.9	45.2	45.7	46.3	47.0	47.6	48.2	48.3
102.5°	55.7	55.8	55.9	56.1	56.2	56.5	57.1	57.7	58.2	58.8	59.0
105°	73.4	73.5	73.6	73.7	73.7	73.8	74.2	74.5	74.7	75.0	75.2
107.5°	92.0	92.1	92.2	92.3	92.4	92.4	92.5	92.5	92.6	92.6	92.7
110°	104.6	104.8	104.9	105.0	105.1	105.2	105.1	105.0	105.0	105.0	104.8



TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	117.7	117.7	117.8	117.8	117.8	117.8	117.6	117.5	117.4	117.3	117.3
115°	137.4	137.4	137.4	137.4	137.4	137.3	137.1	137.1	136.9	136.8	136.7
117.5°	155.9	156.0	156.0	156.0	156.1	156.1	156.0	156.0	155.8	155.7	155.5
120°	168.3	168.5	168.8	169.1	169.4	169.4	169.2	169.0	168.8	168.6	168.3
122.5°	181.1	181.2	181.4	181.5	181.6	181.6	181.5	181.4	181.3	181.2	180.9
125°	200.1	200.1	200.1	200.1	200.1	200.0	200.0	199.9	199.8	199.7	199.7
127.5°	217.3	217.5	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.8	217.6
130°	229.4	229.6	229.8	230.1	230.2	230.3	230.3	230.3	230.3	230.3	230.2
132.5°	241.7	241.9	242.0	242.2	242.4	242.4	242.4	242.3	242.3	242.2	242.0
135°	258.1	258.5	258.9	259.3	259.8	259.9	259.9	259.9	259.9	259.9	259.8
137.5°	275.8	276.1	276.3	276.4	276.6	276.8	276.9	277.0	277.1	277.2	277.1
140°	287.7	287.8	287.9	288.1	288.3	288.3	288.3	288.3	288.3	288.3	288.3
142.5°	298.5	298.6	298.8	298.9	299.1	299.2	299.1	299.0	299.0	298.9	298.9
145°	313.5	313.8	314.1	314.3	314.7	314.9	314.9	315.0	315.0	315.1	315.0
147.5°	328.4	328.8	329.0	329.4	329.8	329.8	329.8	329.8	329.8	329.7	329.6
150°	337.5	337.8	338.0	338.3	338.6	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	346.1	346.3	346.3	346.5	346.7	346.8	346.9	347.0	347.0	347.1	347.2
155°	359.2	359.2	359.2	359.2	359.2	359.2	359.1	359.0	359.0	358.9	359.2
157.5°	370.3	370.1	370.1	370.0	369.8	369.7	369.7	369.7	369.7	369.7	369.9
160°	376.8	376.7	376.7	376.7	376.6	376.5	376.5	376.4	376.3	376.2	376.5
162.5°	382.9	382.7	382.5	382.4	382.2	382.1	382.0	381.9	381.8	381.7	382.2
165°	391.0	390.8	390.7	390.4	390.2	390.0	389.9	389.8	389.6	389.5	389.9
167.5°	397.3	397.0	396.7	396.4	396.1	395.9	396.0	396.0	396.0	396.0	396.5
170°	400.8	400.5	400.1	399.8	399.4	399.3	399.3	399.4	399.5	399.6	399.9
172.5°	403.3	403.1	402.7	402.4	402.2	402.0	402.0	402.1	402.1	402.1	402.5
175°	406.8	406.4	406.1	405.7	405.4	405.2	405.1	405.0	405.0	404.9	405.4
177.5°	408.0	407.7	407.3	407.1	406.8	406.7	406.7	406.7	406.7	406.7	407.1
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	17.0	16.9	16.7	16.7	17.0	17.3	17.6	17.8
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	13.0	13.2	13.5	13.6	13.7	13.8	13.9	14.0
95°	24.3	24.6	24.8	24.9	24.9	24.9	24.9	24.9
97.5°	38.3	38.6	38.9	39.0	39.0	39.0	39.0	39.0
100°	48.5	48.6	48.8	48.9	48.9	48.9	48.9	48.9
102.5°	59.2	59.4	59.6	59.7	59.7	59.8	59.8	59.9
105°	75.4	75.6	75.8	76.1	76.2	76.5	76.7	76.9
107.5°	93.0	93.2	93.4	93.5	93.5	93.5	93.5	93.4
110°	104.7	104.5	104.3	104.4	104.6	104.9	105.0	105.2



TEST NUMBER: P332989-940

CATALOG NUMBER: S124RDIP-S1195D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	117.3	117.2	117.2	117.2	117.3	117.3	117.3	117.3
115°	136.6	136.5	136.4	136.4	136.3	136.3	136.2	136.2
117.5°	155.2	155.0	154.8	154.6	154.4	154.3	154.2	154.0
120°	167.9	167.6	167.2	167.1	167.2	167.4	167.5	167.6
122.5°	180.7	180.5	180.2	179.9	179.8	179.5	179.2	179.0
125°	199.5	199.4	199.2	199.0	198.9	198.8	198.7	198.5
127.5°	217.5	217.3	217.1	217.0	217.0	216.9	216.7	216.6
130°	230.1	229.9	229.8	229.5	229.3	229.0	228.7	228.5
132.5°	241.9	241.7	241.7	241.5	241.4	241.3	241.2	241.0
135°	259.7	259.6	259.4	259.2	259.0	258.8	258.6	258.4
137.5°	276.9	276.7	276.5	276.4	276.4	276.5	276.5	276.6
140°	288.2	288.1	288.0	287.9	287.9	287.8	287.8	287.7
142.5°	298.9	298.9	298.8	298.8	298.8	298.8	298.8	298.8
145°	315.0	314.9	314.9	314.7	314.5	314.2	314.1	313.9
147.5°	329.6	329.5	329.4	329.4	329.3	329.2	329.1	329.1
150°	338.8	338.8	338.8	338.7	338.7	338.6	338.5	338.4
152.5°	347.4	347.6	347.8	347.7	347.5	347.3	347.1	347.0
155°	359.4	359.7	360.0	360.0	359.7	359.4	359.2	358.9
157.5°	370.1	370.3	370.5	370.5	370.2	370.1	369.8	369.5
160°	376.7	376.8	377.1	377.0	376.7	376.3	375.9	375.6
162.5°	382.5	382.9	383.3	383.3	383.0	382.6	382.3	381.9
165°	390.3	390.7	391.1	391.2	390.9	390.7	390.4	390.1
167.5°	396.9	397.3	397.7	397.7	397.3	396.8	396.4	395.9
170°	400.4	400.8	401.3	401.2	400.7	400.2	399.8	399.2
172.5°	403.1	403.5	403.9	403.9	403.5	403.0	402.5	402.0
175°	405.9	406.4	406.9	406.9	406.4	405.9	405.4	404.9
177.5°	407.4	407.9	408.2	408.2	407.8	407.3	406.9	406.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4

(END OF REPORT)