

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332915-940

Luminaire Tested: **S124RDIP-S575D1035U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332915-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D1035U940-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5474.7 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34
2	88	81	75	70	80	74	69	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	55	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	26	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	35	28	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6952	6952	6952	6952
5°	8064	6972	6163	6972
10°	9539	6942	5501	6942
15°	11019	6878	4726	6878
20°	12269	6790	4274	6790
25°	12665	6703	3968	6703
30°	11087	6598	3784	6598
35°	8630	6441	3672	6441
40°	6472	6263	3613	6263
45°	5109	5977	3580	5977
50°	4314	5647	3478	5647
55°	3761	5284	3291	5284
60°	3384	4907	2913	4907
65°	2982	4500	2506	4500
70°	2686	4079	2261	4079
75°	2249	3615	1928	3615
80°	1901	3082	1808	3082
85°	1612	2408	1612	2408



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.4	1.5
10°-20°	251.7	4.6
20°-30°	393.7	7.2
30°-40°	437.6	8.0
40°-50°	388.3	7.1
50°-60°	302.5	5.5
60°-70°	198.1	3.6
70°-80°	97.4	1.8
80°-90°	26.5	0.5
90°-100°	327.3	6.0
100°-110°	681.1	12.4
110°-120°	610.1	11.1
120°-130°	513.2	9.4
130°-140°	427.9	7.8
140°-150°	326.9	6.0
150°-160°	229.8	4.2
160°-170°	135.2	2.5
170°-180°	44.0	0.8
0°-30°	728.8	13.3
0°-40°	1166.4	21.3
0°-60°	1857.2	33.9
0°-90°	2179.2	39.8
90°-120°	1618.5	29.6
90°-150°	2886.5	52.7
90°-180°	3295.0	60.2
0°-180°	5474.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	861	861	861	861	861	
5°	995	860	760	860	995	101
15°	1318	823	566	823	1318	375
25°	1422	752	446	752	1422	631
35°	876	654	373	654	876	549
45°	448	524	314	524	448	354
55°	267	375	234	375	267	243
65°	156	236	131	236	156	157
75°	72	116	62	116	72	79
85°	17	26	17	26	17	20
90°	19	1	19	1	19	16
95°	217	29	217	29	217	337
105°	1252	104	1252	104	1252	1238
115°	1203	183	1203	183	1203	1194
125°	960	256	960	256	960	872
135°	858	304	858	304	858	662
145°	701	350	701	350	701	444
155°	587	398	587	398	587	274
165°	512	434	512	434	512	147
175°	461	452	461	452	461	45
180°	453	453	453	453	453	



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	908.3	910.8	908.3	908.0	905.3	904.5	903.3	899.7	893.0	889.1	890.0
5°	995.1	1003.7	998.9	998.2	990.5	982.9	978.0	967.0	955.1	947.2	940.6
7.5°	1095.4	1100.4	1097.3	1092.4	1080.1	1073.1	1061.8	1047.2	1026.1	1009.9	995.1
10°	1163.7	1167.8	1166.4	1157.4	1148.4	1130.0	1119.6	1099.1	1072.4	1051.2	1031.4
12.5°	1230.8	1235.3	1223.1	1223.5	1206.4	1191.9	1175.4	1149.7	1118.7	1091.5	1066.8
15°	1318.4	1312.9	1312.9	1305.9	1286.8	1266.7	1249.7	1222.6	1183.7	1151.2	1116.9
17.5°	1387.0	1388.9	1386.1	1369.7	1354.7	1333.9	1302.7	1271.1	1235.0	1191.2	1156.2
20°	1428.1	1428.1	1425.0	1413.8	1394.4	1372.2	1338.5	1304.2	1258.4	1214.3	1174.7
22.5°	1444.7	1445.8	1442.2	1433.0	1415.5	1393.8	1365.2	1330.3	1283.1	1233.5	1184.5
25°	1421.8	1428.3	1429.1	1426.6	1421.5	1408.3	1383.7	1347.9	1305.6	1251.8	1199.1
27.5°	1305.4	1313.7	1321.0	1332.9	1348.9	1357.3	1358.3	1340.2	1303.2	1251.5	1198.5
30°	1189.4	1196.2	1218.8	1248.3	1271.2	1292.0	1310.1	1314.9	1294.1	1247.6	1191.8
32.5°	1060.5	1070.0	1092.5	1124.3	1162.4	1197.7	1238.2	1258.8	1258.3	1230.4	1178.8
35°	875.7	882.6	903.5	936.7	982.6	1034.9	1099.1	1149.1	1183.1	1180.6	1149.1
37.5°	706.2	714.1	735.1	762.8	807.2	872.0	934.2	1003.0	1065.9	1101.2	1090.6
40°	614.1	614.5	634.9	663.3	705.0	761.5	829.2	905.5	975.6	1032.9	1043.9
42.5°	541.4	541.4	555.0	585.7	615.6	668.9	733.4	809.2	891.3	957.3	986.8
45°	447.5	450.7	461.8	480.2	503.7	548.8	600.6	671.0	762.9	841.3	890.3
47.5°	379.0	383.6	390.7	405.6	424.5	454.5	497.2	560.5	635.3	721.6	791.2
50°	343.5	344.2	353.2	361.5	377.8	401.8	439.3	492.0	560.7	643.5	720.9
52.5°	313.0	312.8	318.3	328.8	342.1	360.7	390.9	439.0	499.9	574.2	654.1
55°	267.2	268.9	273.0	281.3	291.4	304.6	328.6	364.6	412.5	476.0	548.5
57.5°	232.3	233.2	236.5	240.0	249.2	258.9	276.8	301.8	342.2	394.2	461.8
60°	209.6	209.9	211.0	216.2	223.5	232.5	244.6	265.7	299.8	347.3	400.7
62.5°	187.3	188.0	189.6	193.4	199.0	205.3	217.9	235.0	263.1	303.7	351.9
65°	156.1	156.5	158.9	160.3	164.8	170.3	179.7	191.2	210.6	244.6	281.1
67.5°	130.5	130.5	130.5	132.5	135.6	139.3	144.9	154.1	168.7	189.6	221.7
70°	113.8	113.8	114.5	115.6	117.3	120.4	123.5	130.5	141.2	158.2	182.8
72.5°	98.3	98.5	99.2	99.4	100.3	102.9	105.2	109.6	117.6	130.5	150.3
75°	72.1	73.2	74.9	76.3	78.0	77.8	80.2	82.9	85.3	93.0	104.4
77.5°	53.7	53.1	53.3	54.6	54.8	55.1	56.8	58.9	60.8	64.4	68.5
80°	40.9	40.9	42.0	42.4	42.0	42.4	44.1	45.1	45.8	47.2	51.0
82.5°	30.9	31.5	31.1	31.5	31.7	32.1	33.5	33.7	34.4	35.0	36.6
85°	17.4	17.7	18.0	17.4	17.4	17.4	18.0	18.4	19.1	18.7	19.4
87.5°	9.8	9.5	10.0	9.8	10.0	9.6	9.8	10.2	9.5	9.9	9.5
90°	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1	15.2	16.1	14.3
92.5°	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9	235.2	282.4	247.1
95°	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6	746.0	725.5	547.5
97.5°	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6	937.2	764.1	512.4
100°	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6	943.6	715.7	464.7
102.5°	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6	890.2	655.2	432.7
105°	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0	793.2	584.0	405.0
107.5°	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4	714.8	544.1	400.0
110°	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1	675.6	530.6	401.4



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3	653.6	524.1	405.7
115°	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2	632.9	520.8	413.9
117.5°	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1	623.7	519.9	422.7
120°	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1	618.7	519.9	429.1
122.5°	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6	613.0	519.2	435.5
125°	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0	603.6	518.1	445.1
127.5°	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2	590.9	516.1	452.7
130°	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0	583.1	515.4	458.4
132.5°	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0	576.0	514.7	463.4
135°	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3	565.3	513.6	470.9
137.5°	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7	556.0	513.4	475.4
140°	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0	551.1	512.7	478.9
142.5°	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0	546.8	512.7	481.8
145°	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9	539.5	511.0	483.4
147.5°	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3	532.9	507.7	484.3
150°	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3	527.9	505.6	484.3
152.5°	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4	522.2	502.0	482.9
155°	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7	513.6	496.8	480.7
157.5°	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0	504.9	491.2	478.4
160°	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2	498.6	487.0	476.3
162.5°	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3	492.8	482.7	474.1
165°	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5	483.4	476.3	470.0
167.5°	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0	474.8	469.8	465.7
170°	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6	469.1	465.6	462.9
172.5°	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9	464.1	461.3	460.0
175°	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2	458.4	456.6	456.6
177.5°	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2	454.5	453.8	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	887.3	883.3	881.4	876.9	871.6	868.9	866.4	862.8	858.1	853.1	849.4
5°	932.3	923.9	913.5	901.0	889.9	879.1	869.8	860.4	849.7	838.6	827.5
7.5°	978.5	962.1	944.4	923.9	904.0	885.9	869.2	853.3	835.3	819.0	804.3
10°	1010.7	988.5	963.9	937.8	911.8	889.2	867.0	846.9	824.7	804.9	788.3
12.5°	1036.8	1010.7	981.1	948.6	917.3	890.0	864.5	838.3	813.1	791.6	769.4
15°	1080.0	1044.3	1004.4	965.5	925.0	887.9	853.5	823.0	794.2	764.0	742.8
17.5°	1109.8	1067.4	1019.0	972.2	924.3	880.5	840.9	804.5	771.2	740.5	715.2
20°	1127.6	1080.8	1027.0	973.8	920.1	873.3	830.6	790.3	756.0	722.7	696.7
22.5°	1137.6	1085.7	1027.0	971.3	915.7	865.0	818.1	776.2	738.8	705.5	676.7
25°	1140.8	1085.2	1025.2	961.4	900.4	846.6	798.0	752.5	710.9	677.6	647.0
27.5°	1136.3	1070.9	1009.5	944.0	881.0	824.3	773.3	725.5	683.9	648.1	616.8
30°	1129.6	1059.6	993.6	925.7	861.8	807.4	753.6	707.8	664.4	627.3	595.8
32.5°	1115.3	1045.7	974.8	905.1	840.4	784.3	733.3	687.2	644.7	606.7	573.2
35°	1086.6	1016.2	939.1	867.7	804.2	745.9	698.0	653.6	613.1	572.5	537.1
37.5°	1048.9	977.0	900.4	822.2	758.6	703.6	659.6	618.0	578.3	541.3	502.0
40°	1013.4	947.9	868.8	791.0	725.9	672.7	632.1	594.3	554.5	517.6	478.4
42.5°	970.4	914.5	834.6	756.6	692.2	641.1	603.2	566.3	530.0	494.4	453.4
45°	898.6	856.3	781.3	706.4	641.5	590.8	556.2	523.5	491.6	457.6	419.1
47.5°	816.3	787.6	723.0	646.2	586.2	540.6	507.1	480.5	453.4	419.5	385.7
50°	759.1	740.7	678.3	608.2	551.0	509.0	474.7	449.6	427.1	394.5	364.3
52.5°	698.0	688.3	635.5	568.5	513.2	472.1	442.7	420.3	397.4	370.3	342.1
55°	605.1	610.3	565.5	507.6	455.6	420.9	394.1	375.4	356.0	333.1	311.2
57.5°	510.0	529.1	499.0	448.1	399.3	367.3	347.1	331.4	315.1	296.0	277.4
60°	453.1	469.0	452.1	407.3	364.6	334.8	316.1	303.9	287.6	270.3	256.0
62.5°	397.6	414.6	404.6	368.5	328.9	303.2	286.7	275.4	263.2	248.1	233.3
65°	327.9	338.9	334.1	309.2	281.1	259.1	243.9	235.6	224.4	213.4	200.2
67.5°	251.1	272.6	269.7	256.5	232.2	215.1	205.1	197.8	187.6	179.4	170.4
70°	206.4	226.2	225.9	215.1	201.9	185.9	179.1	172.8	163.7	155.8	148.5
72.5°	169.0	187.1	189.8	181.6	172.5	160.4	153.7	149.5	140.7	135.3	129.3
75°	118.3	131.5	135.0	135.0	130.8	124.6	118.7	115.9	109.6	104.8	101.3
77.5°	77.6	85.9	91.3	92.6	93.2	91.1	86.2	84.3	79.5	77.8	74.5
80°	54.8	60.4	66.6	68.7	70.4	69.7	67.7	66.3	61.8	60.0	58.7
82.5°	37.9	40.9	46.1	50.6	50.2	52.0	50.2	49.0	45.7	45.0	43.6
85°	19.8	20.2	20.8	23.9	25.7	26.4	26.8	26.0	25.0	25.0	22.6
87.5°	9.2	8.9	8.4	8.4	8.5	9.4	9.7	9.6	9.1	8.8	8.2
90°	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9	2.7	5.4	6.2
92.5°	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2	14.8	23.2	34.0
95°	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3	32.0	40.9	52.5
97.5°	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7	52.7	60.4	71.1
100°	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7	67.7	73.9	84.5
102.5°	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9	83.3	88.8	98.8
105°	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2	106.8	111.3	122.0
107.5°	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8	130.5	134.9	146.3
110°	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1	146.9	151.3	162.0





TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8	162.6	167.7	177.7
115°	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4	186.0	192.3	201.2
117.5°	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9	209.4	214.9	224.7
120°	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6	224.4	230.6	240.3
122.5°	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8	238.5	244.8	253.9
125°	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5	259.0	264.4	274.2
127.5°	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1	274.9	281.3	292.5
130°	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3	284.9	291.9	305.3
132.5°	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5	293.4	302.6	315.3
135°	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5	307.1	316.0	331.2
137.5°	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6	319.9	329.8	344.1
140°	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8	328.5	338.3	353.4
142.5°	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8	338.5	347.5	361.9
145°	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8	352.5	361.4	373.9
147.5°	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7	366.6	374.4	387.3
150°	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7	376.6	383.7	394.4
152.5°	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0	385.1	392.3	402.2
155°	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9	398.8	404.1	413.0
157.5°	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5	410.5	415.5	422.5
160°	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4	418.4	422.0	428.2
162.5°	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5	424.8	427.7	433.2
165°	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5	433.5	435.3	439.8
167.5°	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6	440.7	441.6	445.0
170°	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1	444.3	445.1	447.8
172.5°	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6	447.8	447.9	449.9
175°	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2	451.3	451.3	452.2
177.5°	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8	453.1	452.4	453.1
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	845.6	842.8	839.2	835.0	830.0	825.6	823.7	825.3	826.2	823.9	823.7
5°	819.8	811.2	804.2	793.8	785.5	778.6	773.6	771.6	772.3	766.8	765.4
7.5°	790.9	780.6	769.3	756.9	745.4	735.2	729.9	726.9	721.0	718.5	714.3
10°	772.3	758.4	747.3	732.7	719.6	707.4	701.5	696.7	690.8	688.0	682.1
12.5°	753.1	737.1	724.9	709.7	696.2	681.6	676.0	667.0	657.7	651.9	644.4
15°	726.1	706.8	691.8	673.8	657.8	641.1	626.2	609.6	603.3	590.1	582.6
17.5°	694.6	674.8	656.4	632.2	607.6	586.9	571.0	555.1	545.5	537.1	533.2
20°	673.8	655.8	630.1	602.0	574.5	551.6	538.8	528.4	518.0	512.1	507.9
22.5°	654.1	631.1	601.2	570.9	543.5	525.6	514.7	504.0	495.5	489.9	484.4
25°	621.1	590.8	559.3	524.6	505.9	490.3	478.4	469.8	464.6	457.3	454.5
27.5°	587.1	550.5	515.7	492.4	472.9	458.6	448.4	441.8	435.2	430.5	427.0
30°	561.0	523.9	492.7	470.5	450.7	438.9	430.5	422.9	417.8	413.9	411.2
32.5°	535.2	498.1	471.8	448.0	432.4	420.9	412.0	406.3	402.2	397.3	395.6
35°	497.8	464.9	442.0	420.5	404.6	394.1	387.2	381.3	377.8	376.5	375.4
37.5°	462.0	435.0	410.4	392.7	378.5	370.3	362.1	359.3	356.9	354.4	355.5
40°	439.3	413.9	392.1	373.4	361.9	352.8	347.9	344.6	342.4	342.4	342.4
42.5°	419.5	394.8	373.4	356.7	345.2	337.6	332.2	329.2	328.6	328.2	329.9
45°	389.0	366.0	344.6	330.6	320.9	313.3	310.1	307.7	307.7	309.2	309.5
47.5°	358.6	337.2	319.9	304.3	295.4	290.7	287.9	286.7	286.9	288.2	289.8
50°	340.0	318.9	301.8	287.9	279.6	275.1	272.7	272.0	272.7	272.7	275.1
52.5°	319.8	300.8	284.1	272.4	263.0	258.8	257.4	256.5	256.9	258.0	259.0
55°	290.1	273.0	257.1	246.0	239.1	236.3	233.2	233.5	232.8	233.5	233.5
57.5°	260.3	245.0	230.2	221.3	215.3	211.2	207.9	208.7	207.8	207.6	207.1
60°	241.1	224.4	212.7	204.7	197.8	194.3	191.2	191.9	190.8	190.1	188.8
62.5°	220.3	206.4	195.2	187.5	181.9	177.9	174.8	174.1	171.7	169.3	166.2
65°	190.1	178.7	168.6	161.3	156.1	153.0	150.6	148.5	143.3	137.8	135.0
67.5°	160.8	152.5	143.1	137.0	132.8	128.7	124.0	120.5	115.6	112.5	110.8
70°	141.9	133.9	125.9	120.0	115.6	111.7	106.5	104.1	100.6	99.2	97.5
72.5°	123.9	116.5	109.0	103.7	98.9	95.9	91.8	89.3	87.8	87.3	85.5
75°	96.5	90.6	85.0	80.2	76.3	74.3	72.5	70.8	70.1	67.0	65.2
77.5°	70.4	66.4	63.0	59.6	56.8	55.5	52.1	50.1	49.0	47.4	47.1
80°	54.8	52.1	48.6	46.5	42.7	41.3	39.9	39.6	39.2	38.9	38.5
82.5°	41.2	38.4	35.0	33.7	32.7	31.8	31.0	30.7	30.3	30.5	30.5
85°	20.8	19.4	19.4	19.1	18.7	18.4	18.0	18.0	17.7	18.0	17.7
87.5°	8.4	8.1	9.2	8.6	9.3	9.6	9.1	9.3	9.8	9.4	9.4
90°	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1	16.9	17.8	17.8
92.5°	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9	131.6	104.7	86.9
95°	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6	521.7	402.3	316.0
97.5°	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6	923.3	836.2	743.3
100°	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6	1091.4	1047.8	981.9
102.5°	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6	1156.9	1169.6	1142.1
105°	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0	1151.0	1239.1	1275.7
107.5°	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4	1059.4	1183.5	1262.8
110°	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1	988.1	1117.2	1215.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3	925.4	1047.4	1145.3
115°	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2	853.7	957.9	1043.3
117.5°	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1	812.8	894.7	967.1
120°	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1	795.0	866.2	929.3
122.5°	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6	783.5	848.4	903.7
125°	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0	765.5	827.0	875.9
127.5°	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2	744.4	805.7	852.1
130°	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0	727.3	787.8	835.0
132.5°	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0	708.1	767.1	814.4
135°	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3	679.2	733.5	778.0
137.5°	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7	651.7	697.4	737.6
140°	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0	633.8	673.9	711.2
142.5°	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0	618.8	653.3	685.6
145°	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9	598.2	624.9	649.9
147.5°	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3	580.4	601.8	621.3
150°	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3	569.7	587.5	603.6
152.5°	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4	559.0	575.4	588.6
155°	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7	543.9	557.2	567.9
157.5°	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0	529.0	540.2	548.8
160°	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2	519.0	528.8	535.9
162.5°	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3	509.7	517.4	523.8
165°	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5	495.9	502.0	506.5
167.5°	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0	484.1	489.1	491.8
170°	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6	476.3	479.8	482.5
172.5°	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9	469.8	472.0	473.9
175°	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2	461.1	462.9	462.9
177.5°	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2	455.9	455.9	456.6
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	822.0	822.5	820.6	820.0	820.6	822.5	822.0	823.7	823.9	826.2	825.3
5°	762.6	761.9	760.2	760.5	760.2	761.9	762.6	765.4	766.8	772.3	771.6
7.5°	711.8	709.1	709.9	707.0	709.9	709.1	711.8	714.3	718.5	721.0	726.9
10°	680.7	676.9	673.8	671.0	673.8	676.9	680.7	682.1	688.0	690.8	696.7
12.5°	638.3	635.0	630.7	631.6	630.7	635.0	638.3	644.4	651.9	657.7	667.0
15°	578.0	572.8	564.5	565.5	564.5	572.8	578.0	582.6	590.1	603.3	609.6
17.5°	527.0	527.1	523.3	524.1	523.3	527.1	527.0	533.2	537.1	545.5	555.1
20°	500.6	498.2	498.6	497.5	498.6	498.2	500.6	507.9	512.1	518.0	528.4
22.5°	482.3	479.4	476.9	474.7	476.9	479.4	482.3	484.4	489.9	495.5	504.0
25°	451.4	449.3	446.2	445.5	446.2	449.3	451.4	454.5	457.3	464.6	469.8
27.5°	424.2	423.7	422.5	420.9	422.5	423.7	424.2	427.0	430.5	435.2	441.8
30°	408.3	407.7	407.0	405.9	407.0	407.7	408.3	411.2	413.9	417.8	422.9
32.5°	394.2	393.8	393.1	393.2	393.1	393.8	394.2	395.6	397.3	402.2	406.3
35°	374.0	373.6	373.0	372.6	373.0	373.6	374.0	375.4	376.5	377.8	381.3
37.5°	355.2	356.1	355.6	355.5	355.6	356.1	355.2	355.5	354.4	356.9	359.3
40°	342.1	342.4	343.1	342.8	343.1	342.4	342.1	342.4	342.4	342.4	344.6
42.5°	331.3	331.4	332.3	331.1	332.3	331.4	331.3	329.9	328.2	328.6	329.2
45°	311.9	314.0	313.6	313.6	313.6	314.0	311.9	309.5	309.2	307.7	307.7
47.5°	290.7	292.6	293.0	292.9	293.0	292.6	290.7	289.8	288.2	286.9	286.7
50°	276.9	276.2	277.2	276.9	277.2	276.2	276.9	275.1	272.7	272.7	272.0
52.5°	259.9	260.1	260.0	259.7	260.0	260.1	259.9	259.0	258.0	256.9	256.5
55°	233.8	234.2	233.5	233.8	233.5	234.2	233.8	233.5	233.5	232.8	233.5
57.5°	205.5	203.8	204.6	203.8	204.6	203.8	205.5	207.1	207.6	207.8	208.7
60°	185.3	182.5	181.8	180.4	181.8	182.5	185.3	188.8	190.1	190.8	191.9
62.5°	162.5	160.6	158.2	159.3	158.2	160.6	162.5	166.2	169.3	171.7	174.1
65°	132.2	130.8	129.7	131.2	129.7	130.8	132.2	135.0	137.8	143.3	148.5
67.5°	109.4	108.7	108.7	108.0	108.7	108.7	109.4	110.8	112.5	115.6	120.5
70°	97.5	96.5	96.5	95.8	96.5	96.5	97.5	97.5	99.2	100.6	104.1
72.5°	85.2	84.3	84.5	84.1	84.5	84.3	85.2	85.5	87.3	87.8	89.3
75°	63.1	61.4	61.4	61.8	61.4	61.4	63.1	65.2	67.0	70.1	70.8
77.5°	47.1	46.7	47.3	46.6	47.3	46.7	47.1	47.1	47.4	49.0	50.1
80°	38.5	38.2	37.8	38.9	37.8	38.2	38.5	38.5	38.9	39.2	39.6
82.5°	29.9	29.9	29.8	31.1	29.8	29.9	29.9	30.5	30.5	30.3	30.7
85°	18.0	17.4	18.0	17.4	18.0	17.4	18.0	17.7	18.0	17.7	18.0
87.5°	10.2	10.0	9.5	9.8	9.5	10.0	10.2	9.4	9.4	9.8	9.3
90°	18.7	19.6	18.7	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1
92.5°	76.4	71.6	68.6	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9
95°	272.4	244.8	228.8	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6
97.5°	679.4	625.8	599.1	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6
100°	904.5	850.2	823.4	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6
102.5°	1094.6	1055.3	1027.2	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6
105°	1277.5	1270.3	1257.8	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0
107.5°	1306.8	1327.1	1336.1	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4
110°	1278.4	1315.7	1331.8	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.1	1262.3	1284.8	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3
115°	1113.7	1167.1	1195.5	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2
117.5°	1027.2	1072.0	1100.8	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1
120°	980.1	1019.3	1042.4	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1
122.5°	946.6	980.1	999.7	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6
125°	911.6	937.4	954.3	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0
127.5°	887.9	910.9	925.1	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2
130°	871.5	893.8	908.0	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0
132.5°	850.2	875.2	888.8	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0
135°	813.7	838.6	852.8	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3
137.5°	770.9	795.5	807.3	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7
140°	742.4	762.1	774.5	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0
142.5°	713.2	731.4	742.4	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0
145°	672.1	687.2	696.2	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9
147.5°	637.8	650.8	657.5	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3
150°	617.8	629.4	634.7	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3
152.5°	600.7	610.1	613.3	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4
155°	576.8	584.0	586.7	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7
157.5°	555.4	560.8	562.4	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0
160°	541.3	546.6	547.5	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2
162.5°	527.7	533.1	534.0	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3
165°	510.1	513.6	512.7	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5
167.5°	493.6	495.9	495.7	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0
170°	484.3	485.2	484.3	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6
172.5°	475.0	475.9	475.0	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9
175°	462.9	464.7	462.9	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2
177.5°	455.9	456.6	455.2	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	823.7	825.6	830.0	835.0	839.2	842.8	845.6	849.4	853.1	858.1	862.8
5°	773.6	778.6	785.5	793.8	804.2	811.2	819.8	827.5	838.6	849.7	860.4
7.5°	729.9	735.2	745.4	756.9	769.3	780.6	790.9	804.3	819.0	835.3	853.3
10°	701.5	707.4	719.6	732.7	747.3	758.4	772.3	788.3	804.9	824.7	846.9
12.5°	676.0	681.6	696.2	709.7	724.9	737.1	753.1	769.4	791.6	813.1	838.3
15°	626.2	641.1	657.8	673.8	691.8	706.8	726.1	742.8	764.0	794.2	823.0
17.5°	571.0	586.9	607.6	632.2	656.4	674.8	694.6	715.2	740.5	771.2	804.5
20°	538.8	551.6	574.5	602.0	630.1	655.8	673.8	696.7	722.7	756.0	790.3
22.5°	514.7	525.6	543.5	570.9	601.2	631.1	654.1	676.7	705.5	738.8	776.2
25°	478.4	490.3	505.9	524.6	559.3	590.8	621.1	647.0	677.6	710.9	752.5
27.5°	448.4	458.6	472.9	492.4	515.7	550.5	587.1	616.8	648.1	683.9	725.5
30°	430.5	438.9	450.7	470.5	492.7	523.9	561.0	595.8	627.3	664.4	707.8
32.5°	412.0	420.9	432.4	448.0	471.8	498.1	535.2	573.2	606.7	644.7	687.2
35°	387.2	394.1	404.6	420.5	442.0	464.9	497.8	537.1	572.5	613.1	653.6
37.5°	362.1	370.3	378.5	392.7	410.4	435.0	462.0	502.0	541.3	578.3	618.0
40°	347.9	352.8	361.9	373.4	392.1	413.9	439.3	478.4	517.6	554.5	594.3
42.5°	332.2	337.6	345.2	356.7	373.4	394.8	419.5	453.4	494.4	530.0	566.3
45°	310.1	313.3	320.9	330.6	344.6	366.0	389.0	419.1	457.6	491.6	523.5
47.5°	287.9	290.7	295.4	304.3	319.9	337.2	358.6	385.7	419.5	453.4	480.5
50°	272.7	275.1	279.6	287.9	301.8	318.9	340.0	364.3	394.5	427.1	449.6
52.5°	257.4	258.8	263.0	272.4	284.1	300.8	319.8	342.1	370.3	397.4	420.3
55°	233.2	236.3	239.1	246.0	257.1	273.0	290.1	311.2	333.1	356.0	375.4
57.5°	207.9	211.2	215.3	221.3	230.2	245.0	260.3	277.4	296.0	315.1	331.4
60°	191.2	194.3	197.8	204.7	212.7	224.4	241.1	256.0	270.3	287.6	303.9
62.5°	174.8	177.9	181.9	187.5	195.2	206.4	220.3	233.3	248.1	263.2	275.4
65°	150.6	153.0	156.1	161.3	168.6	178.7	190.1	200.2	213.4	224.4	235.6
67.5°	124.0	128.7	132.8	137.0	143.1	152.5	160.8	170.4	179.4	187.6	197.8
70°	106.5	111.7	115.6	120.0	125.9	133.9	141.9	148.5	155.8	163.7	172.8
72.5°	91.8	95.9	98.9	103.7	109.0	116.5	123.9	129.3	135.3	140.7	149.5
75°	72.5	74.3	76.3	80.2	85.0	90.6	96.5	101.3	104.8	109.6	115.9
77.5°	52.1	55.5	56.8	59.6	63.0	66.4	70.4	74.5	77.8	79.5	84.3
80°	39.9	41.3	42.7	46.5	48.6	52.1	54.8	58.7	60.0	61.8	66.3
82.5°	31.0	31.8	32.7	33.7	35.0	38.4	41.2	43.6	45.0	45.7	49.0
85°	18.0	18.4	18.7	19.1	19.4	19.4	20.8	22.6	25.0	25.0	26.0
87.5°	9.1	9.6	9.3	8.6	9.2	8.1	8.4	8.2	8.8	9.1	9.6
90°	15.2	16.1	14.3	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9
92.5°	235.2	282.4	247.1	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2
95°	746.0	725.5	547.5	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3
97.5°	937.2	764.1	512.4	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7
100°	943.6	715.7	464.7	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7
102.5°	890.2	655.2	432.7	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9
105°	793.2	584.0	405.0	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2
107.5°	714.8	544.1	400.0	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8
110°	675.6	530.6	401.4	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	653.6	524.1	405.7	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8
115°	632.9	520.8	413.9	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4
117.5°	623.7	519.9	422.7	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9
120°	618.7	519.9	429.1	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6
122.5°	613.0	519.2	435.5	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8
125°	603.6	518.1	445.1	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5
127.5°	590.9	516.1	452.7	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1
130°	583.1	515.4	458.4	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3
132.5°	576.0	514.7	463.4	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5
135°	565.3	513.6	470.9	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5
137.5°	556.0	513.4	475.4	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6
140°	551.1	512.7	478.9	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8
142.5°	546.8	512.7	481.8	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8
145°	539.5	511.0	483.4	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8
147.5°	532.9	507.7	484.3	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7
150°	527.9	505.6	484.3	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7
152.5°	522.2	502.0	482.9	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0
155°	513.6	496.8	480.7	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9
157.5°	504.9	491.2	478.4	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5
160°	498.6	487.0	476.3	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4
162.5°	492.8	482.7	474.1	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5
165°	483.4	476.3	470.0	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5
167.5°	474.8	469.8	465.7	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6
170°	469.1	465.6	462.9	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1
172.5°	464.1	461.3	460.0	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6
175°	458.4	456.6	456.6	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2
177.5°	454.5	453.8	453.8	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	866.4	868.9	871.6	876.9	881.4	883.3	887.3	890.0	889.1	893.0	899.7
5°	869.8	879.1	889.9	901.0	913.5	923.9	932.3	940.6	947.2	955.1	967.0
7.5°	869.2	885.9	904.0	923.9	944.4	962.1	978.5	995.1	1009.9	1026.1	1047.2
10°	867.0	889.2	911.8	937.8	963.9	988.5	1010.7	1031.4	1051.2	1072.4	1099.1
12.5°	864.5	890.0	917.3	948.6	981.1	1010.7	1036.8	1066.8	1091.5	1118.7	1149.7
15°	853.5	887.9	925.0	965.5	1004.4	1044.3	1080.0	1116.9	1151.2	1183.7	1222.6
17.5°	840.9	880.5	924.3	972.2	1019.0	1067.4	1109.8	1156.2	1191.2	1235.0	1271.1
20°	830.6	873.3	920.1	973.8	1027.0	1080.8	1127.6	1174.7	1214.3	1258.4	1304.2
22.5°	818.1	865.0	915.7	971.3	1027.0	1085.7	1137.6	1184.5	1233.5	1283.1	1330.3
25°	798.0	846.6	900.4	961.4	1025.2	1085.2	1140.8	1199.1	1251.8	1305.6	1347.9
27.5°	773.3	824.3	881.0	944.0	1009.5	1070.9	1136.3	1198.5	1251.5	1303.2	1340.2
30°	753.6	807.4	861.8	925.7	993.6	1059.6	1129.6	1191.8	1247.6	1294.1	1314.9
32.5°	733.3	784.3	840.4	905.1	974.8	1045.7	1115.3	1178.8	1230.4	1258.3	1258.8
35°	698.0	745.9	804.2	867.7	939.1	1016.2	1086.6	1149.1	1180.6	1183.1	1149.1
37.5°	659.6	703.6	758.6	822.2	900.4	977.0	1048.9	1090.6	1101.2	1065.9	1003.0
40°	632.1	672.7	725.9	791.0	868.8	947.9	1013.4	1043.9	1032.9	975.6	905.5
42.5°	603.2	641.1	692.2	756.6	834.6	914.5	970.4	986.8	957.3	891.3	809.2
45°	556.2	590.8	641.5	706.4	781.3	856.3	898.6	890.3	841.3	762.9	671.0
47.5°	507.1	540.6	586.2	646.2	723.0	787.6	816.3	791.2	721.6	635.3	560.5
50°	474.7	509.0	551.0	608.2	678.3	740.7	759.1	720.9	643.5	560.7	492.0
52.5°	442.7	472.1	513.2	568.5	635.5	688.3	698.0	654.1	574.2	499.9	439.0
55°	394.1	420.9	455.6	507.6	565.5	610.3	605.1	548.5	476.0	412.5	364.6
57.5°	347.1	367.3	399.3	448.1	499.0	529.1	510.0	461.8	394.2	342.2	301.8
60°	316.1	334.8	364.6	407.3	452.1	469.0	453.1	400.7	347.3	299.8	265.7
62.5°	286.7	303.2	328.9	368.5	404.6	414.6	397.6	351.9	303.7	263.1	235.0
65°	243.9	259.1	281.1	309.2	334.1	338.9	327.9	281.1	244.6	210.6	191.2
67.5°	205.1	215.1	232.2	256.5	269.7	272.6	251.1	221.7	189.6	168.7	154.1
70°	179.1	185.9	201.9	215.1	225.9	226.2	206.4	182.8	158.2	141.2	130.5
72.5°	153.7	160.4	172.5	181.6	189.8	187.1	169.0	150.3	130.5	117.6	109.6
75°	118.7	124.6	130.8	135.0	135.0	131.5	118.3	104.4	93.0	85.3	82.9
77.5°	86.2	91.1	93.2	92.6	91.3	85.9	77.6	68.5	64.4	60.8	58.9
80°	67.7	69.7	70.4	68.7	66.6	60.4	54.8	51.0	47.2	45.8	45.1
82.5°	50.2	52.0	50.2	50.6	46.1	40.9	37.9	36.6	35.0	34.4	33.7
85°	26.8	26.4	25.7	23.9	20.8	20.2	19.8	19.4	18.7	19.1	18.4
87.5°	9.7	9.4	8.5	8.4	8.4	8.9	9.2	9.5	9.9	9.5	10.2
90°	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1
92.5°	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9
95°	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6
97.5°	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6
100°	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6
102.5°	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6
105°	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0
107.5°	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4
110°	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1





TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3
115°	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2
117.5°	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1
120°	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1
122.5°	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6
125°	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0
127.5°	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2
130°	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0
132.5°	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0
135°	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3
137.5°	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7
140°	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0
142.5°	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0
145°	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9
147.5°	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3
150°	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3
152.5°	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4
155°	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7
157.5°	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0
160°	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2
162.5°	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3
165°	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5
167.5°	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0
170°	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6
172.5°	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9
175°	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2
177.5°	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	903.3	904.5	905.3	908.0	908.3	910.8	908.3
5°	978.0	982.9	990.5	998.2	998.9	1003.7	995.1
7.5°	1061.8	1073.1	1080.1	1092.4	1097.3	1100.4	1095.4
10°	1119.6	1130.0	1148.4	1157.4	1166.4	1167.8	1163.7
12.5°	1175.4	1191.9	1206.4	1223.5	1223.1	1235.3	1230.8
15°	1249.7	1266.7	1286.8	1305.9	1312.9	1312.9	1318.4
17.5°	1302.7	1333.9	1354.7	1369.7	1386.1	1388.9	1387.0
20°	1338.5	1372.2	1394.4	1413.8	1425.0	1428.1	1428.1
22.5°	1365.2	1393.8	1415.5	1433.0	1442.2	1445.8	1444.7
25°	1383.7	1408.3	1421.5	1426.6	1429.1	1428.3	1421.8
27.5°	1358.3	1357.3	1348.9	1332.9	1321.0	1313.7	1305.4
30°	1310.1	1292.0	1271.2	1248.3	1218.8	1196.2	1189.4
32.5°	1238.2	1197.7	1162.4	1124.3	1092.5	1070.0	1060.5
35°	1099.1	1034.9	982.6	936.7	903.5	882.6	875.7
37.5°	934.2	872.0	807.2	762.8	735.1	714.1	706.2
40°	829.2	761.5	705.0	663.3	634.9	614.5	614.1
42.5°	733.4	668.9	615.6	585.7	555.0	541.4	541.4
45°	600.6	548.8	503.7	480.2	461.8	450.7	447.5
47.5°	497.2	454.5	424.5	405.6	390.7	383.6	379.0
50°	439.3	401.8	377.8	361.5	353.2	344.2	343.5
52.5°	390.9	360.7	342.1	328.8	318.3	312.8	313.0
55°	328.6	304.6	291.4	281.3	273.0	268.9	267.2
57.5°	276.8	258.9	249.2	240.0	236.5	233.2	232.3
60°	244.6	232.5	223.5	216.2	211.0	209.9	209.6
62.5°	217.9	205.3	199.0	193.4	189.6	188.0	187.3
65°	179.7	170.3	164.8	160.3	158.9	156.5	156.1
67.5°	144.9	139.3	135.6	132.5	130.5	130.5	130.5
70°	123.5	120.4	117.3	115.6	114.5	113.8	113.8
72.5°	105.2	102.9	100.3	99.4	99.2	98.5	98.3
75°	80.2	77.8	78.0	76.3	74.9	73.2	72.1
77.5°	56.8	55.1	54.8	54.6	53.3	53.1	53.7
80°	44.1	42.4	42.0	42.4	42.0	40.9	40.9
82.5°	33.5	32.1	31.7	31.5	31.1	31.5	30.9
85°	18.0	17.4	17.4	17.4	18.0	17.7	17.4
87.5°	9.8	9.6	10.0	9.8	10.0	9.5	9.8
90°	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8



TEST NUMBER: P332915-940

CATALOG NUMBER: S124RDIP-S575D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)