

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332899-940

Luminaire Tested: **S124RDIP-S575D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332899-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D365U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3225.4 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	111	111	111	111		104	104	104	104		92	92	92		80	80	80		70	70	70	65	
1	101	97	93	90		95	92	88	85		81	78	76		71	69	68		62	61	60	55	
2	93	85	79	74		87	80	75	70		71	67	64		63	60	57		55	53	51	47	
3	85	75	68	62		79	71	65	59		63	58	54		56	52	49		49	46	44	40	
4	78	67	59	53		73	63	56	51		56	51	46		50	46	42		44	41	38	35	
5	72	60	52	46		67	57	49	44		51	45	40		45	40	37		40	36	33	30	
6	66	54	46	40		62	51	44	38		46	40	35		41	36	32		36	32	29	27	
7	61	49	41	35		58	46	39	34		42	36	31		37	32	29		33	29	26	24	
8	57	45	37	31		54	42	35	30		38	32	28		34	29	26		31	27	24	21	
9	53	41	33	28		50	39	32	27		35	29	25		32	27	23		28	24	21	19	
10	50	38	30	25		47	36	29	25		32	27	23		29	25	21		26	22	20	18	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.1	2.6
10°-20°	237.4	7.4
20°-30°	342.8	10.6
30°-40°	388.6	12.0
40°-50°	375.2	11.6
50°-60°	312.0	9.7
60°-70°	215.4	6.7
70°-80°	109.2	3.4
80°-90°	29.2	0.9
90°-100°	26.9	0.8
100°-110°	79.6	2.5
110°-120°	135.1	4.2
120°-130°	178.2	5.5
130°-140°	200.1	6.2
140°-150°	196.6	6.1
150°-160°	165.4	5.1
160°-170°	110.0	3.4
170°-180°	38.5	1.2
0°-30°	665.3	20.6
0°-40°	1053.9	32.7
0°-60°	1741.1	54.0
0°-90°	2095.0	65.0
90°-120°	241.6	7.5
90°-150°	816.5	25.3
90°-180°	1130.0	35.0
0°-180°	3225.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	1	4	7	9	10	3
95°	19	22	24	25	25	21
105°	73	74	75	76	77	78
115°	137	137	137	136	136	135
125°	200	200	200	199	198	178
135°	258	260	260	259	258	200
145°	314	315	315	315	314	196
155°	359	359	359	360	359	165
165°	391	390	390	391	390	110
175°	407	405	405	407	405	39
180°	407	407	407	407	407	



TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	12.9	12.1	11.3	10.4	9.6	9.2	9.2	9.2	9.2	9.2	9.1
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	6.8	7.7	8.5	9.4	10.3	10.9	11.3	11.7	12.1	12.5	12.8
95°	18.9	19.5	20.2	20.8	21.4	22.0	22.5	23.0	23.5	24.0	24.2
97.5°	33.0	33.5	34.1	34.5	35.0	35.6	36.1	36.7	37.3	37.9	38.2
100°	44.1	44.4	44.7	44.9	45.2	45.7	46.3	47.0	47.6	48.2	48.3
102.5°	55.7	55.8	55.9	56.1	56.2	56.5	57.1	57.7	58.2	58.8	59.0
105°	73.4	73.5	73.6	73.7	73.7	73.8	74.2	74.5	74.7	75.0	75.2
107.5°	92.0	92.1	92.2	92.3	92.4	92.4	92.5	92.5	92.6	92.6	92.7
110°	104.6	104.8	104.9	105.0	105.1	105.2	105.1	105.0	105.0	105.0	104.8



TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	117.7	117.7	117.8	117.8	117.8	117.8	117.6	117.5	117.4	117.3	117.3
115°	137.4	137.4	137.4	137.4	137.4	137.3	137.1	137.1	136.9	136.8	136.7
117.5°	155.9	156.0	156.0	156.0	156.1	156.1	156.0	156.0	155.8	155.7	155.5
120°	168.3	168.5	168.8	169.1	169.4	169.4	169.2	169.0	168.8	168.6	168.3
122.5°	181.1	181.2	181.4	181.5	181.6	181.6	181.5	181.4	181.3	181.2	180.9
125°	200.1	200.1	200.1	200.1	200.1	200.0	200.0	199.9	199.8	199.7	199.7
127.5°	217.3	217.5	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.8	217.6
130°	229.4	229.6	229.8	230.1	230.2	230.3	230.3	230.3	230.3	230.3	230.2
132.5°	241.7	241.9	242.0	242.2	242.4	242.4	242.4	242.3	242.3	242.2	242.0
135°	258.1	258.5	258.9	259.3	259.8	259.9	259.9	259.9	259.9	259.9	259.8
137.5°	275.8	276.1	276.3	276.4	276.6	276.8	276.9	277.0	277.1	277.2	277.1
140°	287.7	287.8	287.9	288.1	288.3	288.3	288.3	288.3	288.3	288.3	288.3
142.5°	298.5	298.6	298.8	298.9	299.1	299.2	299.1	299.0	299.0	298.9	298.9
145°	313.5	313.8	314.1	314.3	314.7	314.9	314.9	315.0	315.0	315.1	315.0
147.5°	328.4	328.8	329.0	329.4	329.8	329.8	329.8	329.8	329.8	329.7	329.6
150°	337.5	337.8	338.0	338.3	338.6	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	346.1	346.3	346.3	346.5	346.7	346.8	346.9	347.0	347.0	347.1	347.2
155°	359.2	359.2	359.2	359.2	359.2	359.2	359.1	359.0	359.0	358.9	359.2
157.5°	370.3	370.1	370.1	370.0	369.8	369.7	369.7	369.7	369.7	369.7	369.9
160°	376.8	376.7	376.7	376.7	376.6	376.5	376.5	376.4	376.3	376.2	376.5
162.5°	382.9	382.7	382.5	382.4	382.2	382.1	382.0	381.9	381.8	381.7	382.2
165°	391.0	390.8	390.7	390.4	390.2	390.0	389.9	389.8	389.6	389.5	389.9
167.5°	397.3	397.0	396.7	396.4	396.1	395.9	396.0	396.0	396.0	396.0	396.5
170°	400.8	400.5	400.1	399.8	399.4	399.3	399.3	399.4	399.5	399.6	399.9
172.5°	403.3	403.1	402.7	402.4	402.2	402.0	402.0	402.1	402.1	402.1	402.5
175°	406.8	406.4	406.1	405.7	405.4	405.2	405.1	405.0	405.0	404.9	405.4
177.5°	408.0	407.7	407.3	407.1	406.8	406.7	406.7	406.7	406.7	406.7	407.1
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	9.1	9.0	9.0	9.1	9.2	9.4	9.5	9.6
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	13.0	13.2	13.5	13.6	13.7	13.8	13.9	14.0
95°	24.3	24.6	24.8	24.9	24.9	24.9	24.9	24.9
97.5°	38.3	38.6	38.9	39.0	39.0	39.0	39.0	39.0
100°	48.5	48.6	48.8	48.9	48.9	48.9	48.9	48.9
102.5°	59.2	59.4	59.6	59.7	59.7	59.8	59.8	59.9
105°	75.4	75.6	75.8	76.1	76.2	76.5	76.7	76.9
107.5°	93.0	93.2	93.4	93.5	93.5	93.5	93.5	93.4
110°	104.7	104.5	104.3	104.4	104.6	104.9	105.0	105.2





TEST NUMBER: P332899-940

CATALOG NUMBER: S124RDIP-S575D365U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	117.3	117.2	117.2	117.2	117.3	117.3	117.3	117.3
115°	136.6	136.5	136.4	136.4	136.3	136.3	136.2	136.2
117.5°	155.2	155.0	154.8	154.6	154.4	154.3	154.2	154.0
120°	167.9	167.6	167.2	167.1	167.2	167.4	167.5	167.6
122.5°	180.7	180.5	180.2	179.9	179.8	179.5	179.2	179.0
125°	199.5	199.4	199.2	199.0	198.9	198.8	198.7	198.5
127.5°	217.5	217.3	217.1	217.0	217.0	216.9	216.7	216.6
130°	230.1	229.9	229.8	229.5	229.3	229.0	228.7	228.5
132.5°	241.9	241.7	241.7	241.5	241.4	241.3	241.2	241.0
135°	259.7	259.6	259.4	259.2	259.0	258.8	258.6	258.4
137.5°	276.9	276.7	276.5	276.4	276.4	276.5	276.5	276.6
140°	288.2	288.1	288.0	287.9	287.9	287.8	287.8	287.7
142.5°	298.9	298.9	298.8	298.8	298.8	298.8	298.8	298.8
145°	315.0	314.9	314.9	314.7	314.5	314.2	314.1	313.9
147.5°	329.6	329.5	329.4	329.4	329.3	329.2	329.1	329.1
150°	338.8	338.8	338.8	338.7	338.7	338.6	338.5	338.4
152.5°	347.4	347.6	347.8	347.7	347.5	347.3	347.1	347.0
155°	359.4	359.7	360.0	360.0	359.7	359.4	359.2	358.9
157.5°	370.1	370.3	370.5	370.5	370.2	370.1	369.8	369.5
160°	376.7	376.8	377.1	377.0	376.7	376.3	375.9	375.6
162.5°	382.5	382.9	383.3	383.3	383.0	382.6	382.3	381.9
165°	390.3	390.7	391.1	391.2	390.9	390.7	390.4	390.1
167.5°	396.9	397.3	397.7	397.7	397.3	396.8	396.4	395.9
170°	400.4	400.8	401.3	401.2	400.7	400.2	399.8	399.2
172.5°	403.1	403.5	403.9	403.9	403.5	403.0	402.5	402.0
175°	405.9	406.4	406.9	406.9	406.4	405.9	405.4	404.9
177.5°	407.4	407.9	408.2	408.2	407.8	407.3	406.9	406.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4

(END OF REPORT)