

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332901-940

Luminaire Tested: **S124RDIP-S575D590U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332901-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D590U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4282.4 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	37
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	24	22	19
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6952	6952	6952	6952
5°	8064	6972	6163	6972
10°	9539	6942	5501	6942
15°	11019	6878	4726	6878
20°	12269	6790	4274	6790
25°	12665	6703	3968	6703
30°	11087	6598	3784	6598
35°	8630	6441	3672	6441
40°	6472	6263	3613	6263
45°	5109	5977	3580	5977
50°	4314	5647	3478	5647
55°	3761	5284	3291	5284
60°	3384	4907	2913	4907
65°	2982	4500	2506	4500
70°	2686	4079	2261	4079
75°	2249	3615	1928	3615
80°	1901	3082	1808	3082
85°	1612	2408	1612	2408



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	1.9
10°-20°	251.7	5.9
20°-30°	393.7	9.2
30°-40°	437.6	10.2
40°-50°	388.3	9.1
50°-60°	302.5	7.1
60°-70°	198.1	4.6
70°-80°	97.4	2.3
80°-90°	26.0	0.6
90°-100°	23.3	0.5
100°-110°	148.3	3.5
110°-120°	283.7	6.6
120°-130°	360.1	8.4
130°-140°	385.3	9.0
140°-150°	360.3	8.4
150°-160°	290.6	6.8
160°-170°	187.4	4.4
170°-180°	64.6	1.5
0°-30°	728.8	17.0
0°-40°	1166.4	27.2
0°-60°	1857.2	43.4
0°-90°	2178.7	50.9
90°-120°	455.3	10.6
90°-150°	1561.1	36.5
90°-180°	2104.0	49.1
0°-180°	4282.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	861	861	861	861	861	
5°	995	860	760	860	995	101
15°	1318	823	566	823	1318	375
25°	1422	752	446	752	1422	631
35°	876	654	373	654	876	549
45°	448	524	314	524	448	354
55°	267	375	234	375	267	243
65°	156	236	131	236	156	157
75°	72	116	62	116	72	79
85°	17	26	17	26	17	20
90°	15	2	15	2	15	7
95°	15	28	15	28	15	12
105°	145	153	145	153	145	126
115°	288	286	288	286	288	285
125°	405	402	405	402	405	361
135°	502	498	502	498	502	386
145°	578	575	578	575	578	361
155°	630	630	630	630	630	290
165°	662	665	662	665	662	187
175°	676	680	676	680	676	64
180°	680	680	680	680	680	



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	908.3	910.8	908.3	908.0	905.3	904.5	903.3	899.7	893.0	889.1	890.0
5°	995.1	1003.7	998.9	998.2	990.5	982.9	978.0	967.0	955.1	947.2	940.6
7.5°	1095.4	1100.4	1097.3	1092.4	1080.1	1073.1	1061.8	1047.2	1026.1	1009.9	995.1
10°	1163.7	1167.8	1166.4	1157.4	1148.4	1130.0	1119.6	1099.1	1072.4	1051.2	1031.4
12.5°	1230.8	1235.3	1223.1	1223.5	1206.4	1191.9	1175.4	1149.7	1118.7	1091.5	1066.8
15°	1318.4	1312.9	1312.9	1305.9	1286.8	1266.7	1249.7	1222.6	1183.7	1151.2	1116.9
17.5°	1387.0	1388.9	1386.1	1369.7	1354.7	1333.9	1302.7	1271.1	1235.0	1191.2	1156.2
20°	1428.1	1428.1	1425.0	1413.8	1394.4	1372.2	1338.5	1304.2	1258.4	1214.3	1174.7
22.5°	1444.7	1445.8	1442.2	1433.0	1415.5	1393.8	1365.2	1330.3	1283.1	1233.5	1184.5
25°	1421.8	1428.3	1429.1	1426.6	1421.5	1408.3	1383.7	1347.9	1305.6	1251.8	1199.1
27.5°	1305.4	1313.7	1321.0	1332.9	1348.9	1357.3	1358.3	1340.2	1303.2	1251.5	1198.5
30°	1189.4	1196.2	1218.8	1248.3	1271.2	1292.0	1310.1	1314.9	1294.1	1247.6	1191.8
32.5°	1060.5	1070.0	1092.5	1124.3	1162.4	1197.7	1238.2	1258.8	1258.3	1230.4	1178.8
35°	875.7	882.6	903.5	936.7	982.6	1034.9	1099.1	1149.1	1183.1	1180.6	1149.1
37.5°	706.2	714.1	735.1	762.8	807.2	872.0	934.2	1003.0	1065.9	1101.2	1090.6
40°	614.1	614.5	634.9	663.3	705.0	761.5	829.2	905.5	975.6	1032.9	1043.9
42.5°	541.4	541.4	555.0	585.7	615.6	668.9	733.4	809.2	891.3	957.3	986.8
45°	447.5	450.7	461.8	480.2	503.7	548.8	600.6	671.0	762.9	841.3	890.3
47.5°	379.0	383.6	390.7	405.6	424.5	454.5	497.2	560.5	635.3	721.6	791.2
50°	343.5	344.2	353.2	361.5	377.8	401.8	439.3	492.0	560.7	643.5	720.9
52.5°	313.0	312.8	318.3	328.8	342.1	360.7	390.9	439.0	499.9	574.2	654.1
55°	267.2	268.9	273.0	281.3	291.4	304.6	328.6	364.6	412.5	476.0	548.5
57.5°	232.3	233.2	236.5	240.0	249.2	258.9	276.8	301.8	342.2	394.2	461.8
60°	209.6	209.9	211.0	216.2	223.5	232.5	244.6	265.7	299.8	347.3	400.7
62.5°	187.3	188.0	189.6	193.4	199.0	205.3	217.9	235.0	263.1	303.7	351.9
65°	156.1	156.5	158.9	160.3	164.8	170.3	179.7	191.2	210.6	244.6	281.1
67.5°	130.5	130.5	130.5	132.5	135.6	139.3	144.9	154.1	168.7	189.6	221.7
70°	113.8	113.8	114.5	115.6	117.3	120.4	123.5	130.5	141.2	158.2	182.8
72.5°	98.3	98.5	99.2	99.4	100.3	102.9	105.2	109.6	117.6	130.5	150.3
75°	72.1	73.2	74.9	76.3	78.0	77.8	80.2	82.9	85.3	93.0	104.4
77.5°	53.7	53.1	53.3	54.6	54.8	55.1	56.8	58.9	60.8	64.4	68.5
80°	40.9	40.9	42.0	42.4	42.0	42.4	44.1	45.1	45.8	47.2	51.0
82.5°	30.9	31.5	31.1	31.5	31.7	32.1	33.5	33.7	34.4	35.0	36.6
85°	17.4	17.7	18.0	17.4	17.4	17.4	18.0	18.4	19.1	18.7	19.4
87.5°	9.2	8.8	9.1	9.0	9.3	8.9	9.0	9.5	8.7	8.9	8.7
90°	15.2	15.1	14.8	14.6	14.4	13.9	13.2	12.6	11.9	11.1	10.3
92.5°	14.0	14.0	13.9	13.9	13.8	13.5	12.8	12.1	11.5	10.8	9.9
95°	14.7	14.6	14.5	14.4	14.3	13.9	13.2	12.6	11.9	11.1	11.1
97.5°	14.3	14.1	14.0	13.9	13.8	13.7	13.6	13.6	13.5	13.5	26.0
100°	14.3	14.1	14.0	13.9	13.8	14.7	16.6	18.5	20.4	22.4	38.0
102.5°	14.6	14.6	14.6	14.6	14.5	24.9	45.7	66.3	87.1	107.8	109.9
105°	145.0	149.0	153.1	157.2	161.2	162.7	161.8	160.8	159.7	158.7	158.1
107.5°	202.1	201.6	201.2	200.7	200.3	199.8	199.4	198.9	198.4	197.9	197.1
110°	226.9	226.5	226.1	225.9	225.5	225.2	225.0	224.8	224.5	224.4	223.6



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	251.6	251.3	250.8	250.4	249.9	249.8	249.9	249.9	249.9	249.9	249.7
115°	287.9	287.9	287.9	287.9	287.9	287.8	287.6	287.3	287.1	286.9	287.0
117.5°	324.8	324.8	324.9	324.9	324.9	324.9	325.0	325.0	325.1	325.1	324.9
120°	347.9	348.1	348.4	348.6	348.8	348.8	348.6	348.4	348.1	347.9	348.0
122.5°	370.7	371.0	371.1	371.4	371.6	371.7	371.5	371.4	371.2	371.1	371.0
125°	404.9	404.7	404.7	404.6	404.5	404.2	403.9	403.5	403.2	402.9	403.1
127.5°	434.9	435.0	435.1	435.2	435.2	435.3	435.4	435.5	435.5	435.6	435.1
130°	455.2	455.2	455.2	455.2	455.2	455.2	455.0	455.0	454.9	454.8	454.4
132.5°	473.9	474.0	474.1	474.2	474.3	474.3	474.2	474.1	473.9	473.9	473.4
135°	502.0	501.9	501.6	501.3	501.1	500.9	500.7	500.4	500.2	500.0	499.5
137.5°	526.0	526.1	526.2	526.3	526.3	526.2	526.0	525.8	525.5	525.2	524.8
140°	542.7	542.6	542.5	542.4	542.2	542.1	541.7	541.4	541.0	540.7	540.5
142.5°	556.6	556.5	556.5	556.5	556.5	556.3	556.1	555.8	555.6	555.4	555.2
145°	577.8	577.7	577.4	577.1	576.9	576.8	576.7	576.5	576.4	576.3	576.3
147.5°	595.4	595.3	595.2	595.1	594.9	594.9	594.8	594.7	594.6	594.5	594.6
150°	606.8	606.7	606.6	606.5	606.4	606.3	606.3	606.3	606.3	606.3	606.5
152.5°	616.6	616.6	616.7	616.8	616.9	616.8	616.6	616.4	616.3	616.1	616.3
155°	629.7	630.1	630.4	630.7	631.1	631.0	630.5	630.1	629.6	629.2	629.5
157.5°	640.7	641.3	641.9	642.5	643.0	643.0	642.5	641.9	641.3	640.7	641.1
160°	648.0	648.7	649.3	650.1	650.8	650.8	650.1	649.3	648.7	648.0	648.1
162.5°	653.7	654.5	655.2	656.0	656.8	656.8	656.1	655.5	654.8	654.2	654.2
165°	661.7	662.8	663.8	664.8	665.8	665.9	664.9	664.1	663.2	662.3	662.3
167.5°	667.8	668.9	670.0	671.2	672.3	672.3	671.4	670.4	669.4	668.3	668.4
170°	671.5	672.5	673.7	674.8	675.9	676.1	675.1	674.2	673.3	672.4	672.3
172.5°	673.4	674.7	675.9	677.2	678.3	678.5	677.6	676.7	675.8	674.8	674.8
175°	676.0	677.3	678.7	680.1	681.4	681.6	680.6	679.6	678.5	677.5	677.4
177.5°	677.6	678.7	679.8	680.9	682.0	682.2	681.4	680.7	680.0	679.2	679.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	887.3	883.3	881.4	876.9	871.6	868.9	866.4	862.8	858.1	853.1	849.4
5°	932.3	923.9	913.5	901.0	889.9	879.1	869.8	860.4	849.7	838.6	827.5
7.5°	978.5	962.1	944.4	923.9	904.0	885.9	869.2	853.3	835.3	819.0	804.3
10°	1010.7	988.5	963.9	937.8	911.8	889.2	867.0	846.9	824.7	804.9	788.3
12.5°	1036.8	1010.7	981.1	948.6	917.3	890.0	864.5	838.3	813.1	791.6	769.4
15°	1080.0	1044.3	1004.4	965.5	925.0	887.9	853.5	823.0	794.2	764.0	742.8
17.5°	1109.8	1067.4	1019.0	972.2	924.3	880.5	840.9	804.5	771.2	740.5	715.2
20°	1127.6	1080.8	1027.0	973.8	920.1	873.3	830.6	790.3	756.0	722.7	696.7
22.5°	1137.6	1085.7	1027.0	971.3	915.7	865.0	818.1	776.2	738.8	705.5	676.7
25°	1140.8	1085.2	1025.2	961.4	900.4	846.6	798.0	752.5	710.9	677.6	647.0
27.5°	1136.3	1070.9	1009.5	944.0	881.0	824.3	773.3	725.5	683.9	648.1	616.8
30°	1129.6	1059.6	993.6	925.7	861.8	807.4	753.6	707.8	664.4	627.3	595.8
32.5°	1115.3	1045.7	974.8	905.1	840.4	784.3	733.3	687.2	644.7	606.7	573.2
35°	1086.6	1016.2	939.1	867.7	804.2	745.9	698.0	653.6	613.1	572.5	537.1
37.5°	1048.9	977.0	900.4	822.2	758.6	703.6	659.6	618.0	578.3	541.3	502.0
40°	1013.4	947.9	868.8	791.0	725.9	672.7	632.1	594.3	554.5	517.6	478.4
42.5°	970.4	914.5	834.6	756.6	692.2	641.1	603.2	566.3	530.0	494.4	453.4
45°	898.6	856.3	781.3	706.4	641.5	590.8	556.2	523.5	491.6	457.6	419.1
47.5°	816.3	787.6	723.0	646.2	586.2	540.6	507.1	480.5	453.4	419.5	385.7
50°	759.1	740.7	678.3	608.2	551.0	509.0	474.7	449.6	427.1	394.5	364.3
52.5°	698.0	688.3	635.5	568.5	513.2	472.1	442.7	420.3	397.4	370.3	342.1
55°	605.1	610.3	565.5	507.6	455.6	420.9	394.1	375.4	356.0	333.1	311.2
57.5°	510.0	529.1	499.0	448.1	399.3	367.3	347.1	331.4	315.1	296.0	277.4
60°	453.1	469.0	452.1	407.3	364.6	334.8	316.1	303.9	287.6	270.3	256.0
62.5°	397.6	414.6	404.6	368.5	328.9	303.2	286.7	275.4	263.2	248.1	233.3
65°	327.9	338.9	334.1	309.2	281.1	259.1	243.9	235.6	224.4	213.4	200.2
67.5°	251.1	272.6	269.7	256.5	232.2	215.1	205.1	197.8	187.6	179.4	170.4
70°	206.4	226.2	225.9	215.1	201.9	185.9	179.1	172.8	163.7	155.8	148.5
72.5°	169.0	187.1	189.8	181.6	172.5	160.4	153.7	149.5	140.7	135.3	129.3
75°	118.3	131.5	135.0	135.0	130.8	124.6	118.7	115.9	109.6	104.8	101.3
77.5°	77.6	85.9	91.3	92.6	93.2	91.1	86.2	84.3	79.5	77.8	74.5
80°	54.8	60.4	66.6	68.7	70.4	69.7	67.7	66.3	61.8	60.0	58.7
82.5°	37.9	40.9	46.1	50.6	50.2	52.0	50.2	49.0	45.7	45.0	43.6
85°	19.8	20.2	20.8	23.9	25.7	26.4	26.8	26.0	25.0	25.0	22.6
87.5°	8.6	8.1	8.5	8.2	8.3	9.1	9.7	9.7	9.2	8.6	8.0
90°	9.4	8.5	7.6	6.5	5.3	4.0	2.8	1.5	2.8	4.0	5.3
92.5°	9.0	8.1	7.1	6.7	6.6	6.5	6.5	6.4	6.5	6.5	6.6
95°	11.0	10.9	10.7	12.6	16.4	20.3	24.2	28.0	24.2	20.3	16.4
97.5°	38.7	51.3	63.8	69.0	66.6	64.2	61.8	59.4	61.8	64.2	66.6
100°	53.6	69.2	84.8	91.6	89.5	87.5	85.4	83.4	85.4	87.5	89.5
102.5°	111.9	114.0	116.0	116.3	114.8	113.2	111.7	110.3	111.7	113.2	114.8
105°	157.6	157.0	156.4	155.8	155.2	154.4	153.8	153.1	153.8	154.4	155.2
107.5°	196.4	195.6	194.7	194.2	193.9	193.6	193.2	192.9	193.2	193.6	193.9
110°	222.9	222.3	221.6	221.1	220.8	220.4	220.1	219.7	220.1	220.4	220.8



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.3	249.0	248.7	248.3	247.6	247.0	246.4	245.8	246.4	247.0	247.6
115°	287.1	287.2	287.3	287.2	286.9	286.5	286.2	285.9	286.2	286.5	286.9
117.5°	324.7	324.4	324.1	323.8	323.3	322.9	322.4	322.0	322.4	322.9	323.3
120°	348.1	348.3	348.4	348.2	347.8	347.3	346.9	346.4	346.9	347.3	347.8
122.5°	370.8	370.7	370.5	370.2	370.0	369.7	369.4	369.2	369.4	369.7	370.0
125°	403.3	403.5	403.8	403.7	403.2	402.8	402.3	401.8	402.3	402.8	403.2
127.5°	434.5	434.1	433.5	433.2	433.1	433.0	432.8	432.7	432.8	433.0	433.1
130°	454.1	453.7	453.3	453.2	453.1	452.9	452.8	452.7	452.8	452.9	453.1
132.5°	473.0	472.6	472.2	471.8	471.6	471.4	471.2	471.0	471.2	471.4	471.6
135°	499.1	498.6	498.2	498.0	498.1	498.3	498.4	498.5	498.4	498.3	498.1
137.5°	524.2	523.7	523.3	523.0	522.9	522.9	522.8	522.8	522.8	522.9	522.9
140°	540.3	540.0	539.8	539.6	539.3	539.1	538.9	538.7	538.9	539.1	539.3
142.5°	555.1	554.9	554.8	554.6	554.1	553.8	553.3	552.9	553.3	553.8	554.1
145°	576.3	576.3	576.3	576.1	575.8	575.4	575.2	574.8	575.2	575.4	575.8
147.5°	594.8	594.9	594.9	594.7	594.1	593.4	592.8	592.2	592.8	593.4	594.1
150°	606.5	606.6	606.8	606.6	606.2	605.7	605.2	604.8	605.2	605.7	606.2
152.5°	616.5	616.7	616.9	616.8	616.4	616.1	615.7	615.4	615.7	616.1	616.4
155°	629.9	630.3	630.5	630.7	630.5	630.4	630.4	630.3	630.4	630.4	630.5
157.5°	641.5	641.9	642.2	642.5	642.6	642.6	642.7	642.7	642.7	642.6	642.6
160°	648.3	648.4	648.5	648.7	649.1	649.3	649.7	650.1	649.7	649.3	649.1
162.5°	654.3	654.4	654.6	654.9	655.3	655.7	656.1	656.6	656.1	655.7	655.3
165°	662.3	662.3	662.3	662.5	663.1	663.7	664.2	664.8	664.2	663.7	663.1
167.5°	668.5	668.6	668.6	669.0	669.6	670.1	670.7	671.3	670.7	670.1	669.6
170°	672.2	672.1	672.0	672.3	673.0	673.6	674.3	675.0	674.3	673.6	673.0
172.5°	674.7	674.6	674.4	674.8	675.4	676.1	676.7	677.4	676.7	676.1	675.4
175°	677.3	677.2	677.1	677.3	678.1	678.7	679.4	680.1	679.4	678.7	678.1
177.5°	678.9	678.7	678.5	678.8	679.4	680.0	680.6	681.3	680.6	680.0	679.4
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	845.6	842.8	839.2	835.0	830.0	825.6	823.7	825.3	826.2	823.9	823.7
5°	819.8	811.2	804.2	793.8	785.5	778.6	773.6	771.6	772.3	766.8	765.4
7.5°	790.9	780.6	769.3	756.9	745.4	735.2	729.9	726.9	721.0	718.5	714.3
10°	772.3	758.4	747.3	732.7	719.6	707.4	701.5	696.7	690.8	688.0	682.1
12.5°	753.1	737.1	724.9	709.7	696.2	681.6	676.0	667.0	657.7	651.9	644.4
15°	726.1	706.8	691.8	673.8	657.8	641.1	626.2	609.6	603.3	590.1	582.6
17.5°	694.6	674.8	656.4	632.2	607.6	586.9	571.0	555.1	545.5	537.1	533.2
20°	673.8	655.8	630.1	602.0	574.5	551.6	538.8	528.4	518.0	512.1	507.9
22.5°	654.1	631.1	601.2	570.9	543.5	525.6	514.7	504.0	495.5	489.9	484.4
25°	621.1	590.8	559.3	524.6	505.9	490.3	478.4	469.8	464.6	457.3	454.5
27.5°	587.1	550.5	515.7	492.4	472.9	458.6	448.4	441.8	435.2	430.5	427.0
30°	561.0	523.9	492.7	470.5	450.7	438.9	430.5	422.9	417.8	413.9	411.2
32.5°	535.2	498.1	471.8	448.0	432.4	420.9	412.0	406.3	402.2	397.3	395.6
35°	497.8	464.9	442.0	420.5	404.6	394.1	387.2	381.3	377.8	376.5	375.4
37.5°	462.0	435.0	410.4	392.7	378.5	370.3	362.1	359.3	356.9	354.4	355.5
40°	439.3	413.9	392.1	373.4	361.9	352.8	347.9	344.6	342.4	342.4	342.4
42.5°	419.5	394.8	373.4	356.7	345.2	337.6	332.2	329.2	328.6	328.2	329.9
45°	389.0	366.0	344.6	330.6	320.9	313.3	310.1	307.7	307.7	309.2	309.5
47.5°	358.6	337.2	319.9	304.3	295.4	290.7	287.9	286.7	286.9	288.2	289.8
50°	340.0	318.9	301.8	287.9	279.6	275.1	272.7	272.0	272.7	272.7	275.1
52.5°	319.8	300.8	284.1	272.4	263.0	258.8	257.4	256.5	256.9	258.0	259.0
55°	290.1	273.0	257.1	246.0	239.1	236.3	233.2	233.5	232.8	233.5	233.5
57.5°	260.3	245.0	230.2	221.3	215.3	211.2	207.9	208.7	207.8	207.6	207.1
60°	241.1	224.4	212.7	204.7	197.8	194.3	191.2	191.9	190.8	190.1	188.8
62.5°	220.3	206.4	195.2	187.5	181.9	177.9	174.8	174.1	171.7	169.3	166.2
65°	190.1	178.7	168.6	161.3	156.1	153.0	150.6	148.5	143.3	137.8	135.0
67.5°	160.8	152.5	143.1	137.0	132.8	128.7	124.0	120.5	115.6	112.5	110.8
70°	141.9	133.9	125.9	120.0	115.6	111.7	106.5	104.1	100.6	99.2	97.5
72.5°	123.9	116.5	109.0	103.7	98.9	95.9	91.8	89.3	87.8	87.3	85.5
75°	96.5	90.6	85.0	80.2	76.3	74.3	72.5	70.8	70.1	67.0	65.2
77.5°	70.4	66.4	63.0	59.6	56.8	55.5	52.1	50.1	49.0	47.4	47.1
80°	54.8	52.1	48.6	46.5	42.7	41.3	39.9	39.6	39.2	38.9	38.5
82.5°	41.2	38.4	35.0	33.7	32.7	31.8	31.0	30.7	30.3	30.5	30.5
85°	20.8	19.4	19.4	19.1	18.7	18.4	18.0	18.0	17.7	18.0	17.7
87.5°	8.2	8.2	8.4	8.0	8.5	8.6	8.5	8.6	9.0	8.6	8.7
90°	6.5	7.6	8.5	9.4	10.3	11.1	11.9	12.6	13.2	13.9	14.4
92.5°	6.7	7.1	8.1	9.0	9.9	10.8	11.5	12.1	12.8	13.5	13.8
95°	12.6	10.7	10.9	11.0	11.1	11.1	11.9	12.6	13.2	13.9	14.3
97.5°	69.0	63.8	51.3	38.7	26.0	13.5	13.5	13.6	13.6	13.7	13.8
100°	91.6	84.8	69.2	53.6	38.0	22.4	20.4	18.5	16.6	14.7	13.8
102.5°	116.3	116.0	114.0	111.9	109.9	107.8	87.1	66.3	45.7	24.9	14.5
105°	155.8	156.4	157.0	157.6	158.1	158.7	159.7	160.8	161.8	162.7	161.2
107.5°	194.2	194.7	195.6	196.4	197.1	197.9	198.4	198.9	199.4	199.8	200.3
110°	221.1	221.6	222.3	222.9	223.6	224.4	224.5	224.8	225.0	225.2	225.5



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	248.3	248.7	249.0	249.3	249.7	249.9	249.9	249.9	249.9	249.8	249.9
115°	287.2	287.3	287.2	287.1	287.0	286.9	287.1	287.3	287.6	287.8	287.9
117.5°	323.8	324.1	324.4	324.7	324.9	325.1	325.1	325.0	325.0	324.9	324.9
120°	348.2	348.4	348.3	348.1	348.0	347.9	348.1	348.4	348.6	348.8	348.8
122.5°	370.2	370.5	370.7	370.8	371.0	371.1	371.2	371.4	371.5	371.7	371.6
125°	403.7	403.8	403.5	403.3	403.1	402.9	403.2	403.5	403.9	404.2	404.5
127.5°	433.2	433.5	434.1	434.5	435.1	435.6	435.5	435.5	435.4	435.3	435.2
130°	453.2	453.3	453.7	454.1	454.4	454.8	454.9	455.0	455.0	455.2	455.2
132.5°	471.8	472.2	472.6	473.0	473.4	473.9	473.9	474.1	474.2	474.3	474.3
135°	498.0	498.2	498.6	499.1	499.5	500.0	500.2	500.4	500.7	500.9	501.1
137.5°	523.0	523.3	523.7	524.2	524.8	525.2	525.5	525.8	526.0	526.2	526.3
140°	539.6	539.8	540.0	540.3	540.5	540.7	541.0	541.4	541.7	542.1	542.2
142.5°	554.6	554.8	554.9	555.1	555.2	555.4	555.6	555.8	556.1	556.3	556.5
145°	576.1	576.3	576.3	576.3	576.3	576.3	576.4	576.5	576.7	576.8	576.9
147.5°	594.7	594.9	594.9	594.8	594.6	594.5	594.6	594.7	594.8	594.9	594.9
150°	606.6	606.8	606.6	606.5	606.5	606.3	606.3	606.3	606.3	606.3	606.4
152.5°	616.8	616.9	616.7	616.5	616.3	616.1	616.3	616.4	616.6	616.8	616.9
155°	630.7	630.5	630.3	629.9	629.5	629.2	629.6	630.1	630.5	631.0	631.1
157.5°	642.5	642.2	641.9	641.5	641.1	640.7	641.3	641.9	642.5	643.0	643.0
160°	648.7	648.5	648.4	648.3	648.1	648.0	648.7	649.3	650.1	650.8	650.8
162.5°	654.9	654.6	654.4	654.3	654.2	654.2	654.8	655.5	656.1	656.8	656.8
165°	662.5	662.3	662.3	662.3	662.3	662.3	663.2	664.1	664.9	665.9	665.8
167.5°	669.0	668.6	668.6	668.5	668.4	668.3	669.4	670.4	671.4	672.3	672.3
170°	672.3	672.0	672.1	672.2	672.3	672.4	673.3	674.2	675.1	676.1	675.9
172.5°	674.8	674.4	674.6	674.7	674.8	674.8	675.8	676.7	677.6	678.5	678.3
175°	677.3	677.1	677.2	677.3	677.4	677.5	678.5	679.6	680.6	681.6	681.4
177.5°	678.8	678.5	678.7	678.9	679.0	679.2	680.0	680.7	681.4	682.2	682.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	822.0	822.5	820.6	820.0	820.6	822.5	822.0	823.7	823.9	826.2	825.3
5°	762.6	761.9	760.2	760.5	760.2	761.9	762.6	765.4	766.8	772.3	771.6
7.5°	711.8	709.1	709.9	707.0	709.9	709.1	711.8	714.3	718.5	721.0	726.9
10°	680.7	676.9	673.8	671.0	673.8	676.9	680.7	682.1	688.0	690.8	696.7
12.5°	638.3	635.0	630.7	631.6	630.7	635.0	638.3	644.4	651.9	657.7	667.0
15°	578.0	572.8	564.5	565.5	564.5	572.8	578.0	582.6	590.1	603.3	609.6
17.5°	527.0	527.1	523.3	524.1	523.3	527.1	527.0	533.2	537.1	545.5	555.1
20°	500.6	498.2	498.6	497.5	498.6	498.2	500.6	507.9	512.1	518.0	528.4
22.5°	482.3	479.4	476.9	474.7	476.9	479.4	482.3	484.4	489.9	495.5	504.0
25°	451.4	449.3	446.2	445.5	446.2	449.3	451.4	454.5	457.3	464.6	469.8
27.5°	424.2	423.7	422.5	420.9	422.5	423.7	424.2	427.0	430.5	435.2	441.8
30°	408.3	407.7	407.0	405.9	407.0	407.7	408.3	411.2	413.9	417.8	422.9
32.5°	394.2	393.8	393.1	393.2	393.1	393.8	394.2	395.6	397.3	402.2	406.3
35°	374.0	373.6	373.0	372.6	373.0	373.6	374.0	375.4	376.5	377.8	381.3
37.5°	355.2	356.1	355.6	355.5	355.6	356.1	355.2	355.5	354.4	356.9	359.3
40°	342.1	342.4	343.1	342.8	343.1	342.4	342.1	342.4	342.4	342.4	344.6
42.5°	331.3	331.4	332.3	331.1	332.3	331.4	331.3	329.9	328.2	328.6	329.2
45°	311.9	314.0	313.6	313.6	313.6	314.0	311.9	309.5	309.2	307.7	307.7
47.5°	290.7	292.6	293.0	292.9	293.0	292.6	290.7	289.8	288.2	286.9	286.7
50°	276.9	276.2	277.2	276.9	277.2	276.2	276.9	275.1	272.7	272.7	272.0
52.5°	259.9	260.1	260.0	259.7	260.0	260.1	259.9	259.0	258.0	256.9	256.5
55°	233.8	234.2	233.5	233.8	233.5	234.2	233.8	233.5	233.5	232.8	233.5
57.5°	205.5	203.8	204.6	203.8	204.6	203.8	205.5	207.1	207.6	207.8	208.7
60°	185.3	182.5	181.8	180.4	181.8	182.5	185.3	188.8	190.1	190.8	191.9
62.5°	162.5	160.6	158.2	159.3	158.2	160.6	162.5	166.2	169.3	171.7	174.1
65°	132.2	130.8	129.7	131.2	129.7	130.8	132.2	135.0	137.8	143.3	148.5
67.5°	109.4	108.7	108.7	108.0	108.7	108.7	109.4	110.8	112.5	115.6	120.5
70°	97.5	96.5	96.5	95.8	96.5	96.5	97.5	97.5	99.2	100.6	104.1
72.5°	85.2	84.3	84.5	84.1	84.5	84.3	85.2	85.5	87.3	87.8	89.3
75°	63.1	61.4	61.4	61.8	61.4	61.4	63.1	65.2	67.0	70.1	70.8
77.5°	47.1	46.7	47.3	46.6	47.3	46.7	47.1	47.1	47.4	49.0	50.1
80°	38.5	38.2	37.8	38.9	37.8	38.2	38.5	38.5	38.9	39.2	39.6
82.5°	29.9	29.9	29.8	31.1	29.8	29.9	29.9	30.5	30.5	30.3	30.7
85°	18.0	17.4	18.0	17.4	18.0	17.4	18.0	17.7	18.0	17.7	18.0
87.5°	9.3	9.1	8.8	9.2	8.8	9.1	9.3	8.7	8.6	9.0	8.6
90°	14.6	14.8	15.1	15.2	15.1	14.8	14.6	14.4	13.9	13.2	12.6
92.5°	13.9	13.9	14.0	14.0	14.0	13.9	13.9	13.8	13.5	12.8	12.1
95°	14.4	14.5	14.6	14.7	14.6	14.5	14.4	14.3	13.9	13.2	12.6
97.5°	13.9	14.0	14.1	14.3	14.1	14.0	13.9	13.8	13.7	13.6	13.6
100°	13.9	14.0	14.1	14.3	14.1	14.0	13.9	13.8	14.7	16.6	18.5
102.5°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.5	24.9	45.7	66.3
105°	157.2	153.1	149.0	145.0	149.0	153.1	157.2	161.2	162.7	161.8	160.8
107.5°	200.7	201.2	201.6	202.1	201.6	201.2	200.7	200.3	199.8	199.4	198.9
110°	225.9	226.1	226.5	226.9	226.5	226.1	225.9	225.5	225.2	225.0	224.8



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	250.4	250.8	251.3	251.6	251.3	250.8	250.4	249.9	249.8	249.9	249.9
115°	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.9	287.8	287.6	287.3
117.5°	324.9	324.9	324.8	324.8	324.8	324.9	324.9	324.9	324.9	325.0	325.0
120°	348.6	348.4	348.1	347.9	348.1	348.4	348.6	348.8	348.8	348.6	348.4
122.5°	371.4	371.1	371.0	370.7	371.0	371.1	371.4	371.6	371.7	371.5	371.4
125°	404.6	404.7	404.7	404.9	404.7	404.7	404.6	404.5	404.2	403.9	403.5
127.5°	435.2	435.1	435.0	434.9	435.0	435.1	435.2	435.2	435.3	435.4	435.5
130°	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.2	455.0	455.0
132.5°	474.2	474.1	474.0	473.9	474.0	474.1	474.2	474.3	474.3	474.2	474.1
135°	501.3	501.6	501.9	502.0	501.9	501.6	501.3	501.1	500.9	500.7	500.4
137.5°	526.3	526.2	526.1	526.0	526.1	526.2	526.3	526.3	526.2	526.0	525.8
140°	542.4	542.5	542.6	542.7	542.6	542.5	542.4	542.2	542.1	541.7	541.4
142.5°	556.5	556.5	556.5	556.6	556.5	556.5	556.5	556.5	556.3	556.1	555.8
145°	577.1	577.4	577.7	577.8	577.7	577.4	577.1	576.9	576.8	576.7	576.5
147.5°	595.1	595.2	595.3	595.4	595.3	595.2	595.1	594.9	594.9	594.8	594.7
150°	606.5	606.6	606.7	606.8	606.7	606.6	606.5	606.4	606.3	606.3	606.3
152.5°	616.8	616.7	616.6	616.6	616.6	616.7	616.8	616.9	616.8	616.6	616.4
155°	630.7	630.4	630.1	629.7	630.1	630.4	630.7	631.1	631.0	630.5	630.1
157.5°	642.5	641.9	641.3	640.7	641.3	641.9	642.5	643.0	643.0	642.5	641.9
160°	650.1	649.3	648.7	648.0	648.7	649.3	650.1	650.8	650.8	650.1	649.3
162.5°	656.0	655.2	654.5	653.7	654.5	655.2	656.0	656.8	656.8	656.1	655.5
165°	664.8	663.8	662.8	661.7	662.8	663.8	664.8	665.8	665.9	664.9	664.1
167.5°	671.2	670.0	668.9	667.8	668.9	670.0	671.2	672.3	672.3	671.4	670.4
170°	674.8	673.7	672.5	671.5	672.5	673.7	674.8	675.9	676.1	675.1	674.2
172.5°	677.2	675.9	674.7	673.4	674.7	675.9	677.2	678.3	678.5	677.6	676.7
175°	680.1	678.7	677.3	676.0	677.3	678.7	680.1	681.4	681.6	680.6	679.6
177.5°	680.9	679.8	678.7	677.6	678.7	679.8	680.9	682.0	682.2	681.4	680.7
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	823.7	825.6	830.0	835.0	839.2	842.8	845.6	849.4	853.1	858.1	862.8
5°	773.6	778.6	785.5	793.8	804.2	811.2	819.8	827.5	838.6	849.7	860.4
7.5°	729.9	735.2	745.4	756.9	769.3	780.6	790.9	804.3	819.0	835.3	853.3
10°	701.5	707.4	719.6	732.7	747.3	758.4	772.3	788.3	804.9	824.7	846.9
12.5°	676.0	681.6	696.2	709.7	724.9	737.1	753.1	769.4	791.6	813.1	838.3
15°	626.2	641.1	657.8	673.8	691.8	706.8	726.1	742.8	764.0	794.2	823.0
17.5°	571.0	586.9	607.6	632.2	656.4	674.8	694.6	715.2	740.5	771.2	804.5
20°	538.8	551.6	574.5	602.0	630.1	655.8	673.8	696.7	722.7	756.0	790.3
22.5°	514.7	525.6	543.5	570.9	601.2	631.1	654.1	676.7	705.5	738.8	776.2
25°	478.4	490.3	505.9	524.6	559.3	590.8	621.1	647.0	677.6	710.9	752.5
27.5°	448.4	458.6	472.9	492.4	515.7	550.5	587.1	616.8	648.1	683.9	725.5
30°	430.5	438.9	450.7	470.5	492.7	523.9	561.0	595.8	627.3	664.4	707.8
32.5°	412.0	420.9	432.4	448.0	471.8	498.1	535.2	573.2	606.7	644.7	687.2
35°	387.2	394.1	404.6	420.5	442.0	464.9	497.8	537.1	572.5	613.1	653.6
37.5°	362.1	370.3	378.5	392.7	410.4	435.0	462.0	502.0	541.3	578.3	618.0
40°	347.9	352.8	361.9	373.4	392.1	413.9	439.3	478.4	517.6	554.5	594.3
42.5°	332.2	337.6	345.2	356.7	373.4	394.8	419.5	453.4	494.4	530.0	566.3
45°	310.1	313.3	320.9	330.6	344.6	366.0	389.0	419.1	457.6	491.6	523.5
47.5°	287.9	290.7	295.4	304.3	319.9	337.2	358.6	385.7	419.5	453.4	480.5
50°	272.7	275.1	279.6	287.9	301.8	318.9	340.0	364.3	394.5	427.1	449.6
52.5°	257.4	258.8	263.0	272.4	284.1	300.8	319.8	342.1	370.3	397.4	420.3
55°	233.2	236.3	239.1	246.0	257.1	273.0	290.1	311.2	333.1	356.0	375.4
57.5°	207.9	211.2	215.3	221.3	230.2	245.0	260.3	277.4	296.0	315.1	331.4
60°	191.2	194.3	197.8	204.7	212.7	224.4	241.1	256.0	270.3	287.6	303.9
62.5°	174.8	177.9	181.9	187.5	195.2	206.4	220.3	233.3	248.1	263.2	275.4
65°	150.6	153.0	156.1	161.3	168.6	178.7	190.1	200.2	213.4	224.4	235.6
67.5°	124.0	128.7	132.8	137.0	143.1	152.5	160.8	170.4	179.4	187.6	197.8
70°	106.5	111.7	115.6	120.0	125.9	133.9	141.9	148.5	155.8	163.7	172.8
72.5°	91.8	95.9	98.9	103.7	109.0	116.5	123.9	129.3	135.3	140.7	149.5
75°	72.5	74.3	76.3	80.2	85.0	90.6	96.5	101.3	104.8	109.6	115.9
77.5°	52.1	55.5	56.8	59.6	63.0	66.4	70.4	74.5	77.8	79.5	84.3
80°	39.9	41.3	42.7	46.5	48.6	52.1	54.8	58.7	60.0	61.8	66.3
82.5°	31.0	31.8	32.7	33.7	35.0	38.4	41.2	43.6	45.0	45.7	49.0
85°	18.0	18.4	18.7	19.1	19.4	19.4	20.8	22.6	25.0	25.0	26.0
87.5°	8.5	8.6	8.5	8.0	8.4	8.2	8.2	8.0	8.6	9.2	9.7
90°	11.9	11.1	10.3	9.4	8.5	7.6	6.5	5.3	4.0	2.8	1.5
92.5°	11.5	10.8	9.9	9.0	8.1	7.1	6.7	6.6	6.5	6.5	6.4
95°	11.9	11.1	11.1	11.0	10.9	10.7	12.6	16.4	20.3	24.2	28.0
97.5°	13.5	13.5	26.0	38.7	51.3	63.8	69.0	66.6	64.2	61.8	59.4
100°	20.4	22.4	38.0	53.6	69.2	84.8	91.6	89.5	87.5	85.4	83.4
102.5°	87.1	107.8	109.9	111.9	114.0	116.0	116.3	114.8	113.2	111.7	110.3
105°	159.7	158.7	158.1	157.6	157.0	156.4	155.8	155.2	154.4	153.8	153.1
107.5°	198.4	197.9	197.1	196.4	195.6	194.7	194.2	193.9	193.6	193.2	192.9
110°	224.5	224.4	223.6	222.9	222.3	221.6	221.1	220.8	220.4	220.1	219.7



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	249.9	249.9	249.7	249.3	249.0	248.7	248.3	247.6	247.0	246.4	245.8
115°	287.1	286.9	287.0	287.1	287.2	287.3	287.2	286.9	286.5	286.2	285.9
117.5°	325.1	325.1	324.9	324.7	324.4	324.1	323.8	323.3	322.9	322.4	322.0
120°	348.1	347.9	348.0	348.1	348.3	348.4	348.2	347.8	347.3	346.9	346.4
122.5°	371.2	371.1	371.0	370.8	370.7	370.5	370.2	370.0	369.7	369.4	369.2
125°	403.2	402.9	403.1	403.3	403.5	403.8	403.7	403.2	402.8	402.3	401.8
127.5°	435.5	435.6	435.1	434.5	434.1	433.5	433.2	433.1	433.0	432.8	432.7
130°	454.9	454.8	454.4	454.1	453.7	453.3	453.2	453.1	452.9	452.8	452.7
132.5°	473.9	473.9	473.4	473.0	472.6	472.2	471.8	471.6	471.4	471.2	471.0
135°	500.2	500.0	499.5	499.1	498.6	498.2	498.0	498.1	498.3	498.4	498.5
137.5°	525.5	525.2	524.8	524.2	523.7	523.3	523.0	522.9	522.9	522.8	522.8
140°	541.0	540.7	540.5	540.3	540.0	539.8	539.6	539.3	539.1	538.9	538.7
142.5°	555.6	555.4	555.2	555.1	554.9	554.8	554.6	554.1	553.8	553.3	552.9
145°	576.4	576.3	576.3	576.3	576.3	576.3	576.1	575.8	575.4	575.2	574.8
147.5°	594.6	594.5	594.6	594.8	594.9	594.9	594.7	594.1	593.4	592.8	592.2
150°	606.3	606.3	606.5	606.5	606.6	606.8	606.6	606.2	605.7	605.2	604.8
152.5°	616.3	616.1	616.3	616.5	616.7	616.9	616.8	616.4	616.1	615.7	615.4
155°	629.6	629.2	629.5	629.9	630.3	630.5	630.7	630.5	630.4	630.4	630.3
157.5°	641.3	640.7	641.1	641.5	641.9	642.2	642.5	642.6	642.6	642.7	642.7
160°	648.7	648.0	648.1	648.3	648.4	648.5	648.7	649.1	649.3	649.7	650.1
162.5°	654.8	654.2	654.2	654.3	654.4	654.6	654.9	655.3	655.7	656.1	656.6
165°	663.2	662.3	662.3	662.3	662.3	662.3	662.5	663.1	663.7	664.2	664.8
167.5°	669.4	668.3	668.4	668.5	668.6	668.6	669.0	669.6	670.1	670.7	671.3
170°	673.3	672.4	672.3	672.2	672.1	672.0	672.3	673.0	673.6	674.3	675.0
172.5°	675.8	674.8	674.8	674.7	674.6	674.4	674.8	675.4	676.1	676.7	677.4
175°	678.5	677.5	677.4	677.3	677.2	677.1	677.3	678.1	678.7	679.4	680.1
177.5°	680.0	679.2	679.0	678.9	678.7	678.5	678.8	679.4	680.0	680.6	681.3
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	866.4	868.9	871.6	876.9	881.4	883.3	887.3	890.0	889.1	893.0	899.7
5°	869.8	879.1	889.9	901.0	913.5	923.9	932.3	940.6	947.2	955.1	967.0
7.5°	869.2	885.9	904.0	923.9	944.4	962.1	978.5	995.1	1009.9	1026.1	1047.2
10°	867.0	889.2	911.8	937.8	963.9	988.5	1010.7	1031.4	1051.2	1072.4	1099.1
12.5°	864.5	890.0	917.3	948.6	981.1	1010.7	1036.8	1066.8	1091.5	1118.7	1149.7
15°	853.5	887.9	925.0	965.5	1004.4	1044.3	1080.0	1116.9	1151.2	1183.7	1222.6
17.5°	840.9	880.5	924.3	972.2	1019.0	1067.4	1109.8	1156.2	1191.2	1235.0	1271.1
20°	830.6	873.3	920.1	973.8	1027.0	1080.8	1127.6	1174.7	1214.3	1258.4	1304.2
22.5°	818.1	865.0	915.7	971.3	1027.0	1085.7	1137.6	1184.5	1233.5	1283.1	1330.3
25°	798.0	846.6	900.4	961.4	1025.2	1085.2	1140.8	1199.1	1251.8	1305.6	1347.9
27.5°	773.3	824.3	881.0	944.0	1009.5	1070.9	1136.3	1198.5	1251.5	1303.2	1340.2
30°	753.6	807.4	861.8	925.7	993.6	1059.6	1129.6	1191.8	1247.6	1294.1	1314.9
32.5°	733.3	784.3	840.4	905.1	974.8	1045.7	1115.3	1178.8	1230.4	1258.3	1258.8
35°	698.0	745.9	804.2	867.7	939.1	1016.2	1086.6	1149.1	1180.6	1183.1	1149.1
37.5°	659.6	703.6	758.6	822.2	900.4	977.0	1048.9	1090.6	1101.2	1065.9	1003.0
40°	632.1	672.7	725.9	791.0	868.8	947.9	1013.4	1043.9	1032.9	975.6	905.5
42.5°	603.2	641.1	692.2	756.6	834.6	914.5	970.4	986.8	957.3	891.3	809.2
45°	556.2	590.8	641.5	706.4	781.3	856.3	898.6	890.3	841.3	762.9	671.0
47.5°	507.1	540.6	586.2	646.2	723.0	787.6	816.3	791.2	721.6	635.3	560.5
50°	474.7	509.0	551.0	608.2	678.3	740.7	759.1	720.9	643.5	560.7	492.0
52.5°	442.7	472.1	513.2	568.5	635.5	688.3	698.0	654.1	574.2	499.9	439.0
55°	394.1	420.9	455.6	507.6	565.5	610.3	605.1	548.5	476.0	412.5	364.6
57.5°	347.1	367.3	399.3	448.1	499.0	529.1	510.0	461.8	394.2	342.2	301.8
60°	316.1	334.8	364.6	407.3	452.1	469.0	453.1	400.7	347.3	299.8	265.7
62.5°	286.7	303.2	328.9	368.5	404.6	414.6	397.6	351.9	303.7	263.1	235.0
65°	243.9	259.1	281.1	309.2	334.1	338.9	327.9	281.1	244.6	210.6	191.2
67.5°	205.1	215.1	232.2	256.5	269.7	272.6	251.1	221.7	189.6	168.7	154.1
70°	179.1	185.9	201.9	215.1	225.9	226.2	206.4	182.8	158.2	141.2	130.5
72.5°	153.7	160.4	172.5	181.6	189.8	187.1	169.0	150.3	130.5	117.6	109.6
75°	118.7	124.6	130.8	135.0	135.0	131.5	118.3	104.4	93.0	85.3	82.9
77.5°	86.2	91.1	93.2	92.6	91.3	85.9	77.6	68.5	64.4	60.8	58.9
80°	67.7	69.7	70.4	68.7	66.6	60.4	54.8	51.0	47.2	45.8	45.1
82.5°	50.2	52.0	50.2	50.6	46.1	40.9	37.9	36.6	35.0	34.4	33.7
85°	26.8	26.4	25.7	23.9	20.8	20.2	19.8	19.4	18.7	19.1	18.4
87.5°	9.7	9.1	8.3	8.2	8.5	8.1	8.6	8.7	8.9	8.7	9.5
90°	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9	12.6
92.5°	6.5	6.5	6.6	6.7	7.1	8.1	9.0	9.9	10.8	11.5	12.1
95°	24.2	20.3	16.4	12.6	10.7	10.9	11.0	11.1	11.1	11.9	12.6
97.5°	61.8	64.2	66.6	69.0	63.8	51.3	38.7	26.0	13.5	13.5	13.6
100°	85.4	87.5	89.5	91.6	84.8	69.2	53.6	38.0	22.4	20.4	18.5
102.5°	111.7	113.2	114.8	116.3	116.0	114.0	111.9	109.9	107.8	87.1	66.3
105°	153.8	154.4	155.2	155.8	156.4	157.0	157.6	158.1	158.7	159.7	160.8
107.5°	193.2	193.6	193.9	194.2	194.7	195.6	196.4	197.1	197.9	198.4	198.9
110°	220.1	220.4	220.8	221.1	221.6	222.3	222.9	223.6	224.4	224.5	224.8



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	246.4	247.0	247.6	248.3	248.7	249.0	249.3	249.7	249.9	249.9	249.9
115°	286.2	286.5	286.9	287.2	287.3	287.2	287.1	287.0	286.9	287.1	287.3
117.5°	322.4	322.9	323.3	323.8	324.1	324.4	324.7	324.9	325.1	325.1	325.0
120°	346.9	347.3	347.8	348.2	348.4	348.3	348.1	348.0	347.9	348.1	348.4
122.5°	369.4	369.7	370.0	370.2	370.5	370.7	370.8	371.0	371.1	371.2	371.4
125°	402.3	402.8	403.2	403.7	403.8	403.5	403.3	403.1	402.9	403.2	403.5
127.5°	432.8	433.0	433.1	433.2	433.5	434.1	434.5	435.1	435.6	435.5	435.5
130°	452.8	452.9	453.1	453.2	453.3	453.7	454.1	454.4	454.8	454.9	455.0
132.5°	471.2	471.4	471.6	471.8	472.2	472.6	473.0	473.4	473.9	473.9	474.1
135°	498.4	498.3	498.1	498.0	498.2	498.6	499.1	499.5	500.0	500.2	500.4
137.5°	522.8	522.9	522.9	523.0	523.3	523.7	524.2	524.8	525.2	525.5	525.8
140°	538.9	539.1	539.3	539.6	539.8	540.0	540.3	540.5	540.7	541.0	541.4
142.5°	553.3	553.8	554.1	554.6	554.8	554.9	555.1	555.2	555.4	555.6	555.8
145°	575.2	575.4	575.8	576.1	576.3	576.3	576.3	576.3	576.3	576.4	576.5
147.5°	592.8	593.4	594.1	594.7	594.9	594.9	594.8	594.6	594.5	594.6	594.7
150°	605.2	605.7	606.2	606.6	606.8	606.6	606.5	606.5	606.3	606.3	606.3
152.5°	615.7	616.1	616.4	616.8	616.9	616.7	616.5	616.3	616.1	616.3	616.4
155°	630.4	630.4	630.5	630.7	630.5	630.3	629.9	629.5	629.2	629.6	630.1
157.5°	642.7	642.6	642.6	642.5	642.2	641.9	641.5	641.1	640.7	641.3	641.9
160°	649.7	649.3	649.1	648.7	648.5	648.4	648.3	648.1	648.0	648.7	649.3
162.5°	656.1	655.7	655.3	654.9	654.6	654.4	654.3	654.2	654.2	654.8	655.5
165°	664.2	663.7	663.1	662.5	662.3	662.3	662.3	662.3	662.3	663.2	664.1
167.5°	670.7	670.1	669.6	669.0	668.6	668.6	668.5	668.4	668.3	669.4	670.4
170°	674.3	673.6	673.0	672.3	672.0	672.1	672.2	672.3	672.4	673.3	674.2
172.5°	676.7	676.1	675.4	674.8	674.4	674.6	674.7	674.8	674.8	675.8	676.7
175°	679.4	678.7	678.1	677.3	677.1	677.2	677.3	677.4	677.5	678.5	679.6
177.5°	680.6	680.0	679.4	678.8	678.5	678.7	678.9	679.0	679.2	680.0	680.7
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	903.3	904.5	905.3	908.0	908.3	910.8	908.3
5°	978.0	982.9	990.5	998.2	998.9	1003.7	995.1
7.5°	1061.8	1073.1	1080.1	1092.4	1097.3	1100.4	1095.4
10°	1119.6	1130.0	1148.4	1157.4	1166.4	1167.8	1163.7
12.5°	1175.4	1191.9	1206.4	1223.5	1223.1	1235.3	1230.8
15°	1249.7	1266.7	1286.8	1305.9	1312.9	1312.9	1318.4
17.5°	1302.7	1333.9	1354.7	1369.7	1386.1	1388.9	1387.0
20°	1338.5	1372.2	1394.4	1413.8	1425.0	1428.1	1428.1
22.5°	1365.2	1393.8	1415.5	1433.0	1442.2	1445.8	1444.7
25°	1383.7	1408.3	1421.5	1426.6	1429.1	1428.3	1421.8
27.5°	1358.3	1357.3	1348.9	1332.9	1321.0	1313.7	1305.4
30°	1310.1	1292.0	1271.2	1248.3	1218.8	1196.2	1189.4
32.5°	1238.2	1197.7	1162.4	1124.3	1092.5	1070.0	1060.5
35°	1099.1	1034.9	982.6	936.7	903.5	882.6	875.7
37.5°	934.2	872.0	807.2	762.8	735.1	714.1	706.2
40°	829.2	761.5	705.0	663.3	634.9	614.5	614.1
42.5°	733.4	668.9	615.6	585.7	555.0	541.4	541.4
45°	600.6	548.8	503.7	480.2	461.8	450.7	447.5
47.5°	497.2	454.5	424.5	405.6	390.7	383.6	379.0
50°	439.3	401.8	377.8	361.5	353.2	344.2	343.5
52.5°	390.9	360.7	342.1	328.8	318.3	312.8	313.0
55°	328.6	304.6	291.4	281.3	273.0	268.9	267.2
57.5°	276.8	258.9	249.2	240.0	236.5	233.2	232.3
60°	244.6	232.5	223.5	216.2	211.0	209.9	209.6
62.5°	217.9	205.3	199.0	193.4	189.6	188.0	187.3
65°	179.7	170.3	164.8	160.3	158.9	156.5	156.1
67.5°	144.9	139.3	135.6	132.5	130.5	130.5	130.5
70°	123.5	120.4	117.3	115.6	114.5	113.8	113.8
72.5°	105.2	102.9	100.3	99.4	99.2	98.5	98.3
75°	80.2	77.8	78.0	76.3	74.9	73.2	72.1
77.5°	56.8	55.1	54.8	54.6	53.3	53.1	53.7
80°	44.1	42.4	42.0	42.4	42.0	40.9	40.9
82.5°	33.5	32.1	31.7	31.5	31.1	31.5	30.9
85°	18.0	17.4	17.4	17.4	18.0	17.7	17.4
87.5°	9.0	8.9	9.3	9.0	9.1	8.8	9.2
90°	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	12.8	13.5	13.8	13.9	13.9	14.0	14.0
95°	13.2	13.9	14.3	14.4	14.5	14.6	14.7
97.5°	13.6	13.7	13.8	13.9	14.0	14.1	14.3
100°	16.6	14.7	13.8	13.9	14.0	14.1	14.3
102.5°	45.7	24.9	14.5	14.6	14.6	14.6	14.6
105°	161.8	162.7	161.2	157.2	153.1	149.0	145.0
107.5°	199.4	199.8	200.3	200.7	201.2	201.6	202.1
110°	225.0	225.2	225.5	225.9	226.1	226.5	226.9



TEST NUMBER: P332901-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	249.9	249.8	249.9	250.4	250.8	251.3	251.6
115°	287.6	287.8	287.9	287.9	287.9	287.9	287.9
117.5°	325.0	324.9	324.9	324.9	324.9	324.8	324.8
120°	348.6	348.8	348.8	348.6	348.4	348.1	347.9
122.5°	371.5	371.7	371.6	371.4	371.1	371.0	370.7
125°	403.9	404.2	404.5	404.6	404.7	404.7	404.9
127.5°	435.4	435.3	435.2	435.2	435.1	435.0	434.9
130°	455.0	455.2	455.2	455.2	455.2	455.2	455.2
132.5°	474.2	474.3	474.3	474.2	474.1	474.0	473.9
135°	500.7	500.9	501.1	501.3	501.6	501.9	502.0
137.5°	526.0	526.2	526.3	526.3	526.2	526.1	526.0
140°	541.7	542.1	542.2	542.4	542.5	542.6	542.7
142.5°	556.1	556.3	556.5	556.5	556.5	556.5	556.6
145°	576.7	576.8	576.9	577.1	577.4	577.7	577.8
147.5°	594.8	594.9	594.9	595.1	595.2	595.3	595.4
150°	606.3	606.3	606.4	606.5	606.6	606.7	606.8
152.5°	616.6	616.8	616.9	616.8	616.7	616.6	616.6
155°	630.5	631.0	631.1	630.7	630.4	630.1	629.7
157.5°	642.5	643.0	643.0	642.5	641.9	641.3	640.7
160°	650.1	650.8	650.8	650.1	649.3	648.7	648.0
162.5°	656.1	656.8	656.8	656.0	655.2	654.5	653.7
165°	664.9	665.9	665.8	664.8	663.8	662.8	661.7
167.5°	671.4	672.3	672.3	671.2	670.0	668.9	667.8
170°	675.1	676.1	675.9	674.8	673.7	672.5	671.5
172.5°	677.6	678.5	678.3	677.2	675.9	674.7	673.4
175°	680.6	681.6	681.4	680.1	678.7	677.3	676.0
177.5°	681.4	682.2	682.0	680.9	679.8	678.7	677.6
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1

(END OF REPORT)