

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333144-927

Luminaire Tested: **S125DIP-S375D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333144-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1035U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4160.6 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2785	2785	2785	2785
5°	3225	2795	2447	2795
10°	3752	2781	2144	2781
15°	4153	2760	1978	2760
20°	4649	2728	1844	2728
25°	5447	2691	1779	2691
30°	5883	2655	1723	2655
35°	4837	2588	1686	2588
40°	3438	2494	1645	2494
45°	2641	2367	1621	2367
50°	2255	2210	1619	2210
55°	2008	2057	1633	2057
60°	1811	1888	1674	1888
65°	1673	1721	1718	1721
70°	1522	1545	1743	1545
75°	1342	1362	1727	1362
80°	1131	1112	1581	1112
85°	897	800	1275	800



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	1.0
10°-20°	123.6	3.0
20°-30°	200.7	4.8
30°-40°	244.8	5.9
40°-50°	222.7	5.4
50°-60°	177.4	4.3
60°-70°	123.6	3.0
70°-80°	65.9	1.6
80°-90°	18.8	0.5
90°-100°	284.3	6.8
100°-110°	611.2	14.7
110°-120°	573.6	13.8
120°-130°	464.9	11.2
130°-140°	373.0	9.0
140°-150°	281.5	6.8
150°-160°	198.2	4.8
160°-170°	116.8	2.8
170°-180°	38.0	0.9
0°-30°	365.9	8.8
0°-40°	610.7	14.7
0°-60°	1010.8	24.3
0°-90°	1219.1	29.3
90°-120°	1469.1	35.3
90°-150°	2588.5	62.2
90°-180°	2941.0	70.7
0°-180°	4160.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	498	431	378	431	498	50
15°	621	413	296	413	621	178
25°	764	378	250	378	764	349
35°	614	328	214	328	614	375
45°	289	259	178	259	289	231
55°	178	183	145	183	178	161
65°	110	113	112	113	110	109
75°	54	55	69	55	54	58
85°	12	11	17	11	12	14
90°	18	1	18	1	18	13
95°	186	26	186	26	186	263
105°	1048	89	1048	89	1048	1042
115°	1167	160	1167	160	1167	1140
125°	920	221	920	221	920	832
135°	764	259	764	259	764	592
145°	603	302	603	302	603	383
155°	505	345	505	345	505	236
165°	443	376	443	376	443	127
175°	398	391	398	391	398	39
180°	392	392	392	392	392	



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	456.1	455.6	455.0	453.8	454.7	452.2	451.1	449.0	446.5	445.6	444.6
5°	497.5	498.4	499.4	495.5	495.9	493.3	487.4	482.7	478.9	473.9	470.4
7.5°	547.3	545.2	544.9	542.5	538.2	534.7	528.6	520.8	513.2	504.5	497.4
10°	572.2	572.4	570.8	567.8	563.2	559.9	551.9	544.2	534.9	523.9	516.0
12.5°	591.0	591.8	589.6	585.7	583.4	576.1	569.7	560.6	549.5	540.7	528.8
15°	621.2	619.2	617.8	612.8	609.0	601.3	591.3	581.7	569.7	558.5	547.3
17.5°	650.5	652.1	649.4	644.8	632.9	623.9	610.5	597.4	582.3	567.4	554.1
20°	676.5	678.0	673.8	665.9	651.6	642.7	625.0	608.1	590.7	571.5	556.8
22.5°	709.1	707.9	702.2	690.2	677.9	661.3	642.1	621.5	599.8	578.1	558.6
25°	764.4	756.7	753.2	738.4	722.2	697.8	671.5	641.4	614.3	585.6	560.7
27.5°	795.1	792.7	788.8	778.5	761.4	735.3	704.3	667.7	629.5	593.2	560.5
30°	788.9	789.3	789.6	786.4	775.4	755.8	724.8	685.6	640.1	599.3	561.6
32.5°	734.4	741.1	747.5	755.0	758.1	754.3	735.0	699.4	652.7	606.3	561.0
35°	613.5	615.6	636.3	656.8	684.6	706.2	720.6	704.9	665.6	612.3	560.3
37.5°	478.4	488.3	502.6	525.8	565.9	601.9	648.2	669.4	656.7	614.3	559.0
40°	407.8	417.0	426.4	450.0	483.8	527.4	579.9	624.7	635.2	608.1	554.6
42.5°	353.4	360.6	371.0	388.7	417.0	455.6	505.8	564.4	600.5	590.3	545.4
45°	289.2	293.8	301.8	315.9	336.4	366.6	410.9	475.0	530.8	549.3	523.6
47.5°	247.6	247.6	253.8	263.5	278.3	304.0	336.8	386.9	446.6	490.7	488.6
50°	224.4	223.5	228.5	236.9	248.6	265.6	296.9	337.0	394.3	444.3	458.2
52.5°	204.5	204.6	207.6	213.9	223.7	238.2	261.6	297.8	346.7	398.0	424.2
55°	178.3	177.5	181.0	185.2	192.4	201.9	218.7	246.4	286.1	336.6	370.7
57.5°	154.2	156.3	157.6	160.6	166.5	172.9	187.1	207.4	238.9	282.3	318.2
60°	140.2	142.2	143.3	146.2	151.0	156.5	167.5	183.9	210.5	247.9	283.5
62.5°	127.6	129.2	129.6	132.2	136.1	141.4	150.0	163.9	184.9	217.5	252.5
65°	109.5	109.5	110.2	113.0	114.8	119.5	126.1	136.2	153.0	178.5	208.3
67.5°	92.0	92.8	92.7	93.9	95.5	99.3	103.9	112.3	124.8	143.3	167.2
70°	80.6	81.3	81.1	82.0	83.8	86.2	90.1	97.9	106.9	122.8	143.3
72.5°	70.3	70.6	70.1	71.3	72.4	74.5	78.8	83.0	91.3	104.8	121.7
75°	53.8	54.2	54.6	55.3	56.4	57.5	59.7	63.8	69.4	79.5	90.2
77.5°	40.3	39.6	40.6	40.4	41.0	41.9	43.8	46.0	50.5	57.0	65.3
80°	30.4	30.6	30.6	30.7	31.7	32.2	33.8	35.5	39.0	43.7	49.6
82.5°	22.2	22.7	22.3	22.7	23.4	23.8	24.8	26.1	28.1	31.9	36.1
85°	12.1	11.2	11.6	11.9	11.9	12.1	12.8	13.4	14.5	15.9	17.6
87.5°	7.1	7.4	7.4	7.4	7.6	7.3	7.7	7.5	7.8	8.1	8.4
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3	13.5	12.7	11.1
92.5°	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1	206.4	254.9	259.0
95°	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6	685.6	700.7	571.8
97.5°	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8	867.5	748.3	510.6
100°	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7	911.8	714.1	455.5
102.5°	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1	885.3	654.0	413.8
105°	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1	800.3	573.3	373.3
107.5°	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9	713.6	517.8	356.2
110°	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1	664.2	491.9	351.1



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2	627.6	476.7	351.1
115°	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0	587.6	460.3	353.5
117.5°	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0	563.7	452.2	358.7
120°	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2	550.4	448.4	363.8
122.5°	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1	539.0	445.2	368.2
125°	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3	523.6	441.2	375.7
127.5°	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0	509.3	439.3	384.0
130°	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2	499.8	438.1	389.1
132.5°	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4	492.2	438.1	394.7
135°	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8	483.2	438.1	402.5
137.5°	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4	475.2	439.0	409.6
140°	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9	471.3	439.7	412.8
142.5°	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7	468.2	440.3	414.7
145°	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9	463.4	439.7	416.8
147.5°	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8	458.5	437.6	417.6
150°	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1	454.7	435.7	417.6
152.5°	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8	450.3	433.2	416.9
155°	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3	442.8	428.6	415.2
157.5°	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8	435.9	423.9	413.1
160°	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5	430.2	420.7	411.2
162.5°	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6	425.2	416.9	409.3
165°	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9	417.6	411.2	406.5
167.5°	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7	410.1	405.7	402.0
170°	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6	405.7	402.5	400.1
172.5°	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9	401.2	398.7	397.6
175°	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8	395.4	394.6	394.6
177.5°	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5	392.8	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	443.7	442.7	441.5	439.4	437.0	435.6	433.6	432.3	429.7	427.5	425.1
5°	466.2	461.4	457.1	451.4	445.2	441.2	436.4	431.1	425.6	419.9	413.7
7.5°	489.6	481.1	472.0	462.2	452.5	443.6	435.1	426.9	419.1	409.7	401.8
10°	505.2	494.6	483.2	469.9	456.9	445.5	434.0	424.0	413.7	402.7	393.0
12.5°	520.9	506.8	490.7	476.0	460.4	446.7	433.2	420.3	407.4	395.2	383.9
15°	532.0	519.5	504.7	483.8	466.2	447.3	429.4	412.8	397.2	383.7	369.4
17.5°	539.2	523.2	507.2	487.3	464.2	443.1	422.8	403.7	386.2	369.0	355.3
20°	540.5	524.0	507.4	487.8	464.2	440.1	419.7	396.9	378.0	360.2	343.4
22.5°	540.1	521.4	503.3	483.2	460.1	437.8	413.3	390.0	369.5	352.0	334.5
25°	536.0	516.0	493.3	473.0	450.3	426.7	401.8	377.6	356.8	336.8	319.4
27.5°	532.5	506.7	480.9	457.2	435.3	413.7	389.8	365.1	342.0	321.8	305.4
30°	528.3	499.9	471.0	446.2	423.7	402.7	380.2	356.0	331.8	312.1	294.5
32.5°	524.5	491.4	460.9	434.0	410.1	389.7	368.9	345.9	322.2	302.1	284.6
35°	517.1	478.9	443.9	413.5	388.1	367.0	349.6	328.2	306.4	287.0	270.2
37.5°	507.8	462.4	424.8	393.0	365.1	342.9	326.8	310.3	289.4	270.7	255.5
40°	500.4	450.7	410.9	378.3	349.4	326.4	311.3	295.8	278.5	261.0	244.9
42.5°	491.2	440.1	396.9	361.8	333.2	310.7	294.9	281.8	266.4	250.2	235.3
45°	474.3	421.0	374.1	336.4	307.5	285.3	269.1	259.2	247.6	232.3	219.7
47.5°	449.3	398.1	349.6	310.7	280.8	260.3	245.0	235.5	227.4	216.0	204.5
50°	427.2	381.0	331.8	293.3	263.4	242.7	228.6	220.0	213.1	204.3	194.6
52.5°	402.5	359.4	314.4	276.2	246.7	226.3	212.5	204.9	199.2	192.9	183.3
55°	363.1	326.5	284.8	248.6	221.3	201.4	189.3	182.7	177.9	173.2	167.3
57.5°	319.9	291.2	254.3	221.1	196.0	177.8	166.6	160.2	156.5	154.0	150.6
60°	289.4	264.9	233.1	202.8	178.3	162.2	151.2	146.2	143.1	141.2	138.6
62.5°	261.1	241.0	211.5	183.9	162.5	147.3	137.4	132.6	129.7	128.7	126.6
65°	219.5	203.9	179.6	156.7	138.4	125.4	117.2	112.6	110.7	109.6	109.8
67.5°	178.4	169.0	149.4	129.9	115.3	104.4	97.8	94.3	93.3	91.9	91.9
70°	153.4	146.2	129.8	112.7	99.7	91.3	85.5	81.8	80.9	80.2	80.0
72.5°	131.3	125.0	110.7	97.1	85.4	78.0	73.2	71.0	69.5	69.1	69.0
75°	98.6	95.2	83.8	73.0	65.0	59.9	56.6	54.6	53.5	53.2	53.5
77.5°	70.1	67.1	59.9	52.2	47.1	43.3	40.5	39.8	38.6	38.6	38.4
80°	52.7	50.7	46.1	40.1	35.9	32.6	31.1	29.9	29.5	28.9	29.5
82.5°	38.2	36.0	33.0	29.1	25.6	23.7	22.2	21.8	21.5	21.3	21.4
85°	18.9	19.0	17.2	14.3	12.8	11.7	10.8	10.8	10.6	10.5	10.6
87.5°	8.5	7.9	7.1	6.4	5.3	4.6	4.1	4.1	3.8	4.0	4.4
90°	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8	1.6	3.2	4.8
92.5°	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7	11.7	18.4	28.1
95°	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1	26.9	33.2	41.9
97.5°	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3	44.3	48.7	57.4
100°	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4	57.0	60.1	68.8
102.5°	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7	69.6	72.1	81.4
105°	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4	89.4	93.3	101.2
107.5°	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6	111.2	114.9	121.4
110°	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1	125.7	128.9	136.0



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7	140.3	142.8	150.0
115°	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8	161.3	163.7	170.8
117.5°	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7	181.1	183.6	190.8
120°	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4	193.8	196.9	204.1
122.5°	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7	206.4	208.9	216.0
125°	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4	223.0	227.0	234.1
127.5°	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6	236.9	242.0	251.0
130°	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8	245.2	251.5	261.7
132.5°	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1	252.1	259.7	271.2
135°	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4	262.5	272.0	284.7
137.5°	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4	274.7	283.6	296.3
140°	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0	282.3	291.8	304.4
142.5°	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8	290.6	299.4	312.0
145°	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1	303.6	311.6	322.7
147.5°	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0	317.0	323.8	334.1
150°	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2	325.8	331.4	341.7
152.5°	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1	334.1	339.0	347.9
155°	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8	344.8	349.5	357.4
157.5°	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2	355.1	358.9	365.7
160°	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2	361.4	364.6	370.1
162.5°	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9	367.1	370.3	375.2
165°	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4	374.9	377.2	381.2
167.5°	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1	381.4	382.8	385.0
170°	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0	385.2	386.0	387.5
172.5°	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5	387.1	387.9	389.4
175°	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4	389.8	390.6	391.4
177.5°	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8	391.6	391.6	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	423.8	422.2	420.9	418.0	416.3	414.2	412.4	414.3	412.3	413.1	411.8
5°	410.6	405.4	401.8	396.5	391.9	387.7	384.6	384.0	382.5	381.8	379.6
7.5°	394.7	388.2	382.0	375.0	369.2	363.2	359.4	356.2	354.2	351.4	349.5
10°	385.3	376.7	369.4	361.0	353.6	347.2	342.1	339.5	337.2	333.7	332.4
12.5°	373.8	364.9	355.9	346.9	339.8	332.7	328.4	324.5	322.8	318.9	318.5
15°	359.9	346.5	337.7	328.6	318.9	313.0	309.3	305.1	303.3	300.6	298.6
17.5°	343.3	331.4	320.4	310.9	302.6	297.7	293.1	290.3	287.1	285.3	282.0
20°	331.3	320.0	309.0	298.9	292.5	286.8	283.2	280.4	277.1	276.2	272.9
22.5°	321.2	308.7	298.2	289.7	282.7	276.3	272.4	270.5	268.2	265.4	264.7
25°	304.8	291.8	282.8	274.4	268.2	262.3	259.6	257.2	255.0	252.9	252.2
27.5°	290.6	278.9	268.3	260.7	255.2	249.9	247.6	244.6	243.0	241.4	239.4
30°	280.6	268.7	259.4	252.1	246.2	241.5	238.8	236.9	235.4	233.9	232.8
32.5°	270.4	259.4	250.3	243.1	237.3	233.7	231.4	230.0	228.4	226.6	225.2
35°	256.8	244.7	235.9	229.7	225.1	222.4	219.8	218.6	216.7	216.7	215.2
37.5°	241.5	231.1	223.3	217.7	213.6	211.1	208.3	207.5	206.3	205.5	205.0
40°	232.5	222.8	215.5	209.8	205.4	203.4	201.1	199.7	199.0	198.0	197.7
42.5°	223.1	213.8	206.8	201.6	197.7	196.1	194.0	193.0	191.5	190.3	190.0
45°	208.8	199.9	193.5	189.3	186.0	183.9	182.7	180.5	179.7	178.3	178.1
47.5°	195.4	186.7	180.5	177.0	174.1	172.5	170.5	168.3	167.4	166.7	166.6
50°	185.2	177.4	171.5	168.3	165.5	163.1	161.1	159.6	159.1	159.1	159.5
52.5°	175.0	168.3	163.3	159.3	156.7	154.2	152.3	151.4	150.6	151.5	152.1
55°	160.0	153.2	149.6	145.7	143.1	140.2	139.3	138.9	138.4	139.8	140.6
57.5°	144.1	139.3	135.1	131.3	129.0	127.2	126.0	125.8	126.8	127.5	129.9
60°	134.0	128.5	124.7	121.8	119.0	117.9	117.5	117.2	117.9	119.9	123.0
62.5°	122.9	118.4	114.2	112.1	110.0	108.2	108.1	108.4	109.8	112.2	115.3
65°	106.5	102.7	100.0	97.4	95.7	94.7	95.0	95.7	97.4	100.5	103.9
67.5°	89.9	87.3	84.8	82.8	81.2	81.2	81.6	82.7	84.6	88.2	91.3
70°	79.3	76.4	74.3	73.4	72.1	71.4	72.5	74.3	76.0	79.3	82.0
72.5°	68.6	66.1	64.5	63.8	63.3	62.7	63.1	65.1	67.3	70.6	73.8
75°	52.7	51.8	50.7	50.0	49.4	49.8	50.1	52.0	53.8	57.3	60.9
77.5°	38.5	37.5	36.8	36.7	36.4	36.6	37.6	39.0	40.7	43.3	46.0
80°	29.1	28.8	28.4	28.2	28.2	28.4	29.9	30.7	32.4	34.8	37.0
82.5°	21.2	21.0	20.9	20.8	21.0	21.1	21.9	23.1	24.5	26.3	28.2
85°	11.2	10.8	11.3	11.6	11.2	11.7	12.1	12.8	13.4	14.3	15.2
87.5°	4.9	5.5	5.5	6.0	6.2	6.8	6.8	7.5	8.0	8.4	8.6
90°	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3	15.1	15.8	17.4
92.5°	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1	101.7	76.5	64.9
95°	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6	448.4	351.1	284.7
97.5°	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8	762.5	667.7	575.4
100°	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7	934.0	852.5	770.2
102.5°	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1	1038.9	999.9	944.2
105°	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1	1098.4	1133.2	1124.5
107.5°	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9	1045.4	1134.8	1176.1
110°	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1	985.3	1096.9	1164.1



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2	925.9	1038.6	1117.9
115°	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0	840.7	949.0	1035.1
117.5°	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0	781.6	875.0	954.0
120°	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2	748.1	835.1	904.7
122.5°	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1	724.1	801.5	866.7
125°	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3	692.0	760.7	817.7
127.5°	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0	661.3	725.5	778.8
130°	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2	639.8	701.5	752.9
132.5°	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4	619.5	675.5	725.0
135°	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8	588.4	639.0	684.0
137.5°	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4	560.5	602.6	640.9
140°	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9	544.1	580.4	613.7
142.5°	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7	530.1	561.5	590.3
145°	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9	512.5	536.9	558.3
147.5°	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8	497.7	516.6	532.7
150°	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1	489.5	504.5	518.8
152.5°	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8	481.3	495.0	506.1
155°	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3	469.0	480.1	488.7
157.5°	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8	457.2	465.8	472.6
160°	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5	448.4	456.3	461.8
162.5°	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6	440.8	447.4	452.3
165°	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9	429.4	434.2	438.1
167.5°	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7	418.4	422.0	424.8
170°	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6	412.0	414.4	416.0
172.5°	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9	406.3	408.1	409.0
175°	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8	397.8	399.3	399.3
177.5°	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5	394.1	394.1	394.1
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	410.9	411.9	411.1	412.3	411.1	411.9	410.9	411.8	413.1	412.3	414.3
5°	378.7	377.1	378.2	377.5	378.2	377.1	378.7	379.6	381.8	382.5	384.0
7.5°	349.0	347.5	345.6	344.8	345.6	347.5	349.0	349.5	351.4	354.2	356.2
10°	330.4	328.4	328.2	326.9	328.2	328.4	330.4	332.4	333.7	337.2	339.5
12.5°	316.8	314.9	312.8	312.3	312.8	314.9	316.8	318.5	318.9	322.8	324.5
15°	297.5	296.0	294.7	295.8	294.7	296.0	297.5	298.6	300.6	303.3	305.1
17.5°	281.4	280.2	280.0	278.6	280.0	280.2	281.4	282.0	285.3	287.1	290.3
20°	271.2	270.4	270.8	268.3	270.8	270.4	271.2	272.9	276.2	277.1	280.4
22.5°	263.2	261.4	261.2	260.7	261.2	261.4	263.2	264.7	265.4	268.2	270.5
25°	250.6	249.7	248.7	249.7	248.7	249.7	250.6	252.2	252.9	255.0	257.2
27.5°	239.6	238.4	238.2	238.4	238.2	238.4	239.6	239.4	241.4	243.0	244.6
30°	232.8	231.0	231.2	231.0	231.2	231.0	232.8	232.8	233.9	235.4	236.9
32.5°	225.5	224.3	224.0	223.7	224.0	224.3	225.5	225.2	226.6	228.4	230.0
35°	214.7	214.7	213.8	213.8	213.8	214.7	214.7	215.2	216.7	216.7	218.6
37.5°	204.5	204.4	203.8	203.9	203.8	204.4	204.5	205.0	205.5	206.3	207.5
40°	196.9	196.8	196.2	195.1	196.2	196.8	196.9	197.7	198.0	199.0	199.7
42.5°	189.6	189.0	188.8	188.4	188.8	189.0	189.6	190.0	190.3	191.5	193.0
45°	178.1	178.1	177.8	177.5	177.8	178.1	178.1	178.1	178.3	179.7	180.5
47.5°	166.9	167.2	167.9	167.8	167.9	167.2	166.9	166.6	166.7	167.4	168.3
50°	160.2	160.3	160.9	161.1	160.9	160.3	160.2	159.5	159.1	159.1	159.6
52.5°	152.7	153.8	154.5	154.3	154.5	153.8	152.7	152.1	151.5	150.6	151.4
55°	142.2	143.5	144.8	145.0	144.8	143.5	142.2	140.6	139.8	138.4	138.9
57.5°	131.9	133.6	135.0	135.5	135.0	133.6	131.9	129.9	127.5	126.8	125.8
60°	124.8	127.2	128.9	129.6	128.9	127.2	124.8	123.0	119.9	117.9	117.2
62.5°	118.1	120.8	122.4	122.6	122.4	120.8	118.1	115.3	112.2	109.8	108.4
65°	107.1	109.8	111.3	112.4	111.3	109.8	107.1	103.9	100.5	97.4	95.7
67.5°	95.2	98.0	99.6	100.4	99.6	98.0	95.2	91.3	88.2	84.6	82.7
70°	86.6	89.4	91.5	92.3	91.5	89.4	86.6	82.0	79.3	76.0	74.3
72.5°	78.1	80.6	82.3	83.2	82.3	80.6	78.1	73.8	70.6	67.3	65.1
75°	63.3	66.6	68.3	69.2	68.3	66.6	63.3	60.9	57.3	53.8	52.0
77.5°	48.8	51.8	52.8	53.3	52.8	51.8	48.8	46.0	43.3	40.7	39.0
80°	39.1	41.0	42.3	42.5	42.3	41.0	39.1	37.0	34.8	32.4	30.7
82.5°	30.1	31.6	32.0	32.5	32.0	31.6	30.1	28.2	26.3	24.5	23.1
85°	16.5	17.2	17.4	17.2	17.4	17.2	16.5	15.2	14.3	13.4	12.8
87.5°	8.9	8.7	8.9	9.2	8.9	8.7	8.9	8.6	8.4	8.0	7.5
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3
92.5°	54.7	52.8	51.7	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1
95°	228.5	204.9	198.5	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6
97.5°	526.6	482.2	459.3	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8
100°	715.7	658.8	629.5	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7
102.5°	885.9	845.4	813.6	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1
105°	1099.2	1073.2	1057.3	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1
107.5°	1188.9	1188.7	1183.5	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9
110°	1199.7	1214.7	1220.2	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1169.9	1195.7	1209.5	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2
115°	1096.9	1134.8	1157.0	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0
117.5°	1015.7	1054.9	1076.9	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0
120°	963.2	1001.2	1022.5	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2
122.5°	918.9	953.7	975.1	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1
125°	862.0	894.4	911.8	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3
127.5°	819.0	847.6	864.0	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0
130°	792.4	818.5	834.3	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2
132.5°	764.5	790.7	805.2	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4
135°	718.8	745.0	759.1	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8
137.5°	672.0	695.8	708.9	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4
140°	642.9	663.5	675.3	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9
142.5°	615.1	632.5	643.7	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7
145°	577.3	590.7	599.4	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9
147.5°	547.7	558.5	563.6	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8
150°	530.6	540.1	543.3	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1
152.5°	516.1	523.7	526.8	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8
155°	496.6	502.2	504.5	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3
157.5°	478.8	483.3	485.5	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8
160°	467.4	471.3	472.9	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5
162.5°	456.6	459.9	460.3	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6
165°	441.2	442.8	442.8	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9
167.5°	426.4	427.9	427.2	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7
170°	417.6	418.4	418.4	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6
172.5°	409.3	410.7	409.5	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9
175°	399.3	400.1	398.5	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8
177.5°	393.5	394.1	392.2	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	412.4	414.2	416.3	418.0	420.9	422.2	423.8	425.1	427.5	429.7	432.3
5°	384.6	387.7	391.9	396.5	401.8	405.4	410.6	413.7	419.9	425.6	431.1
7.5°	359.4	363.2	369.2	375.0	382.0	388.2	394.7	401.8	409.7	419.1	426.9
10°	342.1	347.2	353.6	361.0	369.4	376.7	385.3	393.0	402.7	413.7	424.0
12.5°	328.4	332.7	339.8	346.9	355.9	364.9	373.8	383.9	395.2	407.4	420.3
15°	309.3	313.0	318.9	328.6	337.7	346.5	359.9	369.4	383.7	397.2	412.8
17.5°	293.1	297.7	302.6	310.9	320.4	331.4	343.3	355.3	369.0	386.2	403.7
20°	283.2	286.8	292.5	298.9	309.0	320.0	331.3	343.4	360.2	378.0	396.9
22.5°	272.4	276.3	282.7	289.7	298.2	308.7	321.2	334.5	352.0	369.5	390.0
25°	259.6	262.3	268.2	274.4	282.8	291.8	304.8	319.4	336.8	356.8	377.6
27.5°	247.6	249.9	255.2	260.7	268.3	278.9	290.6	305.4	321.8	342.0	365.1
30°	238.8	241.5	246.2	252.1	259.4	268.7	280.6	294.5	312.1	331.8	356.0
32.5°	231.4	233.7	237.3	243.1	250.3	259.4	270.4	284.6	302.1	322.2	345.9
35°	219.8	222.4	225.1	229.7	235.9	244.7	256.8	270.2	287.0	306.4	328.2
37.5°	208.3	211.1	213.6	217.7	223.3	231.1	241.5	255.5	270.7	289.4	310.3
40°	201.1	203.4	205.4	209.8	215.5	222.8	232.5	244.9	261.0	278.5	295.8
42.5°	194.0	196.1	197.7	201.6	206.8	213.8	223.1	235.3	250.2	266.4	281.8
45°	182.7	183.9	186.0	189.3	193.5	199.9	208.8	219.7	232.3	247.6	259.2
47.5°	170.5	172.5	174.1	177.0	180.5	186.7	195.4	204.5	216.0	227.4	235.5
50°	161.1	163.1	165.5	168.3	171.5	177.4	185.2	194.6	204.3	213.1	220.0
52.5°	152.3	154.2	156.7	159.3	163.3	168.3	175.0	183.3	192.9	199.2	204.9
55°	139.3	140.2	143.1	145.7	149.6	153.2	160.0	167.3	173.2	177.9	182.7
57.5°	126.0	127.2	129.0	131.3	135.1	139.3	144.1	150.6	154.0	156.5	160.2
60°	117.5	117.9	119.0	121.8	124.7	128.5	134.0	138.6	141.2	143.1	146.2
62.5°	108.1	108.2	110.0	112.1	114.2	118.4	122.9	126.6	128.7	129.7	132.6
65°	95.0	94.7	95.7	97.4	100.0	102.7	106.5	109.8	109.6	110.7	112.6
67.5°	81.6	81.2	81.2	82.8	84.8	87.3	89.9	91.9	91.9	93.3	94.3
70°	72.5	71.4	72.1	73.4	74.3	76.4	79.3	80.0	80.2	80.9	81.8
72.5°	63.1	62.7	63.3	63.8	64.5	66.1	68.6	69.0	69.1	69.5	71.0
75°	50.1	49.8	49.4	50.0	50.7	51.8	52.7	53.5	53.2	53.5	54.6
77.5°	37.6	36.6	36.4	36.7	36.8	37.5	38.5	38.4	38.6	38.6	39.8
80°	29.9	28.4	28.2	28.2	28.4	28.8	29.1	29.5	28.9	29.5	29.9
82.5°	21.9	21.1	21.0	20.8	20.9	21.0	21.2	21.4	21.3	21.5	21.8
85°	12.1	11.7	11.2	11.6	11.3	10.8	11.2	10.6	10.5	10.6	10.8
87.5°	6.8	6.8	6.2	6.0	5.5	5.5	4.9	4.4	4.0	3.8	4.1
90°	13.5	12.7	11.1	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8
92.5°	206.4	254.9	259.0	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7
95°	685.6	700.7	571.8	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1
97.5°	867.5	748.3	510.6	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3
100°	911.8	714.1	455.5	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4
102.5°	885.3	654.0	413.8	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7
105°	800.3	573.3	373.3	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4
107.5°	713.6	517.8	356.2	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6
110°	664.2	491.9	351.1	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	627.6	476.7	351.1	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7
115°	587.6	460.3	353.5	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8
117.5°	563.7	452.2	358.7	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7
120°	550.4	448.4	363.8	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4
122.5°	539.0	445.2	368.2	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7
125°	523.6	441.2	375.7	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4
127.5°	509.3	439.3	384.0	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6
130°	499.8	438.1	389.1	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8
132.5°	492.2	438.1	394.7	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1
135°	483.2	438.1	402.5	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4
137.5°	475.2	439.0	409.6	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4
140°	471.3	439.7	412.8	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0
142.5°	468.2	440.3	414.7	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8
145°	463.4	439.7	416.8	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1
147.5°	458.5	437.6	417.6	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0
150°	454.7	435.7	417.6	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2
152.5°	450.3	433.2	416.9	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1
155°	442.8	428.6	415.2	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8
157.5°	435.9	423.9	413.1	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2
160°	430.2	420.7	411.2	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2
162.5°	425.2	416.9	409.3	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9
165°	417.6	411.2	406.5	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4
167.5°	410.1	405.7	402.0	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1
170°	405.7	402.5	400.1	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0
172.5°	401.2	398.7	397.6	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5
175°	395.4	394.6	394.6	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4
177.5°	392.8	392.2	392.2	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	433.6	435.6	437.0	439.4	441.5	442.7	443.7	444.6	445.6	446.5	449.0
5°	436.4	441.2	445.2	451.4	457.1	461.4	466.2	470.4	473.9	478.9	482.7
7.5°	435.1	443.6	452.5	462.2	472.0	481.1	489.6	497.4	504.5	513.2	520.8
10°	434.0	445.5	456.9	469.9	483.2	494.6	505.2	516.0	523.9	534.9	544.2
12.5°	433.2	446.7	460.4	476.0	490.7	506.8	520.9	528.8	540.7	549.5	560.6
15°	429.4	447.3	466.2	483.8	504.7	519.5	532.0	547.3	558.5	569.7	581.7
17.5°	422.8	443.1	464.2	487.3	507.2	523.2	539.2	554.1	567.4	582.3	597.4
20°	419.7	440.1	464.2	487.8	507.4	524.0	540.5	556.8	571.5	590.7	608.1
22.5°	413.3	437.8	460.1	483.2	503.3	521.4	540.1	558.6	578.1	599.8	621.5
25°	401.8	426.7	450.3	473.0	493.3	516.0	536.0	560.7	585.6	614.3	641.4
27.5°	389.8	413.7	435.3	457.2	480.9	506.7	532.5	560.5	593.2	629.5	667.7
30°	380.2	402.7	423.7	446.2	471.0	499.9	528.3	561.6	599.3	640.1	685.6
32.5°	368.9	389.7	410.1	434.0	460.9	491.4	524.5	561.0	606.3	652.7	699.4
35°	349.6	367.0	388.1	413.5	443.9	478.9	517.1	560.3	612.3	665.6	704.9
37.5°	326.8	342.9	365.1	393.0	424.8	462.4	507.8	559.0	614.3	656.7	669.4
40°	311.3	326.4	349.4	378.3	410.9	450.7	500.4	554.6	608.1	635.2	624.7
42.5°	294.9	310.7	333.2	361.8	396.9	440.1	491.2	545.4	590.3	600.5	564.4
45°	269.1	285.3	307.5	336.4	374.1	421.0	474.3	523.6	549.3	530.8	475.0
47.5°	245.0	260.3	280.8	310.7	349.6	398.1	449.3	488.6	490.7	446.6	386.9
50°	228.6	242.7	263.4	293.3	331.8	381.0	427.2	458.2	444.3	394.3	337.0
52.5°	212.5	226.3	246.7	276.2	314.4	359.4	402.5	424.2	398.0	346.7	297.8
55°	189.3	201.4	221.3	248.6	284.8	326.5	363.1	370.7	336.6	286.1	246.4
57.5°	166.6	177.8	196.0	221.1	254.3	291.2	319.9	318.2	282.3	238.9	207.4
60°	151.2	162.2	178.3	202.8	233.1	264.9	289.4	283.5	247.9	210.5	183.9
62.5°	137.4	147.3	162.5	183.9	211.5	241.0	261.1	252.5	217.5	184.9	163.9
65°	117.2	125.4	138.4	156.7	179.6	203.9	219.5	208.3	178.5	153.0	136.2
67.5°	97.8	104.4	115.3	129.9	149.4	169.0	178.4	167.2	143.3	124.8	112.3
70°	85.5	91.3	99.7	112.7	129.8	146.2	153.4	143.3	122.8	106.9	97.9
72.5°	73.2	78.0	85.4	97.1	110.7	125.0	131.3	121.7	104.8	91.3	83.0
75°	56.6	59.9	65.0	73.0	83.8	95.2	98.6	90.2	79.5	69.4	63.8
77.5°	40.5	43.3	47.1	52.2	59.9	67.1	70.1	65.3	57.0	50.5	46.0
80°	31.1	32.6	35.9	40.1	46.1	50.7	52.7	49.6	43.7	39.0	35.5
82.5°	22.2	23.7	25.6	29.1	33.0	36.0	38.2	36.1	31.9	28.1	26.1
85°	10.8	11.7	12.8	14.3	17.2	19.0	18.9	17.6	15.9	14.5	13.4
87.5°	4.1	4.6	5.3	6.4	7.1	7.9	8.5	8.4	8.1	7.8	7.5
90°	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3
92.5°	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1
95°	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6
97.5°	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8
100°	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7
102.5°	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1
105°	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1
107.5°	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9
110°	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2
115°	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0
117.5°	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0
120°	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2
122.5°	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1
125°	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3
127.5°	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0
130°	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2
132.5°	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4
135°	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8
137.5°	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4
140°	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9
142.5°	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7
145°	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9
147.5°	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8
150°	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1
152.5°	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8
155°	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3
157.5°	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8
160°	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5
162.5°	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6
165°	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9
167.5°	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7
170°	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6
172.5°	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9
175°	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8
177.5°	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	451.1	452.2	454.7	453.8	455.0	455.6	456.1
5°	487.4	493.3	495.9	495.5	499.4	498.4	497.5
7.5°	528.6	534.7	538.2	542.5	544.9	545.2	547.3
10°	551.9	559.9	563.2	567.8	570.8	572.4	572.2
12.5°	569.7	576.1	583.4	585.7	589.6	591.8	591.0
15°	591.3	601.3	609.0	612.8	617.8	619.2	621.2
17.5°	610.5	623.9	632.9	644.8	649.4	652.1	650.5
20°	625.0	642.7	651.6	665.9	673.8	678.0	676.5
22.5°	642.1	661.3	677.9	690.2	702.2	707.9	709.1
25°	671.5	697.8	722.2	738.4	753.2	756.7	764.4
27.5°	704.3	735.3	761.4	778.5	788.8	792.7	795.1
30°	724.8	755.8	775.4	786.4	789.6	789.3	788.9
32.5°	735.0	754.3	758.1	755.0	747.5	741.1	734.4
35°	720.6	706.2	684.6	656.8	636.3	615.6	613.5
37.5°	648.2	601.9	565.9	525.8	502.6	488.3	478.4
40°	579.9	527.4	483.8	450.0	426.4	417.0	407.8
42.5°	505.8	455.6	417.0	388.7	371.0	360.6	353.4
45°	410.9	366.6	336.4	315.9	301.8	293.8	289.2
47.5°	336.8	304.0	278.3	263.5	253.8	247.6	247.6
50°	296.9	265.6	248.6	236.9	228.5	223.5	224.4
52.5°	261.6	238.2	223.7	213.9	207.6	204.6	204.5
55°	218.7	201.9	192.4	185.2	181.0	177.5	178.3
57.5°	187.1	172.9	166.5	160.6	157.6	156.3	154.2
60°	167.5	156.5	151.0	146.2	143.3	142.2	140.2
62.5°	150.0	141.4	136.1	132.2	129.6	129.2	127.6
65°	126.1	119.5	114.8	113.0	110.2	109.5	109.5
67.5°	103.9	99.3	95.5	93.9	92.7	92.8	92.0
70°	90.1	86.2	83.8	82.0	81.1	81.3	80.6
72.5°	78.8	74.5	72.4	71.3	70.1	70.6	70.3
75°	59.7	57.5	56.4	55.3	54.6	54.2	53.8
77.5°	43.8	41.9	41.0	40.4	40.6	39.6	40.3
80°	33.8	32.2	31.7	30.7	30.6	30.6	30.4
82.5°	24.8	23.8	23.4	22.7	22.3	22.7	22.2
85°	12.8	12.1	11.9	11.9	11.6	11.2	12.1
87.5°	7.7	7.3	7.6	7.4	7.4	7.4	7.1
90°	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333144-927

CATALOG NUMBER: S125DIP-S375D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)