

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333216-927

Luminaire Tested: **S125DIP-S850D590U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333216-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4416.8 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	32	29
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6259	6259	6259	6259
5°	7248	6280	5499	6280
10°	8433	6248	4818	6248
15°	9335	6202	4444	6202
20°	10449	6129	4144	6129
25°	12241	6047	3998	6047
30°	13221	5967	3871	5967
35°	10871	5815	3788	5815
40°	7727	5604	3697	5604
45°	5936	5320	3644	5320
50°	5067	4967	3636	4967
55°	4512	4622	3668	4622
60°	4070	4246	3761	4246
65°	3759	3865	3859	3865
70°	3418	3473	3914	3473
75°	3019	3059	3880	3059
80°	2540	2492	3552	2492
85°	2016	1793	2868	1793



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.3	2.1
10°-20°	277.8	6.3
20°-30°	451.1	10.2
30°-40°	550.2	12.5
40°-50°	500.5	11.3
50°-60°	398.7	9.0
60°-70°	277.7	6.3
70°-80°	148.1	3.4
80°-90°	38.6	0.9
90°-100°	162.5	3.7
100°-110°	349.2	7.9
110°-120°	327.8	7.4
120°-130°	265.6	6.0
130°-140°	213.2	4.8
140°-150°	160.9	3.6
150°-160°	113.2	2.6
160°-170°	66.7	1.5
170°-180°	21.7	0.5
0°-30°	822.1	18.6
0°-40°	1372.3	31.1
0°-60°	2271.6	51.4
0°-90°	2736.0	61.9
90°-120°	839.5	19.0
90°-150°	1479.1	33.5
90°-180°	1681.0	38.1
0°-180°	4416.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1118	969	848	969	1118	113
15°	1396	928	665	928	1396	400
25°	1718	849	561	849	1718	785
35°	1379	738	480	738	1379	844
45°	650	582	399	582	650	520
55°	401	410	326	410	401	361
65°	246	253	252	253	246	244
75°	121	123	156	123	121	130
85°	27	24	39	24	27	32
90°	10	0	10	0	10	8
95°	106	15	106	15	106	150
105°	599	51	599	51	599	595
115°	667	91	667	91	667	652
125°	526	126	526	126	526	475
135°	436	148	436	148	436	338
145°	344	173	344	173	344	219
155°	289	197	289	197	289	135
165°	253	215	253	215	253	72
175°	227	224	227	224	227	22
180°	224	224	224	224	224	



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1025.1	1023.7	1022.5	1019.8	1021.8	1016.2	1013.5	1008.9	1003.4	1001.4	999.1
5°	1118.0	1120.1	1122.1	1113.5	1114.4	1108.6	1095.4	1084.7	1076.1	1065.0	1057.2
7.5°	1229.9	1225.0	1224.6	1219.1	1209.4	1201.7	1187.9	1170.3	1153.3	1133.9	1117.8
10°	1285.9	1286.3	1282.5	1276.0	1265.7	1258.3	1240.2	1222.9	1202.0	1177.3	1159.6
12.5°	1328.0	1329.7	1325.0	1316.1	1311.1	1294.5	1280.3	1259.8	1234.9	1215.1	1188.2
15°	1396.1	1391.5	1388.3	1377.2	1368.6	1351.3	1328.6	1307.3	1280.1	1255.0	1229.9
17.5°	1461.7	1465.4	1459.2	1449.1	1422.3	1402.1	1371.7	1342.4	1308.7	1275.0	1245.1
20°	1520.4	1523.6	1514.2	1496.5	1464.4	1444.2	1404.3	1366.5	1327.4	1284.2	1251.3
22.5°	1593.4	1590.8	1578.0	1551.1	1523.3	1486.1	1442.8	1396.8	1347.8	1299.0	1255.3
25°	1717.8	1700.5	1692.7	1659.4	1622.8	1568.0	1508.8	1441.4	1380.5	1315.9	1260.0
27.5°	1786.7	1781.3	1772.6	1749.4	1710.9	1652.4	1582.5	1500.3	1414.4	1332.9	1259.7
30°	1772.9	1773.7	1774.6	1767.1	1742.5	1698.4	1629.0	1540.5	1438.4	1346.7	1262.0
32.5°	1650.5	1665.5	1679.7	1696.7	1703.6	1695.2	1651.6	1571.8	1466.8	1362.6	1260.7
35°	1378.8	1383.4	1429.8	1475.9	1538.4	1587.0	1619.5	1584.1	1495.6	1375.9	1259.1
37.5°	1075.1	1097.3	1129.5	1181.5	1271.8	1352.6	1456.5	1504.3	1475.8	1380.3	1256.2
40°	916.5	937.1	958.0	1011.1	1087.2	1185.1	1303.1	1403.9	1427.4	1366.5	1246.3
42.5°	794.1	810.3	833.6	873.5	937.2	1023.8	1136.6	1268.4	1349.4	1326.4	1225.7
45°	649.9	660.2	678.3	710.0	756.1	823.9	923.4	1067.5	1192.9	1234.5	1176.5
47.5°	556.3	556.2	570.3	592.2	625.4	683.1	756.7	869.5	1003.5	1102.6	1098.0
50°	504.3	502.2	513.3	532.3	558.6	596.8	667.2	757.2	886.1	998.3	1029.6
52.5°	459.5	459.8	466.6	480.6	502.6	535.4	587.9	669.1	779.1	894.4	953.2
55°	400.7	399.0	406.8	416.3	432.3	453.7	491.5	553.7	642.9	756.5	833.0
57.5°	346.7	351.2	354.3	360.9	374.2	388.6	420.5	466.0	536.9	634.3	715.2
60°	315.1	319.6	322.1	328.7	339.4	351.7	376.4	413.4	473.0	557.0	637.2
62.5°	286.8	290.3	291.1	297.1	305.8	317.8	337.2	368.3	415.4	488.9	567.4
65°	246.0	246.0	247.6	253.8	257.9	268.6	283.4	306.0	343.9	401.1	468.1
67.5°	206.7	208.7	208.2	211.0	214.8	223.0	233.6	252.3	280.4	322.1	375.7
70°	181.0	182.6	182.2	184.3	188.4	193.8	202.4	220.1	240.2	276.0	322.1
72.5°	158.0	158.6	157.6	160.3	162.7	167.4	177.1	186.5	205.3	235.5	273.4
75°	121.0	121.8	122.6	124.2	126.7	129.1	134.1	143.5	155.9	178.6	202.8
77.5°	90.6	89.1	91.1	90.9	92.2	94.1	98.5	103.5	113.6	127.9	146.7
80°	68.3	68.7	68.7	69.1	71.1	72.4	76.1	79.8	87.6	98.3	111.5
82.5°	49.8	50.9	50.3	51.0	52.8	53.6	55.7	58.7	63.3	71.7	81.2
85°	27.2	25.1	25.9	26.8	26.8	27.2	28.8	30.0	32.5	35.8	39.5
87.5°	10.0	10.6	10.9	10.9	11.2	11.0	12.3	12.1	13.1	13.9	15.1
90°	10.4	10.4	9.9	9.9	9.9	9.0	8.6	8.2	7.7	7.2	6.3
92.5°	28.8	29.5	30.2	31.3	37.1	43.7	58.1	80.1	118.0	145.7	148.1
95°	106.2	113.4	117.0	130.6	162.7	200.7	256.2	324.9	391.8	400.4	326.7
97.5°	256.7	262.4	275.5	300.9	328.8	381.6	435.7	483.9	495.7	427.5	291.8
100°	352.4	359.7	376.4	408.9	440.1	487.1	533.7	555.8	521.0	408.1	260.3
102.5°	459.5	464.9	483.1	506.2	539.6	571.3	593.7	580.0	505.8	373.7	236.4
105°	598.7	604.2	613.2	628.1	642.5	647.5	627.6	565.8	457.3	327.6	213.3
107.5°	672.6	676.3	679.3	679.4	672.0	648.5	597.4	514.8	407.8	295.9	203.5
110°	697.3	697.3	694.1	685.5	665.2	626.8	563.1	477.2	379.6	281.1	200.7



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	694.3	691.1	683.3	668.5	638.8	593.5	529.1	447.6	358.6	272.4	200.7
115°	667.0	661.1	648.5	626.8	591.5	542.2	480.4	410.3	335.7	263.0	202.0
117.5°	619.0	615.4	602.9	580.4	545.2	499.9	446.6	386.3	322.1	258.4	204.9
120°	587.9	584.3	572.1	550.4	517.0	477.2	427.5	373.3	314.5	256.2	207.9
122.5°	560.4	557.1	544.9	525.1	495.3	458.0	413.8	363.5	308.0	254.4	210.4
125°	525.5	521.0	511.1	492.6	467.2	434.7	395.4	349.3	299.1	252.2	214.7
127.5°	495.7	493.7	484.3	467.9	445.0	414.5	377.9	334.9	291.0	251.0	219.4
130°	479.4	476.7	467.7	452.8	430.2	400.8	365.6	325.8	285.6	250.3	222.4
132.5°	463.2	460.1	451.8	436.9	414.3	386.0	354.0	316.8	281.2	250.3	225.6
135°	436.5	433.8	425.6	410.7	390.9	365.1	336.2	305.0	276.1	250.3	230.0
137.5°	408.1	405.0	397.6	384.0	366.2	344.4	320.3	295.1	271.5	250.9	234.1
140°	388.2	385.9	379.1	367.4	350.7	331.7	310.9	289.6	269.3	251.3	235.9
142.5°	369.7	367.8	361.4	351.5	337.3	320.8	302.9	284.9	267.5	251.6	236.9
145°	344.4	342.5	337.5	329.9	319.0	306.8	292.8	278.8	264.8	251.3	238.1
147.5°	322.8	322.0	319.1	313.0	304.4	295.2	284.4	273.1	262.0	250.1	238.6
150°	310.9	310.5	308.6	303.2	296.4	288.3	279.7	269.7	259.8	249.0	238.6
152.5°	301.5	301.0	299.2	294.9	289.2	282.9	275.0	266.2	257.3	247.6	238.2
155°	288.8	288.3	286.9	283.8	279.2	274.3	268.0	260.7	253.0	244.9	237.3
157.5°	277.3	277.4	276.2	273.5	270.1	266.2	261.3	255.3	249.1	242.2	236.1
160°	269.7	270.2	269.3	267.0	263.9	260.7	256.2	251.7	245.8	240.4	235.0
162.5°	262.9	263.0	262.8	260.9	258.5	255.6	251.9	247.7	243.0	238.2	233.9
165°	253.0	253.0	253.0	252.2	250.3	248.1	245.3	242.2	238.6	235.0	232.3
167.5°	244.0	244.1	244.5	243.7	242.7	241.1	239.1	236.9	234.3	231.8	229.7
170°	238.6	239.1	239.1	238.6	237.7	236.8	235.4	234.1	231.8	230.0	228.6
172.5°	233.5	234.0	234.7	233.9	233.7	233.1	232.2	230.8	229.3	227.8	227.2
175°	227.3	227.8	228.6	228.2	228.2	228.2	227.3	227.3	225.9	225.5	225.5
177.5°	224.1	224.1	225.2	224.8	225.2	225.2	225.2	224.8	224.5	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	997.1	994.8	992.1	987.5	982.0	979.0	974.4	971.5	965.5	960.6	955.3
5°	1047.7	1037.0	1027.1	1014.4	1000.4	991.3	980.6	968.7	956.4	943.6	929.6
7.5°	1100.1	1081.2	1060.6	1038.5	1016.8	997.0	977.9	959.3	941.8	920.8	902.9
10°	1135.3	1111.4	1085.9	1055.9	1026.7	1001.2	975.3	952.7	929.6	905.0	883.1
12.5°	1170.5	1138.8	1102.7	1069.8	1034.6	1003.9	973.4	944.4	915.5	888.2	862.8
15°	1195.4	1167.4	1134.1	1087.2	1047.7	1005.4	965.0	927.6	892.6	862.2	830.1
17.5°	1211.7	1175.7	1140.0	1095.0	1043.1	995.8	950.1	907.3	867.8	829.3	798.4
20°	1214.7	1177.7	1140.3	1096.2	1043.1	988.9	943.3	891.8	849.5	809.5	771.7
22.5°	1213.7	1171.8	1131.0	1085.7	1034.0	984.0	928.8	876.3	830.4	791.1	751.6
25°	1204.4	1159.6	1108.6	1063.0	1011.9	958.9	902.9	848.6	801.7	756.9	717.8
27.5°	1196.7	1138.5	1080.8	1027.5	978.3	929.6	876.1	820.5	768.5	723.0	686.2
30°	1187.2	1123.4	1058.4	1002.8	952.3	905.0	854.4	800.1	745.8	701.3	661.9
32.5°	1178.6	1104.3	1035.7	975.3	921.6	875.7	829.0	777.4	724.1	679.0	639.4
35°	1162.1	1076.1	997.5	929.2	872.0	824.7	785.7	737.5	688.6	645.0	607.1
37.5°	1141.1	1039.0	954.7	883.1	820.5	770.6	734.3	697.3	650.3	608.3	574.1
40°	1124.6	1012.7	923.4	850.2	785.3	733.4	699.7	664.7	625.7	586.6	550.4
42.5°	1103.9	989.0	891.9	813.1	748.7	698.2	662.8	633.1	598.7	562.2	528.6
45°	1065.8	946.1	840.8	756.1	691.0	641.3	604.7	582.5	556.6	522.0	493.6
47.5°	1009.8	894.5	785.6	698.2	631.1	584.9	550.6	529.3	511.0	485.4	459.6
50°	960.0	856.0	745.8	658.9	591.9	545.4	513.8	494.4	478.8	459.1	437.3
52.5°	904.4	807.6	706.6	620.8	554.4	508.6	477.6	460.6	447.6	433.4	411.9
55°	816.1	733.9	640.1	558.6	497.3	452.5	425.3	410.5	399.8	389.1	376.0
57.5°	718.7	654.4	571.3	496.9	440.5	399.7	374.3	359.9	351.6	346.1	338.3
60°	650.3	595.2	523.6	455.7	400.7	364.5	339.8	328.7	321.7	317.1	311.4
62.5°	586.8	541.6	475.2	413.3	365.1	330.9	308.9	298.1	291.4	289.1	284.4
65°	493.2	458.3	403.5	352.1	311.0	281.8	263.2	252.9	248.8	246.4	246.8
67.5°	401.0	379.7	335.7	291.9	259.0	234.6	219.8	211.8	209.8	206.5	206.4
70°	344.7	328.7	291.7	253.4	224.2	205.3	192.1	183.9	181.8	180.1	179.7
72.5°	295.0	281.0	248.8	218.2	191.9	175.3	164.5	159.5	156.1	155.2	155.1
75°	221.7	213.9	188.4	164.1	146.0	134.5	127.1	122.6	120.1	119.7	120.1
77.5°	157.6	150.8	134.6	117.4	106.0	97.3	91.0	89.4	86.7	86.7	86.3
80°	118.4	113.9	103.7	90.1	80.6	73.2	69.9	67.0	66.2	65.0	66.2
82.5°	85.9	81.0	74.1	65.4	57.6	53.2	49.8	49.0	48.5	47.8	48.2
85°	42.4	42.8	38.7	32.1	28.8	26.3	24.2	24.2	23.8	23.4	23.8
87.5°	15.7	14.8	13.4	12.3	10.4	9.3	8.7	9.0	8.1	7.9	8.5
90°	5.9	5.0	4.5	3.6	2.7	1.8	0.9	0.5	0.9	1.8	2.7
92.5°	103.1	61.7	37.1	23.8	16.1	10.5	6.7	5.5	6.7	10.5	16.1
95°	202.0	102.6	54.3	33.9	23.9	19.0	15.4	14.9	15.4	19.0	23.9
97.5°	161.2	88.4	56.4	41.7	32.8	27.8	25.3	24.8	25.3	27.8	32.8
100°	146.4	87.7	61.5	47.9	39.3	34.4	32.6	31.6	32.6	34.4	39.3
102.5°	140.3	90.9	67.6	54.4	46.6	41.2	39.8	39.2	39.8	41.2	46.6
105°	137.8	97.6	77.7	65.0	57.8	53.3	51.1	51.1	51.1	53.3	57.8
107.5°	142.0	107.6	88.3	76.9	69.4	65.7	63.5	62.7	63.5	65.7	69.4
110°	145.9	114.8	96.3	84.5	77.7	73.7	71.9	71.0	71.9	73.7	77.7



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	151.0	121.7	103.9	92.4	85.7	81.6	80.2	79.3	80.2	81.6	85.7
115°	158.6	132.4	115.7	104.4	97.6	93.6	92.2	91.3	92.2	93.6	97.6
117.5°	167.3	143.5	127.6	116.7	109.0	105.0	103.5	102.1	103.5	105.0	109.0
120°	173.1	151.4	135.5	124.3	116.6	112.5	110.7	109.3	110.7	112.5	116.6
122.5°	179.6	159.0	143.1	131.9	123.4	119.4	118.0	116.9	118.0	119.4	123.4
125°	188.5	169.0	154.1	142.4	133.7	129.7	127.5	126.5	127.5	129.7	133.7
127.5°	196.5	178.6	164.3	152.6	143.5	138.3	135.4	134.0	135.4	138.3	143.5
130°	202.0	184.8	170.8	159.1	149.6	143.7	140.1	138.7	140.1	143.7	149.6
132.5°	206.7	190.6	176.6	164.9	155.0	148.4	144.1	142.4	144.1	148.4	155.0
135°	213.3	198.4	184.3	172.1	162.7	155.4	150.0	148.2	150.0	155.4	162.7
137.5°	218.2	203.9	191.2	178.6	169.3	162.1	157.0	155.7	157.0	162.1	169.3
140°	221.4	207.9	194.8	182.6	174.0	166.8	161.3	159.9	161.3	166.8	174.0
142.5°	223.2	210.4	198.0	186.6	178.3	171.1	166.0	165.0	166.0	171.1	178.3
145°	225.9	214.7	202.9	192.5	184.3	178.0	173.5	172.6	173.5	178.0	184.3
147.5°	227.6	217.4	207.1	197.9	190.8	185.0	181.1	180.5	181.1	185.0	190.8
150°	228.6	219.2	209.2	201.5	195.2	189.3	186.2	185.3	186.2	189.3	195.2
152.5°	229.3	220.9	211.8	204.8	198.8	193.7	190.8	190.4	190.8	193.7	198.8
155°	230.0	222.8	215.1	208.7	204.2	199.7	197.0	197.0	197.0	199.7	204.2
157.5°	230.4	224.3	217.7	212.9	209.0	205.1	202.9	203.0	202.9	205.1	209.0
160°	230.4	225.1	219.2	215.1	211.5	208.3	206.5	207.0	206.5	208.3	211.5
162.5°	230.1	225.8	220.6	217.3	214.4	211.6	209.8	210.2	209.8	211.6	214.4
165°	229.6	225.9	222.4	219.6	217.8	215.6	214.2	215.1	214.2	215.6	217.8
167.5°	228.5	225.9	222.9	221.3	220.0	218.7	217.9	218.3	217.9	218.7	220.0
170°	227.8	225.9	223.7	222.4	221.4	220.5	220.1	220.5	220.1	220.5	221.4
172.5°	227.0	225.6	223.7	223.1	222.5	221.6	221.2	222.0	221.2	221.6	222.5
175°	225.9	225.1	223.7	223.7	223.7	223.2	222.8	223.7	222.8	223.2	223.7
177.5°	224.8	224.5	223.8	223.8	224.1	223.8	223.8	224.5	223.8	223.8	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	952.4	948.7	945.8	939.2	935.6	930.7	926.7	931.0	926.4	928.4	925.3
5°	922.7	911.2	902.9	891.0	880.7	871.2	864.3	863.0	859.7	858.1	853.1
7.5°	886.9	872.5	858.4	842.8	829.6	816.2	807.6	800.6	795.9	789.7	785.5
10°	865.9	846.5	830.1	811.2	794.7	780.3	768.8	763.0	757.7	749.9	747.0
12.5°	839.9	819.9	799.8	779.6	763.8	747.7	737.8	729.1	725.5	716.6	715.7
15°	808.7	778.7	758.9	738.4	716.5	703.4	695.1	685.7	681.6	675.4	670.9
17.5°	771.5	744.7	720.0	698.7	680.0	668.9	658.7	652.2	645.2	641.1	633.7
20°	744.6	719.1	694.3	671.7	657.4	644.6	636.4	630.2	622.8	620.8	613.3
22.5°	721.8	693.7	670.0	651.0	635.3	620.9	612.0	607.8	602.7	596.4	594.8
25°	684.9	655.7	635.6	616.6	602.6	589.5	583.3	578.0	573.0	568.5	566.8
27.5°	653.0	626.9	602.9	585.8	573.7	561.7	556.2	549.7	546.1	542.5	538.1
30°	630.6	603.9	582.9	566.4	553.3	542.6	536.8	532.3	529.0	525.7	523.2
32.5°	607.5	582.8	562.4	546.4	533.2	525.1	520.0	516.8	513.2	509.2	506.1
35°	577.1	549.9	530.2	516.3	506.0	499.8	494.0	491.2	487.0	487.0	483.7
37.5°	542.8	519.4	501.9	489.2	480.0	474.4	468.2	466.2	463.6	461.8	460.7
40°	522.4	500.6	484.2	471.4	461.5	457.0	452.1	448.8	447.1	445.0	444.3
42.5°	501.4	480.5	464.8	453.0	444.4	440.5	435.9	433.6	430.3	427.6	427.1
45°	469.4	449.2	434.8	425.3	418.0	413.4	410.5	405.6	403.9	400.7	400.2
47.5°	438.9	419.6	405.5	397.8	391.3	387.5	383.0	378.1	376.2	374.5	374.4
50°	416.3	398.6	385.4	378.0	371.9	366.5	361.9	358.7	357.4	357.4	358.3
52.5°	393.2	378.2	367.0	358.0	352.1	346.4	342.2	340.2	338.3	340.3	341.8
55°	359.5	344.3	336.0	327.4	321.7	315.1	313.1	312.2	311.0	314.3	315.9
57.5°	323.8	313.1	303.5	294.9	289.8	286.0	283.2	282.7	284.9	286.5	291.9
60°	301.1	288.8	280.1	273.5	267.4	264.9	264.1	263.2	264.9	269.4	276.4
62.5°	276.1	266.1	256.7	251.8	247.3	243.2	243.0	243.5	246.8	252.0	259.0
65°	239.4	230.8	224.6	218.8	215.2	212.7	213.5	215.2	218.8	225.9	233.6
67.5°	202.2	196.2	190.7	186.0	182.4	182.4	183.3	185.8	190.1	198.2	205.3
70°	178.1	171.5	167.0	164.9	162.1	160.4	162.9	167.0	170.7	178.1	184.3
72.5°	154.1	148.5	145.0	143.5	142.4	141.0	141.8	146.2	151.3	158.7	165.9
75°	118.4	116.4	113.9	112.3	111.1	111.9	112.7	116.8	121.0	128.7	137.0
77.5°	86.4	84.3	82.9	82.5	81.8	82.1	84.5	87.5	91.6	97.3	103.5
80°	65.4	64.6	63.8	63.4	63.4	63.8	67.0	69.1	72.8	78.2	83.1
82.5°	47.6	47.1	47.0	46.9	47.2	47.3	49.3	52.0	55.1	59.1	63.4
85°	25.1	24.2	25.5	25.9	25.1	26.3	27.2	28.8	30.0	32.1	34.1
87.5°	9.0	9.8	9.6	10.1	10.1	11.0	10.8	12.1	12.9	13.6	13.5
90°	3.6	4.5	5.0	5.9	6.3	7.2	7.7	8.2	8.6	9.0	9.9
92.5°	23.8	37.1	61.7	103.1	148.1	145.7	118.0	80.1	58.1	43.7	37.1
95°	33.9	54.3	102.6	202.0	326.7	400.4	391.8	324.9	256.2	200.7	162.7
97.5°	41.7	56.4	88.4	161.2	291.8	427.5	495.7	483.9	435.7	381.6	328.8
100°	47.9	61.5	87.7	146.4	260.3	408.1	521.0	555.8	533.7	487.1	440.1
102.5°	54.4	67.6	90.9	140.3	236.4	373.7	505.8	580.0	593.7	571.3	539.6
105°	65.0	77.7	97.6	137.8	213.3	327.6	457.3	565.8	627.6	647.5	642.5
107.5°	76.9	88.3	107.6	142.0	203.5	295.9	407.8	514.8	597.4	648.5	672.0
110°	84.5	96.3	114.8	145.9	200.7	281.1	379.6	477.2	563.1	626.8	665.2



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	92.4	103.9	121.7	151.0	200.7	272.4	358.6	447.6	529.1	593.5	638.8
115°	104.4	115.7	132.4	158.6	202.0	263.0	335.7	410.3	480.4	542.2	591.5
117.5°	116.7	127.6	143.5	167.3	204.9	258.4	322.1	386.3	446.6	499.9	545.2
120°	124.3	135.5	151.4	173.1	207.9	256.2	314.5	373.3	427.5	477.2	517.0
122.5°	131.9	143.1	159.0	179.6	210.4	254.4	308.0	363.5	413.8	458.0	495.3
125°	142.4	154.1	169.0	188.5	214.7	252.2	299.1	349.3	395.4	434.7	467.2
127.5°	152.6	164.3	178.6	196.5	219.4	251.0	291.0	334.9	377.9	414.5	445.0
130°	159.1	170.8	184.8	202.0	222.4	250.3	285.6	325.8	365.6	400.8	430.2
132.5°	164.9	176.6	190.6	206.7	225.6	250.3	281.2	316.8	354.0	386.0	414.3
135°	172.1	184.3	198.4	213.3	230.0	250.3	276.1	305.0	336.2	365.1	390.9
137.5°	178.6	191.2	203.9	218.2	234.1	250.9	271.5	295.1	320.3	344.4	366.2
140°	182.6	194.8	207.9	221.4	235.9	251.3	269.3	289.6	310.9	331.7	350.7
142.5°	186.6	198.0	210.4	223.2	236.9	251.6	267.5	284.9	302.9	320.8	337.3
145°	192.5	202.9	214.7	225.9	238.1	251.3	264.8	278.8	292.8	306.8	319.0
147.5°	197.9	207.1	217.4	227.6	238.6	250.1	262.0	273.1	284.4	295.2	304.4
150°	201.5	209.2	219.2	228.6	238.6	249.0	259.8	269.7	279.7	288.3	296.4
152.5°	204.8	211.8	220.9	229.3	238.2	247.6	257.3	266.2	275.0	282.9	289.2
155°	208.7	215.1	222.8	230.0	237.3	244.9	253.0	260.7	268.0	274.3	279.2
157.5°	212.9	217.7	224.3	230.4	236.1	242.2	249.1	255.3	261.3	266.2	270.1
160°	215.1	219.2	225.1	230.4	235.0	240.4	245.8	251.7	256.2	260.7	263.9
162.5°	217.3	220.6	225.8	230.1	233.9	238.2	243.0	247.7	251.9	255.6	258.5
165°	219.6	222.4	225.9	229.6	232.3	235.0	238.6	242.2	245.3	248.1	250.3
167.5°	221.3	222.9	225.9	228.5	229.7	231.8	234.3	236.9	239.1	241.1	242.7
170°	222.4	223.7	225.9	227.8	228.6	230.0	231.8	234.1	235.4	236.8	237.7
172.5°	223.1	223.7	225.6	227.0	227.2	227.8	229.3	230.8	232.2	233.1	233.7
175°	223.7	223.7	225.1	225.9	225.5	225.5	225.9	227.3	227.3	228.2	228.2
177.5°	223.8	223.8	224.5	224.8	224.1	224.1	224.5	224.8	225.2	225.2	225.2
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	923.4	925.7	923.7	926.4	923.7	925.7	923.4	925.3	928.4	926.4	931.0
5°	851.0	847.4	849.9	848.2	849.9	847.4	851.0	853.1	858.1	859.7	863.0
7.5°	784.3	780.7	776.7	774.8	776.7	780.7	784.3	785.5	789.7	795.9	800.6
10°	742.5	737.9	737.5	734.7	737.5	737.9	742.5	747.0	749.9	757.7	763.0
12.5°	711.9	707.7	703.0	701.8	703.0	707.7	711.9	715.7	716.6	725.5	729.1
15°	668.4	665.1	662.3	664.7	662.3	665.1	668.4	670.9	675.4	681.6	685.7
17.5°	632.3	629.6	629.1	626.1	629.1	629.6	632.3	633.7	641.1	645.2	652.2
20°	609.6	607.5	608.4	603.0	608.4	607.5	609.6	613.3	620.8	622.8	630.2
22.5°	591.5	587.5	587.0	585.9	587.0	587.5	591.5	594.8	596.4	602.7	607.8
25°	563.2	561.1	559.0	561.1	559.0	561.1	563.2	566.8	568.5	573.0	578.0
27.5°	538.4	535.9	535.4	535.6	535.4	535.9	538.4	538.1	542.5	546.1	549.7
30°	523.2	519.1	519.5	519.1	519.5	519.1	523.2	523.2	525.7	529.0	532.3
32.5°	506.8	504.0	503.4	502.6	503.4	504.0	506.8	506.1	509.2	513.2	516.8
35°	482.5	482.5	480.5	480.5	480.5	482.5	482.5	483.7	487.0	487.0	491.2
37.5°	459.7	459.3	458.0	458.3	458.0	459.3	459.7	460.7	461.8	463.6	466.2
40°	442.6	442.2	440.9	438.5	440.9	442.2	442.6	444.3	445.0	447.1	448.8
42.5°	426.1	424.8	424.2	423.3	424.2	424.8	426.1	427.1	427.6	430.3	433.6
45°	400.2	400.2	399.4	399.0	399.4	400.2	400.2	400.2	400.7	403.9	405.6
47.5°	375.1	375.8	377.4	377.2	377.4	375.8	375.1	374.4	374.5	376.2	378.1
50°	359.9	360.4	361.6	361.9	361.6	360.4	359.9	358.3	357.4	357.4	358.7
52.5°	343.2	345.5	347.1	346.8	347.1	345.5	343.2	341.8	340.3	338.3	340.2
55°	319.6	322.5	325.3	325.8	325.3	322.5	319.6	315.9	314.3	311.0	312.2
57.5°	296.4	300.4	303.4	304.4	303.4	300.4	296.4	291.9	286.5	284.9	282.7
60°	280.5	285.9	289.6	291.2	289.6	285.9	280.5	276.4	269.4	264.9	263.2
62.5°	265.4	271.4	275.1	275.4	275.1	271.4	265.4	259.0	252.0	246.8	243.5
65°	240.7	246.8	250.1	252.5	250.1	246.8	240.7	233.6	225.9	218.8	215.2
67.5°	214.0	220.1	223.8	225.8	223.8	220.1	214.0	205.3	198.2	190.1	185.8
70°	194.6	200.7	205.7	207.3	205.7	200.7	194.6	184.3	178.1	170.7	167.0
72.5°	175.5	181.0	185.0	186.9	185.0	181.0	175.5	165.9	158.7	151.3	146.2
75°	142.4	149.7	153.4	155.5	153.4	149.7	142.4	137.0	128.7	121.0	116.8
77.5°	109.7	116.5	118.7	119.8	118.7	116.5	109.7	103.5	97.3	91.6	87.5
80°	88.0	92.1	95.0	95.5	95.0	92.1	88.0	83.1	78.2	72.8	69.1
82.5°	67.7	71.1	72.0	73.0	72.0	71.1	67.7	63.4	59.1	55.1	52.0
85°	37.0	38.7	39.1	38.7	39.1	38.7	37.0	34.1	32.1	30.0	28.8
87.5°	14.2	13.9	13.9	14.6	13.9	13.9	14.2	13.5	13.6	12.9	12.1
90°	9.9	9.9	10.4	10.4	10.4	9.9	9.9	9.9	9.0	8.6	8.2
92.5°	31.3	30.2	29.5	28.8	29.5	30.2	31.3	37.1	43.7	58.1	80.1
95°	130.6	117.0	113.4	106.2	113.4	117.0	130.6	162.7	200.7	256.2	324.9
97.5°	300.9	275.5	262.4	256.7	262.4	275.5	300.9	328.8	381.6	435.7	483.9
100°	408.9	376.4	359.7	352.4	359.7	376.4	408.9	440.1	487.1	533.7	555.8
102.5°	506.2	483.1	464.9	459.5	464.9	483.1	506.2	539.6	571.3	593.7	580.0
105°	628.1	613.2	604.2	598.7	604.2	613.2	628.1	642.5	647.5	627.6	565.8
107.5°	679.4	679.3	676.3	672.6	676.3	679.3	679.4	672.0	648.5	597.4	514.8
110°	685.5	694.1	697.3	697.3	697.3	694.1	685.5	665.2	626.8	563.1	477.2



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	668.5	683.3	691.1	694.3	691.1	683.3	668.5	638.8	593.5	529.1	447.6
115°	626.8	648.5	661.1	667.0	661.1	648.5	626.8	591.5	542.2	480.4	410.3
117.5°	580.4	602.9	615.4	619.0	615.4	602.9	580.4	545.2	499.9	446.6	386.3
120°	550.4	572.1	584.3	587.9	584.3	572.1	550.4	517.0	477.2	427.5	373.3
122.5°	525.1	544.9	557.1	560.4	557.1	544.9	525.1	495.3	458.0	413.8	363.5
125°	492.6	511.1	521.0	525.5	521.0	511.1	492.6	467.2	434.7	395.4	349.3
127.5°	467.9	484.3	493.7	495.7	493.7	484.3	467.9	445.0	414.5	377.9	334.9
130°	452.8	467.7	476.7	479.4	476.7	467.7	452.8	430.2	400.8	365.6	325.8
132.5°	436.9	451.8	460.1	463.2	460.1	451.8	436.9	414.3	386.0	354.0	316.8
135°	410.7	425.6	433.8	436.5	433.8	425.6	410.7	390.9	365.1	336.2	305.0
137.5°	384.0	397.6	405.0	408.1	405.0	397.6	384.0	366.2	344.4	320.3	295.1
140°	367.4	379.1	385.9	388.2	385.9	379.1	367.4	350.7	331.7	310.9	289.6
142.5°	351.5	361.4	367.8	369.7	367.8	361.4	351.5	337.3	320.8	302.9	284.9
145°	329.9	337.5	342.5	344.4	342.5	337.5	329.9	319.0	306.8	292.8	278.8
147.5°	313.0	319.1	322.0	322.8	322.0	319.1	313.0	304.4	295.2	284.4	273.1
150°	303.2	308.6	310.5	310.9	310.5	308.6	303.2	296.4	288.3	279.7	269.7
152.5°	294.9	299.2	301.0	301.5	301.0	299.2	294.9	289.2	282.9	275.0	266.2
155°	283.8	286.9	288.3	288.8	288.3	286.9	283.8	279.2	274.3	268.0	260.7
157.5°	273.5	276.2	277.4	277.3	277.4	276.2	273.5	270.1	266.2	261.3	255.3
160°	267.0	269.3	270.2	269.7	270.2	269.3	267.0	263.9	260.7	256.2	251.7
162.5°	260.9	262.8	263.0	262.9	263.0	262.8	260.9	258.5	255.6	251.9	247.7
165°	252.2	253.0	253.0	253.0	253.0	253.0	252.2	250.3	248.1	245.3	242.2
167.5°	243.7	244.5	244.1	244.0	244.1	244.5	243.7	242.7	241.1	239.1	236.9
170°	238.6	239.1	239.1	238.6	239.1	239.1	238.6	237.7	236.8	235.4	234.1
172.5°	233.9	234.7	234.0	233.5	234.0	234.7	233.9	233.7	233.1	232.2	230.8
175°	228.2	228.6	227.8	227.3	227.8	228.6	228.2	228.2	228.2	227.3	227.3
177.5°	224.8	225.2	224.1	224.1	224.1	225.2	224.8	225.2	225.2	225.2	224.8
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	926.7	930.7	935.6	939.2	945.8	948.7	952.4	955.3	960.6	965.5	971.5
5°	864.3	871.2	880.7	891.0	902.9	911.2	922.7	929.6	943.6	956.4	968.7
7.5°	807.6	816.2	829.6	842.8	858.4	872.5	886.9	902.9	920.8	941.8	959.3
10°	768.8	780.3	794.7	811.2	830.1	846.5	865.9	883.1	905.0	929.6	952.7
12.5°	737.8	747.7	763.8	779.6	799.8	819.9	839.9	862.8	888.2	915.5	944.4
15°	695.1	703.4	716.5	738.4	758.9	778.7	808.7	830.1	862.2	892.6	927.6
17.5°	658.7	668.9	680.0	698.7	720.0	744.7	771.5	798.4	829.3	867.8	907.3
20°	636.4	644.6	657.4	671.7	694.3	719.1	744.6	771.7	809.5	849.5	891.8
22.5°	612.0	620.9	635.3	651.0	670.0	693.7	721.8	751.6	791.1	830.4	876.3
25°	583.3	589.5	602.6	616.6	635.6	655.7	684.9	717.8	756.9	801.7	848.6
27.5°	556.2	561.7	573.7	585.8	602.9	626.9	653.0	686.2	723.0	768.5	820.5
30°	536.8	542.6	553.3	566.4	582.9	603.9	630.6	661.9	701.3	745.8	800.1
32.5°	520.0	525.1	533.2	546.4	562.4	582.8	607.5	639.4	679.0	724.1	777.4
35°	494.0	499.8	506.0	516.3	530.2	549.9	577.1	607.1	645.0	688.6	737.5
37.5°	468.2	474.4	480.0	489.2	501.9	519.4	542.8	574.1	608.3	650.3	697.3
40°	452.1	457.0	461.5	471.4	484.2	500.6	522.4	550.4	586.6	625.7	664.7
42.5°	435.9	440.5	444.4	453.0	464.8	480.5	501.4	528.6	562.2	598.7	633.1
45°	410.5	413.4	418.0	425.3	434.8	449.2	469.4	493.6	522.0	556.6	582.5
47.5°	383.0	387.5	391.3	397.8	405.5	419.6	438.9	459.6	485.4	511.0	529.3
50°	361.9	366.5	371.9	378.0	385.4	398.6	416.3	437.3	459.1	478.8	494.4
52.5°	342.2	346.4	352.1	358.0	367.0	378.2	393.2	411.9	433.4	447.6	460.6
55°	313.1	315.1	321.7	327.4	336.0	344.3	359.5	376.0	389.1	399.8	410.5
57.5°	283.2	286.0	289.8	294.9	303.5	313.1	323.8	338.3	346.1	351.6	359.9
60°	264.1	264.9	267.4	273.5	280.1	288.8	301.1	311.4	317.1	321.7	328.7
62.5°	243.0	243.2	247.3	251.8	256.7	266.1	276.1	284.4	289.1	291.4	298.1
65°	213.5	212.7	215.2	218.8	224.6	230.8	239.4	246.8	246.4	248.8	252.9
67.5°	183.3	182.4	182.4	186.0	190.7	196.2	202.2	206.4	206.5	209.8	211.8
70°	162.9	160.4	162.1	164.9	167.0	171.5	178.1	179.7	180.1	181.8	183.9
72.5°	141.8	141.0	142.4	143.5	145.0	148.5	154.1	155.1	155.2	156.1	159.5
75°	112.7	111.9	111.1	112.3	113.9	116.4	118.4	120.1	119.7	120.1	122.6
77.5°	84.5	82.1	81.8	82.5	82.9	84.3	86.4	86.3	86.7	86.7	89.4
80°	67.0	63.8	63.4	63.4	63.8	64.6	65.4	66.2	65.0	66.2	67.0
82.5°	49.3	47.3	47.2	46.9	47.0	47.1	47.6	48.2	47.8	48.5	49.0
85°	27.2	26.3	25.1	25.9	25.5	24.2	25.1	23.8	23.4	23.8	24.2
87.5°	10.8	11.0	10.1	10.1	9.6	9.8	9.0	8.5	7.9	8.1	9.0
90°	7.7	7.2	6.3	5.9	5.0	4.5	3.6	2.7	1.8	0.9	0.5
92.5°	118.0	145.7	148.1	103.1	61.7	37.1	23.8	16.1	10.5	6.7	5.5
95°	391.8	400.4	326.7	202.0	102.6	54.3	33.9	23.9	19.0	15.4	14.9
97.5°	495.7	427.5	291.8	161.2	88.4	56.4	41.7	32.8	27.8	25.3	24.8
100°	521.0	408.1	260.3	146.4	87.7	61.5	47.9	39.3	34.4	32.6	31.6
102.5°	505.8	373.7	236.4	140.3	90.9	67.6	54.4	46.6	41.2	39.8	39.2
105°	457.3	327.6	213.3	137.8	97.6	77.7	65.0	57.8	53.3	51.1	51.1
107.5°	407.8	295.9	203.5	142.0	107.6	88.3	76.9	69.4	65.7	63.5	62.7
110°	379.6	281.1	200.7	145.9	114.8	96.3	84.5	77.7	73.7	71.9	71.0



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	358.6	272.4	200.7	151.0	121.7	103.9	92.4	85.7	81.6	80.2	79.3
115°	335.7	263.0	202.0	158.6	132.4	115.7	104.4	97.6	93.6	92.2	91.3
117.5°	322.1	258.4	204.9	167.3	143.5	127.6	116.7	109.0	105.0	103.5	102.1
120°	314.5	256.2	207.9	173.1	151.4	135.5	124.3	116.6	112.5	110.7	109.3
122.5°	308.0	254.4	210.4	179.6	159.0	143.1	131.9	123.4	119.4	118.0	116.9
125°	299.1	252.2	214.7	188.5	169.0	154.1	142.4	133.7	129.7	127.5	126.5
127.5°	291.0	251.0	219.4	196.5	178.6	164.3	152.6	143.5	138.3	135.4	134.0
130°	285.6	250.3	222.4	202.0	184.8	170.8	159.1	149.6	143.7	140.1	138.7
132.5°	281.2	250.3	225.6	206.7	190.6	176.6	164.9	155.0	148.4	144.1	142.4
135°	276.1	250.3	230.0	213.3	198.4	184.3	172.1	162.7	155.4	150.0	148.2
137.5°	271.5	250.9	234.1	218.2	203.9	191.2	178.6	169.3	162.1	157.0	155.7
140°	269.3	251.3	235.9	221.4	207.9	194.8	182.6	174.0	166.8	161.3	159.9
142.5°	267.5	251.6	236.9	223.2	210.4	198.0	186.6	178.3	171.1	166.0	165.0
145°	264.8	251.3	238.1	225.9	214.7	202.9	192.5	184.3	178.0	173.5	172.6
147.5°	262.0	250.1	238.6	227.6	217.4	207.1	197.9	190.8	185.0	181.1	180.5
150°	259.8	249.0	238.6	228.6	219.2	209.2	201.5	195.2	189.3	186.2	185.3
152.5°	257.3	247.6	238.2	229.3	220.9	211.8	204.8	198.8	193.7	190.8	190.4
155°	253.0	244.9	237.3	230.0	222.8	215.1	208.7	204.2	199.7	197.0	197.0
157.5°	249.1	242.2	236.1	230.4	224.3	217.7	212.9	209.0	205.1	202.9	203.0
160°	245.8	240.4	235.0	230.4	225.1	219.2	215.1	211.5	208.3	206.5	207.0
162.5°	243.0	238.2	233.9	230.1	225.8	220.6	217.3	214.4	211.6	209.8	210.2
165°	238.6	235.0	232.3	229.6	225.9	222.4	219.6	217.8	215.6	214.2	215.1
167.5°	234.3	231.8	229.7	228.5	225.9	222.9	221.3	220.0	218.7	217.9	218.3
170°	231.8	230.0	228.6	227.8	225.9	223.7	222.4	221.4	220.5	220.1	220.5
172.5°	229.3	227.8	227.2	227.0	225.6	223.7	223.1	222.5	221.6	221.2	222.0
175°	225.9	225.5	225.5	225.9	225.1	223.7	223.7	223.7	223.2	222.8	223.7
177.5°	224.5	224.1	224.1	224.8	224.5	223.8	223.8	224.1	223.8	223.8	224.5
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	974.4	979.0	982.0	987.5	992.1	994.8	997.1	999.1	1001.4	1003.4	1008.9
5°	980.6	991.3	1000.4	1014.4	1027.1	1037.0	1047.7	1057.2	1065.0	1076.1	1084.7
7.5°	977.9	997.0	1016.8	1038.5	1060.6	1081.2	1100.1	1117.8	1133.9	1153.3	1170.3
10°	975.3	1001.2	1026.7	1055.9	1085.9	1111.4	1135.3	1159.6	1177.3	1202.0	1222.9
12.5°	973.4	1003.9	1034.6	1069.8	1102.7	1138.8	1170.5	1188.2	1215.1	1234.9	1259.8
15°	965.0	1005.4	1047.7	1087.2	1134.1	1167.4	1195.4	1229.9	1255.0	1280.1	1307.3
17.5°	950.1	995.8	1043.1	1095.0	1140.0	1175.7	1211.7	1245.1	1275.0	1308.7	1342.4
20°	943.3	988.9	1043.1	1096.2	1140.3	1177.7	1214.7	1251.3	1284.2	1327.4	1366.5
22.5°	928.8	984.0	1034.0	1085.7	1131.0	1171.8	1213.7	1255.3	1299.0	1347.8	1396.8
25°	902.9	958.9	1011.9	1063.0	1108.6	1159.6	1204.4	1260.0	1315.9	1380.5	1441.4
27.5°	876.1	929.6	978.3	1027.5	1080.8	1138.5	1196.7	1259.7	1332.9	1414.4	1500.3
30°	854.4	905.0	952.3	1002.8	1058.4	1123.4	1187.2	1262.0	1346.7	1438.4	1540.5
32.5°	829.0	875.7	921.6	975.3	1035.7	1104.3	1178.6	1260.7	1362.6	1466.8	1571.8
35°	785.7	824.7	872.0	929.2	997.5	1076.1	1162.1	1259.1	1375.9	1495.6	1584.1
37.5°	734.3	770.6	820.5	883.1	954.7	1039.0	1141.1	1256.2	1380.3	1475.8	1504.3
40°	699.7	733.4	785.3	850.2	923.4	1012.7	1124.6	1246.3	1366.5	1427.4	1403.9
42.5°	662.8	698.2	748.7	813.1	891.9	989.0	1103.9	1225.7	1326.4	1349.4	1268.4
45°	604.7	641.3	691.0	756.1	840.8	946.1	1065.8	1176.5	1234.5	1192.9	1067.5
47.5°	550.6	584.9	631.1	698.2	785.6	894.5	1009.8	1098.0	1102.6	1003.5	869.5
50°	513.8	545.4	591.9	658.9	745.8	856.0	960.0	1029.6	998.3	886.1	757.2
52.5°	477.6	508.6	554.4	620.8	706.6	807.6	904.4	953.2	894.4	779.1	669.1
55°	425.3	452.5	497.3	558.6	640.1	733.9	816.1	833.0	756.5	642.9	553.7
57.5°	374.3	399.7	440.5	496.9	571.3	654.4	718.7	715.2	634.3	536.9	466.0
60°	339.8	364.5	400.7	455.7	523.6	595.2	650.3	637.2	557.0	473.0	413.4
62.5°	308.9	330.9	365.1	413.3	475.2	541.6	586.8	567.4	488.9	415.4	368.3
65°	263.2	281.8	311.0	352.1	403.5	458.3	493.2	468.1	401.1	343.9	306.0
67.5°	219.8	234.6	259.0	291.9	335.7	379.7	401.0	375.7	322.1	280.4	252.3
70°	192.1	205.3	224.2	253.4	291.7	328.7	344.7	322.1	276.0	240.2	220.1
72.5°	164.5	175.3	191.9	218.2	248.8	281.0	295.0	273.4	235.5	205.3	186.5
75°	127.1	134.5	146.0	164.1	188.4	213.9	221.7	202.8	178.6	155.9	143.5
77.5°	91.0	97.3	106.0	117.4	134.6	150.8	157.6	146.7	127.9	113.6	103.5
80°	69.9	73.2	80.6	90.1	103.7	113.9	118.4	111.5	98.3	87.6	79.8
82.5°	49.8	53.2	57.6	65.4	74.1	81.0	85.9	81.2	71.7	63.3	58.7
85°	24.2	26.3	28.8	32.1	38.7	42.8	42.4	39.5	35.8	32.5	30.0
87.5°	8.7	9.3	10.4	12.3	13.4	14.8	15.7	15.1	13.9	13.1	12.1
90°	0.9	1.8	2.7	3.6	4.5	5.0	5.9	6.3	7.2	7.7	8.2
92.5°	6.7	10.5	16.1	23.8	37.1	61.7	103.1	148.1	145.7	118.0	80.1
95°	15.4	19.0	23.9	33.9	54.3	102.6	202.0	326.7	400.4	391.8	324.9
97.5°	25.3	27.8	32.8	41.7	56.4	88.4	161.2	291.8	427.5	495.7	483.9
100°	32.6	34.4	39.3	47.9	61.5	87.7	146.4	260.3	408.1	521.0	555.8
102.5°	39.8	41.2	46.6	54.4	67.6	90.9	140.3	236.4	373.7	505.8	580.0
105°	51.1	53.3	57.8	65.0	77.7	97.6	137.8	213.3	327.6	457.3	565.8
107.5°	63.5	65.7	69.4	76.9	88.3	107.6	142.0	203.5	295.9	407.8	514.8
110°	71.9	73.7	77.7	84.5	96.3	114.8	145.9	200.7	281.1	379.6	477.2



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	80.2	81.6	85.7	92.4	103.9	121.7	151.0	200.7	272.4	358.6	447.6
115°	92.2	93.6	97.6	104.4	115.7	132.4	158.6	202.0	263.0	335.7	410.3
117.5°	103.5	105.0	109.0	116.7	127.6	143.5	167.3	204.9	258.4	322.1	386.3
120°	110.7	112.5	116.6	124.3	135.5	151.4	173.1	207.9	256.2	314.5	373.3
122.5°	118.0	119.4	123.4	131.9	143.1	159.0	179.6	210.4	254.4	308.0	363.5
125°	127.5	129.7	133.7	142.4	154.1	169.0	188.5	214.7	252.2	299.1	349.3
127.5°	135.4	138.3	143.5	152.6	164.3	178.6	196.5	219.4	251.0	291.0	334.9
130°	140.1	143.7	149.6	159.1	170.8	184.8	202.0	222.4	250.3	285.6	325.8
132.5°	144.1	148.4	155.0	164.9	176.6	190.6	206.7	225.6	250.3	281.2	316.8
135°	150.0	155.4	162.7	172.1	184.3	198.4	213.3	230.0	250.3	276.1	305.0
137.5°	157.0	162.1	169.3	178.6	191.2	203.9	218.2	234.1	250.9	271.5	295.1
140°	161.3	166.8	174.0	182.6	194.8	207.9	221.4	235.9	251.3	269.3	289.6
142.5°	166.0	171.1	178.3	186.6	198.0	210.4	223.2	236.9	251.6	267.5	284.9
145°	173.5	178.0	184.3	192.5	202.9	214.7	225.9	238.1	251.3	264.8	278.8
147.5°	181.1	185.0	190.8	197.9	207.1	217.4	227.6	238.6	250.1	262.0	273.1
150°	186.2	189.3	195.2	201.5	209.2	219.2	228.6	238.6	249.0	259.8	269.7
152.5°	190.8	193.7	198.8	204.8	211.8	220.9	229.3	238.2	247.6	257.3	266.2
155°	197.0	199.7	204.2	208.7	215.1	222.8	230.0	237.3	244.9	253.0	260.7
157.5°	202.9	205.1	209.0	212.9	217.7	224.3	230.4	236.1	242.2	249.1	255.3
160°	206.5	208.3	211.5	215.1	219.2	225.1	230.4	235.0	240.4	245.8	251.7
162.5°	209.8	211.6	214.4	217.3	220.6	225.8	230.1	233.9	238.2	243.0	247.7
165°	214.2	215.6	217.8	219.6	222.4	225.9	229.6	232.3	235.0	238.6	242.2
167.5°	217.9	218.7	220.0	221.3	222.9	225.9	228.5	229.7	231.8	234.3	236.9
170°	220.1	220.5	221.4	222.4	223.7	225.9	227.8	228.6	230.0	231.8	234.1
172.5°	221.2	221.6	222.5	223.1	223.7	225.6	227.0	227.2	227.8	229.3	230.8
175°	222.8	223.2	223.7	223.7	223.7	225.1	225.9	225.5	225.5	225.9	227.3
177.5°	223.8	223.8	224.1	223.8	223.8	224.5	224.8	224.1	224.1	224.5	224.8
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1013.5	1016.2	1021.8	1019.8	1022.5	1023.7	1025.1
5°	1095.4	1108.6	1114.4	1113.5	1122.1	1120.1	1118.0
7.5°	1187.9	1201.7	1209.4	1219.1	1224.6	1225.0	1229.9
10°	1240.2	1258.3	1265.7	1276.0	1282.5	1286.3	1285.9
12.5°	1280.3	1294.5	1311.1	1316.1	1325.0	1329.7	1328.0
15°	1328.6	1351.3	1368.6	1377.2	1388.3	1391.5	1396.1
17.5°	1371.7	1402.1	1422.3	1449.1	1459.2	1465.4	1461.7
20°	1404.3	1444.2	1464.4	1496.5	1514.2	1523.6	1520.4
22.5°	1442.8	1486.1	1523.3	1551.1	1578.0	1590.8	1593.4
25°	1508.8	1568.0	1622.8	1659.4	1692.7	1700.5	1717.8
27.5°	1582.5	1652.4	1710.9	1749.4	1772.6	1781.3	1786.7
30°	1629.0	1698.4	1742.5	1767.1	1774.6	1773.7	1772.9
32.5°	1651.6	1695.2	1703.6	1696.7	1679.7	1665.5	1650.5
35°	1619.5	1587.0	1538.4	1475.9	1429.8	1383.4	1378.8
37.5°	1456.5	1352.6	1271.8	1181.5	1129.5	1097.3	1075.1
40°	1303.1	1185.1	1087.2	1011.1	958.0	937.1	916.5
42.5°	1136.6	1023.8	937.2	873.5	833.6	810.3	794.1
45°	923.4	823.9	756.1	710.0	678.3	660.2	649.9
47.5°	756.7	683.1	625.4	592.2	570.3	556.2	556.3
50°	667.2	596.8	558.6	532.3	513.3	502.2	504.3
52.5°	587.9	535.4	502.6	480.6	466.6	459.8	459.5
55°	491.5	453.7	432.3	416.3	406.8	399.0	400.7
57.5°	420.5	388.6	374.2	360.9	354.3	351.2	346.7
60°	376.4	351.7	339.4	328.7	322.1	319.6	315.1
62.5°	337.2	317.8	305.8	297.1	291.1	290.3	286.8
65°	283.4	268.6	257.9	253.8	247.6	246.0	246.0
67.5°	233.6	223.0	214.8	211.0	208.2	208.7	206.7
70°	202.4	193.8	188.4	184.3	182.2	182.6	181.0
72.5°	177.1	167.4	162.7	160.3	157.6	158.6	158.0
75°	134.1	129.1	126.7	124.2	122.6	121.8	121.0
77.5°	98.5	94.1	92.2	90.9	91.1	89.1	90.6
80°	76.1	72.4	71.1	69.1	68.7	68.7	68.3
82.5°	55.7	53.6	52.8	51.0	50.3	50.9	49.8
85°	28.8	27.2	26.8	26.8	25.9	25.1	27.2
87.5°	12.3	11.0	11.2	10.9	10.9	10.6	10.0
90°	8.6	9.0	9.9	9.9	9.9	10.4	10.4
92.5°	58.1	43.7	37.1	31.3	30.2	29.5	28.8
95°	256.2	200.7	162.7	130.6	117.0	113.4	106.2
97.5°	435.7	381.6	328.8	300.9	275.5	262.4	256.7
100°	533.7	487.1	440.1	408.9	376.4	359.7	352.4
102.5°	593.7	571.3	539.6	506.2	483.1	464.9	459.5
105°	627.6	647.5	642.5	628.1	613.2	604.2	598.7
107.5°	597.4	648.5	672.0	679.4	679.3	676.3	672.6
110°	563.1	626.8	665.2	685.5	694.1	697.3	697.3



TEST NUMBER: P333216-927

CATALOG NUMBER: S125DIP-S850D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	529.1	593.5	638.8	668.5	683.3	691.1	694.3
115°	480.4	542.2	591.5	626.8	648.5	661.1	667.0
117.5°	446.6	499.9	545.2	580.4	602.9	615.4	619.0
120°	427.5	477.2	517.0	550.4	572.1	584.3	587.9
122.5°	413.8	458.0	495.3	525.1	544.9	557.1	560.4
125°	395.4	434.7	467.2	492.6	511.1	521.0	525.5
127.5°	377.9	414.5	445.0	467.9	484.3	493.7	495.7
130°	365.6	400.8	430.2	452.8	467.7	476.7	479.4
132.5°	354.0	386.0	414.3	436.9	451.8	460.1	463.2
135°	336.2	365.1	390.9	410.7	425.6	433.8	436.5
137.5°	320.3	344.4	366.2	384.0	397.6	405.0	408.1
140°	310.9	331.7	350.7	367.4	379.1	385.9	388.2
142.5°	302.9	320.8	337.3	351.5	361.4	367.8	369.7
145°	292.8	306.8	319.0	329.9	337.5	342.5	344.4
147.5°	284.4	295.2	304.4	313.0	319.1	322.0	322.8
150°	279.7	288.3	296.4	303.2	308.6	310.5	310.9
152.5°	275.0	282.9	289.2	294.9	299.2	301.0	301.5
155°	268.0	274.3	279.2	283.8	286.9	288.3	288.8
157.5°	261.3	266.2	270.1	273.5	276.2	277.4	277.3
160°	256.2	260.7	263.9	267.0	269.3	270.2	269.7
162.5°	251.9	255.6	258.5	260.9	262.8	263.0	262.9
165°	245.3	248.1	250.3	252.2	253.0	253.0	253.0
167.5°	239.1	241.1	242.7	243.7	244.5	244.1	244.0
170°	235.4	236.8	237.7	238.6	239.1	239.1	238.6
172.5°	232.2	233.1	233.7	233.9	234.7	234.0	233.5
175°	227.3	228.2	228.2	228.2	228.6	227.8	227.3
177.5°	225.2	225.2	225.2	224.8	225.2	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1

(END OF REPORT)