

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333594-927

Luminaire Tested: **S125RDIP-S1090D810U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333594-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5680.1 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	66	59	53	72	62	56	50	55	50	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	40	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8412	8412	8412	8412
5°	9678	8423	7439	8423
10°	11101	8380	6564	8380
15°	11990	8294	5834	8294
20°	13221	8194	5388	8194
25°	15302	8062	4999	8062
30°	16651	7923	4745	7923
35°	14046	7761	4511	7761
40°	9809	7470	4309	7470
45°	7277	7077	4112	7077
50°	5801	6666	3943	6666
55°	4925	6159	3792	6159
60°	4255	5704	3550	5704
65°	3791	5213	3055	5213
70°	3331	4775	2787	4775
75°	2882	4135	2615	4135
80°	2187	3481	2187	3481
85°	1823	2734	2060	2734



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.9	2.2
10°-20°	366.0	6.4
20°-30°	580.4	10.2
30°-40°	699.9	12.3
40°-50°	625.0	11.0
50°-60°	479.3	8.4
60°-70°	311.5	5.5
70°-80°	151.4	2.7
80°-90°	37.9	0.7
90°-100°	222.7	3.9
100°-110°	478.7	8.4
110°-120°	449.3	7.9
120°-130°	364.1	6.4
130°-140°	292.2	5.1
140°-150°	220.5	3.9
150°-160°	155.2	2.7
160°-170°	91.5	1.6
170°-180°	29.8	0.5
0°-30°	1071.3	18.9
0°-40°	1771.2	31.2
0°-60°	2875.5	50.6
0°-90°	3376.2	59.4
90°-120°	1150.7	20.3
90°-150°	2027.5	35.7
90°-180°	2304.0	40.6
0°-180°	5680.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1302	1302	1302	1302	1302	
5°	1493	1299	1147	1299	1493	149
15°	1793	1240	873	1240	1793	514
25°	2147	1131	702	1131	2147	986
35°	1782	984	572	984	1782	1076
45°	797	775	450	775	797	636
55°	437	547	337	547	437	397
65°	248	341	200	341	248	247
75°	116	166	105	166	116	123
85°	25	37	28	37	25	29
90°	14	1	14	1	14	11
95°	146	20	146	20	146	206
105°	821	70	821	70	821	816
115°	914	125	914	125	914	893
125°	720	173	720	173	720	652
135°	598	203	598	203	598	464
145°	472	237	472	237	472	300
155°	396	270	396	270	396	184
165°	347	295	347	295	347	99
175°	312	307	312	307	312	30
180°	307	307	307	307	307	



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1370.1	1369.2	1371.0	1366.2	1366.7	1359.4	1359.4	1353.8	1346.6	1341.0	1338.4
5°	1492.8	1493.9	1491.8	1483.8	1478.4	1470.4	1461.3	1445.3	1431.9	1419.0	1408.9
7.5°	1619.2	1619.9	1612.9	1610.4	1597.0	1587.1	1566.9	1545.1	1525.7	1501.2	1482.3
10°	1692.8	1692.3	1684.7	1678.9	1667.1	1652.2	1632.4	1606.7	1582.6	1555.9	1530.3
12.5°	1735.6	1734.2	1731.8	1724.7	1713.7	1700.5	1683.7	1658.4	1628.8	1599.6	1569.6
15°	1793.3	1789.5	1782.6	1773.5	1758.0	1742.5	1723.8	1701.4	1673.0	1639.8	1612.1
17.5°	1864.7	1864.9	1854.2	1841.5	1820.4	1793.1	1764.2	1728.0	1689.5	1653.0	1623.4
20°	1923.7	1922.2	1911.5	1886.9	1862.8	1828.6	1795.5	1751.0	1704.0	1656.5	1619.5
22.5°	2008.5	2004.3	1993.1	1960.9	1923.6	1879.5	1828.8	1774.6	1717.7	1663.7	1615.3
25°	2147.3	2144.0	2122.1	2084.7	2032.3	1964.4	1898.1	1823.8	1742.0	1670.9	1612.1
27.5°	2242.2	2238.7	2222.5	2191.3	2143.0	2071.6	1981.8	1882.5	1780.4	1682.5	1597.8
30°	2232.8	2240.8	2238.7	2224.3	2187.9	2123.8	2040.9	1929.1	1807.8	1692.8	1591.7
32.5°	2098.5	2105.7	2124.5	2152.8	2155.0	2129.3	2067.4	1964.2	1838.6	1707.8	1587.1
35°	1781.5	1791.2	1827.6	1884.8	1959.6	2022.1	2035.0	1979.3	1866.5	1725.9	1580.0
37.5°	1369.6	1422.2	1452.9	1513.1	1626.2	1741.2	1851.9	1892.7	1844.6	1718.5	1568.5
40°	1163.5	1176.3	1230.8	1298.7	1393.9	1513.7	1671.4	1785.3	1789.1	1701.4	1550.5
42.5°	995.8	1012.0	1049.5	1103.7	1185.2	1305.0	1467.8	1618.0	1687.7	1654.3	1527.0
45°	796.7	809.0	836.2	878.0	940.5	1039.4	1179.5	1353.3	1491.2	1545.2	1464.0
47.5°	654.4	661.1	684.8	716.6	762.9	835.0	943.4	1094.2	1259.7	1375.7	1364.3
50°	577.4	584.9	603.1	627.2	666.2	727.1	813.8	939.4	1110.0	1251.6	1280.0
52.5°	517.5	523.8	535.1	557.9	590.1	636.9	706.9	820.5	974.0	1124.7	1190.2
55°	437.4	441.6	450.8	463.6	489.3	522.9	583.4	661.9	786.0	937.8	1034.0
57.5°	371.3	373.4	379.2	391.1	408.8	433.4	477.1	543.7	632.6	769.4	875.6
60°	329.4	331.5	339.0	347.0	360.9	383.3	417.6	464.1	549.6	662.5	769.9
62.5°	296.0	297.3	300.5	308.5	320.7	338.0	365.0	402.9	471.0	570.1	671.5
65°	248.1	248.6	249.7	256.1	263.6	276.4	294.1	320.8	372.2	447.0	536.8
67.5°	202.1	202.9	206.6	208.8	216.7	223.4	233.8	254.2	290.3	340.8	410.7
70°	176.4	175.9	179.7	182.4	185.0	193.1	199.9	216.6	239.0	277.5	335.8
72.5°	152.5	151.1	152.7	153.7	157.2	162.6	169.6	179.7	197.1	223.6	268.2
75°	115.5	116.1	116.1	117.1	119.8	121.9	124.1	129.4	139.0	156.7	180.7
77.5°	81.0	80.2	82.5	82.8	84.4	86.7	88.6	90.7	94.7	101.9	114.3
80°	58.8	58.8	59.3	60.9	60.4	61.5	64.2	66.3	71.1	75.4	79.7
82.5°	45.2	44.7	45.2	45.6	45.5	46.5	47.5	47.9	49.7	51.9	54.8
85°	24.6	24.6	25.1	25.1	25.7	25.7	26.2	26.2	26.2	26.7	27.3
87.5°	12.3	11.8	11.2	11.2	11.7	12.3	11.8	11.2	11.1	10.9	11.2
90°	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2	10.5	9.9	8.6
92.5°	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8	161.7	199.7	202.9
95°	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4	537.0	548.8	447.8
97.5°	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3	679.5	586.1	399.9
100°	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8	714.2	559.4	356.8
102.5°	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0	693.4	512.2	324.1
105°	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5	626.9	449.1	292.4
107.5°	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6	559.0	405.6	279.0
110°	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1	520.3	385.2	275.0



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5	491.5	373.4	275.0
115°	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4	460.2	360.5	276.9
117.5°	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5	441.5	354.2	281.0
120°	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6	431.1	351.2	284.9
122.5°	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3	422.2	348.7	288.4
125°	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8	410.0	345.6	294.2
127.5°	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0	398.9	344.1	300.8
130°	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6	391.5	343.2	304.8
132.5°	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2	385.6	343.2	309.2
135°	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1	378.4	343.2	315.3
137.5°	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5	372.2	343.9	320.8
140°	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0	369.2	344.4	323.3
142.5°	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6	366.7	344.9	324.8
145°	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1	363.0	344.4	326.5
147.5°	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2	359.1	342.8	327.0
150°	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8	356.2	341.3	327.0
152.5°	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8	352.7	339.3	326.5
155°	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4	346.9	335.7	325.2
157.5°	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0	341.4	332.0	323.6
160°	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0	337.0	329.5	322.1
162.5°	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5	333.0	326.5	320.6
165°	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0	327.0	322.1	318.4
167.5°	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8	321.2	317.7	314.9
170°	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8	317.7	315.3	313.4
172.5°	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4	314.3	312.3	311.4
175°	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6	309.7	309.1	309.1
177.5°	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2	307.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1338.4	1335.4	1329.8	1324.7	1318.3	1312.7	1308.9	1304.2	1298.2	1290.9	1284.9
5°	1397.6	1385.8	1370.4	1357.0	1339.9	1326.5	1312.6	1299.3	1285.9	1268.8	1253.8
7.5°	1463.3	1439.0	1415.4	1385.7	1358.8	1334.7	1311.5	1288.2	1265.3	1241.0	1217.6
10°	1503.5	1474.1	1441.5	1404.1	1369.8	1337.2	1307.3	1277.9	1246.9	1219.6	1190.2
12.5°	1541.2	1503.2	1465.9	1418.6	1377.5	1337.7	1299.6	1262.9	1229.8	1194.4	1162.8
15°	1575.2	1537.7	1496.0	1438.3	1381.1	1332.9	1288.0	1240.5	1199.3	1159.7	1124.4
17.5°	1588.3	1549.0	1500.6	1445.1	1382.6	1322.1	1264.2	1212.0	1163.6	1117.5	1077.8
20°	1583.2	1545.2	1495.5	1442.6	1375.7	1312.6	1250.1	1192.3	1138.4	1089.6	1047.4
22.5°	1570.7	1531.5	1483.5	1427.6	1364.1	1297.2	1230.4	1168.8	1112.2	1061.8	1015.8
25°	1552.2	1498.7	1449.5	1395.0	1334.6	1268.3	1199.3	1131.4	1071.0	1019.6	969.4
27.5°	1532.8	1466.1	1403.5	1349.3	1285.5	1226.3	1159.8	1090.2	1026.7	974.4	922.8
30°	1515.3	1440.4	1371.4	1310.0	1249.5	1193.4	1130.3	1062.4	997.2	943.2	890.8
32.5°	1493.4	1413.9	1338.1	1267.2	1208.9	1153.2	1096.1	1031.2	967.7	912.0	858.7
35°	1466.1	1364.5	1282.1	1206.7	1142.1	1088.1	1036.7	984.4	920.8	863.0	811.1
37.5°	1430.1	1314.9	1219.6	1137.5	1069.2	1015.0	974.5	926.6	868.5	813.3	765.1
40°	1408.3	1279.0	1174.6	1093.4	1021.8	964.6	926.6	886.0	833.1	781.2	733.0
42.5°	1379.3	1246.0	1129.3	1044.7	972.6	917.5	879.1	843.6	799.2	750.4	698.8
45°	1322.2	1182.2	1059.7	968.8	896.1	842.1	806.3	774.8	741.1	696.2	651.3
47.5°	1248.0	1115.6	987.5	888.2	817.0	766.8	732.1	707.2	683.1	644.9	601.3
50°	1188.6	1060.8	935.6	839.5	763.5	715.9	683.3	663.5	641.6	606.9	570.5
52.5°	1118.4	1004.3	881.8	783.4	711.8	667.2	635.8	616.1	598.0	569.7	535.0
55°	1007.9	907.9	795.6	706.3	640.6	595.6	565.7	547.0	536.3	512.2	485.0
57.5°	880.3	808.7	709.6	623.5	565.4	521.0	499.1	483.2	471.0	454.1	434.8
60°	791.3	741.1	652.3	570.5	517.1	474.8	455.0	441.6	430.4	416.0	401.0
62.5°	701.1	664.5	587.3	517.1	467.9	432.5	413.9	401.9	389.0	379.2	364.6
65°	580.1	547.5	494.0	438.9	393.6	365.2	351.8	341.1	333.1	322.4	312.3
67.5°	451.3	438.0	401.1	363.1	330.5	305.3	293.7	286.3	276.6	270.2	263.2
70°	372.2	365.8	339.5	314.4	283.9	266.8	256.1	252.9	241.1	234.7	229.9
72.5°	302.0	299.0	283.9	266.5	245.0	230.0	220.1	216.6	209.1	203.9	200.8
75°	206.9	208.0	205.3	194.1	186.1	176.4	167.9	165.7	160.4	156.1	153.4
77.5°	130.9	136.3	136.6	136.0	132.8	126.9	123.4	121.8	116.5	114.9	114.3
80°	89.8	95.7	101.1	100.5	99.4	97.8	95.1	93.6	90.9	89.3	88.2
82.5°	59.9	65.4	69.8	72.7	72.5	70.9	69.1	68.4	67.8	66.6	66.4
85°	28.4	29.4	31.0	34.8	37.4	37.9	37.4	36.9	35.3	35.8	36.4
87.5°	11.5	11.2	11.5	11.2	10.6	12.4	13.5	13.8	13.1	12.4	11.9
90°	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6	1.3	2.5	3.7
92.5°	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5	9.2	14.3	22.0
95°	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4	21.1	26.0	32.8
97.5°	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9	34.7	38.2	45.0
100°	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3	44.6	47.1	53.9
102.5°	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8	54.5	56.5	63.8
105°	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0	70.0	73.1	79.3
107.5°	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9	87.1	90.1	95.1
110°	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3	98.5	100.9	106.5



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6	109.9	111.9	117.4
115°	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1	126.4	128.3	133.8
117.5°	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0	141.9	143.9	149.4
120°	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9	151.8	154.2	159.8
122.5°	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3	161.7	163.7	169.2
125°	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4	174.7	177.8	183.3
127.5°	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7	185.6	189.6	196.6
130°	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1	192.0	196.9	205.0
132.5°	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1	197.5	203.4	212.5
135°	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2	205.7	213.1	223.0
137.5°	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3	215.2	222.1	232.0
140°	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3	221.1	228.5	238.4
142.5°	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2	227.6	234.5	244.4
145°	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6	237.8	244.1	252.7
147.5°	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5	248.3	253.6	261.7
150°	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0	255.2	259.5	267.6
152.5°	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9	261.7	265.5	272.5
155°	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1	270.1	273.8	280.0
157.5°	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2	278.1	281.1	286.4
160°	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7	283.0	285.6	289.9
162.5°	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1	287.6	290.0	293.8
165°	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9	293.6	295.5	298.6
167.5°	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3	298.7	299.8	301.5
170°	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3	301.7	302.3	303.5
172.5°	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3	303.2	303.7	305.0
175°	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6	305.4	306.0	306.6
177.5°	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7	306.7	306.7	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1280.6	1274.7	1270.4	1261.9	1255.8	1253.3	1248.6	1247.3	1252.0	1248.6	1248.2
5°	1242.6	1227.1	1214.8	1202.5	1189.1	1180.6	1167.8	1165.6	1162.4	1157.5	1156.5
7.5°	1196.9	1176.7	1160.9	1140.6	1122.9	1108.7	1092.7	1085.1	1080.9	1074.7	1066.4
10°	1166.1	1142.1	1120.7	1100.3	1078.5	1060.8	1044.7	1032.5	1024.5	1016.9	1013.8
12.5°	1135.8	1111.3	1083.9	1059.3	1034.8	1015.0	997.3	989.3	980.4	971.6	964.2
15°	1088.6	1056.0	1026.0	997.7	976.8	955.5	938.3	926.6	913.2	909.5	895.1
17.5°	1038.6	1006.5	971.5	941.7	917.5	894.0	875.1	861.8	851.8	838.0	831.3
20°	1007.3	969.4	935.2	907.9	881.1	853.3	834.1	822.8	813.3	802.0	796.7
22.5°	974.0	936.8	901.8	869.8	842.6	815.3	801.6	790.0	779.0	768.7	761.6
25°	925.0	887.6	850.6	817.5	789.2	769.4	753.4	740.0	734.1	724.0	716.4
27.5°	876.5	836.8	798.5	765.4	743.2	723.7	710.5	699.9	689.3	680.4	673.9
30°	845.3	804.7	763.0	736.8	713.3	694.5	680.1	669.9	661.9	653.9	649.1
32.5°	814.1	772.2	735.1	706.9	684.6	668.4	653.6	643.9	635.4	626.5	620.8
35°	764.1	721.3	691.3	663.5	641.6	626.6	616.5	602.6	595.6	589.2	583.4
37.5°	717.6	677.8	645.4	621.0	601.9	587.1	573.9	566.4	557.9	552.1	547.2
40°	683.3	647.0	617.6	591.9	578.0	561.4	549.1	539.5	533.1	525.6	520.2
42.5°	652.5	618.7	590.2	567.0	549.8	535.8	523.9	514.3	506.1	500.8	496.3
45°	609.0	575.3	547.5	526.1	510.1	496.7	484.4	479.6	468.9	462.5	460.3
47.5°	564.0	533.9	507.0	487.3	470.9	458.2	446.6	436.8	430.9	424.6	421.2
50°	533.6	504.7	479.6	460.3	444.3	430.4	419.7	413.3	405.3	399.4	395.1
52.5°	503.3	476.5	451.4	433.0	419.1	405.2	393.2	386.8	379.2	375.4	372.5
55°	459.9	431.5	410.1	391.9	377.5	364.6	353.4	347.0	342.2	338.4	337.4
57.5°	410.7	388.2	368.3	351.9	336.9	324.9	315.1	309.0	304.7	304.1	301.0
60°	378.6	358.2	340.1	322.4	309.6	298.3	289.8	282.8	278.5	278.1	276.9
62.5°	346.5	327.0	310.1	294.6	283.0	272.3	264.1	256.4	253.7	251.1	248.7
65°	298.9	281.2	267.4	255.0	242.7	233.6	225.6	220.9	214.9	211.8	205.9
67.5°	252.2	238.4	225.1	214.8	205.1	196.5	189.8	182.7	178.7	176.1	171.8
70°	221.3	210.6	197.3	186.1	178.6	171.7	166.3	158.3	155.6	153.4	151.3
72.5°	192.3	182.8	171.7	162.6	155.0	148.5	142.4	138.6	135.9	133.8	132.5
75°	151.3	142.2	132.6	126.2	120.8	115.5	112.3	109.6	108.5	108.0	105.8
77.5°	111.1	106.3	98.6	93.5	89.9	87.8	84.9	83.5	83.4	81.0	80.3
80°	85.0	82.3	75.9	73.8	71.1	69.0	67.3	64.7	62.0	60.9	59.3
82.5°	63.2	60.5	58.0	54.5	52.3	51.0	49.4	48.4	48.8	47.3	46.5
85°	33.7	31.0	29.9	29.4	28.4	29.4	28.8	28.4	27.8	27.3	27.8
87.5°	11.6	12.0	11.6	12.8	11.6	12.3	12.4	12.0	12.2	12.3	12.1
90°	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2	11.8	12.4	13.6
92.5°	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8	79.7	60.0	50.8
95°	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4	351.2	275.0	223.0
97.5°	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3	597.2	523.0	450.7
100°	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8	731.5	667.7	603.3
102.5°	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0	813.8	783.2	739.6
105°	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5	860.4	887.6	880.8
107.5°	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6	818.9	888.8	921.1
110°	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1	771.7	859.1	911.7



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5	725.2	813.5	875.6
115°	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4	658.5	743.3	810.8
117.5°	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5	612.2	685.3	747.3
120°	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6	586.0	654.1	708.6
122.5°	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3	567.1	627.8	678.9
125°	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8	542.0	595.9	640.5
127.5°	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0	517.9	568.2	610.0
130°	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6	501.1	549.4	589.7
132.5°	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2	485.2	529.1	567.8
135°	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1	460.8	500.5	535.8
137.5°	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5	439.0	472.0	501.9
140°	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0	426.1	454.6	480.6
142.5°	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6	415.3	439.7	462.3
145°	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1	401.4	420.6	437.3
147.5°	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2	389.8	404.6	417.2
150°	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8	383.4	395.1	406.3
152.5°	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8	377.0	387.8	396.4
155°	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4	367.3	376.0	382.8
157.5°	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0	358.1	364.8	370.2
160°	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0	351.2	357.4	361.7
162.5°	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5	345.2	350.5	354.3
165°	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0	336.4	340.1	343.2
167.5°	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8	327.6	330.5	332.7
170°	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8	322.7	324.6	325.8
172.5°	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4	318.2	319.6	320.4
175°	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6	311.6	312.8	312.8
177.5°	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2	308.7	308.7	308.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1247.7	1243.0	1241.7	1243.4	1241.7	1243.0	1247.7	1248.2	1248.6	1252.0	1247.3
5°	1151.2	1145.8	1148.5	1147.4	1148.5	1145.8	1151.2	1156.5	1157.5	1162.4	1165.6
7.5°	1066.3	1059.6	1052.6	1054.8	1052.6	1059.6	1066.3	1066.4	1074.7	1080.9	1085.1
10°	1006.8	1001.5	998.2	1000.9	998.2	1001.5	1006.8	1013.8	1016.9	1024.5	1032.5
12.5°	956.7	953.5	950.8	949.6	950.8	953.5	956.7	964.2	971.6	980.4	989.3
15°	888.7	882.3	879.6	872.6	879.6	882.3	888.7	895.1	909.5	913.2	926.6
17.5°	825.9	823.7	816.7	813.8	816.7	823.7	825.9	831.3	838.0	851.8	861.8
20°	788.6	786.5	779.6	783.9	779.6	786.5	788.6	796.7	802.0	813.3	822.8
22.5°	757.9	753.1	750.9	749.6	750.9	753.1	757.9	761.6	768.7	779.0	790.0
25°	714.3	707.3	704.7	701.5	704.7	707.3	714.3	716.4	724.0	734.1	740.0
27.5°	670.9	667.2	663.6	662.8	663.6	667.2	670.9	673.9	680.4	689.3	699.9
30°	642.7	639.0	636.3	636.3	636.3	639.0	642.7	649.1	653.9	661.9	669.9
32.5°	617.4	614.6	611.9	611.5	611.9	614.6	617.4	620.8	626.5	635.4	643.9
35°	580.7	576.4	575.3	572.1	575.3	576.4	580.7	583.4	589.2	595.6	602.6
37.5°	542.5	538.9	538.8	538.5	538.8	538.9	542.5	547.2	552.1	557.9	566.4
40°	518.1	515.4	514.9	511.1	514.9	515.4	518.1	520.2	525.6	533.1	539.5
42.5°	492.0	490.6	488.8	487.2	488.8	490.6	492.0	496.3	500.8	506.1	514.3
45°	456.6	452.9	452.9	450.2	452.9	452.9	456.6	460.3	462.5	468.9	479.6
47.5°	420.0	417.2	417.5	414.7	417.5	417.2	420.0	421.2	424.6	430.9	436.8
50°	395.7	394.0	393.6	392.4	393.6	394.0	395.7	395.1	399.4	405.3	413.3
52.5°	371.3	370.5	372.6	370.2	372.6	370.5	371.3	372.5	375.4	379.2	386.8
55°	338.4	336.8	340.1	336.8	340.1	336.8	338.4	337.4	338.4	342.2	347.0
57.5°	300.7	299.2	302.1	300.5	302.1	299.2	300.7	301.0	304.1	304.7	309.0
60°	275.9	272.7	274.3	274.8	274.3	272.7	275.9	276.9	278.1	278.5	282.8
62.5°	246.4	244.5	245.7	243.2	245.7	244.5	246.4	248.7	251.1	253.7	256.4
65°	204.8	203.2	201.1	199.9	201.1	203.2	204.8	205.9	211.8	214.9	220.9
67.5°	172.1	168.2	168.1	169.0	168.1	168.2	172.1	171.8	176.1	178.7	182.7
70°	148.1	148.1	147.6	147.6	147.6	148.1	148.1	151.3	153.4	155.6	158.3
72.5°	131.4	131.0	130.0	129.6	130.0	131.0	131.4	132.5	133.8	135.9	138.6
75°	105.8	106.4	105.4	104.8	105.4	106.4	105.8	105.8	108.0	108.5	109.6
77.5°	78.2	75.9	77.1	75.9	77.1	75.9	78.2	80.3	81.0	83.4	83.5
80°	59.3	58.8	60.4	58.8	60.4	58.8	59.3	59.3	60.9	62.0	64.7
82.5°	47.0	46.4	47.1	45.9	47.1	46.4	47.0	46.5	47.3	48.8	48.4
85°	28.4	27.8	27.3	27.8	27.3	27.8	28.4	27.8	27.3	27.8	28.4
87.5°	12.6	12.1	12.3	12.3	12.3	12.1	12.6	12.1	12.3	12.2	12.0
90°	13.6	13.6	14.3	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2
92.5°	42.9	41.4	40.5	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8
95°	179.0	160.4	155.5	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4
97.5°	412.4	377.7	359.7	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3
100°	560.5	515.9	493.1	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8
102.5°	693.9	662.1	637.2	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0
105°	860.9	840.5	828.1	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5
107.5°	931.2	931.1	927.0	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6
110°	939.6	951.4	955.8	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	916.3	936.5	947.3	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5
115°	859.1	888.8	906.2	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4
117.5°	795.6	826.2	843.5	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5
120°	754.4	784.2	800.9	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6
122.5°	719.8	747.0	763.7	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3
125°	675.2	700.5	714.2	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8
127.5°	641.4	663.8	676.8	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0
130°	620.7	641.1	653.5	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6
132.5°	598.8	619.2	630.7	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2
135°	563.0	583.4	594.6	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1
137.5°	526.4	544.9	555.2	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5
140°	503.6	519.7	528.9	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0
142.5°	481.8	495.4	504.2	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6
145°	452.2	462.7	469.5	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1
147.5°	429.0	437.4	441.4	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2
150°	415.7	423.0	425.6	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8
152.5°	404.3	410.2	412.6	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8
155°	389.0	393.3	395.1	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4
157.5°	375.0	378.6	380.3	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0
160°	366.1	369.2	370.4	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0
162.5°	357.7	360.2	360.5	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5
165°	345.6	346.9	346.9	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0
167.5°	334.0	335.1	334.6	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8
170°	327.0	327.6	327.6	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8
172.5°	320.6	321.7	320.8	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4
175°	312.8	313.4	312.2	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6
177.5°	308.2	308.7	307.2	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1248.6	1253.3	1255.8	1261.9	1270.4	1274.7	1280.6	1284.9	1290.9	1298.2	1304.2
5°	1167.8	1180.6	1189.1	1202.5	1214.8	1227.1	1242.6	1253.8	1268.8	1285.9	1299.3
7.5°	1092.7	1108.7	1122.9	1140.6	1160.9	1176.7	1196.9	1217.6	1241.0	1265.3	1288.2
10°	1044.7	1060.8	1078.5	1100.3	1120.7	1142.1	1166.1	1190.2	1219.6	1246.9	1277.9
12.5°	997.3	1015.0	1034.8	1059.3	1083.9	1111.3	1135.8	1162.8	1194.4	1229.8	1262.9
15°	938.3	955.5	976.8	997.7	1026.0	1056.0	1088.6	1124.4	1159.7	1199.3	1240.5
17.5°	875.1	894.0	917.5	941.7	971.5	1006.5	1038.6	1077.8	1117.5	1163.6	1212.0
20°	834.1	853.3	881.1	907.9	935.2	969.4	1007.3	1047.4	1089.6	1138.4	1192.3
22.5°	801.6	815.3	842.6	869.8	901.8	936.8	974.0	1015.8	1061.8	1112.2	1168.8
25°	753.4	769.4	789.2	817.5	850.6	887.6	925.0	969.4	1019.6	1071.0	1131.4
27.5°	710.5	723.7	743.2	765.4	798.5	836.8	876.5	922.8	974.4	1026.7	1090.2
30°	680.1	694.5	713.3	736.8	763.0	804.7	845.3	890.8	943.2	997.2	1062.4
32.5°	653.6	668.4	684.6	706.9	735.1	772.2	814.1	858.7	912.0	967.7	1031.2
35°	616.5	626.6	641.6	663.5	691.3	721.3	764.1	811.1	863.0	920.8	984.4
37.5°	573.9	587.1	601.9	621.0	645.4	677.8	717.6	765.1	813.3	868.5	926.6
40°	549.1	561.4	578.0	591.9	617.6	647.0	683.3	733.0	781.2	833.1	886.0
42.5°	523.9	535.8	549.8	567.0	590.2	618.7	652.5	698.8	750.4	799.2	843.6
45°	484.4	496.7	510.1	526.1	547.5	575.3	609.0	651.3	696.2	741.1	774.8
47.5°	446.6	458.2	470.9	487.3	507.0	533.9	564.0	601.3	644.9	683.1	707.2
50°	419.7	430.4	444.3	460.3	479.6	504.7	533.6	570.5	606.9	641.6	663.5
52.5°	393.2	405.2	419.1	433.0	451.4	476.5	503.3	535.0	569.7	598.0	616.1
55°	353.4	364.6	377.5	391.9	410.1	431.5	459.9	485.0	512.2	536.3	547.0
57.5°	315.1	324.9	336.9	351.9	368.3	388.2	410.7	434.8	454.1	471.0	483.2
60°	289.8	298.3	309.6	322.4	340.1	358.2	378.6	401.0	416.0	430.4	441.6
62.5°	264.1	272.3	283.0	294.6	310.1	327.0	346.5	364.6	379.2	389.0	401.9
65°	225.6	233.6	242.7	255.0	267.4	281.2	298.9	312.3	322.4	333.1	341.1
67.5°	189.8	196.5	205.1	214.8	225.1	238.4	252.2	263.2	270.2	276.6	286.3
70°	166.3	171.7	178.6	186.1	197.3	210.6	221.3	229.9	234.7	241.1	252.9
72.5°	142.4	148.5	155.0	162.6	171.7	182.8	192.3	200.8	203.9	209.1	216.6
75°	112.3	115.5	120.8	126.2	132.6	142.2	151.3	153.4	156.1	160.4	165.7
77.5°	84.9	87.8	89.9	93.5	98.6	106.3	111.1	114.3	114.9	116.5	121.8
80°	67.3	69.0	71.1	73.8	75.9	82.3	85.0	88.2	89.3	90.9	93.6
82.5°	49.4	51.0	52.3	54.5	58.0	60.5	63.2	66.4	66.6	67.8	68.4
85°	28.8	29.4	28.4	29.4	29.9	31.0	33.7	36.4	35.8	35.3	36.9
87.5°	12.4	12.3	11.6	12.8	11.6	12.0	11.6	11.9	12.4	13.1	13.8
90°	10.5	9.9	8.6	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6
92.5°	161.7	199.7	202.9	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5
95°	537.0	548.8	447.8	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4
97.5°	679.5	586.1	399.9	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9
100°	714.2	559.4	356.8	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3
102.5°	693.4	512.2	324.1	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8
105°	626.9	449.1	292.4	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0
107.5°	559.0	405.6	279.0	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9
110°	520.3	385.2	275.0	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	373.4	275.0	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6
115°	460.2	360.5	276.9	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1
117.5°	441.5	354.2	281.0	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0
120°	431.1	351.2	284.9	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9
122.5°	422.2	348.7	288.4	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3
125°	410.0	345.6	294.2	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4
127.5°	398.9	344.1	300.8	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7
130°	391.5	343.2	304.8	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1
132.5°	385.6	343.2	309.2	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1
135°	378.4	343.2	315.3	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2
137.5°	372.2	343.9	320.8	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3
140°	369.2	344.4	323.3	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3
142.5°	366.7	344.9	324.8	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2
145°	363.0	344.4	326.5	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6
147.5°	359.1	342.8	327.0	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5
150°	356.2	341.3	327.0	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0
152.5°	352.7	339.3	326.5	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9
155°	346.9	335.7	325.2	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1
157.5°	341.4	332.0	323.6	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2
160°	337.0	329.5	322.1	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7
162.5°	333.0	326.5	320.6	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1
165°	327.0	322.1	318.4	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9
167.5°	321.2	317.7	314.9	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3
170°	317.7	315.3	313.4	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3
172.5°	314.3	312.3	311.4	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3
175°	309.7	309.1	309.1	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6
177.5°	307.7	307.2	307.2	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1308.9	1312.7	1318.3	1324.7	1329.8	1335.4	1338.4	1338.4	1341.0	1346.6	1353.8
5°	1312.6	1326.5	1339.9	1357.0	1370.4	1385.8	1397.6	1408.9	1419.0	1431.9	1445.3
7.5°	1311.5	1334.7	1358.8	1385.7	1415.4	1439.0	1463.3	1482.3	1501.2	1525.7	1545.1
10°	1307.3	1337.2	1369.8	1404.1	1441.5	1474.1	1503.5	1530.3	1555.9	1582.6	1606.7
12.5°	1299.6	1337.7	1377.5	1418.6	1465.9	1503.2	1541.2	1569.6	1599.6	1628.8	1658.4
15°	1288.0	1332.9	1381.1	1438.3	1496.0	1537.7	1575.2	1612.1	1639.8	1673.0	1701.4
17.5°	1264.2	1322.1	1382.6	1445.1	1500.6	1549.0	1588.3	1623.4	1653.0	1689.5	1728.0
20°	1250.1	1312.6	1375.7	1442.6	1495.5	1545.2	1583.2	1619.5	1656.5	1704.0	1751.0
22.5°	1230.4	1297.2	1364.1	1427.6	1483.5	1531.5	1570.7	1615.3	1663.7	1717.7	1774.6
25°	1199.3	1268.3	1334.6	1395.0	1449.5	1498.7	1552.2	1612.1	1670.9	1742.0	1823.8
27.5°	1159.8	1226.3	1285.5	1349.3	1403.5	1466.1	1532.8	1597.8	1682.5	1780.4	1882.5
30°	1130.3	1193.4	1249.5	1310.0	1371.4	1440.4	1515.3	1591.7	1692.8	1807.8	1929.1
32.5°	1096.1	1153.2	1208.9	1267.2	1338.1	1413.9	1493.4	1587.1	1707.8	1838.6	1964.2
35°	1036.7	1088.1	1142.1	1206.7	1282.1	1364.5	1466.1	1580.0	1725.9	1866.5	1979.3
37.5°	974.5	1015.0	1069.2	1137.5	1219.6	1314.9	1430.1	1568.5	1718.5	1844.6	1892.7
40°	926.6	964.6	1021.8	1093.4	1174.6	1279.0	1408.3	1550.5	1701.4	1789.1	1785.3
42.5°	879.1	917.5	972.6	1044.7	1129.3	1246.0	1379.3	1527.0	1654.3	1687.7	1618.0
45°	806.3	842.1	896.1	968.8	1059.7	1182.2	1322.2	1464.0	1545.2	1491.2	1353.3
47.5°	732.1	766.8	817.0	888.2	987.5	1115.6	1248.0	1364.3	1375.7	1259.7	1094.2
50°	683.3	715.9	763.5	839.5	935.6	1060.8	1188.6	1280.0	1251.6	1110.0	939.4
52.5°	635.8	667.2	711.8	783.4	881.8	1004.3	1118.4	1190.2	1124.7	974.0	820.5
55°	565.7	595.6	640.6	706.3	795.6	907.9	1007.9	1034.0	937.8	786.0	661.9
57.5°	499.1	521.0	565.4	623.5	709.6	808.7	880.3	875.6	769.4	632.6	543.7
60°	455.0	474.8	517.1	570.5	652.3	741.1	791.3	769.9	662.5	549.6	464.1
62.5°	413.9	432.5	467.9	517.1	587.3	664.5	701.1	671.5	570.1	471.0	402.9
65°	351.8	365.2	393.6	438.9	494.0	547.5	580.1	536.8	447.0	372.2	320.8
67.5°	293.7	305.3	330.5	363.1	401.1	438.0	451.3	410.7	340.8	290.3	254.2
70°	256.1	266.8	283.9	314.4	339.5	365.8	372.2	335.8	277.5	239.0	216.6
72.5°	220.1	230.0	245.0	266.5	283.9	299.0	302.0	268.2	223.6	197.1	179.7
75°	167.9	176.4	186.1	194.1	205.3	208.0	206.9	180.7	156.7	139.0	129.4
77.5°	123.4	126.9	132.8	136.0	136.6	136.3	130.9	114.3	101.9	94.7	90.7
80°	95.1	97.8	99.4	100.5	101.1	95.7	89.8	79.7	75.4	71.1	66.3
82.5°	69.1	70.9	72.5	72.7	69.8	65.4	59.9	54.8	51.9	49.7	47.9
85°	37.4	37.9	37.4	34.8	31.0	29.4	28.4	27.3	26.7	26.2	26.2
87.5°	13.5	12.4	10.6	11.2	11.5	11.2	11.5	11.2	10.9	11.1	11.2
90°	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2
92.5°	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8
95°	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4
97.5°	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3
100°	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8
102.5°	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0
105°	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5
107.5°	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6
110°	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5
115°	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4
117.5°	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5
120°	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6
122.5°	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3
125°	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8
127.5°	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0
130°	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6
132.5°	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2
135°	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1
137.5°	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5
140°	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0
142.5°	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6
145°	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1
147.5°	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2
150°	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8
152.5°	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8
155°	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4
157.5°	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0
160°	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0
162.5°	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5
165°	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0
167.5°	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8
170°	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8
172.5°	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4
175°	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6
177.5°	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1359.4	1359.4	1366.7	1366.2	1371.0	1369.2	1370.1
5°	1461.3	1470.4	1478.4	1483.8	1491.8	1493.9	1492.8
7.5°	1566.9	1587.1	1597.0	1610.4	1612.9	1619.9	1619.2
10°	1632.4	1652.2	1667.1	1678.9	1684.7	1692.3	1692.8
12.5°	1683.7	1700.5	1713.7	1724.7	1731.8	1734.2	1735.6
15°	1723.8	1742.5	1758.0	1773.5	1782.6	1789.5	1793.3
17.5°	1764.2	1793.1	1820.4	1841.5	1854.2	1864.9	1864.7
20°	1795.5	1828.6	1862.8	1886.9	1911.5	1922.2	1923.7
22.5°	1828.8	1879.5	1923.6	1960.9	1993.1	2004.3	2008.5
25°	1898.1	1964.4	2032.3	2084.7	2122.1	2144.0	2147.3
27.5°	1981.8	2071.6	2143.0	2191.3	2222.5	2238.7	2242.2
30°	2040.9	2123.8	2187.9	2224.3	2238.7	2240.8	2232.8
32.5°	2067.4	2129.3	2155.0	2152.8	2124.5	2105.7	2098.5
35°	2035.0	2022.1	1959.6	1884.8	1827.6	1791.2	1781.5
37.5°	1851.9	1741.2	1626.2	1513.1	1452.9	1422.2	1369.6
40°	1671.4	1513.7	1393.9	1298.7	1230.8	1176.3	1163.5
42.5°	1467.8	1305.0	1185.2	1103.7	1049.5	1012.0	995.8
45°	1179.5	1039.4	940.5	878.0	836.2	809.0	796.7
47.5°	943.4	835.0	762.9	716.6	684.8	661.1	654.4
50°	813.8	727.1	666.2	627.2	603.1	584.9	577.4
52.5°	706.9	636.9	590.1	557.9	535.1	523.8	517.5
55°	583.4	522.9	489.3	463.6	450.8	441.6	437.4
57.5°	477.1	433.4	408.8	391.1	379.2	373.4	371.3
60°	417.6	383.3	360.9	347.0	339.0	331.5	329.4
62.5°	365.0	338.0	320.7	308.5	300.5	297.3	296.0
65°	294.1	276.4	263.6	256.1	249.7	248.6	248.1
67.5°	233.8	223.4	216.7	208.8	206.6	202.9	202.1
70°	199.9	193.1	185.0	182.4	179.7	175.9	176.4
72.5°	169.6	162.6	157.2	153.7	152.7	151.1	152.5
75°	124.1	121.9	119.8	117.1	116.1	116.1	115.5
77.5°	88.6	86.7	84.4	82.8	82.5	80.2	81.0
80°	64.2	61.5	60.4	60.9	59.3	58.8	58.8
82.5°	47.5	46.5	45.5	45.6	45.2	44.7	45.2
85°	26.2	25.7	25.7	25.1	25.1	24.6	24.6
87.5°	11.8	12.3	11.7	11.2	11.2	11.8	12.3
90°	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333594-927

CATALOG NUMBER: S125RDIP-S1090D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)