

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333636-927

Luminaire Tested: **S125RDIP-S1270D1205U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333636-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7323.7 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	69	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	55	47	42	47	42	37	41	36	33	34	31	29	25
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9715	9715	9715	9715
5°	11177	9728	8591	9728
10°	12821	9678	7581	9678
15°	13848	9579	6738	9579
20°	15270	9465	6222	9465
25°	17672	9311	5773	9311
30°	19231	9150	5480	9150
35°	16222	8964	5210	8964
40°	11328	8627	4977	8627
45°	8404	8173	4748	8173
50°	6701	7700	4554	7700
55°	5687	7113	4380	7113
60°	4914	6589	4100	6589
65°	4378	6021	3529	6021
70°	3846	5516	3218	5516
75°	3329	4776	3019	4776
80°	2525	4020	2525	4020
85°	2104	3157	2379	3157



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	2.0
10°-20°	422.7	5.8
20°-30°	670.3	9.2
30°-40°	808.3	11.0
40°-50°	721.8	9.9
50°-60°	553.6	7.6
60°-70°	359.7	4.9
70°-80°	174.9	2.4
80°-90°	44.3	0.6
90°-100°	330.9	4.5
100°-110°	711.4	9.7
110°-120°	667.6	9.1
120°-130°	541.1	7.4
130°-140°	434.2	5.9
140°-150°	327.7	4.5
150°-160°	230.6	3.1
160°-170°	136.0	1.9
170°-180°	44.2	0.6
0°-30°	1237.3	16.9
0°-40°	2045.6	27.9
0°-60°	3320.9	45.3
0°-90°	3899.9	53.3
90°-120°	1710.0	23.3
90°-150°	3013.0	41.1
90°-180°	3424.0	46.8
0°-180°	7323.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1504	1504	1504	1504	1504	
5°	1724	1501	1325	1501	1724	172
15°	2071	1433	1008	1433	2071	593
25°	2480	1307	810	1307	2480	1139
35°	2058	1137	661	1137	2058	1243
45°	920	895	520	895	920	734
55°	505	632	389	632	505	458
65°	286	394	231	394	286	285
75°	133	191	121	191	133	142
85°	28	43	32	43	28	33
90°	21	1	21	1	21	16
95°	216	30	216	30	216	306
105°	1220	104	1220	104	1220	1212
115°	1359	186	1359	186	1359	1327
125°	1071	258	1071	258	1071	969
135°	889	302	889	302	889	689
145°	701	352	701	352	701	446
155°	588	401	588	401	588	274
165°	516	438	516	438	516	147
175°	463	456	463	456	463	45
180°	456	456	456	456	456	



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1582.3	1581.4	1583.3	1577.9	1578.3	1569.9	1569.9	1563.5	1555.1	1548.7	1545.8
5°	1724.1	1725.4	1722.8	1713.6	1707.5	1698.2	1687.7	1669.1	1653.7	1638.9	1627.1
7.5°	1870.1	1871.0	1862.8	1860.0	1844.4	1833.0	1809.7	1784.5	1762.1	1733.8	1712.0
10°	1955.0	1954.5	1945.8	1939.0	1925.4	1908.1	1885.3	1855.6	1827.9	1797.0	1767.4
12.5°	2004.5	2002.9	2000.1	1991.9	1979.3	1964.0	1944.6	1915.4	1881.2	1847.4	1812.8
15°	2071.2	2066.8	2058.8	2048.3	2030.4	2012.5	1990.8	1964.9	1932.2	1893.9	1861.8
17.5°	2153.6	2153.8	2141.4	2126.9	2102.5	2070.9	2037.6	1995.7	1951.2	1909.1	1874.9
20°	2221.8	2219.9	2207.7	2179.2	2151.4	2111.9	2073.6	2022.4	1968.0	1913.0	1870.4
22.5°	2319.7	2314.8	2302.0	2264.7	2221.6	2170.7	2112.1	2049.5	1983.9	1921.4	1865.5
25°	2479.9	2476.2	2450.9	2407.7	2347.2	2268.7	2192.2	2106.3	2011.9	1929.8	1861.8
27.5°	2589.6	2585.5	2566.7	2530.9	2475.0	2392.5	2288.9	2174.1	2056.2	1943.2	1845.2
30°	2578.7	2588.0	2585.5	2568.9	2526.9	2452.8	2357.1	2228.0	2087.8	1955.0	1838.3
32.5°	2423.6	2431.9	2453.6	2486.3	2488.8	2459.2	2387.7	2268.5	2123.4	1972.4	1832.9
35°	2057.5	2068.7	2110.7	2176.8	2263.2	2335.4	2350.2	2286.1	2155.8	1993.4	1824.8
37.5°	1581.8	1642.6	1677.9	1747.5	1878.1	2011.0	2138.8	2185.9	2130.4	1984.7	1811.6
40°	1343.7	1358.5	1421.5	1499.9	1609.9	1748.2	1930.4	2061.9	2066.2	1964.9	1790.8
42.5°	1150.1	1168.9	1212.0	1274.7	1368.8	1507.1	1695.2	1868.8	1949.2	1910.6	1763.6
45°	920.1	934.3	965.8	1014.0	1086.2	1200.5	1362.2	1562.9	1722.3	1784.6	1690.8
47.5°	755.8	763.5	790.9	827.6	881.1	964.3	1089.6	1263.8	1454.8	1588.9	1575.7
50°	666.9	675.6	696.6	724.4	769.4	839.8	939.8	1085.0	1282.0	1445.6	1478.4
52.5°	597.8	604.9	618.0	644.3	681.5	735.6	816.3	947.6	1124.9	1298.9	1374.6
55°	505.1	510.1	520.5	535.4	565.1	604.0	673.7	764.5	907.8	1083.2	1194.3
57.5°	428.8	431.3	437.9	451.6	472.1	500.6	551.0	627.9	730.6	888.6	1011.2
60°	380.4	382.9	391.5	400.8	416.8	442.8	482.3	536.0	634.8	765.1	889.2
62.5°	341.8	343.3	347.1	356.3	370.4	390.4	421.5	465.3	543.9	658.4	775.6
65°	286.5	287.2	288.4	295.8	304.4	319.2	339.6	370.5	429.8	516.3	620.0
67.5°	233.5	234.2	238.6	241.2	250.3	258.0	270.0	293.6	335.3	393.6	474.3
70°	203.7	203.2	207.5	210.6	213.7	222.9	230.9	250.1	276.0	320.5	387.8
72.5°	176.1	174.5	176.3	177.4	181.6	187.8	195.9	207.6	227.6	258.3	309.7
75°	133.4	134.0	134.0	135.2	138.3	140.8	143.2	149.4	160.6	180.9	208.7
77.5°	93.6	92.6	95.2	95.6	97.4	100.1	102.3	104.7	109.3	117.7	132.1
80°	67.9	67.9	68.5	70.4	69.8	71.0	74.1	76.6	82.1	87.1	92.0
82.5°	52.1	51.7	52.2	52.6	52.5	53.7	54.8	55.3	57.4	59.9	63.4
85°	28.4	28.4	29.0	29.0	29.6	29.6	30.3	30.3	30.3	30.9	31.5
87.5°	15.1	14.6	13.9	13.9	14.4	15.1	14.3	13.7	13.5	13.3	13.5
90°	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6	15.7	14.7	12.9
92.5°	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1	240.3	296.8	301.6
95°	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8	798.0	815.6	665.5
97.5°	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6	1009.8	870.9	594.3
100°	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2	1061.3	831.2	530.2
102.5°	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5	1030.4	761.2	481.6
105°	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5	931.5	667.3	434.4
107.5°	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6	830.7	602.7	414.5
110°	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0	773.2	572.5	408.7



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6	730.5	554.8	408.7
115°	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8	683.9	535.8	411.5
117.5°	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8	656.1	526.3	417.6
120°	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3	640.6	521.9	423.4
122.5°	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5	627.4	518.2	428.6
125°	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5	609.3	513.7	437.2
127.5°	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1	592.8	511.4	446.9
130°	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7	581.8	509.9	452.9
132.5°	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2	572.9	509.9	459.5
135°	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3	562.4	509.9	468.5
137.5°	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1	553.0	511.0	476.8
140°	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0	548.6	511.7	480.5
142.5°	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4	544.9	512.5	482.7
145°	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9	539.4	511.7	485.1
147.5°	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2	533.7	509.4	486.0
150°	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5	529.3	507.2	486.0
152.5°	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2	524.1	504.2	485.3
155°	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1	515.5	498.9	483.2
157.5°	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1	507.4	493.4	480.9
160°	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7	500.7	489.7	478.6
162.5°	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6	494.9	485.3	476.4
165°	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4	486.0	478.6	473.1
167.5°	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7	477.4	472.2	467.9
170°	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8	472.2	468.5	465.8
172.5°	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2	467.1	464.1	462.8
175°	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0	460.3	459.3	459.3
177.5°	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0	457.3	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1545.8	1542.3	1535.9	1529.9	1522.6	1516.2	1511.6	1506.3	1499.4	1491.0	1484.0
5°	1614.2	1600.6	1582.7	1567.3	1547.5	1532.1	1516.0	1500.6	1485.1	1465.4	1448.1
7.5°	1690.0	1662.0	1634.7	1600.4	1569.2	1541.4	1514.7	1487.7	1461.3	1433.2	1406.2
10°	1736.5	1702.5	1664.9	1621.6	1582.1	1544.4	1509.8	1475.8	1440.0	1408.6	1374.6
12.5°	1780.0	1736.1	1693.0	1638.4	1590.9	1544.9	1500.9	1458.6	1420.3	1379.4	1343.0
15°	1819.2	1776.0	1727.8	1661.1	1595.1	1539.4	1487.6	1432.7	1385.1	1339.4	1298.6
17.5°	1834.4	1789.1	1733.1	1669.0	1596.8	1526.9	1460.1	1399.8	1343.9	1290.6	1244.8
20°	1828.4	1784.6	1727.2	1666.0	1588.9	1516.0	1443.8	1377.1	1314.7	1258.5	1209.7
22.5°	1814.2	1768.8	1713.3	1648.8	1575.5	1498.3	1421.0	1349.9	1284.5	1226.4	1173.1
25°	1792.6	1730.9	1674.1	1611.1	1541.3	1464.7	1385.1	1306.6	1236.9	1177.6	1119.6
27.5°	1770.3	1693.2	1621.0	1558.4	1484.6	1416.3	1339.5	1259.1	1185.7	1125.4	1065.8
30°	1750.0	1663.6	1583.9	1512.9	1443.1	1378.3	1305.4	1227.0	1151.7	1089.3	1028.8
32.5°	1724.8	1632.9	1545.4	1463.5	1396.2	1331.9	1265.9	1191.0	1117.6	1053.2	991.7
35°	1693.2	1575.9	1480.8	1393.8	1319.0	1256.6	1197.4	1136.9	1063.3	996.6	936.8
37.5°	1651.7	1518.6	1408.6	1313.7	1234.9	1172.3	1125.5	1070.2	1003.1	939.2	883.7
40°	1626.5	1477.1	1356.7	1262.8	1180.0	1114.0	1070.2	1023.3	962.1	902.2	846.6
42.5°	1592.9	1439.1	1304.3	1206.5	1123.2	1059.6	1015.3	974.3	923.1	866.6	807.1
45°	1527.1	1365.3	1223.9	1119.0	1035.0	972.6	931.2	894.8	855.9	804.0	752.1
47.5°	1441.4	1288.4	1140.4	1025.8	943.6	885.7	845.5	816.7	788.9	744.8	694.4
50°	1372.8	1225.2	1080.6	969.5	881.8	826.9	789.2	766.4	741.0	700.8	658.9
52.5°	1291.7	1159.9	1018.4	904.8	822.0	770.6	734.4	711.5	690.6	657.9	617.9
55°	1164.0	1048.5	918.9	815.7	739.8	687.9	653.3	631.7	619.4	591.6	560.1
57.5°	1016.7	933.9	819.6	720.2	653.0	601.7	576.4	558.0	544.1	524.4	502.2
60°	913.9	855.9	753.4	658.9	597.1	548.3	525.5	510.1	497.1	480.5	463.1
62.5°	809.7	767.5	678.3	597.1	540.3	499.5	478.1	464.1	449.2	437.9	421.1
65°	670.0	632.3	570.6	507.0	454.5	421.8	406.3	394.0	384.7	372.3	360.6
67.5°	521.2	505.9	463.3	419.4	381.8	352.6	339.3	330.7	319.5	312.1	304.0
70°	429.8	422.4	392.1	363.1	327.9	308.2	295.8	292.1	278.5	271.1	265.5
72.5°	348.8	345.3	327.9	307.8	283.0	265.6	254.3	250.1	241.5	235.5	232.0
75°	239.0	240.2	237.1	224.2	214.9	203.7	193.9	191.4	185.3	180.3	177.2
77.5°	151.1	157.5	157.7	157.1	153.4	146.6	142.5	140.7	134.6	132.8	132.1
80°	103.8	110.5	116.7	116.1	114.9	113.0	110.0	108.1	105.0	103.1	101.9
82.5°	69.2	75.5	80.6	84.0	83.7	81.9	79.8	78.9	78.3	76.9	76.7
85°	32.7	34.0	35.8	40.2	43.3	43.8	43.3	42.6	40.7	41.4	42.0
87.5°	13.8	13.4	13.7	13.3	12.4	14.6	15.7	16.0	15.2	14.6	13.9
90°	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0	1.8	3.6	5.5
92.5°	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2	13.6	21.4	32.8
95°	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3	31.3	38.7	48.8
97.5°	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5	51.6	56.7	66.9
100°	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4	66.3	69.9	80.1
102.5°	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9	81.0	84.0	94.8
105°	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0	104.0	108.6	117.8
107.5°	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5	129.4	133.8	141.4
110°	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5	146.4	150.0	158.4



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4	163.3	166.2	174.5
115°	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9	187.7	190.5	198.8
117.5°	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0	210.8	213.7	222.0
120°	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8	225.5	229.2	237.5
122.5°	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2	240.3	243.2	251.4
125°	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7	259.6	264.2	272.4
127.5°	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0	275.8	281.7	292.2
130°	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6	285.3	292.7	304.7
132.5°	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9	293.4	302.3	315.8
135°	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9	305.6	316.6	331.4
137.5°	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0	319.8	330.1	344.8
140°	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8	328.6	339.7	354.4
142.5°	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1	338.2	348.5	363.2
145°	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6	353.5	362.7	375.6
147.5°	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8	368.9	376.8	388.8
150°	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4	379.2	385.7	397.7
152.5°	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7	388.8	394.5	405.0
155°	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3	401.3	406.9	416.1
157.5°	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5	413.3	417.7	425.6
160°	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6	420.6	424.4	430.8
162.5°	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2	427.3	430.9	436.7
165°	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2	436.3	439.1	443.7
167.5°	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8	443.9	445.5	448.1
170°	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2	448.3	449.2	451.1
172.5°	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2	450.5	451.4	453.2
175°	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7	453.8	454.7	455.7
177.5°	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3	455.8	455.8	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1479.1	1472.2	1467.2	1457.3	1450.4	1447.5	1442.0	1440.5	1446.0	1442.0	1441.5
5°	1435.1	1417.2	1403.0	1388.8	1373.3	1363.5	1348.7	1346.2	1342.5	1336.9	1335.7
7.5°	1382.4	1359.1	1340.8	1317.3	1296.9	1280.5	1261.9	1253.2	1248.4	1241.2	1231.6
10°	1346.8	1319.0	1294.3	1270.8	1245.5	1225.2	1206.7	1192.4	1183.1	1174.5	1170.8
12.5°	1311.7	1283.4	1251.8	1223.4	1195.2	1172.3	1151.8	1142.6	1132.3	1122.1	1113.5
15°	1257.3	1219.6	1185.0	1152.3	1128.2	1103.5	1083.7	1070.2	1054.7	1050.4	1033.7
17.5°	1199.4	1162.5	1122.0	1087.6	1059.6	1032.5	1010.7	995.3	983.7	967.8	960.1
20°	1163.4	1119.6	1080.1	1048.5	1017.6	985.6	963.3	950.4	939.2	926.3	920.1
22.5°	1124.9	1082.0	1041.5	1004.6	973.2	941.6	925.7	912.4	899.7	887.7	879.6
25°	1068.3	1025.1	982.5	944.2	911.5	888.6	870.1	854.6	847.9	836.1	827.4
27.5°	1012.3	966.4	922.2	884.0	858.3	835.8	820.5	808.3	796.1	785.8	778.3
30°	976.3	929.4	881.2	851.0	823.8	802.2	785.4	773.7	764.5	755.2	749.6
32.5°	940.2	891.8	849.1	816.3	790.7	772.0	754.9	743.6	733.9	723.6	717.1
35°	882.4	833.1	798.4	766.4	741.0	723.7	712.0	695.9	687.9	680.5	673.7
37.5°	828.7	782.8	745.4	717.2	695.2	678.0	662.8	654.2	644.3	637.6	632.0
40°	789.2	747.2	713.2	683.6	667.6	648.4	634.2	623.1	615.7	607.0	600.9
42.5°	753.6	714.6	681.6	655.0	634.9	618.8	605.1	593.9	584.6	578.4	573.1
45°	703.4	664.5	632.3	607.6	589.1	573.7	559.4	553.9	541.5	534.2	531.7
47.5°	651.3	616.6	585.5	562.8	543.8	529.2	515.9	504.5	497.7	490.4	486.5
50°	616.3	583.0	553.9	531.7	513.2	497.1	484.7	477.4	468.1	461.3	456.4
52.5°	581.2	550.3	521.3	500.0	484.0	467.9	454.2	446.7	437.9	433.6	430.2
55°	531.1	498.4	473.6	452.7	435.9	421.1	408.2	400.8	395.2	390.9	389.7
57.5°	474.3	448.3	425.3	406.5	389.1	375.2	363.8	356.8	351.9	351.3	347.5
60°	437.2	413.8	392.8	372.3	357.5	344.6	334.7	326.7	321.7	321.1	319.9
62.5°	400.1	377.6	358.1	340.2	326.9	314.4	305.1	296.0	293.1	290.0	287.2
65°	345.2	324.8	308.8	294.5	280.4	269.8	260.6	255.0	248.3	244.5	237.7
67.5°	291.2	275.4	260.0	248.0	236.9	226.9	219.2	211.0	206.4	203.4	198.4
70°	255.6	243.3	227.8	214.9	206.3	198.2	192.0	182.8	179.7	177.2	174.8
72.5°	222.0	211.2	198.2	187.7	179.1	171.5	164.4	160.0	157.0	154.5	153.0
75°	174.8	164.3	153.1	145.8	139.6	133.4	129.7	126.6	125.3	124.8	122.2
77.5°	128.3	122.8	113.8	108.0	103.9	101.4	98.1	96.5	96.3	93.6	92.8
80°	98.2	95.1	87.7	85.2	82.1	79.7	77.8	74.7	71.6	70.4	68.5
82.5°	73.0	69.9	66.9	63.0	60.4	58.9	57.0	55.9	56.3	54.6	53.7
85°	38.9	35.8	34.6	34.0	32.7	34.0	33.4	32.7	32.1	31.5	32.1
87.5°	13.8	14.2	13.9	15.2	13.9	14.8	15.0	14.7	14.9	15.1	14.9
90°	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6	17.5	18.4	20.3
92.5°	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1	118.4	89.1	75.5
95°	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8	521.9	408.7	331.4
97.5°	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6	887.6	777.3	669.7
100°	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2	1087.1	992.3	896.5
102.5°	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5	1209.3	1163.9	1099.1
105°	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5	1278.6	1319.1	1308.9
107.5°	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6	1216.9	1320.9	1369.0
110°	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0	1146.9	1276.7	1354.9



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6	1077.7	1208.9	1301.2
115°	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8	978.5	1104.5	1204.9
117.5°	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8	909.8	1018.4	1110.5
120°	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3	870.8	972.0	1053.0
122.5°	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5	842.8	933.0	1008.8
125°	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5	805.4	885.5	951.8
127.5°	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1	769.7	844.5	906.5
130°	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7	744.7	816.5	876.3
132.5°	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2	721.1	786.2	843.9
135°	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3	684.8	743.8	796.2
137.5°	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1	652.4	701.4	746.0
140°	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0	633.3	675.7	714.3
142.5°	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4	617.1	653.6	687.1
145°	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9	596.4	625.0	649.8
147.5°	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2	579.3	601.3	620.0
150°	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5	569.8	587.2	603.8
152.5°	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2	560.2	576.2	589.1
155°	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1	545.8	558.7	568.9
157.5°	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1	532.2	542.2	550.1
160°	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7	521.9	531.1	537.6
162.5°	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6	513.1	520.8	526.5
165°	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4	499.8	505.3	509.9
167.5°	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7	487.0	491.2	494.5
170°	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8	479.6	482.4	484.2
172.5°	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2	472.9	475.0	476.1
175°	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0	463.0	464.9	464.9
177.5°	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0	458.8	458.8	458.8
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1441.1	1435.6	1434.1	1436.1	1434.1	1435.6	1441.1	1441.5	1442.0	1446.0	1440.5
5°	1329.5	1323.3	1326.4	1325.2	1326.4	1323.3	1329.5	1335.7	1336.9	1342.5	1346.2
7.5°	1231.4	1223.8	1215.6	1218.2	1215.6	1223.8	1231.4	1231.6	1241.2	1248.4	1253.2
10°	1162.8	1156.6	1152.9	1156.0	1152.9	1156.6	1162.8	1170.8	1174.5	1183.1	1192.4
12.5°	1105.0	1101.3	1098.0	1096.7	1098.0	1101.3	1105.0	1113.5	1122.1	1132.3	1142.6
15°	1026.3	1018.9	1015.8	1007.8	1015.8	1018.9	1026.3	1033.7	1050.4	1054.7	1070.2
17.5°	953.8	951.3	943.3	939.8	943.3	951.3	953.8	960.1	967.8	983.7	995.3
20°	910.9	908.4	900.3	905.3	900.3	908.4	910.9	920.1	926.3	939.2	950.4
22.5°	875.3	869.8	867.2	865.8	867.2	869.8	875.3	879.6	887.7	899.7	912.4
25°	825.0	817.0	813.9	810.2	813.9	817.0	825.0	827.4	836.1	847.9	854.6
27.5°	774.8	770.6	766.4	765.5	766.4	770.6	774.8	778.3	785.8	796.1	808.3
30°	742.3	737.9	734.8	734.8	734.8	737.9	742.3	749.6	755.2	764.5	773.7
32.5°	713.1	709.8	706.7	706.2	706.7	709.8	713.1	717.1	723.6	733.9	743.6
35°	670.7	665.7	664.5	660.8	664.5	665.7	670.7	673.7	680.5	687.9	695.9
37.5°	626.5	622.4	622.3	621.9	622.3	622.4	626.5	632.0	637.6	644.3	654.2
40°	598.3	595.2	594.7	590.3	594.7	595.2	598.3	600.9	607.0	615.7	623.1
42.5°	568.2	566.6	564.5	562.7	564.5	566.6	568.2	573.1	578.4	584.6	593.9
45°	527.4	523.0	523.0	519.9	523.0	523.0	527.4	531.7	534.2	541.5	553.9
47.5°	485.1	481.8	482.1	479.0	482.1	481.8	485.1	486.5	490.4	497.7	504.5
50°	456.9	455.1	454.5	453.3	454.5	455.1	456.9	456.4	461.3	468.1	477.4
52.5°	428.8	427.9	430.3	427.5	430.3	427.9	428.8	430.2	433.6	437.9	446.7
55°	390.9	389.0	392.8	389.0	392.8	389.0	390.9	389.7	390.9	395.2	400.8
57.5°	347.3	345.5	348.9	347.1	348.9	345.5	347.3	347.5	351.3	351.9	356.8
60°	318.6	315.0	316.8	317.4	316.8	315.0	318.6	319.9	321.1	321.7	326.7
62.5°	284.6	282.3	283.7	280.8	283.7	282.3	284.6	287.2	290.0	293.1	296.0
65°	236.5	234.6	232.2	230.9	232.2	234.6	236.5	237.7	244.5	248.3	255.0
67.5°	198.7	194.2	194.2	195.1	194.2	194.2	198.7	198.4	203.4	206.4	211.0
70°	171.0	171.0	170.4	170.4	170.4	171.0	171.0	174.8	177.2	179.7	182.8
72.5°	151.8	151.3	150.2	149.7	150.2	151.3	151.8	153.0	154.5	157.0	160.0
75°	122.2	122.9	121.7	121.0	121.7	122.9	122.2	122.2	124.8	125.3	126.6
77.5°	90.3	87.7	89.0	87.7	89.0	87.7	90.3	92.8	93.6	96.3	96.5
80°	68.5	67.9	69.8	67.9	69.8	67.9	68.5	68.5	70.4	71.6	74.7
82.5°	54.2	53.6	54.5	53.1	54.5	53.6	54.2	53.7	54.6	56.3	55.9
85°	32.7	32.1	31.5	32.1	31.5	32.1	32.7	32.1	31.5	32.1	32.7
87.5°	15.4	14.9	15.1	15.1	15.1	14.9	15.4	14.9	15.1	14.9	14.7
90°	20.3	20.3	21.2	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6
92.5°	63.7	61.5	60.2	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1
95°	266.0	238.4	231.1	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8
97.5°	612.8	561.3	534.6	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6
100°	833.1	766.8	732.7	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2
102.5°	1031.1	984.0	947.0	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5
105°	1279.5	1249.1	1230.7	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5
107.5°	1383.9	1383.7	1377.6	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6
110°	1396.4	1413.9	1420.3	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1361.8	1391.8	1407.8	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6
115°	1276.7	1320.9	1346.6	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8
117.5°	1182.3	1228.0	1253.5	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8
120°	1121.2	1165.3	1190.2	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3
122.5°	1069.6	1110.1	1135.0	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5
125°	1003.3	1041.1	1061.3	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5
127.5°	953.2	986.6	1005.8	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1
130°	922.3	952.7	971.1	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7
132.5°	889.9	920.3	937.2	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2
135°	836.7	867.1	883.7	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3
137.5°	782.2	809.8	825.1	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1
140°	748.4	772.3	786.1	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0
142.5°	716.0	736.2	749.2	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4
145°	671.9	687.6	697.8	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9
147.5°	637.5	650.1	655.9	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2
150°	617.7	628.7	632.4	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5
152.5°	600.7	609.5	613.2	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2
155°	578.1	584.5	587.2	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1
157.5°	557.2	562.6	565.1	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1
160°	544.0	548.6	550.5	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7
162.5°	531.5	535.4	535.8	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6
165°	513.7	515.5	515.5	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4
167.5°	496.3	498.0	497.3	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7
170°	486.0	487.0	487.0	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8
172.5°	476.4	478.1	476.7	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2
175°	464.9	465.8	463.9	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0
177.5°	458.0	458.8	456.5	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1442.0	1447.5	1450.4	1457.3	1467.2	1472.2	1479.1	1484.0	1491.0	1499.4	1506.3
5°	1348.7	1363.5	1373.3	1388.8	1403.0	1417.2	1435.1	1448.1	1465.4	1485.1	1500.6
7.5°	1261.9	1280.5	1296.9	1317.3	1340.8	1359.1	1382.4	1406.2	1433.2	1461.3	1487.7
10°	1206.7	1225.2	1245.5	1270.8	1294.3	1319.0	1346.8	1374.6	1408.6	1440.0	1475.8
12.5°	1151.8	1172.3	1195.2	1223.4	1251.8	1283.4	1311.7	1343.0	1379.4	1420.3	1458.6
15°	1083.7	1103.5	1128.2	1152.3	1185.0	1219.6	1257.3	1298.6	1339.4	1385.1	1432.7
17.5°	1010.7	1032.5	1059.6	1087.6	1122.0	1162.5	1199.4	1244.8	1290.6	1343.9	1399.8
20°	963.3	985.6	1017.6	1048.5	1080.1	1119.6	1163.4	1209.7	1258.5	1314.7	1377.1
22.5°	925.7	941.6	973.2	1004.6	1041.5	1082.0	1124.9	1173.1	1226.4	1284.5	1349.9
25°	870.1	888.6	911.5	944.2	982.5	1025.1	1068.3	1119.6	1177.6	1236.9	1306.6
27.5°	820.5	835.8	858.3	884.0	922.2	966.4	1012.3	1065.8	1125.4	1185.7	1259.1
30°	785.4	802.2	823.8	851.0	881.2	929.4	976.3	1028.8	1089.3	1151.7	1227.0
32.5°	754.9	772.0	790.7	816.3	849.1	891.8	940.2	991.7	1053.2	1117.6	1191.0
35°	712.0	723.7	741.0	766.4	798.4	833.1	882.4	936.8	996.6	1063.3	1136.9
37.5°	662.8	678.0	695.2	717.2	745.4	782.8	828.7	883.7	939.2	1003.1	1070.2
40°	634.2	648.4	667.6	683.6	713.2	747.2	789.2	846.6	902.2	962.1	1023.3
42.5°	605.1	618.8	634.9	655.0	681.6	714.6	753.6	807.1	866.6	923.1	974.3
45°	559.4	573.7	589.1	607.6	632.3	664.5	703.4	752.1	804.0	855.9	894.8
47.5°	515.9	529.2	543.8	562.8	585.5	616.6	651.3	694.4	744.8	788.9	816.7
50°	484.7	497.1	513.2	531.7	553.9	583.0	616.3	658.9	700.8	741.0	766.4
52.5°	454.2	467.9	484.0	500.0	521.3	550.3	581.2	617.9	657.9	690.6	711.5
55°	408.2	421.1	435.9	452.7	473.6	498.4	531.1	560.1	591.6	619.4	631.7
57.5°	363.8	375.2	389.1	406.5	425.3	448.3	474.3	502.2	524.4	544.1	558.0
60°	334.7	344.6	357.5	372.3	392.8	413.8	437.2	463.1	480.5	497.1	510.1
62.5°	305.1	314.4	326.9	340.2	358.1	377.6	400.1	421.1	437.9	449.2	464.1
65°	260.6	269.8	280.4	294.5	308.8	324.8	345.2	360.6	372.3	384.7	394.0
67.5°	219.2	226.9	236.9	248.0	260.0	275.4	291.2	304.0	312.1	319.5	330.7
70°	192.0	198.2	206.3	214.9	227.8	243.3	255.6	265.5	271.1	278.5	292.1
72.5°	164.4	171.5	179.1	187.7	198.2	211.2	222.0	232.0	235.5	241.5	250.1
75°	129.7	133.4	139.6	145.8	153.1	164.3	174.8	177.2	180.3	185.3	191.4
77.5°	98.1	101.4	103.9	108.0	113.8	122.8	128.3	132.1	132.8	134.6	140.7
80°	77.8	79.7	82.1	85.2	87.7	95.1	98.2	101.9	103.1	105.0	108.1
82.5°	57.0	58.9	60.4	63.0	66.9	69.9	73.0	76.7	76.9	78.3	78.9
85°	33.4	34.0	32.7	34.0	34.6	35.8	38.9	42.0	41.4	40.7	42.6
87.5°	15.0	14.8	13.9	15.2	13.9	14.2	13.8	13.9	14.6	15.2	16.0
90°	15.7	14.7	12.9	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0
92.5°	240.3	296.8	301.6	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2
95°	798.0	815.6	665.5	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3
97.5°	1009.8	870.9	594.3	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5
100°	1061.3	831.2	530.2	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4
102.5°	1030.4	761.2	481.6	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9
105°	931.5	667.3	434.4	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0
107.5°	830.7	602.7	414.5	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5
110°	773.2	572.5	408.7	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	730.5	554.8	408.7	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4
115°	683.9	535.8	411.5	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9
117.5°	656.1	526.3	417.6	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0
120°	640.6	521.9	423.4	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8
122.5°	627.4	518.2	428.6	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2
125°	609.3	513.7	437.2	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7
127.5°	592.8	511.4	446.9	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0
130°	581.8	509.9	452.9	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6
132.5°	572.9	509.9	459.5	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9
135°	562.4	509.9	468.5	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9
137.5°	553.0	511.0	476.8	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0
140°	548.6	511.7	480.5	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8
142.5°	544.9	512.5	482.7	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1
145°	539.4	511.7	485.1	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6
147.5°	533.7	509.4	486.0	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8
150°	529.3	507.2	486.0	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4
152.5°	524.1	504.2	485.3	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7
155°	515.5	498.9	483.2	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3
157.5°	507.4	493.4	480.9	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5
160°	500.7	489.7	478.6	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6
162.5°	494.9	485.3	476.4	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2
165°	486.0	478.6	473.1	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2
167.5°	477.4	472.2	467.9	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8
170°	472.2	468.5	465.8	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2
172.5°	467.1	464.1	462.8	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2
175°	460.3	459.3	459.3	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7
177.5°	457.3	456.5	456.5	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1511.6	1516.2	1522.6	1529.9	1535.9	1542.3	1545.8	1545.8	1548.7	1555.1	1563.5
5°	1516.0	1532.1	1547.5	1567.3	1582.7	1600.6	1614.2	1627.1	1638.9	1653.7	1669.1
7.5°	1514.7	1541.4	1569.2	1600.4	1634.7	1662.0	1690.0	1712.0	1733.8	1762.1	1784.5
10°	1509.8	1544.4	1582.1	1621.6	1664.9	1702.5	1736.5	1767.4	1797.0	1827.9	1855.6
12.5°	1500.9	1544.9	1590.9	1638.4	1693.0	1736.1	1780.0	1812.8	1847.4	1881.2	1915.4
15°	1487.6	1539.4	1595.1	1661.1	1727.8	1776.0	1819.2	1861.8	1893.9	1932.2	1964.9
17.5°	1460.1	1526.9	1596.8	1669.0	1733.1	1789.1	1834.4	1874.9	1909.1	1951.2	1995.7
20°	1443.8	1516.0	1588.9	1666.0	1727.2	1784.6	1828.4	1870.4	1913.0	1968.0	2022.4
22.5°	1421.0	1498.3	1575.5	1648.8	1713.3	1768.8	1814.2	1865.5	1921.4	1983.9	2049.5
25°	1385.1	1464.7	1541.3	1611.1	1674.1	1730.9	1792.6	1861.8	1929.8	2011.9	2106.3
27.5°	1339.5	1416.3	1484.6	1558.4	1621.0	1693.2	1770.3	1845.2	1943.2	2056.2	2174.1
30°	1305.4	1378.3	1443.1	1512.9	1583.9	1663.6	1750.0	1838.3	1955.0	2087.8	2228.0
32.5°	1265.9	1331.9	1396.2	1463.5	1545.4	1632.9	1724.8	1832.9	1972.4	2123.4	2268.5
35°	1197.4	1256.6	1319.0	1393.8	1480.8	1575.9	1693.2	1824.8	1993.4	2155.8	2286.1
37.5°	1125.5	1172.3	1234.9	1313.7	1408.6	1518.6	1651.7	1811.6	1984.7	2130.4	2185.9
40°	1070.2	1114.0	1180.0	1262.8	1356.7	1477.1	1626.5	1790.8	1964.9	2066.2	2061.9
42.5°	1015.3	1059.6	1123.2	1206.5	1304.3	1439.1	1592.9	1763.6	1910.6	1949.2	1868.8
45°	931.2	972.6	1035.0	1119.0	1223.9	1365.3	1527.1	1690.8	1784.6	1722.3	1562.9
47.5°	845.5	885.7	943.6	1025.8	1140.4	1288.4	1441.4	1575.7	1588.9	1454.8	1263.8
50°	789.2	826.9	881.8	969.5	1080.6	1225.2	1372.8	1478.4	1445.6	1282.0	1085.0
52.5°	734.4	770.6	822.0	904.8	1018.4	1159.9	1291.7	1374.6	1298.9	1124.9	947.6
55°	653.3	687.9	739.8	815.7	918.9	1048.5	1164.0	1194.3	1083.2	907.8	764.5
57.5°	576.4	601.7	653.0	720.2	819.6	933.9	1016.7	1011.2	888.6	730.6	627.9
60°	525.5	548.3	597.1	658.9	753.4	855.9	913.9	889.2	765.1	634.8	536.0
62.5°	478.1	499.5	540.3	597.1	678.3	767.5	809.7	775.6	658.4	543.9	465.3
65°	406.3	421.8	454.5	507.0	570.6	632.3	670.0	620.0	516.3	429.8	370.5
67.5°	339.3	352.6	381.8	419.4	463.3	505.9	521.2	474.3	393.6	335.3	293.6
70°	295.8	308.2	327.9	363.1	392.1	422.4	429.8	387.8	320.5	276.0	250.1
72.5°	254.3	265.6	283.0	307.8	327.9	345.3	348.8	309.7	258.3	227.6	207.6
75°	193.9	203.7	214.9	224.2	237.1	240.2	239.0	208.7	180.9	160.6	149.4
77.5°	142.5	146.6	153.4	157.1	157.7	157.5	151.1	132.1	117.7	109.3	104.7
80°	110.0	113.0	114.9	116.1	116.7	110.5	103.8	92.0	87.1	82.1	76.6
82.5°	79.8	81.9	83.7	84.0	80.6	75.5	69.2	63.4	59.9	57.4	55.3
85°	43.3	43.8	43.3	40.2	35.8	34.0	32.7	31.5	30.9	30.3	30.3
87.5°	15.7	14.6	12.4	13.3	13.7	13.4	13.8	13.5	13.3	13.5	13.7
90°	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6
92.5°	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1
95°	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8
97.5°	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6
100°	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2
102.5°	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5
105°	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5
107.5°	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6
110°	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6
115°	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8
117.5°	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8
120°	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3
122.5°	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5
125°	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5
127.5°	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1
130°	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7
132.5°	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2
135°	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3
137.5°	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1
140°	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0
142.5°	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4
145°	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9
147.5°	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2
150°	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5
152.5°	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2
155°	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1
157.5°	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1
160°	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7
162.5°	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6
165°	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4
167.5°	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7
170°	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8
172.5°	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2
175°	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0
177.5°	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1569.9	1569.9	1578.3	1577.9	1583.3	1581.4	1582.3
5°	1687.7	1698.2	1707.5	1713.6	1722.8	1725.4	1724.1
7.5°	1809.7	1833.0	1844.4	1860.0	1862.8	1871.0	1870.1
10°	1885.3	1908.1	1925.4	1939.0	1945.8	1954.5	1955.0
12.5°	1944.6	1964.0	1979.3	1991.9	2000.1	2002.9	2004.5
15°	1990.8	2012.5	2030.4	2048.3	2058.8	2066.8	2071.2
17.5°	2037.6	2070.9	2102.5	2126.9	2141.4	2153.8	2153.6
20°	2073.6	2111.9	2151.4	2179.2	2207.7	2219.9	2221.8
22.5°	2112.1	2170.7	2221.6	2264.7	2302.0	2314.8	2319.7
25°	2192.2	2268.7	2347.2	2407.7	2450.9	2476.2	2479.9
27.5°	2288.9	2392.5	2475.0	2530.9	2566.7	2585.5	2589.6
30°	2357.1	2452.8	2526.9	2568.9	2585.5	2588.0	2578.7
32.5°	2387.7	2459.2	2488.8	2486.3	2453.6	2431.9	2423.6
35°	2350.2	2335.4	2263.2	2176.8	2110.7	2068.7	2057.5
37.5°	2138.8	2011.0	1878.1	1747.5	1677.9	1642.6	1581.8
40°	1930.4	1748.2	1609.9	1499.9	1421.5	1358.5	1343.7
42.5°	1695.2	1507.1	1368.8	1274.7	1212.0	1168.9	1150.1
45°	1362.2	1200.5	1086.2	1014.0	965.8	934.3	920.1
47.5°	1089.6	964.3	881.1	827.6	790.9	763.5	755.8
50°	939.8	839.8	769.4	724.4	696.6	675.6	666.9
52.5°	816.3	735.6	681.5	644.3	618.0	604.9	597.8
55°	673.7	604.0	565.1	535.4	520.5	510.1	505.1
57.5°	551.0	500.6	472.1	451.6	437.9	431.3	428.8
60°	482.3	442.8	416.8	400.8	391.5	382.9	380.4
62.5°	421.5	390.4	370.4	356.3	347.1	343.3	341.8
65°	339.6	319.2	304.4	295.8	288.4	287.2	286.5
67.5°	270.0	258.0	250.3	241.2	238.6	234.2	233.5
70°	230.9	222.9	213.7	210.6	207.5	203.2	203.7
72.5°	195.9	187.8	181.6	177.4	176.3	174.5	176.1
75°	143.2	140.8	138.3	135.2	134.0	134.0	133.4
77.5°	102.3	100.1	97.4	95.6	95.2	92.6	93.6
80°	74.1	71.0	69.8	70.4	68.5	67.9	67.9
82.5°	54.8	53.7	52.5	52.6	52.2	51.7	52.1
85°	30.3	29.6	29.6	29.0	29.0	28.4	28.4
87.5°	14.3	15.1	14.4	13.9	13.9	14.6	15.1
90°	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3



TEST NUMBER: P333636-927

CATALOG NUMBER: S125RDIP-S1270D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)