

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333515-927

Luminaire Tested: **S125RDIP-S375D1205U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333515-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1205U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4458.7 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	40	35	33	31	24	23	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	22	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.8	1.0
10°-20°	125.3	2.8
20°-30°	198.7	4.5
30°-40°	239.6	5.4
40°-50°	214.0	4.8
50°-60°	164.1	3.7
60°-70°	106.6	2.4
70°-80°	51.8	1.2
80°-90°	15.0	0.3
90°-100°	79.2	1.8
100°-110°	234.0	5.2
110°-120°	396.3	8.9
120°-130°	521.5	11.7
130°-140°	584.4	13.1
140°-150°	572.7	12.8
150°-160°	481.1	10.8
160°-170°	319.8	7.2
170°-180°	111.9	2.5
0°-30°	366.8	8.2
0°-40°	606.3	13.6
0°-60°	984.4	22.1
0°-90°	1157.8	26.0
90°-120°	709.5	15.9
90°-150°	2388.1	53.6
90°-180°	3301.0	74.0
0°-180°	4458.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	22	1	22	1	22	13
95°	79	60	79	60	79	81
105°	228	210	228	210	228	242
115°	400	397	400	397	400	396
125°	583	579	583	579	583	520
135°	756	753	756	753	756	583
145°	916	912	916	912	916	572
155°	1044	1044	1044	1044	1044	480
165°	1132	1135	1132	1135	1132	319
175°	1176	1180	1176	1180	1176	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	7.6	7.4	7.1	7.0	7.0	7.1	6.8	6.4	6.3	6.0	5.9
90°	22.1	21.5	20.8	20.3	19.6	18.9	17.8	16.8	15.8	14.7	13.3
92.5°	43.4	43.0	42.5	42.1	41.7	40.7	39.4	38.0	36.7	35.3	33.6
95°	79.1	78.7	78.3	78.0	77.6	76.6	75.2	73.8	72.3	70.9	68.8
97.5°	120.0	119.8	119.5	119.3	119.1	118.3	116.9	115.6	114.2	112.9	110.0
100°	151.0	150.6	150.1	149.7	149.3	148.2	146.4	144.5	142.7	140.9	138.2
102.5°	181.9	181.3	180.8	180.2	179.6	178.3	176.3	174.3	172.3	170.3	169.0
105°	228.3	227.7	227.0	226.5	225.9	224.9	223.7	222.4	221.3	220.0	218.8
107.5°	275.8	275.8	275.9	275.9	276.0	275.7	275.0	274.4	273.9	273.2	272.3
110°	311.2	311.3	311.6	311.7	312.0	311.7	311.2	310.5	309.9	309.3	308.7



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.8	346.1	346.5	346.9	347.2	347.3	347.0	346.7	346.4	346.1	345.3
115°	400.4	400.6	400.8	401.1	401.2	401.5	401.6	401.9	402.1	402.3	401.9
117.5°	453.8	454.6	455.5	456.3	457.1	457.4	457.2	457.1	456.9	456.8	456.4
120°	490.7	491.5	492.3	493.1	493.9	494.3	494.3	494.3	494.3	494.3	494.2
122.5°	527.5	528.1	528.8	529.4	530.1	530.5	530.7	530.8	531.0	531.2	530.6
125°	582.7	582.9	583.1	583.4	583.5	583.8	584.2	584.6	585.0	585.5	585.3
127.5°	635.7	636.1	636.5	637.0	637.4	637.7	637.9	638.1	638.3	638.5	638.3
130°	671.1	671.5	671.9	672.3	672.7	673.0	673.2	673.4	673.7	673.8	673.4
132.5°	704.3	704.8	705.4	705.9	706.5	706.9	707.1	707.3	707.5	707.7	707.8
135°	755.7	756.6	757.4	758.2	759.1	759.5	759.5	759.5	759.5	759.5	759.2
137.5°	806.2	807.2	808.3	809.3	810.3	810.7	810.5	810.2	809.9	809.7	809.3
140°	838.6	839.6	840.7	841.7	842.7	843.0	842.6	842.2	841.8	841.4	840.7
142.5°	869.6	870.6	871.6	872.6	873.6	874.0	873.8	873.5	873.3	873.1	872.3
145°	915.9	916.6	917.2	917.8	918.4	918.7	918.7	918.7	918.7	918.7	918.1
147.5°	955.5	957.0	958.3	959.7	961.1	961.6	961.1	960.6	960.0	959.6	959.1
150°	985.0	985.4	985.8	986.2	986.7	986.8	986.8	986.8	986.8	986.8	986.0
152.5°	1009.3	1010.0	1010.7	1011.5	1012.3	1012.3	1011.9	1011.4	1010.9	1010.4	1010.1
155°	1043.9	1045.0	1045.9	1046.9	1048.0	1048.1	1047.3	1046.5	1045.7	1044.8	1044.7
157.5°	1072.9	1074.2	1075.5	1076.9	1078.2	1078.5	1077.7	1076.8	1076.0	1075.2	1075.0
160°	1092.7	1093.7	1094.7	1095.7	1096.8	1096.9	1096.1	1095.3	1094.4	1093.6	1093.4
162.5°	1109.6	1110.8	1112.0	1113.2	1114.4	1114.5	1113.5	1112.5	1111.5	1110.6	1110.5
165°	1132.3	1133.5	1134.7	1136.0	1137.2	1137.4	1136.5	1135.8	1135.0	1134.1	1133.9
167.5°	1150.3	1151.6	1152.9	1154.1	1155.4	1155.4	1154.2	1152.9	1151.8	1150.5	1150.5
170°	1159.9	1161.3	1162.8	1164.2	1165.6	1165.7	1164.5	1163.2	1162.1	1160.8	1160.8
172.5°	1168.0	1169.3	1170.5	1171.8	1173.1	1173.1	1171.9	1170.6	1169.4	1168.2	1168.2
175°	1175.5	1176.9	1178.5	1179.9	1181.3	1181.4	1180.1	1178.9	1177.7	1176.5	1176.5
177.5°	1180.0	1181.1	1182.3	1183.4	1184.6	1184.6	1183.7	1182.6	1181.7	1180.7	1180.8
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	5.7	5.5	5.3	5.0	4.5	4.9	5.1	4.8	4.9	4.9	5.0
90°	11.9	10.5	9.0	7.4	5.9	4.2	2.5	1.0	2.5	4.2	5.9
92.5°	31.8	30.1	28.3	26.9	25.7	24.6	23.4	22.3	23.4	24.6	25.7
95°	66.8	64.7	62.7	61.5	61.1	60.7	60.2	59.8	60.2	60.7	61.1
97.5°	107.2	104.4	101.6	100.1	99.9	99.7	99.6	99.4	99.6	99.7	99.9
100°	135.5	132.8	130.2	128.9	128.9	128.9	128.9	128.9	128.9	128.9	128.9
102.5°	167.6	166.3	164.9	163.8	163.0	162.2	161.4	160.6	161.4	162.2	163.0
105°	217.5	216.3	215.1	214.0	212.9	211.9	210.9	209.8	210.9	211.9	212.9
107.5°	271.3	270.4	269.4	268.5	267.4	266.4	265.4	264.4	265.4	266.4	267.4
110°	308.1	307.4	306.8	306.0	305.0	304.0	302.9	302.0	302.9	304.0	305.0





TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.6	343.8	343.0	342.4	341.8	341.3	340.8	340.2	340.8	341.3	341.8
115°	401.5	401.1	400.6	400.1	399.2	398.4	397.6	396.7	397.6	398.4	399.2
117.5°	456.1	455.7	455.3	455.0	454.6	454.2	453.8	453.4	453.8	454.2	454.6
120°	493.9	493.7	493.5	492.9	491.9	490.8	489.8	488.8	489.8	490.8	491.9
122.5°	530.1	529.6	529.0	528.5	528.2	527.8	527.5	527.1	527.5	527.8	528.2
125°	585.0	584.9	584.6	583.9	582.7	581.5	580.3	579.0	580.3	581.5	582.7
127.5°	638.0	637.8	637.5	637.1	636.4	635.6	634.9	634.3	634.9	635.6	636.4
130°	673.0	672.6	672.2	671.5	670.5	669.5	668.4	667.4	668.4	669.5	670.5
132.5°	707.9	708.0	708.1	707.3	705.6	703.9	702.2	700.5	702.2	703.9	705.6
135°	759.1	758.8	758.7	758.0	756.7	755.5	754.2	753.0	754.2	755.5	756.7
137.5°	808.8	808.3	807.9	807.1	805.9	804.7	803.5	802.3	803.5	804.7	805.9
140°	840.2	839.6	838.9	838.1	837.1	836.1	835.0	834.0	835.0	836.1	837.1
142.5°	871.5	870.7	870.0	869.1	868.2	867.4	866.6	865.7	866.6	867.4	868.2
145°	917.5	916.9	916.2	915.5	914.7	913.9	913.1	912.3	913.1	913.9	914.7
147.5°	958.6	958.1	957.6	957.1	956.7	956.2	955.8	955.4	955.8	956.2	956.7
150°	985.2	984.4	983.6	983.3	983.5	983.7	983.9	984.0	983.9	983.7	983.5
152.5°	1009.7	1009.4	1009.1	1008.8	1008.5	1008.2	1007.9	1007.7	1007.9	1008.2	1008.5
155°	1044.4	1044.3	1044.0	1043.9	1043.9	1043.9	1043.9	1043.9	1043.9	1043.9	1043.9
157.5°	1074.8	1074.6	1074.4	1074.5	1075.0	1075.4	1075.9	1076.3	1075.9	1075.4	1075.0
160°	1093.2	1093.0	1092.8	1093.0	1093.6	1094.2	1094.9	1095.4	1094.9	1094.2	1093.6
162.5°	1110.5	1110.4	1110.4	1110.6	1111.0	1111.5	1112.0	1112.4	1112.0	1111.5	1111.0
165°	1133.7	1133.5	1133.3	1133.4	1133.9	1134.2	1134.6	1135.0	1134.6	1134.2	1133.9
167.5°	1150.5	1150.5	1150.5	1150.9	1151.8	1152.5	1153.3	1154.2	1153.3	1152.5	1151.8
170°	1160.8	1160.8	1160.8	1161.3	1162.1	1162.8	1163.7	1164.5	1163.7	1162.8	1162.1
172.5°	1168.2	1168.2	1168.2	1168.6	1169.4	1170.2	1171.1	1171.9	1171.1	1170.2	1169.4
175°	1176.5	1176.5	1176.5	1176.9	1177.7	1178.5	1179.3	1180.1	1179.3	1178.5	1177.7
177.5°	1181.1	1181.2	1181.4	1181.8	1182.4	1183.0	1183.8	1184.4	1183.8	1183.0	1182.4
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	5.1	5.5	5.6	6.2	6.0	6.5	6.7	6.7	6.9	7.1	7.1
90°	7.4	9.0	10.5	11.9	13.3	14.7	15.8	16.8	17.8	18.9	19.6
92.5°	26.9	28.3	30.1	31.8	33.6	35.3	36.7	38.0	39.4	40.7	41.7
95°	61.5	62.7	64.7	66.8	68.8	70.9	72.3	73.8	75.2	76.6	77.6
97.5°	100.1	101.6	104.4	107.2	110.0	112.9	114.2	115.6	116.9	118.3	119.1
100°	128.9	130.2	132.8	135.5	138.2	140.9	142.7	144.5	146.4	148.2	149.3
102.5°	163.8	164.9	166.3	167.6	169.0	170.3	172.3	174.3	176.3	178.3	179.6
105°	214.0	215.1	216.3	217.5	218.8	220.0	221.3	222.4	223.7	224.9	225.9
107.5°	268.5	269.4	270.4	271.3	272.3	273.2	273.9	274.4	275.0	275.7	276.0
110°	306.0	306.8	307.4	308.1	308.7	309.3	309.9	310.5	311.2	311.7	312.0



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	342.4	343.0	343.8	344.6	345.3	346.1	346.4	346.7	347.0	347.3	347.2
115°	400.1	400.6	401.1	401.5	401.9	402.3	402.1	401.9	401.6	401.5	401.2
117.5°	455.0	455.3	455.7	456.1	456.4	456.8	456.9	457.1	457.2	457.4	457.1
120°	492.9	493.5	493.7	493.9	494.2	494.3	494.3	494.3	494.3	494.3	493.9
122.5°	528.5	529.0	529.6	530.1	530.6	531.2	531.0	530.8	530.7	530.5	530.1
125°	583.9	584.6	584.9	585.0	585.3	585.5	585.0	584.6	584.2	583.8	583.5
127.5°	637.1	637.5	637.8	638.0	638.3	638.5	638.3	638.1	637.9	637.7	637.4
130°	671.5	672.2	672.6	673.0	673.4	673.8	673.7	673.4	673.2	673.0	672.7
132.5°	707.3	708.1	708.0	707.9	707.8	707.7	707.5	707.3	707.1	706.9	706.5
135°	758.0	758.7	758.8	759.1	759.2	759.5	759.5	759.5	759.5	759.5	759.1
137.5°	807.1	807.9	808.3	808.8	809.3	809.7	809.9	810.2	810.5	810.7	810.3
140°	838.1	838.9	839.6	840.2	840.7	841.4	841.8	842.2	842.6	843.0	842.7
142.5°	869.1	870.0	870.7	871.5	872.3	873.1	873.3	873.5	873.8	874.0	873.6
145°	915.5	916.2	916.9	917.5	918.1	918.7	918.7	918.7	918.7	918.7	918.4
147.5°	957.1	957.6	958.1	958.6	959.1	959.6	960.0	960.6	961.1	961.6	961.1
150°	983.3	983.6	984.4	985.2	986.0	986.8	986.8	986.8	986.8	986.8	986.7
152.5°	1008.8	1009.1	1009.4	1009.7	1010.1	1010.4	1010.9	1011.4	1011.9	1012.3	1012.3
155°	1043.9	1044.0	1044.3	1044.4	1044.7	1044.8	1045.7	1046.5	1047.3	1048.1	1048.0
157.5°	1074.5	1074.4	1074.6	1074.8	1075.0	1075.2	1076.0	1076.8	1077.7	1078.5	1078.2
160°	1093.0	1092.8	1093.0	1093.2	1093.4	1093.6	1094.4	1095.3	1096.1	1096.9	1096.8
162.5°	1110.6	1110.4	1110.4	1110.5	1110.5	1110.6	1111.5	1112.5	1113.5	1114.5	1114.4
165°	1133.4	1133.3	1133.5	1133.7	1133.9	1134.1	1135.0	1135.8	1136.5	1137.4	1137.2
167.5°	1150.9	1150.5	1150.5	1150.5	1150.5	1150.5	1151.8	1152.9	1154.2	1155.4	1155.4
170°	1161.3	1160.8	1160.8	1160.8	1160.8	1160.8	1162.1	1163.2	1164.5	1165.7	1165.6
172.5°	1168.6	1168.2	1168.2	1168.2	1168.2	1168.2	1169.4	1170.6	1171.9	1173.1	1173.1
175°	1176.9	1176.5	1176.5	1176.5	1176.5	1176.5	1177.7	1178.9	1180.1	1181.4	1181.3
177.5°	1181.8	1181.4	1181.2	1181.1	1180.8	1180.7	1181.7	1182.6	1183.7	1184.6	1184.6
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	7.4	7.4	7.5	7.6	7.5	7.4	7.4	7.1	7.1	6.9	6.7
90°	20.3	20.8	21.5	22.1	21.5	20.8	20.3	19.6	18.9	17.8	16.8
92.5°	42.1	42.5	43.0	43.4	43.0	42.5	42.1	41.7	40.7	39.4	38.0
95°	78.0	78.3	78.7	79.1	78.7	78.3	78.0	77.6	76.6	75.2	73.8
97.5°	119.3	119.5	119.8	120.0	119.8	119.5	119.3	119.1	118.3	116.9	115.6
100°	149.7	150.1	150.6	151.0	150.6	150.1	149.7	149.3	148.2	146.4	144.5
102.5°	180.2	180.8	181.3	181.9	181.3	180.8	180.2	179.6	178.3	176.3	174.3
105°	226.5	227.0	227.7	228.3	227.7	227.0	226.5	225.9	224.9	223.7	222.4
107.5°	275.9	275.9	275.8	275.8	275.8	275.9	275.9	276.0	275.7	275.0	274.4
110°	311.7	311.6	311.3	311.2	311.3	311.6	311.7	312.0	311.7	311.2	310.5



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	346.9	346.5	346.1	345.8	346.1	346.5	346.9	347.2	347.3	347.0	346.7
115°	401.1	400.8	400.6	400.4	400.6	400.8	401.1	401.2	401.5	401.6	401.9
117.5°	456.3	455.5	454.6	453.8	454.6	455.5	456.3	457.1	457.4	457.2	457.1
120°	493.1	492.3	491.5	490.7	491.5	492.3	493.1	493.9	494.3	494.3	494.3
122.5°	529.4	528.8	528.1	527.5	528.1	528.8	529.4	530.1	530.5	530.7	530.8
125°	583.4	583.1	582.9	582.7	582.9	583.1	583.4	583.5	583.8	584.2	584.6
127.5°	637.0	636.5	636.1	635.7	636.1	636.5	637.0	637.4	637.7	637.9	638.1
130°	672.3	671.9	671.5	671.1	671.5	671.9	672.3	672.7	673.0	673.2	673.4
132.5°	705.9	705.4	704.8	704.3	704.8	705.4	705.9	706.5	706.9	707.1	707.3
135°	758.2	757.4	756.6	755.7	756.6	757.4	758.2	759.1	759.5	759.5	759.5
137.5°	809.3	808.3	807.2	806.2	807.2	808.3	809.3	810.3	810.7	810.5	810.2
140°	841.7	840.7	839.6	838.6	839.6	840.7	841.7	842.7	843.0	842.6	842.2
142.5°	872.6	871.6	870.6	869.6	870.6	871.6	872.6	873.6	874.0	873.8	873.5
145°	917.8	917.2	916.6	915.9	916.6	917.2	917.8	918.4	918.7	918.7	918.7
147.5°	959.7	958.3	957.0	955.5	957.0	958.3	959.7	961.1	961.6	961.1	960.6
150°	986.2	985.8	985.4	985.0	985.4	985.8	986.2	986.7	986.8	986.8	986.8
152.5°	1011.5	1010.7	1010.0	1009.3	1010.0	1010.7	1011.5	1012.3	1012.3	1011.9	1011.4
155°	1046.9	1045.9	1045.0	1043.9	1045.0	1045.9	1046.9	1048.0	1048.1	1047.3	1046.5
157.5°	1076.9	1075.5	1074.2	1072.9	1074.2	1075.5	1076.9	1078.2	1078.5	1077.7	1076.8
160°	1095.7	1094.7	1093.7	1092.7	1093.7	1094.7	1095.7	1096.8	1096.9	1096.1	1095.3
162.5°	1113.2	1112.0	1110.8	1109.6	1110.8	1112.0	1113.2	1114.4	1114.5	1113.5	1112.5
165°	1136.0	1134.7	1133.5	1132.3	1133.5	1134.7	1136.0	1137.2	1137.4	1136.5	1135.8
167.5°	1154.1	1152.9	1151.6	1150.3	1151.6	1152.9	1154.1	1155.4	1155.4	1154.2	1152.9
170°	1164.2	1162.8	1161.3	1159.9	1161.3	1162.8	1164.2	1165.6	1165.7	1164.5	1163.2
172.5°	1171.8	1170.5	1169.3	1168.0	1169.3	1170.5	1171.8	1173.1	1173.1	1171.9	1170.6
175°	1179.9	1178.5	1176.9	1175.5	1176.9	1178.5	1179.9	1181.3	1181.4	1180.1	1178.9
177.5°	1183.4	1182.3	1181.1	1180.0	1181.1	1182.3	1183.4	1184.6	1184.6	1183.7	1182.6
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	6.7	6.5	6.0	6.2	5.6	5.5	5.1	5.0	4.9	4.9	4.8
90°	15.8	14.7	13.3	11.9	10.5	9.0	7.4	5.9	4.2	2.5	1.0
92.5°	36.7	35.3	33.6	31.8	30.1	28.3	26.9	25.7	24.6	23.4	22.3
95°	72.3	70.9	68.8	66.8	64.7	62.7	61.5	61.1	60.7	60.2	59.8
97.5°	114.2	112.9	110.0	107.2	104.4	101.6	100.1	99.9	99.7	99.6	99.4
100°	142.7	140.9	138.2	135.5	132.8	130.2	128.9	128.9	128.9	128.9	128.9
102.5°	172.3	170.3	169.0	167.6	166.3	164.9	163.8	163.0	162.2	161.4	160.6
105°	221.3	220.0	218.8	217.5	216.3	215.1	214.0	212.9	211.9	210.9	209.8
107.5°	273.9	273.2	272.3	271.3	270.4	269.4	268.5	267.4	266.4	265.4	264.4
110°	309.9	309.3	308.7	308.1	307.4	306.8	306.0	305.0	304.0	302.9	302.0



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	346.4	346.1	345.3	344.6	343.8	343.0	342.4	341.8	341.3	340.8	340.2
115°	402.1	402.3	401.9	401.5	401.1	400.6	400.1	399.2	398.4	397.6	396.7
117.5°	456.9	456.8	456.4	456.1	455.7	455.3	455.0	454.6	454.2	453.8	453.4
120°	494.3	494.3	494.2	493.9	493.7	493.5	492.9	491.9	490.8	489.8	488.8
122.5°	531.0	531.2	530.6	530.1	529.6	529.0	528.5	528.2	527.8	527.5	527.1
125°	585.0	585.5	585.3	585.0	584.9	584.6	583.9	582.7	581.5	580.3	579.0
127.5°	638.3	638.5	638.3	638.0	637.8	637.5	637.1	636.4	635.6	634.9	634.3
130°	673.7	673.8	673.4	673.0	672.6	672.2	671.5	670.5	669.5	668.4	667.4
132.5°	707.5	707.7	707.8	707.9	708.0	708.1	707.3	705.6	703.9	702.2	700.5
135°	759.5	759.5	759.2	759.1	758.8	758.7	758.0	756.7	755.5	754.2	753.0
137.5°	809.9	809.7	809.3	808.8	808.3	807.9	807.1	805.9	804.7	803.5	802.3
140°	841.8	841.4	840.7	840.2	839.6	838.9	838.1	837.1	836.1	835.0	834.0
142.5°	873.3	873.1	872.3	871.5	870.7	870.0	869.1	868.2	867.4	866.6	865.7
145°	918.7	918.7	918.1	917.5	916.9	916.2	915.5	914.7	913.9	913.1	912.3
147.5°	960.0	959.6	959.1	958.6	958.1	957.6	957.1	956.7	956.2	955.8	955.4
150°	986.8	986.8	986.0	985.2	984.4	983.6	983.3	983.5	983.7	983.9	984.0
152.5°	1010.9	1010.4	1010.1	1009.7	1009.4	1009.1	1008.8	1008.5	1008.2	1007.9	1007.7
155°	1045.7	1044.8	1044.7	1044.4	1044.3	1044.0	1043.9	1043.9	1043.9	1043.9	1043.9
157.5°	1076.0	1075.2	1075.0	1074.8	1074.6	1074.4	1074.5	1075.0	1075.4	1075.9	1076.3
160°	1094.4	1093.6	1093.4	1093.2	1093.0	1092.8	1093.0	1093.6	1094.2	1094.9	1095.4
162.5°	1111.5	1110.6	1110.5	1110.5	1110.4	1110.4	1110.6	1111.0	1111.5	1112.0	1112.4
165°	1135.0	1134.1	1133.9	1133.7	1133.5	1133.3	1133.4	1133.9	1134.2	1134.6	1135.0
167.5°	1151.8	1150.5	1150.5	1150.5	1150.5	1150.5	1150.9	1151.8	1152.5	1153.3	1154.2
170°	1162.1	1160.8	1160.8	1160.8	1160.8	1160.8	1161.3	1162.1	1162.8	1163.7	1164.5
172.5°	1169.4	1168.2	1168.2	1168.2	1168.2	1168.2	1168.6	1169.4	1170.2	1171.1	1171.9
175°	1177.7	1176.5	1176.5	1176.5	1176.5	1176.5	1176.9	1177.7	1178.5	1179.3	1180.1
177.5°	1181.7	1180.7	1180.8	1181.1	1181.2	1181.4	1181.8	1182.4	1183.0	1183.8	1184.4
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	5.1	4.9	4.5	5.0	5.3	5.5	5.7	5.9	6.0	6.3	6.4
90°	2.5	4.2	5.9	7.4	9.0	10.5	11.9	13.3	14.7	15.8	16.8
92.5°	23.4	24.6	25.7	26.9	28.3	30.1	31.8	33.6	35.3	36.7	38.0
95°	60.2	60.7	61.1	61.5	62.7	64.7	66.8	68.8	70.9	72.3	73.8
97.5°	99.6	99.7	99.9	100.1	101.6	104.4	107.2	110.0	112.9	114.2	115.6
100°	128.9	128.9	128.9	128.9	130.2	132.8	135.5	138.2	140.9	142.7	144.5
102.5°	161.4	162.2	163.0	163.8	164.9	166.3	167.6	169.0	170.3	172.3	174.3
105°	210.9	211.9	212.9	214.0	215.1	216.3	217.5	218.8	220.0	221.3	222.4
107.5°	265.4	266.4	267.4	268.5	269.4	270.4	271.3	272.3	273.2	273.9	274.4
110°	302.9	304.0	305.0	306.0	306.8	307.4	308.1	308.7	309.3	309.9	310.5





TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	340.8	341.3	341.8	342.4	343.0	343.8	344.6	345.3	346.1	346.4	346.7
115°	397.6	398.4	399.2	400.1	400.6	401.1	401.5	401.9	402.3	402.1	401.9
117.5°	453.8	454.2	454.6	455.0	455.3	455.7	456.1	456.4	456.8	456.9	457.1
120°	489.8	490.8	491.9	492.9	493.5	493.7	493.9	494.2	494.3	494.3	494.3
122.5°	527.5	527.8	528.2	528.5	529.0	529.6	530.1	530.6	531.2	531.0	530.8
125°	580.3	581.5	582.7	583.9	584.6	584.9	585.0	585.3	585.5	585.0	584.6
127.5°	634.9	635.6	636.4	637.1	637.5	637.8	638.0	638.3	638.5	638.3	638.1
130°	668.4	669.5	670.5	671.5	672.2	672.6	673.0	673.4	673.8	673.7	673.4
132.5°	702.2	703.9	705.6	707.3	708.1	708.0	707.9	707.8	707.7	707.5	707.3
135°	754.2	755.5	756.7	758.0	758.7	758.8	759.1	759.2	759.5	759.5	759.5
137.5°	803.5	804.7	805.9	807.1	807.9	808.3	808.8	809.3	809.7	809.9	810.2
140°	835.0	836.1	837.1	838.1	838.9	839.6	840.2	840.7	841.4	841.8	842.2
142.5°	866.6	867.4	868.2	869.1	870.0	870.7	871.5	872.3	873.1	873.3	873.5
145°	913.1	913.9	914.7	915.5	916.2	916.9	917.5	918.1	918.7	918.7	918.7
147.5°	955.8	956.2	956.7	957.1	957.6	958.1	958.6	959.1	959.6	960.0	960.6
150°	983.9	983.7	983.5	983.3	983.6	984.4	985.2	986.0	986.8	986.8	986.8
152.5°	1007.9	1008.2	1008.5	1008.8	1009.1	1009.4	1009.7	1010.1	1010.4	1010.9	1011.4
155°	1043.9	1043.9	1043.9	1043.9	1044.0	1044.3	1044.4	1044.7	1044.8	1045.7	1046.5
157.5°	1075.9	1075.4	1075.0	1074.5	1074.4	1074.6	1074.8	1075.0	1075.2	1076.0	1076.8
160°	1094.9	1094.2	1093.6	1093.0	1092.8	1093.0	1093.2	1093.4	1093.6	1094.4	1095.3
162.5°	1112.0	1111.5	1111.0	1110.6	1110.4	1110.4	1110.5	1110.5	1110.6	1111.5	1112.5
165°	1134.6	1134.2	1133.9	1133.4	1133.3	1133.5	1133.7	1133.9	1134.1	1135.0	1135.8
167.5°	1153.3	1152.5	1151.8	1150.9	1150.5	1150.5	1150.5	1150.5	1150.5	1151.8	1152.9
170°	1163.7	1162.8	1162.1	1161.3	1160.8	1160.8	1160.8	1160.8	1160.8	1162.1	1163.2
172.5°	1171.1	1170.2	1169.4	1168.6	1168.2	1168.2	1168.2	1168.2	1168.2	1169.4	1170.6
175°	1179.3	1178.5	1177.7	1176.9	1176.5	1176.5	1176.5	1176.5	1176.5	1177.7	1178.9
177.5°	1183.8	1183.0	1182.4	1181.8	1181.4	1181.2	1181.1	1180.8	1180.7	1181.7	1182.6
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	6.8	7.1	7.0	7.0	7.1	7.4	7.6
90°	17.8	18.9	19.6	20.3	20.8	21.5	22.1
92.5°	39.4	40.7	41.7	42.1	42.5	43.0	43.4
95°	75.2	76.6	77.6	78.0	78.3	78.7	79.1
97.5°	116.9	118.3	119.1	119.3	119.5	119.8	120.0
100°	146.4	148.2	149.3	149.7	150.1	150.6	151.0
102.5°	176.3	178.3	179.6	180.2	180.8	181.3	181.9
105°	223.7	224.9	225.9	226.5	227.0	227.7	228.3
107.5°	275.0	275.7	276.0	275.9	275.9	275.8	275.8
110°	311.2	311.7	312.0	311.7	311.6	311.3	311.2



TEST NUMBER: P333515-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.0	347.3	347.2	346.9	346.5	346.1	345.8
115°	401.6	401.5	401.2	401.1	400.8	400.6	400.4
117.5°	457.2	457.4	457.1	456.3	455.5	454.6	453.8
120°	494.3	494.3	493.9	493.1	492.3	491.5	490.7
122.5°	530.7	530.5	530.1	529.4	528.8	528.1	527.5
125°	584.2	583.8	583.5	583.4	583.1	582.9	582.7
127.5°	637.9	637.7	637.4	637.0	636.5	636.1	635.7
130°	673.2	673.0	672.7	672.3	671.9	671.5	671.1
132.5°	707.1	706.9	706.5	705.9	705.4	704.8	704.3
135°	759.5	759.5	759.1	758.2	757.4	756.6	755.7
137.5°	810.5	810.7	810.3	809.3	808.3	807.2	806.2
140°	842.6	843.0	842.7	841.7	840.7	839.6	838.6
142.5°	873.8	874.0	873.6	872.6	871.6	870.6	869.6
145°	918.7	918.7	918.4	917.8	917.2	916.6	915.9
147.5°	961.1	961.6	961.1	959.7	958.3	957.0	955.5
150°	986.8	986.8	986.7	986.2	985.8	985.4	985.0
152.5°	1011.9	1012.3	1012.3	1011.5	1010.7	1010.0	1009.3
155°	1047.3	1048.1	1048.0	1046.9	1045.9	1045.0	1043.9
157.5°	1077.7	1078.5	1078.2	1076.9	1075.5	1074.2	1072.9
160°	1096.1	1096.9	1096.8	1095.7	1094.7	1093.7	1092.7
162.5°	1113.5	1114.5	1114.4	1113.2	1112.0	1110.8	1109.6
165°	1136.5	1137.4	1137.2	1136.0	1134.7	1133.5	1132.3
167.5°	1154.2	1155.4	1155.4	1154.1	1152.9	1151.6	1150.3
170°	1164.5	1165.7	1165.6	1164.2	1162.8	1161.3	1159.9
172.5°	1171.9	1173.1	1173.1	1171.8	1170.5	1169.3	1168.0
175°	1180.1	1181.4	1181.3	1179.9	1178.5	1176.9	1175.5
177.5°	1183.7	1184.6	1184.6	1183.4	1182.3	1181.1	1180.0
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9

(END OF REPORT)