

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333516-927

Luminaire Tested: **S125RDIP-S375D1205U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333516-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4581.6 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18
3	77	68	61	56	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14
5	65	54	46	40	57	48	41	37	38	33	30	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	11
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	13	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	0.9
10°-20°	125.3	2.7
20°-30°	198.7	4.3
30°-40°	239.6	5.2
40°-50°	214.0	4.7
50°-60°	164.1	3.6
60°-70°	106.6	2.3
70°-80°	51.8	1.1
80°-90°	14.9	0.3
90°-100°	330.9	7.2
100°-110°	711.4	15.5
110°-120°	667.6	14.6
120°-130°	541.1	11.8
130°-140°	434.2	9.5
140°-150°	327.7	7.2
150°-160°	230.6	5.0
160°-170°	136.0	3.0
170°-180°	44.2	1.0
0°-30°	366.8	8.0
0°-40°	606.3	13.2
0°-60°	984.4	21.5
0°-90°	1157.8	25.3
90°-120°	1710.0	37.3
90°-150°	3013.0	65.8
90°-180°	3424.0	74.7
0°-180°	4581.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	21	1	21	1	21	15
95°	216	30	216	30	216	306
105°	1220	104	1220	104	1220	1212
115°	1359	186	1359	186	1359	1327
125°	1071	258	1071	258	1071	969
135°	889	302	889	302	889	689
145°	701	352	701	352	701	446
155°	588	401	588	401	588	274
165°	516	438	516	438	516	147
175°	463	456	463	456	463	45
180°	456	456	456	456	456	



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	7.4	7.3	7.0	7.0	7.1	7.1	6.7	6.4	6.2	6.0	5.8
90°	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6	15.7	14.7	12.9
92.5°	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1	240.3	296.8	301.6
95°	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8	798.0	815.6	665.5
97.5°	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6	1009.8	870.9	594.3
100°	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2	1061.3	831.2	530.2
102.5°	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5	1030.4	761.2	481.6
105°	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5	931.5	667.3	434.4
107.5°	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6	830.7	602.7	414.5
110°	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0	773.2	572.5	408.7



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6	730.5	554.8	408.7
115°	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8	683.9	535.8	411.5
117.5°	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8	656.1	526.3	417.6
120°	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3	640.6	521.9	423.4
122.5°	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5	627.4	518.2	428.6
125°	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5	609.3	513.7	437.2
127.5°	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1	592.8	511.4	446.9
130°	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7	581.8	509.9	452.9
132.5°	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2	572.9	509.9	459.5
135°	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3	562.4	509.9	468.5
137.5°	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1	553.0	511.0	476.8
140°	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0	548.6	511.7	480.5
142.5°	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4	544.9	512.5	482.7
145°	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9	539.4	511.7	485.1
147.5°	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2	533.7	509.4	486.0
150°	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5	529.3	507.2	486.0
152.5°	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2	524.1	504.2	485.3
155°	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1	515.5	498.9	483.2
157.5°	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1	507.4	493.4	480.9
160°	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7	500.7	489.7	478.6
162.5°	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6	494.9	485.3	476.4
165°	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4	486.0	478.6	473.1
167.5°	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7	477.4	472.2	467.9
170°	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8	472.2	468.5	465.8
172.5°	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2	467.1	464.1	462.8
175°	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0	460.3	459.3	459.3
177.5°	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0	457.3	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	5.8	5.4	5.4	5.0	4.4	4.8	4.9	4.8	4.8	4.8	4.9
90°	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0	1.8	3.6	5.5
92.5°	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2	13.6	21.4	32.8
95°	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3	31.3	38.7	48.8
97.5°	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5	51.6	56.7	66.9
100°	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4	66.3	69.9	80.1
102.5°	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9	81.0	84.0	94.8
105°	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0	104.0	108.6	117.8
107.5°	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5	129.4	133.8	141.4
110°	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5	146.4	150.0	158.4



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4	163.3	166.2	174.5
115°	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9	187.7	190.5	198.8
117.5°	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0	210.8	213.7	222.0
120°	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8	225.5	229.2	237.5
122.5°	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2	240.3	243.2	251.4
125°	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7	259.6	264.2	272.4
127.5°	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0	275.8	281.7	292.2
130°	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6	285.3	292.7	304.7
132.5°	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9	293.4	302.3	315.8
135°	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9	305.6	316.6	331.4
137.5°	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0	319.8	330.1	344.8
140°	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8	328.6	339.7	354.4
142.5°	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1	338.2	348.5	363.2
145°	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6	353.5	362.7	375.6
147.5°	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8	368.9	376.8	388.8
150°	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4	379.2	385.7	397.7
152.5°	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7	388.8	394.5	405.0
155°	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3	401.3	406.9	416.1
157.5°	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5	413.3	417.7	425.6
160°	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6	420.6	424.4	430.8
162.5°	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2	427.3	430.9	436.7
165°	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2	436.3	439.1	443.7
167.5°	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8	443.9	445.5	448.1
170°	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2	448.3	449.2	451.1
172.5°	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2	450.5	451.4	453.2
175°	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7	453.8	454.7	455.7
177.5°	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3	455.8	455.8	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	5.1	5.5	5.5	6.2	5.9	6.5	6.7	6.7	6.9	7.1	7.3
90°	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6	17.5	18.4	20.3
92.5°	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1	118.4	89.1	75.5
95°	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8	521.9	408.7	331.4
97.5°	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6	887.6	777.3	669.7
100°	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2	1087.1	992.3	896.5
102.5°	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5	1209.3	1163.9	1099.1
105°	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5	1278.6	1319.1	1308.9
107.5°	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6	1216.9	1320.9	1369.0
110°	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0	1146.9	1276.7	1354.9



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6	1077.7	1208.9	1301.2
115°	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8	978.5	1104.5	1204.9
117.5°	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8	909.8	1018.4	1110.5
120°	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3	870.8	972.0	1053.0
122.5°	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5	842.8	933.0	1008.8
125°	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5	805.4	885.5	951.8
127.5°	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1	769.7	844.5	906.5
130°	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7	744.7	816.5	876.3
132.5°	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2	721.1	786.2	843.9
135°	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3	684.8	743.8	796.2
137.5°	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1	652.4	701.4	746.0
140°	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0	633.3	675.7	714.3
142.5°	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4	617.1	653.6	687.1
145°	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9	596.4	625.0	649.8
147.5°	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2	579.3	601.3	620.0
150°	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5	569.8	587.2	603.8
152.5°	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2	560.2	576.2	589.1
155°	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1	545.8	558.7	568.9
157.5°	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1	532.2	542.2	550.1
160°	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7	521.9	531.1	537.6
162.5°	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6	513.1	520.8	526.5
165°	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4	499.8	505.3	509.9
167.5°	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7	487.0	491.2	494.5
170°	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8	479.6	482.4	484.2
172.5°	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2	472.9	475.0	476.1
175°	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0	463.0	464.9	464.9
177.5°	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0	458.8	458.8	458.8
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	7.4	7.3	7.4	7.4	7.4	7.3	7.4	7.3	7.1	6.9	6.7
90°	20.3	20.3	21.2	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6
92.5°	63.7	61.5	60.2	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1
95°	266.0	238.4	231.1	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8
97.5°	612.8	561.3	534.6	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6
100°	833.1	766.8	732.7	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2
102.5°	1031.1	984.0	947.0	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5
105°	1279.5	1249.1	1230.7	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5
107.5°	1383.9	1383.7	1377.6	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6
110°	1396.4	1413.9	1420.3	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1361.8	1391.8	1407.8	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6
115°	1276.7	1320.9	1346.6	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8
117.5°	1182.3	1228.0	1253.5	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8
120°	1121.2	1165.3	1190.2	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3
122.5°	1069.6	1110.1	1135.0	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5
125°	1003.3	1041.1	1061.3	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5
127.5°	953.2	986.6	1005.8	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1
130°	922.3	952.7	971.1	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7
132.5°	889.9	920.3	937.2	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2
135°	836.7	867.1	883.7	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3
137.5°	782.2	809.8	825.1	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1
140°	748.4	772.3	786.1	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0
142.5°	716.0	736.2	749.2	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4
145°	671.9	687.6	697.8	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9
147.5°	637.5	650.1	655.9	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2
150°	617.7	628.7	632.4	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5
152.5°	600.7	609.5	613.2	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2
155°	578.1	584.5	587.2	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1
157.5°	557.2	562.6	565.1	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1
160°	544.0	548.6	550.5	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7
162.5°	531.5	535.4	535.8	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6
165°	513.7	515.5	515.5	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4
167.5°	496.3	498.0	497.3	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7
170°	486.0	487.0	487.0	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8
172.5°	476.4	478.1	476.7	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2
175°	464.9	465.8	463.9	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0
177.5°	458.0	458.8	456.5	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	6.7	6.5	5.9	6.2	5.5	5.5	5.1	4.9	4.8	4.8	4.8
90°	15.7	14.7	12.9	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0
92.5°	240.3	296.8	301.6	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2
95°	798.0	815.6	665.5	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3
97.5°	1009.8	870.9	594.3	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5
100°	1061.3	831.2	530.2	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4
102.5°	1030.4	761.2	481.6	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9
105°	931.5	667.3	434.4	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0
107.5°	830.7	602.7	414.5	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5
110°	773.2	572.5	408.7	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	730.5	554.8	408.7	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4
115°	683.9	535.8	411.5	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9
117.5°	656.1	526.3	417.6	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0
120°	640.6	521.9	423.4	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8
122.5°	627.4	518.2	428.6	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2
125°	609.3	513.7	437.2	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7
127.5°	592.8	511.4	446.9	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0
130°	581.8	509.9	452.9	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6
132.5°	572.9	509.9	459.5	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9
135°	562.4	509.9	468.5	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9
137.5°	553.0	511.0	476.8	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0
140°	548.6	511.7	480.5	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8
142.5°	544.9	512.5	482.7	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1
145°	539.4	511.7	485.1	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6
147.5°	533.7	509.4	486.0	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8
150°	529.3	507.2	486.0	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4
152.5°	524.1	504.2	485.3	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7
155°	515.5	498.9	483.2	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3
157.5°	507.4	493.4	480.9	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5
160°	500.7	489.7	478.6	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6
162.5°	494.9	485.3	476.4	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2
165°	486.0	478.6	473.1	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2
167.5°	477.4	472.2	467.9	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8
170°	472.2	468.5	465.8	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2
172.5°	467.1	464.1	462.8	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2
175°	460.3	459.3	459.3	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7
177.5°	457.3	456.5	456.5	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	4.9	4.8	4.4	5.0	5.4	5.4	5.8	5.8	6.0	6.2	6.4
90°	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6
92.5°	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1
95°	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8
97.5°	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6
100°	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2
102.5°	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5
105°	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5
107.5°	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6
110°	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6
115°	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8
117.5°	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8
120°	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3
122.5°	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5
125°	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5
127.5°	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1
130°	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7
132.5°	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2
135°	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3
137.5°	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1
140°	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0
142.5°	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4
145°	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9
147.5°	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2
150°	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5
152.5°	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2
155°	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1
157.5°	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1
160°	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7
162.5°	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6
165°	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4
167.5°	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7
170°	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8
172.5°	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2
175°	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0
177.5°	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	6.7	7.1	7.1	7.0	7.0	7.3	7.4
90°	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3



TEST NUMBER: P333516-927

CATALOG NUMBER: S125RDIP-S375D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)