

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333498-927

Luminaire Tested: **S125RDIP-S375D590U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333498-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2837.3 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	43	37	56	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	1.5
10°-20°	125.3	4.4
20°-30°	198.7	7.0
30°-40°	239.6	8.4
40°-50°	214.0	7.5
50°-60°	164.1	5.8
60°-70°	106.6	3.8
70°-80°	51.8	1.8
80°-90°	13.6	0.5
90°-100°	162.5	5.7
100°-110°	349.2	12.3
110°-120°	327.8	11.6
120°-130°	265.6	9.4
130°-140°	213.2	7.5
140°-150°	160.9	5.7
150°-160°	113.2	4.0
160°-170°	66.7	2.4
170°-180°	21.7	0.8
0°-30°	366.8	12.9
0°-40°	606.3	21.4
0°-60°	984.4	34.7
0°-90°	1156.5	40.8
90°-120°	839.5	29.6
90°-150°	1479.1	52.1
90°-180°	1681.0	59.2
0°-180°	2837.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	10	0	10	0	10	8
95°	106	15	106	15	106	150
105°	599	51	599	51	599	595
115°	667	91	667	91	667	652
125°	526	126	526	126	526	475
135°	436	148	436	148	436	338
145°	344	173	344	173	344	219
155°	289	197	289	197	289	135
165°	253	215	253	215	253	72
175°	227	224	227	224	227	22
180°	224	224	224	224	224	



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	5.3	5.1	4.9	4.9	5.1	5.1	4.9	4.7	4.6	4.5	4.5
90°	10.4	10.4	9.9	9.9	9.9	9.0	8.6	8.2	7.7	7.2	6.3
92.5°	28.8	29.5	30.2	31.3	37.1	43.7	58.1	80.1	118.0	145.7	148.1
95°	106.2	113.4	117.0	130.6	162.7	200.7	256.2	324.9	391.8	400.4	326.7
97.5°	256.7	262.4	275.5	300.9	328.8	381.6	435.7	483.9	495.7	427.5	291.8
100°	352.4	359.7	376.4	408.9	440.1	487.1	533.7	555.8	521.0	408.1	260.3
102.5°	459.5	464.9	483.1	506.2	539.6	571.3	593.7	580.0	505.8	373.7	236.4
105°	598.7	604.2	613.2	628.1	642.5	647.5	627.6	565.8	457.3	327.6	213.3
107.5°	672.6	676.3	679.3	679.4	672.0	648.5	597.4	514.8	407.8	295.9	203.5
110°	697.3	697.3	694.1	685.5	665.2	626.8	563.1	477.2	379.6	281.1	200.7



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	694.3	691.1	683.3	668.5	638.8	593.5	529.1	447.6	358.6	272.4	200.7
115°	667.0	661.1	648.5	626.8	591.5	542.2	480.4	410.3	335.7	263.0	202.0
117.5°	619.0	615.4	602.9	580.4	545.2	499.9	446.6	386.3	322.1	258.4	204.9
120°	587.9	584.3	572.1	550.4	517.0	477.2	427.5	373.3	314.5	256.2	207.9
122.5°	560.4	557.1	544.9	525.1	495.3	458.0	413.8	363.5	308.0	254.4	210.4
125°	525.5	521.0	511.1	492.6	467.2	434.7	395.4	349.3	299.1	252.2	214.7
127.5°	495.7	493.7	484.3	467.9	445.0	414.5	377.9	334.9	291.0	251.0	219.4
130°	479.4	476.7	467.7	452.8	430.2	400.8	365.6	325.8	285.6	250.3	222.4
132.5°	463.2	460.1	451.8	436.9	414.3	386.0	354.0	316.8	281.2	250.3	225.6
135°	436.5	433.8	425.6	410.7	390.9	365.1	336.2	305.0	276.1	250.3	230.0
137.5°	408.1	405.0	397.6	384.0	366.2	344.4	320.3	295.1	271.5	250.9	234.1
140°	388.2	385.9	379.1	367.4	350.7	331.7	310.9	289.6	269.3	251.3	235.9
142.5°	369.7	367.8	361.4	351.5	337.3	320.8	302.9	284.9	267.5	251.6	236.9
145°	344.4	342.5	337.5	329.9	319.0	306.8	292.8	278.8	264.8	251.3	238.1
147.5°	322.8	322.0	319.1	313.0	304.4	295.2	284.4	273.1	262.0	250.1	238.6
150°	310.9	310.5	308.6	303.2	296.4	288.3	279.7	269.7	259.8	249.0	238.6
152.5°	301.5	301.0	299.2	294.9	289.2	282.9	275.0	266.2	257.3	247.6	238.2
155°	288.8	288.3	286.9	283.8	279.2	274.3	268.0	260.7	253.0	244.9	237.3
157.5°	277.3	277.4	276.2	273.5	270.1	266.2	261.3	255.3	249.1	242.2	236.1
160°	269.7	270.2	269.3	267.0	263.9	260.7	256.2	251.7	245.8	240.4	235.0
162.5°	262.9	263.0	262.8	260.9	258.5	255.6	251.9	247.7	243.0	238.2	233.9
165°	253.0	253.0	253.0	252.2	250.3	248.1	245.3	242.2	238.6	235.0	232.3
167.5°	244.0	244.1	244.5	243.7	242.7	241.1	239.1	236.9	234.3	231.8	229.7
170°	238.6	239.1	239.1	238.6	237.7	236.8	235.4	234.1	231.8	230.0	228.6
172.5°	233.5	234.0	234.7	233.9	233.7	233.1	232.2	230.8	229.3	227.8	227.2
175°	227.3	227.8	228.6	228.2	228.2	228.2	227.3	227.3	225.9	225.5	225.5
177.5°	224.1	224.1	225.2	224.8	225.2	225.2	225.2	224.8	224.5	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	4.5	4.4	4.4	4.2	3.9	4.4	4.8	4.8	4.6	4.4	4.4
90°	5.9	5.0	4.5	3.6	2.7	1.8	0.9	0.5	0.9	1.8	2.7
92.5°	103.1	61.7	37.1	23.8	16.1	10.5	6.7	5.5	6.7	10.5	16.1
95°	202.0	102.6	54.3	33.9	23.9	19.0	15.4	14.9	15.4	19.0	23.9
97.5°	161.2	88.4	56.4	41.7	32.8	27.8	25.3	24.8	25.3	27.8	32.8
100°	146.4	87.7	61.5	47.9	39.3	34.4	32.6	31.6	32.6	34.4	39.3
102.5°	140.3	90.9	67.6	54.4	46.6	41.2	39.8	39.2	39.8	41.2	46.6
105°	137.8	97.6	77.7	65.0	57.8	53.3	51.1	51.1	51.1	53.3	57.8
107.5°	142.0	107.6	88.3	76.9	69.4	65.7	63.5	62.7	63.5	65.7	69.4
110°	145.9	114.8	96.3	84.5	77.7	73.7	71.9	71.0	71.9	73.7	77.7



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	151.0	121.7	103.9	92.4	85.7	81.6	80.2	79.3	80.2	81.6	85.7
115°	158.6	132.4	115.7	104.4	97.6	93.6	92.2	91.3	92.2	93.6	97.6
117.5°	167.3	143.5	127.6	116.7	109.0	105.0	103.5	102.1	103.5	105.0	109.0
120°	173.1	151.4	135.5	124.3	116.6	112.5	110.7	109.3	110.7	112.5	116.6
122.5°	179.6	159.0	143.1	131.9	123.4	119.4	118.0	116.9	118.0	119.4	123.4
125°	188.5	169.0	154.1	142.4	133.7	129.7	127.5	126.5	127.5	129.7	133.7
127.5°	196.5	178.6	164.3	152.6	143.5	138.3	135.4	134.0	135.4	138.3	143.5
130°	202.0	184.8	170.8	159.1	149.6	143.7	140.1	138.7	140.1	143.7	149.6
132.5°	206.7	190.6	176.6	164.9	155.0	148.4	144.1	142.4	144.1	148.4	155.0
135°	213.3	198.4	184.3	172.1	162.7	155.4	150.0	148.2	150.0	155.4	162.7
137.5°	218.2	203.9	191.2	178.6	169.3	162.1	157.0	155.7	157.0	162.1	169.3
140°	221.4	207.9	194.8	182.6	174.0	166.8	161.3	159.9	161.3	166.8	174.0
142.5°	223.2	210.4	198.0	186.6	178.3	171.1	166.0	165.0	166.0	171.1	178.3
145°	225.9	214.7	202.9	192.5	184.3	178.0	173.5	172.6	173.5	178.0	184.3
147.5°	227.6	217.4	207.1	197.9	190.8	185.0	181.1	180.5	181.1	185.0	190.8
150°	228.6	219.2	209.2	201.5	195.2	189.3	186.2	185.3	186.2	189.3	195.2
152.5°	229.3	220.9	211.8	204.8	198.8	193.7	190.8	190.4	190.8	193.7	198.8
155°	230.0	222.8	215.1	208.7	204.2	199.7	197.0	197.0	197.0	199.7	204.2
157.5°	230.4	224.3	217.7	212.9	209.0	205.1	202.9	203.0	202.9	205.1	209.0
160°	230.4	225.1	219.2	215.1	211.5	208.3	206.5	207.0	206.5	208.3	211.5
162.5°	230.1	225.8	220.6	217.3	214.4	211.6	209.8	210.2	209.8	211.6	214.4
165°	229.6	225.9	222.4	219.6	217.8	215.6	214.2	215.1	214.2	215.6	217.8
167.5°	228.5	225.9	222.9	221.3	220.0	218.7	217.9	218.3	217.9	218.7	220.0
170°	227.8	225.9	223.7	222.4	221.4	220.5	220.1	220.5	220.1	220.5	221.4
172.5°	227.0	225.6	223.7	223.1	222.5	221.6	221.2	222.0	221.2	221.6	222.5
175°	225.9	225.1	223.7	223.7	223.7	223.2	222.8	223.7	222.8	223.2	223.7
177.5°	224.8	224.5	223.8	223.8	224.1	223.8	223.8	224.5	223.8	223.8	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	4.4	4.6	4.5	5.0	4.6	5.0	5.1	5.0	5.1	5.1	5.2
90°	3.6	4.5	5.0	5.9	6.3	7.2	7.7	8.2	8.6	9.0	9.9
92.5°	23.8	37.1	61.7	103.1	148.1	145.7	118.0	80.1	58.1	43.7	37.1
95°	33.9	54.3	102.6	202.0	326.7	400.4	391.8	324.9	256.2	200.7	162.7
97.5°	41.7	56.4	88.4	161.2	291.8	427.5	495.7	483.9	435.7	381.6	328.8
100°	47.9	61.5	87.7	146.4	260.3	408.1	521.0	555.8	533.7	487.1	440.1
102.5°	54.4	67.6	90.9	140.3	236.4	373.7	505.8	580.0	593.7	571.3	539.6
105°	65.0	77.7	97.6	137.8	213.3	327.6	457.3	565.8	627.6	647.5	642.5
107.5°	76.9	88.3	107.6	142.0	203.5	295.9	407.8	514.8	597.4	648.5	672.0
110°	84.5	96.3	114.8	145.9	200.7	281.1	379.6	477.2	563.1	626.8	665.2



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	92.4	103.9	121.7	151.0	200.7	272.4	358.6	447.6	529.1	593.5	638.8
115°	104.4	115.7	132.4	158.6	202.0	263.0	335.7	410.3	480.4	542.2	591.5
117.5°	116.7	127.6	143.5	167.3	204.9	258.4	322.1	386.3	446.6	499.9	545.2
120°	124.3	135.5	151.4	173.1	207.9	256.2	314.5	373.3	427.5	477.2	517.0
122.5°	131.9	143.1	159.0	179.6	210.4	254.4	308.0	363.5	413.8	458.0	495.3
125°	142.4	154.1	169.0	188.5	214.7	252.2	299.1	349.3	395.4	434.7	467.2
127.5°	152.6	164.3	178.6	196.5	219.4	251.0	291.0	334.9	377.9	414.5	445.0
130°	159.1	170.8	184.8	202.0	222.4	250.3	285.6	325.8	365.6	400.8	430.2
132.5°	164.9	176.6	190.6	206.7	225.6	250.3	281.2	316.8	354.0	386.0	414.3
135°	172.1	184.3	198.4	213.3	230.0	250.3	276.1	305.0	336.2	365.1	390.9
137.5°	178.6	191.2	203.9	218.2	234.1	250.9	271.5	295.1	320.3	344.4	366.2
140°	182.6	194.8	207.9	221.4	235.9	251.3	269.3	289.6	310.9	331.7	350.7
142.5°	186.6	198.0	210.4	223.2	236.9	251.6	267.5	284.9	302.9	320.8	337.3
145°	192.5	202.9	214.7	225.9	238.1	251.3	264.8	278.8	292.8	306.8	319.0
147.5°	197.9	207.1	217.4	227.6	238.6	250.1	262.0	273.1	284.4	295.2	304.4
150°	201.5	209.2	219.2	228.6	238.6	249.0	259.8	269.7	279.7	288.3	296.4
152.5°	204.8	211.8	220.9	229.3	238.2	247.6	257.3	266.2	275.0	282.9	289.2
155°	208.7	215.1	222.8	230.0	237.3	244.9	253.0	260.7	268.0	274.3	279.2
157.5°	212.9	217.7	224.3	230.4	236.1	242.2	249.1	255.3	261.3	266.2	270.1
160°	215.1	219.2	225.1	230.4	235.0	240.4	245.8	251.7	256.2	260.7	263.9
162.5°	217.3	220.6	225.8	230.1	233.9	238.2	243.0	247.7	251.9	255.6	258.5
165°	219.6	222.4	225.9	229.6	232.3	235.0	238.6	242.2	245.3	248.1	250.3
167.5°	221.3	222.9	225.9	228.5	229.7	231.8	234.3	236.9	239.1	241.1	242.7
170°	222.4	223.7	225.9	227.8	228.6	230.0	231.8	234.1	235.4	236.8	237.7
172.5°	223.1	223.7	225.6	227.0	227.2	227.8	229.3	230.8	232.2	233.1	233.7
175°	223.7	223.7	225.1	225.9	225.5	225.5	225.9	227.3	227.3	228.2	228.2
177.5°	223.8	223.8	224.5	224.8	224.1	224.1	224.5	224.8	225.2	225.2	225.2
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	5.4	5.2	5.3	5.3	5.3	5.2	5.4	5.2	5.1	5.1	5.0
90°	9.9	9.9	10.4	10.4	10.4	9.9	9.9	9.9	9.0	8.6	8.2
92.5°	31.3	30.2	29.5	28.8	29.5	30.2	31.3	37.1	43.7	58.1	80.1
95°	130.6	117.0	113.4	106.2	113.4	117.0	130.6	162.7	200.7	256.2	324.9
97.5°	300.9	275.5	262.4	256.7	262.4	275.5	300.9	328.8	381.6	435.7	483.9
100°	408.9	376.4	359.7	352.4	359.7	376.4	408.9	440.1	487.1	533.7	555.8
102.5°	506.2	483.1	464.9	459.5	464.9	483.1	506.2	539.6	571.3	593.7	580.0
105°	628.1	613.2	604.2	598.7	604.2	613.2	628.1	642.5	647.5	627.6	565.8
107.5°	679.4	679.3	676.3	672.6	676.3	679.3	679.4	672.0	648.5	597.4	514.8
110°	685.5	694.1	697.3	697.3	697.3	694.1	685.5	665.2	626.8	563.1	477.2



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	668.5	683.3	691.1	694.3	691.1	683.3	668.5	638.8	593.5	529.1	447.6
115°	626.8	648.5	661.1	667.0	661.1	648.5	626.8	591.5	542.2	480.4	410.3
117.5°	580.4	602.9	615.4	619.0	615.4	602.9	580.4	545.2	499.9	446.6	386.3
120°	550.4	572.1	584.3	587.9	584.3	572.1	550.4	517.0	477.2	427.5	373.3
122.5°	525.1	544.9	557.1	560.4	557.1	544.9	525.1	495.3	458.0	413.8	363.5
125°	492.6	511.1	521.0	525.5	521.0	511.1	492.6	467.2	434.7	395.4	349.3
127.5°	467.9	484.3	493.7	495.7	493.7	484.3	467.9	445.0	414.5	377.9	334.9
130°	452.8	467.7	476.7	479.4	476.7	467.7	452.8	430.2	400.8	365.6	325.8
132.5°	436.9	451.8	460.1	463.2	460.1	451.8	436.9	414.3	386.0	354.0	316.8
135°	410.7	425.6	433.8	436.5	433.8	425.6	410.7	390.9	365.1	336.2	305.0
137.5°	384.0	397.6	405.0	408.1	405.0	397.6	384.0	366.2	344.4	320.3	295.1
140°	367.4	379.1	385.9	388.2	385.9	379.1	367.4	350.7	331.7	310.9	289.6
142.5°	351.5	361.4	367.8	369.7	367.8	361.4	351.5	337.3	320.8	302.9	284.9
145°	329.9	337.5	342.5	344.4	342.5	337.5	329.9	319.0	306.8	292.8	278.8
147.5°	313.0	319.1	322.0	322.8	322.0	319.1	313.0	304.4	295.2	284.4	273.1
150°	303.2	308.6	310.5	310.9	310.5	308.6	303.2	296.4	288.3	279.7	269.7
152.5°	294.9	299.2	301.0	301.5	301.0	299.2	294.9	289.2	282.9	275.0	266.2
155°	283.8	286.9	288.3	288.8	288.3	286.9	283.8	279.2	274.3	268.0	260.7
157.5°	273.5	276.2	277.4	277.3	277.4	276.2	273.5	270.1	266.2	261.3	255.3
160°	267.0	269.3	270.2	269.7	270.2	269.3	267.0	263.9	260.7	256.2	251.7
162.5°	260.9	262.8	263.0	262.9	263.0	262.8	260.9	258.5	255.6	251.9	247.7
165°	252.2	253.0	253.0	253.0	253.0	253.0	252.2	250.3	248.1	245.3	242.2
167.5°	243.7	244.5	244.1	244.0	244.1	244.5	243.7	242.7	241.1	239.1	236.9
170°	238.6	239.1	239.1	238.6	239.1	239.1	238.6	237.7	236.8	235.4	234.1
172.5°	233.9	234.7	234.0	233.5	234.0	234.7	233.9	233.7	233.1	232.2	230.8
175°	228.2	228.6	227.8	227.3	227.8	228.6	228.2	228.2	228.2	227.3	227.3
177.5°	224.8	225.2	224.1	224.1	224.1	225.2	224.8	225.2	225.2	225.2	224.8
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	5.1	5.0	4.6	5.0	4.5	4.6	4.4	4.4	4.4	4.6	4.8
90°	7.7	7.2	6.3	5.9	5.0	4.5	3.6	2.7	1.8	0.9	0.5
92.5°	118.0	145.7	148.1	103.1	61.7	37.1	23.8	16.1	10.5	6.7	5.5
95°	391.8	400.4	326.7	202.0	102.6	54.3	33.9	23.9	19.0	15.4	14.9
97.5°	495.7	427.5	291.8	161.2	88.4	56.4	41.7	32.8	27.8	25.3	24.8
100°	521.0	408.1	260.3	146.4	87.7	61.5	47.9	39.3	34.4	32.6	31.6
102.5°	505.8	373.7	236.4	140.3	90.9	67.6	54.4	46.6	41.2	39.8	39.2
105°	457.3	327.6	213.3	137.8	97.6	77.7	65.0	57.8	53.3	51.1	51.1
107.5°	407.8	295.9	203.5	142.0	107.6	88.3	76.9	69.4	65.7	63.5	62.7
110°	379.6	281.1	200.7	145.9	114.8	96.3	84.5	77.7	73.7	71.9	71.0



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	358.6	272.4	200.7	151.0	121.7	103.9	92.4	85.7	81.6	80.2	79.3
115°	335.7	263.0	202.0	158.6	132.4	115.7	104.4	97.6	93.6	92.2	91.3
117.5°	322.1	258.4	204.9	167.3	143.5	127.6	116.7	109.0	105.0	103.5	102.1
120°	314.5	256.2	207.9	173.1	151.4	135.5	124.3	116.6	112.5	110.7	109.3
122.5°	308.0	254.4	210.4	179.6	159.0	143.1	131.9	123.4	119.4	118.0	116.9
125°	299.1	252.2	214.7	188.5	169.0	154.1	142.4	133.7	129.7	127.5	126.5
127.5°	291.0	251.0	219.4	196.5	178.6	164.3	152.6	143.5	138.3	135.4	134.0
130°	285.6	250.3	222.4	202.0	184.8	170.8	159.1	149.6	143.7	140.1	138.7
132.5°	281.2	250.3	225.6	206.7	190.6	176.6	164.9	155.0	148.4	144.1	142.4
135°	276.1	250.3	230.0	213.3	198.4	184.3	172.1	162.7	155.4	150.0	148.2
137.5°	271.5	250.9	234.1	218.2	203.9	191.2	178.6	169.3	162.1	157.0	155.7
140°	269.3	251.3	235.9	221.4	207.9	194.8	182.6	174.0	166.8	161.3	159.9
142.5°	267.5	251.6	236.9	223.2	210.4	198.0	186.6	178.3	171.1	166.0	165.0
145°	264.8	251.3	238.1	225.9	214.7	202.9	192.5	184.3	178.0	173.5	172.6
147.5°	262.0	250.1	238.6	227.6	217.4	207.1	197.9	190.8	185.0	181.1	180.5
150°	259.8	249.0	238.6	228.6	219.2	209.2	201.5	195.2	189.3	186.2	185.3
152.5°	257.3	247.6	238.2	229.3	220.9	211.8	204.8	198.8	193.7	190.8	190.4
155°	253.0	244.9	237.3	230.0	222.8	215.1	208.7	204.2	199.7	197.0	197.0
157.5°	249.1	242.2	236.1	230.4	224.3	217.7	212.9	209.0	205.1	202.9	203.0
160°	245.8	240.4	235.0	230.4	225.1	219.2	215.1	211.5	208.3	206.5	207.0
162.5°	243.0	238.2	233.9	230.1	225.8	220.6	217.3	214.4	211.6	209.8	210.2
165°	238.6	235.0	232.3	229.6	225.9	222.4	219.6	217.8	215.6	214.2	215.1
167.5°	234.3	231.8	229.7	228.5	225.9	222.9	221.3	220.0	218.7	217.9	218.3
170°	231.8	230.0	228.6	227.8	225.9	223.7	222.4	221.4	220.5	220.1	220.5
172.5°	229.3	227.8	227.2	227.0	225.6	223.7	223.1	222.5	221.6	221.2	222.0
175°	225.9	225.5	225.5	225.9	225.1	223.7	223.7	223.7	223.2	222.8	223.7
177.5°	224.5	224.1	224.1	224.8	224.5	223.8	223.8	224.1	223.8	223.8	224.5
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	4.8	4.4	3.9	4.2	4.4	4.4	4.5	4.5	4.5	4.6	4.7
90°	0.9	1.8	2.7	3.6	4.5	5.0	5.9	6.3	7.2	7.7	8.2
92.5°	6.7	10.5	16.1	23.8	37.1	61.7	103.1	148.1	145.7	118.0	80.1
95°	15.4	19.0	23.9	33.9	54.3	102.6	202.0	326.7	400.4	391.8	324.9
97.5°	25.3	27.8	32.8	41.7	56.4	88.4	161.2	291.8	427.5	495.7	483.9
100°	32.6	34.4	39.3	47.9	61.5	87.7	146.4	260.3	408.1	521.0	555.8
102.5°	39.8	41.2	46.6	54.4	67.6	90.9	140.3	236.4	373.7	505.8	580.0
105°	51.1	53.3	57.8	65.0	77.7	97.6	137.8	213.3	327.6	457.3	565.8
107.5°	63.5	65.7	69.4	76.9	88.3	107.6	142.0	203.5	295.9	407.8	514.8
110°	71.9	73.7	77.7	84.5	96.3	114.8	145.9	200.7	281.1	379.6	477.2



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	80.2	81.6	85.7	92.4	103.9	121.7	151.0	200.7	272.4	358.6	447.6
115°	92.2	93.6	97.6	104.4	115.7	132.4	158.6	202.0	263.0	335.7	410.3
117.5°	103.5	105.0	109.0	116.7	127.6	143.5	167.3	204.9	258.4	322.1	386.3
120°	110.7	112.5	116.6	124.3	135.5	151.4	173.1	207.9	256.2	314.5	373.3
122.5°	118.0	119.4	123.4	131.9	143.1	159.0	179.6	210.4	254.4	308.0	363.5
125°	127.5	129.7	133.7	142.4	154.1	169.0	188.5	214.7	252.2	299.1	349.3
127.5°	135.4	138.3	143.5	152.6	164.3	178.6	196.5	219.4	251.0	291.0	334.9
130°	140.1	143.7	149.6	159.1	170.8	184.8	202.0	222.4	250.3	285.6	325.8
132.5°	144.1	148.4	155.0	164.9	176.6	190.6	206.7	225.6	250.3	281.2	316.8
135°	150.0	155.4	162.7	172.1	184.3	198.4	213.3	230.0	250.3	276.1	305.0
137.5°	157.0	162.1	169.3	178.6	191.2	203.9	218.2	234.1	250.9	271.5	295.1
140°	161.3	166.8	174.0	182.6	194.8	207.9	221.4	235.9	251.3	269.3	289.6
142.5°	166.0	171.1	178.3	186.6	198.0	210.4	223.2	236.9	251.6	267.5	284.9
145°	173.5	178.0	184.3	192.5	202.9	214.7	225.9	238.1	251.3	264.8	278.8
147.5°	181.1	185.0	190.8	197.9	207.1	217.4	227.6	238.6	250.1	262.0	273.1
150°	186.2	189.3	195.2	201.5	209.2	219.2	228.6	238.6	249.0	259.8	269.7
152.5°	190.8	193.7	198.8	204.8	211.8	220.9	229.3	238.2	247.6	257.3	266.2
155°	197.0	199.7	204.2	208.7	215.1	222.8	230.0	237.3	244.9	253.0	260.7
157.5°	202.9	205.1	209.0	212.9	217.7	224.3	230.4	236.1	242.2	249.1	255.3
160°	206.5	208.3	211.5	215.1	219.2	225.1	230.4	235.0	240.4	245.8	251.7
162.5°	209.8	211.6	214.4	217.3	220.6	225.8	230.1	233.9	238.2	243.0	247.7
165°	214.2	215.6	217.8	219.6	222.4	225.9	229.6	232.3	235.0	238.6	242.2
167.5°	217.9	218.7	220.0	221.3	222.9	225.9	228.5	229.7	231.8	234.3	236.9
170°	220.1	220.5	221.4	222.4	223.7	225.9	227.8	228.6	230.0	231.8	234.1
172.5°	221.2	221.6	222.5	223.1	223.7	225.6	227.0	227.2	227.8	229.3	230.8
175°	222.8	223.2	223.7	223.7	223.7	225.1	225.9	225.5	225.5	225.9	227.3
177.5°	223.8	223.8	224.1	223.8	223.8	224.5	224.8	224.1	224.1	224.5	224.8
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1	224.1



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	4.9	5.1	5.1	4.9	4.9	5.1	5.3
90°	8.6	9.0	9.9	9.9	9.9	10.4	10.4
92.5°	58.1	43.7	37.1	31.3	30.2	29.5	28.8
95°	256.2	200.7	162.7	130.6	117.0	113.4	106.2
97.5°	435.7	381.6	328.8	300.9	275.5	262.4	256.7
100°	533.7	487.1	440.1	408.9	376.4	359.7	352.4
102.5°	593.7	571.3	539.6	506.2	483.1	464.9	459.5
105°	627.6	647.5	642.5	628.1	613.2	604.2	598.7
107.5°	597.4	648.5	672.0	679.4	679.3	676.3	672.6
110°	563.1	626.8	665.2	685.5	694.1	697.3	697.3



TEST NUMBER: P333498-927

CATALOG NUMBER: S125RDIP-S375D590U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	529.1	593.5	638.8	668.5	683.3	691.1	694.3
115°	480.4	542.2	591.5	626.8	648.5	661.1	667.0
117.5°	446.6	499.9	545.2	580.4	602.9	615.4	619.0
120°	427.5	477.2	517.0	550.4	572.1	584.3	587.9
122.5°	413.8	458.0	495.3	525.1	544.9	557.1	560.4
125°	395.4	434.7	467.2	492.6	511.1	521.0	525.5
127.5°	377.9	414.5	445.0	467.9	484.3	493.7	495.7
130°	365.6	400.8	430.2	452.8	467.7	476.7	479.4
132.5°	354.0	386.0	414.3	436.9	451.8	460.1	463.2
135°	336.2	365.1	390.9	410.7	425.6	433.8	436.5
137.5°	320.3	344.4	366.2	384.0	397.6	405.0	408.1
140°	310.9	331.7	350.7	367.4	379.1	385.9	388.2
142.5°	302.9	320.8	337.3	351.5	361.4	367.8	369.7
145°	292.8	306.8	319.0	329.9	337.5	342.5	344.4
147.5°	284.4	295.2	304.4	313.0	319.1	322.0	322.8
150°	279.7	288.3	296.4	303.2	308.6	310.5	310.9
152.5°	275.0	282.9	289.2	294.9	299.2	301.0	301.5
155°	268.0	274.3	279.2	283.8	286.9	288.3	288.8
157.5°	261.3	266.2	270.1	273.5	276.2	277.4	277.3
160°	256.2	260.7	263.9	267.0	269.3	270.2	269.7
162.5°	251.9	255.6	258.5	260.9	262.8	263.0	262.9
165°	245.3	248.1	250.3	252.2	253.0	253.0	253.0
167.5°	239.1	241.1	242.7	243.7	244.5	244.1	244.0
170°	235.4	236.8	237.7	238.6	239.1	239.1	238.6
172.5°	232.2	233.1	233.7	233.9	234.7	234.0	233.5
175°	227.3	228.2	228.2	228.2	228.6	227.8	227.3
177.5°	225.2	225.2	225.2	224.8	225.2	224.1	224.1
180°	224.1	224.1	224.1	224.1	224.1	224.1	224.1

(END OF REPORT)