

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333502-927

Luminaire Tested: **S125RDIP-S375D810U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333502-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D810U927-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3723.4 lumens  
Efficiency: N/A  
Efficacy: 119.3 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	20
4	72	61	54	48	64	55	49	44	44	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	12
8	52	40	32	27	46	36	30	25	29	25	21	23	20	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.8	1.1
10°-20°	125.3	3.4
20°-30°	198.7	5.3
30°-40°	239.6	6.4
40°-50°	214.0	5.7
50°-60°	164.1	4.4
60°-70°	106.6	2.9
70°-80°	51.8	1.4
80°-90°	14.1	0.4
90°-100°	30.4	0.8
100°-110°	187.2	5.0
110°-120°	339.5	9.1
120°-130°	435.7	11.7
130°-140°	468.6	12.6
140°-150°	439.8	11.8
150°-160°	355.8	9.6
160°-170°	230.1	6.2
170°-180°	79.4	2.1
0°-30°	366.8	9.8
0°-40°	606.3	16.3
0°-60°	984.4	26.4
0°-90°	1157.0	31.1
90°-120°	557.0	15.0
90°-150°	1901.1	51.1
90°-180°	2566.0	68.9
0°-180°	3723.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	15	1	15	1	15	7
95°	13	35	13	35	13	11
105°	184	182	184	182	184	166
115°	340	342	340	342	340	337
125°	486	486	486	486	486	433
135°	604	606	604	606	604	466
145°	701	703	701	703	701	438
155°	769	774	769	774	769	354
165°	813	817	813	817	813	229
175°	832	836	832	836	832	79
180°	836	836	836	836	836	



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	6.2	5.9	5.7	5.6	5.7	5.9	5.6	5.3	5.2	5.1	5.0
90°	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.3	10.6	9.9	9.0
92.5°	13.9	13.7	13.5	13.3	13.1	12.7	12.0	11.3	10.6	9.9	9.0
95°	13.0	13.0	13.0	13.0	13.0	12.7	12.0	11.3	10.6	9.9	15.1
97.5°	13.0	13.0	13.0	13.0	13.0	15.0	18.9	22.7	26.6	30.5	40.8
100°	13.0	13.5	14.1	14.7	15.2	25.7	46.3	66.8	87.3	107.8	107.3
102.5°	78.0	87.3	96.6	106.0	115.4	122.0	125.9	129.8	133.6	137.5	137.2
105°	184.0	184.1	184.3	184.4	184.6	184.6	184.6	184.6	184.6	184.6	184.6
107.5°	232.0	232.3	232.7	233.2	233.6	233.8	233.8	233.8	233.7	233.7	233.4
110°	265.1	265.0	264.9	264.7	264.6	264.7	265.1	265.5	266.0	266.4	266.1



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	294.9	295.1	295.2	295.5	295.6	296.0	296.5	297.1	297.6	298.1	297.9
115°	339.5	340.3	341.1	342.0	342.8	343.5	344.0	344.6	345.2	345.7	345.5
117.5°	387.1	387.5	387.8	388.2	388.5	389.0	389.8	390.5	391.2	391.9	391.4
120°	416.3	417.0	417.7	418.4	419.1	419.5	419.9	420.1	420.4	420.6	420.3
122.5°	444.1	444.9	445.7	446.5	447.3	447.8	448.1	448.4	448.6	448.9	448.7
125°	486.3	486.7	487.1	487.6	488.0	488.5	489.0	489.6	490.1	490.7	490.7
127.5°	521.9	522.9	523.9	525.0	525.9	526.6	527.0	527.2	527.5	527.8	527.9
130°	547.6	548.3	549.1	549.7	550.4	551.0	551.4	551.8	552.2	552.6	552.5
132.5°	571.5	572.1	572.8	573.5	574.2	574.6	574.6	574.7	574.8	574.9	575.2
135°	604.0	604.8	605.7	606.5	607.4	607.9	608.2	608.5	608.7	609.0	609.3
137.5°	636.8	637.5	638.2	638.9	639.6	639.9	639.8	639.8	639.8	639.7	640.0
140°	656.1	656.9	657.7	658.5	659.4	659.7	659.4	659.1	658.9	658.5	658.7
142.5°	674.4	675.3	676.0	676.9	677.7	678.1	678.0	678.0	677.9	677.9	677.7
145°	701.3	702.1	703.0	703.8	704.6	705.0	704.8	704.6	704.6	704.4	704.4
147.5°	723.5	724.5	725.5	726.4	727.5	727.9	727.7	727.5	727.4	727.2	727.1
150°	737.8	738.9	740.1	741.2	742.3	742.7	742.4	742.1	741.9	741.6	741.3
152.5°	751.2	752.3	753.2	754.2	755.2	755.6	755.3	755.0	754.7	754.5	754.2
155°	768.8	769.9	771.0	772.1	773.2	773.6	773.2	772.8	772.3	771.9	771.7
157.5°	783.5	784.7	785.8	786.9	788.0	788.3	787.9	787.4	787.0	786.6	786.5
160°	793.0	794.1	795.2	796.3	797.4	797.6	797.1	796.5	796.0	795.4	795.4
162.5°	801.5	802.6	803.8	805.0	806.3	806.4	805.7	804.9	804.1	803.4	803.3
165°	812.8	813.9	815.0	816.1	817.2	817.4	816.5	815.7	814.9	814.0	813.9
167.5°	820.8	822.0	823.2	824.4	825.7	825.9	824.8	823.9	822.8	821.9	821.7
170°	825.2	826.4	827.7	828.9	830.1	830.2	829.1	828.0	827.0	825.9	825.7
172.5°	828.1	829.4	830.7	831.9	833.1	833.3	832.3	831.2	830.3	829.3	829.0
175°	832.0	833.3	834.5	835.8	836.9	837.0	835.9	834.8	833.8	832.7	832.5
177.5°	834.2	835.1	836.0	836.9	837.8	837.8	837.0	836.3	835.5	834.7	834.6
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	5.0	4.8	4.8	4.5	4.1	4.7	4.9	4.8	4.8	4.7	4.6
90°	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6	1.7	2.9	4.0
92.5°	8.2	7.4	6.5	6.5	7.2	8.0	8.8	9.5	8.8	8.0	7.2
95°	20.4	25.6	30.8	33.7	34.1	34.5	34.9	35.3	34.9	34.5	34.1
97.5°	51.2	61.6	71.9	76.7	76.0	75.2	74.5	73.8	74.5	75.2	76.0
100°	106.7	106.2	105.6	105.1	104.7	104.3	103.9	103.5	103.9	104.3	104.7
102.5°	136.9	136.6	136.2	135.8	135.2	134.8	134.2	133.7	134.2	134.8	135.2
105°	184.6	184.6	184.6	184.3	183.8	183.2	182.7	182.1	182.7	183.2	183.8
107.5°	233.1	232.8	232.6	232.4	232.4	232.4	232.4	232.4	232.4	232.4	232.4
110°	265.9	265.5	265.3	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1





TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	297.8	297.6	297.5	297.2	296.9	296.5	296.2	295.9	296.2	296.5	296.9
115°	345.4	345.3	345.2	344.8	344.0	343.3	342.7	342.0	342.7	343.3	344.0
117.5°	390.9	390.3	389.8	389.6	389.6	389.6	389.7	389.7	389.7	389.6	389.6
120°	419.9	419.4	419.0	418.8	419.0	419.1	419.3	419.4	419.3	419.1	419.0
122.5°	448.5	448.3	448.1	447.7	447.3	446.7	446.2	445.7	446.2	446.7	447.3
125°	490.7	490.7	490.7	490.2	489.3	488.2	487.3	486.3	487.3	488.2	489.3
127.5°	528.0	528.1	528.1	527.8	527.2	526.5	525.8	525.1	525.8	526.5	527.2
130°	552.3	552.2	552.1	551.7	551.0	550.2	549.6	548.9	549.6	550.2	551.0
132.5°	575.5	575.8	576.2	575.9	575.0	574.3	573.5	572.7	573.5	574.3	575.0
135°	609.5	609.8	610.1	609.8	609.0	608.2	607.4	606.5	607.4	608.2	609.0
137.5°	640.2	640.5	640.7	640.5	639.8	639.1	638.3	637.6	638.3	639.1	639.8
140°	658.9	658.9	659.1	659.0	658.8	658.5	658.2	657.9	658.2	658.5	658.8
142.5°	677.5	677.3	677.1	676.9	676.8	676.6	676.4	676.3	676.4	676.6	676.8
145°	704.4	704.4	704.4	704.3	704.0	703.7	703.5	703.1	703.5	703.7	704.0
147.5°	726.8	726.7	726.5	726.5	726.5	726.6	726.7	726.7	726.7	726.6	726.5
150°	741.0	740.8	740.5	740.5	740.8	741.0	741.3	741.6	741.3	741.0	740.8
152.5°	753.9	753.6	753.4	753.5	754.2	754.7	755.3	756.0	755.3	754.7	754.2
155°	771.3	771.1	770.8	771.1	771.9	772.8	773.6	774.4	773.6	772.8	771.9
157.5°	786.5	786.5	786.4	786.6	787.2	787.7	788.1	788.6	788.1	787.7	787.2
160°	795.2	795.0	795.0	795.3	796.1	796.9	797.7	798.6	797.7	796.9	796.1
162.5°	803.1	803.0	802.9	803.2	804.0	804.9	805.6	806.5	805.6	804.9	804.0
165°	813.8	813.7	813.5	813.8	814.7	815.5	816.3	817.1	816.3	815.5	814.7
167.5°	821.6	821.4	821.3	821.7	822.5	823.4	824.3	825.1	824.3	823.4	822.5
170°	825.5	825.4	825.3	825.7	826.6	827.6	828.5	829.6	828.5	827.6	826.6
172.5°	828.8	828.5	828.3	828.6	829.7	830.6	831.6	832.5	831.6	830.6	829.7
175°	832.3	832.2	832.1	832.4	833.3	834.1	834.9	835.8	834.9	834.1	833.3
177.5°	834.5	834.4	834.3	834.6	835.3	835.9	836.5	837.3	836.5	835.9	835.3
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	4.7	4.9	4.9	5.4	5.1	5.5	5.6	5.6	5.8	5.9	5.9
90°	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.3	12.0	12.7	13.2
92.5°	6.5	6.5	7.4	8.2	9.0	9.9	10.6	11.3	12.0	12.7	13.1
95°	33.7	30.8	25.6	20.4	15.1	9.9	10.6	11.3	12.0	12.7	13.0
97.5°	76.7	71.9	61.6	51.2	40.8	30.5	26.6	22.7	18.9	15.0	13.0
100°	105.1	105.6	106.2	106.7	107.3	107.8	87.3	66.8	46.3	25.7	15.2
102.5°	135.8	136.2	136.6	136.9	137.2	137.5	133.6	129.8	125.9	122.0	115.4
105°	184.3	184.6	184.6	184.6	184.6	184.6	184.6	184.6	184.6	184.6	184.6
107.5°	232.4	232.6	232.8	233.1	233.4	233.7	233.7	233.8	233.8	233.8	233.6
110°	265.1	265.3	265.5	265.9	266.1	266.4	266.0	265.5	265.1	264.7	264.6



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.2	297.5	297.6	297.8	297.9	298.1	297.6	297.1	296.5	296.0	295.6
115°	344.8	345.2	345.3	345.4	345.5	345.7	345.2	344.6	344.0	343.5	342.8
117.5°	389.6	389.8	390.3	390.9	391.4	391.9	391.2	390.5	389.8	389.0	388.5
120°	418.8	419.0	419.4	419.9	420.3	420.6	420.4	420.1	419.9	419.5	419.1
122.5°	447.7	448.1	448.3	448.5	448.7	448.9	448.6	448.4	448.1	447.8	447.3
125°	490.2	490.7	490.7	490.7	490.7	490.7	490.1	489.6	489.0	488.5	488.0
127.5°	527.8	528.1	528.1	528.0	527.9	527.8	527.5	527.2	527.0	526.6	525.9
130°	551.7	552.1	552.2	552.3	552.5	552.6	552.2	551.8	551.4	551.0	550.4
132.5°	575.9	576.2	575.8	575.5	575.2	574.9	574.8	574.7	574.6	574.6	574.2
135°	609.8	610.1	609.8	609.5	609.3	609.0	608.7	608.5	608.2	607.9	607.4
137.5°	640.5	640.7	640.5	640.2	640.0	639.7	639.8	639.8	639.8	639.9	639.6
140°	659.0	659.1	658.9	658.9	658.7	658.5	658.9	659.1	659.4	659.7	659.4
142.5°	676.9	677.1	677.3	677.5	677.7	677.9	677.9	678.0	678.0	678.1	677.7
145°	704.3	704.4	704.4	704.4	704.4	704.4	704.6	704.6	704.8	705.0	704.6
147.5°	726.5	726.5	726.7	726.8	727.1	727.2	727.4	727.5	727.7	727.9	727.5
150°	740.5	740.5	740.8	741.0	741.3	741.6	741.9	742.1	742.4	742.7	742.3
152.5°	753.5	753.4	753.6	753.9	754.2	754.5	754.7	755.0	755.3	755.6	755.2
155°	771.1	770.8	771.1	771.3	771.7	771.9	772.3	772.8	773.2	773.6	773.2
157.5°	786.6	786.4	786.5	786.5	786.5	786.6	787.0	787.4	787.9	788.3	788.0
160°	795.3	795.0	795.0	795.2	795.4	795.4	796.0	796.5	797.1	797.6	797.4
162.5°	803.2	802.9	803.0	803.1	803.3	803.4	804.1	804.9	805.7	806.4	806.3
165°	813.8	813.5	813.7	813.8	813.9	814.0	814.9	815.7	816.5	817.4	817.2
167.5°	821.7	821.3	821.4	821.6	821.7	821.9	822.8	823.9	824.8	825.9	825.7
170°	825.7	825.3	825.4	825.5	825.7	825.9	827.0	828.0	829.1	830.2	830.1
172.5°	828.6	828.3	828.5	828.8	829.0	829.3	830.3	831.2	832.3	833.3	833.1
175°	832.4	832.1	832.2	832.3	832.5	832.7	833.8	834.8	835.9	837.0	836.9
177.5°	834.6	834.3	834.4	834.5	834.6	834.7	835.5	836.3	837.0	837.8	837.8
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	6.1	6.0	6.1	6.2	6.1	6.0	6.1	5.9	5.9	5.8	5.6
90°	13.6	14.0	14.4	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.3
92.5°	13.3	13.5	13.7	13.9	13.7	13.5	13.3	13.1	12.7	12.0	11.3
95°	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0	12.7	12.0	11.3
97.5°	13.0	13.0	13.0	13.0	13.0	13.0	13.0	13.0	15.0	18.9	22.7
100°	14.7	14.1	13.5	13.0	13.5	14.1	14.7	15.2	25.7	46.3	66.8
102.5°	106.0	96.6	87.3	78.0	87.3	96.6	106.0	115.4	122.0	125.9	129.8
105°	184.4	184.3	184.1	184.0	184.1	184.3	184.4	184.6	184.6	184.6	184.6
107.5°	233.2	232.7	232.3	232.0	232.3	232.7	233.2	233.6	233.8	233.8	233.8
110°	264.7	264.9	265.0	265.1	265.0	264.9	264.7	264.6	264.7	265.1	265.5



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	295.5	295.2	295.1	294.9	295.1	295.2	295.5	295.6	296.0	296.5	297.1
115°	342.0	341.1	340.3	339.5	340.3	341.1	342.0	342.8	343.5	344.0	344.6
117.5°	388.2	387.8	387.5	387.1	387.5	387.8	388.2	388.5	389.0	389.8	390.5
120°	418.4	417.7	417.0	416.3	417.0	417.7	418.4	419.1	419.5	419.9	420.1
122.5°	446.5	445.7	444.9	444.1	444.9	445.7	446.5	447.3	447.8	448.1	448.4
125°	487.6	487.1	486.7	486.3	486.7	487.1	487.6	488.0	488.5	489.0	489.6
127.5°	525.0	523.9	522.9	521.9	522.9	523.9	525.0	525.9	526.6	527.0	527.2
130°	549.7	549.1	548.3	547.6	548.3	549.1	549.7	550.4	551.0	551.4	551.8
132.5°	573.5	572.8	572.1	571.5	572.1	572.8	573.5	574.2	574.6	574.6	574.7
135°	606.5	605.7	604.8	604.0	604.8	605.7	606.5	607.4	607.9	608.2	608.5
137.5°	638.9	638.2	637.5	636.8	637.5	638.2	638.9	639.6	639.9	639.8	639.8
140°	658.5	657.7	656.9	656.1	656.9	657.7	658.5	659.4	659.7	659.4	659.1
142.5°	676.9	676.0	675.3	674.4	675.3	676.0	676.9	677.7	678.1	678.0	678.0
145°	703.8	703.0	702.1	701.3	702.1	703.0	703.8	704.6	705.0	704.8	704.6
147.5°	726.4	725.5	724.5	723.5	724.5	725.5	726.4	727.5	727.9	727.7	727.5
150°	741.2	740.1	738.9	737.8	738.9	740.1	741.2	742.3	742.7	742.4	742.1
152.5°	754.2	753.2	752.3	751.2	752.3	753.2	754.2	755.2	755.6	755.3	755.0
155°	772.1	771.0	769.9	768.8	769.9	771.0	772.1	773.2	773.6	773.2	772.8
157.5°	786.9	785.8	784.7	783.5	784.7	785.8	786.9	788.0	788.3	787.9	787.4
160°	796.3	795.2	794.1	793.0	794.1	795.2	796.3	797.4	797.6	797.1	796.5
162.5°	805.0	803.8	802.6	801.5	802.6	803.8	805.0	806.3	806.4	805.7	804.9
165°	816.1	815.0	813.9	812.8	813.9	815.0	816.1	817.2	817.4	816.5	815.7
167.5°	824.4	823.2	822.0	820.8	822.0	823.2	824.4	825.7	825.9	824.8	823.9
170°	828.9	827.7	826.4	825.2	826.4	827.7	828.9	830.1	830.2	829.1	828.0
172.5°	831.9	830.7	829.4	828.1	829.4	830.7	831.9	833.1	833.3	832.3	831.2
175°	835.8	834.5	833.3	832.0	833.3	834.5	835.8	836.9	837.0	835.9	834.8
177.5°	836.9	836.0	835.1	834.2	835.1	836.0	836.9	837.8	837.8	837.0	836.3
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	5.6	5.5	5.1	5.4	4.9	4.9	4.7	4.6	4.7	4.8	4.8
90°	10.6	9.9	9.0	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6
92.5°	10.6	9.9	9.0	8.2	7.4	6.5	6.5	7.2	8.0	8.8	9.5
95°	10.6	9.9	15.1	20.4	25.6	30.8	33.7	34.1	34.5	34.9	35.3
97.5°	26.6	30.5	40.8	51.2	61.6	71.9	76.7	76.0	75.2	74.5	73.8
100°	87.3	107.8	107.3	106.7	106.2	105.6	105.1	104.7	104.3	103.9	103.5
102.5°	133.6	137.5	137.2	136.9	136.6	136.2	135.8	135.2	134.8	134.2	133.7
105°	184.6	184.6	184.6	184.6	184.6	184.6	184.3	183.8	183.2	182.7	182.1
107.5°	233.7	233.7	233.4	233.1	232.8	232.6	232.4	232.4	232.4	232.4	232.4
110°	266.0	266.4	266.1	265.9	265.5	265.3	265.1	265.1	265.1	265.1	265.1



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	297.6	298.1	297.9	297.8	297.6	297.5	297.2	296.9	296.5	296.2	295.9
115°	345.2	345.7	345.5	345.4	345.3	345.2	344.8	344.0	343.3	342.7	342.0
117.5°	391.2	391.9	391.4	390.9	390.3	389.8	389.6	389.6	389.6	389.7	389.7
120°	420.4	420.6	420.3	419.9	419.4	419.0	418.8	419.0	419.1	419.3	419.4
122.5°	448.6	448.9	448.7	448.5	448.3	448.1	447.7	447.3	446.7	446.2	445.7
125°	490.1	490.7	490.7	490.7	490.7	490.7	490.2	489.3	488.2	487.3	486.3
127.5°	527.5	527.8	527.9	528.0	528.1	528.1	527.8	527.2	526.5	525.8	525.1
130°	552.2	552.6	552.5	552.3	552.2	552.1	551.7	551.0	550.2	549.6	548.9
132.5°	574.8	574.9	575.2	575.5	575.8	576.2	575.9	575.0	574.3	573.5	572.7
135°	608.7	609.0	609.3	609.5	609.8	610.1	609.8	609.0	608.2	607.4	606.5
137.5°	639.8	639.7	640.0	640.2	640.5	640.7	640.5	639.8	639.1	638.3	637.6
140°	658.9	658.5	658.7	658.9	658.9	659.1	659.0	658.8	658.5	658.2	657.9
142.5°	677.9	677.9	677.7	677.5	677.3	677.1	676.9	676.8	676.6	676.4	676.3
145°	704.6	704.4	704.4	704.4	704.4	704.4	704.3	704.0	703.7	703.5	703.1
147.5°	727.4	727.2	727.1	726.8	726.7	726.5	726.5	726.5	726.6	726.7	726.7
150°	741.9	741.6	741.3	741.0	740.8	740.5	740.5	740.8	741.0	741.3	741.6
152.5°	754.7	754.5	754.2	753.9	753.6	753.4	753.5	754.2	754.7	755.3	756.0
155°	772.3	771.9	771.7	771.3	771.1	770.8	771.1	771.9	772.8	773.6	774.4
157.5°	787.0	786.6	786.5	786.5	786.5	786.4	786.6	787.2	787.7	788.1	788.6
160°	796.0	795.4	795.4	795.2	795.0	795.0	795.3	796.1	796.9	797.7	798.6
162.5°	804.1	803.4	803.3	803.1	803.0	802.9	803.2	804.0	804.9	805.6	806.5
165°	814.9	814.0	813.9	813.8	813.7	813.5	813.8	814.7	815.5	816.3	817.1
167.5°	822.8	821.9	821.7	821.6	821.4	821.3	821.7	822.5	823.4	824.3	825.1
170°	827.0	825.9	825.7	825.5	825.4	825.3	825.7	826.6	827.6	828.5	829.6
172.5°	830.3	829.3	829.0	828.8	828.5	828.3	828.6	829.7	830.6	831.6	832.5
175°	833.8	832.7	832.5	832.3	832.2	832.1	832.4	833.3	834.1	834.9	835.8
177.5°	835.5	834.7	834.6	834.5	834.4	834.3	834.6	835.3	835.9	836.5	837.3
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	4.9	4.7	4.1	4.5	4.8	4.8	5.0	5.0	5.1	5.2	5.3
90°	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.3
92.5°	8.8	8.0	7.2	6.5	6.5	7.4	8.2	9.0	9.9	10.6	11.3
95°	34.9	34.5	34.1	33.7	30.8	25.6	20.4	15.1	9.9	10.6	11.3
97.5°	74.5	75.2	76.0	76.7	71.9	61.6	51.2	40.8	30.5	26.6	22.7
100°	103.9	104.3	104.7	105.1	105.6	106.2	106.7	107.3	107.8	87.3	66.8
102.5°	134.2	134.8	135.2	135.8	136.2	136.6	136.9	137.2	137.5	133.6	129.8
105°	182.7	183.2	183.8	184.3	184.6	184.6	184.6	184.6	184.6	184.6	184.6
107.5°	232.4	232.4	232.4	232.4	232.6	232.8	233.1	233.4	233.7	233.7	233.8
110°	265.1	265.1	265.1	265.1	265.3	265.5	265.9	266.1	266.4	266.0	265.5





TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	296.2	296.5	296.9	297.2	297.5	297.6	297.8	297.9	298.1	297.6	297.1
115°	342.7	343.3	344.0	344.8	345.2	345.3	345.4	345.5	345.7	345.2	344.6
117.5°	389.7	389.6	389.6	389.6	389.8	390.3	390.9	391.4	391.9	391.2	390.5
120°	419.3	419.1	419.0	418.8	419.0	419.4	419.9	420.3	420.6	420.4	420.1
122.5°	446.2	446.7	447.3	447.7	448.1	448.3	448.5	448.7	448.9	448.6	448.4
125°	487.3	488.2	489.3	490.2	490.7	490.7	490.7	490.7	490.7	490.1	489.6
127.5°	525.8	526.5	527.2	527.8	528.1	528.1	528.0	527.9	527.8	527.5	527.2
130°	549.6	550.2	551.0	551.7	552.1	552.2	552.3	552.5	552.6	552.2	551.8
132.5°	573.5	574.3	575.0	575.9	576.2	575.8	575.5	575.2	574.9	574.8	574.7
135°	607.4	608.2	609.0	609.8	610.1	609.8	609.5	609.3	609.0	608.7	608.5
137.5°	638.3	639.1	639.8	640.5	640.7	640.5	640.2	640.0	639.7	639.8	639.8
140°	658.2	658.5	658.8	659.0	659.1	658.9	658.9	658.7	658.5	658.9	659.1
142.5°	676.4	676.6	676.8	676.9	677.1	677.3	677.5	677.7	677.9	677.9	678.0
145°	703.5	703.7	704.0	704.3	704.4	704.4	704.4	704.4	704.4	704.6	704.6
147.5°	726.7	726.6	726.5	726.5	726.5	726.7	726.8	727.1	727.2	727.4	727.5
150°	741.3	741.0	740.8	740.5	740.5	740.8	741.0	741.3	741.6	741.9	742.1
152.5°	755.3	754.7	754.2	753.5	753.4	753.6	753.9	754.2	754.5	754.7	755.0
155°	773.6	772.8	771.9	771.1	770.8	771.1	771.3	771.7	771.9	772.3	772.8
157.5°	788.1	787.7	787.2	786.6	786.4	786.5	786.5	786.5	786.6	787.0	787.4
160°	797.7	796.9	796.1	795.3	795.0	795.0	795.2	795.4	795.4	796.0	796.5
162.5°	805.6	804.9	804.0	803.2	802.9	803.0	803.1	803.3	803.4	804.1	804.9
165°	816.3	815.5	814.7	813.8	813.5	813.7	813.8	813.9	814.0	814.9	815.7
167.5°	824.3	823.4	822.5	821.7	821.3	821.4	821.6	821.7	821.9	822.8	823.9
170°	828.5	827.6	826.6	825.7	825.3	825.4	825.5	825.7	825.9	827.0	828.0
172.5°	831.6	830.6	829.7	828.6	828.3	828.5	828.8	829.0	829.3	830.3	831.2
175°	834.9	834.1	833.3	832.4	832.1	832.2	832.3	832.5	832.7	833.8	834.8
177.5°	836.5	835.9	835.3	834.6	834.3	834.4	834.5	834.6	834.7	835.5	836.3
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	5.6	5.9	5.7	5.6	5.7	5.9	6.2
90°	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	12.0	12.7	13.1	13.3	13.5	13.7	13.9
95°	12.0	12.7	13.0	13.0	13.0	13.0	13.0
97.5°	18.9	15.0	13.0	13.0	13.0	13.0	13.0
100°	46.3	25.7	15.2	14.7	14.1	13.5	13.0
102.5°	125.9	122.0	115.4	106.0	96.6	87.3	78.0
105°	184.6	184.6	184.6	184.4	184.3	184.1	184.0
107.5°	233.8	233.8	233.6	233.2	232.7	232.3	232.0
110°	265.1	264.7	264.6	264.7	264.9	265.0	265.1



TEST NUMBER: P333502-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	296.5	296.0	295.6	295.5	295.2	295.1	294.9
115°	344.0	343.5	342.8	342.0	341.1	340.3	339.5
117.5°	389.8	389.0	388.5	388.2	387.8	387.5	387.1
120°	419.9	419.5	419.1	418.4	417.7	417.0	416.3
122.5°	448.1	447.8	447.3	446.5	445.7	444.9	444.1
125°	489.0	488.5	488.0	487.6	487.1	486.7	486.3
127.5°	527.0	526.6	525.9	525.0	523.9	522.9	521.9
130°	551.4	551.0	550.4	549.7	549.1	548.3	547.6
132.5°	574.6	574.6	574.2	573.5	572.8	572.1	571.5
135°	608.2	607.9	607.4	606.5	605.7	604.8	604.0
137.5°	639.8	639.9	639.6	638.9	638.2	637.5	636.8
140°	659.4	659.7	659.4	658.5	657.7	656.9	656.1
142.5°	678.0	678.1	677.7	676.9	676.0	675.3	674.4
145°	704.8	705.0	704.6	703.8	703.0	702.1	701.3
147.5°	727.7	727.9	727.5	726.4	725.5	724.5	723.5
150°	742.4	742.7	742.3	741.2	740.1	738.9	737.8
152.5°	755.3	755.6	755.2	754.2	753.2	752.3	751.2
155°	773.2	773.6	773.2	772.1	771.0	769.9	768.8
157.5°	787.9	788.3	788.0	786.9	785.8	784.7	783.5
160°	797.1	797.6	797.4	796.3	795.2	794.1	793.0
162.5°	805.7	806.4	806.3	805.0	803.8	802.6	801.5
165°	816.5	817.4	817.2	816.1	815.0	813.9	812.8
167.5°	824.8	825.9	825.7	824.4	823.2	822.0	820.8
170°	829.1	830.2	830.1	828.9	827.7	826.4	825.2
172.5°	832.3	833.3	833.1	831.9	830.7	829.4	828.1
175°	835.9	837.0	836.9	835.8	834.5	833.3	832.0
177.5°	837.0	837.8	837.8	836.9	836.0	835.1	834.2
180°	835.8	835.8	835.8	835.8	835.8	835.8	835.8

(END OF REPORT)