

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333503-927

Luminaire Tested: **S125RDIP-S375D810U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333503-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D810U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3378.2 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	36	36	29
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	30	28	26	22
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	22	19	18	14
7	56	44	37	31	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	1.3
10°-20°	125.3	3.7
20°-30°	198.7	5.9
30°-40°	239.6	7.1
40°-50°	214.0	6.3
50°-60°	164.1	4.9
60°-70°	106.6	3.2
70°-80°	51.8	1.5
80°-90°	14.1	0.4
90°-100°	53.3	1.6
100°-110°	157.4	4.7
110°-120°	266.7	7.9
120°-130°	350.9	10.4
130°-140°	393.2	11.6
140°-150°	385.4	11.4
150°-160°	323.7	9.6
160°-170°	215.2	6.4
170°-180°	75.3	2.2
0°-30°	366.8	10.9
0°-40°	606.3	17.9
0°-60°	984.4	29.1
0°-90°	1157.0	34.2
90°-120°	477.4	14.1
90°-150°	1607.0	47.6
90°-180°	2221.0	65.7
0°-180°	3378.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	15	1	15	1	15	9
95°	53	40	53	40	53	54
105°	154	141	154	141	154	163
115°	270	267	270	267	270	267
125°	392	390	392	390	392	350
135°	509	507	509	507	509	392
145°	616	614	616	614	616	385
155°	702	702	702	702	702	323
165°	762	764	762	764	762	215
175°	791	794	791	794	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	6.2	5.9	5.7	5.6	5.7	5.9	5.6	5.3	5.2	5.1	5.0
90°	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2	10.6	9.9	9.0
92.5°	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6	24.7	23.8	22.6
95°	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6	48.6	47.7	46.3
97.5°	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8	76.8	76.0	74.1
100°	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3	96.0	94.7	93.0
102.5°	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3	116.0	114.6	113.7
105°	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7	148.9	148.1	147.2
107.5°	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7	184.3	183.9	183.2
110°	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0	208.6	208.1	207.7



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3	233.1	232.9	232.4
115°	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5	270.5	270.7	270.5
117.5°	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6	307.4	307.4	307.1
120°	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6	332.6	332.6	332.5
122.5°	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2	357.3	357.4	357.0
125°	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4	393.7	394.0	393.8
127.5°	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4	429.5	429.7	429.5
130°	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1	453.3	453.4	453.1
132.5°	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9	476.1	476.3	476.3
135°	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0	511.0	511.0	510.9
137.5°	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2	545.0	544.9	544.5
140°	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7	566.5	566.2	565.8
142.5°	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8	587.6	587.5	586.9
145°	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2	618.2	618.2	617.8
147.5°	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3	646.0	645.7	645.4
150°	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1	664.1	664.1	663.5
152.5°	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6	680.2	679.9	679.7
155°	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2	703.6	703.1	702.9
157.5°	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6	724.1	723.5	723.3
160°	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0	736.5	735.9	735.8
162.5°	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6	748.0	747.3	747.3
165°	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3	763.7	763.2	763.0
167.5°	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9	775.0	774.2	774.2
170°	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8	782.0	781.1	781.1
172.5°	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7	786.9	786.1	786.1
175°	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3	792.5	791.6	791.6
177.5°	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8	795.2	794.5	794.6
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	5.0	4.8	4.8	4.5	4.1	4.7	4.9	4.8	4.8	4.7	4.6
90°	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6	1.7	2.9	4.0
92.5°	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0	15.8	16.6	17.3
95°	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2	40.6	40.8	41.1
97.5°	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9	67.0	67.1	67.3
100°	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
102.5°	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1	108.6	109.2	109.7
105°	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2	142.0	142.6	143.3
107.5°	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9	178.6	179.3	180.0
110°	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2	203.9	204.5	205.3



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9	229.3	229.7	230.0
115°	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0	267.5	268.1	268.6
117.5°	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1	305.4	305.6	305.9
120°	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9	329.6	330.3	331.0
122.5°	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7	355.0	355.2	355.5
125°	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6	390.5	391.3	392.1
127.5°	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8	427.3	427.7	428.2
130°	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1	449.8	450.5	451.1
132.5°	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4	472.5	473.6	474.8
135°	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7	507.6	508.3	509.2
137.5°	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0	540.7	541.5	542.3
140°	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3	561.9	562.6	563.3
142.5°	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6	583.1	583.7	584.2
145°	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9	614.4	615.0	615.5
147.5°	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9	643.2	643.5	643.8
150°	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2	662.0	661.9	661.8
152.5°	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0	678.3	678.4	678.7
155°	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
157.5°	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3	724.0	723.7	723.3
160°	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1	736.7	736.3	735.9
162.5°	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5	748.2	747.9	747.7
165°	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8	763.5	763.3	763.0
167.5°	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7	776.1	775.5	775.0
170°	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6	783.1	782.5	782.0
172.5°	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5	788.0	787.4	786.9
175°	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2	793.6	793.1	792.5
177.5°	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0	796.5	796.1	795.7
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	4.7	4.9	4.9	5.4	5.1	5.5	5.6	5.6	5.8	5.9	5.9
90°	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2	12.0	12.7	13.2
92.5°	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6	26.5	27.4	28.0
95°	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6	50.6	51.6	52.2
97.5°	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8	78.7	79.6	80.1
100°	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3	98.5	99.7	100.5
102.5°	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3	118.7	120.0	120.9
105°	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7	150.5	151.4	151.9
107.5°	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7	185.1	185.5	185.7
110°	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0	209.4	209.8	209.9



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3	233.5	233.7	233.7
115°	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5	270.3	270.1	270.0
117.5°	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6	307.7	307.8	307.6
120°	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6	332.6	332.6	332.4
122.5°	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2	357.1	357.0	356.7
125°	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4	393.2	392.8	392.7
127.5°	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4	429.2	429.1	428.9
130°	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1	453.0	452.9	452.7
132.5°	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9	475.8	475.7	475.4
135°	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0	511.0	511.0	510.8
137.5°	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2	545.3	545.5	545.3
140°	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7	567.0	567.3	567.0
142.5°	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8	588.0	588.1	587.9
145°	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2	618.2	618.2	618.0
147.5°	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3	646.7	647.1	646.7
150°	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1	664.1	664.1	663.9
152.5°	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6	680.9	681.2	681.1
155°	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2	704.7	705.3	705.2
157.5°	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6	725.2	725.7	725.6
160°	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0	737.5	738.1	738.1
162.5°	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6	749.3	750.0	749.9
165°	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3	764.9	765.3	765.2
167.5°	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9	776.7	777.5	777.4
170°	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8	783.6	784.4	784.3
172.5°	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7	788.5	789.4	789.4
175°	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3	794.2	795.0	794.9
177.5°	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8	796.5	797.2	797.1
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	6.1	6.0	6.1	6.2	6.1	6.0	6.1	5.9	5.9	5.8	5.6
90°	13.6	14.0	14.4	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2
92.5°	28.4	28.6	28.9	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6
95°	52.4	52.8	53.0	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6
97.5°	80.2	80.4	80.6	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8
100°	100.8	101.0	101.3	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3
102.5°	121.3	121.6	122.0	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3
105°	152.4	152.8	153.2	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7
107.5°	185.7	185.6	185.6	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7
110°	209.8	209.6	209.5	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	233.4	233.1	232.9	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3
115°	269.9	269.7	269.6	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5
117.5°	307.0	306.5	305.9	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6
120°	331.8	331.3	330.7	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6
122.5°	356.2	355.8	355.4	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2
125°	392.5	392.4	392.3	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4
127.5°	428.6	428.3	428.1	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4
130°	452.4	452.1	451.9	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1
132.5°	475.1	474.7	474.3	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9
135°	510.2	509.7	509.1	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0
137.5°	544.5	543.9	543.2	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2
140°	566.4	565.7	565.0	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7
142.5°	587.2	586.5	585.8	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8
145°	617.6	617.2	616.8	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2
147.5°	645.8	644.8	644.0	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3
150°	663.6	663.4	663.1	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1
152.5°	680.6	680.2	679.7	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6
155°	704.5	703.9	703.1	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2
157.5°	724.6	723.7	722.8	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6
160°	737.4	736.7	735.9	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0
162.5°	749.1	748.3	747.5	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6
165°	764.4	763.6	762.7	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3
167.5°	776.7	775.8	774.9	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9
170°	783.4	782.4	781.5	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8
172.5°	788.5	787.7	786.8	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7
175°	793.9	793.0	792.0	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3
177.5°	796.3	795.6	794.8	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	5.6	5.5	5.1	5.4	4.9	4.9	4.7	4.6	4.7	4.8	4.8
90°	10.6	9.9	9.0	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6
92.5°	24.7	23.8	22.6	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0
95°	48.6	47.7	46.3	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2
97.5°	76.8	76.0	74.1	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9
100°	96.0	94.7	93.0	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7
102.5°	116.0	114.6	113.7	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1
105°	148.9	148.1	147.2	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2
107.5°	184.3	183.9	183.2	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9
110°	208.6	208.1	207.7	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	233.1	232.9	232.4	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9
115°	270.5	270.7	270.5	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0
117.5°	307.4	307.4	307.1	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1
120°	332.6	332.6	332.5	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9
122.5°	357.3	357.4	357.0	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7
125°	393.7	394.0	393.8	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6
127.5°	429.5	429.7	429.5	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8
130°	453.3	453.4	453.1	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1
132.5°	476.1	476.3	476.3	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4
135°	511.0	511.0	510.9	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7
137.5°	545.0	544.9	544.5	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0
140°	566.5	566.2	565.8	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3
142.5°	587.6	587.5	586.9	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6
145°	618.2	618.2	617.8	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9
147.5°	646.0	645.7	645.4	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9
150°	664.1	664.1	663.5	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2
152.5°	680.2	679.9	679.7	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0
155°	703.6	703.1	702.9	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4
157.5°	724.1	723.5	723.3	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3
160°	736.5	735.9	735.8	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1
162.5°	748.0	747.3	747.3	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5
165°	763.7	763.2	763.0	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8
167.5°	775.0	774.2	774.2	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7
170°	782.0	781.1	781.1	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6
172.5°	786.9	786.1	786.1	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5
175°	792.5	791.6	791.6	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2
177.5°	795.2	794.5	794.6	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	4.9	4.7	4.1	4.5	4.8	4.8	5.0	5.0	5.1	5.2	5.3
90°	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2
92.5°	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6
95°	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6
97.5°	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8
100°	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3
102.5°	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3
105°	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7
107.5°	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7
110°	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3
115°	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5
117.5°	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6
120°	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6
122.5°	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2
125°	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4
127.5°	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4
130°	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1
132.5°	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9
135°	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0
137.5°	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2
140°	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7
142.5°	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8
145°	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2
147.5°	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3
150°	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1
152.5°	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6
155°	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2
157.5°	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6
160°	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0
162.5°	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6
165°	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3
167.5°	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9
170°	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8
172.5°	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7
175°	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3
177.5°	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	5.6	5.9	5.7	5.6	5.7	5.9	6.2
90°	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333503-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)