

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333504-927

Luminaire Tested: **S125RDIP-S375D810U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333504-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D810U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3460.9 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30	24
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	62	54	48	65	56	50	45	45	41	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	23	21	20	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	29	25	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	1.2
10°-20°	125.3	3.6
20°-30°	198.7	5.7
30°-40°	239.6	6.9
40°-50°	214.0	6.2
50°-60°	164.1	4.7
60°-70°	106.6	3.1
70°-80°	51.8	1.5
80°-90°	14.1	0.4
90°-100°	222.7	6.4
100°-110°	478.7	13.8
110°-120°	449.3	13.0
120°-130°	364.1	10.5
130°-140°	292.2	8.4
140°-150°	220.5	6.4
150°-160°	155.2	4.5
160°-170°	91.5	2.6
170°-180°	29.8	0.9
0°-30°	366.8	10.6
0°-40°	606.3	17.5
0°-60°	984.4	28.4
0°-90°	1157.0	33.4
90°-120°	1150.7	33.2
90°-150°	2027.5	58.6
90°-180°	2304.0	66.6
0°-180°	3460.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	14	1	14	1	14	10
95°	146	20	146	20	146	206
105°	821	70	821	70	821	816
115°	914	125	914	125	914	893
125°	720	173	720	173	720	652
135°	598	203	598	203	598	464
145°	472	237	472	237	472	300
155°	396	270	396	270	396	184
165°	347	295	347	295	347	99
175°	312	307	312	307	312	30
180°	307	307	307	307	307	



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	6.1	5.9	5.6	5.6	5.8	5.9	5.5	5.3	5.1	5.1	5.0
90°	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2	10.5	9.9	8.6
92.5°	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8	161.7	199.7	202.9
95°	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4	537.0	548.8	447.8
97.5°	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3	679.5	586.1	399.9
100°	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8	714.2	559.4	356.8
102.5°	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0	693.4	512.2	324.1
105°	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5	626.9	449.1	292.4
107.5°	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6	559.0	405.6	279.0
110°	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1	520.3	385.2	275.0



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5	491.5	373.4	275.0
115°	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4	460.2	360.5	276.9
117.5°	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5	441.5	354.2	281.0
120°	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6	431.1	351.2	284.9
122.5°	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3	422.2	348.7	288.4
125°	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8	410.0	345.6	294.2
127.5°	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0	398.9	344.1	300.8
130°	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6	391.5	343.2	304.8
132.5°	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2	385.6	343.2	309.2
135°	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1	378.4	343.2	315.3
137.5°	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5	372.2	343.9	320.8
140°	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0	369.2	344.4	323.3
142.5°	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6	366.7	344.9	324.8
145°	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1	363.0	344.4	326.5
147.5°	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2	359.1	342.8	327.0
150°	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8	356.2	341.3	327.0
152.5°	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8	352.7	339.3	326.5
155°	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4	346.9	335.7	325.2
157.5°	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0	341.4	332.0	323.6
160°	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0	337.0	329.5	322.1
162.5°	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5	333.0	326.5	320.6
165°	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0	327.0	322.1	318.4
167.5°	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8	321.2	317.7	314.9
170°	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8	317.7	315.3	313.4
172.5°	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4	314.3	312.3	311.4
175°	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6	309.7	309.1	309.1
177.5°	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2	307.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	5.0	4.8	4.8	4.5	4.1	4.6	4.8	4.8	4.7	4.6	4.5
90°	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6	1.3	2.5	3.7
92.5°	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5	9.2	14.3	22.0
95°	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4	21.1	26.0	32.8
97.5°	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9	34.7	38.2	45.0
100°	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3	44.6	47.1	53.9
102.5°	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8	54.5	56.5	63.8
105°	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0	70.0	73.1	79.3
107.5°	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9	87.1	90.1	95.1
110°	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3	98.5	100.9	106.5



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6	109.9	111.9	117.4
115°	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1	126.4	128.3	133.8
117.5°	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0	141.9	143.9	149.4
120°	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9	151.8	154.2	159.8
122.5°	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3	161.7	163.7	169.2
125°	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4	174.7	177.8	183.3
127.5°	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7	185.6	189.6	196.6
130°	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1	192.0	196.9	205.0
132.5°	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1	197.5	203.4	212.5
135°	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2	205.7	213.1	223.0
137.5°	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3	215.2	222.1	232.0
140°	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3	221.1	228.5	238.4
142.5°	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2	227.6	234.5	244.4
145°	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6	237.8	244.1	252.7
147.5°	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5	248.3	253.6	261.7
150°	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0	255.2	259.5	267.6
152.5°	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9	261.7	265.5	272.5
155°	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1	270.1	273.8	280.0
157.5°	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2	278.1	281.1	286.4
160°	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7	283.0	285.6	289.9
162.5°	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1	287.6	290.0	293.8
165°	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9	293.6	295.5	298.6
167.5°	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3	298.7	299.8	301.5
170°	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3	301.7	302.3	303.5
172.5°	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3	303.2	303.7	305.0
175°	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6	305.4	306.0	306.6
177.5°	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7	306.7	306.7	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	4.7	4.9	4.9	5.4	5.1	5.5	5.6	5.6	5.7	5.9	5.9
90°	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2	11.8	12.4	13.6
92.5°	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8	79.7	60.0	50.8
95°	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4	351.2	275.0	223.0
97.5°	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3	597.2	523.0	450.7
100°	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8	731.5	667.7	603.3
102.5°	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0	813.8	783.2	739.6
105°	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5	860.4	887.6	880.8
107.5°	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6	818.9	888.8	921.1
110°	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1	771.7	859.1	911.7



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5	725.2	813.5	875.6
115°	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4	658.5	743.3	810.8
117.5°	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5	612.2	685.3	747.3
120°	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6	586.0	654.1	708.6
122.5°	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3	567.1	627.8	678.9
125°	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8	542.0	595.9	640.5
127.5°	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0	517.9	568.2	610.0
130°	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6	501.1	549.4	589.7
132.5°	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2	485.2	529.1	567.8
135°	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1	460.8	500.5	535.8
137.5°	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5	439.0	472.0	501.9
140°	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0	426.1	454.6	480.6
142.5°	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6	415.3	439.7	462.3
145°	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1	401.4	420.6	437.3
147.5°	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2	389.8	404.6	417.2
150°	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8	383.4	395.1	406.3
152.5°	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8	377.0	387.8	396.4
155°	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4	367.3	376.0	382.8
157.5°	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0	358.1	364.8	370.2
160°	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0	351.2	357.4	361.7
162.5°	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5	345.2	350.5	354.3
165°	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0	336.4	340.1	343.2
167.5°	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8	327.6	330.5	332.7
170°	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8	322.7	324.6	325.8
172.5°	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4	318.2	319.6	320.4
175°	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6	311.6	312.8	312.8
177.5°	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2	308.7	308.7	308.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	6.1	5.9	6.1	6.1	6.1	5.9	6.1	5.9	5.9	5.7	5.6
90°	13.6	13.6	14.3	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2
92.5°	42.9	41.4	40.5	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8
95°	179.0	160.4	155.5	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4
97.5°	412.4	377.7	359.7	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3
100°	560.5	515.9	493.1	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8
102.5°	693.9	662.1	637.2	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0
105°	860.9	840.5	828.1	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5
107.5°	931.2	931.1	927.0	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6
110°	939.6	951.4	955.8	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	916.3	936.5	947.3	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5
115°	859.1	888.8	906.2	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4
117.5°	795.6	826.2	843.5	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5
120°	754.4	784.2	800.9	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6
122.5°	719.8	747.0	763.7	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3
125°	675.2	700.5	714.2	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8
127.5°	641.4	663.8	676.8	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0
130°	620.7	641.1	653.5	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6
132.5°	598.8	619.2	630.7	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2
135°	563.0	583.4	594.6	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1
137.5°	526.4	544.9	555.2	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5
140°	503.6	519.7	528.9	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0
142.5°	481.8	495.4	504.2	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6
145°	452.2	462.7	469.5	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1
147.5°	429.0	437.4	441.4	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2
150°	415.7	423.0	425.6	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8
152.5°	404.3	410.2	412.6	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8
155°	389.0	393.3	395.1	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4
157.5°	375.0	378.6	380.3	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0
160°	366.1	369.2	370.4	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0
162.5°	357.7	360.2	360.5	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5
165°	345.6	346.9	346.9	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0
167.5°	334.0	335.1	334.6	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8
170°	327.0	327.6	327.6	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8
172.5°	320.6	321.7	320.8	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4
175°	312.8	313.4	312.2	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6
177.5°	308.2	308.7	307.2	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	5.6	5.5	5.1	5.4	4.9	4.9	4.7	4.5	4.6	4.7	4.8
90°	10.5	9.9	8.6	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6
92.5°	161.7	199.7	202.9	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5
95°	537.0	548.8	447.8	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4
97.5°	679.5	586.1	399.9	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9
100°	714.2	559.4	356.8	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3
102.5°	693.4	512.2	324.1	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8
105°	626.9	449.1	292.4	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0
107.5°	559.0	405.6	279.0	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9
110°	520.3	385.2	275.0	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	373.4	275.0	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6
115°	460.2	360.5	276.9	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1
117.5°	441.5	354.2	281.0	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0
120°	431.1	351.2	284.9	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9
122.5°	422.2	348.7	288.4	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3
125°	410.0	345.6	294.2	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4
127.5°	398.9	344.1	300.8	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7
130°	391.5	343.2	304.8	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1
132.5°	385.6	343.2	309.2	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1
135°	378.4	343.2	315.3	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2
137.5°	372.2	343.9	320.8	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3
140°	369.2	344.4	323.3	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3
142.5°	366.7	344.9	324.8	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2
145°	363.0	344.4	326.5	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6
147.5°	359.1	342.8	327.0	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5
150°	356.2	341.3	327.0	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0
152.5°	352.7	339.3	326.5	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9
155°	346.9	335.7	325.2	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1
157.5°	341.4	332.0	323.6	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2
160°	337.0	329.5	322.1	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7
162.5°	333.0	326.5	320.6	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1
165°	327.0	322.1	318.4	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9
167.5°	321.2	317.7	314.9	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3
170°	317.7	315.3	313.4	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3
172.5°	314.3	312.3	311.4	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3
175°	309.7	309.1	309.1	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6
177.5°	307.7	307.2	307.2	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	4.8	4.6	4.1	4.5	4.8	4.8	5.0	5.0	5.1	5.1	5.3
90°	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2
92.5°	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8
95°	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4
97.5°	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3
100°	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8
102.5°	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0
105°	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5
107.5°	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6
110°	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5
115°	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4
117.5°	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5
120°	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6
122.5°	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3
125°	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8
127.5°	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0
130°	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6
132.5°	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2
135°	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1
137.5°	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5
140°	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0
142.5°	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6
145°	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1
147.5°	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2
150°	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8
152.5°	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8
155°	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4
157.5°	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0
160°	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0
162.5°	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5
165°	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0
167.5°	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8
170°	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8
172.5°	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4
175°	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6
177.5°	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	5.5	5.9	5.8	5.6	5.6	5.9	6.1
90°	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333504-927

CATALOG NUMBER: S125RDIP-S375D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)