

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333539-927

Luminaire Tested: **S125RDIP-S610D1035U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333539-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1035U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4737.3 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40	35
2	88	80	75	70	80	74	69	64	61	57	54	49	46	44	37	36	34	29
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	55	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.5
10°-20°	206.0	4.3
20°-30°	326.6	6.9
30°-40°	393.9	8.3
40°-50°	351.8	7.4
50°-60°	269.8	5.7
60°-70°	175.3	3.7
70°-80°	85.2	1.8
80°-90°	22.6	0.5
90°-100°	68.1	1.4
100°-110°	201.0	4.2
110°-120°	340.5	7.2
120°-130°	448.1	9.5
130°-140°	502.1	10.6
140°-150°	492.1	10.4
150°-160°	413.3	8.7
160°-170°	274.7	5.8
170°-180°	96.1	2.0
0°-30°	602.9	12.7
0°-40°	996.8	21.0
0°-60°	1618.4	34.2
0°-90°	1901.5	40.1
90°-120°	609.5	12.9
90°-150°	2051.7	43.3
90°-180°	2836.0	59.9
0°-180°	4737.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	19	1	19	1	19	12
95°	68	51	68	51	68	69
105°	196	180	196	180	196	208
115°	344	341	344	341	344	340
125°	501	498	501	498	501	447
135°	649	647	649	647	649	501
145°	787	784	787	784	787	491
155°	897	897	897	897	897	413
165°	973	975	973	975	973	274
175°	1010	1014	1010	1014	1010	96
180°	1016	1016	1016	1016	1016	



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	9.1	8.7	8.4	8.3	8.4	8.8	8.3	7.9	7.8	7.6	7.6
90°	19.0	18.5	17.9	17.4	16.9	16.2	15.3	14.4	13.5	12.7	11.4
92.5°	37.3	36.9	36.5	36.2	35.8	35.0	33.8	32.7	31.5	30.3	28.8
95°	68.0	67.7	67.3	66.9	66.6	65.8	64.6	63.4	62.1	60.9	59.2
97.5°	103.1	102.9	102.7	102.5	102.3	101.6	100.4	99.3	98.2	97.0	94.5
100°	129.7	129.4	129.0	128.7	128.3	127.3	125.7	124.1	122.6	121.0	118.7
102.5°	156.3	155.8	155.3	154.8	154.3	153.2	151.5	149.7	148.1	146.3	145.1
105°	196.1	195.6	195.1	194.6	194.0	193.2	192.2	191.2	190.0	189.0	188.0
107.5°	236.9	237.0	237.0	237.0	237.1	236.9	236.3	235.8	235.3	234.7	233.9
110°	267.3	267.5	267.7	267.8	268.0	267.8	267.3	266.8	266.3	265.7	265.2



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.1	297.4	297.7	298.0	298.3	298.3	298.1	297.9	297.6	297.4	296.7
115°	344.0	344.2	344.4	344.5	344.8	344.9	345.1	345.2	345.5	345.6	345.2
117.5°	389.9	390.6	391.3	392.0	392.7	393.0	392.8	392.7	392.6	392.4	392.1
120°	421.5	422.2	422.9	423.7	424.4	424.7	424.7	424.7	424.7	424.7	424.5
122.5°	453.2	453.8	454.3	454.9	455.4	455.7	455.9	456.1	456.2	456.3	455.9
125°	500.7	500.8	501.0	501.1	501.3	501.6	501.9	502.3	502.6	503.0	502.8
127.5°	546.2	546.5	546.8	547.2	547.6	547.9	548.0	548.2	548.3	548.6	548.3
130°	576.6	576.9	577.3	577.6	578.0	578.2	578.4	578.5	578.8	578.9	578.5
132.5°	605.0	605.5	606.0	606.5	607.0	607.3	607.5	607.7	607.8	608.0	608.1
135°	649.3	650.0	650.7	651.4	652.1	652.4	652.4	652.4	652.4	652.4	652.3
137.5°	692.7	693.6	694.4	695.3	696.2	696.5	696.2	696.1	695.9	695.6	695.3
140°	720.5	721.4	722.2	723.1	724.0	724.3	723.9	723.6	723.2	722.9	722.3
142.5°	747.0	748.0	748.8	749.7	750.6	750.9	750.7	750.5	750.3	750.0	749.4
145°	787.0	787.4	788.0	788.5	789.0	789.3	789.3	789.3	789.3	789.3	788.8
147.5°	820.9	822.1	823.3	824.5	825.7	826.1	825.7	825.2	824.8	824.4	823.9
150°	846.2	846.6	846.9	847.3	847.6	847.8	847.8	847.8	847.8	847.8	847.1
152.5°	867.1	867.8	868.4	869.0	869.7	869.7	869.3	868.9	868.5	868.1	867.8
155°	896.8	897.7	898.6	899.5	900.4	900.5	899.8	899.0	898.3	897.6	897.5
157.5°	921.7	922.8	924.0	925.2	926.3	926.5	925.8	925.1	924.5	923.8	923.6
160°	938.7	939.7	940.6	941.4	942.3	942.4	941.7	941.0	940.2	939.5	939.4
162.5°	953.3	954.3	955.4	956.4	957.4	957.5	956.6	955.8	955.0	954.1	954.1
165°	972.8	973.8	974.9	976.0	977.0	977.2	976.4	975.7	975.1	974.4	974.1
167.5°	988.2	989.4	990.5	991.6	992.6	992.7	991.6	990.5	989.5	988.4	988.4
170°	996.5	997.8	998.9	1000.2	1001.4	1001.5	1000.4	999.4	998.4	997.3	997.3
172.5°	1003.5	1004.6	1005.7	1006.7	1007.8	1007.8	1006.8	1005.8	1004.6	1003.6	1003.6
175°	1010.0	1011.1	1012.4	1013.7	1014.9	1014.9	1013.9	1012.9	1011.8	1010.7	1010.7
177.5°	1013.8	1014.7	1015.7	1016.7	1017.7	1017.7	1016.9	1016.1	1015.3	1014.4	1014.5
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	7.6	7.4	7.3	7.1	6.6	7.4	7.9	7.8	7.7	7.4	7.3
90°	10.2	9.0	7.8	6.4	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	27.3	25.8	24.3	23.1	22.1	21.1	20.1	19.2	20.1	21.1	22.1
95°	57.4	55.6	53.9	52.8	52.4	52.1	51.7	51.4	51.7	52.1	52.4
97.5°	92.1	89.7	87.3	86.0	85.9	85.7	85.6	85.4	85.6	85.7	85.9
100°	116.5	114.2	111.9	110.7	110.7	110.7	110.7	110.7	110.7	110.7	110.7
102.5°	144.0	142.8	141.6	140.8	140.1	139.3	138.6	137.9	138.6	139.3	140.1
105°	186.9	185.8	184.8	183.9	183.0	182.0	181.2	180.3	181.2	182.0	183.0
107.5°	233.1	232.3	231.5	230.7	229.8	228.9	228.0	227.1	228.0	228.9	229.8
110°	264.7	264.1	263.6	262.9	262.1	261.2	260.3	259.4	260.3	261.2	262.1



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	296.0	295.4	294.7	294.1	293.7	293.2	292.8	292.3	292.8	293.2	293.7
115°	344.9	344.5	344.2	343.6	343.0	342.3	341.6	340.9	341.6	342.3	343.0
117.5°	391.8	391.5	391.2	390.9	390.5	390.2	389.9	389.6	389.9	390.2	390.5
120°	424.4	424.1	424.0	423.5	422.6	421.7	420.8	419.9	420.8	421.7	422.6
122.5°	455.4	455.0	454.5	454.2	453.8	453.5	453.2	452.9	453.2	453.5	453.8
125°	502.6	502.5	502.3	501.7	500.7	499.6	498.5	497.5	498.5	499.6	500.7
127.5°	548.1	548.0	547.7	547.3	546.7	546.1	545.5	544.9	545.5	546.1	546.7
130°	578.2	577.9	577.5	576.9	576.0	575.1	574.3	573.4	574.3	575.1	576.0
132.5°	608.2	608.2	608.3	607.6	606.2	604.8	603.3	601.8	603.3	604.8	606.2
135°	652.1	652.0	651.8	651.2	650.1	649.0	648.0	647.0	648.0	649.0	650.1
137.5°	694.9	694.5	694.1	693.4	692.4	691.3	690.3	689.4	690.3	691.3	692.4
140°	721.8	721.3	720.7	720.0	719.1	718.3	717.4	716.5	717.4	718.3	719.1
142.5°	748.8	748.1	747.4	746.7	745.9	745.2	744.5	743.7	744.5	745.2	745.9
145°	788.2	787.7	787.2	786.6	785.8	785.1	784.5	783.8	784.5	785.1	785.8
147.5°	823.6	823.2	822.8	822.3	822.0	821.6	821.2	820.8	821.2	821.6	822.0
150°	846.4	845.7	845.0	844.8	844.9	845.1	845.3	845.4	845.3	845.1	844.9
152.5°	867.5	867.2	867.0	866.6	866.4	866.2	865.9	865.7	865.9	866.2	866.4
155°	897.3	897.1	896.9	896.8	896.8	896.8	896.8	896.8	896.8	896.8	896.8
157.5°	923.4	923.2	923.1	923.1	923.5	923.9	924.3	924.7	924.3	923.9	923.5
160°	939.2	939.1	938.9	939.1	939.5	940.1	940.6	941.1	940.6	940.1	939.5
162.5°	954.0	954.0	953.9	954.2	954.5	954.9	955.3	955.7	955.3	954.9	954.5
165°	974.0	973.8	973.7	973.8	974.1	974.5	974.8	975.2	974.8	974.5	974.1
167.5°	988.4	988.4	988.4	988.8	989.5	990.2	990.9	991.6	990.9	990.2	989.5
170°	997.3	997.3	997.3	997.7	998.4	999.0	999.7	1000.4	999.7	999.0	998.4
172.5°	1003.6	1003.6	1003.6	1004.0	1004.6	1005.4	1006.1	1006.8	1006.1	1005.4	1004.6
175°	1010.7	1010.7	1010.7	1011.1	1011.8	1012.5	1013.2	1013.9	1013.2	1012.5	1011.8
177.5°	1014.6	1014.8	1014.9	1015.3	1015.8	1016.4	1017.0	1017.6	1017.0	1016.4	1015.8
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	7.3	7.5	7.6	8.3	7.8	8.3	8.5	8.4	8.6	8.8	8.6
90°	6.4	7.8	9.0	10.2	11.4	12.7	13.5	14.4	15.3	16.2	16.9
92.5°	23.1	24.3	25.8	27.3	28.8	30.3	31.5	32.7	33.8	35.0	35.8
95°	52.8	53.9	55.6	57.4	59.2	60.9	62.1	63.4	64.6	65.8	66.6
97.5°	86.0	87.3	89.7	92.1	94.5	97.0	98.2	99.3	100.4	101.6	102.3
100°	110.7	111.9	114.2	116.5	118.7	121.0	122.6	124.1	125.7	127.3	128.3
102.5°	140.8	141.6	142.8	144.0	145.1	146.3	148.1	149.7	151.5	153.2	154.3
105°	183.9	184.8	185.8	186.9	188.0	189.0	190.0	191.2	192.2	193.2	194.0
107.5°	230.7	231.5	232.3	233.1	233.9	234.7	235.3	235.8	236.3	236.9	237.1
110°	262.9	263.6	264.1	264.7	265.2	265.7	266.3	266.8	267.3	267.8	268.0



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	294.1	294.7	295.4	296.0	296.7	297.4	297.6	297.9	298.1	298.3	298.3
115°	343.6	344.2	344.5	344.9	345.2	345.6	345.5	345.2	345.1	344.9	344.8
117.5°	390.9	391.2	391.5	391.8	392.1	392.4	392.6	392.7	392.8	393.0	392.7
120°	423.5	424.0	424.1	424.4	424.5	424.7	424.7	424.7	424.7	424.7	424.4
122.5°	454.2	454.5	455.0	455.4	455.9	456.3	456.2	456.1	455.9	455.7	455.4
125°	501.7	502.3	502.5	502.6	502.8	503.0	502.6	502.3	501.9	501.6	501.3
127.5°	547.3	547.7	548.0	548.1	548.3	548.6	548.3	548.2	548.0	547.9	547.6
130°	576.9	577.5	577.9	578.2	578.5	578.9	578.8	578.5	578.4	578.2	578.0
132.5°	607.6	608.3	608.2	608.2	608.1	608.0	607.8	607.7	607.5	607.3	607.0
135°	651.2	651.8	652.0	652.1	652.3	652.4	652.4	652.4	652.4	652.4	652.1
137.5°	693.4	694.1	694.5	694.9	695.3	695.6	695.9	696.1	696.2	696.5	696.2
140°	720.0	720.7	721.3	721.8	722.3	722.9	723.2	723.6	723.9	724.3	724.0
142.5°	746.7	747.4	748.1	748.8	749.4	750.0	750.3	750.5	750.7	750.9	750.6
145°	786.6	787.2	787.7	788.2	788.8	789.3	789.3	789.3	789.3	789.3	789.0
147.5°	822.3	822.8	823.2	823.6	823.9	824.4	824.8	825.2	825.7	826.1	825.7
150°	844.8	845.0	845.7	846.4	847.1	847.8	847.8	847.8	847.8	847.8	847.6
152.5°	866.6	867.0	867.2	867.5	867.8	868.1	868.5	868.9	869.3	869.7	869.7
155°	896.8	896.9	897.1	897.3	897.5	897.6	898.3	899.0	899.8	900.5	900.4
157.5°	923.1	923.1	923.2	923.4	923.6	923.8	924.5	925.1	925.8	926.5	926.3
160°	939.1	938.9	939.1	939.2	939.4	939.5	940.2	941.0	941.7	942.4	942.3
162.5°	954.2	953.9	954.0	954.0	954.1	954.1	955.0	955.8	956.6	957.5	957.4
165°	973.8	973.7	973.8	974.0	974.1	974.4	975.1	975.7	976.4	977.2	977.0
167.5°	988.8	988.4	988.4	988.4	988.4	988.4	989.5	990.5	991.6	992.7	992.6
170°	997.7	997.3	997.3	997.3	997.3	997.3	998.4	999.4	1000.4	1001.5	1001.4
172.5°	1004.0	1003.6	1003.6	1003.6	1003.6	1003.6	1004.6	1005.8	1006.8	1007.8	1007.8
175°	1011.1	1010.7	1010.7	1010.7	1010.7	1010.7	1011.8	1012.9	1013.9	1014.9	1014.9
177.5°	1015.3	1014.9	1014.8	1014.6	1014.5	1014.4	1015.3	1016.1	1016.9	1017.7	1017.7
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	9.0	8.9	9.0	9.1	9.0	8.9	9.0	8.6	8.8	8.6	8.4
90°	17.4	17.9	18.5	19.0	18.5	17.9	17.4	16.9	16.2	15.3	14.4
92.5°	36.2	36.5	36.9	37.3	36.9	36.5	36.2	35.8	35.0	33.8	32.7
95°	66.9	67.3	67.7	68.0	67.7	67.3	66.9	66.6	65.8	64.6	63.4
97.5°	102.5	102.7	102.9	103.1	102.9	102.7	102.5	102.3	101.6	100.4	99.3
100°	128.7	129.0	129.4	129.7	129.4	129.0	128.7	128.3	127.3	125.7	124.1
102.5°	154.8	155.3	155.8	156.3	155.8	155.3	154.8	154.3	153.2	151.5	149.7
105°	194.6	195.1	195.6	196.1	195.6	195.1	194.6	194.0	193.2	192.2	191.2
107.5°	237.0	237.0	237.0	236.9	237.0	237.0	237.0	237.1	236.9	236.3	235.8
110°	267.8	267.7	267.5	267.3	267.5	267.7	267.8	268.0	267.8	267.3	266.8



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	298.0	297.7	297.4	297.1	297.4	297.7	298.0	298.3	298.3	298.1	297.9
115°	344.5	344.4	344.2	344.0	344.2	344.4	344.5	344.8	344.9	345.1	345.2
117.5°	392.0	391.3	390.6	389.9	390.6	391.3	392.0	392.7	393.0	392.8	392.7
120°	423.7	422.9	422.2	421.5	422.2	422.9	423.7	424.4	424.7	424.7	424.7
122.5°	454.9	454.3	453.8	453.2	453.8	454.3	454.9	455.4	455.7	455.9	456.1
125°	501.1	501.0	500.8	500.7	500.8	501.0	501.1	501.3	501.6	501.9	502.3
127.5°	547.2	546.8	546.5	546.2	546.5	546.8	547.2	547.6	547.9	548.0	548.2
130°	577.6	577.3	576.9	576.6	576.9	577.3	577.6	578.0	578.2	578.4	578.5
132.5°	606.5	606.0	605.5	605.0	605.5	606.0	606.5	607.0	607.3	607.5	607.7
135°	651.4	650.7	650.0	649.3	650.0	650.7	651.4	652.1	652.4	652.4	652.4
137.5°	695.3	694.4	693.6	692.7	693.6	694.4	695.3	696.2	696.5	696.2	696.1
140°	723.1	722.2	721.4	720.5	721.4	722.2	723.1	724.0	724.3	723.9	723.6
142.5°	749.7	748.8	748.0	747.0	748.0	748.8	749.7	750.6	750.9	750.7	750.5
145°	788.5	788.0	787.4	787.0	787.4	788.0	788.5	789.0	789.3	789.3	789.3
147.5°	824.5	823.3	822.1	820.9	822.1	823.3	824.5	825.7	826.1	825.7	825.2
150°	847.3	846.9	846.6	846.2	846.6	846.9	847.3	847.6	847.8	847.8	847.8
152.5°	869.0	868.4	867.8	867.1	867.8	868.4	869.0	869.7	869.7	869.3	868.9
155°	899.5	898.6	897.7	896.8	897.7	898.6	899.5	900.4	900.5	899.8	899.0
157.5°	925.2	924.0	922.8	921.7	922.8	924.0	925.2	926.3	926.5	925.8	925.1
160°	941.4	940.6	939.7	938.7	939.7	940.6	941.4	942.3	942.4	941.7	941.0
162.5°	956.4	955.4	954.3	953.3	954.3	955.4	956.4	957.4	957.5	956.6	955.8
165°	976.0	974.9	973.8	972.8	973.8	974.9	976.0	977.0	977.2	976.4	975.7
167.5°	991.6	990.5	989.4	988.2	989.4	990.5	991.6	992.6	992.7	991.6	990.5
170°	1000.2	998.9	997.8	996.5	997.8	998.9	1000.2	1001.4	1001.5	1000.4	999.4
172.5°	1006.7	1005.7	1004.6	1003.5	1004.6	1005.7	1006.7	1007.8	1007.8	1006.8	1005.8
175°	1013.7	1012.4	1011.1	1010.0	1011.1	1012.4	1013.7	1014.9	1014.9	1013.9	1012.9
177.5°	1016.7	1015.7	1014.7	1013.8	1014.7	1015.7	1016.7	1017.7	1017.7	1016.9	1016.1
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	8.5	8.3	7.8	8.3	7.6	7.5	7.3	7.3	7.4	7.7	7.8
90°	13.5	12.7	11.4	10.2	9.0	7.8	6.4	5.0	3.6	2.2	0.8
92.5°	31.5	30.3	28.8	27.3	25.8	24.3	23.1	22.1	21.1	20.1	19.2
95°	62.1	60.9	59.2	57.4	55.6	53.9	52.8	52.4	52.1	51.7	51.4
97.5°	98.2	97.0	94.5	92.1	89.7	87.3	86.0	85.9	85.7	85.6	85.4
100°	122.6	121.0	118.7	116.5	114.2	111.9	110.7	110.7	110.7	110.7	110.7
102.5°	148.1	146.3	145.1	144.0	142.8	141.6	140.8	140.1	139.3	138.6	137.9
105°	190.0	189.0	188.0	186.9	185.8	184.8	183.9	183.0	182.0	181.2	180.3
107.5°	235.3	234.7	233.9	233.1	232.3	231.5	230.7	229.8	228.9	228.0	227.1
110°	266.3	265.7	265.2	264.7	264.1	263.6	262.9	262.1	261.2	260.3	259.4



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	297.6	297.4	296.7	296.0	295.4	294.7	294.1	293.7	293.2	292.8	292.3
115°	345.5	345.6	345.2	344.9	344.5	344.2	343.6	343.0	342.3	341.6	340.9
117.5°	392.6	392.4	392.1	391.8	391.5	391.2	390.9	390.5	390.2	389.9	389.6
120°	424.7	424.7	424.5	424.4	424.1	424.0	423.5	422.6	421.7	420.8	419.9
122.5°	456.2	456.3	455.9	455.4	455.0	454.5	454.2	453.8	453.5	453.2	452.9
125°	502.6	503.0	502.8	502.6	502.5	502.3	501.7	500.7	499.6	498.5	497.5
127.5°	548.3	548.6	548.3	548.1	548.0	547.7	547.3	546.7	546.1	545.5	544.9
130°	578.8	578.9	578.5	578.2	577.9	577.5	576.9	576.0	575.1	574.3	573.4
132.5°	607.8	608.0	608.1	608.2	608.2	608.3	607.6	606.2	604.8	603.3	601.8
135°	652.4	652.4	652.3	652.1	652.0	651.8	651.2	650.1	649.0	648.0	647.0
137.5°	695.9	695.6	695.3	694.9	694.5	694.1	693.4	692.4	691.3	690.3	689.4
140°	723.2	722.9	722.3	721.8	721.3	720.7	720.0	719.1	718.3	717.4	716.5
142.5°	750.3	750.0	749.4	748.8	748.1	747.4	746.7	745.9	745.2	744.5	743.7
145°	789.3	789.3	788.8	788.2	787.7	787.2	786.6	785.8	785.1	784.5	783.8
147.5°	824.8	824.4	823.9	823.6	823.2	822.8	822.3	822.0	821.6	821.2	820.8
150°	847.8	847.8	847.1	846.4	845.7	845.0	844.8	844.9	845.1	845.3	845.4
152.5°	868.5	868.1	867.8	867.5	867.2	867.0	866.6	866.4	866.2	865.9	865.7
155°	898.3	897.6	897.5	897.3	897.1	896.9	896.8	896.8	896.8	896.8	896.8
157.5°	924.5	923.8	923.6	923.4	923.2	923.1	923.1	923.5	923.9	924.3	924.7
160°	940.2	939.5	939.4	939.2	939.1	938.9	939.1	939.5	940.1	940.6	941.1
162.5°	955.0	954.1	954.1	954.0	954.0	953.9	954.2	954.5	954.9	955.3	955.7
165°	975.1	974.4	974.1	974.0	973.8	973.7	973.8	974.1	974.5	974.8	975.2
167.5°	989.5	988.4	988.4	988.4	988.4	988.4	988.8	989.5	990.2	990.9	991.6
170°	998.4	997.3	997.3	997.3	997.3	997.3	997.7	998.4	999.0	999.7	1000.4
172.5°	1004.6	1003.6	1003.6	1003.6	1003.6	1003.6	1004.0	1004.6	1005.4	1006.1	1006.8
175°	1011.8	1010.7	1010.7	1010.7	1010.7	1010.7	1011.1	1011.8	1012.5	1013.2	1013.9
177.5°	1015.3	1014.4	1014.5	1014.6	1014.8	1014.9	1015.3	1015.8	1016.4	1017.0	1017.6
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.9	7.4	6.6	7.1	7.3	7.4	7.6	7.6	7.6	7.8	7.9
90°	2.2	3.6	5.0	6.4	7.8	9.0	10.2	11.4	12.7	13.5	14.4
92.5°	20.1	21.1	22.1	23.1	24.3	25.8	27.3	28.8	30.3	31.5	32.7
95°	51.7	52.1	52.4	52.8	53.9	55.6	57.4	59.2	60.9	62.1	63.4
97.5°	85.6	85.7	85.9	86.0	87.3	89.7	92.1	94.5	97.0	98.2	99.3
100°	110.7	110.7	110.7	110.7	111.9	114.2	116.5	118.7	121.0	122.6	124.1
102.5°	138.6	139.3	140.1	140.8	141.6	142.8	144.0	145.1	146.3	148.1	149.7
105°	181.2	182.0	183.0	183.9	184.8	185.8	186.9	188.0	189.0	190.0	191.2
107.5°	228.0	228.9	229.8	230.7	231.5	232.3	233.1	233.9	234.7	235.3	235.8
110°	260.3	261.2	262.1	262.9	263.6	264.1	264.7	265.2	265.7	266.3	266.8



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	292.8	293.2	293.7	294.1	294.7	295.4	296.0	296.7	297.4	297.6	297.9
115°	341.6	342.3	343.0	343.6	344.2	344.5	344.9	345.2	345.6	345.5	345.2
117.5°	389.9	390.2	390.5	390.9	391.2	391.5	391.8	392.1	392.4	392.6	392.7
120°	420.8	421.7	422.6	423.5	424.0	424.1	424.4	424.5	424.7	424.7	424.7
122.5°	453.2	453.5	453.8	454.2	454.5	455.0	455.4	455.9	456.3	456.2	456.1
125°	498.5	499.6	500.7	501.7	502.3	502.5	502.6	502.8	503.0	502.6	502.3
127.5°	545.5	546.1	546.7	547.3	547.7	548.0	548.1	548.3	548.6	548.3	548.2
130°	574.3	575.1	576.0	576.9	577.5	577.9	578.2	578.5	578.9	578.8	578.5
132.5°	603.3	604.8	606.2	607.6	608.3	608.2	608.2	608.1	608.0	607.8	607.7
135°	648.0	649.0	650.1	651.2	651.8	652.0	652.1	652.3	652.4	652.4	652.4
137.5°	690.3	691.3	692.4	693.4	694.1	694.5	694.9	695.3	695.6	695.9	696.1
140°	717.4	718.3	719.1	720.0	720.7	721.3	721.8	722.3	722.9	723.2	723.6
142.5°	744.5	745.2	745.9	746.7	747.4	748.1	748.8	749.4	750.0	750.3	750.5
145°	784.5	785.1	785.8	786.6	787.2	787.7	788.2	788.8	789.3	789.3	789.3
147.5°	821.2	821.6	822.0	822.3	822.8	823.2	823.6	823.9	824.4	824.8	825.2
150°	845.3	845.1	844.9	844.8	845.0	845.7	846.4	847.1	847.8	847.8	847.8
152.5°	865.9	866.2	866.4	866.6	867.0	867.2	867.5	867.8	868.1	868.5	868.9
155°	896.8	896.8	896.8	896.8	896.9	897.1	897.3	897.5	897.6	898.3	899.0
157.5°	924.3	923.9	923.5	923.1	923.1	923.2	923.4	923.6	923.8	924.5	925.1
160°	940.6	940.1	939.5	939.1	938.9	939.1	939.2	939.4	939.5	940.2	941.0
162.5°	955.3	954.9	954.5	954.2	953.9	954.0	954.0	954.1	954.1	955.0	955.8
165°	974.8	974.5	974.1	973.8	973.7	973.8	974.0	974.1	974.4	975.1	975.7
167.5°	990.9	990.2	989.5	988.8	988.4	988.4	988.4	988.4	988.4	989.5	990.5
170°	999.7	999.0	998.4	997.7	997.3	997.3	997.3	997.3	997.3	998.4	999.4
172.5°	1006.1	1005.4	1004.6	1004.0	1003.6	1003.6	1003.6	1003.6	1003.6	1004.6	1005.8
175°	1013.2	1012.5	1011.8	1011.1	1010.7	1010.7	1010.7	1010.7	1010.7	1011.8	1012.9
177.5°	1017.0	1016.4	1015.8	1015.3	1014.9	1014.8	1014.6	1014.5	1014.4	1015.3	1016.1
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	8.3	8.8	8.4	8.3	8.4	8.7	9.1
90°	15.3	16.2	16.9	17.4	17.9	18.5	19.0
92.5°	33.8	35.0	35.8	36.2	36.5	36.9	37.3
95°	64.6	65.8	66.6	66.9	67.3	67.7	68.0
97.5°	100.4	101.6	102.3	102.5	102.7	102.9	103.1
100°	125.7	127.3	128.3	128.7	129.0	129.4	129.7
102.5°	151.5	153.2	154.3	154.8	155.3	155.8	156.3
105°	192.2	193.2	194.0	194.6	195.1	195.6	196.1
107.5°	236.3	236.9	237.1	237.0	237.0	237.0	236.9
110°	267.3	267.8	268.0	267.8	267.7	267.5	267.3



TEST NUMBER: P333539-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	298.1	298.3	298.3	298.0	297.7	297.4	297.1
115°	345.1	344.9	344.8	344.5	344.4	344.2	344.0
117.5°	392.8	393.0	392.7	392.0	391.3	390.6	389.9
120°	424.7	424.7	424.4	423.7	422.9	422.2	421.5
122.5°	455.9	455.7	455.4	454.9	454.3	453.8	453.2
125°	501.9	501.6	501.3	501.1	501.0	500.8	500.7
127.5°	548.0	547.9	547.6	547.2	546.8	546.5	546.2
130°	578.4	578.2	578.0	577.6	577.3	576.9	576.6
132.5°	607.5	607.3	607.0	606.5	606.0	605.5	605.0
135°	652.4	652.4	652.1	651.4	650.7	650.0	649.3
137.5°	696.2	696.5	696.2	695.3	694.4	693.6	692.7
140°	723.9	724.3	724.0	723.1	722.2	721.4	720.5
142.5°	750.7	750.9	750.6	749.7	748.8	748.0	747.0
145°	789.3	789.3	789.0	788.5	788.0	787.4	787.0
147.5°	825.7	826.1	825.7	824.5	823.3	822.1	820.9
150°	847.8	847.8	847.6	847.3	846.9	846.6	846.2
152.5°	869.3	869.7	869.7	869.0	868.4	867.8	867.1
155°	899.8	900.5	900.4	899.5	898.6	897.7	896.8
157.5°	925.8	926.5	926.3	925.2	924.0	922.8	921.7
160°	941.7	942.4	942.3	941.4	940.6	939.7	938.7
162.5°	956.6	957.5	957.4	956.4	955.4	954.3	953.3
165°	976.4	977.2	977.0	976.0	974.9	973.8	972.8
167.5°	991.6	992.7	992.6	991.6	990.5	989.4	988.2
170°	1000.4	1001.5	1001.4	1000.2	998.9	997.8	996.5
172.5°	1006.8	1007.8	1007.8	1006.7	1005.7	1004.6	1003.5
175°	1013.9	1014.9	1014.9	1013.7	1012.4	1011.1	1010.0
177.5°	1016.9	1017.7	1017.7	1016.7	1015.7	1014.7	1013.8
180°	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3	1016.3

(END OF REPORT)