

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333540-927

Luminaire Tested: **S125RDIP-S610D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333540-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1035U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4842.9 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34
2	87	80	74	70	79	73	68	64	60	57	54	48	46	43	37	35	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.5
10°-20°	206.0	4.3
20°-30°	326.6	6.7
30°-40°	393.9	8.1
40°-50°	351.8	7.3
50°-60°	269.8	5.6
60°-70°	175.3	3.6
70°-80°	85.2	1.8
80°-90°	22.5	0.5
90°-100°	284.3	5.9
100°-110°	611.2	12.6
110°-120°	573.6	11.8
120°-130°	464.9	9.6
130°-140°	373.0	7.7
140°-150°	281.5	5.8
150°-160°	198.2	4.1
160°-170°	116.8	2.4
170°-180°	38.0	0.8
0°-30°	602.9	12.5
0°-40°	996.8	20.6
0°-60°	1618.4	33.4
0°-90°	1901.4	39.3
90°-120°	1469.1	30.3
90°-150°	2588.5	53.4
90°-180°	2941.0	60.7
0°-180°	4842.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	18	1	18	1	18	13
95°	186	26	186	26	186	263
105°	1048	89	1048	89	1048	1042
115°	1167	160	1167	160	1167	1140
125°	920	221	920	221	920	832
135°	764	259	764	259	764	592
145°	603	302	603	302	603	383
155°	505	345	505	345	505	236
165°	443	376	443	376	443	127
175°	398	391	398	391	398	39
180°	392	392	392	392	392	



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	9.0	8.7	8.3	8.3	8.6	8.7	8.3	7.9	7.8	7.6	7.5
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3	13.5	12.7	11.1
92.5°	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1	206.4	254.9	259.0
95°	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6	685.6	700.7	571.8
97.5°	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8	867.5	748.3	510.6
100°	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7	911.8	714.1	455.5
102.5°	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1	885.3	654.0	413.8
105°	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1	800.3	573.3	373.3
107.5°	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9	713.6	517.8	356.2
110°	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1	664.2	491.9	351.1



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2	627.6	476.7	351.1
115°	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0	587.6	460.3	353.5
117.5°	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0	563.7	452.2	358.7
120°	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2	550.4	448.4	363.8
122.5°	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1	539.0	445.2	368.2
125°	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3	523.6	441.2	375.7
127.5°	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0	509.3	439.3	384.0
130°	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2	499.8	438.1	389.1
132.5°	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4	492.2	438.1	394.7
135°	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8	483.2	438.1	402.5
137.5°	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4	475.2	439.0	409.6
140°	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9	471.3	439.7	412.8
142.5°	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7	468.2	440.3	414.7
145°	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9	463.4	439.7	416.8
147.5°	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8	458.5	437.6	417.6
150°	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1	454.7	435.7	417.6
152.5°	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8	450.3	433.2	416.9
155°	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3	442.8	428.6	415.2
157.5°	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8	435.9	423.9	413.1
160°	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5	430.2	420.7	411.2
162.5°	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6	425.2	416.9	409.3
165°	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9	417.6	411.2	406.5
167.5°	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7	410.1	405.7	402.0
170°	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6	405.7	402.5	400.1
172.5°	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9	401.2	398.7	397.6
175°	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8	395.4	394.6	394.6
177.5°	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5	392.8	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	7.6	7.3	7.4	7.1	6.5	7.4	7.8	7.8	7.5	7.4	7.2
90°	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8	1.6	3.2	4.8
92.5°	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7	11.7	18.4	28.1
95°	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1	26.9	33.2	41.9
97.5°	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3	44.3	48.7	57.4
100°	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4	57.0	60.1	68.8
102.5°	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7	69.6	72.1	81.4
105°	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4	89.4	93.3	101.2
107.5°	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6	111.2	114.9	121.4
110°	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1	125.7	128.9	136.0



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7	140.3	142.8	150.0
115°	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8	161.3	163.7	170.8
117.5°	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7	181.1	183.6	190.8
120°	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4	193.8	196.9	204.1
122.5°	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7	206.4	208.9	216.0
125°	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4	223.0	227.0	234.1
127.5°	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6	236.9	242.0	251.0
130°	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8	245.2	251.5	261.7
132.5°	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1	252.1	259.7	271.2
135°	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4	262.5	272.0	284.7
137.5°	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4	274.7	283.6	296.3
140°	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0	282.3	291.8	304.4
142.5°	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8	290.6	299.4	312.0
145°	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1	303.6	311.6	322.7
147.5°	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0	317.0	323.8	334.1
150°	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2	325.8	331.4	341.7
152.5°	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1	334.1	339.0	347.9
155°	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8	344.8	349.5	357.4
157.5°	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2	355.1	358.9	365.7
160°	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2	361.4	364.6	370.1
162.5°	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9	367.1	370.3	375.2
165°	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4	374.9	377.2	381.2
167.5°	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1	381.4	382.8	385.0
170°	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0	385.2	386.0	387.5
172.5°	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5	387.1	387.9	389.4
175°	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4	389.8	390.6	391.4
177.5°	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8	391.6	391.6	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	7.3	7.6	7.5	8.3	7.8	8.3	8.5	8.4	8.6	8.7	8.8
90°	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3	15.1	15.8	17.4
92.5°	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1	101.7	76.5	64.9
95°	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6	448.4	351.1	284.7
97.5°	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8	762.5	667.7	575.4
100°	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7	934.0	852.5	770.2
102.5°	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1	1038.9	999.9	944.2
105°	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1	1098.4	1133.2	1124.5
107.5°	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9	1045.4	1134.8	1176.1
110°	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1	985.3	1096.9	1164.1



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2	925.9	1038.6	1117.9
115°	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0	840.7	949.0	1035.1
117.5°	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0	781.6	875.0	954.0
120°	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2	748.1	835.1	904.7
122.5°	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1	724.1	801.5	866.7
125°	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3	692.0	760.7	817.7
127.5°	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0	661.3	725.5	778.8
130°	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2	639.8	701.5	752.9
132.5°	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4	619.5	675.5	725.0
135°	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8	588.4	639.0	684.0
137.5°	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4	560.5	602.6	640.9
140°	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9	544.1	580.4	613.7
142.5°	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7	530.1	561.5	590.3
145°	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9	512.5	536.9	558.3
147.5°	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8	497.7	516.6	532.7
150°	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1	489.5	504.5	518.8
152.5°	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8	481.3	495.0	506.1
155°	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3	469.0	480.1	488.7
157.5°	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8	457.2	465.8	472.6
160°	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5	448.4	456.3	461.8
162.5°	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6	440.8	447.4	452.3
165°	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9	429.4	434.2	438.1
167.5°	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7	418.4	422.0	424.8
170°	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6	412.0	414.4	416.0
172.5°	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9	406.3	408.1	409.0
175°	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8	397.8	399.3	399.3
177.5°	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5	394.1	394.1	394.1
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	9.0	8.8	9.0	9.0	9.0	8.8	9.0	8.8	8.7	8.6	8.4
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3
92.5°	54.7	52.8	51.7	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1
95°	228.5	204.9	198.5	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6
97.5°	526.6	482.2	459.3	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8
100°	715.7	658.8	629.5	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7
102.5°	885.9	845.4	813.6	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1
105°	1099.2	1073.2	1057.3	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1
107.5°	1188.9	1188.7	1183.5	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9
110°	1199.7	1214.7	1220.2	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1169.9	1195.7	1209.5	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2
115°	1096.9	1134.8	1157.0	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0
117.5°	1015.7	1054.9	1076.9	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0
120°	963.2	1001.2	1022.5	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2
122.5°	918.9	953.7	975.1	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1
125°	862.0	894.4	911.8	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3
127.5°	819.0	847.6	864.0	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0
130°	792.4	818.5	834.3	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2
132.5°	764.5	790.7	805.2	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4
135°	718.8	745.0	759.1	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8
137.5°	672.0	695.8	708.9	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4
140°	642.9	663.5	675.3	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9
142.5°	615.1	632.5	643.7	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7
145°	577.3	590.7	599.4	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9
147.5°	547.7	558.5	563.6	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8
150°	530.6	540.1	543.3	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1
152.5°	516.1	523.7	526.8	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8
155°	496.6	502.2	504.5	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3
157.5°	478.8	483.3	485.5	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8
160°	467.4	471.3	472.9	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5
162.5°	456.6	459.9	460.3	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6
165°	441.2	442.8	442.8	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9
167.5°	426.4	427.9	427.2	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7
170°	417.6	418.4	418.4	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6
172.5°	409.3	410.7	409.5	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9
175°	399.3	400.1	398.5	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8
177.5°	393.5	394.1	392.2	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	8.5	8.3	7.8	8.3	7.5	7.6	7.3	7.2	7.4	7.5	7.8
90°	13.5	12.7	11.1	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8
92.5°	206.4	254.9	259.0	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7
95°	685.6	700.7	571.8	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1
97.5°	867.5	748.3	510.6	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3
100°	911.8	714.1	455.5	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4
102.5°	885.3	654.0	413.8	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7
105°	800.3	573.3	373.3	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4
107.5°	713.6	517.8	356.2	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6
110°	664.2	491.9	351.1	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	627.6	476.7	351.1	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7
115°	587.6	460.3	353.5	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8
117.5°	563.7	452.2	358.7	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7
120°	550.4	448.4	363.8	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4
122.5°	539.0	445.2	368.2	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7
125°	523.6	441.2	375.7	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4
127.5°	509.3	439.3	384.0	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6
130°	499.8	438.1	389.1	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8
132.5°	492.2	438.1	394.7	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1
135°	483.2	438.1	402.5	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4
137.5°	475.2	439.0	409.6	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4
140°	471.3	439.7	412.8	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0
142.5°	468.2	440.3	414.7	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8
145°	463.4	439.7	416.8	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1
147.5°	458.5	437.6	417.6	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0
150°	454.7	435.7	417.6	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2
152.5°	450.3	433.2	416.9	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1
155°	442.8	428.6	415.2	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8
157.5°	435.9	423.9	413.1	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2
160°	430.2	420.7	411.2	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2
162.5°	425.2	416.9	409.3	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9
165°	417.6	411.2	406.5	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4
167.5°	410.1	405.7	402.0	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1
170°	405.7	402.5	400.1	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0
172.5°	401.2	398.7	397.6	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5
175°	395.4	394.6	394.6	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4
177.5°	392.8	392.2	392.2	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.8	7.4	6.5	7.1	7.4	7.3	7.6	7.5	7.6	7.8	7.9
90°	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3
92.5°	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1
95°	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6
97.5°	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8
100°	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7
102.5°	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1
105°	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1
107.5°	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9
110°	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2
115°	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0
117.5°	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0
120°	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2
122.5°	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1
125°	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3
127.5°	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0
130°	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2
132.5°	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4
135°	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8
137.5°	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4
140°	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9
142.5°	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7
145°	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9
147.5°	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8
150°	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1
152.5°	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8
155°	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3
157.5°	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8
160°	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5
162.5°	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6
165°	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9
167.5°	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7
170°	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6
172.5°	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9
175°	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8
177.5°	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	8.3	8.7	8.6	8.3	8.3	8.7	9.0
90°	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333540-927

CATALOG NUMBER: S125RDIP-S610D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)