

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333546-927

Luminaire Tested: **S125RDIP-S610D1205U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333546-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5325.6 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27	22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19
5	66	55	48	42	60	50	44	39	41	36	32	33	29	26	25	22	21	17
6	61	50	42	36	55	45	38	34	37	32	28	30	26	23	22	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.3
10°-20°	206.0	3.9
20°-30°	326.6	6.1
30°-40°	393.9	7.4
40°-50°	351.8	6.6
50°-60°	269.8	5.1
60°-70°	175.3	3.3
70°-80°	85.2	1.6
80°-90°	22.9	0.4
90°-100°	330.9	6.2
100°-110°	711.4	13.4
110°-120°	667.6	12.5
120°-130°	541.1	10.2
130°-140°	434.2	8.2
140°-150°	327.7	6.2
150°-160°	230.6	4.3
160°-170°	136.0	2.6
170°-180°	44.2	0.8
0°-30°	602.9	11.3
0°-40°	996.8	18.7
0°-60°	1618.4	30.4
0°-90°	1901.8	35.7
90°-120°	1710.0	32.1
90°-150°	3013.0	56.6
90°-180°	3424.0	64.3
0°-180°	5325.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	21	1	21	1	21	15
95°	216	30	216	30	216	306
105°	1220	104	1220	104	1220	1212
115°	1359	186	1359	186	1359	1327
125°	1071	258	1071	258	1071	969
135°	889	302	889	302	889	689
145°	701	352	701	352	701	446
155°	588	401	588	401	588	274
165°	516	438	516	438	516	147
175°	463	456	463	456	463	45
180°	456	456	456	456	456	



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	9.5	9.3	8.9	8.9	9.1	9.2	8.8	8.4	8.2	8.0	7.8
90°	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6	15.7	14.7	12.9
92.5°	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1	240.3	296.8	301.6
95°	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8	798.0	815.6	665.5
97.5°	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6	1009.8	870.9	594.3
100°	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2	1061.3	831.2	530.2
102.5°	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5	1030.4	761.2	481.6
105°	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5	931.5	667.3	434.4
107.5°	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6	830.7	602.7	414.5
110°	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0	773.2	572.5	408.7



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6	730.5	554.8	408.7
115°	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8	683.9	535.8	411.5
117.5°	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8	656.1	526.3	417.6
120°	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3	640.6	521.9	423.4
122.5°	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5	627.4	518.2	428.6
125°	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5	609.3	513.7	437.2
127.5°	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1	592.8	511.4	446.9
130°	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7	581.8	509.9	452.9
132.5°	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2	572.9	509.9	459.5
135°	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3	562.4	509.9	468.5
137.5°	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1	553.0	511.0	476.8
140°	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0	548.6	511.7	480.5
142.5°	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4	544.9	512.5	482.7
145°	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9	539.4	511.7	485.1
147.5°	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2	533.7	509.4	486.0
150°	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5	529.3	507.2	486.0
152.5°	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2	524.1	504.2	485.3
155°	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1	515.5	498.9	483.2
157.5°	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1	507.4	493.4	480.9
160°	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7	500.7	489.7	478.6
162.5°	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6	494.9	485.3	476.4
165°	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4	486.0	478.6	473.1
167.5°	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7	477.4	472.2	467.9
170°	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8	472.2	468.5	465.8
172.5°	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2	467.1	464.1	462.8
175°	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0	460.3	459.3	459.3
177.5°	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0	457.3	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	7.9	7.5	7.6	7.3	6.7	7.4	7.8	7.9	7.6	7.4	7.4
90°	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0	1.8	3.6	5.5
92.5°	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2	13.6	21.4	32.8
95°	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3	31.3	38.7	48.8
97.5°	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5	51.6	56.7	66.9
100°	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4	66.3	69.9	80.1
102.5°	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9	81.0	84.0	94.8
105°	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0	104.0	108.6	117.8
107.5°	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5	129.4	133.8	141.4
110°	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5	146.4	150.0	158.4



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4	163.3	166.2	174.5
115°	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9	187.7	190.5	198.8
117.5°	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0	210.8	213.7	222.0
120°	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8	225.5	229.2	237.5
122.5°	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2	240.3	243.2	251.4
125°	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7	259.6	264.2	272.4
127.5°	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0	275.8	281.7	292.2
130°	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6	285.3	292.7	304.7
132.5°	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9	293.4	302.3	315.8
135°	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9	305.6	316.6	331.4
137.5°	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0	319.8	330.1	344.8
140°	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8	328.6	339.7	354.4
142.5°	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1	338.2	348.5	363.2
145°	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6	353.5	362.7	375.6
147.5°	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8	368.9	376.8	388.8
150°	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4	379.2	385.7	397.7
152.5°	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7	388.8	394.5	405.0
155°	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3	401.3	406.9	416.1
157.5°	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5	413.3	417.7	425.6
160°	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6	420.6	424.4	430.8
162.5°	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2	427.3	430.9	436.7
165°	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2	436.3	439.1	443.7
167.5°	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8	443.9	445.5	448.1
170°	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2	448.3	449.2	451.1
172.5°	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2	450.5	451.4	453.2
175°	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7	453.8	454.7	455.7
177.5°	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3	455.8	455.8	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	7.5	7.8	7.8	8.6	8.1	8.7	8.9	8.9	9.0	9.2	9.3
90°	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6	17.5	18.4	20.3
92.5°	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1	118.4	89.1	75.5
95°	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8	521.9	408.7	331.4
97.5°	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6	887.6	777.3	669.7
100°	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2	1087.1	992.3	896.5
102.5°	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5	1209.3	1163.9	1099.1
105°	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5	1278.6	1319.1	1308.9
107.5°	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6	1216.9	1320.9	1369.0
110°	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0	1146.9	1276.7	1354.9



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6	1077.7	1208.9	1301.2
115°	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8	978.5	1104.5	1204.9
117.5°	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8	909.8	1018.4	1110.5
120°	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3	870.8	972.0	1053.0
122.5°	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5	842.8	933.0	1008.8
125°	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5	805.4	885.5	951.8
127.5°	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1	769.7	844.5	906.5
130°	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7	744.7	816.5	876.3
132.5°	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2	721.1	786.2	843.9
135°	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3	684.8	743.8	796.2
137.5°	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1	652.4	701.4	746.0
140°	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0	633.3	675.7	714.3
142.5°	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4	617.1	653.6	687.1
145°	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9	596.4	625.0	649.8
147.5°	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2	579.3	601.3	620.0
150°	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5	569.8	587.2	603.8
152.5°	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2	560.2	576.2	589.1
155°	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1	545.8	558.7	568.9
157.5°	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1	532.2	542.2	550.1
160°	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7	521.9	531.1	537.6
162.5°	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6	513.1	520.8	526.5
165°	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4	499.8	505.3	509.9
167.5°	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7	487.0	491.2	494.5
170°	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8	479.6	482.4	484.2
172.5°	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2	472.9	475.0	476.1
175°	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0	463.0	464.9	464.9
177.5°	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0	458.8	458.8	458.8
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	9.6	9.3	9.5	9.5	9.5	9.3	9.6	9.3	9.2	9.0	8.9
90°	20.3	20.3	21.2	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6
92.5°	63.7	61.5	60.2	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1
95°	266.0	238.4	231.1	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8
97.5°	612.8	561.3	534.6	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6
100°	833.1	766.8	732.7	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2
102.5°	1031.1	984.0	947.0	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5
105°	1279.5	1249.1	1230.7	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5
107.5°	1383.9	1383.7	1377.6	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6
110°	1396.4	1413.9	1420.3	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1361.8	1391.8	1407.8	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6
115°	1276.7	1320.9	1346.6	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8
117.5°	1182.3	1228.0	1253.5	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8
120°	1121.2	1165.3	1190.2	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3
122.5°	1069.6	1110.1	1135.0	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5
125°	1003.3	1041.1	1061.3	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5
127.5°	953.2	986.6	1005.8	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1
130°	922.3	952.7	971.1	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7
132.5°	889.9	920.3	937.2	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2
135°	836.7	867.1	883.7	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3
137.5°	782.2	809.8	825.1	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1
140°	748.4	772.3	786.1	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0
142.5°	716.0	736.2	749.2	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4
145°	671.9	687.6	697.8	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9
147.5°	637.5	650.1	655.9	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2
150°	617.7	628.7	632.4	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5
152.5°	600.7	609.5	613.2	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2
155°	578.1	584.5	587.2	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1
157.5°	557.2	562.6	565.1	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1
160°	544.0	548.6	550.5	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7
162.5°	531.5	535.4	535.8	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6
165°	513.7	515.5	515.5	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4
167.5°	496.3	498.0	497.3	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7
170°	486.0	487.0	487.0	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8
172.5°	476.4	478.1	476.7	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2
175°	464.9	465.8	463.9	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0
177.5°	458.0	458.8	456.5	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	8.9	8.7	8.1	8.6	7.8	7.8	7.5	7.4	7.4	7.6	7.9
90°	15.7	14.7	12.9	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0
92.5°	240.3	296.8	301.6	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2
95°	798.0	815.6	665.5	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3
97.5°	1009.8	870.9	594.3	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5
100°	1061.3	831.2	530.2	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4
102.5°	1030.4	761.2	481.6	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9
105°	931.5	667.3	434.4	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0
107.5°	830.7	602.7	414.5	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5
110°	773.2	572.5	408.7	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	730.5	554.8	408.7	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4
115°	683.9	535.8	411.5	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9
117.5°	656.1	526.3	417.6	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0
120°	640.6	521.9	423.4	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8
122.5°	627.4	518.2	428.6	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2
125°	609.3	513.7	437.2	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7
127.5°	592.8	511.4	446.9	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0
130°	581.8	509.9	452.9	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6
132.5°	572.9	509.9	459.5	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9
135°	562.4	509.9	468.5	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9
137.5°	553.0	511.0	476.8	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0
140°	548.6	511.7	480.5	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8
142.5°	544.9	512.5	482.7	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1
145°	539.4	511.7	485.1	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6
147.5°	533.7	509.4	486.0	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8
150°	529.3	507.2	486.0	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4
152.5°	524.1	504.2	485.3	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7
155°	515.5	498.9	483.2	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3
157.5°	507.4	493.4	480.9	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5
160°	500.7	489.7	478.6	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6
162.5°	494.9	485.3	476.4	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2
165°	486.0	478.6	473.1	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2
167.5°	477.4	472.2	467.9	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8
170°	472.2	468.5	465.8	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2
172.5°	467.1	464.1	462.8	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2
175°	460.3	459.3	459.3	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7
177.5°	457.3	456.5	456.5	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.8	7.4	6.7	7.3	7.6	7.5	7.9	7.8	8.0	8.2	8.4
90°	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6
92.5°	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1
95°	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8
97.5°	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6
100°	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2
102.5°	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5
105°	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5
107.5°	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6
110°	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6
115°	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8
117.5°	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8
120°	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3
122.5°	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5
125°	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5
127.5°	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1
130°	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7
132.5°	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2
135°	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3
137.5°	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1
140°	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0
142.5°	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4
145°	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9
147.5°	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2
150°	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5
152.5°	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2
155°	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1
157.5°	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1
160°	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7
162.5°	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6
165°	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4
167.5°	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7
170°	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8
172.5°	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2
175°	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0
177.5°	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	8.8	9.2	9.1	8.9	8.9	9.3	9.5
90°	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3



TEST NUMBER: P333546-927

CATALOG NUMBER: S125RDIP-S610D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)