

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333522-927

Luminaire Tested: **S125RDIP-S610D365U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333522-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D365U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2941.4 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60	56
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	47
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	50	47	44	41
4	78	67	60	54	73	64	57	51	57	51	47	51	46	43	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31
6	66	54	46	40	62	52	44	39	46	40	36	41	36	33	37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	35	30	38	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	26	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	2.4
10°-20°	206.0	7.0
20°-30°	326.6	11.1
30°-40°	393.9	13.4
40°-50°	351.8	12.0
50°-60°	269.8	9.2
60°-70°	175.3	6.0
70°-80°	85.2	2.9
80°-90°	21.1	0.7
90°-100°	100.7	3.4
100°-110°	216.4	7.4
110°-120°	203.1	6.9
120°-130°	164.6	5.6
130°-140°	132.1	4.5
140°-150°	99.7	3.4
150°-160°	70.1	2.4
160°-170°	41.4	1.4
170°-180°	13.5	0.5
0°-30°	602.9	20.5
0°-40°	996.8	33.9
0°-60°	1618.4	55.0
0°-90°	1900.0	64.6
90°-120°	520.1	17.7
90°-150°	916.4	31.2
90°-180°	1041.0	35.4
0°-180°	2941.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	6	0	6	0	6	5
95°	66	9	66	9	66	93
105°	371	32	371	32	371	369
115°	413	57	413	57	413	404
125°	326	78	326	78	326	295
135°	270	92	270	92	270	210
145°	213	107	213	107	213	136
155°	179	122	179	122	179	83
165°	157	133	157	133	157	45
175°	141	139	141	139	141	14
180°	139	139	139	139	139	



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	6.6	6.3	6.0	6.0	6.3	6.7	6.3	6.1	6.0	5.9	6.1
90°	6.4	6.4	6.2	6.2	6.2	5.6	5.3	5.1	4.8	4.5	3.9
92.5°	17.8	18.3	18.7	19.4	23.0	27.1	36.0	49.6	73.0	90.2	91.7
95°	65.8	70.3	72.5	80.9	100.8	124.3	158.8	201.3	242.7	248.0	202.4
97.5°	159.0	162.6	170.7	186.4	203.7	236.4	270.0	299.8	307.1	264.9	180.8
100°	218.4	222.8	233.2	253.3	272.7	301.8	330.7	344.4	322.8	252.8	161.3
102.5°	284.7	288.0	299.3	313.6	334.3	354.0	367.8	359.3	313.4	231.6	146.5
105°	371.0	374.3	379.9	389.1	398.2	401.2	388.9	350.5	283.4	203.0	132.1
107.5°	416.8	419.0	420.9	420.9	416.4	401.7	370.1	318.9	252.6	183.3	126.1
110°	432.0	432.0	430.0	424.7	412.1	388.3	348.9	295.6	235.2	174.1	124.3



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.2	428.2	423.3	414.2	395.8	367.7	327.8	277.3	222.2	168.7	124.3
115°	413.2	409.6	401.7	388.3	366.5	336.0	297.6	254.2	208.0	163.0	125.2
117.5°	383.5	381.3	373.5	359.6	337.8	309.7	276.7	239.3	199.6	160.1	127.0
120°	364.2	362.0	354.4	341.0	320.3	295.6	264.8	231.2	194.9	158.8	128.8
122.5°	347.2	345.2	337.6	325.3	306.8	283.8	256.4	225.2	190.8	157.6	130.3
125°	325.6	322.8	316.6	305.1	289.5	269.3	244.9	216.4	185.4	156.2	133.0
127.5°	307.1	305.9	300.1	289.9	275.7	256.8	234.1	207.5	180.3	155.6	135.9
130°	297.1	295.4	289.8	280.5	266.6	248.3	226.5	201.8	177.0	155.1	137.8
132.5°	286.9	285.0	279.9	270.7	256.7	239.2	219.4	196.2	174.3	155.1	139.7
135°	270.5	268.8	263.7	254.5	242.2	226.2	208.3	189.0	171.0	155.1	142.5
137.5°	252.8	251.0	246.3	237.9	226.9	213.3	198.4	182.8	168.2	155.4	145.0
140°	240.5	239.1	234.9	227.6	217.2	205.5	192.6	179.4	166.8	155.7	146.2
142.5°	229.1	227.9	223.9	217.8	209.0	198.8	187.7	176.6	165.7	155.9	146.8
145°	213.3	212.2	209.1	204.4	197.6	190.1	181.4	172.8	164.1	155.7	147.5
147.5°	200.0	199.5	197.7	193.9	188.6	182.9	176.2	169.1	162.3	155.0	147.8
150°	192.6	192.3	191.2	187.8	183.6	178.6	173.3	167.2	161.0	154.2	147.8
152.5°	186.8	186.5	185.4	182.7	179.2	175.2	170.4	164.9	159.4	153.4	147.6
155°	178.9	178.6	177.8	175.8	173.0	169.9	166.0	161.5	156.8	151.8	146.9
157.5°	171.8	171.9	171.1	169.5	167.3	164.9	161.8	158.2	154.3	150.0	146.2
160°	167.2	167.4	166.8	165.5	163.5	161.5	158.8	156.0	152.3	148.9	145.6
162.5°	162.9	163.0	162.8	161.7	160.2	158.4	156.1	153.4	150.5	147.6	144.9
165°	156.8	156.8	156.8	156.2	155.1	153.7	152.0	150.0	147.8	145.6	143.9
167.5°	151.1	151.2	151.5	151.0	150.4	149.4	148.1	146.8	145.2	143.6	142.4
170°	147.8	148.1	148.1	147.8	147.3	146.7	145.8	145.0	143.6	142.5	141.6
172.5°	144.7	145.0	145.4	144.9	144.8	144.5	143.9	143.0	142.0	141.2	140.8
175°	140.9	141.1	141.6	141.4	141.4	141.4	140.9	140.9	140.0	139.7	139.7
177.5°	138.9	138.9	139.5	139.3	139.5	139.5	139.5	139.3	139.1	138.9	138.9
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	6.3	6.2	6.3	6.3	5.9	7.0	7.6	7.8	7.4	7.0	6.6
90°	3.6	3.1	2.8	2.2	1.7	1.1	0.6	0.3	0.6	1.1	1.7
92.5°	63.8	38.3	23.0	14.8	10.0	6.5	4.1	3.4	4.1	6.5	10.0
95°	125.2	63.5	33.6	21.0	14.8	11.7	9.5	9.3	9.5	11.7	14.8
97.5°	99.9	54.7	34.9	25.9	20.4	17.3	15.7	15.4	15.7	17.3	20.4
100°	90.7	54.3	38.1	29.7	24.3	21.3	20.1	19.6	20.1	21.3	24.3
102.5°	86.9	56.3	41.9	33.7	28.8	25.5	24.6	24.3	24.6	25.5	28.8
105°	85.4	60.4	48.2	40.3	35.8	33.0	31.6	31.6	31.6	33.0	35.8
107.5°	87.9	66.6	54.7	47.7	43.0	40.7	39.4	38.8	39.4	40.7	43.0
110°	90.5	71.1	59.7	52.4	48.2	45.6	44.5	44.0	44.5	45.6	48.2



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	93.6	75.3	64.3	57.3	53.1	50.5	49.7	49.1	49.7	50.5	53.1
115°	98.2	82.1	71.7	64.6	60.4	58.0	57.1	56.6	57.1	58.0	60.4
117.5°	103.6	88.9	79.1	72.3	67.5	65.0	64.1	63.3	64.1	65.0	67.5
120°	107.3	93.8	84.0	77.0	72.2	69.7	68.6	67.7	68.6	69.7	72.2
122.5°	111.2	98.5	88.7	81.7	76.5	74.0	73.0	72.5	73.0	74.0	76.5
125°	116.8	104.7	95.5	88.2	82.9	80.3	79.0	78.4	79.0	80.3	82.9
127.5°	121.8	110.7	101.8	94.5	88.9	85.6	83.9	83.0	83.9	85.6	88.9
130°	125.2	114.5	105.8	98.5	92.7	89.0	86.8	86.0	86.8	89.0	92.7
132.5°	128.1	118.1	109.4	102.1	96.0	92.0	89.3	88.2	89.3	92.0	96.0
135°	132.1	122.9	114.2	106.7	100.8	96.3	92.9	91.8	92.9	96.3	100.8
137.5°	135.1	126.4	118.4	110.7	104.9	100.4	97.3	96.4	97.3	100.4	104.9
140°	137.2	128.8	120.6	113.1	107.8	103.3	100.0	99.1	100.0	103.3	107.8
142.5°	138.3	130.3	122.7	115.6	110.5	106.0	102.8	102.3	102.8	106.0	110.5
145°	140.0	133.0	125.7	119.3	114.2	110.3	107.5	106.9	107.5	110.3	114.2
147.5°	141.0	134.7	128.3	122.6	118.3	114.6	112.2	111.9	112.2	114.6	118.3
150°	141.6	135.8	129.6	124.8	121.0	117.3	115.3	114.8	115.3	117.3	121.0
152.5°	142.1	136.9	131.2	126.9	123.2	120.0	118.3	118.0	118.3	120.0	123.2
155°	142.5	138.0	133.2	129.4	126.5	123.7	122.1	122.1	122.1	123.7	126.5
157.5°	142.8	138.9	134.9	131.9	129.4	127.1	125.7	125.8	125.7	127.1	129.4
160°	142.8	139.4	135.8	133.2	131.0	129.0	127.9	128.3	127.9	129.0	131.0
162.5°	142.6	139.9	136.7	134.6	132.8	131.1	130.0	130.2	130.0	131.1	132.8
165°	142.2	140.0	137.8	136.1	134.9	133.6	132.7	133.2	132.7	133.6	134.9
167.5°	141.6	140.0	138.2	137.0	136.3	135.5	135.0	135.3	135.0	135.5	136.3
170°	141.1	140.0	138.6	137.8	137.2	136.7	136.3	136.7	136.3	136.7	137.2
172.5°	140.7	139.7	138.6	138.2	137.8	137.3	137.0	137.5	137.0	137.3	137.8
175°	140.0	139.4	138.6	138.6	138.6	138.3	138.0	138.6	138.0	138.3	138.6
177.5°	139.3	139.1	138.6	138.6	138.9	138.6	138.6	139.1	138.6	138.6	138.9
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	6.5	6.6	6.4	7.0	6.3	6.7	6.7	6.6	6.6	6.7	6.5
90°	2.2	2.8	3.1	3.6	3.9	4.5	4.8	5.1	5.3	5.6	6.2
92.5°	14.8	23.0	38.3	63.8	91.7	90.2	73.0	49.6	36.0	27.1	23.0
95°	21.0	33.6	63.5	125.2	202.4	248.0	242.7	201.3	158.8	124.3	100.8
97.5°	25.9	34.9	54.7	99.9	180.8	264.9	307.1	299.8	270.0	236.4	203.7
100°	29.7	38.1	54.3	90.7	161.3	252.8	322.8	344.4	330.7	301.8	272.7
102.5°	33.7	41.9	56.3	86.9	146.5	231.6	313.4	359.3	367.8	354.0	334.3
105°	40.3	48.2	60.4	85.4	132.1	203.0	283.4	350.5	388.9	401.2	398.2
107.5°	47.7	54.7	66.6	87.9	126.1	183.3	252.6	318.9	370.1	401.7	416.4
110°	52.4	59.7	71.1	90.5	124.3	174.1	235.2	295.6	348.9	388.3	412.1



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	57.3	64.3	75.3	93.6	124.3	168.7	222.2	277.3	327.8	367.7	395.8
115°	64.6	71.7	82.1	98.2	125.2	163.0	208.0	254.2	297.6	336.0	366.5
117.5°	72.3	79.1	88.9	103.6	127.0	160.1	199.6	239.3	276.7	309.7	337.8
120°	77.0	84.0	93.8	107.3	128.8	158.8	194.9	231.2	264.8	295.6	320.3
122.5°	81.7	88.7	98.5	111.2	130.3	157.6	190.8	225.2	256.4	283.8	306.8
125°	88.2	95.5	104.7	116.8	133.0	156.2	185.4	216.4	244.9	269.3	289.5
127.5°	94.5	101.8	110.7	121.8	135.9	155.6	180.3	207.5	234.1	256.8	275.7
130°	98.5	105.8	114.5	125.2	137.8	155.1	177.0	201.8	226.5	248.3	266.6
132.5°	102.1	109.4	118.1	128.1	139.7	155.1	174.3	196.2	219.4	239.2	256.7
135°	106.7	114.2	122.9	132.1	142.5	155.1	171.0	189.0	208.3	226.2	242.2
137.5°	110.7	118.4	126.4	135.1	145.0	155.4	168.2	182.8	198.4	213.3	226.9
140°	113.1	120.6	128.8	137.2	146.2	155.7	166.8	179.4	192.6	205.5	217.2
142.5°	115.6	122.7	130.3	138.3	146.8	155.9	165.7	176.6	187.7	198.8	209.0
145°	119.3	125.7	133.0	140.0	147.5	155.7	164.1	172.8	181.4	190.1	197.6
147.5°	122.6	128.3	134.7	141.0	147.8	155.0	162.3	169.1	176.2	182.9	188.6
150°	124.8	129.6	135.8	141.6	147.8	154.2	161.0	167.2	173.3	178.6	183.6
152.5°	126.9	131.2	136.9	142.1	147.6	153.4	159.4	164.9	170.4	175.2	179.2
155°	129.4	133.2	138.0	142.5	146.9	151.8	156.8	161.5	166.0	169.9	173.0
157.5°	131.9	134.9	138.9	142.8	146.2	150.0	154.3	158.2	161.8	164.9	167.3
160°	133.2	135.8	139.4	142.8	145.6	148.9	152.3	156.0	158.8	161.5	163.5
162.5°	134.6	136.7	139.9	142.6	144.9	147.6	150.5	153.4	156.1	158.4	160.2
165°	136.1	137.8	140.0	142.2	143.9	145.6	147.8	150.0	152.0	153.7	155.1
167.5°	137.0	138.2	140.0	141.6	142.4	143.6	145.2	146.8	148.1	149.4	150.4
170°	137.8	138.6	140.0	141.1	141.6	142.5	143.6	145.0	145.8	146.7	147.3
172.5°	138.2	138.6	139.7	140.7	140.8	141.2	142.0	143.0	143.9	144.5	144.8
175°	138.6	138.6	139.4	140.0	139.7	139.7	140.0	140.9	140.9	141.4	141.4
177.5°	138.6	138.6	139.1	139.3	138.9	138.9	139.1	139.3	139.5	139.5	139.5
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	6.7	6.5	6.6	6.6	6.6	6.5	6.7	6.5	6.7	6.6	6.6
90°	6.2	6.2	6.4	6.4	6.4	6.2	6.2	6.2	5.6	5.3	5.1
92.5°	19.4	18.7	18.3	17.8	18.3	18.7	19.4	23.0	27.1	36.0	49.6
95°	80.9	72.5	70.3	65.8	70.3	72.5	80.9	100.8	124.3	158.8	201.3
97.5°	186.4	170.7	162.6	159.0	162.6	170.7	186.4	203.7	236.4	270.0	299.8
100°	253.3	233.2	222.8	218.4	222.8	233.2	253.3	272.7	301.8	330.7	344.4
102.5°	313.6	299.3	288.0	284.7	288.0	299.3	313.6	334.3	354.0	367.8	359.3
105°	389.1	379.9	374.3	371.0	374.3	379.9	389.1	398.2	401.2	388.9	350.5
107.5°	420.9	420.9	419.0	416.8	419.0	420.9	420.9	416.4	401.7	370.1	318.9
110°	424.7	430.0	432.0	432.0	432.0	430.0	424.7	412.1	388.3	348.9	295.6



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	414.2	423.3	428.2	430.2	428.2	423.3	414.2	395.8	367.7	327.8	277.3
115°	388.3	401.7	409.6	413.2	409.6	401.7	388.3	366.5	336.0	297.6	254.2
117.5°	359.6	373.5	381.3	383.5	381.3	373.5	359.6	337.8	309.7	276.7	239.3
120°	341.0	354.4	362.0	364.2	362.0	354.4	341.0	320.3	295.6	264.8	231.2
122.5°	325.3	337.6	345.2	347.2	345.2	337.6	325.3	306.8	283.8	256.4	225.2
125°	305.1	316.6	322.8	325.6	322.8	316.6	305.1	289.5	269.3	244.9	216.4
127.5°	289.9	300.1	305.9	307.1	305.9	300.1	289.9	275.7	256.8	234.1	207.5
130°	280.5	289.8	295.4	297.1	295.4	289.8	280.5	266.6	248.3	226.5	201.8
132.5°	270.7	279.9	285.0	286.9	285.0	279.9	270.7	256.7	239.2	219.4	196.2
135°	254.5	263.7	268.8	270.5	268.8	263.7	254.5	242.2	226.2	208.3	189.0
137.5°	237.9	246.3	251.0	252.8	251.0	246.3	237.9	226.9	213.3	198.4	182.8
140°	227.6	234.9	239.1	240.5	239.1	234.9	227.6	217.2	205.5	192.6	179.4
142.5°	217.8	223.9	227.9	229.1	227.9	223.9	217.8	209.0	198.8	187.7	176.6
145°	204.4	209.1	212.2	213.3	212.2	209.1	204.4	197.6	190.1	181.4	172.8
147.5°	193.9	197.7	199.5	200.0	199.5	197.7	193.9	188.6	182.9	176.2	169.1
150°	187.8	191.2	192.3	192.6	192.3	191.2	187.8	183.6	178.6	173.3	167.2
152.5°	182.7	185.4	186.5	186.8	186.5	185.4	182.7	179.2	175.2	170.4	164.9
155°	175.8	177.8	178.6	178.9	178.6	177.8	175.8	173.0	169.9	166.0	161.5
157.5°	169.5	171.1	171.9	171.8	171.9	171.1	169.5	167.3	164.9	161.8	158.2
160°	165.5	166.8	167.4	167.2	167.4	166.8	165.5	163.5	161.5	158.8	156.0
162.5°	161.7	162.8	163.0	162.9	163.0	162.8	161.7	160.2	158.4	156.1	153.4
165°	156.2	156.8	156.8	156.8	156.8	156.8	156.2	155.1	153.7	152.0	150.0
167.5°	151.0	151.5	151.2	151.1	151.2	151.5	151.0	150.4	149.4	148.1	146.8
170°	147.8	148.1	148.1	147.8	148.1	148.1	147.8	147.3	146.7	145.8	145.0
172.5°	144.9	145.4	145.0	144.7	145.0	145.4	144.9	144.8	144.5	143.9	143.0
175°	141.4	141.6	141.1	140.9	141.1	141.6	141.4	141.4	141.4	140.9	140.9
177.5°	139.3	139.5	138.9	138.9	138.9	139.5	139.3	139.5	139.5	139.5	139.3
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	6.7	6.7	6.3	7.0	6.4	6.6	6.5	6.6	7.0	7.4	7.8
90°	4.8	4.5	3.9	3.6	3.1	2.8	2.2	1.7	1.1	0.6	0.3
92.5°	73.0	90.2	91.7	63.8	38.3	23.0	14.8	10.0	6.5	4.1	3.4
95°	242.7	248.0	202.4	125.2	63.5	33.6	21.0	14.8	11.7	9.5	9.3
97.5°	307.1	264.9	180.8	99.9	54.7	34.9	25.9	20.4	17.3	15.7	15.4
100°	322.8	252.8	161.3	90.7	54.3	38.1	29.7	24.3	21.3	20.1	19.6
102.5°	313.4	231.6	146.5	86.9	56.3	41.9	33.7	28.8	25.5	24.6	24.3
105°	283.4	203.0	132.1	85.4	60.4	48.2	40.3	35.8	33.0	31.6	31.6
107.5°	252.6	183.3	126.1	87.9	66.6	54.7	47.7	43.0	40.7	39.4	38.8
110°	235.2	174.1	124.3	90.5	71.1	59.7	52.4	48.2	45.6	44.5	44.0



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.2	168.7	124.3	93.6	75.3	64.3	57.3	53.1	50.5	49.7	49.1
115°	208.0	163.0	125.2	98.2	82.1	71.7	64.6	60.4	58.0	57.1	56.6
117.5°	199.6	160.1	127.0	103.6	88.9	79.1	72.3	67.5	65.0	64.1	63.3
120°	194.9	158.8	128.8	107.3	93.8	84.0	77.0	72.2	69.7	68.6	67.7
122.5°	190.8	157.6	130.3	111.2	98.5	88.7	81.7	76.5	74.0	73.0	72.5
125°	185.4	156.2	133.0	116.8	104.7	95.5	88.2	82.9	80.3	79.0	78.4
127.5°	180.3	155.6	135.9	121.8	110.7	101.8	94.5	88.9	85.6	83.9	83.0
130°	177.0	155.1	137.8	125.2	114.5	105.8	98.5	92.7	89.0	86.8	86.0
132.5°	174.3	155.1	139.7	128.1	118.1	109.4	102.1	96.0	92.0	89.3	88.2
135°	171.0	155.1	142.5	132.1	122.9	114.2	106.7	100.8	96.3	92.9	91.8
137.5°	168.2	155.4	145.0	135.1	126.4	118.4	110.7	104.9	100.4	97.3	96.4
140°	166.8	155.7	146.2	137.2	128.8	120.6	113.1	107.8	103.3	100.0	99.1
142.5°	165.7	155.9	146.8	138.3	130.3	122.7	115.6	110.5	106.0	102.8	102.3
145°	164.1	155.7	147.5	140.0	133.0	125.7	119.3	114.2	110.3	107.5	106.9
147.5°	162.3	155.0	147.8	141.0	134.7	128.3	122.6	118.3	114.6	112.2	111.9
150°	161.0	154.2	147.8	141.6	135.8	129.6	124.8	121.0	117.3	115.3	114.8
152.5°	159.4	153.4	147.6	142.1	136.9	131.2	126.9	123.2	120.0	118.3	118.0
155°	156.8	151.8	146.9	142.5	138.0	133.2	129.4	126.5	123.7	122.1	122.1
157.5°	154.3	150.0	146.2	142.8	138.9	134.9	131.9	129.4	127.1	125.7	125.8
160°	152.3	148.9	145.6	142.8	139.4	135.8	133.2	131.0	129.0	127.9	128.3
162.5°	150.5	147.6	144.9	142.6	139.9	136.7	134.6	132.8	131.1	130.0	130.2
165°	147.8	145.6	143.9	142.2	140.0	137.8	136.1	134.9	133.6	132.7	133.2
167.5°	145.2	143.6	142.4	141.6	140.0	138.2	137.0	136.3	135.5	135.0	135.3
170°	143.6	142.5	141.6	141.1	140.0	138.6	137.8	137.2	136.7	136.3	136.7
172.5°	142.0	141.2	140.8	140.7	139.7	138.6	138.2	137.8	137.3	137.0	137.5
175°	140.0	139.7	139.7	140.0	139.4	138.6	138.6	138.6	138.3	138.0	138.6
177.5°	139.1	138.9	138.9	139.3	139.1	138.6	138.6	138.9	138.6	138.6	139.1
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.6	7.0	5.9	6.3	6.3	6.2	6.3	6.1	5.9	6.0	6.1
90°	0.6	1.1	1.7	2.2	2.8	3.1	3.6	3.9	4.5	4.8	5.1
92.5°	4.1	6.5	10.0	14.8	23.0	38.3	63.8	91.7	90.2	73.0	49.6
95°	9.5	11.7	14.8	21.0	33.6	63.5	125.2	202.4	248.0	242.7	201.3
97.5°	15.7	17.3	20.4	25.9	34.9	54.7	99.9	180.8	264.9	307.1	299.8
100°	20.1	21.3	24.3	29.7	38.1	54.3	90.7	161.3	252.8	322.8	344.4
102.5°	24.6	25.5	28.8	33.7	41.9	56.3	86.9	146.5	231.6	313.4	359.3
105°	31.6	33.0	35.8	40.3	48.2	60.4	85.4	132.1	203.0	283.4	350.5
107.5°	39.4	40.7	43.0	47.7	54.7	66.6	87.9	126.1	183.3	252.6	318.9
110°	44.5	45.6	48.2	52.4	59.7	71.1	90.5	124.3	174.1	235.2	295.6



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	49.7	50.5	53.1	57.3	64.3	75.3	93.6	124.3	168.7	222.2	277.3
115°	57.1	58.0	60.4	64.6	71.7	82.1	98.2	125.2	163.0	208.0	254.2
117.5°	64.1	65.0	67.5	72.3	79.1	88.9	103.6	127.0	160.1	199.6	239.3
120°	68.6	69.7	72.2	77.0	84.0	93.8	107.3	128.8	158.8	194.9	231.2
122.5°	73.0	74.0	76.5	81.7	88.7	98.5	111.2	130.3	157.6	190.8	225.2
125°	79.0	80.3	82.9	88.2	95.5	104.7	116.8	133.0	156.2	185.4	216.4
127.5°	83.9	85.6	88.9	94.5	101.8	110.7	121.8	135.9	155.6	180.3	207.5
130°	86.8	89.0	92.7	98.5	105.8	114.5	125.2	137.8	155.1	177.0	201.8
132.5°	89.3	92.0	96.0	102.1	109.4	118.1	128.1	139.7	155.1	174.3	196.2
135°	92.9	96.3	100.8	106.7	114.2	122.9	132.1	142.5	155.1	171.0	189.0
137.5°	97.3	100.4	104.9	110.7	118.4	126.4	135.1	145.0	155.4	168.2	182.8
140°	100.0	103.3	107.8	113.1	120.6	128.8	137.2	146.2	155.7	166.8	179.4
142.5°	102.8	106.0	110.5	115.6	122.7	130.3	138.3	146.8	155.9	165.7	176.6
145°	107.5	110.3	114.2	119.3	125.7	133.0	140.0	147.5	155.7	164.1	172.8
147.5°	112.2	114.6	118.3	122.6	128.3	134.7	141.0	147.8	155.0	162.3	169.1
150°	115.3	117.3	121.0	124.8	129.6	135.8	141.6	147.8	154.2	161.0	167.2
152.5°	118.3	120.0	123.2	126.9	131.2	136.9	142.1	147.6	153.4	159.4	164.9
155°	122.1	123.7	126.5	129.4	133.2	138.0	142.5	146.9	151.8	156.8	161.5
157.5°	125.7	127.1	129.4	131.9	134.9	138.9	142.8	146.2	150.0	154.3	158.2
160°	127.9	129.0	131.0	133.2	135.8	139.4	142.8	145.6	148.9	152.3	156.0
162.5°	130.0	131.1	132.8	134.6	136.7	139.9	142.6	144.9	147.6	150.5	153.4
165°	132.7	133.6	134.9	136.1	137.8	140.0	142.2	143.9	145.6	147.8	150.0
167.5°	135.0	135.5	136.3	137.0	138.2	140.0	141.6	142.4	143.6	145.2	146.8
170°	136.3	136.7	137.2	137.8	138.6	140.0	141.1	141.6	142.5	143.6	145.0
172.5°	137.0	137.3	137.8	138.2	138.6	139.7	140.7	140.8	141.2	142.0	143.0
175°	138.0	138.3	138.6	138.6	138.6	139.4	140.0	139.7	139.7	140.0	140.9
177.5°	138.6	138.6	138.9	138.6	138.6	139.1	139.3	138.9	138.9	139.1	139.3
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9	138.9



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	6.3	6.7	6.3	6.0	6.0	6.3	6.6
90°	5.3	5.6	6.2	6.2	6.2	6.4	6.4
92.5°	36.0	27.1	23.0	19.4	18.7	18.3	17.8
95°	158.8	124.3	100.8	80.9	72.5	70.3	65.8
97.5°	270.0	236.4	203.7	186.4	170.7	162.6	159.0
100°	330.7	301.8	272.7	253.3	233.2	222.8	218.4
102.5°	367.8	354.0	334.3	313.6	299.3	288.0	284.7
105°	388.9	401.2	398.2	389.1	379.9	374.3	371.0
107.5°	370.1	401.7	416.4	420.9	420.9	419.0	416.8
110°	348.9	388.3	412.1	424.7	430.0	432.0	432.0



TEST NUMBER: P333522-927

CATALOG NUMBER: S125RDIP-S610D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	327.8	367.7	395.8	414.2	423.3	428.2	430.2
115°	297.6	336.0	366.5	388.3	401.7	409.6	413.2
117.5°	276.7	309.7	337.8	359.6	373.5	381.3	383.5
120°	264.8	295.6	320.3	341.0	354.4	362.0	364.2
122.5°	256.4	283.8	306.8	325.3	337.6	345.2	347.2
125°	244.9	269.3	289.5	305.1	316.6	322.8	325.6
127.5°	234.1	256.8	275.7	289.9	300.1	305.9	307.1
130°	226.5	248.3	266.6	280.5	289.8	295.4	297.1
132.5°	219.4	239.2	256.7	270.7	279.9	285.0	286.9
135°	208.3	226.2	242.2	254.5	263.7	268.8	270.5
137.5°	198.4	213.3	226.9	237.9	246.3	251.0	252.8
140°	192.6	205.5	217.2	227.6	234.9	239.1	240.5
142.5°	187.7	198.8	209.0	217.8	223.9	227.9	229.1
145°	181.4	190.1	197.6	204.4	209.1	212.2	213.3
147.5°	176.2	182.9	188.6	193.9	197.7	199.5	200.0
150°	173.3	178.6	183.6	187.8	191.2	192.3	192.6
152.5°	170.4	175.2	179.2	182.7	185.4	186.5	186.8
155°	166.0	169.9	173.0	175.8	177.8	178.6	178.9
157.5°	161.8	164.9	167.3	169.5	171.1	171.9	171.8
160°	158.8	161.5	163.5	165.5	166.8	167.4	167.2
162.5°	156.1	158.4	160.2	161.7	162.8	163.0	162.9
165°	152.0	153.7	155.1	156.2	156.8	156.8	156.8
167.5°	148.1	149.4	150.4	151.0	151.5	151.2	151.1
170°	145.8	146.7	147.3	147.8	148.1	148.1	147.8
172.5°	143.9	144.5	144.8	144.9	145.4	145.0	144.7
175°	140.9	141.4	141.4	141.4	141.6	141.1	140.9
177.5°	139.5	139.5	139.5	139.3	139.5	138.9	138.9
180°	138.9	138.9	138.9	138.9	138.9	138.9	138.9

(END OF REPORT)