

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333533-927

Luminaire Tested: **S125RDIP-S610D810U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333533-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S610D810U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4122.2 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46
1	97	93	89	86	89	86	83	80	72	69	67	59	57	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	67	60	55	56	52	48	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	41	45	40	35	37	33	30	30	28	25	22
6	63	51	43	38	58	48	41	35	40	35	31	34	30	27	28	25	22	19
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	1.7
10°-20°	206.0	5.0
20°-30°	326.6	7.9
30°-40°	393.9	9.6
40°-50°	351.8	8.5
50°-60°	269.8	6.5
60°-70°	175.3	4.3
70°-80°	85.2	2.1
80°-90°	22.1	0.5
90°-100°	53.3	1.3
100°-110°	157.4	3.8
110°-120°	266.7	6.5
120°-130°	350.9	8.5
130°-140°	393.2	9.5
140°-150°	385.4	9.3
150°-160°	323.7	7.9
160°-170°	215.2	5.2
170°-180°	75.3	1.8
0°-30°	602.9	14.6
0°-40°	996.8	24.2
0°-60°	1618.4	39.3
0°-90°	1901.0	46.1
90°-120°	477.4	11.6
90°-150°	1607.0	39.0
90°-180°	2221.0	53.9
0°-180°	4122.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	15	1	15	1	15	9
95°	53	40	53	40	53	54
105°	154	141	154	141	154	163
115°	270	267	270	267	270	267
125°	392	390	392	390	392	350
135°	509	507	509	507	509	392
145°	616	614	616	614	616	385
155°	702	702	702	702	702	323
165°	762	764	762	764	762	215
175°	791	794	791	794	791	75
180°	796	796	796	796	796	



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	8.2	7.9	7.6	7.5	7.7	8.1	7.7	7.3	7.2	7.1	7.1
90°	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2	10.6	9.9	9.0
92.5°	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6	24.7	23.8	22.6
95°	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6	48.6	47.7	46.3
97.5°	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8	76.8	76.0	74.1
100°	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3	96.0	94.7	93.0
102.5°	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3	116.0	114.6	113.7
105°	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7	148.9	148.1	147.2
107.5°	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7	184.3	183.9	183.2
110°	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0	208.6	208.1	207.7



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3	233.1	232.9	232.4
115°	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5	270.5	270.7	270.5
117.5°	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6	307.4	307.4	307.1
120°	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6	332.6	332.6	332.5
122.5°	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2	357.3	357.4	357.0
125°	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4	393.7	394.0	393.8
127.5°	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4	429.5	429.7	429.5
130°	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1	453.3	453.4	453.1
132.5°	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9	476.1	476.3	476.3
135°	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0	511.0	511.0	510.9
137.5°	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2	545.0	544.9	544.5
140°	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7	566.5	566.2	565.8
142.5°	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8	587.6	587.5	586.9
145°	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2	618.2	618.2	617.8
147.5°	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3	646.0	645.7	645.4
150°	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1	664.1	664.1	663.5
152.5°	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6	680.2	679.9	679.7
155°	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2	703.6	703.1	702.9
157.5°	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6	724.1	723.5	723.3
160°	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0	736.5	735.9	735.8
162.5°	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6	748.0	747.3	747.3
165°	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3	763.7	763.2	763.0
167.5°	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9	775.0	774.2	774.2
170°	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8	782.0	781.1	781.1
172.5°	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7	786.9	786.1	786.1
175°	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3	792.5	791.6	791.6
177.5°	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8	795.2	794.5	794.6
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	7.1	7.0	7.0	6.8	6.3	7.3	7.8	7.8	7.6	7.3	7.1
90°	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6	1.7	2.9	4.0
92.5°	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0	15.8	16.6	17.3
95°	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2	40.6	40.8	41.1
97.5°	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9	67.0	67.1	67.3
100°	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
102.5°	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1	108.6	109.2	109.7
105°	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2	142.0	142.6	143.3
107.5°	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9	178.6	179.3	180.0
110°	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2	203.9	204.5	205.3





TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9	229.3	229.7	230.0
115°	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0	267.5	268.1	268.6
117.5°	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1	305.4	305.6	305.9
120°	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9	329.6	330.3	331.0
122.5°	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7	355.0	355.2	355.5
125°	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6	390.5	391.3	392.1
127.5°	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8	427.3	427.7	428.2
130°	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1	449.8	450.5	451.1
132.5°	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4	472.5	473.6	474.8
135°	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7	507.6	508.3	509.2
137.5°	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0	540.7	541.5	542.3
140°	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3	561.9	562.6	563.3
142.5°	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6	583.1	583.7	584.2
145°	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9	614.4	615.0	615.5
147.5°	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9	643.2	643.5	643.8
150°	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2	662.0	661.9	661.8
152.5°	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0	678.3	678.4	678.7
155°	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4	702.4	702.4	702.4
157.5°	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3	724.0	723.7	723.3
160°	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1	736.7	736.3	735.9
162.5°	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5	748.2	747.9	747.7
165°	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8	763.5	763.3	763.0
167.5°	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7	776.1	775.5	775.0
170°	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6	783.1	782.5	782.0
172.5°	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5	788.0	787.4	786.9
175°	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2	793.6	793.1	792.5
177.5°	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0	796.5	796.1	795.7
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	7.1	7.2	7.2	7.8	7.3	7.8	7.9	7.8	7.9	8.1	7.9
90°	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2	12.0	12.7	13.2
92.5°	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6	26.5	27.4	28.0
95°	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6	50.6	51.6	52.2
97.5°	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8	78.7	79.6	80.1
100°	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3	98.5	99.7	100.5
102.5°	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3	118.7	120.0	120.9
105°	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7	150.5	151.4	151.9
107.5°	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7	185.1	185.5	185.7
110°	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0	209.4	209.8	209.9



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3	233.5	233.7	233.7
115°	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5	270.3	270.1	270.0
117.5°	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6	307.7	307.8	307.6
120°	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6	332.6	332.6	332.4
122.5°	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2	357.1	357.0	356.7
125°	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4	393.2	392.8	392.7
127.5°	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4	429.2	429.1	428.9
130°	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1	453.0	452.9	452.7
132.5°	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9	475.8	475.7	475.4
135°	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0	511.0	511.0	510.8
137.5°	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2	545.3	545.5	545.3
140°	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7	567.0	567.3	567.0
142.5°	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8	588.0	588.1	587.9
145°	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2	618.2	618.2	618.0
147.5°	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3	646.7	647.1	646.7
150°	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1	664.1	664.1	663.9
152.5°	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6	680.9	681.2	681.1
155°	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2	704.7	705.3	705.2
157.5°	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6	725.2	725.7	725.6
160°	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0	737.5	738.1	738.1
162.5°	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6	749.3	750.0	749.9
165°	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3	764.9	765.3	765.2
167.5°	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9	776.7	777.5	777.4
170°	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8	783.6	784.4	784.3
172.5°	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7	788.5	789.4	789.4
175°	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3	794.2	795.0	794.9
177.5°	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8	796.5	797.2	797.1
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	8.2	8.1	8.2	8.2	8.2	8.1	8.2	7.9	8.1	7.9	7.8
90°	13.6	14.0	14.4	14.9	14.4	14.0	13.6	13.2	12.7	12.0	11.2
92.5°	28.4	28.6	28.9	29.2	28.9	28.6	28.4	28.0	27.4	26.5	25.6
95°	52.4	52.8	53.0	53.2	53.0	52.8	52.4	52.2	51.6	50.6	49.6
97.5°	80.2	80.4	80.6	80.8	80.6	80.4	80.2	80.1	79.6	78.7	77.8
100°	100.8	101.0	101.3	101.6	101.3	101.0	100.8	100.5	99.7	98.5	97.3
102.5°	121.3	121.6	122.0	122.4	122.0	121.6	121.3	120.9	120.0	118.7	117.3
105°	152.4	152.8	153.2	153.6	153.2	152.8	152.4	151.9	151.4	150.5	149.7
107.5°	185.7	185.6	185.6	185.6	185.6	185.6	185.7	185.7	185.5	185.1	184.7
110°	209.8	209.6	209.5	209.4	209.5	209.6	209.8	209.9	209.8	209.4	209.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	233.4	233.1	232.9	232.7	232.9	233.1	233.4	233.7	233.7	233.5	233.3
115°	269.9	269.7	269.6	269.5	269.6	269.7	269.9	270.0	270.1	270.3	270.5
117.5°	307.0	306.5	305.9	305.4	305.9	306.5	307.0	307.6	307.8	307.7	307.6
120°	331.8	331.3	330.7	330.2	330.7	331.3	331.8	332.4	332.6	332.6	332.6
122.5°	356.2	355.8	355.4	355.0	355.4	355.8	356.2	356.7	357.0	357.1	357.2
125°	392.5	392.4	392.3	392.1	392.3	392.4	392.5	392.7	392.8	393.2	393.4
127.5°	428.6	428.3	428.1	427.8	428.1	428.3	428.6	428.9	429.1	429.2	429.4
130°	452.4	452.1	451.9	451.5	451.9	452.1	452.4	452.7	452.9	453.0	453.1
132.5°	475.1	474.7	474.3	473.9	474.3	474.7	475.1	475.4	475.7	475.8	475.9
135°	510.2	509.7	509.1	508.6	509.1	509.7	510.2	510.8	511.0	511.0	511.0
137.5°	544.5	543.9	543.2	542.5	543.2	543.9	544.5	545.3	545.5	545.3	545.2
140°	566.4	565.7	565.0	564.4	565.0	565.7	566.4	567.0	567.3	567.0	566.7
142.5°	587.2	586.5	585.8	585.1	585.8	586.5	587.2	587.9	588.1	588.0	587.8
145°	617.6	617.2	616.8	616.3	616.8	617.2	617.6	618.0	618.2	618.2	618.2
147.5°	645.8	644.8	644.0	643.0	644.0	644.8	645.8	646.7	647.1	646.7	646.3
150°	663.6	663.4	663.1	662.8	663.1	663.4	663.6	663.9	664.1	664.1	664.1
152.5°	680.6	680.2	679.7	679.1	679.7	680.2	680.6	681.1	681.2	680.9	680.6
155°	704.5	703.9	703.1	702.4	703.1	703.9	704.5	705.2	705.3	704.7	704.2
157.5°	724.6	723.7	722.8	721.9	722.8	723.7	724.6	725.6	725.7	725.2	724.6
160°	737.4	736.7	735.9	735.3	735.9	736.7	737.4	738.1	738.1	737.5	737.0
162.5°	749.1	748.3	747.5	746.7	747.5	748.3	749.1	749.9	750.0	749.3	748.6
165°	764.4	763.6	762.7	761.9	762.7	763.6	764.4	765.2	765.3	764.9	764.3
167.5°	776.7	775.8	774.9	774.0	774.9	775.8	776.7	777.4	777.5	776.7	775.9
170°	783.4	782.4	781.5	780.5	781.5	782.4	783.4	784.3	784.4	783.6	782.8
172.5°	788.5	787.7	786.8	785.9	786.8	787.7	788.5	789.4	789.4	788.5	787.7
175°	793.9	793.0	792.0	791.1	792.0	793.0	793.9	794.9	795.0	794.2	793.3
177.5°	796.3	795.6	794.8	794.0	794.8	795.6	796.3	797.1	797.2	796.5	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	7.9	7.8	7.3	7.8	7.2	7.2	7.1	7.1	7.3	7.6	7.8
90°	10.6	9.9	9.0	8.0	7.1	6.0	5.0	4.0	2.9	1.7	0.6
92.5°	24.7	23.8	22.6	21.4	20.2	19.0	18.1	17.3	16.6	15.8	15.0
95°	48.6	47.7	46.3	44.9	43.6	42.2	41.4	41.1	40.8	40.6	40.2
97.5°	76.8	76.0	74.1	72.2	70.3	68.4	67.3	67.3	67.1	67.0	66.9
100°	96.0	94.7	93.0	91.2	89.4	87.6	86.7	86.7	86.7	86.7	86.7
102.5°	116.0	114.6	113.7	112.8	111.9	111.0	110.3	109.7	109.2	108.6	108.1
105°	148.9	148.1	147.2	146.4	145.6	144.7	144.0	143.3	142.6	142.0	141.2
107.5°	184.3	183.9	183.2	182.6	182.0	181.3	180.7	180.0	179.3	178.6	177.9
110°	208.6	208.1	207.7	207.3	206.9	206.5	206.0	205.3	204.5	203.9	203.2



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	233.1	232.9	232.4	231.9	231.3	230.8	230.4	230.0	229.7	229.3	228.9
115°	270.5	270.7	270.5	270.1	269.9	269.6	269.2	268.6	268.1	267.5	267.0
117.5°	307.4	307.4	307.1	306.9	306.7	306.4	306.1	305.9	305.6	305.4	305.1
120°	332.6	332.6	332.5	332.4	332.2	332.1	331.7	331.0	330.3	329.6	328.9
122.5°	357.3	357.4	357.0	356.7	356.3	356.0	355.7	355.5	355.2	355.0	354.7
125°	393.7	394.0	393.8	393.7	393.6	393.4	392.9	392.1	391.3	390.5	389.6
127.5°	429.5	429.7	429.5	429.3	429.1	429.0	428.6	428.2	427.7	427.3	426.8
130°	453.3	453.4	453.1	452.9	452.6	452.3	451.9	451.1	450.5	449.8	449.1
132.5°	476.1	476.3	476.3	476.3	476.4	476.4	475.9	474.8	473.6	472.5	471.4
135°	511.0	511.0	510.9	510.8	510.6	510.5	510.0	509.2	508.3	507.6	506.7
137.5°	545.0	544.9	544.5	544.2	544.0	543.7	543.1	542.3	541.5	540.7	540.0
140°	566.5	566.2	565.8	565.4	564.9	564.5	564.0	563.3	562.6	561.9	561.3
142.5°	587.6	587.5	586.9	586.5	585.9	585.4	584.9	584.2	583.7	583.1	582.6
145°	618.2	618.2	617.8	617.3	617.0	616.6	616.1	615.5	615.0	614.4	613.9
147.5°	646.0	645.7	645.4	645.1	644.8	644.4	644.0	643.8	643.5	643.2	642.9
150°	664.1	664.1	663.5	663.0	662.4	661.9	661.6	661.8	661.9	662.0	662.2
152.5°	680.2	679.9	679.7	679.5	679.2	679.1	678.8	678.7	678.4	678.3	678.0
155°	703.6	703.1	702.9	702.8	702.7	702.5	702.4	702.4	702.4	702.4	702.4
157.5°	724.1	723.5	723.3	723.3	723.1	722.9	723.0	723.3	723.7	724.0	724.3
160°	736.5	735.9	735.8	735.6	735.5	735.4	735.5	735.9	736.3	736.7	737.1
162.5°	748.0	747.3	747.3	747.3	747.2	747.2	747.3	747.7	747.9	748.2	748.5
165°	763.7	763.2	763.0	762.9	762.7	762.6	762.7	763.0	763.3	763.5	763.8
167.5°	775.0	774.2	774.2	774.2	774.2	774.2	774.4	775.0	775.5	776.1	776.7
170°	782.0	781.1	781.1	781.1	781.1	781.1	781.4	782.0	782.5	783.1	783.6
172.5°	786.9	786.1	786.1	786.1	786.1	786.1	786.3	786.9	787.4	788.0	788.5
175°	792.5	791.6	791.6	791.6	791.6	791.6	791.9	792.5	793.1	793.6	794.2
177.5°	795.2	794.5	794.6	794.7	794.9	795.0	795.2	795.7	796.1	796.5	797.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.8	7.3	6.3	6.8	7.0	7.0	7.1	7.1	7.1	7.2	7.3
90°	1.7	2.9	4.0	5.0	6.0	7.1	8.0	9.0	9.9	10.6	11.2
92.5°	15.8	16.6	17.3	18.1	19.0	20.2	21.4	22.6	23.8	24.7	25.6
95°	40.6	40.8	41.1	41.4	42.2	43.6	44.9	46.3	47.7	48.6	49.6
97.5°	67.0	67.1	67.3	67.3	68.4	70.3	72.2	74.1	76.0	76.8	77.8
100°	86.7	86.7	86.7	86.7	87.6	89.4	91.2	93.0	94.7	96.0	97.3
102.5°	108.6	109.2	109.7	110.3	111.0	111.9	112.8	113.7	114.6	116.0	117.3
105°	142.0	142.6	143.3	144.0	144.7	145.6	146.4	147.2	148.1	148.9	149.7
107.5°	178.6	179.3	180.0	180.7	181.3	182.0	182.6	183.2	183.9	184.3	184.7
110°	203.9	204.5	205.3	206.0	206.5	206.9	207.3	207.7	208.1	208.6	209.0





TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	229.3	229.7	230.0	230.4	230.8	231.3	231.9	232.4	232.9	233.1	233.3
115°	267.5	268.1	268.6	269.2	269.6	269.9	270.1	270.5	270.7	270.5	270.5
117.5°	305.4	305.6	305.9	306.1	306.4	306.7	306.9	307.1	307.4	307.4	307.6
120°	329.6	330.3	331.0	331.7	332.1	332.2	332.4	332.5	332.6	332.6	332.6
122.5°	355.0	355.2	355.5	355.7	356.0	356.3	356.7	357.0	357.4	357.3	357.2
125°	390.5	391.3	392.1	392.9	393.4	393.6	393.7	393.8	394.0	393.7	393.4
127.5°	427.3	427.7	428.2	428.6	429.0	429.1	429.3	429.5	429.7	429.5	429.4
130°	449.8	450.5	451.1	451.9	452.3	452.6	452.9	453.1	453.4	453.3	453.1
132.5°	472.5	473.6	474.8	475.9	476.4	476.4	476.3	476.3	476.3	476.1	475.9
135°	507.6	508.3	509.2	510.0	510.5	510.6	510.8	510.9	511.0	511.0	511.0
137.5°	540.7	541.5	542.3	543.1	543.7	544.0	544.2	544.5	544.9	545.0	545.2
140°	561.9	562.6	563.3	564.0	564.5	564.9	565.4	565.8	566.2	566.5	566.7
142.5°	583.1	583.7	584.2	584.9	585.4	585.9	586.5	586.9	587.5	587.6	587.8
145°	614.4	615.0	615.5	616.1	616.6	617.0	617.3	617.8	618.2	618.2	618.2
147.5°	643.2	643.5	643.8	644.0	644.4	644.8	645.1	645.4	645.7	646.0	646.3
150°	662.0	661.9	661.8	661.6	661.9	662.4	663.0	663.5	664.1	664.1	664.1
152.5°	678.3	678.4	678.7	678.8	679.1	679.2	679.5	679.7	679.9	680.2	680.6
155°	702.4	702.4	702.4	702.4	702.5	702.7	702.8	702.9	703.1	703.6	704.2
157.5°	724.0	723.7	723.3	723.0	722.9	723.1	723.3	723.3	723.5	724.1	724.6
160°	736.7	736.3	735.9	735.5	735.4	735.5	735.6	735.8	735.9	736.5	737.0
162.5°	748.2	747.9	747.7	747.3	747.2	747.2	747.3	747.3	747.3	748.0	748.6
165°	763.5	763.3	763.0	762.7	762.6	762.7	762.9	763.0	763.2	763.7	764.3
167.5°	776.1	775.5	775.0	774.4	774.2	774.2	774.2	774.2	774.2	775.0	775.9
170°	783.1	782.5	782.0	781.4	781.1	781.1	781.1	781.1	781.1	782.0	782.8
172.5°	788.0	787.4	786.9	786.3	786.1	786.1	786.1	786.1	786.1	786.9	787.7
175°	793.6	793.1	792.5	791.9	791.6	791.6	791.6	791.6	791.6	792.5	793.3
177.5°	796.5	796.1	795.7	795.2	795.0	794.9	794.7	794.6	794.5	795.2	795.8
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0	796.0



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	7.7	8.1	7.7	7.5	7.6	7.9	8.2
90°	12.0	12.7	13.2	13.6	14.0	14.4	14.9
92.5°	26.5	27.4	28.0	28.4	28.6	28.9	29.2
95°	50.6	51.6	52.2	52.4	52.8	53.0	53.2
97.5°	78.7	79.6	80.1	80.2	80.4	80.6	80.8
100°	98.5	99.7	100.5	100.8	101.0	101.3	101.6
102.5°	118.7	120.0	120.9	121.3	121.6	122.0	122.4
105°	150.5	151.4	151.9	152.4	152.8	153.2	153.6
107.5°	185.1	185.5	185.7	185.7	185.6	185.6	185.6
110°	209.4	209.8	209.9	209.8	209.6	209.5	209.4



TEST NUMBER: P333533-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.7	233.7	233.4	233.1	232.9	232.7
115°	270.3	270.1	270.0	269.9	269.7	269.6	269.5
117.5°	307.7	307.8	307.6	307.0	306.5	305.9	305.4
120°	332.6	332.6	332.4	331.8	331.3	330.7	330.2
122.5°	357.1	357.0	356.7	356.2	355.8	355.4	355.0
125°	393.2	392.8	392.7	392.5	392.4	392.3	392.1
127.5°	429.2	429.1	428.9	428.6	428.3	428.1	427.8
130°	453.0	452.9	452.7	452.4	452.1	451.9	451.5
132.5°	475.8	475.7	475.4	475.1	474.7	474.3	473.9
135°	511.0	511.0	510.8	510.2	509.7	509.1	508.6
137.5°	545.3	545.5	545.3	544.5	543.9	543.2	542.5
140°	567.0	567.3	567.0	566.4	565.7	565.0	564.4
142.5°	588.0	588.1	587.9	587.2	586.5	585.8	585.1
145°	618.2	618.2	618.0	617.6	617.2	616.8	616.3
147.5°	646.7	647.1	646.7	645.8	644.8	644.0	643.0
150°	664.1	664.1	663.9	663.6	663.4	663.1	662.8
152.5°	680.9	681.2	681.1	680.6	680.2	679.7	679.1
155°	704.7	705.3	705.2	704.5	703.9	703.1	702.4
157.5°	725.2	725.7	725.6	724.6	723.7	722.8	721.9
160°	737.5	738.1	738.1	737.4	736.7	735.9	735.3
162.5°	749.3	750.0	749.9	749.1	748.3	747.5	746.7
165°	764.9	765.3	765.2	764.4	763.6	762.7	761.9
167.5°	776.7	777.5	777.4	776.7	775.8	774.9	774.0
170°	783.6	784.4	784.3	783.4	782.4	781.5	780.5
172.5°	788.5	789.4	789.4	788.5	787.7	786.8	785.9
175°	794.2	795.0	794.9	793.9	793.0	792.0	791.1
177.5°	796.5	797.2	797.1	796.3	795.6	794.8	794.0
180°	796.0	796.0	796.0	796.0	796.0	796.0	796.0

(END OF REPORT)