

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333534-927

Luminaire Tested: **S125RDIP-S610D810U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333534-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D810U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4204.9 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45																												
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39																												
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38	33																												
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	28																												
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28	25																												
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	22																												
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19																												
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17																												
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15																												
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14																												
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	17	14	12																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.7
10°-20°	206.0	4.9
20°-30°	326.6	7.8
30°-40°	393.9	9.4
40°-50°	351.8	8.4
50°-60°	269.8	6.4
60°-70°	175.3	4.2
70°-80°	85.2	2.0
80°-90°	22.1	0.5
90°-100°	222.7	5.3
100°-110°	478.7	11.4
110°-120°	449.3	10.7
120°-130°	364.1	8.7
130°-140°	292.2	6.9
140°-150°	220.5	5.2
150°-160°	155.2	3.7
160°-170°	91.5	2.2
170°-180°	29.8	0.7
0°-30°	602.9	14.3
0°-40°	996.8	23.7
0°-60°	1618.4	38.5
0°-90°	1901.0	45.2
90°-120°	1150.7	27.4
90°-150°	2027.5	48.2
90°-180°	2304.0	54.8
0°-180°	4204.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	14	1	14	1	14	10
95°	146	20	146	20	146	206
105°	821	70	821	70	821	816
115°	914	125	914	125	914	893
125°	720	173	720	173	720	652
135°	598	203	598	203	598	464
145°	472	237	472	237	472	300
155°	396	270	396	270	396	184
165°	347	295	347	295	347	99
175°	312	307	312	307	312	30
180°	307	307	307	307	307	



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	8.2	7.9	7.5	7.5	7.8	8.0	7.7	7.3	7.1	7.1	7.1
90°	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2	10.5	9.9	8.6
92.5°	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8	161.7	199.7	202.9
95°	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4	537.0	548.8	447.8
97.5°	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3	679.5	586.1	399.9
100°	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8	714.2	559.4	356.8
102.5°	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0	693.4	512.2	324.1
105°	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5	626.9	449.1	292.4
107.5°	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6	559.0	405.6	279.0
110°	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1	520.3	385.2	275.0



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5	491.5	373.4	275.0
115°	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4	460.2	360.5	276.9
117.5°	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5	441.5	354.2	281.0
120°	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6	431.1	351.2	284.9
122.5°	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3	422.2	348.7	288.4
125°	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8	410.0	345.6	294.2
127.5°	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0	398.9	344.1	300.8
130°	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6	391.5	343.2	304.8
132.5°	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2	385.6	343.2	309.2
135°	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1	378.4	343.2	315.3
137.5°	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5	372.2	343.9	320.8
140°	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0	369.2	344.4	323.3
142.5°	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6	366.7	344.9	324.8
145°	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1	363.0	344.4	326.5
147.5°	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2	359.1	342.8	327.0
150°	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8	356.2	341.3	327.0
152.5°	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8	352.7	339.3	326.5
155°	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4	346.9	335.7	325.2
157.5°	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0	341.4	332.0	323.6
160°	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0	337.0	329.5	322.1
162.5°	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5	333.0	326.5	320.6
165°	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0	327.0	322.1	318.4
167.5°	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8	321.2	317.7	314.9
170°	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8	317.7	315.3	313.4
172.5°	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4	314.3	312.3	311.4
175°	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6	309.7	309.1	309.1
177.5°	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2	307.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	7.1	6.9	7.1	6.7	6.3	7.2	7.7	7.8	7.4	7.2	7.0
90°	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6	1.3	2.5	3.7
92.5°	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5	9.2	14.3	22.0
95°	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4	21.1	26.0	32.8
97.5°	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9	34.7	38.2	45.0
100°	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3	44.6	47.1	53.9
102.5°	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8	54.5	56.5	63.8
105°	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0	70.0	73.1	79.3
107.5°	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9	87.1	90.1	95.1
110°	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3	98.5	100.9	106.5



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6	109.9	111.9	117.4
115°	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1	126.4	128.3	133.8
117.5°	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0	141.9	143.9	149.4
120°	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9	151.8	154.2	159.8
122.5°	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3	161.7	163.7	169.2
125°	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4	174.7	177.8	183.3
127.5°	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7	185.6	189.6	196.6
130°	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1	192.0	196.9	205.0
132.5°	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1	197.5	203.4	212.5
135°	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2	205.7	213.1	223.0
137.5°	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3	215.2	222.1	232.0
140°	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3	221.1	228.5	238.4
142.5°	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2	227.6	234.5	244.4
145°	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6	237.8	244.1	252.7
147.5°	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5	248.3	253.6	261.7
150°	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0	255.2	259.5	267.6
152.5°	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9	261.7	265.5	272.5
155°	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1	270.1	273.8	280.0
157.5°	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2	278.1	281.1	286.4
160°	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7	283.0	285.6	289.9
162.5°	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1	287.6	290.0	293.8
165°	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9	293.6	295.5	298.6
167.5°	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3	298.7	299.8	301.5
170°	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3	301.7	302.3	303.5
172.5°	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3	303.2	303.7	305.0
175°	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6	305.4	306.0	306.6
177.5°	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7	306.7	306.7	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	7.0	7.3	7.1	7.8	7.3	7.8	7.9	7.8	7.9	8.0	8.0
90°	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2	11.8	12.4	13.6
92.5°	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8	79.7	60.0	50.8
95°	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4	351.2	275.0	223.0
97.5°	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3	597.2	523.0	450.7
100°	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8	731.5	667.7	603.3
102.5°	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0	813.8	783.2	739.6
105°	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5	860.4	887.6	880.8
107.5°	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6	818.9	888.8	921.1
110°	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1	771.7	859.1	911.7



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5	725.2	813.5	875.6
115°	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4	658.5	743.3	810.8
117.5°	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5	612.2	685.3	747.3
120°	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6	586.0	654.1	708.6
122.5°	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3	567.1	627.8	678.9
125°	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8	542.0	595.9	640.5
127.5°	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0	517.9	568.2	610.0
130°	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6	501.1	549.4	589.7
132.5°	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2	485.2	529.1	567.8
135°	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1	460.8	500.5	535.8
137.5°	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5	439.0	472.0	501.9
140°	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0	426.1	454.6	480.6
142.5°	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6	415.3	439.7	462.3
145°	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1	401.4	420.6	437.3
147.5°	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2	389.8	404.6	417.2
150°	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8	383.4	395.1	406.3
152.5°	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8	377.0	387.8	396.4
155°	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4	367.3	376.0	382.8
157.5°	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0	358.1	364.8	370.2
160°	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0	351.2	357.4	361.7
162.5°	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5	345.2	350.5	354.3
165°	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0	336.4	340.1	343.2
167.5°	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8	327.6	330.5	332.7
170°	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8	322.7	324.6	325.8
172.5°	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4	318.2	319.6	320.4
175°	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6	311.6	312.8	312.8
177.5°	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2	308.7	308.7	308.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	8.2	8.0	8.2	8.2	8.2	8.0	8.2	8.0	8.0	7.9	7.8
90°	13.6	13.6	14.3	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2
92.5°	42.9	41.4	40.5	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8
95°	179.0	160.4	155.5	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4
97.5°	412.4	377.7	359.7	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3
100°	560.5	515.9	493.1	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8
102.5°	693.9	662.1	637.2	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0
105°	860.9	840.5	828.1	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5
107.5°	931.2	931.1	927.0	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6
110°	939.6	951.4	955.8	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	916.3	936.5	947.3	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5
115°	859.1	888.8	906.2	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4
117.5°	795.6	826.2	843.5	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5
120°	754.4	784.2	800.9	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6
122.5°	719.8	747.0	763.7	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3
125°	675.2	700.5	714.2	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8
127.5°	641.4	663.8	676.8	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0
130°	620.7	641.1	653.5	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6
132.5°	598.8	619.2	630.7	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2
135°	563.0	583.4	594.6	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1
137.5°	526.4	544.9	555.2	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5
140°	503.6	519.7	528.9	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0
142.5°	481.8	495.4	504.2	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6
145°	452.2	462.7	469.5	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1
147.5°	429.0	437.4	441.4	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2
150°	415.7	423.0	425.6	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8
152.5°	404.3	410.2	412.6	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8
155°	389.0	393.3	395.1	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4
157.5°	375.0	378.6	380.3	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0
160°	366.1	369.2	370.4	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0
162.5°	357.7	360.2	360.5	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5
165°	345.6	346.9	346.9	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0
167.5°	334.0	335.1	334.6	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8
170°	327.0	327.6	327.6	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8
172.5°	320.6	321.7	320.8	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4
175°	312.8	313.4	312.2	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6
177.5°	308.2	308.7	307.2	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	7.9	7.8	7.3	7.8	7.1	7.3	7.0	7.0	7.2	7.4	7.8
90°	10.5	9.9	8.6	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6
92.5°	161.7	199.7	202.9	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5
95°	537.0	548.8	447.8	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4
97.5°	679.5	586.1	399.9	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9
100°	714.2	559.4	356.8	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3
102.5°	693.4	512.2	324.1	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8
105°	626.9	449.1	292.4	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0
107.5°	559.0	405.6	279.0	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9
110°	520.3	385.2	275.0	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	373.4	275.0	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6
115°	460.2	360.5	276.9	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1
117.5°	441.5	354.2	281.0	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0
120°	431.1	351.2	284.9	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9
122.5°	422.2	348.7	288.4	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3
125°	410.0	345.6	294.2	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4
127.5°	398.9	344.1	300.8	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7
130°	391.5	343.2	304.8	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1
132.5°	385.6	343.2	309.2	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1
135°	378.4	343.2	315.3	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2
137.5°	372.2	343.9	320.8	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3
140°	369.2	344.4	323.3	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3
142.5°	366.7	344.9	324.8	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2
145°	363.0	344.4	326.5	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6
147.5°	359.1	342.8	327.0	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5
150°	356.2	341.3	327.0	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0
152.5°	352.7	339.3	326.5	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9
155°	346.9	335.7	325.2	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1
157.5°	341.4	332.0	323.6	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2
160°	337.0	329.5	322.1	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7
162.5°	333.0	326.5	320.6	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1
165°	327.0	322.1	318.4	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9
167.5°	321.2	317.7	314.9	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3
170°	317.7	315.3	313.4	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3
172.5°	314.3	312.3	311.4	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3
175°	309.7	309.1	309.1	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6
177.5°	307.7	307.2	307.2	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.7	7.2	6.3	6.7	7.1	6.9	7.1	7.1	7.1	7.1	7.3
90°	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2
92.5°	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8
95°	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4
97.5°	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3
100°	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8
102.5°	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0
105°	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5
107.5°	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6
110°	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5
115°	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4
117.5°	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5
120°	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6
122.5°	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3
125°	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8
127.5°	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0
130°	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6
132.5°	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2
135°	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1
137.5°	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5
140°	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0
142.5°	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6
145°	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1
147.5°	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2
150°	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8
152.5°	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8
155°	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4
157.5°	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0
160°	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0
162.5°	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5
165°	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0
167.5°	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8
170°	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8
172.5°	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4
175°	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6
177.5°	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	7.7	8.0	7.8	7.5	7.5	7.9	8.2
90°	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333534-927

CATALOG NUMBER: S125RDIP-S610D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)