

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333570-927

Luminaire Tested: **S125RDIP-S850D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333570-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1035U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5539.8 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47																												
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40																												
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	42	41	39	34																												
3	81	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34	29																												
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	31	29	26																												
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22																												
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20																												
7	58	46	39	33	54	43	36	31	37	31	28	31	27	24	26	23	20	18																												
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	23	20	18	16																												
9	51	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16	14																												
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6471	6471	6471	6471
5°	7445	6480	5723	6480
10°	8540	6447	5050	6447
15°	9225	6381	4488	6381
20°	10172	6304	4144	6304
25°	11771	6202	3846	6202
30°	12810	6095	3650	6095
35°	10806	5970	3470	5970
40°	7546	5746	3315	5746
45°	5598	5444	3163	5444
50°	4464	5129	3033	5129
55°	3788	4738	2917	4738
60°	3273	4389	2731	4389
65°	2916	4010	2350	4010
70°	2564	3675	2143	3675
75°	2218	3182	2011	3182
80°	1681	2678	1681	2678
85°	1401	2104	1586	2104



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.1	1.7
10°-20°	281.6	5.1
20°-30°	446.5	8.1
30°-40°	538.4	9.7
40°-50°	480.8	8.7
50°-60°	368.7	6.7
60°-70°	239.6	4.3
70°-80°	116.5	2.1
80°-90°	30.0	0.5
90°-100°	284.3	5.1
100°-110°	611.2	11.0
110°-120°	573.6	10.4
120°-130°	464.9	8.4
130°-140°	373.0	6.7
140°-150°	281.5	5.1
150°-160°	198.2	3.6
160°-170°	116.8	2.1
170°-180°	38.0	0.7
0°-30°	824.2	14.9
0°-40°	1362.6	24.6
0°-60°	2212.2	39.9
0°-90°	2598.3	46.9
90°-120°	1469.1	26.5
90°-150°	2588.5	46.7
90°-180°	2941.0	53.1
0°-180°	5539.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1002	1002	1002	1002	1002	
5°	1148	1000	883	1000	1148	115
15°	1380	954	671	954	1380	395
25°	1652	870	540	870	1652	758
35°	1371	757	440	757	1371	828
45°	613	596	346	596	613	489
55°	336	421	259	421	336	305
65°	191	262	154	262	191	190
75°	89	128	81	128	89	95
85°	19	28	21	28	19	22
90°	18	1	18	1	18	13
95°	186	26	186	26	186	263
105°	1048	89	1048	89	1048	1042
115°	1167	160	1167	160	1167	1140
125°	920	221	920	221	920	832
135°	764	259	764	259	764	592
145°	603	302	603	302	603	383
155°	505	345	505	345	505	236
165°	443	376	443	376	443	127
175°	398	391	398	391	398	39
180°	392	392	392	392	392	



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1054.0	1053.4	1054.7	1051.1	1051.4	1045.8	1045.8	1041.5	1035.9	1031.7	1029.7
5°	1148.4	1149.3	1147.6	1141.5	1137.3	1131.2	1124.2	1111.8	1101.5	1091.7	1083.9
7.5°	1245.7	1246.3	1240.9	1239.0	1228.6	1221.0	1205.5	1188.7	1173.8	1154.8	1140.4
10°	1302.3	1301.9	1296.2	1291.6	1282.5	1271.1	1255.8	1236.0	1217.6	1197.0	1177.3
12.5°	1335.2	1334.1	1332.3	1326.8	1318.4	1308.2	1295.3	1275.9	1253.1	1230.6	1207.5
15°	1379.7	1376.7	1371.4	1364.4	1352.5	1340.5	1326.2	1308.9	1287.1	1261.6	1240.2
17.5°	1434.6	1434.6	1426.5	1416.7	1400.5	1379.5	1357.2	1329.4	1299.7	1271.7	1248.9
20°	1480.0	1478.8	1470.5	1451.6	1433.1	1406.8	1381.2	1347.1	1310.9	1274.3	1245.9
22.5°	1545.2	1542.0	1533.4	1508.6	1479.9	1446.0	1406.9	1365.2	1321.4	1279.9	1242.7
25°	1651.9	1649.5	1632.6	1603.9	1563.5	1511.2	1460.2	1403.1	1340.1	1285.5	1240.2
27.5°	1725.0	1722.3	1709.8	1685.8	1648.7	1593.7	1524.6	1448.3	1369.7	1294.4	1229.2
30°	1717.8	1723.9	1722.3	1711.2	1683.2	1633.9	1570.1	1484.2	1390.8	1302.3	1224.6
32.5°	1614.4	1619.9	1634.4	1656.2	1657.9	1638.2	1590.5	1511.1	1414.4	1313.8	1220.9
35°	1370.6	1378.0	1406.0	1450.0	1507.5	1555.7	1565.6	1522.8	1436.0	1327.8	1215.5
37.5°	1053.7	1094.2	1117.7	1164.0	1251.0	1339.6	1424.7	1456.0	1419.1	1322.1	1206.7
40°	895.1	904.9	946.9	999.2	1072.4	1164.5	1285.9	1373.5	1376.3	1308.9	1192.9
42.5°	766.0	778.6	807.4	849.1	911.8	1003.9	1129.2	1244.8	1298.4	1272.7	1174.8
45°	612.9	622.3	643.3	675.4	723.6	799.6	907.4	1041.1	1147.2	1188.7	1126.2
47.5°	503.5	508.6	526.9	551.3	586.9	642.4	725.8	841.9	969.2	1058.4	1049.6
50°	444.3	450.0	464.0	482.5	512.5	559.4	626.1	722.7	854.0	963.0	984.8
52.5°	398.2	403.0	411.7	429.2	453.9	490.0	543.8	631.2	749.3	865.2	915.6
55°	336.4	339.8	346.7	356.6	376.4	402.3	448.8	509.2	604.7	721.5	795.5
57.5°	285.7	287.2	291.8	300.9	314.5	333.4	367.0	418.3	486.7	591.9	673.6
60°	253.4	255.0	260.8	267.0	277.7	294.9	321.2	357.0	422.9	509.6	592.3
62.5°	227.8	228.7	231.2	237.3	246.7	260.1	280.7	310.0	362.3	438.6	516.7
65°	190.8	191.3	192.1	197.0	202.8	212.7	226.2	246.8	286.3	343.9	413.0
67.5°	155.5	156.1	158.9	160.7	166.7	171.8	179.8	195.6	223.4	262.2	315.9
70°	135.8	135.3	138.2	140.3	142.4	148.5	153.8	166.6	183.9	213.5	258.3
72.5°	117.3	116.2	117.5	118.2	121.0	125.2	130.5	138.3	151.6	172.0	206.4
75°	88.9	89.3	89.3	90.1	92.1	93.8	95.5	99.6	106.9	120.5	139.0
77.5°	62.3	61.7	63.5	63.7	64.9	66.7	68.1	69.8	72.8	78.4	87.9
80°	45.2	45.2	45.6	46.9	46.5	47.3	49.4	51.0	54.7	58.0	61.3
82.5°	34.7	34.4	34.8	35.0	34.9	35.8	36.5	36.8	38.3	39.9	42.2
85°	18.9	18.9	19.3	19.3	19.7	19.7	20.1	20.1	20.1	20.6	21.0
87.5°	10.9	10.5	10.1	10.1	10.4	10.7	10.2	9.7	9.6	9.4	9.4
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3	13.5	12.7	11.1
92.5°	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1	206.4	254.9	259.0
95°	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6	685.6	700.7	571.8
97.5°	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8	867.5	748.3	510.6
100°	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7	911.8	714.1	455.5
102.5°	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1	885.3	654.0	413.8
105°	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1	800.3	573.3	373.3
107.5°	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9	713.6	517.8	356.2
110°	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1	664.2	491.9	351.1



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2	627.6	476.7	351.1
115°	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0	587.6	460.3	353.5
117.5°	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0	563.7	452.2	358.7
120°	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2	550.4	448.4	363.8
122.5°	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1	539.0	445.2	368.2
125°	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3	523.6	441.2	375.7
127.5°	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0	509.3	439.3	384.0
130°	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2	499.8	438.1	389.1
132.5°	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4	492.2	438.1	394.7
135°	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8	483.2	438.1	402.5
137.5°	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4	475.2	439.0	409.6
140°	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9	471.3	439.7	412.8
142.5°	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7	468.2	440.3	414.7
145°	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9	463.4	439.7	416.8
147.5°	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8	458.5	437.6	417.6
150°	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1	454.7	435.7	417.6
152.5°	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8	450.3	433.2	416.9
155°	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3	442.8	428.6	415.2
157.5°	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8	435.9	423.9	413.1
160°	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5	430.2	420.7	411.2
162.5°	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6	425.2	416.9	409.3
165°	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9	417.6	411.2	406.5
167.5°	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7	410.1	405.7	402.0
170°	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6	405.7	402.5	400.1
172.5°	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9	401.2	398.7	397.6
175°	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8	395.4	394.6	394.6
177.5°	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5	392.8	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1029.7	1027.4	1023.1	1019.1	1014.2	1010.0	1006.9	1003.4	998.7	993.2	988.6
5°	1075.2	1066.2	1054.2	1044.0	1030.8	1020.6	1009.9	999.6	989.3	976.1	964.6
7.5°	1125.8	1107.1	1088.9	1066.0	1045.3	1026.7	1009.0	991.0	973.4	954.7	936.7
10°	1156.7	1134.1	1109.0	1080.1	1053.8	1028.7	1005.8	983.1	959.3	938.3	915.6
12.5°	1185.7	1156.4	1127.8	1091.4	1059.8	1029.1	999.8	971.6	946.1	918.9	894.6
15°	1211.8	1183.0	1151.0	1106.5	1062.5	1025.5	990.9	954.3	922.7	892.2	865.1
17.5°	1221.9	1191.8	1154.4	1111.7	1063.7	1017.1	972.6	932.4	895.2	859.7	829.2
20°	1218.0	1188.7	1150.5	1109.8	1058.4	1009.9	961.7	917.3	875.8	838.3	805.8
22.5°	1208.4	1178.2	1141.3	1098.3	1049.5	998.0	946.6	899.2	855.6	816.9	781.5
25°	1194.1	1153.0	1115.2	1073.2	1026.7	975.7	922.7	870.4	823.9	784.4	745.8
27.5°	1179.2	1127.9	1079.7	1038.1	989.0	943.4	892.3	838.7	789.9	749.6	710.0
30°	1165.8	1108.2	1055.1	1007.8	961.3	918.1	869.6	817.3	767.1	725.6	685.3
32.5°	1149.0	1087.7	1029.4	974.9	930.0	887.2	843.3	793.3	744.4	701.6	660.6
35°	1127.9	1049.7	986.4	928.4	878.6	837.1	797.6	757.2	708.3	663.9	624.0
37.5°	1100.3	1011.5	938.3	875.1	822.6	780.9	749.7	712.9	668.2	625.7	588.6
40°	1083.5	983.9	903.7	841.2	786.1	742.0	712.9	681.6	640.9	600.9	564.0
42.5°	1061.1	958.6	868.9	803.7	748.2	705.8	676.3	649.0	614.9	577.3	537.7
45°	1017.2	909.5	815.3	745.4	689.4	647.8	620.3	596.0	570.1	535.6	501.0
47.5°	960.1	858.3	759.6	683.3	628.5	589.9	563.2	544.1	525.5	496.1	462.6
50°	914.4	816.1	719.9	645.8	587.4	550.8	525.7	510.5	493.6	466.8	438.9
52.5°	860.5	772.7	678.3	602.7	547.6	513.3	489.2	474.0	460.0	438.2	411.6
55°	775.4	698.5	612.0	543.4	492.8	458.2	435.2	420.8	412.6	394.0	373.1
57.5°	677.2	622.1	545.9	479.7	435.0	400.8	384.0	371.7	362.4	349.3	334.5
60°	608.8	570.1	501.8	438.9	397.8	365.3	350.1	339.8	331.1	320.0	308.5
62.5°	539.3	511.2	451.8	397.8	359.9	332.7	318.5	309.2	299.2	291.8	280.5
65°	446.3	421.2	380.1	337.7	302.8	280.9	270.7	262.4	256.3	248.0	240.2
67.5°	347.1	337.0	308.6	279.4	254.3	234.9	226.0	220.2	212.9	207.9	202.6
70°	286.3	281.4	261.2	241.9	218.4	205.3	197.0	194.6	185.5	180.6	176.9
72.5°	232.3	230.0	218.4	205.0	188.5	177.0	169.4	166.6	160.8	156.9	154.5
75°	159.1	160.0	158.0	149.3	143.1	135.8	129.1	127.5	123.4	120.1	118.0
77.5°	100.7	104.9	105.0	104.6	102.2	97.7	94.9	93.7	89.7	88.4	87.9
80°	69.1	73.6	77.7	77.3	76.5	75.3	73.2	72.0	69.9	68.7	67.9
82.5°	46.1	50.3	53.7	55.9	55.8	54.6	53.2	52.6	52.1	51.3	51.1
85°	21.8	22.7	23.8	26.8	28.8	29.2	28.8	28.4	27.2	27.6	28.0
87.5°	9.6	9.3	9.5	9.2	8.6	9.8	10.5	10.7	10.2	9.8	9.5
90°	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8	1.6	3.2	4.8
92.5°	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7	11.7	18.4	28.1
95°	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1	26.9	33.2	41.9
97.5°	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3	44.3	48.7	57.4
100°	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4	57.0	60.1	68.8
102.5°	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7	69.6	72.1	81.4
105°	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4	89.4	93.3	101.2
107.5°	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6	111.2	114.9	121.4
110°	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1	125.7	128.9	136.0



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7	140.3	142.8	150.0
115°	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8	161.3	163.7	170.8
117.5°	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7	181.1	183.6	190.8
120°	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4	193.8	196.9	204.1
122.5°	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7	206.4	208.9	216.0
125°	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4	223.0	227.0	234.1
127.5°	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6	236.9	242.0	251.0
130°	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8	245.2	251.5	261.7
132.5°	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1	252.1	259.7	271.2
135°	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4	262.5	272.0	284.7
137.5°	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4	274.7	283.6	296.3
140°	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0	282.3	291.8	304.4
142.5°	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8	290.6	299.4	312.0
145°	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1	303.6	311.6	322.7
147.5°	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0	317.0	323.8	334.1
150°	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2	325.8	331.4	341.7
152.5°	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1	334.1	339.0	347.9
155°	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8	344.8	349.5	357.4
157.5°	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2	355.1	358.9	365.7
160°	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2	361.4	364.6	370.1
162.5°	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9	367.1	370.3	375.2
165°	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4	374.9	377.2	381.2
167.5°	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1	381.4	382.8	385.0
170°	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0	385.2	386.0	387.5
172.5°	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5	387.1	387.9	389.4
175°	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4	389.8	390.6	391.4
177.5°	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8	391.6	391.6	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	985.2	980.6	977.3	970.7	966.1	964.2	960.6	959.6	963.2	960.6	960.2
5°	955.9	944.0	934.5	925.1	914.8	908.2	898.3	896.8	894.2	890.6	889.7
7.5°	920.8	905.3	893.1	877.5	863.9	852.9	840.6	834.8	831.6	826.8	820.4
10°	897.1	878.6	862.1	846.5	829.7	816.1	803.7	794.3	788.1	782.4	779.9
12.5°	873.8	854.9	833.9	814.9	796.1	780.9	767.2	761.0	754.2	747.5	741.7
15°	837.5	812.4	789.3	767.5	751.5	735.1	721.9	712.9	702.6	699.7	688.6
17.5°	799.0	774.4	747.4	724.5	705.8	687.8	673.3	663.0	655.3	644.7	639.5
20°	775.0	745.8	719.5	698.5	677.9	656.5	641.7	633.0	625.7	617.0	612.9
22.5°	749.3	720.7	693.8	669.2	648.2	627.2	616.7	607.7	599.3	591.4	585.9
25°	711.6	682.9	654.4	628.9	607.1	591.9	579.6	569.3	564.7	557.0	551.2
27.5°	674.4	643.7	614.3	588.9	571.8	556.7	546.6	538.4	530.3	523.5	518.5
30°	650.3	619.1	587.0	566.8	548.7	534.3	523.2	515.4	509.2	503.0	499.4
32.5°	626.3	594.1	565.6	543.8	526.6	514.3	502.8	495.4	488.9	482.0	477.7
35°	587.8	554.9	531.9	510.5	493.6	482.1	474.3	463.6	458.2	453.3	448.8
37.5°	552.0	521.4	496.5	477.8	463.1	451.6	441.6	435.8	429.2	424.8	421.0
40°	525.7	497.7	475.1	455.3	444.7	431.9	422.5	415.0	410.1	404.3	400.2
42.5°	502.0	476.0	454.0	436.3	422.9	412.2	403.1	395.6	389.4	385.2	381.8
45°	468.5	442.6	421.2	404.7	392.4	382.1	372.6	369.0	360.8	355.8	354.2
47.5°	433.9	410.7	390.1	374.9	362.3	352.5	343.6	336.0	331.5	326.7	324.1
50°	410.5	388.3	369.0	354.2	341.8	331.1	322.9	318.0	311.8	307.3	304.0
52.5°	387.1	366.6	347.3	333.1	322.4	311.7	302.5	297.5	291.8	288.8	286.5
55°	353.8	331.9	315.5	301.5	290.4	280.5	271.9	267.0	263.2	260.4	259.5
57.5°	315.9	298.7	283.4	270.8	259.2	249.9	242.3	237.7	234.4	233.9	231.5
60°	291.2	275.6	261.6	248.0	238.1	229.5	222.9	217.6	214.3	213.9	213.1
62.5°	266.6	251.6	238.6	226.6	217.8	209.5	203.2	197.2	195.2	193.1	191.4
65°	230.0	216.3	205.7	196.2	186.7	179.7	173.6	169.8	165.3	162.9	158.4
67.5°	194.0	183.5	173.2	165.2	157.8	151.1	146.0	140.5	137.4	135.5	132.2
70°	170.3	162.1	151.8	143.1	137.4	132.1	127.9	121.8	119.7	118.0	116.4
72.5°	147.9	140.7	132.1	125.1	119.3	114.2	109.5	106.6	104.6	102.9	102.0
75°	116.4	109.4	102.0	97.0	93.0	88.9	86.3	84.3	83.5	83.1	81.4
77.5°	85.5	81.8	75.8	71.9	69.2	67.6	65.4	64.2	64.2	62.3	61.8
80°	65.4	63.4	58.4	56.8	54.7	53.1	51.8	49.7	47.7	46.9	45.6
82.5°	48.6	46.6	44.6	42.0	40.2	39.2	38.0	37.2	37.5	36.4	35.8
85°	25.9	23.8	23.1	22.7	21.8	22.7	22.2	21.8	21.4	21.0	21.4
87.5°	9.5	9.8	9.7	10.6	9.7	10.5	10.6	10.4	10.5	10.7	10.7
90°	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3	15.1	15.8	17.4
92.5°	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1	101.7	76.5	64.9
95°	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6	448.4	351.1	284.7
97.5°	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8	762.5	667.7	575.4
100°	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7	934.0	852.5	770.2
102.5°	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1	1038.9	999.9	944.2
105°	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1	1098.4	1133.2	1124.5
107.5°	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9	1045.4	1134.8	1176.1
110°	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1	985.3	1096.9	1164.1



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2	925.9	1038.6	1117.9
115°	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0	840.7	949.0	1035.1
117.5°	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0	781.6	875.0	954.0
120°	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2	748.1	835.1	904.7
122.5°	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1	724.1	801.5	866.7
125°	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3	692.0	760.7	817.7
127.5°	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0	661.3	725.5	778.8
130°	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2	639.8	701.5	752.9
132.5°	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4	619.5	675.5	725.0
135°	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8	588.4	639.0	684.0
137.5°	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4	560.5	602.6	640.9
140°	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9	544.1	580.4	613.7
142.5°	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7	530.1	561.5	590.3
145°	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9	512.5	536.9	558.3
147.5°	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8	497.7	516.6	532.7
150°	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1	489.5	504.5	518.8
152.5°	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8	481.3	495.0	506.1
155°	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3	469.0	480.1	488.7
157.5°	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8	457.2	465.8	472.6
160°	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5	448.4	456.3	461.8
162.5°	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6	440.8	447.4	452.3
165°	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9	429.4	434.2	438.1
167.5°	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7	418.4	422.0	424.8
170°	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6	412.0	414.4	416.0
172.5°	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9	406.3	408.1	409.0
175°	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8	397.8	399.3	399.3
177.5°	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5	394.1	394.1	394.1
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	959.9	956.3	955.3	956.6	955.3	956.3	959.9	960.2	960.6	963.2	959.6
5°	885.6	881.5	883.5	882.7	883.5	881.5	885.6	889.7	890.6	894.2	896.8
7.5°	820.3	815.2	809.8	811.5	809.8	815.2	820.3	820.4	826.8	831.6	834.8
10°	774.5	770.5	767.9	770.0	767.9	770.5	774.5	779.9	782.4	788.1	794.3
12.5°	736.0	733.6	731.4	730.6	731.4	733.6	736.0	741.7	747.5	754.2	761.0
15°	683.7	678.7	676.7	671.3	676.7	678.7	683.7	688.6	699.7	702.6	712.9
17.5°	635.3	633.7	628.4	626.1	628.4	633.7	635.3	639.5	644.7	655.3	663.0
20°	606.7	605.1	599.8	603.0	599.8	605.1	606.7	612.9	617.0	625.7	633.0
22.5°	583.0	579.4	577.7	576.7	577.7	579.4	583.0	585.9	591.4	599.3	607.7
25°	549.5	544.2	542.2	539.7	542.2	544.2	549.5	551.2	557.0	564.7	569.3
27.5°	516.2	513.3	510.6	509.9	510.6	513.3	516.2	518.5	523.5	530.3	538.4
30°	494.4	491.5	489.5	489.5	489.5	491.5	494.4	499.4	503.0	509.2	515.4
32.5°	475.0	472.8	470.7	470.4	470.7	472.8	475.0	477.7	482.0	488.9	495.4
35°	446.7	443.5	442.6	440.1	442.6	443.5	446.7	448.8	453.3	458.2	463.6
37.5°	417.3	414.6	414.5	414.3	414.5	414.6	417.3	421.0	424.8	429.2	435.8
40°	398.6	396.6	396.1	393.2	396.1	396.6	398.6	400.2	404.3	410.1	415.0
42.5°	378.5	377.5	376.0	374.8	376.0	377.5	378.5	381.8	385.2	389.4	395.6
45°	351.3	348.4	348.4	346.3	348.4	348.4	351.3	354.2	355.8	360.8	369.0
47.5°	323.1	320.9	321.2	319.0	321.2	320.9	323.1	324.1	326.7	331.5	336.0
50°	304.4	303.2	302.8	301.9	302.8	303.2	304.4	304.0	307.3	311.8	318.0
52.5°	285.7	285.0	286.6	284.8	286.6	285.0	285.7	286.5	288.8	291.8	297.5
55°	260.4	259.1	261.6	259.1	261.6	259.1	260.4	259.5	260.4	263.2	267.0
57.5°	231.3	230.2	232.4	231.2	232.4	230.2	231.3	231.5	233.9	234.4	237.7
60°	212.2	209.8	211.0	211.4	211.0	209.8	212.2	213.1	213.9	214.3	217.6
62.5°	189.6	188.1	188.9	187.1	188.9	188.1	189.6	191.4	193.1	195.2	197.2
65°	157.6	156.3	154.6	153.8	154.6	156.3	157.6	158.4	162.9	165.3	169.8
67.5°	132.4	129.4	129.4	130.0	129.4	129.4	132.4	132.2	135.5	137.4	140.5
70°	113.9	113.9	113.5	113.5	113.5	113.9	113.9	116.4	118.0	119.7	121.8
72.5°	101.1	100.8	100.1	99.7	100.1	100.8	101.1	102.0	102.9	104.6	106.6
75°	81.4	81.8	81.0	80.6	81.0	81.8	81.4	81.4	83.1	83.5	84.3
77.5°	60.1	58.4	59.3	58.4	59.3	58.4	60.1	61.8	62.3	64.2	64.2
80°	45.6	45.2	46.5	45.2	46.5	45.2	45.6	45.6	46.9	47.7	49.7
82.5°	36.1	35.7	36.3	35.4	36.3	35.7	36.1	35.8	36.4	37.5	37.2
85°	21.8	21.4	21.0	21.4	21.0	21.4	21.8	21.4	21.0	21.4	21.8
87.5°	11.0	10.7	10.9	10.9	10.9	10.7	11.0	10.7	10.7	10.5	10.4
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.1	14.3
92.5°	54.7	52.8	51.7	50.5	51.7	52.8	54.7	64.9	76.5	101.7	140.1
95°	228.5	204.9	198.5	185.8	198.5	204.9	228.5	284.7	351.1	448.4	568.6
97.5°	526.6	482.2	459.3	449.2	459.3	482.2	526.6	575.4	667.7	762.5	846.8
100°	715.7	658.8	629.5	616.9	629.5	658.8	715.7	770.2	852.5	934.0	972.7
102.5°	885.9	845.4	813.6	804.1	813.6	845.4	885.9	944.2	999.9	1038.9	1015.1
105°	1099.2	1073.2	1057.3	1047.8	1057.3	1073.2	1099.2	1124.5	1133.2	1098.4	990.1
107.5°	1188.9	1188.7	1183.5	1177.2	1183.5	1188.7	1188.9	1176.1	1134.8	1045.4	900.9
110°	1199.7	1214.7	1220.2	1220.2	1220.2	1214.7	1199.7	1164.1	1096.9	985.3	835.1



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1169.9	1195.7	1209.5	1215.1	1209.5	1195.7	1169.9	1117.9	1038.6	925.9	783.2
115°	1096.9	1134.8	1157.0	1167.3	1157.0	1134.8	1096.9	1035.1	949.0	840.7	718.0
117.5°	1015.7	1054.9	1076.9	1083.2	1076.9	1054.9	1015.7	954.0	875.0	781.6	676.0
120°	963.2	1001.2	1022.5	1028.9	1022.5	1001.2	963.2	904.7	835.1	748.1	653.2
122.5°	918.9	953.7	975.1	980.8	975.1	953.7	918.9	866.7	801.5	724.1	636.1
125°	862.0	894.4	911.8	919.7	911.8	894.4	862.0	817.7	760.7	692.0	611.3
127.5°	819.0	847.6	864.0	867.5	864.0	847.6	819.0	778.8	725.5	661.3	586.0
130°	792.4	818.5	834.3	839.1	834.3	818.5	792.4	752.9	701.5	639.8	570.2
132.5°	764.5	790.7	805.2	810.6	805.2	790.7	764.5	725.0	675.5	619.5	554.4
135°	718.8	745.0	759.1	763.9	759.1	745.0	718.8	684.0	639.0	588.4	533.8
137.5°	672.0	695.8	708.9	714.1	708.9	695.8	672.0	640.9	602.6	560.5	516.4
140°	642.9	663.5	675.3	679.3	675.3	663.5	642.9	613.7	580.4	544.1	506.9
142.5°	615.1	632.5	643.7	647.1	643.7	632.5	615.1	590.3	561.5	530.1	498.7
145°	577.3	590.7	599.4	602.6	599.4	590.7	577.3	558.3	536.9	512.5	487.9
147.5°	547.7	558.5	563.6	565.0	563.6	558.5	547.7	532.7	516.6	497.7	477.8
150°	530.6	540.1	543.3	544.1	543.3	540.1	530.6	518.8	504.5	489.5	472.1
152.5°	516.1	523.7	526.8	527.6	526.8	523.7	516.1	506.1	495.0	481.3	465.8
155°	496.6	502.2	504.5	505.3	504.5	502.2	496.6	488.7	480.1	469.0	456.3
157.5°	478.8	483.3	485.5	485.4	485.5	483.3	478.8	472.6	465.8	457.2	446.8
160°	467.4	471.3	472.9	472.1	472.9	471.3	467.4	461.8	456.3	448.4	440.5
162.5°	456.6	459.9	460.3	460.1	460.3	459.9	456.6	452.3	447.4	440.8	433.6
165°	441.2	442.8	442.8	442.8	442.8	442.8	441.2	438.1	434.2	429.4	423.9
167.5°	426.4	427.9	427.2	427.1	427.2	427.9	426.4	424.8	422.0	418.4	414.7
170°	417.6	418.4	418.4	417.6	418.4	418.4	417.6	416.0	414.4	412.0	409.6
172.5°	409.3	410.7	409.5	408.7	409.5	410.7	409.3	409.0	408.1	406.3	403.9
175°	399.3	400.1	398.5	397.8	398.5	400.1	399.3	399.3	399.3	397.8	397.8
177.5°	393.5	394.1	392.2	392.2	392.2	394.1	393.5	394.1	394.1	394.1	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	960.6	964.2	966.1	970.7	977.3	980.6	985.2	988.6	993.2	998.7	1003.4
5°	898.3	908.2	914.8	925.1	934.5	944.0	955.9	964.6	976.1	989.3	999.6
7.5°	840.6	852.9	863.9	877.5	893.1	905.3	920.8	936.7	954.7	973.4	991.0
10°	803.7	816.1	829.7	846.5	862.1	878.6	897.1	915.6	938.3	959.3	983.1
12.5°	767.2	780.9	796.1	814.9	833.9	854.9	873.8	894.6	918.9	946.1	971.6
15°	721.9	735.1	751.5	767.5	789.3	812.4	837.5	865.1	892.2	922.7	954.3
17.5°	673.3	687.8	705.8	724.5	747.4	774.4	799.0	829.2	859.7	895.2	932.4
20°	641.7	656.5	677.9	698.5	719.5	745.8	775.0	805.8	838.3	875.8	917.3
22.5°	616.7	627.2	648.2	669.2	693.8	720.7	749.3	781.5	816.9	855.6	899.2
25°	579.6	591.9	607.1	628.9	654.4	682.9	711.6	745.8	784.4	823.9	870.4
27.5°	546.6	556.7	571.8	588.9	614.3	643.7	674.4	710.0	749.6	789.9	838.7
30°	523.2	534.3	548.7	566.8	587.0	619.1	650.3	685.3	725.6	767.1	817.3
32.5°	502.8	514.3	526.6	543.8	565.6	594.1	626.3	660.6	701.6	744.4	793.3
35°	474.3	482.1	493.6	510.5	531.9	554.9	587.8	624.0	663.9	708.3	757.2
37.5°	441.6	451.6	463.1	477.8	496.5	521.4	552.0	588.6	625.7	668.2	712.9
40°	422.5	431.9	444.7	455.3	475.1	497.7	525.7	564.0	600.9	640.9	681.6
42.5°	403.1	412.2	422.9	436.3	454.0	476.0	502.0	537.7	577.3	614.9	649.0
45°	372.6	382.1	392.4	404.7	421.2	442.6	468.5	501.0	535.6	570.1	596.0
47.5°	343.6	352.5	362.3	374.9	390.1	410.7	433.9	462.6	496.1	525.5	544.1
50°	322.9	331.1	341.8	354.2	369.0	388.3	410.5	438.9	466.8	493.6	510.5
52.5°	302.5	311.7	322.4	333.1	347.3	366.6	387.1	411.6	438.2	460.0	474.0
55°	271.9	280.5	290.4	301.5	315.5	331.9	353.8	373.1	394.0	412.6	420.8
57.5°	242.3	249.9	259.2	270.8	283.4	298.7	315.9	334.5	349.3	362.4	371.7
60°	222.9	229.5	238.1	248.0	261.6	275.6	291.2	308.5	320.0	331.1	339.8
62.5°	203.2	209.5	217.8	226.6	238.6	251.6	266.6	280.5	291.8	299.2	309.2
65°	173.6	179.7	186.7	196.2	205.7	216.3	230.0	240.2	248.0	256.3	262.4
67.5°	146.0	151.1	157.8	165.2	173.2	183.5	194.0	202.6	207.9	212.9	220.2
70°	127.9	132.1	137.4	143.1	151.8	162.1	170.3	176.9	180.6	185.5	194.6
72.5°	109.5	114.2	119.3	125.1	132.1	140.7	147.9	154.5	156.9	160.8	166.6
75°	86.3	88.9	93.0	97.0	102.0	109.4	116.4	118.0	120.1	123.4	127.5
77.5°	65.4	67.6	69.2	71.9	75.8	81.8	85.5	87.9	88.4	89.7	93.7
80°	51.8	53.1	54.7	56.8	58.4	63.4	65.4	67.9	68.7	69.9	72.0
82.5°	38.0	39.2	40.2	42.0	44.6	46.6	48.6	51.1	51.3	52.1	52.6
85°	22.2	22.7	21.8	22.7	23.1	23.8	25.9	28.0	27.6	27.2	28.4
87.5°	10.6	10.5	9.7	10.6	9.7	9.8	9.5	9.5	9.8	10.2	10.7
90°	13.5	12.7	11.1	10.3	8.7	7.9	6.3	4.8	3.2	1.6	0.8
92.5°	206.4	254.9	259.0	180.5	108.1	64.9	41.7	28.1	18.4	11.7	9.7
95°	685.6	700.7	571.8	353.5	179.5	94.9	59.3	41.9	33.2	26.9	26.1
97.5°	867.5	748.3	510.6	282.2	154.7	98.7	73.0	57.4	48.7	44.3	43.3
100°	911.8	714.1	455.5	256.2	153.4	107.6	83.8	68.8	60.1	57.0	55.4
102.5°	885.3	654.0	413.8	245.5	159.1	118.3	95.2	81.4	72.1	69.6	68.7
105°	800.3	573.3	373.3	241.2	170.8	136.0	113.9	101.2	93.3	89.4	89.4
107.5°	713.6	517.8	356.2	248.5	188.2	154.6	134.6	121.4	114.9	111.2	109.6
110°	664.2	491.9	351.1	255.4	200.9	168.4	147.9	136.0	128.9	125.7	124.1



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	627.6	476.7	351.1	264.3	212.9	181.7	161.8	150.0	142.8	140.3	138.7
115°	587.6	460.3	353.5	277.6	231.7	202.5	182.7	170.8	163.7	161.3	159.8
117.5°	563.7	452.2	358.7	292.8	251.0	223.3	204.2	190.8	183.6	181.1	178.7
120°	550.4	448.4	363.8	302.9	264.9	237.3	217.5	204.1	196.9	193.8	191.4
122.5°	539.0	445.2	368.2	314.3	278.2	250.6	230.8	216.0	208.9	206.4	204.7
125°	523.6	441.2	375.7	329.8	295.8	269.7	249.1	234.1	227.0	223.0	221.4
127.5°	509.3	439.3	384.0	344.0	312.7	287.6	267.0	251.0	242.0	236.9	234.6
130°	499.8	438.1	389.1	353.5	323.4	298.9	278.4	261.7	251.5	245.2	242.8
132.5°	492.2	438.1	394.7	361.7	333.6	309.0	288.5	271.2	259.7	252.1	249.1
135°	483.2	438.1	402.5	373.3	347.1	322.7	301.3	284.7	272.0	262.5	259.4
137.5°	475.2	439.0	409.6	381.8	356.8	334.5	312.5	296.3	283.6	274.7	272.4
140°	471.3	439.7	412.8	387.5	363.8	340.9	319.5	304.4	291.8	282.3	280.0
142.5°	468.2	440.3	414.7	390.6	368.2	346.5	326.5	312.0	299.4	290.6	288.8
145°	463.4	439.7	416.8	395.4	375.7	355.1	336.9	322.7	311.6	303.6	302.1
147.5°	458.5	437.6	417.6	398.2	380.4	362.3	346.3	334.1	323.8	317.0	316.0
150°	454.7	435.7	417.6	400.1	383.6	366.1	352.7	341.7	331.4	325.8	324.2
152.5°	450.3	433.2	416.9	401.4	386.7	370.6	358.4	347.9	339.0	334.1	333.1
155°	442.8	428.6	415.2	402.5	389.8	376.4	365.4	357.4	349.5	344.8	344.8
157.5°	435.9	423.9	413.1	403.3	392.5	381.0	372.6	365.7	358.9	355.1	355.2
160°	430.2	420.7	411.2	403.3	393.8	383.6	376.4	370.1	364.6	361.4	362.2
162.5°	425.2	416.9	409.3	402.7	395.1	386.1	380.2	375.2	370.3	367.1	367.9
165°	417.6	411.2	406.5	401.7	395.4	389.1	384.4	381.2	377.2	374.9	376.4
167.5°	410.1	405.7	402.0	399.8	395.4	390.1	387.2	385.0	382.8	381.4	382.1
170°	405.7	402.5	400.1	398.5	395.4	391.4	389.1	387.5	386.0	385.2	386.0
172.5°	401.2	398.7	397.6	397.3	394.7	391.4	390.3	389.4	387.9	387.1	388.5
175°	395.4	394.6	394.6	395.4	393.8	391.4	391.4	391.4	390.6	389.8	391.4
177.5°	392.8	392.2	392.2	393.5	392.8	391.6	391.6	392.2	391.6	391.6	392.8
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1006.9	1010.0	1014.2	1019.1	1023.1	1027.4	1029.7	1029.7	1031.7	1035.9	1041.5
5°	1009.9	1020.6	1030.8	1044.0	1054.2	1066.2	1075.2	1083.9	1091.7	1101.5	1111.8
7.5°	1009.0	1026.7	1045.3	1066.0	1088.9	1107.1	1125.8	1140.4	1154.8	1173.8	1188.7
10°	1005.8	1028.7	1053.8	1080.1	1109.0	1134.1	1156.7	1177.3	1197.0	1217.6	1236.0
12.5°	999.8	1029.1	1059.8	1091.4	1127.8	1156.4	1185.7	1207.5	1230.6	1253.1	1275.9
15°	990.9	1025.5	1062.5	1106.5	1151.0	1183.0	1211.8	1240.2	1261.6	1287.1	1308.9
17.5°	972.6	1017.1	1063.7	1111.7	1154.4	1191.8	1221.9	1248.9	1271.7	1299.7	1329.4
20°	961.7	1009.9	1058.4	1109.8	1150.5	1188.7	1218.0	1245.9	1274.3	1310.9	1347.1
22.5°	946.6	998.0	1049.5	1098.3	1141.3	1178.2	1208.4	1242.7	1279.9	1321.4	1365.2
25°	922.7	975.7	1026.7	1073.2	1115.2	1153.0	1194.1	1240.2	1285.5	1340.1	1403.1
27.5°	892.3	943.4	989.0	1038.1	1079.7	1127.9	1179.2	1229.2	1294.4	1369.7	1448.3
30°	869.6	918.1	961.3	1007.8	1055.1	1108.2	1165.8	1224.6	1302.3	1390.8	1484.2
32.5°	843.3	887.2	930.0	974.9	1029.4	1087.7	1149.0	1220.9	1313.8	1414.4	1511.1
35°	797.6	837.1	878.6	928.4	986.4	1049.7	1127.9	1215.5	1327.8	1436.0	1522.8
37.5°	749.7	780.9	822.6	875.1	938.3	1011.5	1100.3	1206.7	1322.1	1419.1	1456.0
40°	712.9	742.0	786.1	841.2	903.7	983.9	1083.5	1192.9	1308.9	1376.3	1373.5
42.5°	676.3	705.8	748.2	803.7	868.9	958.6	1061.1	1174.8	1272.7	1298.4	1244.8
45°	620.3	647.8	689.4	745.4	815.3	909.5	1017.2	1126.2	1188.7	1147.2	1041.1
47.5°	563.2	589.9	628.5	683.3	759.6	858.3	960.1	1049.6	1058.4	969.2	841.9
50°	525.7	550.8	587.4	645.8	719.9	816.1	914.4	984.8	963.0	854.0	722.7
52.5°	489.2	513.3	547.6	602.7	678.3	772.7	860.5	915.6	865.2	749.3	631.2
55°	435.2	458.2	492.8	543.4	612.0	698.5	775.4	795.5	721.5	604.7	509.2
57.5°	384.0	400.8	435.0	479.7	545.9	622.1	677.2	673.6	591.9	486.7	418.3
60°	350.1	365.3	397.8	438.9	501.8	570.1	608.8	592.3	509.6	422.9	357.0
62.5°	318.5	332.7	359.9	397.8	451.8	511.2	539.3	516.7	438.6	362.3	310.0
65°	270.7	280.9	302.8	337.7	380.1	421.2	446.3	413.0	343.9	286.3	246.8
67.5°	226.0	234.9	254.3	279.4	308.6	337.0	347.1	315.9	262.2	223.4	195.6
70°	197.0	205.3	218.4	241.9	261.2	281.4	286.3	258.3	213.5	183.9	166.6
72.5°	169.4	177.0	188.5	205.0	218.4	230.0	232.3	206.4	172.0	151.6	138.3
75°	129.1	135.8	143.1	149.3	158.0	160.0	159.1	139.0	120.5	106.9	99.6
77.5°	94.9	97.7	102.2	104.6	105.0	104.9	100.7	87.9	78.4	72.8	69.8
80°	73.2	75.3	76.5	77.3	77.7	73.6	69.1	61.3	58.0	54.7	51.0
82.5°	53.2	54.6	55.8	55.9	53.7	50.3	46.1	42.2	39.9	38.3	36.8
85°	28.8	29.2	28.8	26.8	23.8	22.7	21.8	21.0	20.6	20.1	20.1
87.5°	10.5	9.8	8.6	9.2	9.5	9.3	9.6	9.4	9.4	9.6	9.7
90°	1.6	3.2	4.8	6.3	7.9	8.7	10.3	11.1	12.7	13.5	14.3
92.5°	11.7	18.4	28.1	41.7	64.9	108.1	180.5	259.0	254.9	206.4	140.1
95°	26.9	33.2	41.9	59.3	94.9	179.5	353.5	571.8	700.7	685.6	568.6
97.5°	44.3	48.7	57.4	73.0	98.7	154.7	282.2	510.6	748.3	867.5	846.8
100°	57.0	60.1	68.8	83.8	107.6	153.4	256.2	455.5	714.1	911.8	972.7
102.5°	69.6	72.1	81.4	95.2	118.3	159.1	245.5	413.8	654.0	885.3	1015.1
105°	89.4	93.3	101.2	113.9	136.0	170.8	241.2	373.3	573.3	800.3	990.1
107.5°	111.2	114.9	121.4	134.6	154.6	188.2	248.5	356.2	517.8	713.6	900.9
110°	125.7	128.9	136.0	147.9	168.4	200.9	255.4	351.1	491.9	664.2	835.1



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.3	142.8	150.0	161.8	181.7	212.9	264.3	351.1	476.7	627.6	783.2
115°	161.3	163.7	170.8	182.7	202.5	231.7	277.6	353.5	460.3	587.6	718.0
117.5°	181.1	183.6	190.8	204.2	223.3	251.0	292.8	358.7	452.2	563.7	676.0
120°	193.8	196.9	204.1	217.5	237.3	264.9	302.9	363.8	448.4	550.4	653.2
122.5°	206.4	208.9	216.0	230.8	250.6	278.2	314.3	368.2	445.2	539.0	636.1
125°	223.0	227.0	234.1	249.1	269.7	295.8	329.8	375.7	441.2	523.6	611.3
127.5°	236.9	242.0	251.0	267.0	287.6	312.7	344.0	384.0	439.3	509.3	586.0
130°	245.2	251.5	261.7	278.4	298.9	323.4	353.5	389.1	438.1	499.8	570.2
132.5°	252.1	259.7	271.2	288.5	309.0	333.6	361.7	394.7	438.1	492.2	554.4
135°	262.5	272.0	284.7	301.3	322.7	347.1	373.3	402.5	438.1	483.2	533.8
137.5°	274.7	283.6	296.3	312.5	334.5	356.8	381.8	409.6	439.0	475.2	516.4
140°	282.3	291.8	304.4	319.5	340.9	363.8	387.5	412.8	439.7	471.3	506.9
142.5°	290.6	299.4	312.0	326.5	346.5	368.2	390.6	414.7	440.3	468.2	498.7
145°	303.6	311.6	322.7	336.9	355.1	375.7	395.4	416.8	439.7	463.4	487.9
147.5°	317.0	323.8	334.1	346.3	362.3	380.4	398.2	417.6	437.6	458.5	477.8
150°	325.8	331.4	341.7	352.7	366.1	383.6	400.1	417.6	435.7	454.7	472.1
152.5°	334.1	339.0	347.9	358.4	370.6	386.7	401.4	416.9	433.2	450.3	465.8
155°	344.8	349.5	357.4	365.4	376.4	389.8	402.5	415.2	428.6	442.8	456.3
157.5°	355.1	358.9	365.7	372.6	381.0	392.5	403.3	413.1	423.9	435.9	446.8
160°	361.4	364.6	370.1	376.4	383.6	393.8	403.3	411.2	420.7	430.2	440.5
162.5°	367.1	370.3	375.2	380.2	386.1	395.1	402.7	409.3	416.9	425.2	433.6
165°	374.9	377.2	381.2	384.4	389.1	395.4	401.7	406.5	411.2	417.6	423.9
167.5°	381.4	382.8	385.0	387.2	390.1	395.4	399.8	402.0	405.7	410.1	414.7
170°	385.2	386.0	387.5	389.1	391.4	395.4	398.5	400.1	402.5	405.7	409.6
172.5°	387.1	387.9	389.4	390.3	391.4	394.7	397.3	397.6	398.7	401.2	403.9
175°	389.8	390.6	391.4	391.4	391.4	393.8	395.4	394.6	394.6	395.4	397.8
177.5°	391.6	391.6	392.2	391.6	391.6	392.8	393.5	392.2	392.2	392.8	393.5
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2	392.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1045.8	1045.8	1051.4	1051.1	1054.7	1053.4	1054.0
5°	1124.2	1131.2	1137.3	1141.5	1147.6	1149.3	1148.4
7.5°	1205.5	1221.0	1228.6	1239.0	1240.9	1246.3	1245.7
10°	1255.8	1271.1	1282.5	1291.6	1296.2	1301.9	1302.3
12.5°	1295.3	1308.2	1318.4	1326.8	1332.3	1334.1	1335.2
15°	1326.2	1340.5	1352.5	1364.4	1371.4	1376.7	1379.7
17.5°	1357.2	1379.5	1400.5	1416.7	1426.5	1434.6	1434.6
20°	1381.2	1406.8	1433.1	1451.6	1470.5	1478.8	1480.0
22.5°	1406.9	1446.0	1479.9	1508.6	1533.4	1542.0	1545.2
25°	1460.2	1511.2	1563.5	1603.9	1632.6	1649.5	1651.9
27.5°	1524.6	1593.7	1648.7	1685.8	1709.8	1722.3	1725.0
30°	1570.1	1633.9	1683.2	1711.2	1722.3	1723.9	1717.8
32.5°	1590.5	1638.2	1657.9	1656.2	1634.4	1619.9	1614.4
35°	1565.6	1555.7	1507.5	1450.0	1406.0	1378.0	1370.6
37.5°	1424.7	1339.6	1251.0	1164.0	1117.7	1094.2	1053.7
40°	1285.9	1164.5	1072.4	999.2	946.9	904.9	895.1
42.5°	1129.2	1003.9	911.8	849.1	807.4	778.6	766.0
45°	907.4	799.6	723.6	675.4	643.3	622.3	612.9
47.5°	725.8	642.4	586.9	551.3	526.9	508.6	503.5
50°	626.1	559.4	512.5	482.5	464.0	450.0	444.3
52.5°	543.8	490.0	453.9	429.2	411.7	403.0	398.2
55°	448.8	402.3	376.4	356.6	346.7	339.8	336.4
57.5°	367.0	333.4	314.5	300.9	291.8	287.2	285.7
60°	321.2	294.9	277.7	267.0	260.8	255.0	253.4
62.5°	280.7	260.1	246.7	237.3	231.2	228.7	227.8
65°	226.2	212.7	202.8	197.0	192.1	191.3	190.8
67.5°	179.8	171.8	166.7	160.7	158.9	156.1	155.5
70°	153.8	148.5	142.4	140.3	138.2	135.3	135.8
72.5°	130.5	125.2	121.0	118.2	117.5	116.2	117.3
75°	95.5	93.8	92.1	90.1	89.3	89.3	88.9
77.5°	68.1	66.7	64.9	63.7	63.5	61.7	62.3
80°	49.4	47.3	46.5	46.9	45.6	45.2	45.2
82.5°	36.5	35.8	34.9	35.0	34.8	34.4	34.7
85°	20.1	19.7	19.7	19.3	19.3	18.9	18.9
87.5°	10.2	10.7	10.4	10.1	10.1	10.5	10.9
90°	15.1	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.7	76.5	64.9	54.7	52.8	51.7	50.5
95°	448.4	351.1	284.7	228.5	204.9	198.5	185.8
97.5°	762.5	667.7	575.4	526.6	482.2	459.3	449.2
100°	934.0	852.5	770.2	715.7	658.8	629.5	616.9
102.5°	1038.9	999.9	944.2	885.9	845.4	813.6	804.1
105°	1098.4	1133.2	1124.5	1099.2	1073.2	1057.3	1047.8
107.5°	1045.4	1134.8	1176.1	1188.9	1188.7	1183.5	1177.2
110°	985.3	1096.9	1164.1	1199.7	1214.7	1220.2	1220.2



TEST NUMBER: P333570-927

CATALOG NUMBER: S125RDIP-S850D1035U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.9	1038.6	1117.9	1169.9	1195.7	1209.5	1215.1
115°	840.7	949.0	1035.1	1096.9	1134.8	1157.0	1167.3
117.5°	781.6	875.0	954.0	1015.7	1054.9	1076.9	1083.2
120°	748.1	835.1	904.7	963.2	1001.2	1022.5	1028.9
122.5°	724.1	801.5	866.7	918.9	953.7	975.1	980.8
125°	692.0	760.7	817.7	862.0	894.4	911.8	919.7
127.5°	661.3	725.5	778.8	819.0	847.6	864.0	867.5
130°	639.8	701.5	752.9	792.4	818.5	834.3	839.1
132.5°	619.5	675.5	725.0	764.5	790.7	805.2	810.6
135°	588.4	639.0	684.0	718.8	745.0	759.1	763.9
137.5°	560.5	602.6	640.9	672.0	695.8	708.9	714.1
140°	544.1	580.4	613.7	642.9	663.5	675.3	679.3
142.5°	530.1	561.5	590.3	615.1	632.5	643.7	647.1
145°	512.5	536.9	558.3	577.3	590.7	599.4	602.6
147.5°	497.7	516.6	532.7	547.7	558.5	563.6	565.0
150°	489.5	504.5	518.8	530.6	540.1	543.3	544.1
152.5°	481.3	495.0	506.1	516.1	523.7	526.8	527.6
155°	469.0	480.1	488.7	496.6	502.2	504.5	505.3
157.5°	457.2	465.8	472.6	478.8	483.3	485.5	485.4
160°	448.4	456.3	461.8	467.4	471.3	472.9	472.1
162.5°	440.8	447.4	452.3	456.6	459.9	460.3	460.1
165°	429.4	434.2	438.1	441.2	442.8	442.8	442.8
167.5°	418.4	422.0	424.8	426.4	427.9	427.2	427.1
170°	412.0	414.4	416.0	417.6	418.4	418.4	417.6
172.5°	406.3	408.1	409.0	409.3	410.7	409.5	408.7
175°	397.8	399.3	399.3	399.3	400.1	398.5	397.8
177.5°	394.1	394.1	394.1	393.5	394.1	392.2	392.2
180°	392.2	392.2	392.2	392.2	392.2	392.2	392.2

(END OF REPORT)