

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333564-927

Luminaire Tested: **S125RDIP-S850D810U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333564-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4901.7 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	73	66	61	76	68	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6471	6471	6471	6471
5°	7445	6480	5723	6480
10°	8540	6447	5050	6447
15°	9225	6381	4488	6381
20°	10172	6304	4144	6304
25°	11771	6202	3846	6202
30°	12810	6095	3650	6095
35°	10806	5970	3470	5970
40°	7546	5746	3315	5746
45°	5598	5444	3163	5444
50°	4464	5129	3033	5129
55°	3788	4738	2917	4738
60°	3273	4389	2731	4389
65°	2916	4010	2350	4010
70°	2564	3675	2143	3675
75°	2218	3182	2011	3182
80°	1681	2678	1681	2678
85°	1401	2104	1586	2104



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.1	2.0
10°-20°	281.6	5.7
20°-30°	446.5	9.1
30°-40°	538.4	11.0
40°-50°	480.8	9.8
50°-60°	368.7	7.5
60°-70°	239.6	4.9
70°-80°	116.5	2.4
80°-90°	29.5	0.6
90°-100°	222.7	4.5
100°-110°	478.7	9.8
110°-120°	449.3	9.2
120°-130°	364.1	7.4
130°-140°	292.2	6.0
140°-150°	220.5	4.5
150°-160°	155.2	3.2
160°-170°	91.5	1.9
170°-180°	29.8	0.6
0°-30°	824.2	16.8
0°-40°	1362.6	27.8
0°-60°	2212.2	45.1
0°-90°	2597.8	53.0
90°-120°	1150.7	23.5
90°-150°	2027.5	41.4
90°-180°	2304.0	47.0
0°-180°	4901.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1002	1002	1002	1002	1002	
5°	1148	1000	883	1000	1148	115
15°	1380	954	671	954	1380	395
25°	1652	870	540	870	1652	758
35°	1371	757	440	757	1371	828
45°	613	596	346	596	613	489
55°	336	421	259	421	336	305
65°	191	262	154	262	191	190
75°	89	128	81	128	89	95
85°	19	28	21	28	19	22
90°	14	1	14	1	14	11
95°	146	20	146	20	146	206
105°	821	70	821	70	821	816
115°	914	125	914	125	914	893
125°	720	173	720	173	720	652
135°	598	203	598	203	598	464
145°	472	237	472	237	472	300
155°	396	270	396	270	396	184
165°	347	295	347	295	347	99
175°	312	307	312	307	312	30
180°	307	307	307	307	307	



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1054.0	1053.4	1054.7	1051.1	1051.4	1045.8	1045.8	1041.5	1035.9	1031.7	1029.7
5°	1148.4	1149.3	1147.6	1141.5	1137.3	1131.2	1124.2	1111.8	1101.5	1091.7	1083.9
7.5°	1245.7	1246.3	1240.9	1239.0	1228.6	1221.0	1205.5	1188.7	1173.8	1154.8	1140.4
10°	1302.3	1301.9	1296.2	1291.6	1282.5	1271.1	1255.8	1236.0	1217.6	1197.0	1177.3
12.5°	1335.2	1334.1	1332.3	1326.8	1318.4	1308.2	1295.3	1275.9	1253.1	1230.6	1207.5
15°	1379.7	1376.7	1371.4	1364.4	1352.5	1340.5	1326.2	1308.9	1287.1	1261.6	1240.2
17.5°	1434.6	1434.6	1426.5	1416.7	1400.5	1379.5	1357.2	1329.4	1299.7	1271.7	1248.9
20°	1480.0	1478.8	1470.5	1451.6	1433.1	1406.8	1381.2	1347.1	1310.9	1274.3	1245.9
22.5°	1545.2	1542.0	1533.4	1508.6	1479.9	1446.0	1406.9	1365.2	1321.4	1279.9	1242.7
25°	1651.9	1649.5	1632.6	1603.9	1563.5	1511.2	1460.2	1403.1	1340.1	1285.5	1240.2
27.5°	1725.0	1722.3	1709.8	1685.8	1648.7	1593.7	1524.6	1448.3	1369.7	1294.4	1229.2
30°	1717.8	1723.9	1722.3	1711.2	1683.2	1633.9	1570.1	1484.2	1390.8	1302.3	1224.6
32.5°	1614.4	1619.9	1634.4	1656.2	1657.9	1638.2	1590.5	1511.1	1414.4	1313.8	1220.9
35°	1370.6	1378.0	1406.0	1450.0	1507.5	1555.7	1565.6	1522.8	1436.0	1327.8	1215.5
37.5°	1053.7	1094.2	1117.7	1164.0	1251.0	1339.6	1424.7	1456.0	1419.1	1322.1	1206.7
40°	895.1	904.9	946.9	999.2	1072.4	1164.5	1285.9	1373.5	1376.3	1308.9	1192.9
42.5°	766.0	778.6	807.4	849.1	911.8	1003.9	1129.2	1244.8	1298.4	1272.7	1174.8
45°	612.9	622.3	643.3	675.4	723.6	799.6	907.4	1041.1	1147.2	1188.7	1126.2
47.5°	503.5	508.6	526.9	551.3	586.9	642.4	725.8	841.9	969.2	1058.4	1049.6
50°	444.3	450.0	464.0	482.5	512.5	559.4	626.1	722.7	854.0	963.0	984.8
52.5°	398.2	403.0	411.7	429.2	453.9	490.0	543.8	631.2	749.3	865.2	915.6
55°	336.4	339.8	346.7	356.6	376.4	402.3	448.8	509.2	604.7	721.5	795.5
57.5°	285.7	287.2	291.8	300.9	314.5	333.4	367.0	418.3	486.7	591.9	673.6
60°	253.4	255.0	260.8	267.0	277.7	294.9	321.2	357.0	422.9	509.6	592.3
62.5°	227.8	228.7	231.2	237.3	246.7	260.1	280.7	310.0	362.3	438.6	516.7
65°	190.8	191.3	192.1	197.0	202.8	212.7	226.2	246.8	286.3	343.9	413.0
67.5°	155.5	156.1	158.9	160.7	166.7	171.8	179.8	195.6	223.4	262.2	315.9
70°	135.8	135.3	138.2	140.3	142.4	148.5	153.8	166.6	183.9	213.5	258.3
72.5°	117.3	116.2	117.5	118.2	121.0	125.2	130.5	138.3	151.6	172.0	206.4
75°	88.9	89.3	89.3	90.1	92.1	93.8	95.5	99.6	106.9	120.5	139.0
77.5°	62.3	61.7	63.5	63.7	64.9	66.7	68.1	69.8	72.8	78.4	87.9
80°	45.2	45.2	45.6	46.9	46.5	47.3	49.4	51.0	54.7	58.0	61.3
82.5°	34.7	34.4	34.8	35.0	34.9	35.8	36.5	36.8	38.3	39.9	42.2
85°	18.9	18.9	19.3	19.3	19.7	19.7	20.1	20.1	20.1	20.6	21.0
87.5°	10.1	9.7	9.3	9.3	9.7	10.1	9.6	9.1	9.0	8.9	9.0
90°	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2	10.5	9.9	8.6
92.5°	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8	161.7	199.7	202.9
95°	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4	537.0	548.8	447.8
97.5°	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3	679.5	586.1	399.9
100°	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8	714.2	559.4	356.8
102.5°	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0	693.4	512.2	324.1
105°	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5	626.9	449.1	292.4
107.5°	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6	559.0	405.6	279.0
110°	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1	520.3	385.2	275.0



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5	491.5	373.4	275.0
115°	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4	460.2	360.5	276.9
117.5°	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5	441.5	354.2	281.0
120°	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6	431.1	351.2	284.9
122.5°	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3	422.2	348.7	288.4
125°	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8	410.0	345.6	294.2
127.5°	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0	398.9	344.1	300.8
130°	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6	391.5	343.2	304.8
132.5°	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2	385.6	343.2	309.2
135°	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1	378.4	343.2	315.3
137.5°	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5	372.2	343.9	320.8
140°	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0	369.2	344.4	323.3
142.5°	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6	366.7	344.9	324.8
145°	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1	363.0	344.4	326.5
147.5°	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2	359.1	342.8	327.0
150°	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8	356.2	341.3	327.0
152.5°	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8	352.7	339.3	326.5
155°	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4	346.9	335.7	325.2
157.5°	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0	341.4	332.0	323.6
160°	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0	337.0	329.5	322.1
162.5°	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5	333.0	326.5	320.6
165°	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0	327.0	322.1	318.4
167.5°	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8	321.2	317.7	314.9
170°	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8	317.7	315.3	313.4
172.5°	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4	314.3	312.3	311.4
175°	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6	309.7	309.1	309.1
177.5°	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2	307.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1029.7	1027.4	1023.1	1019.1	1014.2	1010.0	1006.9	1003.4	998.7	993.2	988.6
5°	1075.2	1066.2	1054.2	1044.0	1030.8	1020.6	1009.9	999.6	989.3	976.1	964.6
7.5°	1125.8	1107.1	1088.9	1066.0	1045.3	1026.7	1009.0	991.0	973.4	954.7	936.7
10°	1156.7	1134.1	1109.0	1080.1	1053.8	1028.7	1005.8	983.1	959.3	938.3	915.6
12.5°	1185.7	1156.4	1127.8	1091.4	1059.8	1029.1	999.8	971.6	946.1	918.9	894.6
15°	1211.8	1183.0	1151.0	1106.5	1062.5	1025.5	990.9	954.3	922.7	892.2	865.1
17.5°	1221.9	1191.8	1154.4	1111.7	1063.7	1017.1	972.6	932.4	895.2	859.7	829.2
20°	1218.0	1188.7	1150.5	1109.8	1058.4	1009.9	961.7	917.3	875.8	838.3	805.8
22.5°	1208.4	1178.2	1141.3	1098.3	1049.5	998.0	946.6	899.2	855.6	816.9	781.5
25°	1194.1	1153.0	1115.2	1073.2	1026.7	975.7	922.7	870.4	823.9	784.4	745.8
27.5°	1179.2	1127.9	1079.7	1038.1	989.0	943.4	892.3	838.7	789.9	749.6	710.0
30°	1165.8	1108.2	1055.1	1007.8	961.3	918.1	869.6	817.3	767.1	725.6	685.3
32.5°	1149.0	1087.7	1029.4	974.9	930.0	887.2	843.3	793.3	744.4	701.6	660.6
35°	1127.9	1049.7	986.4	928.4	878.6	837.1	797.6	757.2	708.3	663.9	624.0
37.5°	1100.3	1011.5	938.3	875.1	822.6	780.9	749.7	712.9	668.2	625.7	588.6
40°	1083.5	983.9	903.7	841.2	786.1	742.0	712.9	681.6	640.9	600.9	564.0
42.5°	1061.1	958.6	868.9	803.7	748.2	705.8	676.3	649.0	614.9	577.3	537.7
45°	1017.2	909.5	815.3	745.4	689.4	647.8	620.3	596.0	570.1	535.6	501.0
47.5°	960.1	858.3	759.6	683.3	628.5	589.9	563.2	544.1	525.5	496.1	462.6
50°	914.4	816.1	719.9	645.8	587.4	550.8	525.7	510.5	493.6	466.8	438.9
52.5°	860.5	772.7	678.3	602.7	547.6	513.3	489.2	474.0	460.0	438.2	411.6
55°	775.4	698.5	612.0	543.4	492.8	458.2	435.2	420.8	412.6	394.0	373.1
57.5°	677.2	622.1	545.9	479.7	435.0	400.8	384.0	371.7	362.4	349.3	334.5
60°	608.8	570.1	501.8	438.9	397.8	365.3	350.1	339.8	331.1	320.0	308.5
62.5°	539.3	511.2	451.8	397.8	359.9	332.7	318.5	309.2	299.2	291.8	280.5
65°	446.3	421.2	380.1	337.7	302.8	280.9	270.7	262.4	256.3	248.0	240.2
67.5°	347.1	337.0	308.6	279.4	254.3	234.9	226.0	220.2	212.9	207.9	202.6
70°	286.3	281.4	261.2	241.9	218.4	205.3	197.0	194.6	185.5	180.6	176.9
72.5°	232.3	230.0	218.4	205.0	188.5	177.0	169.4	166.6	160.8	156.9	154.5
75°	159.1	160.0	158.0	149.3	143.1	135.8	129.1	127.5	123.4	120.1	118.0
77.5°	100.7	104.9	105.0	104.6	102.2	97.7	94.9	93.7	89.7	88.4	87.9
80°	69.1	73.6	77.7	77.3	76.5	75.3	73.2	72.0	69.9	68.7	67.9
82.5°	46.1	50.3	53.7	55.9	55.8	54.6	53.2	52.6	52.1	51.3	51.1
85°	21.8	22.7	23.8	26.8	28.8	29.2	28.8	28.4	27.2	27.6	28.0
87.5°	9.2	9.0	9.1	8.9	8.3	9.7	10.5	10.6	10.1	9.7	9.3
90°	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6	1.3	2.5	3.7
92.5°	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5	9.2	14.3	22.0
95°	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4	21.1	26.0	32.8
97.5°	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9	34.7	38.2	45.0
100°	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3	44.6	47.1	53.9
102.5°	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8	54.5	56.5	63.8
105°	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0	70.0	73.1	79.3
107.5°	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9	87.1	90.1	95.1
110°	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3	98.5	100.9	106.5



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6	109.9	111.9	117.4
115°	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1	126.4	128.3	133.8
117.5°	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0	141.9	143.9	149.4
120°	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9	151.8	154.2	159.8
122.5°	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3	161.7	163.7	169.2
125°	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4	174.7	177.8	183.3
127.5°	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7	185.6	189.6	196.6
130°	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1	192.0	196.9	205.0
132.5°	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1	197.5	203.4	212.5
135°	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2	205.7	213.1	223.0
137.5°	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3	215.2	222.1	232.0
140°	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3	221.1	228.5	238.4
142.5°	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2	227.6	234.5	244.4
145°	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6	237.8	244.1	252.7
147.5°	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5	248.3	253.6	261.7
150°	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0	255.2	259.5	267.6
152.5°	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9	261.7	265.5	272.5
155°	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1	270.1	273.8	280.0
157.5°	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2	278.1	281.1	286.4
160°	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7	283.0	285.6	289.9
162.5°	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1	287.6	290.0	293.8
165°	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9	293.6	295.5	298.6
167.5°	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3	298.7	299.8	301.5
170°	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3	301.7	302.3	303.5
172.5°	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3	303.2	303.7	305.0
175°	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6	305.4	306.0	306.6
177.5°	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7	306.7	306.7	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	985.2	980.6	977.3	970.7	966.1	964.2	960.6	959.6	963.2	960.6	960.2
5°	955.9	944.0	934.5	925.1	914.8	908.2	898.3	896.8	894.2	890.6	889.7
7.5°	920.8	905.3	893.1	877.5	863.9	852.9	840.6	834.8	831.6	826.8	820.4
10°	897.1	878.6	862.1	846.5	829.7	816.1	803.7	794.3	788.1	782.4	779.9
12.5°	873.8	854.9	833.9	814.9	796.1	780.9	767.2	761.0	754.2	747.5	741.7
15°	837.5	812.4	789.3	767.5	751.5	735.1	721.9	712.9	702.6	699.7	688.6
17.5°	799.0	774.4	747.4	724.5	705.8	687.8	673.3	663.0	655.3	644.7	639.5
20°	775.0	745.8	719.5	698.5	677.9	656.5	641.7	633.0	625.7	617.0	612.9
22.5°	749.3	720.7	693.8	669.2	648.2	627.2	616.7	607.7	599.3	591.4	585.9
25°	711.6	682.9	654.4	628.9	607.1	591.9	579.6	569.3	564.7	557.0	551.2
27.5°	674.4	643.7	614.3	588.9	571.8	556.7	546.6	538.4	530.3	523.5	518.5
30°	650.3	619.1	587.0	566.8	548.7	534.3	523.2	515.4	509.2	503.0	499.4
32.5°	626.3	594.1	565.6	543.8	526.6	514.3	502.8	495.4	488.9	482.0	477.7
35°	587.8	554.9	531.9	510.5	493.6	482.1	474.3	463.6	458.2	453.3	448.8
37.5°	552.0	521.4	496.5	477.8	463.1	451.6	441.6	435.8	429.2	424.8	421.0
40°	525.7	497.7	475.1	455.3	444.7	431.9	422.5	415.0	410.1	404.3	400.2
42.5°	502.0	476.0	454.0	436.3	422.9	412.2	403.1	395.6	389.4	385.2	381.8
45°	468.5	442.6	421.2	404.7	392.4	382.1	372.6	369.0	360.8	355.8	354.2
47.5°	433.9	410.7	390.1	374.9	362.3	352.5	343.6	336.0	331.5	326.7	324.1
50°	410.5	388.3	369.0	354.2	341.8	331.1	322.9	318.0	311.8	307.3	304.0
52.5°	387.1	366.6	347.3	333.1	322.4	311.7	302.5	297.5	291.8	288.8	286.5
55°	353.8	331.9	315.5	301.5	290.4	280.5	271.9	267.0	263.2	260.4	259.5
57.5°	315.9	298.7	283.4	270.8	259.2	249.9	242.3	237.7	234.4	233.9	231.5
60°	291.2	275.6	261.6	248.0	238.1	229.5	222.9	217.6	214.3	213.9	213.1
62.5°	266.6	251.6	238.6	226.6	217.8	209.5	203.2	197.2	195.2	193.1	191.4
65°	230.0	216.3	205.7	196.2	186.7	179.7	173.6	169.8	165.3	162.9	158.4
67.5°	194.0	183.5	173.2	165.2	157.8	151.1	146.0	140.5	137.4	135.5	132.2
70°	170.3	162.1	151.8	143.1	137.4	132.1	127.9	121.8	119.7	118.0	116.4
72.5°	147.9	140.7	132.1	125.1	119.3	114.2	109.5	106.6	104.6	102.9	102.0
75°	116.4	109.4	102.0	97.0	93.0	88.9	86.3	84.3	83.5	83.1	81.4
77.5°	85.5	81.8	75.8	71.9	69.2	67.6	65.4	64.2	64.2	62.3	61.8
80°	65.4	63.4	58.4	56.8	54.7	53.1	51.8	49.7	47.7	46.9	45.6
82.5°	48.6	46.6	44.6	42.0	40.2	39.2	38.0	37.2	37.5	36.4	35.8
85°	25.9	23.8	23.1	22.7	21.8	22.7	22.2	21.8	21.4	21.0	21.4
87.5°	9.2	9.4	9.3	10.1	9.3	9.9	10.0	9.8	9.9	10.1	10.0
90°	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2	11.8	12.4	13.6
92.5°	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8	79.7	60.0	50.8
95°	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4	351.2	275.0	223.0
97.5°	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3	597.2	523.0	450.7
100°	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8	731.5	667.7	603.3
102.5°	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0	813.8	783.2	739.6
105°	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5	860.4	887.6	880.8
107.5°	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6	818.9	888.8	921.1
110°	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1	771.7	859.1	911.7



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5	725.2	813.5	875.6
115°	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4	658.5	743.3	810.8
117.5°	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5	612.2	685.3	747.3
120°	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6	586.0	654.1	708.6
122.5°	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3	567.1	627.8	678.9
125°	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8	542.0	595.9	640.5
127.5°	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0	517.9	568.2	610.0
130°	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6	501.1	549.4	589.7
132.5°	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2	485.2	529.1	567.8
135°	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1	460.8	500.5	535.8
137.5°	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5	439.0	472.0	501.9
140°	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0	426.1	454.6	480.6
142.5°	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6	415.3	439.7	462.3
145°	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1	401.4	420.6	437.3
147.5°	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2	389.8	404.6	417.2
150°	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8	383.4	395.1	406.3
152.5°	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8	377.0	387.8	396.4
155°	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4	367.3	376.0	382.8
157.5°	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0	358.1	364.8	370.2
160°	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0	351.2	357.4	361.7
162.5°	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5	345.2	350.5	354.3
165°	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0	336.4	340.1	343.2
167.5°	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8	327.6	330.5	332.7
170°	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8	322.7	324.6	325.8
172.5°	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4	318.2	319.6	320.4
175°	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6	311.6	312.8	312.8
177.5°	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2	308.7	308.7	308.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	959.9	956.3	955.3	956.6	955.3	956.3	959.9	960.2	960.6	963.2	959.6
5°	885.6	881.5	883.5	882.7	883.5	881.5	885.6	889.7	890.6	894.2	896.8
7.5°	820.3	815.2	809.8	811.5	809.8	815.2	820.3	820.4	826.8	831.6	834.8
10°	774.5	770.5	767.9	770.0	767.9	770.5	774.5	779.9	782.4	788.1	794.3
12.5°	736.0	733.6	731.4	730.6	731.4	733.6	736.0	741.7	747.5	754.2	761.0
15°	683.7	678.7	676.7	671.3	676.7	678.7	683.7	688.6	699.7	702.6	712.9
17.5°	635.3	633.7	628.4	626.1	628.4	633.7	635.3	639.5	644.7	655.3	663.0
20°	606.7	605.1	599.8	603.0	599.8	605.1	606.7	612.9	617.0	625.7	633.0
22.5°	583.0	579.4	577.7	576.7	577.7	579.4	583.0	585.9	591.4	599.3	607.7
25°	549.5	544.2	542.2	539.7	542.2	544.2	549.5	551.2	557.0	564.7	569.3
27.5°	516.2	513.3	510.6	509.9	510.6	513.3	516.2	518.5	523.5	530.3	538.4
30°	494.4	491.5	489.5	489.5	489.5	491.5	494.4	499.4	503.0	509.2	515.4
32.5°	475.0	472.8	470.7	470.4	470.7	472.8	475.0	477.7	482.0	488.9	495.4
35°	446.7	443.5	442.6	440.1	442.6	443.5	446.7	448.8	453.3	458.2	463.6
37.5°	417.3	414.6	414.5	414.3	414.5	414.6	417.3	421.0	424.8	429.2	435.8
40°	398.6	396.6	396.1	393.2	396.1	396.6	398.6	400.2	404.3	410.1	415.0
42.5°	378.5	377.5	376.0	374.8	376.0	377.5	378.5	381.8	385.2	389.4	395.6
45°	351.3	348.4	348.4	346.3	348.4	348.4	351.3	354.2	355.8	360.8	369.0
47.5°	323.1	320.9	321.2	319.0	321.2	320.9	323.1	324.1	326.7	331.5	336.0
50°	304.4	303.2	302.8	301.9	302.8	303.2	304.4	304.0	307.3	311.8	318.0
52.5°	285.7	285.0	286.6	284.8	286.6	285.0	285.7	286.5	288.8	291.8	297.5
55°	260.4	259.1	261.6	259.1	261.6	259.1	260.4	259.5	260.4	263.2	267.0
57.5°	231.3	230.2	232.4	231.2	232.4	230.2	231.3	231.5	233.9	234.4	237.7
60°	212.2	209.8	211.0	211.4	211.0	209.8	212.2	213.1	213.9	214.3	217.6
62.5°	189.6	188.1	188.9	187.1	188.9	188.1	189.6	191.4	193.1	195.2	197.2
65°	157.6	156.3	154.6	153.8	154.6	156.3	157.6	158.4	162.9	165.3	169.8
67.5°	132.4	129.4	129.4	130.0	129.4	129.4	132.4	132.2	135.5	137.4	140.5
70°	113.9	113.9	113.5	113.5	113.5	113.9	113.9	116.4	118.0	119.7	121.8
72.5°	101.1	100.8	100.1	99.7	100.1	100.8	101.1	102.0	102.9	104.6	106.6
75°	81.4	81.8	81.0	80.6	81.0	81.8	81.4	81.4	83.1	83.5	84.3
77.5°	60.1	58.4	59.3	58.4	59.3	58.4	60.1	61.8	62.3	64.2	64.2
80°	45.6	45.2	46.5	45.2	46.5	45.2	45.6	45.6	46.9	47.7	49.7
82.5°	36.1	35.7	36.3	35.4	36.3	35.7	36.1	35.8	36.4	37.5	37.2
85°	21.8	21.4	21.0	21.4	21.0	21.4	21.8	21.4	21.0	21.4	21.8
87.5°	10.3	10.0	10.1	10.1	10.1	10.0	10.3	10.0	10.1	9.9	9.8
90°	13.6	13.6	14.3	14.3	14.3	13.6	13.6	13.6	12.4	11.8	11.2
92.5°	42.9	41.4	40.5	39.5	40.5	41.4	42.9	50.8	60.0	79.7	109.8
95°	179.0	160.4	155.5	145.5	155.5	160.4	179.0	223.0	275.0	351.2	445.4
97.5°	412.4	377.7	359.7	351.8	359.7	377.7	412.4	450.7	523.0	597.2	663.3
100°	560.5	515.9	493.1	483.2	493.1	515.9	560.5	603.3	667.7	731.5	761.8
102.5°	693.9	662.1	637.2	629.8	637.2	662.1	693.9	739.6	783.2	813.8	795.0
105°	860.9	840.5	828.1	820.7	828.1	840.5	860.9	880.8	887.6	860.4	775.5
107.5°	931.2	931.1	927.0	922.0	927.0	931.1	931.2	921.1	888.8	818.9	705.6
110°	939.6	951.4	955.8	955.8	955.8	951.4	939.6	911.7	859.1	771.7	654.1



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	916.3	936.5	947.3	951.8	947.3	936.5	916.3	875.6	813.5	725.2	613.5
115°	859.1	888.8	906.2	914.3	906.2	888.8	859.1	810.8	743.3	658.5	562.4
117.5°	795.6	826.2	843.5	848.4	843.5	826.2	795.6	747.3	685.3	612.2	529.5
120°	754.4	784.2	800.9	805.8	800.9	784.2	754.4	708.6	654.1	586.0	511.6
122.5°	719.8	747.0	763.7	768.2	763.7	747.0	719.8	678.9	627.8	567.1	498.3
125°	675.2	700.5	714.2	720.3	714.2	700.5	675.2	640.5	595.9	542.0	478.8
127.5°	641.4	663.8	676.8	679.5	676.8	663.8	641.4	610.0	568.2	517.9	459.0
130°	620.7	641.1	653.5	657.2	653.5	641.1	620.7	589.7	549.4	501.1	446.6
132.5°	598.8	619.2	630.7	634.9	630.7	619.2	598.8	567.8	529.1	485.2	434.2
135°	563.0	583.4	594.6	598.3	594.6	583.4	563.0	535.8	500.5	460.8	418.1
137.5°	526.4	544.9	555.2	559.4	555.2	544.9	526.4	501.9	472.0	439.0	404.5
140°	503.6	519.7	528.9	532.0	528.9	519.7	503.6	480.6	454.6	426.1	397.0
142.5°	481.8	495.4	504.2	506.8	504.2	495.4	481.8	462.3	439.7	415.3	390.6
145°	452.2	462.7	469.5	472.0	469.5	462.7	452.2	437.3	420.6	401.4	382.1
147.5°	429.0	437.4	441.4	442.5	441.4	437.4	429.0	417.2	404.6	389.8	374.2
150°	415.7	423.0	425.6	426.1	425.6	423.0	415.7	406.3	395.1	383.4	369.8
152.5°	404.3	410.2	412.6	413.3	412.6	410.2	404.3	396.4	387.8	377.0	364.8
155°	389.0	393.3	395.1	395.8	395.1	393.3	389.0	382.8	376.0	367.3	357.4
157.5°	375.0	378.6	380.3	380.2	380.3	378.6	375.0	370.2	364.8	358.1	350.0
160°	366.1	369.2	370.4	369.8	370.4	369.2	366.1	361.7	357.4	351.2	345.0
162.5°	357.7	360.2	360.5	360.4	360.5	360.2	357.7	354.3	350.5	345.2	339.5
165°	345.6	346.9	346.9	346.9	346.9	346.9	345.6	343.2	340.1	336.4	332.0
167.5°	334.0	335.1	334.6	334.5	334.6	335.1	334.0	332.7	330.5	327.6	324.8
170°	327.0	327.6	327.6	327.0	327.6	327.6	327.0	325.8	324.6	322.7	320.8
172.5°	320.6	321.7	320.8	320.1	320.8	321.7	320.6	320.4	319.6	318.2	316.4
175°	312.8	313.4	312.2	311.6	312.2	313.4	312.8	312.8	312.8	311.6	311.6
177.5°	308.2	308.7	307.2	307.2	307.2	308.7	308.2	308.7	308.7	308.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	960.6	964.2	966.1	970.7	977.3	980.6	985.2	988.6	993.2	998.7	1003.4
5°	898.3	908.2	914.8	925.1	934.5	944.0	955.9	964.6	976.1	989.3	999.6
7.5°	840.6	852.9	863.9	877.5	893.1	905.3	920.8	936.7	954.7	973.4	991.0
10°	803.7	816.1	829.7	846.5	862.1	878.6	897.1	915.6	938.3	959.3	983.1
12.5°	767.2	780.9	796.1	814.9	833.9	854.9	873.8	894.6	918.9	946.1	971.6
15°	721.9	735.1	751.5	767.5	789.3	812.4	837.5	865.1	892.2	922.7	954.3
17.5°	673.3	687.8	705.8	724.5	747.4	774.4	799.0	829.2	859.7	895.2	932.4
20°	641.7	656.5	677.9	698.5	719.5	745.8	775.0	805.8	838.3	875.8	917.3
22.5°	616.7	627.2	648.2	669.2	693.8	720.7	749.3	781.5	816.9	855.6	899.2
25°	579.6	591.9	607.1	628.9	654.4	682.9	711.6	745.8	784.4	823.9	870.4
27.5°	546.6	556.7	571.8	588.9	614.3	643.7	674.4	710.0	749.6	789.9	838.7
30°	523.2	534.3	548.7	566.8	587.0	619.1	650.3	685.3	725.6	767.1	817.3
32.5°	502.8	514.3	526.6	543.8	565.6	594.1	626.3	660.6	701.6	744.4	793.3
35°	474.3	482.1	493.6	510.5	531.9	554.9	587.8	624.0	663.9	708.3	757.2
37.5°	441.6	451.6	463.1	477.8	496.5	521.4	552.0	588.6	625.7	668.2	712.9
40°	422.5	431.9	444.7	455.3	475.1	497.7	525.7	564.0	600.9	640.9	681.6
42.5°	403.1	412.2	422.9	436.3	454.0	476.0	502.0	537.7	577.3	614.9	649.0
45°	372.6	382.1	392.4	404.7	421.2	442.6	468.5	501.0	535.6	570.1	596.0
47.5°	343.6	352.5	362.3	374.9	390.1	410.7	433.9	462.6	496.1	525.5	544.1
50°	322.9	331.1	341.8	354.2	369.0	388.3	410.5	438.9	466.8	493.6	510.5
52.5°	302.5	311.7	322.4	333.1	347.3	366.6	387.1	411.6	438.2	460.0	474.0
55°	271.9	280.5	290.4	301.5	315.5	331.9	353.8	373.1	394.0	412.6	420.8
57.5°	242.3	249.9	259.2	270.8	283.4	298.7	315.9	334.5	349.3	362.4	371.7
60°	222.9	229.5	238.1	248.0	261.6	275.6	291.2	308.5	320.0	331.1	339.8
62.5°	203.2	209.5	217.8	226.6	238.6	251.6	266.6	280.5	291.8	299.2	309.2
65°	173.6	179.7	186.7	196.2	205.7	216.3	230.0	240.2	248.0	256.3	262.4
67.5°	146.0	151.1	157.8	165.2	173.2	183.5	194.0	202.6	207.9	212.9	220.2
70°	127.9	132.1	137.4	143.1	151.8	162.1	170.3	176.9	180.6	185.5	194.6
72.5°	109.5	114.2	119.3	125.1	132.1	140.7	147.9	154.5	156.9	160.8	166.6
75°	86.3	88.9	93.0	97.0	102.0	109.4	116.4	118.0	120.1	123.4	127.5
77.5°	65.4	67.6	69.2	71.9	75.8	81.8	85.5	87.9	88.4	89.7	93.7
80°	51.8	53.1	54.7	56.8	58.4	63.4	65.4	67.9	68.7	69.9	72.0
82.5°	38.0	39.2	40.2	42.0	44.6	46.6	48.6	51.1	51.3	52.1	52.6
85°	22.2	22.7	21.8	22.7	23.1	23.8	25.9	28.0	27.6	27.2	28.4
87.5°	10.0	9.9	9.3	10.1	9.3	9.4	9.2	9.3	9.7	10.1	10.6
90°	10.5	9.9	8.6	8.1	6.8	6.2	5.0	3.7	2.5	1.3	0.6
92.5°	161.7	199.7	202.9	141.3	84.6	50.8	32.7	22.0	14.3	9.2	7.5
95°	537.0	548.8	447.8	276.9	140.6	74.3	46.4	32.8	26.0	21.1	20.4
97.5°	679.5	586.1	399.9	221.0	121.1	77.3	57.2	45.0	38.2	34.7	33.9
100°	714.2	559.4	356.8	200.7	120.2	84.2	65.7	53.9	47.1	44.6	43.3
102.5°	693.4	512.2	324.1	192.3	124.6	92.7	74.5	63.8	56.5	54.5	53.8
105°	626.9	449.1	292.4	188.9	133.8	106.5	89.2	79.3	73.1	70.0	70.0
107.5°	559.0	405.6	279.0	194.6	147.4	121.0	105.4	95.1	90.1	87.1	85.9
110°	520.3	385.2	275.0	200.1	157.3	131.9	115.8	106.5	100.9	98.5	97.3



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	491.5	373.4	275.0	207.0	166.8	142.4	126.7	117.4	111.9	109.9	108.6
115°	460.2	360.5	276.9	217.4	181.5	158.6	143.1	133.8	128.3	126.4	125.1
117.5°	441.5	354.2	281.0	229.3	196.6	174.9	159.9	149.4	143.9	141.9	140.0
120°	431.1	351.2	284.9	237.3	207.5	185.8	170.3	159.8	154.2	151.8	149.9
122.5°	422.2	348.7	288.4	246.1	217.9	196.2	180.8	169.2	163.7	161.7	160.3
125°	410.0	345.6	294.2	258.3	231.6	211.2	195.1	183.3	177.8	174.7	173.4
127.5°	398.9	344.1	300.8	269.4	244.9	225.2	209.1	196.6	189.6	185.6	183.7
130°	391.5	343.2	304.8	276.9	253.3	234.2	218.0	205.0	196.9	192.0	190.1
132.5°	385.6	343.2	309.2	283.3	261.3	242.1	225.9	212.5	203.4	197.5	195.1
135°	378.4	343.2	315.3	292.4	272.0	252.7	236.0	223.0	213.1	205.7	203.2
137.5°	372.2	343.9	320.8	299.0	279.5	262.0	244.8	232.0	222.1	215.2	213.3
140°	369.2	344.4	323.3	303.5	284.9	267.0	250.3	238.4	228.5	221.1	219.3
142.5°	366.7	344.9	324.8	306.0	288.4	271.4	255.7	244.4	234.5	227.6	226.2
145°	363.0	344.4	326.5	309.7	294.2	278.1	263.9	252.7	244.1	237.8	236.6
147.5°	359.1	342.8	327.0	312.0	297.9	283.8	271.3	261.7	253.6	248.3	247.5
150°	356.2	341.3	327.0	313.4	300.4	286.8	276.2	267.6	259.5	255.2	254.0
152.5°	352.7	339.3	326.5	314.4	302.9	290.3	280.7	272.5	265.5	261.7	260.9
155°	346.9	335.7	325.2	315.3	305.4	294.9	286.1	280.0	273.8	270.1	270.1
157.5°	341.4	332.0	323.6	315.9	307.4	298.4	291.8	286.4	281.1	278.1	278.2
160°	337.0	329.5	322.1	315.9	308.5	300.4	294.9	289.9	285.6	283.0	283.7
162.5°	333.0	326.5	320.6	315.4	309.4	302.4	297.8	293.8	290.0	287.6	288.1
165°	327.0	322.1	318.4	314.7	309.7	304.8	301.0	298.6	295.5	293.6	294.9
167.5°	321.2	317.7	314.9	313.1	309.7	305.6	303.2	301.5	299.8	298.7	299.3
170°	317.7	315.3	313.4	312.2	309.7	306.6	304.8	303.5	302.3	301.7	302.3
172.5°	314.3	312.3	311.4	311.2	309.2	306.6	305.7	305.0	303.7	303.2	304.3
175°	309.7	309.1	309.1	309.7	308.5	306.6	306.6	306.6	306.0	305.4	306.6
177.5°	307.7	307.2	307.2	308.2	307.7	306.7	306.7	307.2	306.7	306.7	307.7
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1006.9	1010.0	1014.2	1019.1	1023.1	1027.4	1029.7	1029.7	1031.7	1035.9	1041.5
5°	1009.9	1020.6	1030.8	1044.0	1054.2	1066.2	1075.2	1083.9	1091.7	1101.5	1111.8
7.5°	1009.0	1026.7	1045.3	1066.0	1088.9	1107.1	1125.8	1140.4	1154.8	1173.8	1188.7
10°	1005.8	1028.7	1053.8	1080.1	1109.0	1134.1	1156.7	1177.3	1197.0	1217.6	1236.0
12.5°	999.8	1029.1	1059.8	1091.4	1127.8	1156.4	1185.7	1207.5	1230.6	1253.1	1275.9
15°	990.9	1025.5	1062.5	1106.5	1151.0	1183.0	1211.8	1240.2	1261.6	1287.1	1308.9
17.5°	972.6	1017.1	1063.7	1111.7	1154.4	1191.8	1221.9	1248.9	1271.7	1299.7	1329.4
20°	961.7	1009.9	1058.4	1109.8	1150.5	1188.7	1218.0	1245.9	1274.3	1310.9	1347.1
22.5°	946.6	998.0	1049.5	1098.3	1141.3	1178.2	1208.4	1242.7	1279.9	1321.4	1365.2
25°	922.7	975.7	1026.7	1073.2	1115.2	1153.0	1194.1	1240.2	1285.5	1340.1	1403.1
27.5°	892.3	943.4	989.0	1038.1	1079.7	1127.9	1179.2	1229.2	1294.4	1369.7	1448.3
30°	869.6	918.1	961.3	1007.8	1055.1	1108.2	1165.8	1224.6	1302.3	1390.8	1484.2
32.5°	843.3	887.2	930.0	974.9	1029.4	1087.7	1149.0	1220.9	1313.8	1414.4	1511.1
35°	797.6	837.1	878.6	928.4	986.4	1049.7	1127.9	1215.5	1327.8	1436.0	1522.8
37.5°	749.7	780.9	822.6	875.1	938.3	1011.5	1100.3	1206.7	1322.1	1419.1	1456.0
40°	712.9	742.0	786.1	841.2	903.7	983.9	1083.5	1192.9	1308.9	1376.3	1373.5
42.5°	676.3	705.8	748.2	803.7	868.9	958.6	1061.1	1174.8	1272.7	1298.4	1244.8
45°	620.3	647.8	689.4	745.4	815.3	909.5	1017.2	1126.2	1188.7	1147.2	1041.1
47.5°	563.2	589.9	628.5	683.3	759.6	858.3	960.1	1049.6	1058.4	969.2	841.9
50°	525.7	550.8	587.4	645.8	719.9	816.1	914.4	984.8	963.0	854.0	722.7
52.5°	489.2	513.3	547.6	602.7	678.3	772.7	860.5	915.6	865.2	749.3	631.2
55°	435.2	458.2	492.8	543.4	612.0	698.5	775.4	795.5	721.5	604.7	509.2
57.5°	384.0	400.8	435.0	479.7	545.9	622.1	677.2	673.6	591.9	486.7	418.3
60°	350.1	365.3	397.8	438.9	501.8	570.1	608.8	592.3	509.6	422.9	357.0
62.5°	318.5	332.7	359.9	397.8	451.8	511.2	539.3	516.7	438.6	362.3	310.0
65°	270.7	280.9	302.8	337.7	380.1	421.2	446.3	413.0	343.9	286.3	246.8
67.5°	226.0	234.9	254.3	279.4	308.6	337.0	347.1	315.9	262.2	223.4	195.6
70°	197.0	205.3	218.4	241.9	261.2	281.4	286.3	258.3	213.5	183.9	166.6
72.5°	169.4	177.0	188.5	205.0	218.4	230.0	232.3	206.4	172.0	151.6	138.3
75°	129.1	135.8	143.1	149.3	158.0	160.0	159.1	139.0	120.5	106.9	99.6
77.5°	94.9	97.7	102.2	104.6	105.0	104.9	100.7	87.9	78.4	72.8	69.8
80°	73.2	75.3	76.5	77.3	77.7	73.6	69.1	61.3	58.0	54.7	51.0
82.5°	53.2	54.6	55.8	55.9	53.7	50.3	46.1	42.2	39.9	38.3	36.8
85°	28.8	29.2	28.8	26.8	23.8	22.7	21.8	21.0	20.6	20.1	20.1
87.5°	10.5	9.7	8.3	8.9	9.1	9.0	9.2	9.0	8.9	9.0	9.1
90°	1.3	2.5	3.7	5.0	6.2	6.8	8.1	8.6	9.9	10.5	11.2
92.5°	9.2	14.3	22.0	32.7	50.8	84.6	141.3	202.9	199.7	161.7	109.8
95°	21.1	26.0	32.8	46.4	74.3	140.6	276.9	447.8	548.8	537.0	445.4
97.5°	34.7	38.2	45.0	57.2	77.3	121.1	221.0	399.9	586.1	679.5	663.3
100°	44.6	47.1	53.9	65.7	84.2	120.2	200.7	356.8	559.4	714.2	761.8
102.5°	54.5	56.5	63.8	74.5	92.7	124.6	192.3	324.1	512.2	693.4	795.0
105°	70.0	73.1	79.3	89.2	106.5	133.8	188.9	292.4	449.1	626.9	775.5
107.5°	87.1	90.1	95.1	105.4	121.0	147.4	194.6	279.0	405.6	559.0	705.6
110°	98.5	100.9	106.5	115.8	131.9	157.3	200.1	275.0	385.2	520.3	654.1



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.9	111.9	117.4	126.7	142.4	166.8	207.0	275.0	373.4	491.5	613.5
115°	126.4	128.3	133.8	143.1	158.6	181.5	217.4	276.9	360.5	460.2	562.4
117.5°	141.9	143.9	149.4	159.9	174.9	196.6	229.3	281.0	354.2	441.5	529.5
120°	151.8	154.2	159.8	170.3	185.8	207.5	237.3	284.9	351.2	431.1	511.6
122.5°	161.7	163.7	169.2	180.8	196.2	217.9	246.1	288.4	348.7	422.2	498.3
125°	174.7	177.8	183.3	195.1	211.2	231.6	258.3	294.2	345.6	410.0	478.8
127.5°	185.6	189.6	196.6	209.1	225.2	244.9	269.4	300.8	344.1	398.9	459.0
130°	192.0	196.9	205.0	218.0	234.2	253.3	276.9	304.8	343.2	391.5	446.6
132.5°	197.5	203.4	212.5	225.9	242.1	261.3	283.3	309.2	343.2	385.6	434.2
135°	205.7	213.1	223.0	236.0	252.7	272.0	292.4	315.3	343.2	378.4	418.1
137.5°	215.2	222.1	232.0	244.8	262.0	279.5	299.0	320.8	343.9	372.2	404.5
140°	221.1	228.5	238.4	250.3	267.0	284.9	303.5	323.3	344.4	369.2	397.0
142.5°	227.6	234.5	244.4	255.7	271.4	288.4	306.0	324.8	344.9	366.7	390.6
145°	237.8	244.1	252.7	263.9	278.1	294.2	309.7	326.5	344.4	363.0	382.1
147.5°	248.3	253.6	261.7	271.3	283.8	297.9	312.0	327.0	342.8	359.1	374.2
150°	255.2	259.5	267.6	276.2	286.8	300.4	313.4	327.0	341.3	356.2	369.8
152.5°	261.7	265.5	272.5	280.7	290.3	302.9	314.4	326.5	339.3	352.7	364.8
155°	270.1	273.8	280.0	286.1	294.9	305.4	315.3	325.2	335.7	346.9	357.4
157.5°	278.1	281.1	286.4	291.8	298.4	307.4	315.9	323.6	332.0	341.4	350.0
160°	283.0	285.6	289.9	294.9	300.4	308.5	315.9	322.1	329.5	337.0	345.0
162.5°	287.6	290.0	293.8	297.8	302.4	309.4	315.4	320.6	326.5	333.0	339.5
165°	293.6	295.5	298.6	301.0	304.8	309.7	314.7	318.4	322.1	327.0	332.0
167.5°	298.7	299.8	301.5	303.2	305.6	309.7	313.1	314.9	317.7	321.2	324.8
170°	301.7	302.3	303.5	304.8	306.6	309.7	312.2	313.4	315.3	317.7	320.8
172.5°	303.2	303.7	305.0	305.7	306.6	309.2	311.2	311.4	312.3	314.3	316.4
175°	305.4	306.0	306.6	306.6	306.6	308.5	309.7	309.1	309.1	309.7	311.6
177.5°	306.7	306.7	307.2	306.7	306.7	307.7	308.2	307.2	307.2	307.7	308.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2	307.2



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1045.8	1045.8	1051.4	1051.1	1054.7	1053.4	1054.0
5°	1124.2	1131.2	1137.3	1141.5	1147.6	1149.3	1148.4
7.5°	1205.5	1221.0	1228.6	1239.0	1240.9	1246.3	1245.7
10°	1255.8	1271.1	1282.5	1291.6	1296.2	1301.9	1302.3
12.5°	1295.3	1308.2	1318.4	1326.8	1332.3	1334.1	1335.2
15°	1326.2	1340.5	1352.5	1364.4	1371.4	1376.7	1379.7
17.5°	1357.2	1379.5	1400.5	1416.7	1426.5	1434.6	1434.6
20°	1381.2	1406.8	1433.1	1451.6	1470.5	1478.8	1480.0
22.5°	1406.9	1446.0	1479.9	1508.6	1533.4	1542.0	1545.2
25°	1460.2	1511.2	1563.5	1603.9	1632.6	1649.5	1651.9
27.5°	1524.6	1593.7	1648.7	1685.8	1709.8	1722.3	1725.0
30°	1570.1	1633.9	1683.2	1711.2	1722.3	1723.9	1717.8
32.5°	1590.5	1638.2	1657.9	1656.2	1634.4	1619.9	1614.4
35°	1565.6	1555.7	1507.5	1450.0	1406.0	1378.0	1370.6
37.5°	1424.7	1339.6	1251.0	1164.0	1117.7	1094.2	1053.7
40°	1285.9	1164.5	1072.4	999.2	946.9	904.9	895.1
42.5°	1129.2	1003.9	911.8	849.1	807.4	778.6	766.0
45°	907.4	799.6	723.6	675.4	643.3	622.3	612.9
47.5°	725.8	642.4	586.9	551.3	526.9	508.6	503.5
50°	626.1	559.4	512.5	482.5	464.0	450.0	444.3
52.5°	543.8	490.0	453.9	429.2	411.7	403.0	398.2
55°	448.8	402.3	376.4	356.6	346.7	339.8	336.4
57.5°	367.0	333.4	314.5	300.9	291.8	287.2	285.7
60°	321.2	294.9	277.7	267.0	260.8	255.0	253.4
62.5°	280.7	260.1	246.7	237.3	231.2	228.7	227.8
65°	226.2	212.7	202.8	197.0	192.1	191.3	190.8
67.5°	179.8	171.8	166.7	160.7	158.9	156.1	155.5
70°	153.8	148.5	142.4	140.3	138.2	135.3	135.8
72.5°	130.5	125.2	121.0	118.2	117.5	116.2	117.3
75°	95.5	93.8	92.1	90.1	89.3	89.3	88.9
77.5°	68.1	66.7	64.9	63.7	63.5	61.7	62.3
80°	49.4	47.3	46.5	46.9	45.6	45.2	45.2
82.5°	36.5	35.8	34.9	35.0	34.8	34.4	34.7
85°	20.1	19.7	19.7	19.3	19.3	18.9	18.9
87.5°	9.6	10.1	9.7	9.3	9.3	9.7	10.1
90°	11.8	12.4	13.6	13.6	13.6	14.3	14.3
92.5°	79.7	60.0	50.8	42.9	41.4	40.5	39.5
95°	351.2	275.0	223.0	179.0	160.4	155.5	145.5
97.5°	597.2	523.0	450.7	412.4	377.7	359.7	351.8
100°	731.5	667.7	603.3	560.5	515.9	493.1	483.2
102.5°	813.8	783.2	739.6	693.9	662.1	637.2	629.8
105°	860.4	887.6	880.8	860.9	840.5	828.1	820.7
107.5°	818.9	888.8	921.1	931.2	931.1	927.0	922.0
110°	771.7	859.1	911.7	939.6	951.4	955.8	955.8



TEST NUMBER: P333564-927

CATALOG NUMBER: S125RDIP-S850D810U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	725.2	813.5	875.6	916.3	936.5	947.3	951.8
115°	658.5	743.3	810.8	859.1	888.8	906.2	914.3
117.5°	612.2	685.3	747.3	795.6	826.2	843.5	848.4
120°	586.0	654.1	708.6	754.4	784.2	800.9	805.8
122.5°	567.1	627.8	678.9	719.8	747.0	763.7	768.2
125°	542.0	595.9	640.5	675.2	700.5	714.2	720.3
127.5°	517.9	568.2	610.0	641.4	663.8	676.8	679.5
130°	501.1	549.4	589.7	620.7	641.1	653.5	657.2
132.5°	485.2	529.1	567.8	598.8	619.2	630.7	634.9
135°	460.8	500.5	535.8	563.0	583.4	594.6	598.3
137.5°	439.0	472.0	501.9	526.4	544.9	555.2	559.4
140°	426.1	454.6	480.6	503.6	519.7	528.9	532.0
142.5°	415.3	439.7	462.3	481.8	495.4	504.2	506.8
145°	401.4	420.6	437.3	452.2	462.7	469.5	472.0
147.5°	389.8	404.6	417.2	429.0	437.4	441.4	442.5
150°	383.4	395.1	406.3	415.7	423.0	425.6	426.1
152.5°	377.0	387.8	396.4	404.3	410.2	412.6	413.3
155°	367.3	376.0	382.8	389.0	393.3	395.1	395.8
157.5°	358.1	364.8	370.2	375.0	378.6	380.3	380.2
160°	351.2	357.4	361.7	366.1	369.2	370.4	369.8
162.5°	345.2	350.5	354.3	357.7	360.2	360.5	360.4
165°	336.4	340.1	343.2	345.6	346.9	346.9	346.9
167.5°	327.6	330.5	332.7	334.0	335.1	334.6	334.5
170°	322.7	324.6	325.8	327.0	327.6	327.6	327.0
172.5°	318.2	319.6	320.4	320.6	321.7	320.8	320.1
175°	311.6	312.8	312.8	312.8	313.4	312.2	311.6
177.5°	308.7	308.7	308.7	308.2	308.7	307.2	307.2
180°	307.2	307.2	307.2	307.2	307.2	307.2	307.2

(END OF REPORT)