

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333261-830

Luminaire Tested: **S125DIP-S1090D590U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333261-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6230.7 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	73	73	73	68																				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58																				
2	93	86	80	74	88	81	76	71	73	68	65	65	61	58	57	55	53	49																				
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42																				
4	78	67	59	53	73	64	56	51	57	51	47	51	47	43	46	42	39	36																				
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31																				
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	28																				
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24																				
8	57	44	37	31	54	42	35	30	39	32	28	35	30	26	31	27	24	22																				
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20																				
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	2.3
10°-20°	429.6	6.9
20°-30°	697.6	11.2
30°-40°	850.9	13.7
40°-50°	774.1	12.4
50°-60°	616.6	9.9
60°-70°	429.5	6.9
70°-80°	229.0	3.7
80°-90°	59.3	1.0
90°-100°	193.3	3.1
100°-110°	415.5	6.7
110°-120°	390.0	6.3
120°-130°	316.0	5.1
130°-140°	253.6	4.1
140°-150°	191.4	3.1
150°-160°	134.7	2.2
160°-170°	79.4	1.3
170°-180°	25.8	0.4
0°-30°	1271.5	20.4
0°-40°	2122.4	34.1
0°-60°	3513.1	56.4
0°-90°	4230.9	67.9
90°-120°	998.8	16.0
90°-150°	1759.9	28.2
90°-180°	2000.0	32.1
0°-180°	6230.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	12	1	12	1	12	10
95°	126	18	126	18	126	179
105°	712	61	712	61	712	708
115°	794	109	794	109	794	775
125°	625	150	625	150	625	566
135°	519	176	519	176	519	402
145°	410	205	410	205	410	260
155°	344	234	344	234	344	160
165°	301	256	301	256	301	86
175°	270	266	270	266	270	26
180°	267	267	267	267	267	



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	14.7	15.7	16.1	16.1	16.6	16.4	18.3	18.2	19.6	21.0	22.9
90°	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7	9.1	8.6	7.5
92.5°	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3	140.3	173.3	176.2
95°	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5	466.2	476.4	388.7
97.5°	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7	589.8	508.7	347.1
100°	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3	619.9	485.5	309.7
102.5°	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1	601.8	444.6	281.3
105°	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2	544.1	389.8	253.7
107.5°	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5	485.2	352.0	242.1
110°	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8	451.7	334.4	238.7



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5	426.7	324.1	238.7
115°	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1	399.4	312.9	240.3
117.5°	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6	383.2	307.5	243.8
120°	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1	374.2	304.8	247.3
122.5°	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5	366.5	302.7	250.3
125°	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6	355.9	300.0	255.4
127.5°	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4	346.3	298.7	261.1
130°	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7	339.8	297.8	264.6
132.5°	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9	334.6	297.8	268.4
135°	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9	328.5	297.8	273.6
137.5°	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1	323.0	298.5	278.5
140°	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6	320.5	299.0	280.7
142.5°	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0	318.3	299.4	281.9
145°	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8	315.1	299.0	283.3
147.5°	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9	311.7	297.6	283.9
150°	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9	309.2	296.2	283.9
152.5°	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7	306.1	294.5	283.4
155°	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2	301.0	291.4	282.3
157.5°	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8	296.3	288.1	280.9
160°	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4	292.5	286.1	279.6
162.5°	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7	289.1	283.4	278.3
165°	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1	283.9	279.6	276.4
167.5°	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9	278.8	275.8	273.3
170°	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5	275.8	273.6	272.0
172.5°	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7	272.8	271.1	270.3
175°	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4	268.8	268.2	268.2
177.5°	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5	267.1	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	23.8	22.5	20.5	18.7	15.9	14.1	13.5	13.9	12.4	12.2	12.8
90°	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6	1.0	2.2	3.2
92.5°	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6	7.9	12.4	19.1
95°	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7	18.3	22.6	28.5
97.5°	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5	30.1	33.1	39.0
100°	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6	38.7	40.9	46.8
102.5°	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7	47.3	49.0	55.4
105°	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8	60.8	63.4	68.8
107.5°	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6	75.6	78.1	82.6
110°	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5	85.5	87.7	92.5



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3	95.4	97.1	102.0
115°	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6	109.7	111.3	116.1
117.5°	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5	123.1	124.9	129.7
120°	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1	131.8	133.8	138.7
122.5°	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1	140.3	142.0	146.8
125°	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5	151.7	154.3	159.1
127.5°	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5	161.1	164.6	170.7
130°	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0	166.6	171.0	178.0
132.5°	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4	171.4	176.5	184.5
135°	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3	178.5	184.9	193.6
137.5°	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2	186.8	192.8	201.4
140°	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3	191.9	198.4	207.0
142.5°	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3	197.6	203.6	212.2
145°	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4	206.4	211.8	219.3
147.5°	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8	215.5	220.1	227.1
150°	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5	221.5	225.3	232.2
152.5°	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5	227.1	230.5	236.6
155°	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4	234.4	237.6	243.0
157.5°	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5	241.4	244.0	248.6
160°	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3	245.7	247.9	251.7
162.5°	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2	249.6	251.8	255.1
165°	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9	254.9	256.5	259.1
167.5°	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8	259.3	260.2	261.7
170°	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4	261.8	262.4	263.4
172.5°	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1	263.2	263.6	264.8
175°	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2	265.0	265.6	266.2
177.5°	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1	266.3	266.3	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	13.6	14.8	14.4	15.2	15.3	16.5	16.1	18.2	19.3	20.5	20.2
90°	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7	10.2	10.7	11.8
92.5°	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3	69.2	52.0	44.1
95°	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5	304.8	238.7	193.6
97.5°	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7	518.4	454.0	391.2
100°	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3	635.0	579.6	523.7
102.5°	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1	706.3	679.8	642.0
105°	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2	746.8	770.4	764.5
107.5°	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5	710.8	771.6	799.6
110°	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8	670.0	745.7	791.5



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5	629.5	706.2	760.1
115°	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1	571.6	645.2	703.8
117.5°	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6	531.4	594.8	648.7
120°	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1	508.6	567.8	615.1
122.5°	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5	492.3	545.0	589.3
125°	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6	470.4	517.3	555.9
127.5°	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4	449.6	493.2	529.5
130°	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7	435.0	476.9	511.8
132.5°	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9	421.2	459.3	492.9
135°	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9	400.0	434.4	465.1
137.5°	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1	381.1	409.7	435.7
140°	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6	369.9	394.6	417.3
142.5°	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0	360.4	381.7	401.3
145°	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8	348.4	365.0	379.6
147.5°	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9	338.4	351.2	362.1
150°	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9	332.8	343.0	352.7
152.5°	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7	327.3	336.6	344.1
155°	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2	318.9	326.3	332.2
157.5°	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8	310.9	316.7	321.3
160°	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4	304.8	310.2	314.0
162.5°	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7	299.7	304.2	307.6
165°	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1	291.9	295.2	297.8
167.5°	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9	284.5	286.9	288.8
170°	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5	280.1	281.7	282.8
172.5°	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7	276.3	277.4	278.1
175°	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4	270.4	271.5	271.5
177.5°	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5	268.0	268.0	268.0
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	21.2	20.6	20.8	21.8	20.8	20.6	21.2	20.2	20.5	19.3	18.2
90°	11.8	11.8	12.3	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7
92.5°	37.2	35.9	35.2	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3
95°	155.4	139.2	135.0	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5
97.5°	358.0	327.8	312.3	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7
100°	486.5	447.9	428.0	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3
102.5°	602.3	574.8	553.2	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1
105°	747.3	729.6	718.9	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2
107.5°	808.3	808.2	804.6	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5
110°	815.6	825.9	829.6	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	795.4	812.9	822.3	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5
115°	745.7	771.6	786.6	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1
117.5°	690.6	717.3	732.2	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6
120°	654.9	680.7	695.2	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1
122.5°	624.7	648.4	662.9	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5
125°	586.1	608.1	619.9	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6
127.5°	556.8	576.3	587.4	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4
130°	538.8	556.5	567.2	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7
132.5°	519.8	537.5	547.4	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9
135°	488.7	506.4	516.1	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9
137.5°	456.9	473.1	481.9	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1
140°	437.2	451.1	459.1	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6
142.5°	418.2	430.0	437.6	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0
145°	392.5	401.6	407.6	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8
147.5°	372.4	379.7	383.1	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9
150°	360.8	367.2	369.4	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9
152.5°	350.9	356.0	358.2	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7
155°	337.6	341.4	343.0	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2
157.5°	325.5	328.6	330.1	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8
160°	317.7	320.5	321.5	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4
162.5°	310.5	312.7	312.9	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7
165°	300.0	301.0	301.0	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1
167.5°	289.9	290.9	290.4	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9
170°	283.9	284.5	284.5	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5
172.5°	278.3	279.3	278.4	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7
175°	271.5	272.0	271.0	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4
177.5°	267.5	268.0	266.6	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	16.1	16.5	15.3	15.2	14.4	14.8	13.6	12.8	12.2	12.4	13.9
90°	9.1	8.6	7.5	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6
92.5°	140.3	173.3	176.2	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6
95°	466.2	476.4	388.7	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7
97.5°	589.8	508.7	347.1	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5
100°	619.9	485.5	309.7	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6
102.5°	601.8	444.6	281.3	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7
105°	544.1	389.8	253.7	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8
107.5°	485.2	352.0	242.1	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6
110°	451.7	334.4	238.7	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	426.7	324.1	238.7	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3
115°	399.4	312.9	240.3	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6
117.5°	383.2	307.5	243.8	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5
120°	374.2	304.8	247.3	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1
122.5°	366.5	302.7	250.3	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1
125°	355.9	300.0	255.4	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5
127.5°	346.3	298.7	261.1	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5
130°	339.8	297.8	264.6	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0
132.5°	334.6	297.8	268.4	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4
135°	328.5	297.8	273.6	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3
137.5°	323.0	298.5	278.5	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2
140°	320.5	299.0	280.7	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3
142.5°	318.3	299.4	281.9	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3
145°	315.1	299.0	283.3	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4
147.5°	311.7	297.6	283.9	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8
150°	309.2	296.2	283.9	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5
152.5°	306.1	294.5	283.4	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5
155°	301.0	291.4	282.3	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4
157.5°	296.3	288.1	280.9	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5
160°	292.5	286.1	279.6	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3
162.5°	289.1	283.4	278.3	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2
165°	283.9	279.6	276.4	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9
167.5°	278.8	275.8	273.3	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8
170°	275.8	273.6	272.0	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4
172.5°	272.8	271.1	270.3	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1
175°	268.8	268.2	268.2	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2
177.5°	267.1	266.6	266.6	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.5	14.1	15.9	18.7	20.5	22.5	23.8	22.9	21.0	19.6	18.2
90°	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7
92.5°	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3
95°	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5
97.5°	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7
100°	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3
102.5°	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1
105°	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2
107.5°	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5
110°	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5
115°	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1
117.5°	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6
120°	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1
122.5°	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5
125°	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6
127.5°	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4
130°	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7
132.5°	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9
135°	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9
137.5°	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1
140°	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6
142.5°	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0
145°	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8
147.5°	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9
150°	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9
152.5°	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7
155°	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2
157.5°	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8
160°	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4
162.5°	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7
165°	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1
167.5°	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9
170°	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5
172.5°	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7
175°	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4
177.5°	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	18.3	16.4	16.6	16.1	16.1	15.7	14.7
90°	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333261-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)