

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333266-830

Luminaire Tested: **S125DIP-S1090D590U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333266-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6114.7 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94		83	83	83		73	73	73	68
1	102	97	93	90	96	92	88	85	82	79	77		73	71	69		64	63	62	57
2	93	85	79	73	87	80	75	70	72	67	64		64	61	58		57	54	52	48
3	85	75	67	61	80	71	64	58	63	58	53		57	52	49		50	47	44	41
4	77	66	58	52	73	63	55	50	56	50	46		50	46	42		45	41	38	35
5	71	59	51	44	67	56	48	43	51	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35		41	36	32		37	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31		37	32	28		34	29	26	24
8	56	44	36	30	53	42	34	29	38	32	27		34	29	25		31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	24		32	26	23		28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22		29	24	21		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	2.5
10°-20°	428.4	7.0
20°-30°	632.5	10.3
30°-40°	738.0	12.1
40°-50°	741.2	12.1
50°-60°	650.7	10.6
60°-70°	484.8	7.9
70°-80°	277.2	4.5
80°-90°	82.2	1.3
90°-100°	46.3	0.8
100°-110°	136.7	2.2
110°-120°	231.5	3.8
120°-130°	304.6	5.0
130°-140°	341.3	5.6
140°-150°	334.5	5.5
150°-160°	281.0	4.6
160°-170°	186.8	3.1
170°-180°	65.4	1.1
0°-30°	1212.5	19.8
0°-40°	1950.5	31.9
0°-60°	3342.4	54.7
0°-90°	4186.6	68.5
90°-120°	414.4	6.8
90°-150°	1394.9	22.8
90°-180°	1928.0	31.5
0°-180°	6114.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	1	5	9	11	13	6
95°	35	36	41	45	46	37
105°	123	125	128	132	133	131
115°	232	234	235	234	234	229
125°	338	341	342	341	340	303
135°	440	443	444	444	442	339
145°	533	535	537	536	535	333
155°	610	610	610	612	610	281
165°	663	662	662	664	661	187
175°	689	687	687	690	687	65
180°	691	691	691	691	691	



TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.6	27.8	28.0	28.2	28.4	28.5	28.4	28.3	28.3	28.2	28.3
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	13.0	13.7	14.3	15.0	15.6	16.5	17.5	18.6	19.6	20.6	21.4
95°	35.0	35.2	35.4	35.6	35.9	36.7	37.8	39.0	40.2	41.4	42.2
97.5°	58.1	58.2	58.2	58.3	58.4	59.3	61.0	62.6	64.3	65.9	66.7
100°	75.3	75.3	75.3	75.3	75.3	76.1	77.6	79.2	80.7	82.3	83.3
102.5°	93.8	94.3	94.7	95.2	95.7	96.3	97.1	97.9	98.7	99.4	100.7
105°	122.6	123.2	123.8	124.4	125.0	125.6	126.4	127.1	127.8	128.5	129.2
107.5°	154.4	155.0	155.6	156.2	156.8	157.4	158.0	158.4	159.0	159.6	159.9
110°	176.3	176.9	177.6	178.1	178.8	179.3	179.6	179.9	180.3	180.7	181.1



TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	198.7	199.1	199.3	199.6	200.0	200.4	200.9	201.2	201.7	202.2	202.4
115°	231.8	232.2	232.7	233.2	233.7	234.0	234.2	234.5	234.7	235.0	234.9
117.5°	264.9	265.0	265.3	265.5	265.7	266.0	266.2	266.4	266.6	266.8	266.9
120°	285.5	286.2	286.7	287.3	287.9	288.2	288.4	288.5	288.6	288.7	288.7
122.5°	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.6	309.9	310.3	310.2
125°	338.2	338.9	339.6	340.4	341.1	341.5	341.6	341.8	341.9	342.0	341.8
127.5°	370.5	370.9	371.3	371.6	372.1	372.4	372.5	372.7	372.8	373.0	372.9
130°	389.8	390.4	391.1	391.6	392.2	392.7	392.9	393.1	393.3	393.6	393.5
132.5°	409.2	410.2	411.1	412.1	413.1	413.6	413.5	413.5	413.4	413.4	413.3
135°	439.8	440.5	441.3	442.0	442.7	443.1	443.3	443.4	443.5	443.6	443.6
137.5°	468.6	469.4	470.0	470.7	471.5	471.9	472.2	472.4	472.7	473.0	473.1
140°	487.1	487.8	488.3	488.9	489.6	490.0	490.4	490.8	491.1	491.4	491.7
142.5°	505.7	506.1	506.6	507.2	507.7	508.1	508.6	509.1	509.5	509.9	510.1
145°	532.8	533.3	533.9	534.3	534.8	535.2	535.6	535.9	536.3	536.6	536.6
147.5°	558.0	558.3	558.6	558.8	559.1	559.3	559.6	560.0	560.2	560.5	560.8
150°	574.8	574.7	574.6	574.5	574.3	574.5	575.0	575.4	575.9	576.4	576.4
152.5°	588.5	588.7	588.9	589.1	589.2	589.4	589.6	589.7	589.9	590.2	590.5
155°	609.7	609.7	609.7	609.7	609.7	609.8	609.9	610.0	610.2	610.3	610.8
157.5°	628.7	628.4	628.1	627.9	627.6	627.5	627.6	627.8	627.9	628.0	628.5
160°	639.9	639.5	639.1	638.8	638.4	638.3	638.4	638.6	638.7	638.8	639.2
162.5°	649.8	649.5	649.2	648.9	648.7	648.6	648.6	648.7	648.7	648.7	649.2
165°	663.0	662.7	662.5	662.2	662.0	661.9	662.0	662.2	662.3	662.4	662.9
167.5°	674.2	673.7	673.2	672.7	672.2	672.0	672.0	672.0	672.0	672.0	672.7
170°	680.1	679.7	679.2	678.7	678.3	678.1	678.1	678.1	678.1	678.1	678.7
172.5°	684.5	684.0	683.5	683.1	682.6	682.3	682.3	682.3	682.3	682.3	683.1
175°	689.3	688.8	688.3	687.9	687.4	687.2	687.2	687.2	687.2	687.2	687.9
177.5°	691.8	691.4	691.1	690.7	690.2	690.0	689.9	689.8	689.8	689.7	690.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	28.5	28.6	28.7	28.6	28.2	27.8	27.4	27.1
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	22.2	23.0	23.8	24.3	24.6	24.9	25.1	25.4
95°	43.1	43.9	44.8	45.2	45.5	45.8	46.0	46.3
97.5°	67.5	68.3	69.1	69.6	69.7	69.8	69.9	70.1
100°	84.5	85.5	86.5	87.2	87.5	87.8	87.9	88.2
102.5°	101.8	103.0	104.2	104.9	105.3	105.6	105.9	106.2
105°	130.0	130.6	131.4	132.0	132.2	132.6	133.0	133.4
107.5°	160.3	160.7	161.0	161.2	161.2	161.2	161.1	161.1
110°	181.3	181.7	182.1	182.2	182.1	182.0	181.8	181.7



TEST NUMBER: P333266-830

CATALOG NUMBER: S125DIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.6	202.6	202.8	202.8	202.6	202.4	202.2	202.0
115°	234.7	234.6	234.5	234.4	234.2	234.1	234.0	233.9
117.5°	267.0	267.1	267.2	267.0	266.6	266.1	265.6	265.0
120°	288.7	288.7	288.7	288.5	288.0	287.6	287.1	286.6
122.5°	310.1	310.0	309.9	309.6	309.2	308.9	308.5	308.1
125°	341.5	341.3	341.0	340.8	340.7	340.6	340.4	340.4
127.5°	372.7	372.6	372.5	372.3	372.0	371.8	371.6	371.4
130°	393.3	393.2	393.1	392.9	392.7	392.5	392.2	392.0
132.5°	413.1	413.0	412.9	412.6	412.4	412.0	411.7	411.3
135°	443.6	443.6	443.6	443.4	442.9	442.4	442.0	441.5
137.5°	473.3	473.3	473.5	473.3	472.7	472.1	471.6	470.9
140°	491.9	492.2	492.4	492.2	491.6	491.1	490.4	489.8
142.5°	510.2	510.4	510.5	510.3	509.7	509.1	508.5	507.9
145°	536.6	536.6	536.6	536.4	536.1	535.7	535.4	535.0
147.5°	561.1	561.4	561.7	561.4	560.5	559.8	558.9	558.2
150°	576.4	576.4	576.4	576.3	576.1	575.8	575.6	575.3
152.5°	590.8	591.1	591.4	591.3	590.8	590.4	589.9	589.6
155°	611.2	611.7	612.2	612.2	611.5	611.0	610.3	609.7
157.5°	629.0	629.4	629.9	629.8	629.0	628.2	627.5	626.6
160°	639.7	640.2	640.6	640.6	640.1	639.4	638.9	638.3
162.5°	649.8	650.4	651.0	650.9	650.3	649.5	648.8	648.1
165°	663.4	663.8	664.4	664.2	663.5	662.8	662.0	661.4
167.5°	673.4	674.2	674.9	674.9	674.1	673.4	672.6	671.9
170°	679.5	680.1	680.9	680.8	680.0	679.2	678.3	677.5
172.5°	683.8	684.5	685.2	685.2	684.5	683.7	683.0	682.2
175°	688.6	689.3	690.0	689.9	689.2	688.3	687.5	686.6
177.5°	690.8	691.4	691.9	691.9	691.3	690.6	689.8	689.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0

(END OF REPORT)