

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333270-830

Luminaire Tested: **S125DIP-S1090D810U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333270-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D810U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6972.6 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	43	36	30	52	41	34	29	37	31	27	32	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	35	28	23	31	25	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	2.1
10°-20°	429.6	6.2
20°-30°	697.6	10.0
30°-40°	850.9	12.2
40°-50°	774.1	11.1
50°-60°	616.6	8.8
60°-70°	429.5	6.2
70°-80°	229.0	3.3
80°-90°	59.8	0.9
90°-100°	264.9	3.8
100°-110°	569.6	8.2
110°-120°	534.5	7.7
120°-130°	433.2	6.2
130°-140°	347.7	5.0
140°-150°	262.4	3.8
150°-160°	184.7	2.6
160°-170°	108.8	1.6
170°-180°	35.4	0.5
0°-30°	1271.5	18.2
0°-40°	2122.4	30.4
0°-60°	3513.1	50.4
0°-90°	4231.4	60.7
90°-120°	1369.1	19.6
90°-150°	2412.3	34.6
90°-180°	2741.0	39.3
0°-180°	6972.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	17	1	17	1	17	13
95°	173	24	173	24	173	245
105°	976	83	976	83	976	971
115°	1088	149	1088	149	1088	1063
125°	857	206	857	206	857	775
135°	712	242	712	242	712	552
145°	562	282	562	282	562	357
155°	471	321	471	321	471	219
165°	413	351	413	351	413	118
175°	371	365	371	365	371	36
180°	366	366	366	366	366	



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	15.6	16.6	17.0	17.0	17.5	17.2	19.0	18.9	20.4	21.7	23.5
90°	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3	12.5	11.8	10.3
92.5°	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6	192.4	237.6	241.4
95°	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9	638.9	653.0	532.8
97.5°	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2	808.4	697.3	475.8
100°	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4	849.7	665.5	424.5
102.5°	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9	825.0	609.4	385.6
105°	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7	745.8	534.3	347.9
107.5°	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5	665.1	482.6	332.0
110°	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3	619.1	458.4	327.3



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9	584.8	444.2	327.3
115°	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2	547.5	429.0	329.4
117.5°	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0	525.3	421.4	334.3
120°	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7	512.9	417.8	339.0
122.5°	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9	502.3	414.9	343.1
125°	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7	487.9	411.2	350.1
127.5°	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1	474.6	409.4	357.9
130°	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3	465.8	408.3	362.6
132.5°	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6	458.7	408.3	367.9
135°	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5	450.3	408.3	375.1
137.5°	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3	442.8	409.2	381.7
140°	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4	439.2	409.7	384.7
142.5°	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8	436.3	410.4	386.4
145°	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7	431.9	409.7	388.4
147.5°	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3	427.3	407.8	389.1
150°	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0	423.8	406.0	389.1
152.5°	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0	419.6	403.7	388.5
155°	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3	412.7	399.4	386.9
157.5°	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4	406.2	395.0	385.0
160°	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5	401.0	392.1	383.2
162.5°	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0	396.2	388.5	381.4
165°	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0	389.1	383.2	378.8
167.5°	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4	382.2	378.1	374.7
170°	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7	378.1	375.1	372.9
172.5°	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5	373.9	371.6	370.5
175°	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7	368.4	367.8	367.8
177.5°	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7	366.1	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	24.3	23.0	20.8	18.9	16.1	14.3	13.6	13.9	12.5	12.3	13.1
90°	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8	1.5	2.9	4.4
92.5°	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0	10.9	17.1	26.2
95°	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3	25.1	30.9	39.0
97.5°	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3	41.3	45.4	53.5
100°	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6	53.1	56.0	64.1
102.5°	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0	64.8	67.2	75.9
105°	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3	83.3	87.0	94.3
107.5°	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2	103.6	107.2	113.2
110°	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7	117.2	120.1	126.8



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2	130.7	133.1	139.7
115°	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8	150.3	152.6	159.2
117.5°	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5	168.8	171.2	177.8
120°	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3	180.6	183.5	190.1
122.5°	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8	192.4	194.7	201.3
125°	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3	207.8	211.5	218.1
127.5°	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6	220.8	225.6	233.9
130°	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2	228.5	234.3	243.9
132.5°	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1	235.0	242.0	252.8
135°	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8	244.7	253.5	265.3
137.5°	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8	256.0	264.3	276.1
140°	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9	263.1	271.9	283.7
142.5°	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1	270.8	279.0	290.8
145°	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5	283.0	290.4	300.7
147.5°	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5	295.4	301.7	311.3
150°	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2	303.6	308.8	318.4
152.5°	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4	311.3	315.8	324.2
155°	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3	321.3	325.7	333.1
157.5°	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0	330.9	334.4	340.7
160°	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5	336.8	339.8	344.9
162.5°	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8	342.1	345.1	349.6
165°	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8	349.3	351.6	355.2
167.5°	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1	355.3	356.7	358.7
170°	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7	358.9	359.7	361.1
172.5°	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0	360.7	361.4	362.9
175°	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8	363.4	364.1	364.8
177.5°	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1	365.0	365.0	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	13.9	15.2	14.9	15.6	15.8	17.2	16.8	18.9	20.1	21.3	21.0
90°	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3	14.0	14.7	16.2
92.5°	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6	94.8	71.4	60.4
95°	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9	417.8	327.3	265.3
97.5°	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2	710.6	622.3	536.2
100°	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4	870.3	794.5	717.8
102.5°	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9	968.3	931.8	880.0
105°	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7	1023.7	1056.1	1048.0
107.5°	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5	974.3	1057.5	1096.0
110°	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3	918.2	1022.2	1084.8



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9	862.8	967.9	1041.8
115°	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2	783.4	884.4	964.7
117.5°	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0	728.4	815.4	889.1
120°	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7	697.2	778.3	843.1
122.5°	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9	674.8	747.0	807.8
125°	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7	644.9	709.0	762.0
127.5°	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1	616.2	676.1	725.8
130°	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3	596.3	653.7	701.6
132.5°	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6	577.3	629.5	675.6
135°	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5	548.3	595.5	637.4
137.5°	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3	522.4	561.6	597.2
140°	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4	507.0	540.9	571.8
142.5°	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8	494.1	523.2	550.1
145°	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7	477.6	500.4	520.3
147.5°	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3	463.8	481.4	496.4
150°	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0	456.2	470.1	483.4
152.5°	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0	448.6	461.4	471.6
155°	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3	437.1	447.3	455.4
157.5°	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4	426.1	434.0	440.5
160°	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5	417.8	425.3	430.4
162.5°	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0	410.8	417.0	421.5
165°	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0	400.2	404.6	408.3
167.5°	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4	389.8	393.2	395.9
170°	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7	384.0	386.2	387.7
172.5°	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5	378.6	380.3	381.2
175°	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7	370.7	372.2	372.2
177.5°	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7	367.3	367.3	367.3
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	22.1	21.6	21.7	22.7	21.7	21.6	22.1	21.0	21.3	20.1	18.9
90°	16.2	16.2	17.0	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3
92.5°	51.0	49.2	48.2	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6
95°	213.0	190.9	185.0	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9
97.5°	490.7	449.4	428.0	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2
100°	666.9	613.9	586.6	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4
102.5°	825.6	787.8	758.2	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9
105°	1024.4	1000.0	985.3	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7
107.5°	1108.0	1107.8	1103.0	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5
110°	1117.9	1132.0	1137.2	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1090.2	1114.3	1127.1	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9
115°	1022.2	1057.5	1078.2	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2
117.5°	946.6	983.1	1003.6	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0
120°	897.6	933.0	952.9	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7
122.5°	856.4	888.8	908.7	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9
125°	803.3	833.5	849.7	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7
127.5°	763.2	789.9	805.2	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1
130°	738.5	762.8	777.5	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3
132.5°	712.5	736.8	750.4	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6
135°	669.9	694.2	707.5	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5
137.5°	626.3	648.4	660.6	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3
140°	599.2	618.3	629.3	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4
142.5°	573.3	589.5	599.9	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8
145°	538.0	550.5	558.6	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7
147.5°	510.4	520.5	525.2	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3
150°	494.6	503.3	506.3	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0
152.5°	481.0	488.0	491.0	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0
155°	462.8	468.0	470.1	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3
157.5°	446.2	450.4	452.5	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4
160°	435.5	439.2	440.7	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5
162.5°	425.6	428.6	429.0	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0
165°	411.2	412.7	412.7	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0
167.5°	397.4	398.7	398.1	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4
170°	389.1	389.8	389.8	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7
172.5°	381.4	382.8	381.6	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5
175°	372.2	372.9	371.5	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7
177.5°	366.7	367.3	365.5	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	16.8	17.2	15.8	15.6	14.9	15.2	13.9	13.1	12.3	12.5	13.9
90°	12.5	11.8	10.3	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8
92.5°	192.4	237.6	241.4	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0
95°	638.9	653.0	532.8	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3
97.5°	808.4	697.3	475.8	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3
100°	849.7	665.5	424.5	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6
102.5°	825.0	609.4	385.6	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0
105°	745.8	534.3	347.9	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3
107.5°	665.1	482.6	332.0	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2
110°	619.1	458.4	327.3	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	584.8	444.2	327.3	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2
115°	547.5	429.0	329.4	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8
117.5°	525.3	421.4	334.3	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5
120°	512.9	417.8	339.0	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3
122.5°	502.3	414.9	343.1	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8
125°	487.9	411.2	350.1	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3
127.5°	474.6	409.4	357.9	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6
130°	465.8	408.3	362.6	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2
132.5°	458.7	408.3	367.9	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1
135°	450.3	408.3	375.1	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8
137.5°	442.8	409.2	381.7	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8
140°	439.2	409.7	384.7	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9
142.5°	436.3	410.4	386.4	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1
145°	431.9	409.7	388.4	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5
147.5°	427.3	407.8	389.1	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5
150°	423.8	406.0	389.1	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2
152.5°	419.6	403.7	388.5	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4
155°	412.7	399.4	386.9	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3
157.5°	406.2	395.0	385.0	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0
160°	401.0	392.1	383.2	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5
162.5°	396.2	388.5	381.4	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8
165°	389.1	383.2	378.8	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8
167.5°	382.2	378.1	374.7	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1
170°	378.1	375.1	372.9	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7
172.5°	373.9	371.6	370.5	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0
175°	368.4	367.8	367.8	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8
177.5°	366.1	365.5	365.5	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.6	14.3	16.1	18.9	20.8	23.0	24.3	23.5	21.7	20.4	18.9
90°	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3
92.5°	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6
95°	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9
97.5°	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2
100°	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4
102.5°	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9
105°	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7
107.5°	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5
110°	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9
115°	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2
117.5°	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0
120°	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7
122.5°	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9
125°	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7
127.5°	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1
130°	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3
132.5°	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6
135°	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5
137.5°	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3
140°	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4
142.5°	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8
145°	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7
147.5°	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3
150°	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0
152.5°	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0
155°	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3
157.5°	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4
160°	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5
162.5°	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0
165°	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0
167.5°	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4
170°	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7
172.5°	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5
175°	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7
177.5°	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	19.0	17.2	17.5	17.0	17.0	16.6	15.6
90°	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2



TEST NUMBER: P333270-830

CATALOG NUMBER: S125DIP-S1090D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)