

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333306-830

Luminaire Tested: **S125DIP-S1270D590U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333306-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6886.0 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	44
4	79	68	60	53	74	64	57	52	58	52	48	53	48	44	47	44	41	38
5	72	61	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	35	31	29
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	36	31	28	26
8	58	45	37	31	54	43	36	31	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11180	11180	11180	11180
5°	12947	11218	9822	11218
10°	15062	11160	8605	11160
15°	16673	11078	7938	11078
20°	18664	10948	7403	10948
25°	21865	10802	7142	10802
30°	23616	10657	6915	10657
35°	19418	10387	6766	10387
40°	13801	10010	6604	10010
45°	10602	9502	6509	9502
50°	9051	8874	6497	8874
55°	8059	8257	6552	8257
60°	7270	7582	6719	7582
65°	6715	6906	6894	6906
70°	6105	6201	6992	6201
75°	5390	5465	6932	5465
80°	4537	4456	6338	4456
85°	3586	3216	5120	3216



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	2.4
10°-20°	496.2	7.2
20°-30°	805.7	11.7
30°-40°	982.8	14.3
40°-50°	894.0	13.0
50°-60°	712.1	10.3
60°-70°	496.0	7.2
70°-80°	264.5	3.8
80°-90°	68.2	1.0
90°-100°	193.3	2.8
100°-110°	415.5	6.0
110°-120°	390.0	5.7
120°-130°	316.0	4.6
130°-140°	253.6	3.7
140°-150°	191.4	2.8
150°-160°	134.7	2.0
160°-170°	79.4	1.2
170°-180°	25.8	0.4
0°-30°	1468.5	21.3
0°-40°	2451.2	35.6
0°-60°	4057.4	58.9
0°-90°	4886.1	71.0
90°-120°	998.8	14.5
90°-150°	1759.9	25.6
90°-180°	2000.0	29.0
0°-180°	6886.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1731	1731	1731	1731	1731	
5°	1997	1730	1515	1730	1997	201
15°	2494	1657	1187	1657	2494	714
25°	3068	1516	1002	1516	3068	1401
35°	2463	1317	858	1317	2463	1507
45°	1161	1040	713	1040	1161	929
55°	716	733	582	733	716	645
65°	439	452	451	452	439	436
75°	216	219	278	219	216	233
85°	48	43	69	43	48	56
90°	12	1	12	1	12	10
95°	126	18	126	18	126	179
105°	712	61	712	61	712	708
115°	794	109	794	109	794	775
125°	625	150	625	150	625	566
135°	519	176	519	176	519	402
145°	410	205	410	205	410	260
155°	344	234	344	234	344	160
165°	301	256	301	256	301	86
175°	270	266	270	266	270	26
180°	267	267	267	267	267	



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1831.0	1828.6	1826.3	1821.6	1825.0	1815.1	1810.3	1802.1	1792.2	1788.7	1784.5
5°	1997.0	2000.6	2004.3	1989.0	1990.4	1980.1	1956.6	1937.5	1922.0	1902.2	1888.3
7.5°	2196.9	2188.2	2187.5	2177.5	2160.3	2146.5	2121.8	2090.3	2059.9	2025.2	1996.6
10°	2296.8	2297.5	2290.9	2279.2	2260.8	2247.6	2215.3	2184.3	2146.9	2102.8	2071.2
12.5°	2372.0	2375.1	2366.7	2350.9	2341.8	2312.2	2286.9	2250.2	2205.6	2170.4	2122.3
15°	2493.7	2485.6	2479.7	2459.8	2444.5	2413.6	2373.2	2335.0	2286.5	2241.6	2196.9
17.5°	2610.9	2617.4	2606.4	2588.3	2540.4	2504.4	2450.2	2397.8	2337.5	2277.4	2223.9
20°	2715.6	2721.5	2704.5	2673.0	2615.6	2579.6	2508.4	2440.8	2371.0	2293.9	2235.1
22.5°	2846.1	2841.4	2818.6	2770.5	2720.8	2654.3	2577.2	2494.8	2407.4	2320.3	2242.1
25°	3068.3	3037.3	3023.4	2963.9	2898.5	2800.8	2695.0	2574.5	2465.8	2350.4	2250.5
27.5°	3191.4	3181.6	3166.1	3124.7	3055.9	2951.4	2826.7	2679.8	2526.5	2380.9	2250.0
30°	3166.7	3168.2	3169.7	3156.4	3112.4	3033.7	2909.5	2751.6	2569.4	2405.6	2254.2
32.5°	2948.1	2974.8	3000.4	3030.7	3043.0	3027.8	2950.1	2807.5	2619.9	2433.7	2251.8
35°	2462.9	2470.9	2553.9	2636.2	2747.9	2834.6	2892.7	2829.4	2671.4	2457.7	2249.0
37.5°	1920.3	1960.0	2017.4	2110.4	2271.6	2415.9	2601.5	2686.9	2635.9	2465.5	2243.9
40°	1637.0	1673.8	1711.2	1806.0	1941.9	2116.8	2327.6	2507.6	2549.5	2440.8	2226.3
42.5°	1418.3	1447.5	1489.0	1560.3	1673.9	1828.7	2030.2	2265.5	2410.2	2369.1	2189.2
45°	1160.8	1179.2	1211.5	1268.2	1350.5	1471.7	1649.4	1906.7	2130.7	2204.9	2101.3
47.5°	993.6	993.5	1018.6	1057.7	1117.1	1220.1	1351.6	1553.1	1792.4	1969.5	1961.3
50°	900.8	897.1	916.9	950.7	997.8	1066.1	1191.8	1352.6	1582.6	1783.2	1839.0
52.5°	820.9	821.2	833.5	858.5	897.9	956.2	1050.1	1195.1	1391.6	1597.4	1702.7
55°	715.7	712.7	726.6	743.6	772.2	810.4	878.0	988.9	1148.4	1351.1	1487.8
57.5°	619.3	627.4	632.9	644.7	668.5	694.0	751.0	832.5	958.9	1132.9	1277.4
60°	562.8	570.9	575.3	587.0	606.1	628.2	672.3	738.4	845.0	994.9	1138.1
62.5°	512.3	518.6	520.0	530.7	546.2	567.7	602.4	657.9	742.1	873.2	1013.5
65°	439.4	439.4	442.3	453.4	460.7	479.8	506.2	546.7	614.3	716.3	836.1
67.5°	369.1	372.7	371.9	376.7	383.5	398.4	417.4	450.7	500.8	575.3	671.1
70°	323.3	326.2	325.5	329.1	336.5	346.1	361.5	393.0	429.0	493.0	575.3
72.5°	282.1	283.3	281.4	286.3	290.7	299.1	316.2	333.1	366.7	420.8	488.3
75°	216.0	217.4	219.0	221.9	226.3	230.7	239.5	256.5	278.4	318.9	362.2
77.5°	161.9	159.1	162.7	162.2	164.8	168.1	175.9	184.8	202.9	228.5	262.0
80°	122.0	122.7	122.7	123.5	127.1	129.3	135.9	142.5	156.5	175.6	199.2
82.5°	89.1	91.0	89.8	91.1	94.2	95.8	99.4	104.9	113.0	128.0	145.1
85°	48.4	44.9	46.3	47.8	47.8	48.4	51.5	53.6	58.1	63.9	70.5
87.5°	16.6	17.7	18.2	18.2	18.9	18.6	20.8	20.7	22.4	24.0	26.2
90°	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7	9.1	8.6	7.5
92.5°	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3	140.3	173.3	176.2
95°	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5	466.2	476.4	388.7
97.5°	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7	589.8	508.7	347.1
100°	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3	619.9	485.5	309.7
102.5°	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1	601.8	444.6	281.3
105°	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2	544.1	389.8	253.7
107.5°	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5	485.2	352.0	242.1
110°	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8	451.7	334.4	238.7



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5	426.7	324.1	238.7
115°	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1	399.4	312.9	240.3
117.5°	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6	383.2	307.5	243.8
120°	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1	374.2	304.8	247.3
122.5°	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5	366.5	302.7	250.3
125°	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6	355.9	300.0	255.4
127.5°	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4	346.3	298.7	261.1
130°	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7	339.8	297.8	264.6
132.5°	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9	334.6	297.8	268.4
135°	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9	328.5	297.8	273.6
137.5°	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1	323.0	298.5	278.5
140°	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6	320.5	299.0	280.7
142.5°	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0	318.3	299.4	281.9
145°	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8	315.1	299.0	283.3
147.5°	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9	311.7	297.6	283.9
150°	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9	309.2	296.2	283.9
152.5°	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7	306.1	294.5	283.4
155°	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2	301.0	291.4	282.3
157.5°	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8	296.3	288.1	280.9
160°	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4	292.5	286.1	279.6
162.5°	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7	289.1	283.4	278.3
165°	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1	283.9	279.6	276.4
167.5°	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9	278.8	275.8	273.3
170°	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5	275.8	273.6	272.0
172.5°	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7	272.8	271.1	270.3
175°	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4	268.8	268.2	268.2
177.5°	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5	267.1	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1781.0	1776.9	1772.2	1764.0	1754.0	1748.7	1740.4	1735.1	1724.6	1715.7	1706.4
5°	1871.3	1852.3	1834.7	1811.8	1786.9	1770.7	1751.6	1730.3	1708.3	1685.5	1660.5
7.5°	1965.0	1931.2	1894.4	1854.9	1816.3	1780.7	1746.7	1713.4	1682.2	1644.6	1612.8
10°	2027.9	1985.3	1939.7	1886.0	1833.9	1788.4	1742.0	1701.7	1660.5	1616.4	1577.4
12.5°	2090.7	2034.0	1969.6	1910.7	1848.0	1793.0	1738.5	1687.0	1635.2	1586.4	1541.1
15°	2135.1	2085.2	2025.6	1941.9	1871.3	1795.7	1723.7	1656.8	1594.4	1540.0	1482.7
17.5°	2164.4	2100.0	2036.1	1955.7	1863.3	1778.7	1697.0	1620.5	1550.1	1481.2	1426.0
20°	2169.6	2103.6	2036.6	1958.0	1863.3	1766.3	1684.7	1592.9	1517.2	1446.0	1378.4
22.5°	2167.9	2092.9	2020.2	1939.3	1846.8	1757.5	1658.9	1565.3	1483.1	1413.1	1342.5
25°	2151.3	2071.2	1980.1	1898.6	1807.4	1712.7	1612.8	1515.8	1432.0	1351.9	1282.1
27.5°	2137.5	2033.6	1930.4	1835.3	1747.4	1660.5	1564.8	1465.5	1372.6	1291.5	1225.7
30°	2120.4	2006.6	1890.5	1791.3	1700.9	1616.4	1526.1	1429.1	1332.1	1252.7	1182.2
32.5°	2105.2	1972.5	1849.9	1741.9	1646.2	1564.1	1480.7	1388.5	1293.3	1212.8	1142.2
35°	2075.7	1922.0	1781.7	1659.7	1557.6	1473.1	1403.4	1317.4	1229.9	1152.1	1084.5
37.5°	2038.2	1856.0	1705.3	1577.4	1465.5	1376.5	1311.5	1245.5	1161.6	1086.6	1025.4
40°	2008.7	1808.9	1649.4	1518.7	1402.6	1310.0	1249.8	1187.3	1117.6	1047.7	983.1
42.5°	1971.7	1766.6	1593.1	1452.3	1337.4	1247.2	1183.9	1130.9	1069.3	1004.3	944.2
45°	1903.7	1689.9	1501.8	1350.5	1234.4	1145.5	1080.1	1040.4	994.1	932.4	881.7
47.5°	1803.6	1597.7	1403.2	1247.0	1127.2	1044.8	983.5	945.5	912.9	867.0	821.0
50°	1714.9	1529.0	1332.1	1177.0	1057.2	974.2	917.7	883.2	855.3	819.9	781.0
52.5°	1615.5	1442.6	1262.2	1108.9	990.2	908.4	853.0	822.7	799.4	774.1	735.7
55°	1457.7	1310.8	1143.2	997.8	888.3	808.2	759.7	733.3	714.2	695.0	671.6
57.5°	1283.8	1168.9	1020.6	887.6	786.7	713.9	668.6	642.9	628.0	618.2	604.4
60°	1161.6	1063.2	935.3	814.1	715.7	651.0	606.9	587.0	574.6	566.5	556.2
62.5°	1048.2	967.3	848.9	738.3	652.1	591.0	551.7	532.3	520.5	516.5	508.0
65°	880.9	818.5	720.8	629.0	555.4	503.3	470.2	451.9	444.5	440.1	440.8
67.5°	716.2	678.2	599.6	521.3	462.7	419.0	392.5	378.4	374.8	368.8	368.7
70°	615.7	587.0	520.9	452.6	400.4	366.6	343.1	328.4	324.7	321.8	321.1
72.5°	527.0	501.8	444.5	389.7	342.8	313.1	293.8	284.9	278.9	277.1	277.0
75°	396.1	382.1	336.5	293.1	260.8	240.3	227.1	219.0	214.5	213.8	214.5
77.5°	281.5	269.4	240.4	209.7	189.3	173.7	162.5	159.8	154.8	154.9	154.1
80°	211.6	203.5	185.1	160.9	144.0	130.8	124.9	119.8	118.3	116.1	118.3
82.5°	153.4	144.8	132.2	116.8	102.8	94.9	89.1	87.5	86.5	85.5	86.0
85°	75.7	76.4	69.1	57.3	51.5	47.0	43.4	43.4	42.6	41.8	42.6
87.5°	27.2	25.8	23.4	21.4	18.3	16.3	15.5	16.0	14.3	13.9	14.8
90°	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6	1.0	2.2	3.2
92.5°	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6	7.9	12.4	19.1
95°	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7	18.3	22.6	28.5
97.5°	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5	30.1	33.1	39.0
100°	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6	38.7	40.9	46.8
102.5°	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7	47.3	49.0	55.4
105°	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8	60.8	63.4	68.8
107.5°	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6	75.6	78.1	82.6
110°	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5	85.5	87.7	92.5



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3	95.4	97.1	102.0
115°	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6	109.7	111.3	116.1
117.5°	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5	123.1	124.9	129.7
120°	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1	131.8	133.8	138.7
122.5°	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1	140.3	142.0	146.8
125°	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5	151.7	154.3	159.1
127.5°	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5	161.1	164.6	170.7
130°	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0	166.6	171.0	178.0
132.5°	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4	171.4	176.5	184.5
135°	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3	178.5	184.9	193.6
137.5°	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2	186.8	192.8	201.4
140°	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3	191.9	198.4	207.0
142.5°	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3	197.6	203.6	212.2
145°	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4	206.4	211.8	219.3
147.5°	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8	215.5	220.1	227.1
150°	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5	221.5	225.3	232.2
152.5°	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5	227.1	230.5	236.6
155°	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4	234.4	237.6	243.0
157.5°	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5	241.4	244.0	248.6
160°	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3	245.7	247.9	251.7
162.5°	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2	249.6	251.8	255.1
165°	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9	254.9	256.5	259.1
167.5°	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8	259.3	260.2	261.7
170°	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4	261.8	262.4	263.4
172.5°	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1	263.2	263.6	264.8
175°	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2	265.0	265.6	266.2
177.5°	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1	266.3	266.3	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1701.0	1694.6	1689.3	1677.5	1671.0	1662.3	1655.2	1662.8	1654.6	1658.1	1652.8
5°	1648.0	1627.4	1612.8	1591.4	1573.1	1556.1	1543.7	1541.4	1535.6	1532.7	1523.8
7.5°	1584.2	1558.5	1533.2	1505.3	1481.8	1457.8	1442.6	1429.9	1421.5	1410.5	1403.1
10°	1546.6	1512.1	1482.7	1448.9	1419.5	1393.8	1373.2	1362.9	1353.4	1339.4	1334.3
12.5°	1500.2	1464.4	1428.6	1392.5	1364.2	1335.6	1318.0	1302.4	1295.8	1280.1	1278.5
15°	1444.4	1390.8	1355.6	1318.8	1279.9	1256.4	1241.7	1224.8	1217.5	1206.5	1198.3
17.5°	1378.1	1330.1	1286.1	1248.0	1214.7	1194.9	1176.6	1165.0	1152.4	1145.2	1131.9
20°	1329.8	1284.3	1240.2	1199.9	1174.1	1151.3	1136.6	1125.6	1112.4	1108.7	1095.5
22.5°	1289.3	1239.1	1196.7	1162.8	1134.7	1109.0	1093.2	1085.6	1076.6	1065.3	1062.5
25°	1223.3	1171.2	1135.2	1101.4	1076.4	1052.9	1041.9	1032.3	1023.5	1015.4	1012.5
27.5°	1166.3	1119.7	1076.9	1046.4	1024.6	1003.2	993.5	981.9	975.4	968.9	961.0
30°	1126.3	1078.6	1041.1	1011.7	988.3	969.1	958.8	950.7	944.9	939.0	934.6
32.5°	1085.2	1040.9	1004.7	975.9	952.3	937.9	928.9	923.1	916.6	909.6	904.0
35°	1030.9	982.3	947.1	922.1	903.7	892.7	882.4	877.2	870.0	870.0	864.0
37.5°	969.6	927.7	896.5	873.7	857.2	847.4	836.3	832.7	828.0	824.9	822.9
40°	933.1	894.2	864.8	842.0	824.3	816.2	807.5	801.6	798.6	794.9	793.5
42.5°	895.5	858.3	830.1	809.1	793.8	786.9	778.6	774.6	768.6	763.8	763.0
45°	838.3	802.3	776.7	759.7	746.5	738.4	733.3	724.4	721.5	715.7	714.9
47.5°	784.1	749.6	724.3	710.5	698.9	692.3	684.2	675.3	672.0	669.0	668.7
50°	743.6	712.0	688.4	675.2	664.2	654.7	646.6	640.6	638.5	638.5	640.0
52.5°	702.4	675.5	655.5	639.3	629.0	618.8	611.3	607.8	604.4	607.9	610.6
55°	642.2	615.0	600.3	584.8	574.6	562.8	559.1	557.7	555.4	561.4	564.3
57.5°	578.3	559.3	542.1	526.8	517.6	510.8	505.8	504.9	509.1	511.8	521.3
60°	537.8	515.8	500.4	488.6	477.6	473.2	471.7	470.2	473.2	481.3	493.7
62.5°	493.1	475.2	458.6	449.8	441.7	434.4	434.0	435.0	440.8	450.1	462.6
65°	427.6	412.2	401.1	390.9	384.3	379.8	381.4	384.3	390.9	403.4	417.4
67.5°	361.1	350.4	340.6	332.2	325.9	325.9	327.4	331.8	339.6	354.0	366.7
70°	318.1	306.4	298.3	294.6	289.5	286.5	291.0	298.3	304.9	318.1	329.1
72.5°	275.2	265.2	258.9	256.5	254.2	251.8	253.4	261.3	270.2	283.4	296.2
75°	211.6	207.9	203.5	200.6	198.4	199.8	201.3	208.7	216.0	230.0	244.7
77.5°	154.5	150.6	148.0	147.2	146.1	146.8	150.9	156.4	163.5	173.7	184.8
80°	116.8	115.4	113.9	113.1	113.1	113.9	119.8	123.5	130.1	139.6	148.5
82.5°	85.1	84.2	83.9	83.8	84.4	84.5	88.0	92.8	98.3	105.5	113.1
85°	44.9	43.4	45.5	46.3	44.9	47.0	48.4	51.5	53.6	57.3	61.0
87.5°	15.6	17.0	16.5	17.2	17.3	18.8	18.3	20.7	22.1	23.3	22.9
90°	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7	10.2	10.7	11.8
92.5°	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3	69.2	52.0	44.1
95°	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5	304.8	238.7	193.6
97.5°	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7	518.4	454.0	391.2
100°	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3	635.0	579.6	523.7
102.5°	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1	706.3	679.8	642.0
105°	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2	746.8	770.4	764.5
107.5°	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5	710.8	771.6	799.6
110°	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8	670.0	745.7	791.5



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5	629.5	706.2	760.1
115°	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1	571.6	645.2	703.8
117.5°	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6	531.4	594.8	648.7
120°	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1	508.6	567.8	615.1
122.5°	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5	492.3	545.0	589.3
125°	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6	470.4	517.3	555.9
127.5°	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4	449.6	493.2	529.5
130°	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7	435.0	476.9	511.8
132.5°	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9	421.2	459.3	492.9
135°	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9	400.0	434.4	465.1
137.5°	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1	381.1	409.7	435.7
140°	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6	369.9	394.6	417.3
142.5°	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0	360.4	381.7	401.3
145°	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8	348.4	365.0	379.6
147.5°	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9	338.4	351.2	362.1
150°	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9	332.8	343.0	352.7
152.5°	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7	327.3	336.6	344.1
155°	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2	318.9	326.3	332.2
157.5°	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8	310.9	316.7	321.3
160°	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4	304.8	310.2	314.0
162.5°	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7	299.7	304.2	307.6
165°	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1	291.9	295.2	297.8
167.5°	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9	284.5	286.9	288.8
170°	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5	280.1	281.7	282.8
172.5°	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7	276.3	277.4	278.1
175°	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4	270.4	271.5	271.5
177.5°	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5	268.0	268.0	268.0
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1649.4	1653.4	1649.9	1654.6	1649.9	1653.4	1649.4	1652.8	1658.1	1654.6	1662.8
5°	1520.1	1513.5	1518.0	1515.0	1518.0	1513.5	1520.1	1523.8	1532.7	1535.6	1541.4
7.5°	1400.8	1394.5	1387.3	1383.9	1387.3	1394.5	1400.8	1403.1	1410.5	1421.5	1429.9
10°	1326.2	1318.1	1317.4	1312.2	1317.4	1318.1	1326.2	1334.3	1339.4	1353.4	1362.9
12.5°	1271.5	1264.0	1255.7	1253.5	1255.7	1264.0	1271.5	1278.5	1280.1	1295.8	1302.4
15°	1193.9	1188.1	1182.9	1187.3	1182.9	1188.1	1193.9	1198.3	1206.5	1217.5	1224.8
17.5°	1129.4	1124.5	1123.7	1118.2	1123.7	1124.5	1129.4	1131.9	1145.2	1152.4	1165.0
20°	1088.9	1085.2	1086.7	1077.1	1086.7	1085.2	1088.9	1095.5	1108.7	1112.4	1125.6
22.5°	1056.6	1049.3	1048.5	1046.6	1048.5	1049.3	1056.6	1062.5	1065.3	1076.6	1085.6
25°	1005.9	1002.2	998.5	1002.2	998.5	1002.2	1005.9	1012.5	1015.4	1023.5	1032.3
27.5°	961.6	957.2	956.2	956.6	956.2	957.2	961.6	961.0	968.9	975.4	981.9
30°	934.6	927.3	927.9	927.3	927.9	927.3	934.6	934.6	939.0	944.9	950.7
32.5°	905.2	900.2	899.2	897.9	899.2	900.2	905.2	904.0	909.6	916.6	923.1
35°	861.9	861.9	858.2	858.2	858.2	861.9	861.9	864.0	870.0	870.0	877.2
37.5°	821.1	820.4	818.2	818.5	818.2	820.4	821.1	822.9	824.9	828.0	832.7
40°	790.6	789.9	787.6	783.3	787.6	789.9	790.6	793.5	794.9	798.6	801.6
42.5°	761.2	758.7	757.6	756.2	757.6	758.7	761.2	763.0	763.8	768.6	774.6
45°	714.9	714.9	713.4	712.7	713.4	714.9	714.9	714.9	715.7	721.5	724.4
47.5°	670.0	671.3	674.0	673.6	674.0	671.3	670.0	668.7	669.0	672.0	675.3
50°	642.9	643.7	645.8	646.6	645.8	643.7	642.9	640.0	638.5	638.5	640.6
52.5°	612.9	617.2	620.0	619.5	620.0	617.2	612.9	610.6	607.9	604.4	607.8
55°	570.9	576.0	581.2	581.9	581.2	576.0	570.9	564.3	561.4	555.4	557.7
57.5°	529.3	536.5	542.0	543.7	542.0	536.5	529.3	521.3	511.8	509.1	504.9
60°	501.1	510.7	517.3	520.2	517.3	510.7	501.1	493.7	481.3	473.2	470.2
62.5°	474.0	484.7	491.3	492.0	491.3	484.7	474.0	462.6	450.1	440.8	435.0
65°	429.8	440.8	446.7	451.1	446.7	440.8	429.8	417.4	403.4	390.9	384.3
67.5°	382.2	393.2	399.7	403.2	399.7	393.2	382.2	366.7	354.0	339.6	331.8
70°	347.5	358.5	367.4	370.3	367.4	358.5	347.5	329.1	318.1	304.9	298.3
72.5°	313.4	323.3	330.4	333.8	330.4	323.3	313.4	296.2	283.4	270.2	261.3
75°	254.2	267.4	274.1	277.8	274.1	267.4	254.2	244.7	230.0	216.0	208.7
77.5°	196.0	208.1	212.1	214.0	212.1	208.1	196.0	184.8	173.7	163.5	156.4
80°	157.2	164.6	169.8	170.4	169.8	164.6	157.2	148.5	139.6	130.1	123.5
82.5°	120.8	127.0	128.6	130.4	128.6	127.0	120.8	113.1	105.5	98.3	92.8
85°	66.2	69.1	69.8	69.1	69.8	69.1	66.2	61.0	57.3	53.6	51.5
87.5°	24.1	23.6	23.7	24.8	23.7	23.6	24.1	22.9	23.3	22.1	20.7
90°	11.8	11.8	12.3	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7
92.5°	37.2	35.9	35.2	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3
95°	155.4	139.2	135.0	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5
97.5°	358.0	327.8	312.3	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7
100°	486.5	447.9	428.0	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3
102.5°	602.3	574.8	553.2	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1
105°	747.3	729.6	718.9	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2
107.5°	808.3	808.2	804.6	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5
110°	815.6	825.9	829.6	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	795.4	812.9	822.3	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5
115°	745.7	771.6	786.6	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1
117.5°	690.6	717.3	732.2	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6
120°	654.9	680.7	695.2	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1
122.5°	624.7	648.4	662.9	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5
125°	586.1	608.1	619.9	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6
127.5°	556.8	576.3	587.4	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4
130°	538.8	556.5	567.2	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7
132.5°	519.8	537.5	547.4	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9
135°	488.7	506.4	516.1	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9
137.5°	456.9	473.1	481.9	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1
140°	437.2	451.1	459.1	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6
142.5°	418.2	430.0	437.6	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0
145°	392.5	401.6	407.6	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8
147.5°	372.4	379.7	383.1	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9
150°	360.8	367.2	369.4	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9
152.5°	350.9	356.0	358.2	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7
155°	337.6	341.4	343.0	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2
157.5°	325.5	328.6	330.1	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8
160°	317.7	320.5	321.5	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4
162.5°	310.5	312.7	312.9	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7
165°	300.0	301.0	301.0	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1
167.5°	289.9	290.9	290.4	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9
170°	283.9	284.5	284.5	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5
172.5°	278.3	279.3	278.4	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7
175°	271.5	272.0	271.0	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4
177.5°	267.5	268.0	266.6	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1655.2	1662.3	1671.0	1677.5	1689.3	1694.6	1701.0	1706.4	1715.7	1724.6	1735.1
5°	1543.7	1556.1	1573.1	1591.4	1612.8	1627.4	1648.0	1660.5	1685.5	1708.3	1730.3
7.5°	1442.6	1457.8	1481.8	1505.3	1533.2	1558.5	1584.2	1612.8	1644.6	1682.2	1713.4
10°	1373.2	1393.8	1419.5	1448.9	1482.7	1512.1	1546.6	1577.4	1616.4	1660.5	1701.7
12.5°	1318.0	1335.6	1364.2	1392.5	1428.6	1464.4	1500.2	1541.1	1586.4	1635.2	1687.0
15°	1241.7	1256.4	1279.9	1318.8	1355.6	1390.8	1444.4	1482.7	1540.0	1594.4	1656.8
17.5°	1176.6	1194.9	1214.7	1248.0	1286.1	1330.1	1378.1	1426.0	1481.2	1550.1	1620.5
20°	1136.6	1151.3	1174.1	1199.9	1240.2	1284.3	1329.8	1378.4	1446.0	1517.2	1592.9
22.5°	1093.2	1109.0	1134.7	1162.8	1196.7	1239.1	1289.3	1342.5	1413.1	1483.1	1565.3
25°	1041.9	1052.9	1076.4	1101.4	1135.2	1171.2	1223.3	1282.1	1351.9	1432.0	1515.8
27.5°	993.5	1003.2	1024.6	1046.4	1076.9	1119.7	1166.3	1225.7	1291.5	1372.6	1465.5
30°	958.8	969.1	988.3	1011.7	1041.1	1078.6	1126.3	1182.2	1252.7	1332.1	1429.1
32.5°	928.9	937.9	952.3	975.9	1004.7	1040.9	1085.2	1142.2	1212.8	1293.3	1388.5
35°	882.4	892.7	903.7	922.1	947.1	982.3	1030.9	1084.5	1152.1	1229.9	1317.4
37.5°	836.3	847.4	857.2	873.7	896.5	927.7	969.6	1025.4	1086.6	1161.6	1245.5
40°	807.5	816.2	824.3	842.0	864.8	894.2	933.1	983.1	1047.7	1117.6	1187.3
42.5°	778.6	786.9	793.8	809.1	830.1	858.3	895.5	944.2	1004.3	1069.3	1130.9
45°	733.3	738.4	746.5	759.7	776.7	802.3	838.3	881.7	932.4	994.1	1040.4
47.5°	684.2	692.3	698.9	710.5	724.3	749.6	784.1	821.0	867.0	912.9	945.5
50°	646.6	654.7	664.2	675.2	688.4	712.0	743.6	781.0	819.9	855.3	883.2
52.5°	611.3	618.8	629.0	639.3	655.5	675.5	702.4	735.7	774.1	799.4	822.7
55°	559.1	562.8	574.6	584.8	600.3	615.0	642.2	671.6	695.0	714.2	733.3
57.5°	505.8	510.8	517.6	526.8	542.1	559.3	578.3	604.4	618.2	628.0	642.9
60°	471.7	473.2	477.6	488.6	500.4	515.8	537.8	556.2	566.5	574.6	587.0
62.5°	434.0	434.4	441.7	449.8	458.6	475.2	493.1	508.0	516.5	520.5	532.3
65°	381.4	379.8	384.3	390.9	401.1	412.2	427.6	440.8	440.1	444.5	451.9
67.5°	327.4	325.9	325.9	332.2	340.6	350.4	361.1	368.7	368.8	374.8	378.4
70°	291.0	286.5	289.5	294.6	298.3	306.4	318.1	321.1	321.8	324.7	328.4
72.5°	253.4	251.8	254.2	256.5	258.9	265.2	275.2	277.0	277.1	278.9	284.9
75°	201.3	199.8	198.4	200.6	203.5	207.9	211.6	214.5	213.8	214.5	219.0
77.5°	150.9	146.8	146.1	147.2	148.0	150.6	154.5	154.1	154.9	154.8	159.8
80°	119.8	113.9	113.1	113.1	113.9	115.4	116.8	118.3	116.1	118.3	119.8
82.5°	88.0	84.5	84.4	83.8	83.9	84.2	85.1	86.0	85.5	86.5	87.5
85°	48.4	47.0	44.9	46.3	45.5	43.4	44.9	42.6	41.8	42.6	43.4
87.5°	18.3	18.8	17.3	17.2	16.5	17.0	15.6	14.8	13.9	14.3	16.0
90°	9.1	8.6	7.5	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6
92.5°	140.3	173.3	176.2	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6
95°	466.2	476.4	388.7	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7
97.5°	589.8	508.7	347.1	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5
100°	619.9	485.5	309.7	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6
102.5°	601.8	444.6	281.3	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7
105°	544.1	389.8	253.7	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8
107.5°	485.2	352.0	242.1	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6
110°	451.7	334.4	238.7	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	426.7	324.1	238.7	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3
115°	399.4	312.9	240.3	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6
117.5°	383.2	307.5	243.8	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5
120°	374.2	304.8	247.3	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1
122.5°	366.5	302.7	250.3	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1
125°	355.9	300.0	255.4	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5
127.5°	346.3	298.7	261.1	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5
130°	339.8	297.8	264.6	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0
132.5°	334.6	297.8	268.4	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4
135°	328.5	297.8	273.6	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3
137.5°	323.0	298.5	278.5	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2
140°	320.5	299.0	280.7	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3
142.5°	318.3	299.4	281.9	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3
145°	315.1	299.0	283.3	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4
147.5°	311.7	297.6	283.9	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8
150°	309.2	296.2	283.9	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5
152.5°	306.1	294.5	283.4	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5
155°	301.0	291.4	282.3	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4
157.5°	296.3	288.1	280.9	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5
160°	292.5	286.1	279.6	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3
162.5°	289.1	283.4	278.3	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2
165°	283.9	279.6	276.4	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9
167.5°	278.8	275.8	273.3	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8
170°	275.8	273.6	272.0	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4
172.5°	272.8	271.1	270.3	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1
175°	268.8	268.2	268.2	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2
177.5°	267.1	266.6	266.6	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1740.4	1748.7	1754.0	1764.0	1772.2	1776.9	1781.0	1784.5	1788.7	1792.2	1802.1
5°	1751.6	1770.7	1786.9	1811.8	1834.7	1852.3	1871.3	1888.3	1902.2	1922.0	1937.5
7.5°	1746.7	1780.7	1816.3	1854.9	1894.4	1931.2	1965.0	1996.6	2025.2	2059.9	2090.3
10°	1742.0	1788.4	1833.9	1886.0	1939.7	1985.3	2027.9	2071.2	2102.8	2146.9	2184.3
12.5°	1738.5	1793.0	1848.0	1910.7	1969.6	2034.0	2090.7	2122.3	2170.4	2205.6	2250.2
15°	1723.7	1795.7	1871.3	1941.9	2025.6	2085.2	2135.1	2196.9	2241.6	2286.5	2335.0
17.5°	1697.0	1778.7	1863.3	1955.7	2036.1	2100.0	2164.4	2223.9	2277.4	2337.5	2397.8
20°	1684.7	1766.3	1863.3	1958.0	2036.6	2103.6	2169.6	2235.1	2293.9	2371.0	2440.8
22.5°	1658.9	1757.5	1846.8	1939.3	2020.2	2092.9	2167.9	2242.1	2320.3	2407.4	2494.8
25°	1612.8	1712.7	1807.4	1898.6	1980.1	2071.2	2151.3	2250.5	2350.4	2465.8	2574.5
27.5°	1564.8	1660.5	1747.4	1835.3	1930.4	2033.6	2137.5	2250.0	2380.9	2526.5	2679.8
30°	1526.1	1616.4	1700.9	1791.3	1890.5	2006.6	2120.4	2254.2	2405.6	2569.4	2751.6
32.5°	1480.7	1564.1	1646.2	1741.9	1849.9	1972.5	2105.2	2251.8	2433.7	2619.9	2807.5
35°	1403.4	1473.1	1557.6	1659.7	1781.7	1922.0	2075.7	2249.0	2457.7	2671.4	2829.4
37.5°	1311.5	1376.5	1465.5	1577.4	1705.3	1856.0	2038.2	2243.9	2465.5	2635.9	2686.9
40°	1249.8	1310.0	1402.6	1518.7	1649.4	1808.9	2008.7	2226.3	2440.8	2549.5	2507.6
42.5°	1183.9	1247.2	1337.4	1452.3	1593.1	1766.6	1971.7	2189.2	2369.1	2410.2	2265.5
45°	1080.1	1145.5	1234.4	1350.5	1501.8	1689.9	1903.7	2101.3	2204.9	2130.7	1906.7
47.5°	983.5	1044.8	1127.2	1247.0	1403.2	1597.7	1803.6	1961.3	1969.5	1792.4	1553.1
50°	917.7	974.2	1057.2	1177.0	1332.1	1529.0	1714.9	1839.0	1783.2	1582.6	1352.6
52.5°	853.0	908.4	990.2	1108.9	1262.2	1442.6	1615.5	1702.7	1597.4	1391.6	1195.1
55°	759.7	808.2	888.3	997.8	1143.2	1310.8	1457.7	1487.8	1351.1	1148.4	988.9
57.5°	668.6	713.9	786.7	887.6	1020.6	1168.9	1283.8	1277.4	1132.9	958.9	832.5
60°	606.9	651.0	715.7	814.1	935.3	1063.2	1161.6	1138.1	994.9	845.0	738.4
62.5°	551.7	591.0	652.1	738.3	848.9	967.3	1048.2	1013.5	873.2	742.1	657.9
65°	470.2	503.3	555.4	629.0	720.8	818.5	880.9	836.1	716.3	614.3	546.7
67.5°	392.5	419.0	462.7	521.3	599.6	678.2	716.2	671.1	575.3	500.8	450.7
70°	343.1	366.6	400.4	452.6	520.9	587.0	615.7	575.3	493.0	429.0	393.0
72.5°	293.8	313.1	342.8	389.7	444.5	501.8	527.0	488.3	420.8	366.7	333.1
75°	227.1	240.3	260.8	293.1	336.5	382.1	396.1	362.2	318.9	278.4	256.5
77.5°	162.5	173.7	189.3	209.7	240.4	269.4	281.5	262.0	228.5	202.9	184.8
80°	124.9	130.8	144.0	160.9	185.1	203.5	211.6	199.2	175.6	156.5	142.5
82.5°	89.1	94.9	102.8	116.8	132.2	144.8	153.4	145.1	128.0	113.0	104.9
85°	43.4	47.0	51.5	57.3	69.1	76.4	75.7	70.5	63.9	58.1	53.6
87.5°	15.5	16.3	18.3	21.4	23.4	25.8	27.2	26.2	24.0	22.4	20.7
90°	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7
92.5°	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3
95°	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5
97.5°	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7
100°	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3
102.5°	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1
105°	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2
107.5°	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5
110°	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5
115°	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1
117.5°	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6
120°	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1
122.5°	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5
125°	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6
127.5°	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4
130°	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7
132.5°	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9
135°	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9
137.5°	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1
140°	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6
142.5°	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0
145°	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8
147.5°	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9
150°	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9
152.5°	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7
155°	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2
157.5°	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8
160°	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4
162.5°	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7
165°	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1
167.5°	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9
170°	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5
172.5°	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7
175°	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4
177.5°	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1810.3	1815.1	1825.0	1821.6	1826.3	1828.6	1831.0
5°	1956.6	1980.1	1990.4	1989.0	2004.3	2000.6	1997.0
7.5°	2121.8	2146.5	2160.3	2177.5	2187.5	2188.2	2196.9
10°	2215.3	2247.6	2260.8	2279.2	2290.9	2297.5	2296.8
12.5°	2286.9	2312.2	2341.8	2350.9	2366.7	2375.1	2372.0
15°	2373.2	2413.6	2444.5	2459.8	2479.7	2485.6	2493.7
17.5°	2450.2	2504.4	2540.4	2588.3	2606.4	2617.4	2610.9
20°	2508.4	2579.6	2615.6	2673.0	2704.5	2721.5	2715.6
22.5°	2577.2	2654.3	2720.8	2770.5	2818.6	2841.4	2846.1
25°	2695.0	2800.8	2898.5	2963.9	3023.4	3037.3	3068.3
27.5°	2826.7	2951.4	3055.9	3124.7	3166.1	3181.6	3191.4
30°	2909.5	3033.7	3112.4	3156.4	3169.7	3168.2	3166.7
32.5°	2950.1	3027.8	3043.0	3030.7	3000.4	2974.8	2948.1
35°	2892.7	2834.6	2747.9	2636.2	2553.9	2470.9	2462.9
37.5°	2601.5	2415.9	2271.6	2110.4	2017.4	1960.0	1920.3
40°	2327.6	2116.8	1941.9	1806.0	1711.2	1673.8	1637.0
42.5°	2030.2	1828.7	1673.9	1560.3	1489.0	1447.5	1418.3
45°	1649.4	1471.7	1350.5	1268.2	1211.5	1179.2	1160.8
47.5°	1351.6	1220.1	1117.1	1057.7	1018.6	993.5	993.6
50°	1191.8	1066.1	997.8	950.7	916.9	897.1	900.8
52.5°	1050.1	956.2	897.9	858.5	833.5	821.2	820.9
55°	878.0	810.4	772.2	743.6	726.6	712.7	715.7
57.5°	751.0	694.0	668.5	644.7	632.9	627.4	619.3
60°	672.3	628.2	606.1	587.0	575.3	570.9	562.8
62.5°	602.4	567.7	546.2	530.7	520.0	518.6	512.3
65°	506.2	479.8	460.7	453.4	442.3	439.4	439.4
67.5°	417.4	398.4	383.5	376.7	371.9	372.7	369.1
70°	361.5	346.1	336.5	329.1	325.5	326.2	323.3
72.5°	316.2	299.1	290.7	286.3	281.4	283.3	282.1
75°	239.5	230.7	226.3	221.9	219.0	217.4	216.0
77.5°	175.9	168.1	164.8	162.2	162.7	159.1	161.9
80°	135.9	129.3	127.1	123.5	122.7	122.7	122.0
82.5°	99.4	95.8	94.2	91.1	89.8	91.0	89.1
85°	51.5	48.4	47.8	47.8	46.3	44.9	48.4
87.5°	20.8	18.6	18.9	18.2	18.2	17.7	16.6
90°	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333306-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)