

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333311-830

Luminaire Tested: **S125DIP-S1270D590U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333311-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D590U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6763.1 lumens  
Efficiency: N/A  
Efficacy: 122.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	61	80	72	65	59	65	59	54	58	54	50	52	49	46	42
4	78	67	58	52	74	63	56	50	57	51	47	52	47	43	47	43	39	36
5	72	60	51	45	68	57	49	43	51	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.1	2.6
10°-20°	494.7	7.3
20°-30°	730.5	10.8
30°-40°	852.4	12.6
40°-50°	856.1	12.7
50°-60°	751.5	11.1
60°-70°	559.9	8.3
70°-80°	320.2	4.7
80°-90°	94.7	1.4
90°-100°	46.3	0.7
100°-110°	136.7	2.0
110°-120°	231.5	3.4
120°-130°	304.6	4.5
130°-140°	341.3	5.0
140°-150°	334.5	4.9
150°-160°	281.0	4.2
160°-170°	186.8	2.8
170°-180°	65.4	1.0
0°-30°	1400.3	20.7
0°-40°	2252.7	33.3
0°-60°	3860.3	57.1
0°-90°	4835.0	71.5
90°-120°	414.4	6.1
90°-150°	1394.9	20.6
90°-180°	1928.0	28.5
0°-180°	6763.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	5	9	11	13	6
95°	35	36	41	45	46	37
105°	123	125	128	132	133	131
115°	232	234	235	234	234	229
125°	338	341	342	341	340	303
135°	440	443	444	444	442	339
145°	533	535	537	536	535	333
155°	610	610	610	612	610	281
165°	663	662	662	664	661	187
175°	689	687	687	690	687	65
180°	691	691	691	691	691	



TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	31.9	32.0	32.2	32.4	32.6	32.7	32.6	32.5	32.4	32.3	32.4
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	13.0	13.7	14.3	15.0	15.6	16.5	17.5	18.6	19.6	20.6	21.4
95°	35.0	35.2	35.4	35.6	35.9	36.7	37.8	39.0	40.2	41.4	42.2
97.5°	58.1	58.2	58.2	58.3	58.4	59.3	61.0	62.6	64.3	65.9	66.7
100°	75.3	75.3	75.3	75.3	75.3	76.1	77.6	79.2	80.7	82.3	83.3
102.5°	93.8	94.3	94.7	95.2	95.7	96.3	97.1	97.9	98.7	99.4	100.7
105°	122.6	123.2	123.8	124.4	125.0	125.6	126.4	127.1	127.8	128.5	129.2
107.5°	154.4	155.0	155.6	156.2	156.8	157.4	158.0	158.4	159.0	159.6	159.9
110°	176.3	176.9	177.6	178.1	178.8	179.3	179.6	179.9	180.3	180.7	181.1



TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	198.7	199.1	199.3	199.6	200.0	200.4	200.9	201.2	201.7	202.2	202.4
115°	231.8	232.2	232.7	233.2	233.7	234.0	234.2	234.5	234.7	235.0	234.9
117.5°	264.9	265.0	265.3	265.5	265.7	266.0	266.2	266.4	266.6	266.8	266.9
120°	285.5	286.2	286.7	287.3	287.9	288.2	288.4	288.5	288.6	288.7	288.7
122.5°	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.6	309.9	310.3	310.2
125°	338.2	338.9	339.6	340.4	341.1	341.5	341.6	341.8	341.9	342.0	341.8
127.5°	370.5	370.9	371.3	371.6	372.1	372.4	372.5	372.7	372.8	373.0	372.9
130°	389.8	390.4	391.1	391.6	392.2	392.7	392.9	393.1	393.3	393.6	393.5
132.5°	409.2	410.2	411.1	412.1	413.1	413.6	413.5	413.5	413.4	413.4	413.3
135°	439.8	440.5	441.3	442.0	442.7	443.1	443.3	443.4	443.5	443.6	443.6
137.5°	468.6	469.4	470.0	470.7	471.5	471.9	472.2	472.4	472.7	473.0	473.1
140°	487.1	487.8	488.3	488.9	489.6	490.0	490.4	490.8	491.1	491.4	491.7
142.5°	505.7	506.1	506.6	507.2	507.7	508.1	508.6	509.1	509.5	509.9	510.1
145°	532.8	533.3	533.9	534.3	534.8	535.2	535.6	535.9	536.3	536.6	536.6
147.5°	558.0	558.3	558.6	558.8	559.1	559.3	559.6	560.0	560.2	560.5	560.8
150°	574.8	574.7	574.6	574.5	574.3	574.5	575.0	575.4	575.9	576.4	576.4
152.5°	588.5	588.7	588.9	589.1	589.2	589.4	589.6	589.7	589.9	590.2	590.5
155°	609.7	609.7	609.7	609.7	609.7	609.8	609.9	610.0	610.2	610.3	610.8
157.5°	628.7	628.4	628.1	627.9	627.6	627.5	627.6	627.8	627.9	628.0	628.5
160°	639.9	639.5	639.1	638.8	638.4	638.3	638.4	638.6	638.7	638.8	639.2
162.5°	649.8	649.5	649.2	648.9	648.7	648.6	648.6	648.7	648.7	648.7	649.2
165°	663.0	662.7	662.5	662.2	662.0	661.9	662.0	662.2	662.3	662.4	662.9
167.5°	674.2	673.7	673.2	672.7	672.2	672.0	672.0	672.0	672.0	672.0	672.7
170°	680.1	679.7	679.2	678.7	678.3	678.1	678.1	678.1	678.1	678.1	678.7
172.5°	684.5	684.0	683.5	683.1	682.6	682.3	682.3	682.3	682.3	682.3	683.1
175°	689.3	688.8	688.3	687.9	687.4	687.2	687.2	687.2	687.2	687.2	687.9
177.5°	691.8	691.4	691.1	690.7	690.2	690.0	689.9	689.8	689.8	689.7	690.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	32.5	32.6	32.8	32.6	32.1	31.7	31.3	30.8
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	22.2	23.0	23.8	24.3	24.6	24.9	25.1	25.4
95°	43.1	43.9	44.8	45.2	45.5	45.8	46.0	46.3
97.5°	67.5	68.3	69.1	69.6	69.7	69.8	69.9	70.1
100°	84.5	85.5	86.5	87.2	87.5	87.8	87.9	88.2
102.5°	101.8	103.0	104.2	104.9	105.3	105.6	105.9	106.2
105°	130.0	130.6	131.4	132.0	132.2	132.6	133.0	133.4
107.5°	160.3	160.7	161.0	161.2	161.2	161.2	161.1	161.1
110°	181.3	181.7	182.1	182.2	182.1	182.0	181.8	181.7





TEST NUMBER: P333311-830

CATALOG NUMBER: S125DIP-S1270D590U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.6	202.6	202.8	202.8	202.6	202.4	202.2	202.0
115°	234.7	234.6	234.5	234.4	234.2	234.1	234.0	233.9
117.5°	267.0	267.1	267.2	267.0	266.6	266.1	265.6	265.0
120°	288.7	288.7	288.7	288.5	288.0	287.6	287.1	286.6
122.5°	310.1	310.0	309.9	309.6	309.2	308.9	308.5	308.1
125°	341.5	341.3	341.0	340.8	340.7	340.6	340.4	340.4
127.5°	372.7	372.6	372.5	372.3	372.0	371.8	371.6	371.4
130°	393.3	393.2	393.1	392.9	392.7	392.5	392.2	392.0
132.5°	413.1	413.0	412.9	412.6	412.4	412.0	411.7	411.3
135°	443.6	443.6	443.6	443.4	442.9	442.4	442.0	441.5
137.5°	473.3	473.3	473.5	473.3	472.7	472.1	471.6	470.9
140°	491.9	492.2	492.4	492.2	491.6	491.1	490.4	489.8
142.5°	510.2	510.4	510.5	510.3	509.7	509.1	508.5	507.9
145°	536.6	536.6	536.6	536.4	536.1	535.7	535.4	535.0
147.5°	561.1	561.4	561.7	561.4	560.5	559.8	558.9	558.2
150°	576.4	576.4	576.4	576.3	576.1	575.8	575.6	575.3
152.5°	590.8	591.1	591.4	591.3	590.8	590.4	589.9	589.6
155°	611.2	611.7	612.2	612.2	611.5	611.0	610.3	609.7
157.5°	629.0	629.4	629.9	629.8	629.0	628.2	627.5	626.6
160°	639.7	640.2	640.6	640.6	640.1	639.4	638.9	638.3
162.5°	649.8	650.4	651.0	650.9	650.3	649.5	648.8	648.1
165°	663.4	663.8	664.4	664.2	663.5	662.8	662.0	661.4
167.5°	673.4	674.2	674.9	674.9	674.1	673.4	672.6	671.9
170°	679.5	680.1	680.9	680.8	680.0	679.2	678.3	677.5
172.5°	683.8	684.5	685.2	685.2	684.5	683.7	683.0	682.2
175°	688.6	689.3	690.0	689.9	689.2	688.3	687.5	686.6
177.5°	690.8	691.4	691.9	691.9	691.3	690.6	689.8	689.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0

(END OF REPORT)