

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333144-830

Luminaire Tested: **S125DIP-S375D1035U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333144-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1035U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4950.3 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3314	3314	3314	3314
5°	3837	3325	2912	3325
10°	4465	3308	2551	3308
15°	4942	3284	2353	3284
20°	5532	3245	2194	3245
25°	6481	3202	2117	3202
30°	7000	3159	2049	3159
35°	5755	3079	2006	3079
40°	4091	2967	1957	2967
45°	3143	2817	1929	2817
50°	2683	2629	1925	2629
55°	2389	2448	1942	2448
60°	2155	2248	1992	2248
65°	1991	2046	2043	2046
70°	1811	1839	2073	1839
75°	1597	1619	2054	1619
80°	1346	1320	1878	1320
85°	1067	948	1519	948



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.0
10°-20°	147.1	3.0
20°-30°	238.8	4.8
30°-40°	291.3	5.9
40°-50°	265.0	5.4
50°-60°	211.1	4.3
60°-70°	147.0	3.0
70°-80°	78.4	1.6
80°-90°	22.4	0.5
90°-100°	338.3	6.8
100°-110°	727.2	14.7
110°-120°	682.5	13.8
120°-130°	553.1	11.2
130°-140°	443.9	9.0
140°-150°	334.9	6.8
150°-160°	235.8	4.8
160°-170°	139.0	2.8
170°-180°	45.2	0.9
0°-30°	435.3	8.8
0°-40°	726.6	14.7
0°-60°	1202.7	24.3
0°-90°	1450.5	29.3
90°-120°	1747.9	35.3
90°-150°	3079.8	62.2
90°-180°	3500.0	70.7
0°-180°	4950.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	592	513	449	513	592	60
15°	739	491	352	491	739	212
25°	910	449	297	449	910	415
35°	730	390	254	390	730	447
45°	344	308	211	308	344	275
55°	212	217	172	217	212	191
65°	130	134	134	134	130	129
75°	64	65	82	65	64	69
85°	14	13	20	13	14	17
90°	22	1	22	1	22	15
95°	221	31	221	31	221	313
105°	1247	106	1247	106	1247	1239
115°	1389	190	1389	190	1389	1357
125°	1094	263	1094	263	1094	990
135°	909	309	909	309	909	704
145°	717	359	717	359	717	456
155°	601	410	601	410	601	280
165°	527	448	527	448	527	151
175°	473	466	473	466	473	46
180°	467	467	467	467	467	



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	542.7	542.1	541.3	540.0	541.0	538.0	536.7	534.2	531.2	530.2	529.0
5°	591.9	593.0	594.2	589.6	590.0	586.9	579.9	574.3	569.8	563.8	559.7
7.5°	651.2	648.7	648.4	645.5	640.4	636.2	629.0	619.6	610.6	600.3	591.8
10°	680.8	681.1	679.1	675.6	670.1	666.2	656.7	647.5	636.4	623.3	614.0
12.5°	703.1	704.1	701.5	696.8	694.2	685.4	677.9	667.0	653.8	643.4	629.1
15°	739.1	736.8	735.1	729.2	724.6	715.5	703.5	692.1	677.8	664.5	651.2
17.5°	773.9	775.9	772.6	767.2	753.0	742.3	726.3	710.8	692.9	675.0	659.2
20°	804.9	806.7	801.7	792.3	775.3	764.7	743.6	723.5	702.9	680.0	662.5
22.5°	843.7	842.3	835.5	821.2	806.5	786.8	763.9	739.5	713.6	687.8	664.6
25°	909.5	900.3	896.2	878.5	859.2	830.2	798.9	763.2	730.9	696.7	667.1
27.5°	946.0	943.1	938.5	926.2	905.9	874.9	837.9	794.4	748.9	705.8	666.9
30°	938.7	939.1	939.5	935.7	922.6	899.3	862.4	815.7	761.6	713.0	668.2
32.5°	873.8	881.7	889.4	898.3	902.0	897.5	874.5	832.2	776.6	721.4	667.5
35°	730.0	732.4	757.1	781.5	814.5	840.3	857.4	838.7	791.9	728.5	666.7
37.5°	569.2	581.0	598.0	625.6	673.4	716.1	771.2	796.4	781.4	730.8	665.2
40°	485.2	496.2	507.3	535.4	575.6	627.5	689.9	743.3	755.7	723.5	659.9
42.5°	420.5	429.0	441.4	462.5	496.2	542.1	601.8	671.6	714.4	702.3	648.9
45°	344.1	349.6	359.1	375.9	400.3	436.2	488.9	565.1	631.6	653.6	622.9
47.5°	294.5	294.5	302.0	313.5	331.1	361.7	400.7	460.3	531.3	583.8	581.4
50°	267.0	265.9	271.8	281.8	295.8	316.0	353.3	401.0	469.1	528.6	545.2
52.5°	243.3	243.5	247.0	254.5	266.2	283.4	311.2	354.3	412.5	473.5	504.7
55°	212.2	211.2	215.4	220.4	228.9	240.3	260.2	293.1	340.4	400.5	441.0
57.5°	183.5	186.0	187.6	191.1	198.1	205.8	222.6	246.8	284.3	335.8	378.6
60°	166.8	169.2	170.5	174.0	179.6	186.2	199.3	218.9	250.4	294.9	337.3
62.5°	151.8	153.7	154.2	157.3	161.9	168.2	178.5	195.0	220.0	258.8	300.4
65°	130.3	130.3	131.1	134.4	136.6	142.2	150.1	162.0	182.1	212.4	247.9
67.5°	109.4	110.5	110.3	111.7	113.7	118.1	123.7	133.6	148.5	170.5	199.0
70°	95.9	96.7	96.5	97.6	99.7	102.5	107.2	116.5	127.1	146.1	170.5
72.5°	83.6	84.0	83.4	84.8	86.1	88.6	93.8	98.8	108.7	124.7	144.8
75°	64.0	64.5	64.9	65.8	67.1	68.4	71.0	76.0	82.6	94.5	107.4
77.5°	48.0	47.1	48.3	48.1	48.8	49.9	52.1	54.8	60.1	67.8	77.7
80°	36.2	36.4	36.4	36.6	37.7	38.4	40.2	42.2	46.4	52.0	59.0
82.5°	26.4	27.0	26.6	27.1	27.9	28.4	29.5	31.1	33.5	38.0	43.0
85°	14.4	13.3	13.8	14.1	14.1	14.4	15.3	15.9	17.2	18.9	20.9
87.5°	8.5	8.9	8.9	8.9	9.0	8.7	9.1	9.0	9.3	9.6	10.0
90°	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0	16.0	15.1	13.2
92.5°	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7	245.5	303.3	308.2
95°	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6	815.8	833.7	680.3
97.5°	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6	1032.2	890.3	607.5
100°	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3	1084.9	849.6	542.0
102.5°	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8	1053.3	778.2	492.3
105°	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0	952.3	682.1	444.1
107.5°	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9	849.0	616.1	423.8
110°	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6	790.3	585.2	417.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9	746.7	567.2	417.7
115°	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3	699.1	547.6	420.6
117.5°	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3	670.7	538.0	426.8
120°	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2	654.9	533.5	432.8
122.5°	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9	641.3	529.7	438.1
125°	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4	622.9	525.0	447.0
127.5°	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2	606.0	522.7	456.9
130°	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4	594.7	521.2	463.0
132.5°	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6	585.6	521.2	469.7
135°	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1	574.9	521.2	478.9
137.5°	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4	565.3	522.4	487.4
140°	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1	560.8	523.1	491.2
142.5°	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3	557.0	523.9	493.4
145°	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5	551.4	523.1	495.9
147.5°	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5	545.5	520.7	496.8
150°	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8	541.0	518.4	496.8
152.5°	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2	535.7	515.5	496.1
155°	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9	526.9	510.0	494.0
157.5°	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6	518.6	504.4	491.5
160°	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1	511.9	500.6	489.3
162.5°	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9	505.9	496.1	487.0
165°	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4	496.8	489.3	483.6
167.5°	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4	488.0	482.7	478.3
170°	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4	482.7	478.9	476.1
172.5°	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6	477.4	474.4	473.1
175°	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3	470.4	469.5	469.5
177.5°	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2	467.4	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	527.9	526.7	525.3	522.8	519.9	518.3	515.9	514.3	511.2	508.6	505.8
5°	554.7	549.0	543.8	537.1	529.7	524.9	519.2	512.9	506.3	499.6	492.2
7.5°	582.5	572.4	561.6	549.9	538.4	527.8	517.7	507.9	498.7	487.5	478.1
10°	601.1	588.4	575.0	559.1	543.6	530.1	516.4	504.4	492.2	479.2	467.6
12.5°	619.7	602.9	583.8	566.4	547.8	531.5	515.4	500.0	484.7	470.2	456.8
15°	632.9	618.1	600.5	575.6	554.7	532.3	511.0	491.2	472.6	456.5	439.5
17.5°	641.6	622.5	603.5	579.8	552.3	527.3	503.0	480.3	459.5	439.0	422.7
20°	643.1	623.5	603.7	580.4	552.3	523.6	499.4	472.2	449.8	428.6	408.6
22.5°	642.6	620.4	598.8	574.9	547.4	520.9	491.7	464.0	439.6	418.9	397.9
25°	637.7	614.0	586.9	562.8	535.7	507.7	478.1	449.3	424.5	400.8	380.0
27.5°	633.6	602.9	572.2	544.0	517.9	492.2	463.8	434.4	406.9	382.9	363.4
30°	628.6	594.7	560.3	530.9	504.2	479.2	452.3	423.6	394.8	371.4	350.4
32.5°	624.1	584.7	548.4	516.3	488.0	463.6	438.9	411.6	383.3	359.5	338.6
35°	615.3	569.8	528.1	492.0	461.8	436.7	415.9	390.5	364.6	341.5	321.5
37.5°	604.2	550.2	505.5	467.6	434.4	408.0	388.8	369.2	344.3	322.1	304.0
40°	595.4	536.2	488.9	450.2	415.8	388.3	370.4	351.9	331.3	310.6	291.4
42.5°	584.5	523.7	472.2	430.5	396.4	369.7	350.9	335.3	317.0	297.7	279.9
45°	564.3	501.0	445.2	400.3	365.9	339.5	320.2	308.4	294.6	276.4	261.4
47.5°	534.6	473.6	415.9	369.7	334.1	309.7	291.5	280.2	270.6	257.0	243.4
50°	508.3	453.3	394.8	348.9	313.4	288.8	272.0	261.7	253.5	243.1	231.5
52.5°	478.9	427.6	374.1	328.7	293.5	269.3	252.9	243.8	237.0	229.5	218.1
55°	432.1	388.5	338.8	295.8	263.3	239.6	225.2	217.4	211.7	206.0	199.1
57.5°	380.6	346.5	302.6	263.1	233.2	211.6	198.2	190.6	186.2	183.2	179.2
60°	344.3	315.2	277.3	241.3	212.2	192.9	179.9	174.0	170.3	168.0	164.9
62.5°	310.7	286.7	251.7	218.9	193.3	175.2	163.5	157.8	154.3	153.1	150.6
65°	261.2	242.6	213.7	186.4	164.7	149.2	139.4	133.9	131.8	130.4	130.6
67.5°	212.3	201.0	177.8	154.6	137.1	124.2	116.3	112.2	111.0	109.3	109.3
70°	182.5	174.0	154.4	134.1	118.7	108.7	101.7	97.4	96.2	95.4	95.2
72.5°	156.2	148.7	131.8	115.6	101.6	92.8	87.1	84.5	82.7	82.2	82.1
75°	117.3	113.3	99.7	86.9	77.3	71.3	67.3	64.9	63.6	63.3	63.6
77.5°	83.4	79.8	71.3	62.1	56.1	51.5	48.2	47.3	45.9	45.9	45.7
80°	62.7	60.3	54.9	47.7	42.7	38.7	37.0	35.5	35.1	34.4	35.1
82.5°	45.4	42.9	39.2	34.6	30.4	28.2	26.4	25.9	25.6	25.4	25.4
85°	22.4	22.6	20.5	17.0	15.3	13.9	12.8	12.8	12.6	12.4	12.6
87.5°	10.1	9.4	8.5	7.6	6.3	5.5	4.9	4.9	4.5	4.8	5.3
90°	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9	1.9	3.8	5.7
92.5°	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5	13.9	21.9	33.5
95°	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0	32.0	39.5	49.9
97.5°	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6	52.7	58.0	68.3
100°	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9	67.8	71.5	81.8
102.5°	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7	82.8	85.8	96.9
105°	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3	106.3	111.0	120.5
107.5°	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4	132.3	136.8	144.5
110°	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7	149.6	153.4	161.8



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0	166.9	169.9	178.4
115°	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1	191.9	194.7	203.2
117.5°	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6	215.5	218.5	227.0
120°	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7	230.5	234.3	242.8
122.5°	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6	245.5	248.5	257.0
125°	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4	265.3	270.0	278.5
127.5°	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1	281.9	287.9	298.7
130°	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9	291.7	299.3	311.4
132.5°	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4	299.9	309.0	322.7
135°	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6	312.4	323.7	338.7
137.5°	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0	326.9	337.4	352.5
140°	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1	335.9	347.2	362.2
142.5°	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7	345.7	356.2	371.3
145°	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4	361.3	370.7	383.9
147.5°	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0	377.1	385.2	397.5
150°	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8	387.7	394.3	406.5
152.5°	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3	397.5	403.3	414.0
155°	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2	410.2	415.8	425.3
157.5°	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6	422.4	427.0	435.1
160°	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9	430.0	433.8	440.4
162.5°	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7	436.8	440.5	446.4
165°	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9	446.0	448.8	453.6
167.5°	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7	453.7	455.4	458.1
170°	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2	458.3	459.2	461.1
172.5°	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2	460.5	461.5	463.3
175°	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7	463.8	464.8	465.7
177.5°	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4	465.9	465.9	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	504.3	502.3	500.8	497.3	495.3	492.8	490.7	492.9	490.5	491.5	489.9
5°	488.5	482.4	478.1	471.7	466.3	461.3	457.6	456.9	455.2	454.3	451.7
7.5°	469.6	461.9	454.5	446.2	439.2	432.2	427.6	423.9	421.4	418.1	415.8
10°	458.5	448.2	439.5	429.5	420.8	413.1	407.1	404.0	401.1	397.0	395.5
12.5°	444.7	434.1	423.5	412.7	404.4	395.9	390.7	386.1	384.1	379.5	379.0
15°	428.2	412.3	401.8	391.0	379.4	372.4	368.1	363.1	360.9	357.6	355.2
17.5°	408.5	394.3	381.3	369.9	360.1	354.2	348.7	345.3	341.6	339.4	335.5
20°	394.2	380.7	367.6	355.6	348.0	341.3	337.0	333.7	329.7	328.7	324.7
22.5°	382.2	367.3	354.8	344.7	336.4	328.8	324.0	321.8	319.1	315.8	315.0
25°	362.6	347.1	336.5	326.5	319.1	312.1	308.9	306.0	303.4	301.0	300.1
27.5°	345.7	331.9	319.2	310.2	303.7	297.4	294.5	291.1	289.2	287.2	284.8
30°	333.8	319.7	308.6	299.9	292.9	287.3	284.2	281.8	280.1	278.3	277.0
32.5°	321.7	308.6	297.8	289.3	282.3	278.1	275.3	273.6	271.7	269.7	268.0
35°	305.6	291.2	280.7	273.3	267.9	264.6	261.6	260.0	257.9	257.9	256.1
37.5°	287.4	274.9	265.7	259.0	254.1	251.2	247.9	246.9	245.4	244.5	243.9
40°	276.6	265.0	256.4	249.6	244.4	242.0	239.3	237.6	236.8	235.6	235.3
42.5°	265.4	254.4	246.1	239.9	235.3	233.3	230.8	229.6	227.8	226.4	226.1
45°	248.5	237.8	230.2	225.2	221.3	218.9	217.4	214.7	213.9	212.2	211.9
47.5°	232.4	222.2	214.7	210.6	207.2	205.2	202.8	200.2	199.2	198.3	198.2
50°	220.4	211.0	204.1	200.2	196.9	194.1	191.6	189.9	189.3	189.3	189.7
52.5°	208.2	200.2	194.4	189.5	186.4	183.4	181.2	180.1	179.2	180.2	181.0
55°	190.4	182.3	178.0	173.3	170.3	166.8	165.7	165.3	164.7	166.4	167.3
57.5°	171.4	165.8	160.7	156.2	153.4	151.4	150.0	149.7	150.9	151.7	154.6
60°	159.4	152.9	148.4	144.9	141.6	140.3	139.8	139.4	140.3	142.6	146.4
62.5°	146.2	140.9	135.9	133.4	130.9	128.8	128.7	128.9	130.6	133.5	137.1
65°	126.8	122.2	118.9	115.8	113.9	112.6	113.0	113.9	115.8	119.6	123.7
67.5°	107.0	103.9	100.9	98.5	96.6	96.6	97.1	98.4	100.7	104.9	108.7
70°	94.3	90.9	88.4	87.4	85.8	84.9	86.2	88.4	90.4	94.3	97.6
72.5°	81.6	78.6	76.7	76.0	75.3	74.6	75.1	77.5	80.1	84.0	87.8
75°	62.7	61.6	60.3	59.5	58.8	59.3	59.7	61.8	64.0	68.1	72.5
77.5°	45.8	44.7	43.8	43.6	43.3	43.5	44.8	46.4	48.4	51.5	54.8
80°	34.6	34.2	33.7	33.6	33.6	33.7	35.5	36.6	38.5	41.4	44.0
82.5°	25.3	25.0	24.9	24.8	25.0	25.1	26.1	27.5	29.1	31.3	33.6
85°	13.3	12.8	13.5	13.8	13.3	13.9	14.4	15.3	15.9	17.0	18.1
87.5°	5.8	6.6	6.6	7.2	7.4	8.1	8.1	9.0	9.5	10.0	10.3
90°	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0	17.9	18.9	20.7
92.5°	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7	121.0	91.0	77.2
95°	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6	533.5	417.7	338.7
97.5°	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6	907.2	794.5	684.6
100°	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3	1111.3	1014.3	916.4
102.5°	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8	1236.1	1189.7	1123.4
105°	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0	1306.9	1348.3	1337.9
107.5°	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9	1243.9	1350.2	1399.3
110°	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6	1172.3	1305.0	1385.1



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9	1101.6	1235.8	1330.1
115°	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3	1000.2	1129.1	1231.6
117.5°	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3	930.0	1041.0	1135.1
120°	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2	890.1	993.6	1076.4
122.5°	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9	861.5	953.7	1031.2
125°	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4	823.3	905.1	972.9
127.5°	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2	786.8	863.2	926.6
130°	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4	761.2	834.6	895.8
132.5°	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6	737.1	803.7	862.6
135°	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1	700.0	760.3	813.9
137.5°	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4	666.9	717.0	762.5
140°	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1	647.3	690.6	730.2
142.5°	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3	630.7	668.1	702.3
145°	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5	609.7	638.9	664.3
147.5°	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5	592.2	614.6	633.8
150°	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8	582.4	600.3	617.3
152.5°	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2	572.6	589.0	602.2
155°	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9	558.0	571.2	581.5
157.5°	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6	544.0	554.2	562.3
160°	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1	533.5	542.9	549.5
162.5°	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9	524.4	532.3	538.2
165°	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4	511.0	516.6	521.2
167.5°	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4	497.8	502.1	505.5
170°	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4	490.2	493.0	494.9
172.5°	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6	483.4	485.5	486.6
175°	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3	473.3	475.1	475.1
177.5°	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2	468.9	468.9	468.9
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	488.9	490.1	489.1	490.5	489.1	490.1	488.9	489.9	491.5	490.5	492.9
5°	450.6	448.7	450.0	449.1	450.0	448.7	450.6	451.7	454.3	455.2	456.9
7.5°	415.3	413.4	411.2	410.2	411.2	413.4	415.3	415.8	418.1	421.4	423.9
10°	393.1	390.7	390.5	389.0	390.5	390.7	393.1	395.5	397.0	401.1	404.0
12.5°	376.9	374.7	372.2	371.6	372.2	374.7	376.9	379.0	379.5	384.1	386.1
15°	353.9	352.1	350.6	351.9	350.6	352.1	353.9	355.2	357.6	360.9	363.1
17.5°	334.8	333.4	333.1	331.5	333.1	333.4	334.8	335.5	339.4	341.6	345.3
20°	322.7	321.7	322.2	319.2	322.2	321.7	322.7	324.7	328.7	329.7	333.7
22.5°	313.2	311.0	310.8	310.2	310.8	311.0	313.2	315.0	315.8	319.1	321.8
25°	298.1	297.1	296.0	297.1	296.0	297.1	298.1	300.1	301.0	303.4	306.0
27.5°	285.0	283.7	283.4	283.6	283.4	283.7	285.0	284.8	287.2	289.2	291.1
30°	277.0	274.8	275.0	274.8	275.0	274.8	277.0	277.0	278.3	280.1	281.8
32.5°	268.3	266.8	266.6	266.2	266.6	266.8	268.3	268.0	269.7	271.7	273.6
35°	255.4	255.4	254.4	254.4	254.4	255.4	255.4	256.1	257.9	257.9	260.0
37.5°	243.4	243.2	242.5	242.6	242.5	243.2	243.4	243.9	244.5	245.4	246.9
40°	234.3	234.1	233.5	232.1	233.5	234.1	234.3	235.3	235.6	236.8	237.6
42.5°	225.6	224.9	224.6	224.1	224.6	224.9	225.6	226.1	226.4	227.8	229.6
45°	211.9	211.9	211.5	211.2	211.5	211.9	211.9	211.9	212.2	213.9	214.7
47.5°	198.6	199.0	199.8	199.6	199.8	199.0	198.6	198.2	198.3	199.2	200.2
50°	190.6	190.8	191.4	191.6	191.4	190.8	190.6	189.7	189.3	189.3	189.9
52.5°	181.7	182.9	183.8	183.6	183.8	182.9	181.7	181.0	180.2	179.2	180.1
55°	169.2	170.8	172.3	172.5	172.3	170.8	169.2	167.3	166.4	164.7	165.3
57.5°	156.9	159.0	160.6	161.2	160.6	159.0	156.9	154.6	151.7	150.9	149.7
60°	148.5	151.4	153.4	154.2	153.4	151.4	148.5	146.4	142.6	140.3	139.4
62.5°	140.5	143.7	145.6	145.8	145.6	143.7	140.5	137.1	133.5	130.6	128.9
65°	127.4	130.6	132.4	133.7	132.4	130.6	127.4	123.7	119.6	115.8	113.9
67.5°	113.3	116.6	118.5	119.5	118.5	116.6	113.3	108.7	104.9	100.7	98.4
70°	103.0	106.3	108.9	109.8	108.9	106.3	103.0	97.6	94.3	90.4	88.4
72.5°	92.9	95.9	97.9	99.0	97.9	95.9	92.9	87.8	84.0	80.1	77.5
75°	75.3	79.3	81.2	82.3	81.2	79.3	75.3	72.5	68.1	64.0	61.8
77.5°	58.1	61.6	62.9	63.4	62.9	61.6	58.1	54.8	51.5	48.4	46.4
80°	46.6	48.8	50.3	50.5	50.3	48.8	46.6	44.0	41.4	38.5	36.6
82.5°	35.8	37.6	38.1	38.6	38.1	37.6	35.8	33.6	31.3	29.1	27.5
85°	19.6	20.5	20.7	20.5	20.7	20.5	19.6	18.1	17.0	15.9	15.3
87.5°	10.6	10.4	10.6	10.9	10.6	10.4	10.6	10.3	10.0	9.5	9.0
90°	20.7	20.7	21.7	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0
92.5°	65.1	62.9	61.5	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7
95°	271.9	243.7	236.2	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6
97.5°	626.5	573.7	546.5	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6
100°	851.5	783.8	748.9	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3
102.5°	1054.0	1005.9	968.0	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8
105°	1307.9	1276.9	1258.0	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0
107.5°	1414.6	1414.4	1408.2	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9
110°	1427.4	1445.2	1451.8	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1391.9	1422.7	1439.1	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9
115°	1305.0	1350.2	1376.6	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3
117.5°	1208.5	1255.2	1281.3	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3
120°	1146.0	1191.2	1216.6	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2
122.5°	1093.3	1134.7	1160.2	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9
125°	1025.6	1064.1	1084.9	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4
127.5°	974.4	1008.4	1028.0	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2
130°	942.8	973.8	992.7	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4
132.5°	909.6	940.8	958.0	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6
135°	855.3	886.4	903.2	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1
137.5°	799.6	827.8	843.5	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4
140°	765.0	789.5	803.5	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1
142.5°	731.9	752.5	765.9	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3
145°	686.8	702.9	713.2	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5
147.5°	651.7	664.5	670.5	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5
150°	631.3	642.6	646.4	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8
152.5°	614.1	623.1	626.8	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2
155°	590.9	597.5	600.3	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9
157.5°	569.7	575.0	577.7	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6
160°	556.1	560.8	562.7	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1
162.5°	543.3	547.2	547.6	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9
165°	525.0	526.9	526.9	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4
167.5°	507.4	509.1	508.3	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4
170°	496.8	497.8	497.8	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4
172.5°	487.0	488.7	487.2	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6
175°	475.1	476.1	474.2	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3
177.5°	468.2	468.9	466.7	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	490.7	492.8	495.3	497.3	500.8	502.3	504.3	505.8	508.6	511.2	514.3
5°	457.6	461.3	466.3	471.7	478.1	482.4	488.5	492.2	499.6	506.3	512.9
7.5°	427.6	432.2	439.2	446.2	454.5	461.9	469.6	478.1	487.5	498.7	507.9
10°	407.1	413.1	420.8	429.5	439.5	448.2	458.5	467.6	479.2	492.2	504.4
12.5°	390.7	395.9	404.4	412.7	423.5	434.1	444.7	456.8	470.2	484.7	500.0
15°	368.1	372.4	379.4	391.0	401.8	412.3	428.2	439.5	456.5	472.6	491.2
17.5°	348.7	354.2	360.1	369.9	381.3	394.3	408.5	422.7	439.0	459.5	480.3
20°	337.0	341.3	348.0	355.6	367.6	380.7	394.2	408.6	428.6	449.8	472.2
22.5°	324.0	328.8	336.4	344.7	354.8	367.3	382.2	397.9	418.9	439.6	464.0
25°	308.9	312.1	319.1	326.5	336.5	347.1	362.6	380.0	400.8	424.5	449.3
27.5°	294.5	297.4	303.7	310.2	319.2	331.9	345.7	363.4	382.9	406.9	434.4
30°	284.2	287.3	292.9	299.9	308.6	319.7	333.8	350.4	371.4	394.8	423.6
32.5°	275.3	278.1	282.3	289.3	297.8	308.6	321.7	338.6	359.5	383.3	411.6
35°	261.6	264.6	267.9	273.3	280.7	291.2	305.6	321.5	341.5	364.6	390.5
37.5°	247.9	251.2	254.1	259.0	265.7	274.9	287.4	304.0	322.1	344.3	369.2
40°	239.3	242.0	244.4	249.6	256.4	265.0	276.6	291.4	310.6	331.3	351.9
42.5°	230.8	233.3	235.3	239.9	246.1	254.4	265.4	279.9	297.7	317.0	335.3
45°	217.4	218.9	221.3	225.2	230.2	237.8	248.5	261.4	276.4	294.6	308.4
47.5°	202.8	205.2	207.2	210.6	214.7	222.2	232.4	243.4	257.0	270.6	280.2
50°	191.6	194.1	196.9	200.2	204.1	211.0	220.4	231.5	243.1	253.5	261.7
52.5°	181.2	183.4	186.4	189.5	194.4	200.2	208.2	218.1	229.5	237.0	243.8
55°	165.7	166.8	170.3	173.3	178.0	182.3	190.4	199.1	206.0	211.7	217.4
57.5°	150.0	151.4	153.4	156.2	160.7	165.8	171.4	179.2	183.2	186.2	190.6
60°	139.8	140.3	141.6	144.9	148.4	152.9	159.4	164.9	168.0	170.3	174.0
62.5°	128.7	128.8	130.9	133.4	135.9	140.9	146.2	150.6	153.1	154.3	157.8
65°	113.0	112.6	113.9	115.8	118.9	122.2	126.8	130.6	130.4	131.8	133.9
67.5°	97.1	96.6	96.6	98.5	100.9	103.9	107.0	109.3	109.3	111.0	112.2
70°	86.2	84.9	85.8	87.4	88.4	90.9	94.3	95.2	95.4	96.2	97.4
72.5°	75.1	74.6	75.3	76.0	76.7	78.6	81.6	82.1	82.2	82.7	84.5
75°	59.7	59.3	58.8	59.5	60.3	61.6	62.7	63.6	63.3	63.6	64.9
77.5°	44.8	43.5	43.3	43.6	43.8	44.7	45.8	45.7	45.9	45.9	47.3
80°	35.5	33.7	33.6	33.6	33.7	34.2	34.6	35.1	34.4	35.1	35.5
82.5°	26.1	25.1	25.0	24.8	24.9	25.0	25.3	25.4	25.4	25.6	25.9
85°	14.4	13.9	13.3	13.8	13.5	12.8	13.3	12.6	12.4	12.6	12.8
87.5°	8.1	8.1	7.4	7.2	6.6	6.6	5.8	5.3	4.8	4.5	4.9
90°	16.0	15.1	13.2	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9
92.5°	245.5	303.3	308.2	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5
95°	815.8	833.7	680.3	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0
97.5°	1032.2	890.3	607.5	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6
100°	1084.9	849.6	542.0	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9
102.5°	1053.3	778.2	492.3	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7
105°	952.3	682.1	444.1	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3
107.5°	849.0	616.1	423.8	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4
110°	790.3	585.2	417.7	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	746.7	567.2	417.7	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0
115°	699.1	547.6	420.6	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1
117.5°	670.7	538.0	426.8	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6
120°	654.9	533.5	432.8	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7
122.5°	641.3	529.7	438.1	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6
125°	622.9	525.0	447.0	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4
127.5°	606.0	522.7	456.9	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1
130°	594.7	521.2	463.0	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9
132.5°	585.6	521.2	469.7	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4
135°	574.9	521.2	478.9	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6
137.5°	565.3	522.4	487.4	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0
140°	560.8	523.1	491.2	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1
142.5°	557.0	523.9	493.4	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7
145°	551.4	523.1	495.9	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4
147.5°	545.5	520.7	496.8	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0
150°	541.0	518.4	496.8	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8
152.5°	535.7	515.5	496.1	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3
155°	526.9	510.0	494.0	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2
157.5°	518.6	504.4	491.5	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6
160°	511.9	500.6	489.3	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9
162.5°	505.9	496.1	487.0	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7
165°	496.8	489.3	483.6	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9
167.5°	488.0	482.7	478.3	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7
170°	482.7	478.9	476.1	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2
172.5°	477.4	474.4	473.1	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2
175°	470.4	469.5	469.5	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7
177.5°	467.4	466.7	466.7	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	515.9	518.3	519.9	522.8	525.3	526.7	527.9	529.0	530.2	531.2	534.2
5°	519.2	524.9	529.7	537.1	543.8	549.0	554.7	559.7	563.8	569.8	574.3
7.5°	517.7	527.8	538.4	549.9	561.6	572.4	582.5	591.8	600.3	610.6	619.6
10°	516.4	530.1	543.6	559.1	575.0	588.4	601.1	614.0	623.3	636.4	647.5
12.5°	515.4	531.5	547.8	566.4	583.8	602.9	619.7	629.1	643.4	653.8	667.0
15°	511.0	532.3	554.7	575.6	600.5	618.1	632.9	651.2	664.5	677.8	692.1
17.5°	503.0	527.3	552.3	579.8	603.5	622.5	641.6	659.2	675.0	692.9	710.8
20°	499.4	523.6	552.3	580.4	603.7	623.5	643.1	662.5	680.0	702.9	723.5
22.5°	491.7	520.9	547.4	574.9	598.8	620.4	642.6	664.6	687.8	713.6	739.5
25°	478.1	507.7	535.7	562.8	586.9	614.0	637.7	667.1	696.7	730.9	763.2
27.5°	463.8	492.2	517.9	544.0	572.2	602.9	633.6	666.9	705.8	748.9	794.4
30°	452.3	479.2	504.2	530.9	560.3	594.7	628.6	668.2	713.0	761.6	815.7
32.5°	438.9	463.6	488.0	516.3	548.4	584.7	624.1	667.5	721.4	776.6	832.2
35°	415.9	436.7	461.8	492.0	528.1	569.8	615.3	666.7	728.5	791.9	838.7
37.5°	388.8	408.0	434.4	467.6	505.5	550.2	604.2	665.2	730.8	781.4	796.4
40°	370.4	388.3	415.8	450.2	488.9	536.2	595.4	659.9	723.5	755.7	743.3
42.5°	350.9	369.7	396.4	430.5	472.2	523.7	584.5	648.9	702.3	714.4	671.6
45°	320.2	339.5	365.9	400.3	445.2	501.0	564.3	622.9	653.6	631.6	565.1
47.5°	291.5	309.7	334.1	369.7	415.9	473.6	534.6	581.4	583.8	531.3	460.3
50°	272.0	288.8	313.4	348.9	394.8	453.3	508.3	545.2	528.6	469.1	401.0
52.5°	252.9	269.3	293.5	328.7	374.1	427.6	478.9	504.7	473.5	412.5	354.3
55°	225.2	239.6	263.3	295.8	338.8	388.5	432.1	441.0	400.5	340.4	293.1
57.5°	198.2	211.6	233.2	263.1	302.6	346.5	380.6	378.6	335.8	284.3	246.8
60°	179.9	192.9	212.2	241.3	277.3	315.2	344.3	337.3	294.9	250.4	218.9
62.5°	163.5	175.2	193.3	218.9	251.7	286.7	310.7	300.4	258.8	220.0	195.0
65°	139.4	149.2	164.7	186.4	213.7	242.6	261.2	247.9	212.4	182.1	162.0
67.5°	116.3	124.2	137.1	154.6	177.8	201.0	212.3	199.0	170.5	148.5	133.6
70°	101.7	108.7	118.7	134.1	154.4	174.0	182.5	170.5	146.1	127.1	116.5
72.5°	87.1	92.8	101.6	115.6	131.8	148.7	156.2	144.8	124.7	108.7	98.8
75°	67.3	71.3	77.3	86.9	99.7	113.3	117.3	107.4	94.5	82.6	76.0
77.5°	48.2	51.5	56.1	62.1	71.3	79.8	83.4	77.7	67.8	60.1	54.8
80°	37.0	38.7	42.7	47.7	54.9	60.3	62.7	59.0	52.0	46.4	42.2
82.5°	26.4	28.2	30.4	34.6	39.2	42.9	45.4	43.0	38.0	33.5	31.1
85°	12.8	13.9	15.3	17.0	20.5	22.6	22.4	20.9	18.9	17.2	15.9
87.5°	4.9	5.5	6.3	7.6	8.5	9.4	10.1	10.0	9.6	9.3	9.0
90°	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0
92.5°	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7
95°	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6
97.5°	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6
100°	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3
102.5°	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8
105°	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0
107.5°	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9
110°	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9
115°	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3
117.5°	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3
120°	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2
122.5°	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9
125°	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4
127.5°	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2
130°	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4
132.5°	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6
135°	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1
137.5°	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4
140°	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1
142.5°	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3
145°	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5
147.5°	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5
150°	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8
152.5°	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2
155°	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9
157.5°	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6
160°	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1
162.5°	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9
165°	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4
167.5°	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4
170°	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4
172.5°	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6
175°	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3
177.5°	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	536.7	538.0	541.0	540.0	541.3	542.1	542.7
5°	579.9	586.9	590.0	589.6	594.2	593.0	591.9
7.5°	629.0	636.2	640.4	645.5	648.4	648.7	651.2
10°	656.7	666.2	670.1	675.6	679.1	681.1	680.8
12.5°	677.9	685.4	694.2	696.8	701.5	704.1	703.1
15°	703.5	715.5	724.6	729.2	735.1	736.8	739.1
17.5°	726.3	742.3	753.0	767.2	772.6	775.9	773.9
20°	743.6	764.7	775.3	792.3	801.7	806.7	804.9
22.5°	763.9	786.8	806.5	821.2	835.5	842.3	843.7
25°	798.9	830.2	859.2	878.5	896.2	900.3	909.5
27.5°	837.9	874.9	905.9	926.2	938.5	943.1	946.0
30°	862.4	899.3	922.6	935.7	939.5	939.1	938.7
32.5°	874.5	897.5	902.0	898.3	889.4	881.7	873.8
35°	857.4	840.3	814.5	781.5	757.1	732.4	730.0
37.5°	771.2	716.1	673.4	625.6	598.0	581.0	569.2
40°	689.9	627.5	575.6	535.4	507.3	496.2	485.2
42.5°	601.8	542.1	496.2	462.5	441.4	429.0	420.5
45°	488.9	436.2	400.3	375.9	359.1	349.6	344.1
47.5°	400.7	361.7	331.1	313.5	302.0	294.5	294.5
50°	353.3	316.0	295.8	281.8	271.8	265.9	267.0
52.5°	311.2	283.4	266.2	254.5	247.0	243.5	243.3
55°	260.2	240.3	228.9	220.4	215.4	211.2	212.2
57.5°	222.6	205.8	198.1	191.1	187.6	186.0	183.5
60°	199.3	186.2	179.6	174.0	170.5	169.2	166.8
62.5°	178.5	168.2	161.9	157.3	154.2	153.7	151.8
65°	150.1	142.2	136.6	134.4	131.1	130.3	130.3
67.5°	123.7	118.1	113.7	111.7	110.3	110.5	109.4
70°	107.2	102.5	99.7	97.6	96.5	96.7	95.9
72.5°	93.8	88.6	86.1	84.8	83.4	84.0	83.6
75°	71.0	68.4	67.1	65.8	64.9	64.5	64.0
77.5°	52.1	49.9	48.8	48.1	48.3	47.1	48.0
80°	40.2	38.4	37.7	36.6	36.4	36.4	36.2
82.5°	29.5	28.4	27.9	27.1	26.6	27.0	26.4
85°	15.3	14.4	14.1	14.1	13.8	13.3	14.4
87.5°	9.1	8.7	9.0	8.9	8.9	8.9	8.5
90°	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333144-830

CATALOG NUMBER: S125DIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)