

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333153-830

Luminaire Tested: **S125DIP-S375D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333153-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1205U830-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5524.6 lumens  
Efficiency: N/A  
Efficacy: 130.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	71	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	63	54	47	43	42	38	34	31	28	26	21	20	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3314	3314	3314	3314
5°	3837	3325	2912	3325
10°	4465	3308	2551	3308
15°	4942	3284	2353	3284
20°	5532	3245	2194	3245
25°	6481	3202	2117	3202
30°	7000	3159	2049	3159
35°	5755	3079	2006	3079
40°	4091	2967	1957	2967
45°	3143	2817	1929	2817
50°	2683	2629	1925	2629
55°	2389	2448	1942	2448
60°	2155	2248	1992	2248
65°	1991	2046	2043	2046
70°	1811	1839	2073	1839
75°	1597	1619	2054	1619
80°	1346	1320	1878	1320
85°	1067	948	1519	948



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.4	0.9
10°-20°	147.1	2.7
20°-30°	238.8	4.3
30°-40°	291.3	5.3
40°-50°	265.0	4.8
50°-60°	211.1	3.8
60°-70°	147.0	2.7
70°-80°	78.4	1.4
80°-90°	22.8	0.4
90°-100°	393.7	7.1
100°-110°	846.4	15.3
110°-120°	794.4	14.4
120°-130°	643.8	11.7
130°-140°	516.6	9.4
140°-150°	389.9	7.1
150°-160°	274.4	5.0
160°-170°	161.8	2.9
170°-180°	52.6	1.0
0°-30°	435.3	7.9
0°-40°	726.6	13.2
0°-60°	1202.7	21.8
0°-90°	1450.9	26.3
90°-120°	2034.5	36.8
90°-150°	3584.8	64.9
90°-180°	4074.0	73.7
0°-180°	5524.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	592	513	449	513	592	60
15°	739	491	352	491	739	212
25°	910	449	297	449	910	415
35°	730	390	254	390	730	447
45°	344	308	211	308	344	275
55°	212	217	172	217	212	191
65°	130	134	134	134	130	129
75°	64	65	82	65	64	69
85°	14	13	20	13	14	17
90°	25	1	25	1	25	18
95°	257	36	257	36	257	365
105°	1451	124	1451	124	1451	1442
115°	1616	221	1616	221	1616	1579
125°	1274	307	1274	307	1274	1152
135°	1058	359	1058	359	1058	820
145°	834	418	834	418	834	530
155°	700	478	700	478	700	326
165°	613	521	613	521	613	175
175°	551	542	551	542	551	54
180°	543	543	543	543	543	



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	542.7	542.1	541.3	540.0	541.0	538.0	536.7	534.2	531.2	530.2	529.0
5°	591.9	593.0	594.2	589.6	590.0	586.9	579.9	574.3	569.8	563.8	559.7
7.5°	651.2	648.7	648.4	645.5	640.4	636.2	629.0	619.6	610.6	600.3	591.8
10°	680.8	681.1	679.1	675.6	670.1	666.2	656.7	647.5	636.4	623.3	614.0
12.5°	703.1	704.1	701.5	696.8	694.2	685.4	677.9	667.0	653.8	643.4	629.1
15°	739.1	736.8	735.1	729.2	724.6	715.5	703.5	692.1	677.8	664.5	651.2
17.5°	773.9	775.9	772.6	767.2	753.0	742.3	726.3	710.8	692.9	675.0	659.2
20°	804.9	806.7	801.7	792.3	775.3	764.7	743.6	723.5	702.9	680.0	662.5
22.5°	843.7	842.3	835.5	821.2	806.5	786.8	763.9	739.5	713.6	687.8	664.6
25°	909.5	900.3	896.2	878.5	859.2	830.2	798.9	763.2	730.9	696.7	667.1
27.5°	946.0	943.1	938.5	926.2	905.9	874.9	837.9	794.4	748.9	705.8	666.9
30°	938.7	939.1	939.5	935.7	922.6	899.3	862.4	815.7	761.6	713.0	668.2
32.5°	873.8	881.7	889.4	898.3	902.0	897.5	874.5	832.2	776.6	721.4	667.5
35°	730.0	732.4	757.1	781.5	814.5	840.3	857.4	838.7	791.9	728.5	666.7
37.5°	569.2	581.0	598.0	625.6	673.4	716.1	771.2	796.4	781.4	730.8	665.2
40°	485.2	496.2	507.3	535.4	575.6	627.5	689.9	743.3	755.7	723.5	659.9
42.5°	420.5	429.0	441.4	462.5	496.2	542.1	601.8	671.6	714.4	702.3	648.9
45°	344.1	349.6	359.1	375.9	400.3	436.2	488.9	565.1	631.6	653.6	622.9
47.5°	294.5	294.5	302.0	313.5	331.1	361.7	400.7	460.3	531.3	583.8	581.4
50°	267.0	265.9	271.8	281.8	295.8	316.0	353.3	401.0	469.1	528.6	545.2
52.5°	243.3	243.5	247.0	254.5	266.2	283.4	311.2	354.3	412.5	473.5	504.7
55°	212.2	211.2	215.4	220.4	228.9	240.3	260.2	293.1	340.4	400.5	441.0
57.5°	183.5	186.0	187.6	191.1	198.1	205.8	222.6	246.8	284.3	335.8	378.6
60°	166.8	169.2	170.5	174.0	179.6	186.2	199.3	218.9	250.4	294.9	337.3
62.5°	151.8	153.7	154.2	157.3	161.9	168.2	178.5	195.0	220.0	258.8	300.4
65°	130.3	130.3	131.1	134.4	136.6	142.2	150.1	162.0	182.1	212.4	247.9
67.5°	109.4	110.5	110.3	111.7	113.7	118.1	123.7	133.6	148.5	170.5	199.0
70°	95.9	96.7	96.5	97.6	99.7	102.5	107.2	116.5	127.1	146.1	170.5
72.5°	83.6	84.0	83.4	84.8	86.1	88.6	93.8	98.8	108.7	124.7	144.8
75°	64.0	64.5	64.9	65.8	67.1	68.4	71.0	76.0	82.6	94.5	107.4
77.5°	48.0	47.1	48.3	48.1	48.8	49.9	52.1	54.8	60.1	67.8	77.7
80°	36.2	36.4	36.4	36.6	37.7	38.4	40.2	42.2	46.4	52.0	59.0
82.5°	26.4	27.0	26.6	27.1	27.9	28.4	29.5	31.1	33.5	38.0	43.0
85°	14.4	13.3	13.8	14.1	14.1	14.4	15.3	15.9	17.2	18.9	20.9
87.5°	9.2	9.6	9.5	9.5	9.7	9.2	9.7	9.5	9.8	10.1	10.4
90°	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7	18.7	17.5	15.4
92.5°	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1	285.9	353.1	358.8
95°	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4	949.5	970.3	791.8
97.5°	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7	1201.5	1036.2	707.1
100°	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1	1262.7	988.9	630.8
102.5°	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8	1226.0	905.7	573.0
105°	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2	1108.3	794.0	516.9
107.5°	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6	988.4	717.1	493.2
110°	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5	919.9	681.2	486.3



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7	869.1	660.2	486.3
115°	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5	813.7	637.4	489.6
117.5°	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1	780.6	626.2	496.8
120°	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7	762.2	620.9	503.8
122.5°	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0	746.5	616.6	509.9
125°	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6	725.0	611.1	520.2
127.5°	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5	705.3	608.5	531.8
130°	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7	692.2	606.7	538.9
132.5°	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7	681.6	606.7	546.7
135°	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2	669.2	606.7	557.4
137.5°	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2	658.0	608.0	567.3
140°	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0	652.7	608.9	571.7
142.5°	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6	648.4	609.8	574.3
145°	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7	641.8	608.9	577.2
147.5°	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8	635.0	606.1	578.2
150°	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8	629.7	603.4	578.2
152.5°	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1	623.6	599.9	577.4
155°	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9	613.3	593.6	575.0
157.5°	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8	603.7	587.0	572.1
160°	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0	595.8	582.7	569.5
162.5°	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4	588.8	577.4	566.8
165°	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0	578.2	569.5	562.9
167.5°	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3	568.0	561.8	556.8
170°	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3	561.8	557.4	554.2
172.5°	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4	555.7	552.2	550.6
175°	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9	547.6	546.5	546.5
177.5°	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0	544.1	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	527.9	526.7	525.3	522.8	519.9	518.3	515.9	514.3	511.2	508.6	505.8
5°	554.7	549.0	543.8	537.1	529.7	524.9	519.2	512.9	506.3	499.6	492.2
7.5°	582.5	572.4	561.6	549.9	538.4	527.8	517.7	507.9	498.7	487.5	478.1
10°	601.1	588.4	575.0	559.1	543.6	530.1	516.4	504.4	492.2	479.2	467.6
12.5°	619.7	602.9	583.8	566.4	547.8	531.5	515.4	500.0	484.7	470.2	456.8
15°	632.9	618.1	600.5	575.6	554.7	532.3	511.0	491.2	472.6	456.5	439.5
17.5°	641.6	622.5	603.5	579.8	552.3	527.3	503.0	480.3	459.5	439.0	422.7
20°	643.1	623.5	603.7	580.4	552.3	523.6	499.4	472.2	449.8	428.6	408.6
22.5°	642.6	620.4	598.8	574.9	547.4	520.9	491.7	464.0	439.6	418.9	397.9
25°	637.7	614.0	586.9	562.8	535.7	507.7	478.1	449.3	424.5	400.8	380.0
27.5°	633.6	602.9	572.2	544.0	517.9	492.2	463.8	434.4	406.9	382.9	363.4
30°	628.6	594.7	560.3	530.9	504.2	479.2	452.3	423.6	394.8	371.4	350.4
32.5°	624.1	584.7	548.4	516.3	488.0	463.6	438.9	411.6	383.3	359.5	338.6
35°	615.3	569.8	528.1	492.0	461.8	436.7	415.9	390.5	364.6	341.5	321.5
37.5°	604.2	550.2	505.5	467.6	434.4	408.0	388.8	369.2	344.3	322.1	304.0
40°	595.4	536.2	488.9	450.2	415.8	388.3	370.4	351.9	331.3	310.6	291.4
42.5°	584.5	523.7	472.2	430.5	396.4	369.7	350.9	335.3	317.0	297.7	279.9
45°	564.3	501.0	445.2	400.3	365.9	339.5	320.2	308.4	294.6	276.4	261.4
47.5°	534.6	473.6	415.9	369.7	334.1	309.7	291.5	280.2	270.6	257.0	243.4
50°	508.3	453.3	394.8	348.9	313.4	288.8	272.0	261.7	253.5	243.1	231.5
52.5°	478.9	427.6	374.1	328.7	293.5	269.3	252.9	243.8	237.0	229.5	218.1
55°	432.1	388.5	338.8	295.8	263.3	239.6	225.2	217.4	211.7	206.0	199.1
57.5°	380.6	346.5	302.6	263.1	233.2	211.6	198.2	190.6	186.2	183.2	179.2
60°	344.3	315.2	277.3	241.3	212.2	192.9	179.9	174.0	170.3	168.0	164.9
62.5°	310.7	286.7	251.7	218.9	193.3	175.2	163.5	157.8	154.3	153.1	150.6
65°	261.2	242.6	213.7	186.4	164.7	149.2	139.4	133.9	131.8	130.4	130.6
67.5°	212.3	201.0	177.8	154.6	137.1	124.2	116.3	112.2	111.0	109.3	109.3
70°	182.5	174.0	154.4	134.1	118.7	108.7	101.7	97.4	96.2	95.4	95.2
72.5°	156.2	148.7	131.8	115.6	101.6	92.8	87.1	84.5	82.7	82.2	82.1
75°	117.3	113.3	99.7	86.9	77.3	71.3	67.3	64.9	63.6	63.3	63.6
77.5°	83.4	79.8	71.3	62.1	56.1	51.5	48.2	47.3	45.9	45.9	45.7
80°	62.7	60.3	54.9	47.7	42.7	38.7	37.0	35.5	35.1	34.4	35.1
82.5°	45.4	42.9	39.2	34.6	30.4	28.2	26.4	25.9	25.6	25.4	25.4
85°	22.4	22.6	20.5	17.0	15.3	13.9	12.8	12.8	12.6	12.4	12.6
87.5°	10.6	9.7	8.8	7.8	6.5	5.6	5.0	4.9	4.6	4.9	5.5
90°	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1	2.2	4.3	6.6
92.5°	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4	16.2	25.4	39.0
95°	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1	37.2	46.0	58.1
97.5°	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0	61.4	67.5	79.6
100°	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6	78.9	83.2	95.3
102.5°	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1	96.4	99.9	112.8
105°	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8	123.8	129.2	140.2
107.5°	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7	154.0	159.2	168.2
110°	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9	174.2	178.5	188.4





TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1	194.3	197.7	207.6
115°	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2	223.4	226.7	236.6
117.5°	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5	250.8	254.3	264.2
120°	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0	268.3	272.7	282.6
122.5°	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4	285.9	289.4	299.2
125°	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6	308.9	314.3	324.1
127.5°	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8	328.1	335.2	347.6
130°	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2	339.5	348.3	362.5
132.5°	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0	349.1	359.7	375.7
135°	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2	363.6	376.7	394.3
137.5°	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2	380.5	392.8	410.3
140°	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7	391.0	404.2	421.7
142.5°	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9	402.4	414.6	432.2
145°	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4	420.6	431.5	446.9
147.5°	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6	438.9	448.4	462.6
150°	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0	451.2	458.9	473.2
152.5°	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3	462.6	469.4	481.9
155°	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5	477.5	484.1	495.0
157.5°	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0	491.7	497.0	506.4
160°	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6	500.5	504.9	512.6
162.5°	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4	508.4	512.7	519.5
165°	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3	519.2	522.5	527.9
167.5°	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2	528.1	530.1	533.1
170°	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4	533.4	534.4	536.7
172.5°	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0	536.0	537.1	539.2
175°	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2	539.9	541.0	542.2
177.5°	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1	542.3	542.3	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	504.3	502.3	500.8	497.3	495.3	492.8	490.7	492.9	490.5	491.5	489.9
5°	488.5	482.4	478.1	471.7	466.3	461.3	457.6	456.9	455.2	454.3	451.7
7.5°	469.6	461.9	454.5	446.2	439.2	432.2	427.6	423.9	421.4	418.1	415.8
10°	458.5	448.2	439.5	429.5	420.8	413.1	407.1	404.0	401.1	397.0	395.5
12.5°	444.7	434.1	423.5	412.7	404.4	395.9	390.7	386.1	384.1	379.5	379.0
15°	428.2	412.3	401.8	391.0	379.4	372.4	368.1	363.1	360.9	357.6	355.2
17.5°	408.5	394.3	381.3	369.9	360.1	354.2	348.7	345.3	341.6	339.4	335.5
20°	394.2	380.7	367.6	355.6	348.0	341.3	337.0	333.7	329.7	328.7	324.7
22.5°	382.2	367.3	354.8	344.7	336.4	328.8	324.0	321.8	319.1	315.8	315.0
25°	362.6	347.1	336.5	326.5	319.1	312.1	308.9	306.0	303.4	301.0	300.1
27.5°	345.7	331.9	319.2	310.2	303.7	297.4	294.5	291.1	289.2	287.2	284.8
30°	333.8	319.7	308.6	299.9	292.9	287.3	284.2	281.8	280.1	278.3	277.0
32.5°	321.7	308.6	297.8	289.3	282.3	278.1	275.3	273.6	271.7	269.7	268.0
35°	305.6	291.2	280.7	273.3	267.9	264.6	261.6	260.0	257.9	257.9	256.1
37.5°	287.4	274.9	265.7	259.0	254.1	251.2	247.9	246.9	245.4	244.5	243.9
40°	276.6	265.0	256.4	249.6	244.4	242.0	239.3	237.6	236.8	235.6	235.3
42.5°	265.4	254.4	246.1	239.9	235.3	233.3	230.8	229.6	227.8	226.4	226.1
45°	248.5	237.8	230.2	225.2	221.3	218.9	217.4	214.7	213.9	212.2	211.9
47.5°	232.4	222.2	214.7	210.6	207.2	205.2	202.8	200.2	199.2	198.3	198.2
50°	220.4	211.0	204.1	200.2	196.9	194.1	191.6	189.9	189.3	189.3	189.7
52.5°	208.2	200.2	194.4	189.5	186.4	183.4	181.2	180.1	179.2	180.2	181.0
55°	190.4	182.3	178.0	173.3	170.3	166.8	165.7	165.3	164.7	166.4	167.3
57.5°	171.4	165.8	160.7	156.2	153.4	151.4	150.0	149.7	150.9	151.7	154.6
60°	159.4	152.9	148.4	144.9	141.6	140.3	139.8	139.4	140.3	142.6	146.4
62.5°	146.2	140.9	135.9	133.4	130.9	128.8	128.7	128.9	130.6	133.5	137.1
65°	126.8	122.2	118.9	115.8	113.9	112.6	113.0	113.9	115.8	119.6	123.7
67.5°	107.0	103.9	100.9	98.5	96.6	96.6	97.1	98.4	100.7	104.9	108.7
70°	94.3	90.9	88.4	87.4	85.8	84.9	86.2	88.4	90.4	94.3	97.6
72.5°	81.6	78.6	76.7	76.0	75.3	74.6	75.1	77.5	80.1	84.0	87.8
75°	62.7	61.6	60.3	59.5	58.8	59.3	59.7	61.8	64.0	68.1	72.5
77.5°	45.8	44.7	43.8	43.6	43.3	43.5	44.8	46.4	48.4	51.5	54.8
80°	34.6	34.2	33.7	33.6	33.6	33.7	35.5	36.6	38.5	41.4	44.0
82.5°	25.3	25.0	24.9	24.8	25.0	25.1	26.1	27.5	29.1	31.3	33.6
85°	13.3	12.8	13.5	13.8	13.3	13.9	14.4	15.3	15.9	17.0	18.1
87.5°	6.1	6.9	7.0	7.5	7.7	8.6	8.6	9.5	10.1	10.7	10.9
90°	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7	20.8	21.9	24.1
92.5°	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1	140.8	106.0	89.8
95°	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4	620.9	486.3	394.3
97.5°	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7	1056.0	924.8	796.8
100°	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1	1293.5	1180.6	1066.7
102.5°	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8	1438.9	1384.8	1307.7
105°	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2	1521.3	1569.4	1557.4
107.5°	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6	1447.8	1571.6	1628.8
110°	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5	1364.6	1519.0	1612.1



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7	1282.2	1438.4	1548.1
115°	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5	1164.2	1314.2	1433.6
117.5°	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1	1082.5	1211.7	1321.3
120°	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7	1036.0	1156.5	1252.9
122.5°	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0	1002.8	1110.1	1200.3
125°	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6	958.3	1053.6	1132.5
127.5°	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5	915.8	1004.8	1078.6
130°	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7	886.0	971.5	1042.6
132.5°	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7	858.0	935.5	1004.1
135°	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2	814.8	885.0	947.3
137.5°	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2	776.3	834.5	887.6
140°	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0	753.5	803.9	849.9
142.5°	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6	734.2	777.6	817.5
145°	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7	709.6	743.7	773.2
147.5°	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8	689.3	715.4	737.7
150°	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8	678.0	698.7	718.4
152.5°	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1	666.6	685.6	701.0
155°	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9	649.4	664.8	676.8
157.5°	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8	633.2	645.1	654.5
160°	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0	620.9	631.9	639.6
162.5°	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4	610.5	619.6	626.4
165°	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0	594.7	601.2	606.7
167.5°	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3	579.4	584.4	588.3
170°	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3	570.6	573.9	576.1
172.5°	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4	562.7	565.1	566.5
175°	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9	550.9	553.1	553.1
177.5°	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0	545.8	545.8	545.8
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	488.9	490.1	489.1	490.5	489.1	490.1	488.9	489.9	491.5	490.5	492.9
5°	450.6	448.7	450.0	449.1	450.0	448.7	450.6	451.7	454.3	455.2	456.9
7.5°	415.3	413.4	411.2	410.2	411.2	413.4	415.3	415.8	418.1	421.4	423.9
10°	393.1	390.7	390.5	389.0	390.5	390.7	393.1	395.5	397.0	401.1	404.0
12.5°	376.9	374.7	372.2	371.6	372.2	374.7	376.9	379.0	379.5	384.1	386.1
15°	353.9	352.1	350.6	351.9	350.6	352.1	353.9	355.2	357.6	360.9	363.1
17.5°	334.8	333.4	333.1	331.5	333.1	333.4	334.8	335.5	339.4	341.6	345.3
20°	322.7	321.7	322.2	319.2	322.2	321.7	322.7	324.7	328.7	329.7	333.7
22.5°	313.2	311.0	310.8	310.2	310.8	311.0	313.2	315.0	315.8	319.1	321.8
25°	298.1	297.1	296.0	297.1	296.0	297.1	298.1	300.1	301.0	303.4	306.0
27.5°	285.0	283.7	283.4	283.6	283.4	283.7	285.0	284.8	287.2	289.2	291.1
30°	277.0	274.8	275.0	274.8	275.0	274.8	277.0	277.0	278.3	280.1	281.8
32.5°	268.3	266.8	266.6	266.2	266.6	266.8	268.3	268.0	269.7	271.7	273.6
35°	255.4	255.4	254.4	254.4	254.4	255.4	255.4	256.1	257.9	257.9	260.0
37.5°	243.4	243.2	242.5	242.6	242.5	243.2	243.4	243.9	244.5	245.4	246.9
40°	234.3	234.1	233.5	232.1	233.5	234.1	234.3	235.3	235.6	236.8	237.6
42.5°	225.6	224.9	224.6	224.1	224.6	224.9	225.6	226.1	226.4	227.8	229.6
45°	211.9	211.9	211.5	211.2	211.5	211.9	211.9	211.9	212.2	213.9	214.7
47.5°	198.6	199.0	199.8	199.6	199.8	199.0	198.6	198.2	198.3	199.2	200.2
50°	190.6	190.8	191.4	191.6	191.4	190.8	190.6	189.7	189.3	189.3	189.9
52.5°	181.7	182.9	183.8	183.6	183.8	182.9	181.7	181.0	180.2	179.2	180.1
55°	169.2	170.8	172.3	172.5	172.3	170.8	169.2	167.3	166.4	164.7	165.3
57.5°	156.9	159.0	160.6	161.2	160.6	159.0	156.9	154.6	151.7	150.9	149.7
60°	148.5	151.4	153.4	154.2	153.4	151.4	148.5	146.4	142.6	140.3	139.4
62.5°	140.5	143.7	145.6	145.8	145.6	143.7	140.5	137.1	133.5	130.6	128.9
65°	127.4	130.6	132.4	133.7	132.4	130.6	127.4	123.7	119.6	115.8	113.9
67.5°	113.3	116.6	118.5	119.5	118.5	116.6	113.3	108.7	104.9	100.7	98.4
70°	103.0	106.3	108.9	109.8	108.9	106.3	103.0	97.6	94.3	90.4	88.4
72.5°	92.9	95.9	97.9	99.0	97.9	95.9	92.9	87.8	84.0	80.1	77.5
75°	75.3	79.3	81.2	82.3	81.2	79.3	75.3	72.5	68.1	64.0	61.8
77.5°	58.1	61.6	62.9	63.4	62.9	61.6	58.1	54.8	51.5	48.4	46.4
80°	46.6	48.8	50.3	50.5	50.3	48.8	46.6	44.0	41.4	38.5	36.6
82.5°	35.8	37.6	38.1	38.6	38.1	37.6	35.8	33.6	31.3	29.1	27.5
85°	19.6	20.5	20.7	20.5	20.7	20.5	19.6	18.1	17.0	15.9	15.3
87.5°	11.3	11.1	11.3	11.7	11.3	11.1	11.3	10.9	10.7	10.1	9.5
90°	24.1	24.1	25.2	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7
92.5°	75.8	73.1	71.6	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1
95°	316.5	283.6	274.9	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4
97.5°	729.2	667.9	636.1	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7
100°	991.2	912.3	871.8	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1
102.5°	1226.8	1170.7	1126.7	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8
105°	1522.3	1486.2	1464.2	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2
107.5°	1646.5	1646.3	1639.1	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6
110°	1661.4	1682.2	1689.9	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1620.2	1656.0	1675.0	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7
115°	1519.0	1571.6	1602.2	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5
117.5°	1406.7	1461.0	1491.5	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1
120°	1334.0	1386.5	1416.1	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7
122.5°	1272.6	1320.8	1350.4	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0
125°	1193.7	1238.7	1262.7	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6
127.5°	1134.2	1173.8	1196.7	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5
130°	1097.4	1133.5	1155.5	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7
132.5°	1058.9	1095.0	1115.1	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7
135°	995.5	1031.7	1051.4	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2
137.5°	930.7	963.6	981.8	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2
140°	890.4	918.9	935.3	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0
142.5°	851.9	875.9	891.5	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6
145°	799.5	818.1	830.2	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7
147.5°	758.6	773.5	780.4	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8
150°	734.9	748.0	752.4	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8
152.5°	714.7	725.2	729.6	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1
155°	687.8	695.4	698.7	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9
157.5°	663.0	669.4	672.4	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8
160°	647.2	652.7	655.0	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0
162.5°	632.4	637.0	637.4	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4
165°	611.1	613.3	613.3	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0
167.5°	590.5	592.5	591.6	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3
170°	578.2	579.4	579.4	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3
172.5°	566.8	568.8	567.1	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4
175°	553.1	554.2	552.0	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9
177.5°	545.0	545.8	543.2	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	490.7	492.8	495.3	497.3	500.8	502.3	504.3	505.8	508.6	511.2	514.3
5°	457.6	461.3	466.3	471.7	478.1	482.4	488.5	492.2	499.6	506.3	512.9
7.5°	427.6	432.2	439.2	446.2	454.5	461.9	469.6	478.1	487.5	498.7	507.9
10°	407.1	413.1	420.8	429.5	439.5	448.2	458.5	467.6	479.2	492.2	504.4
12.5°	390.7	395.9	404.4	412.7	423.5	434.1	444.7	456.8	470.2	484.7	500.0
15°	368.1	372.4	379.4	391.0	401.8	412.3	428.2	439.5	456.5	472.6	491.2
17.5°	348.7	354.2	360.1	369.9	381.3	394.3	408.5	422.7	439.0	459.5	480.3
20°	337.0	341.3	348.0	355.6	367.6	380.7	394.2	408.6	428.6	449.8	472.2
22.5°	324.0	328.8	336.4	344.7	354.8	367.3	382.2	397.9	418.9	439.6	464.0
25°	308.9	312.1	319.1	326.5	336.5	347.1	362.6	380.0	400.8	424.5	449.3
27.5°	294.5	297.4	303.7	310.2	319.2	331.9	345.7	363.4	382.9	406.9	434.4
30°	284.2	287.3	292.9	299.9	308.6	319.7	333.8	350.4	371.4	394.8	423.6
32.5°	275.3	278.1	282.3	289.3	297.8	308.6	321.7	338.6	359.5	383.3	411.6
35°	261.6	264.6	267.9	273.3	280.7	291.2	305.6	321.5	341.5	364.6	390.5
37.5°	247.9	251.2	254.1	259.0	265.7	274.9	287.4	304.0	322.1	344.3	369.2
40°	239.3	242.0	244.4	249.6	256.4	265.0	276.6	291.4	310.6	331.3	351.9
42.5°	230.8	233.3	235.3	239.9	246.1	254.4	265.4	279.9	297.7	317.0	335.3
45°	217.4	218.9	221.3	225.2	230.2	237.8	248.5	261.4	276.4	294.6	308.4
47.5°	202.8	205.2	207.2	210.6	214.7	222.2	232.4	243.4	257.0	270.6	280.2
50°	191.6	194.1	196.9	200.2	204.1	211.0	220.4	231.5	243.1	253.5	261.7
52.5°	181.2	183.4	186.4	189.5	194.4	200.2	208.2	218.1	229.5	237.0	243.8
55°	165.7	166.8	170.3	173.3	178.0	182.3	190.4	199.1	206.0	211.7	217.4
57.5°	150.0	151.4	153.4	156.2	160.7	165.8	171.4	179.2	183.2	186.2	190.6
60°	139.8	140.3	141.6	144.9	148.4	152.9	159.4	164.9	168.0	170.3	174.0
62.5°	128.7	128.8	130.9	133.4	135.9	140.9	146.2	150.6	153.1	154.3	157.8
65°	113.0	112.6	113.9	115.8	118.9	122.2	126.8	130.6	130.4	131.8	133.9
67.5°	97.1	96.6	96.6	98.5	100.9	103.9	107.0	109.3	109.3	111.0	112.2
70°	86.2	84.9	85.8	87.4	88.4	90.9	94.3	95.2	95.4	96.2	97.4
72.5°	75.1	74.6	75.3	76.0	76.7	78.6	81.6	82.1	82.2	82.7	84.5
75°	59.7	59.3	58.8	59.5	60.3	61.6	62.7	63.6	63.3	63.6	64.9
77.5°	44.8	43.5	43.3	43.6	43.8	44.7	45.8	45.7	45.9	45.9	47.3
80°	35.5	33.7	33.6	33.6	33.7	34.2	34.6	35.1	34.4	35.1	35.5
82.5°	26.1	25.1	25.0	24.8	24.9	25.0	25.3	25.4	25.4	25.6	25.9
85°	14.4	13.9	13.3	13.8	13.5	12.8	13.3	12.6	12.4	12.6	12.8
87.5°	8.6	8.6	7.7	7.5	7.0	6.9	6.1	5.5	4.9	4.6	4.9
90°	18.7	17.5	15.4	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1
92.5°	285.9	353.1	358.8	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4
95°	949.5	970.3	791.8	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1
97.5°	1201.5	1036.2	707.1	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0
100°	1262.7	988.9	630.8	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6
102.5°	1226.0	905.7	573.0	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1
105°	1108.3	794.0	516.9	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8
107.5°	988.4	717.1	493.2	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7
110°	919.9	681.2	486.3	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	869.1	660.2	486.3	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1
115°	813.7	637.4	489.6	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2
117.5°	780.6	626.2	496.8	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5
120°	762.2	620.9	503.8	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0
122.5°	746.5	616.6	509.9	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4
125°	725.0	611.1	520.2	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6
127.5°	705.3	608.5	531.8	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8
130°	692.2	606.7	538.9	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2
132.5°	681.6	606.7	546.7	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0
135°	669.2	606.7	557.4	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2
137.5°	658.0	608.0	567.3	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2
140°	652.7	608.9	571.7	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7
142.5°	648.4	609.8	574.3	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9
145°	641.8	608.9	577.2	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4
147.5°	635.0	606.1	578.2	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6
150°	629.7	603.4	578.2	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0
152.5°	623.6	599.9	577.4	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3
155°	613.3	593.6	575.0	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5
157.5°	603.7	587.0	572.1	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0
160°	595.8	582.7	569.5	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6
162.5°	588.8	577.4	566.8	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4
165°	578.2	569.5	562.9	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3
167.5°	568.0	561.8	556.8	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2
170°	561.8	557.4	554.2	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4
172.5°	555.7	552.2	550.6	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0
175°	547.6	546.5	546.5	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2
177.5°	544.1	543.2	543.2	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	515.9	518.3	519.9	522.8	525.3	526.7	527.9	529.0	530.2	531.2	534.2
5°	519.2	524.9	529.7	537.1	543.8	549.0	554.7	559.7	563.8	569.8	574.3
7.5°	517.7	527.8	538.4	549.9	561.6	572.4	582.5	591.8	600.3	610.6	619.6
10°	516.4	530.1	543.6	559.1	575.0	588.4	601.1	614.0	623.3	636.4	647.5
12.5°	515.4	531.5	547.8	566.4	583.8	602.9	619.7	629.1	643.4	653.8	667.0
15°	511.0	532.3	554.7	575.6	600.5	618.1	632.9	651.2	664.5	677.8	692.1
17.5°	503.0	527.3	552.3	579.8	603.5	622.5	641.6	659.2	675.0	692.9	710.8
20°	499.4	523.6	552.3	580.4	603.7	623.5	643.1	662.5	680.0	702.9	723.5
22.5°	491.7	520.9	547.4	574.9	598.8	620.4	642.6	664.6	687.8	713.6	739.5
25°	478.1	507.7	535.7	562.8	586.9	614.0	637.7	667.1	696.7	730.9	763.2
27.5°	463.8	492.2	517.9	544.0	572.2	602.9	633.6	666.9	705.8	748.9	794.4
30°	452.3	479.2	504.2	530.9	560.3	594.7	628.6	668.2	713.0	761.6	815.7
32.5°	438.9	463.6	488.0	516.3	548.4	584.7	624.1	667.5	721.4	776.6	832.2
35°	415.9	436.7	461.8	492.0	528.1	569.8	615.3	666.7	728.5	791.9	838.7
37.5°	388.8	408.0	434.4	467.6	505.5	550.2	604.2	665.2	730.8	781.4	796.4
40°	370.4	388.3	415.8	450.2	488.9	536.2	595.4	659.9	723.5	755.7	743.3
42.5°	350.9	369.7	396.4	430.5	472.2	523.7	584.5	648.9	702.3	714.4	671.6
45°	320.2	339.5	365.9	400.3	445.2	501.0	564.3	622.9	653.6	631.6	565.1
47.5°	291.5	309.7	334.1	369.7	415.9	473.6	534.6	581.4	583.8	531.3	460.3
50°	272.0	288.8	313.4	348.9	394.8	453.3	508.3	545.2	528.6	469.1	401.0
52.5°	252.9	269.3	293.5	328.7	374.1	427.6	478.9	504.7	473.5	412.5	354.3
55°	225.2	239.6	263.3	295.8	338.8	388.5	432.1	441.0	400.5	340.4	293.1
57.5°	198.2	211.6	233.2	263.1	302.6	346.5	380.6	378.6	335.8	284.3	246.8
60°	179.9	192.9	212.2	241.3	277.3	315.2	344.3	337.3	294.9	250.4	218.9
62.5°	163.5	175.2	193.3	218.9	251.7	286.7	310.7	300.4	258.8	220.0	195.0
65°	139.4	149.2	164.7	186.4	213.7	242.6	261.2	247.9	212.4	182.1	162.0
67.5°	116.3	124.2	137.1	154.6	177.8	201.0	212.3	199.0	170.5	148.5	133.6
70°	101.7	108.7	118.7	134.1	154.4	174.0	182.5	170.5	146.1	127.1	116.5
72.5°	87.1	92.8	101.6	115.6	131.8	148.7	156.2	144.8	124.7	108.7	98.8
75°	67.3	71.3	77.3	86.9	99.7	113.3	117.3	107.4	94.5	82.6	76.0
77.5°	48.2	51.5	56.1	62.1	71.3	79.8	83.4	77.7	67.8	60.1	54.8
80°	37.0	38.7	42.7	47.7	54.9	60.3	62.7	59.0	52.0	46.4	42.2
82.5°	26.4	28.2	30.4	34.6	39.2	42.9	45.4	43.0	38.0	33.5	31.1
85°	12.8	13.9	15.3	17.0	20.5	22.6	22.4	20.9	18.9	17.2	15.9
87.5°	5.0	5.6	6.5	7.8	8.8	9.7	10.6	10.4	10.1	9.8	9.5
90°	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7
92.5°	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1
95°	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4
97.5°	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7
100°	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1
102.5°	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8
105°	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2
107.5°	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6
110°	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5





TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7
115°	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5
117.5°	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1
120°	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7
122.5°	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0
125°	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6
127.5°	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5
130°	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7
132.5°	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7
135°	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2
137.5°	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2
140°	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0
142.5°	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6
145°	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7
147.5°	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8
150°	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8
152.5°	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1
155°	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9
157.5°	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8
160°	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0
162.5°	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4
165°	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0
167.5°	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3
170°	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3
172.5°	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4
175°	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9
177.5°	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	536.7	538.0	541.0	540.0	541.3	542.1	542.7
5°	579.9	586.9	590.0	589.6	594.2	593.0	591.9
7.5°	629.0	636.2	640.4	645.5	648.4	648.7	651.2
10°	656.7	666.2	670.1	675.6	679.1	681.1	680.8
12.5°	677.9	685.4	694.2	696.8	701.5	704.1	703.1
15°	703.5	715.5	724.6	729.2	735.1	736.8	739.1
17.5°	726.3	742.3	753.0	767.2	772.6	775.9	773.9
20°	743.6	764.7	775.3	792.3	801.7	806.7	804.9
22.5°	763.9	786.8	806.5	821.2	835.5	842.3	843.7
25°	798.9	830.2	859.2	878.5	896.2	900.3	909.5
27.5°	837.9	874.9	905.9	926.2	938.5	943.1	946.0
30°	862.4	899.3	922.6	935.7	939.5	939.1	938.7
32.5°	874.5	897.5	902.0	898.3	889.4	881.7	873.8
35°	857.4	840.3	814.5	781.5	757.1	732.4	730.0
37.5°	771.2	716.1	673.4	625.6	598.0	581.0	569.2
40°	689.9	627.5	575.6	535.4	507.3	496.2	485.2
42.5°	601.8	542.1	496.2	462.5	441.4	429.0	420.5
45°	488.9	436.2	400.3	375.9	359.1	349.6	344.1
47.5°	400.7	361.7	331.1	313.5	302.0	294.5	294.5
50°	353.3	316.0	295.8	281.8	271.8	265.9	267.0
52.5°	311.2	283.4	266.2	254.5	247.0	243.5	243.3
55°	260.2	240.3	228.9	220.4	215.4	211.2	212.2
57.5°	222.6	205.8	198.1	191.1	187.6	186.0	183.5
60°	199.3	186.2	179.6	174.0	170.5	169.2	166.8
62.5°	178.5	168.2	161.9	157.3	154.2	153.7	151.8
65°	150.1	142.2	136.6	134.4	131.1	130.3	130.3
67.5°	123.7	118.1	113.7	111.7	110.3	110.5	109.4
70°	107.2	102.5	99.7	97.6	96.5	96.7	95.9
72.5°	93.8	88.6	86.1	84.8	83.4	84.0	83.6
75°	71.0	68.4	67.1	65.8	64.9	64.5	64.0
77.5°	52.1	49.9	48.8	48.1	48.3	47.1	48.0
80°	40.2	38.4	37.7	36.6	36.4	36.4	36.2
82.5°	29.5	28.4	27.9	27.1	26.6	27.0	26.4
85°	15.3	14.4	14.1	14.1	13.8	13.3	14.4
87.5°	9.7	9.2	9.7	9.5	9.5	9.6	9.2
90°	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333153-830

CATALOG NUMBER: S125DIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)