

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333117-830

Luminaire Tested: **S125DIP-S375D365U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333117-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D365U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2687.9 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3314	3314	3314	3314
5°	3837	3325	2912	3325
10°	4465	3308	2551	3308
15°	4942	3284	2353	3284
20°	5532	3245	2194	3245
25°	6481	3202	2117	3202
30°	7000	3159	2049	3159
35°	5755	3079	2006	3079
40°	4091	2967	1957	2967
45°	3143	2817	1929	2817
50°	2683	2629	1925	2629
55°	2389	2448	1942	2448
60°	2155	2248	1992	2248
65°	1991	2046	2043	2046
70°	1811	1839	2073	1839
75°	1597	1619	2054	1619
80°	1346	1320	1878	1320
85°	1067	948	1519	948



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.8
10°-20°	147.1	5.5
20°-30°	238.8	8.9
30°-40°	291.3	10.8
40°-50°	265.0	9.9
50°-60°	211.1	7.9
60°-70°	147.0	5.5
70°-80°	78.4	2.9
80°-90°	20.7	0.8
90°-100°	119.8	4.5
100°-110°	257.4	9.6
110°-120°	241.6	9.0
120°-130°	195.8	7.3
130°-140°	157.1	5.8
140°-150°	118.6	4.4
150°-160°	83.5	3.1
160°-170°	49.2	1.8
170°-180°	16.0	0.6
0°-30°	435.3	16.2
0°-40°	726.6	27.0
0°-60°	1202.7	44.7
0°-90°	1448.8	53.9
90°-120°	618.8	23.0
90°-150°	1090.3	40.6
90°-180°	1239.0	46.1
0°-180°	2687.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	592	513	449	513	592	60
15°	739	491	352	491	739	212
25°	910	449	297	449	910	415
35°	730	390	254	390	730	447
45°	344	308	211	308	344	275
55°	212	217	172	217	212	191
65°	130	134	134	134	130	129
75°	64	65	82	65	64	69
85°	14	13	20	13	14	17
90°	8	0	8	0	8	6
95°	78	11	78	11	78	111
105°	441	38	441	38	441	439
115°	492	67	492	67	492	480
125°	387	93	387	93	387	350
135°	322	109	322	109	322	249
145°	254	127	254	127	254	161
155°	213	145	213	145	213	99
165°	186	158	186	158	186	53
175°	168	165	168	165	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	542.7	542.1	541.3	540.0	541.0	538.0	536.7	534.2	531.2	530.2	529.0
5°	591.9	593.0	594.2	589.6	590.0	586.9	579.9	574.3	569.8	563.8	559.7
7.5°	651.2	648.7	648.4	645.5	640.4	636.2	629.0	619.6	610.6	600.3	591.8
10°	680.8	681.1	679.1	675.6	670.1	666.2	656.7	647.5	636.4	623.3	614.0
12.5°	703.1	704.1	701.5	696.8	694.2	685.4	677.9	667.0	653.8	643.4	629.1
15°	739.1	736.8	735.1	729.2	724.6	715.5	703.5	692.1	677.8	664.5	651.2
17.5°	773.9	775.9	772.6	767.2	753.0	742.3	726.3	710.8	692.9	675.0	659.2
20°	804.9	806.7	801.7	792.3	775.3	764.7	743.6	723.5	702.9	680.0	662.5
22.5°	843.7	842.3	835.5	821.2	806.5	786.8	763.9	739.5	713.6	687.8	664.6
25°	909.5	900.3	896.2	878.5	859.2	830.2	798.9	763.2	730.9	696.7	667.1
27.5°	946.0	943.1	938.5	926.2	905.9	874.9	837.9	794.4	748.9	705.8	666.9
30°	938.7	939.1	939.5	935.7	922.6	899.3	862.4	815.7	761.6	713.0	668.2
32.5°	873.8	881.7	889.4	898.3	902.0	897.5	874.5	832.2	776.6	721.4	667.5
35°	730.0	732.4	757.1	781.5	814.5	840.3	857.4	838.7	791.9	728.5	666.7
37.5°	569.2	581.0	598.0	625.6	673.4	716.1	771.2	796.4	781.4	730.8	665.2
40°	485.2	496.2	507.3	535.4	575.6	627.5	689.9	743.3	755.7	723.5	659.9
42.5°	420.5	429.0	441.4	462.5	496.2	542.1	601.8	671.6	714.4	702.3	648.9
45°	344.1	349.6	359.1	375.9	400.3	436.2	488.9	565.1	631.6	653.6	622.9
47.5°	294.5	294.5	302.0	313.5	331.1	361.7	400.7	460.3	531.3	583.8	581.4
50°	267.0	265.9	271.8	281.8	295.8	316.0	353.3	401.0	469.1	528.6	545.2
52.5°	243.3	243.5	247.0	254.5	266.2	283.4	311.2	354.3	412.5	473.5	504.7
55°	212.2	211.2	215.4	220.4	228.9	240.3	260.2	293.1	340.4	400.5	441.0
57.5°	183.5	186.0	187.6	191.1	198.1	205.8	222.6	246.8	284.3	335.8	378.6
60°	166.8	169.2	170.5	174.0	179.6	186.2	199.3	218.9	250.4	294.9	337.3
62.5°	151.8	153.7	154.2	157.3	161.9	168.2	178.5	195.0	220.0	258.8	300.4
65°	130.3	130.3	131.1	134.4	136.6	142.2	150.1	162.0	182.1	212.4	247.9
67.5°	109.4	110.5	110.3	111.7	113.7	118.1	123.7	133.6	148.5	170.5	199.0
70°	95.9	96.7	96.5	97.6	99.7	102.5	107.2	116.5	127.1	146.1	170.5
72.5°	83.6	84.0	83.4	84.8	86.1	88.6	93.8	98.8	108.7	124.7	144.8
75°	64.0	64.5	64.9	65.8	67.1	68.4	71.0	76.0	82.6	94.5	107.4
77.5°	48.0	47.1	48.3	48.1	48.8	49.9	52.1	54.8	60.1	67.8	77.7
80°	36.2	36.4	36.4	36.6	37.7	38.4	40.2	42.2	46.4	52.0	59.0
82.5°	26.4	27.0	26.6	27.1	27.9	28.4	29.5	31.1	33.5	38.0	43.0
85°	14.4	13.3	13.8	14.1	14.1	14.4	15.3	15.9	17.2	18.9	20.9
87.5°	5.7	6.0	6.1	6.1	6.3	6.2	6.9	6.8	7.3	7.7	8.3
90°	7.6	7.6	7.4	7.4	7.4	6.7	6.3	6.0	5.7	5.4	4.6
92.5°	21.2	21.8	22.2	23.1	27.3	32.2	42.8	59.0	86.9	107.4	109.1
95°	78.3	83.6	86.2	96.2	119.9	147.9	188.9	239.5	288.8	295.1	240.8
97.5°	189.2	193.5	203.1	221.8	242.3	281.3	321.2	356.7	365.4	315.2	215.1
100°	259.9	265.1	277.5	301.4	324.4	359.1	393.4	409.7	384.1	300.8	191.9
102.5°	338.7	342.7	356.1	373.2	397.8	421.2	437.6	427.5	372.9	275.5	174.3
105°	441.4	445.4	452.0	463.0	473.7	477.3	462.7	417.1	337.1	241.5	157.2
107.5°	495.9	498.5	500.8	500.8	495.4	478.0	440.4	379.5	300.6	218.1	150.1
110°	514.0	514.0	511.6	505.3	490.3	462.0	415.1	351.8	279.8	207.2	147.9



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	511.9	509.4	503.7	492.8	470.9	437.5	390.0	329.9	264.4	200.8	147.9
115°	491.6	487.3	478.0	462.0	436.0	399.7	354.1	302.5	247.5	193.9	148.9
117.5°	456.3	453.6	444.4	427.8	401.9	368.5	329.2	284.7	237.4	190.5	151.1
120°	433.4	430.7	421.7	405.8	381.1	351.8	315.1	275.1	231.9	188.9	153.3
122.5°	413.1	410.8	401.7	387.1	365.0	337.6	305.0	268.0	227.1	187.6	155.0
125°	387.4	384.1	376.7	363.1	344.4	320.5	291.4	257.5	220.6	185.9	158.3
127.5°	365.4	363.9	357.0	345.0	328.0	305.6	278.5	246.9	214.5	185.1	161.7
130°	353.5	351.5	344.8	333.8	317.2	295.5	269.5	240.2	210.6	184.5	163.9
132.5°	341.4	339.1	333.0	322.1	305.4	284.6	261.0	233.5	207.4	184.5	166.3
135°	321.8	319.8	313.8	302.8	288.1	269.2	247.8	224.9	203.5	184.5	169.6
137.5°	300.8	298.6	293.0	283.0	269.9	253.8	236.1	217.5	200.1	184.9	172.6
140°	286.2	284.5	279.5	270.8	258.4	244.5	229.1	213.5	198.5	185.2	173.9
142.5°	272.6	271.2	266.5	259.1	248.6	236.5	223.3	210.1	197.2	185.5	174.7
145°	253.8	252.5	248.8	243.2	235.2	226.2	215.8	205.6	195.2	185.2	175.5
147.5°	238.0	237.3	235.3	230.7	224.4	217.6	209.6	201.2	193.1	184.4	175.9
150°	229.1	228.8	227.5	223.5	218.5	212.5	206.2	198.9	191.5	183.5	175.9
152.5°	222.3	221.9	220.6	217.4	213.2	208.5	202.7	196.2	189.6	182.5	175.6
155°	212.8	212.5	211.5	209.2	205.9	202.2	197.6	192.2	186.5	180.6	174.8
157.5°	204.4	204.5	203.6	201.7	199.1	196.2	192.6	188.2	183.6	178.5	174.0
160°	198.9	199.2	198.5	196.9	194.5	192.2	188.9	185.6	181.3	177.2	173.2
162.5°	193.8	193.9	193.7	192.4	190.6	188.5	185.7	182.6	179.1	175.6	172.4
165°	186.5	186.5	186.5	185.9	184.5	182.9	180.9	178.5	175.9	173.2	171.3
167.5°	179.8	179.9	180.2	179.6	179.0	177.8	176.3	174.7	172.8	170.9	169.4
170°	175.9	176.3	176.3	175.9	175.2	174.6	173.5	172.6	170.9	169.6	168.5
172.5°	172.1	172.5	173.1	172.4	172.3	171.9	171.2	170.1	169.0	168.0	167.5
175°	167.6	167.9	168.5	168.2	168.2	168.2	167.6	167.6	166.5	166.3	166.3
177.5°	165.2	165.2	166.0	165.8	166.0	166.0	166.0	165.8	165.5	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	527.9	526.7	525.3	522.8	519.9	518.3	515.9	514.3	511.2	508.6	505.8
5°	554.7	549.0	543.8	537.1	529.7	524.9	519.2	512.9	506.3	499.6	492.2
7.5°	582.5	572.4	561.6	549.9	538.4	527.8	517.7	507.9	498.7	487.5	478.1
10°	601.1	588.4	575.0	559.1	543.6	530.1	516.4	504.4	492.2	479.2	467.6
12.5°	619.7	602.9	583.8	566.4	547.8	531.5	515.4	500.0	484.7	470.2	456.8
15°	632.9	618.1	600.5	575.6	554.7	532.3	511.0	491.2	472.6	456.5	439.5
17.5°	641.6	622.5	603.5	579.8	552.3	527.3	503.0	480.3	459.5	439.0	422.7
20°	643.1	623.5	603.7	580.4	552.3	523.6	499.4	472.2	449.8	428.6	408.6
22.5°	642.6	620.4	598.8	574.9	547.4	520.9	491.7	464.0	439.6	418.9	397.9
25°	637.7	614.0	586.9	562.8	535.7	507.7	478.1	449.3	424.5	400.8	380.0
27.5°	633.6	602.9	572.2	544.0	517.9	492.2	463.8	434.4	406.9	382.9	363.4
30°	628.6	594.7	560.3	530.9	504.2	479.2	452.3	423.6	394.8	371.4	350.4
32.5°	624.1	584.7	548.4	516.3	488.0	463.6	438.9	411.6	383.3	359.5	338.6
35°	615.3	569.8	528.1	492.0	461.8	436.7	415.9	390.5	364.6	341.5	321.5
37.5°	604.2	550.2	505.5	467.6	434.4	408.0	388.8	369.2	344.3	322.1	304.0
40°	595.4	536.2	488.9	450.2	415.8	388.3	370.4	351.9	331.3	310.6	291.4
42.5°	584.5	523.7	472.2	430.5	396.4	369.7	350.9	335.3	317.0	297.7	279.9
45°	564.3	501.0	445.2	400.3	365.9	339.5	320.2	308.4	294.6	276.4	261.4
47.5°	534.6	473.6	415.9	369.7	334.1	309.7	291.5	280.2	270.6	257.0	243.4
50°	508.3	453.3	394.8	348.9	313.4	288.8	272.0	261.7	253.5	243.1	231.5
52.5°	478.9	427.6	374.1	328.7	293.5	269.3	252.9	243.8	237.0	229.5	218.1
55°	432.1	388.5	338.8	295.8	263.3	239.6	225.2	217.4	211.7	206.0	199.1
57.5°	380.6	346.5	302.6	263.1	233.2	211.6	198.2	190.6	186.2	183.2	179.2
60°	344.3	315.2	277.3	241.3	212.2	192.9	179.9	174.0	170.3	168.0	164.9
62.5°	310.7	286.7	251.7	218.9	193.3	175.2	163.5	157.8	154.3	153.1	150.6
65°	261.2	242.6	213.7	186.4	164.7	149.2	139.4	133.9	131.8	130.4	130.6
67.5°	212.3	201.0	177.8	154.6	137.1	124.2	116.3	112.2	111.0	109.3	109.3
70°	182.5	174.0	154.4	134.1	118.7	108.7	101.7	97.4	96.2	95.4	95.2
72.5°	156.2	148.7	131.8	115.6	101.6	92.8	87.1	84.5	82.7	82.2	82.1
75°	117.3	113.3	99.7	86.9	77.3	71.3	67.3	64.9	63.6	63.3	63.6
77.5°	83.4	79.8	71.3	62.1	56.1	51.5	48.2	47.3	45.9	45.9	45.7
80°	62.7	60.3	54.9	47.7	42.7	38.7	37.0	35.5	35.1	34.4	35.1
82.5°	45.4	42.9	39.2	34.6	30.4	28.2	26.4	25.9	25.6	25.4	25.4
85°	22.4	22.6	20.5	17.0	15.3	13.9	12.8	12.8	12.6	12.4	12.6
87.5°	8.6	8.0	7.3	6.6	5.7	5.0	4.6	4.8	4.3	4.2	4.6
90°	4.3	3.7	3.3	2.6	2.0	1.3	0.7	0.4	0.7	1.3	2.0
92.5°	76.0	45.5	27.3	17.6	11.9	7.7	4.9	4.1	4.9	7.7	11.9
95°	148.9	75.6	40.0	25.0	17.6	13.9	11.3	11.0	11.3	13.9	17.6
97.5°	118.9	65.1	41.6	30.8	24.2	20.5	18.7	18.3	18.7	20.5	24.2
100°	107.9	64.7	45.3	35.3	28.9	25.4	23.9	23.3	23.9	25.4	28.9
102.5°	103.4	67.0	49.9	40.2	34.3	30.3	29.3	28.9	29.3	30.3	34.3
105°	101.6	71.9	57.3	48.0	42.6	39.3	37.6	37.6	37.6	39.3	42.6
107.5°	104.6	79.3	65.1	56.7	51.2	48.4	46.8	46.2	46.8	48.4	51.2
110°	107.6	84.6	71.0	62.3	57.3	54.3	53.0	52.3	53.0	54.3	57.3



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.3	89.6	76.5	68.1	63.2	60.1	59.1	58.4	59.1	60.1	63.2
115°	116.9	97.6	85.3	76.9	71.9	69.0	68.0	67.3	68.0	69.0	71.9
117.5°	123.3	105.8	94.1	86.1	80.3	77.4	76.3	75.3	76.3	77.4	80.3
120°	127.6	111.6	99.9	91.6	86.0	82.9	81.6	80.6	81.6	82.9	86.0
122.5°	132.3	117.2	105.6	97.2	91.0	88.0	86.9	86.2	86.9	88.0	91.0
125°	138.9	124.6	113.6	104.9	98.6	95.6	94.0	93.3	94.0	95.6	98.6
127.5°	144.9	131.7	121.1	112.4	105.8	101.9	99.8	98.8	99.8	101.9	105.8
130°	148.9	136.2	125.9	117.3	110.3	105.9	103.3	102.3	103.3	105.9	110.3
132.5°	152.4	140.5	130.2	121.5	114.2	109.4	106.2	104.9	106.2	109.4	114.2
135°	157.2	146.2	135.9	127.0	119.9	114.6	110.6	109.2	110.6	114.6	119.9
137.5°	160.8	150.3	140.9	131.7	124.8	119.4	115.7	114.7	115.7	119.4	124.8
140°	163.2	153.3	143.5	134.6	128.3	122.9	118.9	117.9	118.9	122.9	128.3
142.5°	164.6	155.0	146.0	137.5	131.5	126.1	122.3	121.7	122.3	126.1	131.5
145°	166.5	158.3	149.6	141.9	135.9	131.2	127.9	127.2	127.9	131.2	135.9
147.5°	167.8	160.2	152.6	145.9	140.7	136.4	133.5	133.1	133.5	136.4	140.7
150°	168.5	161.6	154.2	148.5	143.9	139.6	137.2	136.6	137.2	139.6	143.9
152.5°	169.1	162.9	156.1	151.0	146.6	142.8	140.7	140.3	140.7	142.8	146.6
155°	169.6	164.2	158.5	153.9	150.5	147.2	145.2	145.2	145.2	147.2	150.5
157.5°	169.8	165.3	160.5	156.9	154.0	151.2	149.6	149.7	149.6	151.2	154.0
160°	169.8	165.9	161.6	158.5	155.9	153.5	152.2	152.6	152.2	153.5	155.9
162.5°	169.7	166.5	162.6	160.1	158.1	156.0	154.7	155.0	154.7	156.0	158.1
165°	169.2	166.5	163.9	161.9	160.5	158.9	157.9	158.5	157.9	158.9	160.5
167.5°	168.4	166.5	164.4	163.1	162.1	161.3	160.6	161.0	160.6	161.3	162.1
170°	167.9	166.5	164.9	163.9	163.2	162.6	162.2	162.6	162.2	162.6	163.2
172.5°	167.4	166.3	164.9	164.4	164.0	163.3	163.1	163.6	163.1	163.3	164.0
175°	166.5	165.9	164.9	164.9	164.9	164.6	164.2	164.9	164.2	164.6	164.9
177.5°	165.8	165.5	164.9	164.9	165.2	164.9	164.9	165.5	164.9	164.9	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	504.3	502.3	500.8	497.3	495.3	492.8	490.7	492.9	490.5	491.5	489.9
5°	488.5	482.4	478.1	471.7	466.3	461.3	457.6	456.9	455.2	454.3	451.7
7.5°	469.6	461.9	454.5	446.2	439.2	432.2	427.6	423.9	421.4	418.1	415.8
10°	458.5	448.2	439.5	429.5	420.8	413.1	407.1	404.0	401.1	397.0	395.5
12.5°	444.7	434.1	423.5	412.7	404.4	395.9	390.7	386.1	384.1	379.5	379.0
15°	428.2	412.3	401.8	391.0	379.4	372.4	368.1	363.1	360.9	357.6	355.2
17.5°	408.5	394.3	381.3	369.9	360.1	354.2	348.7	345.3	341.6	339.4	335.5
20°	394.2	380.7	367.6	355.6	348.0	341.3	337.0	333.7	329.7	328.7	324.7
22.5°	382.2	367.3	354.8	344.7	336.4	328.8	324.0	321.8	319.1	315.8	315.0
25°	362.6	347.1	336.5	326.5	319.1	312.1	308.9	306.0	303.4	301.0	300.1
27.5°	345.7	331.9	319.2	310.2	303.7	297.4	294.5	291.1	289.2	287.2	284.8
30°	333.8	319.7	308.6	299.9	292.9	287.3	284.2	281.8	280.1	278.3	277.0
32.5°	321.7	308.6	297.8	289.3	282.3	278.1	275.3	273.6	271.7	269.7	268.0
35°	305.6	291.2	280.7	273.3	267.9	264.6	261.6	260.0	257.9	257.9	256.1
37.5°	287.4	274.9	265.7	259.0	254.1	251.2	247.9	246.9	245.4	244.5	243.9
40°	276.6	265.0	256.4	249.6	244.4	242.0	239.3	237.6	236.8	235.6	235.3
42.5°	265.4	254.4	246.1	239.9	235.3	233.3	230.8	229.6	227.8	226.4	226.1
45°	248.5	237.8	230.2	225.2	221.3	218.9	217.4	214.7	213.9	212.2	211.9
47.5°	232.4	222.2	214.7	210.6	207.2	205.2	202.8	200.2	199.2	198.3	198.2
50°	220.4	211.0	204.1	200.2	196.9	194.1	191.6	189.9	189.3	189.3	189.7
52.5°	208.2	200.2	194.4	189.5	186.4	183.4	181.2	180.1	179.2	180.2	181.0
55°	190.4	182.3	178.0	173.3	170.3	166.8	165.7	165.3	164.7	166.4	167.3
57.5°	171.4	165.8	160.7	156.2	153.4	151.4	150.0	149.7	150.9	151.7	154.6
60°	159.4	152.9	148.4	144.9	141.6	140.3	139.8	139.4	140.3	142.6	146.4
62.5°	146.2	140.9	135.9	133.4	130.9	128.8	128.7	128.9	130.6	133.5	137.1
65°	126.8	122.2	118.9	115.8	113.9	112.6	113.0	113.9	115.8	119.6	123.7
67.5°	107.0	103.9	100.9	98.5	96.6	96.6	97.1	98.4	100.7	104.9	108.7
70°	94.3	90.9	88.4	87.4	85.8	84.9	86.2	88.4	90.4	94.3	97.6
72.5°	81.6	78.6	76.7	76.0	75.3	74.6	75.1	77.5	80.1	84.0	87.8
75°	62.7	61.6	60.3	59.5	58.8	59.3	59.7	61.8	64.0	68.1	72.5
77.5°	45.8	44.7	43.8	43.6	43.3	43.5	44.8	46.4	48.4	51.5	54.8
80°	34.6	34.2	33.7	33.6	33.6	33.7	35.5	36.6	38.5	41.4	44.0
82.5°	25.3	25.0	24.9	24.8	25.0	25.1	26.1	27.5	29.1	31.3	33.6
85°	13.3	12.8	13.5	13.8	13.3	13.9	14.4	15.3	15.9	17.0	18.1
87.5°	4.9	5.4	5.3	5.6	5.7	6.1	6.0	6.8	7.2	7.6	7.5
90°	2.6	3.3	3.7	4.3	4.6	5.4	5.7	6.0	6.3	6.7	7.4
92.5°	17.6	27.3	45.5	76.0	109.1	107.4	86.9	59.0	42.8	32.2	27.3
95°	25.0	40.0	75.6	148.9	240.8	295.1	288.8	239.5	188.9	147.9	119.9
97.5°	30.8	41.6	65.1	118.9	215.1	315.2	365.4	356.7	321.2	281.3	242.3
100°	35.3	45.3	64.7	107.9	191.9	300.8	384.1	409.7	393.4	359.1	324.4
102.5°	40.2	49.9	67.0	103.4	174.3	275.5	372.9	427.5	437.6	421.2	397.8
105°	48.0	57.3	71.9	101.6	157.2	241.5	337.1	417.1	462.7	477.3	473.7
107.5°	56.7	65.1	79.3	104.6	150.1	218.1	300.6	379.5	440.4	478.0	495.4
110°	62.3	71.0	84.6	107.6	147.9	207.2	279.8	351.8	415.1	462.0	490.3



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	68.1	76.5	89.6	111.3	147.9	200.8	264.4	329.9	390.0	437.5	470.9
115°	76.9	85.3	97.6	116.9	148.9	193.9	247.5	302.5	354.1	399.7	436.0
117.5°	86.1	94.1	105.8	123.3	151.1	190.5	237.4	284.7	329.2	368.5	401.9
120°	91.6	99.9	111.6	127.6	153.3	188.9	231.9	275.1	315.1	351.8	381.1
122.5°	97.2	105.6	117.2	132.3	155.0	187.6	227.1	268.0	305.0	337.6	365.0
125°	104.9	113.6	124.6	138.9	158.3	185.9	220.6	257.5	291.4	320.5	344.4
127.5°	112.4	121.1	131.7	144.9	161.7	185.1	214.5	246.9	278.5	305.6	328.0
130°	117.3	125.9	136.2	148.9	163.9	184.5	210.6	240.2	269.5	295.5	317.2
132.5°	121.5	130.2	140.5	152.4	166.3	184.5	207.4	233.5	261.0	284.6	305.4
135°	127.0	135.9	146.2	157.2	169.6	184.5	203.5	224.9	247.8	269.2	288.1
137.5°	131.7	140.9	150.3	160.8	172.6	184.9	200.1	217.5	236.1	253.8	269.9
140°	134.6	143.5	153.3	163.2	173.9	185.2	198.5	213.5	229.1	244.5	258.4
142.5°	137.5	146.0	155.0	164.6	174.7	185.5	197.2	210.1	223.3	236.5	248.6
145°	141.9	149.6	158.3	166.5	175.5	185.2	195.2	205.6	215.8	226.2	235.2
147.5°	145.9	152.6	160.2	167.8	175.9	184.4	193.1	201.2	209.6	217.6	224.4
150°	148.5	154.2	161.6	168.5	175.9	183.5	191.5	198.9	206.2	212.5	218.5
152.5°	151.0	156.1	162.9	169.1	175.6	182.5	189.6	196.2	202.7	208.5	213.2
155°	153.9	158.5	164.2	169.6	174.8	180.6	186.5	192.2	197.6	202.2	205.9
157.5°	156.9	160.5	165.3	169.8	174.0	178.5	183.6	188.2	192.6	196.2	199.1
160°	158.5	161.6	165.9	169.8	173.2	177.2	181.3	185.6	188.9	192.2	194.5
162.5°	160.1	162.6	166.5	169.7	172.4	175.6	179.1	182.6	185.7	188.5	190.6
165°	161.9	163.9	166.5	169.2	171.3	173.2	175.9	178.5	180.9	182.9	184.5
167.5°	163.1	164.4	166.5	168.4	169.4	170.9	172.8	174.7	176.3	177.8	179.0
170°	163.9	164.9	166.5	167.9	168.5	169.6	170.9	172.6	173.5	174.6	175.2
172.5°	164.4	164.9	166.3	167.4	167.5	168.0	169.0	170.1	171.2	171.9	172.3
175°	164.9	164.9	165.9	166.5	166.3	166.3	166.5	167.6	167.6	168.2	168.2
177.5°	164.9	164.9	165.5	165.8	165.2	165.2	165.5	165.8	166.0	166.0	166.0
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	488.9	490.1	489.1	490.5	489.1	490.1	488.9	489.9	491.5	490.5	492.9
5°	450.6	448.7	450.0	449.1	450.0	448.7	450.6	451.7	454.3	455.2	456.9
7.5°	415.3	413.4	411.2	410.2	411.2	413.4	415.3	415.8	418.1	421.4	423.9
10°	393.1	390.7	390.5	389.0	390.5	390.7	393.1	395.5	397.0	401.1	404.0
12.5°	376.9	374.7	372.2	371.6	372.2	374.7	376.9	379.0	379.5	384.1	386.1
15°	353.9	352.1	350.6	351.9	350.6	352.1	353.9	355.2	357.6	360.9	363.1
17.5°	334.8	333.4	333.1	331.5	333.1	333.4	334.8	335.5	339.4	341.6	345.3
20°	322.7	321.7	322.2	319.2	322.2	321.7	322.7	324.7	328.7	329.7	333.7
22.5°	313.2	311.0	310.8	310.2	310.8	311.0	313.2	315.0	315.8	319.1	321.8
25°	298.1	297.1	296.0	297.1	296.0	297.1	298.1	300.1	301.0	303.4	306.0
27.5°	285.0	283.7	283.4	283.6	283.4	283.7	285.0	284.8	287.2	289.2	291.1
30°	277.0	274.8	275.0	274.8	275.0	274.8	277.0	277.0	278.3	280.1	281.8
32.5°	268.3	266.8	266.6	266.2	266.6	266.8	268.3	268.0	269.7	271.7	273.6
35°	255.4	255.4	254.4	254.4	254.4	255.4	255.4	256.1	257.9	257.9	260.0
37.5°	243.4	243.2	242.5	242.6	242.5	243.2	243.4	243.9	244.5	245.4	246.9
40°	234.3	234.1	233.5	232.1	233.5	234.1	234.3	235.3	235.6	236.8	237.6
42.5°	225.6	224.9	224.6	224.1	224.6	224.9	225.6	226.1	226.4	227.8	229.6
45°	211.9	211.9	211.5	211.2	211.5	211.9	211.9	211.9	212.2	213.9	214.7
47.5°	198.6	199.0	199.8	199.6	199.8	199.0	198.6	198.2	198.3	199.2	200.2
50°	190.6	190.8	191.4	191.6	191.4	190.8	190.6	189.7	189.3	189.3	189.9
52.5°	181.7	182.9	183.8	183.6	183.8	182.9	181.7	181.0	180.2	179.2	180.1
55°	169.2	170.8	172.3	172.5	172.3	170.8	169.2	167.3	166.4	164.7	165.3
57.5°	156.9	159.0	160.6	161.2	160.6	159.0	156.9	154.6	151.7	150.9	149.7
60°	148.5	151.4	153.4	154.2	153.4	151.4	148.5	146.4	142.6	140.3	139.4
62.5°	140.5	143.7	145.6	145.8	145.6	143.7	140.5	137.1	133.5	130.6	128.9
65°	127.4	130.6	132.4	133.7	132.4	130.6	127.4	123.7	119.6	115.8	113.9
67.5°	113.3	116.6	118.5	119.5	118.5	116.6	113.3	108.7	104.9	100.7	98.4
70°	103.0	106.3	108.9	109.8	108.9	106.3	103.0	97.6	94.3	90.4	88.4
72.5°	92.9	95.9	97.9	99.0	97.9	95.9	92.9	87.8	84.0	80.1	77.5
75°	75.3	79.3	81.2	82.3	81.2	79.3	75.3	72.5	68.1	64.0	61.8
77.5°	58.1	61.6	62.9	63.4	62.9	61.6	58.1	54.8	51.5	48.4	46.4
80°	46.6	48.8	50.3	50.5	50.3	48.8	46.6	44.0	41.4	38.5	36.6
82.5°	35.8	37.6	38.1	38.6	38.1	37.6	35.8	33.6	31.3	29.1	27.5
85°	19.6	20.5	20.7	20.5	20.7	20.5	19.6	18.1	17.0	15.9	15.3
87.5°	7.9	7.7	7.8	8.2	7.8	7.7	7.9	7.5	7.6	7.2	6.8
90°	7.4	7.4	7.6	7.6	7.6	7.4	7.4	7.4	6.7	6.3	6.0
92.5°	23.1	22.2	21.8	21.2	21.8	22.2	23.1	27.3	32.2	42.8	59.0
95°	96.2	86.2	83.6	78.3	83.6	86.2	96.2	119.9	147.9	188.9	239.5
97.5°	221.8	203.1	193.5	189.2	193.5	203.1	221.8	242.3	281.3	321.2	356.7
100°	301.4	277.5	265.1	259.9	265.1	277.5	301.4	324.4	359.1	393.4	409.7
102.5°	373.2	356.1	342.7	338.7	342.7	356.1	373.2	397.8	421.2	437.6	427.5
105°	463.0	452.0	445.4	441.4	445.4	452.0	463.0	473.7	477.3	462.7	417.1
107.5°	500.8	500.8	498.5	495.9	498.5	500.8	500.8	495.4	478.0	440.4	379.5
110°	505.3	511.6	514.0	514.0	514.0	511.6	505.3	490.3	462.0	415.1	351.8



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.8	503.7	509.4	511.9	509.4	503.7	492.8	470.9	437.5	390.0	329.9
115°	462.0	478.0	487.3	491.6	487.3	478.0	462.0	436.0	399.7	354.1	302.5
117.5°	427.8	444.4	453.6	456.3	453.6	444.4	427.8	401.9	368.5	329.2	284.7
120°	405.8	421.7	430.7	433.4	430.7	421.7	405.8	381.1	351.8	315.1	275.1
122.5°	387.1	401.7	410.8	413.1	410.8	401.7	387.1	365.0	337.6	305.0	268.0
125°	363.1	376.7	384.1	387.4	384.1	376.7	363.1	344.4	320.5	291.4	257.5
127.5°	345.0	357.0	363.9	365.4	363.9	357.0	345.0	328.0	305.6	278.5	246.9
130°	333.8	344.8	351.5	353.5	351.5	344.8	333.8	317.2	295.5	269.5	240.2
132.5°	322.1	333.0	339.1	341.4	339.1	333.0	322.1	305.4	284.6	261.0	233.5
135°	302.8	313.8	319.8	321.8	319.8	313.8	302.8	288.1	269.2	247.8	224.9
137.5°	283.0	293.0	298.6	300.8	298.6	293.0	283.0	269.9	253.8	236.1	217.5
140°	270.8	279.5	284.5	286.2	284.5	279.5	270.8	258.4	244.5	229.1	213.5
142.5°	259.1	266.5	271.2	272.6	271.2	266.5	259.1	248.6	236.5	223.3	210.1
145°	243.2	248.8	252.5	253.8	252.5	248.8	243.2	235.2	226.2	215.8	205.6
147.5°	230.7	235.3	237.3	238.0	237.3	235.3	230.7	224.4	217.6	209.6	201.2
150°	223.5	227.5	228.8	229.1	228.8	227.5	223.5	218.5	212.5	206.2	198.9
152.5°	217.4	220.6	221.9	222.3	221.9	220.6	217.4	213.2	208.5	202.7	196.2
155°	209.2	211.5	212.5	212.8	212.5	211.5	209.2	205.9	202.2	197.6	192.2
157.5°	201.7	203.6	204.5	204.4	204.5	203.6	201.7	199.1	196.2	192.6	188.2
160°	196.9	198.5	199.2	198.9	199.2	198.5	196.9	194.5	192.2	188.9	185.6
162.5°	192.4	193.7	193.9	193.8	193.9	193.7	192.4	190.6	188.5	185.7	182.6
165°	185.9	186.5	186.5	186.5	186.5	186.5	185.9	184.5	182.9	180.9	178.5
167.5°	179.6	180.2	179.9	179.8	179.9	180.2	179.6	179.0	177.8	176.3	174.7
170°	175.9	176.3	176.3	175.9	176.3	176.3	175.9	175.2	174.6	173.5	172.6
172.5°	172.4	173.1	172.5	172.1	172.5	173.1	172.4	172.3	171.9	171.2	170.1
175°	168.2	168.5	167.9	167.6	167.9	168.5	168.2	168.2	168.2	167.6	167.6
177.5°	165.8	166.0	165.2	165.2	165.2	166.0	165.8	166.0	166.0	166.0	165.8
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	490.7	492.8	495.3	497.3	500.8	502.3	504.3	505.8	508.6	511.2	514.3
5°	457.6	461.3	466.3	471.7	478.1	482.4	488.5	492.2	499.6	506.3	512.9
7.5°	427.6	432.2	439.2	446.2	454.5	461.9	469.6	478.1	487.5	498.7	507.9
10°	407.1	413.1	420.8	429.5	439.5	448.2	458.5	467.6	479.2	492.2	504.4
12.5°	390.7	395.9	404.4	412.7	423.5	434.1	444.7	456.8	470.2	484.7	500.0
15°	368.1	372.4	379.4	391.0	401.8	412.3	428.2	439.5	456.5	472.6	491.2
17.5°	348.7	354.2	360.1	369.9	381.3	394.3	408.5	422.7	439.0	459.5	480.3
20°	337.0	341.3	348.0	355.6	367.6	380.7	394.2	408.6	428.6	449.8	472.2
22.5°	324.0	328.8	336.4	344.7	354.8	367.3	382.2	397.9	418.9	439.6	464.0
25°	308.9	312.1	319.1	326.5	336.5	347.1	362.6	380.0	400.8	424.5	449.3
27.5°	294.5	297.4	303.7	310.2	319.2	331.9	345.7	363.4	382.9	406.9	434.4
30°	284.2	287.3	292.9	299.9	308.6	319.7	333.8	350.4	371.4	394.8	423.6
32.5°	275.3	278.1	282.3	289.3	297.8	308.6	321.7	338.6	359.5	383.3	411.6
35°	261.6	264.6	267.9	273.3	280.7	291.2	305.6	321.5	341.5	364.6	390.5
37.5°	247.9	251.2	254.1	259.0	265.7	274.9	287.4	304.0	322.1	344.3	369.2
40°	239.3	242.0	244.4	249.6	256.4	265.0	276.6	291.4	310.6	331.3	351.9
42.5°	230.8	233.3	235.3	239.9	246.1	254.4	265.4	279.9	297.7	317.0	335.3
45°	217.4	218.9	221.3	225.2	230.2	237.8	248.5	261.4	276.4	294.6	308.4
47.5°	202.8	205.2	207.2	210.6	214.7	222.2	232.4	243.4	257.0	270.6	280.2
50°	191.6	194.1	196.9	200.2	204.1	211.0	220.4	231.5	243.1	253.5	261.7
52.5°	181.2	183.4	186.4	189.5	194.4	200.2	208.2	218.1	229.5	237.0	243.8
55°	165.7	166.8	170.3	173.3	178.0	182.3	190.4	199.1	206.0	211.7	217.4
57.5°	150.0	151.4	153.4	156.2	160.7	165.8	171.4	179.2	183.2	186.2	190.6
60°	139.8	140.3	141.6	144.9	148.4	152.9	159.4	164.9	168.0	170.3	174.0
62.5°	128.7	128.8	130.9	133.4	135.9	140.9	146.2	150.6	153.1	154.3	157.8
65°	113.0	112.6	113.9	115.8	118.9	122.2	126.8	130.6	130.4	131.8	133.9
67.5°	97.1	96.6	96.6	98.5	100.9	103.9	107.0	109.3	109.3	111.0	112.2
70°	86.2	84.9	85.8	87.4	88.4	90.9	94.3	95.2	95.4	96.2	97.4
72.5°	75.1	74.6	75.3	76.0	76.7	78.6	81.6	82.1	82.2	82.7	84.5
75°	59.7	59.3	58.8	59.5	60.3	61.6	62.7	63.6	63.3	63.6	64.9
77.5°	44.8	43.5	43.3	43.6	43.8	44.7	45.8	45.7	45.9	45.9	47.3
80°	35.5	33.7	33.6	33.6	33.7	34.2	34.6	35.1	34.4	35.1	35.5
82.5°	26.1	25.1	25.0	24.8	24.9	25.0	25.3	25.4	25.4	25.6	25.9
85°	14.4	13.9	13.3	13.8	13.5	12.8	13.3	12.6	12.4	12.6	12.8
87.5°	6.0	6.1	5.7	5.6	5.3	5.4	4.9	4.6	4.2	4.3	4.8
90°	5.7	5.4	4.6	4.3	3.7	3.3	2.6	2.0	1.3	0.7	0.4
92.5°	86.9	107.4	109.1	76.0	45.5	27.3	17.6	11.9	7.7	4.9	4.1
95°	288.8	295.1	240.8	148.9	75.6	40.0	25.0	17.6	13.9	11.3	11.0
97.5°	365.4	315.2	215.1	118.9	65.1	41.6	30.8	24.2	20.5	18.7	18.3
100°	384.1	300.8	191.9	107.9	64.7	45.3	35.3	28.9	25.4	23.9	23.3
102.5°	372.9	275.5	174.3	103.4	67.0	49.9	40.2	34.3	30.3	29.3	28.9
105°	337.1	241.5	157.2	101.6	71.9	57.3	48.0	42.6	39.3	37.6	37.6
107.5°	300.6	218.1	150.1	104.6	79.3	65.1	56.7	51.2	48.4	46.8	46.2
110°	279.8	207.2	147.9	107.6	84.6	71.0	62.3	57.3	54.3	53.0	52.3



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	264.4	200.8	147.9	111.3	89.6	76.5	68.1	63.2	60.1	59.1	58.4
115°	247.5	193.9	148.9	116.9	97.6	85.3	76.9	71.9	69.0	68.0	67.3
117.5°	237.4	190.5	151.1	123.3	105.8	94.1	86.1	80.3	77.4	76.3	75.3
120°	231.9	188.9	153.3	127.6	111.6	99.9	91.6	86.0	82.9	81.6	80.6
122.5°	227.1	187.6	155.0	132.3	117.2	105.6	97.2	91.0	88.0	86.9	86.2
125°	220.6	185.9	158.3	138.9	124.6	113.6	104.9	98.6	95.6	94.0	93.3
127.5°	214.5	185.1	161.7	144.9	131.7	121.1	112.4	105.8	101.9	99.8	98.8
130°	210.6	184.5	163.9	148.9	136.2	125.9	117.3	110.3	105.9	103.3	102.3
132.5°	207.4	184.5	166.3	152.4	140.5	130.2	121.5	114.2	109.4	106.2	104.9
135°	203.5	184.5	169.6	157.2	146.2	135.9	127.0	119.9	114.6	110.6	109.2
137.5°	200.1	184.9	172.6	160.8	150.3	140.9	131.7	124.8	119.4	115.7	114.7
140°	198.5	185.2	173.9	163.2	153.3	143.5	134.6	128.3	122.9	118.9	117.9
142.5°	197.2	185.5	174.7	164.6	155.0	146.0	137.5	131.5	126.1	122.3	121.7
145°	195.2	185.2	175.5	166.5	158.3	149.6	141.9	135.9	131.2	127.9	127.2
147.5°	193.1	184.4	175.9	167.8	160.2	152.6	145.9	140.7	136.4	133.5	133.1
150°	191.5	183.5	175.9	168.5	161.6	154.2	148.5	143.9	139.6	137.2	136.6
152.5°	189.6	182.5	175.6	169.1	162.9	156.1	151.0	146.6	142.8	140.7	140.3
155°	186.5	180.6	174.8	169.6	164.2	158.5	153.9	150.5	147.2	145.2	145.2
157.5°	183.6	178.5	174.0	169.8	165.3	160.5	156.9	154.0	151.2	149.6	149.7
160°	181.3	177.2	173.2	169.8	165.9	161.6	158.5	155.9	153.5	152.2	152.6
162.5°	179.1	175.6	172.4	169.7	166.5	162.6	160.1	158.1	156.0	154.7	155.0
165°	175.9	173.2	171.3	169.2	166.5	163.9	161.9	160.5	158.9	157.9	158.5
167.5°	172.8	170.9	169.4	168.4	166.5	164.4	163.1	162.1	161.3	160.6	161.0
170°	170.9	169.6	168.5	167.9	166.5	164.9	163.9	163.2	162.6	162.2	162.6
172.5°	169.0	168.0	167.5	167.4	166.3	164.9	164.4	164.0	163.3	163.1	163.6
175°	166.5	166.3	166.3	166.5	165.9	164.9	164.9	164.9	164.6	164.2	164.9
177.5°	165.5	165.2	165.2	165.8	165.5	164.9	164.9	165.2	164.9	164.9	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	515.9	518.3	519.9	522.8	525.3	526.7	527.9	529.0	530.2	531.2	534.2
5°	519.2	524.9	529.7	537.1	543.8	549.0	554.7	559.7	563.8	569.8	574.3
7.5°	517.7	527.8	538.4	549.9	561.6	572.4	582.5	591.8	600.3	610.6	619.6
10°	516.4	530.1	543.6	559.1	575.0	588.4	601.1	614.0	623.3	636.4	647.5
12.5°	515.4	531.5	547.8	566.4	583.8	602.9	619.7	629.1	643.4	653.8	667.0
15°	511.0	532.3	554.7	575.6	600.5	618.1	632.9	651.2	664.5	677.8	692.1
17.5°	503.0	527.3	552.3	579.8	603.5	622.5	641.6	659.2	675.0	692.9	710.8
20°	499.4	523.6	552.3	580.4	603.7	623.5	643.1	662.5	680.0	702.9	723.5
22.5°	491.7	520.9	547.4	574.9	598.8	620.4	642.6	664.6	687.8	713.6	739.5
25°	478.1	507.7	535.7	562.8	586.9	614.0	637.7	667.1	696.7	730.9	763.2
27.5°	463.8	492.2	517.9	544.0	572.2	602.9	633.6	666.9	705.8	748.9	794.4
30°	452.3	479.2	504.2	530.9	560.3	594.7	628.6	668.2	713.0	761.6	815.7
32.5°	438.9	463.6	488.0	516.3	548.4	584.7	624.1	667.5	721.4	776.6	832.2
35°	415.9	436.7	461.8	492.0	528.1	569.8	615.3	666.7	728.5	791.9	838.7
37.5°	388.8	408.0	434.4	467.6	505.5	550.2	604.2	665.2	730.8	781.4	796.4
40°	370.4	388.3	415.8	450.2	488.9	536.2	595.4	659.9	723.5	755.7	743.3
42.5°	350.9	369.7	396.4	430.5	472.2	523.7	584.5	648.9	702.3	714.4	671.6
45°	320.2	339.5	365.9	400.3	445.2	501.0	564.3	622.9	653.6	631.6	565.1
47.5°	291.5	309.7	334.1	369.7	415.9	473.6	534.6	581.4	583.8	531.3	460.3
50°	272.0	288.8	313.4	348.9	394.8	453.3	508.3	545.2	528.6	469.1	401.0
52.5°	252.9	269.3	293.5	328.7	374.1	427.6	478.9	504.7	473.5	412.5	354.3
55°	225.2	239.6	263.3	295.8	338.8	388.5	432.1	441.0	400.5	340.4	293.1
57.5°	198.2	211.6	233.2	263.1	302.6	346.5	380.6	378.6	335.8	284.3	246.8
60°	179.9	192.9	212.2	241.3	277.3	315.2	344.3	337.3	294.9	250.4	218.9
62.5°	163.5	175.2	193.3	218.9	251.7	286.7	310.7	300.4	258.8	220.0	195.0
65°	139.4	149.2	164.7	186.4	213.7	242.6	261.2	247.9	212.4	182.1	162.0
67.5°	116.3	124.2	137.1	154.6	177.8	201.0	212.3	199.0	170.5	148.5	133.6
70°	101.7	108.7	118.7	134.1	154.4	174.0	182.5	170.5	146.1	127.1	116.5
72.5°	87.1	92.8	101.6	115.6	131.8	148.7	156.2	144.8	124.7	108.7	98.8
75°	67.3	71.3	77.3	86.9	99.7	113.3	117.3	107.4	94.5	82.6	76.0
77.5°	48.2	51.5	56.1	62.1	71.3	79.8	83.4	77.7	67.8	60.1	54.8
80°	37.0	38.7	42.7	47.7	54.9	60.3	62.7	59.0	52.0	46.4	42.2
82.5°	26.4	28.2	30.4	34.6	39.2	42.9	45.4	43.0	38.0	33.5	31.1
85°	12.8	13.9	15.3	17.0	20.5	22.6	22.4	20.9	18.9	17.2	15.9
87.5°	4.6	5.0	5.7	6.6	7.3	8.0	8.6	8.3	7.7	7.3	6.8
90°	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7	6.0
92.5°	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9	59.0
95°	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8	239.5
97.5°	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4	356.7
100°	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1	409.7
102.5°	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9	427.5
105°	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1	417.1
107.5°	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6	379.5
110°	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8	351.8



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4	329.9
115°	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5	302.5
117.5°	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4	284.7
120°	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9	275.1
122.5°	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1	268.0
125°	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6	257.5
127.5°	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5	246.9
130°	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6	240.2
132.5°	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4	233.5
135°	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5	224.9
137.5°	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1	217.5
140°	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5	213.5
142.5°	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2	210.1
145°	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2	205.6
147.5°	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1	201.2
150°	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5	198.9
152.5°	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6	196.2
155°	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5	192.2
157.5°	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6	188.2
160°	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3	185.6
162.5°	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1	182.6
165°	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9	178.5
167.5°	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8	174.7
170°	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9	172.6
172.5°	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0	170.1
175°	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5	167.6
177.5°	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5	165.8
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	513.1	513.1	513.1	513.1	513.1	513.1	513.1
2.5°	536.7	538.0	541.0	540.0	541.3	542.1	542.7
5°	579.9	586.9	590.0	589.6	594.2	593.0	591.9
7.5°	629.0	636.2	640.4	645.5	648.4	648.7	651.2
10°	656.7	666.2	670.1	675.6	679.1	681.1	680.8
12.5°	677.9	685.4	694.2	696.8	701.5	704.1	703.1
15°	703.5	715.5	724.6	729.2	735.1	736.8	739.1
17.5°	726.3	742.3	753.0	767.2	772.6	775.9	773.9
20°	743.6	764.7	775.3	792.3	801.7	806.7	804.9
22.5°	763.9	786.8	806.5	821.2	835.5	842.3	843.7
25°	798.9	830.2	859.2	878.5	896.2	900.3	909.5
27.5°	837.9	874.9	905.9	926.2	938.5	943.1	946.0
30°	862.4	899.3	922.6	935.7	939.5	939.1	938.7
32.5°	874.5	897.5	902.0	898.3	889.4	881.7	873.8
35°	857.4	840.3	814.5	781.5	757.1	732.4	730.0
37.5°	771.2	716.1	673.4	625.6	598.0	581.0	569.2
40°	689.9	627.5	575.6	535.4	507.3	496.2	485.2
42.5°	601.8	542.1	496.2	462.5	441.4	429.0	420.5
45°	488.9	436.2	400.3	375.9	359.1	349.6	344.1
47.5°	400.7	361.7	331.1	313.5	302.0	294.5	294.5
50°	353.3	316.0	295.8	281.8	271.8	265.9	267.0
52.5°	311.2	283.4	266.2	254.5	247.0	243.5	243.3
55°	260.2	240.3	228.9	220.4	215.4	211.2	212.2
57.5°	222.6	205.8	198.1	191.1	187.6	186.0	183.5
60°	199.3	186.2	179.6	174.0	170.5	169.2	166.8
62.5°	178.5	168.2	161.9	157.3	154.2	153.7	151.8
65°	150.1	142.2	136.6	134.4	131.1	130.3	130.3
67.5°	123.7	118.1	113.7	111.7	110.3	110.5	109.4
70°	107.2	102.5	99.7	97.6	96.5	96.7	95.9
72.5°	93.8	88.6	86.1	84.8	83.4	84.0	83.6
75°	71.0	68.4	67.1	65.8	64.9	64.5	64.0
77.5°	52.1	49.9	48.8	48.1	48.3	47.1	48.0
80°	40.2	38.4	37.7	36.6	36.4	36.4	36.2
82.5°	29.5	28.4	27.9	27.1	26.6	27.0	26.4
85°	15.3	14.4	14.1	14.1	13.8	13.3	14.4
87.5°	6.9	6.2	6.3	6.1	6.1	6.0	5.7
90°	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	415.1	462.0	490.3	505.3	511.6	514.0	514.0



TEST NUMBER: P333117-830

CATALOG NUMBER: S125DIP-S375D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)