

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333162-830

Luminaire Tested: **S125DIP-S610D365U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333162-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D365U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3620.3 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	81	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	68	62	80	71	65	59	63	58	54	56	52	49	50	46	44	40
4	78	67	59	53	73	63	56	50	57	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	45	40	62	51	43	38	46	40	35	41	36	32	36	32	29	27
7	61	49	40	35	57	46	39	34	42	35	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	31	26	23	21
9	53	40	33	28	50	39	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5448	5448	5448	5448
5°	6309	5466	4786	5466
10°	7340	5438	4194	5438
15°	8125	5398	3869	5398
20°	9095	5335	3608	5335
25°	10655	5264	3480	5264
30°	11508	5193	3370	5193
35°	9462	5062	3297	5062
40°	6726	4878	3217	4878
45°	5167	4631	3172	4631
50°	4410	4324	3166	4324
55°	3926	4023	3193	4023
60°	3543	3695	3274	3695
65°	3272	3365	3359	3365
70°	2974	3021	3408	3021
75°	2628	2662	3376	2662
80°	2213	2168	3087	2168
85°	1756	1564	2490	1564



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	2.2
10°-20°	241.8	6.7
20°-30°	392.6	10.8
30°-40°	478.9	13.2
40°-50°	435.7	12.0
50°-60°	347.0	9.6
60°-70°	241.7	6.7
70°-80°	128.9	3.6
80°-90°	33.5	0.9
90°-100°	119.8	3.3
100°-110°	257.4	7.1
110°-120°	241.6	6.7
120°-130°	195.8	5.4
130°-140°	157.1	4.3
140°-150°	118.6	3.3
150°-160°	83.5	2.3
160°-170°	49.2	1.4
170°-180°	16.0	0.4
0°-30°	715.6	19.8
0°-40°	1194.5	33.0
0°-60°	1977.3	54.6
0°-90°	2381.3	65.8
90°-120°	618.8	17.1
90°-150°	1090.3	30.1
90°-180°	1239.0	34.2
0°-180°	3620.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	844	844	844	844	844	
5°	973	843	738	843	973	98
15°	1215	807	579	807	1215	348
25°	1495	739	488	739	1495	683
35°	1200	642	418	642	1200	735
45°	566	507	347	507	566	453
55°	349	357	284	357	349	314
65°	214	220	220	220	214	212
75°	105	107	135	107	105	113
85°	24	21	34	21	24	27
90°	8	0	8	0	8	6
95°	78	11	78	11	78	111
105°	441	38	441	38	441	439
115°	492	67	492	67	492	480
125°	387	93	387	93	387	350
135°	322	109	322	109	322	249
145°	254	127	254	127	254	161
155°	213	145	213	145	213	99
165°	186	158	186	158	186	53
175°	168	165	168	165	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	892.3	891.1	889.9	887.7	889.4	884.5	882.2	878.3	873.4	871.7	869.6
5°	973.2	975.0	976.8	969.2	970.0	965.0	953.5	944.1	936.7	927.0	920.2
7.5°	1070.5	1066.3	1066.0	1061.1	1052.7	1046.0	1034.0	1018.6	1003.8	986.9	973.0
10°	1119.3	1119.6	1116.4	1110.7	1101.7	1095.2	1079.5	1064.5	1046.2	1024.7	1009.4
12.5°	1155.9	1157.4	1153.4	1145.7	1141.2	1126.8	1114.5	1096.6	1074.9	1057.7	1034.3
15°	1215.2	1211.3	1208.4	1198.7	1191.2	1176.2	1156.5	1137.8	1114.3	1092.4	1070.5
17.5°	1272.3	1275.5	1270.2	1261.3	1238.0	1220.4	1194.0	1168.6	1139.1	1109.8	1083.7
20°	1323.3	1326.3	1318.0	1302.6	1274.7	1257.1	1222.4	1189.4	1155.5	1117.9	1089.2
22.5°	1387.0	1384.7	1373.6	1350.1	1326.0	1293.5	1255.9	1215.8	1173.2	1130.7	1092.6
25°	1495.2	1480.2	1473.4	1444.4	1412.5	1364.9	1313.3	1254.6	1201.6	1145.4	1096.7
27.5°	1555.2	1550.5	1542.9	1522.7	1489.2	1438.3	1377.5	1306.0	1231.1	1160.3	1096.5
30°	1543.2	1543.9	1544.6	1538.1	1516.7	1478.4	1417.9	1340.9	1252.1	1172.2	1098.5
32.5°	1436.6	1449.6	1462.2	1476.9	1482.9	1475.6	1437.7	1368.1	1276.8	1186.0	1097.3
35°	1200.1	1204.1	1244.6	1284.7	1339.1	1381.4	1409.7	1378.8	1301.8	1197.7	1096.0
37.5°	935.8	955.2	983.2	1028.5	1107.0	1177.3	1267.8	1309.4	1284.5	1201.5	1093.4
40°	797.8	815.7	833.9	880.1	946.3	1031.5	1134.3	1222.0	1242.5	1189.4	1084.9
42.5°	691.2	705.4	725.7	760.3	815.7	891.2	989.4	1104.0	1174.5	1154.5	1066.9
45°	565.7	574.7	590.4	618.0	658.1	717.2	803.8	929.2	1038.3	1074.5	1024.0
47.5°	484.2	484.2	496.4	515.5	544.4	594.6	658.6	756.9	873.5	959.8	955.7
50°	438.9	437.2	446.9	463.4	486.3	519.5	580.8	659.2	771.3	869.0	896.2
52.5°	400.0	400.2	406.1	418.3	437.5	466.0	511.7	582.4	678.2	778.4	829.7
55°	348.7	347.3	354.1	362.3	376.4	394.9	427.9	481.9	559.6	658.5	725.0
57.5°	301.8	305.7	308.4	314.1	325.7	338.2	366.0	405.7	467.3	552.1	622.5
60°	274.3	278.2	280.3	286.1	295.4	306.1	327.6	359.9	411.8	484.8	554.6
62.5°	249.6	252.7	253.4	258.5	266.2	276.6	293.5	320.6	361.7	425.5	493.9
65°	214.1	214.1	215.6	220.9	224.5	233.8	246.7	266.4	299.4	349.1	407.5
67.5°	179.8	181.6	181.3	183.6	186.9	194.2	203.4	219.6	244.0	280.3	327.1
70°	157.5	159.0	158.6	160.4	164.0	168.6	176.2	191.5	209.1	240.3	280.3
72.5°	137.5	138.1	137.1	139.5	141.7	145.7	154.1	162.3	178.7	205.0	238.0
75°	105.3	105.9	106.7	108.1	110.3	112.4	116.7	125.0	135.7	155.4	176.5
77.5°	78.9	77.6	79.3	79.1	80.3	81.9	85.7	90.1	98.9	111.3	127.7
80°	59.5	59.8	59.8	60.1	61.9	63.1	66.3	69.5	76.3	85.6	97.0
82.5°	43.4	44.3	43.7	44.4	45.9	46.7	48.4	51.1	55.0	62.4	70.7
85°	23.7	21.9	22.5	23.3	23.3	23.7	25.1	26.1	28.3	31.1	34.4
87.5°	8.4	9.0	9.2	9.2	9.5	9.3	10.5	10.4	11.1	12.0	13.0
90°	7.6	7.6	7.4	7.4	7.4	6.7	6.3	6.0	5.7	5.4	4.6
92.5°	21.2	21.8	22.2	23.1	27.3	32.2	42.8	59.0	86.9	107.4	109.1
95°	78.3	83.6	86.2	96.2	119.9	147.9	188.9	239.5	288.8	295.1	240.8
97.5°	189.2	193.5	203.1	221.8	242.3	281.3	321.2	356.7	365.4	315.2	215.1
100°	259.9	265.1	277.5	301.4	324.4	359.1	393.4	409.7	384.1	300.8	191.9
102.5°	338.7	342.7	356.1	373.2	397.8	421.2	437.6	427.5	372.9	275.5	174.3
105°	441.4	445.4	452.0	463.0	473.7	477.3	462.7	417.1	337.1	241.5	157.2
107.5°	495.9	498.5	500.8	500.8	495.4	478.0	440.4	379.5	300.6	218.1	150.1
110°	514.0	514.0	511.6	505.3	490.3	462.0	415.1	351.8	279.8	207.2	147.9



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	511.9	509.4	503.7	492.8	470.9	437.5	390.0	329.9	264.4	200.8	147.9
115°	491.6	487.3	478.0	462.0	436.0	399.7	354.1	302.5	247.5	193.9	148.9
117.5°	456.3	453.6	444.4	427.8	401.9	368.5	329.2	284.7	237.4	190.5	151.1
120°	433.4	430.7	421.7	405.8	381.1	351.8	315.1	275.1	231.9	188.9	153.3
122.5°	413.1	410.8	401.7	387.1	365.0	337.6	305.0	268.0	227.1	187.6	155.0
125°	387.4	384.1	376.7	363.1	344.4	320.5	291.4	257.5	220.6	185.9	158.3
127.5°	365.4	363.9	357.0	345.0	328.0	305.6	278.5	246.9	214.5	185.1	161.7
130°	353.5	351.5	344.8	333.8	317.2	295.5	269.5	240.2	210.6	184.5	163.9
132.5°	341.4	339.1	333.0	322.1	305.4	284.6	261.0	233.5	207.4	184.5	166.3
135°	321.8	319.8	313.8	302.8	288.1	269.2	247.8	224.9	203.5	184.5	169.6
137.5°	300.8	298.6	293.0	283.0	269.9	253.8	236.1	217.5	200.1	184.9	172.6
140°	286.2	284.5	279.5	270.8	258.4	244.5	229.1	213.5	198.5	185.2	173.9
142.5°	272.6	271.2	266.5	259.1	248.6	236.5	223.3	210.1	197.2	185.5	174.7
145°	253.8	252.5	248.8	243.2	235.2	226.2	215.8	205.6	195.2	185.2	175.5
147.5°	238.0	237.3	235.3	230.7	224.4	217.6	209.6	201.2	193.1	184.4	175.9
150°	229.1	228.8	227.5	223.5	218.5	212.5	206.2	198.9	191.5	183.5	175.9
152.5°	222.3	221.9	220.6	217.4	213.2	208.5	202.7	196.2	189.6	182.5	175.6
155°	212.8	212.5	211.5	209.2	205.9	202.2	197.6	192.2	186.5	180.6	174.8
157.5°	204.4	204.5	203.6	201.7	199.1	196.2	192.6	188.2	183.6	178.5	174.0
160°	198.9	199.2	198.5	196.9	194.5	192.2	188.9	185.6	181.3	177.2	173.2
162.5°	193.8	193.9	193.7	192.4	190.6	188.5	185.7	182.6	179.1	175.6	172.4
165°	186.5	186.5	186.5	185.9	184.5	182.9	180.9	178.5	175.9	173.2	171.3
167.5°	179.8	179.9	180.2	179.6	179.0	177.8	176.3	174.7	172.8	170.9	169.4
170°	175.9	176.3	176.3	175.9	175.2	174.6	173.5	172.6	170.9	169.6	168.5
172.5°	172.1	172.5	173.1	172.4	172.3	171.9	171.2	170.1	169.0	168.0	167.5
175°	167.6	167.9	168.5	168.2	168.2	168.2	167.6	167.6	166.5	166.3	166.3
177.5°	165.2	165.2	166.0	165.8	166.0	166.0	166.0	165.8	165.5	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	867.9	865.9	863.7	859.6	854.7	852.2	848.2	845.6	840.4	836.1	831.5
5°	911.9	902.7	894.1	883.0	870.8	862.9	853.6	843.2	832.5	821.3	809.2
7.5°	957.5	941.1	923.2	903.9	885.1	867.8	851.2	835.0	819.8	801.4	785.9
10°	988.3	967.4	945.3	919.1	893.7	871.5	848.9	829.2	809.2	787.7	768.7
12.5°	1018.9	991.2	959.9	931.1	900.6	873.8	847.3	822.1	796.9	773.1	751.0
15°	1040.5	1016.2	987.1	946.3	911.9	875.1	840.0	807.4	776.9	750.5	722.6
17.5°	1054.7	1023.4	992.2	953.1	908.0	866.8	827.0	789.8	755.4	721.8	694.9
20°	1057.3	1025.1	992.5	954.2	908.0	860.7	821.0	776.3	739.3	704.6	671.7
22.5°	1056.5	1019.9	984.5	945.0	900.0	856.5	808.4	762.8	722.7	688.6	654.2
25°	1048.4	1009.4	965.0	925.2	880.8	834.6	785.9	738.7	697.9	658.8	624.8
27.5°	1041.6	991.0	940.8	894.4	851.5	809.2	762.6	714.2	668.9	629.3	597.3
30°	1033.3	977.8	921.2	872.9	828.9	787.7	743.7	696.4	649.1	610.5	576.1
32.5°	1025.9	961.2	901.5	848.9	802.3	762.2	721.6	676.7	630.3	591.0	556.7
35°	1011.5	936.7	868.3	808.8	759.0	717.9	683.9	642.0	599.4	561.4	528.5
37.5°	993.3	904.5	831.0	768.7	714.2	670.8	639.1	607.0	566.1	529.5	499.7
40°	978.9	881.6	803.8	740.1	683.5	638.4	609.1	578.6	544.6	510.6	479.1
42.5°	960.8	860.9	776.3	707.8	651.8	607.8	576.9	551.1	521.1	489.4	460.1
45°	927.7	823.5	731.9	658.1	601.5	558.2	526.3	507.0	484.5	454.4	429.7
47.5°	878.9	778.6	683.8	607.7	549.3	509.2	479.3	460.7	444.9	422.5	400.1
50°	835.7	745.1	649.1	573.6	515.2	474.8	447.2	430.4	416.8	399.5	380.6
52.5°	787.3	702.9	615.1	540.4	482.6	442.7	415.7	400.9	389.6	377.2	358.5
55°	710.4	638.8	557.1	486.3	432.9	393.9	370.2	357.3	348.0	338.7	327.3
57.5°	625.7	569.7	497.3	432.5	383.4	347.9	325.8	313.3	306.0	301.2	294.5
60°	566.1	518.1	455.8	396.7	348.7	317.3	295.8	286.1	280.0	276.1	271.1
62.5°	510.8	471.4	413.7	359.8	317.8	288.0	268.8	259.5	253.6	251.8	247.5
65°	429.3	398.9	351.3	306.5	270.7	245.2	229.1	220.2	216.6	214.4	214.8
67.5°	349.0	330.5	292.3	254.1	225.5	204.2	191.2	184.4	182.6	179.7	179.6
70°	300.0	286.1	253.8	220.6	195.1	178.7	167.2	160.0	158.3	156.8	156.5
72.5°	256.7	244.6	216.6	189.9	167.1	152.6	143.2	138.8	135.9	135.1	135.0
75°	193.0	186.2	164.0	142.9	127.1	117.1	110.7	106.7	104.5	104.2	104.5
77.5°	137.2	131.3	117.2	102.2	92.3	84.6	79.2	77.9	75.4	75.5	75.1
80°	103.1	99.2	90.2	78.4	70.2	63.7	60.9	58.3	57.7	56.6	57.7
82.5°	74.7	70.5	64.5	56.9	50.1	46.3	43.4	42.6	42.1	41.7	41.8
85°	36.9	37.2	33.6	27.9	25.1	22.9	21.1	21.1	20.7	20.5	20.7
87.5°	13.5	12.7	11.6	10.6	9.0	8.0	7.5	7.8	7.0	6.9	7.3
90°	4.3	3.7	3.3	2.6	2.0	1.3	0.7	0.4	0.7	1.3	2.0
92.5°	76.0	45.5	27.3	17.6	11.9	7.7	4.9	4.1	4.9	7.7	11.9
95°	148.9	75.6	40.0	25.0	17.6	13.9	11.3	11.0	11.3	13.9	17.6
97.5°	118.9	65.1	41.6	30.8	24.2	20.5	18.7	18.3	18.7	20.5	24.2
100°	107.9	64.7	45.3	35.3	28.9	25.4	23.9	23.3	23.9	25.4	28.9
102.5°	103.4	67.0	49.9	40.2	34.3	30.3	29.3	28.9	29.3	30.3	34.3
105°	101.6	71.9	57.3	48.0	42.6	39.3	37.6	37.6	37.6	39.3	42.6
107.5°	104.6	79.3	65.1	56.7	51.2	48.4	46.8	46.2	46.8	48.4	51.2
110°	107.6	84.6	71.0	62.3	57.3	54.3	53.0	52.3	53.0	54.3	57.3



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.3	89.6	76.5	68.1	63.2	60.1	59.1	58.4	59.1	60.1	63.2
115°	116.9	97.6	85.3	76.9	71.9	69.0	68.0	67.3	68.0	69.0	71.9
117.5°	123.3	105.8	94.1	86.1	80.3	77.4	76.3	75.3	76.3	77.4	80.3
120°	127.6	111.6	99.9	91.6	86.0	82.9	81.6	80.6	81.6	82.9	86.0
122.5°	132.3	117.2	105.6	97.2	91.0	88.0	86.9	86.2	86.9	88.0	91.0
125°	138.9	124.6	113.6	104.9	98.6	95.6	94.0	93.3	94.0	95.6	98.6
127.5°	144.9	131.7	121.1	112.4	105.8	101.9	99.8	98.8	99.8	101.9	105.8
130°	148.9	136.2	125.9	117.3	110.3	105.9	103.3	102.3	103.3	105.9	110.3
132.5°	152.4	140.5	130.2	121.5	114.2	109.4	106.2	104.9	106.2	109.4	114.2
135°	157.2	146.2	135.9	127.0	119.9	114.6	110.6	109.2	110.6	114.6	119.9
137.5°	160.8	150.3	140.9	131.7	124.8	119.4	115.7	114.7	115.7	119.4	124.8
140°	163.2	153.3	143.5	134.6	128.3	122.9	118.9	117.9	118.9	122.9	128.3
142.5°	164.6	155.0	146.0	137.5	131.5	126.1	122.3	121.7	122.3	126.1	131.5
145°	166.5	158.3	149.6	141.9	135.9	131.2	127.9	127.2	127.9	131.2	135.9
147.5°	167.8	160.2	152.6	145.9	140.7	136.4	133.5	133.1	133.5	136.4	140.7
150°	168.5	161.6	154.2	148.5	143.9	139.6	137.2	136.6	137.2	139.6	143.9
152.5°	169.1	162.9	156.1	151.0	146.6	142.8	140.7	140.3	140.7	142.8	146.6
155°	169.6	164.2	158.5	153.9	150.5	147.2	145.2	145.2	145.2	147.2	150.5
157.5°	169.8	165.3	160.5	156.9	154.0	151.2	149.6	149.7	149.6	151.2	154.0
160°	169.8	165.9	161.6	158.5	155.9	153.5	152.2	152.6	152.2	153.5	155.9
162.5°	169.7	166.5	162.6	160.1	158.1	156.0	154.7	155.0	154.7	156.0	158.1
165°	169.2	166.5	163.9	161.9	160.5	158.9	157.9	158.5	157.9	158.9	160.5
167.5°	168.4	166.5	164.4	163.1	162.1	161.3	160.6	161.0	160.6	161.3	162.1
170°	167.9	166.5	164.9	163.9	163.2	162.6	162.2	162.6	162.2	162.6	163.2
172.5°	167.4	166.3	164.9	164.4	164.0	163.3	163.1	163.6	163.1	163.3	164.0
175°	166.5	165.9	164.9	164.9	164.9	164.6	164.2	164.9	164.2	164.6	164.9
177.5°	165.8	165.5	164.9	164.9	165.2	164.9	164.9	165.5	164.9	164.9	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	829.0	825.8	823.2	817.5	814.4	810.0	806.6	810.3	806.3	808.0	805.5
5°	803.1	793.1	785.9	775.5	766.6	758.4	752.2	751.2	748.3	746.9	742.6
7.5°	772.0	759.5	747.2	733.6	722.1	710.5	702.9	696.8	692.8	687.4	683.7
10°	753.7	736.9	722.6	706.1	691.7	679.2	669.2	664.2	659.5	652.7	650.3
12.5°	731.0	713.7	696.2	678.5	664.9	650.8	642.2	634.7	631.5	623.8	623.0
15°	703.9	677.8	660.6	642.7	623.7	612.3	605.1	596.9	593.3	588.0	584.0
17.5°	671.6	648.2	626.7	608.2	591.9	582.3	573.3	567.7	561.6	558.1	551.6
20°	648.1	625.8	604.4	584.7	572.1	561.1	553.9	548.6	542.1	540.3	533.9
22.5°	628.3	603.8	583.2	566.7	553.0	540.5	532.7	529.0	524.6	519.1	517.8
25°	596.2	570.7	553.2	536.7	524.5	513.1	507.7	503.0	498.8	494.8	493.4
27.5°	568.4	545.6	524.8	509.9	499.4	488.9	484.2	478.5	475.3	472.2	468.3
30°	548.9	525.7	507.4	493.0	481.5	472.3	467.2	463.4	460.4	457.6	455.4
32.5°	528.9	507.3	489.6	475.6	464.1	457.1	452.6	449.9	446.7	443.3	440.5
35°	502.4	478.7	461.6	449.3	440.4	435.0	430.0	427.5	424.0	424.0	421.0
37.5°	472.5	452.0	436.9	425.7	417.7	412.9	407.6	405.9	403.5	402.0	401.1
40°	454.7	435.7	421.4	410.3	401.7	397.8	393.5	390.6	389.2	387.4	386.7
42.5°	436.4	418.3	404.5	394.3	386.8	383.4	379.5	377.5	374.6	372.2	371.8
45°	408.5	391.0	378.4	370.2	363.8	359.9	357.3	353.1	351.6	348.7	348.4
47.5°	382.1	365.2	353.0	346.2	340.5	337.3	333.4	329.1	327.4	326.0	325.9
50°	362.3	346.9	335.5	329.0	323.7	319.1	315.1	312.3	311.1	311.1	311.9
52.5°	342.3	329.2	319.4	311.6	306.5	301.5	297.9	296.1	294.5	296.2	297.6
55°	312.9	299.7	292.6	285.0	280.0	274.3	272.5	271.7	270.7	273.5	274.9
57.5°	281.8	272.6	264.2	256.7	252.2	248.9	246.5	246.1	248.1	249.4	254.1
60°	262.1	251.4	243.8	238.1	232.7	230.5	229.9	229.1	230.5	234.5	240.6
62.5°	240.3	231.6	223.5	219.2	215.3	211.7	211.5	212.0	214.8	219.3	225.5
65°	208.4	200.9	195.5	190.5	187.3	185.1	185.9	187.3	190.5	196.6	203.4
67.5°	176.0	170.8	166.0	161.9	158.8	158.8	159.6	161.7	165.5	172.5	178.7
70°	155.0	149.3	145.3	143.5	141.1	139.7	141.8	145.3	148.5	155.0	160.4
72.5°	134.1	129.2	126.2	125.0	123.9	122.7	123.5	127.3	131.7	138.2	144.4
75°	103.1	101.3	99.2	97.7	96.7	97.4	98.1	101.7	105.3	112.1	119.2
77.5°	75.3	73.4	72.1	71.7	71.2	71.5	73.5	76.2	79.7	84.6	90.1
80°	56.9	56.2	55.5	55.1	55.1	55.5	58.3	60.1	63.3	68.1	72.3
82.5°	41.5	41.0	40.9	40.8	41.1	41.2	42.9	45.2	47.9	51.5	55.1
85°	21.9	21.1	22.2	22.5	21.9	22.9	23.7	25.1	26.1	27.9	29.7
87.5°	7.7	8.4	8.2	8.6	8.7	9.3	9.1	10.4	11.0	11.7	11.5
90°	2.6	3.3	3.7	4.3	4.6	5.4	5.7	6.0	6.3	6.7	7.4
92.5°	17.6	27.3	45.5	76.0	109.1	107.4	86.9	59.0	42.8	32.2	27.3
95°	25.0	40.0	75.6	148.9	240.8	295.1	288.8	239.5	188.9	147.9	119.9
97.5°	30.8	41.6	65.1	118.9	215.1	315.2	365.4	356.7	321.2	281.3	242.3
100°	35.3	45.3	64.7	107.9	191.9	300.8	384.1	409.7	393.4	359.1	324.4
102.5°	40.2	49.9	67.0	103.4	174.3	275.5	372.9	427.5	437.6	421.2	397.8
105°	48.0	57.3	71.9	101.6	157.2	241.5	337.1	417.1	462.7	477.3	473.7
107.5°	56.7	65.1	79.3	104.6	150.1	218.1	300.6	379.5	440.4	478.0	495.4
110°	62.3	71.0	84.6	107.6	147.9	207.2	279.8	351.8	415.1	462.0	490.3



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	68.1	76.5	89.6	111.3	147.9	200.8	264.4	329.9	390.0	437.5	470.9
115°	76.9	85.3	97.6	116.9	148.9	193.9	247.5	302.5	354.1	399.7	436.0
117.5°	86.1	94.1	105.8	123.3	151.1	190.5	237.4	284.7	329.2	368.5	401.9
120°	91.6	99.9	111.6	127.6	153.3	188.9	231.9	275.1	315.1	351.8	381.1
122.5°	97.2	105.6	117.2	132.3	155.0	187.6	227.1	268.0	305.0	337.6	365.0
125°	104.9	113.6	124.6	138.9	158.3	185.9	220.6	257.5	291.4	320.5	344.4
127.5°	112.4	121.1	131.7	144.9	161.7	185.1	214.5	246.9	278.5	305.6	328.0
130°	117.3	125.9	136.2	148.9	163.9	184.5	210.6	240.2	269.5	295.5	317.2
132.5°	121.5	130.2	140.5	152.4	166.3	184.5	207.4	233.5	261.0	284.6	305.4
135°	127.0	135.9	146.2	157.2	169.6	184.5	203.5	224.9	247.8	269.2	288.1
137.5°	131.7	140.9	150.3	160.8	172.6	184.9	200.1	217.5	236.1	253.8	269.9
140°	134.6	143.5	153.3	163.2	173.9	185.2	198.5	213.5	229.1	244.5	258.4
142.5°	137.5	146.0	155.0	164.6	174.7	185.5	197.2	210.1	223.3	236.5	248.6
145°	141.9	149.6	158.3	166.5	175.5	185.2	195.2	205.6	215.8	226.2	235.2
147.5°	145.9	152.6	160.2	167.8	175.9	184.4	193.1	201.2	209.6	217.6	224.4
150°	148.5	154.2	161.6	168.5	175.9	183.5	191.5	198.9	206.2	212.5	218.5
152.5°	151.0	156.1	162.9	169.1	175.6	182.5	189.6	196.2	202.7	208.5	213.2
155°	153.9	158.5	164.2	169.6	174.8	180.6	186.5	192.2	197.6	202.2	205.9
157.5°	156.9	160.5	165.3	169.8	174.0	178.5	183.6	188.2	192.6	196.2	199.1
160°	158.5	161.6	165.9	169.8	173.2	177.2	181.3	185.6	188.9	192.2	194.5
162.5°	160.1	162.6	166.5	169.7	172.4	175.6	179.1	182.6	185.7	188.5	190.6
165°	161.9	163.9	166.5	169.2	171.3	173.2	175.9	178.5	180.9	182.9	184.5
167.5°	163.1	164.4	166.5	168.4	169.4	170.9	172.8	174.7	176.3	177.8	179.0
170°	163.9	164.9	166.5	167.9	168.5	169.6	170.9	172.6	173.5	174.6	175.2
172.5°	164.4	164.9	166.3	167.4	167.5	168.0	169.0	170.1	171.2	171.9	172.3
175°	164.9	164.9	165.9	166.5	166.3	166.3	166.5	167.6	167.6	168.2	168.2
177.5°	164.9	164.9	165.5	165.8	165.2	165.2	165.5	165.8	166.0	166.0	166.0
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	803.7	805.8	804.1	806.3	804.1	805.8	803.7	805.5	808.0	806.3	810.3
5°	740.8	737.5	739.7	738.3	739.7	737.5	740.8	742.6	746.9	748.3	751.2
7.5°	682.7	679.6	676.1	674.4	676.1	679.6	682.7	683.7	687.4	692.8	696.8
10°	646.3	642.3	642.0	639.5	642.0	642.3	646.3	650.3	652.7	659.5	664.2
12.5°	619.6	616.0	611.9	610.9	611.9	616.0	619.6	623.0	623.8	631.5	634.7
15°	581.8	579.0	576.5	578.6	576.5	579.0	581.8	584.0	588.0	593.3	596.9
17.5°	550.4	548.0	547.6	545.0	547.6	548.0	550.4	551.6	558.1	561.6	567.7
20°	530.7	528.9	529.5	524.9	529.5	528.9	530.7	533.9	540.3	542.1	548.6
22.5°	514.9	511.3	511.0	510.0	511.0	511.3	514.9	517.8	519.1	524.6	529.0
25°	490.2	488.4	486.6	488.4	486.6	488.4	490.2	493.4	494.8	498.8	503.0
27.5°	468.6	466.5	466.0	466.2	466.0	466.5	468.6	468.3	472.2	475.3	478.5
30°	455.4	451.9	452.2	451.9	452.2	451.9	455.4	455.4	457.6	460.4	463.4
32.5°	441.1	438.7	438.2	437.5	438.2	438.7	441.1	440.5	443.3	446.7	449.9
35°	420.0	420.0	418.2	418.2	418.2	420.0	420.0	421.0	424.0	424.0	427.5
37.5°	400.1	399.8	398.7	398.9	398.7	399.8	400.1	401.1	402.0	403.5	405.9
40°	385.2	384.9	383.8	381.6	383.8	384.9	385.2	386.7	387.4	389.2	390.6
42.5°	371.0	369.8	369.2	368.5	369.2	369.8	371.0	371.8	372.2	374.6	377.5
45°	348.4	348.4	347.7	347.3	347.7	348.4	348.4	348.4	348.7	351.6	353.1
47.5°	326.5	327.2	328.5	328.3	328.5	327.2	326.5	325.9	326.0	327.4	329.1
50°	313.3	313.7	314.7	315.1	314.7	313.7	313.3	311.9	311.1	311.1	312.3
52.5°	298.7	300.8	302.1	301.9	302.1	300.8	298.7	297.6	296.2	294.5	296.1
55°	278.2	280.7	283.2	283.6	283.2	280.7	278.2	274.9	273.5	270.7	271.7
57.5°	258.0	261.5	264.1	264.9	264.1	261.5	258.0	254.1	249.4	248.1	246.1
60°	244.2	248.8	252.0	253.5	252.0	248.8	244.2	240.6	234.5	230.5	229.1
62.5°	231.0	236.2	239.5	239.8	239.5	236.2	231.0	225.5	219.3	214.8	212.0
65°	209.4	214.8	217.7	219.8	217.7	214.8	209.4	203.4	196.6	190.5	187.3
67.5°	186.2	191.6	194.8	196.5	194.8	191.6	186.2	178.7	172.5	165.5	161.7
70°	169.4	174.7	179.0	180.5	179.0	174.7	169.4	160.4	155.0	148.5	145.3
72.5°	152.8	157.5	161.0	162.7	161.0	157.5	152.8	144.4	138.2	131.7	127.3
75°	123.9	130.4	133.6	135.3	133.6	130.4	123.9	119.2	112.1	105.3	101.7
77.5°	95.6	101.4	103.3	104.2	103.3	101.4	95.6	90.1	84.6	79.7	76.2
80°	76.6	80.2	82.8	83.0	82.8	80.2	76.6	72.3	68.1	63.3	60.1
82.5°	58.9	61.8	62.7	63.6	62.7	61.8	58.9	55.1	51.5	47.9	45.2
85°	32.2	33.6	34.0	33.6	34.0	33.6	32.2	29.7	27.9	26.1	25.1
87.5°	12.1	11.8	11.9	12.4	11.9	11.8	12.1	11.5	11.7	11.0	10.4
90°	7.4	7.4	7.6	7.6	7.6	7.4	7.4	7.4	6.7	6.3	6.0
92.5°	23.1	22.2	21.8	21.2	21.8	22.2	23.1	27.3	32.2	42.8	59.0
95°	96.2	86.2	83.6	78.3	83.6	86.2	96.2	119.9	147.9	188.9	239.5
97.5°	221.8	203.1	193.5	189.2	193.5	203.1	221.8	242.3	281.3	321.2	356.7
100°	301.4	277.5	265.1	259.9	265.1	277.5	301.4	324.4	359.1	393.4	409.7
102.5°	373.2	356.1	342.7	338.7	342.7	356.1	373.2	397.8	421.2	437.6	427.5
105°	463.0	452.0	445.4	441.4	445.4	452.0	463.0	473.7	477.3	462.7	417.1
107.5°	500.8	500.8	498.5	495.9	498.5	500.8	500.8	495.4	478.0	440.4	379.5
110°	505.3	511.6	514.0	514.0	514.0	511.6	505.3	490.3	462.0	415.1	351.8



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.8	503.7	509.4	511.9	509.4	503.7	492.8	470.9	437.5	390.0	329.9
115°	462.0	478.0	487.3	491.6	487.3	478.0	462.0	436.0	399.7	354.1	302.5
117.5°	427.8	444.4	453.6	456.3	453.6	444.4	427.8	401.9	368.5	329.2	284.7
120°	405.8	421.7	430.7	433.4	430.7	421.7	405.8	381.1	351.8	315.1	275.1
122.5°	387.1	401.7	410.8	413.1	410.8	401.7	387.1	365.0	337.6	305.0	268.0
125°	363.1	376.7	384.1	387.4	384.1	376.7	363.1	344.4	320.5	291.4	257.5
127.5°	345.0	357.0	363.9	365.4	363.9	357.0	345.0	328.0	305.6	278.5	246.9
130°	333.8	344.8	351.5	353.5	351.5	344.8	333.8	317.2	295.5	269.5	240.2
132.5°	322.1	333.0	339.1	341.4	339.1	333.0	322.1	305.4	284.6	261.0	233.5
135°	302.8	313.8	319.8	321.8	319.8	313.8	302.8	288.1	269.2	247.8	224.9
137.5°	283.0	293.0	298.6	300.8	298.6	293.0	283.0	269.9	253.8	236.1	217.5
140°	270.8	279.5	284.5	286.2	284.5	279.5	270.8	258.4	244.5	229.1	213.5
142.5°	259.1	266.5	271.2	272.6	271.2	266.5	259.1	248.6	236.5	223.3	210.1
145°	243.2	248.8	252.5	253.8	252.5	248.8	243.2	235.2	226.2	215.8	205.6
147.5°	230.7	235.3	237.3	238.0	237.3	235.3	230.7	224.4	217.6	209.6	201.2
150°	223.5	227.5	228.8	229.1	228.8	227.5	223.5	218.5	212.5	206.2	198.9
152.5°	217.4	220.6	221.9	222.3	221.9	220.6	217.4	213.2	208.5	202.7	196.2
155°	209.2	211.5	212.5	212.8	212.5	211.5	209.2	205.9	202.2	197.6	192.2
157.5°	201.7	203.6	204.5	204.4	204.5	203.6	201.7	199.1	196.2	192.6	188.2
160°	196.9	198.5	199.2	198.9	199.2	198.5	196.9	194.5	192.2	188.9	185.6
162.5°	192.4	193.7	193.9	193.8	193.9	193.7	192.4	190.6	188.5	185.7	182.6
165°	185.9	186.5	186.5	186.5	186.5	186.5	185.9	184.5	182.9	180.9	178.5
167.5°	179.6	180.2	179.9	179.8	179.9	180.2	179.6	179.0	177.8	176.3	174.7
170°	175.9	176.3	176.3	175.9	176.3	176.3	175.9	175.2	174.6	173.5	172.6
172.5°	172.4	173.1	172.5	172.1	172.5	173.1	172.4	172.3	171.9	171.2	170.1
175°	168.2	168.5	167.9	167.6	167.9	168.5	168.2	168.2	168.2	167.6	167.6
177.5°	165.8	166.0	165.2	165.2	165.2	166.0	165.8	166.0	166.0	166.0	165.8
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	806.6	810.0	814.4	817.5	823.2	825.8	829.0	831.5	836.1	840.4	845.6
5°	752.2	758.4	766.6	775.5	785.9	793.1	803.1	809.2	821.3	832.5	843.2
7.5°	702.9	710.5	722.1	733.6	747.2	759.5	772.0	785.9	801.4	819.8	835.0
10°	669.2	679.2	691.7	706.1	722.6	736.9	753.7	768.7	787.7	809.2	829.2
12.5°	642.2	650.8	664.9	678.5	696.2	713.7	731.0	751.0	773.1	796.9	822.1
15°	605.1	612.3	623.7	642.7	660.6	677.8	703.9	722.6	750.5	776.9	807.4
17.5°	573.3	582.3	591.9	608.2	626.7	648.2	671.6	694.9	721.8	755.4	789.8
20°	553.9	561.1	572.1	584.7	604.4	625.8	648.1	671.7	704.6	739.3	776.3
22.5°	532.7	540.5	553.0	566.7	583.2	603.8	628.3	654.2	688.6	722.7	762.8
25°	507.7	513.1	524.5	536.7	553.2	570.7	596.2	624.8	658.8	697.9	738.7
27.5°	484.2	488.9	499.4	509.9	524.8	545.6	568.4	597.3	629.3	668.9	714.2
30°	467.2	472.3	481.5	493.0	507.4	525.7	548.9	576.1	610.5	649.1	696.4
32.5°	452.6	457.1	464.1	475.6	489.6	507.3	528.9	556.7	591.0	630.3	676.7
35°	430.0	435.0	440.4	449.3	461.6	478.7	502.4	528.5	561.4	599.4	642.0
37.5°	407.6	412.9	417.7	425.7	436.9	452.0	472.5	499.7	529.5	566.1	607.0
40°	393.5	397.8	401.7	410.3	421.4	435.7	454.7	479.1	510.6	544.6	578.6
42.5°	379.5	383.4	386.8	394.3	404.5	418.3	436.4	460.1	489.4	521.1	551.1
45°	357.3	359.9	363.8	370.2	378.4	391.0	408.5	429.7	454.4	484.5	507.0
47.5°	333.4	337.3	340.5	346.2	353.0	365.2	382.1	400.1	422.5	444.9	460.7
50°	315.1	319.1	323.7	329.0	335.5	346.9	362.3	380.6	399.5	416.8	430.4
52.5°	297.9	301.5	306.5	311.6	319.4	329.2	342.3	358.5	377.2	389.6	400.9
55°	272.5	274.3	280.0	285.0	292.6	299.7	312.9	327.3	338.7	348.0	357.3
57.5°	246.5	248.9	252.2	256.7	264.2	272.6	281.8	294.5	301.2	306.0	313.3
60°	229.9	230.5	232.7	238.1	243.8	251.4	262.1	271.1	276.1	280.0	286.1
62.5°	211.5	211.7	215.3	219.2	223.5	231.6	240.3	247.5	251.8	253.6	259.5
65°	185.9	185.1	187.3	190.5	195.5	200.9	208.4	214.8	214.4	216.6	220.2
67.5°	159.6	158.8	158.8	161.9	166.0	170.8	176.0	179.6	179.7	182.6	184.4
70°	141.8	139.7	141.1	143.5	145.3	149.3	155.0	156.5	156.8	158.3	160.0
72.5°	123.5	122.7	123.9	125.0	126.2	129.2	134.1	135.0	135.1	135.9	138.8
75°	98.1	97.4	96.7	97.7	99.2	101.3	103.1	104.5	104.2	104.5	106.7
77.5°	73.5	71.5	71.2	71.7	72.1	73.4	75.3	75.1	75.5	75.4	77.9
80°	58.3	55.5	55.1	55.1	55.5	56.2	56.9	57.7	56.6	57.7	58.3
82.5°	42.9	41.2	41.1	40.8	40.9	41.0	41.5	41.8	41.7	42.1	42.6
85°	23.7	22.9	21.9	22.5	22.2	21.1	21.9	20.7	20.5	20.7	21.1
87.5°	9.1	9.3	8.7	8.6	8.2	8.4	7.7	7.3	6.9	7.0	7.8
90°	5.7	5.4	4.6	4.3	3.7	3.3	2.6	2.0	1.3	0.7	0.4
92.5°	86.9	107.4	109.1	76.0	45.5	27.3	17.6	11.9	7.7	4.9	4.1
95°	288.8	295.1	240.8	148.9	75.6	40.0	25.0	17.6	13.9	11.3	11.0
97.5°	365.4	315.2	215.1	118.9	65.1	41.6	30.8	24.2	20.5	18.7	18.3
100°	384.1	300.8	191.9	107.9	64.7	45.3	35.3	28.9	25.4	23.9	23.3
102.5°	372.9	275.5	174.3	103.4	67.0	49.9	40.2	34.3	30.3	29.3	28.9
105°	337.1	241.5	157.2	101.6	71.9	57.3	48.0	42.6	39.3	37.6	37.6
107.5°	300.6	218.1	150.1	104.6	79.3	65.1	56.7	51.2	48.4	46.8	46.2
110°	279.8	207.2	147.9	107.6	84.6	71.0	62.3	57.3	54.3	53.0	52.3



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	264.4	200.8	147.9	111.3	89.6	76.5	68.1	63.2	60.1	59.1	58.4
115°	247.5	193.9	148.9	116.9	97.6	85.3	76.9	71.9	69.0	68.0	67.3
117.5°	237.4	190.5	151.1	123.3	105.8	94.1	86.1	80.3	77.4	76.3	75.3
120°	231.9	188.9	153.3	127.6	111.6	99.9	91.6	86.0	82.9	81.6	80.6
122.5°	227.1	187.6	155.0	132.3	117.2	105.6	97.2	91.0	88.0	86.9	86.2
125°	220.6	185.9	158.3	138.9	124.6	113.6	104.9	98.6	95.6	94.0	93.3
127.5°	214.5	185.1	161.7	144.9	131.7	121.1	112.4	105.8	101.9	99.8	98.8
130°	210.6	184.5	163.9	148.9	136.2	125.9	117.3	110.3	105.9	103.3	102.3
132.5°	207.4	184.5	166.3	152.4	140.5	130.2	121.5	114.2	109.4	106.2	104.9
135°	203.5	184.5	169.6	157.2	146.2	135.9	127.0	119.9	114.6	110.6	109.2
137.5°	200.1	184.9	172.6	160.8	150.3	140.9	131.7	124.8	119.4	115.7	114.7
140°	198.5	185.2	173.9	163.2	153.3	143.5	134.6	128.3	122.9	118.9	117.9
142.5°	197.2	185.5	174.7	164.6	155.0	146.0	137.5	131.5	126.1	122.3	121.7
145°	195.2	185.2	175.5	166.5	158.3	149.6	141.9	135.9	131.2	127.9	127.2
147.5°	193.1	184.4	175.9	167.8	160.2	152.6	145.9	140.7	136.4	133.5	133.1
150°	191.5	183.5	175.9	168.5	161.6	154.2	148.5	143.9	139.6	137.2	136.6
152.5°	189.6	182.5	175.6	169.1	162.9	156.1	151.0	146.6	142.8	140.7	140.3
155°	186.5	180.6	174.8	169.6	164.2	158.5	153.9	150.5	147.2	145.2	145.2
157.5°	183.6	178.5	174.0	169.8	165.3	160.5	156.9	154.0	151.2	149.6	149.7
160°	181.3	177.2	173.2	169.8	165.9	161.6	158.5	155.9	153.5	152.2	152.6
162.5°	179.1	175.6	172.4	169.7	166.5	162.6	160.1	158.1	156.0	154.7	155.0
165°	175.9	173.2	171.3	169.2	166.5	163.9	161.9	160.5	158.9	157.9	158.5
167.5°	172.8	170.9	169.4	168.4	166.5	164.4	163.1	162.1	161.3	160.6	161.0
170°	170.9	169.6	168.5	167.9	166.5	164.9	163.9	163.2	162.6	162.2	162.6
172.5°	169.0	168.0	167.5	167.4	166.3	164.9	164.4	164.0	163.3	163.1	163.6
175°	166.5	166.3	166.3	166.5	165.9	164.9	164.9	164.9	164.6	164.2	164.9
177.5°	165.5	165.2	165.2	165.8	165.5	164.9	164.9	165.2	164.9	164.9	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	848.2	852.2	854.7	859.6	863.7	865.9	867.9	869.6	871.7	873.4	878.3
5°	853.6	862.9	870.8	883.0	894.1	902.7	911.9	920.2	927.0	936.7	944.1
7.5°	851.2	867.8	885.1	903.9	923.2	941.1	957.5	973.0	986.9	1003.8	1018.6
10°	848.9	871.5	893.7	919.1	945.3	967.4	988.3	1009.4	1024.7	1046.2	1064.5
12.5°	847.3	873.8	900.6	931.1	959.9	991.2	1018.9	1034.3	1057.7	1074.9	1096.6
15°	840.0	875.1	911.9	946.3	987.1	1016.2	1040.5	1070.5	1092.4	1114.3	1137.8
17.5°	827.0	866.8	908.0	953.1	992.2	1023.4	1054.7	1083.7	1109.8	1139.1	1168.6
20°	821.0	860.7	908.0	954.2	992.5	1025.1	1057.3	1089.2	1117.9	1155.5	1189.4
22.5°	808.4	856.5	900.0	945.0	984.5	1019.9	1056.5	1092.6	1130.7	1173.2	1215.8
25°	785.9	834.6	880.8	925.2	965.0	1009.4	1048.4	1096.7	1145.4	1201.6	1254.6
27.5°	762.6	809.2	851.5	894.4	940.8	991.0	1041.6	1096.5	1160.3	1231.1	1306.0
30°	743.7	787.7	828.9	872.9	921.2	977.8	1033.3	1098.5	1172.2	1252.1	1340.9
32.5°	721.6	762.2	802.3	848.9	901.5	961.2	1025.9	1097.3	1186.0	1276.8	1368.1
35°	683.9	717.9	759.0	808.8	868.3	936.7	1011.5	1096.0	1197.7	1301.8	1378.8
37.5°	639.1	670.8	714.2	768.7	831.0	904.5	993.3	1093.4	1201.5	1284.5	1309.4
40°	609.1	638.4	683.5	740.1	803.8	881.6	978.9	1084.9	1189.4	1242.5	1222.0
42.5°	576.9	607.8	651.8	707.8	776.3	860.9	960.8	1066.9	1154.5	1174.5	1104.0
45°	526.3	558.2	601.5	658.1	731.9	823.5	927.7	1024.0	1074.5	1038.3	929.2
47.5°	479.3	509.2	549.3	607.7	683.8	778.6	878.9	955.7	959.8	873.5	756.9
50°	447.2	474.8	515.2	573.6	649.1	745.1	835.7	896.2	869.0	771.3	659.2
52.5°	415.7	442.7	482.6	540.4	615.1	702.9	787.3	829.7	778.4	678.2	582.4
55°	370.2	393.9	432.9	486.3	557.1	638.8	710.4	725.0	658.5	559.6	481.9
57.5°	325.8	347.9	383.4	432.5	497.3	569.7	625.7	622.5	552.1	467.3	405.7
60°	295.8	317.3	348.7	396.7	455.8	518.1	566.1	554.6	484.8	411.8	359.9
62.5°	268.8	288.0	317.8	359.8	413.7	471.4	510.8	493.9	425.5	361.7	320.6
65°	229.1	245.2	270.7	306.5	351.3	398.9	429.3	407.5	349.1	299.4	266.4
67.5°	191.2	204.2	225.5	254.1	292.3	330.5	349.0	327.1	280.3	244.0	219.6
70°	167.2	178.7	195.1	220.6	253.8	286.1	300.0	280.3	240.3	209.1	191.5
72.5°	143.2	152.6	167.1	189.9	216.6	244.6	256.7	238.0	205.0	178.7	162.3
75°	110.7	117.1	127.1	142.9	164.0	186.2	193.0	176.5	155.4	135.7	125.0
77.5°	79.2	84.6	92.3	102.2	117.2	131.3	137.2	127.7	111.3	98.9	90.1
80°	60.9	63.7	70.2	78.4	90.2	99.2	103.1	97.0	85.6	76.3	69.5
82.5°	43.4	46.3	50.1	56.9	64.5	70.5	74.7	70.7	62.4	55.0	51.1
85°	21.1	22.9	25.1	27.9	33.6	37.2	36.9	34.4	31.1	28.3	26.1
87.5°	7.5	8.0	9.0	10.6	11.6	12.7	13.5	13.0	12.0	11.1	10.4
90°	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7	6.0
92.5°	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9	59.0
95°	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8	239.5
97.5°	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4	356.7
100°	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1	409.7
102.5°	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9	427.5
105°	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1	417.1
107.5°	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6	379.5
110°	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8	351.8



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4	329.9
115°	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5	302.5
117.5°	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4	284.7
120°	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9	275.1
122.5°	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1	268.0
125°	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6	257.5
127.5°	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5	246.9
130°	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6	240.2
132.5°	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4	233.5
135°	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5	224.9
137.5°	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1	217.5
140°	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5	213.5
142.5°	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2	210.1
145°	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2	205.6
147.5°	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1	201.2
150°	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5	198.9
152.5°	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6	196.2
155°	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5	192.2
157.5°	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6	188.2
160°	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3	185.6
162.5°	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1	182.6
165°	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9	178.5
167.5°	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8	174.7
170°	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9	172.6
172.5°	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0	170.1
175°	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5	167.6
177.5°	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5	165.8
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	882.2	884.5	889.4	887.7	889.9	891.1	892.3
5°	953.5	965.0	970.0	969.2	976.8	975.0	973.2
7.5°	1034.0	1046.0	1052.7	1061.1	1066.0	1066.3	1070.5
10°	1079.5	1095.2	1101.7	1110.7	1116.4	1119.6	1119.3
12.5°	1114.5	1126.8	1141.2	1145.7	1153.4	1157.4	1155.9
15°	1156.5	1176.2	1191.2	1198.7	1208.4	1211.3	1215.2
17.5°	1194.0	1220.4	1238.0	1261.3	1270.2	1275.5	1272.3
20°	1222.4	1257.1	1274.7	1302.6	1318.0	1326.3	1323.3
22.5°	1255.9	1293.5	1326.0	1350.1	1373.6	1384.7	1387.0
25°	1313.3	1364.9	1412.5	1444.4	1473.4	1480.2	1495.2
27.5°	1377.5	1438.3	1489.2	1522.7	1542.9	1550.5	1555.2
30°	1417.9	1478.4	1516.7	1538.1	1544.6	1543.9	1543.2
32.5°	1437.7	1475.6	1482.9	1476.9	1462.2	1449.6	1436.6
35°	1409.7	1381.4	1339.1	1284.7	1244.6	1204.1	1200.1
37.5°	1267.8	1177.3	1107.0	1028.5	983.2	955.2	935.8
40°	1134.3	1031.5	946.3	880.1	833.9	815.7	797.8
42.5°	989.4	891.2	815.7	760.3	725.7	705.4	691.2
45°	803.8	717.2	658.1	618.0	590.4	574.7	565.7
47.5°	658.6	594.6	544.4	515.5	496.4	484.2	484.2
50°	580.8	519.5	486.3	463.4	446.9	437.2	438.9
52.5°	511.7	466.0	437.5	418.3	406.1	400.2	400.0
55°	427.9	394.9	376.4	362.3	354.1	347.3	348.7
57.5°	366.0	338.2	325.7	314.1	308.4	305.7	301.8
60°	327.6	306.1	295.4	286.1	280.3	278.2	274.3
62.5°	293.5	276.6	266.2	258.5	253.4	252.7	249.6
65°	246.7	233.8	224.5	220.9	215.6	214.1	214.1
67.5°	203.4	194.2	186.9	183.6	181.3	181.6	179.8
70°	176.2	168.6	164.0	160.4	158.6	159.0	157.5
72.5°	154.1	145.7	141.7	139.5	137.1	138.1	137.5
75°	116.7	112.4	110.3	108.1	106.7	105.9	105.3
77.5°	85.7	81.9	80.3	79.1	79.3	77.6	78.9
80°	66.3	63.1	61.9	60.1	59.8	59.8	59.5
82.5°	48.4	46.7	45.9	44.4	43.7	44.3	43.4
85°	25.1	23.7	23.3	23.3	22.5	21.9	23.7
87.5°	10.5	9.3	9.5	9.2	9.2	9.0	8.4
90°	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	415.1	462.0	490.3	505.3	511.6	514.0	514.0



TEST NUMBER: P333162-830

CATALOG NUMBER: S125DIP-S610D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)